

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585101

Luminaire Tested: **HCC8S60D010MB-HM86080835-81WWWB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585101  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S60D010MB-HM86080835-81WWWB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5894.8 lumens  
Efficiency: N/A  
Efficacy: 105.3 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 56  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585101  
CATALOG NUMBER: HCC8S60D010MB-HM86080835-81WWWB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585101

CATALOG NUMBER: HCC8S60D010MB-HM86080835-81WWWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87					87			
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75					75			
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65					65			
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57					57			
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50					50			
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45					45			
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40					40			
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37					37			
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33					33			
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30					30			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	90378	90378	90378
5°	93692	90080	86990
10°	96338	89299	83431
15°	98486	87718	79743
20°	98640	84293	76509
25°	96748	79610	73802
30°	91758	73827	70565
35°	83378	67233	67391
40°	72904	60329	63517
45°	63181	53740	59186
50°	55327	47733	53926
55°	49240	42300	48794
60°	44423	37997	42881
65°	40102	33418	37365
70°	36037	28148	27778
75°	31740	22315	20838
80°	26601	18468	19978
85°	20592	16204	17655



TEST NUMBER: P585101  
 CATALOG NUMBER: HCC8S60D010MB-HM86080835-81WWWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	276.5	4.7
10°-20°	778.8	13.2
20°-30°	1113.0	18.9
30°-40°	1182.6	20.1
40°-50°	1018.2	17.3
50°-60°	761.2	12.9
60°-70°	485.6	8.2
70°-80°	221.0	3.7
80°-90°	58.0	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2168.3	36.8
0°-40°	3350.9	56.8
0°-60°	5130.3	87.0
0°-90°	5894.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5894.8	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2931	2931	2931	2931	2931	
5°	3027	2985	2910	2835	2810	290
15°	3085	2981	2748	2560	2498	869
25°	2844	2664	2340	2198	2169	1302
35°	2215	2061	1786	1740	1790	1379
45°	1449	1370	1232	1266	1357	1126
55°	916	841	787	854	908	824
65°	550	487	458	479	512	548
75°	266	229	187	171	175	283
85°	58	50	46	50	50	70
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585101

CATALOG NUMBER: HCC8S60D010MB-HM86080835-81WWWB

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2930.9	2930.9	2930.9	2930.9	2930.9	2930.9	2930.9	2930.9	2930.9	2930.9	2930.9
2.5°	2985.1	2976.7	2981.0	2976.7	2981.0	2981.0	2972.5	2972.5	2972.5	2972.5	2960.1
5°	3026.8	3022.5	3022.5	3018.3	3014.2	3018.3	3014.2	3010.0	3001.7	2997.6	2985.1
7.5°	3051.7	3051.7	3051.7	3051.7	3047.5	3043.4	3039.2	3030.9	3022.5	3014.2	3005.9
10°	3076.7	3080.8	3076.7	3072.5	3068.4	3060.0	3055.8	3047.5	3035.1	3022.5	3014.2
12.5°	3089.2	3089.2	3085.0	3085.0	3076.7	3072.5	3060.0	3047.5	3035.1	3022.5	3001.7
15°	3085.0	3085.0	3080.8	3076.7	3064.1	3060.0	3051.7	3039.2	3018.3	3001.7	2981.0
17.5°	3060.0	3055.8	3047.5	3047.5	3030.9	3026.8	3018.3	3001.7	2981.0	2955.9	2930.9
20°	3005.9	3005.9	3001.7	2997.6	2981.0	2968.4	2960.1	2939.3	2922.6	2893.4	2868.5
22.5°	2930.9	2939.3	2930.9	2922.6	2901.8	2897.7	2885.1	2860.2	2835.2	2801.8	2772.8
25°	2843.5	2839.3	2835.2	2826.9	2810.3	2801.8	2785.2	2760.2	2735.3	2697.8	2664.5
27.5°	2731.1	2714.4	2714.4	2697.8	2685.3	2672.8	2664.5	2639.6	2606.2	2577.0	2535.4
30°	2577.0	2581.2	2560.4	2556.3	2535.4	2527.1	2510.5	2485.5	2456.3	2423.1	2389.7
32.5°	2410.5	2398.0	2398.0	2381.4	2364.7	2352.2	2348.1	2318.9	2294.0	2260.7	2227.3
35°	2214.9	2214.9	2202.4	2198.3	2181.5	2173.2	2160.8	2144.1	2115.0	2085.8	2060.8
37.5°	2023.3	2015.0	2010.8	2002.5	1990.1	1977.5	1977.5	1948.4	1944.3	1911.0	1877.6
40°	1811.1	1819.4	1811.1	1798.5	1794.3	1786.0	1781.9	1765.3	1752.7	1723.6	1702.8
42.5°	1632.1	1623.6	1623.6	1619.5	1602.9	1602.9	1594.6	1586.2	1565.4	1557.1	1532.1
45°	1448.8	1457.1	1444.6	1448.8	1432.2	1432.2	1432.2	1415.6	1398.8	1386.4	1369.7
47.5°	1290.7	1294.8	1294.8	1282.2	1278.1	1278.1	1269.8	1261.5	1249.0	1232.3	1219.8
50°	1153.3	1157.4	1149.0	1144.9	1136.6	1132.4	1132.4	1115.8	1107.4	1090.8	1082.5
52.5°	1028.4	1028.4	1024.2	1024.2	1011.6	1011.6	1003.3	990.9	982.6	974.2	953.4
55°	915.9	915.9	911.8	907.6	907.6	895.2	890.9	878.4	870.1	853.5	840.9
57.5°	807.7	811.9	807.7	803.5	799.3	795.2	786.8	774.4	766.1	753.5	745.2
60°	720.3	720.3	716.0	711.9	703.6	699.4	695.3	687.0	674.4	666.1	653.6
62.5°	637.0	632.9	628.6	624.5	616.1	616.1	607.8	599.5	587.0	578.7	570.4
65°	549.6	549.6	545.4	545.4	541.2	532.9	528.7	524.6	508.0	503.8	487.1
67.5°	470.5	474.6	466.3	466.3	458.0	458.0	453.7	441.3	437.1	428.8	420.5
70°	399.7	399.7	399.7	395.5	387.2	383.0	378.9	370.6	366.3	358.0	349.7
72.5°	328.9	328.9	324.7	324.7	320.5	316.4	312.2	303.9	303.9	295.6	287.3
75°	266.4	266.4	262.3	258.1	254.0	254.0	249.8	245.7	237.3	233.1	228.9
77.5°	204.0	204.0	204.0	199.9	195.6	195.6	195.6	187.3	179.0	179.0	174.9
80°	149.8	149.8	145.7	145.7	141.5	141.5	141.5	137.4	133.2	129.1	124.9
82.5°	99.9	99.9	99.9	99.9	95.7	95.7	95.7	91.6	87.4	87.4	87.4
85°	58.2	58.2	58.2	58.2	54.1	54.1	54.1	54.1	54.1	49.9	49.9
87.5°	25.0	20.8	25.0	20.8	25.0	20.8	25.0	20.8	20.8	20.8	20.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585101

CATALOG NUMBER: HCC8S60D010MB-HM86080835-81WWWB

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2930.9	2930.9	2930.9	2930.9	2930.9	2930.9	2930.9	2930.9	2930.9	2930.9	2930.9
2.5°	2964.2	2960.1	2955.9	2951.8	2951.8	2947.6	2939.3	2935.1	2930.9	2926.8	2926.8
5°	2981.0	2976.7	2968.4	2960.1	2955.9	2947.6	2939.3	2930.9	2922.6	2910.1	2906.0
7.5°	2993.4	2981.0	2972.5	2955.9	2951.8	2943.5	2930.9	2918.4	2901.8	2885.1	2872.7
10°	2993.4	2976.7	2964.2	2943.5	2935.1	2926.8	2910.1	2889.3	2868.5	2851.9	2831.0
12.5°	2985.1	2964.2	2943.5	2922.6	2910.1	2897.7	2872.7	2851.9	2826.9	2801.8	2785.2
15°	2955.9	2930.9	2906.0	2881.0	2868.5	2851.9	2826.9	2797.7	2772.8	2747.7	2718.6
17.5°	2901.8	2876.8	2847.6	2818.6	2801.8	2789.4	2751.9	2731.1	2693.7	2668.6	2643.7
20°	2831.0	2801.8	2764.5	2735.3	2714.4	2702.0	2672.8	2635.4	2606.2	2568.7	2543.7
22.5°	2739.4	2702.0	2664.5	2635.4	2614.5	2597.9	2560.4	2522.9	2497.9	2464.7	2435.5
25°	2631.1	2593.8	2556.3	2514.6	2493.8	2477.2	2443.8	2410.5	2377.3	2339.8	2314.8
27.5°	2502.1	2460.5	2427.2	2389.7	2368.9	2343.9	2306.5	2273.1	2239.8	2214.9	2181.5
30°	2360.5	2314.8	2281.4	2244.1	2223.2	2202.4	2164.9	2131.6	2102.4	2073.4	2056.6
32.5°	2189.8	2156.6	2123.3	2085.8	2069.2	2056.6	2019.1	1985.9	1952.6	1927.6	1915.1
35°	2027.6	1990.1	1960.9	1927.6	1906.8	1894.3	1861.0	1831.8	1815.2	1786.0	1769.4
37.5°	1856.9	1827.7	1794.3	1761.0	1748.6	1736.1	1711.1	1682.0	1657.0	1636.2	1627.8
40°	1677.9	1652.8	1623.6	1602.9	1590.4	1577.9	1557.1	1536.2	1519.6	1498.7	1490.4
42.5°	1507.1	1490.4	1465.5	1440.5	1428.0	1423.9	1398.8	1382.2	1373.9	1365.5	1357.2
45°	1353.1	1328.1	1311.4	1294.8	1282.2	1273.9	1261.5	1249.0	1240.7	1232.3	1224.0
47.5°	1203.2	1182.4	1165.7	1153.3	1140.7	1136.6	1128.3	1115.8	1107.4	1107.4	1107.4
50°	1065.7	1049.1	1032.5	1024.2	1020.0	1011.6	1003.3	999.2	995.0	995.0	995.0
52.5°	945.1	928.4	915.9	907.6	907.6	899.3	890.9	886.7	886.7	886.7	886.7
55°	832.6	820.2	811.9	803.5	795.2	791.0	791.0	791.0	786.8	786.8	791.0
57.5°	732.8	724.5	711.9	703.6	699.4	699.4	695.3	691.1	695.3	699.4	703.6
60°	641.2	632.9	628.6	616.1	616.1	616.1	612.0	612.0	612.0	616.1	620.3
62.5°	557.9	553.7	545.4	541.2	537.0	537.0	532.9	532.9	532.9	532.9	537.0
65°	482.9	474.6	466.3	466.3	466.3	462.2	462.2	453.7	458.0	458.0	453.7
67.5°	412.1	403.8	399.7	395.5	391.3	391.3	387.2	383.0	378.9	378.9	378.9
70°	345.6	337.3	337.3	328.9	328.9	324.7	320.5	320.5	316.4	312.2	308.1
72.5°	278.9	274.7	270.6	266.4	266.4	266.4	262.3	258.1	254.0	249.8	241.5
75°	220.6	220.6	212.3	208.2	208.2	204.0	199.9	195.6	191.5	187.3	183.2
77.5°	170.7	166.6	158.2	154.1	154.1	154.1	149.8	145.7	141.5	137.4	133.2
80°	124.9	120.8	116.6	112.5	112.5	112.5	108.2	108.2	104.0	104.0	104.0
82.5°	83.3	83.3	79.1	79.1	79.1	79.1	75.0	75.0	75.0	75.0	75.0
85°	49.9	49.9	45.8	45.8	45.8	45.8	45.8	45.8	45.8	45.8	45.8
87.5°	20.8	20.8	20.8	20.8	20.8	20.8	20.8	20.8	20.8	20.8	20.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585101

CATALOG NUMBER: HCC8S60D010MB-HM86080835-81WWWB

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2930.9	2930.9	2930.9	2930.9	2930.9	2930.9	2930.9	2930.9	2930.9	2930.9	2930.9
2.5°	2918.4	2918.4	2910.1	2906.0	2901.8	2906.0	2897.7	2893.4	2889.3	2889.3	2885.1
5°	2893.4	2889.3	2872.7	2868.5	2864.4	2860.2	2851.9	2843.5	2835.2	2831.0	2826.9
7.5°	2860.2	2847.6	2831.0	2826.9	2822.7	2810.3	2797.7	2789.4	2776.9	2772.8	2764.5
10°	2814.4	2797.7	2785.2	2772.8	2764.5	2751.9	2739.4	2727.0	2710.3	2706.1	2693.7
12.5°	2760.2	2739.4	2714.4	2710.3	2697.8	2681.2	2664.5	2652.0	2639.6	2631.1	2618.7
15°	2693.7	2672.8	2647.9	2635.4	2622.8	2610.4	2589.6	2572.9	2560.4	2548.0	2535.4
17.5°	2614.5	2589.6	2568.7	2556.3	2548.0	2527.1	2510.5	2489.6	2477.2	2464.7	2452.1
20°	2518.8	2497.9	2468.9	2456.3	2452.1	2435.5	2414.6	2406.3	2389.7	2377.3	2368.9
22.5°	2410.5	2389.7	2364.7	2356.4	2339.8	2331.5	2310.6	2302.3	2294.0	2281.4	2277.3
25°	2289.8	2269.0	2248.2	2244.1	2231.5	2223.2	2210.7	2198.3	2198.3	2185.7	2185.7
27.5°	2164.9	2144.1	2127.4	2119.1	2115.0	2106.6	2094.1	2090.0	2085.8	2081.7	2081.7
30°	2031.7	2006.7	1998.4	1994.2	1990.1	1981.8	1977.5	1969.2	1973.4	1977.5	1973.4
32.5°	1890.1	1881.8	1865.2	1856.9	1861.0	1856.9	1848.4	1856.9	1852.7	1861.0	1865.2
35°	1752.7	1744.4	1736.1	1736.1	1727.8	1727.8	1727.8	1731.9	1740.2	1744.4	1752.7
37.5°	1619.5	1607.0	1602.9	1598.7	1602.9	1602.9	1602.9	1611.2	1619.5	1627.8	1640.4
40°	1478.0	1469.7	1469.7	1469.7	1469.7	1482.1	1478.0	1486.3	1494.6	1507.1	1519.6
42.5°	1344.7	1344.7	1348.9	1348.9	1348.9	1348.9	1357.2	1369.7	1382.2	1394.7	1407.1
45°	1219.8	1219.8	1219.8	1228.1	1228.1	1232.3	1249.0	1257.3	1265.6	1278.1	1290.7
47.5°	1103.2	1103.2	1107.4	1111.6	1115.8	1124.1	1132.4	1144.9	1157.4	1165.7	1178.2
50°	995.0	999.2	1007.5	1015.8	1015.8	1020.0	1032.5	1040.8	1049.1	1061.6	1065.7
52.5°	890.9	899.3	907.6	911.8	915.9	924.2	928.4	940.9	945.1	957.6	961.7
55°	795.2	799.3	811.9	816.0	816.0	824.3	832.6	840.9	853.5	853.5	861.8
57.5°	707.7	711.9	720.3	724.5	720.3	732.8	736.9	745.2	749.4	757.7	761.9
60°	620.3	628.6	632.9	632.9	637.0	641.2	649.5	649.5	657.8	666.1	666.1
62.5°	537.0	541.2	545.4	549.6	553.7	549.6	562.1	562.1	570.4	574.5	582.8
65°	458.0	462.2	462.2	466.3	466.3	470.5	470.5	474.6	478.8	487.1	491.2
67.5°	378.9	378.9	378.9	383.0	378.9	383.0	383.0	387.2	387.2	395.5	399.7
70°	308.1	303.9	299.8	299.8	299.8	299.8	295.6	299.8	299.8	303.9	303.9
72.5°	237.3	233.1	228.9	224.8	224.8	220.6	216.5	220.6	220.6	224.8	224.8
75°	179.0	170.7	170.7	170.7	166.6	166.6	166.6	170.7	170.7	170.7	174.9
77.5°	133.2	133.2	129.1	129.1	129.1	133.2	133.2	137.4	137.4	137.4	137.4
80°	99.9	104.0	104.0	104.0	104.0	108.2	108.2	108.2	108.2	112.5	112.5
82.5°	75.0	75.0	75.0	75.0	79.1	79.1	79.1	79.1	79.1	79.1	79.1
85°	45.8	49.9	49.9	45.8	49.9	49.9	49.9	49.9	49.9	49.9	49.9
87.5°	20.8	20.8	20.8	20.8	20.8	20.8	20.8	20.8	20.8	20.8	20.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585101

CATALOG NUMBER: HCC8S60D010MB-HM86080835-81WWWB

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2930.9	2930.9	2930.9	2930.9	2930.9	2930.9	2930.9	2930.9
2.5°	2881.0	2881.0	2881.0	2881.0	2876.8	2876.8	2876.8	2872.7
5°	2818.6	2818.6	2818.6	2810.3	2814.4	2814.4	2806.0	2810.3
7.5°	2756.0	2751.9	2747.7	2747.7	2743.6	2739.4	2735.3	2739.4
10°	2685.3	2672.8	2672.8	2668.6	2668.6	2660.3	2660.3	2664.5
12.5°	2606.2	2597.9	2597.9	2593.8	2589.6	2585.3	2581.2	2581.2
15°	2527.1	2518.8	2514.6	2510.5	2506.3	2497.9	2502.1	2497.9
17.5°	2448.0	2435.5	2435.5	2431.4	2427.2	2418.9	2418.9	2414.6
20°	2356.4	2352.2	2343.9	2348.1	2343.9	2335.6	2331.5	2331.5
22.5°	2264.8	2264.8	2260.7	2260.7	2256.5	2252.4	2248.2	2248.2
25°	2177.4	2173.2	2177.4	2177.4	2164.9	2164.9	2164.9	2169.1
27.5°	2077.5	2081.7	2077.5	2077.5	2077.5	2077.5	2081.7	2077.5
30°	1977.5	1977.5	1977.5	1981.8	1990.1	1985.9	1985.9	1981.8
32.5°	1869.3	1873.5	1873.5	1877.6	1881.8	1890.1	1890.1	1894.3
35°	1761.0	1769.4	1773.6	1769.4	1781.9	1781.9	1790.2	1790.2
37.5°	1648.7	1652.8	1661.1	1665.3	1673.6	1677.9	1682.0	1682.0
40°	1527.9	1544.5	1548.8	1552.9	1565.4	1565.4	1569.5	1577.9
42.5°	1415.6	1432.2	1436.3	1440.5	1448.8	1461.4	1457.1	1465.5
45°	1307.3	1319.7	1323.9	1328.1	1340.6	1344.7	1344.7	1357.2
47.5°	1190.7	1199.1	1203.2	1211.5	1219.8	1228.1	1236.4	1232.3
50°	1074.2	1086.6	1094.9	1099.1	1111.6	1115.8	1120.0	1124.1
52.5°	970.0	978.3	982.6	986.7	999.2	1003.3	1007.5	1015.8
55°	870.1	874.3	882.6	878.4	890.9	895.2	899.3	907.6
57.5°	770.2	774.4	778.5	778.5	786.8	795.2	799.3	803.5
60°	674.4	682.8	687.0	687.0	687.0	695.3	695.3	695.3
62.5°	587.0	587.0	591.2	591.2	599.5	599.5	599.5	599.5
65°	495.4	499.5	503.8	503.8	512.1	508.0	516.3	512.1
67.5°	399.7	399.7	408.0	408.0	403.8	408.0	408.0	408.0
70°	303.9	303.9	308.1	308.1	308.1	308.1	308.1	308.1
72.5°	224.8	224.8	224.8	228.9	224.8	224.8	228.9	224.8
75°	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9
77.5°	137.4	137.4	141.5	141.5	141.5	141.5	141.5	141.5
80°	112.5	112.5	112.5	112.5	116.6	112.5	112.5	112.5
82.5°	83.3	79.1	83.3	79.1	83.3	83.3	83.3	83.3
85°	49.9	49.9	49.9	49.9	49.9	49.9	49.9	49.9
87.5°	20.8	20.8	20.8	20.8	20.8	20.8	20.8	20.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)