

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585109

Luminaire Tested: **HCC8S60D010SL-HM86080840-81RWWC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585109  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S60D010SL-HM86080840-81RWWC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6208.2 lumens  
Efficiency: N/A  
Efficacy: 110.9 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 56  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585109  
CATALOG NUMBER: HCC8S60D010SL-HM86080840-81RWWC

### Luminous Intensity Polar Plot





TEST NUMBER: P585109

CATALOG NUMBER: HCC8S60D010SL-HM86080840-81RWWC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	84	82	79	77					77			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67					67			
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59					59			
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52					52			
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47					47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42					42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38					38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35					35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32					32			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	100727	100727	100727
5°	102059	100304	99356
10°	103101	99278	97775
15°	104143	97180	95230
20°	103614	93596	91450
25°	101198	87993	86806
30°	96120	81682	81368
35°	87508	74532	75194
40°	76720	66709	69168
45°	66181	59339	63521
50°	57956	52094	57534
55°	51348	44783	50643
60°	46267	37657	41962
65°	41685	30229	32141
70°	36560	22017	17698
75°	31180	11438	4670
80°	24009	3090	781
85°	15426	0	0



TEST NUMBER: P585109  
 CATALOG NUMBER: HCC8S60D010SL-HM86080840-81RWWC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	308.2	5.0
10°-20°	866.4	14.0
20°-30°	1229.7	19.8
30°-40°	1294.4	20.9
40°-50°	1101.2	17.7
50°-60°	795.8	12.8
60°-70°	452.6	7.3
70°-80°	142.6	2.3
80°-90°	17.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2404.3	38.7
0°-40°	3698.8	59.6
0°-60°	5595.7	90.1
0°-90°	6208.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6208.2	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	3266	3266	3266	3266	3266	
5°	3297	3280	3240	3219	3210	315
15°	3262	3179	3044	2987	2983	919
25°	2974	2826	2586	2543	2551	1362
35°	2325	2189	1980	1967	1998	1446
45°	1518	1461	1361	1396	1457	1180
55°	955	885	833	881	942	861
65°	571	493	414	410	440	567
75°	262	201	96	44	39	282
85°	44	26	0	0	0	56
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585109

CATALOG NUMBER: HCC8S60D010SL-HM86080840-81RWWC

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	3266.5	3266.5	3266.5	3266.5	3266.5	3266.5	3266.5	3266.5	3266.5	3266.5	3266.5
2.5°	3284.0	3288.3	3279.6	3279.6	3288.3	3279.6	3284.0	3284.0	3279.6	3279.6	3275.2
5°	3297.1	3292.7	3292.7	3292.7	3297.1	3288.3	3284.0	3288.3	3279.6	3279.6	3279.6
7.5°	3301.4	3301.4	3297.1	3292.7	3292.7	3292.7	3288.3	3284.0	3279.6	3270.9	3266.5
10°	3292.7	3292.7	3297.1	3288.3	3288.3	3279.6	3279.6	3270.9	3270.9	3262.2	3249.1
12.5°	3284.0	3279.6	3279.6	3270.9	3270.9	3262.2	3262.2	3249.1	3244.7	3231.6	3218.6
15°	3262.2	3257.8	3249.1	3244.7	3240.4	3236.0	3227.3	3222.9	3209.8	3192.4	3179.3
17.5°	3218.6	3214.2	3209.8	3201.1	3192.4	3188.0	3183.6	3170.6	3153.2	3140.0	3118.2
20°	3157.5	3153.2	3153.2	3140.0	3135.7	3122.6	3118.2	3100.8	3087.8	3061.6	3044.1
22.5°	3074.6	3079.0	3070.2	3061.6	3052.8	3039.8	3031.0	3013.6	2991.8	2965.6	2943.8
25°	2974.3	2978.7	2970.0	2961.2	2948.2	2939.4	2930.7	2904.5	2882.7	2852.2	2826.1
27.5°	2847.9	2847.9	2847.9	2839.1	2817.3	2812.9	2804.3	2778.1	2747.5	2721.3	2695.3
30°	2699.5	2695.3	2695.3	2682.1	2673.4	2655.9	2642.9	2621.1	2599.3	2568.7	2538.2
32.5°	2520.8	2525.1	2512.0	2503.3	2490.2	2490.2	2472.8	2455.4	2429.2	2398.6	2368.2
35°	2324.6	2328.8	2320.2	2315.8	2294.0	2289.6	2285.2	2263.4	2246.0	2224.2	2189.3
37.5°	2123.9	2119.5	2115.2	2115.2	2102.1	2093.4	2084.7	2071.5	2045.4	2027.9	2010.5
40°	1905.9	1905.9	1905.9	1901.5	1897.1	1888.3	1884.1	1875.3	1857.9	1840.4	1827.3
42.5°	1709.6	1709.6	1705.2	1700.9	1692.2	1696.5	1687.8	1679.0	1661.6	1648.6	1639.8
45°	1517.6	1517.6	1517.6	1522.0	1513.4	1500.2	1500.2	1491.6	1482.8	1474.0	1461.0
47.5°	1347.6	1360.7	1352.0	1347.6	1352.0	1334.5	1334.5	1325.8	1317.1	1308.3	1290.9
50°	1208.1	1208.1	1208.1	1199.3	1194.9	1194.9	1181.9	1173.1	1168.7	1160.1	1142.7
52.5°	1081.5	1072.9	1072.9	1068.5	1064.1	1055.4	1055.4	1046.7	1029.3	1020.5	1007.4
55°	955.1	955.1	950.7	946.4	942.0	937.6	933.3	920.2	911.5	898.4	885.3
57.5°	841.8	850.4	846.0	837.4	828.6	828.6	820.0	811.2	798.2	785.0	772.0
60°	750.2	745.8	745.8	741.4	732.6	728.4	724.0	710.8	697.8	684.7	671.6
62.5°	654.2	654.2	654.2	645.4	636.7	632.4	628.0	619.3	601.8	588.8	580.0
65°	571.3	567.0	562.6	558.2	553.9	545.1	540.8	532.1	519.0	505.9	492.8
67.5°	488.5	484.1	484.1	479.7	466.7	462.3	462.3	449.2	436.1	423.1	409.9
70°	405.5	405.5	405.5	396.9	392.5	388.1	383.7	375.1	361.9	348.9	335.8
72.5°	335.8	331.5	331.5	327.1	314.0	309.7	305.3	296.5	283.5	274.7	266.1
75°	261.7	261.7	257.3	252.9	248.6	244.2	239.9	231.1	218.1	205.0	200.6
77.5°	200.6	196.3	196.3	191.9	183.2	178.8	178.8	170.1	157.0	148.3	139.6
80°	135.2	139.6	135.2	130.8	126.5	122.1	117.8	113.4	104.6	96.0	87.2
82.5°	82.8	87.2	82.8	82.8	78.5	74.2	74.2	65.4	61.0	56.7	52.4
85°	43.6	43.6	43.6	43.6	39.2	39.2	39.2	34.8	30.6	26.2	26.2
87.5°	13.0	17.4	13.0	13.0	13.0	13.0	13.0	13.0	8.8	8.8	8.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585109

CATALOG NUMBER: HCC8S60D010SL-HM86080840-81RWWC

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	3266.5	3266.5	3266.5	3266.5	3266.5	3266.5	3266.5	3266.5	3266.5	3266.5	3266.5
2.5°	3279.6	3275.2	3270.9	3270.9	3270.9	3270.9	3270.9	3266.5	3262.2	3262.2	3262.2
5°	3270.9	3270.9	3270.9	3266.5	3262.2	3262.2	3253.4	3249.1	3244.7	3240.4	3236.0
7.5°	3262.2	3253.4	3249.1	3244.7	3240.4	3240.4	3231.6	3222.9	3222.9	3214.2	3205.4
10°	3236.0	3231.6	3222.9	3214.2	3209.8	3205.4	3196.8	3183.6	3179.3	3170.6	3161.8
12.5°	3205.4	3196.8	3188.0	3170.6	3166.2	3161.8	3144.4	3131.4	3122.6	3118.2	3096.4
15°	3166.2	3148.8	3135.7	3113.8	3109.6	3100.8	3087.8	3074.6	3057.2	3044.1	3035.4
17.5°	3096.4	3079.0	3057.2	3035.4	3026.6	3026.6	3004.8	2987.4	2965.6	2956.9	2939.4
20°	3013.6	2991.8	2974.3	2948.2	2935.1	2922.0	2908.9	2882.7	2865.3	2852.2	2830.4
22.5°	2917.6	2887.1	2865.3	2839.1	2817.3	2804.3	2782.5	2760.7	2738.9	2725.7	2708.3
25°	2795.5	2769.3	2734.5	2708.3	2695.3	2677.7	2651.6	2629.8	2608.0	2586.2	2577.5
27.5°	2660.3	2625.5	2594.9	2564.4	2551.3	2538.2	2507.7	2481.5	2464.1	2442.2	2433.6
30°	2512.0	2477.2	2442.2	2416.1	2403.0	2381.2	2363.8	2333.2	2311.4	2294.0	2272.2
32.5°	2342.0	2315.8	2285.2	2246.0	2237.2	2219.8	2193.7	2180.6	2154.4	2141.3	2123.9
35°	2158.8	2141.3	2110.8	2080.3	2067.2	2058.5	2036.7	2010.5	1993.1	1979.9	1971.3
37.5°	1984.3	1962.5	1932.1	1910.1	1901.5	1888.3	1862.3	1849.1	1831.7	1822.9	1805.5
40°	1796.8	1775.0	1753.2	1740.1	1727.0	1718.3	1700.9	1687.8	1670.4	1657.2	1652.9
42.5°	1613.6	1600.6	1583.2	1565.6	1561.4	1548.2	1539.4	1526.4	1513.4	1509.0	1495.8
45°	1447.9	1434.8	1417.4	1400.0	1395.6	1386.8	1382.5	1369.4	1360.7	1360.7	1360.7
47.5°	1282.2	1269.1	1251.7	1242.9	1247.3	1229.9	1229.9	1225.5	1216.7	1216.7	1221.1
50°	1133.9	1116.5	1112.1	1103.3	1094.7	1085.9	1090.3	1077.2	1077.2	1085.9	1081.5
52.5°	994.3	976.9	972.5	963.8	959.5	959.5	955.1	955.1	950.7	955.1	955.1
55°	867.8	854.8	846.0	837.4	833.0	833.0	833.0	828.6	824.2	833.0	837.4
57.5°	754.4	750.2	741.4	728.4	724.0	719.6	715.2	715.2	715.2	715.2	719.6
60°	654.2	645.4	636.7	623.6	623.6	619.3	614.9	610.6	610.6	610.6	610.6
62.5°	567.0	553.9	540.8	532.1	527.7	523.3	519.0	510.3	510.3	510.3	510.3
65°	479.7	466.7	457.9	449.2	440.5	440.5	431.7	427.5	418.7	414.3	405.5
67.5°	396.9	388.1	379.5	366.3	361.9	357.7	348.9	344.5	331.5	327.1	322.7
70°	322.7	309.7	300.9	292.2	287.9	279.1	270.4	261.7	252.9	244.2	235.5
72.5°	252.9	239.9	231.1	222.4	213.7	213.7	200.6	191.9	178.8	170.1	157.0
75°	187.5	174.4	165.7	152.6	148.3	143.9	130.8	122.1	109.0	96.0	87.2
77.5°	126.5	117.8	109.0	96.0	87.2	87.2	74.2	65.4	56.7	43.6	39.2
80°	78.5	69.8	61.0	52.4	52.4	43.6	39.2	30.6	21.8	17.4	13.0
82.5°	43.6	39.2	34.8	26.2	26.2	21.8	17.4	13.0	8.8	4.4	4.4
85°	21.8	17.4	13.0	13.0	8.8	8.8	8.8	4.4	4.4	0.0	0.0
87.5°	8.8	4.4	4.4	4.4	4.4	4.4	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585109

CATALOG NUMBER: HCC8S60D010SL-HM86080840-81RWWC

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	3266.5	3266.5	3266.5	3266.5	3266.5	3266.5	3266.5	3266.5	3266.5	3266.5	3266.5
2.5°	3257.8	3257.8	3253.4	3253.4	3253.4	3249.1	3253.4	3249.1	3249.1	3249.1	3253.4
5°	3240.4	3231.6	3231.6	3227.3	3227.3	3222.9	3227.3	3222.9	3218.6	3214.2	3218.6
7.5°	3205.4	3196.8	3192.4	3188.0	3188.0	3188.0	3183.6	3179.3	3183.6	3170.6	3179.3
10°	3157.5	3153.2	3144.4	3140.0	3135.7	3140.0	3135.7	3127.0	3127.0	3127.0	3122.6
12.5°	3096.4	3087.8	3083.4	3079.0	3070.2	3070.2	3074.6	3066.0	3066.0	3057.2	3057.2
15°	3022.3	3013.6	3004.8	3004.8	2996.2	2996.2	2991.8	2991.8	2987.4	2983.0	2983.0
17.5°	2930.7	2917.6	2908.9	2913.3	2908.9	2904.5	2904.5	2895.8	2891.5	2895.8	2895.8
20°	2821.7	2812.9	2804.3	2808.6	2799.9	2795.5	2799.9	2786.8	2791.1	2791.1	2791.1
22.5°	2699.5	2695.3	2682.1	2682.1	2673.4	2669.1	2673.4	2673.4	2677.7	2673.4	2673.4
25°	2564.4	2555.7	2546.9	2546.9	2542.6	2538.2	2542.6	2546.9	2542.6	2546.9	2546.9
27.5°	2420.4	2407.4	2407.4	2398.6	2398.6	2403.0	2398.6	2403.0	2407.4	2407.4	2416.1
30°	2263.4	2259.0	2254.8	2250.4	2250.4	2254.8	2254.8	2254.8	2259.0	2267.8	2267.8
32.5°	2115.2	2106.5	2097.7	2097.7	2106.5	2102.1	2106.5	2106.5	2115.2	2115.2	2123.9
35°	1953.9	1953.9	1945.1	1949.5	1949.5	1949.5	1949.5	1958.1	1966.9	1971.3	1979.9
37.5°	1805.5	1792.5	1796.8	1796.8	1801.1	1796.8	1809.9	1809.9	1818.6	1818.6	1827.3
40°	1644.2	1644.2	1648.6	1644.2	1648.6	1648.6	1657.2	1666.0	1670.4	1679.0	1683.4
42.5°	1491.6	1500.2	1491.6	1495.8	1500.2	1504.6	1509.0	1513.4	1530.8	1539.4	1552.6
45°	1352.0	1356.3	1360.7	1365.0	1360.7	1369.4	1373.8	1382.5	1395.6	1400.0	1404.3
47.5°	1216.7	1221.1	1225.5	1229.9	1229.9	1238.5	1242.9	1251.7	1260.4	1264.7	1269.1
50°	1085.9	1094.7	1099.1	1099.1	1103.3	1112.1	1120.9	1120.9	1129.5	1142.7	1146.9
52.5°	968.2	968.2	976.9	981.3	985.6	985.6	998.7	1003.1	1007.4	1016.1	1024.9
55°	837.4	850.4	854.8	854.8	863.6	872.2	876.6	881.0	881.0	898.4	898.4
57.5°	724.0	728.4	737.0	737.0	737.0	750.2	750.2	758.8	763.2	767.6	776.2
60°	610.6	619.3	619.3	623.6	619.3	628.0	632.4	641.1	645.4	649.8	654.2
62.5°	505.9	505.9	510.3	510.3	510.3	510.3	519.0	519.0	527.7	532.1	536.4
65°	405.5	405.5	405.5	405.5	405.5	405.5	405.5	405.5	409.9	409.9	418.7
67.5°	314.0	309.7	300.9	305.3	300.9	300.9	296.5	296.5	300.9	300.9	309.7
70°	226.8	222.4	213.7	213.7	209.3	205.0	200.6	196.3	191.9	191.9	191.9
72.5°	148.3	139.6	126.5	122.1	122.1	113.4	104.6	100.3	100.3	100.3	100.3
75°	74.2	65.4	56.7	52.4	52.4	43.6	48.0	43.6	43.6	43.6	43.6
77.5°	30.6	21.8	17.4	17.4	17.4	13.0	13.0	13.0	13.0	13.0	13.0
80°	8.8	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4
82.5°	4.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585109

CATALOG NUMBER: HCC8S60D010SL-HM86080840-81RWWC

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	3266.5	3266.5	3266.5	3266.5	3266.5	3266.5	3266.5	3266.5
2.5°	3249.1	3249.1	3240.4	3244.7	3244.7	3244.7	3244.7	3244.7
5°	3209.8	3214.2	3209.8	3214.2	3214.2	3209.8	3209.8	3209.8
7.5°	3170.6	3175.0	3170.6	3175.0	3175.0	3175.0	3170.6	3170.6
10°	3122.6	3122.6	3122.6	3122.6	3122.6	3118.2	3122.6	3122.6
12.5°	3057.2	3057.2	3057.2	3061.6	3061.6	3057.2	3057.2	3052.8
15°	2987.4	2978.7	2983.0	2987.4	2983.0	2983.0	2983.0	2983.0
17.5°	2891.5	2895.8	2891.5	2891.5	2891.5	2891.5	2895.8	2891.5
20°	2791.1	2791.1	2795.5	2791.1	2791.1	2791.1	2791.1	2786.8
22.5°	2677.7	2673.4	2673.4	2677.7	2677.7	2673.4	2677.7	2677.7
25°	2551.3	2555.7	2551.3	2551.3	2555.7	2555.7	2555.7	2551.3
27.5°	2416.1	2420.4	2424.8	2420.4	2420.4	2420.4	2424.8	2429.2
30°	2276.6	2285.2	2276.6	2276.6	2285.2	2280.8	2285.2	2285.2
32.5°	2128.3	2141.3	2132.6	2141.3	2141.3	2145.7	2141.3	2145.7
35°	1979.9	1993.1	1993.1	1993.1	1997.5	2001.8	2001.8	1997.5
37.5°	1840.4	1844.7	1844.7	1853.5	1857.9	1862.3	1862.3	1857.9
40°	1696.5	1705.2	1709.6	1709.6	1709.6	1718.3	1727.0	1718.3
42.5°	1557.0	1561.4	1565.6	1565.6	1574.4	1578.8	1583.2	1583.2
45°	1421.8	1430.4	1434.8	1439.2	1443.6	1452.2	1447.9	1456.6
47.5°	1282.2	1295.3	1299.7	1304.0	1312.7	1317.1	1321.5	1325.8
50°	1155.7	1164.5	1164.5	1173.1	1186.3	1186.3	1194.9	1199.3
52.5°	1029.3	1033.6	1037.9	1042.3	1051.1	1059.7	1059.7	1068.5
55°	907.1	911.5	911.5	915.8	920.2	937.6	942.0	942.0
57.5°	780.6	780.6	789.4	793.8	798.2	806.8	806.8	806.8
60°	658.6	662.9	662.9	667.2	671.6	680.4	684.7	680.4
62.5°	536.4	540.8	540.8	545.1	553.9	558.2	553.9	553.9
65°	423.1	427.5	427.5	431.7	440.5	440.5	436.1	440.5
67.5°	309.7	309.7	309.7	309.7	309.7	309.7	309.7	309.7
70°	196.3	191.9	187.5	191.9	191.9	191.9	187.5	196.3
72.5°	96.0	100.3	100.3	100.3	100.3	100.3	100.3	96.0
75°	43.6	43.6	39.2	39.2	39.2	43.6	43.6	39.2
77.5°	13.0	13.0	13.0	13.0	13.0	13.0	13.0	13.0
80°	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)