

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585133

Luminaire Tested: **HCC8S60D010SL-HM86080927-81WWBB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585133  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S60D010SL-HM86080927-81WWBB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3783.7 lumens  
Efficiency: N/A  
Efficacy: 67.6 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 56  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585133  
CATALOG NUMBER: HCC8S60D010SL-HM86080927-81WWBB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585133

CATALOG NUMBER: HCC8S60D010SL-HM86080927-81WWBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77					77			
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67					67			
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59					59			
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53					53			
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47					47			
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43					43			
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39					39			
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35					35			
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32					32			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	62641	62641	62641
5°	65230	62499	59868
10°	67409	61703	56950
15°	69112	60292	53990
20°	69250	57791	51317
25°	68079	54136	48658
30°	64437	49949	46381
35°	58751	44921	43551
40°	51090	39598	40214
45°	43832	34294	36810
50°	37438	29570	33068
55°	32811	25467	28730
60°	29214	21721	24157
65°	25917	17723	19270
70°	22991	13145	10954
75°	19170	6875	3253
80°	15094	2149	533
85°	10720	1061	0



TEST NUMBER: P585133  
 CATALOG NUMBER: HCC8S60D010SL-HM86080927-81WWBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	191.4	5.1
10°-20°	536.5	14.2
20°-30°	759.3	20.1
30°-40°	794.4	21.0
40°-50°	662.6	17.5
50°-60°	469.9	12.4
60°-70°	270.6	7.2
70°-80°	87.1	2.3
80°-90°	12.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1487.2	39.3
0°-40°	2281.6	60.3
0°-60°	3414.1	90.2
0°-90°	3783.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3783.7	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2031	2031	2031	2031	2031	
5°	2107	2080	2019	1958	1934	202
15°	2165	2077	1889	1740	1691	609
25°	2001	1852	1591	1464	1430	913
35°	1561	1424	1193	1130	1157	968
45°	1005	923	786	796	844	779
55°	610	547	474	498	534	551
65°	355	298	243	243	264	355
75°	161	118	58	27	27	174
85°	30	15	3	0	0	38
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585133

CATALOG NUMBER: HCC8S60D010SL-HM86080927-81WWBB

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2031.4	2031.4	2031.4	2031.4	2031.4	2031.4	2031.4	2031.4	2031.4	2031.4	2031.4
2.5°	2073.8	2070.8	2067.8	2070.8	2067.8	2070.8	2067.8	2067.8	2064.7	2061.7	2061.7
5°	2107.3	2104.3	2104.3	2104.3	2101.1	2098.1	2098.1	2095.2	2089.0	2086.0	2079.9
7.5°	2128.5	2131.5	2131.5	2131.5	2125.5	2125.5	2119.4	2113.4	2107.3	2101.1	2092.0
10°	2152.8	2152.8	2149.7	2146.7	2140.6	2137.6	2134.6	2128.5	2119.4	2107.3	2098.1
12.5°	2161.9	2161.9	2158.8	2152.8	2149.7	2146.7	2143.7	2134.6	2122.5	2107.3	2095.2
15°	2164.9	2158.8	2155.8	2152.8	2146.7	2137.6	2137.6	2125.5	2110.3	2092.0	2076.9
17.5°	2140.6	2143.7	2137.6	2131.5	2122.5	2116.4	2107.3	2098.1	2079.9	2058.7	2043.5
20°	2110.3	2107.3	2104.3	2095.2	2082.9	2079.9	2070.8	2055.6	2040.5	2016.1	1994.9
22.5°	2061.7	2058.7	2052.6	2046.5	2034.4	2028.3	2019.1	2000.9	1979.7	1955.5	1931.1
25°	2000.9	1994.9	1985.8	1973.7	1964.6	1958.5	1946.4	1928.1	1903.8	1876.5	1852.2
27.5°	1903.8	1912.9	1906.8	1888.6	1879.5	1867.4	1864.4	1840.0	1818.8	1791.5	1764.1
30°	1809.7	1809.7	1800.6	1791.5	1776.2	1767.1	1755.0	1736.8	1715.6	1682.1	1660.9
32.5°	1691.2	1688.2	1676.1	1673.0	1660.9	1642.7	1639.7	1615.3	1594.1	1569.8	1542.4
35°	1560.7	1554.7	1542.4	1533.3	1527.3	1518.2	1509.1	1487.8	1466.5	1442.3	1424.1
37.5°	1411.9	1411.9	1408.9	1393.7	1387.7	1381.5	1372.4	1351.2	1339.1	1314.8	1296.5
40°	1269.2	1266.2	1257.1	1254.0	1248.0	1238.9	1232.8	1220.6	1202.4	1184.2	1166.0
42.5°	1129.5	1132.5	1120.4	1123.4	1111.3	1105.2	1102.2	1084.0	1074.9	1056.6	1041.5
45°	1005.1	1002.0	996.0	992.8	986.8	980.7	974.6	965.6	950.4	932.2	923.1
47.5°	889.6	880.5	880.5	877.5	874.5	862.3	859.3	850.2	841.1	822.8	810.7
50°	780.4	780.4	780.4	777.3	768.2	765.2	759.1	749.9	740.8	728.7	710.5
52.5°	692.3	692.3	692.3	689.3	677.2	674.0	671.0	658.9	646.7	637.6	625.5
55°	610.3	613.4	610.3	604.3	595.2	595.2	586.0	579.9	567.8	558.7	546.6
57.5°	540.5	540.5	534.4	531.4	525.3	522.3	516.1	510.1	494.9	485.8	470.6
60°	473.7	470.6	470.6	464.6	458.5	452.4	449.4	440.3	434.3	419.0	406.9
62.5°	412.9	412.9	406.9	406.9	394.7	394.7	391.7	382.6	373.5	358.2	352.2
65°	355.2	355.2	352.2	349.1	340.0	337.0	334.0	324.9	315.8	306.7	297.6
67.5°	303.7	303.7	297.6	294.6	288.5	285.5	279.4	273.2	264.1	255.0	245.9
70°	255.0	252.0	249.0	245.9	239.9	236.8	230.8	224.7	215.6	209.5	200.3
72.5°	206.5	206.5	203.5	197.3	194.3	191.3	188.2	182.2	173.1	164.0	157.9
75°	160.9	160.9	160.9	154.9	148.8	145.8	145.8	139.7	133.6	124.5	118.5
77.5°	124.5	121.5	118.5	118.5	112.3	109.3	106.2	103.2	94.1	91.1	85.0
80°	85.0	88.0	85.0	82.0	78.9	75.9	75.9	69.8	66.8	60.8	54.7
82.5°	57.7	54.7	54.7	51.7	51.7	48.6	48.6	42.6	39.4	36.4	33.4
85°	30.3	30.3	27.3	27.3	27.3	24.3	24.3	21.2	21.2	18.2	15.2
87.5°	9.1	9.1	9.1	9.1	9.1	9.1	9.1	9.1	6.1	6.1	6.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585133

CATALOG NUMBER: HCC8S60D010SL-HM86080927-81WWBB

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2031.4	2031.4	2031.4	2031.4	2031.4	2031.4	2031.4	2031.4	2031.4	2031.4	2031.4
2.5°	2058.7	2052.6	2049.6	2049.6	2046.5	2043.5	2040.5	2037.4	2031.4	2031.4	2025.3
5°	2073.8	2067.8	2064.7	2055.6	2049.6	2049.6	2037.4	2034.4	2025.3	2019.1	2013.1
7.5°	2086.0	2073.8	2064.7	2055.6	2049.6	2043.5	2031.4	2019.1	2007.0	1994.9	1988.8
10°	2086.0	2073.8	2058.7	2043.5	2037.4	2031.4	2016.1	1997.9	1982.8	1970.6	1955.5
12.5°	2079.9	2061.7	2043.5	2031.4	2019.1	2010.0	1991.9	1973.7	1955.5	1931.1	1919.0
15°	2061.7	2037.4	2019.1	1997.9	1988.8	1973.7	1958.5	1931.1	1909.9	1888.6	1873.5
17.5°	2025.3	1994.9	1973.7	1952.4	1937.3	1928.1	1903.8	1879.5	1855.2	1830.9	1812.7
20°	1970.6	1943.2	1919.0	1891.7	1879.5	1867.4	1837.0	1812.7	1788.5	1761.1	1742.9
22.5°	1903.8	1876.5	1843.1	1821.8	1803.6	1788.5	1761.1	1733.8	1709.5	1685.2	1660.9
25°	1821.8	1794.5	1764.1	1730.8	1718.6	1703.5	1673.0	1645.7	1618.3	1591.1	1569.8
27.5°	1733.8	1697.3	1673.0	1636.6	1624.4	1609.3	1575.9	1545.6	1521.2	1500.0	1475.7
30°	1627.4	1600.2	1566.8	1533.3	1521.2	1506.0	1478.8	1451.4	1427.1	1402.8	1378.5
32.5°	1512.1	1484.8	1451.4	1427.1	1408.9	1396.8	1369.4	1345.1	1320.9	1296.5	1275.3
35°	1390.7	1360.3	1336.0	1311.8	1296.5	1281.3	1254.0	1232.8	1214.5	1193.3	1172.1
37.5°	1266.2	1244.9	1220.6	1193.3	1178.1	1166.0	1144.7	1120.4	1105.2	1087.1	1071.9
40°	1144.7	1120.4	1099.2	1074.9	1062.7	1053.6	1032.4	1014.2	999.0	983.7	974.6
42.5°	1020.2	999.0	977.7	962.5	953.4	944.3	929.2	907.8	898.7	883.6	874.5
45°	904.8	886.6	871.4	850.2	844.1	838.1	819.8	804.6	795.5	786.4	780.4
47.5°	795.5	783.4	765.2	753.1	743.9	737.8	725.7	713.5	704.5	698.4	692.3
50°	701.4	686.3	674.0	661.9	655.8	646.7	634.6	628.5	622.5	616.4	616.4
52.5°	613.4	598.2	586.0	576.9	570.8	564.8	555.7	552.6	546.6	546.6	543.5
55°	531.4	522.3	510.1	497.9	494.9	491.9	485.8	479.7	476.7	473.7	476.7
57.5°	461.5	452.4	440.3	431.1	428.1	425.1	422.0	416.0	412.9	412.9	412.9
60°	397.8	388.7	379.6	370.5	370.5	364.4	361.4	358.2	355.2	352.2	352.2
62.5°	340.0	330.9	321.9	315.8	312.8	309.7	303.7	300.6	297.6	297.6	294.6
65°	288.5	276.4	273.2	264.1	261.1	258.1	255.0	249.0	245.9	242.9	239.9
67.5°	236.8	230.8	221.7	215.6	212.6	209.5	206.5	200.3	197.3	194.3	188.2
70°	191.3	185.2	179.1	173.1	170.0	167.0	160.9	154.9	151.8	145.8	136.7
72.5°	148.8	142.7	136.7	130.6	127.6	124.5	118.5	112.3	106.2	100.2	94.1
75°	112.3	106.2	97.1	91.1	88.0	88.0	78.9	72.9	66.8	57.7	51.7
77.5°	78.9	69.8	66.8	60.8	57.7	51.7	45.6	39.4	33.4	30.3	24.3
80°	51.7	45.6	39.4	36.4	33.4	30.3	27.3	21.2	15.2	12.1	9.1
82.5°	30.3	27.3	24.3	21.2	18.2	15.2	12.1	12.1	9.1	6.1	3.0
85°	15.2	12.1	9.1	9.1	6.1	6.1	6.1	3.0	3.0	3.0	3.0
87.5°	6.1	3.0	3.0	3.0	3.0	3.0	3.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585133

CATALOG NUMBER: HCC8S60D010SL-HM86080927-81WWBB

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2031.4	2031.4	2031.4	2031.4	2031.4	2031.4	2031.4	2031.4	2031.4	2031.4	2031.4
2.5°	2022.3	2019.1	2016.1	2013.1	2013.1	2007.0	2007.0	2004.0	1997.9	1994.9	1994.9
5°	2004.0	1994.9	1988.8	1985.8	1982.8	1973.7	1970.6	1964.6	1958.5	1952.4	1949.4
7.5°	1976.7	1961.5	1955.5	1952.4	1943.2	1934.1	1928.1	1919.0	1909.9	1900.8	1897.7
10°	1943.2	1928.1	1912.9	1906.8	1897.7	1891.7	1879.5	1867.4	1858.2	1849.1	1840.0
12.5°	1900.8	1882.6	1867.4	1861.4	1852.2	1840.0	1821.8	1815.8	1800.6	1794.5	1782.3
15°	1852.2	1830.9	1815.8	1806.7	1797.6	1779.4	1767.1	1755.0	1739.9	1733.8	1721.7
17.5°	1791.5	1767.1	1752.0	1742.9	1736.8	1721.7	1703.5	1688.2	1673.0	1667.0	1657.9
20°	1718.6	1703.5	1682.1	1673.0	1667.0	1648.8	1630.6	1624.4	1612.3	1600.2	1591.1
22.5°	1636.6	1621.4	1600.2	1591.1	1588.0	1572.9	1557.7	1548.6	1539.4	1530.3	1521.2
25°	1551.6	1533.3	1515.1	1509.1	1503.0	1490.9	1478.8	1472.7	1463.5	1457.4	1451.4
27.5°	1460.6	1442.3	1427.1	1418.0	1411.9	1402.8	1396.8	1390.7	1384.5	1378.5	1375.4
30°	1363.3	1345.1	1333.0	1326.9	1320.9	1317.8	1308.6	1305.6	1302.6	1296.5	1299.5
32.5°	1266.2	1251.0	1238.9	1229.8	1229.8	1223.6	1220.6	1220.6	1217.6	1217.6	1217.6
35°	1159.9	1150.7	1141.6	1138.6	1135.6	1132.5	1129.5	1132.5	1129.5	1132.5	1135.6
37.5°	1062.7	1053.6	1047.5	1044.5	1041.5	1044.5	1041.5	1041.5	1044.5	1050.6	1053.6
40°	962.5	956.5	950.4	953.4	950.4	950.4	950.4	959.5	962.5	965.6	968.6
42.5°	868.4	862.3	859.3	859.3	862.3	859.3	865.4	868.4	874.5	883.6	889.6
45°	777.3	774.3	774.3	777.3	774.3	780.4	780.4	786.4	795.5	801.6	807.7
47.5°	692.3	692.3	692.3	695.4	695.4	698.4	704.5	707.5	713.5	719.6	725.7
50°	613.4	616.4	619.4	619.4	619.4	625.5	631.6	634.6	637.6	640.7	649.8
52.5°	543.5	546.6	546.6	549.6	552.6	555.7	558.7	564.8	567.8	573.9	576.9
55°	476.7	476.7	482.8	485.8	485.8	485.8	491.9	491.9	497.9	501.0	507.0
57.5°	412.9	416.0	416.0	419.0	419.0	422.0	425.1	428.1	431.1	434.3	437.3
60°	352.2	352.2	352.2	355.2	358.2	361.4	358.2	364.4	364.4	370.5	373.5
62.5°	294.6	297.6	297.6	297.6	297.6	297.6	297.6	300.6	303.7	306.7	309.7
65°	239.9	239.9	239.9	236.8	239.9	236.8	239.9	242.9	242.9	245.9	249.0
67.5°	185.2	185.2	179.1	179.1	182.2	182.2	182.2	182.2	179.1	185.2	185.2
70°	133.6	130.6	127.6	124.5	124.5	121.5	121.5	118.5	118.5	118.5	118.5
72.5°	88.0	82.0	75.9	72.9	69.8	69.8	63.8	60.8	63.8	63.8	63.8
75°	45.6	39.4	36.4	33.4	30.3	30.3	27.3	27.3	27.3	27.3	27.3
77.5°	18.2	15.2	12.1	12.1	9.1	9.1	9.1	9.1	9.1	9.1	9.1
80°	6.1	6.1	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
82.5°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
85°	3.0	0.0	0.0	3.0	0.0	3.0	3.0	3.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585133

CATALOG NUMBER: HCC8S60D010SL-HM86080927-81WWBB

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2031.4	2031.4	2031.4	2031.4	2031.4	2031.4	2031.4	2031.4
2.5°	1991.9	1991.9	1988.8	1991.9	1985.8	1988.8	1985.8	1985.8
5°	1946.4	1940.2	1940.2	1940.2	1937.3	1937.3	1934.1	1934.1
7.5°	1891.7	1888.6	1885.6	1882.6	1879.5	1876.5	1876.5	1876.5
10°	1837.0	1830.9	1830.9	1827.9	1821.8	1818.8	1818.8	1818.8
12.5°	1773.2	1770.2	1767.1	1767.1	1755.0	1758.0	1755.0	1755.0
15°	1712.6	1709.5	1709.5	1700.3	1694.3	1694.3	1694.3	1691.2
17.5°	1648.8	1645.7	1642.7	1636.6	1630.6	1630.6	1627.4	1630.6
20°	1582.0	1578.9	1572.9	1572.9	1569.8	1566.8	1560.7	1563.8
22.5°	1515.1	1509.1	1506.0	1506.0	1503.0	1503.0	1496.9	1496.9
25°	1445.3	1442.3	1439.2	1442.3	1436.2	1436.2	1430.1	1430.1
27.5°	1372.4	1369.4	1369.4	1369.4	1366.3	1369.4	1366.3	1366.3
30°	1299.5	1299.5	1296.5	1296.5	1299.5	1296.5	1299.5	1302.6
32.5°	1220.6	1220.6	1223.6	1223.6	1226.6	1226.6	1226.6	1226.6
35°	1138.6	1144.7	1144.7	1147.7	1150.7	1153.9	1153.9	1156.9
37.5°	1062.7	1065.7	1068.9	1071.9	1078.0	1078.0	1078.0	1078.0
40°	980.7	983.7	989.8	986.8	999.0	1002.0	999.0	999.0
42.5°	895.7	901.8	904.8	911.0	914.0	920.1	923.1	923.1
45°	816.8	819.8	825.9	831.9	835.1	844.1	844.1	844.1
47.5°	734.8	740.8	743.9	749.9	753.1	762.2	765.2	762.2
50°	655.8	661.9	668.0	668.0	677.2	680.2	686.3	689.3
52.5°	579.9	582.9	589.0	592.0	598.2	604.3	607.3	610.3
55°	507.0	510.1	516.1	516.1	525.3	528.4	534.4	534.4
57.5°	440.3	443.4	449.4	446.4	452.4	458.5	458.5	455.5
60°	376.5	376.5	376.5	382.6	385.6	388.7	391.7	391.7
62.5°	309.7	315.8	318.8	318.8	321.9	324.9	324.9	321.9
65°	249.0	255.0	258.1	258.1	261.1	261.1	261.1	264.1
67.5°	188.2	188.2	188.2	191.3	188.2	188.2	188.2	188.2
70°	118.5	118.5	118.5	118.5	115.3	118.5	118.5	121.5
72.5°	63.8	63.8	63.8	63.8	63.8	63.8	63.8	63.8
75°	27.3	27.3	27.3	30.3	27.3	27.3	27.3	27.3
77.5°	12.1	9.1	12.1	12.1	9.1	9.1	9.1	9.1
80°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
82.5°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
85°	0.0	3.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)