

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585134

Luminaire Tested: **HCC8W60D010MW-HM86080927-81WWW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585134
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W60D010MW-HM86080927-81WWW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4129.9 lumens
Efficiency: N/A
Efficacy: 73.7 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 56
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585134
CATALOG NUMBER: HCC8W60D010MW-HM86080927-81WWW

Luminous Intensity Polar Plot





TEST NUMBER: P585134

CATALOG NUMBER: HCC8W60D010MW-HM86080927-81WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100		
	1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87	87	87	87	87	87		
	2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76	76	76	76	76	76		
	3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66	66	66	66	66	66		
	4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58	58	58	58	58	58		
	5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51	51	51	51	51	51		
	6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46	46	46	46	46	46		
	7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41	41	41	41	41	41		
	8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38	38	38	38	38	38		
	9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34	34	34	34	34	34		
	10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32	32	32	32	32	32		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	69006	69006	69006
5°	71430	68610	65886
10°	73016	67409	62179
15°	74058	65141	58064
20°	73831	61975	53906
25°	72009	57953	49485
30°	68219	53300	45409
35°	62068	48233	41262
40°	54512	42899	37279
45°	47538	37739	33239
50°	41367	33068	29278
55°	36896	29058	25467
60°	33519	25465	21721
65°	30127	22159	19715
70°	26831	18888	17788
75°	23507	15917	15203
80°	19942	12946	13478
85°	15072	9659	10720



TEST NUMBER: P585134
 CATALOG NUMBER: HCC8W60D010MW-HM86080927-81WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	209.6	5.1
10°-20°	577.5	14.0
20°-30°	801.6	19.4
30°-40°	828.8	20.1
40°-50°	694.0	16.8
50°-60°	503.8	12.2
60°-70°	317.9	7.7
70°-80°	157.5	3.8
80°-90°	39.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1588.8	38.5
0°-40°	2417.6	58.5
0°-60°	3615.4	87.5
0°-90°	4129.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4129.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2238	2238	2238	2238	2238	
5°	2308	2280	2216	2156	2128	221
15°	2320	2232	2040	1876	1819	653
25°	2116	1980	1703	1518	1454	970
35°	1649	1527	1281	1136	1096	1027
45°	1090	1011	865	780	762	843
55°	686	626	540	495	474	619
65°	413	361	304	267	270	412
75°	197	164	134	128	128	212
85°	43	33	27	30	30	52
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585134

CATALOG NUMBER: HCC8W60D010MW-HM86080927-81WWW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2237.8	2237.8	2237.8	2237.8	2237.8	2237.8	2237.8	2237.8	2237.8	2237.8	2237.8
2.5°	2274.3	2274.3	2277.3	2274.3	2274.3	2274.3	2271.2	2271.2	2268.2	2268.2	2262.0
5°	2307.6	2301.6	2307.6	2301.6	2301.6	2301.6	2298.5	2292.5	2289.4	2283.4	2280.3
7.5°	2322.8	2319.8	2319.8	2316.7	2316.7	2313.7	2310.7	2307.6	2295.5	2292.5	2283.4
10°	2331.9	2328.8	2328.8	2325.8	2319.8	2319.8	2313.7	2310.7	2295.5	2289.4	2277.3
12.5°	2328.8	2328.8	2328.8	2325.8	2316.7	2313.7	2307.6	2298.5	2286.4	2274.3	2262.0
15°	2319.8	2319.8	2313.7	2310.7	2301.6	2295.5	2292.5	2277.3	2265.2	2249.9	2231.7
17.5°	2289.4	2289.4	2286.4	2280.3	2271.2	2265.2	2259.0	2243.8	2231.7	2207.4	2189.3
20°	2249.9	2246.9	2243.8	2234.7	2225.6	2222.6	2213.5	2192.3	2177.0	2158.8	2134.6
22.5°	2192.3	2189.3	2186.2	2180.2	2164.9	2158.8	2152.8	2137.6	2110.3	2092.0	2061.7
25°	2116.4	2116.4	2110.3	2101.1	2085.9	2079.9	2070.8	2055.6	2031.4	2004.0	1979.7
27.5°	2028.3	2025.3	2016.1	2010.0	1997.9	1988.8	1973.6	1955.4	1931.1	1909.9	1879.5
30°	1915.9	1915.9	1909.9	1900.8	1885.6	1879.5	1867.4	1846.1	1821.8	1794.5	1773.2
32.5°	1788.5	1788.5	1779.4	1773.2	1764.1	1748.9	1745.9	1721.6	1700.3	1679.1	1654.8
35°	1648.8	1651.8	1645.7	1633.6	1618.3	1618.3	1612.3	1591.0	1566.8	1545.6	1527.3
37.5°	1509.1	1500.0	1496.9	1490.9	1481.8	1469.5	1463.5	1454.4	1433.2	1418.0	1390.7
40°	1354.2	1357.2	1351.2	1345.1	1342.1	1333.0	1329.9	1314.8	1299.5	1281.3	1269.2
42.5°	1214.5	1214.5	1214.5	1208.4	1202.4	1193.3	1190.3	1181.2	1163.0	1150.7	1132.5
45°	1090.1	1081.0	1081.0	1077.9	1074.9	1068.7	1059.7	1053.6	1041.5	1032.4	1011.1
47.5°	968.6	971.6	968.6	965.5	956.4	953.4	950.4	938.3	926.1	917.0	901.8
50°	862.3	868.4	862.3	862.3	856.3	853.2	847.2	838.1	828.9	813.7	798.6
52.5°	774.3	774.3	771.3	768.2	759.1	753.1	749.9	746.9	731.7	719.6	707.5
55°	686.3	689.3	689.3	680.2	677.2	671.0	668.0	658.9	652.8	634.6	625.5
57.5°	610.3	607.3	610.3	604.3	598.2	592.0	589.0	582.9	573.8	561.7	549.6
60°	543.5	537.5	537.5	534.4	528.4	525.3	519.3	510.1	501.0	488.8	479.7
62.5°	476.7	473.7	470.6	467.6	461.5	458.5	455.5	446.4	437.3	428.1	419.0
65°	412.9	412.9	409.9	403.8	400.8	397.8	394.7	388.7	376.5	370.5	361.4
67.5°	355.2	352.2	352.2	346.1	340.0	337.0	337.0	330.9	321.8	312.8	306.7
70°	297.6	300.6	297.6	294.6	288.5	288.5	282.4	279.4	267.2	264.1	255.0
72.5°	245.9	245.9	242.9	242.9	236.8	233.8	233.8	227.7	221.7	215.6	209.5
75°	197.3	197.3	197.3	194.3	191.2	185.2	185.2	182.2	176.1	170.0	164.0
77.5°	154.9	151.8	151.8	148.8	145.8	142.7	142.7	139.7	133.6	130.6	124.5
80°	112.3	109.3	109.3	109.3	103.2	106.2	103.2	100.2	97.1	94.1	91.1
82.5°	72.9	75.9	75.9	72.9	69.8	69.8	69.8	66.8	66.8	63.8	60.8
85°	42.6	42.6	42.6	42.6	39.4	39.4	39.4	36.4	36.4	36.4	33.4
87.5°	18.2	18.2	18.2	18.2	18.2	18.2	15.2	15.2	15.2	15.2	15.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585134

CATALOG NUMBER: HCC8W60D010MW-HM86080927-81WWW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2237.8	2237.8	2237.8	2237.8	2237.8	2237.8	2237.8	2237.8	2237.8	2237.8	2237.8
2.5°	2262.0	2256.1	2252.9	2249.9	2249.9	2246.9	2243.8	2237.8	2237.8	2231.7	2228.7
5°	2274.3	2265.2	2259.0	2252.9	2249.9	2243.8	2237.8	2228.7	2225.6	2216.5	2207.4
7.5°	2277.3	2262.0	2256.1	2243.8	2237.8	2231.7	2219.6	2210.5	2198.4	2189.3	2177.0
10°	2265.2	2252.9	2237.8	2222.6	2219.6	2210.5	2192.3	2180.2	2164.9	2152.8	2134.6
12.5°	2246.9	2228.7	2213.5	2195.3	2186.2	2177.0	2158.8	2140.6	2119.4	2098.1	2079.9
15°	2216.5	2195.3	2174.0	2152.8	2140.6	2131.5	2110.3	2089.0	2067.8	2040.5	2022.3
17.5°	2171.0	2146.7	2125.5	2098.1	2085.9	2076.8	2049.6	2025.3	1997.9	1970.6	1952.4
20°	2113.3	2082.9	2058.7	2028.3	2019.1	2004.0	1976.7	1949.4	1919.0	1888.6	1867.4
22.5°	2037.4	2007.0	1979.7	1949.4	1934.1	1919.0	1891.7	1858.2	1827.9	1803.6	1782.3
25°	1949.4	1922.0	1888.6	1861.2	1843.0	1824.8	1794.5	1767.1	1739.8	1703.3	1682.1
27.5°	1852.1	1818.8	1794.5	1758.0	1739.8	1727.7	1694.3	1657.9	1633.6	1600.1	1575.9
30°	1742.9	1712.5	1685.2	1648.8	1630.6	1618.3	1588.0	1554.7	1530.3	1496.9	1472.7
32.5°	1627.4	1594.1	1560.7	1536.4	1515.1	1503.0	1469.5	1448.3	1418.0	1390.7	1363.3
35°	1503.0	1469.5	1445.3	1411.9	1399.8	1387.7	1360.3	1333.0	1305.6	1281.3	1260.1
37.5°	1369.4	1345.1	1317.8	1293.5	1284.4	1272.2	1238.9	1214.5	1193.3	1169.0	1150.7
40°	1238.9	1217.5	1199.3	1175.1	1159.9	1150.7	1126.5	1105.2	1081.0	1065.7	1047.5
42.5°	1120.4	1096.1	1077.9	1059.7	1044.5	1035.4	1014.2	999.0	980.7	965.5	944.3
45°	996.0	983.7	962.5	947.3	938.3	926.1	911.0	892.7	877.5	865.4	850.2
47.5°	886.6	874.5	859.3	841.1	834.9	825.8	810.7	798.6	786.4	774.3	759.1
50°	786.4	771.3	759.1	746.9	740.8	731.7	716.6	710.5	701.4	689.3	680.2
52.5°	695.3	683.2	671.0	655.8	652.8	646.7	637.6	625.5	616.4	610.3	604.3
55°	613.4	601.2	592.0	579.9	576.9	570.8	558.7	552.6	546.6	540.5	534.4
57.5°	540.5	528.4	516.1	510.1	504.0	497.9	494.9	485.8	479.7	476.7	470.6
60°	473.7	461.5	452.4	443.3	440.3	437.3	431.1	425.1	419.0	412.9	409.9
62.5°	409.9	397.8	391.7	385.6	379.6	379.6	373.5	367.4	361.4	358.2	352.2
65°	352.2	346.1	337.0	327.9	324.9	324.9	315.8	312.8	309.7	303.7	297.6
67.5°	297.6	291.5	282.4	279.4	276.4	273.2	270.2	264.1	258.1	255.0	249.0
70°	249.0	242.9	236.8	233.8	230.8	227.7	221.7	218.6	212.6	209.5	206.5
72.5°	200.3	197.3	191.2	188.2	185.2	182.2	179.1	176.1	170.0	167.0	164.0
75°	160.9	157.9	151.8	148.8	145.8	145.8	142.7	136.7	133.6	133.6	130.6
77.5°	121.5	118.5	115.3	112.3	109.3	109.3	106.2	103.2	100.2	100.2	97.1
80°	88.0	85.0	82.0	82.0	82.0	78.9	75.9	75.9	72.9	72.9	69.8
82.5°	57.7	57.7	54.7	54.7	54.7	51.7	51.7	48.6	48.6	48.6	48.6
85°	33.4	33.4	33.4	30.3	30.3	30.3	30.3	30.3	30.3	27.3	30.3
87.5°	15.2	15.2	15.2	15.2	15.2	15.2	15.2	15.2	12.1	12.1	12.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585134

CATALOG NUMBER: HCC8W60D010MW-HM86080927-81WWW

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2237.8	2237.8	2237.8	2237.8	2237.8	2237.8	2237.8	2237.8	2237.8	2237.8	2237.8
2.5°	2225.6	2222.6	2216.5	2216.5	2210.5	2210.5	2207.4	2204.4	2201.4	2198.4	2195.3
5°	2204.4	2192.3	2186.2	2183.2	2177.0	2174.0	2164.9	2158.8	2155.8	2149.7	2143.7
7.5°	2164.9	2152.8	2140.6	2137.6	2134.6	2122.4	2113.3	2104.1	2098.1	2092.0	2085.9
10°	2119.4	2107.3	2092.0	2085.9	2079.9	2064.7	2052.6	2043.5	2031.4	2019.1	2016.1
12.5°	2064.7	2046.5	2028.3	2022.3	2013.1	1997.9	1985.8	1970.6	1961.5	1946.4	1943.2
15°	2000.9	1979.7	1964.5	1949.4	1943.2	1928.1	1906.8	1894.7	1876.5	1870.4	1855.2
17.5°	1925.0	1903.8	1882.6	1876.5	1867.4	1846.1	1824.8	1809.7	1791.5	1782.3	1773.2
20°	1846.1	1818.8	1797.6	1791.5	1779.4	1761.1	1739.8	1724.7	1709.5	1691.2	1682.1
22.5°	1755.0	1724.7	1706.5	1691.2	1688.2	1667.0	1642.7	1630.6	1618.3	1603.2	1591.0
25°	1654.8	1627.4	1606.2	1594.1	1588.0	1569.8	1551.6	1536.4	1518.2	1509.1	1493.9
27.5°	1551.6	1533.3	1506.0	1493.9	1484.8	1469.5	1448.3	1439.2	1421.0	1408.9	1399.8
30°	1451.3	1424.1	1408.9	1393.7	1384.5	1369.4	1351.2	1342.1	1326.9	1314.8	1305.6
32.5°	1342.1	1323.9	1302.6	1296.5	1284.4	1269.2	1257.1	1241.9	1229.8	1217.5	1214.5
35°	1241.9	1217.5	1196.3	1190.3	1181.2	1166.0	1159.9	1150.7	1135.6	1132.5	1120.4
37.5°	1132.5	1120.4	1096.1	1087.0	1084.0	1071.9	1059.7	1053.6	1044.5	1035.4	1032.4
40°	1029.3	1014.2	1002.0	992.8	986.8	977.7	965.5	962.5	956.4	944.3	941.3
42.5°	932.2	917.0	904.8	901.8	892.7	883.6	877.5	868.4	865.4	862.3	856.3
45°	838.1	828.9	816.8	813.7	810.7	798.6	792.5	786.4	780.4	777.3	771.3
47.5°	753.1	743.9	734.8	731.7	725.7	722.6	713.5	710.5	701.4	698.4	695.3
50°	671.0	664.9	658.9	655.8	649.8	646.7	640.7	634.6	628.5	625.5	622.5
52.5°	598.2	592.0	586.0	582.9	579.9	573.8	567.8	561.7	558.7	555.7	552.6
55°	528.4	522.3	519.3	516.1	513.1	510.1	501.0	497.9	494.9	491.9	485.8
57.5°	464.6	458.5	452.4	452.4	449.4	446.4	440.3	434.3	434.3	428.1	422.0
60°	406.9	400.8	394.7	391.7	388.7	382.6	379.6	376.5	373.5	370.5	364.4
62.5°	346.1	343.1	337.0	337.0	330.9	327.9	324.9	321.8	318.8	312.8	309.7
65°	294.6	291.5	285.5	282.4	282.4	279.4	273.2	270.2	267.2	267.2	264.1
67.5°	245.9	242.9	236.8	233.8	233.8	230.8	227.7	227.7	224.7	221.7	224.7
70°	203.5	197.3	197.3	194.3	194.3	191.2	188.2	188.2	188.2	191.2	191.2
72.5°	160.9	157.9	154.9	154.9	154.9	154.9	151.8	151.8	154.9	157.9	157.9
75°	127.6	124.5	124.5	124.5	121.5	121.5	124.5	124.5	127.6	127.6	127.6
77.5°	94.1	94.1	94.1	94.1	94.1	94.1	97.1	97.1	100.2	100.2	100.2
80°	69.8	69.8	69.8	69.8	69.8	72.9	72.9	72.9	72.9	72.9	75.9
82.5°	48.6	48.6	48.6	48.6	48.6	48.6	48.6	51.7	51.7	51.7	51.7
85°	27.3	30.3	30.3	30.3	30.3	30.3	30.3	30.3	30.3	30.3	30.3
87.5°	12.1	12.1	12.1	12.1	12.1	12.1	12.1	12.1	12.1	12.1	12.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585134

CATALOG NUMBER: HCC8W60D010MW-HM86080927-81WWW

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2237.8	2237.8	2237.8	2237.8	2237.8	2237.8	2237.8	2237.8
2.5°	2192.3	2192.3	2192.3	2195.3	2189.3	2189.3	2189.3	2189.3
5°	2140.6	2137.6	2134.6	2137.6	2131.5	2131.5	2128.5	2128.5
7.5°	2076.8	2073.8	2070.8	2070.8	2064.7	2064.7	2061.7	2058.7
10°	2007.0	2000.9	2004.0	1997.9	1994.9	1991.8	1988.8	1985.8
12.5°	1931.1	1925.0	1922.0	1915.9	1909.9	1906.8	1909.9	1903.8
15°	1849.1	1840.0	1837.0	1830.9	1824.8	1821.8	1821.8	1818.8
17.5°	1758.0	1752.0	1748.9	1742.9	1739.8	1733.8	1730.7	1727.7
20°	1673.0	1657.9	1660.9	1654.8	1651.8	1639.7	1639.7	1642.7
22.5°	1578.9	1569.8	1563.8	1557.7	1554.7	1548.6	1548.6	1545.6
25°	1484.8	1475.7	1472.7	1466.5	1463.5	1457.4	1454.4	1454.4
27.5°	1393.7	1381.5	1381.5	1375.4	1369.4	1366.3	1363.3	1360.3
30°	1296.5	1287.4	1284.4	1284.4	1281.3	1281.3	1272.2	1275.3
32.5°	1205.4	1199.3	1196.3	1190.3	1190.3	1187.2	1187.2	1178.1
35°	1114.3	1105.2	1108.3	1102.2	1099.2	1096.1	1099.2	1096.1
37.5°	1026.3	1020.2	1020.2	1014.2	1014.2	1011.1	1008.1	1014.2
40°	938.3	935.2	932.2	929.2	932.2	929.2	923.1	926.1
42.5°	850.2	850.2	847.2	847.2	844.1	844.1	844.1	844.1
45°	771.3	768.2	768.2	765.2	765.2	765.2	765.2	762.2
47.5°	692.3	689.3	689.3	689.3	686.3	686.3	683.2	686.3
50°	616.4	616.4	613.4	613.4	616.4	613.4	610.3	610.3
52.5°	546.6	546.6	543.5	543.5	540.5	537.5	540.5	540.5
55°	482.8	479.7	476.7	476.7	473.7	470.6	470.6	473.7
57.5°	422.0	419.0	416.0	416.0	409.9	406.9	406.9	406.9
60°	364.4	358.2	358.2	355.2	355.2	352.2	352.2	352.2
62.5°	309.7	306.7	306.7	306.7	306.7	303.7	303.7	303.7
65°	264.1	264.1	264.1	267.2	267.2	270.2	270.2	270.2
67.5°	227.7	230.8	230.8	230.8	233.8	233.8	233.8	230.8
70°	194.3	194.3	194.3	197.3	197.3	197.3	197.3	197.3
72.5°	160.9	160.9	160.9	160.9	160.9	160.9	160.9	160.9
75°	127.6	130.6	130.6	130.6	127.6	130.6	130.6	127.6
77.5°	100.2	100.2	100.2	100.2	100.2	100.2	100.2	100.2
80°	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9
82.5°	51.7	51.7	51.7	51.7	51.7	51.7	51.7	51.7
85°	30.3	30.3	30.3	30.3	30.3	30.3	30.3	30.3
87.5°	12.1	12.1	12.1	12.1	12.1	12.1	12.1	12.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)