

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585135

Luminaire Tested: **HCC8W60D010MW-HM86080927-81WWWB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585135  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W60D010MW-HM86080927-81WWWB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4300.0 lumens  
Efficiency: N/A  
Efficacy: 76.8 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 56  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585135  
CATALOG NUMBER: HCC8W60D010MW-HM86080927-81WWWB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585135

CATALOG NUMBER: HCC8W60D010MW-HM86080927-81WWWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75								
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65								
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57								
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50								
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45								
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40								
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37								
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33								
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	65925	65925	65925
5°	68340	65709	63453
10°	70274	65138	60858
15°	71842	63989	58169
20°	71951	61489	55809
25°	70573	58069	53833
30°	66933	53848	51473
35°	60822	49047	49160
40°	53179	44010	46332
45°	46090	39205	43177
50°	40355	34819	39338
55°	35923	30854	35595
60°	32403	27722	31274
65°	29252	24370	27260
70°	26290	20538	20259
75°	23149	16287	15203
80°	19409	13478	14561
85°	15072	11817	12879



TEST NUMBER: P585135  
 CATALOG NUMBER: HCC8W60D010MW-HM86080927-81WWWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	201.7	4.7
10°-20°	568.1	13.2
20°-30°	811.9	18.9
30°-40°	862.7	20.1
40°-50°	742.7	17.3
50°-60°	555.3	12.9
60°-70°	354.2	8.2
70°-80°	161.2	3.7
80°-90°	42.3	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1581.7	36.8
0°-40°	2444.3	56.8
0°-60°	3742.3	87.0
0°-90°	4300.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4300.0	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2138	2138	2138	2138	2138	
5°	2208	2178	2123	2068	2050	212
15°	2250	2174	2004	1868	1822	634
25°	2074	1944	1707	1604	1582	949
35°	1616	1503	1303	1269	1306	1006
45°	1057	999	899	923	990	822
55°	668	614	574	623	662	601
65°	401	355	334	349	374	400
75°	194	167	137	125	128	206
85°	43	36	33	36	36	51
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585135

CATALOG NUMBER: HCC8W60D010MW-HM86080927-81WWWB

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2137.9	2137.9	2137.9	2137.9	2137.9	2137.9	2137.9	2137.9	2137.9	2137.9	2137.9
2.5°	2177.5	2171.4	2174.4	2171.4	2174.4	2174.4	2168.4	2168.4	2168.4	2168.4	2159.3
5°	2207.8	2204.8	2204.8	2201.7	2198.7	2201.7	2198.7	2195.7	2189.6	2186.6	2177.5
7.5°	2226.1	2226.1	2226.1	2226.1	2223.1	2219.9	2217.0	2210.8	2204.8	2198.7	2192.6
10°	2244.3	2247.3	2244.3	2241.3	2238.2	2232.2	2229.1	2223.1	2214.0	2204.8	2198.7
12.5°	2253.4	2253.4	2250.4	2250.4	2244.3	2241.3	2232.2	2223.1	2214.0	2204.8	2189.6
15°	2250.4	2250.4	2247.3	2244.3	2235.2	2232.2	2226.1	2217.0	2201.7	2189.6	2174.4
17.5°	2232.2	2229.1	2223.1	2223.1	2210.8	2207.8	2201.7	2189.6	2174.4	2156.2	2137.9
20°	2192.6	2192.6	2189.6	2186.6	2174.4	2165.3	2159.3	2144.1	2131.9	2110.6	2092.4
22.5°	2137.9	2144.1	2137.9	2131.9	2116.7	2113.7	2104.6	2086.4	2068.2	2043.8	2022.6
25°	2074.2	2071.2	2068.2	2062.0	2049.9	2043.8	2031.7	2013.5	1995.3	1967.9	1943.6
27.5°	1992.2	1980.0	1980.0	1967.9	1958.8	1949.7	1943.6	1925.4	1901.1	1879.8	1849.5
30°	1879.8	1882.9	1867.7	1864.7	1849.5	1843.4	1831.3	1813.0	1791.8	1767.5	1743.1
32.5°	1758.4	1749.2	1749.2	1737.1	1724.9	1715.8	1712.8	1691.6	1673.4	1649.0	1624.8
35°	1615.7	1615.7	1606.6	1603.5	1591.3	1585.2	1576.1	1564.0	1542.8	1521.4	1503.2
37.5°	1475.9	1469.9	1466.8	1460.8	1451.7	1442.6	1442.6	1421.2	1418.2	1393.9	1369.7
40°	1321.1	1327.1	1321.1	1312.0	1308.9	1302.9	1299.8	1287.7	1278.5	1257.3	1242.1
42.5°	1190.4	1184.4	1184.4	1181.3	1169.2	1169.2	1163.1	1157.1	1141.9	1135.8	1117.5
45°	1056.9	1062.9	1053.7	1056.9	1044.7	1044.7	1044.7	1032.5	1020.4	1011.3	999.2
47.5°	941.4	944.5	944.5	935.4	932.3	932.3	926.3	920.2	911.1	899.0	889.8
50°	841.2	844.3	838.2	835.2	829.1	826.1	826.1	813.8	807.8	795.6	789.6
52.5°	750.2	750.2	747.1	747.1	737.9	737.9	731.9	722.8	716.7	710.6	695.5
55°	668.2	668.2	665.1	662.1	662.1	652.9	649.9	640.8	634.7	622.6	613.5
57.5°	589.2	592.2	589.2	586.2	583.0	580.0	573.9	564.8	558.8	549.7	543.6
60°	525.4	525.4	522.4	519.3	513.3	510.1	507.1	501.0	491.9	485.9	476.8
62.5°	464.6	461.6	458.6	455.5	449.5	449.5	443.4	437.4	428.3	422.1	416.0
65°	400.9	400.9	397.8	397.8	394.8	388.7	385.7	382.7	370.5	367.5	355.4
67.5°	343.1	346.3	340.1	340.1	334.0	334.0	331.0	321.9	318.9	312.8	306.7
70°	291.6	291.6	291.6	288.5	282.5	279.4	276.4	270.2	267.2	261.1	255.1
72.5°	239.9	239.9	236.9	236.9	233.8	230.8	227.8	221.7	221.7	215.6	209.6
75°	194.3	194.3	191.3	188.2	185.2	185.2	182.2	179.1	173.1	170.0	167.0
77.5°	148.8	148.8	148.8	145.8	142.8	142.8	142.8	136.7	130.6	130.6	127.6
80°	109.3	109.3	106.3	106.3	103.2	103.2	103.2	100.2	97.2	94.1	91.1
82.5°	72.9	72.9	72.9	72.9	69.9	69.9	69.9	66.8	63.8	63.8	63.8
85°	42.6	42.6	42.6	42.6	39.4	39.4	39.4	39.4	39.4	36.4	36.4
87.5°	18.2	15.2	18.2	15.2	18.2	15.2	18.2	15.2	15.2	15.2	15.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585135

CATALOG NUMBER: HCC8W60D010MW-HM86080927-81WWWB

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2137.9	2137.9	2137.9	2137.9	2137.9	2137.9	2137.9	2137.9	2137.9	2137.9	2137.9
2.5°	2162.3	2159.3	2156.2	2153.2	2153.2	2150.2	2144.1	2141.1	2137.9	2134.9	2134.9
5°	2174.4	2171.4	2165.3	2159.3	2156.2	2150.2	2144.1	2137.9	2131.9	2122.8	2119.7
7.5°	2183.5	2174.4	2168.4	2156.2	2153.2	2147.1	2137.9	2128.8	2116.7	2104.6	2095.5
10°	2183.5	2171.4	2162.3	2147.1	2141.1	2134.9	2122.8	2107.6	2092.4	2080.3	2065.0
12.5°	2177.5	2162.3	2147.1	2131.9	2122.8	2113.7	2095.5	2080.3	2062.0	2043.8	2031.7
15°	2156.2	2137.9	2119.7	2101.5	2092.4	2080.3	2062.0	2040.8	2022.6	2004.4	1983.0
17.5°	2116.7	2098.5	2077.3	2055.9	2043.8	2034.7	2007.4	1992.2	1964.8	1946.7	1928.5
20°	2065.0	2043.8	2016.5	1995.3	1980.0	1970.9	1949.7	1922.4	1901.1	1873.8	1855.6
22.5°	1998.3	1970.9	1943.6	1922.4	1907.1	1895.0	1867.7	1840.4	1822.1	1797.8	1776.6
25°	1919.4	1892.0	1864.7	1834.3	1819.1	1806.9	1782.7	1758.4	1734.0	1706.7	1688.5
27.5°	1825.1	1794.8	1770.5	1743.1	1728.0	1709.8	1682.5	1658.1	1633.9	1615.7	1591.3
30°	1721.9	1688.5	1664.2	1636.9	1621.7	1606.6	1579.2	1554.9	1533.7	1512.3	1500.2
32.5°	1597.5	1573.1	1548.8	1521.4	1509.3	1500.2	1472.9	1448.6	1424.3	1406.1	1397.0
35°	1479.0	1451.7	1430.3	1406.1	1390.9	1381.8	1357.4	1336.2	1324.1	1302.9	1290.7
37.5°	1354.4	1333.2	1308.9	1284.7	1275.5	1266.4	1248.2	1226.9	1208.6	1193.5	1187.4
40°	1223.9	1205.6	1184.4	1169.2	1160.1	1151.0	1135.8	1120.6	1108.4	1093.3	1087.2
42.5°	1099.3	1087.2	1069.0	1050.7	1041.6	1038.6	1020.4	1008.3	1002.2	996.1	990.1
45°	987.0	968.7	956.6	944.5	935.4	929.3	920.2	911.1	905.0	899.0	892.8
47.5°	877.6	862.5	850.3	841.2	832.1	829.1	823.0	813.8	807.8	807.8	807.8
50°	777.4	765.3	753.2	747.1	744.1	737.9	731.9	728.8	725.8	725.8	725.8
52.5°	689.4	677.3	668.2	662.1	662.1	655.9	649.9	646.8	646.8	646.8	646.8
55°	607.4	598.3	592.2	586.2	580.0	577.0	577.0	577.0	573.9	573.9	577.0
57.5°	534.5	528.4	519.3	513.3	510.1	510.1	507.1	504.2	507.1	510.1	513.3
60°	467.7	461.6	458.6	449.5	449.5	449.5	446.5	446.5	446.5	449.5	452.5
62.5°	406.9	403.9	397.8	394.8	391.8	391.8	388.7	388.7	388.7	388.7	391.8
65°	352.2	346.3	340.1	340.1	340.1	337.1	337.1	331.0	334.0	334.0	331.0
67.5°	300.7	294.6	291.6	288.5	285.5	285.5	282.5	279.4	276.4	276.4	276.4
70°	252.0	246.0	246.0	239.9	239.9	236.9	233.8	233.8	230.8	227.8	224.7
72.5°	203.5	200.5	197.3	194.3	194.3	194.3	191.3	188.2	185.2	182.2	176.1
75°	160.9	160.9	154.9	151.8	151.8	148.8	145.8	142.8	139.7	136.7	133.7
77.5°	124.6	121.5	115.5	112.3	112.3	112.3	109.3	106.3	103.2	100.2	97.2
80°	91.1	88.1	85.0	82.0	82.0	82.0	79.0	79.0	75.9	75.9	75.9
82.5°	60.8	60.8	57.7	57.7	57.7	57.7	54.7	54.7	54.7	54.7	54.7
85°	36.4	36.4	33.4	33.4	33.4	33.4	33.4	33.4	33.4	33.4	33.4
87.5°	15.2	15.2	15.2	15.2	15.2	15.2	15.2	15.2	15.2	15.2	15.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585135

CATALOG NUMBER: HCC8W60D010MW-HM86080927-81WWWB

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2137.9	2137.9	2137.9	2137.9	2137.9	2137.9	2137.9	2137.9	2137.9	2137.9	2137.9
2.5°	2128.8	2128.8	2122.8	2119.7	2116.7	2119.7	2113.7	2110.6	2107.6	2107.6	2104.6
5°	2110.6	2107.6	2095.5	2092.4	2089.4	2086.4	2080.3	2074.2	2068.2	2065.0	2062.0
7.5°	2086.4	2077.3	2065.0	2062.0	2059.0	2049.9	2040.8	2034.7	2025.6	2022.6	2016.5
10°	2052.9	2040.8	2031.7	2022.6	2016.5	2007.4	1998.3	1989.2	1977.0	1973.9	1964.8
12.5°	2013.5	1998.3	1980.0	1977.0	1967.9	1955.7	1943.6	1934.5	1925.4	1919.4	1910.3
15°	1964.8	1949.7	1931.5	1922.4	1913.3	1904.1	1888.9	1876.8	1867.7	1858.6	1849.5
17.5°	1907.1	1888.9	1873.8	1864.7	1858.6	1843.4	1831.3	1816.0	1806.9	1797.8	1788.7
20°	1837.4	1822.1	1800.9	1791.8	1788.7	1776.6	1761.4	1755.4	1743.1	1734.0	1728.0
22.5°	1758.4	1743.1	1724.9	1718.9	1706.7	1700.7	1685.5	1679.4	1673.4	1664.2	1661.1
25°	1670.2	1655.1	1639.9	1636.9	1627.8	1621.7	1612.6	1603.5	1603.5	1594.3	1594.3
27.5°	1579.2	1564.0	1551.9	1545.8	1542.8	1536.7	1527.6	1524.6	1521.4	1518.5	1518.5
30°	1482.0	1463.8	1457.7	1454.7	1451.7	1445.6	1442.6	1436.4	1439.4	1442.6	1439.4
32.5°	1378.8	1372.7	1360.6	1354.4	1357.4	1354.4	1348.4	1354.4	1351.4	1357.4	1360.6
35°	1278.5	1272.4	1266.4	1266.4	1260.3	1260.3	1260.3	1263.3	1269.4	1272.4	1278.5
37.5°	1181.3	1172.2	1169.2	1166.2	1169.2	1169.2	1169.2	1175.3	1181.3	1187.4	1196.5
40°	1078.1	1072.0	1072.0	1072.0	1072.0	1081.1	1078.1	1084.2	1090.2	1099.3	1108.4
42.5°	981.0	981.0	984.0	984.0	984.0	984.0	990.1	999.2	1008.3	1017.4	1026.5
45°	889.8	889.8	889.8	895.8	895.8	899.0	911.1	917.2	923.2	932.3	941.4
47.5°	804.7	804.7	807.8	810.8	813.8	820.0	826.1	835.2	844.3	850.3	859.4
50°	725.8	728.8	734.9	741.1	741.1	744.1	753.2	759.2	765.3	774.4	777.4
52.5°	649.9	655.9	662.1	665.1	668.2	674.2	677.3	686.4	689.4	698.5	701.5
55°	580.0	583.0	592.2	595.3	595.3	601.3	607.4	613.5	622.6	622.6	628.6
57.5°	516.3	519.3	525.4	528.4	525.4	534.5	537.5	543.6	546.6	552.7	555.7
60°	452.5	458.6	461.6	461.6	464.6	467.7	473.7	473.7	479.8	485.9	485.9
62.5°	391.8	394.8	397.8	400.9	403.9	400.9	410.0	410.0	416.0	419.1	425.1
65°	334.0	337.1	337.1	340.1	340.1	343.1	343.1	346.3	349.2	355.4	358.4
67.5°	276.4	276.4	276.4	279.4	276.4	279.4	279.4	282.5	282.5	288.5	291.6
70°	224.7	221.7	218.7	218.7	218.7	218.7	215.6	218.7	218.7	221.7	221.7
72.5°	173.1	170.0	167.0	164.0	164.0	160.9	157.9	160.9	160.9	164.0	164.0
75°	130.6	124.6	124.6	124.6	121.5	121.5	121.5	124.6	124.6	124.6	127.6
77.5°	97.2	97.2	94.1	94.1	94.1	97.2	97.2	100.2	100.2	100.2	100.2
80°	72.9	75.9	75.9	75.9	75.9	79.0	79.0	79.0	79.0	82.0	82.0
82.5°	54.7	54.7	54.7	54.7	57.7	57.7	57.7	57.7	57.7	57.7	57.7
85°	33.4	36.4	36.4	33.4	36.4	36.4	36.4	36.4	36.4	36.4	36.4
87.5°	15.2	15.2	15.2	15.2	15.2	15.2	15.2	15.2	15.2	15.2	15.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585135

CATALOG NUMBER: HCC8W60D010MW-HM86080927-81WWWB

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2137.9	2137.9	2137.9	2137.9	2137.9	2137.9	2137.9	2137.9
2.5°	2101.5	2101.5	2101.5	2101.5	2098.5	2098.5	2098.5	2095.5
5°	2055.9	2055.9	2055.9	2049.9	2052.9	2052.9	2046.8	2049.9
7.5°	2010.4	2007.4	2004.4	2004.4	2001.3	1998.3	1995.3	1998.3
10°	1958.8	1949.7	1949.7	1946.7	1946.7	1940.6	1940.6	1943.6
12.5°	1901.1	1895.0	1895.0	1892.0	1888.9	1885.9	1882.9	1882.9
15°	1843.4	1837.4	1834.3	1831.3	1828.3	1822.1	1825.1	1822.1
17.5°	1785.7	1776.6	1776.6	1773.6	1770.5	1764.5	1764.5	1761.4
20°	1718.9	1715.8	1709.8	1712.8	1709.8	1703.7	1700.7	1700.7
22.5°	1652.1	1652.1	1649.0	1649.0	1646.0	1643.0	1639.9	1639.9
25°	1588.3	1585.2	1588.3	1588.3	1579.2	1579.2	1579.2	1582.2
27.5°	1515.5	1518.5	1515.5	1515.5	1515.5	1515.5	1518.5	1515.5
30°	1442.6	1442.6	1442.6	1445.6	1451.7	1448.6	1448.6	1445.6
32.5°	1363.5	1366.5	1366.5	1369.7	1372.7	1378.8	1378.8	1381.8
35°	1284.7	1290.7	1293.8	1290.7	1299.8	1299.8	1305.9	1305.9
37.5°	1202.7	1205.6	1211.8	1214.8	1220.9	1223.9	1226.9	1226.9
40°	1114.5	1126.6	1129.8	1132.8	1141.9	1141.9	1144.9	1151.0
42.5°	1032.5	1044.7	1047.7	1050.7	1056.9	1066.0	1062.9	1069.0
45°	953.6	962.7	965.7	968.7	977.9	981.0	981.0	990.1
47.5°	868.5	874.6	877.6	883.7	889.8	895.8	902.0	899.0
50°	783.5	792.6	798.7	801.7	810.8	813.8	817.0	820.0
52.5°	707.6	713.7	716.7	719.7	728.8	731.9	734.9	741.1
55°	634.7	637.7	643.8	640.8	649.9	652.9	655.9	662.1
57.5°	561.8	564.8	567.9	567.9	573.9	580.0	583.0	586.2
60°	491.9	498.0	501.0	501.0	501.0	507.1	507.1	507.1
62.5°	428.3	428.3	431.3	431.3	437.4	437.4	437.4	437.4
65°	361.4	364.5	367.5	367.5	373.6	370.5	376.6	373.6
67.5°	291.6	291.6	297.6	297.6	294.6	297.6	297.6	297.6
70°	221.7	221.7	224.7	224.7	224.7	224.7	224.7	224.7
72.5°	164.0	164.0	164.0	167.0	164.0	164.0	167.0	164.0
75°	127.6	127.6	127.6	127.6	127.6	127.6	127.6	127.6
77.5°	100.2	100.2	103.2	103.2	103.2	103.2	103.2	103.2
80°	82.0	82.0	82.0	82.0	85.0	82.0	82.0	82.0
82.5°	60.8	57.7	60.8	57.7	60.8	60.8	60.8	60.8
85°	36.4	36.4	36.4	36.4	36.4	36.4	36.4	36.4
87.5°	15.2	15.2	15.2	15.2	15.2	15.2	15.2	15.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)