

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585144

Luminaire Tested: **HCC8W60D010SL-HM86080930-81RWWH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585144  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-15)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W60D010SL-HM86080930-81RWWH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4496.2 lumens  
Efficiency: N/A  
Efficacy: 80.3 lumens/watt  
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.16  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 56  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585144  
CATALOG NUMBER: HCC8W60D010SL-HM86080930-81RWWH

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585144

CATALOG NUMBER: HCC8W60D010SL-HM86080930-81RWWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77					77			
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67					67			
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59					59			
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52					52			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47					47			
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42					42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38					38			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36	35					35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32					32			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	73958	73958	73958
5°	75345	73637	71925
10°	76523	72350	69297
15°	77291	70549	66297
20°	76998	67826	63238
25°	74965	63911	59709
30°	71399	59246	56241
35°	64473	54072	52239
40°	56641	48530	48401
45°	48895	42658	44499
50°	42561	37414	39909
55°	37741	32499	34768
60°	33673	27457	28857
65°	30353	22291	22765
70°	26958	16698	13479
75°	23233	9674	5814
80°	17882	3463	1740
85°	11499	1132	1132



TEST NUMBER: P585144  
 CATALOG NUMBER: HCC8W60D010SL-HM86080930-81RWWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	225.1	5.0
10°-20°	626.8	13.9
20°-30°	886.5	19.7
30°-40°	934.1	20.8
40°-50°	793.9	17.7
50°-60°	571.7	12.7
60°-70°	329.8	7.3
70°-80°	112.8	2.5
80°-90°	15.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1738.4	38.7
0°-40°	2672.5	59.4
0°-60°	4038.1	89.8
0°-90°	4496.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4496.2	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2398	2398	2398	2398	2398	
5°	2434	2418	2379	2337	2324	233
15°	2421	2346	2210	2112	2077	682
25°	2203	2090	1878	1781	1755	1010
35°	1713	1612	1436	1384	1388	1067
45°	1121	1069	978	985	1020	871
55°	702	647	604	627	647	632
65°	416	357	306	299	312	414
75°	195	146	81	52	49	206
85°	32	20	3	3	3	44
90°	0	0	0	0	0	



TEST NUMBER: P585144

CATALOG NUMBER: HCC8W60D010SL-HM86080930-81RWWH

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	2398.4	2398.4	2398.4	2398.4	2398.4	2398.4	2398.4	2398.4	2398.4	2398.4	2398.4
2.5°	2421.1	2424.3	2421.1	2421.1	2417.9	2414.6	2411.4	2408.2	2401.6	2395.2	2395.2
5°	2434.1	2440.6	2434.1	2434.1	2424.3	2417.9	2411.4	2401.6	2388.7	2378.9	2378.9
7.5°	2443.9	2443.9	2443.9	2434.1	2427.7	2417.9	2401.6	2385.3	2369.1	2352.9	2346.4
10°	2443.9	2443.9	2440.6	2427.7	2421.1	2401.6	2385.3	2362.6	2339.9	2317.2	2310.6
12.5°	2434.1	2437.4	2430.9	2417.9	2401.6	2378.9	2356.2	2326.9	2300.9	2274.9	2261.9
15°	2421.1	2417.9	2411.4	2395.2	2375.7	2346.4	2323.6	2291.1	2255.4	2222.9	2209.9
17.5°	2388.7	2388.7	2378.9	2362.6	2336.7	2304.1	2268.4	2232.6	2193.7	2157.9	2141.6
20°	2346.4	2346.4	2333.4	2313.8	2287.9	2245.7	2206.7	2164.4	2118.9	2083.2	2066.9
22.5°	2284.7	2287.9	2271.6	2248.9	2219.6	2170.9	2131.9	2079.9	2034.4	1992.2	1979.1
25°	2203.3	2209.9	2193.7	2170.9	2131.9	2089.6	2040.9	1992.2	1940.1	1897.9	1878.4
27.5°	2109.1	2112.5	2096.2	2073.4	2034.4	1988.9	1940.1	1888.1	1839.4	1793.9	1774.4
30°	2005.2	1992.2	1985.7	1956.4	1914.2	1875.2	1819.9	1777.6	1725.7	1686.6	1663.9
32.5°	1858.9	1865.4	1845.9	1823.2	1790.7	1745.2	1699.7	1651.0	1602.2	1572.9	1556.6
35°	1712.7	1719.1	1709.5	1686.6	1651.0	1611.9	1566.4	1530.7	1488.5	1452.7	1436.4
37.5°	1560.0	1560.0	1553.4	1540.5	1514.4	1478.7	1433.2	1397.5	1361.7	1332.4	1322.7
40°	1407.1	1400.7	1397.5	1387.7	1364.9	1332.4	1303.2	1273.9	1238.2	1218.7	1205.6
42.5°	1257.7	1257.7	1251.2	1241.4	1218.7	1202.4	1173.2	1140.7	1114.6	1095.2	1095.2
45°	1121.2	1124.4	1114.6	1108.2	1095.2	1069.2	1043.3	1020.4	997.7	984.7	978.2
47.5°	1000.9	1000.9	991.2	984.7	971.7	948.9	926.2	906.7	890.4	880.7	877.5
50°	887.2	887.2	887.2	870.9	854.7	838.4	822.3	799.4	789.7	783.2	779.9
52.5°	789.7	786.5	786.5	773.5	757.2	737.7	721.5	702.0	692.3	685.7	688.9
55°	702.0	702.0	698.7	682.5	666.2	646.7	630.4	614.2	607.7	601.3	604.5
56°	666.2	666.2	663.0	649.9	630.4	614.2	594.7	578.4	568.7	572.0	572.0
57°	640.3	633.7	633.7	617.4	601.3	578.4	562.2	546.0	539.4	536.2	536.2
58°	607.7	604.5	601.3	585.0	568.7	549.2	533.0	516.7	506.9	506.9	503.7
59°	575.2	575.2	568.7	555.7	539.4	520.0	503.7	487.4	477.7	474.5	474.5
60°	546.0	549.2	539.4	526.5	513.5	490.8	471.3	458.2	448.4	445.2	445.2
61°	520.0	520.0	513.5	497.2	481.0	464.7	445.2	428.9	422.5	416.0	416.0
62°	497.2	490.8	487.4	471.3	455.0	435.5	419.3	403.0	393.2	386.7	390.0
63°	467.9	464.7	458.2	445.2	428.9	409.5	390.0	376.9	367.2	357.4	360.8
64°	445.2	442.0	432.2	419.3	403.0	383.5	364.0	351.0	344.5	334.7	331.5
65°	416.0	412.7	409.5	393.2	376.9	357.4	341.3	328.3	318.5	312.0	305.5
66°	390.0	393.2	386.7	373.7	354.2	337.9	315.2	302.2	295.7	286.0	279.5
67°	367.2	367.2	360.8	347.8	328.3	312.0	295.7	279.5	269.8	260.0	256.7
67.5°	354.2	354.2	347.8	331.5	318.5	299.0	282.7	269.8	256.7	250.3	243.7
68°	341.3	341.3	337.9	325.0	308.8	289.3	273.0	256.7	243.7	234.0	230.8
69°	318.5	321.7	315.2	302.2	286.0	266.4	250.3	237.3	224.2	214.5	208.0
70°	299.0	295.7	289.3	276.2	260.0	246.9	230.8	214.5	201.5	188.5	185.2
71°	273.0	273.0	266.4	256.7	240.5	224.2	208.0	195.0	182.0	165.7	162.5
72°	253.5	253.5	246.9	234.0	221.0	204.7	188.5	172.2	162.5	146.3	139.8
72.5°	240.5	243.7	237.3	224.2	211.2	191.7	178.8	165.7	149.5	136.4	130.0
73°	234.0	230.8	227.5	214.5	198.3	185.2	169.0	155.9	139.8	126.8	120.3



TEST NUMBER: P585144  
 CATALOG NUMBER: HCC8W60D010SL-HM86080930-81RWWH

**CANDELA DISTRIBUTION (continued):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
77.5°	146.3	146.3	143.0	130.0	117.0	104.0	91.0	78.0	65.1	52.0	45.4
80°	100.7	104.0	97.5	91.0	81.2	68.3	55.2	45.4	32.5	26.0	19.5
82.5°	65.1	65.1	61.7	55.2	48.8	39.0	32.5	22.7	16.3	13.0	9.8
85°	32.5	35.8	32.5	29.3	22.7	19.5	16.3	9.8	6.5	3.2	3.2
87.5°	13.0	13.0	13.0	9.8	9.8	6.5	3.2	3.2	3.2	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585144

CATALOG NUMBER: HCC8W60D010SL-HM86080930-81RWWH

**CANDELA DISTRIBUTION (continued):**

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	2398.4	2398.4	2398.4	2398.4	2398.4	2398.4	2398.4	2398.4	2398.4	2398.4
2.5°	2388.7	2388.7	2382.1	2378.9	2375.7	2372.4	2369.1	2365.9	2365.9	2369.1
5°	2369.1	2362.6	2349.6	2346.4	2336.7	2333.4	2326.9	2323.6	2326.9	2323.6
7.5°	2339.9	2326.9	2310.6	2304.1	2291.1	2284.7	2274.9	2274.9	2268.4	2271.6
10°	2300.9	2281.4	2261.9	2248.9	2239.1	2229.4	2222.9	2216.4	2213.1	2213.1
12.5°	2252.1	2229.4	2209.9	2190.4	2174.2	2167.7	2154.7	2154.7	2148.1	2144.9
15°	2196.9	2167.7	2144.9	2125.4	2112.5	2099.4	2089.6	2083.2	2076.7	2076.7
17.5°	2125.4	2099.4	2076.7	2053.9	2034.4	2024.7	2014.9	2005.2	2005.2	1998.6
20°	2047.4	2018.1	1998.6	1975.9	1959.6	1943.4	1930.4	1930.4	1923.9	1927.1
22.5°	1959.6	1923.9	1904.4	1888.1	1871.9	1858.9	1845.9	1845.9	1842.7	1839.4
25°	1862.2	1832.9	1810.1	1790.7	1781.0	1767.9	1764.7	1758.1	1754.9	1754.9
27.5°	1758.1	1735.4	1706.2	1696.4	1683.4	1676.9	1676.9	1673.7	1667.1	1670.5
30°	1647.6	1621.7	1605.4	1599.0	1585.9	1585.9	1582.7	1576.1	1576.1	1579.5
32.5°	1540.5	1514.4	1501.4	1498.2	1485.2	1485.2	1481.9	1485.2	1485.2	1488.5
35°	1423.4	1400.7	1397.5	1387.7	1384.4	1384.4	1384.4	1390.9	1397.5	1387.7
37.5°	1312.9	1296.7	1287.0	1283.7	1287.0	1287.0	1290.2	1299.9	1296.7	1293.4
40°	1199.2	1186.2	1179.7	1179.7	1186.2	1192.7	1192.7	1202.4	1205.6	1202.4
42.5°	1085.5	1075.7	1075.7	1079.0	1085.5	1088.7	1098.5	1108.2	1111.4	1114.6
45°	978.2	978.2	978.2	981.4	984.7	991.2	1004.2	1014.0	1017.2	1020.4
47.5°	874.2	870.9	880.7	884.0	893.7	897.0	906.7	919.7	923.0	926.2
50°	776.7	783.2	786.5	796.2	802.8	802.8	815.7	822.3	831.9	831.9
52.5°	685.7	695.5	698.7	708.4	711.8	715.0	721.5	731.3	737.7	737.7
55°	604.5	607.7	614.2	617.4	627.2	630.4	637.0	640.3	649.9	646.7
56°	568.7	575.2	578.4	585.0	591.5	594.7	601.3	604.5	611.0	614.2
57°	536.2	539.4	549.2	552.5	558.9	558.9	562.2	572.0	572.0	575.2
58°	503.7	510.3	513.5	516.7	523.2	526.5	533.0	536.2	539.4	536.2
59°	474.5	477.7	481.0	481.0	487.4	487.4	497.2	503.7	506.9	506.9
60°	445.2	445.2	448.4	451.7	458.2	461.5	461.5	467.9	467.9	467.9
61°	416.0	416.0	419.3	422.5	425.7	425.7	432.2	432.2	435.5	438.8
62°	390.0	386.7	386.7	390.0	390.0	396.4	399.8	403.0	406.2	403.0
63°	360.8	357.4	357.4	357.4	357.4	364.0	364.0	367.2	373.7	370.5
64°	328.3	328.3	328.3	328.3	331.5	331.5	337.9	341.3	344.5	347.8
65°	305.5	299.0	295.7	295.7	299.0	302.2	305.5	308.8	312.0	312.0
66°	279.5	273.0	269.8	269.8	269.8	269.8	276.2	276.2	282.7	282.7
67°	250.3	243.7	240.5	237.3	237.3	237.3	246.9	243.7	243.7	243.7
67.5°	240.5	230.8	227.5	224.2	221.0	227.5	224.2	227.5	227.5	224.2
68°	227.5	221.0	214.5	208.0	208.0	208.0	211.2	214.5	211.2	208.0
69°	201.5	198.3	188.5	182.0	178.8	182.0	178.8	182.0	178.8	182.0
70°	178.8	169.0	159.3	155.9	152.7	152.7	152.7	149.5	152.7	149.5
71°	155.9	146.3	136.4	130.0	126.8	126.8	123.5	126.8	123.5	126.8
72°	133.2	123.5	110.5	104.0	104.0	104.0	104.0	100.7	104.0	100.7
72.5°	123.5	110.5	100.7	94.2	91.0	91.0	91.0	91.0	87.8	91.0
73°	113.7	100.7	87.8	84.5	84.5	84.5	81.2	78.0	81.2	81.2





TEST NUMBER: P585144  
CATALOG NUMBER: HCC8W60D010SL-HM86080930-81RWWH

**CANDELA DISTRIBUTION (continued):**

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
77.5°	39.0	29.3	26.0	26.0	26.0	26.0	26.0	26.0	22.7	22.7
80°	16.3	13.0	9.8	9.8	9.8	9.8	9.8	9.8	9.8	9.8
82.5°	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5
85°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



74°	211.2	211.2	204.7	195.0	178.8	162.5	149.5	136.4	120.3	104.0	97.5
75°	195.0	191.7	185.2	175.5	162.5	146.3	133.2	117.0	104.0	87.8	81.2

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



74°	94.2	78.0	71.5	65.1	65.1	65.1	61.7	61.7	61.7	65.1
75°	74.7	61.7	55.2	48.8	52.0	48.8	52.0	48.8	48.8	48.8

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)