

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585160

Luminaire Tested: **HCC8W60D010MW-HM86080935-81RWWC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585160
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W60D010MW-HM86080935-81RWWC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5260.1 lumens
Efficiency: N/A
Efficacy: 93.9 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 56
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585160
CATALOG NUMBER: HCC8W60D010MW-HM86080935-81RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585160

CATALOG NUMBER: HCC8W60D010MW-HM86080935-81RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	84	82	79	77								
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67								
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59								
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	85346	85346	85346
5°	86470	84981	84183
10°	87354	84117	82842
15°	88238	82339	80685
20°	87791	79302	77484
25°	85744	74554	73550
30°	81443	69205	68942
35°	74140	63152	63709
40°	65002	56521	58606
45°	56077	50277	53818
50°	49100	44140	48745
55°	43504	37945	42912
60°	39193	31903	35554
65°	35322	25618	27231
70°	30979	18654	14994
75°	26414	9686	3956
80°	20333	2628	657
85°	13055	0	0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P585160

CATALOG NUMBER: HCC8W60D010MW-HM86080935-81RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	261.1	5.0
10°-20°	734.1	14.0
20°-30°	1041.9	19.8
30°-40°	1096.8	20.9
40°-50°	933.0	17.7
50°-60°	674.2	12.8
60°-70°	383.5	7.3
70°-80°	120.8	2.3
80°-90°	14.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2037.1	38.7
0°-40°	3133.9	59.6
0°-60°	4741.1	90.1
0°-90°	5260.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5260.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2768	2768	2768	2768	2768	
5°	2794	2779	2745	2727	2720	267
15°	2764	2694	2579	2531	2527	778
25°	2520	2394	2191	2154	2162	1154
35°	1970	1855	1678	1666	1692	1226
45°	1286	1238	1153	1182	1234	1000
55°	809	750	706	746	798	730
65°	484	418	351	347	373	480
75°	222	170	81	37	33	239
85°	37	22	0	0	0	48
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585160

CATALOG NUMBER: HCC8W60D010MW-HM86080935-81RWWC

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2767.7	2767.7	2767.7	2767.7	2767.7	2767.7	2767.7	2767.7	2767.7	2767.7	2767.7
2.5°	2782.5	2786.2	2778.8	2778.8	2786.2	2778.8	2782.5	2782.5	2778.8	2778.8	2775.1
5°	2793.5	2789.8	2789.8	2789.8	2793.5	2786.2	2782.5	2786.2	2778.8	2778.8	2778.8
7.5°	2797.2	2797.2	2793.5	2789.8	2789.8	2789.8	2786.2	2782.5	2778.8	2771.4	2767.7
10°	2789.8	2789.8	2793.5	2786.2	2786.2	2778.8	2778.8	2771.4	2771.4	2764.0	2752.9
12.5°	2782.5	2778.8	2778.8	2771.4	2771.4	2764.0	2764.0	2752.9	2749.1	2738.1	2727.0
15°	2764.0	2760.3	2752.9	2749.1	2745.4	2741.7	2734.4	2730.7	2719.6	2704.8	2693.8
17.5°	2727.0	2723.3	2719.6	2712.2	2704.8	2701.1	2697.5	2686.4	2671.6	2660.5	2642.0
20°	2675.3	2671.6	2671.6	2660.5	2656.9	2645.7	2642.0	2627.2	2616.1	2594.0	2579.2
22.5°	2605.1	2608.8	2601.4	2594.0	2586.6	2575.5	2568.2	2553.4	2534.8	2512.7	2494.2
25°	2520.1	2523.8	2516.4	2509.0	2497.9	2490.5	2483.2	2461.0	2442.4	2416.6	2394.5
27.5°	2412.9	2412.9	2412.9	2405.5	2387.1	2383.4	2376.0	2353.9	2327.9	2305.8	2283.6
30°	2287.3	2283.6	2283.6	2272.5	2265.2	2250.4	2239.2	2220.8	2202.3	2176.5	2150.6
32.5°	2135.8	2139.4	2128.4	2121.0	2109.9	2109.9	2095.2	2080.4	2058.2	2032.3	2006.5
35°	1969.5	1973.2	1965.9	1962.2	1943.6	1939.9	1936.2	1917.8	1903.0	1884.5	1855.0
37.5°	1799.5	1795.8	1792.2	1792.2	1781.1	1773.7	1766.3	1755.2	1733.0	1718.2	1703.5
40°	1614.8	1614.8	1614.8	1611.1	1607.4	1600.0	1596.3	1588.9	1574.2	1559.4	1548.2
42.5°	1448.4	1448.4	1444.7	1441.1	1433.7	1437.4	1430.0	1422.6	1407.8	1396.8	1389.4
45°	1285.9	1285.9	1285.9	1289.6	1282.2	1271.2	1271.2	1263.8	1256.4	1248.9	1237.8
47.5°	1141.8	1152.9	1145.4	1141.8	1145.4	1130.7	1130.7	1123.3	1115.9	1108.5	1093.8
50°	1023.5	1023.5	1023.5	1016.1	1012.5	1012.5	1001.4	994.0	990.3	982.9	968.2
52.5°	916.4	909.0	909.0	905.3	901.6	894.2	894.2	886.8	872.1	864.7	853.6
55°	809.2	809.2	805.5	801.8	798.2	794.5	790.8	779.7	772.3	761.2	750.2
57.5°	713.1	720.5	716.8	709.5	702.1	702.1	694.7	687.3	676.2	665.2	654.1
60°	635.5	631.8	631.8	628.1	620.8	617.1	613.4	602.3	591.2	580.2	569.1
62.5°	554.3	554.3	554.3	546.8	539.4	535.8	532.1	524.7	509.9	498.8	491.5
65°	484.1	480.4	476.7	473.0	469.3	461.9	458.2	450.9	439.7	428.6	417.5
67.5°	413.8	410.1	410.1	406.5	395.4	391.7	391.7	380.6	369.5	358.5	347.3
70°	343.6	343.6	343.6	336.2	332.5	328.8	325.1	317.8	306.7	295.6	284.5
72.5°	284.5	280.9	280.9	277.2	266.1	262.4	258.7	251.3	240.1	232.8	225.4
75°	221.7	221.7	218.0	214.3	210.6	206.9	203.2	195.8	184.8	173.7	170.0
77.5°	170.0	166.3	166.3	162.6	155.2	151.6	151.6	144.1	133.0	125.6	118.2
80°	114.5	118.2	114.5	110.8	107.2	103.5	99.8	96.1	88.7	81.3	73.9
82.5°	70.2	73.9	70.2	70.2	66.6	62.9	62.9	55.5	51.8	48.0	44.3
85°	36.9	36.9	36.9	36.9	33.2	33.2	33.2	29.5	25.8	22.1	22.1
87.5°	11.1	14.8	11.1	11.1	11.1	11.1	11.1	11.1	7.4	7.4	7.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585160

CATALOG NUMBER: HCC8W60D010MW-HM86080935-81RWWC

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2767.7	2767.7	2767.7	2767.7	2767.7	2767.7	2767.7	2767.7	2767.7	2767.7	2767.7
2.5°	2778.8	2775.1	2771.4	2771.4	2771.4	2771.4	2771.4	2767.7	2764.0	2764.0	2764.0
5°	2771.4	2771.4	2771.4	2767.7	2764.0	2764.0	2756.6	2752.9	2749.1	2745.4	2741.7
7.5°	2764.0	2756.6	2752.9	2749.1	2745.4	2745.4	2738.1	2730.7	2730.7	2723.3	2715.9
10°	2741.7	2738.1	2730.7	2723.3	2719.6	2715.9	2708.5	2697.5	2693.8	2686.4	2679.0
12.5°	2715.9	2708.5	2701.1	2686.4	2682.7	2679.0	2664.2	2653.2	2645.7	2642.0	2623.5
15°	2682.7	2667.9	2656.9	2638.3	2634.6	2627.2	2616.1	2605.1	2590.3	2579.2	2571.9
17.5°	2623.5	2608.8	2590.3	2571.9	2564.5	2564.5	2545.9	2531.1	2512.7	2505.3	2490.5
20°	2553.4	2534.8	2520.1	2497.9	2486.8	2475.8	2464.7	2442.4	2427.7	2416.6	2398.1
22.5°	2472.1	2446.1	2427.7	2405.5	2387.1	2376.0	2357.5	2339.0	2320.5	2309.5	2294.7
25°	2368.6	2346.4	2316.8	2294.7	2283.6	2268.9	2246.6	2228.1	2209.7	2191.2	2183.8
27.5°	2254.1	2224.4	2198.6	2172.8	2161.7	2150.6	2124.7	2102.5	2087.8	2069.3	2061.9
30°	2128.4	2098.8	2069.3	2047.1	2036.0	2017.5	2002.8	1976.9	1958.5	1943.6	1925.1
32.5°	1984.3	1962.2	1936.2	1903.0	1895.6	1880.8	1858.7	1847.5	1825.4	1814.3	1799.5
35°	1829.1	1814.3	1788.5	1762.6	1751.6	1744.1	1725.6	1703.5	1688.7	1677.6	1670.2
37.5°	1681.3	1662.9	1636.9	1618.5	1611.1	1600.0	1577.9	1566.8	1552.0	1544.5	1529.8
40°	1522.4	1503.9	1485.5	1474.4	1463.3	1455.9	1441.1	1430.0	1415.2	1404.1	1400.5
42.5°	1367.2	1356.2	1341.3	1326.5	1322.8	1311.8	1304.4	1293.3	1282.2	1278.5	1267.5
45°	1226.8	1215.7	1200.9	1186.2	1182.5	1175.1	1171.4	1160.3	1152.9	1152.9	1152.9
47.5°	1086.4	1075.3	1060.6	1053.2	1056.9	1042.0	1042.0	1038.3	1030.9	1030.9	1034.6
50°	960.8	945.9	942.2	934.8	927.4	920.1	923.8	912.7	912.7	920.1	916.4
52.5°	842.4	827.7	824.0	816.6	812.9	812.9	809.2	809.2	805.5	809.2	809.2
55°	735.3	724.2	716.8	709.5	705.8	705.8	705.8	702.1	698.4	705.8	709.5
57.5°	639.2	635.5	628.1	617.1	613.4	609.7	606.0	606.0	606.0	606.0	609.7
60°	554.3	546.8	539.4	528.4	528.4	524.7	521.0	517.3	517.3	517.3	517.3
62.5°	480.4	469.3	458.2	450.9	447.1	443.4	439.7	432.3	432.3	432.3	432.3
65°	406.5	395.4	388.0	380.6	373.2	373.2	365.9	362.2	354.8	351.1	343.6
67.5°	336.2	328.8	321.5	310.4	306.7	303.0	295.6	291.9	280.9	277.2	273.5
70°	273.5	262.4	255.0	247.5	243.8	236.4	229.1	221.7	214.3	206.9	199.5
72.5°	214.3	203.2	195.8	188.5	181.1	181.1	170.0	162.6	151.6	144.1	133.0
75°	158.9	147.8	140.4	129.3	125.6	121.9	110.8	103.5	92.4	81.3	73.9
77.5°	107.2	99.8	92.4	81.3	73.9	73.9	62.9	55.5	48.0	36.9	33.2
80°	66.6	59.2	51.8	44.3	44.3	36.9	33.2	25.8	18.5	14.8	11.1
82.5°	36.9	33.2	29.5	22.1	22.1	18.5	14.8	11.1	7.4	3.7	3.7
85°	18.5	14.8	11.1	11.1	7.4	7.4	7.4	3.7	3.7	0.0	0.0
87.5°	7.4	3.7	3.7	3.7	3.7	3.7	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585160

CATALOG NUMBER: HCC8W60D010MW-HM86080935-81RWWC

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2767.7	2767.7	2767.7	2767.7	2767.7	2767.7	2767.7	2767.7	2767.7	2767.7	2767.7
2.5°	2760.3	2760.3	2756.6	2756.6	2756.6	2752.9	2756.6	2752.9	2752.9	2752.9	2756.6
5°	2745.4	2738.1	2738.1	2734.4	2734.4	2730.7	2734.4	2730.7	2727.0	2723.3	2727.0
7.5°	2715.9	2708.5	2704.8	2701.1	2701.1	2701.1	2697.5	2693.8	2697.5	2686.4	2693.8
10°	2675.3	2671.6	2664.2	2660.5	2656.9	2660.5	2656.9	2649.4	2649.4	2649.4	2645.7
12.5°	2623.5	2616.1	2612.5	2608.8	2601.4	2601.4	2605.1	2597.7	2597.7	2590.3	2590.3
15°	2560.8	2553.4	2545.9	2545.9	2538.5	2538.5	2534.8	2534.8	2531.1	2527.4	2527.4
17.5°	2483.2	2472.1	2464.7	2468.4	2464.7	2461.0	2461.0	2453.6	2449.8	2453.6	2453.6
20°	2390.8	2383.4	2376.0	2379.7	2372.3	2368.6	2372.3	2361.2	2364.9	2364.9	2364.9
22.5°	2287.3	2283.6	2272.5	2272.5	2265.2	2261.5	2265.2	2265.2	2268.9	2265.2	2265.2
25°	2172.8	2165.4	2158.0	2158.0	2154.3	2150.6	2154.3	2158.0	2154.3	2158.0	2158.0
27.5°	2050.9	2039.7	2039.7	2032.3	2032.3	2036.0	2032.3	2036.0	2039.7	2039.7	2047.1
30°	1917.8	1914.1	1910.4	1906.7	1906.7	1910.4	1910.4	1910.4	1914.1	1921.4	1921.4
32.5°	1792.2	1784.8	1777.4	1777.4	1784.8	1781.1	1784.8	1784.8	1792.2	1792.2	1799.5
35°	1655.5	1655.5	1648.0	1651.8	1651.8	1651.8	1651.8	1659.2	1666.5	1670.2	1677.6
37.5°	1529.8	1518.7	1522.4	1522.4	1526.1	1522.4	1533.4	1533.4	1540.8	1540.8	1548.2
40°	1393.1	1393.1	1396.8	1393.1	1396.8	1396.8	1404.1	1411.5	1415.2	1422.6	1426.3
42.5°	1263.8	1271.2	1263.8	1267.5	1271.2	1274.9	1278.5	1282.2	1297.0	1304.4	1315.5
45°	1145.4	1149.1	1152.9	1156.6	1152.9	1160.3	1164.0	1171.4	1182.5	1186.2	1189.8
47.5°	1030.9	1034.6	1038.3	1042.0	1042.0	1049.4	1053.2	1060.6	1067.9	1071.6	1075.3
50°	920.1	927.4	931.1	931.1	934.8	942.2	949.6	949.6	957.1	968.2	971.9
52.5°	820.3	820.3	827.7	831.4	835.1	835.1	846.1	849.8	853.6	861.0	868.4
55°	709.5	720.5	724.2	724.2	731.6	739.0	742.7	746.4	746.4	761.2	761.2
57.5°	613.4	617.1	624.5	624.5	624.5	635.5	635.5	642.9	646.6	650.4	657.8
60°	517.3	524.7	524.7	528.4	524.7	532.1	535.8	543.1	546.8	550.6	554.3
62.5°	428.6	428.6	432.3	432.3	432.3	432.3	439.7	439.7	447.1	450.9	454.6
65°	343.6	343.6	343.6	343.6	343.6	343.6	343.6	343.6	347.3	347.3	354.8
67.5°	266.1	262.4	255.0	258.7	255.0	255.0	251.3	251.3	255.0	255.0	262.4
70°	192.2	188.5	181.1	181.1	177.4	173.7	170.0	166.3	162.6	162.6	162.6
72.5°	125.6	118.2	107.2	103.5	103.5	96.1	88.7	85.0	85.0	85.0	85.0
75°	62.9	55.5	48.0	44.3	44.3	36.9	40.6	36.9	36.9	36.9	36.9
77.5°	25.8	18.5	14.8	14.8	14.8	11.1	11.1	11.1	11.1	11.1	11.1
80°	7.4	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
82.5°	3.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585160

CATALOG NUMBER: HCC8W60D010MW-HM86080935-81RWWC

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2767.7	2767.7	2767.7	2767.7	2767.7	2767.7	2767.7	2767.7
2.5°	2752.9	2752.9	2745.4	2749.1	2749.1	2749.1	2749.1	2749.1
5°	2719.6	2723.3	2719.6	2723.3	2723.3	2719.6	2719.6	2719.6
7.5°	2686.4	2690.1	2686.4	2690.1	2690.1	2690.1	2686.4	2686.4
10°	2645.7	2645.7	2645.7	2645.7	2645.7	2642.0	2645.7	2645.7
12.5°	2590.3	2590.3	2590.3	2594.0	2594.0	2590.3	2590.3	2586.6
15°	2531.1	2523.8	2527.4	2531.1	2527.4	2527.4	2527.4	2527.4
17.5°	2449.8	2453.6	2449.8	2449.8	2449.8	2449.8	2453.6	2449.8
20°	2364.9	2364.9	2368.6	2364.9	2364.9	2364.9	2364.9	2361.2
22.5°	2268.9	2265.2	2265.2	2268.9	2268.9	2265.2	2268.9	2268.9
25°	2161.7	2165.4	2161.7	2161.7	2165.4	2165.4	2165.4	2161.7
27.5°	2047.1	2050.9	2054.6	2050.9	2050.9	2050.9	2054.6	2058.2
30°	1928.8	1936.2	1928.8	1928.8	1936.2	1932.5	1936.2	1936.2
32.5°	1803.2	1814.3	1806.9	1814.3	1814.3	1818.0	1814.3	1818.0
35°	1677.6	1688.7	1688.7	1688.7	1692.4	1696.1	1696.1	1692.4
37.5°	1559.4	1563.1	1563.1	1570.5	1574.2	1577.9	1577.9	1574.2
40°	1437.4	1444.7	1448.4	1448.4	1448.4	1455.9	1463.3	1455.9
42.5°	1319.1	1322.8	1326.5	1326.5	1333.9	1337.6	1341.3	1341.3
45°	1204.6	1212.0	1215.7	1219.4	1223.1	1230.4	1226.8	1234.1
47.5°	1086.4	1097.5	1101.2	1104.8	1112.2	1115.9	1119.6	1123.3
50°	979.2	986.6	986.6	994.0	1005.1	1005.1	1012.5	1016.1
52.5°	872.1	875.8	879.5	883.2	890.5	897.9	897.9	905.3
55°	768.6	772.3	772.3	776.0	779.7	794.5	798.2	798.2
57.5°	661.5	661.5	668.9	672.5	676.2	683.6	683.6	683.6
60°	558.0	561.7	561.7	565.4	569.1	576.5	580.2	576.5
62.5°	454.6	458.2	458.2	461.9	469.3	473.0	469.3	469.3
65°	358.5	362.2	362.2	365.9	373.2	373.2	369.5	373.2
67.5°	262.4	262.4	262.4	262.4	262.4	262.4	262.4	262.4
70°	166.3	162.6	158.9	162.6	162.6	162.6	158.9	166.3
72.5°	81.3	85.0	85.0	85.0	85.0	85.0	85.0	81.3
75°	36.9	36.9	33.2	33.2	33.2	36.9	36.9	33.2
77.5°	11.1	11.1	11.1	11.1	11.1	11.1	11.1	11.1
80°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)