

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585186

Luminaire Tested: **HCC8S60D010MW-HM86080940-81WWWB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585186  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S60D010MW-HM86080940-81WWWB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5395.2 lumens  
Efficiency: N/A  
Efficacy: 96.3 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 56  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585186  
CATALOG NUMBER: HCC8S60D010MW-HM86080940-81WWWB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585186

CATALOG NUMBER: HCC8S60D010MW-HM86080940-81WWWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87					87			
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75					75			
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65					65			
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57					57			
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50					50			
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45					45			
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40					40			
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37					37			
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33					33			
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30					30			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	82721	82721	82721
5°	85746	82443	79617
10°	88172	81727	76357
15°	90138	80286	72988
20°	90278	77149	70021
25°	88548	72859	67545
30°	83982	67567	64580
35°	76309	61537	61680
40°	66725	55216	58135
45°	57830	49187	54171
50°	50635	43689	49354
55°	45068	38719	44660
60°	40655	34777	39242
65°	36701	30580	34191
70°	32971	25768	25425
75°	29047	20433	19075
80°	24346	16923	18273
85°	18893	14825	16169



TEST NUMBER: P585186  
 CATALOG NUMBER: HCC8S60D010MW-HM86080940-81WWWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	253.1	4.7
10°-20°	712.8	13.2
20°-30°	1018.7	18.9
30°-40°	1082.4	20.1
40°-50°	931.9	17.3
50°-60°	696.7	12.9
60°-70°	444.4	8.2
70°-80°	202.2	3.7
80°-90°	53.1	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1984.5	36.8
0°-40°	3066.9	56.8
0°-60°	4695.5	87.0
0°-90°	5395.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5395.2	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2683	2683	2683	2683	2683	
5°	2770	2732	2663	2595	2572	265
15°	2824	2728	2515	2343	2286	795
25°	2602	2439	2141	2012	1985	1191
35°	2027	1886	1635	1593	1638	1262
45°	1326	1254	1128	1158	1242	1031
55°	838	770	720	781	831	754
65°	503	446	419	438	469	502
75°	244	210	172	156	160	259
85°	53	46	42	46	46	64
90°	0	0	0	0	0	



TEST NUMBER: P585186

CATALOG NUMBER: HCC8S60D010MW-HM86080940-81WWWB

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2682.6	2682.6	2682.6	2682.6	2682.6	2682.6	2682.6	2682.6	2682.6	2682.6	2682.6
2.5°	2732.1	2724.4	2728.3	2724.4	2728.3	2728.3	2720.6	2720.6	2720.6	2720.6	2709.2
5°	2770.1	2766.3	2766.3	2762.5	2758.7	2762.5	2758.7	2754.9	2747.3	2743.5	2732.1
7.5°	2793.1	2793.1	2793.1	2793.1	2789.3	2785.5	2781.7	2773.9	2766.3	2758.7	2751.1
10°	2815.9	2819.7	2815.9	2812.1	2808.3	2800.7	2796.9	2789.3	2777.7	2766.3	2758.7
12.5°	2827.3	2827.3	2823.5	2823.5	2815.9	2812.1	2800.7	2789.3	2777.7	2766.3	2747.3
15°	2823.5	2823.5	2819.7	2815.9	2804.5	2800.7	2793.1	2781.7	2762.5	2747.3	2728.3
17.5°	2800.7	2796.9	2789.3	2789.3	2773.9	2770.1	2762.5	2747.3	2728.3	2705.4	2682.6
20°	2751.1	2751.1	2747.3	2743.5	2728.3	2716.8	2709.2	2690.2	2675.0	2648.2	2625.4
22.5°	2682.6	2690.2	2682.6	2675.0	2655.8	2652.0	2640.6	2617.8	2594.9	2564.4	2537.7
25°	2602.5	2598.7	2594.9	2587.3	2572.1	2564.4	2549.1	2526.3	2503.5	2469.2	2438.6
27.5°	2499.6	2484.4	2484.4	2469.2	2457.7	2446.2	2438.6	2415.8	2385.3	2358.6	2320.5
30°	2358.6	2362.5	2343.4	2339.6	2320.5	2312.9	2297.7	2274.9	2248.1	2217.6	2187.2
32.5°	2206.2	2194.8	2194.8	2179.6	2164.4	2152.9	2149.0	2122.4	2099.5	2069.1	2038.5
35°	2027.1	2027.1	2015.7	2011.9	1996.7	1989.0	1977.6	1962.4	1935.6	1909.0	1886.2
37.5°	1851.9	1844.3	1840.5	1832.8	1821.3	1809.9	1809.9	1783.3	1779.5	1749.0	1718.5
40°	1657.6	1665.2	1657.6	1646.1	1642.3	1634.7	1630.9	1615.6	1604.1	1577.5	1558.5
42.5°	1493.7	1486.0	1486.0	1482.2	1467.0	1467.0	1459.4	1451.8	1432.8	1425.1	1402.2
45°	1326.1	1333.7	1322.3	1326.1	1310.7	1310.7	1310.7	1295.5	1280.3	1268.9	1253.6
47.5°	1181.2	1185.0	1185.0	1173.6	1169.8	1169.8	1162.2	1154.6	1143.1	1127.9	1116.5
50°	1055.5	1059.3	1051.7	1047.9	1040.3	1036.4	1036.4	1021.2	1013.6	998.4	990.7
52.5°	941.2	941.2	937.4	937.4	925.9	925.9	918.3	906.9	899.3	891.7	872.5
55°	838.3	838.3	834.5	830.7	830.7	819.3	815.5	804.0	796.4	781.1	769.7
57.5°	739.2	743.0	739.2	735.4	731.6	727.8	720.2	708.8	701.2	689.7	682.1
60°	659.2	659.2	655.4	651.6	643.9	640.1	636.3	628.7	617.3	609.7	598.3
62.5°	583.0	579.2	575.3	571.5	563.9	563.9	556.3	548.7	537.3	529.6	522.0
65°	503.0	503.0	499.2	499.2	495.4	487.8	484.0	480.2	464.8	461.0	445.8
67.5°	430.6	434.4	426.8	426.8	419.1	419.1	415.3	403.9	400.1	392.5	384.9
70°	365.7	365.7	365.7	361.9	354.3	350.5	346.7	339.1	335.3	327.7	320.1
72.5°	301.0	301.0	297.2	297.2	293.4	289.6	285.8	278.2	278.2	270.6	263.0
75°	243.8	243.8	240.0	236.2	232.4	232.4	228.6	224.8	217.2	213.4	209.6
77.5°	186.7	186.7	186.7	182.9	179.1	179.1	179.1	171.5	163.9	163.9	160.1
80°	137.1	137.1	133.3	133.3	129.5	129.5	129.5	125.7	121.9	118.1	114.3
82.5°	91.5	91.5	91.5	91.5	87.7	87.7	87.7	83.9	80.0	80.0	80.0
85°	53.4	53.4	53.4	53.4	49.5	49.5	49.5	49.5	49.5	45.7	45.7
87.5°	22.8	19.0	22.8	19.0	22.8	19.0	22.8	19.0	19.0	19.0	19.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585186

CATALOG NUMBER: HCC8S60D010MW-HM86080940-81WWWB

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2682.6	2682.6	2682.6	2682.6	2682.6	2682.6	2682.6	2682.6	2682.6	2682.6	2682.6
2.5°	2713.0	2709.2	2705.4	2701.6	2701.6	2697.8	2690.2	2686.4	2682.6	2678.8	2678.8
5°	2728.3	2724.4	2716.8	2709.2	2705.4	2697.8	2690.2	2682.6	2675.0	2663.4	2659.6
7.5°	2739.7	2728.3	2720.6	2705.4	2701.6	2694.0	2682.6	2671.0	2655.8	2640.6	2629.2
10°	2739.7	2724.4	2713.0	2694.0	2686.4	2678.8	2663.4	2644.4	2625.4	2610.1	2591.1
12.5°	2732.1	2713.0	2694.0	2675.0	2663.4	2652.0	2629.2	2610.1	2587.3	2564.4	2549.1
15°	2705.4	2682.6	2659.6	2636.8	2625.4	2610.1	2587.3	2560.5	2537.7	2514.9	2488.2
17.5°	2655.8	2633.0	2606.3	2579.7	2564.4	2552.9	2518.7	2499.6	2465.4	2442.4	2419.6
20°	2591.1	2564.4	2530.1	2503.5	2484.4	2473.0	2446.2	2412.0	2385.3	2351.0	2328.1
22.5°	2507.3	2473.0	2438.6	2412.0	2393.0	2377.7	2343.4	2309.1	2286.3	2255.8	2229.1
25°	2408.2	2373.9	2339.6	2301.5	2282.5	2267.2	2236.7	2206.2	2175.8	2141.4	2118.6
27.5°	2290.1	2251.9	2221.4	2187.2	2168.2	2145.2	2111.0	2080.5	2050.1	2027.1	1996.7
30°	2160.5	2118.6	2088.1	2053.9	2034.7	2015.7	1981.4	1951.0	1924.2	1897.6	1882.3
32.5°	2004.3	1973.8	1943.4	1909.0	1893.8	1882.3	1848.1	1817.5	1787.1	1764.2	1752.8
35°	1855.7	1821.3	1794.7	1764.2	1745.2	1733.8	1703.2	1676.6	1661.4	1634.7	1619.4
37.5°	1699.4	1672.8	1642.3	1611.8	1600.3	1588.9	1566.1	1539.4	1516.5	1497.5	1489.8
40°	1535.6	1512.7	1486.0	1467.0	1455.6	1444.2	1425.1	1406.0	1390.8	1371.7	1364.1
42.5°	1379.4	1364.1	1341.3	1318.5	1306.9	1303.1	1280.3	1265.0	1257.4	1249.8	1242.2
45°	1238.4	1215.6	1200.2	1185.0	1173.6	1166.0	1154.6	1143.1	1135.5	1127.9	1120.3
47.5°	1101.2	1082.1	1066.9	1055.5	1044.1	1040.3	1032.6	1021.2	1013.6	1013.6	1013.6
50°	975.4	960.2	945.0	937.4	933.6	925.9	918.3	914.5	910.7	910.7	910.7
52.5°	864.9	849.7	838.3	830.7	830.7	823.1	815.5	811.6	811.6	811.6	811.6
55°	762.1	750.6	743.0	735.4	727.8	724.0	724.0	724.0	720.2	720.2	724.0
57.5°	670.6	663.0	651.6	643.9	640.1	640.1	636.3	632.5	636.3	640.1	643.9
60°	586.8	579.2	575.3	563.9	563.9	563.9	560.1	560.1	560.1	563.9	567.7
62.5°	510.6	506.8	499.2	495.4	491.6	491.6	487.8	487.8	487.8	487.8	491.6
65°	442.0	434.4	426.8	426.8	426.8	423.0	423.0	415.3	419.1	419.1	415.3
67.5°	377.3	369.7	365.7	361.9	358.1	358.1	354.3	350.5	346.7	346.7	346.7
70°	316.3	308.6	308.6	301.0	301.0	297.2	293.4	293.4	289.6	285.8	282.0
72.5°	255.2	251.4	247.6	243.8	243.8	243.8	240.0	236.2	232.4	228.6	221.0
75°	202.0	202.0	194.3	190.5	190.5	186.7	182.9	179.1	175.3	171.5	167.7
77.5°	156.2	152.4	144.8	140.9	140.9	140.9	137.1	133.3	129.5	125.7	121.9
80°	114.3	110.5	106.7	102.9	102.9	102.9	99.1	99.1	95.3	95.3	95.3
82.5°	76.2	76.2	72.4	72.4	72.4	72.4	68.6	68.6	68.6	68.6	68.6
85°	45.7	45.7	41.9	41.9	41.9	41.9	41.9	41.9	41.9	41.9	41.9
87.5°	19.0	19.0	19.0	19.0	19.0	19.0	19.0	19.0	19.0	19.0	19.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585186

CATALOG NUMBER: HCC8S6D010MW-HM86080940-81WWWB

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2682.6	2682.6	2682.6	2682.6	2682.6	2682.6	2682.6	2682.6	2682.6	2682.6	2682.6
2.5°	2671.0	2671.0	2663.4	2659.6	2655.8	2659.6	2652.0	2648.2	2644.4	2644.4	2640.6
5°	2648.2	2644.4	2629.2	2625.4	2621.6	2617.8	2610.1	2602.5	2594.9	2591.1	2587.3
7.5°	2617.8	2606.3	2591.1	2587.3	2583.5	2572.1	2560.5	2552.9	2541.5	2537.7	2530.1
10°	2575.9	2560.5	2549.1	2537.7	2530.1	2518.7	2507.3	2495.8	2480.6	2476.8	2465.4
12.5°	2526.3	2507.3	2484.4	2480.6	2469.2	2453.9	2438.6	2427.2	2415.8	2408.2	2396.8
15°	2465.4	2446.2	2423.4	2412.0	2400.6	2389.2	2370.1	2354.8	2343.4	2331.9	2320.5
17.5°	2393.0	2370.1	2351.0	2339.6	2331.9	2312.9	2297.7	2278.7	2267.2	2255.8	2244.3
20°	2305.3	2286.3	2259.6	2248.1	2244.3	2229.1	2210.0	2202.4	2187.2	2175.8	2168.2
22.5°	2206.2	2187.2	2164.4	2156.7	2141.4	2133.8	2114.8	2107.1	2099.5	2088.1	2084.3
25°	2095.7	2076.7	2057.7	2053.9	2042.3	2034.7	2023.3	2011.9	2011.9	2000.5	2000.5
27.5°	1981.4	1962.4	1947.2	1939.4	1935.6	1928.0	1916.6	1912.8	1909.0	1905.2	1905.2
30°	1859.5	1836.7	1828.9	1825.1	1821.3	1813.7	1809.9	1802.3	1806.1	1809.9	1806.1
32.5°	1729.9	1722.3	1707.0	1699.4	1703.2	1699.4	1691.8	1699.4	1695.6	1703.2	1707.0
35°	1604.1	1596.5	1588.9	1588.9	1581.3	1581.3	1581.3	1585.1	1592.7	1596.5	1604.1
37.5°	1482.2	1470.8	1467.0	1463.2	1467.0	1467.0	1467.0	1474.6	1482.2	1489.8	1501.3
40°	1352.7	1345.1	1345.1	1345.1	1345.1	1356.5	1352.7	1360.3	1367.9	1379.4	1390.8
42.5°	1230.8	1230.8	1234.6	1234.6	1234.6	1234.6	1242.2	1253.6	1265.0	1276.5	1287.9
45°	1116.5	1116.5	1116.5	1124.1	1124.1	1127.9	1143.1	1150.7	1158.4	1169.8	1181.2
47.5°	1009.8	1009.8	1013.6	1017.4	1021.2	1028.8	1036.4	1047.9	1059.3	1066.9	1078.3
50°	910.7	914.5	922.1	929.8	929.8	933.6	945.0	952.6	960.2	971.6	975.4
52.5°	815.5	823.1	830.7	834.5	838.3	845.9	849.7	861.1	864.9	876.4	880.2
55°	727.8	731.6	743.0	746.8	746.8	754.4	762.1	769.7	781.1	781.1	788.8
57.5°	647.7	651.6	659.2	663.0	659.2	670.6	674.4	682.1	685.9	693.5	697.3
60°	567.7	575.3	579.2	579.2	583.0	586.8	594.5	594.5	602.1	609.7	609.7
62.5°	491.6	495.4	499.2	503.0	506.8	503.0	514.4	514.4	522.0	525.8	533.4
65°	419.1	423.0	423.0	426.8	426.8	430.6	430.6	434.4	438.2	445.8	449.6
67.5°	346.7	346.7	346.7	350.5	346.7	350.5	350.5	354.3	354.3	361.9	365.7
70°	282.0	278.2	274.4	274.4	274.4	274.4	270.6	274.4	274.4	278.2	278.2
72.5°	217.2	213.4	209.6	205.8	205.8	202.0	198.2	202.0	202.0	205.8	205.8
75°	163.9	156.2	156.2	156.2	152.4	152.4	152.4	156.2	156.2	156.2	160.1
77.5°	121.9	121.9	118.1	118.1	118.1	121.9	121.9	125.7	125.7	125.7	125.7
80°	91.5	95.3	95.3	95.3	95.3	99.1	99.1	99.1	99.1	102.9	102.9
82.5°	68.6	68.6	68.6	68.6	72.4	72.4	72.4	72.4	72.4	72.4	72.4
85°	41.9	45.7	45.7	41.9	45.7	45.7	45.7	45.7	45.7	45.7	45.7
87.5°	19.0	19.0	19.0	19.0	19.0	19.0	19.0	19.0	19.0	19.0	19.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585186

CATALOG NUMBER: HCC8S60D010MW-HM86080940-81WWWB

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2682.6	2682.6	2682.6	2682.6	2682.6	2682.6	2682.6	2682.6
2.5°	2636.8	2636.8	2636.8	2636.8	2633.0	2633.0	2633.0	2629.2
5°	2579.7	2579.7	2579.7	2572.1	2575.9	2575.9	2568.2	2572.1
7.5°	2522.5	2518.7	2514.9	2514.9	2511.1	2507.3	2503.5	2507.3
10°	2457.7	2446.2	2446.2	2442.4	2442.4	2434.8	2434.8	2438.6
12.5°	2385.3	2377.7	2377.7	2373.9	2370.1	2366.3	2362.5	2362.5
15°	2312.9	2305.3	2301.5	2297.7	2293.9	2286.3	2290.1	2286.3
17.5°	2240.5	2229.1	2229.1	2225.3	2221.4	2213.8	2213.8	2210.0
20°	2156.7	2152.9	2145.2	2149.0	2145.2	2137.6	2133.8	2133.8
22.5°	2072.9	2072.9	2069.1	2069.1	2065.3	2061.5	2057.7	2057.7
25°	1992.8	1989.0	1992.8	1992.8	1981.4	1981.4	1981.4	1985.2
27.5°	1901.4	1905.2	1901.4	1901.4	1901.4	1901.4	1905.2	1901.4
30°	1809.9	1809.9	1809.9	1813.7	1821.3	1817.5	1817.5	1813.7
32.5°	1710.8	1714.6	1714.6	1718.5	1722.3	1729.9	1729.9	1733.8
35°	1611.8	1619.4	1623.2	1619.4	1630.9	1630.9	1638.5	1638.5
37.5°	1508.9	1512.7	1520.3	1524.2	1531.8	1535.6	1539.4	1539.4
40°	1398.4	1413.6	1417.5	1421.3	1432.8	1432.8	1436.6	1444.2
42.5°	1295.5	1310.7	1314.6	1318.5	1326.1	1337.5	1333.7	1341.3
45°	1196.4	1208.0	1211.8	1215.6	1227.0	1230.8	1230.8	1242.2
47.5°	1089.7	1097.3	1101.2	1108.9	1116.5	1124.1	1131.7	1127.9
50°	983.0	994.5	1002.2	1006.0	1017.4	1021.2	1025.0	1028.8
52.5°	887.8	895.5	899.3	903.1	914.5	918.3	922.1	929.8
55°	796.4	800.2	807.8	804.0	815.5	819.3	823.1	830.7
57.5°	705.0	708.8	712.6	712.6	720.2	727.8	731.6	735.4
60°	617.3	624.9	628.7	628.7	628.7	636.3	636.3	636.3
62.5°	537.3	537.3	541.1	541.1	548.7	548.7	548.7	548.7
65°	453.4	457.2	461.0	461.0	468.6	464.8	472.5	468.6
67.5°	365.7	365.7	373.5	373.5	369.7	373.5	373.5	373.5
70°	278.2	278.2	282.0	282.0	282.0	282.0	282.0	282.0
72.5°	205.8	205.8	205.8	209.6	205.8	205.8	209.6	205.8
75°	160.1	160.1	160.1	160.1	160.1	160.1	160.1	160.1
77.5°	125.7	125.7	129.5	129.5	129.5	129.5	129.5	129.5
80°	102.9	102.9	102.9	102.9	106.7	102.9	102.9	102.9
82.5°	76.2	72.4	76.2	72.4	76.2	76.2	76.2	76.2
85°	45.7	45.7	45.7	45.7	45.7	45.7	45.7	45.7
87.5°	19.0	19.0	19.0	19.0	19.0	19.0	19.0	19.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)