

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585195

Luminaire Tested: **HCC8S80D010MW-HM86080827-81RWWH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585195  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-15)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S80D010MW-HM86080827-81RWWH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5763.9 lumens  
Efficiency: N/A  
Efficacy: 82.3 lumens/watt  
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.16  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 70  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585195  
CATALOG NUMBER: HCC8S80D010MW-HM86080827-81RWWH

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585195

CATALOG NUMBER: HCC8S80D010MW-HM86080827-81RWWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77					77			
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67					67			
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59					59			
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52					52			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47					47			
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42					42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38					38			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36	35					35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32					32			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	94809	94809	94809
5°	96589	94401	92206
10°	98097	92752	88838
15°	99086	90441	84988
20°	98705	86951	81070
25°	96108	81933	76544
30°	91527	75953	72093
35°	82652	69318	66969
40°	72618	62221	62047
45°	62679	54686	57045
50°	54564	47963	51163
55°	48375	41660	44574
60°	43171	35197	37004
65°	38912	28580	29186
70°	34558	21404	17284
75°	29774	12415	7446
80°	22925	4439	2220
85°	14718	1486	1486



TEST NUMBER: P585195  
 CATALOG NUMBER: HCC8S80D010MW-HM86080827-81RWWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	288.6	5.0
10°-20°	803.5	13.9
20°-30°	1136.4	19.7
30°-40°	1197.5	20.8
40°-50°	1017.7	17.7
50°-60°	732.8	12.7
60°-70°	422.8	7.3
70°-80°	144.6	2.5
80°-90°	19.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2228.6	38.7
0°-40°	3426.1	59.4
0°-60°	5176.6	89.8
0°-90°	5763.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5763.9	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	3075	3075	3075	3075	3075	
5°	3120	3100	3050	2995	2979	298
15°	3104	3008	2833	2708	2662	874
25°	2825	2679	2408	2283	2250	1295
35°	2196	2066	1841	1775	1779	1367
45°	1437	1371	1254	1262	1308	1117
55°	900	829	775	804	829	810
65°	533	458	392	383	400	530
75°	250	188	104	67	62	264
85°	42	25	4	4	4	56
90°	0	0	0	0	0	



TEST NUMBER: P585195

CATALOG NUMBER: HCC8S80D010MW-HM86080827-81RWWH

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	3074.6	3074.6	3074.6	3074.6	3074.6	3074.6	3074.6	3074.6	3074.6	3074.6	3074.6
2.5°	3103.8	3107.9	3103.8	3103.8	3099.6	3095.4	3091.3	3087.1	3078.8	3070.5	3070.5
5°	3120.4	3128.7	3120.4	3120.4	3107.9	3099.6	3091.3	3078.8	3062.2	3049.7	3049.7
7.5°	3132.9	3132.9	3132.9	3120.4	3112.1	3099.6	3078.8	3058.0	3037.1	3016.3	3007.9
10°	3132.9	3132.9	3128.7	3112.1	3103.8	3078.8	3058.0	3028.7	2999.6	2970.5	2962.2
12.5°	3120.4	3124.6	3116.3	3099.6	3078.8	3049.7	3020.4	2983.0	2949.7	2916.3	2899.6
15°	3103.8	3099.6	3091.3	3070.5	3045.5	3007.9	2978.8	2937.2	2891.3	2849.7	2833.0
17.5°	3062.2	3062.2	3049.7	3028.7	2995.4	2953.8	2907.9	2862.2	2812.1	2766.3	2745.5
20°	3007.9	3007.9	2991.3	2966.3	2933.0	2878.8	2828.9	2774.7	2716.3	2670.5	2649.7
22.5°	2928.7	2933.0	2912.1	2883.0	2845.5	2783.0	2733.0	2666.3	2608.0	2553.9	2537.2
25°	2824.7	2833.0	2812.1	2783.0	2733.0	2678.8	2616.4	2553.9	2487.2	2433.1	2408.1
27.5°	2703.8	2707.9	2687.1	2658.0	2608.0	2549.7	2487.2	2420.6	2358.0	2299.8	2274.7
30°	2570.5	2553.9	2545.5	2508.1	2453.9	2403.9	2333.1	2278.8	2212.3	2162.2	2133.1
32.5°	2383.0	2391.3	2366.3	2337.2	2295.6	2237.2	2178.8	2116.4	2053.9	2016.4	1995.6
35°	2195.6	2203.9	2191.4	2162.2	2116.4	2066.4	2008.1	1962.2	1908.1	1862.2	1841.4
37.5°	1999.8	1999.8	1991.5	1974.8	1941.4	1895.6	1837.2	1791.5	1745.6	1708.1	1695.6
40°	1804.0	1795.6	1791.5	1779.0	1749.7	1708.1	1670.7	1633.1	1587.3	1562.3	1545.7
42.5°	1612.3	1612.3	1604.0	1591.5	1562.3	1541.4	1504.0	1462.4	1428.9	1404.0	1404.0
45°	1437.3	1441.5	1428.9	1420.6	1404.0	1370.7	1337.4	1308.1	1279.0	1262.4	1254.0
47.5°	1283.2	1283.2	1270.7	1262.4	1245.7	1216.5	1187.3	1162.4	1141.6	1129.1	1124.9
50°	1137.4	1137.4	1137.4	1116.5	1095.7	1074.9	1054.0	1024.9	1012.3	1004.0	999.8
52.5°	1012.3	1008.2	1008.2	991.5	970.7	945.7	924.9	899.8	887.4	879.0	883.2
55°	899.8	899.8	895.7	874.9	854.1	829.1	808.3	787.4	779.0	770.7	774.9
56°	854.1	854.1	849.9	833.3	808.3	787.4	762.4	741.6	729.1	733.3	733.3
57°	820.8	812.4	812.4	791.5	770.7	741.6	720.8	700.0	691.5	687.4	687.4
58°	779.0	774.9	770.7	749.9	729.1	704.1	683.2	662.4	649.9	649.9	645.7
59°	737.4	737.4	729.1	712.4	691.5	666.6	645.7	624.9	612.5	608.3	608.3
60°	700.0	704.1	691.5	674.9	658.2	629.1	604.1	587.5	574.9	570.7	570.7
61°	666.6	666.6	658.2	637.4	616.6	595.8	570.7	549.9	541.6	533.3	533.3
62°	637.4	629.1	624.9	604.1	583.2	558.2	537.4	516.6	504.1	495.8	500.0
63°	600.0	595.8	587.5	570.7	549.9	524.9	500.0	483.3	470.7	458.2	462.4
64°	570.7	566.6	554.1	537.4	516.6	491.7	466.6	449.9	441.6	429.1	424.9
65°	533.3	529.1	524.9	504.1	483.3	458.2	437.4	420.8	408.3	400.0	391.7
66°	500.0	504.1	495.8	479.0	454.1	433.3	404.1	387.5	379.2	366.6	358.2
67°	470.7	470.7	462.4	445.8	420.8	400.0	379.2	358.2	345.8	333.3	329.1
67.5°	454.1	454.1	445.8	424.9	408.3	383.3	362.4	345.8	329.1	320.8	312.5
68°	437.4	437.4	433.3	416.6	395.8	370.7	349.9	329.1	312.5	300.0	295.8
69°	408.3	412.5	404.1	387.5	366.6	341.6	320.8	304.1	287.5	275.0	266.7
70°	383.3	379.2	370.7	354.1	333.3	316.6	295.8	275.0	258.3	241.6	237.4
71°	349.9	349.9	341.6	329.1	308.3	287.5	266.7	249.9	233.3	212.5	208.3
72°	325.0	325.0	316.6	300.0	283.3	262.4	241.6	220.8	208.3	187.5	179.2
72.5°	308.3	312.5	304.1	287.5	270.9	245.8	229.1	212.5	191.7	175.0	166.7
73°	300.0	295.8	291.7	275.0	254.1	237.4	216.6	200.0	179.2	162.5	154.1



TEST NUMBER: P585195  
 CATALOG NUMBER: HCC8S80D010MW-HM86080827-81RWWH

**CANDELA DISTRIBUTION (continued):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
77.5°	187.5	187.5	183.3	166.7	149.9	133.3	116.6	100.0	83.3	66.7	58.4
80°	129.1	133.3	125.0	116.6	104.2	87.5	70.9	58.4	41.6	33.3	25.0
82.5°	83.3	83.3	79.2	70.9	62.5	49.9	41.6	29.1	20.8	16.6	12.5
85°	41.6	45.8	41.6	37.5	29.1	25.0	20.8	12.5	8.3	4.2	4.2
87.5°	16.6	16.6	16.6	12.5	12.5	8.3	4.2	4.2	4.2	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585195

CATALOG NUMBER: HCC8S80D010MW-HM86080827-81RWWH

**CANDELA DISTRIBUTION (continued):**

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	3074.6	3074.6	3074.6	3074.6	3074.6	3074.6	3074.6	3074.6	3074.6	3074.6
2.5°	3062.2	3062.2	3053.8	3049.7	3045.5	3041.3	3037.1	3032.9	3032.9	3037.1
5°	3037.1	3028.7	3012.1	3007.9	2995.4	2991.3	2983.0	2978.8	2983.0	2978.8
7.5°	2999.6	2983.0	2962.2	2953.8	2937.2	2928.7	2916.3	2916.3	2907.9	2912.1
10°	2949.7	2924.6	2899.6	2883.0	2870.5	2858.0	2849.7	2841.4	2837.2	2837.2
12.5°	2887.1	2858.0	2833.0	2807.9	2787.1	2778.8	2762.2	2762.2	2753.8	2749.7
15°	2816.3	2778.8	2749.7	2724.7	2707.9	2691.3	2678.8	2670.5	2662.2	2662.2
17.5°	2724.7	2691.3	2662.2	2633.0	2608.0	2595.5	2583.0	2570.5	2570.5	2562.2
20°	2624.7	2587.1	2562.2	2533.0	2512.2	2491.3	2474.7	2474.7	2466.3	2470.5
22.5°	2512.2	2466.3	2441.4	2420.6	2399.8	2383.0	2366.3	2366.3	2362.2	2358.0
25°	2387.2	2349.7	2320.6	2295.6	2283.0	2266.4	2262.2	2253.9	2249.7	2249.7
27.5°	2253.9	2224.7	2187.3	2174.7	2158.0	2149.7	2149.7	2145.6	2137.2	2141.4
30°	2112.3	2079.0	2058.0	2049.7	2033.1	2033.1	2028.9	2020.6	2020.6	2024.7
32.5°	1974.8	1941.4	1924.8	1920.6	1903.9	1903.9	1899.8	1903.9	1903.9	1908.1
35°	1824.8	1795.6	1791.5	1779.0	1774.8	1774.8	1774.8	1783.1	1791.5	1779.0
37.5°	1683.1	1662.3	1649.7	1645.6	1649.7	1649.7	1654.0	1666.5	1662.3	1658.2
40°	1537.3	1520.6	1512.3	1512.3	1520.6	1528.9	1528.9	1541.4	1545.7	1541.4
42.5°	1391.5	1379.0	1379.0	1383.2	1391.5	1395.6	1408.1	1420.6	1424.8	1428.9
45°	1254.0	1254.0	1254.0	1258.2	1262.4	1270.7	1287.3	1299.8	1304.0	1308.1
47.5°	1120.8	1116.5	1129.1	1133.2	1145.7	1149.9	1162.4	1179.0	1183.2	1187.3
50°	995.7	1004.0	1008.2	1020.8	1029.1	1029.1	1045.7	1054.0	1066.5	1066.5
52.5°	879.0	891.5	895.7	908.3	912.4	916.6	924.9	937.4	945.7	945.7
55°	774.9	779.0	787.4	791.5	804.1	808.3	816.6	820.8	833.3	829.1
56°	729.1	737.4	741.6	749.9	758.2	762.4	770.7	774.9	783.2	787.4
57°	687.4	691.5	704.1	708.3	716.6	716.6	720.8	733.3	733.3	737.4
58°	645.7	654.1	658.2	662.4	670.7	674.9	683.2	687.4	691.5	687.4
59°	608.3	612.5	616.6	616.6	624.9	624.9	637.4	645.7	649.9	649.9
60°	570.7	570.7	574.9	579.0	587.5	591.6	591.6	600.0	600.0	600.0
61°	533.3	533.3	537.4	541.6	545.8	545.8	554.1	554.1	558.2	562.4
62°	500.0	495.8	495.8	500.0	500.0	508.3	512.5	516.6	520.8	516.6
63°	462.4	458.2	458.2	458.2	458.2	466.6	466.6	470.7	479.0	474.9
64°	420.8	420.8	420.8	420.8	424.9	424.9	433.3	437.4	441.6	445.8
65°	391.7	383.3	379.2	379.2	383.3	387.5	391.7	395.8	400.0	400.0
66°	358.2	349.9	345.8	345.8	345.8	345.8	354.1	354.1	362.4	362.4
67°	320.8	312.5	308.3	304.1	304.1	304.1	316.6	312.5	312.5	312.5
67.5°	308.3	295.8	291.7	287.5	283.3	291.7	287.5	291.7	291.7	287.5
68°	291.7	283.3	275.0	266.7	266.7	266.7	270.9	275.0	270.9	266.7
69°	258.3	254.1	241.6	233.3	229.1	233.3	229.1	233.3	229.1	233.3
70°	229.1	216.6	204.2	200.0	195.8	195.8	195.8	191.7	195.8	191.7
71°	200.0	187.5	175.0	166.7	162.5	162.5	158.3	162.5	158.3	162.5
72°	170.9	158.3	141.6	133.3	133.3	133.3	133.3	129.1	133.3	129.1
72.5°	158.3	141.6	129.1	120.8	116.6	116.6	116.6	116.6	112.5	116.6
73°	145.8	129.1	112.5	108.3	108.3	108.3	104.2	100.0	104.2	104.2





TEST NUMBER: P585195  
CATALOG NUMBER: HCC8S80D010MW-HM86080827-81RWWH

**CANDELA DISTRIBUTION (continued):**

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
77.5°	49.9	37.5	33.3	33.3	33.3	33.3	33.3	33.3	29.1	29.1
80°	20.8	16.6	12.5	12.5	12.5	12.5	12.5	12.5	12.5	12.5
82.5°	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.3
85°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



74°	270.9	270.9	262.4	249.9	229.1	208.3	191.7	175.0	154.1	133.3	125.0
75°	249.9	245.8	237.4	225.0	208.3	187.5	170.9	149.9	133.3	112.5	104.2

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



74°	120.8	100.0	91.7	83.3	83.3	83.3	79.2	79.2	79.2	83.3
75°	95.8	79.2	70.9	62.5	66.7	62.5	66.7	62.5	62.5	62.5

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)