

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585219

Luminaire Tested: **HCC8S80D010MB-HM86080830-81WWW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585219
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S80D010MB-HM86080830-81WWW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5622.9 lumens
Efficiency: N/A
Efficacy: 80.3 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 70
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585219
CATALOG NUMBER: HCC8S80D010MB-HM86080830-81WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585219

CATALOG NUMBER: HCC8S80D010MB-HM86080830-81WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	93952	93952	93952
5°	97252	93413	89702
10°	99413	91776	84658
15°	100826	88688	79054
20°	100523	84378	73391
25°	98037	78905	67375
30°	92880	72570	61824
35°	84500	65670	56180
40°	74220	58413	50756
45°	64720	51380	45249
50°	56320	45022	39865
55°	50229	39563	34671
60°	45638	34679	29572
65°	41028	30164	26844
70°	36524	25713	24226
75°	32014	21672	20683
80°	27152	17616	18344
85°	20485	13162	14648



TEST NUMBER: P585219
 CATALOG NUMBER: HCC8S80D010MB-HM86080830-81WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	285.4	5.1
10°-20°	786.3	14.0
20°-30°	1091.4	19.4
30°-40°	1128.5	20.1
40°-50°	944.9	16.8
50°-60°	685.9	12.2
60°-70°	432.9	7.7
70°-80°	214.4	3.8
80°-90°	53.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2163.1	38.5
0°-40°	3291.6	58.5
0°-60°	4922.4	87.5
0°-90°	5622.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5622.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	3047	3047	3047	3047	3047	
5°	3142	3105	3018	2935	2898	301
15°	3158	3038	2778	2555	2476	889
25°	2881	2695	2319	2067	1980	1320
35°	2245	2079	1744	1546	1492	1398
45°	1484	1377	1178	1062	1038	1148
55°	934	852	736	674	645	843
65°	562	492	413	364	368	561
75°	269	223	182	174	174	288
85°	58	45	37	41	41	70
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585219

CATALOG NUMBER: HCC8S80D010MB-HM86080830-81WWW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	3046.8	3046.8	3046.8	3046.8	3046.8	3046.8	3046.8	3046.8	3046.8	3046.8	3046.8
2.5°	3096.4	3096.4	3100.6	3096.4	3096.4	3096.4	3092.2	3092.2	3088.1	3088.1	3079.9
5°	3141.8	3133.6	3141.8	3133.6	3133.6	3133.6	3129.4	3121.1	3117.1	3108.8	3104.6
7.5°	3162.5	3158.3	3158.3	3154.3	3154.3	3150.1	3146.0	3141.8	3125.3	3121.1	3108.8
10°	3174.9	3170.8	3170.8	3166.7	3158.3	3158.3	3150.1	3146.0	3125.3	3117.1	3100.6
12.5°	3170.8	3170.8	3170.8	3166.7	3154.3	3150.1	3141.8	3129.4	3112.9	3096.4	3079.9
15°	3158.3	3158.3	3150.1	3146.0	3133.6	3125.3	3121.1	3100.6	3084.0	3063.3	3038.5
17.5°	3117.1	3117.1	3112.9	3104.6	3092.2	3084.0	3075.7	3055.0	3038.5	3005.4	2980.6
20°	3063.3	3059.2	3055.0	3042.7	3030.3	3026.1	3013.8	2984.7	2964.1	2939.3	2906.3
22.5°	2984.7	2980.6	2976.5	2968.2	2947.5	2939.3	2931.0	2910.3	2873.1	2848.4	2807.0
25°	2881.4	2881.4	2873.1	2860.7	2840.0	2831.8	2819.4	2798.8	2765.6	2728.4	2695.3
27.5°	2761.6	2757.4	2745.0	2736.7	2720.2	2707.8	2687.1	2662.3	2629.2	2600.3	2559.0
30°	2608.5	2608.5	2600.3	2587.9	2567.2	2559.0	2542.4	2513.4	2480.4	2443.2	2414.3
32.5°	2435.0	2435.0	2422.6	2414.3	2401.9	2381.2	2377.0	2344.0	2315.1	2286.1	2253.0
35°	2244.7	2248.9	2240.7	2224.1	2203.5	2203.5	2195.1	2166.2	2133.2	2104.2	2079.4
37.5°	2054.6	2042.2	2038.1	2029.9	2017.4	2000.8	1992.6	1980.2	1951.3	1930.6	1893.4
40°	1843.8	1847.9	1839.6	1831.4	1827.3	1814.9	1810.7	1790.0	1769.4	1744.5	1728.0
42.5°	1653.7	1653.7	1653.7	1645.3	1637.0	1624.6	1620.5	1608.1	1583.3	1566.7	1542.0
45°	1484.1	1471.7	1471.7	1467.6	1463.4	1455.2	1442.7	1434.5	1418.0	1405.5	1376.6
47.5°	1318.7	1322.9	1318.7	1314.6	1302.2	1298.0	1294.0	1277.5	1260.9	1248.4	1227.8
50°	1174.0	1182.3	1174.0	1174.0	1165.8	1161.7	1153.4	1141.0	1128.6	1107.9	1087.2
52.5°	1054.2	1054.2	1050.0	1046.0	1033.5	1025.3	1021.1	1017.0	996.3	979.7	963.2
55°	934.3	938.5	938.5	926.0	921.8	913.6	909.5	897.1	888.8	864.0	851.6
57.5°	831.0	826.8	831.0	822.7	814.3	806.1	802.0	793.8	781.3	764.8	748.2
60°	740.0	731.7	731.7	727.5	719.3	715.2	706.9	694.5	682.1	665.6	653.1
62.5°	649.1	644.9	640.8	636.6	628.4	624.2	620.1	607.7	595.3	582.8	570.5
65°	562.3	562.3	558.1	549.8	545.6	541.6	537.4	529.1	512.6	504.4	491.9
67.5°	483.7	479.5	479.5	471.3	463.0	458.8	458.8	450.6	438.1	425.8	417.6
70°	405.1	409.3	405.1	401.0	392.7	392.7	384.5	380.4	363.8	359.7	347.3
72.5°	334.8	334.8	330.8	330.8	322.5	318.3	318.3	310.1	301.8	293.6	285.2
75°	268.7	268.7	268.7	264.6	260.4	252.2	252.2	248.0	239.8	231.5	223.3
77.5°	210.8	206.6	206.6	202.6	198.4	194.3	194.3	190.1	181.9	177.8	169.6
80°	152.9	148.9	148.9	148.9	140.5	144.7	140.5	136.4	132.3	128.2	124.0
82.5°	99.2	103.3	103.3	99.2	95.1	95.1	95.1	91.0	91.0	86.8	82.6
85°	57.9	57.9	57.9	57.9	53.7	53.7	53.7	49.6	49.6	49.6	45.4
87.5°	24.9	24.9	24.9	24.9	24.9	24.9	20.7	20.7	20.7	20.7	20.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585219

CATALOG NUMBER: HCC8S80D010MB-HM86080830-81WWW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	3046.8	3046.8	3046.8	3046.8	3046.8	3046.8	3046.8	3046.8	3046.8	3046.8	3046.8
2.5°	3079.9	3071.5	3067.4	3063.3	3063.3	3059.2	3055.0	3046.8	3046.8	3038.5	3034.3
5°	3096.4	3084.0	3075.7	3067.4	3063.3	3055.0	3046.8	3034.3	3030.3	3017.8	3005.4
7.5°	3100.6	3079.9	3071.5	3055.0	3046.8	3038.5	3022.0	3009.6	2993.1	2980.6	2964.1
10°	3084.0	3067.4	3046.8	3026.1	3022.0	3009.6	2984.7	2968.2	2947.5	2931.0	2906.3
12.5°	3059.2	3034.3	3013.8	2988.9	2976.5	2964.1	2939.3	2914.5	2885.6	2856.6	2831.8
15°	3017.8	2988.9	2960.0	2931.0	2914.5	2902.1	2873.1	2844.2	2815.3	2778.1	2753.2
17.5°	2955.9	2922.8	2893.8	2856.6	2840.0	2827.7	2790.5	2757.4	2720.2	2683.0	2658.1
20°	2877.3	2835.9	2802.8	2761.6	2749.1	2728.4	2691.3	2654.1	2612.7	2571.3	2542.4
22.5°	2773.9	2732.6	2695.3	2654.1	2633.4	2612.7	2575.5	2530.1	2488.7	2455.6	2426.6
25°	2654.1	2616.9	2571.3	2534.1	2509.4	2484.5	2443.2	2405.9	2368.8	2319.1	2290.3
27.5°	2521.8	2476.3	2443.2	2393.6	2368.8	2352.2	2306.8	2257.2	2224.1	2178.6	2145.6
30°	2372.9	2331.6	2294.4	2244.7	2220.0	2203.5	2162.1	2116.7	2083.6	2038.1	2005.0
32.5°	2215.8	2170.4	2124.9	2091.8	2062.9	2046.4	2000.8	1972.0	1930.6	1893.4	1856.1
35°	2046.4	2000.8	1967.8	1922.4	1905.7	1889.2	1852.0	1814.9	1777.7	1744.5	1715.6
37.5°	1864.5	1831.4	1794.2	1761.1	1748.7	1732.1	1686.7	1653.7	1624.6	1591.6	1566.7
40°	1686.7	1657.7	1633.0	1599.9	1579.2	1566.7	1533.7	1504.8	1471.7	1451.1	1426.2
42.5°	1525.5	1492.4	1467.6	1442.7	1422.0	1409.7	1380.8	1360.1	1335.2	1314.6	1285.7
45°	1355.9	1339.4	1310.5	1289.8	1277.5	1260.9	1240.2	1215.4	1194.7	1178.2	1157.5
47.5°	1207.2	1190.5	1170.0	1145.1	1136.8	1124.4	1103.7	1087.2	1070.7	1054.2	1033.5
50°	1070.7	1050.0	1033.5	1017.0	1008.7	996.3	975.6	967.4	955.0	938.5	926.0
52.5°	946.7	930.2	913.6	892.9	888.8	880.6	868.1	851.6	839.2	831.0	822.7
55°	835.0	818.5	806.1	789.6	785.5	777.2	760.6	752.4	744.1	735.9	727.5
57.5°	735.9	719.3	702.8	694.5	686.3	678.0	673.8	661.4	653.1	649.1	640.8
60°	644.9	628.4	616.0	603.5	599.4	595.3	587.0	578.8	570.5	562.3	558.1
62.5°	558.1	541.6	533.3	525.1	516.7	516.7	508.5	500.2	491.9	487.8	479.5
65°	479.5	471.3	458.8	446.5	442.3	442.3	429.9	425.8	421.6	413.4	405.1
67.5°	405.1	396.9	384.5	380.4	376.2	372.0	367.9	359.7	351.3	347.3	339.0
70°	339.0	330.8	322.5	318.3	314.1	310.1	301.8	297.6	289.4	285.2	281.1
72.5°	272.9	268.7	260.4	256.3	252.2	248.0	243.9	239.8	231.5	227.3	223.3
75°	219.1	215.0	206.6	202.6	198.4	198.4	194.3	186.1	181.9	181.9	177.8
77.5°	165.4	161.2	157.1	152.9	148.9	148.9	144.7	140.5	136.4	136.4	132.3
80°	119.9	115.8	111.6	111.6	111.6	107.5	103.3	103.3	99.2	99.2	95.1
82.5°	78.6	78.6	74.4	74.4	74.4	70.3	70.3	66.1	66.1	66.1	66.1
85°	45.4	45.4	45.4	41.4	41.4	41.4	41.4	41.4	41.4	37.2	41.4
87.5°	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7	16.5	16.5	16.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585219

CATALOG NUMBER: HCC8S80D010MB-HM86080830-81WWW

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	3046.8	3046.8	3046.8	3046.8	3046.8	3046.8	3046.8	3046.8	3046.8	3046.8	3046.8
2.5°	3030.3	3026.1	3017.8	3017.8	3009.6	3009.6	3005.4	3001.3	2997.1	2993.1	2988.9
5°	3001.3	2984.7	2976.5	2972.4	2964.1	2960.0	2947.5	2939.3	2935.2	2926.8	2918.6
7.5°	2947.5	2931.0	2914.5	2910.3	2906.3	2889.6	2877.3	2864.9	2856.6	2848.4	2840.0
10°	2885.6	2869.1	2848.4	2840.0	2831.8	2811.2	2794.6	2782.1	2765.6	2749.1	2745.0
12.5°	2811.2	2786.3	2761.6	2753.2	2740.9	2720.2	2703.7	2683.0	2670.6	2649.9	2645.8
15°	2724.4	2695.3	2674.7	2654.1	2645.8	2625.1	2596.2	2579.7	2554.8	2546.6	2525.9
17.5°	2620.9	2592.0	2563.1	2554.8	2542.4	2513.4	2484.5	2463.8	2439.1	2426.6	2414.3
20°	2513.4	2476.3	2447.3	2439.1	2422.6	2397.7	2368.8	2348.2	2327.5	2302.6	2290.3
22.5°	2389.4	2348.2	2323.3	2302.6	2298.5	2269.6	2236.5	2220.0	2203.5	2182.8	2166.2
25°	2253.0	2215.8	2186.9	2170.4	2162.1	2137.3	2112.5	2091.8	2067.0	2054.6	2033.9
27.5°	2112.5	2087.6	2050.4	2033.9	2021.5	2000.8	1972.0	1959.5	1934.7	1918.2	1905.7
30°	1976.1	1938.9	1918.2	1897.5	1885.2	1864.5	1839.6	1827.3	1806.6	1790.0	1777.7
32.5°	1827.3	1802.4	1773.5	1765.2	1748.7	1728.0	1711.4	1690.8	1674.2	1657.7	1653.7
35°	1690.8	1657.7	1628.8	1620.5	1608.1	1587.4	1579.2	1566.7	1546.2	1542.0	1525.5
37.5°	1542.0	1525.5	1492.4	1479.9	1475.8	1459.3	1442.7	1434.5	1422.0	1409.7	1405.5
40°	1401.5	1380.8	1364.3	1351.8	1343.6	1331.2	1314.6	1310.5	1302.2	1285.7	1281.5
42.5°	1269.1	1248.4	1231.9	1227.8	1215.4	1203.0	1194.7	1182.3	1178.2	1174.0	1165.8
45°	1141.0	1128.6	1112.1	1107.9	1103.7	1087.2	1079.0	1070.7	1062.5	1058.3	1050.0
47.5°	1025.3	1012.8	1000.4	996.3	988.1	983.9	971.5	967.4	955.0	950.8	946.7
50°	913.6	905.3	897.1	892.9	884.7	880.6	872.3	864.0	855.7	851.6	847.5
52.5°	814.3	806.1	797.8	793.8	789.6	781.3	773.1	764.8	760.6	756.6	752.4
55°	719.3	711.0	706.9	702.8	698.7	694.5	682.1	678.0	673.8	669.8	661.4
57.5°	632.5	624.2	616.0	616.0	611.9	607.7	599.4	591.2	591.2	582.8	574.6
60°	554.0	545.6	537.4	533.3	529.1	520.9	516.7	512.6	508.5	504.4	496.1
62.5°	471.3	467.2	458.8	458.8	450.6	446.5	442.3	438.1	434.1	425.8	421.6
65°	401.0	396.9	388.6	384.5	384.5	380.4	372.0	367.9	363.8	363.8	359.7
67.5°	334.8	330.8	322.5	318.3	318.3	314.1	310.1	310.1	305.9	301.8	305.9
70°	277.0	268.7	268.7	264.6	264.6	260.4	256.3	256.3	256.3	260.4	260.4
72.5°	219.1	215.0	210.8	210.8	210.8	210.8	206.6	206.6	210.8	215.0	215.0
75°	173.6	169.6	169.6	169.6	165.4	165.4	169.6	169.6	173.6	173.6	173.6
77.5°	128.2	128.2	128.2	128.2	128.2	128.2	132.3	132.3	136.4	136.4	136.4
80°	95.1	95.1	95.1	95.1	95.1	99.2	99.2	99.2	99.2	99.2	103.3
82.5°	66.1	66.1	66.1	66.1	66.1	66.1	66.1	70.3	70.3	70.3	70.3
85°	37.2	41.4	41.4	41.4	41.4	41.4	41.4	41.4	41.4	41.4	41.4
87.5°	16.5	16.5	16.5	16.5	16.5	16.5	16.5	16.5	16.5	16.5	16.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585219

CATALOG NUMBER: HCC8S80D010MB-HM86080830-81WWW

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	3046.8	3046.8	3046.8	3046.8	3046.8	3046.8	3046.8	3046.8
2.5°	2984.7	2984.7	2984.7	2988.9	2980.6	2980.6	2980.6	2980.6
5°	2914.5	2910.3	2906.3	2910.3	2902.1	2902.1	2897.9	2897.9
7.5°	2827.7	2823.5	2819.4	2819.4	2811.2	2811.2	2807.0	2802.8
10°	2732.6	2724.4	2728.4	2720.2	2716.0	2711.9	2707.8	2703.7
12.5°	2629.2	2620.9	2616.9	2608.5	2600.3	2596.2	2600.3	2592.0
15°	2517.6	2505.2	2501.1	2492.9	2484.5	2480.4	2480.4	2476.3
17.5°	2393.6	2385.4	2381.2	2372.9	2368.8	2360.5	2356.4	2352.2
20°	2277.9	2257.2	2261.4	2253.0	2248.9	2232.3	2232.3	2236.5
22.5°	2149.7	2137.3	2129.0	2120.7	2116.7	2108.3	2108.3	2104.2
25°	2021.5	2009.2	2005.0	1996.7	1992.6	1984.3	1980.2	1980.2
27.5°	1897.5	1881.0	1881.0	1872.7	1864.5	1860.3	1856.1	1852.0
30°	1765.2	1752.8	1748.7	1748.7	1744.5	1744.5	1732.1	1736.3
32.5°	1641.2	1633.0	1628.8	1620.5	1620.5	1616.4	1616.4	1604.0
35°	1517.2	1504.8	1509.0	1500.6	1496.5	1492.4	1496.5	1492.4
37.5°	1397.3	1389.0	1389.0	1380.8	1380.8	1376.6	1372.5	1380.8
40°	1277.5	1273.3	1269.1	1265.0	1269.1	1265.0	1256.8	1260.9
42.5°	1157.5	1157.5	1153.4	1153.4	1149.3	1149.3	1149.3	1149.3
45°	1050.0	1046.0	1046.0	1041.8	1041.8	1041.8	1041.8	1037.6
47.5°	942.5	938.5	938.5	938.5	934.3	934.3	930.2	934.3
50°	839.2	839.2	835.0	835.0	839.2	835.0	831.0	831.0
52.5°	744.1	744.1	740.0	740.0	735.9	731.7	735.9	735.9
55°	657.3	653.1	649.1	649.1	644.9	640.8	640.8	644.9
57.5°	574.6	570.5	566.3	566.3	558.1	554.0	554.0	554.0
60°	496.1	487.8	487.8	483.7	483.7	479.5	479.5	479.5
62.5°	421.6	417.6	417.6	417.6	417.6	413.4	413.4	413.4
65°	359.7	359.7	359.7	363.8	363.8	367.9	367.9	367.9
67.5°	310.1	314.1	314.1	314.1	318.3	318.3	318.3	314.1
70°	264.6	264.6	264.6	268.7	268.7	268.7	268.7	268.7
72.5°	219.1	219.1	219.1	219.1	219.1	219.1	219.1	219.1
75°	173.6	177.8	177.8	177.8	173.6	177.8	177.8	173.6
77.5°	136.4	136.4	136.4	136.4	136.4	136.4	136.4	136.4
80°	103.3	103.3	103.3	103.3	103.3	103.3	103.3	103.3
82.5°	70.3	70.3	70.3	70.3	70.3	70.3	70.3	70.3
85°	41.4	41.4	41.4	41.4	41.4	41.4	41.4	41.4
87.5°	16.5	16.5	16.5	16.5	16.5	16.5	16.5	16.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)