

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585229

Luminaire Tested: **HCC8S80D010SL-HM86080835-81RWWH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585229  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-15)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S80D010SL-HM86080835-81RWWH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6882.2 lumens  
Efficiency: N/A  
Efficacy: 98.3 lumens/watt  
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.16  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 70  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585229  
CATALOG NUMBER: HCC8S80D010SL-HM86080835-81RWWH

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585229

CATALOG NUMBER: HCC8S80D010SL-HM86080835-81RWWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77								
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67								
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59								
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47								
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	113206	113206	113206
5°	115332	112713	110098
10°	117132	110744	106073
15°	118311	107986	101477
20°	117856	103818	96799
25°	114753	97826	91396
30°	109288	90690	86083
35°	98684	82768	79956
40°	86707	74293	74091
45°	74842	65296	68117
50°	65152	57275	61089
55°	57767	49745	53224
60°	51540	42030	44182
65°	46457	34118	34841
70°	41257	25569	20637
75°	35552	14821	8900
80°	27383	5292	2664
85°	17584	1769	1769



TEST NUMBER: P585229  
 CATALOG NUMBER: HCC8S80D010SL-HM86080835-81RWWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	344.6	5.0
10°-20°	959.4	13.9
20°-30°	1356.9	19.7
30°-40°	1429.8	20.8
40°-50°	1215.2	17.7
50°-60°	875.0	12.7
60°-70°	504.8	7.3
70°-80°	172.7	2.5
80°-90°	23.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2660.9	38.7
0°-40°	4090.8	59.4
0°-60°	6181.0	89.8
0°-90°	6882.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6882.2	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	3671	3671	3671	3671	3671	
5°	3726	3701	3641	3577	3557	356
15°	3706	3592	3383	3233	3179	1043
25°	3373	3198	2875	2726	2686	1547
35°	2622	2467	2199	2119	2124	1633
45°	1716	1636	1497	1507	1562	1333
55°	1074	990	925	960	990	967
65°	637	547	468	458	478	633
75°	298	224	124	80	75	315
85°	50	30	5	5	5	67
90°	0	0	0	0	0	



TEST NUMBER: P585229

CATALOG NUMBER: HCC8S80D010SL-HM86080835-81RWWH

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	3671.2	3671.2	3671.2	3671.2	3671.2	3671.2	3671.2	3671.2	3671.2	3671.2	3671.2
2.5°	3706.0	3711.0	3706.0	3706.0	3701.0	3696.0	3691.0	3686.0	3676.2	3666.2	3666.2
5°	3725.9	3735.8	3725.9	3725.9	3711.0	3701.0	3691.0	3676.2	3656.2	3641.3	3641.3
7.5°	3740.8	3740.8	3740.8	3725.9	3715.9	3701.0	3676.2	3651.3	3626.3	3601.5	3591.5
10°	3740.8	3740.8	3735.8	3715.9	3706.0	3676.2	3651.3	3616.5	3581.6	3546.8	3536.8
12.5°	3725.9	3730.8	3720.9	3701.0	3676.2	3641.3	3606.5	3561.6	3521.9	3482.1	3462.2
15°	3706.0	3701.0	3691.0	3666.2	3636.3	3591.5	3556.8	3507.0	3452.3	3402.6	3382.6
17.5°	3656.2	3656.2	3641.3	3616.5	3576.6	3526.9	3472.1	3417.4	3357.7	3303.0	3278.2
20°	3591.5	3591.5	3571.6	3541.8	3502.0	3437.4	3377.6	3313.0	3243.4	3188.7	3163.7
22.5°	3497.1	3502.0	3477.1	3442.3	3397.6	3322.9	3263.2	3183.7	3114.0	3049.3	3029.5
25°	3372.7	3382.6	3357.7	3322.9	3263.2	3198.5	3124.0	3049.3	2969.8	2905.1	2875.2
27.5°	3228.4	3233.4	3208.5	3173.7	3114.0	3044.3	2969.8	2890.1	2815.6	2745.9	2716.0
30°	3069.3	3049.3	3039.4	2994.6	2929.9	2870.2	2785.7	2721.0	2641.5	2581.8	2547.0
32.5°	2845.4	2855.4	2825.5	2790.7	2740.9	2671.3	2601.7	2527.0	2452.4	2407.6	2382.8
35°	2621.5	2631.5	2616.5	2581.8	2527.0	2467.3	2397.7	2342.9	2278.2	2223.5	2198.7
37.5°	2387.7	2387.7	2377.8	2357.9	2318.1	2263.4	2193.7	2139.0	2084.3	2039.5	2024.6
40°	2154.0	2144.0	2139.0	2124.0	2089.3	2039.5	1994.8	1950.0	1895.3	1865.4	1845.6
42.5°	1925.1	1925.1	1915.1	1900.3	1865.4	1840.6	1795.7	1746.0	1706.2	1676.4	1676.4
45°	1716.2	1721.2	1706.2	1696.2	1676.4	1636.5	1596.8	1562.0	1527.2	1507.3	1497.3
47.5°	1532.1	1532.1	1517.2	1507.3	1487.3	1452.5	1417.8	1387.9	1363.0	1348.1	1343.1
50°	1358.1	1358.1	1358.1	1333.1	1308.3	1283.4	1258.6	1223.7	1208.7	1198.9	1193.9
52.5°	1208.7	1203.9	1203.9	1183.9	1159.0	1129.2	1104.3	1074.5	1059.5	1049.6	1054.5
55°	1074.5	1074.5	1069.5	1044.7	1019.8	990.0	965.0	940.1	930.3	920.3	925.3
56°	1019.8	1019.8	1014.8	994.8	965.0	940.1	910.3	885.4	870.6	875.5	875.5
57°	980.0	970.0	970.0	945.1	920.3	885.4	860.6	835.7	825.8	820.8	820.8
58°	930.3	925.3	920.3	895.4	870.6	840.6	815.8	790.9	776.1	776.1	771.1
59°	880.5	880.5	870.6	850.6	825.8	795.9	771.1	746.2	731.2	726.2	726.2
60°	835.7	840.6	825.8	805.9	785.9	751.1	721.2	701.4	686.5	681.5	681.5
61°	795.9	795.9	785.9	761.1	736.2	711.4	681.5	656.7	646.7	636.7	636.7
62°	761.1	751.1	746.2	721.2	696.4	666.6	641.7	616.9	601.9	592.0	596.9
63°	716.4	711.4	701.4	681.5	656.7	626.7	596.9	577.0	562.2	547.2	552.2
64°	681.5	676.5	661.6	641.7	616.9	587.0	557.2	537.2	527.3	512.3	507.3
65°	636.7	631.7	626.7	601.9	577.0	547.2	522.3	502.5	487.5	477.5	467.6
66°	596.9	601.9	592.0	572.0	542.2	517.3	482.5	462.6	452.7	437.8	427.8
67°	562.2	562.2	552.2	532.3	502.5	477.5	452.7	427.8	412.8	398.0	393.0
67.5°	542.2	542.2	532.3	507.3	487.5	457.6	432.8	412.8	393.0	383.0	373.1
68°	522.3	522.3	517.3	497.5	472.6	442.8	417.8	393.0	373.1	358.1	353.1
69°	487.5	492.5	482.5	462.6	437.8	407.9	383.0	363.1	343.3	328.3	318.4
70°	457.6	452.7	442.8	422.8	398.0	378.1	353.1	328.3	308.4	288.6	283.6
71°	417.8	417.8	407.9	393.0	368.1	343.3	318.4	298.4	278.6	253.7	248.7
72°	388.0	388.0	378.1	358.1	338.3	313.4	288.6	263.6	248.7	223.9	213.9
72.5°	368.1	373.1	363.1	343.3	323.3	293.4	273.6	253.7	228.9	208.9	198.9
73°	358.1	353.1	348.3	328.3	303.4	283.6	258.7	238.8	213.9	194.0	184.1

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P585229

CATALOG NUMBER: HCC8S80D010SL-HM86080835-81RWWH

**CANDELA DISTRIBUTION (continued):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
77.5°	223.9	223.9	218.9	198.9	179.1	159.2	139.2	119.4	99.5	79.5	69.7
80°	154.2	159.2	149.2	139.2	124.4	104.5	84.5	69.7	49.7	39.8	29.8
82.5°	99.5	99.5	94.5	84.5	74.7	59.7	49.7	34.8	24.9	19.9	15.0
85°	49.7	54.7	49.7	44.8	34.8	29.8	24.9	15.0	10.0	5.0	5.0
87.5°	19.9	19.9	19.9	15.0	15.0	10.0	5.0	5.0	5.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P585229

CATALOG NUMBER: HCC8S80D010SL-HM86080835-81RWWH

**CANDELA DISTRIBUTION (continued):**

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	3671.2	3671.2	3671.2	3671.2	3671.2	3671.2	3671.2	3671.2	3671.2	3671.2
2.5°	3656.2	3656.2	3646.3	3641.3	3636.3	3631.3	3626.3	3621.3	3621.3	3626.3
5°	3626.3	3616.5	3596.5	3591.5	3576.6	3571.6	3561.6	3556.8	3561.6	3556.8
7.5°	3581.6	3561.6	3536.8	3526.9	3507.0	3497.1	3482.1	3482.1	3472.1	3477.1
10°	3521.9	3492.1	3462.2	3442.3	3427.4	3412.4	3402.6	3392.6	3387.6	3387.6
12.5°	3447.3	3412.4	3382.6	3352.7	3327.9	3317.9	3298.0	3298.0	3288.1	3283.2
15°	3362.7	3317.9	3283.2	3253.3	3233.4	3213.5	3198.5	3188.7	3178.7	3178.7
17.5°	3253.3	3213.5	3178.7	3143.8	3114.0	3099.1	3084.1	3069.3	3069.3	3059.3
20°	3133.8	3089.1	3059.3	3024.5	2999.6	2974.8	2954.8	2954.8	2944.9	2949.8
22.5°	2999.6	2944.9	2915.1	2890.1	2865.3	2845.4	2825.5	2825.5	2820.5	2815.6
25°	2850.4	2805.6	2770.7	2740.9	2726.0	2706.0	2701.2	2691.2	2686.2	2686.2
27.5°	2691.2	2656.3	2611.6	2596.7	2576.8	2566.8	2566.8	2561.8	2551.8	2556.8
30°	2522.0	2482.3	2457.4	2447.4	2427.6	2427.6	2422.6	2412.6	2412.6	2417.6
32.5°	2357.9	2318.1	2298.2	2293.2	2273.4	2273.4	2268.4	2273.4	2273.4	2278.2
35°	2178.8	2144.0	2139.0	2124.0	2119.2	2119.2	2119.2	2129.0	2139.0	2124.0
37.5°	2009.6	1984.8	1969.9	1964.9	1969.9	1969.9	1974.8	1989.8	1984.8	1979.8
40°	1835.6	1815.7	1805.7	1805.7	1815.7	1825.6	1825.6	1840.6	1845.6	1840.6
42.5°	1661.5	1646.5	1646.5	1651.5	1661.5	1666.4	1681.4	1696.2	1701.2	1706.2
45°	1497.3	1497.3	1497.3	1502.3	1507.3	1517.2	1537.1	1552.0	1557.0	1562.0
47.5°	1338.1	1333.1	1348.1	1353.1	1367.9	1372.9	1387.9	1407.8	1412.8	1417.8
50°	1188.9	1198.9	1203.9	1218.7	1228.7	1228.7	1248.6	1258.6	1273.4	1273.4
52.5°	1049.6	1064.5	1069.5	1084.5	1089.4	1094.4	1104.3	1119.2	1129.2	1129.2
55°	925.3	930.3	940.1	945.1	960.1	965.0	975.0	980.0	994.8	990.0
56°	870.6	880.5	885.4	895.4	905.3	910.3	920.3	925.3	935.1	940.1
57°	820.8	825.8	840.6	845.6	855.6	855.6	860.6	875.5	875.5	880.5
58°	771.1	780.9	785.9	790.9	800.9	805.9	815.8	820.8	825.8	820.8
59°	726.2	731.2	736.2	736.2	746.2	746.2	761.1	771.1	776.1	776.1
60°	681.5	681.5	686.5	691.4	701.4	706.4	706.4	716.4	716.4	716.4
61°	636.7	636.7	641.7	646.7	651.7	651.7	661.6	661.6	666.6	671.5
62°	596.9	592.0	592.0	596.9	596.9	606.9	611.9	616.9	621.8	616.9
63°	552.2	547.2	547.2	547.2	547.2	557.2	557.2	562.2	572.0	567.0
64°	502.5	502.5	502.5	502.5	507.3	507.3	517.3	522.3	527.3	532.3
65°	467.6	457.6	452.7	452.7	457.6	462.6	467.6	472.6	477.5	477.5
66°	427.8	417.8	412.8	412.8	412.8	412.8	422.8	422.8	432.8	432.8
67°	383.0	373.1	368.1	363.1	363.1	363.1	378.1	373.1	373.1	373.1
67.5°	368.1	353.1	348.3	343.3	338.3	348.3	343.3	348.3	348.3	343.3
68°	348.3	338.3	328.3	318.4	318.4	318.4	323.3	328.3	323.3	318.4
69°	308.4	303.4	288.6	278.6	273.6	278.6	273.6	278.6	273.6	278.6
70°	273.6	258.7	243.7	238.8	233.8	233.8	233.8	228.9	233.8	228.9
71°	238.8	223.9	208.9	198.9	194.0	194.0	189.1	194.0	189.1	194.0
72°	203.9	189.1	169.1	159.2	159.2	159.2	159.2	154.2	159.2	154.2
72.5°	189.1	169.1	154.2	144.2	139.2	139.2	139.2	139.2	134.4	139.2
73°	174.1	154.2	134.4	129.4	129.4	129.4	124.4	119.4	124.4	124.4





TEST NUMBER: P585229  
CATALOG NUMBER: HCC8S80D010SL-HM86080835-81RWWH

**CANDELA DISTRIBUTION (continued):**

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
77.5°	59.7	44.8	39.8	39.8	39.8	39.8	39.8	39.8	34.8	34.8
80°	24.9	19.9	15.0	15.0	15.0	15.0	15.0	15.0	15.0	15.0
82.5°	10.0	10.0	10.0	10.0	10.0	10.0	10.0	10.0	10.0	10.0
85°	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



74°	323.3	323.3	313.4	298.4	273.6	248.7	228.9	208.9	184.1	159.2	149.2
75°	298.4	293.4	283.6	268.6	248.7	223.9	203.9	179.1	159.2	134.4	124.4

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



74°	144.2	119.4	109.4	99.5	99.5	99.5	94.5	94.5	94.5	99.5
75°	114.4	94.5	84.5	74.7	79.5	74.7	79.5	74.7	74.7	74.7

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)