

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585245

Luminaire Tested: **HCC8S80D010SL-HM86080840-81RWWC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585245  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S80D010SL-HM86080840-81RWWC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7415.7 lumens  
Efficiency: N/A  
Efficacy: 105.9 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 70  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585245  
CATALOG NUMBER: HCC8S80D010SL-HM86080840-81RWWC

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585245

CATALOG NUMBER: HCC8S80D010SL-HM86080840-81RWWC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	84	82	79	77					77			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67					67			
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59					59			
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52					52			
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47					47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42					42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38					38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35					35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32					32			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	120317	120317	120317
5°	121907	119811	118678
10°	123153	118585	116791
15°	124395	116082	113752
20°	123766	111802	109236
25°	120884	105104	103688
30°	114817	97570	97196
35°	104523	89029	89812
40°	91638	79687	82621
45°	79059	70882	75880
50°	69225	62226	68726
55°	61331	53493	60498
60°	55259	44978	50121
65°	49799	36110	38387
70°	43682	26308	21142
75°	37244	13654	5576
80°	28679	3694	923
85°	18433	0	0



TEST NUMBER: P585245  
 CATALOG NUMBER: HCC8S80D010SL-HM86080840-81RWWC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	368.1	5.0
10°-20°	1034.9	14.0
20°-30°	1468.9	19.8
30°-40°	1546.2	20.9
40°-50°	1315.4	17.7
50°-60°	950.5	12.8
60°-70°	540.6	7.3
70°-80°	170.3	2.3
80°-90°	20.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2871.9	38.7
0°-40°	4418.1	59.6
0°-60°	6684.0	90.1
0°-90°	7415.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7415.7	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	3902	3902	3902	3902	3902	
5°	3938	3917	3871	3844	3834	376
15°	3897	3798	3636	3568	3563	1097
25°	3553	3376	3089	3037	3048	1627
35°	2777	2615	2365	2350	2386	1728
45°	1813	1745	1625	1667	1740	1409
55°	1141	1058	995	1052	1125	1029
65°	682	589	495	490	526	677
75°	313	240	115	52	47	336
85°	52	31	0	0	0	67
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585245

CATALOG NUMBER: HCC8S80D010SL-HM86080840-81RWWC

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	3901.8	3901.8	3901.8	3901.8	3901.8	3901.8	3901.8	3901.8	3901.8	3901.8	3901.8
2.5°	3922.6	3927.9	3917.4	3917.4	3927.9	3917.4	3922.6	3922.6	3917.4	3917.4	3912.3
5°	3938.3	3933.1	3933.1	3933.1	3938.3	3927.9	3922.6	3927.9	3917.4	3917.4	3917.4
7.5°	3943.6	3943.6	3938.3	3933.1	3933.1	3933.1	3927.9	3922.6	3917.4	3907.1	3901.8
10°	3933.1	3933.1	3938.3	3927.9	3927.9	3917.4	3917.4	3907.1	3907.1	3896.6	3881.0
12.5°	3922.6	3917.4	3917.4	3907.1	3907.1	3896.6	3896.6	3881.0	3875.8	3860.1	3844.5
15°	3896.6	3891.4	3881.0	3875.8	3870.6	3865.3	3855.0	3849.7	3834.0	3813.2	3797.7
17.5°	3844.5	3839.3	3834.0	3823.7	3813.2	3808.0	3802.9	3787.2	3766.4	3750.7	3724.7
20°	3771.6	3766.4	3766.4	3750.7	3745.6	3729.9	3724.7	3703.9	3688.3	3657.0	3636.2
22.5°	3672.6	3677.8	3667.4	3657.0	3646.5	3631.0	3620.5	3599.7	3573.7	3542.4	3516.3
25°	3552.9	3558.0	3547.6	3537.2	3521.6	3511.1	3500.7	3469.5	3443.3	3407.0	3375.7
27.5°	3401.7	3401.7	3401.7	3391.3	3365.2	3360.0	3349.7	3318.4	3281.9	3250.6	3219.3
30°	3224.6	3219.3	3219.3	3203.8	3193.3	3172.5	3156.9	3130.9	3104.8	3068.3	3031.8
32.5°	3011.0	3016.3	3000.6	2990.2	2974.5	2974.5	2953.7	2932.9	2901.6	2865.1	2828.7
35°	2776.6	2781.8	2771.4	2766.2	2740.2	2734.9	2729.7	2703.7	2682.9	2656.8	2615.1
37.5°	2537.0	2531.7	2526.5	2526.5	2510.9	2500.5	2490.1	2474.4	2443.2	2422.3	2401.5
40°	2276.5	2276.5	2276.5	2271.3	2266.1	2255.7	2250.4	2240.1	2219.1	2198.3	2182.8
42.5°	2042.1	2042.1	2036.9	2031.6	2021.2	2026.4	2016.1	2005.6	1984.8	1969.1	1958.8
45°	1812.9	1812.9	1812.9	1818.1	1807.6	1792.1	1792.1	1781.6	1771.1	1760.8	1745.1
47.5°	1609.7	1625.4	1614.9	1609.7	1614.9	1594.1	1594.1	1583.6	1573.3	1562.8	1542.0
50°	1443.0	1443.0	1443.0	1432.6	1427.4	1427.4	1411.7	1401.4	1396.1	1385.7	1364.9
52.5°	1292.0	1281.5	1281.5	1276.3	1271.0	1260.7	1260.7	1250.2	1229.4	1219.0	1203.4
55°	1140.8	1140.8	1135.6	1130.4	1125.3	1120.0	1114.8	1099.2	1088.8	1073.1	1057.5
57.5°	1005.4	1015.9	1010.6	1000.2	989.7	989.7	979.4	968.9	953.3	937.6	922.1
60°	896.0	890.8	890.8	885.6	875.2	870.0	864.8	849.2	833.5	817.9	802.2
62.5°	781.4	781.4	781.4	770.9	760.6	755.4	750.1	739.7	718.9	703.3	692.8
65°	682.5	677.3	672.0	666.8	661.6	651.2	646.0	635.5	619.9	604.2	588.7
67.5°	583.4	578.2	578.2	573.0	557.4	552.2	552.2	536.6	520.9	505.3	489.6
70°	484.5	484.5	484.5	474.1	468.8	463.6	458.5	448.0	432.3	416.7	401.2
72.5°	401.2	395.9	395.9	390.7	375.1	369.9	364.7	354.2	338.6	328.2	317.8
75°	312.6	312.6	307.4	302.1	296.9	291.8	286.5	276.1	260.5	244.8	239.6
77.5°	239.6	234.5	234.5	229.2	218.8	213.5	213.5	203.2	187.5	177.2	166.7
80°	161.5	166.7	161.5	156.2	151.1	145.9	140.7	135.4	125.1	114.6	104.2
82.5°	98.9	104.2	98.9	98.9	93.8	88.6	88.6	78.1	72.9	67.8	62.5
85°	52.1	52.1	52.1	52.1	46.8	46.8	46.8	41.7	36.5	31.3	31.3
87.5°	15.6	20.8	15.6	15.6	15.6	15.6	15.6	15.6	10.5	10.5	10.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585245

CATALOG NUMBER: HCC8S80D010SL-HM86080840-81RWWC

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	3901.8	3901.8	3901.8	3901.8	3901.8	3901.8	3901.8	3901.8	3901.8	3901.8	3901.8
2.5°	3917.4	3912.3	3907.1	3907.1	3907.1	3907.1	3907.1	3901.8	3896.6	3896.6	3896.6
5°	3907.1	3907.1	3907.1	3901.8	3896.6	3896.6	3886.2	3881.0	3875.8	3870.6	3865.3
7.5°	3896.6	3886.2	3881.0	3875.8	3870.6	3870.6	3860.1	3849.7	3849.7	3839.3	3828.9
10°	3865.3	3860.1	3849.7	3839.3	3834.0	3828.9	3818.5	3802.9	3797.7	3787.2	3776.7
12.5°	3828.9	3818.5	3808.0	3787.2	3782.0	3776.7	3755.9	3740.4	3729.9	3724.7	3698.6
15°	3782.0	3761.2	3745.6	3719.5	3714.3	3703.9	3688.3	3672.6	3651.8	3636.2	3625.7
17.5°	3698.6	3677.8	3651.8	3625.7	3615.3	3615.3	3589.2	3568.4	3542.4	3531.9	3511.1
20°	3599.7	3573.7	3552.9	3521.6	3505.9	3490.3	3474.6	3443.3	3422.5	3407.0	3380.9
22.5°	3485.1	3448.6	3422.5	3391.3	3365.2	3349.7	3323.6	3297.6	3271.5	3255.8	3235.0
25°	3339.2	3307.9	3266.3	3235.0	3219.3	3198.5	3167.3	3141.2	3115.2	3089.1	3078.8
27.5°	3177.7	3136.0	3099.6	3063.1	3047.5	3031.8	2995.4	2964.2	2943.3	2917.2	2906.9
30°	3000.6	2958.9	2917.2	2885.9	2870.4	2844.3	2823.5	2787.0	2761.0	2740.2	2714.1
32.5°	2797.5	2766.2	2729.7	2682.9	2672.4	2651.6	2620.3	2604.7	2573.5	2557.8	2537.0
35°	2578.6	2557.8	2521.4	2484.9	2469.2	2458.9	2432.8	2401.5	2380.7	2365.0	2354.7
37.5°	2370.3	2344.2	2307.7	2281.7	2271.3	2255.7	2224.4	2208.8	2187.9	2177.5	2156.7
40°	2146.3	2120.2	2094.2	2078.5	2062.9	2052.5	2031.6	2016.1	1995.1	1979.6	1974.3
42.5°	1927.5	1911.8	1891.0	1870.2	1864.9	1849.4	1838.9	1823.3	1807.6	1802.4	1786.8
45°	1729.5	1713.9	1693.0	1672.2	1667.0	1656.6	1651.4	1635.7	1625.4	1625.4	1625.4
47.5°	1531.6	1516.0	1495.0	1484.7	1489.9	1469.0	1469.0	1463.8	1453.4	1453.4	1458.7
50°	1354.4	1333.6	1328.4	1318.0	1307.5	1297.1	1302.3	1286.7	1286.7	1297.1	1292.0
52.5°	1187.7	1166.9	1161.7	1151.3	1146.1	1146.1	1140.8	1140.8	1135.6	1140.8	1140.8
55°	1036.7	1021.0	1010.6	1000.2	995.0	995.0	995.0	989.7	984.6	995.0	1000.2
57.5°	901.3	896.0	885.6	870.0	864.8	859.5	854.3	854.3	854.3	854.3	859.5
60°	781.4	770.9	760.6	744.9	744.9	739.7	734.6	729.3	729.3	729.3	729.3
62.5°	677.3	661.6	646.0	635.5	630.3	625.2	619.9	609.5	609.5	609.5	609.5
65°	573.0	557.4	546.9	536.6	526.1	526.1	515.7	510.6	500.1	494.9	484.5
67.5°	474.1	463.6	453.2	437.6	432.3	427.2	416.7	411.5	395.9	390.7	385.5
70°	385.5	369.9	359.4	349.0	343.9	333.4	322.9	312.6	302.1	291.8	281.3
72.5°	302.1	286.5	276.1	265.6	255.3	255.3	239.6	229.2	213.5	203.2	187.5
75°	224.0	208.4	198.0	182.3	177.2	171.9	156.2	145.9	130.2	114.6	104.2
77.5°	151.1	140.7	130.2	114.6	104.2	104.2	88.6	78.1	67.8	52.1	46.8
80°	93.8	83.3	72.9	62.5	62.5	52.1	46.8	36.5	26.0	20.8	15.6
82.5°	52.1	46.8	41.7	31.3	31.3	26.0	20.8	15.6	10.5	5.2	5.2
85°	26.0	20.8	15.6	15.6	10.5	10.5	10.5	5.2	5.2	0.0	0.0
87.5°	10.5	5.2	5.2	5.2	5.2	5.2	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585245

CATALOG NUMBER: HCC8S80D010SL-HM86080840-81RWWC

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	3901.8	3901.8	3901.8	3901.8	3901.8	3901.8	3901.8	3901.8	3901.8	3901.8	3901.8
2.5°	3891.4	3891.4	3886.2	3886.2	3886.2	3881.0	3886.2	3881.0	3881.0	3881.0	3886.2
5°	3870.6	3860.1	3860.1	3855.0	3855.0	3849.7	3855.0	3849.7	3844.5	3839.3	3844.5
7.5°	3828.9	3818.5	3813.2	3808.0	3808.0	3808.0	3802.9	3797.7	3802.9	3787.2	3797.7
10°	3771.6	3766.4	3755.9	3750.7	3745.6	3750.7	3745.6	3735.1	3735.1	3735.1	3729.9
12.5°	3698.6	3688.3	3683.0	3677.8	3667.4	3667.4	3672.6	3662.2	3662.2	3651.8	3651.8
15°	3610.0	3599.7	3589.2	3589.2	3578.9	3578.9	3573.7	3573.7	3568.4	3563.2	3563.2
17.5°	3500.7	3485.1	3474.6	3479.8	3474.6	3469.5	3469.5	3459.0	3453.8	3459.0	3459.0
20°	3370.5	3360.0	3349.7	3354.9	3344.4	3339.2	3344.4	3328.8	3334.0	3334.0	3334.0
22.5°	3224.6	3219.3	3203.8	3203.8	3193.3	3188.2	3193.3	3193.3	3198.5	3193.3	3193.3
25°	3063.1	3052.6	3042.3	3042.3	3037.1	3031.8	3037.1	3042.3	3037.1	3042.3	3042.3
27.5°	2891.2	2875.6	2875.6	2865.1	2865.1	2870.4	2865.1	2870.4	2875.6	2875.6	2885.9
30°	2703.7	2698.4	2693.2	2688.1	2688.1	2693.2	2693.2	2693.2	2698.4	2708.9	2708.9
32.5°	2526.5	2516.2	2505.7	2505.7	2516.2	2510.9	2516.2	2516.2	2526.5	2526.5	2537.0
35°	2333.8	2333.8	2323.4	2328.5	2328.5	2328.5	2328.5	2339.0	2349.5	2354.7	2365.0
37.5°	2156.7	2141.0	2146.3	2146.3	2151.5	2146.3	2161.8	2161.8	2172.3	2172.3	2182.8
40°	1964.0	1964.0	1969.1	1964.0	1969.1	1969.1	1979.6	1990.0	1995.1	2005.6	2010.8
42.5°	1781.6	1792.1	1781.6	1786.8	1792.1	1797.3	1802.4	1807.6	1828.4	1838.9	1854.5
45°	1614.9	1620.1	1625.4	1630.5	1625.4	1635.7	1640.9	1651.4	1667.0	1672.2	1677.4
47.5°	1453.4	1458.7	1463.8	1469.0	1469.0	1479.5	1484.7	1495.0	1505.5	1510.7	1516.0
50°	1297.1	1307.5	1312.8	1312.8	1318.0	1328.4	1338.8	1338.8	1349.3	1364.9	1370.1
52.5°	1156.5	1156.5	1166.9	1172.1	1177.3	1177.3	1192.9	1198.2	1203.4	1213.7	1224.2
55°	1000.2	1015.9	1021.0	1021.0	1031.5	1041.9	1047.0	1052.3	1052.3	1073.1	1073.1
57.5°	864.8	870.0	880.3	880.3	880.3	896.0	896.0	906.4	911.6	916.8	927.3
60°	729.3	739.7	739.7	744.9	739.7	750.1	755.4	765.8	770.9	776.2	781.4
62.5°	604.2	604.2	609.5	609.5	609.5	609.5	619.9	619.9	630.3	635.5	640.8
65°	484.5	484.5	484.5	484.5	484.5	484.5	484.5	484.5	489.6	489.6	500.1
67.5°	375.1	369.9	359.4	364.7	359.4	359.4	354.2	354.2	359.4	359.4	369.9
70°	270.9	265.6	255.3	255.3	250.0	244.8	239.6	234.5	229.2	229.2	229.2
72.5°	177.2	166.7	151.1	145.9	145.9	135.4	125.1	119.9	119.9	119.9	119.9
75°	88.6	78.1	67.8	62.5	62.5	52.1	57.3	52.1	52.1	52.1	52.1
77.5°	36.5	26.0	20.8	20.8	20.8	15.6	15.6	15.6	15.6	15.6	15.6
80°	10.5	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
82.5°	5.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585245

CATALOG NUMBER: HCC8S80D010SL-HM86080840-81RWWC

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	3901.8	3901.8	3901.8	3901.8	3901.8	3901.8	3901.8	3901.8
2.5°	3881.0	3881.0	3870.6	3875.8	3875.8	3875.8	3875.8	3875.8
5°	3834.0	3839.3	3834.0	3839.3	3839.3	3834.0	3834.0	3834.0
7.5°	3787.2	3792.4	3787.2	3792.4	3792.4	3792.4	3787.2	3787.2
10°	3729.9	3729.9	3729.9	3729.9	3729.9	3724.7	3729.9	3729.9
12.5°	3651.8	3651.8	3651.8	3657.0	3657.0	3651.8	3651.8	3646.5
15°	3568.4	3558.0	3563.2	3568.4	3563.2	3563.2	3563.2	3563.2
17.5°	3453.8	3459.0	3453.8	3453.8	3453.8	3453.8	3459.0	3453.8
20°	3334.0	3334.0	3339.2	3334.0	3334.0	3334.0	3334.0	3328.8
22.5°	3198.5	3193.3	3193.3	3198.5	3198.5	3193.3	3198.5	3198.5
25°	3047.5	3052.6	3047.5	3047.5	3052.6	3052.6	3052.6	3047.5
27.5°	2885.9	2891.2	2896.4	2891.2	2891.2	2891.2	2896.4	2901.6
30°	2719.2	2729.7	2719.2	2719.2	2729.7	2724.5	2729.7	2729.7
32.5°	2542.2	2557.8	2547.4	2557.8	2557.8	2563.0	2557.8	2563.0
35°	2365.0	2380.7	2380.7	2380.7	2385.8	2391.1	2391.1	2385.8
37.5°	2198.3	2203.6	2203.6	2214.0	2219.1	2224.4	2224.4	2219.1
40°	2026.4	2036.9	2042.1	2042.1	2042.1	2052.5	2062.9	2052.5
42.5°	1859.7	1864.9	1870.2	1870.2	1880.6	1885.8	1891.0	1891.0
45°	1698.2	1708.7	1713.9	1719.1	1724.3	1734.8	1729.5	1740.0
47.5°	1531.6	1547.1	1552.4	1557.6	1568.1	1573.3	1578.4	1583.6
50°	1380.4	1390.9	1390.9	1401.4	1416.9	1416.9	1427.4	1432.6
52.5°	1229.4	1234.7	1239.9	1245.0	1255.5	1265.9	1265.9	1276.3
55°	1083.5	1088.8	1088.8	1094.0	1099.2	1120.0	1125.3	1125.3
57.5°	932.5	932.5	942.9	948.1	953.3	963.7	963.7	963.7
60°	786.6	791.9	791.9	797.0	802.2	812.7	817.9	812.7
62.5°	640.8	646.0	646.0	651.2	661.6	666.8	661.6	661.6
65°	505.3	510.6	510.6	515.7	526.1	526.1	520.9	526.1
67.5°	369.9	369.9	369.9	369.9	369.9	369.9	369.9	369.9
70°	234.5	229.2	224.0	229.2	229.2	229.2	224.0	234.5
72.5°	114.6	119.9	119.9	119.9	119.9	119.9	119.9	114.6
75°	52.1	52.1	46.8	46.8	46.8	52.1	52.1	46.8
77.5°	15.6	15.6	15.6	15.6	15.6	15.6	15.6	15.6
80°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)