

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585271

Luminaire Tested: **HCC8S80D010MW-HM86080927-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585271
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S80D010MW-HM86080927-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5136.3 lumens
Efficiency: N/A
Efficacy: 73.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 70
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585271
CATALOG NUMBER: HCC8S80D010MW-HM86080927-81WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585271

CATALOG NUMBER: HCC8S80D010MW-HM86080927-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87					87			
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75					75			
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65					65			
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57					57			
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50					50			
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45					45			
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40					40			
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37					37			
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33					33			
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30					30			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	78747	78747	78747
5°	81632	78490	75794
10°	83938	77807	72694
15°	85812	76433	69483
20°	85947	73447	66661
25°	84298	69365	64302
30°	79951	64327	61482
35°	72650	58582	58717
40°	63517	52568	55341
45°	55052	46827	51572
50°	48203	41592	46985
55°	42907	36859	42515
60°	38706	33106	37361
65°	34936	29113	32557
70°	31403	24523	24208
75°	27665	19444	18145
80°	23192	16106	17403
85°	17973	14152	15391



TEST NUMBER: P585271
 CATALOG NUMBER: HCC8S80D010MW-HM86080927-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	240.9	4.7
10°-20°	678.6	13.2
20°-30°	969.8	18.9
30°-40°	1030.4	20.1
40°-50°	887.2	17.3
50°-60°	663.3	12.9
60°-70°	423.1	8.2
70°-80°	192.5	3.7
80°-90°	50.6	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1889.3	36.8
0°-40°	2919.7	56.8
0°-60°	4470.1	87.0
0°-90°	5136.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5136.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2554	2554	2554	2554	2554	
5°	2637	2601	2536	2470	2449	253
15°	2688	2597	2394	2231	2176	757
25°	2478	2322	2039	1915	1890	1134
35°	1930	1796	1556	1516	1560	1202
45°	1262	1193	1074	1103	1183	981
55°	798	733	686	744	791	718
65°	479	424	399	417	446	478
75°	232	200	163	149	152	247
85°	51	44	40	44	44	61
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585271

CATALOG NUMBER: HCC8S80D010MW-HM86080927-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2553.7	2553.7	2553.7	2553.7	2553.7	2553.7	2553.7	2553.7	2553.7	2553.7	2553.7
2.5°	2600.9	2593.7	2597.4	2593.7	2597.4	2597.4	2590.1	2590.1	2590.1	2590.1	2579.2
5°	2637.2	2633.6	2633.6	2629.9	2626.4	2629.9	2626.4	2622.7	2615.4	2611.9	2600.9
7.5°	2659.0	2659.0	2659.0	2659.0	2655.4	2651.7	2648.1	2640.9	2633.6	2626.4	2619.1
10°	2680.7	2684.4	2680.7	2677.2	2673.5	2666.2	2662.6	2655.4	2644.5	2633.6	2626.4
12.5°	2691.7	2691.7	2688.0	2688.0	2680.7	2677.2	2666.2	2655.4	2644.5	2633.6	2615.4
15°	2688.0	2688.0	2684.4	2680.7	2669.9	2666.2	2659.0	2648.1	2629.9	2615.4	2597.4
17.5°	2666.2	2662.6	2655.4	2655.4	2640.9	2637.2	2629.9	2615.4	2597.4	2575.5	2553.7
20°	2619.1	2619.1	2615.4	2611.9	2597.4	2586.4	2579.2	2561.0	2546.5	2521.2	2499.4
22.5°	2553.7	2561.0	2553.7	2546.5	2528.4	2524.7	2513.9	2492.1	2470.4	2441.4	2415.9
25°	2477.6	2474.0	2470.4	2463.1	2448.6	2441.4	2426.9	2405.1	2383.2	2350.7	2321.6
27.5°	2379.7	2365.2	2365.2	2350.7	2339.7	2328.9	2321.6	2299.9	2270.9	2245.4	2209.2
30°	2245.4	2249.1	2230.9	2227.4	2209.2	2201.9	2187.4	2165.6	2140.2	2111.2	2082.2
32.5°	2100.4	2089.4	2089.4	2074.9	2060.4	2049.6	2045.9	2020.6	1998.8	1969.7	1940.7
35°	1929.9	1929.9	1918.9	1915.4	1900.9	1893.6	1882.7	1868.2	1842.8	1817.4	1795.6
37.5°	1762.9	1755.7	1752.1	1744.9	1733.9	1723.1	1723.1	1697.7	1694.1	1665.1	1636.1
40°	1577.9	1585.2	1577.9	1567.1	1563.4	1556.2	1552.6	1538.1	1527.2	1501.8	1483.6
42.5°	1422.0	1414.8	1414.8	1411.1	1396.6	1396.6	1389.3	1382.1	1363.9	1356.6	1334.9
45°	1262.4	1269.6	1258.8	1262.4	1247.9	1247.9	1247.9	1233.3	1218.8	1208.0	1193.4
47.5°	1124.6	1128.1	1128.1	1117.3	1113.6	1113.6	1106.4	1099.1	1088.3	1073.8	1062.8
50°	1004.8	1008.5	1001.3	997.6	990.3	986.6	986.6	972.1	964.9	950.4	943.1
52.5°	896.0	896.0	892.3	892.3	881.5	881.5	874.3	863.3	856.1	848.8	830.8
55°	798.1	798.1	794.4	790.8	790.8	779.9	776.3	765.4	758.1	743.6	732.8
57.5°	703.8	707.3	703.8	700.1	696.5	692.8	685.6	674.8	667.5	656.6	649.3
60°	627.6	627.6	624.0	620.3	613.0	609.5	605.8	598.5	587.6	580.4	569.5
62.5°	555.0	551.3	547.8	544.1	536.8	536.8	529.6	522.3	511.5	504.3	497.0
65°	478.8	478.8	475.2	475.2	471.6	464.3	460.7	457.1	442.5	439.0	424.5
67.5°	410.0	413.5	406.3	406.3	399.0	399.0	395.3	384.5	380.8	373.6	366.3
70°	348.3	348.3	348.3	344.6	337.3	333.8	330.1	322.8	319.2	312.0	304.7
72.5°	286.5	286.5	283.0	283.0	279.3	275.7	272.0	264.8	264.8	257.5	250.3
75°	232.2	232.2	228.5	225.0	221.3	221.3	217.7	214.0	206.8	203.2	199.5
77.5°	177.8	177.8	177.8	174.1	170.5	170.5	170.5	163.2	156.0	156.0	152.3
80°	130.6	130.6	127.0	127.0	123.3	123.3	123.3	119.7	116.0	112.5	108.8
82.5°	87.0	87.0	87.0	87.0	83.5	83.5	83.5	79.8	76.2	76.2	76.2
85°	50.8	50.8	50.8	50.8	47.2	47.2	47.2	47.2	47.2	43.5	43.5
87.5°	21.8	18.2	21.8	18.2	21.8	18.2	21.8	18.2	18.2	18.2	18.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585271

CATALOG NUMBER: HCC8S80D010MW-HM86080927-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2553.7	2553.7	2553.7	2553.7	2553.7	2553.7	2553.7	2553.7	2553.7	2553.7	2553.7
2.5°	2582.7	2579.2	2575.5	2571.9	2571.9	2568.2	2561.0	2557.4	2553.7	2550.2	2550.2
5°	2597.4	2593.7	2586.4	2579.2	2575.5	2568.2	2561.0	2553.7	2546.5	2535.7	2532.0
7.5°	2608.2	2597.4	2590.1	2575.5	2571.9	2564.7	2553.7	2542.9	2528.4	2513.9	2503.0
10°	2608.2	2593.7	2582.7	2564.7	2557.4	2550.2	2535.7	2517.5	2499.4	2484.9	2466.7
12.5°	2600.9	2582.7	2564.7	2546.5	2535.7	2524.7	2503.0	2484.9	2463.1	2441.4	2426.9
15°	2575.5	2553.7	2532.0	2510.2	2499.4	2484.9	2463.1	2437.7	2415.9	2394.2	2368.7
17.5°	2528.4	2506.6	2481.2	2455.9	2441.4	2430.4	2397.9	2379.7	2347.0	2325.2	2303.4
20°	2466.7	2441.4	2408.7	2383.2	2365.2	2354.2	2328.9	2296.2	2270.9	2238.2	2216.4
22.5°	2386.9	2354.2	2321.6	2296.2	2278.1	2263.6	2230.9	2198.3	2176.5	2147.5	2122.1
25°	2292.6	2259.9	2227.4	2191.1	2172.9	2158.4	2129.4	2100.4	2071.4	2038.7	2016.9
27.5°	2180.2	2143.9	2114.9	2082.2	2064.1	2042.3	2009.6	1980.6	1951.6	1929.9	1900.9
30°	2056.9	2016.9	1987.9	1955.2	1937.1	1918.9	1886.3	1857.3	1831.9	1806.6	1792.1
32.5°	1908.1	1879.1	1850.1	1817.4	1802.9	1792.1	1759.4	1730.4	1701.3	1679.6	1668.6
35°	1766.6	1733.9	1708.6	1679.6	1661.4	1650.6	1621.6	1596.1	1581.6	1556.2	1541.7
37.5°	1617.9	1592.4	1563.4	1534.4	1523.6	1512.6	1490.9	1465.6	1443.8	1425.6	1418.4
40°	1461.9	1440.1	1414.8	1396.6	1385.7	1374.8	1356.6	1338.6	1324.1	1305.9	1298.6
42.5°	1313.1	1298.6	1276.9	1255.1	1244.3	1240.6	1218.8	1204.3	1197.1	1189.8	1182.6
45°	1178.9	1157.1	1142.6	1128.1	1117.3	1110.1	1099.1	1088.3	1081.0	1073.8	1066.5
47.5°	1048.3	1030.3	1015.8	1004.8	993.9	990.3	983.1	972.1	964.9	964.9	964.9
50°	928.6	914.1	899.6	892.3	888.8	881.5	874.3	870.6	867.0	867.0	867.0
52.5°	823.5	809.0	798.1	790.8	790.8	783.6	776.3	772.6	772.6	772.6	772.6
55°	725.5	714.6	707.3	700.1	692.8	689.3	689.3	689.3	685.6	685.6	689.3
57.5°	638.5	631.2	620.3	613.0	609.5	609.5	605.8	602.2	605.8	609.5	613.0
60°	558.6	551.3	547.8	536.8	536.8	536.8	533.3	533.3	533.3	536.8	540.5
62.5°	486.1	482.5	475.2	471.6	468.0	468.0	464.3	464.3	464.3	464.3	468.0
65°	420.8	413.5	406.3	406.3	406.3	402.7	402.7	395.3	399.0	399.0	395.3
67.5°	359.1	351.8	348.3	344.6	341.0	341.0	337.3	333.8	330.1	330.1	330.1
70°	301.1	293.8	293.8	286.5	286.5	283.0	279.3	279.3	275.7	272.0	268.5
72.5°	243.0	239.5	235.8	232.2	232.2	232.2	228.5	225.0	221.3	217.7	210.5
75°	192.3	192.3	185.0	181.3	181.3	177.8	174.1	170.5	166.8	163.2	159.6
77.5°	148.7	145.1	137.8	134.2	134.2	134.2	130.6	127.0	123.3	119.7	116.0
80°	108.8	105.2	101.5	98.0	98.0	98.0	94.3	94.3	90.7	90.7	90.7
82.5°	72.5	72.5	69.0	69.0	69.0	69.0	65.3	65.3	65.3	65.3	65.3
85°	43.5	43.5	40.0	40.0	40.0	40.0	40.0	40.0	40.0	40.0	40.0
87.5°	18.2	18.2	18.2	18.2	18.2	18.2	18.2	18.2	18.2	18.2	18.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585271

CATALOG NUMBER: HCC8S80D010MW-HM86080927-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2553.7	2553.7	2553.7	2553.7	2553.7	2553.7	2553.7	2553.7	2553.7	2553.7	2553.7
2.5°	2542.9	2542.9	2535.7	2532.0	2528.4	2532.0	2524.7	2521.2	2517.5	2517.5	2513.9
5°	2521.2	2517.5	2503.0	2499.4	2495.7	2492.1	2484.9	2477.6	2470.4	2466.7	2463.1
7.5°	2492.1	2481.2	2466.7	2463.1	2459.4	2448.6	2437.7	2430.4	2419.6	2415.9	2408.7
10°	2452.2	2437.7	2426.9	2415.9	2408.7	2397.9	2386.9	2376.0	2361.5	2357.9	2347.0
12.5°	2405.1	2386.9	2365.2	2361.5	2350.7	2336.1	2321.6	2310.7	2299.9	2292.6	2281.7
15°	2347.0	2328.9	2307.1	2296.2	2285.4	2274.4	2256.4	2241.9	2230.9	2220.1	2209.2
17.5°	2278.1	2256.4	2238.2	2227.4	2220.1	2201.9	2187.4	2169.2	2158.4	2147.5	2136.6
20°	2194.7	2176.5	2151.1	2140.2	2136.6	2122.1	2103.9	2096.7	2082.2	2071.4	2064.1
22.5°	2100.4	2082.2	2060.4	2053.2	2038.7	2031.4	2013.3	2006.1	1998.8	1987.9	1984.2
25°	1995.1	1977.0	1958.9	1955.2	1944.4	1937.1	1926.2	1915.4	1915.4	1904.4	1904.4
27.5°	1886.3	1868.2	1853.7	1846.4	1842.8	1835.6	1824.6	1821.1	1817.4	1813.8	1813.8
30°	1770.2	1748.4	1741.2	1737.6	1733.9	1726.7	1723.1	1715.8	1719.4	1723.1	1719.4
32.5°	1646.9	1639.6	1625.1	1617.9	1621.6	1617.9	1610.6	1617.9	1614.3	1621.6	1625.1
35°	1527.2	1519.9	1512.6	1512.6	1505.4	1505.4	1505.4	1509.1	1516.3	1519.9	1527.2
37.5°	1411.1	1400.3	1396.6	1392.9	1396.6	1396.6	1396.6	1403.9	1411.1	1418.4	1429.3
40°	1287.8	1280.6	1280.6	1280.6	1280.6	1291.4	1287.8	1295.1	1302.3	1313.1	1324.1
42.5°	1171.6	1171.6	1175.3	1175.3	1175.3	1175.3	1182.6	1193.4	1204.3	1215.3	1226.1
45°	1062.8	1062.8	1062.8	1070.1	1070.1	1073.8	1088.3	1095.5	1102.8	1113.6	1124.6
47.5°	961.3	961.3	964.9	968.6	972.1	979.4	986.6	997.6	1008.5	1015.8	1026.6
50°	867.0	870.6	877.8	885.1	885.1	888.8	899.6	906.9	914.1	925.0	928.6
52.5°	776.3	783.6	790.8	794.4	798.1	805.3	809.0	819.8	823.5	834.3	838.0
55°	692.8	696.5	707.3	711.0	711.0	718.3	725.5	732.8	743.6	743.6	750.9
57.5°	616.7	620.3	627.6	631.2	627.6	638.5	642.1	649.3	653.0	660.3	663.8
60°	540.5	547.8	551.3	551.3	555.0	558.6	565.8	565.8	573.1	580.4	580.4
62.5°	468.0	471.6	475.2	478.8	482.5	478.8	489.7	489.7	497.0	500.6	507.8
65°	399.0	402.7	402.7	406.3	406.3	410.0	410.0	413.5	417.2	424.5	428.0
67.5°	330.1	330.1	330.1	333.8	330.1	333.8	333.8	337.3	337.3	344.6	348.3
70°	268.5	264.8	261.2	261.2	261.2	261.2	257.5	261.2	261.2	264.8	264.8
72.5°	206.8	203.2	199.5	195.8	195.8	192.3	188.6	192.3	192.3	195.8	195.8
75°	156.0	148.7	148.7	148.7	145.1	145.1	145.1	148.7	148.7	148.7	152.3
77.5°	116.0	116.0	112.5	112.5	112.5	116.0	116.0	119.7	119.7	119.7	119.7
80°	87.0	90.7	90.7	90.7	90.7	94.3	94.3	94.3	94.3	98.0	98.0
82.5°	65.3	65.3	65.3	65.3	69.0	69.0	69.0	69.0	69.0	69.0	69.0
85°	40.0	43.5	43.5	40.0	43.5	43.5	43.5	43.5	43.5	43.5	43.5
87.5°	18.2	18.2	18.2	18.2	18.2	18.2	18.2	18.2	18.2	18.2	18.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585271

CATALOG NUMBER: HCC8S80D010MW-HM86080927-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2553.7	2553.7	2553.7	2553.7	2553.7	2553.7	2553.7	2553.7
2.5°	2510.2	2510.2	2510.2	2510.2	2506.6	2506.6	2506.6	2503.0
5°	2455.9	2455.9	2455.9	2448.6	2452.2	2452.2	2444.9	2448.6
7.5°	2401.4	2397.9	2394.2	2394.2	2390.6	2386.9	2383.2	2386.9
10°	2339.7	2328.9	2328.9	2325.2	2325.2	2318.0	2318.0	2321.6
12.5°	2270.9	2263.6	2263.6	2259.9	2256.4	2252.7	2249.1	2249.1
15°	2201.9	2194.7	2191.1	2187.4	2183.7	2176.5	2180.2	2176.5
17.5°	2132.9	2122.1	2122.1	2118.4	2114.9	2107.6	2107.6	2103.9
20°	2053.2	2049.6	2042.3	2045.9	2042.3	2035.1	2031.4	2031.4
22.5°	1973.4	1973.4	1969.7	1969.7	1966.1	1962.4	1958.9	1958.9
25°	1897.2	1893.6	1897.2	1897.2	1886.3	1886.3	1886.3	1889.9
27.5°	1810.1	1813.8	1810.1	1810.1	1810.1	1810.1	1813.8	1810.1
30°	1723.1	1723.1	1723.1	1726.7	1733.9	1730.4	1730.4	1726.7
32.5°	1628.8	1632.4	1632.4	1636.1	1639.6	1646.9	1646.9	1650.6
35°	1534.4	1541.7	1545.3	1541.7	1552.6	1552.6	1559.8	1559.8
37.5°	1436.5	1440.1	1447.4	1451.1	1458.3	1461.9	1465.6	1465.6
40°	1331.3	1345.8	1349.4	1353.1	1363.9	1363.9	1367.6	1374.8
42.5°	1233.3	1247.9	1251.5	1255.1	1262.4	1273.3	1269.6	1276.9
45°	1139.1	1149.9	1153.6	1157.1	1168.1	1171.6	1171.6	1182.6
47.5°	1037.5	1044.8	1048.3	1055.6	1062.8	1070.1	1077.4	1073.8
50°	935.9	946.8	954.1	957.6	968.6	972.1	975.8	979.4
52.5°	845.3	852.5	856.1	859.8	870.6	874.3	877.8	885.1
55°	758.1	761.8	769.0	765.4	776.3	779.9	783.6	790.8
57.5°	671.1	674.8	678.3	678.3	685.6	692.8	696.5	700.1
60°	587.6	594.9	598.5	598.5	598.5	605.8	605.8	605.8
62.5°	511.5	511.5	515.1	515.1	522.3	522.3	522.3	522.3
65°	431.7	435.3	439.0	439.0	446.2	442.5	449.8	446.2
67.5°	348.3	348.3	355.5	355.5	351.8	355.5	355.5	355.5
70°	264.8	264.8	268.5	268.5	268.5	268.5	268.5	268.5
72.5°	195.8	195.8	195.8	199.5	195.8	195.8	199.5	195.8
75°	152.3	152.3	152.3	152.3	152.3	152.3	152.3	152.3
77.5°	119.7	119.7	123.3	123.3	123.3	123.3	123.3	123.3
80°	98.0	98.0	98.0	98.0	101.5	98.0	98.0	98.0
82.5°	72.5	69.0	72.5	69.0	72.5	72.5	72.5	72.5
85°	43.5	43.5	43.5	43.5	43.5	43.5	43.5	43.5
87.5°	18.2	18.2	18.2	18.2	18.2	18.2	18.2	18.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)