

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585304

Luminaire Tested: **HCC8S80D010BZ-HM86080935-81WWW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585304
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S80D010BZ-HM86080935-81WWW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6000.7 lumens
Efficiency: N/A
Efficacy: 85.7 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 70
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585304
CATALOG NUMBER: HCC8S80D010BZ-HM86080935-81WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585304

CATALOG NUMBER: HCC8S80D010BZ-HM86080935-81WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	100261	100261	100261
5°	103789	99691	95732
10°	106094	97941	90345
15°	107603	94649	84366
20°	107280	90049	78324
25°	104624	84210	71900
30°	99122	77445	65976
35°	90180	70082	59956
40°	79208	62337	54166
45°	69073	54834	48288
50°	60110	48045	42542
55°	53606	42219	36999
60°	48703	37004	31558
65°	43779	32192	28646
70°	38976	27445	25858
75°	34170	23137	22065
80°	28981	18806	19587
85°	21830	14046	15603



TEST NUMBER: P585304
 CATALOG NUMBER: HCC8S80D010BZ-HM86080935-81WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	304.5	5.1
10°-20°	839.1	14.0
20°-30°	1164.8	19.4
30°-40°	1204.3	20.1
40°-50°	1008.4	16.8
50°-60°	732.0	12.2
60°-70°	461.9	7.7
70°-80°	228.8	3.8
80°-90°	56.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2308.5	38.5
0°-40°	3512.7	58.5
0°-60°	5253.1	87.5
0°-90°	6000.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6000.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	3251	3251	3251	3251	3251	
5°	3353	3313	3221	3132	3093	321
15°	3371	3243	2965	2726	2643	949
25°	3075	2876	2475	2206	2113	1409
35°	2396	2219	1862	1650	1593	1492
45°	1584	1469	1257	1134	1107	1225
55°	997	909	785	719	688	900
65°	600	525	441	388	393	598
75°	287	238	194	185	185	308
85°	62	48	40	44	44	75
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585304

CATALOG NUMBER: HCC8S80D010BZ-HM86080935-81WWW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	3251.4	3251.4	3251.4	3251.4	3251.4	3251.4	3251.4	3251.4	3251.4	3251.4	3251.4
2.5°	3304.5	3304.5	3308.9	3304.5	3304.5	3304.5	3300.1	3300.1	3295.6	3295.6	3286.8
5°	3353.0	3344.2	3353.0	3344.2	3344.2	3344.2	3339.8	3330.9	3326.5	3317.7	3313.3
7.5°	3375.0	3370.6	3370.6	3366.2	3366.2	3361.8	3357.4	3353.0	3335.3	3330.9	3317.7
10°	3388.3	3383.9	3383.9	3379.4	3370.6	3370.6	3361.8	3357.4	3335.3	3326.5	3308.9
12.5°	3383.9	3383.9	3383.9	3379.4	3366.2	3361.8	3353.0	3339.8	3322.1	3304.5	3286.8
15°	3370.6	3370.6	3361.8	3357.4	3344.2	3335.3	3330.9	3308.9	3291.2	3269.2	3242.6
17.5°	3326.5	3326.5	3322.1	3313.3	3300.1	3291.2	3282.4	3260.4	3242.6	3207.3	3180.9
20°	3269.2	3264.8	3260.4	3247.0	3233.8	3229.4	3216.2	3185.3	3163.2	3136.8	3101.5
22.5°	3185.3	3180.9	3176.5	3167.6	3145.6	3136.8	3127.9	3105.9	3066.2	3039.7	2995.6
25°	3075.0	3075.0	3066.2	3053.0	3030.9	3022.1	3008.9	2986.8	2951.5	2911.7	2876.4
27.5°	2947.1	2942.7	2929.5	2920.7	2902.9	2889.7	2867.6	2841.2	2805.9	2775.0	2730.9
30°	2783.8	2783.8	2775.0	2761.8	2739.7	2730.9	2713.3	2682.4	2647.1	2607.4	2576.4
32.5°	2598.6	2598.6	2585.4	2576.4	2563.2	2541.1	2536.7	2501.5	2470.6	2439.7	2404.4
35°	2395.6	2400.0	2391.2	2373.6	2351.5	2351.5	2342.7	2311.8	2276.5	2245.5	2219.1
37.5°	2192.6	2179.4	2175.0	2166.2	2152.9	2135.3	2126.5	2113.2	2082.4	2060.3	2020.6
40°	1967.7	1972.1	1963.3	1954.5	1950.0	1936.8	1932.4	1910.2	1888.3	1861.7	1844.1
42.5°	1764.7	1764.7	1764.7	1755.9	1747.1	1733.8	1729.4	1716.2	1689.7	1672.1	1645.6
45°	1583.9	1570.6	1570.6	1566.2	1561.8	1553.0	1539.8	1530.8	1513.2	1500.0	1469.1
47.5°	1407.4	1411.8	1407.4	1402.9	1389.7	1385.3	1380.9	1363.2	1345.6	1332.4	1310.3
50°	1253.0	1261.8	1253.0	1253.0	1244.2	1239.8	1230.9	1217.7	1204.5	1182.3	1160.3
52.5°	1125.0	1125.0	1120.6	1116.2	1102.9	1094.1	1089.7	1085.3	1063.2	1045.6	1027.9
55°	997.1	1001.5	1001.5	988.3	983.8	975.0	970.6	957.4	948.6	922.1	908.9
57.5°	886.8	882.4	886.8	878.0	869.2	860.2	855.8	847.0	833.8	816.1	798.5
60°	789.7	780.9	780.9	776.4	767.6	763.2	754.4	741.2	727.9	710.3	697.1
62.5°	692.6	688.2	683.8	679.4	670.6	666.2	661.8	648.5	635.3	622.1	608.8
65°	600.0	600.0	595.6	586.8	582.4	578.0	573.6	564.7	547.1	538.3	524.9
67.5°	516.1	511.7	511.7	502.9	494.1	489.7	489.7	480.8	467.6	454.4	445.6
70°	432.3	436.7	432.3	427.9	419.1	419.1	410.3	405.9	388.2	383.8	370.6
72.5°	357.4	357.4	352.9	352.9	344.1	339.7	339.7	330.9	322.1	313.2	304.4
75°	286.8	286.8	286.8	282.4	278.0	269.1	269.1	264.7	255.9	247.1	238.3
77.5°	225.0	220.6	220.6	216.2	211.8	207.4	207.4	203.0	194.2	189.8	180.8
80°	163.2	158.9	158.9	158.9	150.1	154.5	150.1	145.5	141.1	136.7	132.3
82.5°	105.9	110.3	110.3	105.9	101.4	101.4	101.4	97.0	97.0	92.6	88.2
85°	61.7	61.7	61.7	61.7	57.3	57.3	57.3	52.9	52.9	52.9	48.5
87.5°	26.5	26.5	26.5	26.5	26.5	26.5	22.1	22.1	22.1	22.1	22.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585304

CATALOG NUMBER: HCC8S80D010BZ-HM86080935-81WWW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	3251.4	3251.4	3251.4	3251.4	3251.4	3251.4	3251.4	3251.4	3251.4	3251.4	3251.4
2.5°	3286.8	3278.0	3273.6	3269.2	3269.2	3264.8	3260.4	3251.4	3251.4	3242.6	3238.2
5°	3304.5	3291.2	3282.4	3273.6	3269.2	3260.4	3251.4	3238.2	3233.8	3220.6	3207.3
7.5°	3308.9	3286.8	3278.0	3260.4	3251.4	3242.6	3225.0	3211.7	3194.1	3180.9	3163.2
10°	3291.2	3273.6	3251.4	3229.4	3225.0	3211.7	3185.3	3167.6	3145.6	3127.9	3101.5
12.5°	3264.8	3238.2	3216.2	3189.7	3176.5	3163.2	3136.8	3110.3	3079.4	3048.6	3022.1
15°	3220.6	3189.7	3158.8	3127.9	3110.3	3097.1	3066.2	3035.3	3004.5	2964.8	2938.3
17.5°	3154.4	3119.1	3088.3	3048.6	3030.9	3017.7	2978.0	2942.7	2902.9	2863.2	2836.8
20°	3070.6	3026.5	2991.2	2947.1	2933.9	2911.7	2872.0	2832.3	2788.2	2744.1	2713.3
22.5°	2960.3	2916.1	2876.4	2832.3	2810.3	2788.2	2748.5	2700.0	2655.9	2620.6	2589.8
25°	2832.3	2792.6	2744.1	2704.4	2678.0	2651.5	2607.4	2567.6	2527.9	2475.0	2444.1
27.5°	2691.2	2642.7	2607.4	2554.4	2527.9	2510.3	2461.8	2408.8	2373.6	2325.0	2289.8
30°	2532.3	2488.2	2448.5	2395.6	2369.1	2351.5	2307.4	2258.9	2223.5	2175.0	2139.7
32.5°	2364.7	2316.2	2267.7	2232.3	2201.4	2183.8	2135.3	2104.4	2060.3	2020.6	1980.9
35°	2183.8	2135.3	2100.0	2051.5	2033.8	2016.2	1976.5	1936.8	1897.0	1861.7	1830.9
37.5°	1989.7	1954.5	1914.8	1879.5	1866.1	1848.5	1800.0	1764.7	1733.8	1698.5	1672.1
40°	1800.0	1769.1	1742.6	1707.4	1685.3	1672.1	1636.8	1605.9	1570.6	1548.6	1522.0
42.5°	1628.0	1592.7	1566.2	1539.8	1517.6	1504.4	1473.5	1451.5	1425.0	1402.9	1372.1
45°	1447.0	1429.4	1398.5	1376.5	1363.2	1345.6	1323.6	1297.1	1275.0	1257.4	1235.3
47.5°	1288.3	1270.6	1248.6	1222.1	1213.3	1200.1	1177.9	1160.3	1142.6	1125.0	1102.9
50°	1142.6	1120.6	1102.9	1085.3	1076.5	1063.2	1041.2	1032.4	1019.1	1001.5	988.3
52.5°	1010.3	992.7	975.0	953.0	948.6	939.7	926.5	908.9	895.6	886.8	878.0
55°	891.2	873.6	860.2	842.6	838.2	829.4	811.7	802.9	794.1	785.3	776.4
57.5°	785.3	767.6	750.0	741.2	732.3	723.5	719.1	705.9	697.1	692.6	683.8
60°	688.2	670.6	657.4	644.1	639.7	635.3	626.5	617.7	608.8	600.0	595.6
62.5°	595.6	578.0	569.2	560.3	551.5	551.5	542.7	533.9	524.9	520.5	511.7
65°	511.7	502.9	489.7	476.4	472.0	472.0	458.8	454.4	450.0	441.2	432.3
67.5°	432.3	423.5	410.3	405.9	401.5	397.0	392.6	383.8	375.0	370.6	361.8
70°	361.8	352.9	344.1	339.7	335.3	330.9	322.1	317.7	308.8	304.4	300.0
72.5°	291.2	286.8	278.0	273.6	269.1	264.7	260.3	255.9	247.1	242.7	238.3
75°	233.9	229.4	220.6	216.2	211.8	211.8	207.4	198.6	194.2	194.2	189.8
77.5°	176.4	172.0	167.6	163.2	158.9	158.9	154.5	150.1	145.5	145.5	141.1
80°	127.9	123.5	119.1	119.1	119.1	114.7	110.3	110.3	105.9	105.9	101.4
82.5°	83.8	83.8	79.4	79.4	79.4	75.0	75.0	70.6	70.6	70.6	70.6
85°	48.5	48.5	48.5	44.1	44.1	44.1	44.1	44.1	44.1	39.7	44.1
87.5°	22.1	22.1	22.1	22.1	22.1	22.1	22.1	22.1	17.6	17.6	17.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585304

CATALOG NUMBER: HCC8S80D010BZ-HM86080935-81WWW

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	3251.4	3251.4	3251.4	3251.4	3251.4	3251.4	3251.4	3251.4	3251.4	3251.4	3251.4
2.5°	3233.8	3229.4	3220.6	3220.6	3211.7	3211.7	3207.3	3202.9	3198.5	3194.1	3189.7
5°	3202.9	3185.3	3176.5	3172.1	3163.2	3158.8	3145.6	3136.8	3132.4	3123.5	3114.7
7.5°	3145.6	3127.9	3110.3	3105.9	3101.5	3083.8	3070.6	3057.4	3048.6	3039.7	3030.9
10°	3079.4	3061.8	3039.7	3030.9	3022.1	3000.0	2982.4	2969.2	2951.5	2933.9	2929.5
12.5°	3000.0	2973.6	2947.1	2938.3	2925.1	2902.9	2885.3	2863.2	2850.0	2827.9	2823.5
15°	2907.3	2876.4	2854.4	2832.3	2823.5	2801.5	2770.6	2753.0	2726.5	2717.7	2695.6
17.5°	2797.1	2766.2	2735.3	2726.5	2713.3	2682.4	2651.5	2629.5	2603.0	2589.8	2576.4
20°	2682.4	2642.7	2611.8	2603.0	2585.4	2558.8	2527.9	2505.9	2483.8	2457.4	2444.1
22.5°	2550.0	2505.9	2479.4	2457.4	2452.9	2422.1	2386.8	2369.1	2351.5	2329.4	2311.8
25°	2404.4	2364.7	2333.9	2316.2	2307.4	2280.9	2254.5	2232.3	2206.0	2192.6	2170.6
27.5°	2254.5	2227.9	2188.2	2170.6	2157.3	2135.3	2104.4	2091.2	2064.7	2047.1	2033.8
30°	2108.8	2069.1	2047.1	2025.0	2011.8	1989.7	1963.3	1950.0	1928.0	1910.2	1897.0
32.5°	1950.0	1923.6	1892.7	1883.9	1866.1	1844.1	1826.4	1804.4	1786.8	1769.1	1764.7
35°	1804.4	1769.1	1738.2	1729.4	1716.2	1694.1	1685.3	1672.1	1650.0	1645.6	1628.0
37.5°	1645.6	1628.0	1592.7	1579.5	1574.9	1557.4	1539.8	1530.8	1517.6	1504.4	1500.0
40°	1495.6	1473.5	1455.9	1442.6	1433.8	1420.6	1402.9	1398.5	1389.7	1372.1	1367.7
42.5°	1354.4	1332.4	1314.7	1310.3	1297.1	1283.9	1275.0	1261.8	1257.4	1253.0	1244.2
45°	1217.7	1204.5	1186.7	1182.3	1177.9	1160.3	1151.4	1142.6	1133.8	1129.4	1120.6
47.5°	1094.1	1080.9	1067.6	1063.2	1054.4	1050.0	1036.8	1032.4	1019.1	1014.7	1010.3
50°	975.0	966.2	957.4	953.0	944.1	939.7	930.9	922.1	913.3	908.9	904.5
52.5°	869.2	860.2	851.4	847.0	842.6	833.8	825.0	816.1	811.7	807.3	802.9
55°	767.6	758.8	754.4	750.0	745.6	741.2	727.9	723.5	719.1	714.7	705.9
57.5°	675.0	666.2	657.4	657.4	653.0	648.5	639.7	630.9	630.9	622.1	613.3
60°	591.2	582.4	573.6	569.2	564.7	555.9	551.5	547.1	542.7	538.3	529.5
62.5°	502.9	498.5	489.7	489.7	480.8	476.4	472.0	467.6	463.2	454.4	450.0
65°	427.9	423.5	414.7	410.3	410.3	405.9	397.0	392.6	388.2	388.2	383.8
67.5°	357.4	352.9	344.1	339.7	339.7	335.3	330.9	330.9	326.5	322.1	326.5
70°	295.6	286.8	286.8	282.4	282.4	278.0	273.6	273.6	273.6	278.0	278.0
72.5°	233.9	229.4	225.0	225.0	225.0	225.0	220.6	220.6	225.0	229.4	229.4
75°	185.2	180.8	180.8	180.8	176.4	176.4	180.8	180.8	185.2	185.2	185.2
77.5°	136.7	136.7	136.7	136.7	136.7	136.7	141.1	141.1	145.5	145.5	145.5
80°	101.4	101.4	101.4	101.4	101.4	105.9	105.9	105.9	105.9	105.9	110.3
82.5°	70.6	70.6	70.6	70.6	70.6	70.6	70.6	75.0	75.0	75.0	75.0
85°	39.7	44.1	44.1	44.1	44.1	44.1	44.1	44.1	44.1	44.1	44.1
87.5°	17.6	17.6	17.6	17.6	17.6	17.6	17.6	17.6	17.6	17.6	17.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585304

CATALOG NUMBER: HCC8S80D010BZ-HM86080935-81WWW

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	3251.4	3251.4	3251.4	3251.4	3251.4	3251.4	3251.4	3251.4
2.5°	3185.3	3185.3	3185.3	3189.7	3180.9	3180.9	3180.9	3180.9
5°	3110.3	3105.9	3101.5	3105.9	3097.1	3097.1	3092.7	3092.7
7.5°	3017.7	3013.3	3008.9	3008.9	3000.0	3000.0	2995.6	2991.2
10°	2916.1	2907.3	2911.7	2902.9	2898.5	2894.1	2889.7	2885.3
12.5°	2805.9	2797.1	2792.6	2783.8	2775.0	2770.6	2775.0	2766.2
15°	2686.8	2673.6	2669.2	2660.3	2651.5	2647.1	2647.1	2642.7
17.5°	2554.4	2545.6	2541.1	2532.3	2527.9	2519.1	2514.7	2510.3
20°	2430.9	2408.8	2413.2	2404.4	2400.0	2382.4	2382.4	2386.8
22.5°	2294.2	2280.9	2272.1	2263.3	2258.9	2250.1	2250.1	2245.5
25°	2157.3	2144.1	2139.7	2130.9	2126.5	2117.6	2113.2	2113.2
27.5°	2025.0	2007.4	2007.4	1998.6	1989.7	1985.3	1980.9	1976.5
30°	1883.9	1870.7	1866.1	1866.1	1861.7	1861.7	1848.5	1852.9
32.5°	1751.5	1742.6	1738.2	1729.4	1729.4	1725.0	1725.0	1711.8
35°	1619.2	1605.9	1610.3	1601.5	1597.1	1592.7	1597.1	1592.7
37.5°	1491.2	1482.3	1482.3	1473.5	1473.5	1469.1	1464.7	1473.5
40°	1363.2	1358.8	1354.4	1350.0	1354.4	1350.0	1341.2	1345.6
42.5°	1235.3	1235.3	1230.9	1230.9	1226.5	1226.5	1226.5	1226.5
45°	1120.6	1116.2	1116.2	1111.7	1111.7	1111.7	1111.7	1107.3
47.5°	1005.9	1001.5	1001.5	1001.5	997.1	997.1	992.7	997.1
50°	895.6	895.6	891.2	891.2	895.6	891.2	886.8	886.8
52.5°	794.1	794.1	789.7	789.7	785.3	780.9	785.3	785.3
55°	701.5	697.1	692.6	692.6	688.2	683.8	683.8	688.2
57.5°	613.3	608.8	604.4	604.4	595.6	591.2	591.2	591.2
60°	529.5	520.5	520.5	516.1	516.1	511.7	511.7	511.7
62.5°	450.0	445.6	445.6	445.6	445.6	441.2	441.2	441.2
65°	383.8	383.8	383.8	388.2	388.2	392.6	392.6	392.6
67.5°	330.9	335.3	335.3	335.3	339.7	339.7	339.7	335.3
70°	282.4	282.4	282.4	286.8	286.8	286.8	286.8	286.8
72.5°	233.9	233.9	233.9	233.9	233.9	233.9	233.9	233.9
75°	185.2	189.8	189.8	189.8	185.2	189.8	189.8	185.2
77.5°	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5
80°	110.3	110.3	110.3	110.3	110.3	110.3	110.3	110.3
82.5°	75.0	75.0	75.0	75.0	75.0	75.0	75.0	75.0
85°	44.1	44.1	44.1	44.1	44.1	44.1	44.1	44.1
87.5°	17.6	17.6	17.6	17.6	17.6	17.6	17.6	17.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)