

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585322

Luminaire Tested: **HCC8W80D010BZ-HM86080940-81WWWB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585322  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W80D010BZ-HM86080940-81WWWB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6444.5 lumens  
Efficiency: N/A  
Efficacy: 92.1 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 70  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585322  
CATALOG NUMBER: HCC8W80D010BZ-HM86080940-81WWWB

### Luminous Intensity Polar Plot





TEST NUMBER: P585322

CATALOG NUMBER: HCC8W80D010BZ-HM86080940-81WWWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75								
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65								
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57								
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50								
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45								
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40								
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37								
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33								
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	98806	98806	98806
5°	102427	98480	95100
10°	105321	97625	91209
15°	107667	95900	87182
20°	107838	92155	83643
25°	105767	87030	80681
30°	100315	80706	77142
35°	91152	73504	73673
40°	79699	65960	69438
45°	69073	58755	64707
50°	60484	52185	58959
55°	53837	46246	53342
60°	48561	41543	46877
65°	43837	36534	40846
70°	39400	30780	30366
75°	34706	24412	22780
80°	29087	20209	21824
85°	22538	17726	19318

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P585322

CATALOG NUMBER: HCC8W80D010BZ-HM86080940-81WWWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	302.3	4.7
10°-20°	851.4	13.2
20°-30°	1216.8	18.9
30°-40°	1292.9	20.1
40°-50°	1113.1	17.3
50°-60°	832.2	12.9
60°-70°	530.8	8.2
70°-80°	241.6	3.7
80°-90°	63.4	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2370.5	36.8
0°-40°	3663.3	56.8
0°-60°	5608.7	87.0
0°-90°	6444.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6444.5	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	3204	3204	3204	3204	3204	
5°	3309	3263	3182	3100	3072	317
15°	3373	3259	3004	2799	2731	950
25°	3109	2913	2558	2403	2371	1423
35°	2421	2253	1953	1902	1957	1508
45°	1584	1497	1347	1384	1484	1231
55°	1001	920	860	933	992	900
65°	601	533	501	523	560	599
75°	291	250	205	187	191	310
85°	64	55	50	55	55	77
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585322

CATALOG NUMBER: HCC8W80D010BZ-HM86080940-81WWWB

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	3204.2	3204.2	3204.2	3204.2	3204.2	3204.2	3204.2	3204.2	3204.2	3204.2	3204.2
2.5°	3263.4	3254.3	3258.8	3254.3	3258.8	3258.8	3249.8	3249.8	3249.8	3249.8	3236.1
5°	3309.0	3304.3	3304.3	3299.8	3295.3	3299.8	3295.3	3290.7	3281.6	3277.1	3263.4
7.5°	3336.2	3336.2	3336.2	3336.2	3331.7	3327.2	3322.5	3313.5	3304.3	3295.3	3286.2
10°	3363.6	3368.1	3363.6	3359.0	3354.4	3345.4	3340.7	3331.7	3318.0	3304.3	3295.3
12.5°	3377.2	3377.2	3372.6	3372.6	3363.6	3359.0	3345.4	3331.7	3318.0	3304.3	3281.6
15°	3372.6	3372.6	3368.1	3363.6	3349.9	3345.4	3336.2	3322.5	3299.8	3281.6	3258.8
17.5°	3345.4	3340.7	3331.7	3331.7	3313.5	3309.0	3299.8	3281.6	3258.8	3231.6	3204.2
20°	3286.2	3286.2	3281.6	3277.1	3258.8	3245.3	3236.1	3213.4	3195.2	3163.3	3136.0
22.5°	3204.2	3213.4	3204.2	3195.2	3172.4	3167.9	3154.2	3126.8	3099.6	3063.1	3031.2
25°	3108.6	3104.1	3099.6	3090.4	3072.3	3063.1	3044.9	3017.7	2990.3	2949.3	2912.9
27.5°	2985.8	2967.6	2967.6	2949.3	2935.8	2922.1	2912.9	2885.6	2849.2	2817.3	2771.8
30°	2817.3	2822.0	2799.1	2794.6	2771.8	2762.8	2744.6	2717.2	2685.4	2649.0	2612.6
32.5°	2635.3	2621.6	2621.6	2603.4	2585.2	2571.6	2567.1	2535.2	2507.8	2471.5	2435.1
35°	2421.4	2421.4	2407.7	2403.2	2385.0	2375.9	2362.2	2344.0	2312.1	2280.3	2253.0
37.5°	2212.0	2202.9	2198.3	2189.3	2175.6	2162.0	2162.0	2130.1	2125.6	2089.1	2052.7
40°	1979.9	1989.0	1979.9	1966.2	1961.7	1952.6	1948.1	1929.9	1916.2	1884.3	1861.5
42.5°	1784.2	1775.1	1775.1	1770.5	1752.3	1752.3	1743.2	1734.2	1711.3	1702.3	1674.9
45°	1583.9	1593.0	1579.3	1583.9	1565.7	1565.7	1565.7	1547.5	1529.3	1515.6	1497.4
47.5°	1411.0	1415.5	1415.5	1401.8	1397.3	1397.3	1388.2	1379.1	1365.4	1347.3	1333.6
50°	1260.8	1265.3	1256.2	1251.7	1242.5	1238.0	1238.0	1219.8	1210.6	1192.4	1183.4
52.5°	1124.2	1124.2	1119.7	1119.7	1106.0	1106.0	1096.9	1083.3	1074.1	1065.1	1042.3
55°	1001.4	1001.4	996.7	992.2	992.2	978.5	974.0	960.4	951.3	933.0	919.5
57.5°	883.0	887.6	883.0	878.4	873.9	869.3	860.2	846.6	837.5	823.9	814.7
60°	787.4	787.4	782.8	778.3	769.2	764.6	760.1	751.0	737.3	728.3	714.6
62.5°	696.4	691.9	687.2	682.7	673.6	673.6	664.5	655.4	641.7	632.7	623.5
65°	600.8	600.8	596.3	596.3	591.6	582.6	578.1	573.5	555.3	550.7	532.6
67.5°	514.4	518.9	509.7	509.7	500.7	500.7	496.2	482.5	477.9	468.8	459.7
70°	437.0	437.0	437.0	432.4	423.3	418.8	414.1	405.1	400.6	391.4	382.4
72.5°	359.6	359.6	355.0	355.0	350.5	345.9	341.4	332.2	332.2	323.2	314.0
75°	291.3	291.3	286.8	282.1	277.6	277.6	273.1	268.6	259.4	254.9	250.3
77.5°	223.1	223.1	223.1	218.4	213.9	213.9	213.9	204.9	195.7	195.7	191.2
80°	163.8	163.8	159.3	159.3	154.8	154.8	154.8	150.2	145.7	141.1	136.5
82.5°	109.3	109.3	109.3	109.3	104.6	104.6	104.6	100.1	95.6	95.6	95.6
85°	63.7	63.7	63.7	63.7	59.2	59.2	59.2	59.2	59.2	54.6	54.6
87.5°	27.3	22.7	27.3	22.7	27.3	22.7	27.3	22.7	22.7	22.7	22.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585322

CATALOG NUMBER: HCC8W80D010BZ-HM86080940-81WWWB

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	3204.2	3204.2	3204.2	3204.2	3204.2	3204.2	3204.2	3204.2	3204.2	3204.2	3204.2
2.5°	3240.6	3236.1	3231.6	3226.9	3226.9	3222.4	3213.4	3208.8	3204.2	3199.7	3199.7
5°	3258.8	3254.3	3245.3	3236.1	3231.6	3222.4	3213.4	3204.2	3195.2	3181.5	3176.9
7.5°	3272.5	3258.8	3249.8	3231.6	3226.9	3217.9	3204.2	3190.6	3172.4	3154.2	3140.5
10°	3272.5	3254.3	3240.6	3217.9	3208.8	3199.7	3181.5	3158.7	3136.0	3117.8	3095.0
12.5°	3263.4	3240.6	3217.9	3195.2	3181.5	3167.9	3140.5	3117.8	3090.4	3063.1	3044.9
15°	3231.6	3204.2	3176.9	3149.7	3136.0	3117.8	3090.4	3058.6	3031.2	3004.0	2972.1
17.5°	3172.4	3145.0	3113.2	3081.4	3063.1	3049.5	3008.5	2985.8	2944.8	2917.4	2890.2
20°	3095.0	3063.1	3022.2	2990.3	2967.6	2954.0	2922.1	2881.1	2849.2	2808.3	2781.0
22.5°	2994.9	2954.0	2912.9	2881.1	2858.4	2840.2	2799.1	2758.2	2730.9	2694.5	2662.6
25°	2876.5	2835.5	2794.6	2749.1	2726.4	2708.2	2671.7	2635.3	2598.9	2557.9	2530.7
27.5°	2735.4	2689.9	2653.5	2612.6	2589.8	2562.5	2521.5	2485.1	2448.7	2421.4	2385.0
30°	2580.7	2530.7	2494.2	2453.3	2430.4	2407.7	2366.8	2330.3	2298.5	2266.6	2248.4
32.5°	2394.1	2357.7	2321.3	2280.3	2262.1	2248.4	2207.5	2171.1	2134.6	2107.4	2093.7
35°	2216.5	2175.6	2143.8	2107.4	2084.6	2070.9	2034.5	2002.6	1984.4	1952.6	1934.4
37.5°	2030.0	1998.1	1961.7	1925.2	1911.7	1898.0	1870.7	1838.8	1811.4	1788.7	1779.6
40°	1834.3	1806.9	1775.1	1752.3	1738.7	1725.0	1702.3	1679.5	1661.3	1638.6	1629.4
42.5°	1647.6	1629.4	1602.2	1574.8	1561.2	1556.6	1529.3	1511.1	1501.9	1492.9	1483.8
45°	1479.2	1451.9	1433.7	1415.5	1401.8	1392.8	1379.1	1365.4	1356.3	1347.3	1338.1
47.5°	1315.4	1292.6	1274.4	1260.8	1247.1	1242.5	1233.5	1219.8	1210.6	1210.6	1210.6
50°	1165.2	1147.0	1128.7	1119.7	1115.2	1106.0	1096.9	1092.3	1087.8	1087.8	1087.8
52.5°	1033.2	1014.9	1001.4	992.2	992.2	983.1	974.0	969.5	969.5	969.5	969.5
55°	910.3	896.6	887.6	878.4	869.3	864.8	864.8	864.8	860.2	860.2	864.8
57.5°	801.0	792.0	778.3	769.2	764.6	764.6	760.1	755.5	760.1	764.6	769.2
60°	700.9	691.9	687.2	673.6	673.6	673.6	669.1	669.1	669.1	673.6	678.2
62.5°	610.0	605.3	596.3	591.6	587.1	587.1	582.6	582.6	582.6	582.6	587.1
65°	527.9	518.9	509.7	509.7	509.7	505.2	505.2	496.2	500.7	500.7	496.2
67.5°	450.6	441.5	437.0	432.4	427.8	427.8	423.3	418.8	414.1	414.1	414.1
70°	377.7	368.7	368.7	359.6	359.6	355.0	350.5	350.5	345.9	341.4	336.8
72.5°	305.0	300.3	295.8	291.3	291.3	291.3	286.8	282.1	277.6	273.1	264.0
75°	241.2	241.2	232.1	227.6	227.6	223.1	218.4	213.9	209.4	204.9	200.2
77.5°	186.6	182.0	173.0	168.4	168.4	168.4	163.8	159.3	154.8	150.2	145.7
80°	136.5	132.0	127.5	122.9	122.9	122.9	118.3	118.3	113.8	113.8	113.8
82.5°	91.1	91.1	86.4	86.4	86.4	86.4	81.9	81.9	81.9	81.9	81.9
85°	54.6	54.6	50.1	50.1	50.1	50.1	50.1	50.1	50.1	50.1	50.1
87.5°	22.7	22.7	22.7	22.7	22.7	22.7	22.7	22.7	22.7	22.7	22.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585322

CATALOG NUMBER: HCC8W80D010BZ-HM86080940-81WWWB

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	3204.2	3204.2	3204.2	3204.2	3204.2	3204.2	3204.2	3204.2	3204.2	3204.2	3204.2
2.5°	3190.6	3190.6	3181.5	3176.9	3172.4	3176.9	3167.9	3163.3	3158.7	3158.7	3154.2
5°	3163.3	3158.7	3140.5	3136.0	3131.5	3126.8	3117.8	3108.6	3099.6	3095.0	3090.4
7.5°	3126.8	3113.2	3095.0	3090.4	3085.9	3072.3	3058.6	3049.5	3035.9	3031.2	3022.2
10°	3076.8	3058.6	3044.9	3031.2	3022.2	3008.5	2994.9	2981.2	2963.0	2958.5	2944.8
12.5°	3017.7	2994.9	2967.6	2963.0	2949.3	2931.1	2912.9	2899.3	2885.6	2876.5	2862.9
15°	2944.8	2922.1	2894.7	2881.1	2867.4	2853.8	2831.0	2812.8	2799.1	2785.5	2771.8
17.5°	2858.4	2831.0	2808.3	2794.6	2785.5	2762.8	2744.6	2721.7	2708.2	2694.5	2680.8
20°	2753.6	2730.9	2699.0	2685.4	2680.8	2662.6	2639.8	2630.8	2612.6	2598.9	2589.8
22.5°	2635.3	2612.6	2585.2	2576.1	2557.9	2548.9	2526.0	2517.0	2507.8	2494.2	2489.6
25°	2503.3	2480.6	2457.8	2453.3	2439.6	2430.4	2416.9	2403.2	2403.2	2389.5	2389.5
27.5°	2366.8	2344.0	2325.8	2316.6	2312.1	2303.1	2289.4	2284.9	2280.3	2275.7	2275.7
30°	2221.2	2193.8	2184.7	2180.2	2175.6	2166.5	2162.0	2152.8	2157.4	2162.0	2157.4
32.5°	2066.4	2057.3	2039.0	2030.0	2034.5	2030.0	2020.8	2030.0	2025.5	2034.5	2039.0
35°	1916.2	1907.0	1898.0	1898.0	1888.8	1888.8	1888.8	1893.4	1902.5	1907.0	1916.2
37.5°	1770.5	1756.9	1752.3	1747.7	1752.3	1752.3	1752.3	1761.4	1770.5	1779.6	1793.2
40°	1615.7	1606.7	1606.7	1606.7	1606.7	1620.4	1615.7	1624.9	1633.9	1647.6	1661.3
42.5°	1470.1	1470.1	1474.7	1474.7	1474.7	1474.7	1483.8	1497.4	1511.1	1524.8	1538.4
45°	1333.6	1333.6	1333.6	1342.7	1342.7	1347.3	1365.4	1374.6	1383.6	1397.3	1411.0
47.5°	1206.1	1206.1	1210.6	1215.3	1219.8	1229.0	1238.0	1251.7	1265.3	1274.4	1288.0
50°	1087.8	1092.3	1101.5	1110.5	1110.5	1115.2	1128.7	1137.9	1147.0	1160.6	1165.2
52.5°	974.0	983.1	992.2	996.7	1001.4	1010.4	1014.9	1028.6	1033.2	1046.8	1051.4
55°	869.3	873.9	887.6	892.1	892.1	901.1	910.3	919.5	933.0	933.0	942.2
57.5°	773.8	778.3	787.4	792.0	787.4	801.0	805.7	814.7	819.2	828.4	832.9
60°	678.2	687.2	691.9	691.9	696.4	700.9	710.1	710.1	719.1	728.3	728.3
62.5°	587.1	591.6	596.3	600.8	605.3	600.8	614.5	614.5	623.5	628.1	637.2
65°	500.7	505.2	505.2	509.7	509.7	514.4	514.4	518.9	523.4	532.6	537.1
67.5°	414.1	414.1	414.1	418.8	414.1	418.8	418.8	423.3	423.3	432.4	437.0
70°	336.8	332.2	327.7	327.7	327.7	327.7	323.2	327.7	327.7	332.2	332.2
72.5°	259.4	254.9	250.3	245.8	245.8	241.2	236.7	241.2	241.2	245.8	245.8
75°	195.7	186.6	186.6	186.6	182.0	182.0	182.0	186.6	186.6	186.6	191.2
77.5°	145.7	145.7	141.1	141.1	141.1	145.7	145.7	150.2	150.2	150.2	150.2
80°	109.3	113.8	113.8	113.8	113.8	118.3	118.3	118.3	118.3	122.9	122.9
82.5°	81.9	81.9	81.9	81.9	86.4	86.4	86.4	86.4	86.4	86.4	86.4
85°	50.1	54.6	54.6	50.1	54.6	54.6	54.6	54.6	54.6	54.6	54.6
87.5°	22.7	22.7	22.7	22.7	22.7	22.7	22.7	22.7	22.7	22.7	22.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585322

CATALOG NUMBER: HCC8W80D010BZ-HM86080940-81WWWB

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	3204.2	3204.2	3204.2	3204.2	3204.2	3204.2	3204.2	3204.2
2.5°	3149.7	3149.7	3149.7	3149.7	3145.0	3145.0	3145.0	3140.5
5°	3081.4	3081.4	3081.4	3072.3	3076.8	3076.8	3067.7	3072.3
7.5°	3013.0	3008.5	3004.0	3004.0	2999.4	2994.9	2990.3	2994.9
10°	2935.8	2922.1	2922.1	2917.4	2917.4	2908.4	2908.4	2912.9
12.5°	2849.2	2840.2	2840.2	2835.5	2831.0	2826.5	2822.0	2822.0
15°	2762.8	2753.6	2749.1	2744.6	2740.1	2730.9	2735.4	2730.9
17.5°	2676.3	2662.6	2662.6	2658.0	2653.5	2644.5	2644.5	2639.8
20°	2576.1	2571.6	2562.5	2567.1	2562.5	2553.4	2548.9	2548.9
22.5°	2476.0	2476.0	2471.5	2471.5	2466.9	2462.3	2457.8	2457.8
25°	2380.4	2375.9	2380.4	2380.4	2366.8	2366.8	2366.8	2371.3
27.5°	2271.2	2275.7	2271.2	2271.2	2271.2	2271.2	2275.7	2271.2
30°	2162.0	2162.0	2162.0	2166.5	2175.6	2171.1	2171.1	2166.5
32.5°	2043.7	2048.2	2048.2	2052.7	2057.3	2066.4	2066.4	2070.9
35°	1925.2	1934.4	1938.9	1934.4	1948.1	1948.1	1957.1	1957.1
37.5°	1802.4	1806.9	1816.1	1820.6	1829.8	1834.3	1838.8	1838.8
40°	1670.4	1688.6	1693.1	1697.7	1711.3	1711.3	1716.0	1725.0
42.5°	1547.5	1565.7	1570.3	1574.8	1583.9	1597.5	1593.0	1602.2
45°	1429.2	1442.9	1447.4	1451.9	1465.6	1470.1	1470.1	1483.8
47.5°	1301.7	1310.9	1315.4	1324.4	1333.6	1342.7	1351.8	1347.3
50°	1174.3	1187.9	1197.1	1201.6	1215.3	1219.8	1224.3	1229.0
52.5°	1060.5	1069.6	1074.1	1078.7	1092.3	1096.9	1101.5	1110.5
55°	951.3	955.8	964.9	960.4	974.0	978.5	983.1	992.2
57.5°	842.0	846.6	851.1	851.1	860.2	869.3	873.9	878.4
60°	737.3	746.5	751.0	751.0	751.0	760.1	760.1	760.1
62.5°	641.7	641.7	646.3	646.3	655.4	655.4	655.4	655.4
65°	541.6	546.2	550.7	550.7	559.8	555.3	564.4	559.8
67.5°	437.0	437.0	446.0	446.0	441.5	446.0	446.0	446.0
70°	332.2	332.2	336.8	336.8	336.8	336.8	336.8	336.8
72.5°	245.8	245.8	245.8	250.3	245.8	245.8	250.3	245.8
75°	191.2	191.2	191.2	191.2	191.2	191.2	191.2	191.2
77.5°	150.2	150.2	154.8	154.8	154.8	154.8	154.8	154.8
80°	122.9	122.9	122.9	122.9	127.5	122.9	122.9	122.9
82.5°	91.1	86.4	91.1	86.4	91.1	91.1	91.1	91.1
85°	54.6	54.6	54.6	54.6	54.6	54.6	54.6	54.6
87.5°	22.7	22.7	22.7	22.7	22.7	22.7	22.7	22.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)