

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P855585

Luminaire Tested: **HLS4079FS1EWH-3500K**

Issue Date: 7/16/2024

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P855585
 Test Lab:
 Issue Date: 7/16/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO
 Catalog Number: HLS4079FS1EWH-3500K
 Description: 4IN 750LM, 90CRI, DIMMING TO 10%, DAMP LOCATION
 Light Source: SELECTABLE CCT 90CRI / 3500K CCT
 Ballast/Driver: -

Summary

Lumens per Lamp: 770.28 (1 lamp)
 Luminaire Lumens: 785.0 lumens
 Efficiency: 101.9%
 Efficacy: 86.3 lumens/watt
 Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.37
 Luminous Opening: Circular (Dia: 0.33' x H: 0')
 CIE Type: Direct


Input Watts (W): 9.1
 Input Voltage (V): NR
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT



Meas		Calibration Due Date	
Instrument	Identificatio		
Photometer	GONIO 1 11111111	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P855585
CATALOG NUMBER: HLS4079FS1EWH-3500K

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° ···· 90°-270° - · - · 135°-315°

TEST NUMBER: P855585
 CATALOG NUMBER: HLS4079FS1EWH-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	121	121	121	121	119	119	119	119	113	113	113	108	108	108	104	104	104	104	104	104	102
1	110	105	100	96	107	102	98	94	98	94	91	94	91	88	90	88	86	86	86	86	84
2	100	91	84	77	97	89	82	76	85	80	75	82	77	73	79	75	71	71	71	71	69
3	91	80	71	64	88	78	70	63	75	68	62	72	66	61	69	64	60	60	60	60	58
4	83	70	61	54	81	69	60	54	66	59	53	64	57	52	62	56	51	51	51	51	49
5	76	63	53	46	74	62	53	46	59	52	46	57	51	45	56	49	45	45	45	45	42
6	70	57	47	40	68	56	47	40	54	46	40	52	45	40	50	44	39	39	39	39	37
7	65	51	42	36	63	50	42	36	49	41	35	47	40	35	46	40	35	35	35	35	33
8	61	47	38	32	59	46	38	32	45	37	32	43	36	31	42	36	31	31	31	31	29
9	57	43	34	29	55	42	34	29	41	34	28	40	33	28	39	33	28	28	28	28	26
10	53	40	31	26	52	39	31	26	38	31	26	37	30	26	36	30	25	25	25	25	24

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	33463	33463	33463	33463
5°	33414	33490	33440	33339
10°	33341	33494	33366	33187
15°	33198	33445	33211	33002
20°	33026	33374	33040	32758
25°	32813	33243	32826	32396
30°	32551	33046	32551	32057
35°	32263	32847	32279	31649
40°	31904	32660	31953	31198
45°	31502	32392	31538	30701
50°	31052	32090	31071	30073
55°	30520	31749	30586	29357
60°	29877	31412	29952	28467
65°	29153	30910	29302	27426
70°	28480	30541	28664	26272
75°	28154	30585	28348	25285
80°	29352	32106	29569	25366
85°	37832	41442	37976	30901

TEST NUMBER: P855585
 CATALOG NUMBER: HLS4079FS1EWH-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture	% Lamp
0°-10°	25.1	3.2	3.3
10°-20°	72.0	9.2	9.3
20°-30°	109.0	13.9	14.1
30°-40°	131.4	16.7	17.1
40°-50°	136.7	17.4	17.7
50°-60°	124.4	15.8	16.2
60°-70°	97.0	12.4	12.6
70°-80°	61.3	7.8	8.0
80°-90°	28.0	3.6	3.6
90°-100°	0.0	0.0	0.0
100°-110°	0.0	0.0	0.0
110°-120°	0.0	0.0	0.0
120°-130°	0.0	0.0	0.0
130°-140°	0.0	0.0	0.0
140°-150°	0.0	0.0	0.0
150°-160°	0.0	0.0	0.0
160°-170°	0.0	0.0	0.0
170°-180°	0.0	0.0	0.0
0°-30°	206.1	26.3	26.8
0°-40°	337.5	43.0	43.8
0°-60°	598.6	76.3	77.7
0°-90°	785.0	100.0	101.9
90°-120°	0.0	0.0	0.0
90°-150°	0.0	0.0	0.0
90°-180°	0.0	0.0	0.0
0°-180°	785.0	100.0	101.9

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	266	266	266	266	266	
5°	264	265	265	264	264	25
15°	255	257	255	253	255	72
25°	236	239	236	233	236	109
35°	210	214	210	206	210	131
45°	177	182	177	172	177	137
55°	139	145	139	134	139	124
65°	98	104	98	92	98	97
75°	58	63	58	52	58	61
85°	26	29	26	21	26	29
90°	0	0	0	0	0	

TEST NUMBER: P855585
 CATALOG NUMBER: HLS4079FS1EWH-3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	265.9	265.9	265.9	265.9	265.9	265.9	265.9	265.9	265.9	265.9	265.9
0.5°	265.6	265.8	266.0	266.1	265.8	266.2	266.1	265.7	265.7	265.6	265.9
1°	265.6	265.8	266.0	266.1	266.0	266.2	266.1	265.9	265.5	265.8	265.8
1.5°	265.8	265.7	265.6	266.5	266.1	266.1	266.2	265.9	265.8	265.5	265.5
2°	265.5	265.8	265.8	266.2	266.1	265.9	266.0	265.7	265.7	265.2	265.6
2.5°	265.4	265.7	266.0	266.0	265.7	266.1	266.1	265.5	265.4	265.4	265.6
3°	265.4	265.5	265.6	265.9	265.6	266.0	265.9	265.6	265.2	265.4	265.0
3.5°	265.4	265.4	265.4	266.1	265.8	265.9	265.5	265.2	265.4	264.7	264.9
4°	264.9	265.4	265.4	265.9	265.7	265.5	265.5	264.8	264.9	265.0	265.0
4.5°	264.6	265.0	265.2	265.6	265.2	265.7	265.5	265.0	264.7	264.6	264.6
5°	264.5	264.6	264.9	265.2	265.1	265.4	265.0	264.8	264.7	264.1	264.2
5.5°	264.3	264.6	264.7	265.2	265.1	264.8	264.8	264.4	264.3	264.0	264.2
6°	264.1	264.4	264.8	265.0	264.6	264.7	264.7	264.3	263.6	264.1	263.7
6.5°	263.8	264.1	264.2	264.7	264.4	264.7	264.4	264.2	263.7	263.2	263.3
7°	263.5	263.8	263.8	264.3	264.4	264.2	264.0	263.7	263.8	263.1	263.0
7.5°	263.0	263.4	263.8	264.0	264.0	264.1	263.9	263.3	263.0	262.8	262.7
8°	262.6	263.2	263.3	263.9	263.4	263.9	263.5	263.0	262.5	262.3	262.2
8.5°	262.4	262.7	262.7	263.3	263.4	263.4	263.0	262.8	262.3	261.7	261.6
9°	261.9	262.3	262.5	262.8	263.2	262.8	262.5	262.3	261.8	261.6	261.2
9.5°	261.2	262.0	262.1	262.6	262.3	262.5	262.3	261.6	261.3	261.1	261.0
10°	260.9	261.4	261.5	262.2	262.1	262.3	262.0	261.3	261.1	260.3	260.3
10.5°	260.5	260.9	261.2	261.9	261.8	261.8	261.3	261.2	260.5	259.7	259.7
11°	259.8	260.7	260.7	261.4	261.2	261.1	260.9	260.2	259.8	259.5	259.3
11.5°	259.4	260.0	260.6	260.7	260.6	260.6	260.6	259.8	259.3	258.8	258.8
12°	258.9	259.4	259.7	260.3	260.3	260.2	259.8	259.5	259.0	258.3	258.1
12.5°	258.2	258.8	259.1	259.9	259.8	259.7	259.3	259.0	258.3	257.8	257.2
13°	257.4	258.5	258.7	259.3	259.2	259.2	258.8	258.3	257.5	257.2	257.0
13.5°	257.1	257.6	258.3	258.4	258.5	258.7	258.2	257.4	256.9	256.2	256.4
14°	256.5	257.2	257.3	257.8	257.9	258.1	257.4	256.8	256.5	255.9	255.3
14.5°	255.7	256.3	256.9	257.5	257.5	257.3	256.8	256.5	255.6	255.2	254.6
15°	254.8	255.7	256.2	256.8	256.7	256.6	256.3	255.6	254.9	254.2	254.2
15.5°	254.4	255.0	255.3	256.0	256.1	256.1	255.8	254.8	254.3	253.5	253.3
16°	253.5	254.5	254.6	255.3	255.6	255.3	254.7	254.2	253.3	252.9	252.4
16.5°	252.6	253.4	254.1	254.5	254.6	254.4	254.1	253.4	252.5	251.9	251.9
17°	251.9	252.7	253.3	253.9	253.8	253.8	253.5	252.6	252.0	251.3	250.9
17.5°	251.2	252.1	252.3	253.0	253.2	253.2	252.6	251.9	251.2	250.4	249.8
18°	250.1	251.2	251.6	251.9	252.6	252.2	251.6	251.2	250.1	249.4	249.2
18.5°	249.5	250.4	251.0	251.4	251.6	251.6	251.1	250.2	249.3	248.5	248.4
19°	248.6	249.7	249.9	250.8	250.7	250.9	250.2	249.0	248.6	248.0	247.3
19.5°	247.6	248.5	249.1	249.7	250.0	249.9	249.2	248.6	247.5	246.8	246.4
20°	246.6	247.6	248.6	248.8	249.2	248.9	248.4	247.7	246.7	245.8	245.5
20.5°	245.9	247.0	247.3	247.9	247.9	247.8	247.5	246.5	245.9	244.8	244.4
21°	244.9	246.0	246.2	247.1	247.3	247.1	246.5	245.6	244.7	244.0	243.4
21.5°	243.9	244.8	245.6	246.1	246.6	246.3	245.6	244.8	243.6	242.8	242.6
22°	242.9	244.0	244.6	244.9	245.4	245.2	244.7	243.5	242.9	242.0	241.5

TEST NUMBER: P855585
 CATALOG NUMBER: HLS4079FS1EWH-3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
22.5°	241.9	243.0	243.6	244.2	244.2	244.3	243.7	242.5	241.9	241.0	240.2
23°	240.6	241.8	242.5	243.1	243.4	243.4	242.5	241.8	240.5	239.9	239.2
23.5°	239.6	240.9	241.5	242.3	242.5	242.3	241.6	240.7	239.7	238.7	238.5
24°	238.9	239.9	240.3	241.0	241.6	241.2	240.6	239.5	238.7	237.7	236.9
24.5°	237.6	238.6	239.4	239.8	240.3	240.1	239.3	238.6	237.3	236.5	235.8
25°	236.3	237.5	238.2	239.0	239.4	239.2	238.5	237.4	236.4	235.3	234.8
25.5°	235.3	236.8	237.2	237.9	238.3	238.0	237.4	236.1	235.4	234.2	233.8
26°	234.2	235.4	235.9	236.6	237.1	236.7	236.1	234.9	233.9	233.1	232.3
26.5°	232.9	234.0	234.7	235.4	235.8	235.7	235.0	234.2	232.6	231.8	231.3
27°	231.9	233.0	233.7	234.5	234.8	234.6	234.1	232.8	231.8	230.7	230.1
27.5°	230.5	231.9	232.6	233.3	233.8	233.3	232.5	231.5	230.5	229.5	228.9
28°	229.2	230.4	231.3	231.9	232.4	232.1	231.4	230.1	229.0	228.1	227.2
28.5°	227.9	229.3	230.1	230.6	231.0	230.9	230.4	229.2	227.9	226.9	226.3
29°	226.8	228.0	228.7	229.5	230.0	229.6	229.0	227.8	226.9	225.8	225.2
29.5°	225.5	226.5	227.7	228.3	228.8	228.3	227.5	226.7	225.2	224.4	223.4
30°	224.0	225.3	226.0	227.2	227.4	227.3	226.5	225.2	224.0	222.8	222.1
30.5°	222.7	224.3	224.8	225.6	226.3	225.9	225.2	224.1	222.9	221.7	221.0
31°	221.4	222.7	223.8	224.2	225.1	224.6	223.8	222.8	221.4	220.3	219.5
31.5°	220.1	221.4	222.4	223.0	223.5	223.1	222.5	221.1	219.8	218.9	217.9
32°	218.6	220.1	220.7	221.9	222.2	222.0	221.2	219.8	218.7	217.5	216.7
32.5°	217.4	218.7	219.6	220.3	220.9	220.6	219.7	218.6	217.3	216.1	215.3
33°	215.7	217.3	218.1	218.9	219.7	219.1	218.2	217.2	215.6	214.7	213.7
33.5°	214.3	215.8	216.9	217.4	218.2	217.7	217.1	215.6	214.5	213.2	212.2
34°	212.9	214.6	215.3	216.0	216.8	216.6	215.7	214.2	213.1	211.9	210.9
34.5°	211.6	212.9	213.8	214.8	215.4	214.9	214.1	213.0	211.3	210.2	209.4
35°	210.0	211.3	212.5	213.3	213.8	213.3	212.7	211.4	210.1	208.6	207.7
35.5°	208.5	210.0	211.0	211.7	212.3	212.1	211.2	209.9	208.7	207.3	206.3
36°	206.9	208.5	209.4	210.1	211.0	210.6	209.7	208.5	206.9	205.8	204.9
36.5°	205.5	207.1	208.0	208.9	209.6	209.2	208.2	207.1	205.4	204.1	203.1
37°	203.9	205.4	206.5	207.3	207.8	207.6	206.9	205.4	204.1	202.6	201.4
37.5°	202.3	203.9	205.0	205.6	206.3	206.0	205.2	203.7	202.4	201.1	200.2
38°	200.8	202.4	203.3	204.0	205.1	204.7	203.6	202.2	200.7	199.4	198.5
38.5°	199.1	200.7	201.8	202.7	203.5	202.9	201.9	200.7	199.4	197.9	196.6
39°	197.5	199.0	200.4	201.1	201.9	201.2	200.5	199.1	197.6	196.4	195.0
39.5°	196.0	197.7	198.6	199.5	200.3	199.8	198.9	197.5	195.9	194.5	193.5
40°	194.2	195.8	197.0	197.7	198.8	198.2	197.2	195.9	194.5	192.9	191.8
40.5°	192.5	194.0	195.5	196.2	197.1	196.6	195.6	194.3	192.8	191.3	190.2
41°	191.0	192.5	193.7	194.7	195.4	194.9	194.0	192.4	190.8	189.6	188.5
41.5°	189.3	191.0	192.0	192.9	193.8	193.3	192.3	190.8	189.2	187.9	186.8
42°	187.6	189.1	190.5	191.1	192.3	191.8	190.7	189.4	187.7	186.3	184.9
42.5°	185.9	187.5	188.8	189.6	190.4	189.9	189.1	187.6	186.0	184.4	183.4
43°	184.0	185.8	186.9	188.1	188.7	188.3	187.4	185.7	184.3	182.7	181.7
43.5°	182.3	184.1	185.3	186.2	187.2	186.7	185.4	184.1	182.6	181.0	179.8
44°	180.7	182.3	183.6	184.2	185.4	184.9	183.9	182.4	180.7	179.2	177.9
44.5°	179.0	180.6	181.9	182.7	183.7	183.0	182.1	180.6	178.9	177.4	176.4

TEST NUMBER: P855585
 CATALOG NUMBER: HLS4079FS1EWH-3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
45°	177.0	178.9	180.1	181.0	182.0	181.5	180.4	178.8	177.2	175.8	174.3
45.5°	175.2	176.9	178.4	179.3	180.4	179.8	178.6	177.2	175.6	174.0	172.7
46°	173.6	175.1	176.7	177.5	178.5	177.8	176.9	175.4	173.6	172.1	170.9
46.5°	171.6	173.5	174.7	175.5	176.5	176.1	175.0	173.5	171.7	170.3	169.0
47°	169.7	171.6	172.9	173.9	175.0	174.3	173.3	171.6	170.1	168.5	167.0
47.5°	168.1	169.7	171.2	172.1	173.3	172.6	171.5	170.0	168.2	166.6	165.4
48°	166.1	168.0	169.3	170.1	171.2	170.8	169.6	168.1	166.4	164.6	163.4
48.5°	164.1	166.2	167.4	168.2	169.4	168.9	167.6	166.3	164.5	163.0	161.4
49°	162.4	164.1	165.7	166.5	167.7	167.1	165.9	164.2	162.8	161.0	159.5
49.5°	160.8	162.1	163.8	164.7	165.7	165.1	164.1	162.5	160.8	159.0	157.9
50°	158.6	160.6	161.9	162.8	163.9	163.4	162.2	160.7	158.7	157.1	155.8
50.5°	156.6	158.5	159.9	160.8	162.1	161.6	160.3	158.6	156.8	155.4	153.9
51°	154.9	156.5	158.1	159.0	160.1	159.6	158.5	156.7	155.0	153.3	151.9
51.5°	152.9	154.6	156.4	157.1	158.2	157.5	156.5	154.9	153.1	151.4	150.0
52°	150.9	152.9	154.4	155.2	156.4	155.8	154.6	153.1	151.2	149.5	148.0
52.5°	149.0	150.8	152.3	153.2	154.5	153.9	152.7	151.0	149.3	147.4	146.1
53°	147.0	148.9	150.3	151.2	152.5	152.0	150.8	149.1	147.3	145.4	144.1
53.5°	144.9	146.9	148.5	149.4	150.6	149.9	148.9	147.1	145.2	143.7	142.0
54°	143.1	144.8	146.6	147.5	148.7	148.2	146.8	145.2	143.4	141.5	140.0
54.5°	141.2	142.7	144.5	145.4	146.8	146.1	144.8	143.2	141.4	139.5	138.0
55°	139.1	141.1	142.6	143.5	144.7	144.1	142.9	141.3	139.4	137.5	136.0
55.5°	137.0	139.0	140.8	141.5	142.8	142.1	141.0	139.2	137.2	135.6	134.1
56°	135.0	136.9	138.7	139.5	141.0	140.3	138.9	137.2	135.3	133.5	132.0
56.5°	132.9	134.8	136.5	137.4	138.7	138.0	137.0	135.2	133.4	131.4	129.9
57°	130.9	132.8	134.6	135.3	136.7	136.2	135.0	133.0	131.2	129.4	127.8
57.5°	129.0	130.9	132.6	133.5	134.7	134.3	132.9	131.1	129.2	127.3	126.0
58°	127.0	128.8	130.5	131.5	132.8	132.1	130.7	129.2	127.2	125.3	123.8
58.5°	124.7	126.8	128.5	129.5	130.6	130.0	128.9	127.0	125.2	123.3	121.8
59°	122.8	124.7	126.5	127.3	128.6	128.2	127.0	125.1	123.1	121.3	119.6
59.5°	120.7	122.6	124.4	125.2	126.6	126.1	124.7	123.0	121.1	119.1	117.6
60°	118.7	120.5	122.3	123.2	124.8	124.0	122.6	120.8	119.0	117.1	115.4
60.5°	116.5	118.7	120.2	121.2	122.4	121.8	120.6	118.8	116.9	115.0	113.4
61°	114.6	116.5	118.3	119.1	120.4	119.9	118.5	117.0	114.8	112.9	111.2
61.5°	112.4	114.3	116.0	117.0	118.5	117.8	116.6	114.8	112.8	110.8	109.3
62°	110.4	112.3	114.1	115.0	116.4	115.7	114.5	112.6	110.7	108.9	107.2
62.5°	108.2	110.3	112.0	113.0	114.2	113.6	112.4	110.5	108.6	106.6	105.1
63°	106.2	108.1	110.0	110.7	112.2	111.6	110.3	108.5	106.6	104.6	102.9
63.5°	104.0	106.0	107.8	108.6	110.0	109.5	108.1	106.5	104.5	102.6	100.8
64°	102.0	104.1	105.7	106.6	108.0	107.4	106.1	104.3	102.4	100.4	98.7
64.5°	100.0	102.0	103.6	104.5	105.8	105.3	104.1	102.2	100.4	98.2	96.8
65°	97.9	99.8	101.7	102.5	103.8	103.2	102.0	100.1	98.4	96.3	94.6
65.5°	95.7	97.8	99.5	100.3	101.7	101.0	99.9	98.0	96.1	94.3	92.6
66°	93.7	95.7	97.4	98.2	99.6	99.1	97.9	96.0	94.0	92.1	90.5
66.5°	91.6	93.5	95.3	96.2	97.5	97.0	95.7	94.0	92.1	90.1	88.3
67°	89.6	91.4	93.2	94.0	95.5	94.9	93.6	91.9	90.1	88.0	86.3

TEST NUMBER: P855585
 CATALOG NUMBER: HLS4079FS1EWH-3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
67.5°	87.5	89.6	91.0	92.0	93.3	92.8	91.6	89.8	88.0	86.0	84.3
68°	85.5	87.4	89.0	89.9	91.1	90.7	89.6	87.8	85.9	83.9	82.3
68.5°	83.3	85.3	87.1	87.8	89.1	88.7	87.4	85.7	83.9	81.8	80.3
69°	81.3	83.3	85.0	85.8	87.2	86.6	85.4	83.7	82.0	79.9	78.3
69.5°	79.3	81.2	82.9	83.6	85.1	84.7	83.3	81.7	79.9	77.8	76.2
70°	77.4	79.1	80.8	81.5	83.0	82.6	81.2	79.8	77.9	75.8	74.0
70.5°	75.3	77.2	78.8	79.6	81.0	80.6	79.1	77.7	75.9	73.8	72.2
71°	73.3	75.2	76.6	77.5	78.9	78.5	77.4	75.6	73.8	71.8	70.2
71.5°	71.3	73.2	74.7	75.5	76.8	76.4	75.4	73.6	71.8	69.9	68.1
72°	69.2	71.1	72.7	73.4	74.9	74.4	73.2	71.6	69.9	67.9	66.1
72.5°	67.5	69.2	70.7	71.4	73.0	72.4	71.3	69.6	68.0	65.8	64.2
73°	65.5	67.3	68.6	69.4	70.7	70.4	69.3	67.7	65.9	63.9	62.2
73.5°	63.5	65.3	66.6	67.5	68.7	68.4	67.4	65.7	64.0	62.0	60.3
74°	61.5	63.3	64.9	65.5	66.8	66.3	65.3	63.8	62.1	60.1	58.4
74.5°	59.7	61.5	62.9	63.5	64.9	64.3	63.4	61.8	60.3	58.2	56.5
75°	57.9	59.5	60.9	61.5	62.9	62.5	61.5	60.0	58.3	56.3	54.6
75.5°	56.0	57.7	58.9	59.6	61.0	60.6	59.5	58.1	56.5	54.4	52.9
76°	54.1	55.8	57.1	57.7	59.0	58.6	57.7	56.2	54.6	52.7	51.0
76.5°	52.3	54.0	55.3	55.8	57.1	56.7	55.8	54.3	52.8	50.9	49.1
77°	50.6	52.1	53.4	53.9	55.2	54.8	53.9	52.4	51.0	49.0	47.3
77.5°	48.8	50.4	51.6	52.1	53.4	53.0	52.1	50.7	49.3	47.3	45.7
78°	47.1	48.6	49.8	50.4	51.5	51.2	50.3	49.0	47.5	45.6	43.9
78.5°	45.4	46.9	48.0	48.5	49.7	49.3	48.6	47.2	45.8	43.9	42.2
79°	43.7	45.0	46.3	46.7	47.9	47.5	46.8	45.5	44.1	42.2	40.6
79.5°	42.1	43.5	44.5	44.9	46.1	45.9	45.0	43.8	42.5	40.6	38.9
80°	40.5	41.8	42.7	43.3	44.3	44.1	43.4	42.1	40.8	39.0	37.3
80.5°	38.8	40.1	41.1	41.6	42.6	42.3	41.7	40.5	39.3	37.4	35.8
81°	37.3	38.5	39.5	39.9	41.0	40.7	40.0	38.9	37.7	35.9	34.2
81.5°	35.9	37.0	38.0	38.3	39.3	39.1	38.4	37.3	36.2	34.3	32.7
82°	34.5	35.6	36.4	36.8	37.6	37.4	36.8	35.8	34.6	32.8	31.3
82.5°	33.1	34.1	34.9	35.3	36.1	35.9	35.3	34.3	33.2	31.4	29.8
83°	31.6	32.7	33.5	33.9	34.5	34.4	33.7	32.8	31.7	29.9	28.4
83.5°	30.1	31.3	32.0	32.3	33.1	32.8	32.2	31.3	30.3	28.7	27.1
84°	28.9	29.8	30.5	30.9	31.6	31.3	30.9	29.9	29.0	27.2	25.8
84.5°	27.5	28.5	29.1	29.4	30.1	29.9	29.4	28.6	27.6	26.0	24.5
85°	26.2	27.1	27.7	28.0	28.7	28.6	28.0	27.2	26.3	24.6	23.1
85.5°	24.8	25.8	26.4	26.7	27.3	27.1	26.7	25.9	25.0	23.5	22.0
86°	23.7	24.5	25.1	25.3	26.0	25.9	25.3	24.6	23.8	22.2	20.7
86.5°	22.4	23.3	23.8	24.1	24.7	24.5	24.1	23.4	22.5	21.1	19.7
87°	21.2	22.0	22.6	22.8	23.5	23.3	22.8	22.1	21.3	19.9	18.6
87.5°	20.0	20.9	21.4	21.6	22.2	22.1	21.7	21.0	20.1	18.8	17.4
88°	18.9	19.7	20.2	20.4	21.1	20.9	20.5	19.8	19.1	17.6	16.5
88.5°	17.7	18.6	19.1	19.3	19.9	19.7	19.4	18.8	17.9	16.7	15.4
89°	16.7	17.4	18.0	18.2	18.8	18.6	18.2	17.6	16.8	15.6	14.5
89.5°	15.6	16.4	17.0	17.1	17.6	17.5	17.2	16.6	15.8	14.7	13.6

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



TEST NUMBER: P855585
CATALOG NUMBER: HLS4079FS1EWH-3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P855585
 CATALOG NUMBER: HLS4079FS1EWH-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	265.9	265.9	265.9	265.9	265.9	265.9
0.5°	266.2	265.8	265.9	266.0	265.9	265.6
1°	265.9	265.6	265.9	265.9	265.5	265.6
1.5°	265.8	265.4	266.0	265.7	265.4	265.8
2°	265.8	265.7	265.7	265.6	265.8	265.5
2.5°	265.9	265.4	265.4	265.7	265.5	265.4
3°	265.6	264.8	265.5	265.4	265.0	265.4
3.5°	265.1	264.7	265.0	265.1	265.1	265.4
4°	264.9	264.7	264.5	265.0	264.8	264.9
4.5°	264.8	264.2	264.5	264.7	264.5	264.6
5°	264.5	263.9	264.4	264.2	264.2	264.5
5.5°	263.9	263.8	264.1	264.2	264.2	264.3
6°	263.9	263.4	263.6	264.0	263.8	264.1
6.5°	263.8	262.7	263.2	263.5	263.3	263.8
7°	263.3	262.3	263.0	263.0	262.8	263.5
7.5°	262.6	262.2	262.6	262.7	263.0	263.0
8°	262.2	261.7	262.0	262.4	262.4	262.6
8.5°	261.9	261.1	261.5	261.9	261.7	262.4
9°	261.7	260.8	261.2	261.4	261.4	261.9
9.5°	261.0	260.2	260.7	261.0	261.1	261.2
10°	260.2	259.7	259.8	260.2	260.3	260.9
10.5°	259.7	259.3	259.5	259.6	259.9	260.5
11°	259.4	258.7	259.2	259.4	259.3	259.8
11.5°	258.9	257.9	258.5	258.8	259.2	259.4
12°	257.9	257.2	257.6	257.9	258.3	258.9
12.5°	257.4	256.7	257.4	257.4	257.5	258.2
13°	256.8	256.2	256.5	256.8	257.1	257.4
13.5°	256.2	255.4	255.7	256.1	256.6	257.1
14°	255.4	254.5	255.0	255.4	255.7	256.5
14.5°	254.6	253.9	254.6	254.7	255.1	255.7
15°	254.1	253.3	253.5	253.8	254.3	254.8
15.5°	253.5	252.2	252.8	253.2	253.6	254.4
16°	252.3	251.7	252.0	252.5	252.8	253.5
16.5°	251.5	250.8	251.3	251.5	252.0	252.6
17°	250.7	249.7	250.3	250.7	251.3	251.9
17.5°	250.0	248.9	249.6	249.9	250.2	251.2
18°	249.0	248.4	248.8	249.0	249.4	250.1
18.5°	248.0	247.3	247.9	248.1	248.8	249.5
19°	247.3	246.2	246.9	247.3	247.8	248.6
19.5°	246.5	245.2	245.9	246.3	246.9	247.6
20°	245.2	244.6	244.8	245.2	246.2	246.6
20.5°	244.2	243.4	244.1	244.4	245.0	245.9
21°	243.1	242.1	242.9	243.6	243.9	244.9
21.5°	242.3	241.4	241.9	242.2	243.0	243.9
22°	241.4	240.3	240.9	241.2	242.2	242.9

TEST NUMBER: P855585
 CATALOG NUMBER: HLS4079FS1EWH-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
22.5°	240.1	239.0	239.8	240.4	241.0	241.9
23°	239.0	237.8	238.7	239.3	239.9	240.6
23.5°	237.9	236.9	237.4	237.9	238.8	239.6
24°	236.9	235.9	236.3	237.0	237.8	238.9
24.5°	235.7	234.7	235.2	235.8	236.6	237.6
25°	234.5	233.3	234.1	234.5	235.5	236.3
25.5°	233.2	232.3	232.7	233.3	234.4	235.3
26°	232.1	231.0	231.5	232.3	233.0	234.2
26.5°	230.9	229.6	230.5	230.9	231.8	232.9
27°	229.8	228.5	229.4	229.7	230.7	231.9
27.5°	228.3	227.4	227.9	228.5	229.6	230.5
28°	227.1	226.0	226.5	227.3	228.2	229.2
28.5°	225.7	224.4	225.4	225.8	226.9	227.9
29°	224.6	223.2	224.0	224.7	225.5	226.8
29.5°	223.2	222.1	222.5	223.3	224.6	225.5
30°	221.9	220.6	221.2	222.0	223.0	224.0
30.5°	220.3	219.1	220.0	220.5	221.6	222.7
31°	218.9	218.1	218.5	219.2	220.3	221.4
31.5°	217.6	216.5	217.2	217.7	219.0	220.1
32°	216.3	214.9	215.5	216.6	217.3	218.6
32.5°	214.9	213.5	214.3	214.9	216.0	217.4
33°	213.3	212.1	212.6	213.4	214.8	215.7
33.5°	211.9	210.5	211.1	212.1	213.2	214.3
34°	210.4	209.0	209.8	210.6	211.7	212.9
34.5°	208.9	207.6	208.4	208.9	210.3	211.6
35°	207.3	206.0	206.5	207.7	208.8	210.0
35.5°	205.8	204.5	205.0	205.9	207.1	208.5
36°	204.1	202.9	203.5	204.3	205.6	206.9
36.5°	202.8	201.5	202.2	202.9	204.1	205.5
37°	201.1	200.0	200.3	201.4	202.5	203.9
37.5°	199.5	198.2	198.8	199.6	200.9	202.3
38°	197.8	196.4	197.4	198.0	199.2	200.8
38.5°	196.4	194.9	195.6	196.5	197.7	199.1
39°	194.6	193.4	193.7	194.7	196.2	197.5
39.5°	193.0	191.6	192.3	193.1	194.5	196.0
40°	191.1	189.9	190.6	191.5	192.8	194.2
40.5°	189.6	188.4	189.0	189.9	191.2	192.5
41°	188.0	186.5	187.3	188.0	189.4	191.0
41.5°	186.2	184.9	185.4	186.3	187.6	189.3
42°	184.4	182.9	183.7	184.8	186.1	187.6
42.5°	182.7	181.3	182.0	182.8	184.4	185.9
43°	180.9	179.5	180.1	181.1	182.5	184.0
43.5°	179.2	177.8	178.3	179.4	180.8	182.3
44°	177.2	175.8	176.6	177.6	179.1	180.7
44.5°	175.6	174.1	175.1	175.7	177.2	179.0

TEST NUMBER: P855585
 CATALOG NUMBER: HLS4079FS1EWH-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
45°	173.9	172.5	172.9	173.9	175.4	177.0
45.5°	172.1	170.6	171.1	172.1	173.7	175.2
46°	170.3	168.7	169.4	170.5	171.9	173.6
46.5°	168.3	166.9	167.7	168.5	170.0	171.6
47°	166.4	165.1	165.6	166.6	168.1	169.7
47.5°	164.5	163.0	163.8	164.7	166.4	168.1
48°	162.9	161.2	161.9	163.0	164.5	166.1
48.5°	160.9	159.4	160.0	160.9	162.7	164.1
49°	158.8	157.4	158.0	159.1	160.7	162.4
49.5°	157.0	155.5	156.0	157.2	158.8	160.8
50°	155.0	153.6	154.3	155.1	156.9	158.6
50.5°	153.2	151.6	152.4	153.2	154.9	156.6
51°	151.2	149.6	150.1	151.5	152.9	154.9
51.5°	149.2	147.7	148.3	149.5	151.2	152.9
52°	147.1	145.8	146.4	147.4	149.2	150.9
52.5°	145.3	143.6	144.4	145.3	147.1	149.0
53°	143.3	141.8	142.3	143.7	145.0	147.0
53.5°	141.2	139.8	140.4	141.5	143.2	144.9
54°	139.2	137.8	138.4	139.4	141.3	143.1
54.5°	137.4	135.6	136.2	137.5	139.2	141.2
55°	135.3	133.8	134.2	135.4	137.2	139.1
55.5°	133.2	131.7	132.4	133.2	135.1	137.0
56°	131.1	129.6	130.2	131.4	133.0	135.0
56.5°	129.1	127.6	128.1	129.3	131.1	132.9
57°	127.0	125.6	126.2	127.2	129.2	130.9
57.5°	125.1	123.4	124.1	125.2	127.0	129.0
58°	122.8	121.4	122.0	123.1	124.9	127.0
58.5°	120.8	119.3	119.8	120.9	122.8	124.7
59°	118.9	117.3	117.8	119.0	120.8	122.8
59.5°	116.7	115.1	115.8	116.9	118.8	120.7
60°	114.5	113.1	113.6	114.9	116.7	118.7
60.5°	112.4	110.9	111.5	112.7	114.6	116.5
61°	110.5	108.9	109.5	110.5	112.6	114.6
61.5°	108.3	106.8	107.4	108.4	110.3	112.4
62°	106.1	104.7	105.2	106.5	108.2	110.4
62.5°	104.1	102.6	103.1	104.4	106.1	108.2
63°	102.0	100.4	101.0	102.3	104.3	106.2
63.5°	99.9	98.3	98.9	100.1	102.0	104.0
64°	97.8	96.3	96.8	98.1	100.0	102.0
64.5°	95.6	94.3	94.7	95.9	97.9	100.0
65°	93.6	92.1	92.7	93.8	95.8	97.9
65.5°	91.6	90.0	90.5	91.9	93.6	95.7
66°	89.5	87.9	88.3	89.8	91.6	93.7
66.5°	87.3	85.8	86.3	87.6	89.7	91.6
67°	85.3	83.8	84.2	85.5	87.5	89.6

TEST NUMBER: P855585
 CATALOG NUMBER: HLS4079FS1EWH-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
67.5°	83.2	81.7	82.3	83.5	85.4	87.5
68°	81.2	79.6	80.1	81.4	83.4	85.5
68.5°	79.1	77.5	78.1	79.3	81.3	83.3
69°	77.3	75.5	76.1	77.4	79.2	81.3
69.5°	75.2	73.4	74.0	75.3	77.3	79.3
70°	73.2	71.4	71.8	73.2	75.3	77.4
70.5°	71.1	69.4	70.0	71.2	73.3	75.3
71°	69.1	67.5	68.0	69.3	71.2	73.3
71.5°	67.0	65.4	65.9	67.4	69.2	71.3
72°	65.2	63.4	64.0	65.3	67.4	69.2
72.5°	63.2	61.5	62.0	63.3	65.4	67.5
73°	61.2	59.5	60.1	61.4	63.4	65.5
73.5°	59.3	57.6	58.2	59.5	61.4	63.5
74°	57.3	55.8	56.2	57.6	59.6	61.5
74.5°	55.5	53.9	54.4	55.7	57.7	59.7
75°	53.6	52.0	52.5	53.9	55.8	57.9
75.5°	51.7	50.3	50.8	52.0	54.0	56.0
76°	49.9	48.5	48.9	50.3	52.2	54.1
76.5°	48.1	46.6	47.1	48.5	50.4	52.3
77°	46.3	44.8	45.4	46.7	48.6	50.6
77.5°	44.5	43.2	43.7	44.9	46.9	48.8
78°	43.0	41.5	42.0	43.3	45.1	47.1
78.5°	41.2	39.8	40.4	41.6	43.5	45.4
79°	39.5	38.2	38.6	39.9	41.8	43.7
79.5°	37.8	36.5	37.0	38.4	40.1	42.1
80°	36.3	35.0	35.6	36.8	38.5	40.5
80.5°	34.7	33.6	34.1	35.3	37.0	38.8
81°	33.3	32.1	32.6	33.9	35.6	37.3
81.5°	31.7	30.7	31.2	32.4	34.1	35.9
82°	30.2	29.2	29.7	31.0	32.6	34.5
82.5°	28.9	27.8	28.4	29.5	31.3	33.1
83°	27.4	26.4	26.9	28.0	29.8	31.6
83.5°	26.1	25.1	25.5	26.7	28.4	30.1
84°	24.8	23.8	24.3	25.4	27.0	28.9
84.5°	23.6	22.5	23.0	24.2	25.8	27.5
85°	22.3	21.4	21.8	22.9	24.5	26.2
85.5°	21.1	20.2	20.6	21.7	23.3	24.8
86°	19.9	19.0	19.5	20.5	22.1	23.7
86.5°	18.8	17.9	18.4	19.4	21.0	22.4
87°	17.6	16.8	17.3	18.4	19.7	21.2
87.5°	16.6	15.8	16.3	17.3	18.7	20.0
88°	15.6	14.8	15.2	16.3	17.6	18.9
88.5°	14.6	13.9	14.3	15.2	16.6	17.7
89°	13.7	12.9	13.3	14.3	15.5	16.7
89.5°	12.7	12.0	12.4	13.3	14.6	15.6

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



TEST NUMBER: P855585
CATALOG NUMBER: HLS4079FS1EWH-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
90°	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)