

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642177

Luminaire Tested: ML5612LSWFL5597FS1E - 693SNB - 1200LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642177
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-65)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSWFL5597FS1E - 693SNB - 1200LM - 3000K
Description: ML56 RR, 55D TIR OPTIC, 6" SATIN NICKLE BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1521.5 lumens
Efficiency: N/A
Efficacy: 92.2 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 16.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642177

CATALOG NUMBER: ML5612LSWFL5597FS1E - 693SNB - 1200LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P642177

CATALOG NUMBER: ML5612LSWFL5597FS1E - 693SNB - 1200LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93			93
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86			86
3	101	95	89	85	99	93	88	85	91	87	83	88	85	82	86	83	81	79			79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73			73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	69	76	72	69	67			67
6	86	76	70	65	84	75	70	65	74	69	65	72	68	64	71	67	64	62			62
7	81	71	65	60	80	71	65	60	69	64	60	68	63	60	67	63	59	58			58
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	55	54			54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	49	56	52	48	47			47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	88529
5°	84828
10°	80437
15°	75840
20°	68600
25°	58461
30°	47761
35°	37390
40°	27723
45°	18025
50°	7769
55°	2858
60°	1338
65°	350
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18025 cd/sqm



TEST NUMBER: P642177

CATALOG NUMBER: ML5612LSWFL5597FS1E - 693SNB - 1200LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.2	9.5
10°-20°	371.9	24.4
20°-30°	441.6	29.0
30°-40°	349.4	23.0
40°-50°	177.4	11.7
50°-60°	33.2	2.2
60°-70°	3.8	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	957.7	62.9
0°-40°	1307.1	85.9
0°-60°	1517.7	99.7
0°-90°	1521.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1521.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1615	
5°	1542	144
15°	1336	372
25°	966	442
35°	559	349
45°	232	177
55°	30	33
65°	3	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P642177

CATALOG NUMBER: ML5612LSWFL5597FS1E - 693SNB - 1200LM - 3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1614.9
2.5°	1595.9
5°	1541.5
7.5°	1491.2
10°	1445.0
12.5°	1393.4
15°	1336.3
17.5°	1261.5
20°	1175.9
22.5°	1075.3
25°	966.5
27.5°	859.1
30°	754.5
32.5°	655.2
35°	558.7
37.5°	469.0
40°	387.4
42.5°	308.6
45°	232.5
47.5°	152.2
50°	91.1
52.5°	48.9
55°	29.9
57.5°	20.4
60°	12.2
62.5°	5.4
65°	2.7
67.5°	1.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)