

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642489

Luminaire Tested: ML5615LSFL409FS1E - 594SNB - 900LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642489
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-33)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSFL409FS1E - 594SNB - 900LM - 4000K
Description: ML56 RR, 40D TIR OPTIC, 5" SATIN NICKLE GIMBAL TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1305.1 lumens
Efficiency: N/A
Efficacy: 124.3 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642489
CATALOG NUMBER: ML5615LSFL409FS1E - 594SNB - 900LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P642489

CATALOG NUMBER: ML5615LSFL409FS1E - 594SNB - 900LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	87	85	83	81			
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	79	75	72	71			
6	88	79	74	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66			
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59			
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56			
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	167007
5°	161797
10°	140807
15°	115609
20°	90484
25°	68488
30°	49195
35°	33392
40°	21548
45°	13955
50°	8093
55°	4542
60°	3047
65°	2129
70°	1569
75°	1373
80°	1046
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13955 cd/sqm



TEST NUMBER: P642489

CATALOG NUMBER: ML5615LSFL409FS1E - 594SNB - 900LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.4	14.2
10°-20°	391.1	30.0
20°-30°	360.0	27.6
30°-40°	220.2	16.9
40°-50°	98.4	7.5
50°-60°	32.6	2.5
60°-70°	12.2	0.9
70°-80°	4.5	0.3
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	936.6	71.8
0°-40°	1156.8	88.6
0°-60°	1287.8	98.7
0°-90°	1305.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1305.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2116	
5°	2042	185
15°	1415	391
25°	786	360
35°	346	220
45°	125	98
55°	33	33
65°	11	12
75°	4	4
85°	0	1
90°	0	



TEST NUMBER: P642489

CATALOG NUMBER: ML5615LSFL409FS1E - 594SNB - 900LM - 4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2115.6
2.5°	2103.1
5°	2041.8
7.5°	1916.8
10°	1756.6
12.5°	1585.0
15°	1414.6
17.5°	1241.9
20°	1077.1
22.5°	922.6
25°	786.3
27.5°	656.7
30°	539.7
32.5°	435.2
35°	346.5
37.5°	271.6
40°	209.1
42.5°	161.3
45°	125.0
47.5°	92.0
50°	65.9
52.5°	46.6
55°	33.0
57.5°	25.0
60°	19.3
62.5°	15.9
65°	11.4
67.5°	9.1
70°	6.8
72.5°	5.7
75°	4.5
77.5°	2.3
80°	2.3
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)