

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P272215

Luminaire Tested: **LA56069271EWH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P272215
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (A1805269A001)
Test Lab:
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: LA56069271EWH
Description: HALO LA 5/6 INCH LED LUMINAIRE
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 614.0 lumens
Efficiency: N/A
Efficacy: 71.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.27
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 8.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P272215
CATALOG NUMBER: LA56069271EWH

Luminous Intensity Polar Plot





TEST NUMBER: P272215
 CATALOG NUMBER: LA56069271EWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	103	99	108	104	101	98	100	97	94	96	94	92	92	91	89	87
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75
3	93	84	76	71	91	82	75	70	79	73	69	77	72	68	74	70	66	64
4	86	75	67	61	84	74	66	60	71	65	60	69	63	59	67	62	58	56
5	79	68	59	53	77	66	59	53	64	58	52	62	56	52	61	55	51	49
6	74	61	53	47	72	60	52	47	59	52	46	57	51	46	55	50	46	44
7	69	56	48	42	67	55	47	42	54	46	41	52	46	41	51	45	41	39
8	64	51	43	38	62	50	43	37	49	42	37	48	42	37	47	41	37	35
9	60	47	39	34	59	47	39	34	45	39	34	44	38	34	43	38	33	32
10	56	44	36	31	55	43	36	31	42	35	31	41	35	31	40	35	31	29

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14917	14917	14917	14917
5°	14924	14963	14874	14836
10°	14885	14963	14785	14712
15°	14796	14926	14654	14529
20°	14655	14841	14450	14264
25°	14420	14680	14142	13876
30°	14059	14407	13711	13350
35°	13559	13987	13117	12669
40°	12874	13404	12337	11801
45°	12001	12637	11358	10730
50°	10908	11650	10149	9467
55°	9663	10446	8850	8153
60°	8398	9188	7598	6896
65°	7225	8003	6421	5733
70°	6155	6940	5001	4600
75°	4469	5931	3050	3410
80°	2241	4925	1294	1989
85°	440	3774	252	440



TEST NUMBER: P272215
 CATALOG NUMBER: LA56069271EWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.7	4.2
10°-20°	73.1	11.9
20°-30°	108.6	17.7
30°-40°	124.2	20.2
40°-50°	115.9	18.9
50°-60°	87.0	14.2
60°-70°	52.7	8.6
70°-80°	22.5	3.7
80°-90°	3.5	0.6
90°-100°	0.1	0.0
100°-110°	0.1	0.0
110°-120°	0.1	0.0
120°-130°	0.1	0.0
130°-140°	0.1	0.0
140°-150°	0.1	0.0
150°-160°	0.1	0.0
160°-170°	0.1	0.0
170°-180°	0.0	0.0
0°-30°	207.4	33.8
0°-40°	331.7	54.0
0°-60°	534.6	87.1
0°-90°	613.2	99.9
90°-120°	0.3	0.0
90°-150°	0.6	0.1
90°-180°	1.0	0.2
0°-180°	614.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	272	272	272	272	272	
5°	271	272	270	270	271	26
15°	261	263	258	256	261	74
25°	238	243	234	229	238	110
35°	203	209	196	189	203	126
45°	155	163	146	138	155	119
55°	101	109	93	85	101	91
65°	56	62	50	44	56	56
75°	21	28	14	16	21	23
85°	1	6	0	1	1	2
90°	0	1	0	0	0	0
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: P272215
 CATALOG NUMBER: LA56069271EWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	272.1	272.1	272.1	272.1	272.1	272.1	272.1	272.1	272.1	272.1	272.1
0.5°	272.1	272.3	272.2	272.3	272.3	272.2	272.2	272.1	272.0	272.1	272.0
1°	272.2	272.3	272.3	272.3	272.4	272.3	272.2	272.1	271.9	272.0	271.9
1.5°	272.1	272.3	272.3	272.4	272.3	272.2	272.2	272.0	271.8	271.8	271.7
2°	272.1	272.3	272.4	272.4	272.4	272.2	272.1	271.9	271.7	271.6	271.5
2.5°	272.0	272.3	272.3	272.4	272.3	272.1	272.1	271.8	271.5	271.4	271.2
3°	271.9	272.2	272.3	272.3	272.3	272.1	271.9	271.6	271.4	271.1	271.0
3.5°	271.7	272.1	272.2	272.3	272.2	272.0	271.9	271.4	271.1	270.9	270.7
4°	271.6	271.9	272.1	272.2	272.2	271.9	271.6	271.2	270.9	270.6	270.4
4.5°	271.4	271.8	272.0	272.0	272.0	271.7	271.4	271.0	270.6	270.3	270.0
5°	271.2	271.6	271.8	271.9	271.9	271.5	271.2	270.7	270.3	269.9	269.7
5.5°	270.9	271.4	271.5	271.7	271.7	271.3	270.9	270.4	269.9	269.6	269.3
6°	270.7	271.2	271.4	271.4	271.5	271.1	270.6	270.0	269.5	269.2	268.8
6.5°	270.3	270.8	271.1	271.2	271.2	270.8	270.3	269.8	269.1	268.7	268.4
7°	270.0	270.5	270.9	270.9	270.9	270.5	269.9	269.3	268.7	268.2	267.9
7.5°	269.6	270.2	270.5	270.6	270.6	270.2	269.6	268.9	268.3	267.8	267.4
8°	269.2	269.9	270.2	270.3	270.3	269.8	269.2	268.4	267.8	267.2	266.9
8.5°	268.8	269.5	269.8	269.9	270.0	269.4	268.8	268.0	267.3	266.7	266.3
9°	268.4	269.1	269.5	269.6	269.6	269.0	268.4	267.4	266.8	266.1	265.7
9.5°	267.9	268.6	269.0	269.2	269.2	268.6	267.9	267.0	266.3	265.6	265.1
10°	267.4	268.2	268.7	268.7	268.8	268.1	267.3	266.4	265.6	264.9	264.4
10.5°	266.8	267.7	268.1	268.3	268.3	267.6	266.8	265.9	265.0	264.3	263.7
11°	266.3	267.2	267.7	267.8	267.8	267.1	266.3	265.2	264.3	263.5	263.1
11.5°	265.7	266.6	267.0	267.3	267.3	266.6	265.7	264.6	263.7	262.9	262.3
12°	265.1	266.1	266.6	266.8	266.8	266.0	265.1	263.9	263.0	262.1	261.5
12.5°	264.4	265.4	266.0	266.1	266.2	265.4	264.5	263.3	262.3	261.4	260.7
13°	263.8	264.8	265.4	265.6	265.6	264.8	263.8	262.5	261.5	260.5	259.8
13.5°	263.0	264.1	264.7	264.9	265.0	264.1	263.1	261.8	260.7	259.7	259.0
14°	262.3	263.5	264.2	264.3	264.4	263.4	262.4	261.1	259.9	258.8	258.1
14.5°	261.5	262.7	263.4	263.6	263.6	262.7	261.6	260.3	259.1	258.0	257.2
15°	260.7	262.0	262.7	262.9	263.0	262.0	260.8	259.4	258.2	257.0	256.2
15.5°	259.9	261.2	261.9	262.2	262.3	261.2	260.0	258.6	257.2	256.2	255.2
16°	259.1	260.4	261.2	261.4	261.5	260.4	259.2	257.6	256.3	255.1	254.3
16.5°	258.2	259.5	260.4	260.6	260.7	259.6	258.3	256.8	255.3	254.1	253.2
17°	257.4	258.7	259.6	259.8	259.9	258.7	257.4	255.8	254.3	253.1	252.1
17.5°	256.4	257.8	258.7	259.0	259.1	257.9	256.4	254.9	253.3	251.9	251.0
18°	255.4	256.9	257.8	258.2	258.2	256.9	255.5	253.8	252.3	250.8	249.9
18.5°	254.4	256.0	256.9	257.2	257.3	256.0	254.5	252.8	251.2	249.7	248.7
19°	253.4	255.0	256.0	256.3	256.4	255.0	253.5	251.7	250.0	248.5	247.5
19.5°	252.3	253.9	255.0	255.3	255.4	254.0	252.5	250.7	248.9	247.3	246.2
20°	251.2	252.9	254.0	254.4	254.4	253.0	251.4	249.4	247.7	246.1	244.9
20.5°	250.1	251.8	252.9	253.3	253.3	251.9	250.3	248.3	246.5	244.8	243.6
21°	249.0	250.7	251.9	252.3	252.3	250.8	249.2	247.1	245.2	243.5	242.3
21.5°	247.7	249.6	250.7	251.2	251.3	249.7	247.9	245.9	243.9	242.0	240.8
22°	246.6	248.4	249.6	250.1	250.1	248.5	246.8	244.6	242.5	240.7	239.5



TEST NUMBER: P272215
 CATALOG NUMBER: LA56069271EWH

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
22.5°	245.2	247.2	248.4	248.9	248.9	247.4	245.5	243.3	241.2	239.3	237.9
23°	243.9	245.9	247.2	247.8	247.8	246.1	244.2	241.9	239.8	237.8	236.5
23.5°	242.6	244.7	245.9	246.5	246.5	244.9	242.9	240.6	238.4	236.3	234.9
24°	241.3	243.3	244.7	245.3	245.3	243.6	241.6	239.1	236.9	234.8	233.4
24.5°	239.8	242.0	243.3	243.9	244.0	242.3	240.2	237.7	235.3	233.2	231.7
25°	238.4	240.6	242.0	242.7	242.7	240.9	238.9	236.2	233.8	231.7	230.1
25.5°	236.9	239.1	240.6	241.3	241.3	239.6	237.4	234.7	232.3	230.0	228.4
26°	235.5	237.6	239.2	239.9	239.9	238.1	235.9	233.1	230.6	228.4	226.8
26.5°	233.8	236.2	237.7	238.4	238.5	236.6	234.4	231.6	229.0	226.7	224.9
27°	232.3	234.7	236.3	237.0	237.1	235.1	232.8	229.9	227.3	224.9	223.3
27.5°	230.7	233.1	234.7	235.5	235.6	233.6	231.2	228.3	225.6	223.1	221.3
28°	229.0	231.5	233.2	234.0	234.0	232.0	229.6	226.6	223.9	221.3	219.6
28.5°	227.4	229.9	231.6	232.4	232.5	230.4	227.9	224.9	222.1	219.5	217.6
29°	225.7	228.3	230.0	230.8	230.9	228.8	226.3	223.1	220.2	217.6	215.8
29.5°	223.9	226.6	228.3	229.1	229.2	227.1	224.5	221.3	218.4	215.7	213.7
30°	222.1	224.8	226.6	227.4	227.6	225.4	222.8	219.5	216.6	213.8	211.8
30.5°	220.3	223.1	224.9	225.7	225.8	223.7	220.9	217.7	214.7	211.8	209.8
31°	218.5	221.2	223.2	224.0	224.1	221.9	219.1	215.8	212.7	209.8	207.8
31.5°	216.6	219.5	221.4	222.1	222.4	220.1	217.3	213.9	210.7	207.7	205.7
32°	214.7	217.6	219.6	220.4	220.5	218.2	215.4	212.0	208.7	205.6	203.6
32.5°	212.7	215.7	217.7	218.6	218.7	216.3	213.5	209.9	206.6	203.6	201.4
33°	210.8	213.8	215.9	216.7	216.8	214.4	211.5	208.0	204.6	201.5	199.3
33.5°	208.7	211.8	213.9	214.7	215.0	212.5	209.5	205.9	202.5	199.3	197.0
34°	206.7	209.8	212.0	212.9	212.9	210.5	207.6	203.8	200.3	197.2	194.9
34.5°	204.6	207.8	210.0	210.9	211.0	208.5	205.5	201.7	198.1	194.9	192.5
35°	202.6	205.7	208.0	208.9	209.0	206.5	203.5	199.6	196.0	192.7	190.3
35.5°	200.4	203.7	206.0	206.7	207.0	204.5	201.3	197.4	193.7	190.4	187.9
36°	198.3	201.5	203.9	204.8	204.9	202.4	199.2	195.2	191.5	188.1	185.7
36.5°	196.0	199.4	201.8	202.7	202.8	200.2	197.0	193.0	189.1	185.8	183.2
37°	193.8	197.2	199.7	200.5	200.7	198.1	194.8	190.8	186.8	183.3	180.9
37.5°	191.6	195.1	197.5	198.4	198.6	195.9	192.6	188.5	184.5	181.0	178.4
38°	189.3	192.8	195.3	196.2	196.4	193.7	190.3	186.1	182.1	178.6	176.0
38.5°	187.0	190.6	193.1	194.0	194.1	191.5	188.0	183.8	179.7	176.1	173.5
39°	184.7	188.2	190.9	191.8	192.0	189.2	185.7	181.5	177.3	173.6	171.1
39.5°	182.3	186.0	188.6	189.5	189.7	186.9	183.4	179.1	174.9	171.2	168.5
40°	179.9	183.6	186.3	187.3	187.3	184.6	181.0	176.7	172.4	168.6	166.0
40.5°	177.5	181.3	183.9	184.9	185.0	182.2	178.6	174.2	169.9	166.1	163.4
41°	175.0	178.9	181.6	182.5	182.6	179.8	176.2	171.7	167.4	163.5	160.9
41.5°	172.6	176.5	179.2	180.2	180.3	177.4	173.8	169.2	164.9	161.0	158.3
42°	170.1	174.1	176.8	177.8	178.0	175.0	171.3	166.7	162.3	158.4	155.7
42.5°	167.7	171.6	174.4	175.3	175.5	172.6	168.8	164.2	159.7	155.8	153.0
43°	165.0	169.1	171.9	172.9	173.0	170.1	166.3	161.6	157.1	153.2	150.4
43.5°	162.5	166.6	169.4	170.4	170.5	167.6	163.8	159.0	154.5	150.5	147.7
44°	160.0	164.1	166.9	167.9	168.1	165.1	161.2	156.5	151.9	147.9	145.0
44.5°	157.4	161.6	164.4	165.4	165.5	162.5	158.6	153.8	149.2	145.2	142.3



TEST NUMBER: P272215
 CATALOG NUMBER: LA56069271EWH

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
45°	154.8	159.0	161.9	162.9	163.0	160.0	155.9	151.2	146.5	142.5	139.6
45.5°	152.2	156.4	159.3	160.3	160.4	157.4	153.4	148.5	143.8	139.8	136.9
46°	149.5	153.8	156.7	157.7	157.9	154.8	150.7	145.8	141.2	137.1	134.2
46.5°	146.9	151.2	154.1	155.1	155.3	152.2	148.1	143.2	138.5	134.4	131.5
47°	144.2	148.6	151.4	152.5	152.6	149.5	145.4	140.5	135.7	131.7	128.7
47.5°	141.6	145.9	148.8	149.8	150.0	146.9	142.7	137.7	133.0	129.0	125.9
48°	138.8	143.2	146.2	147.2	147.4	144.2	140.0	135.0	130.3	126.2	123.2
48.5°	136.1	140.5	143.5	144.5	144.6	141.5	137.3	132.3	127.5	123.4	120.4
49°	133.3	137.9	140.8	141.8	142.0	138.8	134.6	129.6	124.7	120.6	117.6
49.5°	130.7	135.1	138.1	139.1	139.3	136.1	131.9	126.9	121.9	117.8	114.8
50°	127.9	132.5	135.4	136.4	136.6	133.3	129.1	124.1	119.0	115.0	112.1
50.5°	125.3	129.7	132.6	133.7	133.8	130.6	126.3	121.4	116.2	112.3	109.4
51°	122.5	127.0	129.9	130.9	131.2	127.9	123.6	118.6	113.7	109.6	106.7
51.5°	119.8	124.2	127.2	128.2	128.4	125.1	120.8	115.8	111.0	106.9	104.1
52°	117.0	121.6	124.4	125.5	125.7	122.4	118.0	113.0	108.3	104.3	101.4
52.5°	114.4	118.8	121.7	122.7	122.9	119.6	115.3	110.3	105.6	101.6	98.9
53°	111.7	116.1	119.0	120.0	120.2	116.9	112.5	107.6	103.0	99.0	96.3
53.5°	109.0	113.4	116.3	117.2	117.4	114.1	109.8	105.0	100.3	96.4	93.7
54°	106.4	110.7	113.6	114.6	114.7	111.4	107.2	102.3	97.7	93.9	91.2
54.5°	103.7	108.0	110.9	111.9	112.0	108.7	104.5	99.7	95.2	91.4	88.7
55°	101.1	105.4	108.2	109.2	109.3	106.1	101.8	97.1	92.6	88.9	86.2
55.5°	98.5	102.8	105.6	106.5	106.6	103.4	99.2	94.6	90.2	86.4	83.8
56°	95.9	100.2	103.0	103.8	104.0	100.8	96.7	92.1	87.7	84.0	81.5
56.5°	93.4	97.5	100.3	101.2	101.4	98.2	94.2	89.6	85.3	81.6	79.1
57°	90.9	95.1	97.8	98.6	98.8	95.6	91.6	87.1	82.8	79.3	76.7
57.5°	88.5	92.6	95.2	96.0	96.1	93.1	89.1	84.7	80.5	77.0	74.6
58°	85.9	90.0	92.6	93.5	93.6	90.7	86.7	82.3	78.2	74.7	72.3
58.5°	83.6	87.5	90.2	91.0	91.1	88.1	84.3	80.0	75.8	72.5	70.1
59°	81.2	85.2	87.8	88.5	88.6	85.7	81.9	77.7	73.6	70.3	68.0
59.5°	78.9	82.8	85.3	86.0	86.2	83.3	79.5	75.4	71.4	68.1	65.8
60°	76.6	80.4	82.9	83.7	83.8	81.0	77.2	73.1	69.3	66.0	63.7
60.5°	74.3	78.1	80.6	81.3	81.4	78.6	75.0	70.9	67.1	63.9	61.7
61°	72.1	75.8	78.3	79.0	79.1	76.4	72.8	68.7	65.0	61.9	59.7
61.5°	70.0	73.6	76.0	76.6	76.8	74.1	70.6	66.6	63.0	59.9	57.7
62°	67.8	71.4	73.7	74.4	74.6	71.9	68.4	64.5	61.0	57.9	55.8
62.5°	65.7	69.2	71.5	72.2	72.3	69.7	66.3	62.4	59.0	56.0	53.9
63°	63.6	67.0	69.3	70.0	70.1	67.6	64.2	60.3	57.0	54.1	52.0
63.5°	61.7	65.0	67.2	67.9	68.0	65.4	62.2	58.3	55.1	52.2	50.2
64°	59.7	63.0	65.2	65.8	65.9	63.4	60.2	56.3	53.2	50.4	48.4
64.5°	57.7	61.0	63.1	63.7	63.8	61.4	58.2	54.3	51.3	48.6	46.6
65°	55.7	58.9	61.0	61.7	61.7	59.4	56.3	52.4	49.5	46.8	44.9
65.5°	53.7	57.0	59.0	59.6	59.7	57.4	54.4	50.5	47.7	45.1	43.2
66°	51.9	55.1	57.1	57.7	57.8	55.5	52.5	48.7	46.0	43.4	41.6
66.5°	50.2	53.3	55.2	55.7	55.8	53.6	50.7	46.8	44.2	41.7	39.9
67°	48.4	51.5	53.9	53.6	54.0	51.8	48.8	45.0	42.5	40.1	38.3



TEST NUMBER: P272215
 CATALOG NUMBER: LA56069271EWH

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
67.5°	46.7	49.7	52.0	51.9	52.1	50.0	47.1	43.2	40.7	38.5	36.8
68°	44.9	47.8	50.1	50.1	50.2	48.2	45.3	41.4	38.7	37.0	35.2
68.5°	43.3	46.0	48.1	48.4	48.5	46.4	43.6	39.5	36.8	35.4	33.7
69°	41.6	44.3	46.1	46.7	46.7	44.7	42.0	37.8	34.9	33.9	32.2
69.5°	39.9	42.7	44.4	44.9	45.0	43.0	40.3	36.0	33.0	32.2	30.8
70°	38.4	41.0	42.7	43.2	43.3	41.4	38.7	34.2	31.2	30.5	29.4
70.5°	36.8	39.4	41.0	41.6	41.6	39.8	37.1	32.5	29.3	28.8	28.0
71°	35.2	37.8	39.5	40.0	40.0	38.2	35.6	30.7	27.5	27.1	26.6
71.5°	33.5	36.2	37.9	38.3	38.5	36.6	34.1	29.0	25.7	25.5	25.3
72°	31.7	34.7	36.3	36.8	36.8	35.1	32.6	27.4	23.9	23.9	24.0
72.5°	30.0	33.2	34.7	35.2	35.3	33.6	31.1	25.8	22.1	22.3	22.6
73°	28.1	31.7	33.3	33.7	33.8	32.1	29.7	24.2	20.4	20.8	21.4
73.5°	26.3	30.3	31.8	32.3	32.4	30.7	28.2	22.7	18.8	19.3	20.1
74°	24.6	28.7	30.3	30.8	30.9	29.3	26.8	21.2	17.3	17.8	18.9
74.5°	22.8	27.2	28.9	29.4	29.4	27.9	25.4	19.8	15.7	16.5	17.6
75°	21.1	25.6	27.3	28.0	28.0	26.5	24.1	18.4	14.4	15.1	16.5
75.5°	19.4	24.0	25.8	26.6	26.7	25.2	22.8	17.0	13.1	14.0	15.3
76°	17.7	22.4	24.3	25.2	25.3	23.9	21.5	15.7	11.9	12.8	14.2
76.5°	16.1	20.9	22.7	23.9	24.1	22.6	20.2	14.5	10.7	11.6	13.1
77°	14.6	19.4	21.3	22.7	22.7	21.3	19.0	13.4	9.5	10.5	12.1
77.5°	13.1	18.0	19.9	21.4	21.5	20.1	17.8	12.3	8.3	9.3	11.0
78°	11.7	16.5	18.6	20.2	20.3	18.9	16.6	11.2	7.3	8.4	10.0
78.5°	10.4	15.2	17.3	18.9	19.1	17.7	15.4	10.1	6.5	7.5	8.9
79°	9.2	13.9	16.1	17.8	17.9	16.6	14.3	9.1	5.6	6.7	8.0
79.5°	8.1	12.6	14.9	16.6	16.7	15.5	13.3	8.2	4.9	5.9	7.1
80°	7.1	11.4	13.7	15.5	15.6	14.4	12.2	7.3	4.1	5.1	6.3
80.5°	6.2	10.3	12.7	14.4	14.5	13.4	11.1	6.5	3.5	4.3	5.5
81°	5.4	9.3	11.6	13.3	13.5	12.4	10.1	5.7	2.8	3.6	4.8
81.5°	4.7	8.3	10.6	12.3	12.5	11.4	9.0	5.0	2.2	3.1	4.1
82°	4.0	7.3	9.7	11.3	11.5	10.4	8.1	4.2	1.7	2.6	3.4
82.5°	3.2	6.4	8.8	10.3	10.5	9.4	7.3	3.5	1.3	2.1	2.8
83°	2.5	5.6	8.0	9.4	9.5	8.5	6.4	3.0	1.0	1.7	2.3
83.5°	1.8	4.9	7.2	8.5	8.6	7.6	5.7	2.5	0.8	1.4	1.8
84°	1.3	4.2	6.4	7.6	7.7	6.8	4.9	2.1	0.6	1.1	1.3
84.5°	1.0	3.4	5.7	6.7	6.8	6.0	4.2	1.7	0.5	0.8	1.0
85°	0.7	2.7	5.0	5.9	6.0	5.2	3.6	1.4	0.4	0.7	0.7
85.5°	0.5	2.2	4.4	5.2	5.2	4.5	3.0	1.1	0.4	0.5	0.6
86°	0.4	1.8	3.7	4.5	4.5	3.8	2.4	0.9	0.3	0.4	0.4
86.5°	0.3	1.4	3.1	3.8	3.8	3.1	1.9	0.7	0.3	0.3	0.3
87°	0.3	1.1	2.5	3.0	3.1	2.5	1.5	0.6	0.2	0.3	0.1
87.5°	0.3	0.8	1.9	2.4	2.5	1.9	1.1	0.5	0.2	0.2	0.1
88°	0.2	0.6	1.5	1.9	1.9	1.5	0.8	0.4	0.1	0.1	0.1
88.5°	0.2	0.5	1.1	1.4	1.5	1.1	0.7	0.3	0.1	0.1	0.1
89°	0.1	0.4	0.8	1.0	1.1	0.8	0.5	0.2	0.1	0.1	0.1
89.5°	0.1	0.3	0.6	0.8	0.8	0.6	0.4	0.2	0.1	0.1	0.1



TEST NUMBER: P272215
 CATALOG NUMBER: LA56069271EWH

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
90°	0.1	0.2	0.5	0.6	0.6	0.5	0.2	0.2	0.1	0.1	0.1
90.5°	0.1	0.1	0.3	0.4	0.4	0.3	0.1	0.2	0.1	0.1	0.1
91°	0.1	0.1	0.2	0.2	0.3	0.1	0.1	0.1	0.1	0.1	0.1
91.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
92°	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.1	0.0
92.5°	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.1	0.0
93°	0.0	0.1	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.1	0.0
93.5°	0.0	0.1	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.1	0.0
94°	0.0	0.1	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.1	0.0
94.5°	0.0	0.1	0.1	0.1	0.0	0.1	0.1	0.1	0.0	0.1	0.0
95°	0.0	0.0	0.1	0.1	0.0	0.1	0.1	0.1	0.0	0.1	0.0
95.5°	0.0	0.0	0.1	0.1	0.0	0.1	0.1	0.0	0.0	0.1	0.0
96°	0.0	0.0	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.0
97.5°	0.1	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.1	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.1	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.1	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.1	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.1	0.0	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
100.5°	0.1	0.0	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
101°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
101.5°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
102°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
103°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
103.5°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.1	0.0
104°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.1	0.1
104.5°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.1	0.1
105°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.1	0.1
105.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.1	0.1
106°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.1	0.1
106.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.1	0.1
107°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.1	0.1	0.1
107.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.1	0.1	0.1
108°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.1	0.1	0.1
108.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
109°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
109.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
110°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
110.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
111°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
111.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
112°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: P272215
 CATALOG NUMBER: LA56069271EWH

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
112.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
113°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
113.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
114°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
114.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
115°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
115.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
116°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
116.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
117°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
117.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
118°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
118.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
119°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
119.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
120°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
120.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
121°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
121.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
122°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
122.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
123°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
123.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
124°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
124.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
125°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
125.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
126°	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
126.5°	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
127°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
127.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
128°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
128.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
129°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
129.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
130°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
130.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
131°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
131.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
132°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
132.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
133°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
133.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
134°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
134.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: P272215
 CATALOG NUMBER: LA56069271EWH

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
135°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
135.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
136°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
136.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
138°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
138.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
139°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
139.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
141°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
141.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
142°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
142.5°	0.3	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
143°	0.3	0.3	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.2	0.1
143.5°	0.3	0.3	0.3	0.3	0.1	0.1	0.1	0.1	0.2	0.2	0.1
144°	0.3	0.3	0.3	0.3	0.1	0.1	0.1	0.1	0.2	0.2	0.2
144.5°	0.3	0.3	0.3	0.3	0.1	0.1	0.1	0.1	0.2	0.2	0.2
145°	0.3	0.3	0.3	0.3	0.1	0.1	0.1	0.2	0.2	0.2	0.2
145.5°	0.3	0.3	0.3	0.3	0.1	0.1	0.1	0.2	0.2	0.2	0.2
146°	0.3	0.3	0.3	0.3	0.1	0.1	0.2	0.2	0.2	0.2	0.2
146.5°	0.3	0.3	0.3	0.3	0.1	0.1	0.2	0.2	0.2	0.2	0.2
147°	0.3	0.3	0.3	0.3	0.1	0.2	0.2	0.2	0.2	0.2	0.2
147.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
148°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
148.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
149°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
149.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
150°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
150.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
151°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
151.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
152°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
152.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
153°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
153.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
154°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
154.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
155°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
155.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
156°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
156.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
157°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2



TEST NUMBER: P272215
 CATALOG NUMBER: LA56069271EWH

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
157.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
158°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
158.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
159°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
159.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
160°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
160.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
161°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
161.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
162°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
162.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
163°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
163.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
164°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
164.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
165°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
165.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
166°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
166.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
167°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
167.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
168°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
168.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
169°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
169.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
170°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
170.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
171°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
171.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
172°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.3	0.3
172.5°	0.3	0.3	0.3	0.3	0.3	0.2	0.3	0.3	0.3	0.3	0.3
173°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
173.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
174°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
174.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
175°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
175.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
176°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
176.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
177°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
177.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
178°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
178.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
179°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
179.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3



TEST NUMBER: P272215
CATALOG NUMBER: LA56069271EWH

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
180°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3



TEST NUMBER: P272215
 CATALOG NUMBER: LA56069271EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	272.1	272.1	272.1	272.1	272.1	272.1
0.5°	272.0	272.0	272.1	272.1	272.2	272.1
1°	271.9	271.9	271.9	272.0	272.1	272.2
1.5°	271.7	271.7	271.7	271.9	272.0	272.1
2°	271.5	271.5	271.6	271.7	271.9	272.1
2.5°	271.2	271.3	271.3	271.5	271.8	272.0
3°	270.9	271.0	271.1	271.3	271.6	271.9
3.5°	270.7	270.7	270.8	271.2	271.5	271.7
4°	270.3	270.4	270.5	270.8	271.2	271.6
4.5°	270.0	270.0	270.2	270.6	271.0	271.4
5°	269.6	269.6	269.9	270.3	270.7	271.2
5.5°	269.2	269.2	269.4	269.9	270.4	270.9
6°	268.8	268.8	269.1	269.6	270.1	270.7
6.5°	268.3	268.3	268.6	269.2	269.7	270.3
7°	267.8	267.9	268.2	268.7	269.4	270.0
7.5°	267.3	267.3	267.7	268.3	269.0	269.6
8°	266.7	266.8	267.1	267.8	268.5	269.2
8.5°	266.2	266.2	266.5	267.3	268.1	268.8
9°	265.6	265.6	266.0	266.7	267.6	268.4
9.5°	265.0	265.0	265.4	266.2	267.1	267.9
10°	264.3	264.3	264.8	265.6	266.6	267.4
10.5°	263.6	263.6	264.1	265.0	266.0	266.8
11°	262.9	262.9	263.5	264.3	265.4	266.3
11.5°	262.2	262.1	262.7	263.6	264.7	265.7
12°	261.4	261.4	261.9	262.9	264.1	265.1
12.5°	260.6	260.5	261.2	262.2	263.4	264.4
13°	259.7	259.7	260.3	261.4	262.7	263.8
13.5°	258.8	258.8	259.5	260.6	261.9	263.0
14°	257.9	257.9	258.6	259.7	261.2	262.3
14.5°	257.1	257.0	257.7	258.9	260.3	261.5
15°	256.1	256.0	256.8	258.0	259.5	260.7
15.5°	255.1	255.0	255.8	257.1	258.6	259.9
16°	254.0	253.9	254.8	256.1	257.7	259.1
16.5°	253.0	252.9	253.8	255.1	256.8	258.2
17°	251.9	251.8	252.7	254.2	255.9	257.4
17.5°	250.8	250.7	251.6	253.1	254.9	256.4
18°	249.6	249.5	250.4	252.0	253.9	255.4
18.5°	248.4	248.3	249.3	250.9	252.8	254.4
19°	247.2	247.1	248.1	249.7	251.7	253.4
19.5°	245.9	245.8	246.9	248.5	250.6	252.3
20°	244.6	244.5	245.5	247.3	249.5	251.2
20.5°	243.3	243.1	244.2	246.0	248.2	250.1
21°	241.9	241.8	242.8	244.8	247.0	249.0
21.5°	240.6	240.4	241.5	243.5	245.7	247.7
22°	239.0	238.9	240.0	242.1	244.4	246.6



TEST NUMBER: P272215
 CATALOG NUMBER: LA56069271EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
22.5°	237.6	237.4	238.7	240.7	243.2	245.2
23°	236.0	235.9	237.1	239.3	241.8	243.9
23.5°	234.6	234.3	235.7	237.8	240.3	242.6
24°	232.9	232.7	234.1	236.4	238.9	241.3
24.5°	231.3	231.1	232.5	234.7	237.5	239.8
25°	229.7	229.4	230.8	233.2	235.9	238.4
25.5°	228.0	227.8	229.3	231.6	234.5	236.9
26°	226.2	226.1	227.4	230.0	232.8	235.5
26.5°	224.5	224.3	225.8	228.3	231.3	233.8
27°	222.7	222.5	224.0	226.6	229.6	232.3
27.5°	220.9	220.7	222.3	224.9	228.0	230.7
28°	218.9	218.8	220.3	223.1	226.2	229.0
28.5°	217.2	216.9	218.6	221.2	224.6	227.4
29°	215.1	215.0	216.6	219.5	222.7	225.7
29.5°	213.2	213.0	214.8	217.6	220.9	223.9
30°	211.2	210.9	212.8	215.6	218.9	222.1
30.5°	209.2	209.0	210.8	213.7	217.2	220.3
31°	207.1	206.9	208.7	211.7	215.2	218.5
31.5°	205.0	204.8	206.8	209.8	213.4	216.6
32°	202.9	202.6	204.6	207.7	211.3	214.7
32.5°	200.8	200.6	202.5	205.7	209.4	212.7
33°	198.6	198.4	200.3	203.6	207.3	210.8
33.5°	196.4	196.2	198.2	201.5	205.2	208.7
34°	194.1	193.9	196.0	199.3	203.1	206.7
34.5°	191.9	191.6	193.8	197.1	201.0	204.6
35°	189.5	189.3	191.5	194.9	198.8	202.6
35.5°	187.2	187.1	189.3	192.7	196.7	200.4
36°	184.9	184.7	186.8	190.4	194.4	198.3
36.5°	182.5	182.3	184.6	188.0	192.2	196.0
37°	180.1	179.8	182.1	185.7	189.8	193.8
37.5°	177.7	177.5	179.8	183.4	187.5	191.6
38°	175.2	175.0	177.3	181.0	185.1	189.3
38.5°	172.7	172.5	175.0	178.6	182.9	187.0
39°	170.2	170.0	172.4	176.1	180.4	184.7
39.5°	167.7	167.5	170.0	173.7	178.1	182.3
40°	165.2	164.9	167.4	171.2	175.6	179.9
40.5°	162.5	162.3	164.9	168.7	173.1	177.5
41°	160.0	159.8	162.3	166.2	170.5	175.0
41.5°	157.4	157.2	159.8	163.7	168.1	172.6
42°	154.7	154.5	157.1	161.1	165.4	170.1
42.5°	152.1	151.9	154.6	158.6	163.0	167.7
43°	149.5	149.2	151.9	155.9	160.4	165.0
43.5°	146.7	146.6	149.3	153.3	157.9	162.5
44°	144.0	143.8	146.6	150.6	155.1	160.0
44.5°	141.3	141.1	144.0	148.0	152.6	157.4



TEST NUMBER: P272215
 CATALOG NUMBER: LA56069271EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
45°	138.6	138.4	141.2	145.4	149.9	154.8
45.5°	135.8	135.6	138.6	142.7	147.3	152.2
46°	133.1	132.9	135.8	139.9	144.6	149.5
46.5°	130.4	130.2	133.1	137.3	141.9	146.9
47°	127.7	127.4	130.4	134.5	139.2	144.2
47.5°	124.9	124.6	127.6	131.8	136.5	141.6
48°	122.1	122.0	124.8	129.1	133.8	138.8
48.5°	119.2	119.2	122.2	126.4	131.0	136.1
49°	116.4	116.4	119.4	123.5	128.3	133.3
49.5°	113.8	113.7	116.7	120.9	125.5	130.7
50°	111.0	111.0	114.0	118.1	122.8	127.9
50.5°	108.3	108.3	111.2	115.4	120.1	125.3
51°	105.6	105.6	108.5	112.8	117.4	122.5
51.5°	103.0	103.0	105.9	110.0	114.6	119.8
52°	100.4	100.4	103.3	107.4	112.0	117.0
52.5°	97.8	97.7	100.7	104.7	109.2	114.4
53°	95.2	95.2	98.0	102.1	106.6	111.7
53.5°	92.7	92.7	95.4	99.6	103.9	109.0
54°	90.2	90.2	92.9	96.9	101.3	106.4
54.5°	87.7	87.6	90.4	94.4	98.7	103.7
55°	85.2	85.3	87.9	91.9	96.2	101.1
55.5°	82.8	82.9	85.5	89.4	93.7	98.5
56°	80.5	80.4	83.1	87.0	91.1	95.9
56.5°	78.2	78.1	80.7	84.4	88.6	93.4
57°	75.9	75.8	78.4	82.2	86.2	90.9
57.5°	73.6	73.6	76.2	79.8	83.8	88.5
58°	71.4	71.4	73.9	77.5	81.5	85.9
58.5°	69.2	69.2	71.6	75.3	79.1	83.6
59°	67.1	67.0	69.5	73.0	76.8	81.2
59.5°	65.0	65.0	67.3	70.8	74.6	78.9
60°	62.9	62.9	65.2	68.6	72.4	76.6
60.5°	60.9	60.8	63.2	66.5	70.2	74.3
61°	58.9	58.9	61.1	64.5	68.0	72.1
61.5°	57.0	56.8	59.1	62.4	65.9	70.0
62°	55.1	55.0	57.2	60.4	63.9	67.8
62.5°	53.2	53.2	55.2	58.4	61.8	65.7
63°	51.3	51.4	54.1	56.4	59.8	63.6
63.5°	49.5	49.5	52.1	54.5	57.8	61.7
64°	47.7	47.7	50.2	52.7	55.9	59.7
64.5°	46.0	45.9	48.2	50.9	53.9	57.7
65°	44.2	44.2	46.2	49.1	52.1	55.7
65.5°	42.6	42.5	44.4	47.3	50.3	53.7
66°	40.9	40.9	42.7	45.5	48.5	51.9
66.5°	39.3	39.2	41.1	43.8	46.8	50.2
67°	37.7	37.6	39.5	42.1	45.0	48.4



TEST NUMBER: P272215
 CATALOG NUMBER: LA56069271EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
67.5°	36.2	36.1	37.9	40.5	43.4	46.7
68°	34.6	34.6	36.3	38.9	41.7	44.9
68.5°	33.1	33.0	34.8	37.3	40.1	43.3
69°	31.7	31.6	33.3	35.7	38.4	41.6
69.5°	30.2	30.1	31.8	34.2	36.9	39.9
70°	28.8	28.7	30.3	32.7	35.3	38.4
70.5°	27.4	27.3	28.9	31.3	33.8	36.8
71°	26.0	26.0	27.5	29.8	32.3	35.2
71.5°	24.7	24.6	26.2	28.4	30.8	33.5
72°	23.4	23.3	24.8	27.0	29.2	31.7
72.5°	22.1	22.1	23.5	25.6	27.7	30.0
73°	20.9	20.8	22.2	24.3	26.1	28.1
73.5°	19.7	19.6	21.0	23.0	24.5	26.3
74°	18.4	18.4	19.7	21.7	22.9	24.6
74.5°	17.3	17.2	18.5	20.5	21.4	22.8
75°	16.2	16.1	17.4	19.2	19.9	21.1
75.5°	15.0	15.0	16.2	18.0	18.4	19.4
76°	13.9	13.9	15.1	16.8	17.0	17.7
76.5°	13.0	12.8	14.0	15.6	15.6	16.1
77°	12.0	11.8	13.0	14.5	14.3	14.6
77.5°	11.0	10.8	11.9	13.4	13.0	13.1
78°	10.0	9.8	10.9	12.3	11.8	11.7
78.5°	9.0	8.9	9.9	11.2	10.6	10.4
79°	8.1	8.0	9.0	10.2	9.6	9.2
79.5°	7.2	7.2	8.1	9.2	8.5	8.1
80°	6.4	6.3	7.2	8.3	7.6	7.1
80.5°	5.6	5.5	6.4	7.4	6.7	6.2
81°	4.8	4.8	5.6	6.5	5.8	5.4
81.5°	4.1	4.2	4.9	5.7	5.1	4.7
82°	3.4	3.5	4.2	5.0	4.4	4.0
82.5°	2.8	2.8	3.5	4.3	3.7	3.2
83°	2.2	2.2	2.8	3.6	3.0	2.5
83.5°	1.7	1.7	2.2	3.0	2.5	1.8
84°	1.3	1.2	1.7	2.4	2.0	1.3
84.5°	0.9	0.9	1.3	1.8	1.6	1.0
85°	0.7	0.7	0.9	1.4	1.3	0.7
85.5°	0.5	0.5	0.7	1.0	1.0	0.5
86°	0.4	0.4	0.5	0.8	0.8	0.4
86.5°	0.2	0.2	0.4	0.6	0.6	0.3
87°	0.1	0.1	0.2	0.4	0.5	0.3
87.5°	0.0	0.1	0.1	0.3	0.4	0.3
88°	0.0	0.1	0.1	0.1	0.3	0.2
88.5°	0.0	0.1	0.1	0.1	0.2	0.2
89°	0.0	0.1	0.1	0.1	0.1	0.1
89.5°	0.0	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: P272215
 CATALOG NUMBER: LA56069271EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
90°	0.0	0.1	0.1	0.1	0.1	0.1
90.5°	0.0	0.1	0.1	0.1	0.1	0.1
91°	0.0	0.1	0.1	0.1	0.1	0.1
91.5°	0.0	0.1	0.1	0.1	0.1	0.1
92°	0.0	0.1	0.1	0.1	0.1	0.1
92.5°	0.0	0.1	0.1	0.1	0.1	0.1
93°	0.0	0.1	0.1	0.1	0.1	0.0
93.5°	0.0	0.1	0.1	0.1	0.0	0.0
94°	0.0	0.1	0.1	0.1	0.0	0.0
94.5°	0.0	0.1	0.1	0.1	0.0	0.0
95°	0.0	0.1	0.1	0.1	0.0	0.0
95.5°	0.0	0.1	0.1	0.1	0.0	0.0
96°	0.0	0.1	0.1	0.1	0.0	0.0
96.5°	0.0	0.1	0.1	0.1	0.0	0.0
97°	0.0	0.1	0.1	0.1	0.1	0.0
97.5°	0.0	0.1	0.1	0.1	0.1	0.1
98°	0.0	0.1	0.1	0.1	0.1	0.1
98.5°	0.0	0.1	0.1	0.1	0.1	0.1
99°	0.0	0.1	0.1	0.1	0.1	0.1
99.5°	0.0	0.1	0.1	0.1	0.1	0.1
100°	0.0	0.1	0.1	0.1	0.1	0.1
100.5°	0.0	0.1	0.1	0.1	0.1	0.1
101°	0.0	0.1	0.1	0.1	0.1	0.1
101.5°	0.0	0.1	0.1	0.1	0.1	0.1
102°	0.0	0.1	0.1	0.1	0.1	0.1
102.5°	0.0	0.1	0.1	0.1	0.1	0.1
103°	0.0	0.1	0.1	0.1	0.1	0.1
103.5°	0.0	0.1	0.1	0.1	0.1	0.1
104°	0.0	0.1	0.1	0.1	0.1	0.1
104.5°	0.0	0.1	0.1	0.1	0.1	0.1
105°	0.1	0.1	0.1	0.1	0.1	0.1
105.5°	0.1	0.1	0.1	0.1	0.1	0.1
106°	0.1	0.1	0.1	0.1	0.1	0.1
106.5°	0.1	0.1	0.1	0.1	0.1	0.1
107°	0.1	0.1	0.1	0.1	0.1	0.1
107.5°	0.1	0.1	0.1	0.1	0.1	0.1
108°	0.1	0.1	0.1	0.1	0.1	0.1
108.5°	0.1	0.1	0.1	0.1	0.1	0.1
109°	0.1	0.1	0.1	0.1	0.1	0.1
109.5°	0.1	0.1	0.1	0.1	0.1	0.1
110°	0.1	0.1	0.1	0.1	0.1	0.1
110.5°	0.1	0.1	0.1	0.1	0.1	0.1
111°	0.1	0.1	0.1	0.1	0.1	0.1
111.5°	0.1	0.1	0.1	0.1	0.1	0.1
112°	0.1	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: P272215
 CATALOG NUMBER: LA56069271EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
112.5°	0.1	0.1	0.1	0.1	0.1	0.1
113°	0.1	0.1	0.1	0.1	0.1	0.1
113.5°	0.1	0.1	0.1	0.1	0.1	0.1
114°	0.1	0.1	0.1	0.1	0.1	0.1
114.5°	0.1	0.1	0.1	0.1	0.1	0.1
115°	0.1	0.1	0.1	0.1	0.1	0.1
115.5°	0.1	0.1	0.1	0.1	0.1	0.1
116°	0.1	0.1	0.1	0.1	0.1	0.1
116.5°	0.1	0.1	0.1	0.1	0.1	0.1
117°	0.1	0.1	0.1	0.1	0.1	0.1
117.5°	0.1	0.1	0.1	0.1	0.1	0.1
118°	0.1	0.1	0.1	0.1	0.1	0.1
118.5°	0.1	0.1	0.1	0.1	0.1	0.1
119°	0.1	0.1	0.1	0.1	0.1	0.1
119.5°	0.1	0.1	0.1	0.1	0.1	0.1
120°	0.1	0.1	0.1	0.1	0.1	0.1
120.5°	0.1	0.1	0.1	0.1	0.1	0.1
121°	0.1	0.1	0.1	0.1	0.1	0.1
121.5°	0.1	0.1	0.1	0.1	0.1	0.1
122°	0.1	0.1	0.1	0.1	0.1	0.1
122.5°	0.1	0.1	0.1	0.1	0.1	0.1
123°	0.1	0.1	0.1	0.1	0.1	0.1
123.5°	0.1	0.1	0.1	0.1	0.1	0.1
124°	0.1	0.2	0.2	0.1	0.1	0.1
124.5°	0.1	0.2	0.2	0.2	0.1	0.1
125°	0.1	0.2	0.2	0.2	0.1	0.1
125.5°	0.1	0.2	0.2	0.2	0.2	0.1
126°	0.1	0.2	0.2	0.2	0.2	0.2
126.5°	0.1	0.2	0.2	0.2	0.2	0.2
127°	0.1	0.2	0.2	0.2	0.2	0.2
127.5°	0.1	0.2	0.2	0.2	0.2	0.2
128°	0.1	0.2	0.2	0.2	0.2	0.2
128.5°	0.1	0.2	0.2	0.2	0.2	0.2
129°	0.1	0.2	0.2	0.2	0.2	0.2
129.5°	0.1	0.2	0.2	0.2	0.2	0.2
130°	0.1	0.2	0.2	0.2	0.2	0.2
130.5°	0.1	0.2	0.2	0.2	0.2	0.2
131°	0.1	0.2	0.2	0.2	0.2	0.2
131.5°	0.1	0.2	0.2	0.2	0.2	0.2
132°	0.1	0.2	0.2	0.2	0.2	0.2
132.5°	0.1	0.2	0.2	0.2	0.2	0.2
133°	0.1	0.2	0.2	0.2	0.2	0.2
133.5°	0.1	0.2	0.2	0.2	0.2	0.2
134°	0.1	0.2	0.2	0.2	0.2	0.2
134.5°	0.1	0.2	0.2	0.2	0.2	0.2



TEST NUMBER: P272215
 CATALOG NUMBER: LA56069271EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
135°	0.1	0.2	0.2	0.2	0.2	0.2
135.5°	0.1	0.2	0.2	0.2	0.2	0.2
136°	0.1	0.2	0.2	0.2	0.2	0.2
136.5°	0.1	0.2	0.2	0.2	0.2	0.2
137°	0.1	0.2	0.2	0.2	0.2	0.2
137.5°	0.1	0.2	0.2	0.2	0.2	0.2
138°	0.1	0.2	0.2	0.2	0.2	0.2
138.5°	0.1	0.2	0.2	0.2	0.2	0.2
139°	0.1	0.2	0.2	0.2	0.2	0.2
139.5°	0.1	0.2	0.2	0.2	0.2	0.2
140°	0.1	0.2	0.2	0.2	0.2	0.2
140.5°	0.1	0.2	0.2	0.2	0.2	0.2
141°	0.1	0.2	0.2	0.2	0.2	0.2
141.5°	0.1	0.3	0.3	0.2	0.2	0.2
142°	0.1	0.3	0.3	0.3	0.2	0.2
142.5°	0.1	0.3	0.3	0.3	0.3	0.3
143°	0.1	0.3	0.3	0.3	0.3	0.3
143.5°	0.1	0.3	0.3	0.3	0.3	0.3
144°	0.2	0.3	0.3	0.3	0.3	0.3
144.5°	0.2	0.3	0.3	0.3	0.3	0.3
145°	0.2	0.3	0.3	0.3	0.3	0.3
145.5°	0.2	0.3	0.3	0.3	0.3	0.3
146°	0.2	0.3	0.3	0.3	0.3	0.3
146.5°	0.2	0.3	0.3	0.3	0.3	0.3
147°	0.2	0.3	0.3	0.3	0.3	0.3
147.5°	0.2	0.3	0.3	0.3	0.3	0.3
148°	0.2	0.3	0.3	0.3	0.3	0.3
148.5°	0.2	0.3	0.3	0.3	0.3	0.3
149°	0.2	0.3	0.3	0.3	0.3	0.3
149.5°	0.2	0.3	0.3	0.3	0.3	0.3
150°	0.2	0.3	0.3	0.3	0.3	0.3
150.5°	0.2	0.3	0.3	0.3	0.3	0.3
151°	0.2	0.3	0.3	0.3	0.3	0.3
151.5°	0.2	0.3	0.3	0.3	0.3	0.3
152°	0.2	0.3	0.3	0.3	0.3	0.3
152.5°	0.2	0.3	0.3	0.3	0.3	0.3
153°	0.2	0.3	0.3	0.3	0.3	0.3
153.5°	0.2	0.3	0.3	0.3	0.3	0.3
154°	0.2	0.3	0.3	0.3	0.3	0.3
154.5°	0.2	0.3	0.3	0.3	0.3	0.3
155°	0.2	0.3	0.3	0.3	0.3	0.3
155.5°	0.2	0.3	0.3	0.3	0.3	0.3
156°	0.2	0.3	0.3	0.3	0.3	0.3
156.5°	0.2	0.3	0.3	0.3	0.3	0.3
157°	0.2	0.3	0.3	0.3	0.3	0.3



TEST NUMBER: P272215
 CATALOG NUMBER: LA56069271EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
157.5°	0.2	0.3	0.3	0.3	0.3	0.3
158°	0.2	0.3	0.3	0.3	0.3	0.3
158.5°	0.2	0.3	0.3	0.3	0.3	0.3
159°	0.2	0.3	0.3	0.3	0.3	0.3
159.5°	0.2	0.3	0.3	0.3	0.3	0.3
160°	0.2	0.3	0.3	0.3	0.3	0.3
160.5°	0.2	0.3	0.3	0.3	0.3	0.3
161°	0.2	0.3	0.3	0.3	0.3	0.3
161.5°	0.2	0.3	0.3	0.3	0.3	0.3
162°	0.2	0.3	0.3	0.3	0.3	0.3
162.5°	0.2	0.3	0.3	0.3	0.3	0.3
163°	0.2	0.3	0.3	0.3	0.3	0.3
163.5°	0.2	0.3	0.3	0.3	0.3	0.3
164°	0.2	0.3	0.3	0.3	0.3	0.3
164.5°	0.2	0.3	0.3	0.3	0.3	0.3
165°	0.2	0.3	0.3	0.3	0.3	0.3
165.5°	0.2	0.3	0.3	0.3	0.3	0.3
166°	0.2	0.3	0.3	0.3	0.3	0.3
166.5°	0.2	0.3	0.3	0.3	0.3	0.3
167°	0.2	0.3	0.3	0.3	0.3	0.3
167.5°	0.2	0.3	0.3	0.3	0.3	0.3
168°	0.2	0.3	0.3	0.3	0.3	0.3
168.5°	0.2	0.3	0.3	0.3	0.3	0.3
169°	0.2	0.3	0.3	0.3	0.3	0.3
169.5°	0.2	0.3	0.3	0.3	0.3	0.3
170°	0.2	0.3	0.3	0.3	0.3	0.3
170.5°	0.2	0.3	0.3	0.3	0.3	0.3
171°	0.2	0.3	0.3	0.3	0.3	0.3
171.5°	0.2	0.3	0.3	0.3	0.3	0.3
172°	0.3	0.3	0.3	0.3	0.3	0.3
172.5°	0.3	0.3	0.3	0.3	0.3	0.3
173°	0.3	0.3	0.3	0.3	0.3	0.3
173.5°	0.3	0.3	0.3	0.3	0.3	0.3
174°	0.3	0.3	0.3	0.3	0.3	0.3
174.5°	0.3	0.3	0.3	0.3	0.3	0.3
175°	0.3	0.3	0.3	0.3	0.3	0.3
175.5°	0.3	0.3	0.3	0.3	0.3	0.3
176°	0.3	0.3	0.3	0.3	0.3	0.3
176.5°	0.3	0.3	0.3	0.3	0.3	0.3
177°	0.3	0.3	0.3	0.3	0.3	0.3
177.5°	0.3	0.3	0.3	0.3	0.3	0.3
178°	0.3	0.3	0.3	0.3	0.3	0.3
178.5°	0.3	0.3	0.3	0.3	0.3	0.3
179°	0.3	0.3	0.3	0.3	0.3	0.3
179.5°	0.3	0.3	0.3	0.3	0.3	0.3



TEST NUMBER: P272215
CATALOG NUMBER: LA56069271EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
180°	0.3	0.3	0.3	0.3	0.3	0.3

(END OF REPORT)