

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: HALO

Report Number: P979226

Luminaire Tested: L820S15SP935XXXXBLSHBXXXX

Issue Date: 4/1/2025

Test Information

Test Method: LM-79-2019
Report Number: P979226
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (3DTHCNLSLWHSTLFWHST15LRS30KWH)
Test Lab: INNOVATION CENTER
Issue Date: 4/1/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: L820S15SP935XXXXBLSHBXXXX
Description: 2IN Sustainable LED Track Luminaire with spot optic
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1428.0 lumens
Efficiency: N/A
Efficacy: 107.4 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.22' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: 0.9
Total Harmonic Distortion (THDi): 20
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P979226
CATALOG NUMBER: L820S15SP935XXXXBLSHBXXXX

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270° - · - 135°-315°



TEST NUMBER: P979226
 CATALOG NUMBER: L820S15SP935XXXXBLSHBXXXX

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	
1	115	113	111	109	113	111	109	107	107	105	104	103	102	101	100	99	98	96	96	96	96	
2	111	107	104	102	109	106	103	101	103	100	99	100	98	96	97	96	94	93	93	93	93	
3	108	103	99	96	106	102	98	96	99	96	94	97	95	93	95	93	91	90	91	91	91	
4	104	99	95	92	103	98	94	91	96	93	90	94	91	89	92	90	88	87	88	88	87	
5	101	95	91	88	100	94	91	88	93	90	87	91	89	86	90	88	86	84	86	86	84	
6	98	92	88	85	97	91	88	85	90	87	84	89	86	84	88	85	83	82	83	83	82	
7	96	89	85	82	95	89	85	82	88	84	82	87	83	81	86	83	81	80	81	81	80	
8	93	87	83	80	92	86	82	80	85	82	79	84	81	79	83	81	79	78	79	79	78	
9	91	84	80	77	90	84	80	77	83	80	77	82	79	77	82	79	77	76	77	77	76	
10	89	82	78	75	88	82	78	75	81	78	75	80	77	75	80	77	75	74	75	75	74	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	2575925	2575925	2575925	2575925
5°	2144115	2351271	2296758	2097809
10°	873913	1151087	1061500	835263
15°	355154	432171	410871	343439
20°	212294	235399	232979	206907
25°	164436	173039	173069	162943
30°	119037	139512	133823	114035
35°	32784	53968	45805	27001
40°	4347	5054	4842	4241
45°	2680	3063	3139	2757
50°	2316	2569	2695	2443
55°	2171	2313	2454	2266
60°	2599	2599	2707	2653
65°	3203	3075	3203	3331
70°	3483	3799	3720	3324
75°	3138	3138	3033	2929
80°	4053	3897	3742	3742
85°	621	1242	932	621

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 65°
 Vertical Angle: 82.5°
 Luminance: 4355 cd/sqm



TEST NUMBER: P979226
 CATALOG NUMBER: L820S15SP935XXXXBLSHBXXXX

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	617.7	43.3
10°-20°	433.6	30.4
20°-30°	261.8	18.3
30°-40°	91.4	6.4
40°-50°	6.4	0.4
50°-60°	4.5	0.3
60°-70°	4.9	0.3
70°-80°	3.2	0.2
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.1	0.0
110°-120°	0.1	0.0
120°-130°	0.0	0.0
130°-140°	0.1	0.0
140°-150°	0.4	0.0
150°-160°	1.1	0.1
160°-170°	1.3	0.1
170°-180°	0.5	0.0
0°-30°	1313.2	92.0
0°-40°	1404.5	98.4
0°-60°	1415.5	99.1
0°-90°	1424.5	99.7
90°-120°	0.2	0.0
90°-150°	0.7	0.0
90°-180°	4.0	0.3
0°-180°	1428.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	9515	9515	9515	9515	9515	
5°	7890	8652	8452	7720	7890	588
15°	1267	1542	1466	1225	1267	396
25°	550	579	579	546	550	254
35°	99	163	139	82	99	82
45°	7	8	8	7	7	6
55°	5	5	5	5	5	4
65°	5	5	5	5	5	5
75°	3	3	3	3	3	3
85°	0	0	0	0	0	1
90°	0	0	0	0	0	0
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	1	0	0	1	1	0
155°	3	2	2	3	3	1
165°	5	5	5	5	5	1
175°	5	5	5	4	5	0
180°	4	4	4	4	4	



TEST NUMBER: P979226
 CATALOG NUMBER: L820S15SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2
2.5°	9143.7	9143.7	9144.3	9145.4	9146.9	9149.1	9151.8	9155.0	9158.9	9163.4	9168.5
5°	7890.0	7900.4	7913.3	7928.4	7945.9	7965.6	7987.4	8011.2	8037.1	8065.0	8094.7
7.5°	5471.3	5486.4	5505.0	5527.3	5553.2	5582.8	5616.0	5652.8	5693.2	5737.2	5784.8
10°	3179.1	3191.2	3206.2	3224.3	3245.5	3269.7	3297.1	3327.5	3361.0	3397.6	3437.2
12.5°	1893.6	1899.3	1906.5	1915.3	1925.7	1937.6	1951.1	1966.1	1982.7	2000.9	2020.6
15°	1267.2	1270.1	1273.8	1278.2	1283.4	1289.3	1296.0	1303.3	1311.4	1320.1	1329.5
17.5°	930.2	932.0	934.3	937.0	940.2	943.8	947.8	952.3	957.2	962.6	968.4
20°	736.9	738.2	739.7	741.6	743.7	746.0	748.5	751.3	754.3	757.5	760.9
22.5°	626.2	626.5	627.0	627.6	628.4	629.4	630.6	632.0	633.6	635.4	637.2
25°	550.5	550.7	551.0	551.3	551.8	552.5	553.2	554.0	554.9	556.0	557.0
27.5°	499.2	499.4	499.8	500.3	500.9	501.5	502.2	503.0	503.9	504.7	505.4
30°	380.8	381.8	383.0	384.4	386.1	388.0	390.1	392.5	395.1	397.9	400.4
32.5°	237.3	238.1	239.1	240.5	242.0	243.9	246.1	248.6	251.4	254.5	257.0
35°	99.2	99.9	100.9	102.1	103.5	105.1	107.0	109.1	111.3	113.8	115.6
37.5°	18.8	19.0	19.3	19.6	20.1	20.6	21.2	21.9	22.7	23.6	24.2
40°	12.3	12.3	12.4	12.4	12.4	12.4	12.5	12.5	12.6	12.6	12.7
42.5°	8.6	8.6	8.6	8.6	8.7	8.7	8.8	8.8	8.9	8.9	9.0
45°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0
47.5°	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2
50°	5.5	5.5	5.5	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4
52.5°	5.0	5.0	5.0	4.9	4.9	4.9	4.9	4.9	4.8	4.8	4.8
55°	4.6	4.6	4.6	4.6	4.5	4.5	4.5	4.5	4.5	4.5	4.5
57.5°	4.5	4.5	4.5	4.4	4.4	4.4	4.3	4.3	4.3	4.3	4.3
60°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.7	4.7
62.5°	4.9	4.9	4.9	4.8	4.8	4.8	4.8	4.8	4.7	4.7	4.7
65°	5.0	4.9	4.9	4.9	4.9	4.9	4.9	4.8	4.8	4.8	4.8
67.5°	5.2	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.2	5.2
70°	4.4	4.4	4.4	4.4	4.5	4.5	4.5	4.5	4.5	4.5	4.5
72.5°	3.4	3.4	3.5	3.5	3.5	3.5	3.5	3.6	3.6	3.6	3.6
75°	3.0	3.0	3.0	3.0	2.9	2.9	2.9	2.9	2.9	2.9	2.9
77.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.7	2.7	2.7	2.7	2.7
80°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
82.5°	1.7	1.7	1.7	1.7	1.7	1.8	1.8	1.8	1.8	1.8	1.8
85°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.1
102.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
105°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
107.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
110°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: P979226
 CATALOG NUMBER: L820S15SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
115°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
132.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
140°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
142.5°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
145°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
147.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
150°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
152.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.8	1.8
155°	2.6	2.6	2.6	2.6	2.6	2.6	2.5	2.5	2.5	2.5	2.5
157.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.2	3.2	3.2
160°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	3.9
162.5°	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.5	4.5	4.5	4.5
165°	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
167.5°	5.2	5.2	5.2	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3
170°	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3
172.5°	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.2	5.2	5.2	5.2
175°	4.7	4.7	4.7	4.7	4.8	4.8	4.8	4.8	4.8	4.8	4.9
177.5°	4.2	4.2	4.3	4.3	4.4	4.4	4.4	4.4	4.4	4.4	4.4
180°	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9



TEST NUMBER: P979226
 CATALOG NUMBER: L820S15SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2
2.5°	9174.2	9180.7	9187.8	9195.6	9204.1	9213.4	9223.4	9234.1	9258.8	9254.4	9253.5
5°	8126.2	8159.4	8194.2	8214.6	8227.0	8312.0	8294.2	8279.5	8293.0	8308.8	8327.0
7.5°	5836.0	5887.2	5908.2	5932.5	5960.1	6042.6	6024.8	6058.6	6095.0	6133.7	6174.8
10°	3480.0	3502.3	3522.6	3545.3	3633.0	3615.0	3630.6	3667.6	3706.6	3747.4	3790.1
12.5°	2038.3	2048.3	2059.5	2071.7	2108.4	2100.1	2117.3	2136.9	2157.5	2179.2	2201.8
15°	1335.7	1339.9	1344.6	1349.9	1364.8	1362.6	1371.4	1380.7	1390.5	1400.6	1409.5
17.5°	971.1	973.2	975.7	988.6	985.7	985.1	989.5	994.3	999.2	1004.4	1007.8
20°	761.7	762.6	763.7	770.5	768.6	768.7	771.5	774.4	777.6	780.9	782.8
22.5°	637.9	638.7	639.7	644.4	643.2	643.3	644.6	646.0	647.5	648.7	653.1
25°	557.2	557.5	557.9	560.4	559.5	559.6	560.4	561.3	562.3	563.2	566.3
27.5°	505.7	506.0	506.6	509.1	508.6	508.8	509.5	510.1	510.8	511.1	512.8
30°	401.9	403.6	405.5	411.7	410.7	412.2	414.8	417.5	420.4	422.0	427.5
32.5°	258.6	260.3	262.3	269.2	267.8	269.4	272.1	275.1	278.4	279.9	285.7
35°	116.6	117.7	119.0	124.0	122.5	124.0	126.3	128.7	131.4	132.6	137.7
37.5°	24.6	25.0	25.5	27.0	26.5	27.4	28.5	29.6	30.6	31.2	33.1
40°	12.7	12.8	12.9	13.0	13.0	13.0	13.1	13.2	13.3	13.3	13.5
42.5°	9.0	9.0	9.1	9.2	9.2	9.2	9.3	9.4	9.5	9.5	9.7
45°	7.0	7.0	7.0	7.1	7.1	7.1	7.1	7.1	7.2	7.2	7.2
47.5°	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.3	6.3
50°	5.4	5.5	5.5	5.5	5.5	5.5	5.5	5.6	5.6	5.6	5.6
52.5°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.9	4.9	5.0
55°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.6
57.5°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
60°	4.7	4.7	4.7	4.7	4.6	4.6	4.6	4.6	4.6	4.6	4.6
62.5°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
65°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.7	4.7	4.7	4.7
67.5°	5.2	5.2	5.2	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3
70°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.4	4.4	4.4	4.5
72.5°	3.6	3.6	3.6	3.7	3.7	3.7	3.7	3.7	3.8	3.8	3.8
75°	2.9	2.9	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
77.5°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.6
80°	2.6	2.6	2.6	2.6	2.5	2.5	2.5	2.5	2.5	2.5	2.5
82.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	2.0	2.0	2.0	2.0
85°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0
97.5°	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
100°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
102.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
105°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
107.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
110°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: P979226
 CATALOG NUMBER: L820S15SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1
117.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0
120°	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
132.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
140°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
142.5°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
145°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
147.5°	0.9	0.9	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
150°	1.3	1.3	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2
152.5°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.7	1.7
155°	2.5	2.5	2.5	2.5	2.5	2.4	2.4	2.4	2.4	2.4	2.4
157.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.1	3.1
160°	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9
162.5°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5
165°	5.0	5.0	5.0	5.0	5.0	5.0	5.0	4.9	4.9	4.9	4.9
167.5°	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.2	5.2	5.2	5.2
170°	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3
172.5°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
175°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
177.5°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5
180°	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9



TEST NUMBER: P979226
 CATALOG NUMBER: L820S15SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2
2.5°	9260.1	9267.0	9274.3	9282.0	9290.0	9298.3	9327.8	9322.9	9323.1	9328.8	9335.1
5°	8347.5	8370.5	8395.9	8448.2	8452.1	8462.0	8469.2	8480.1	8494.8	8546.7	8530.6
7.5°	6218.1	6348.8	6303.7	6310.2	6331.0	6354.0	6379.2	6491.2	6435.5	6465.0	6495.9
10°	3834.3	3886.8	3881.7	3908.4	3934.7	3960.5	3985.5	4018.0	4039.2	4069.7	4099.9
12.5°	2249.6	2228.0	2245.5	2262.9	2279.6	2295.7	2335.6	2327.5	2346.5	2364.5	2379.0
15°	1427.7	1423.5	1433.0	1442.5	1451.8	1460.9	1475.0	1481.2	1492.8	1501.9	1509.2
17.5°	1015.0	1014.5	1019.3	1024.2	1029.2	1046.0	1038.9	1044.9	1050.7	1054.4	1070.6
20°	786.7	787.3	790.1	793.0	795.8	804.3	801.4	804.3	806.7	808.4	815.2
22.5°	650.8	651.4	652.9	654.3	655.8	660.0	659.0	661.1	662.5	663.5	666.9
25°	565.0	566.0	567.1	568.1	569.1	571.3	571.0	572.3	573.1	574.0	576.2
27.5°	511.7	512.1	512.7	513.3	514.1	515.7	515.8	516.5	517.0	517.6	518.9
30°	424.9	426.2	427.7	429.3	431.1	434.8	434.9	436.1	436.3	436.9	438.9
32.5°	282.7	284.4	286.1	288.0	290.1	293.9	294.6	296.3	297.5	298.7	300.8
35°	135.5	137.2	139.1	141.0	143.0	146.2	147.3	149.1	150.6	152.2	154.2
37.5°	32.3	33.4	34.3	35.1	35.7	36.5	37.0	38.2	39.2	39.9	40.3
40°	13.4	13.5	13.5	13.6	13.6	13.7	13.7	13.8	13.9	13.9	14.0
42.5°	9.7	9.8	9.8	9.9	10.0	10.1	10.1	10.2	10.2	10.4	10.3
45°	7.3	7.3	7.3	7.4	7.4	7.5	7.5	7.6	7.6	7.7	7.7
47.5°	6.3	6.4	6.4	6.4	6.5	6.5	6.6	6.6	6.7	6.8	6.8
50°	5.6	5.6	5.6	5.7	5.7	5.7	5.7	5.8	5.8	5.9	5.9
52.5°	5.0	5.0	5.1	5.1	5.2	5.2	5.3	5.3	5.3	5.4	5.4
55°	4.6	4.6	4.6	4.7	4.7	4.8	4.8	4.8	4.8	4.8	4.8
57.5°	4.4	4.4	4.4	4.4	4.4	4.5	4.5	4.5	4.5	4.5	4.5
60°	4.6	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.8
62.5°	4.7	4.7	4.7	4.7	4.7	4.8	4.8	4.8	4.8	4.8	4.8
65°	4.7	4.7	4.7	4.7	4.7	4.7	4.8	4.8	4.8	4.8	4.8
67.5°	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.2	5.2	5.2	5.2
70°	4.5	4.5	4.5	4.5	4.5	4.6	4.6	4.6	4.6	4.7	4.7
72.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.7	3.7	3.7	3.7
75°	2.8	2.8	2.8	2.8	2.9	2.9	2.9	2.9	2.9	2.9	2.9
77.5°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
80°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
82.5°	2.0	2.0	2.0	2.0	2.1	2.1	2.1	2.1	2.1	2.1	2.1
85°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.4	0.4	0.4
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2
90°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
92.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.1	0.1	0.1	0.1
105°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
107.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
110°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: P979226
 CATALOG NUMBER: L820S15SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
115°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
117.5°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
120°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.1
132.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.4	0.4	0.4	0.3	0.4	0.3	0.3	0.3	0.3	0.3	0.3
145°	0.6	0.6	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
147.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
150°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.1	1.1	1.1	1.1
152.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.6
155°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.3	2.4	2.3
157.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.0
160°	3.9	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
162.5°	4.5	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4
165°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
167.5°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
170°	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3
172.5°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
175°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
177.5°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5
180°	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9



TEST NUMBER: P979226
 CATALOG NUMBER: L820S15SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2
2.5°	9342.0	9349.5	9357.7	9372.4	9367.1	9365.9	9365.1	9364.9	9365.1	9370.6	9367.6
5°	8543.7	8560.1	8579.7	8652.3	8627.4	8638.7	8628.7	8622.4	8653.5	8616.8	8619.6
7.5°	6528.0	6561.3	6587.3	6594.9	6607.1	6617.9	6704.8	6636.1	6653.6	6672.8	6693.3
10°	4123.2	4153.4	4164.8	4187.4	4208.2	4306.7	4243.8	4259.2	4270.6	4279.1	4324.4
12.5°	2419.6	2407.1	2422.8	2435.4	2444.6	2462.9	2462.9	2475.9	2488.9	2551.1	2514.5
15°	1521.2	1525.8	1534.6	1542.0	1570.6	1552.7	1559.8	1566.1	1572.8	1591.6	1584.8
17.5°	1061.5	1065.3	1068.5	1071.0	1080.7	1075.2	1078.8	1082.9	1086.5	1092.3	1092.1
20°	811.6	813.8	815.7	817.1	821.0	819.4	821.1	823.3	825.0	826.4	827.4
22.5°	665.3	666.5	667.6	668.7	670.8	670.7	671.5	672.0	676.0	672.5	673.1
25°	576.0	577.2	578.3	579.3	580.4	580.6	580.7	580.7	582.4	580.5	580.8
27.5°	518.8	519.2	519.6	520.1	520.5	520.7	520.8	520.9	522.3	521.5	521.9
30°	438.3	439.2	440.2	446.3	443.1	443.7	443.3	443.0	445.2	442.8	442.7
32.5°	300.9	302.0	303.0	308.8	304.8	305.7	306.4	307.1	310.2	308.0	308.2
35°	155.3	156.7	158.0	163.3	160.2	161.1	161.9	162.6	165.0	163.9	164.6
37.5°	41.3	42.1	42.6	44.7	43.0	44.4	45.7	46.5	47.8	47.7	48.2
40°	14.1	14.1	14.2	14.3	14.3	14.3	14.3	14.4	14.5	14.5	14.6
42.5°	10.4	10.4	10.5	10.6	10.6	10.7	10.7	10.8	10.8	10.8	10.9
45°	7.8	7.9	7.9	8.0	8.0	8.1	8.1	8.2	8.2	8.3	8.3
47.5°	6.9	7.0	7.1	7.2	7.2	7.2	7.3	7.3	7.3	7.4	7.4
50°	6.0	6.0	6.1	6.1	6.2	6.2	6.3	6.3	6.4	6.4	6.5
52.5°	5.5	5.5	5.6	5.6	5.6	5.7	5.7	5.7	5.7	5.7	5.8
55°	4.8	4.8	4.9	4.9	5.0	5.0	5.0	5.1	5.1	5.2	5.2
57.5°	4.5	4.5	4.5	4.5	4.6	4.6	4.6	4.6	4.7	4.7	4.7
60°	4.8	4.8	4.8	4.8	4.8	4.9	4.9	4.9	4.9	4.9	4.9
62.5°	4.8	4.8	4.8	4.8	4.8	4.9	4.9	4.9	4.9	4.9	4.9
65°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.9	4.9	4.9
67.5°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
70°	4.7	4.7	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
72.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.6	3.6	3.6	3.6	3.6
75°	3.0	3.0	3.0	3.0	3.0	3.0	3.1	3.1	3.1	3.1	3.1
77.5°	2.6	2.6	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
80°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
82.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
85°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.5	0.5	0.5	0.5
87.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
90°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
92.5°	0.0	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.1
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
102.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
105°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
107.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
110°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: P979226
 CATALOG NUMBER: L820S15SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
115°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
117.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
120°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0
132.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
145°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
147.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
150°	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.0
152.5°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
155°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.2
157.5°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
160°	3.8	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
162.5°	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4
165°	4.9	4.9	4.9	4.9	4.9	4.8	4.9	4.9	4.9	4.8	4.8
167.5°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
170°	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3
172.5°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
175°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
177.5°	4.5	4.5	4.6	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5
180°	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9



TEST NUMBER: P979226
 CATALOG NUMBER: L820S15SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2
2.5°	9370.1	9373.2	9376.9	9393.0	9385.8	9380.4	9375.3	9370.4	9365.7	9361.6	9359.9
5°	8626.8	8638.4	8679.9	8666.3	8676.3	8671.5	8673.4	8682.1	8671.8	8666.5	8665.3
7.5°	6760.1	6714.9	6706.4	6698.8	6691.9	6690.5	6682.2	6674.7	6662.6	6739.1	6648.8
10°	4295.5	4309.9	4322.6	4333.1	4351.8	4329.0	4308.5	4294.7	4282.3	4273.8	4268.4
12.5°	2521.8	2524.2	2521.5	2538.2	2508.6	2507.9	2515.4	2522.2	2555.1	2522.3	2513.3
15°	1589.2	1590.6	1589.1	1588.5	1582.6	1584.7	1588.5	1590.0	1595.8	1587.7	1584.3
17.5°	1093.4	1093.4	1103.7	1089.5	1089.8	1093.9	1096.8	1112.1	1099.3	1100.1	1100.3
20°	827.7	827.5	831.5	825.7	827.2	829.6	831.3	838.9	833.0	833.2	832.8
22.5°	673.4	673.6	676.1	673.6	675.2	676.8	677.9	681.9	679.0	679.0	678.7
25°	581.0	581.1	582.5	581.0	581.8	582.4	583.0	585.0	583.6	583.7	583.7
27.5°	522.2	522.4	523.0	522.6	522.9	523.1	523.3	524.5	523.7	523.7	523.6
30°	442.8	442.9	444.3	443.4	443.6	443.7	443.6	445.5	443.0	442.3	441.6
32.5°	308.3	308.4	309.3	308.2	308.2	307.9	307.5	308.8	306.3	305.8	305.1
35°	165.1	165.5	166.1	165.8	165.9	165.9	165.6	166.8	164.5	163.5	162.2
37.5°	48.3	48.1	47.7	48.5	49.4	49.9	50.0	50.4	49.5	49.2	48.5
40°	14.6	14.6	14.6	14.7	14.7	14.7	14.8	14.8	14.9	14.9	14.8
42.5°	10.9	11.1	11.0	11.0	11.1	11.2	11.2	11.3	11.3	11.3	11.3
45°	8.3	8.4	8.4	8.5	8.5	8.6	8.6	8.6	8.7	8.7	8.7
47.5°	7.5	7.5	7.5	7.5	7.5	7.6	7.6	7.6	7.6	7.7	7.7
50°	6.6	6.6	6.7	6.7	6.7	6.8	6.8	6.8	6.9	6.9	6.9
52.5°	5.8	5.9	5.9	5.9	5.9	5.9	6.0	6.0	6.0	6.1	6.1
55°	5.2	5.3	5.3	5.3	5.3	5.4	5.4	5.4	5.4	5.5	5.5
57.5°	4.8	4.8	4.8	4.8	4.9	4.9	4.9	4.9	5.0	5.0	5.0
60°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
62.5°	4.9	4.9	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
65°	4.9	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.1
67.5°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
70°	4.8	4.9	4.8	4.9	4.9	4.9	4.9	4.9	4.9	5.0	5.0
72.5°	3.5	3.5	3.5	3.5	3.6	3.6	3.6	3.6	3.6	3.6	3.6
75°	3.1	3.1	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
77.5°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.6
80°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
82.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.0	2.0
85°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
87.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
90°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
92.5°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0
100°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
102.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0
105°	0.1	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
107.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
110°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: P979226
 CATALOG NUMBER: L820S15SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
115°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
117.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
120°	0.1	0.0	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.1	0.1
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
145°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
147.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
150°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
152.5°	1.6	1.6	1.6	1.6	1.6	1.5	1.6	1.6	1.6	1.6	1.6
155°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
157.5°	3.0	3.0	3.0	3.0	3.0	2.9	3.0	3.0	3.0	3.0	3.0
160°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
162.5°	4.4	4.4	4.4	4.4	4.4	4.3	4.4	4.3	4.3	4.3	4.3
165°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
167.5°	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1
170°	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3
172.5°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
175°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
177.5°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5
180°	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9



TEST NUMBER: P979226
 CATALOG NUMBER: L820S15SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2
2.5°	9358.6	9358.1	9358.5	9359.8	9350.8	9342.1	9333.9	9324.0	9317.9	9307.6	9298.3
5°	8704.6	8671.8	8652.3	8638.1	8628.4	8672.6	8627.4	8609.8	8596.8	8581.8	8564.3
7.5°	6655.1	6657.0	6654.2	6646.3	6692.9	6621.7	6602.5	6579.3	6551.6	6519.2	6481.7
10°	4267.1	4258.7	4243.2	4293.3	4222.5	4207.9	4190.4	4166.9	4137.3	4101.7	4060.0
12.5°	2499.9	2482.1	2459.9	2469.4	2444.6	2444.4	2439.5	2429.9	2415.6	2396.9	2379.3
15°	1578.5	1570.3	1563.4	1568.4	1559.0	1555.3	1549.7	1542.2	1532.8	1521.7	1515.3
17.5°	1099.3	1097.1	1109.9	1099.5	1095.8	1093.5	1090.5	1086.6	1081.9	1076.4	1074.3
20°	832.0	830.6	837.1	832.1	831.7	831.4	830.5	829.1	827.3	824.9	824.2
22.5°	678.2	677.9	681.2	678.2	678.5	678.3	677.9	677.1	676.0	674.7	674.9
25°	583.6	583.5	585.4	583.6	583.8	583.8	583.7	583.3	582.8	582.3	582.6
27.5°	523.5	523.5	525.0	524.2	524.5	524.6	524.6	524.4	524.1	523.8	524.2
30°	440.8	440.5	443.0	440.1	439.6	439.0	438.2	437.2	436.1	435.2	435.2
32.5°	304.3	304.2	307.0	303.4	302.4	301.2	299.7	298.0	296.1	294.7	294.2
35°	160.6	160.1	161.8	158.8	158.1	157.2	155.9	154.3	152.5	151.1	150.5
37.5°	47.6	47.8	48.9	47.2	46.7	46.0	45.1	43.8	42.4	41.4	41.0
40°	14.8	14.7	14.8	14.7	14.6	14.6	14.5	14.5	14.4	14.4	14.3
42.5°	11.4	11.3	11.4	11.3	11.2	11.2	11.1	11.0	11.0	10.9	10.8
45°	8.7	8.7	8.8	8.8	8.8	8.8	8.8	8.8	8.8	8.7	8.7
47.5°	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7
50°	6.9	6.9	6.9	6.8	6.8	6.8	6.7	6.7	6.7	6.7	6.6
52.5°	6.1	6.1	6.1	6.1	6.1	6.0	6.0	6.0	6.0	6.0	5.9
55°	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.4
57.5°	5.0	5.0	5.0	5.0	5.0	5.0	4.9	4.9	4.9	4.9	4.9
60°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
62.5°	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
65°	5.1	5.1	5.1	5.1	5.1	5.0	5.0	5.0	5.0	5.0	5.0
67.5°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
70°	5.0	5.0	5.0	5.0	5.0	5.0	4.9	4.9	4.9	4.9	4.9
72.5°	3.6	3.6	3.6	3.6	3.6	3.5	3.5	3.5	3.5	3.5	3.5
75°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
77.5°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
80°	2.5	2.5	2.5	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
82.5°	2.0	2.1	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
85°	0.5	0.5	0.5	0.5	0.5	0.4	0.4	0.4	0.3	0.3	0.3
87.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
90°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.1	0.1	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1
102.5°	0.0	0.0	0.0	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0
105°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
107.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
110°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: P979226
 CATALOG NUMBER: L820S15SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
115°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
117.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
120°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.2	0.2
145°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
147.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.6	0.6	0.6
150°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
152.5°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
155°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
157.5°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
160°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
162.5°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
165°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
167.5°	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1
170°	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3
172.5°	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1
175°	4.9	4.9	4.9	4.9	4.9	4.8	4.8	4.8	4.8	4.8	4.8
177.5°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5
180°	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9



TEST NUMBER: P979226
 CATALOG NUMBER: L820S15SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2
2.5°	9289.9	9280.8	9277.3	9274.1	9272.0	9271.0	9271.1	9273.1	9275.6	9278.4	9281.6
5°	8543.8	8519.9	8545.4	8522.4	8499.0	8475.4	8451.7	8445.0	8438.4	8431.9	8425.5
7.5°	6441.3	6503.0	6451.5	6399.6	6347.4	6295.0	6242.5	6229.3	6216.2	6203.1	6190.1
10°	4040.6	4083.8	4039.6	3995.2	3950.7	3906.1	3861.5	3846.7	3831.8	3817.1	3802.3
12.5°	2372.7	2398.5	2371.6	2344.5	2317.5	2290.4	2263.2	2254.1	2245.1	2236.0	2226.9
15°	1512.2	1523.0	1511.6	1500.2	1488.9	1477.4	1466.0	1461.7	1457.3	1453.0	1448.6
17.5°	1084.7	1078.6	1072.5	1066.4	1060.3	1054.2	1048.1	1046.1	1044.1	1042.2	1040.2
20°	829.9	826.4	822.9	819.3	815.8	812.2	808.7	807.9	807.1	806.2	805.4
22.5°	679.0	677.4	675.8	674.3	672.7	671.1	669.5	669.0	668.4	667.9	667.4
25°	585.7	584.6	583.6	582.5	581.5	580.4	579.4	579.1	578.8	578.6	578.3
27.5°	526.2	525.9	525.6	525.3	525.0	524.7	524.4	524.3	524.3	524.3	524.3
30°	439.8	437.8	435.9	433.9	432.0	430.1	428.1	427.8	427.5	427.2	426.9
32.5°	298.9	296.3	293.7	291.1	288.5	285.9	283.3	282.6	281.9	281.3	280.6
35°	154.4	151.8	149.2	146.5	143.9	141.2	138.6	137.7	136.9	136.1	135.2
37.5°	42.8	41.2	39.7	38.1	36.5	34.9	33.3	32.8	32.4	31.9	31.4
40°	14.4	14.2	14.1	14.0	13.9	13.8	13.7	13.7	13.6	13.6	13.6
42.5°	10.9	10.8	10.7	10.5	10.4	10.3	10.2	10.1	10.1	10.0	10.0
45°	8.6	8.6	8.5	8.4	8.4	8.3	8.2	8.2	8.2	8.1	8.1
47.5°	7.6	7.6	7.5	7.4	7.3	7.2	7.2	7.1	7.1	7.1	7.1
50°	6.6	6.6	6.6	6.5	6.5	6.4	6.4	6.4	6.4	6.3	6.3
52.5°	5.9	5.9	5.9	5.8	5.8	5.8	5.7	5.7	5.7	5.7	5.7
55°	5.4	5.4	5.3	5.3	5.3	5.2	5.2	5.2	5.1	5.1	5.0
57.5°	4.9	4.9	4.8	4.8	4.8	4.8	4.8	4.8	4.7	4.7	4.7
60°	4.9	4.9	4.9	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
62.5°	5.0	5.0	5.0	5.0	5.0	5.0	5.0	4.9	4.9	4.9	4.9
65°	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
67.5°	5.2	5.3	5.3	5.3	5.3	5.3	5.4	5.3	5.3	5.3	5.3
70°	4.9	4.8	4.8	4.8	4.7	4.7	4.7	4.7	4.7	4.7	4.7
72.5°	3.5	3.5	3.5	3.5	3.5	3.4	3.4	3.4	3.4	3.5	3.5
75°	3.0	2.9	2.9	2.9	2.9	2.9	2.9	2.8	2.8	2.8	2.8
77.5°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
80°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
82.5°	2.0	2.0	2.0	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
85°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.2
87.5°	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
107.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
110°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: P979226
 CATALOG NUMBER: L820S15SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
115°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
117.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1
132.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
145°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
147.5°	0.6	0.6	0.6	0.6	0.6	0.7	0.7	0.7	0.7	0.7	0.7
150°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
152.5°	1.5	1.5	1.5	1.5	1.6	1.6	1.6	1.6	1.6	1.6	1.6
155°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.3	2.3	2.3
157.5°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
160°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
162.5°	4.3	4.3	4.3	4.3	4.4	4.4	4.4	4.4	4.4	4.4	4.4
165°	4.8	4.8	4.8	4.8	4.9	4.9	4.9	4.9	4.9	4.9	4.9
167.5°	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1
170°	5.3	5.3	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
172.5°	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1
175°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.7
177.5°	4.5	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4
180°	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9



TEST NUMBER: P979226
 CATALOG NUMBER: L820S15SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2
2.5°	9284.0	9271.0	9262.9	9255.7	9249.4	9250.1	9231.5	9224.2	9218.3	9214.1	9204.0
5°	8348.3	8332.3	8311.8	8287.4	8259.6	8233.8	8226.2	8261.3	8159.7	8129.6	8099.2
7.5°	6177.1	6045.5	6027.7	6006.2	5977.9	5943.0	5901.7	5854.1	5871.7	5789.6	5759.9
10°	3787.6	3682.6	3642.4	3626.9	3606.2	3580.5	3549.8	3514.2	3477.0	3496.9	3422.8
12.5°	2217.9	2165.4	2141.5	2128.5	2117.7	2104.3	2088.4	2070.0	2049.1	2046.8	2012.6
15°	1444.3	1419.8	1408.3	1399.3	1393.7	1387.2	1379.6	1371.1	1361.6	1357.1	1341.3
17.5°	1038.2	1036.2	1018.3	1012.3	1009.0	1005.0	1000.5	995.5	989.9	985.7	987.8
20°	804.6	803.8	794.2	790.8	788.8	786.5	783.8	780.7	777.2	773.9	774.8
22.5°	666.8	666.3	660.5	658.4	656.9	655.3	653.5	651.5	649.4	647.1	647.4
25°	578.1	577.8	574.3	573.0	572.2	571.3	570.3	569.1	567.8	566.3	566.5
27.5°	524.2	524.2	521.5	520.7	519.8	518.9	518.0	517.0	516.0	514.9	514.9
30°	426.6	426.3	418.8	416.3	414.7	413.5	412.1	410.5	408.7	406.8	407.6
32.5°	279.9	279.3	271.0	268.1	266.2	264.9	263.3	261.5	259.3	256.9	257.4
35°	134.4	133.5	126.1	123.2	121.2	119.8	118.1	116.1	113.9	111.5	111.4
37.5°	30.9	30.5	27.7	26.6	25.9	25.6	25.1	24.5	23.8	23.0	22.9
40°	13.5	13.5	13.3	13.3	13.2	13.1	13.1	13.0	12.9	12.9	12.8
42.5°	9.9	9.8	9.6	9.5	9.4	9.4	9.3	9.3	9.2	9.2	9.1
45°	8.0	8.0	7.8	7.8	7.7	7.7	7.6	7.6	7.6	7.5	7.5
47.5°	7.0	7.0	6.9	6.9	6.8	6.8	6.8	6.7	6.7	6.6	6.6
50°	6.3	6.3	6.2	6.2	6.1	6.1	6.1	6.0	6.0	5.9	5.9
52.5°	5.6	5.6	5.6	5.6	5.5	5.5	5.5	5.4	5.4	5.3	5.3
55°	5.0	4.9	4.8	4.8	4.7	4.7	4.7	4.7	4.8	4.8	4.8
57.5°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
60°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
62.5°	4.9	4.9	4.9	4.9	4.8	4.8	4.8	4.8	4.8	4.8	4.8
65°	5.0	5.0	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	5.0
67.5°	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3
70°	4.7	4.7	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.5	4.5
72.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
75°	2.8	2.8	2.8	2.8	2.8	2.7	2.7	2.7	2.7	2.7	2.7
77.5°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
80°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
82.5°	1.9	1.9	1.8	1.8	1.7	1.7	1.7	1.7	1.7	1.7	1.6
85°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
105°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
107.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
110°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: P979226
 CATALOG NUMBER: L820S15SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
115°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
117.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
120°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0
132.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
145°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
147.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
150°	1.0	1.0	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
152.5°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.7	1.7	1.7
155°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.4	2.4
157.5°	3.0	3.0	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
160°	3.7	3.7	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
162.5°	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.5	4.5	4.5	4.5
165°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
167.5°	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.2	5.2
170°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
172.5°	5.1	5.1	5.1	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
175°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
177.5°	4.4	4.4	4.4	4.4	4.4	4.3	4.3	4.3	4.3	4.3	4.3
180°	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9



TEST NUMBER: P979226
 CATALOG NUMBER: L820S15SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2
2.5°	9195.5	9188.0	9181.5	9176.7	9163.9	9154.7	9146.6	9139.7	9133.9	9143.5	9113.0
5°	8068.8	8104.4	8021.3	7998.3	7976.8	7958.7	7923.5	7893.5	7866.5	7846.7	7863.1
7.5°	5725.6	5687.0	5644.5	5695.9	5554.7	5530.4	5502.7	5477.9	5450.9	5427.3	5402.2
10°	3405.4	3382.9	3355.7	3332.8	3300.1	3270.5	3244.7	3233.8	3227.4	3209.0	3194.0
12.5°	2006.1	1997.1	1985.7	1971.8	1978.2	1945.5	1930.0	1915.5	1911.6	1926.2	1903.1
15°	1334.6	1329.1	1322.5	1314.7	1311.0	1300.1	1292.7	1284.6	1279.6	1281.2	1276.4
17.5°	972.1	969.0	965.3	960.9	956.5	962.0	948.1	943.2	937.8	934.3	940.5
20°	765.6	763.6	761.5	759.0	756.1	758.5	750.9	747.7	744.2	741.0	743.0
22.5°	642.5	641.0	639.7	638.2	636.6	637.3	633.1	631.1	629.1	627.2	627.9
25°	563.5	562.2	561.3	560.1	558.9	558.9	556.4	555.0	553.5	551.9	552.4
27.5°	511.8	510.4	509.3	508.3	507.3	507.4	503.9	502.2	500.6	499.2	499.1
30°	402.4	400.2	398.7	397.0	395.0	395.1	390.1	387.4	384.7	381.9	381.0
32.5°	251.8	249.1	247.8	246.2	244.5	244.6	239.9	237.2	234.2	231.0	229.3
35°	107.0	104.7	103.9	102.8	101.4	101.2	98.2	96.4	94.3	92.0	90.5
37.5°	21.8	21.2	21.1	20.8	20.3	20.0	19.7	19.4	18.9	18.2	17.6
40°	12.7	12.6	12.6	12.6	12.6	12.6	12.5	12.5	12.4	12.4	12.4
42.5°	9.0	9.0	8.9	8.9	8.9	8.9	8.9	8.8	8.8	8.8	8.7
45°	7.5	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4
47.5°	6.6	6.5	6.5	6.5	6.4	6.4	6.4	6.4	6.3	6.3	6.3
50°	5.9	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8
52.5°	5.3	5.2	5.2	5.2	5.1	5.1	5.1	5.1	5.1	5.0	5.0
55°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.7	4.7	4.7	4.7
57.5°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
60°	4.9	5.0	5.0	5.0	4.9	4.9	4.9	4.9	4.9	4.8	4.8
62.5°	4.8	4.8	4.8	4.8	4.8	4.8	4.9	4.9	4.9	4.9	4.9
65°	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.1	5.1	5.1
67.5°	5.3	5.3	5.2	5.2	5.2	5.2	5.3	5.2	5.2	5.2	5.1
70°	4.5	4.5	4.5	4.4	4.4	4.4	4.4	4.4	4.4	4.3	4.3
72.5°	3.5	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
75°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
77.5°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
80°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
82.5°	1.7	1.5	1.5	1.5	1.5	1.5	1.5	1.4	1.4	1.3	1.3
85°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1
100°	0.0	0.0	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0
102.5°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.1	0.1	0.1	0.1
105°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
107.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
110°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: P979226
 CATALOG NUMBER: L820S15SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
115°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
117.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
120°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
122.5°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0
132.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
145°	0.4	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
147.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.8	0.7	0.8	0.8	0.8
150°	1.1	1.1	1.1	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2
152.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.8	1.8	1.8
155°	2.4	2.4	2.4	2.4	2.4	2.4	2.5	2.4	2.5	2.5	2.5
157.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
160°	3.8	3.8	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9
162.5°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.6	4.6
165°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
167.5°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
170°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
172.5°	5.0	5.0	5.0	5.0	5.0	5.0	5.0	4.9	4.9	4.9	4.9
175°	4.7	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6
177.5°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.2	4.2	4.2	4.2
180°	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9



TEST NUMBER: P979226
 CATALOG NUMBER: L820S15SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2
2.5°	9104.9	9098.4	9093.4	9098.0	9079.4	9072.9	9067.7	9063.7	9060.9	9067.1	9053.3
5°	7792.5	7765.5	7742.0	7722.0	7768.1	7694.4	7684.4	7677.0	7666.4	7719.6	7616.7
7.5°	5375.8	5389.8	5326.9	5309.2	5288.8	5266.0	5327.4	5222.1	5199.5	5176.7	5159.9
10°	3174.8	3151.7	3160.2	3105.1	3094.0	3084.7	3071.5	3122.9	3052.3	3038.5	3021.7
12.5°	1895.9	1886.0	1873.6	1893.4	1850.6	1843.6	1840.4	1845.1	1835.4	1832.1	1826.8
15°	1273.0	1268.1	1261.7	1263.4	1247.3	1238.9	1234.3	1230.3	1243.9	1225.4	1221.7
17.5°	928.8	925.4	921.5	919.2	913.1	908.5	903.9	901.4	905.1	897.3	894.8
20°	736.7	734.4	731.9	729.3	727.2	724.9	722.5	721.0	721.9	718.2	716.6
22.5°	624.4	623.0	621.5	620.1	621.8	617.6	616.4	615.3	615.3	613.4	612.4
25°	551.1	550.6	550.0	549.4	550.4	548.2	547.5	546.8	546.3	545.5	544.8
27.5°	496.5	495.2	494.1	493.3	494.5	491.1	490.2	489.4	488.6	487.3	486.2
30°	377.7	375.7	373.7	371.7	372.6	367.1	364.7	362.3	360.7	364.8	358.0
32.5°	226.6	224.8	222.9	220.9	221.3	216.7	214.6	212.5	210.9	214.9	209.1
35°	89.4	88.5	87.3	86.0	85.9	83.1	81.5	79.8	78.5	81.7	78.2
37.5°	17.9	17.9	17.7	17.3	16.8	16.6	16.3	15.9	15.7	16.3	16.4
40°	12.3	12.2	12.2	12.1	12.1	12.0	12.0	11.9	11.9	12.0	11.9
42.5°	8.8	8.7	8.6	8.6	8.5	8.5	8.5	8.4	8.4	8.4	8.4
45°	7.4	7.3	7.3	7.3	7.3	7.3	7.2	7.2	7.2	7.2	7.2
47.5°	6.3	6.3	6.3	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4
50°	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8
52.5°	5.0	5.0	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1
55°	4.7	4.7	4.7	4.7	4.7	4.8	4.8	4.8	4.8	4.8	4.8
57.5°	4.7	4.7	4.7	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
60°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.9	4.9
62.5°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
65°	5.1	5.1	5.1	5.2	5.2	5.1	5.2	5.2	5.2	5.2	5.2
67.5°	5.2	5.1	5.1	5.1	5.1	5.1	5.1	5.0	5.0	5.0	5.0
70°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.2	4.2	4.2	4.2
72.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.3	3.3
75°	2.7	2.7	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
77.5°	2.6	2.6	2.6	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
80°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.3
82.5°	1.3	1.3	1.2	1.2	1.2	1.3	1.2	1.2	1.1	1.1	1.0
85°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.0	0.0
97.5°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0
100°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0
102.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
105°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
107.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
110°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: P979226
 CATALOG NUMBER: L820S15SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
115°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
117.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
120°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
122.5°	0.0	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1
132.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.4	0.4	0.4	0.4
145°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.6	0.6	0.6
147.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
150°	1.2	1.2	1.2	1.2	1.2	1.3	1.2	1.3	1.3	1.3	1.3
152.5°	1.8	1.8	1.8	1.8	1.9	1.9	1.9	1.9	1.9	1.9	1.9
155°	2.5	2.5	2.5	2.5	2.6	2.6	2.6	2.6	2.6	2.6	2.6
157.5°	3.2	3.2	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
160°	3.9	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0
162.5°	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6
165°	4.9	5.0	4.9	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
167.5°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
170°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.1	5.1
172.5°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
175°	4.6	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.4
177.5°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.1	4.1	4.1	4.1
180°	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9



TEST NUMBER: P979226
 CATALOG NUMBER: L820S15SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2
2.5°	9048.3	9044.0	9040.4	9037.5	9035.4	9040.8	9053.7	9026.2	9025.4	9025.9	9027.7
5°	7597.4	7582.6	7572.1	7608.8	7554.5	7548.8	7545.8	7545.5	7544.6	7569.9	7532.5
7.5°	5136.1	5126.8	5117.5	5108.4	5099.8	5174.6	5092.3	5089.1	5086.3	5084.3	5094.7
10°	3012.2	2993.9	2985.6	2984.7	2981.4	2982.8	2977.2	2975.9	2972.9	2968.5	2963.0
12.5°	1819.6	1831.8	1808.4	1803.4	1802.7	1800.7	1817.2	1799.7	1798.6	1796.6	1794.1
15°	1217.1	1215.5	1207.6	1202.6	1199.2	1197.6	1199.9	1197.0	1197.5	1197.6	1197.4
17.5°	891.9	888.7	894.9	883.6	880.8	880.8	880.7	889.8	882.7	883.3	883.7
20°	714.9	712.9	715.3	710.0	708.4	707.8	708.1	712.6	709.8	710.5	711.1
22.5°	611.3	610.2	611.3	608.9	608.2	607.8	608.1	610.6	608.6	608.8	609.1
25°	544.2	543.5	543.9	542.7	542.4	542.2	542.3	543.5	542.8	543.1	543.3
27.5°	485.4	485.0	486.0	483.5	482.8	482.3	481.7	482.8	480.3	479.9	479.9
30°	356.8	355.7	356.0	353.6	352.8	352.0	351.6	353.3	351.1	350.9	350.9
32.5°	208.2	207.4	207.7	206.0	205.2	204.5	203.9	205.1	203.6	203.6	203.7
35°	77.8	77.3	77.0	76.2	75.6	74.8	74.2	75.1	74.5	74.8	75.0
37.5°	16.5	16.4	16.1	16.0	15.9	15.8	15.7	16.0	16.3	16.5	16.5
40°	11.9	11.9	11.9	11.8	11.8	11.8	11.8	11.8	11.7	11.7	11.7
42.5°	8.4	8.4	8.4	8.4	8.4	8.3	8.3	8.3	8.4	8.4	8.4
45°	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2
47.5°	6.4	6.5	6.5	6.5	6.5	6.5	6.6	6.6	6.6	6.5	6.5
50°	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8
52.5°	5.1	5.1	5.1	5.2	5.1	5.1	5.2	5.2	5.2	5.2	5.2
55°	4.8	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.8	4.8
57.5°	4.8	4.9	4.9	4.9	4.9	4.9	5.0	5.0	5.0	4.9	4.9
60°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.8	4.8
62.5°	4.9	4.9	4.9	4.9	5.0	5.0	5.0	5.0	5.0	5.0	5.0
65°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
67.5°	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
70°	4.2	4.2	4.1	4.1	4.0	4.0	3.9	3.8	3.9	3.8	3.8
72.5°	3.2	3.2	3.2	3.1	3.1	3.1	3.1	3.0	3.1	3.1	3.1
75°	2.8	2.8	2.8	2.8	2.8	2.7	2.7	2.7	2.7	2.8	2.8
77.5°	2.6	2.6	2.5	2.5	2.4	2.4	2.3	2.3	2.2	2.1	1.9
80°	2.2	2.2	2.1	2.0	2.0	1.9	1.8	1.8	1.7	1.6	1.5
82.5°	0.9	0.8	0.8	0.7	0.7	0.6	0.6	0.6	0.6	0.6	0.6
85°	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.1
102.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.1
105°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
107.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
110°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: P979226
 CATALOG NUMBER: L820S15SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
115°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.1	0.1
117.5°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
132.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.3	0.3
142.5°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
145°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
147.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
150°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.4
152.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
155°	2.6	2.6	2.6	2.6	2.6	2.7	2.7	2.7	2.7	2.7	2.7
157.5°	3.3	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
160°	4.0	4.0	4.0	4.0	4.1	4.1	4.1	4.1	4.1	4.1	4.1
162.5°	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6
165°	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
167.5°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
170°	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1
172.5°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
175°	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.3
177.5°	4.1	4.1	4.1	4.1	4.1	4.1	4.0	4.0	4.0	4.0	4.0
180°	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9



TEST NUMBER: P979226
 CATALOG NUMBER: L820S15SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2
2.5°	9030.9	9035.3	9040.9	9054.2	9070.8	9052.2	9048.3	9045.3	9043.3	9042.4	9042.4
5°	7530.9	7532.3	7536.6	7543.8	7553.9	7566.9	7618.1	7673.4	7598.0	7614.8	7626.4
7.5°	5166.2	5078.9	5078.9	5081.0	5085.3	5091.8	5100.6	5160.9	5123.6	5138.5	5155.7
10°	2980.7	2955.6	2958.5	2959.9	2960.9	2961.8	2962.9	2980.0	3023.9	2982.2	2991.0
12.5°	1791.1	1815.8	1792.1	1793.4	1794.4	1795.2	1795.9	1797.6	1819.2	1804.1	1808.4
15°	1196.9	1206.3	1198.1	1199.5	1201.1	1202.6	1204.1	1205.7	1216.4	1211.7	1215.2
17.5°	883.9	887.8	884.9	885.6	886.7	887.9	889.1	890.4	895.8	903.1	897.0
20°	711.6	713.4	712.9	713.7	714.5	715.2	715.9	716.6	719.2	723.3	719.3
22.5°	609.3	610.2	613.5	610.9	611.1	611.3	611.6	611.9	613.3	615.9	613.9
25°	543.5	543.8	545.7	543.9	544.0	544.0	544.1	544.2	544.8	546.3	545.0
27.5°	480.2	480.8	484.7	481.6	482.0	481.7	481.8	482.2	483.6	486.6	484.0
30°	351.1	351.4	356.4	352.3	352.9	353.0	353.4	353.9	355.6	360.1	356.9
32.5°	204.0	204.3	208.9	205.4	206.1	206.6	207.2	208.1	209.9	214.6	211.7
35°	75.1	75.2	78.5	75.9	76.1	76.4	76.8	77.3	78.3	82.0	79.9
37.5°	16.4	16.1	16.1	15.9	15.9	16.2	16.4	16.4	16.4	16.8	16.6
40°	11.7	11.7	11.8	11.7	11.8	11.8	11.7	11.7	11.8	11.8	11.7
42.5°	8.4	8.4	8.4	8.4	8.3	8.3	8.3	8.3	8.3	8.3	8.3
45°	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1
47.5°	6.5	6.5	6.5	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.3
50°	5.8	5.8	5.9	5.9	5.9	5.8	5.8	5.8	5.7	5.7	5.7
52.5°	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1
55°	4.8	4.8	4.8	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
57.5°	4.9	4.9	4.9	4.9	4.9	4.9	4.8	4.8	4.8	4.7	4.7
60°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
62.5°	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
65°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
67.5°	4.9	4.9	4.9	4.9	4.9	4.8	4.9	4.9	4.9	5.0	5.0
70°	3.8	3.8	3.8	3.7	3.7	3.7	3.8	3.9	3.9	4.0	4.0
72.5°	3.1	3.1	3.1	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.1
75°	2.8	2.8	2.8	2.8	2.8	2.9	2.8	2.8	2.8	2.8	2.8
77.5°	1.8	1.7	1.5	1.4	1.3	1.2	1.3	1.4	1.5	1.6	1.7
80°	1.5	1.5	1.4	1.4	1.4	1.4	1.5	1.5	1.6	1.7	1.8
82.5°	0.6	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.8	0.8	0.8
85°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
102.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
105°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
107.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
110°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: P979226
 CATALOG NUMBER: L820S15SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
115°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
117.5°	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
132.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
140°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
142.5°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
145°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
147.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
150°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
152.5°	1.9	1.9	1.9	1.9	2.0	2.0	2.0	2.0	2.0	2.0	2.0
155°	2.7	2.7	2.7	2.6	2.7	2.7	2.7	2.6	2.6	2.6	2.6
157.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.3
160°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1
162.5°	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6
165°	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
167.5°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
170°	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1
172.5°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
175°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.4	4.4
177.5°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0
180°	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9



TEST NUMBER: P979226
 CATALOG NUMBER: L820S15SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2	9515.2
2.5°	9043.4	9045.4	9048.2	9051.8	9056.3	9061.5	9067.5	9074.2	9081.5	9089.4	9098.0
5°	7628.3	7633.6	7642.2	7654.0	7668.9	7686.8	7707.7	7731.5	7758.0	7787.2	7819.0
7.5°	5175.5	5182.6	5191.4	5203.3	5218.6	5237.2	5259.2	5284.6	5313.6	5346.2	5382.3
10°	3000.6	3010.1	3015.1	3021.8	3030.3	3040.7	3053.3	3068.2	3085.4	3105.2	3127.6
12.5°	1813.1	1818.4	1820.9	1822.9	1825.7	1829.5	1834.4	1840.4	1847.6	1856.0	1865.8
15°	1218.9	1222.9	1225.8	1227.2	1229.2	1231.8	1234.9	1238.8	1243.3	1248.4	1254.3
17.5°	899.6	902.4	905.0	905.9	907.0	908.4	910.1	912.1	914.5	917.3	920.4
20°	720.3	721.4	722.4	722.8	723.2	723.9	724.8	725.9	727.3	728.9	730.7
22.5°	614.7	615.6	616.6	616.9	617.1	617.5	618.0	618.6	619.4	620.3	621.3
25°	545.4	545.8	546.3	546.4	546.6	546.9	547.2	547.7	548.2	548.8	549.6
27.5°	485.0	486.3	487.8	488.3	488.7	489.3	490.2	491.3	492.6	494.1	495.7
30°	358.3	360.0	361.9	363.1	363.9	365.0	366.4	367.9	369.8	371.8	374.2
32.5°	213.3	215.2	217.2	218.6	219.7	221.0	222.6	224.5	226.6	228.9	231.5
35°	81.1	82.3	83.6	84.6	85.4	86.3	87.4	88.7	90.2	91.9	93.7
37.5°	16.6	16.6	16.6	16.7	16.9	17.1	17.2	17.3	17.5	17.6	17.8
40°	11.7	11.8	11.8	11.8	11.8	11.8	11.9	11.9	12.0	12.0	12.1
42.5°	8.3	8.2	8.2	8.2	8.2	8.3	8.3	8.3	8.3	8.4	8.4
45°	7.1	7.1	7.1	7.1	7.0	7.0	7.0	7.0	7.0	7.0	7.0
47.5°	6.3	6.3	6.3	6.3	6.3	6.3	6.2	6.2	6.2	6.2	6.2
50°	5.6	5.6	5.6	5.6	5.6	5.6	5.5	5.5	5.5	5.5	5.5
52.5°	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.0	5.0
55°	4.7	4.7	4.7	4.7	4.7	4.6	4.6	4.6	4.6	4.6	4.6
57.5°	4.7	4.6	4.6	4.6	4.6	4.6	4.6	4.5	4.5	4.5	4.5
60°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
62.5°	5.0	5.0	5.0	5.0	5.0	5.0	5.0	4.9	4.9	4.9	4.9
65°	5.2	5.2	5.2	5.2	5.2	5.1	5.1	5.1	5.1	5.0	5.0
67.5°	5.0	5.1	5.1	5.2	5.2	5.2	5.2	5.1	5.1	5.1	5.1
70°	4.1	4.1	4.1	4.2	4.2	4.2	4.2	4.2	4.2	4.3	4.3
72.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.2	3.2	3.3	3.3	3.3
75°	2.7	2.7	2.7	2.7	2.7	2.7	2.8	2.8	2.8	2.9	2.9
77.5°	1.8	1.9	2.0	2.2	2.3	2.3	2.4	2.5	2.5	2.6	2.7
80°	1.9	1.9	2.0	2.1	2.1	2.2	2.2	2.3	2.3	2.4	2.5
82.5°	0.8	0.9	0.9	0.9	1.0	1.0	1.1	1.2	1.3	1.4	1.4
85°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.1	0.1	0.1	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1
102.5°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
107.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
110°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0



TEST NUMBER: P979226
 CATALOG NUMBER: L820S15SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0
132.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
140°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
142.5°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
145°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
147.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
150°	1.4	1.4	1.4	1.4	1.3	1.3	1.3	1.3	1.3	1.3	1.3
152.5°	2.0	2.0	2.0	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
155°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
157.5°	3.4	3.4	3.4	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
160°	4.1	4.1	4.1	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0
162.5°	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6
165°	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
167.5°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
170°	5.1	5.1	5.1	5.1	5.1	5.2	5.2	5.2	5.2	5.2	5.2
172.5°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	5.0	5.0	5.0
175°	4.4	4.4	4.4	4.4	4.4	4.4	4.5	4.5	4.5	4.5	4.5
177.5°	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	4.0	4.0
180°	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9



TEST NUMBER: P979226
 CATALOG NUMBER: L820S15SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	9515.2	9515.2
2.5°	9107.1	9143.7
5°	7853.3	7890.0
7.5°	5422.1	5471.3
10°	3152.9	3179.1
12.5°	1877.0	1893.6
15°	1260.9	1267.2
17.5°	923.9	930.2
20°	732.9	736.9
22.5°	622.5	626.2
25°	550.4	550.5
27.5°	497.5	499.2
30°	376.7	380.8
32.5°	234.4	237.3
35°	95.8	99.2
37.5°	18.0	18.8
40°	12.2	12.3
42.5°	8.5	8.6
45°	7.0	7.0
47.5°	6.2	6.2
50°	5.5	5.5
52.5°	5.0	5.0
55°	4.6	4.6
57.5°	4.5	4.5
60°	4.8	4.8
62.5°	4.9	4.9
65°	5.0	5.0
67.5°	5.1	5.2
70°	4.4	4.4
72.5°	3.4	3.4
75°	2.9	3.0
77.5°	2.7	2.8
80°	2.5	2.6
82.5°	1.5	1.7
85°	0.2	0.2
87.5°	0.1	0.1
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.1	0.1
97.5°	0.0	0.0
100°	0.1	0.1
102.5°	0.0	0.1
105°	0.1	0.1
107.5°	0.1	0.1
110°	0.0	0.1



TEST NUMBER: P979226
CATALOG NUMBER: L820S15SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.1
115°	0.0	0.1
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.1
132.5°	0.1	0.1
135°	0.1	0.1
137.5°	0.2	0.2
140°	0.3	0.3
142.5°	0.4	0.4
145°	0.6	0.6
147.5°	0.9	0.9
150°	1.3	1.3
152.5°	1.9	1.9
155°	2.6	2.6
157.5°	3.3	3.3
160°	4.0	4.0
162.5°	4.6	4.6
165°	5.0	5.0
167.5°	5.2	5.2
170°	5.2	5.3
172.5°	5.0	5.1
175°	4.6	4.7
177.5°	4.1	4.2
180°	3.9	3.9

(END OF REPORT)