

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P671780

Luminaire Tested: **CCP-SA-1C-722-U-SLR**

Issue Date: 04/16/2023



Test Information

Test Method: LM-79-08
Report Number: P671780
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/16/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCP-SA-1C-722-U-SLR
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @615mA w/ SLR distribution lens
Light Source: (16) 2200K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2763.8 lumens
Efficiency: N/A
Efficacy: 86.4 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G1


Input Watts (W): 32
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



REPORT NUMBER: P671780
 CATALOG NUMBER: CCP-SA-1C-722-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 3.9 fc
 Type IV - Short - N/A

REPORT NUMBER: P671780
CATALOG NUMBER: CCP-SA-1C-722-U-SLR

Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P671780

CATALOG NUMBER: CCP-SA-1C-722-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	568.7	0.0	568.7
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	2195.1	0.0	2195.1
	% Fixture	79.4	0.0	79.4
Total	Lumens	2763.8	0.0	2763.8
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.6	2.5
10°-20°	144.8	5.2
20°-30°	211.8	7.7
30°-40°	298.4	10.8
40°-50°	410.1	14.8
50°-60°	559.0	20.2
60°-70°	611.8	22.1
70°-80°	353.3	12.8
80°-90°	105.9	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2763.8	100.0
0°-180°	2763.8	100.0



REPORT NUMBER: P671780


CATALOG NUMBER: CCP-SA-1C-722-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	283.8	10.3			
FM (30°-60°)	1008.6	36.5			
FH (60°-80°)	812.7	29.4			G1/1800
FVH (80°-90°)	90.0	3.3			G1/100
BL (0°-30°)	141.4	5.1	B1/500		
BM (30°-60°)	258.9	9.4	B1/1000		
BH (60°-80°)	152.4	5.5	B1/500		G1/500
BVH (80°-90°)	15.9	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type IV Short





REPORT NUMBER: P671780

CATALOG NUMBER: CCP-SA-1C-722-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6
2.5°	910.8	905.9	902.2	898.5	893.6	889.9	885.0	880.1	874.0	869.1	863.0
5°	858.1	843.4	828.6	820.1	810.3	801.7	791.9	780.8	769.8	757.5	746.5
7.5°	800.5	782.1	763.7	749.0	733.0	718.3	702.4	688.9	675.4	661.9	648.5
10°	746.5	729.4	712.2	693.8	674.2	655.8	636.2	617.8	599.4	581.0	562.6
12.5°	711.0	690.1	670.5	649.7	630.1	609.2	588.4	571.2	554.1	535.7	518.5
15°	695.0	675.4	657.0	636.2	615.4	594.5	573.7	554.1	535.7	516.1	496.5
17.5°	733.0	704.8	676.6	649.7	622.7	595.7	568.8	544.3	519.7	495.2	470.7
20°	782.1	746.5	712.2	679.1	644.8	611.7	577.4	543.0	508.7	474.4	440.1
22.5°	844.6	804.1	764.9	722.0	677.9	635.0	590.8	547.9	505.0	460.9	418.0
25°	956.1	908.3	860.5	799.2	736.7	675.4	612.9	556.5	501.4	445.0	388.6
27.5°	1051.7	986.8	923.0	849.5	775.9	702.4	628.8	563.9	500.1	435.2	370.2
30°	1108.1	1044.4	980.6	891.2	802.9	713.4	623.9	551.6	480.5	408.2	335.9
32.5°	1159.6	1088.5	1017.4	919.4	820.1	722.0	622.7	543.0	464.6	384.9	305.2
35°	1230.7	1152.3	1075.0	961.0	847.0	733.0	619.0	536.9	453.5	371.4	288.1
37.5°	1306.7	1209.9	1114.3	988.0	861.7	735.5	609.2	528.3	447.4	366.5	285.6
40°	1390.1	1272.4	1155.9	1016.2	877.7	737.9	598.2	517.3	436.4	354.3	273.4
42.5°	1444.0	1316.5	1189.0	1038.3	888.7	737.9	587.2	507.5	427.8	346.9	267.2
45°	1474.6	1350.8	1228.3	1065.2	902.2	739.2	576.1	497.7	419.2	339.5	261.1
47.5°	1488.1	1372.9	1257.7	1086.1	915.7	744.1	572.5	492.8	411.9	332.2	251.3
50°	1523.7	1421.9	1320.2	1136.3	953.7	769.8	585.9	500.1	415.5	329.7	243.9
52.5°	1544.5	1457.5	1370.4	1181.7	992.9	804.1	615.4	519.7	424.1	328.5	232.9
55°	1620.5	1537.2	1453.8	1252.8	1050.5	849.5	647.2	541.8	436.4	329.7	224.3
57.5°	1717.4	1629.1	1542.1	1325.1	1108.1	891.2	674.2	561.4	447.4	334.6	220.6
60°	1784.8	1699.0	1614.4	1383.9	1152.3	921.8	690.1	572.5	454.8	335.9	218.2
62.5°	1792.1	1681.8	1572.7	1348.4	1124.1	898.5	674.2	560.2	446.2	331.0	217.0
65°	1745.5	1616.8	1488.1	1273.6	1059.1	844.6	630.1	525.9	421.7	316.3	212.1
67.5°	1652.4	1501.6	1350.8	1154.7	958.6	762.5	566.3	476.8	388.6	299.1	209.6
70°	1435.4	1303.0	1171.9	1001.5	832.3	661.9	491.5	418.0	345.7	272.1	198.6
72.5°	1205.0	1081.2	958.6	820.1	682.8	544.3	405.7	350.6	295.4	239.0	183.9
75°	923.0	829.9	737.9	635.0	532.0	427.8	324.8	284.4	243.9	203.5	163.0
77.5°	648.5	598.2	549.2	471.9	394.7	317.5	240.3	213.3	186.3	159.4	132.4
80°	440.1	411.9	384.9	329.7	274.6	218.2	163.0	145.9	127.5	110.3	91.9
82.5°	273.4	272.1	269.7	231.7	193.7	155.7	117.7	103.0	89.5	74.8	60.1
85°	125.0	145.9	165.5	144.6	123.8	103.0	82.1	72.3	62.5	51.5	41.7
87.5°	39.2	47.8	55.2	52.7	49.0	46.6	42.9	36.8	30.6	24.5	18.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671780
 CATALOG NUMBER: CCP-SA-1C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671780
 CATALOG NUMBER: CCP-SA-1C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6
2.5°	858.1	854.4	849.5	844.6	838.4	833.5	827.4	821.3	820.1	817.6	816.4
5°	739.2	731.8	723.2	715.9	708.5	699.9	692.6	684.0	677.9	670.5	664.4
7.5°	635.0	622.7	609.2	595.7	583.5	571.2	557.7	545.5	539.4	533.2	527.1
10°	551.6	539.4	528.3	516.1	507.5	500.1	491.5	483.0	475.6	468.3	460.9
12.5°	509.9	501.4	492.8	484.2	474.4	465.8	456.0	446.2	437.6	430.3	421.7
15°	484.2	471.9	458.5	446.2	432.7	420.5	407.0	393.5	383.7	375.1	365.3
17.5°	453.5	435.2	418.0	399.6	384.9	370.2	354.3	339.5	328.5	316.3	305.2
20°	419.2	398.4	376.3	355.5	338.3	322.4	305.2	288.1	275.8	262.3	250.1
22.5°	389.8	362.8	334.6	306.5	288.1	269.7	250.1	231.7	220.6	208.4	197.4
25°	357.9	328.5	297.9	267.2	248.8	229.2	210.8	191.2	182.6	175.3	166.7
27.5°	340.8	311.4	280.7	251.3	234.1	215.7	198.6	180.2	174.1	166.7	160.6
30°	306.5	278.3	248.8	219.4	207.2	196.1	183.9	171.6	169.2	167.9	165.5
32.5°	275.8	246.4	217.0	187.5	176.5	165.5	154.5	143.4	142.2	139.7	138.5
35°	259.9	231.7	202.3	174.1	164.3	153.2	143.4	132.4	129.9	126.3	123.8
37.5°	256.2	226.8	196.1	166.7	156.9	147.1	136.1	126.3	123.8	121.4	118.9
40°	246.4	218.2	191.2	163.0	153.2	143.4	132.4	122.6	120.1	117.7	115.2
42.5°	239.0	212.1	183.9	155.7	147.1	138.5	128.7	120.1	117.7	115.2	111.5
45°	232.9	204.7	175.3	147.1	141.0	134.8	127.5	121.4	118.9	115.2	112.8
47.5°	223.1	196.1	167.9	139.7	133.6	128.7	122.6	116.5	114.0	111.5	109.1
50°	215.7	187.5	159.4	131.2	126.3	121.4	116.5	111.5	111.5	112.8	112.8
52.5°	205.9	179.0	152.0	125.0	120.1	115.2	110.3	105.4	106.6	107.9	109.1
55°	197.4	171.6	144.6	117.7	112.8	107.9	101.7	96.8	98.1	99.3	100.5
57.5°	193.7	166.7	139.7	112.8	107.9	101.7	96.8	90.7	90.7	90.7	90.7
60°	191.2	163.0	136.1	107.9	101.7	96.8	90.7	84.6	83.4	83.4	82.1
62.5°	190.0	161.8	134.8	106.6	99.3	93.2	85.8	78.5	77.2	76.0	74.8
65°	185.1	159.4	132.4	105.4	96.8	89.5	80.9	72.3	71.1	71.1	69.9
67.5°	183.9	156.9	131.2	104.2	95.6	85.8	77.2	67.4	66.2	65.0	63.7
70°	174.1	150.8	126.3	101.7	91.9	83.4	73.5	63.7	62.5	60.1	58.8
72.5°	161.8	141.0	118.9	96.8	87.0	77.2	67.4	57.6	56.4	55.2	52.7
75°	143.4	123.8	104.2	84.6	76.0	68.6	60.1	51.5	50.3	49.0	46.6
77.5°	117.7	101.7	87.0	71.1	65.0	58.8	52.7	46.6	45.4	44.1	41.7
80°	83.4	73.5	65.0	55.2	51.5	46.6	42.9	38.0	38.0	36.8	36.8
82.5°	55.2	50.3	45.4	40.5	38.0	35.5	33.1	30.6	30.6	29.4	29.4
85°	39.2	36.8	33.1	30.6	29.4	27.0	25.7	23.3	23.3	23.3	23.3
87.5°	18.4	18.4	17.2	17.2	15.9	15.9	14.7	13.5	13.5	13.5	13.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671780
 CATALOG NUMBER: CCP-SA-1C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671780
 CATALOG NUMBER: CCP-SA-1C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6
2.5°	813.9	810.3	806.6	801.7	798.0	793.1	787.0	782.1	775.9	775.9	774.7
5°	657.0	653.4	649.7	644.8	641.1	636.2	632.5	627.6	622.7	622.7	621.5
7.5°	521.0	513.6	506.3	497.7	490.3	485.4	480.5	474.4	469.5	465.8	462.1
10°	453.5	446.2	437.6	430.3	421.7	415.5	409.4	402.1	395.9	391.0	386.1
12.5°	413.1	404.5	395.9	387.4	378.8	370.2	362.8	354.3	345.7	339.5	333.4
15°	355.5	346.9	338.3	329.7	321.2	311.4	301.5	290.5	280.7	275.8	272.1
17.5°	293.0	284.4	274.6	266.0	256.2	248.8	241.5	234.1	226.8	221.9	218.2
20°	236.6	226.8	217.0	207.2	197.4	192.5	187.5	182.6	177.7	174.1	171.6
22.5°	185.1	179.0	174.1	167.9	161.8	158.1	155.7	152.0	148.3	148.3	148.3
25°	158.1	154.5	152.0	148.3	144.6	143.4	142.2	139.7	138.5	137.3	137.3
27.5°	153.2	149.5	145.9	142.2	138.5	137.3	136.1	133.6	132.4	132.4	132.4
30°	163.0	161.8	160.6	159.4	158.1	155.7	152.0	149.5	145.9	143.4	141.0
32.5°	136.1	134.8	134.8	133.6	132.4	134.8	136.1	138.5	139.7	141.0	142.2
35°	120.1	117.7	115.2	112.8	110.3	109.1	107.9	106.6	105.4	105.4	104.2
37.5°	116.5	114.0	111.5	109.1	106.6	105.4	104.2	103.0	101.7	101.7	100.5
40°	112.8	110.3	109.1	106.6	104.2	103.0	101.7	99.3	98.1	96.8	96.8
42.5°	109.1	107.9	105.4	104.2	101.7	100.5	99.3	96.8	95.6	94.4	93.2
45°	109.1	106.6	104.2	101.7	99.3	98.1	95.6	94.4	91.9	91.9	90.7
47.5°	106.6	104.2	101.7	99.3	96.8	95.6	93.2	91.9	89.5	88.3	87.0
50°	112.8	109.1	104.2	100.5	95.6	94.4	91.9	90.7	88.3	87.0	85.8
52.5°	110.3	106.6	101.7	98.1	93.2	90.7	89.5	87.0	84.6	83.4	82.1
55°	101.7	98.1	95.6	91.9	88.3	85.8	83.4	80.9	78.5	77.2	77.2
57.5°	90.7	89.5	88.3	87.0	85.8	83.4	80.9	77.2	74.8	73.5	72.3
60°	80.9	82.1	83.4	84.6	85.8	82.1	78.5	74.8	71.1	69.9	68.6
62.5°	73.5	76.0	78.5	79.7	82.1	78.5	74.8	71.1	67.4	66.2	65.0
65°	68.6	69.9	69.9	71.1	71.1	68.6	67.4	65.0	62.5	61.3	61.3
67.5°	62.5	62.5	62.5	61.3	61.3	60.1	60.1	58.8	57.6	56.4	56.4
70°	56.4	56.4	56.4	55.2	55.2	53.9	53.9	52.7	51.5	51.5	50.3
72.5°	51.5	51.5	50.3	50.3	49.0	49.0	49.0	47.8	47.8	46.6	46.6
75°	45.4	45.4	44.1	44.1	42.9	42.9	42.9	41.7	41.7	41.7	40.5
77.5°	40.5	40.5	39.2	39.2	38.0	38.0	38.0	36.8	36.8	35.5	35.5
80°	35.5	35.5	34.3	34.3	33.1	33.1	31.9	31.9	30.6	30.6	29.4
82.5°	28.2	28.2	28.2	28.2	28.2	27.0	27.0	25.7	24.5	24.5	23.3
85°	23.3	23.3	23.3	22.1	22.1	22.1	20.8	20.8	19.6	18.4	18.4
87.5°	13.5	13.5	13.5	12.3	12.3	12.3	12.3	12.3	12.3	12.3	11.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671780
 CATALOG NUMBER: CCP-SA-1C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671780
 CATALOG NUMBER: CCP-SA-1C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6
2.5°	774.7	773.5	768.6	763.7	768.6	773.5	773.5	773.5	772.3	772.3	772.3
5°	621.5	620.3	617.8	615.4	615.4	614.1	616.6	619.0	621.5	623.9	626.4
7.5°	457.2	453.5	449.9	446.2	448.6	449.9	453.5	456.0	459.7	462.1	468.3
10°	381.2	376.3	372.6	369.0	366.5	364.1	361.6	360.4	357.9	355.5	357.9
12.5°	326.1	319.9	313.8	306.5	305.2	304.0	301.5	299.1	296.6	294.2	293.0
15°	267.2	262.3	259.9	256.2	251.3	246.4	243.9	242.7	240.3	237.8	236.6
17.5°	213.3	208.4	204.7	201.0	199.8	197.4	197.4	197.4	197.4	197.4	197.4
20°	167.9	164.3	164.3	163.0	163.0	161.8	163.0	164.3	164.3	165.5	166.7
22.5°	147.1	147.1	145.9	144.6	145.9	145.9	147.1	148.3	149.5	150.8	152.0
25°	136.1	134.8	136.1	137.3	137.3	137.3	138.5	138.5	139.7	139.7	139.7
27.5°	131.2	131.2	132.4	132.4	133.6	133.6	133.6	132.4	132.4	131.2	131.2
30°	138.5	136.1	136.1	136.1	134.8	133.6	132.4	132.4	131.2	129.9	128.7
32.5°	143.4	144.6	143.4	141.0	139.7	137.3	136.1	133.6	132.4	129.9	127.5
35°	104.2	103.0	105.4	106.6	107.9	109.1	110.3	111.5	111.5	112.8	112.8
37.5°	100.5	99.3	99.3	98.1	98.1	98.1	98.1	98.1	96.8	96.8	98.1
40°	95.6	94.4	94.4	93.2	93.2	91.9	91.9	91.9	91.9	91.9	91.9
42.5°	91.9	90.7	90.7	90.7	90.7	89.5	89.5	88.3	88.3	87.0	87.0
45°	90.7	89.5	88.3	87.0	87.0	85.8	85.8	85.8	84.6	84.6	84.6
47.5°	85.8	84.6	84.6	83.4	83.4	82.1	82.1	82.1	80.9	80.9	80.9
50°	83.4	82.1	82.1	80.9	80.9	79.7	79.7	79.7	78.5	78.5	78.5
52.5°	79.7	78.5	78.5	78.5	77.2	76.0	76.0	76.0	74.8	74.8	74.8
55°	76.0	74.8	74.8	74.8	73.5	72.3	72.3	72.3	71.1	71.1	71.1
57.5°	71.1	69.9	69.9	68.6	68.6	68.6	68.6	68.6	67.4	67.4	67.4
60°	67.4	66.2	66.2	65.0	65.0	63.7	63.7	63.7	63.7	63.7	63.7
62.5°	63.7	62.5	61.3	60.1	61.3	61.3	61.3	61.3	60.1	60.1	60.1
65°	60.1	58.8	57.6	56.4	56.4	56.4	56.4	56.4	56.4	56.4	56.4
67.5°	55.2	53.9	52.7	51.5	52.7	52.7	52.7	52.7	52.7	52.7	52.7
70°	50.3	49.0	49.0	47.8	47.8	46.6	46.6	47.8	47.8	47.8	47.8
72.5°	45.4	44.1	44.1	42.9	42.9	42.9	42.9	42.9	42.9	42.9	42.9
75°	40.5	39.2	39.2	38.0	38.0	38.0	38.0	38.0	38.0	38.0	38.0
77.5°	34.3	33.1	33.1	33.1	33.1	33.1	33.1	34.3	34.3	34.3	34.3
80°	29.4	28.2	28.2	28.2	28.2	28.2	28.2	28.2	28.2	28.2	28.2
82.5°	23.3	22.1	22.1	22.1	22.1	22.1	22.1	22.1	22.1	22.1	22.1
85°	17.2	15.9	15.9	15.9	17.2	17.2	17.2	17.2	17.2	17.2	17.2
87.5°	11.0	9.8	9.8	9.8	11.0	11.0	11.0	11.0	9.8	9.8	9.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671780
 CATALOG NUMBER: CCP-SA-1C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671780
 CATALOG NUMBER: CCP-SA-1C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6
2.5°	772.3	772.3	772.3	771.0	769.8	768.6	767.4	771.0	773.5	777.2	779.6
5°	627.6	630.1	631.3	635.0	638.6	642.3	646.0	648.5	650.9	652.1	654.6
7.5°	473.2	479.3	484.2	489.1	494.0	497.7	502.6	506.3	509.9	513.6	517.3
10°	359.2	361.6	362.8	367.7	371.4	376.3	380.0	383.7	387.4	389.8	393.5
12.5°	291.7	289.3	288.1	288.1	288.1	288.1	288.1	290.5	293.0	295.4	297.9
15°	235.4	234.1	232.9	231.7	230.5	228.0	226.8	229.2	231.7	234.1	236.6
17.5°	197.4	197.4	197.4	196.1	194.9	193.7	192.5	193.7	194.9	194.9	196.1
20°	169.2	170.4	171.6	172.8	172.8	174.1	174.1	175.3	176.5	176.5	177.7
22.5°	152.0	153.2	153.2	153.2	154.5	154.5	154.5	155.7	156.9	158.1	159.4
25°	138.5	138.5	137.3	137.3	138.5	138.5	138.5	138.5	139.7	139.7	139.7
27.5°	131.2	129.9	129.9	129.9	129.9	128.7	128.7	128.7	128.7	128.7	128.7
30°	127.5	126.3	125.0	123.8	123.8	122.6	121.4	121.4	121.4	121.4	121.4
32.5°	126.3	123.8	121.4	120.1	120.1	118.9	117.7	116.5	116.5	115.2	114.0
35°	112.8	111.5	111.5	110.3	109.1	107.9	106.6	106.6	106.6	105.4	105.4
37.5°	98.1	99.3	99.3	99.3	100.5	100.5	100.5	100.5	101.7	101.7	101.7
40°	91.9	91.9	91.9	93.2	94.4	94.4	95.6	95.6	96.8	96.8	96.8
42.5°	87.0	85.8	85.8	87.0	87.0	88.3	88.3	89.5	90.7	90.7	91.9
45°	84.6	83.4	83.4	83.4	83.4	82.1	82.1	83.4	84.6	85.8	87.0
47.5°	79.7	79.7	78.5	78.5	78.5	78.5	78.5	78.5	79.7	79.7	79.7
50°	77.2	77.2	76.0	76.0	76.0	76.0	76.0	76.0	76.0	76.0	76.0
52.5°	74.8	73.5	73.5	73.5	73.5	72.3	72.3	72.3	72.3	72.3	72.3
55°	71.1	69.9	69.9	69.9	69.9	69.9	69.9	69.9	71.1	71.1	71.1
57.5°	67.4	66.2	66.2	66.2	67.4	67.4	67.4	67.4	68.6	68.6	68.6
60°	63.7	63.7	63.7	63.7	63.7	63.7	63.7	65.0	65.0	66.2	66.2
62.5°	60.1	60.1	60.1	60.1	61.3	61.3	61.3	61.3	62.5	62.5	62.5
65°	56.4	56.4	56.4	56.4	57.6	57.6	57.6	57.6	57.6	57.6	57.6
67.5°	52.7	52.7	52.7	52.7	52.7	52.7	52.7	53.9	53.9	55.2	55.2
70°	47.8	46.6	46.6	47.8	47.8	49.0	49.0	50.3	50.3	51.5	51.5
72.5°	42.9	42.9	42.9	42.9	42.9	42.9	42.9	44.1	45.4	45.4	46.6
75°	38.0	38.0	38.0	38.0	39.2	39.2	39.2	40.5	40.5	41.7	41.7
77.5°	34.3	33.1	33.1	33.1	34.3	34.3	34.3	35.5	35.5	36.8	36.8
80°	28.2	28.2	28.2	28.2	29.4	29.4	29.4	29.4	30.6	30.6	30.6
82.5°	23.3	23.3	23.3	23.3	23.3	23.3	23.3	23.3	24.5	24.5	24.5
85°	17.2	17.2	17.2	17.2	18.4	18.4	18.4	18.4	18.4	18.4	18.4
87.5°	11.0	11.0	11.0	11.0	11.0	11.0	11.0	11.0	12.3	12.3	12.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671780
 CATALOG NUMBER: CCP-SA-1C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671780
 CATALOG NUMBER: CCP-SA-1C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6
2.5°	779.6	779.6	779.6	779.6	782.1	783.3	785.7	787.0	785.7	784.5	782.1
5°	655.8	657.0	657.0	658.3	658.3	658.3	658.3	658.3	660.7	663.2	665.6
7.5°	518.5	519.7	521.0	522.2	522.2	522.2	521.0	521.0	522.2	522.2	523.4
10°	397.2	402.1	405.7	409.4	407.0	403.3	400.8	397.2	397.2	397.2	395.9
12.5°	300.3	301.5	304.0	305.2	304.0	304.0	302.8	301.5	302.8	305.2	306.5
15°	237.8	237.8	239.0	239.0	240.3	241.5	241.5	242.7	245.2	246.4	248.8
17.5°	197.4	198.6	198.6	199.8	199.8	201.0	201.0	201.0	203.5	205.9	209.6
20°	177.7	177.7	177.7	177.7	177.7	176.5	176.5	175.3	176.5	179.0	180.2
22.5°	159.4	160.6	160.6	160.6	159.4	158.1	155.7	154.5	154.5	155.7	155.7
25°	139.7	138.5	138.5	137.3	137.3	138.5	138.5	138.5	139.7	139.7	141.0
27.5°	128.7	127.5	127.5	126.3	126.3	127.5	127.5	127.5	127.5	127.5	127.5
30°	120.1	120.1	118.9	117.7	118.9	118.9	120.1	120.1	121.4	121.4	122.6
32.5°	114.0	112.8	112.8	111.5	112.8	112.8	114.0	114.0	115.2	116.5	116.5
35°	105.4	105.4	105.4	105.4	105.4	105.4	104.2	104.2	104.2	104.2	104.2
37.5°	100.5	100.5	99.3	98.1	98.1	98.1	98.1	98.1	96.8	95.6	94.4
40°	96.8	95.6	95.6	94.4	93.2	93.2	91.9	90.7	90.7	89.5	89.5
42.5°	91.9	90.7	90.7	89.5	88.3	88.3	87.0	85.8	85.8	85.8	84.6
45°	85.8	85.8	84.6	83.4	83.4	83.4	82.1	82.1	82.1	82.1	80.9
47.5°	79.7	79.7	78.5	78.5	78.5	78.5	77.2	77.2	77.2	77.2	77.2
50°	76.0	76.0	76.0	76.0	76.0	76.0	74.8	74.8	74.8	74.8	74.8
52.5°	72.3	72.3	72.3	72.3	72.3	72.3	72.3	72.3	72.3	72.3	72.3
55°	71.1	71.1	71.1	71.1	71.1	71.1	69.9	69.9	69.9	71.1	71.1
57.5°	68.6	68.6	67.4	67.4	67.4	67.4	67.4	67.4	67.4	67.4	67.4
60°	66.2	66.2	66.2	66.2	66.2	66.2	66.2	66.2	66.2	66.2	66.2
62.5°	62.5	62.5	62.5	62.5	62.5	63.7	63.7	63.7	63.7	63.7	62.5
65°	57.6	58.8	58.8	58.8	58.8	58.8	58.8	58.8	58.8	58.8	58.8
67.5°	55.2	55.2	55.2	55.2	55.2	55.2	55.2	55.2	55.2	55.2	55.2
70°	51.5	51.5	50.3	50.3	50.3	51.5	51.5	51.5	51.5	51.5	51.5
72.5°	46.6	46.6	46.6	46.6	46.6	46.6	46.6	46.6	46.6	47.8	47.8
75°	41.7	41.7	41.7	41.7	41.7	41.7	41.7	41.7	41.7	41.7	41.7
77.5°	36.8	36.8	35.5	35.5	35.5	36.8	36.8	36.8	36.8	38.0	38.0
80°	30.6	30.6	30.6	30.6	30.6	30.6	30.6	30.6	30.6	31.9	31.9
82.5°	24.5	24.5	24.5	24.5	24.5	24.5	24.5	24.5	24.5	25.7	25.7
85°	18.4	19.6	19.6	19.6	19.6	19.6	19.6	19.6	19.6	20.8	20.8
87.5°	12.3	12.3	12.3	12.3	12.3	12.3	11.0	11.0	11.0	11.0	9.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671780
 CATALOG NUMBER: CCP-SA-1C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671780
 CATALOG NUMBER: CCP-SA-1C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6
2.5°	780.8	782.1	783.3	783.3	784.5	785.7	785.7	790.6	795.5	798.0	800.5
5°	668.1	666.8	666.8	665.6	664.4	668.1	671.7	679.1	686.5	687.7	690.1
7.5°	523.4	524.6	525.9	525.9	527.1	523.4	518.5	519.7	521.0	527.1	532.0
10°	395.9	397.2	398.4	398.4	399.6	398.4	395.9	399.6	403.3	408.2	414.3
12.5°	307.7	311.4	315.0	317.5	321.2	323.6	324.8	329.7	333.4	339.5	345.7
15°	251.3	253.7	256.2	258.6	261.1	263.5	266.0	270.9	275.8	283.2	290.5
17.5°	212.1	212.1	213.3	213.3	213.3	215.7	218.2	220.6	221.9	229.2	236.6
20°	181.4	180.2	179.0	177.7	176.5	179.0	180.2	181.4	182.6	187.5	191.2
22.5°	155.7	155.7	156.9	156.9	156.9	155.7	153.2	154.5	154.5	156.9	160.6
25°	141.0	141.0	141.0	139.7	139.7	141.0	142.2	142.2	141.0	142.2	143.4
27.5°	127.5	128.7	128.7	129.9	129.9	131.2	131.2	131.2	131.2	132.4	133.6
30°	122.6	122.6	123.8	123.8	123.8	125.0	126.3	126.3	126.3	127.5	129.9
32.5°	117.7	118.9	120.1	121.4	122.6	123.8	123.8	125.0	125.0	126.3	127.5
35°	104.2	103.0	103.0	101.7	100.5	100.5	100.5	100.5	99.3	100.5	100.5
37.5°	93.2	93.2	93.2	91.9	91.9	93.2	93.2	93.2	93.2	94.4	94.4
40°	88.3	88.3	88.3	88.3	88.3	88.3	88.3	89.5	89.5	90.7	91.9
42.5°	84.6	84.6	84.6	84.6	84.6	85.8	85.8	85.8	85.8	87.0	87.0
45°	80.9	80.9	80.9	80.9	80.9	80.9	80.9	82.1	82.1	83.4	84.6
47.5°	77.2	77.2	77.2	77.2	77.2	78.5	79.7	79.7	79.7	80.9	80.9
50°	74.8	74.8	74.8	74.8	74.8	76.0	76.0	77.2	77.2	78.5	79.7
52.5°	72.3	72.3	72.3	72.3	72.3	73.5	73.5	74.8	74.8	76.0	77.2
55°	71.1	71.1	71.1	69.9	69.9	71.1	71.1	72.3	72.3	73.5	73.5
57.5°	67.4	67.4	67.4	67.4	67.4	67.4	67.4	68.6	68.6	69.9	71.1
60°	66.2	66.2	65.0	65.0	63.7	65.0	65.0	66.2	66.2	67.4	67.4
62.5°	62.5	62.5	62.5	61.3	61.3	62.5	62.5	62.5	62.5	63.7	65.0
65°	58.8	58.8	58.8	57.6	57.6	58.8	58.8	58.8	58.8	60.1	61.3
67.5°	55.2	55.2	55.2	53.9	53.9	53.9	53.9	55.2	55.2	56.4	57.6
70°	51.5	51.5	51.5	50.3	50.3	50.3	49.0	50.3	51.5	52.7	52.7
72.5°	47.8	47.8	47.8	46.6	46.6	46.6	45.4	46.6	46.6	47.8	47.8
75°	41.7	41.7	41.7	41.7	41.7	41.7	40.5	40.5	40.5	41.7	41.7
77.5°	38.0	38.0	38.0	36.8	36.8	36.8	35.5	35.5	35.5	36.8	36.8
80°	31.9	31.9	31.9	30.6	30.6	30.6	29.4	29.4	29.4	30.6	30.6
82.5°	25.7	25.7	25.7	24.5	24.5	24.5	23.3	23.3	23.3	24.5	24.5
85°	20.8	20.8	20.8	20.8	20.8	20.8	19.6	19.6	19.6	20.8	22.1
87.5°	9.8	9.8	11.0	11.0	11.0	11.0	9.8	9.8	8.6	8.6	9.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671780
 CATALOG NUMBER: CCP-SA-1C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671780
 CATALOG NUMBER: CCP-SA-1C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6
2.5°	802.9	805.4	811.5	816.4	822.5	827.4	831.1	836.0	839.7	843.4	845.8
5°	691.4	692.6	698.7	704.8	709.7	715.9	724.5	733.0	741.6	750.2	756.3
7.5°	538.1	543.0	550.4	559.0	566.3	573.7	582.3	592.1	600.6	609.2	617.8
10°	419.2	424.1	431.5	438.8	445.0	452.3	462.1	471.9	481.7	491.5	501.4
12.5°	351.8	357.9	366.5	375.1	382.5	391.0	403.3	414.3	426.6	437.6	449.9
15°	296.6	304.0	315.0	327.3	338.3	349.4	361.6	373.9	384.9	397.2	409.4
17.5°	243.9	251.3	261.1	272.1	281.9	291.7	306.5	319.9	334.6	348.1	361.6
20°	196.1	199.8	209.6	219.4	229.2	239.0	250.1	261.1	272.1	283.2	300.3
22.5°	163.0	165.5	170.4	174.1	179.0	182.6	193.7	204.7	214.5	225.5	241.5
25°	143.4	144.6	148.3	150.8	154.5	156.9	164.3	170.4	177.7	183.9	198.6
27.5°	133.6	134.8	136.1	137.3	138.5	139.7	144.6	149.5	153.2	158.1	171.6
30°	131.2	132.4	136.1	138.5	142.2	144.6	147.1	149.5	152.0	154.5	163.0
32.5°	128.7	129.9	129.9	128.7	128.7	127.5	129.9	131.2	133.6	134.8	142.2
35°	101.7	101.7	103.0	104.2	105.4	106.6	110.3	112.8	116.5	118.9	125.0
37.5°	95.6	95.6	96.8	99.3	100.5	101.7	104.2	106.6	109.1	111.5	117.7
40°	91.9	93.2	94.4	95.6	96.8	98.1	100.5	101.7	104.2	105.4	110.3
42.5°	88.3	88.3	89.5	91.9	93.2	94.4	96.8	98.1	100.5	101.7	106.6
45°	85.8	87.0	88.3	89.5	89.5	90.7	93.2	95.6	96.8	99.3	104.2
47.5°	82.1	82.1	84.6	85.8	88.3	89.5	91.9	93.2	95.6	96.8	101.7
50°	79.7	80.9	83.4	84.6	87.0	88.3	91.9	94.4	98.1	100.5	103.0
52.5°	77.2	78.5	80.9	82.1	84.6	85.8	90.7	95.6	99.3	104.2	104.2
55°	74.8	74.8	77.2	80.9	83.4	85.8	88.3	91.9	94.4	96.8	96.8
57.5°	71.1	72.3	74.8	78.5	80.9	83.4	85.8	88.3	89.5	91.9	90.7
60°	68.6	68.6	72.3	76.0	79.7	83.4	83.4	83.4	82.1	82.1	82.1
62.5°	65.0	66.2	71.1	77.2	82.1	87.0	83.4	79.7	76.0	72.3	73.5
65°	62.5	63.7	66.2	69.9	72.3	74.8	72.3	71.1	68.6	66.2	67.4
67.5°	57.6	58.8	60.1	60.1	61.3	61.3	61.3	61.3	61.3	61.3	62.5
70°	53.9	53.9	53.9	55.2	55.2	55.2	55.2	55.2	55.2	55.2	56.4
72.5°	49.0	49.0	49.0	49.0	49.0	49.0	49.0	49.0	49.0	49.0	50.3
75°	42.9	42.9	42.9	42.9	42.9	42.9	42.9	42.9	42.9	42.9	44.1
77.5°	38.0	38.0	38.0	38.0	38.0	38.0	38.0	38.0	36.8	36.8	38.0
80°	31.9	31.9	31.9	31.9	30.6	30.6	30.6	30.6	30.6	30.6	31.9
82.5°	25.7	25.7	25.7	25.7	24.5	24.5	24.5	24.5	23.3	23.3	24.5
85°	23.3	24.5	24.5	25.7	25.7	25.7	24.5	23.3	22.1	20.8	20.8
87.5°	9.8	9.8	9.8	9.8	8.6	8.6	8.6	8.6	8.6	8.6	8.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671780
 CATALOG NUMBER: CCP-SA-1C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671780
 CATALOG NUMBER: CCP-SA-1C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6
2.5°	849.5	851.9	854.4	858.1	863.0	866.6	870.3	877.7	886.3	893.6	901.0
5°	762.5	768.6	774.7	782.1	789.4	795.5	802.9	817.6	832.3	845.8	860.5
7.5°	625.2	633.7	641.1	653.4	664.4	676.6	687.7	706.1	723.2	741.6	758.8
10°	511.2	521.0	530.8	546.7	563.9	579.8	595.7	610.5	626.4	641.1	655.8
12.5°	462.1	473.2	485.4	495.2	506.3	516.1	525.9	543.0	560.2	577.4	594.5
15°	421.7	433.9	446.2	458.5	469.5	481.7	492.8	507.5	523.4	538.1	552.8
17.5°	375.1	387.4	400.8	414.3	427.8	441.3	454.8	475.6	496.5	516.1	536.9
20°	316.3	333.4	349.4	367.7	386.1	404.5	422.9	445.0	467.0	487.9	509.9
22.5°	257.4	273.4	289.3	311.4	333.4	354.3	376.3	405.7	433.9	463.4	491.5
25°	214.5	229.2	243.9	268.5	291.7	316.3	339.5	375.1	409.4	445.0	479.3
27.5°	185.1	198.6	212.1	237.8	263.5	288.1	313.8	353.0	391.0	430.3	468.3
30°	171.6	180.2	188.8	213.3	237.8	261.1	285.6	323.6	361.6	399.6	437.6
32.5°	149.5	156.9	164.3	186.3	208.4	229.2	251.3	290.5	328.5	367.7	405.7
35°	132.4	138.5	144.6	165.5	185.1	205.9	225.5	264.8	304.0	343.2	382.5
37.5°	122.6	128.7	133.6	152.0	171.6	190.0	208.4	247.6	285.6	324.8	362.8
40°	115.2	118.9	123.8	142.2	159.4	177.7	194.9	230.5	267.2	302.8	338.3
42.5°	110.3	115.2	118.9	134.8	152.0	167.9	183.9	218.2	252.5	285.6	319.9
45°	109.1	114.0	118.9	132.4	145.9	158.1	171.6	204.7	237.8	270.9	304.0
47.5°	106.6	110.3	115.2	126.3	136.1	147.1	156.9	190.0	223.1	255.0	288.1
50°	105.4	106.6	109.1	118.9	128.7	138.5	148.3	181.4	214.5	247.6	280.7
52.5°	104.2	104.2	104.2	112.8	121.4	128.7	137.3	170.4	204.7	237.8	270.9
55°	96.8	95.6	95.6	104.2	111.5	120.1	127.5	160.6	193.7	225.5	258.6
57.5°	89.5	88.3	87.0	94.4	101.7	109.1	116.5	149.5	183.9	217.0	250.1
60°	82.1	80.9	80.9	88.3	94.4	101.7	107.9	142.2	175.3	209.6	242.7
62.5°	73.5	74.8	74.8	80.9	88.3	94.4	100.5	134.8	170.4	204.7	239.0
65°	67.4	68.6	68.6	76.0	83.4	90.7	98.1	131.2	165.5	198.6	231.7
67.5°	62.5	63.7	63.7	72.3	79.7	88.3	95.6	125.0	155.7	185.1	214.5
70°	57.6	57.6	58.8	67.4	76.0	84.6	93.2	118.9	144.6	169.2	194.9
72.5°	51.5	52.7	53.9	62.5	69.9	78.5	85.8	109.1	132.4	155.7	179.0
75°	45.4	46.6	47.8	55.2	62.5	69.9	77.2	99.3	120.1	142.2	163.0
77.5°	40.5	41.7	42.9	49.0	55.2	61.3	67.4	83.4	100.5	116.5	132.4
80°	33.1	33.1	34.3	39.2	44.1	47.8	52.7	63.7	74.8	84.6	95.6
82.5°	24.5	25.7	25.7	29.4	31.9	35.5	38.0	44.1	49.0	55.2	60.1
85°	20.8	19.6	19.6	22.1	23.3	25.7	27.0	30.6	33.1	36.8	39.2
87.5°	8.6	7.4	7.4	8.6	11.0	12.3	13.5	13.5	14.7	14.7	14.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671780
 CATALOG NUMBER: CCP-SA-1C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671780

CATALOG NUMBER: CCP-SA-1C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6
2.5°	904.6	907.1	910.8	913.2	919.4	924.3	930.4	935.3	939.0	945.1	942.6
5°	871.5	882.6	893.6	904.6	913.2	921.8	929.2	937.7	947.5	965.9	970.8
7.5°	773.5	788.2	801.7	816.4	833.5	850.7	867.9	885.0	901.0	924.3	939.0
10°	676.6	697.5	717.1	737.9	753.9	769.8	784.5	800.5	822.5	845.8	872.8
12.5°	615.4	636.2	657.0	677.9	701.2	723.2	746.5	768.6	789.4	807.8	838.4
15°	574.9	598.2	620.3	642.3	670.5	697.5	725.7	752.6	783.3	807.8	828.6
17.5°	565.1	593.3	620.3	648.5	677.9	707.3	736.7	766.1	796.8	833.5	860.5
20°	547.9	585.9	623.9	661.9	699.9	736.7	774.7	811.5	851.9	896.1	908.3
22.5°	538.1	583.5	630.1	675.4	726.9	779.6	831.1	882.6	925.5	958.6	995.4
25°	536.9	593.3	650.9	707.3	772.3	836.0	901.0	964.7	1019.9	1053.0	1082.4
27.5°	535.7	604.3	671.7	739.2	818.8	897.3	977.0	1055.4	1106.9	1154.7	1179.2
30°	521.0	603.1	686.5	768.6	858.1	947.5	1037.0	1126.5	1179.2	1212.3	1224.6
32.5°	502.6	599.4	696.3	793.1	894.8	996.6	1097.1	1198.8	1240.5	1268.7	1258.9
35°	487.9	594.5	699.9	805.4	913.2	1022.3	1130.2	1238.1	1298.1	1337.4	1321.4
37.5°	474.4	585.9	697.5	809.0	935.3	1061.5	1187.8	1314.1	1371.7	1413.4	1395.0
40°	458.5	577.4	697.5	816.4	961.0	1104.4	1249.1	1392.5	1467.3	1502.8	1474.6
42.5°	445.0	568.8	693.8	817.6	972.1	1126.5	1281.0	1435.4	1518.8	1569.0	1533.5
45°	427.8	551.6	674.2	798.0	968.4	1138.8	1307.9	1478.3	1575.2	1614.4	1565.4
47.5°	409.4	532.0	653.4	774.7	956.1	1137.5	1319.0	1500.4	1589.9	1636.4	1591.1
50°	403.3	525.9	647.2	769.8	965.9	1163.3	1359.4	1555.5	1620.5	1658.5	1598.4
52.5°	402.1	532.0	663.2	793.1	990.4	1186.6	1383.9	1580.1	1632.8	1673.2	1619.3
55°	398.4	539.4	679.1	818.8	1024.8	1231.9	1437.9	1643.8	1696.5	1725.9	1685.5
57.5°	402.1	554.1	704.8	856.8	1068.9	1281.0	1493.0	1705.1	1768.8	1789.7	1781.1
60°	404.5	566.3	726.9	888.7	1095.9	1303.0	1510.2	1717.4	1783.5	1835.0	1844.8
62.5°	398.4	557.7	715.9	875.2	1062.8	1250.3	1437.9	1625.4	1734.5	1810.5	1854.6
65°	380.0	527.1	675.4	822.5	995.4	1169.4	1342.3	1515.1	1630.3	1743.1	1778.6
67.5°	339.5	464.6	589.6	714.6	865.4	1016.2	1165.7	1316.5	1461.2	1570.3	1619.3
70°	294.2	392.3	491.5	589.6	726.9	864.2	1001.5	1138.8	1266.3	1386.4	1433.0
72.5°	256.2	332.2	409.4	485.4	583.5	680.3	778.4	875.2	1026.0	1146.1	1191.5
75°	218.2	273.4	327.3	382.5	449.9	517.3	583.5	650.9	757.5	865.4	910.8
77.5°	167.9	204.7	240.3	275.8	322.4	367.7	414.3	459.7	534.5	615.4	638.6
80°	116.5	137.3	156.9	177.7	214.5	251.3	288.1	324.8	373.9	419.2	454.8
82.5°	72.3	85.8	98.1	110.3	139.7	169.2	197.4	226.8	246.4	248.8	284.4
85°	46.6	55.2	62.5	69.9	87.0	105.4	122.6	139.7	125.0	116.5	138.5
87.5°	18.4	23.3	27.0	30.6	29.4	28.2	27.0	25.7	22.1	19.6	24.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671780
 CATALOG NUMBER: CCP-SA-1C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671780

CATALOG NUMBER: CCP-SA-1C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6
2.5°	945.1	948.8	952.4	954.9	958.6	959.8	961.0	961.0	962.3	963.5	965.9
5°	990.4	997.8	1005.2	1011.3	1018.6	1024.8	1029.7	1035.8	1040.7	1040.7	1039.5
7.5°	952.4	970.8	989.2	1007.6	1026.0	1039.5	1051.7	1065.2	1077.5	1079.9	1082.4
10°	902.2	921.8	940.2	959.8	978.2	999.0	1018.6	1038.3	1059.1	1062.8	1067.7
12.5°	855.6	878.9	902.2	924.3	947.5	962.3	977.0	990.4	1005.2	1015.0	1024.8
15°	854.4	874.0	893.6	912.0	931.6	940.2	948.8	956.1	964.7	964.7	965.9
17.5°	882.6	894.8	907.1	918.1	930.4	931.6	934.1	935.3	936.5	932.8	929.2
20°	937.7	942.6	947.5	952.4	957.4	948.8	941.4	932.8	924.3	914.4	905.9
22.5°	1018.6	1007.6	996.6	985.5	974.5	959.8	943.9	929.2	913.2	901.0	888.7
25°	1094.6	1081.2	1067.7	1054.2	1040.7	1008.8	977.0	943.9	912.0	898.5	885.0
27.5°	1196.4	1175.5	1154.7	1133.9	1113.0	1070.1	1027.2	984.3	941.4	918.1	896.1
30°	1220.9	1197.6	1174.3	1149.8	1126.5	1084.8	1044.4	1002.7	961.0	934.1	908.3
32.5°	1256.4	1229.5	1202.5	1175.5	1148.6	1108.1	1067.7	1026.0	985.5	961.0	935.3
35°	1315.3	1284.6	1254.0	1222.1	1191.5	1149.8	1109.4	1067.7	1026.0	997.8	970.8
37.5°	1365.5	1330.0	1294.4	1258.9	1223.4	1186.6	1148.6	1111.8	1073.8	1045.6	1018.6
40°	1421.9	1382.7	1343.5	1305.5	1266.3	1231.9	1197.6	1162.1	1127.7	1105.7	1083.6
42.5°	1471.0	1423.2	1376.6	1330.0	1282.2	1258.9	1236.8	1213.5	1190.3	1179.2	1167.0
45°	1505.3	1461.2	1415.8	1371.7	1327.5	1310.4	1293.2	1276.1	1258.9	1269.9	1281.0
47.5°	1520.0	1484.4	1450.1	1415.8	1380.3	1386.4	1392.5	1397.4	1403.5	1418.3	1434.2
50°	1533.5	1513.9	1493.0	1473.4	1452.6	1475.9	1497.9	1521.2	1544.5	1575.2	1605.8
52.5°	1560.4	1549.4	1539.6	1528.6	1517.5	1558.0	1598.4	1638.9	1679.4	1713.7	1748.0
55°	1641.4	1632.8	1624.2	1614.4	1605.8	1663.4	1719.8	1777.4	1835.0	1870.6	1906.1
57.5°	1752.9	1748.0	1741.9	1737.0	1730.8	1787.2	1842.4	1897.5	1953.9	1988.3	2023.8
60°	1837.5	1838.7	1838.7	1839.9	1839.9	1882.8	1925.7	1969.9	2012.8	2042.2	2072.8
62.5°	1882.8	1880.4	1877.9	1875.5	1873.0	1908.6	1944.1	1979.7	2015.2	2037.3	2059.4
65°	1833.8	1847.3	1860.8	1874.3	1887.7	1892.6	1896.3	1901.2	1904.9	1918.4	1931.9
67.5°	1669.5	1696.5	1722.3	1749.2	1775.0	1756.6	1739.4	1721.0	1702.6	1706.3	1708.8
70°	1486.9	1517.5	1549.4	1580.1	1610.7	1567.8	1524.9	1480.8	1437.9	1423.2	1408.4
72.5°	1254.0	1281.0	1309.2	1336.1	1363.1	1310.4	1258.9	1206.2	1153.5	1127.7	1102.0
75°	958.6	990.4	1023.5	1055.4	1087.3	1028.4	968.4	909.5	849.5	832.3	816.4
77.5°	698.7	736.7	774.7	812.7	850.7	798.0	745.3	691.4	638.6	628.8	619.0
80°	508.7	538.1	566.3	595.7	623.9	593.3	562.6	532.0	501.4	500.1	498.9
82.5°	343.2	369.0	393.5	419.2	443.7	431.5	420.5	408.2	395.9	408.2	421.7
85°	176.5	212.1	248.8	284.4	319.9	316.3	313.8	310.1	306.5	322.4	337.1
87.5°	35.5	66.2	96.8	126.3	156.9	149.5	142.2	133.6	126.3	131.2	134.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671780
 CATALOG NUMBER: CCP-SA-1C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671780

CATALOG NUMBER: CCP-SA-1C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6
2.5°	967.2	968.4	968.4	968.4	968.4	968.4	965.9	964.7	962.3	959.8	956.1
5°	1039.5	1038.3	1033.4	1028.4	1022.3	1017.4	1013.7	1008.8	1005.2	1000.3	992.9
7.5°	1084.8	1087.3	1078.7	1071.4	1062.8	1054.2	1045.6	1037.0	1028.4	1019.9	1002.7
10°	1071.4	1075.0	1070.1	1065.2	1059.1	1054.2	1044.4	1033.4	1023.5	1012.5	991.7
12.5°	1033.4	1043.2	1040.7	1038.3	1035.8	1033.4	1027.2	1019.9	1013.7	1006.4	983.1
15°	965.9	965.9	967.2	968.4	968.4	969.6	970.8	972.1	973.3	974.5	961.0
17.5°	925.5	921.8	921.8	921.8	921.8	921.8	926.7	932.8	937.7	942.6	939.0
20°	896.1	887.5	886.3	886.3	885.0	883.8	892.4	902.2	910.8	919.4	924.3
22.5°	876.4	864.2	863.0	861.7	860.5	859.3	870.3	881.4	892.4	903.4	920.6
25°	871.5	858.1	859.3	860.5	860.5	861.7	870.3	878.9	887.5	896.1	925.5
27.5°	872.8	850.7	851.9	853.2	853.2	854.4	867.9	880.1	893.6	905.9	942.6
30°	881.4	855.6	853.2	850.7	848.3	845.8	864.2	882.6	901.0	919.4	947.5
32.5°	910.8	886.3	880.1	874.0	867.9	861.7	883.8	904.6	926.7	947.5	970.8
35°	942.6	915.7	913.2	910.8	907.1	904.6	924.3	945.1	964.7	984.3	1005.2
37.5°	990.4	963.5	961.0	957.4	954.9	951.2	973.3	994.1	1016.2	1037.0	1055.4
40°	1061.5	1039.5	1038.3	1038.3	1037.0	1035.8	1053.0	1071.4	1088.5	1105.7	1117.9
42.5°	1155.9	1144.9	1148.6	1153.5	1157.2	1160.8	1174.3	1189.0	1202.5	1216.0	1212.3
45°	1292.0	1303.0	1304.3	1305.5	1306.7	1307.9	1311.6	1316.5	1320.2	1323.9	1309.2
47.5°	1448.9	1463.6	1471.0	1478.3	1484.4	1491.8	1486.9	1480.8	1475.9	1469.7	1433.0
50°	1635.2	1665.9	1664.6	1663.4	1661.0	1659.7	1649.9	1640.1	1629.1	1619.3	1565.4
52.5°	1782.3	1816.6	1822.8	1828.9	1835.0	1841.2	1822.8	1804.4	1784.8	1766.4	1699.0
55°	1940.4	1976.0	1977.2	1978.4	1978.4	1979.7	1953.9	1928.2	1901.2	1875.5	1805.6
57.5°	2058.1	2092.4	2088.8	2086.3	2082.6	2079.0	2048.3	2017.7	1987.0	1956.4	1886.5
60°	2102.3	2131.7	2124.3	2117.0	2108.4	2101.0	2077.7	2054.4	2029.9	2006.6	1939.2
62.5°	2081.4	2103.5	2092.4	2082.6	2071.6	2060.6	2031.2	2000.5	1971.1	1940.4	1891.4
65°	1944.1	1957.6	1942.9	1929.4	1915.9	1901.2	1876.7	1852.2	1826.4	1801.9	1768.8
67.5°	1712.4	1714.9	1713.7	1712.4	1711.2	1710.0	1674.4	1638.9	1602.1	1566.6	1564.1
70°	1395.0	1380.3	1382.7	1386.4	1388.8	1391.3	1364.3	1338.6	1311.6	1284.6	1296.9
72.5°	1076.3	1050.5	1056.6	1064.0	1070.1	1076.3	1054.2	1033.4	1011.3	989.2	1006.4
75°	799.2	783.3	789.4	796.8	802.9	809.0	800.5	791.9	782.1	773.5	789.4
77.5°	609.2	599.4	600.6	600.6	601.9	601.9	603.1	605.5	606.8	608.0	625.2
80°	496.5	495.2	494.0	492.8	490.3	489.1	501.4	513.6	525.9	538.1	546.7
82.5°	433.9	446.2	438.8	432.7	425.4	418.0	429.0	440.1	451.1	462.1	458.5
85°	353.0	367.7	354.3	340.8	326.1	312.6	322.4	331.0	340.8	349.4	344.5
87.5°	139.7	143.4	121.4	100.5	78.5	56.4	89.5	121.4	154.5	186.3	191.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671780
 CATALOG NUMBER: CCP-SA-1C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671780

CATALOG NUMBER: CCP-SA-1C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6	882.6
2.5°	952.4	947.5	943.9	942.6	940.2	939.0	936.5	934.1	930.4	927.9	924.3
5°	984.3	977.0	968.4	956.1	945.1	932.8	920.6	909.5	898.5	886.3	875.2
7.5°	985.5	968.4	951.2	935.3	918.1	902.2	885.0	870.3	854.4	838.4	823.7
10°	972.1	951.2	930.4	909.5	889.9	869.1	848.3	831.1	812.7	794.3	777.2
12.5°	961.0	937.7	914.4	889.9	866.6	842.1	817.6	800.5	783.3	766.1	749.0
15°	947.5	932.8	919.4	897.3	875.2	853.2	831.1	807.8	785.7	762.5	739.2
17.5°	936.5	932.8	929.2	914.4	899.7	883.8	869.1	845.8	822.5	798.0	774.7
20°	930.4	935.3	940.2	932.8	925.5	916.9	909.5	892.4	875.2	856.8	839.7
22.5°	937.7	956.1	973.3	974.5	977.0	978.2	979.4	963.5	947.5	930.4	914.4
25°	954.9	984.3	1013.7	1029.7	1045.6	1062.8	1078.7	1068.9	1059.1	1049.3	1039.5
27.5°	978.2	1015.0	1051.7	1075.0	1097.1	1120.4	1143.7	1142.4	1141.2	1138.8	1137.5
30°	974.5	1002.7	1030.9	1059.1	1087.3	1115.5	1143.7	1158.4	1171.9	1186.6	1201.3
32.5°	995.4	1018.6	1043.2	1072.6	1102.0	1132.6	1162.1	1192.7	1222.1	1252.8	1283.4
35°	1027.2	1048.1	1070.1	1102.0	1135.1	1167.0	1200.1	1236.8	1274.8	1312.8	1349.6
37.5°	1075.0	1093.4	1113.0	1140.0	1168.2	1195.2	1223.4	1277.3	1331.2	1386.4	1440.3
40°	1130.2	1142.4	1154.7	1180.4	1206.2	1231.9	1257.7	1325.1	1392.5	1459.9	1527.4
42.5°	1209.9	1206.2	1202.5	1223.4	1245.4	1266.3	1288.3	1349.6	1410.9	1472.2	1533.5
45°	1294.4	1279.7	1265.0	1274.8	1285.9	1295.7	1306.7	1369.2	1431.7	1495.5	1558.0
47.5°	1396.2	1359.4	1322.6	1314.1	1305.5	1295.7	1287.1	1354.5	1421.9	1490.6	1558.0
50°	1511.4	1456.3	1402.3	1380.3	1357.0	1334.9	1311.6	1366.8	1423.2	1479.5	1534.7
52.5°	1631.5	1562.9	1495.5	1461.2	1426.8	1391.3	1357.0	1403.5	1451.4	1499.2	1545.7
55°	1734.5	1664.6	1593.5	1553.1	1512.6	1472.2	1431.7	1478.3	1524.9	1571.5	1618.1
57.5°	1816.6	1746.8	1676.9	1638.9	1599.7	1561.7	1522.4	1566.6	1611.9	1657.3	1701.4
60°	1873.0	1805.6	1738.2	1701.4	1664.6	1627.9	1591.1	1643.8	1696.5	1750.4	1803.2
62.5°	1843.6	1794.6	1745.5	1729.6	1713.7	1696.5	1680.6	1730.8	1779.9	1830.1	1880.4
65°	1735.7	1702.6	1669.5	1685.5	1702.6	1718.6	1735.7	1768.8	1801.9	1836.3	1869.4
67.5°	1560.4	1558.0	1554.3	1589.9	1625.4	1662.2	1697.7	1719.8	1740.6	1762.7	1784.8
70°	1309.2	1322.6	1334.9	1396.2	1457.5	1518.8	1580.1	1588.6	1597.2	1605.8	1614.4
72.5°	1024.8	1041.9	1060.3	1141.2	1220.9	1301.8	1382.7	1377.8	1372.9	1366.8	1361.9
75°	806.6	822.5	839.7	914.4	989.2	1064.0	1138.8	1117.9	1098.3	1077.5	1056.6
77.5°	643.5	660.7	679.1	749.0	818.8	889.9	959.8	909.5	859.3	809.0	758.8
80°	554.1	562.6	570.0	617.8	664.4	712.2	760.0	708.5	655.8	603.1	551.6
82.5°	454.8	449.9	446.2	474.4	502.6	530.8	559.0	509.9	460.9	410.6	361.6
85°	339.5	334.6	329.7	344.5	359.2	375.1	389.8	333.4	277.0	219.4	163.0
87.5°	197.4	202.3	207.2	223.1	239.0	256.2	272.1	214.5	156.9	98.1	40.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671780
 CATALOG NUMBER: CCP-SA-1C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671780
CATALOG NUMBER: CCP-SA-1C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	882.6	882.6
2.5°	916.9	910.8
5°	866.6	858.1
7.5°	811.5	800.5
10°	761.2	746.5
12.5°	729.4	711.0
15°	717.1	695.0
17.5°	753.9	733.0
20°	810.3	782.1
22.5°	878.9	844.6
25°	997.8	956.1
27.5°	1094.6	1051.7
30°	1154.7	1108.1
32.5°	1220.9	1159.6
35°	1289.5	1230.7
37.5°	1372.9	1306.7
40°	1458.7	1390.1
42.5°	1488.1	1444.0
45°	1516.3	1474.6
47.5°	1522.4	1488.1
50°	1528.6	1523.7
52.5°	1545.7	1544.5
55°	1619.3	1620.5
57.5°	1710.0	1717.4
60°	1793.4	1784.8
62.5°	1836.3	1792.1
65°	1806.8	1745.5
67.5°	1718.6	1652.4
70°	1524.9	1435.4
72.5°	1283.4	1205.0
75°	989.2	923.0
77.5°	703.6	648.5
80°	495.2	440.1
82.5°	317.5	273.4
85°	143.4	125.0
87.5°	40.5	39.2
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P671780
CATALOG NUMBER: CCP-SA-1C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)