

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P671790

Luminaire Tested: **CCP-SA-1B-727-U-SLR**

Issue Date: 04/16/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P671790  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 04/16/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: CCP-SA-1B-727-U-SLR  
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @450mA w/ SLR distribution lens  
Light Source: (16) 2700K CCT, 70 CRI LEDs  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2396.9 lumens  
Efficiency: N/A  
Efficacy: 99.9 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B1 - U0 - G1

Input Watts (W): 24  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

REPORT NUMBER: P671790  
 CATALOG NUMBER: CCP-SA-1B-727-U-SLR

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 3.4 fc  
 Type IV - Short - N/A

REPORT NUMBER: P671790  
CATALOG NUMBER: CCP-SA-1B-727-U-SLR

### Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral      - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P671790  
 CATALOG NUMBER: CCP-SA-1B-727-U-SLR


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	493.2	0.0	493.2
	% Fixture	20.6	0.0	20.6
<b>Street Side</b>	Lumens	1903.7	0.0	1903.7
	% Fixture	79.4	0.0	79.4
<b>Total</b>	Lumens	2396.9	0.0	2396.9
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	59.5	2.5
10°-20°	125.6	5.2
20°-30°	183.7	7.7
30°-40°	258.8	10.8
40°-50°	355.7	14.8
50°-60°	484.8	20.2
60°-70°	530.6	22.1
70°-80°	306.4	12.8
80°-90°	91.8	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2396.9	100.0
0°-180°	2396.9	100.0



REPORT NUMBER: P671790


CATALOG NUMBER: CCP-SA-1B-727-U-SLR

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	246.2	10.3			
FM (30°-60°)	874.7	36.5			
FH (60°-80°)	704.8	29.4			G1/1800
FVH (80°-90°)	78.0	3.3			G1/100
BL (0°-30°)	122.6	5.1	B1/500		
BM (30°-60°)	224.6	9.4	B1/1000		
BH (60°-80°)	132.2	5.5	B1/500		G1/500
BVH (80°-90°)	13.8	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B1-U0-G1**

Type IV Short





REPORT NUMBER: P671790

CATALOG NUMBER: CCP-SA-1B-727-U-SLR

**CANDELA DISTRIBUTION (FULL):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4
2.5°	789.9	785.6	782.4	779.2	775.0	771.8	767.5	763.3	758.0	753.7	748.4
5°	744.2	731.4	718.6	711.2	702.7	695.3	686.7	677.2	667.6	657.0	647.4
7.5°	694.2	678.2	662.3	649.5	635.7	623.0	609.1	597.4	585.8	574.1	562.4
10°	647.4	632.5	617.6	601.7	584.7	568.7	551.7	535.8	519.8	503.9	488.0
12.5°	616.6	598.5	581.5	563.4	546.4	528.3	510.3	495.4	480.5	464.6	449.7
15°	602.8	585.8	569.8	551.7	533.7	515.6	497.5	480.5	464.6	447.6	430.5
17.5°	635.7	611.3	586.8	563.4	540.0	516.7	493.3	472.0	450.7	429.5	408.2
20°	678.2	647.4	617.6	588.9	559.2	530.5	500.7	470.9	441.2	411.4	381.6
22.5°	732.5	697.4	663.4	626.2	587.9	550.7	512.4	475.2	438.0	399.7	362.5
25°	829.2	787.7	746.3	693.1	638.9	585.8	531.5	482.6	434.8	385.9	337.0
27.5°	912.1	855.8	800.5	736.7	672.9	609.1	545.4	489.0	433.7	377.4	321.0
30°	961.0	905.7	850.5	772.9	696.3	618.7	541.1	478.4	416.7	354.0	291.3
32.5°	1005.7	944.0	882.4	797.3	711.2	626.2	540.0	470.9	402.9	333.8	264.7
35°	1067.3	999.3	932.3	833.5	734.6	635.7	536.9	465.6	393.3	322.1	249.8
37.5°	1133.2	1049.3	966.3	856.8	747.3	637.8	528.3	458.2	388.0	317.9	247.7
40°	1205.5	1103.5	1002.5	881.3	761.2	640.0	518.8	448.6	378.5	307.2	237.1
42.5°	1252.3	1141.7	1031.2	900.4	770.7	640.0	509.2	440.1	371.0	300.9	231.8
45°	1278.9	1171.5	1065.2	923.8	782.4	641.0	499.6	431.6	363.6	294.5	226.4
47.5°	1290.6	1190.6	1090.7	941.9	794.1	645.3	496.5	427.4	357.2	288.1	217.9
50°	1321.4	1233.2	1144.9	985.5	827.1	667.6	508.2	433.7	360.4	286.0	211.6
52.5°	1339.5	1264.0	1188.5	1024.8	861.1	697.4	533.7	450.7	367.8	284.9	202.0
55°	1405.4	1333.1	1260.8	1086.5	911.1	736.7	561.3	469.9	378.5	286.0	194.5
57.5°	1489.4	1412.8	1337.3	1149.2	961.0	772.9	584.7	486.9	388.0	290.2	191.4
60°	1547.8	1473.4	1400.1	1200.2	999.3	799.4	598.5	496.5	394.4	291.3	189.2
62.5°	1554.2	1458.5	1363.9	1169.4	974.8	779.2	584.7	485.8	387.0	287.0	188.2
65°	1513.8	1402.2	1290.6	1104.5	918.5	732.5	546.4	456.1	365.7	274.3	183.9
67.5°	1433.0	1302.3	1171.5	1001.4	831.3	661.2	491.1	413.5	337.0	259.4	181.8
70°	1244.9	1130.0	1016.3	868.5	721.8	574.1	426.3	362.5	299.8	236.0	172.2
72.5°	1045.0	937.6	831.3	711.2	592.1	472.0	351.9	304.0	256.2	207.3	159.5
75°	800.5	719.7	640.0	550.7	461.4	371.0	281.7	246.6	211.6	176.5	141.4
77.5°	562.4	518.8	476.3	409.3	342.3	275.3	208.4	185.0	161.6	138.2	114.8
80°	381.6	357.2	333.8	286.0	238.1	189.2	141.4	126.5	110.6	95.7	79.7
82.5°	237.1	236.0	233.9	200.9	168.0	135.0	102.1	89.3	77.6	64.8	52.1
85°	108.4	126.5	143.5	125.4	107.4	89.3	71.2	62.7	54.2	44.6	36.1
87.5°	34.0	41.5	47.8	45.7	42.5	40.4	37.2	31.9	26.6	21.3	15.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671790  
 CATALOG NUMBER: CCP-SA-1B-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671790  
 CATALOG NUMBER: CCP-SA-1B-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4
2.5°	744.2	741.0	736.7	732.5	727.1	722.9	717.6	712.3	711.2	709.1	708.0
5°	641.0	634.7	627.2	620.8	614.5	607.0	600.6	593.2	587.9	581.5	576.2
7.5°	550.7	540.0	528.3	516.7	506.0	495.4	483.7	473.1	467.8	462.4	457.1
10°	478.4	467.8	458.2	447.6	440.1	433.7	426.3	418.9	412.5	406.1	399.7
12.5°	442.2	434.8	427.4	419.9	411.4	404.0	395.5	387.0	379.5	373.1	365.7
15°	419.9	409.3	397.6	387.0	375.3	364.6	352.9	341.2	332.7	325.3	316.8
17.5°	393.3	377.4	362.5	346.6	333.8	321.0	307.2	294.5	284.9	274.3	264.7
20°	363.6	345.5	326.4	308.3	293.4	279.6	264.7	249.8	239.2	227.5	216.9
22.5°	338.1	314.7	290.2	265.8	249.8	233.9	216.9	200.9	191.4	180.7	171.2
25°	310.4	284.9	258.3	231.8	215.8	198.8	182.8	165.8	158.4	152.0	144.6
27.5°	295.5	270.0	243.4	217.9	203.0	187.1	172.2	156.3	151.0	144.6	139.3
30°	265.8	241.3	215.8	190.3	179.7	170.1	159.5	148.8	146.7	145.6	143.5
32.5°	239.2	213.7	188.2	162.7	153.1	143.5	133.9	124.4	123.3	121.2	120.1
35°	225.4	200.9	175.4	151.0	142.5	132.9	124.4	114.8	112.7	109.5	107.4
37.5°	222.2	196.7	170.1	144.6	136.1	127.6	118.0	109.5	107.4	105.2	103.1
40°	213.7	189.2	165.8	141.4	132.9	124.4	114.8	106.3	104.2	102.1	99.9
42.5°	207.3	183.9	159.5	135.0	127.6	120.1	111.6	104.2	102.1	99.9	96.7
45°	202.0	177.5	152.0	127.6	122.3	116.9	110.6	105.2	103.1	99.9	97.8
47.5°	193.5	170.1	145.6	121.2	115.9	111.6	106.3	101.0	98.9	96.7	94.6
50°	187.1	162.7	138.2	113.7	109.5	105.2	101.0	96.7	96.7	97.8	97.8
52.5°	178.6	155.2	131.8	108.4	104.2	99.9	95.7	91.4	92.5	93.6	94.6
55°	171.2	148.8	125.4	102.1	97.8	93.6	88.2	84.0	85.0	86.1	87.2
57.5°	168.0	144.6	121.2	97.8	93.6	88.2	84.0	78.7	78.7	78.7	78.7
60°	165.8	141.4	118.0	93.6	88.2	84.0	78.7	73.4	72.3	72.3	71.2
62.5°	164.8	140.3	116.9	92.5	86.1	80.8	74.4	68.0	67.0	65.9	64.8
65°	160.5	138.2	114.8	91.4	84.0	77.6	70.2	62.7	61.7	61.7	60.6
67.5°	159.5	136.1	113.7	90.4	82.9	74.4	67.0	58.5	57.4	56.3	55.3
70°	151.0	130.8	109.5	88.2	79.7	72.3	63.8	55.3	54.2	52.1	51.0
72.5°	140.3	122.3	103.1	84.0	75.5	67.0	58.5	50.0	48.9	47.8	45.7
75°	124.4	107.4	90.4	73.4	65.9	59.5	52.1	44.6	43.6	42.5	40.4
77.5°	102.1	88.2	75.5	61.7	56.3	51.0	45.7	40.4	39.3	38.3	36.1
80°	72.3	63.8	56.3	47.8	44.6	40.4	37.2	33.0	33.0	31.9	31.9
82.5°	47.8	43.6	39.3	35.1	33.0	30.8	28.7	26.6	26.6	25.5	25.5
85°	34.0	31.9	28.7	26.6	25.5	23.4	22.3	20.2	20.2	20.2	20.2
87.5°	15.9	15.9	14.9	14.9	13.8	13.8	12.8	11.7	11.7	11.7	11.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671790  
 CATALOG NUMBER: CCP-SA-1B-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671790  
 CATALOG NUMBER: CCP-SA-1B-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4
2.5°	705.9	702.7	699.5	695.3	692.1	687.8	682.5	678.2	672.9	672.9	671.9
5°	569.8	566.6	563.4	559.2	556.0	551.7	548.5	544.3	540.0	540.0	539.0
7.5°	451.8	445.4	439.1	431.6	425.2	421.0	416.7	411.4	407.2	404.0	400.8
10°	393.3	387.0	379.5	373.1	365.7	360.4	355.1	348.7	343.4	339.1	334.9
12.5°	358.3	350.8	343.4	335.9	328.5	321.0	314.7	307.2	299.8	294.5	289.2
15°	308.3	300.9	293.4	286.0	278.5	270.0	261.5	251.9	243.4	239.2	236.0
17.5°	254.1	246.6	238.1	230.7	222.2	215.8	209.4	203.0	196.7	192.4	189.2
20°	205.2	196.7	188.2	179.7	171.2	166.9	162.7	158.4	154.1	151.0	148.8
22.5°	160.5	155.2	151.0	145.6	140.3	137.1	135.0	131.8	128.6	128.6	128.6
25°	137.1	133.9	131.8	128.6	125.4	124.4	123.3	121.2	120.1	119.1	119.1
27.5°	132.9	129.7	126.5	123.3	120.1	119.1	118.0	115.9	114.8	114.8	114.8
30°	141.4	140.3	139.3	138.2	137.1	135.0	131.8	129.7	126.5	124.4	122.3
32.5°	118.0	116.9	116.9	115.9	114.8	116.9	118.0	120.1	121.2	122.3	123.3
35°	104.2	102.1	99.9	97.8	95.7	94.6	93.6	92.5	91.4	91.4	90.4
37.5°	101.0	98.9	96.7	94.6	92.5	91.4	90.4	89.3	88.2	88.2	87.2
40°	97.8	95.7	94.6	92.5	90.4	89.3	88.2	86.1	85.0	84.0	84.0
42.5°	94.6	93.6	91.4	90.4	88.2	87.2	86.1	84.0	82.9	81.9	80.8
45°	94.6	92.5	90.4	88.2	86.1	85.0	82.9	81.9	79.7	79.7	78.7
47.5°	92.5	90.4	88.2	86.1	84.0	82.9	80.8	79.7	77.6	76.5	75.5
50°	97.8	94.6	90.4	87.2	82.9	81.9	79.7	78.7	76.5	75.5	74.4
52.5°	95.7	92.5	88.2	85.0	80.8	78.7	77.6	75.5	73.4	72.3	71.2
55°	88.2	85.0	82.9	79.7	76.5	74.4	72.3	70.2	68.0	67.0	67.0
57.5°	78.7	77.6	76.5	75.5	74.4	72.3	70.2	67.0	64.8	63.8	62.7
60°	70.2	71.2	72.3	73.4	74.4	71.2	68.0	64.8	61.7	60.6	59.5
62.5°	63.8	65.9	68.0	69.1	71.2	68.0	64.8	61.7	58.5	57.4	56.3
65°	59.5	60.6	60.6	61.7	61.7	59.5	58.5	56.3	54.2	53.2	53.2
67.5°	54.2	54.2	54.2	53.2	53.2	52.1	52.1	51.0	50.0	48.9	48.9
70°	48.9	48.9	48.9	47.8	47.8	46.8	46.8	45.7	44.6	44.6	43.6
72.5°	44.6	44.6	43.6	43.6	42.5	42.5	42.5	41.5	41.5	40.4	40.4
75°	39.3	39.3	38.3	38.3	37.2	37.2	37.2	36.1	36.1	36.1	35.1
77.5°	35.1	35.1	34.0	34.0	33.0	33.0	33.0	31.9	31.9	30.8	30.8
80°	30.8	30.8	29.8	29.8	28.7	28.7	27.6	27.6	26.6	26.6	25.5
82.5°	24.5	24.5	24.5	24.5	24.5	23.4	23.4	22.3	21.3	21.3	20.2
85°	20.2	20.2	20.2	19.1	19.1	19.1	18.1	18.1	17.0	15.9	15.9
87.5°	11.7	11.7	11.7	10.6	10.6	10.6	10.6	10.6	10.6	10.6	9.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671790  
 CATALOG NUMBER: CCP-SA-1B-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671790  
 CATALOG NUMBER: CCP-SA-1B-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4
2.5°	671.9	670.8	666.5	662.3	666.5	670.8	670.8	670.8	669.7	669.7	669.7
5°	539.0	537.9	535.8	533.7	533.7	532.6	534.7	536.9	539.0	541.1	543.2
7.5°	396.5	393.3	390.1	387.0	389.1	390.1	393.3	395.5	398.7	400.8	406.1
10°	330.6	326.4	323.2	320.0	317.9	315.7	313.6	312.5	310.4	308.3	310.4
12.5°	282.8	277.5	272.1	265.8	264.7	263.6	261.5	259.4	257.3	255.1	254.1
15°	231.8	227.5	225.4	222.2	217.9	213.7	211.6	210.5	208.4	206.2	205.2
17.5°	185.0	180.7	177.5	174.3	173.3	171.2	171.2	171.2	171.2	171.2	171.2
20°	145.6	142.5	142.5	141.4	141.4	140.3	141.4	142.5	142.5	143.5	144.6
22.5°	127.6	127.6	126.5	125.4	126.5	126.5	127.6	128.6	129.7	130.8	131.8
25°	118.0	116.9	118.0	119.1	119.1	119.1	120.1	120.1	121.2	121.2	121.2
27.5°	113.7	113.7	114.8	114.8	115.9	115.9	115.9	114.8	114.8	113.7	113.7
30°	120.1	118.0	118.0	118.0	116.9	115.9	114.8	114.8	113.7	112.7	111.6
32.5°	124.4	125.4	124.4	122.3	121.2	119.1	118.0	115.9	114.8	112.7	110.6
35°	90.4	89.3	91.4	92.5	93.6	94.6	95.7	96.7	96.7	97.8	97.8
37.5°	87.2	86.1	86.1	85.0	85.0	85.0	85.0	85.0	84.0	84.0	85.0
40°	82.9	81.9	81.9	80.8	80.8	79.7	79.7	79.7	79.7	79.7	79.7
42.5°	79.7	78.7	78.7	78.7	78.7	77.6	77.6	76.5	76.5	75.5	75.5
45°	78.7	77.6	76.5	75.5	75.5	74.4	74.4	74.4	73.4	73.4	73.4
47.5°	74.4	73.4	73.4	72.3	72.3	71.2	71.2	71.2	70.2	70.2	70.2
50°	72.3	71.2	71.2	70.2	70.2	69.1	69.1	69.1	68.0	68.0	68.0
52.5°	69.1	68.0	68.0	68.0	67.0	65.9	65.9	65.9	64.8	64.8	64.8
55°	65.9	64.8	64.8	64.8	63.8	62.7	62.7	62.7	61.7	61.7	61.7
57.5°	61.7	60.6	60.6	59.5	59.5	59.5	59.5	59.5	58.5	58.5	58.5
60°	58.5	57.4	57.4	56.3	56.3	55.3	55.3	55.3	55.3	55.3	55.3
62.5°	55.3	54.2	53.2	52.1	53.2	53.2	53.2	53.2	52.1	52.1	52.1
65°	52.1	51.0	50.0	48.9	48.9	48.9	48.9	48.9	48.9	48.9	48.9
67.5°	47.8	46.8	45.7	44.6	45.7	45.7	45.7	45.7	45.7	45.7	45.7
70°	43.6	42.5	42.5	41.5	41.5	40.4	40.4	41.5	41.5	41.5	41.5
72.5°	39.3	38.3	38.3	37.2	37.2	37.2	37.2	37.2	37.2	37.2	37.2
75°	35.1	34.0	34.0	33.0	33.0	33.0	33.0	33.0	33.0	33.0	33.0
77.5°	29.8	28.7	28.7	28.7	28.7	28.7	28.7	29.8	29.8	29.8	29.8
80°	25.5	24.5	24.5	24.5	24.5	24.5	24.5	24.5	24.5	24.5	24.5
82.5°	20.2	19.1	19.1	19.1	19.1	19.1	19.1	19.1	19.1	19.1	19.1
85°	14.9	13.8	13.8	13.8	14.9	14.9	14.9	14.9	14.9	14.9	14.9
87.5°	9.6	8.5	8.5	8.5	9.6	9.6	9.6	9.6	8.5	8.5	8.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671790  
 CATALOG NUMBER: CCP-SA-1B-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671790  
 CATALOG NUMBER: CCP-SA-1B-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4
2.5°	669.7	669.7	669.7	668.7	667.6	666.5	665.5	668.7	670.8	674.0	676.1
5°	544.3	546.4	547.5	550.7	553.9	557.1	560.2	562.4	564.5	565.6	567.7
7.5°	410.3	415.7	419.9	424.2	428.4	431.6	435.9	439.1	442.2	445.4	448.6
10°	311.5	313.6	314.7	318.9	322.1	326.4	329.6	332.7	335.9	338.1	341.2
12.5°	253.0	250.9	249.8	249.8	249.8	249.8	249.8	251.9	254.1	256.2	258.3
15°	204.1	203.0	202.0	200.9	199.9	197.7	196.7	198.8	200.9	203.0	205.2
17.5°	171.2	171.2	171.2	170.1	169.0	168.0	166.9	168.0	169.0	169.0	170.1
20°	146.7	147.8	148.8	149.9	149.9	151.0	151.0	152.0	153.1	153.1	154.1
22.5°	131.8	132.9	132.9	132.9	133.9	133.9	133.9	135.0	136.1	137.1	138.2
25°	120.1	120.1	119.1	119.1	120.1	120.1	120.1	120.1	121.2	121.2	121.2
27.5°	113.7	112.7	112.7	112.7	112.7	111.6	111.6	111.6	111.6	111.6	111.6
30°	110.6	109.5	108.4	107.4	107.4	106.3	105.2	105.2	105.2	105.2	105.2
32.5°	109.5	107.4	105.2	104.2	104.2	103.1	102.1	101.0	101.0	99.9	98.9
35°	97.8	96.7	96.7	95.7	94.6	93.6	92.5	92.5	92.5	91.4	91.4
37.5°	85.0	86.1	86.1	86.1	87.2	87.2	87.2	87.2	88.2	88.2	88.2
40°	79.7	79.7	79.7	80.8	81.9	81.9	82.9	82.9	84.0	84.0	84.0
42.5°	75.5	74.4	74.4	75.5	75.5	76.5	76.5	77.6	78.7	78.7	79.7
45°	73.4	72.3	72.3	72.3	72.3	71.2	71.2	72.3	73.4	74.4	75.5
47.5°	69.1	69.1	68.0	68.0	68.0	68.0	68.0	68.0	69.1	69.1	69.1
50°	67.0	67.0	65.9	65.9	65.9	65.9	65.9	65.9	65.9	65.9	65.9
52.5°	64.8	63.8	63.8	63.8	63.8	62.7	62.7	62.7	62.7	62.7	62.7
55°	61.7	60.6	60.6	60.6	60.6	60.6	60.6	60.6	61.7	61.7	61.7
57.5°	58.5	57.4	57.4	57.4	58.5	58.5	58.5	58.5	59.5	59.5	59.5
60°	55.3	55.3	55.3	55.3	55.3	55.3	55.3	56.3	56.3	57.4	57.4
62.5°	52.1	52.1	52.1	52.1	53.2	53.2	53.2	53.2	54.2	54.2	54.2
65°	48.9	48.9	48.9	48.9	50.0	50.0	50.0	50.0	50.0	50.0	50.0
67.5°	45.7	45.7	45.7	45.7	45.7	45.7	45.7	46.8	46.8	47.8	47.8
70°	41.5	40.4	40.4	41.5	41.5	42.5	42.5	43.6	43.6	44.6	44.6
72.5°	37.2	37.2	37.2	37.2	37.2	37.2	37.2	38.3	39.3	39.3	40.4
75°	33.0	33.0	33.0	33.0	34.0	34.0	34.0	35.1	35.1	36.1	36.1
77.5°	29.8	28.7	28.7	28.7	29.8	29.8	29.8	30.8	30.8	31.9	31.9
80°	24.5	24.5	24.5	24.5	25.5	25.5	25.5	25.5	26.6	26.6	26.6
82.5°	20.2	20.2	20.2	20.2	20.2	20.2	20.2	20.2	21.3	21.3	21.3
85°	14.9	14.9	14.9	14.9	15.9	15.9	15.9	15.9	15.9	15.9	15.9
87.5°	9.6	9.6	9.6	9.6	9.6	9.6	9.6	9.6	10.6	10.6	10.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671790  
 CATALOG NUMBER: CCP-SA-1B-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671790  
 CATALOG NUMBER: CCP-SA-1B-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4
2.5°	676.1	676.1	676.1	676.1	678.2	679.3	681.4	682.5	681.4	680.4	678.2
5°	568.7	569.8	569.8	570.9	570.9	570.9	570.9	570.9	573.0	575.1	577.3
7.5°	449.7	450.7	451.8	452.9	452.9	452.9	451.8	451.8	452.9	452.9	453.9
10°	344.4	348.7	351.9	355.1	352.9	349.8	347.6	344.4	344.4	344.4	343.4
12.5°	260.5	261.5	263.6	264.7	263.6	263.6	262.6	261.5	262.6	264.7	265.8
15°	206.2	206.2	207.3	207.3	208.4	209.4	209.4	210.5	212.6	213.7	215.8
17.5°	171.2	172.2	172.2	173.3	173.3	174.3	174.3	174.3	176.5	178.6	181.8
20°	154.1	154.1	154.1	154.1	154.1	153.1	153.1	152.0	153.1	155.2	156.3
22.5°	138.2	139.3	139.3	139.3	138.2	137.1	135.0	133.9	133.9	135.0	135.0
25°	121.2	120.1	120.1	119.1	119.1	120.1	120.1	120.1	121.2	121.2	122.3
27.5°	111.6	110.6	110.6	109.5	109.5	110.6	110.6	110.6	110.6	110.6	110.6
30°	104.2	104.2	103.1	102.1	103.1	103.1	104.2	104.2	105.2	105.2	106.3
32.5°	98.9	97.8	97.8	96.7	97.8	97.8	98.9	98.9	99.9	101.0	101.0
35°	91.4	91.4	91.4	91.4	91.4	91.4	90.4	90.4	90.4	90.4	90.4
37.5°	87.2	87.2	86.1	85.0	85.0	85.0	85.0	85.0	84.0	82.9	81.9
40°	84.0	82.9	82.9	81.9	80.8	80.8	79.7	78.7	78.7	77.6	77.6
42.5°	79.7	78.7	78.7	77.6	76.5	76.5	75.5	74.4	74.4	74.4	73.4
45°	74.4	74.4	73.4	72.3	72.3	72.3	71.2	71.2	71.2	71.2	70.2
47.5°	69.1	69.1	68.0	68.0	68.0	68.0	67.0	67.0	67.0	67.0	67.0
50°	65.9	65.9	65.9	65.9	65.9	65.9	64.8	64.8	64.8	64.8	64.8
52.5°	62.7	62.7	62.7	62.7	62.7	62.7	62.7	62.7	62.7	62.7	62.7
55°	61.7	61.7	61.7	61.7	61.7	61.7	60.6	60.6	60.6	61.7	61.7
57.5°	59.5	59.5	58.5	58.5	58.5	58.5	58.5	58.5	58.5	58.5	58.5
60°	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4
62.5°	54.2	54.2	54.2	54.2	54.2	55.3	55.3	55.3	55.3	55.3	54.2
65°	50.0	51.0	51.0	51.0	51.0	51.0	51.0	51.0	51.0	51.0	51.0
67.5°	47.8	47.8	47.8	47.8	47.8	47.8	47.8	47.8	47.8	47.8	47.8
70°	44.6	44.6	43.6	43.6	43.6	44.6	44.6	44.6	44.6	44.6	44.6
72.5°	40.4	40.4	40.4	40.4	40.4	40.4	40.4	40.4	40.4	41.5	41.5
75°	36.1	36.1	36.1	36.1	36.1	36.1	36.1	36.1	36.1	36.1	36.1
77.5°	31.9	31.9	30.8	30.8	30.8	31.9	31.9	31.9	31.9	33.0	33.0
80°	26.6	26.6	26.6	26.6	26.6	26.6	26.6	26.6	26.6	27.6	27.6
82.5°	21.3	21.3	21.3	21.3	21.3	21.3	21.3	21.3	21.3	22.3	22.3
85°	15.9	17.0	17.0	17.0	17.0	17.0	17.0	17.0	17.0	18.1	18.1
87.5°	10.6	10.6	10.6	10.6	10.6	10.6	9.6	9.6	9.6	9.6	8.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671790  
 CATALOG NUMBER: CCP-SA-1B-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671790  
 CATALOG NUMBER: CCP-SA-1B-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4
2.5°	677.2	678.2	679.3	679.3	680.4	681.4	681.4	685.7	689.9	692.1	694.2
5°	579.4	578.3	578.3	577.3	576.2	579.4	582.6	588.9	595.3	596.4	598.5
7.5°	453.9	455.0	456.1	456.1	457.1	453.9	449.7	450.7	451.8	457.1	461.4
10°	343.4	344.4	345.5	345.5	346.6	345.5	343.4	346.6	349.8	354.0	359.3
12.5°	266.8	270.0	273.2	275.3	278.5	280.7	281.7	286.0	289.2	294.5	299.8
15°	217.9	220.1	222.2	224.3	226.4	228.6	230.7	234.9	239.2	245.6	251.9
17.5°	183.9	183.9	185.0	185.0	185.0	187.1	189.2	191.4	192.4	198.8	205.2
20°	157.3	156.3	155.2	154.1	153.1	155.2	156.3	157.3	158.4	162.7	165.8
22.5°	135.0	135.0	136.1	136.1	136.1	135.0	132.9	133.9	133.9	136.1	139.3
25°	122.3	122.3	122.3	121.2	121.2	122.3	123.3	123.3	122.3	123.3	124.4
27.5°	110.6	111.6	111.6	112.7	112.7	113.7	113.7	113.7	113.7	114.8	115.9
30°	106.3	106.3	107.4	107.4	107.4	108.4	109.5	109.5	109.5	110.6	112.7
32.5°	102.1	103.1	104.2	105.2	106.3	107.4	107.4	108.4	108.4	109.5	110.6
35°	90.4	89.3	89.3	88.2	87.2	87.2	87.2	87.2	86.1	87.2	87.2
37.5°	80.8	80.8	80.8	79.7	79.7	80.8	80.8	80.8	80.8	81.9	81.9
40°	76.5	76.5	76.5	76.5	76.5	76.5	76.5	77.6	77.6	78.7	79.7
42.5°	73.4	73.4	73.4	73.4	73.4	74.4	74.4	74.4	74.4	75.5	75.5
45°	70.2	70.2	70.2	70.2	70.2	70.2	70.2	71.2	71.2	72.3	73.4
47.5°	67.0	67.0	67.0	67.0	67.0	68.0	69.1	69.1	69.1	70.2	70.2
50°	64.8	64.8	64.8	64.8	64.8	65.9	65.9	67.0	67.0	68.0	69.1
52.5°	62.7	62.7	62.7	62.7	62.7	63.8	63.8	64.8	64.8	65.9	67.0
55°	61.7	61.7	61.7	60.6	60.6	61.7	61.7	62.7	62.7	63.8	63.8
57.5°	58.5	58.5	58.5	58.5	58.5	58.5	58.5	59.5	59.5	60.6	61.7
60°	57.4	57.4	56.3	56.3	55.3	56.3	56.3	57.4	57.4	58.5	58.5
62.5°	54.2	54.2	54.2	53.2	53.2	54.2	54.2	54.2	54.2	55.3	56.3
65°	51.0	51.0	51.0	50.0	50.0	51.0	51.0	51.0	51.0	52.1	53.2
67.5°	47.8	47.8	47.8	46.8	46.8	46.8	46.8	47.8	47.8	48.9	50.0
70°	44.6	44.6	44.6	43.6	43.6	43.6	42.5	43.6	44.6	45.7	45.7
72.5°	41.5	41.5	41.5	40.4	40.4	40.4	39.3	40.4	40.4	41.5	41.5
75°	36.1	36.1	36.1	36.1	36.1	36.1	35.1	35.1	35.1	36.1	36.1
77.5°	33.0	33.0	33.0	31.9	31.9	31.9	30.8	30.8	30.8	31.9	31.9
80°	27.6	27.6	27.6	26.6	26.6	26.6	25.5	25.5	25.5	26.6	26.6
82.5°	22.3	22.3	22.3	21.3	21.3	21.3	20.2	20.2	20.2	21.3	21.3
85°	18.1	18.1	18.1	18.1	18.1	18.1	17.0	17.0	17.0	18.1	19.1
87.5°	8.5	8.5	9.6	9.6	9.6	9.6	8.5	8.5	7.4	7.4	8.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671790  
 CATALOG NUMBER: CCP-SA-1B-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671790  
 CATALOG NUMBER: CCP-SA-1B-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4
2.5°	696.3	698.4	703.8	708.0	713.3	717.6	720.8	725.0	728.2	731.4	733.5
5°	599.6	600.6	606.0	611.3	615.5	620.8	628.3	635.7	643.2	650.6	655.9
7.5°	466.7	470.9	477.3	484.8	491.1	497.5	505.0	513.5	520.9	528.3	535.8
10°	363.6	367.8	374.2	380.6	385.9	392.3	400.8	409.3	417.8	426.3	434.8
12.5°	305.1	310.4	317.9	325.3	331.7	339.1	349.8	359.3	370.0	379.5	390.1
15°	257.3	263.6	273.2	283.8	293.4	303.0	313.6	324.2	333.8	344.4	355.1
17.5°	211.6	217.9	226.4	236.0	244.5	253.0	265.8	277.5	290.2	301.9	313.6
20°	170.1	173.3	181.8	190.3	198.8	207.3	216.9	226.4	236.0	245.6	260.5
22.5°	141.4	143.5	147.8	151.0	155.2	158.4	168.0	177.5	186.0	195.6	209.4
25°	124.4	125.4	128.6	130.8	133.9	136.1	142.5	147.8	154.1	159.5	172.2
27.5°	115.9	116.9	118.0	119.1	120.1	121.2	125.4	129.7	132.9	137.1	148.8
30°	113.7	114.8	118.0	120.1	123.3	125.4	127.6	129.7	131.8	133.9	141.4
32.5°	111.6	112.7	112.7	111.6	111.6	110.6	112.7	113.7	115.9	116.9	123.3
35°	88.2	88.2	89.3	90.4	91.4	92.5	95.7	97.8	101.0	103.1	108.4
37.5°	82.9	82.9	84.0	86.1	87.2	88.2	90.4	92.5	94.6	96.7	102.1
40°	79.7	80.8	81.9	82.9	84.0	85.0	87.2	88.2	90.4	91.4	95.7
42.5°	76.5	76.5	77.6	79.7	80.8	81.9	84.0	85.0	87.2	88.2	92.5
45°	74.4	75.5	76.5	77.6	77.6	78.7	80.8	82.9	84.0	86.1	90.4
47.5°	71.2	71.2	73.4	74.4	76.5	77.6	79.7	80.8	82.9	84.0	88.2
50°	69.1	70.2	72.3	73.4	75.5	76.5	79.7	81.9	85.0	87.2	89.3
52.5°	67.0	68.0	70.2	71.2	73.4	74.4	78.7	82.9	86.1	90.4	90.4
55°	64.8	64.8	67.0	70.2	72.3	74.4	76.5	79.7	81.9	84.0	84.0
57.5°	61.7	62.7	64.8	68.0	70.2	72.3	74.4	76.5	77.6	79.7	78.7
60°	59.5	59.5	62.7	65.9	69.1	72.3	72.3	72.3	71.2	71.2	71.2
62.5°	56.3	57.4	61.7	67.0	71.2	75.5	72.3	69.1	65.9	62.7	63.8
65°	54.2	55.3	57.4	60.6	62.7	64.8	62.7	61.7	59.5	57.4	58.5
67.5°	50.0	51.0	52.1	52.1	53.2	53.2	53.2	53.2	53.2	53.2	54.2
70°	46.8	46.8	46.8	47.8	47.8	47.8	47.8	47.8	47.8	47.8	48.9
72.5°	42.5	42.5	42.5	42.5	42.5	42.5	42.5	42.5	42.5	42.5	43.6
75°	37.2	37.2	37.2	37.2	37.2	37.2	37.2	37.2	37.2	37.2	38.3
77.5°	33.0	33.0	33.0	33.0	33.0	33.0	33.0	33.0	31.9	31.9	33.0
80°	27.6	27.6	27.6	27.6	26.6	26.6	26.6	26.6	26.6	26.6	27.6
82.5°	22.3	22.3	22.3	22.3	21.3	21.3	21.3	21.3	20.2	20.2	21.3
85°	20.2	21.3	21.3	22.3	22.3	22.3	21.3	20.2	19.1	18.1	18.1
87.5°	8.5	8.5	8.5	8.5	7.4	7.4	7.4	7.4	7.4	7.4	7.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671790  
 CATALOG NUMBER: CCP-SA-1B-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671790  
 CATALOG NUMBER: CCP-SA-1B-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4
2.5°	736.7	738.8	741.0	744.2	748.4	751.6	754.8	761.2	768.6	775.0	781.4
5°	661.2	666.5	671.9	678.2	684.6	689.9	696.3	709.1	721.8	733.5	746.3
7.5°	542.2	549.6	556.0	566.6	576.2	586.8	596.4	612.3	627.2	643.2	658.0
10°	443.3	451.8	460.3	474.1	489.0	502.8	516.7	529.4	543.2	556.0	568.7
12.5°	400.8	410.3	421.0	429.5	439.1	447.6	456.1	470.9	485.8	500.7	515.6
15°	365.7	376.3	387.0	397.6	407.2	417.8	427.4	440.1	453.9	466.7	479.4
17.5°	325.3	335.9	347.6	359.3	371.0	382.7	394.4	412.5	430.5	447.6	465.6
20°	274.3	289.2	303.0	318.9	334.9	350.8	366.8	385.9	405.0	423.1	442.2
22.5°	223.2	237.1	250.9	270.0	289.2	307.2	326.4	351.9	376.3	401.8	426.3
25°	186.0	198.8	211.6	232.8	253.0	274.3	294.5	325.3	355.1	385.9	415.7
27.5°	160.5	172.2	183.9	206.2	228.6	249.8	272.1	306.2	339.1	373.1	406.1
30°	148.8	156.3	163.7	185.0	206.2	226.4	247.7	280.7	313.6	346.6	379.5
32.5°	129.7	136.1	142.5	161.6	180.7	198.8	217.9	251.9	284.9	318.9	351.9
35°	114.8	120.1	125.4	143.5	160.5	178.6	195.6	229.6	263.6	297.7	331.7
37.5°	106.3	111.6	115.9	131.8	148.8	164.8	180.7	214.7	247.7	281.7	314.7
40°	99.9	103.1	107.4	123.3	138.2	154.1	169.0	199.9	231.8	262.6	293.4
42.5°	95.7	99.9	103.1	116.9	131.8	145.6	159.5	189.2	219.0	247.7	277.5
45°	94.6	98.9	103.1	114.8	126.5	137.1	148.8	177.5	206.2	234.9	263.6
47.5°	92.5	95.7	99.9	109.5	118.0	127.6	136.1	164.8	193.5	221.1	249.8
50°	91.4	92.5	94.6	103.1	111.6	120.1	128.6	157.3	186.0	214.7	243.4
52.5°	90.4	90.4	90.4	97.8	105.2	111.6	119.1	147.8	177.5	206.2	234.9
55°	84.0	82.9	82.9	90.4	96.7	104.2	110.6	139.3	168.0	195.6	224.3
57.5°	77.6	76.5	75.5	81.9	88.2	94.6	101.0	129.7	159.5	188.2	216.9
60°	71.2	70.2	70.2	76.5	81.9	88.2	93.6	123.3	152.0	181.8	210.5
62.5°	63.8	64.8	64.8	70.2	76.5	81.9	87.2	116.9	147.8	177.5	207.3
65°	58.5	59.5	59.5	65.9	72.3	78.7	85.0	113.7	143.5	172.2	200.9
67.5°	54.2	55.3	55.3	62.7	69.1	76.5	82.9	108.4	135.0	160.5	186.0
70°	50.0	50.0	51.0	58.5	65.9	73.4	80.8	103.1	125.4	146.7	169.0
72.5°	44.6	45.7	46.8	54.2	60.6	68.0	74.4	94.6	114.8	135.0	155.2
75°	39.3	40.4	41.5	47.8	54.2	60.6	67.0	86.1	104.2	123.3	141.4
77.5°	35.1	36.1	37.2	42.5	47.8	53.2	58.5	72.3	87.2	101.0	114.8
80°	28.7	28.7	29.8	34.0	38.3	41.5	45.7	55.3	64.8	73.4	82.9
82.5°	21.3	22.3	22.3	25.5	27.6	30.8	33.0	38.3	42.5	47.8	52.1
85°	18.1	17.0	17.0	19.1	20.2	22.3	23.4	26.6	28.7	31.9	34.0
87.5°	7.4	6.4	6.4	7.4	9.6	10.6	11.7	11.7	12.8	12.8	12.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671790  
 CATALOG NUMBER: CCP-SA-1B-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671790

CATALOG NUMBER: CCP-SA-1B-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4
2.5°	784.5	786.7	789.9	792.0	797.3	801.6	806.9	811.1	814.3	819.6	817.5
5°	755.8	765.4	775.0	784.5	792.0	799.4	805.8	813.3	821.8	837.7	842.0
7.5°	670.8	683.6	695.3	708.0	722.9	737.8	752.7	767.5	781.4	801.6	814.3
10°	586.8	604.9	621.9	640.0	653.8	667.6	680.4	694.2	713.3	733.5	756.9
12.5°	533.7	551.7	569.8	587.9	608.1	627.2	647.4	666.5	684.6	700.6	727.1
15°	498.6	518.8	537.9	557.1	581.5	604.9	629.3	652.7	679.3	700.6	718.6
17.5°	490.1	514.5	537.9	562.4	587.9	613.4	638.9	664.4	691.0	722.9	746.3
20°	475.2	508.2	541.1	574.1	607.0	638.9	671.9	703.8	738.8	777.1	787.7
22.5°	466.7	506.0	546.4	585.8	630.4	676.1	720.8	765.4	802.6	831.3	863.2
25°	465.6	514.5	564.5	613.4	669.7	725.0	781.4	836.6	884.5	913.2	938.7
27.5°	464.6	524.1	582.6	641.0	710.1	778.2	847.3	915.3	960.0	1001.4	1022.7
30°	451.8	523.0	595.3	666.5	744.2	821.8	899.4	977.0	1022.7	1051.4	1062.0
32.5°	435.9	519.8	603.8	687.8	776.0	864.3	951.5	1039.7	1075.8	1100.3	1091.8
35°	423.1	515.6	607.0	698.4	792.0	886.6	980.2	1073.7	1125.8	1159.8	1146.0
37.5°	411.4	508.2	604.9	701.6	811.1	920.6	1030.1	1139.6	1189.6	1225.7	1209.8
40°	397.6	500.7	604.9	708.0	833.5	957.8	1083.3	1207.7	1272.5	1303.3	1278.9
42.5°	385.9	493.3	601.7	709.1	843.0	977.0	1110.9	1244.9	1317.2	1360.7	1329.9
45°	371.0	478.4	584.7	692.1	839.8	987.6	1134.3	1282.1	1366.1	1400.1	1357.5
47.5°	355.1	461.4	566.6	671.9	829.2	986.5	1143.9	1301.2	1378.8	1419.2	1379.9
50°	349.8	456.1	561.3	667.6	837.7	1008.9	1179.0	1349.0	1405.4	1438.3	1386.3
52.5°	348.7	461.4	575.1	687.8	859.0	1029.1	1200.2	1370.3	1416.0	1451.1	1404.3
55°	345.5	467.8	588.9	710.1	888.7	1068.4	1247.0	1425.6	1471.3	1496.8	1461.7
57.5°	348.7	480.5	611.3	743.1	927.0	1110.9	1294.8	1478.7	1534.0	1552.1	1544.6
60°	350.8	491.1	630.4	770.7	950.4	1130.0	1309.7	1489.4	1546.8	1591.4	1599.9
62.5°	345.5	483.7	620.8	759.0	921.7	1084.3	1247.0	1409.6	1504.3	1570.2	1608.4
65°	329.6	457.1	585.8	713.3	863.2	1014.2	1164.1	1314.0	1413.9	1511.7	1542.5
67.5°	294.5	402.9	511.3	619.8	750.5	881.3	1011.0	1141.7	1267.2	1361.8	1404.3
70°	255.1	340.2	426.3	511.3	630.4	749.5	868.5	987.6	1098.2	1202.3	1242.7
72.5°	222.2	288.1	355.1	421.0	506.0	590.0	675.1	759.0	889.8	994.0	1033.3
75°	189.2	237.1	283.8	331.7	390.1	448.6	506.0	564.5	657.0	750.5	789.9
77.5°	145.6	177.5	208.4	239.2	279.6	318.9	359.3	398.7	463.5	533.7	553.9
80°	101.0	119.1	136.1	154.1	186.0	217.9	249.8	281.7	324.2	363.6	394.4
82.5°	62.7	74.4	85.0	95.7	121.2	146.7	171.2	196.7	213.7	215.8	246.6
85°	40.4	47.8	54.2	60.6	75.5	91.4	106.3	121.2	108.4	101.0	120.1
87.5°	15.9	20.2	23.4	26.6	25.5	24.5	23.4	22.3	19.1	17.0	21.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671790  
 CATALOG NUMBER: CCP-SA-1B-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671790

CATALOG NUMBER: CCP-SA-1B-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4
2.5°	819.6	822.8	826.0	828.1	831.3	832.4	833.5	833.5	834.5	835.6	837.7
5°	859.0	865.3	871.7	877.0	883.4	888.7	893.0	898.3	902.6	902.6	901.5
7.5°	826.0	842.0	857.9	873.8	889.8	901.5	912.1	923.8	934.4	936.6	938.7
10°	782.4	799.4	815.4	832.4	848.3	866.4	883.4	900.4	918.5	921.7	925.9
12.5°	742.0	762.2	782.4	801.6	821.8	834.5	847.3	859.0	871.7	880.2	888.7
15°	741.0	758.0	775.0	790.9	807.9	815.4	822.8	829.2	836.6	836.6	837.7
17.5°	765.4	776.0	786.7	796.2	806.9	807.9	810.1	811.1	812.2	809.0	805.8
20°	813.3	817.5	821.8	826.0	830.3	822.8	816.4	809.0	801.6	793.1	785.6
22.5°	883.4	873.8	864.3	854.7	845.1	832.4	818.6	805.8	792.0	781.4	770.7
25°	949.3	937.6	925.9	914.2	902.6	874.9	847.3	818.6	790.9	779.2	767.5
27.5°	1037.6	1019.5	1001.4	983.3	965.3	928.1	890.9	853.6	816.4	796.2	777.1
30°	1058.8	1038.6	1018.4	997.2	977.0	940.8	905.7	869.6	833.5	810.1	787.7
32.5°	1089.7	1066.3	1042.9	1019.5	996.1	961.0	925.9	889.8	854.7	833.5	811.1
35°	1140.7	1114.1	1087.5	1059.9	1033.3	997.2	962.1	925.9	889.8	865.3	842.0
37.5°	1184.3	1153.4	1122.6	1091.8	1060.9	1029.1	996.1	964.2	931.3	906.8	883.4
40°	1233.2	1199.1	1165.1	1132.2	1098.2	1068.4	1038.6	1007.8	978.0	958.9	939.8
42.5°	1275.7	1234.2	1193.8	1153.4	1112.0	1091.8	1072.6	1052.4	1032.2	1022.7	1012.0
45°	1305.5	1267.2	1227.9	1189.6	1151.3	1136.4	1121.5	1106.7	1091.8	1101.3	1110.9
47.5°	1318.2	1287.4	1257.6	1227.9	1197.0	1202.3	1207.7	1211.9	1217.2	1230.0	1243.8
50°	1329.9	1312.9	1294.8	1277.8	1259.7	1279.9	1299.1	1319.3	1339.5	1366.1	1392.6
52.5°	1353.3	1343.7	1335.2	1325.7	1316.1	1351.2	1386.3	1421.3	1456.4	1486.2	1515.9
55°	1423.5	1416.0	1408.6	1400.1	1392.6	1442.6	1491.5	1541.5	1591.4	1622.3	1653.1
57.5°	1520.2	1515.9	1510.6	1506.4	1501.1	1550.0	1597.8	1645.6	1694.5	1724.3	1755.1
60°	1593.6	1594.6	1594.6	1595.7	1595.7	1632.9	1670.1	1708.4	1745.6	1771.1	1797.7
62.5°	1632.9	1630.8	1628.6	1626.5	1624.4	1655.2	1686.0	1716.9	1747.7	1766.8	1786.0
65°	1590.4	1602.1	1613.7	1625.4	1637.1	1641.4	1644.6	1648.8	1652.0	1663.7	1675.4
67.5°	1447.9	1471.3	1493.6	1517.0	1539.3	1523.4	1508.5	1492.6	1476.6	1479.8	1481.9
70°	1289.5	1316.1	1343.7	1370.3	1396.9	1359.7	1322.5	1284.2	1247.0	1234.2	1221.5
72.5°	1087.5	1110.9	1135.4	1158.8	1182.1	1136.4	1091.8	1046.1	1000.4	978.0	955.7
75°	831.3	859.0	887.7	915.3	942.9	891.9	839.8	788.8	736.7	721.8	708.0
77.5°	606.0	638.9	671.9	704.8	737.8	692.1	646.3	599.6	553.9	545.4	536.9
80°	441.2	466.7	491.1	516.7	541.1	514.5	488.0	461.4	434.8	433.7	432.7
82.5°	297.7	320.0	341.2	363.6	384.8	374.2	364.6	354.0	343.4	354.0	365.7
85°	153.1	183.9	215.8	246.6	277.5	274.3	272.1	269.0	265.8	279.6	292.3
87.5°	30.8	57.4	84.0	109.5	136.1	129.7	123.3	115.9	109.5	113.7	116.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671790  
 CATALOG NUMBER: CCP-SA-1B-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671790

CATALOG NUMBER: CCP-SA-1B-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4
2.5°	838.8	839.8	839.8	839.8	839.8	839.8	837.7	836.6	834.5	832.4	829.2
5°	901.5	900.4	896.2	891.9	886.6	882.4	879.2	874.9	871.7	867.5	861.1
7.5°	940.8	942.9	935.5	929.1	921.7	914.2	906.8	899.4	891.9	884.5	869.6
10°	929.1	932.3	928.1	923.8	918.5	914.2	905.7	896.2	887.7	878.1	860.0
12.5°	896.2	904.7	902.6	900.4	898.3	896.2	890.9	884.5	879.2	872.8	852.6
15°	837.7	837.7	838.8	839.8	839.8	840.9	842.0	843.0	844.1	845.1	833.5
17.5°	802.6	799.4	799.4	799.4	799.4	799.4	803.7	809.0	813.3	817.5	814.3
20°	777.1	769.7	768.6	768.6	767.5	766.5	773.9	782.4	789.9	797.3	801.6
22.5°	760.1	749.5	748.4	747.3	746.3	745.2	754.8	764.4	773.9	783.5	798.4
25°	755.8	744.2	745.2	746.3	746.3	747.3	754.8	762.2	769.7	777.1	802.6
27.5°	756.9	737.8	738.8	739.9	739.9	741.0	752.7	763.3	775.0	785.6	817.5
30°	764.4	742.0	739.9	737.8	735.6	733.5	749.5	765.4	781.4	797.3	821.8
32.5°	789.9	768.6	763.3	758.0	752.7	747.3	766.5	784.5	803.7	821.8	842.0
35°	817.5	794.1	792.0	789.9	786.7	784.5	801.6	819.6	836.6	853.6	871.7
37.5°	859.0	835.6	833.5	830.3	828.1	824.9	844.1	862.2	881.3	899.4	915.3
40°	920.6	901.5	900.4	900.4	899.4	898.3	913.2	929.1	944.0	958.9	969.5
42.5°	1002.5	992.9	996.1	1000.4	1003.5	1006.7	1018.4	1031.2	1042.9	1054.6	1051.4
45°	1120.5	1130.0	1131.1	1132.2	1133.2	1134.3	1137.5	1141.7	1144.9	1148.1	1135.4
47.5°	1256.6	1269.3	1275.7	1282.1	1287.4	1293.8	1289.5	1284.2	1279.9	1274.6	1242.7
50°	1418.1	1444.7	1443.7	1442.6	1440.5	1439.4	1430.9	1422.4	1412.8	1404.3	1357.5
52.5°	1545.7	1575.5	1580.8	1586.1	1591.4	1596.7	1580.8	1564.8	1547.8	1531.9	1473.4
55°	1682.8	1713.7	1714.7	1715.8	1715.8	1716.9	1694.5	1672.2	1648.8	1626.5	1565.9
57.5°	1784.9	1814.7	1811.5	1809.4	1806.2	1803.0	1776.4	1749.8	1723.2	1696.7	1636.1
60°	1823.2	1848.7	1842.3	1835.9	1828.5	1822.1	1801.9	1781.7	1760.5	1740.3	1681.8
62.5°	1805.1	1824.2	1814.7	1806.2	1796.6	1787.0	1761.5	1734.9	1709.4	1682.8	1640.3
65°	1686.0	1697.7	1685.0	1673.3	1661.6	1648.8	1627.6	1606.3	1584.0	1562.7	1534.0
67.5°	1485.1	1487.2	1486.2	1485.1	1484.1	1483.0	1452.2	1421.3	1389.4	1358.6	1356.5
70°	1209.8	1197.0	1199.1	1202.3	1204.5	1206.6	1183.2	1160.9	1137.5	1114.1	1124.7
72.5°	933.4	911.1	916.4	922.7	928.1	933.4	914.2	896.2	877.0	857.9	872.8
75°	693.1	679.3	684.6	691.0	696.3	701.6	694.2	686.7	678.2	670.8	684.6
77.5°	528.3	519.8	520.9	520.9	522.0	522.0	523.0	525.2	526.2	527.3	542.2
80°	430.5	429.5	428.4	427.4	425.2	424.2	434.8	445.4	456.1	466.7	474.1
82.5°	376.3	387.0	380.6	375.3	368.9	362.5	372.1	381.6	391.2	400.8	397.6
85°	306.2	318.9	307.2	295.5	282.8	271.1	279.6	287.0	295.5	303.0	298.7
87.5°	121.2	124.4	105.2	87.2	68.0	48.9	77.6	105.2	133.9	161.6	165.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671790  
 CATALOG NUMBER: CCP-SA-1B-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671790

CATALOG NUMBER: CCP-SA-1B-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4	765.4
2.5°	826.0	821.8	818.6	817.5	815.4	814.3	812.2	810.1	806.9	804.7	801.6
5°	853.6	847.3	839.8	829.2	819.6	809.0	798.4	788.8	779.2	768.6	759.0
7.5°	854.7	839.8	824.9	811.1	796.2	782.4	767.5	754.8	741.0	727.1	714.4
10°	843.0	824.9	806.9	788.8	771.8	753.7	735.6	720.8	704.8	688.9	674.0
12.5°	833.5	813.3	793.1	771.8	751.6	730.3	709.1	694.2	679.3	664.4	649.5
15°	821.8	809.0	797.3	778.2	759.0	739.9	720.8	700.6	681.4	661.2	641.0
17.5°	812.2	809.0	805.8	793.1	780.3	766.5	753.7	733.5	713.3	692.1	671.9
20°	806.9	811.1	815.4	809.0	802.6	795.2	788.8	773.9	759.0	743.1	728.2
22.5°	813.3	829.2	844.1	845.1	847.3	848.3	849.4	835.6	821.8	806.9	793.1
25°	828.1	853.6	879.2	893.0	906.8	921.7	935.5	927.0	918.5	910.0	901.5
27.5°	848.3	880.2	912.1	932.3	951.5	971.7	991.8	990.8	989.7	987.6	986.5
30°	845.1	869.6	894.0	918.5	942.9	967.4	991.8	1004.6	1016.3	1029.1	1041.8
32.5°	863.2	883.4	904.7	930.2	955.7	982.3	1007.8	1034.4	1059.9	1086.5	1113.0
35°	890.9	908.9	928.1	955.7	984.4	1012.0	1040.8	1072.6	1105.6	1138.6	1170.4
37.5°	932.3	948.3	965.3	988.7	1013.1	1036.5	1060.9	1107.7	1154.5	1202.3	1249.1
40°	980.2	990.8	1001.4	1023.7	1046.1	1068.4	1090.7	1149.2	1207.7	1266.1	1324.6
42.5°	1049.3	1046.1	1042.9	1060.9	1080.1	1098.2	1117.3	1170.4	1223.6	1276.8	1329.9
45°	1122.6	1109.9	1097.1	1105.6	1115.2	1123.7	1133.2	1187.5	1241.7	1297.0	1351.2
47.5°	1210.8	1179.0	1147.1	1139.6	1132.2	1123.7	1116.2	1174.7	1233.2	1292.7	1351.2
50°	1310.8	1262.9	1216.2	1197.0	1176.8	1157.7	1137.5	1185.3	1234.2	1283.1	1331.0
52.5°	1415.0	1355.4	1297.0	1267.2	1237.4	1206.6	1176.8	1217.2	1258.7	1300.1	1340.5
55°	1504.3	1443.7	1382.0	1346.9	1311.8	1276.8	1241.7	1282.1	1322.5	1362.9	1403.3
57.5°	1575.5	1514.9	1454.3	1421.3	1387.3	1354.4	1320.3	1358.6	1397.9	1437.3	1475.5
60°	1624.4	1565.9	1507.4	1475.5	1443.7	1411.8	1379.9	1425.6	1471.3	1518.1	1563.8
62.5°	1598.9	1556.3	1513.8	1500.0	1486.2	1471.3	1457.5	1501.1	1543.6	1587.2	1630.8
65°	1505.3	1476.6	1447.9	1461.7	1476.6	1490.4	1505.3	1534.0	1562.7	1592.5	1621.2
67.5°	1353.3	1351.2	1348.0	1378.8	1409.6	1441.5	1472.4	1491.5	1509.6	1528.7	1547.8
70°	1135.4	1147.1	1157.7	1210.8	1264.0	1317.2	1370.3	1377.7	1385.2	1392.6	1400.1
72.5°	888.7	903.6	919.6	989.7	1058.8	1129.0	1199.1	1194.9	1190.6	1185.3	1181.1
75°	699.5	713.3	728.2	793.1	857.9	922.7	987.6	969.5	952.5	934.4	916.4
77.5°	558.1	573.0	588.9	649.5	710.1	771.8	832.4	788.8	745.2	701.6	658.0
80°	480.5	488.0	494.3	535.8	576.2	617.6	659.1	614.5	568.7	523.0	478.4
82.5°	394.4	390.1	387.0	411.4	435.9	460.3	484.8	442.2	399.7	356.1	313.6
85°	294.5	290.2	286.0	298.7	311.5	325.3	338.1	289.2	240.3	190.3	141.4
87.5°	171.2	175.4	179.7	193.5	207.3	222.2	236.0	186.0	136.1	85.0	35.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671790  
 CATALOG NUMBER: CCP-SA-1B-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671790  
 CATALOG NUMBER: CCP-SA-1B-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
0°	765.4	765.4
2.5°	795.2	789.9
5°	751.6	744.2
7.5°	703.8	694.2
10°	660.2	647.4
12.5°	632.5	616.6
15°	621.9	602.8
17.5°	653.8	635.7
20°	702.7	678.2
22.5°	762.2	732.5
25°	865.3	829.2
27.5°	949.3	912.1
30°	1001.4	961.0
32.5°	1058.8	1005.7
35°	1118.4	1067.3
37.5°	1190.6	1133.2
40°	1265.1	1205.5
42.5°	1290.6	1252.3
45°	1315.0	1278.9
47.5°	1320.3	1290.6
50°	1325.7	1321.4
52.5°	1340.5	1339.5
55°	1404.3	1405.4
57.5°	1483.0	1489.4
60°	1555.3	1547.8
62.5°	1592.5	1554.2
65°	1567.0	1513.8
67.5°	1490.4	1433.0
70°	1322.5	1244.9
72.5°	1113.0	1045.0
75°	857.9	800.5
77.5°	610.2	562.4
80°	429.5	381.6
82.5°	275.3	237.1
85°	124.4	108.4
87.5°	35.1	34.0
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P671790  
CATALOG NUMBER: CCP-SA-1B-727-U-SLR

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)