

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P671803

Luminaire Tested: **CCP-SA-1D-730-U-SLR**

Issue Date: 04/16/2023



Test Information

Test Method: LM-79-08
Report Number: P671803
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/16/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCP-SA-1D-730-U-SLR
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @800mA w/ SLR distribution lens
Light Source: (16) 3000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4214.4 lumens
Efficiency: N/A
Efficacy: 95.8 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2

Input Watts (W): 44
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P671803
 CATALOG NUMBER: CCP-SA-1D-730-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 6 fc
 Type IV - Short - N/A

REPORT NUMBER: P671803
CATALOG NUMBER: CCP-SA-1D-730-U-SLR

Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P671803
 CATALOG NUMBER: CCP-SA-1D-730-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	867.1	0.0	867.1
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	3347.2	0.0	3347.2
	% Fixture	79.4	0.0	79.4
Total	Lumens	4214.4	0.0	4214.4
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.6	2.5
10°-20°	220.8	5.2
20°-30°	323.0	7.7
30°-40°	455.1	10.8
40°-50°	625.4	14.8
50°-60°	852.4	20.2
60°-70°	932.9	22.1
70°-80°	538.8	12.8
80°-90°	161.5	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4214.4	100.0
0°-180°	4214.4	100.0



REPORT NUMBER: P671803


CATALOG NUMBER: CCP-SA-1D-730-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	432.8	10.3			
FM (30°-60°)	1537.9	36.5			
FH (60°-80°)	1239.3	29.4			G1/1800
FVH (80°-90°)	137.2	3.3			G2/225
BL (0°-30°)	215.6	5.1	B1/500		
BM (30°-60°)	394.9	9.4	B1/1000		
BH (60°-80°)	232.4	5.5	B1/500		G1/500
BVH (80°-90°)	24.3	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P671803

CATALOG NUMBER: CCP-SA-1D-730-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8
2.5°	1388.8	1381.3	1375.7	1370.1	1362.6	1357.0	1349.5	1342.1	1332.7	1325.2	1315.9
5°	1308.4	1286.0	1263.6	1250.5	1235.5	1222.4	1207.5	1190.7	1173.8	1155.1	1138.3
7.5°	1220.6	1192.5	1164.5	1142.1	1117.8	1095.3	1071.0	1050.5	1029.9	1009.4	988.8
10°	1138.3	1112.2	1086.0	1058.0	1028.0	1000.0	970.1	942.1	914.0	886.0	858.0
12.5°	1084.1	1052.3	1022.4	990.7	960.8	929.0	897.2	871.0	844.9	816.8	790.7
15°	1059.8	1029.9	1001.9	970.1	938.3	906.5	874.8	844.9	816.8	786.9	757.0
17.5°	1117.8	1074.8	1031.8	990.7	949.5	908.4	867.3	829.9	792.5	755.1	717.8
20°	1192.5	1138.3	1086.0	1035.5	983.2	932.7	880.4	828.0	775.7	723.4	671.0
22.5°	1287.9	1226.2	1166.4	1100.9	1033.7	968.2	900.9	835.5	770.1	702.8	637.4
25°	1458.0	1385.1	1312.2	1218.7	1123.4	1029.9	934.6	848.6	764.5	678.5	592.5
27.5°	1603.8	1504.7	1407.5	1295.3	1183.2	1071.0	958.9	859.8	762.6	663.6	564.5
30°	1689.7	1592.5	1495.3	1358.9	1224.3	1087.9	951.4	841.1	732.7	622.4	512.2
32.5°	1768.2	1659.8	1551.4	1401.9	1250.5	1100.9	949.5	828.0	708.4	586.9	465.4
35°	1876.6	1757.0	1639.3	1465.4	1291.6	1117.8	943.9	818.7	691.6	566.4	439.3
37.5°	1992.5	1844.9	1699.1	1506.6	1314.0	1121.5	929.0	805.6	682.2	558.9	435.5
40°	2119.6	1940.2	1762.6	1549.5	1338.3	1125.2	912.2	788.8	665.4	540.2	416.8
42.5°	2201.9	2007.5	1813.1	1583.2	1355.2	1125.2	895.3	773.8	652.3	529.0	407.5
45°	2248.6	2059.8	1872.9	1624.3	1375.7	1127.1	878.5	758.9	639.3	517.8	398.1
47.5°	2269.2	2093.5	1917.8	1656.1	1396.3	1134.6	872.9	751.4	628.0	506.5	383.2
50°	2323.4	2168.2	2013.1	1732.7	1454.2	1173.8	893.5	762.6	633.6	502.8	372.0
52.5°	2355.2	2222.4	2089.7	1801.9	1514.0	1226.2	938.3	792.5	646.7	500.9	355.1
55°	2471.0	2343.9	2216.8	1910.3	1601.9	1295.3	986.9	826.2	665.4	502.8	342.1
57.5°	2618.7	2484.1	2351.4	2020.6	1689.7	1358.9	1028.0	856.1	682.2	510.3	336.5
60°	2721.5	2590.7	2461.7	2110.3	1757.0	1405.6	1052.3	872.9	693.5	512.2	332.7
62.5°	2732.7	2564.5	2398.1	2056.1	1714.0	1370.1	1028.0	854.2	680.4	504.7	330.8
65°	2661.7	2465.4	2269.2	1942.1	1615.0	1287.9	960.8	801.9	643.0	482.2	323.4
67.5°	2519.6	2289.7	2059.8	1760.8	1461.7	1162.6	863.6	727.1	592.5	456.1	319.6
70°	2188.8	1986.9	1786.9	1527.1	1269.2	1009.4	749.5	637.4	527.1	415.0	302.8
72.5°	1837.4	1648.6	1461.7	1250.5	1041.1	829.9	618.7	534.6	450.5	364.5	280.4
75°	1407.5	1265.4	1125.2	968.2	811.2	652.3	495.3	433.6	372.0	310.3	248.6
77.5°	988.8	912.2	837.4	719.6	601.9	484.1	366.4	325.2	284.1	243.0	201.9
80°	671.0	628.0	586.9	502.8	418.7	332.7	248.6	222.4	194.4	168.2	140.2
82.5°	416.8	415.0	411.2	353.3	295.3	237.4	179.4	157.0	136.4	114.0	91.6
85°	190.7	222.4	252.3	220.6	188.8	157.0	125.2	110.3	95.3	78.5	63.6
87.5°	59.8	72.9	84.1	80.4	74.8	71.0	65.4	56.1	46.7	37.4	28.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671803
 CATALOG NUMBER: CCP-SA-1D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671803
 CATALOG NUMBER: CCP-SA-1D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8
2.5°	1308.4	1302.8	1295.3	1287.9	1278.5	1271.0	1261.7	1252.3	1250.5	1246.7	1244.9
5°	1127.1	1115.9	1102.8	1091.6	1080.4	1067.3	1056.1	1043.0	1033.7	1022.4	1013.1
7.5°	968.2	949.5	929.0	908.4	889.7	871.0	850.5	831.8	822.4	813.1	803.7
10°	841.1	822.4	805.6	786.9	773.8	762.6	749.5	736.5	725.2	714.0	702.8
12.5°	777.6	764.5	751.4	738.3	723.4	710.3	695.3	680.4	667.3	656.1	643.0
15°	738.3	719.6	699.1	680.4	659.8	641.1	620.6	600.0	585.1	572.0	557.0
17.5°	691.6	663.6	637.4	609.4	586.9	564.5	540.2	517.8	500.9	482.2	465.4
20°	639.3	607.5	573.8	542.1	515.9	491.6	465.4	439.3	420.6	400.0	381.3
22.5°	594.4	553.3	510.3	467.3	439.3	411.2	381.3	353.3	336.5	317.8	300.9
25°	545.8	500.9	454.2	407.5	379.4	349.5	321.5	291.6	278.5	267.3	254.2
27.5°	519.6	474.8	428.0	383.2	357.0	329.0	302.8	274.8	265.4	254.2	244.9
30°	467.3	424.3	379.4	334.6	315.9	299.1	280.4	261.7	257.9	256.1	252.3
32.5°	420.6	375.7	330.8	286.0	269.2	252.3	235.5	218.7	216.8	213.1	211.2
35°	396.3	353.3	308.4	265.4	250.5	233.6	218.7	201.9	198.1	192.5	188.8
37.5°	390.7	345.8	299.1	254.2	239.3	224.3	207.5	192.5	188.8	185.0	181.3
40°	375.7	332.7	291.6	248.6	233.6	218.7	201.9	186.9	183.2	179.4	175.7
42.5°	364.5	323.4	280.4	237.4	224.3	211.2	196.3	183.2	179.4	175.7	170.1
45°	355.1	312.2	267.3	224.3	215.0	205.6	194.4	185.0	181.3	175.7	172.0
47.5°	340.2	299.1	256.1	213.1	203.7	196.3	186.9	177.6	173.8	170.1	166.4
50°	329.0	286.0	243.0	200.0	192.5	185.0	177.6	170.1	170.1	172.0	172.0
52.5°	314.0	272.9	231.8	190.7	183.2	175.7	168.2	160.7	162.6	164.5	166.4
55°	300.9	261.7	220.6	179.4	172.0	164.5	155.1	147.7	149.5	151.4	153.3
57.5°	295.3	254.2	213.1	172.0	164.5	155.1	147.7	138.3	138.3	138.3	138.3
60°	291.6	248.6	207.5	164.5	155.1	147.7	138.3	129.0	127.1	127.1	125.2
62.5°	289.7	246.7	205.6	162.6	151.4	142.1	130.8	119.6	117.8	115.9	114.0
65°	282.2	243.0	201.9	160.7	147.7	136.4	123.4	110.3	108.4	108.4	106.5
67.5°	280.4	239.3	200.0	158.9	145.8	130.8	117.8	102.8	100.9	99.1	97.2
70°	265.4	229.9	192.5	155.1	140.2	127.1	112.2	97.2	95.3	91.6	89.7
72.5°	246.7	215.0	181.3	147.7	132.7	117.8	102.8	87.9	86.0	84.1	80.4
75°	218.7	188.8	158.9	129.0	115.9	104.7	91.6	78.5	76.6	74.8	71.0
77.5°	179.4	155.1	132.7	108.4	99.1	89.7	80.4	71.0	69.2	67.3	63.6
80°	127.1	112.2	99.1	84.1	78.5	71.0	65.4	57.9	57.9	56.1	56.1
82.5°	84.1	76.6	69.2	61.7	57.9	54.2	50.5	46.7	46.7	44.9	44.9
85°	59.8	56.1	50.5	46.7	44.9	41.1	39.3	35.5	35.5	35.5	35.5
87.5°	28.0	28.0	26.2	26.2	24.3	24.3	22.4	20.6	20.6	20.6	20.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671803
 CATALOG NUMBER: CCP-SA-1D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671803
 CATALOG NUMBER: CCP-SA-1D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8
2.5°	1241.1	1235.5	1229.9	1222.4	1216.8	1209.4	1200.0	1192.5	1183.2	1183.2	1181.3
5°	1001.9	996.3	990.7	983.2	977.6	970.1	964.5	957.0	949.5	949.5	947.7
7.5°	794.4	783.2	772.0	758.9	747.7	740.2	732.7	723.4	715.9	710.3	704.7
10°	691.6	680.4	667.3	656.1	643.0	633.6	624.3	613.1	603.7	596.3	588.8
12.5°	629.9	616.8	603.7	590.7	577.6	564.5	553.3	540.2	527.1	517.8	508.4
15°	542.1	529.0	515.9	502.8	489.7	474.8	459.8	443.0	428.0	420.6	415.0
17.5°	446.7	433.6	418.7	405.6	390.7	379.4	368.2	357.0	345.8	338.3	332.7
20°	360.8	345.8	330.8	315.9	300.9	293.5	286.0	278.5	271.0	265.4	261.7
22.5°	282.2	272.9	265.4	256.1	246.7	241.1	237.4	231.8	226.2	226.2	226.2
25°	241.1	235.5	231.8	226.2	220.6	218.7	216.8	213.1	211.2	209.3	209.3
27.5°	233.6	228.0	222.4	216.8	211.2	209.3	207.5	203.7	201.9	201.9	201.9
30°	248.6	246.7	244.9	243.0	241.1	237.4	231.8	228.0	222.4	218.7	215.0
32.5°	207.5	205.6	205.6	203.7	201.9	205.6	207.5	211.2	213.1	215.0	216.8
35°	183.2	179.4	175.7	172.0	168.2	166.4	164.5	162.6	160.7	160.7	158.9
37.5°	177.6	173.8	170.1	166.4	162.6	160.7	158.9	157.0	155.1	155.1	153.3
40°	172.0	168.2	166.4	162.6	158.9	157.0	155.1	151.4	149.5	147.7	147.7
42.5°	166.4	164.5	160.7	158.9	155.1	153.3	151.4	147.7	145.8	143.9	142.1
45°	166.4	162.6	158.9	155.1	151.4	149.5	145.8	143.9	140.2	140.2	138.3
47.5°	162.6	158.9	155.1	151.4	147.7	145.8	142.1	140.2	136.4	134.6	132.7
50°	172.0	166.4	158.9	153.3	145.8	143.9	140.2	138.3	134.6	132.7	130.8
52.5°	168.2	162.6	155.1	149.5	142.1	138.3	136.4	132.7	129.0	127.1	125.2
55°	155.1	149.5	145.8	140.2	134.6	130.8	127.1	123.4	119.6	117.8	117.8
57.5°	138.3	136.4	134.6	132.7	130.8	127.1	123.4	117.8	114.0	112.2	110.3
60°	123.4	125.2	127.1	129.0	130.8	125.2	119.6	114.0	108.4	106.5	104.7
62.5°	112.2	115.9	119.6	121.5	125.2	119.6	114.0	108.4	102.8	100.9	99.1
65°	104.7	106.5	106.5	108.4	108.4	104.7	102.8	99.1	95.3	93.5	93.5
67.5°	95.3	95.3	95.3	93.5	93.5	91.6	91.6	89.7	87.9	86.0	86.0
70°	86.0	86.0	86.0	84.1	84.1	82.2	82.2	80.4	78.5	78.5	76.6
72.5°	78.5	78.5	76.6	76.6	74.8	74.8	74.8	72.9	72.9	71.0	71.0
75°	69.2	69.2	67.3	67.3	65.4	65.4	65.4	63.6	63.6	63.6	61.7
77.5°	61.7	61.7	59.8	59.8	57.9	57.9	57.9	56.1	56.1	54.2	54.2
80°	54.2	54.2	52.3	52.3	50.5	50.5	48.6	48.6	46.7	46.7	44.9
82.5°	43.0	43.0	43.0	43.0	43.0	41.1	41.1	39.3	37.4	37.4	35.5
85°	35.5	35.5	35.5	33.6	33.6	33.6	31.8	31.8	29.9	28.0	28.0
87.5°	20.6	20.6	20.6	18.7	18.7	18.7	18.7	18.7	18.7	18.7	16.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671803
 CATALOG NUMBER: CCP-SA-1D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671803
 CATALOG NUMBER: CCP-SA-1D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8
2.5°	1181.3	1179.4	1172.0	1164.5	1172.0	1179.4	1179.4	1179.4	1177.6	1177.6	1177.6
5°	947.7	945.8	942.1	938.3	938.3	936.5	940.2	943.9	947.7	951.4	955.1
7.5°	697.2	691.6	686.0	680.4	684.1	686.0	691.6	695.3	700.9	704.7	714.0
10°	581.3	573.8	568.2	562.6	558.9	555.1	551.4	549.5	545.8	542.1	545.8
12.5°	497.2	487.9	478.5	467.3	465.4	463.6	459.8	456.1	452.3	448.6	446.7
15°	407.5	400.0	396.3	390.7	383.2	375.7	372.0	370.1	366.4	362.6	360.8
17.5°	325.2	317.8	312.2	306.5	304.7	300.9	300.9	300.9	300.9	300.9	300.9
20°	256.1	250.5	250.5	248.6	248.6	246.7	248.6	250.5	250.5	252.3	254.2
22.5°	224.3	224.3	222.4	220.6	222.4	222.4	224.3	226.2	228.0	229.9	231.8
25°	207.5	205.6	207.5	209.3	209.3	209.3	211.2	211.2	213.1	213.1	213.1
27.5°	200.0	200.0	201.9	201.9	203.7	203.7	203.7	201.9	201.9	200.0	200.0
30°	211.2	207.5	207.5	207.5	205.6	203.7	201.9	201.9	200.0	198.1	196.3
32.5°	218.7	220.6	218.7	215.0	213.1	209.3	207.5	203.7	201.9	198.1	194.4
35°	158.9	157.0	160.7	162.6	164.5	166.4	168.2	170.1	170.1	172.0	172.0
37.5°	153.3	151.4	151.4	149.5	149.5	149.5	149.5	149.5	147.7	147.7	149.5
40°	145.8	143.9	143.9	142.1	142.1	140.2	140.2	140.2	140.2	140.2	140.2
42.5°	140.2	138.3	138.3	138.3	138.3	136.4	136.4	134.6	134.6	132.7	132.7
45°	138.3	136.4	134.6	132.7	132.7	130.8	130.8	130.8	129.0	129.0	129.0
47.5°	130.8	129.0	129.0	127.1	127.1	125.2	125.2	125.2	123.4	123.4	123.4
50°	127.1	125.2	125.2	123.4	123.4	121.5	121.5	121.5	119.6	119.6	119.6
52.5°	121.5	119.6	119.6	119.6	117.8	115.9	115.9	115.9	114.0	114.0	114.0
55°	115.9	114.0	114.0	114.0	112.2	110.3	110.3	110.3	108.4	108.4	108.4
57.5°	108.4	106.5	106.5	104.7	104.7	104.7	104.7	104.7	102.8	102.8	102.8
60°	102.8	100.9	100.9	99.1	99.1	97.2	97.2	97.2	97.2	97.2	97.2
62.5°	97.2	95.3	93.5	91.6	93.5	93.5	93.5	93.5	91.6	91.6	91.6
65°	91.6	89.7	87.9	86.0	86.0	86.0	86.0	86.0	86.0	86.0	86.0
67.5°	84.1	82.2	80.4	78.5	80.4	80.4	80.4	80.4	80.4	80.4	80.4
70°	76.6	74.8	74.8	72.9	72.9	71.0	71.0	72.9	72.9	72.9	72.9
72.5°	69.2	67.3	67.3	65.4	65.4	65.4	65.4	65.4	65.4	65.4	65.4
75°	61.7	59.8	59.8	57.9	57.9	57.9	57.9	57.9	57.9	57.9	57.9
77.5°	52.3	50.5	50.5	50.5	50.5	50.5	50.5	52.3	52.3	52.3	52.3
80°	44.9	43.0	43.0	43.0	43.0	43.0	43.0	43.0	43.0	43.0	43.0
82.5°	35.5	33.6	33.6	33.6	33.6	33.6	33.6	33.6	33.6	33.6	33.6
85°	26.2	24.3	24.3	24.3	26.2	26.2	26.2	26.2	26.2	26.2	26.2
87.5°	16.8	15.0	15.0	15.0	16.8	16.8	16.8	16.8	15.0	15.0	15.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671803
 CATALOG NUMBER: CCP-SA-1D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671803
 CATALOG NUMBER: CCP-SA-1D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8
2.5°	1177.6	1177.6	1177.6	1175.7	1173.8	1172.0	1170.1	1175.7	1179.4	1185.1	1188.8
5°	957.0	960.8	962.6	968.2	973.8	979.4	985.1	988.8	992.5	994.4	998.1
7.5°	721.5	730.8	738.3	745.8	753.3	758.9	766.4	772.0	777.6	783.2	788.8
10°	547.7	551.4	553.3	560.8	566.4	573.8	579.4	585.1	590.7	594.4	600.0
12.5°	444.9	441.1	439.3	439.3	439.3	439.3	439.3	443.0	446.7	450.5	454.2
15°	358.9	357.0	355.1	353.3	351.4	347.7	345.8	349.5	353.3	357.0	360.8
17.5°	300.9	300.9	300.9	299.1	297.2	295.3	293.5	295.3	297.2	297.2	299.1
20°	257.9	259.8	261.7	263.6	263.6	265.4	265.4	267.3	269.2	269.2	271.0
22.5°	231.8	233.6	233.6	233.6	235.5	235.5	235.5	237.4	239.3	241.1	243.0
25°	211.2	211.2	209.3	209.3	211.2	211.2	211.2	211.2	213.1	213.1	213.1
27.5°	200.0	198.1	198.1	198.1	198.1	196.3	196.3	196.3	196.3	196.3	196.3
30°	194.4	192.5	190.7	188.8	188.8	186.9	185.0	185.0	185.0	185.0	185.0
32.5°	192.5	188.8	185.0	183.2	183.2	181.3	179.4	177.6	177.6	175.7	173.8
35°	172.0	170.1	170.1	168.2	166.4	164.5	162.6	162.6	162.6	160.7	160.7
37.5°	149.5	151.4	151.4	151.4	153.3	153.3	153.3	153.3	155.1	155.1	155.1
40°	140.2	140.2	140.2	142.1	143.9	143.9	145.8	145.8	147.7	147.7	147.7
42.5°	132.7	130.8	130.8	132.7	132.7	134.6	134.6	136.4	138.3	138.3	140.2
45°	129.0	127.1	127.1	127.1	127.1	125.2	125.2	127.1	129.0	130.8	132.7
47.5°	121.5	121.5	119.6	119.6	119.6	119.6	119.6	119.6	121.5	121.5	121.5
50°	117.8	117.8	115.9	115.9	115.9	115.9	115.9	115.9	115.9	115.9	115.9
52.5°	114.0	112.2	112.2	112.2	112.2	110.3	110.3	110.3	110.3	110.3	110.3
55°	108.4	106.5	106.5	106.5	106.5	106.5	106.5	106.5	108.4	108.4	108.4
57.5°	102.8	100.9	100.9	100.9	102.8	102.8	102.8	102.8	104.7	104.7	104.7
60°	97.2	97.2	97.2	97.2	97.2	97.2	97.2	99.1	99.1	100.9	100.9
62.5°	91.6	91.6	91.6	91.6	93.5	93.5	93.5	93.5	95.3	95.3	95.3
65°	86.0	86.0	86.0	86.0	87.9	87.9	87.9	87.9	87.9	87.9	87.9
67.5°	80.4	80.4	80.4	80.4	80.4	80.4	80.4	82.2	82.2	84.1	84.1
70°	72.9	71.0	71.0	72.9	72.9	74.8	74.8	76.6	76.6	78.5	78.5
72.5°	65.4	65.4	65.4	65.4	65.4	65.4	65.4	67.3	69.2	69.2	71.0
75°	57.9	57.9	57.9	57.9	59.8	59.8	59.8	61.7	61.7	63.6	63.6
77.5°	52.3	50.5	50.5	50.5	52.3	52.3	52.3	54.2	54.2	56.1	56.1
80°	43.0	43.0	43.0	43.0	44.9	44.9	44.9	44.9	46.7	46.7	46.7
82.5°	35.5	35.5	35.5	35.5	35.5	35.5	35.5	35.5	37.4	37.4	37.4
85°	26.2	26.2	26.2	26.2	28.0	28.0	28.0	28.0	28.0	28.0	28.0
87.5°	16.8	16.8	16.8	16.8	16.8	16.8	16.8	16.8	18.7	18.7	18.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671803
 CATALOG NUMBER: CCP-SA-1D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671803
 CATALOG NUMBER: CCP-SA-1D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8
2.5°	1188.8	1188.8	1188.8	1188.8	1192.5	1194.4	1198.1	1200.0	1198.1	1196.3	1192.5
5°	1000.0	1001.9	1001.9	1003.7	1003.7	1003.7	1003.7	1003.7	1007.5	1011.2	1015.0
7.5°	790.7	792.5	794.4	796.3	796.3	796.3	794.4	794.4	796.3	796.3	798.1
10°	605.6	613.1	618.7	624.3	620.6	615.0	611.2	605.6	605.6	605.6	603.7
12.5°	457.9	459.8	463.6	465.4	463.6	463.6	461.7	459.8	461.7	465.4	467.3
15°	362.6	362.6	364.5	364.5	366.4	368.2	368.2	370.1	373.8	375.7	379.4
17.5°	300.9	302.8	302.8	304.7	304.7	306.5	306.5	306.5	310.3	314.0	319.6
20°	271.0	271.0	271.0	271.0	271.0	269.2	269.2	267.3	269.2	272.9	274.8
22.5°	243.0	244.9	244.9	244.9	243.0	241.1	237.4	235.5	235.5	237.4	237.4
25°	213.1	211.2	211.2	209.3	209.3	211.2	211.2	211.2	213.1	213.1	215.0
27.5°	196.3	194.4	194.4	192.5	192.5	194.4	194.4	194.4	194.4	194.4	194.4
30°	183.2	183.2	181.3	179.4	181.3	181.3	183.2	183.2	185.0	185.0	186.9
32.5°	173.8	172.0	172.0	170.1	172.0	172.0	173.8	173.8	175.7	177.6	177.6
35°	160.7	160.7	160.7	160.7	160.7	160.7	158.9	158.9	158.9	158.9	158.9
37.5°	153.3	153.3	151.4	149.5	149.5	149.5	149.5	149.5	147.7	145.8	143.9
40°	147.7	145.8	145.8	143.9	142.1	142.1	140.2	138.3	138.3	136.4	136.4
42.5°	140.2	138.3	138.3	136.4	134.6	134.6	132.7	130.8	130.8	130.8	129.0
45°	130.8	130.8	129.0	127.1	127.1	127.1	125.2	125.2	125.2	125.2	123.4
47.5°	121.5	121.5	119.6	119.6	119.6	119.6	117.8	117.8	117.8	117.8	117.8
50°	115.9	115.9	115.9	115.9	115.9	115.9	114.0	114.0	114.0	114.0	114.0
52.5°	110.3	110.3	110.3	110.3	110.3	110.3	110.3	110.3	110.3	110.3	110.3
55°	108.4	108.4	108.4	108.4	108.4	108.4	106.5	106.5	106.5	108.4	108.4
57.5°	104.7	104.7	102.8	102.8	102.8	102.8	102.8	102.8	102.8	102.8	102.8
60°	100.9	100.9	100.9	100.9	100.9	100.9	100.9	100.9	100.9	100.9	100.9
62.5°	95.3	95.3	95.3	95.3	95.3	97.2	97.2	97.2	97.2	97.2	95.3
65°	87.9	89.7	89.7	89.7	89.7	89.7	89.7	89.7	89.7	89.7	89.7
67.5°	84.1	84.1	84.1	84.1	84.1	84.1	84.1	84.1	84.1	84.1	84.1
70°	78.5	78.5	76.6	76.6	76.6	78.5	78.5	78.5	78.5	78.5	78.5
72.5°	71.0	71.0	71.0	71.0	71.0	71.0	71.0	71.0	71.0	72.9	72.9
75°	63.6	63.6	63.6	63.6	63.6	63.6	63.6	63.6	63.6	63.6	63.6
77.5°	56.1	56.1	54.2	54.2	54.2	56.1	56.1	56.1	56.1	57.9	57.9
80°	46.7	46.7	46.7	46.7	46.7	46.7	46.7	46.7	46.7	48.6	48.6
82.5°	37.4	37.4	37.4	37.4	37.4	37.4	37.4	37.4	37.4	39.3	39.3
85°	28.0	29.9	29.9	29.9	29.9	29.9	29.9	29.9	29.9	31.8	31.8
87.5°	18.7	18.7	18.7	18.7	18.7	18.7	16.8	16.8	16.8	16.8	15.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671803
 CATALOG NUMBER: CCP-SA-1D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671803
 CATALOG NUMBER: CCP-SA-1D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8
2.5°	1190.7	1192.5	1194.4	1194.4	1196.3	1198.1	1198.1	1205.6	1213.1	1216.8	1220.6
5°	1018.7	1016.8	1016.8	1015.0	1013.1	1018.7	1024.3	1035.5	1046.7	1048.6	1052.3
7.5°	798.1	800.0	801.9	801.9	803.7	798.1	790.7	792.5	794.4	803.7	811.2
10°	603.7	605.6	607.5	607.5	609.4	607.5	603.7	609.4	615.0	622.4	631.8
12.5°	469.2	474.8	480.4	484.1	489.7	493.5	495.3	502.8	508.4	517.8	527.1
15°	383.2	386.9	390.7	394.4	398.1	401.9	405.6	413.1	420.6	431.8	443.0
17.5°	323.4	323.4	325.2	325.2	325.2	329.0	332.7	336.5	338.3	349.5	360.8
20°	276.6	274.8	272.9	271.0	269.2	272.9	274.8	276.6	278.5	286.0	291.6
22.5°	237.4	237.4	239.3	239.3	239.3	237.4	233.6	235.5	235.5	239.3	244.9
25°	215.0	215.0	215.0	213.1	213.1	215.0	216.8	216.8	215.0	216.8	218.7
27.5°	194.4	196.3	196.3	198.1	198.1	200.0	200.0	200.0	200.0	201.9	203.7
30°	186.9	186.9	188.8	188.8	188.8	190.7	192.5	192.5	192.5	194.4	198.1
32.5°	179.4	181.3	183.2	185.0	186.9	188.8	188.8	190.7	190.7	192.5	194.4
35°	158.9	157.0	157.0	155.1	153.3	153.3	153.3	153.3	151.4	153.3	153.3
37.5°	142.1	142.1	142.1	140.2	140.2	142.1	142.1	142.1	142.1	143.9	143.9
40°	134.6	134.6	134.6	134.6	134.6	134.6	134.6	136.4	136.4	138.3	140.2
42.5°	129.0	129.0	129.0	129.0	129.0	130.8	130.8	130.8	130.8	132.7	132.7
45°	123.4	123.4	123.4	123.4	123.4	123.4	123.4	125.2	125.2	127.1	129.0
47.5°	117.8	117.8	117.8	117.8	117.8	119.6	121.5	121.5	121.5	123.4	123.4
50°	114.0	114.0	114.0	114.0	114.0	115.9	115.9	117.8	117.8	119.6	121.5
52.5°	110.3	110.3	110.3	110.3	110.3	112.2	112.2	114.0	114.0	115.9	117.8
55°	108.4	108.4	108.4	106.5	106.5	108.4	108.4	110.3	110.3	112.2	112.2
57.5°	102.8	102.8	102.8	102.8	102.8	102.8	102.8	104.7	104.7	106.5	108.4
60°	100.9	100.9	99.1	99.1	97.2	99.1	99.1	100.9	100.9	102.8	102.8
62.5°	95.3	95.3	95.3	93.5	93.5	95.3	95.3	95.3	95.3	97.2	99.1
65°	89.7	89.7	89.7	87.9	87.9	89.7	89.7	89.7	89.7	91.6	93.5
67.5°	84.1	84.1	84.1	82.2	82.2	82.2	82.2	84.1	84.1	86.0	87.9
70°	78.5	78.5	78.5	76.6	76.6	76.6	74.8	76.6	78.5	80.4	80.4
72.5°	72.9	72.9	72.9	71.0	71.0	71.0	69.2	71.0	71.0	72.9	72.9
75°	63.6	63.6	63.6	63.6	63.6	63.6	61.7	61.7	61.7	63.6	63.6
77.5°	57.9	57.9	57.9	56.1	56.1	56.1	54.2	54.2	54.2	56.1	56.1
80°	48.6	48.6	48.6	46.7	46.7	46.7	44.9	44.9	44.9	46.7	46.7
82.5°	39.3	39.3	39.3	37.4	37.4	37.4	35.5	35.5	35.5	37.4	37.4
85°	31.8	31.8	31.8	31.8	31.8	31.8	29.9	29.9	29.9	31.8	33.6
87.5°	15.0	15.0	16.8	16.8	16.8	16.8	15.0	15.0	13.1	13.1	15.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671803
 CATALOG NUMBER: CCP-SA-1D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671803

CATALOG NUMBER: CCP-SA-1D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8
2.5°	1224.3	1228.0	1237.4	1244.9	1254.2	1261.7	1267.3	1274.8	1280.4	1286.0	1289.7
5°	1054.2	1056.1	1065.4	1074.8	1082.3	1091.6	1104.7	1117.8	1130.8	1143.9	1153.3
7.5°	820.6	828.0	839.3	852.3	863.6	874.8	887.9	902.8	915.9	929.0	942.1
10°	639.3	646.7	657.9	669.2	678.5	689.7	704.7	719.6	734.6	749.5	764.5
12.5°	536.5	545.8	558.9	572.0	583.2	596.3	615.0	631.8	650.5	667.3	686.0
15°	452.3	463.6	480.4	499.1	515.9	532.7	551.4	570.1	586.9	605.6	624.3
17.5°	372.0	383.2	398.1	415.0	429.9	444.9	467.3	487.9	510.3	530.8	551.4
20°	299.1	304.7	319.6	334.6	349.5	364.5	381.3	398.1	415.0	431.8	457.9
22.5°	248.6	252.3	259.8	265.4	272.9	278.5	295.3	312.2	327.1	343.9	368.2
25°	218.7	220.6	226.2	229.9	235.5	239.3	250.5	259.8	271.0	280.4	302.8
27.5°	203.7	205.6	207.5	209.3	211.2	213.1	220.6	228.0	233.6	241.1	261.7
30°	200.0	201.9	207.5	211.2	216.8	220.6	224.3	228.0	231.8	235.5	248.6
32.5°	196.3	198.1	198.1	196.3	196.3	194.4	198.1	200.0	203.7	205.6	216.8
35°	155.1	155.1	157.0	158.9	160.7	162.6	168.2	172.0	177.6	181.3	190.7
37.5°	145.8	145.8	147.7	151.4	153.3	155.1	158.9	162.6	166.4	170.1	179.4
40°	140.2	142.1	143.9	145.8	147.7	149.5	153.3	155.1	158.9	160.7	168.2
42.5°	134.6	134.6	136.4	140.2	142.1	143.9	147.7	149.5	153.3	155.1	162.6
45°	130.8	132.7	134.6	136.4	136.4	138.3	142.1	145.8	147.7	151.4	158.9
47.5°	125.2	125.2	129.0	130.8	134.6	136.4	140.2	142.1	145.8	147.7	155.1
50°	121.5	123.4	127.1	129.0	132.7	134.6	140.2	143.9	149.5	153.3	157.0
52.5°	117.8	119.6	123.4	125.2	129.0	130.8	138.3	145.8	151.4	158.9	158.9
55°	114.0	114.0	117.8	123.4	127.1	130.8	134.6	140.2	143.9	147.7	147.7
57.5°	108.4	110.3	114.0	119.6	123.4	127.1	130.8	134.6	136.4	140.2	138.3
60°	104.7	104.7	110.3	115.9	121.5	127.1	127.1	127.1	125.2	125.2	125.2
62.5°	99.1	100.9	108.4	117.8	125.2	132.7	127.1	121.5	115.9	110.3	112.2
65°	95.3	97.2	100.9	106.5	110.3	114.0	110.3	108.4	104.7	100.9	102.8
67.5°	87.9	89.7	91.6	91.6	93.5	93.5	93.5	93.5	93.5	93.5	95.3
70°	82.2	82.2	82.2	84.1	84.1	84.1	84.1	84.1	84.1	84.1	86.0
72.5°	74.8	74.8	74.8	74.8	74.8	74.8	74.8	74.8	74.8	74.8	76.6
75°	65.4	65.4	65.4	65.4	65.4	65.4	65.4	65.4	65.4	65.4	67.3
77.5°	57.9	57.9	57.9	57.9	57.9	57.9	57.9	57.9	56.1	56.1	57.9
80°	48.6	48.6	48.6	48.6	46.7	46.7	46.7	46.7	46.7	46.7	48.6
82.5°	39.3	39.3	39.3	39.3	37.4	37.4	37.4	37.4	35.5	35.5	37.4
85°	35.5	37.4	37.4	39.3	39.3	39.3	37.4	35.5	33.6	31.8	31.8
87.5°	15.0	15.0	15.0	15.0	13.1	13.1	13.1	13.1	13.1	13.1	13.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671803
 CATALOG NUMBER: CCP-SA-1D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671803

CATALOG NUMBER: CCP-SA-1D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8
2.5°	1295.3	1299.1	1302.8	1308.4	1315.9	1321.5	1327.1	1338.3	1351.4	1362.6	1373.8
5°	1162.6	1172.0	1181.3	1192.5	1203.7	1213.1	1224.3	1246.7	1269.2	1289.7	1312.2
7.5°	953.3	966.4	977.6	996.3	1013.1	1031.8	1048.6	1076.6	1102.8	1130.8	1157.0
10°	779.4	794.4	809.4	833.7	859.8	884.1	908.4	930.8	955.1	977.6	1000.0
12.5°	704.7	721.5	740.2	755.1	772.0	786.9	801.9	828.0	854.2	880.4	906.5
15°	643.0	661.7	680.4	699.1	715.9	734.6	751.4	773.8	798.1	820.6	843.0
17.5°	572.0	590.7	611.2	631.8	652.3	672.9	693.5	725.2	757.0	786.9	818.7
20°	482.2	508.4	532.7	560.8	588.8	616.8	644.9	678.5	712.2	743.9	777.6
22.5°	392.5	416.8	441.1	474.8	508.4	540.2	573.8	618.7	661.7	706.5	749.5
25°	327.1	349.5	372.0	409.3	444.9	482.2	517.8	572.0	624.3	678.5	730.8
27.5°	282.2	302.8	323.4	362.6	401.9	439.3	478.5	538.3	596.3	656.1	714.0
30°	261.7	274.8	287.9	325.2	362.6	398.1	435.5	493.5	551.4	609.4	667.3
32.5°	228.0	239.3	250.5	284.1	317.8	349.5	383.2	443.0	500.9	560.8	618.7
35°	201.9	211.2	220.6	252.3	282.2	314.0	343.9	403.7	463.6	523.4	583.2
37.5°	186.9	196.3	203.7	231.8	261.7	289.7	317.8	377.6	435.5	495.3	553.3
40°	175.7	181.3	188.8	216.8	243.0	271.0	297.2	351.4	407.5	461.7	515.9
42.5°	168.2	175.7	181.3	205.6	231.8	256.1	280.4	332.7	385.0	435.5	487.9
45°	166.4	173.8	181.3	201.9	222.4	241.1	261.7	312.2	362.6	413.1	463.6
47.5°	162.6	168.2	175.7	192.5	207.5	224.3	239.3	289.7	340.2	388.8	439.3
50°	160.7	162.6	166.4	181.3	196.3	211.2	226.2	276.6	327.1	377.6	428.0
52.5°	158.9	158.9	158.9	172.0	185.0	196.3	209.3	259.8	312.2	362.6	413.1
55°	147.7	145.8	145.8	158.9	170.1	183.2	194.4	244.9	295.3	343.9	394.4
57.5°	136.4	134.6	132.7	143.9	155.1	166.4	177.6	228.0	280.4	330.8	381.3
60°	125.2	123.4	123.4	134.6	143.9	155.1	164.5	216.8	267.3	319.6	370.1
62.5°	112.2	114.0	114.0	123.4	134.6	143.9	153.3	205.6	259.8	312.2	364.5
65°	102.8	104.7	104.7	115.9	127.1	138.3	149.5	200.0	252.3	302.8	353.3
67.5°	95.3	97.2	97.2	110.3	121.5	134.6	145.8	190.7	237.4	282.2	327.1
70°	87.9	87.9	89.7	102.8	115.9	129.0	142.1	181.3	220.6	257.9	297.2
72.5°	78.5	80.4	82.2	95.3	106.5	119.6	130.8	166.4	201.9	237.4	272.9
75°	69.2	71.0	72.9	84.1	95.3	106.5	117.8	151.4	183.2	216.8	248.6
77.5°	61.7	63.6	65.4	74.8	84.1	93.5	102.8	127.1	153.3	177.6	201.9
80°	50.5	50.5	52.3	59.8	67.3	72.9	80.4	97.2	114.0	129.0	145.8
82.5°	37.4	39.3	39.3	44.9	48.6	54.2	57.9	67.3	74.8	84.1	91.6
85°	31.8	29.9	29.9	33.6	35.5	39.3	41.1	46.7	50.5	56.1	59.8
87.5°	13.1	11.2	11.2	13.1	16.8	18.7	20.6	20.6	22.4	22.4	22.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671803
 CATALOG NUMBER: CCP-SA-1D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671803

CATALOG NUMBER: CCP-SA-1D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8
2.5°	1379.4	1383.2	1388.8	1392.5	1401.9	1409.4	1418.7	1426.2	1431.8	1441.1	1437.4
5°	1329.0	1345.8	1362.6	1379.4	1392.5	1405.6	1416.8	1429.9	1444.9	1472.9	1480.4
7.5°	1179.4	1201.9	1222.4	1244.9	1271.0	1297.2	1323.4	1349.5	1373.8	1409.4	1431.8
10°	1031.8	1063.6	1093.5	1125.2	1149.5	1173.8	1196.3	1220.6	1254.2	1289.7	1330.9
12.5°	938.3	970.1	1001.9	1033.7	1069.2	1102.8	1138.3	1172.0	1203.7	1231.8	1278.5
15°	876.6	912.2	945.8	979.4	1022.4	1063.6	1106.6	1147.7	1194.4	1231.8	1263.6
17.5°	861.7	904.7	945.8	988.8	1033.7	1078.5	1123.4	1168.2	1215.0	1271.0	1312.2
20°	835.5	893.5	951.4	1009.4	1067.3	1123.4	1181.3	1237.4	1299.1	1366.4	1385.1
22.5°	820.6	889.7	960.8	1029.9	1108.4	1188.8	1267.3	1345.8	1411.2	1461.7	1517.8
25°	818.7	904.7	992.5	1078.5	1177.6	1274.8	1373.8	1471.0	1555.2	1605.6	1650.5
27.5°	816.8	921.5	1024.3	1127.1	1248.6	1368.2	1489.7	1609.4	1687.9	1760.8	1798.1
30°	794.4	919.6	1046.7	1172.0	1308.4	1444.9	1581.3	1717.8	1798.1	1848.6	1867.3
32.5°	766.4	914.0	1061.7	1209.4	1364.5	1519.6	1672.9	1828.1	1891.6	1934.6	1919.6
35°	743.9	906.5	1067.3	1228.0	1392.5	1558.9	1723.4	1887.9	1979.5	2039.3	2015.0
37.5°	723.4	893.5	1063.6	1233.7	1426.2	1618.7	1811.2	2003.8	2091.6	2155.2	2127.1
40°	699.1	880.4	1063.6	1244.9	1465.4	1684.1	1904.7	2123.4	2237.4	2291.6	2248.6
42.5°	678.5	867.3	1058.0	1246.7	1482.3	1717.8	1953.3	2188.8	2315.9	2392.5	2338.3
45°	652.3	841.1	1028.0	1216.8	1476.6	1736.5	1994.4	2254.2	2401.9	2461.7	2386.9
47.5°	624.3	811.2	996.3	1181.3	1458.0	1734.6	2011.2	2287.9	2424.3	2495.3	2426.2
50°	615.0	801.9	986.9	1173.8	1472.9	1773.8	2072.9	2372.0	2471.0	2529.0	2437.4
52.5°	613.1	811.2	1011.2	1209.4	1510.3	1809.4	2110.3	2409.4	2489.7	2551.4	2469.2
55°	607.5	822.4	1035.5	1248.6	1562.6	1878.5	2192.5	2506.6	2586.9	2631.8	2570.1
57.5°	613.1	844.9	1074.8	1306.6	1629.9	1953.3	2276.7	2600.0	2697.2	2729.0	2715.9
60°	616.8	863.6	1108.4	1355.2	1671.0	1986.9	2302.8	2618.7	2719.6	2798.2	2813.1
62.5°	607.5	850.5	1091.6	1334.6	1620.6	1906.6	2192.5	2478.5	2644.9	2760.8	2828.1
65°	579.4	803.7	1029.9	1254.2	1517.8	1783.2	2046.7	2310.3	2486.0	2658.0	2712.2
67.5°	517.8	708.4	899.1	1089.7	1319.6	1549.5	1777.6	2007.5	2228.1	2394.4	2469.2
70°	448.6	598.1	749.5	899.1	1108.4	1317.8	1527.1	1736.5	1930.9	2114.0	2185.1
72.5°	390.7	506.5	624.3	740.2	889.7	1037.4	1186.9	1334.6	1564.5	1747.7	1816.8
75°	332.7	416.8	499.1	583.2	686.0	788.8	889.7	992.5	1155.1	1319.6	1388.8
77.5°	256.1	312.2	366.4	420.6	491.6	560.8	631.8	700.9	815.0	938.3	973.8
80°	177.6	209.3	239.3	271.0	327.1	383.2	439.3	495.3	570.1	639.3	693.5
82.5°	110.3	130.8	149.5	168.2	213.1	257.9	300.9	345.8	375.7	379.4	433.6
85°	71.0	84.1	95.3	106.5	132.7	160.7	186.9	213.1	190.7	177.6	211.2
87.5°	28.0	35.5	41.1	46.7	44.9	43.0	41.1	39.3	33.6	29.9	37.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671803
 CATALOG NUMBER: CCP-SA-1D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671803

CATALOG NUMBER: CCP-SA-1D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8
2.5°	1441.1	1446.7	1452.3	1456.1	1461.7	1463.6	1465.4	1465.4	1467.3	1469.2	1472.9
5°	1510.3	1521.5	1532.7	1542.1	1553.3	1562.6	1570.1	1579.5	1586.9	1586.9	1585.1
7.5°	1452.3	1480.4	1508.4	1536.5	1564.5	1585.1	1603.8	1624.3	1643.0	1646.7	1650.5
10°	1375.7	1405.6	1433.7	1463.6	1491.6	1523.4	1553.3	1583.2	1615.0	1620.6	1628.0
12.5°	1304.7	1340.2	1375.7	1409.4	1444.9	1467.3	1489.7	1510.3	1532.7	1547.7	1562.6
15°	1302.8	1332.7	1362.6	1390.7	1420.6	1433.7	1446.7	1458.0	1471.0	1471.0	1472.9
17.5°	1345.8	1364.5	1383.2	1400.0	1418.7	1420.6	1424.3	1426.2	1428.0	1422.4	1416.8
20°	1429.9	1437.4	1444.9	1452.3	1459.8	1446.7	1435.5	1422.4	1409.4	1394.4	1381.3
22.5°	1553.3	1536.5	1519.6	1502.8	1486.0	1463.6	1439.3	1416.8	1392.5	1373.8	1355.2
25°	1669.2	1648.6	1628.0	1607.5	1586.9	1538.3	1489.7	1439.3	1390.7	1370.1	1349.5
27.5°	1824.3	1792.5	1760.8	1729.0	1697.2	1631.8	1566.4	1500.9	1435.5	1400.0	1366.4
30°	1861.7	1826.2	1790.7	1753.3	1717.8	1654.2	1592.5	1529.0	1465.4	1424.3	1385.1
32.5°	1915.9	1874.8	1833.7	1792.5	1751.4	1689.7	1628.0	1564.5	1502.8	1465.4	1426.2
35°	2005.6	1958.9	1912.2	1863.6	1816.8	1753.3	1691.6	1628.0	1564.5	1521.5	1480.4
37.5°	2082.3	2028.1	1973.8	1919.6	1865.4	1809.4	1751.4	1695.3	1637.4	1594.4	1553.3
40°	2168.2	2108.4	2048.6	1990.7	1930.9	1878.5	1826.2	1772.0	1719.6	1686.0	1652.3
42.5°	2243.0	2170.1	2099.1	2028.1	1955.2	1919.6	1886.0	1850.5	1815.0	1798.1	1779.5
45°	2295.3	2228.1	2158.9	2091.6	2024.3	1998.1	1972.0	1945.8	1919.6	1936.5	1953.3
47.5°	2317.8	2263.6	2211.2	2158.9	2104.7	2114.0	2123.4	2130.9	2140.2	2162.6	2186.9
50°	2338.3	2308.4	2276.7	2246.7	2215.0	2250.5	2284.1	2319.6	2355.2	2401.9	2448.6
52.5°	2379.5	2362.6	2347.7	2330.9	2314.0	2375.7	2437.4	2499.1	2560.8	2613.1	2665.4
55°	2502.8	2489.7	2476.7	2461.7	2448.6	2536.5	2622.4	2710.3	2798.2	2852.4	2906.6
57.5°	2672.9	2665.4	2656.1	2648.6	2639.3	2725.3	2809.4	2893.5	2979.5	3031.8	3086.0
60°	2801.9	2803.8	2803.8	2805.6	2805.6	2871.0	2936.5	3003.8	3069.2	3114.0	3160.8
62.5°	2871.0	2867.3	2863.6	2859.8	2856.1	2910.3	2964.5	3018.7	3072.9	3106.6	3140.2
65°	2796.3	2816.8	2837.4	2858.0	2878.5	2886.0	2891.6	2899.1	2904.7	2925.3	2945.8
67.5°	2545.8	2586.9	2626.2	2667.3	2706.6	2678.5	2652.4	2624.3	2596.3	2601.9	2605.6
70°	2267.3	2314.0	2362.6	2409.4	2456.1	2390.7	2325.3	2258.0	2192.5	2170.1	2147.7
72.5°	1912.2	1953.3	1996.3	2037.4	2078.5	1998.1	1919.6	1839.3	1758.9	1719.6	1680.4
75°	1461.7	1510.3	1560.8	1609.4	1658.0	1568.2	1476.6	1386.9	1295.3	1269.2	1244.9
77.5°	1065.4	1123.4	1181.3	1239.3	1297.2	1216.8	1136.5	1054.2	973.8	958.9	943.9
80°	775.7	820.6	863.6	908.4	951.4	904.7	858.0	811.2	764.5	762.6	760.8
82.5°	523.4	562.6	600.0	639.3	676.6	657.9	641.1	622.4	603.7	622.4	643.0
85°	269.2	323.4	379.4	433.6	487.9	482.2	478.5	472.9	467.3	491.6	514.0
87.5°	54.2	100.9	147.7	192.5	239.3	228.0	216.8	203.7	192.5	200.0	205.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671803
 CATALOG NUMBER: CCP-SA-1D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671803

CATALOG NUMBER: CCP-SA-1D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8
2.5°	1474.8	1476.6	1476.6	1476.6	1476.6	1476.6	1472.9	1471.0	1467.3	1463.6	1458.0
5°	1585.1	1583.2	1575.7	1568.2	1558.9	1551.4	1545.8	1538.3	1532.7	1525.2	1514.0
7.5°	1654.2	1658.0	1644.9	1633.7	1620.6	1607.5	1594.4	1581.3	1568.2	1555.2	1529.0
10°	1633.7	1639.3	1631.8	1624.3	1615.0	1607.5	1592.5	1575.7	1560.8	1543.9	1512.2
12.5°	1575.7	1590.7	1586.9	1583.2	1579.5	1575.7	1566.4	1555.2	1545.8	1534.6	1499.1
15°	1472.9	1472.9	1474.8	1476.6	1476.6	1478.5	1480.4	1482.3	1484.1	1486.0	1465.4
17.5°	1411.2	1405.6	1405.6	1405.6	1405.6	1405.6	1413.1	1422.4	1429.9	1437.4	1431.8
20°	1366.4	1353.3	1351.4	1351.4	1349.5	1347.7	1360.8	1375.7	1388.8	1401.9	1409.4
22.5°	1336.5	1317.8	1315.9	1314.0	1312.2	1310.3	1327.1	1343.9	1360.8	1377.6	1403.7
25°	1329.0	1308.4	1310.3	1312.2	1312.2	1314.0	1327.1	1340.2	1353.3	1366.4	1411.2
27.5°	1330.9	1297.2	1299.1	1300.9	1300.9	1302.8	1323.4	1342.1	1362.6	1381.3	1437.4
30°	1343.9	1304.7	1300.9	1297.2	1293.5	1289.7	1317.8	1345.8	1373.8	1401.9	1444.9
32.5°	1388.8	1351.4	1342.1	1332.7	1323.4	1314.0	1347.7	1379.4	1413.1	1444.9	1480.4
35°	1437.4	1396.3	1392.5	1388.8	1383.2	1379.4	1409.4	1441.1	1471.0	1500.9	1532.7
37.5°	1510.3	1469.2	1465.4	1459.8	1456.1	1450.5	1484.1	1515.9	1549.5	1581.3	1609.4
40°	1618.7	1585.1	1583.2	1583.2	1581.3	1579.5	1605.6	1633.7	1659.8	1686.0	1704.7
42.5°	1762.6	1745.8	1751.4	1758.9	1764.5	1770.1	1790.7	1813.1	1833.7	1854.2	1848.6
45°	1970.1	1986.9	1988.8	1990.7	1992.5	1994.4	2000.0	2007.5	2013.1	2018.7	1996.3
47.5°	2209.4	2231.8	2243.0	2254.2	2263.6	2274.8	2267.3	2258.0	2250.5	2241.1	2185.1
50°	2493.5	2540.2	2538.3	2536.5	2532.7	2530.9	2515.9	2501.0	2484.1	2469.2	2386.9
52.5°	2717.8	2770.1	2779.5	2788.8	2798.2	2807.5	2779.5	2751.4	2721.5	2693.5	2590.7
55°	2958.9	3013.1	3015.0	3016.8	3016.8	3018.7	2979.5	2940.2	2899.1	2859.8	2753.3
57.5°	3138.3	3190.7	3185.1	3181.3	3175.7	3170.1	3123.4	3076.7	3029.9	2983.2	2876.7
60°	3205.6	3250.5	3239.3	3228.1	3215.0	3203.8	3168.2	3132.7	3095.4	3059.8	2957.0
62.5°	3173.9	3207.5	3190.7	3175.7	3158.9	3142.1	3097.2	3050.5	3005.6	2958.9	2884.1
65°	2964.5	2985.1	2962.6	2942.1	2921.5	2899.1	2861.7	2824.3	2785.1	2747.7	2697.2
67.5°	2611.2	2615.0	2613.1	2611.2	2609.4	2607.5	2553.3	2499.1	2443.0	2388.8	2385.1
70°	2127.1	2104.7	2108.4	2114.0	2117.8	2121.5	2080.4	2041.1	2000.0	1958.9	1977.6
72.5°	1641.1	1601.9	1611.2	1622.4	1631.8	1641.1	1607.5	1575.7	1542.1	1508.4	1534.6
75°	1218.7	1194.4	1203.7	1215.0	1224.3	1233.7	1220.6	1207.5	1192.5	1179.4	1203.7
77.5°	929.0	914.0	915.9	915.9	917.8	917.8	919.6	923.4	925.2	927.1	953.3
80°	757.0	755.1	753.3	751.4	747.7	745.8	764.5	783.2	801.9	820.6	833.7
82.5°	661.7	680.4	669.2	659.8	648.6	637.4	654.2	671.0	687.9	704.7	699.1
85°	538.3	560.8	540.2	519.6	497.2	476.6	491.6	504.7	519.6	532.7	525.2
87.5°	213.1	218.7	185.0	153.3	119.6	86.0	136.4	185.0	235.5	284.1	291.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671803
 CATALOG NUMBER: CCP-SA-1D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671803

CATALOG NUMBER: CCP-SA-1D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8	1345.8
2.5°	1452.3	1444.9	1439.3	1437.4	1433.7	1431.8	1428.0	1424.3	1418.7	1415.0	1409.4
5°	1500.9	1489.7	1476.6	1458.0	1441.1	1422.4	1403.7	1386.9	1370.1	1351.4	1334.6
7.5°	1502.8	1476.6	1450.5	1426.2	1400.0	1375.7	1349.5	1327.1	1302.8	1278.5	1256.1
10°	1482.3	1450.5	1418.7	1386.9	1357.0	1325.2	1293.5	1267.3	1239.3	1211.2	1185.1
12.5°	1465.4	1429.9	1394.4	1357.0	1321.5	1284.1	1246.7	1220.6	1194.4	1168.2	1142.1
15°	1444.9	1422.4	1401.9	1368.2	1334.6	1300.9	1267.3	1231.8	1198.1	1162.6	1127.1
17.5°	1428.0	1422.4	1416.8	1394.4	1372.0	1347.7	1325.2	1289.7	1254.2	1216.8	1181.3
20°	1418.7	1426.2	1433.7	1422.4	1411.2	1398.1	1386.9	1360.8	1334.6	1306.6	1280.4
22.5°	1429.9	1458.0	1484.1	1486.0	1489.7	1491.6	1493.5	1469.2	1444.9	1418.7	1394.4
25°	1456.1	1500.9	1545.8	1570.1	1594.4	1620.6	1644.9	1629.9	1615.0	1600.0	1585.1
27.5°	1491.6	1547.7	1603.8	1639.3	1672.9	1708.4	1743.9	1742.1	1740.2	1736.5	1734.6
30°	1486.0	1529.0	1572.0	1615.0	1658.0	1700.9	1743.9	1766.4	1786.9	1809.4	1831.8
32.5°	1517.8	1553.3	1590.7	1635.5	1680.4	1727.1	1772.0	1818.7	1863.6	1910.3	1957.0
35°	1566.4	1598.1	1631.8	1680.4	1730.9	1779.5	1829.9	1886.0	1943.9	2001.9	2058.0
37.5°	1639.3	1667.3	1697.2	1738.3	1781.3	1822.4	1865.4	1947.7	2029.9	2114.0	2196.3
40°	1723.4	1742.1	1760.8	1800.0	1839.3	1878.5	1917.8	2020.6	2123.4	2226.2	2329.0
42.5°	1844.9	1839.3	1833.7	1865.4	1899.1	1930.9	1964.5	2058.0	2151.4	2244.9	2338.3
45°	1973.8	1951.4	1929.0	1943.9	1960.8	1975.7	1992.5	2087.9	2183.2	2280.4	2375.7
47.5°	2129.0	2072.9	2016.8	2003.8	1990.7	1975.7	1962.6	2065.4	2168.2	2272.9	2375.7
50°	2304.7	2220.6	2138.3	2104.7	2069.2	2035.5	2000.0	2084.1	2170.1	2256.1	2340.2
52.5°	2487.9	2383.2	2280.4	2228.1	2175.7	2121.5	2069.2	2140.2	2213.1	2286.0	2357.0
55°	2644.9	2538.3	2429.9	2368.2	2306.6	2244.9	2183.2	2254.2	2325.3	2396.3	2467.3
57.5°	2770.1	2663.6	2557.0	2499.1	2439.3	2381.3	2321.5	2388.8	2458.0	2527.1	2594.4
60°	2856.1	2753.3	2650.5	2594.4	2538.3	2482.3	2426.2	2506.6	2586.9	2669.2	2749.6
62.5°	2811.2	2736.5	2661.7	2637.4	2613.1	2586.9	2562.6	2639.3	2714.0	2790.7	2867.3
65°	2646.7	2596.3	2545.8	2570.1	2596.3	2620.6	2646.7	2697.2	2747.7	2800.0	2850.5
67.5°	2379.5	2375.7	2370.1	2424.3	2478.5	2534.6	2588.8	2622.4	2654.2	2687.9	2721.5
70°	1996.3	2016.8	2035.5	2129.0	2222.4	2315.9	2409.4	2422.4	2435.5	2448.6	2461.7
72.5°	1562.6	1588.8	1616.8	1740.2	1861.7	1985.1	2108.4	2101.0	2093.5	2084.1	2076.7
75°	1229.9	1254.2	1280.4	1394.4	1508.4	1622.4	1736.5	1704.7	1674.8	1643.0	1611.2
77.5°	981.3	1007.5	1035.5	1142.1	1248.6	1357.0	1463.6	1386.9	1310.3	1233.7	1157.0
80°	844.9	858.0	869.2	942.1	1013.1	1086.0	1158.9	1080.4	1000.0	919.6	841.1
82.5°	693.5	686.0	680.4	723.4	766.4	809.4	852.3	777.6	702.8	626.2	551.4
85°	517.8	510.3	502.8	525.2	547.7	572.0	594.4	508.4	422.4	334.6	248.6
87.5°	300.9	308.4	315.9	340.2	364.5	390.7	415.0	327.1	239.3	149.5	61.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671803
 CATALOG NUMBER: CCP-SA-1D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671803
 CATALOG NUMBER: CCP-SA-1D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1345.8	1345.8
2.5°	1398.1	1388.8
5°	1321.5	1308.4
7.5°	1237.4	1220.6
10°	1160.8	1138.3
12.5°	1112.2	1084.1
15°	1093.5	1059.8
17.5°	1149.5	1117.8
20°	1235.5	1192.5
22.5°	1340.2	1287.9
25°	1521.5	1458.0
27.5°	1669.2	1603.8
30°	1760.8	1689.7
32.5°	1861.7	1768.2
35°	1966.4	1876.6
37.5°	2093.5	1992.5
40°	2224.3	2119.6
42.5°	2269.2	2201.9
45°	2312.2	2248.6
47.5°	2321.5	2269.2
50°	2330.9	2323.4
52.5°	2357.0	2355.2
55°	2469.2	2471.0
57.5°	2607.5	2618.7
60°	2734.6	2721.5
62.5°	2800.0	2732.7
65°	2755.2	2661.7
67.5°	2620.6	2519.6
70°	2325.3	2188.8
72.5°	1957.0	1837.4
75°	1508.4	1407.5
77.5°	1072.9	988.8
80°	755.1	671.0
82.5°	484.1	416.8
85°	218.7	190.7
87.5°	61.7	59.8
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P671803
CATALOG NUMBER: CCP-SA-1D-730-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)