

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P671810

Luminaire Tested: **CCP-SA-2E-730-U-SLR**

Issue Date: 04/16/2023



Test Information

Test Method: LM-79-08
Report Number: P671810
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/16/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCP-SA-2E-730-U-SLR
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @1050mA w/ SLR distribution lens
Light Source: (32) 3000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10332.5 lumens
Efficiency: N/A
Efficacy: 96.9 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B2 - U0 - G3

Input Watts (W): 106.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P671810
 CATALOG NUMBER: CCP-SA-2E-730-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 14.7 fc
 Type IV - Short - N/A

REPORT NUMBER: P671810
CATALOG NUMBER: CCP-SA-2E-730-U-SLR

Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P671810
 CATALOG NUMBER: CCP-SA-2E-730-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2126.0	0.0	2126.0
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	8206.5	0.0	8206.5
	% Fixture	79.4	0.0	79.4
Total	Lumens	10332.5	0.0	10332.5
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	256.4	2.5
10°-20°	541.3	5.2
20°-30°	792.0	7.7
30°-40°	1115.8	10.8
40°-50°	1533.2	14.8
50°-60°	2089.8	20.2
60°-70°	2287.2	22.1
70°-80°	1320.9	12.8
80°-90°	395.9	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	10332.5	100.0
0°-180°	10332.5	100.0



REPORT NUMBER: P671810


CATALOG NUMBER: CCP-SA-2E-730-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1061.2	10.3			
FM (30°-60°)	3770.6	36.5			
FH (60°-80°)	3038.4	29.4			G2/5000
FVH (80°-90°)	336.3	3.3			G3/500
BL (0°-30°)	528.5	5.1	B2/1000		
BM (30°-60°)	968.1	9.4	B1/1000		
BH (60°-80°)	569.7	5.5	B2/1000		G2/1000
BVH (80°-90°)	59.6	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G3

Type IV Short





REPORT NUMBER: P671810

CATALOG NUMBER: CCP-SA-2E-730-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6
2.5°	3405.0	3386.6	3372.9	3359.1	3340.8	3327.1	3308.7	3290.4	3267.5	3249.1	3226.2
5°	3207.9	3152.9	3097.9	3065.8	3029.2	2997.1	2960.4	2919.2	2877.9	2832.1	2790.9
7.5°	2992.5	2923.8	2855.0	2800.0	2740.5	2685.5	2625.9	2575.5	2525.1	2474.7	2424.3
10°	2790.9	2726.7	2662.6	2593.8	2520.5	2451.8	2378.4	2309.7	2240.9	2172.2	2103.5
12.5°	2658.0	2580.1	2506.7	2428.8	2355.5	2277.6	2199.7	2135.5	2071.4	2002.6	1938.5
15°	2598.4	2525.1	2456.3	2378.4	2300.5	2222.6	2144.7	2071.4	2002.6	1929.3	1856.0
17.5°	2740.5	2635.1	2529.7	2428.8	2328.0	2227.2	2126.4	2034.7	1943.1	1851.4	1759.8
20°	2923.8	2790.9	2662.6	2538.8	2410.5	2286.8	2158.5	2030.1	1901.8	1773.5	1645.2
22.5°	3157.5	3006.3	2859.6	2699.2	2534.2	2373.8	2208.9	2048.5	1888.1	1723.1	1562.7
25°	3574.5	3395.8	3217.1	2987.9	2754.2	2525.1	2291.4	2080.6	1874.3	1663.5	1452.7
27.5°	3932.0	3689.1	3450.8	3175.8	2900.9	2625.9	2350.9	2108.0	1869.7	1626.9	1384.0
30°	4142.8	3904.5	3666.2	3331.6	3001.7	2667.1	2332.6	2062.2	1796.4	1526.0	1255.7
32.5°	4335.2	4069.5	3803.7	3437.0	3065.8	2699.2	2328.0	2030.1	1736.8	1439.0	1141.1
35°	4601.0	4307.8	4019.0	3592.8	3166.7	2740.5	2314.3	2007.2	1695.6	1388.6	1076.9
37.5°	4885.2	4523.1	4165.7	3693.7	3221.6	2749.6	2277.6	1975.2	1672.7	1370.2	1067.8
40°	5196.8	4756.9	4321.5	3799.1	3281.2	2758.8	2236.4	1933.9	1631.4	1324.4	1021.9
42.5°	5398.4	4921.8	4445.2	3881.6	3322.5	2758.8	2195.1	1897.2	1599.4	1296.9	999.0
45°	5513.0	5050.2	4591.9	3982.4	3372.9	2763.4	2153.9	1860.6	1567.3	1269.4	976.1
47.5°	5563.4	5132.6	4701.9	4060.3	3423.3	2781.7	2140.1	1842.3	1539.8	1241.9	939.5
50°	5696.3	5316.0	4935.6	4248.2	3565.4	2877.9	2190.5	1869.7	1553.5	1232.8	912.0
52.5°	5774.2	5448.8	5123.5	4417.7	3712.0	3006.3	2300.5	1943.1	1585.6	1228.2	870.7
55°	6058.4	5746.7	5435.1	4683.5	3927.4	3175.8	2419.7	2025.6	1631.4	1232.8	838.6
57.5°	6420.4	6090.4	5765.1	4953.9	4142.8	3331.6	2520.5	2098.9	1672.7	1251.1	824.9
60°	6672.4	6351.6	6035.4	5173.9	4307.8	3446.2	2580.1	2140.1	1700.2	1255.7	815.7
62.5°	6699.9	6287.5	5879.6	5041.0	4202.4	3359.1	2520.5	2094.3	1668.1	1237.3	811.1
65°	6525.8	6044.6	5563.4	4761.4	3959.5	3157.5	2355.5	1966.0	1576.5	1182.3	792.8
67.5°	6177.5	5613.8	5050.2	4316.9	3583.7	2850.4	2117.2	1782.7	1452.7	1118.2	783.6
70°	5366.4	4871.4	4381.1	3744.1	3111.7	2474.7	1837.7	1562.7	1292.3	1017.4	742.4
72.5°	4504.8	4042.0	3583.7	3065.8	2552.6	2034.7	1516.9	1310.7	1104.4	893.6	687.4
75°	3450.8	3102.5	2758.8	2373.8	1988.9	1599.4	1214.4	1063.2	912.0	760.7	609.5
77.5°	2424.3	2236.4	2053.1	1764.3	1475.6	1186.9	898.2	797.4	696.6	595.8	494.9
80°	1645.2	1539.8	1439.0	1232.8	1026.5	815.7	609.5	545.3	476.6	412.4	343.7
82.5°	1021.9	1017.4	1008.2	866.1	724.1	582.0	439.9	384.9	334.5	279.5	224.6
85°	467.4	545.3	618.7	540.8	462.9	384.9	307.0	270.4	233.7	192.5	155.8
87.5°	146.6	178.7	206.2	197.1	183.3	174.1	160.4	137.5	114.6	91.7	68.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671810
 CATALOG NUMBER: CCP-SA-2E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671810

CATALOG NUMBER: CCP-SA-2E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6
2.5°	3207.9	3194.2	3175.8	3157.5	3134.6	3116.2	3093.3	3070.4	3065.8	3056.7	3052.1
5°	2763.4	2735.9	2703.8	2676.3	2648.8	2616.7	2589.2	2557.2	2534.2	2506.7	2483.8
7.5°	2373.8	2328.0	2277.6	2227.2	2181.4	2135.5	2085.1	2039.3	2016.4	1993.5	1970.6
10°	2062.2	2016.4	1975.2	1929.3	1897.2	1869.7	1837.7	1805.6	1778.1	1750.6	1723.1
12.5°	1906.4	1874.3	1842.3	1810.2	1773.5	1741.4	1704.8	1668.1	1636.0	1608.5	1576.5
15°	1810.2	1764.3	1713.9	1668.1	1617.7	1571.9	1521.5	1471.1	1434.4	1402.3	1365.6
17.5°	1695.6	1626.9	1562.7	1494.0	1439.0	1384.0	1324.4	1269.4	1228.2	1182.3	1141.1
20°	1567.3	1489.4	1406.9	1329.0	1264.8	1205.3	1141.1	1076.9	1031.1	980.7	934.9
22.5°	1457.3	1356.5	1251.1	1145.7	1076.9	1008.2	934.9	866.1	824.9	779.1	737.8
25°	1338.2	1228.2	1113.6	999.0	930.3	857.0	788.2	714.9	682.8	655.3	623.2
27.5°	1274.0	1164.0	1049.4	939.5	875.3	806.6	742.4	673.7	650.7	623.2	600.3
30°	1145.7	1040.3	930.3	820.3	774.5	733.2	687.4	641.6	632.4	627.8	618.7
32.5°	1031.1	921.1	811.1	701.2	659.9	618.7	577.4	536.2	531.6	522.4	517.8
35°	971.5	866.1	756.1	650.7	614.1	572.8	536.2	494.9	485.8	472.0	462.9
37.5°	957.8	847.8	733.2	623.2	586.6	549.9	508.7	472.0	462.9	453.7	444.5
40°	921.1	815.7	714.9	609.5	572.8	536.2	494.9	458.3	449.1	439.9	430.8
42.5°	893.6	792.8	687.4	582.0	549.9	517.8	481.2	449.1	439.9	430.8	417.0
45°	870.7	765.3	655.3	549.9	527.0	504.1	476.6	453.7	444.5	430.8	421.6
47.5°	834.1	733.2	627.8	522.4	499.5	481.2	458.3	435.4	426.2	417.0	407.9
50°	806.6	701.2	595.8	490.4	472.0	453.7	435.4	417.0	417.0	421.6	421.6
52.5°	769.9	669.1	568.3	467.4	449.1	430.8	412.4	394.1	398.7	403.3	407.9
55°	737.8	641.6	540.8	439.9	421.6	403.3	380.4	362.0	366.6	371.2	375.8
57.5°	724.1	623.2	522.4	421.6	403.3	380.4	362.0	339.1	339.1	339.1	339.1
60°	714.9	609.5	508.7	403.3	380.4	362.0	339.1	316.2	311.6	311.6	307.0
62.5°	710.3	604.9	504.1	398.7	371.2	348.3	320.8	293.3	288.7	284.1	279.5
65°	692.0	595.8	494.9	394.1	362.0	334.5	302.5	270.4	265.8	265.8	261.2
67.5°	687.4	586.6	490.4	389.5	357.5	320.8	288.7	252.0	247.5	242.9	238.3
70°	650.7	563.7	472.0	380.4	343.7	311.6	275.0	238.3	233.7	224.6	220.0
72.5°	604.9	527.0	444.5	362.0	325.4	288.7	252.0	215.4	210.8	206.2	197.1
75°	536.2	462.9	389.5	316.2	284.1	256.6	224.6	192.5	187.9	183.3	174.1
77.5°	439.9	380.4	325.4	265.8	242.9	220.0	197.1	174.1	169.6	165.0	155.8
80°	311.6	275.0	242.9	206.2	192.5	174.1	160.4	142.1	142.1	137.5	137.5
82.5°	206.2	187.9	169.6	151.2	142.1	132.9	123.7	114.6	114.6	110.0	110.0
85°	146.6	137.5	123.7	114.6	110.0	100.8	96.2	87.1	87.1	87.1	87.1
87.5°	68.7	68.7	64.2	64.2	59.6	59.6	55.0	50.4	50.4	50.4	50.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671810
 CATALOG NUMBER: CCP-SA-2E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671810

CATALOG NUMBER: CCP-SA-2E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6
2.5°	3042.9	3029.2	3015.4	2997.1	2983.3	2965.0	2942.1	2923.8	2900.9	2900.9	2896.3
5°	2456.3	2442.6	2428.8	2410.5	2396.8	2378.4	2364.7	2346.4	2328.0	2328.0	2323.4
7.5°	1947.7	1920.2	1892.7	1860.6	1833.1	1814.8	1796.4	1773.5	1755.2	1741.4	1727.7
10°	1695.6	1668.1	1636.0	1608.5	1576.5	1553.5	1530.6	1503.1	1480.2	1461.9	1443.6
12.5°	1544.4	1512.3	1480.2	1448.1	1416.1	1384.0	1356.5	1324.4	1292.3	1269.4	1246.5
15°	1329.0	1296.9	1264.8	1232.8	1200.7	1164.0	1127.3	1086.1	1049.4	1031.1	1017.4
17.5°	1095.3	1063.2	1026.5	994.4	957.8	930.3	902.8	875.3	847.8	829.5	815.7
20°	884.5	847.8	811.1	774.5	737.8	719.5	701.2	682.8	664.5	650.7	641.6
22.5°	692.0	669.1	650.7	627.8	604.9	591.2	582.0	568.3	554.5	554.5	554.5
25°	591.2	577.4	568.3	554.5	540.8	536.2	531.6	522.4	517.8	513.3	513.3
27.5°	572.8	559.1	545.3	531.6	517.8	513.3	508.7	499.5	494.9	494.9	494.9
30°	609.5	604.9	600.3	595.8	591.2	582.0	568.3	559.1	545.3	536.2	527.0
32.5°	508.7	504.1	504.1	499.5	494.9	504.1	508.7	517.8	522.4	527.0	531.6
35°	449.1	439.9	430.8	421.6	412.4	407.9	403.3	398.7	394.1	394.1	389.5
37.5°	435.4	426.2	417.0	407.9	398.7	394.1	389.5	384.9	380.4	380.4	375.8
40°	421.6	412.4	407.9	398.7	389.5	384.9	380.4	371.2	366.6	362.0	362.0
42.5°	407.9	403.3	394.1	389.5	380.4	375.8	371.2	362.0	357.5	352.9	348.3
45°	407.9	398.7	389.5	380.4	371.2	366.6	357.5	352.9	343.7	343.7	339.1
47.5°	398.7	389.5	380.4	371.2	362.0	357.5	348.3	343.7	334.5	330.0	325.4
50°	421.6	407.9	389.5	375.8	357.5	352.9	343.7	339.1	330.0	325.4	320.8
52.5°	412.4	398.7	380.4	366.6	348.3	339.1	334.5	325.4	316.2	311.6	307.0
55°	380.4	366.6	357.5	343.7	330.0	320.8	311.6	302.5	293.3	288.7	288.7
57.5°	339.1	334.5	330.0	325.4	320.8	311.6	302.5	288.7	279.5	275.0	270.4
60°	302.5	307.0	311.6	316.2	320.8	307.0	293.3	279.5	265.8	261.2	256.6
62.5°	275.0	284.1	293.3	297.9	307.0	293.3	279.5	265.8	252.0	247.5	242.9
65°	256.6	261.2	261.2	265.8	265.8	256.6	252.0	242.9	233.7	229.1	229.1
67.5°	233.7	233.7	233.7	229.1	229.1	224.6	224.6	220.0	215.4	210.8	210.8
70°	210.8	210.8	210.8	206.2	206.2	201.6	201.6	197.1	192.5	192.5	187.9
72.5°	192.5	192.5	187.9	187.9	183.3	183.3	183.3	178.7	178.7	174.1	174.1
75°	169.6	169.6	165.0	165.0	160.4	160.4	160.4	155.8	155.8	155.8	151.2
77.5°	151.2	151.2	146.6	146.6	142.1	142.1	142.1	137.5	137.5	132.9	132.9
80°	132.9	132.9	128.3	128.3	123.7	123.7	119.2	119.2	114.6	114.6	110.0
82.5°	105.4	105.4	105.4	105.4	105.4	100.8	100.8	96.2	91.7	91.7	87.1
85°	87.1	87.1	87.1	82.5	82.5	82.5	77.9	77.9	73.3	68.7	68.7
87.5°	50.4	50.4	50.4	45.8	45.8	45.8	45.8	45.8	45.8	45.8	41.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671810
 CATALOG NUMBER: CCP-SA-2E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671810

CATALOG NUMBER: CCP-SA-2E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6
2.5°	2896.3	2891.7	2873.4	2855.0	2873.4	2891.7	2891.7	2891.7	2887.1	2887.1	2887.1
5°	2323.4	2318.9	2309.7	2300.5	2300.5	2295.9	2305.1	2314.3	2323.4	2332.6	2341.8
7.5°	1709.4	1695.6	1681.9	1668.1	1677.3	1681.9	1695.6	1704.8	1718.5	1727.7	1750.6
10°	1425.2	1406.9	1393.1	1379.4	1370.2	1361.1	1351.9	1347.3	1338.2	1329.0	1338.2
12.5°	1219.0	1196.1	1173.2	1145.7	1141.1	1136.5	1127.3	1118.2	1109.0	1099.9	1095.3
15°	999.0	980.7	971.5	957.8	939.5	921.1	912.0	907.4	898.2	889.0	884.5
17.5°	797.4	779.1	765.3	751.6	747.0	737.8	737.8	737.8	737.8	737.8	737.8
20°	627.8	614.1	614.1	609.5	609.5	604.9	609.5	614.1	614.1	618.7	623.2
22.5°	549.9	549.9	545.3	540.8	545.3	545.3	549.9	554.5	559.1	563.7	568.3
25°	508.7	504.1	508.7	513.3	513.3	513.3	517.8	517.8	522.4	522.4	522.4
27.5°	490.4	490.4	494.9	494.9	499.5	499.5	499.5	494.9	494.9	490.4	490.4
30°	517.8	508.7	508.7	508.7	504.1	499.5	494.9	494.9	490.4	485.8	481.2
32.5°	536.2	540.8	536.2	527.0	522.4	513.3	508.7	499.5	494.9	485.8	476.6
35°	389.5	384.9	394.1	398.7	403.3	407.9	412.4	417.0	417.0	421.6	421.6
37.5°	375.8	371.2	371.2	366.6	366.6	366.6	366.6	366.6	362.0	362.0	366.6
40°	357.5	352.9	352.9	348.3	348.3	343.7	343.7	343.7	343.7	343.7	343.7
42.5°	343.7	339.1	339.1	339.1	339.1	334.5	334.5	330.0	330.0	325.4	325.4
45°	339.1	334.5	330.0	325.4	325.4	320.8	320.8	320.8	316.2	316.2	316.2
47.5°	320.8	316.2	316.2	311.6	311.6	307.0	307.0	307.0	302.5	302.5	302.5
50°	311.6	307.0	307.0	302.5	302.5	297.9	297.9	297.9	293.3	293.3	293.3
52.5°	297.9	293.3	293.3	293.3	288.7	284.1	284.1	284.1	279.5	279.5	279.5
55°	284.1	279.5	279.5	279.5	275.0	270.4	270.4	270.4	265.8	265.8	265.8
57.5°	265.8	261.2	261.2	256.6	256.6	256.6	256.6	256.6	252.0	252.0	252.0
60°	252.0	247.5	247.5	242.9	242.9	238.3	238.3	238.3	238.3	238.3	238.3
62.5°	238.3	233.7	229.1	224.6	229.1	229.1	229.1	229.1	224.6	224.6	224.6
65°	224.6	220.0	215.4	210.8	210.8	210.8	210.8	210.8	210.8	210.8	210.8
67.5°	206.2	201.6	197.1	192.5	197.1	197.1	197.1	197.1	197.1	197.1	197.1
70°	187.9	183.3	183.3	178.7	178.7	174.1	174.1	178.7	178.7	178.7	178.7
72.5°	169.6	165.0	165.0	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4
75°	151.2	146.6	146.6	142.1	142.1	142.1	142.1	142.1	142.1	142.1	142.1
77.5°	128.3	123.7	123.7	123.7	123.7	123.7	123.7	128.3	128.3	128.3	128.3
80°	110.0	105.4	105.4	105.4	105.4	105.4	105.4	105.4	105.4	105.4	105.4
82.5°	87.1	82.5	82.5	82.5	82.5	82.5	82.5	82.5	82.5	82.5	82.5
85°	64.2	59.6	59.6	59.6	64.2	64.2	64.2	64.2	64.2	64.2	64.2
87.5°	41.2	36.7	36.7	36.7	41.2	41.2	41.2	41.2	36.7	36.7	36.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671810
 CATALOG NUMBER: CCP-SA-2E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671810

CATALOG NUMBER: CCP-SA-2E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6
2.5°	2887.1	2887.1	2887.1	2882.5	2877.9	2873.4	2868.8	2882.5	2891.7	2905.4	2914.6
5°	2346.4	2355.5	2360.1	2373.8	2387.6	2401.3	2415.1	2424.3	2433.4	2438.0	2447.2
7.5°	1768.9	1791.8	1810.2	1828.5	1846.8	1860.6	1878.9	1892.7	1906.4	1920.2	1933.9
10°	1342.7	1351.9	1356.5	1374.8	1388.6	1406.9	1420.6	1434.4	1448.1	1457.3	1471.1
12.5°	1090.7	1081.5	1076.9	1076.9	1076.9	1076.9	1076.9	1086.1	1095.3	1104.4	1113.6
15°	879.9	875.3	870.7	866.1	861.6	852.4	847.8	857.0	866.1	875.3	884.5
17.5°	737.8	737.8	737.8	733.2	728.7	724.1	719.5	724.1	728.7	728.7	733.2
20°	632.4	637.0	641.6	646.2	646.2	650.7	650.7	655.3	659.9	659.9	664.5
22.5°	568.3	572.8	572.8	572.8	577.4	577.4	577.4	582.0	586.6	591.2	595.8
25°	517.8	517.8	513.3	513.3	517.8	517.8	517.8	517.8	522.4	522.4	522.4
27.5°	490.4	485.8	485.8	485.8	485.8	481.2	481.2	481.2	481.2	481.2	481.2
30°	476.6	472.0	467.4	462.9	462.9	458.3	453.7	453.7	453.7	453.7	453.7
32.5°	472.0	462.9	453.7	449.1	449.1	444.5	439.9	435.4	435.4	430.8	426.2
35°	421.6	417.0	417.0	412.4	407.9	403.3	398.7	398.7	398.7	394.1	394.1
37.5°	366.6	371.2	371.2	371.2	375.8	375.8	375.8	375.8	380.4	380.4	380.4
40°	343.7	343.7	343.7	348.3	352.9	352.9	357.5	357.5	362.0	362.0	362.0
42.5°	325.4	320.8	320.8	325.4	325.4	330.0	330.0	334.5	339.1	339.1	343.7
45°	316.2	311.6	311.6	311.6	311.6	307.0	307.0	311.6	316.2	320.8	325.4
47.5°	297.9	297.9	293.3	293.3	293.3	293.3	293.3	293.3	297.9	297.9	297.9
50°	288.7	288.7	284.1	284.1	284.1	284.1	284.1	284.1	284.1	284.1	284.1
52.5°	279.5	275.0	275.0	275.0	275.0	270.4	270.4	270.4	270.4	270.4	270.4
55°	265.8	261.2	261.2	261.2	261.2	261.2	261.2	261.2	265.8	265.8	265.8
57.5°	252.0	247.5	247.5	247.5	252.0	252.0	252.0	252.0	256.6	256.6	256.6
60°	238.3	238.3	238.3	238.3	238.3	238.3	238.3	242.9	242.9	247.5	247.5
62.5°	224.6	224.6	224.6	224.6	229.1	229.1	229.1	229.1	233.7	233.7	233.7
65°	210.8	210.8	210.8	210.8	215.4	215.4	215.4	215.4	215.4	215.4	215.4
67.5°	197.1	197.1	197.1	197.1	197.1	197.1	197.1	201.6	201.6	206.2	206.2
70°	178.7	174.1	174.1	178.7	178.7	183.3	183.3	187.9	187.9	192.5	192.5
72.5°	160.4	160.4	160.4	160.4	160.4	160.4	160.4	165.0	169.6	169.6	174.1
75°	142.1	142.1	142.1	142.1	146.6	146.6	146.6	151.2	151.2	155.8	155.8
77.5°	128.3	123.7	123.7	123.7	128.3	128.3	128.3	132.9	132.9	137.5	137.5
80°	105.4	105.4	105.4	105.4	110.0	110.0	110.0	110.0	114.6	114.6	114.6
82.5°	87.1	87.1	87.1	87.1	87.1	87.1	87.1	87.1	91.7	91.7	91.7
85°	64.2	64.2	64.2	64.2	68.7	68.7	68.7	68.7	68.7	68.7	68.7
87.5°	41.2	41.2	41.2	41.2	41.2	41.2	41.2	41.2	45.8	45.8	45.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671810
 CATALOG NUMBER: CCP-SA-2E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671810

CATALOG NUMBER: CCP-SA-2E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6
2.5°	2914.6	2914.6	2914.6	2914.6	2923.8	2928.4	2937.5	2942.1	2937.5	2932.9	2923.8
5°	2451.8	2456.3	2456.3	2460.9	2460.9	2460.9	2460.9	2460.9	2470.1	2479.2	2488.4
7.5°	1938.5	1943.1	1947.7	1952.2	1952.2	1952.2	1947.7	1947.7	1952.2	1952.2	1956.8
10°	1484.8	1503.1	1516.9	1530.6	1521.5	1507.7	1498.5	1484.8	1484.8	1484.8	1480.2
12.5°	1122.8	1127.3	1136.5	1141.1	1136.5	1136.5	1131.9	1127.3	1131.9	1141.1	1145.7
15°	889.0	889.0	893.6	893.6	898.2	902.8	902.8	907.4	916.5	921.1	930.3
17.5°	737.8	742.4	742.4	747.0	747.0	751.6	751.6	751.6	760.7	769.9	783.6
20°	664.5	664.5	664.5	664.5	664.5	659.9	659.9	655.3	659.9	669.1	673.7
22.5°	595.8	600.3	600.3	600.3	595.8	591.2	582.0	577.4	577.4	582.0	582.0
25°	522.4	517.8	517.8	513.3	513.3	517.8	517.8	517.8	522.4	522.4	527.0
27.5°	481.2	476.6	476.6	472.0	472.0	476.6	476.6	476.6	476.6	476.6	476.6
30°	449.1	449.1	444.5	439.9	444.5	444.5	449.1	449.1	453.7	453.7	458.3
32.5°	426.2	421.6	421.6	417.0	421.6	421.6	426.2	426.2	430.8	435.4	435.4
35°	394.1	394.1	394.1	394.1	394.1	394.1	389.5	389.5	389.5	389.5	389.5
37.5°	375.8	375.8	371.2	366.6	366.6	366.6	366.6	366.6	362.0	357.5	352.9
40°	362.0	357.5	357.5	352.9	348.3	348.3	343.7	339.1	339.1	334.5	334.5
42.5°	343.7	339.1	339.1	334.5	330.0	330.0	325.4	320.8	320.8	320.8	316.2
45°	320.8	320.8	316.2	311.6	311.6	311.6	307.0	307.0	307.0	307.0	302.5
47.5°	297.9	297.9	293.3	293.3	293.3	293.3	288.7	288.7	288.7	288.7	288.7
50°	284.1	284.1	284.1	284.1	284.1	284.1	279.5	279.5	279.5	279.5	279.5
52.5°	270.4	270.4	270.4	270.4	270.4	270.4	270.4	270.4	270.4	270.4	270.4
55°	265.8	265.8	265.8	265.8	265.8	265.8	261.2	261.2	261.2	265.8	265.8
57.5°	256.6	256.6	252.0	252.0	252.0	252.0	252.0	252.0	252.0	252.0	252.0
60°	247.5	247.5	247.5	247.5	247.5	247.5	247.5	247.5	247.5	247.5	247.5
62.5°	233.7	233.7	233.7	233.7	233.7	238.3	238.3	238.3	238.3	238.3	233.7
65°	215.4	220.0	220.0	220.0	220.0	220.0	220.0	220.0	220.0	220.0	220.0
67.5°	206.2	206.2	206.2	206.2	206.2	206.2	206.2	206.2	206.2	206.2	206.2
70°	192.5	192.5	187.9	187.9	187.9	192.5	192.5	192.5	192.5	192.5	192.5
72.5°	174.1	174.1	174.1	174.1	174.1	174.1	174.1	174.1	174.1	178.7	178.7
75°	155.8	155.8	155.8	155.8	155.8	155.8	155.8	155.8	155.8	155.8	155.8
77.5°	137.5	137.5	132.9	132.9	132.9	137.5	137.5	137.5	137.5	142.1	142.1
80°	114.6	114.6	114.6	114.6	114.6	114.6	114.6	114.6	114.6	119.2	119.2
82.5°	91.7	91.7	91.7	91.7	91.7	91.7	91.7	91.7	91.7	96.2	96.2
85°	68.7	73.3	73.3	73.3	73.3	73.3	73.3	73.3	73.3	77.9	77.9
87.5°	45.8	45.8	45.8	45.8	45.8	45.8	41.2	41.2	41.2	41.2	36.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671810
 CATALOG NUMBER: CCP-SA-2E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671810

CATALOG NUMBER: CCP-SA-2E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6
2.5°	2919.2	2923.8	2928.4	2928.4	2932.9	2937.5	2937.5	2955.9	2974.2	2983.3	2992.5
5°	2497.6	2493.0	2493.0	2488.4	2483.8	2497.6	2511.3	2538.8	2566.3	2570.9	2580.1
7.5°	1956.8	1961.4	1966.0	1966.0	1970.6	1956.8	1938.5	1943.1	1947.7	1970.6	1988.9
10°	1480.2	1484.8	1489.4	1489.4	1494.0	1489.4	1480.2	1494.0	1507.7	1526.0	1549.0
12.5°	1150.3	1164.0	1177.8	1186.9	1200.7	1209.8	1214.4	1232.8	1246.5	1269.4	1292.3
15°	939.5	948.6	957.8	967.0	976.1	985.3	994.4	1012.8	1031.1	1058.6	1086.1
17.5°	792.8	792.8	797.4	797.4	797.4	806.6	815.7	824.9	829.5	857.0	884.5
20°	678.2	673.7	669.1	664.5	659.9	669.1	673.7	678.2	682.8	701.2	714.9
22.5°	582.0	582.0	586.6	586.6	586.6	582.0	572.8	577.4	577.4	586.6	600.3
25°	527.0	527.0	527.0	522.4	522.4	527.0	531.6	531.6	527.0	531.6	536.2
27.5°	476.6	481.2	481.2	485.8	485.8	490.4	490.4	490.4	490.4	494.9	499.5
30°	458.3	458.3	462.9	462.9	462.9	467.4	472.0	472.0	472.0	476.6	485.8
32.5°	439.9	444.5	449.1	453.7	458.3	462.9	462.9	467.4	467.4	472.0	476.6
35°	389.5	384.9	384.9	380.4	375.8	375.8	375.8	375.8	371.2	375.8	375.8
37.5°	348.3	348.3	348.3	343.7	343.7	348.3	348.3	348.3	348.3	352.9	352.9
40°	330.0	330.0	330.0	330.0	330.0	330.0	330.0	334.5	334.5	339.1	343.7
42.5°	316.2	316.2	316.2	316.2	316.2	320.8	320.8	320.8	320.8	325.4	325.4
45°	302.5	302.5	302.5	302.5	302.5	302.5	302.5	307.0	307.0	311.6	316.2
47.5°	288.7	288.7	288.7	288.7	288.7	293.3	297.9	297.9	297.9	302.5	302.5
50°	279.5	279.5	279.5	279.5	279.5	284.1	284.1	288.7	288.7	293.3	297.9
52.5°	270.4	270.4	270.4	270.4	270.4	275.0	275.0	279.5	279.5	284.1	288.7
55°	265.8	265.8	265.8	261.2	261.2	265.8	265.8	270.4	270.4	275.0	275.0
57.5°	252.0	252.0	252.0	252.0	252.0	252.0	252.0	256.6	256.6	261.2	265.8
60°	247.5	247.5	242.9	242.9	238.3	242.9	242.9	247.5	247.5	252.0	252.0
62.5°	233.7	233.7	233.7	229.1	229.1	233.7	233.7	233.7	233.7	238.3	242.9
65°	220.0	220.0	220.0	215.4	215.4	220.0	220.0	220.0	220.0	224.6	229.1
67.5°	206.2	206.2	206.2	201.6	201.6	201.6	201.6	206.2	206.2	210.8	215.4
70°	192.5	192.5	192.5	187.9	187.9	187.9	183.3	187.9	192.5	197.1	197.1
72.5°	178.7	178.7	178.7	174.1	174.1	174.1	169.6	174.1	174.1	178.7	178.7
75°	155.8	155.8	155.8	155.8	155.8	155.8	151.2	151.2	151.2	155.8	155.8
77.5°	142.1	142.1	142.1	137.5	137.5	137.5	132.9	132.9	132.9	137.5	137.5
80°	119.2	119.2	119.2	114.6	114.6	114.6	110.0	110.0	110.0	114.6	114.6
82.5°	96.2	96.2	96.2	91.7	91.7	91.7	87.1	87.1	87.1	91.7	91.7
85°	77.9	77.9	77.9	77.9	77.9	77.9	73.3	73.3	73.3	77.9	82.5
87.5°	36.7	36.7	41.2	41.2	41.2	41.2	36.7	36.7	32.1	32.1	36.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671810
 CATALOG NUMBER: CCP-SA-2E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671810

CATALOG NUMBER: CCP-SA-2E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6
2.5°	3001.7	3010.8	3033.8	3052.1	3075.0	3093.3	3107.1	3125.4	3139.2	3152.9	3162.1
5°	2584.7	2589.2	2612.1	2635.1	2653.4	2676.3	2708.4	2740.5	2772.5	2804.6	2827.5
7.5°	2011.8	2030.1	2057.6	2089.7	2117.2	2144.7	2176.8	2213.5	2245.5	2277.6	2309.7
10°	1567.3	1585.6	1613.1	1640.6	1663.5	1691.0	1727.7	1764.3	1801.0	1837.7	1874.3
12.5°	1315.2	1338.2	1370.2	1402.3	1429.8	1461.9	1507.7	1549.0	1594.8	1636.0	1681.9
15°	1109.0	1136.5	1177.8	1223.6	1264.8	1306.1	1351.9	1397.7	1439.0	1484.8	1530.6
17.5°	912.0	939.5	976.1	1017.4	1054.0	1090.7	1145.7	1196.1	1251.1	1301.5	1351.9
20°	733.2	747.0	783.6	820.3	857.0	893.6	934.9	976.1	1017.4	1058.6	1122.8
22.5°	609.5	618.7	637.0	650.7	669.1	682.8	724.1	765.3	802.0	843.2	902.8
25°	536.2	540.8	554.5	563.7	577.4	586.6	614.1	637.0	664.5	687.4	742.4
27.5°	499.5	504.1	508.7	513.3	517.8	522.4	540.8	559.1	572.8	591.2	641.6
30°	490.4	494.9	508.7	517.8	531.6	540.8	549.9	559.1	568.3	577.4	609.5
32.5°	481.2	485.8	485.8	481.2	481.2	476.6	485.8	490.4	499.5	504.1	531.6
35°	380.4	380.4	384.9	389.5	394.1	398.7	412.4	421.6	435.4	444.5	467.4
37.5°	357.5	357.5	362.0	371.2	375.8	380.4	389.5	398.7	407.9	417.0	439.9
40°	343.7	348.3	352.9	357.5	362.0	366.6	375.8	380.4	389.5	394.1	412.4
42.5°	330.0	330.0	334.5	343.7	348.3	352.9	362.0	366.6	375.8	380.4	398.7
45°	320.8	325.4	330.0	334.5	334.5	339.1	348.3	357.5	362.0	371.2	389.5
47.5°	307.0	307.0	316.2	320.8	330.0	334.5	343.7	348.3	357.5	362.0	380.4
50°	297.9	302.5	311.6	316.2	325.4	330.0	343.7	352.9	366.6	375.8	384.9
52.5°	288.7	293.3	302.5	307.0	316.2	320.8	339.1	357.5	371.2	389.5	389.5
55°	279.5	279.5	288.7	302.5	311.6	320.8	330.0	343.7	352.9	362.0	362.0
57.5°	265.8	270.4	279.5	293.3	302.5	311.6	320.8	330.0	334.5	343.7	339.1
60°	256.6	256.6	270.4	284.1	297.9	311.6	311.6	311.6	307.0	307.0	307.0
62.5°	242.9	247.5	265.8	288.7	307.0	325.4	311.6	297.9	284.1	270.4	275.0
65°	233.7	238.3	247.5	261.2	270.4	279.5	270.4	265.8	256.6	247.5	252.0
67.5°	215.4	220.0	224.6	224.6	229.1	229.1	229.1	229.1	229.1	229.1	233.7
70°	201.6	201.6	201.6	206.2	206.2	206.2	206.2	206.2	206.2	206.2	210.8
72.5°	183.3	183.3	183.3	183.3	183.3	183.3	183.3	183.3	183.3	183.3	187.9
75°	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4	165.0
77.5°	142.1	142.1	142.1	142.1	142.1	142.1	142.1	142.1	137.5	137.5	142.1
80°	119.2	119.2	119.2	119.2	114.6	114.6	114.6	114.6	114.6	114.6	119.2
82.5°	96.2	96.2	96.2	96.2	91.7	91.7	91.7	91.7	87.1	87.1	91.7
85°	87.1	91.7	91.7	96.2	96.2	96.2	91.7	87.1	82.5	77.9	77.9
87.5°	36.7	36.7	36.7	36.7	32.1	32.1	32.1	32.1	32.1	32.1	32.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671810
 CATALOG NUMBER: CCP-SA-2E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671810

CATALOG NUMBER: CCP-SA-2E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6
2.5°	3175.8	3185.0	3194.2	3207.9	3226.2	3240.0	3253.7	3281.2	3313.3	3340.8	3368.3
5°	2850.4	2873.4	2896.3	2923.8	2951.3	2974.2	3001.7	3056.7	3111.7	3162.1	3217.1
7.5°	2337.2	2369.3	2396.8	2442.6	2483.8	2529.7	2570.9	2639.6	2703.8	2772.5	2836.7
10°	1911.0	1947.7	1984.3	2043.9	2108.0	2167.6	2227.2	2282.2	2341.8	2396.8	2451.8
12.5°	1727.7	1768.9	1814.8	1851.4	1892.7	1929.3	1966.0	2030.1	2094.3	2158.5	2222.6
15°	1576.5	1622.3	1668.1	1713.9	1755.2	1801.0	1842.3	1897.2	1956.8	2011.8	2066.8
17.5°	1402.3	1448.1	1498.5	1549.0	1599.4	1649.8	1700.2	1778.1	1856.0	1929.3	2007.2
20°	1182.3	1246.5	1306.1	1374.8	1443.6	1512.3	1581.0	1663.5	1746.0	1823.9	1906.4
22.5°	962.4	1021.9	1081.5	1164.0	1246.5	1324.4	1406.9	1516.9	1622.3	1732.3	1837.7
25°	802.0	857.0	912.0	1003.6	1090.7	1182.3	1269.4	1402.3	1530.6	1663.5	1791.8
27.5°	692.0	742.4	792.8	889.0	985.3	1076.9	1173.2	1319.8	1461.9	1608.5	1750.6
30°	641.6	673.7	705.7	797.4	889.0	976.1	1067.8	1209.8	1351.9	1494.0	1636.0
32.5°	559.1	586.6	614.1	696.6	779.1	857.0	939.5	1086.1	1228.2	1374.8	1516.9
35°	494.9	517.8	540.8	618.7	692.0	769.9	843.2	989.9	1136.5	1283.2	1429.8
37.5°	458.3	481.2	499.5	568.3	641.6	710.3	779.1	925.7	1067.8	1214.4	1356.5
40°	430.8	444.5	462.9	531.6	595.8	664.5	728.7	861.6	999.0	1131.9	1264.8
42.5°	412.4	430.8	444.5	504.1	568.3	627.8	687.4	815.7	944.0	1067.8	1196.1
45°	407.9	426.2	444.5	494.9	545.3	591.2	641.6	765.3	889.0	1012.8	1136.5
47.5°	398.7	412.4	430.8	472.0	508.7	549.9	586.6	710.3	834.1	953.2	1076.9
50°	394.1	398.7	407.9	444.5	481.2	517.8	554.5	678.2	802.0	925.7	1049.4
52.5°	389.5	389.5	389.5	421.6	453.7	481.2	513.3	637.0	765.3	889.0	1012.8
55°	362.0	357.5	357.5	389.5	417.0	449.1	476.6	600.3	724.1	843.2	967.0
57.5°	334.5	330.0	325.4	352.9	380.4	407.9	435.4	559.1	687.4	811.1	934.9
60°	307.0	302.5	302.5	330.0	352.9	380.4	403.3	531.6	655.3	783.6	907.4
62.5°	275.0	279.5	279.5	302.5	330.0	352.9	375.8	504.1	637.0	765.3	893.6
65°	252.0	256.6	256.6	284.1	311.6	339.1	366.6	490.4	618.7	742.4	866.1
67.5°	233.7	238.3	238.3	270.4	297.9	330.0	357.5	467.4	582.0	692.0	802.0
70°	215.4	215.4	220.0	252.0	284.1	316.2	348.3	444.5	540.8	632.4	728.7
72.5°	192.5	197.1	201.6	233.7	261.2	293.3	320.8	407.9	494.9	582.0	669.1
75°	169.6	174.1	178.7	206.2	233.7	261.2	288.7	371.2	449.1	531.6	609.5
77.5°	151.2	155.8	160.4	183.3	206.2	229.1	252.0	311.6	375.8	435.4	494.9
80°	123.7	123.7	128.3	146.6	165.0	178.7	197.1	238.3	279.5	316.2	357.5
82.5°	91.7	96.2	96.2	110.0	119.2	132.9	142.1	165.0	183.3	206.2	224.6
85°	77.9	73.3	73.3	82.5	87.1	96.2	100.8	114.6	123.7	137.5	146.6
87.5°	32.1	27.5	27.5	32.1	41.2	45.8	50.4	50.4	55.0	55.0	55.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671810
 CATALOG NUMBER: CCP-SA-2E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671810

CATALOG NUMBER: CCP-SA-2E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6
2.5°	3382.0	3391.2	3405.0	3414.1	3437.0	3455.4	3478.3	3496.6	3510.4	3533.3	3524.1
5°	3258.3	3299.6	3340.8	3382.0	3414.1	3446.2	3473.7	3505.8	3542.4	3611.2	3629.5
7.5°	2891.7	2946.7	2997.1	3052.1	3116.2	3180.4	3244.6	3308.7	3368.3	3455.4	3510.4
10°	2529.7	2607.6	2680.9	2758.8	2818.4	2877.9	2932.9	2992.5	3075.0	3162.1	3262.9
12.5°	2300.5	2378.4	2456.3	2534.2	2621.3	2703.8	2790.9	2873.4	2951.3	3020.0	3134.6
15°	2149.3	2236.4	2318.9	2401.3	2506.7	2607.6	2713.0	2813.8	2928.4	3020.0	3097.9
17.5°	2112.6	2218.0	2318.9	2424.3	2534.2	2644.2	2754.2	2864.2	2978.8	3116.2	3217.1
20°	2048.5	2190.5	2332.6	2474.7	2616.7	2754.2	2896.3	3033.8	3185.0	3350.0	3395.8
22.5°	2011.8	2181.4	2355.5	2525.1	2717.6	2914.6	3107.1	3299.6	3460.0	3583.7	3721.2
25°	2007.2	2218.0	2433.4	2644.2	2887.1	3125.4	3368.3	3606.6	3812.8	3936.6	4046.5
27.5°	2002.6	2259.3	2511.3	2763.4	3061.3	3354.5	3652.4	3945.7	4138.2	4316.9	4408.6
30°	1947.7	2254.7	2566.3	2873.4	3207.9	3542.4	3877.0	4211.5	4408.6	4532.3	4578.1
32.5°	1878.9	2240.9	2603.0	2965.0	3345.4	3725.7	4101.5	4481.9	4637.7	4743.1	4706.4
35°	1823.9	2222.6	2616.7	3010.8	3414.1	3822.0	4225.3	4628.5	4853.1	4999.7	4940.2
37.5°	1773.5	2190.5	2607.6	3024.6	3496.6	3968.6	4440.7	4912.7	5128.1	5283.9	5215.1
40°	1713.9	2158.5	2607.6	3052.1	3592.8	4129.0	4669.8	5206.0	5485.5	5618.4	5513.0
42.5°	1663.5	2126.4	2593.8	3056.7	3634.1	4211.5	4788.9	5366.4	5678.0	5865.9	5733.0
45°	1599.4	2062.2	2520.5	2983.3	3620.3	4257.3	4889.8	5526.8	5888.8	6035.4	5852.1
47.5°	1530.6	1988.9	2442.6	2896.3	3574.5	4252.8	4931.0	5609.2	5943.8	6117.9	5948.4
50°	1507.7	1966.0	2419.7	2877.9	3611.2	4349.0	5082.2	5815.5	6058.4	6200.4	5975.9
52.5°	1503.1	1988.9	2479.2	2965.0	3702.8	4436.1	5173.9	5907.1	6104.2	6255.4	6053.8
55°	1489.4	2016.4	2538.8	3061.3	3831.2	4605.6	5375.5	6145.4	6342.5	6452.5	6301.2
57.5°	1503.1	2071.4	2635.1	3203.3	3996.1	4788.9	5581.7	6374.6	6612.9	6690.8	6658.7
60°	1512.3	2117.2	2717.6	3322.5	4096.9	4871.4	5645.9	6420.4	6667.9	6860.3	6897.0
62.5°	1489.4	2085.1	2676.3	3272.1	3973.2	4674.4	5375.5	6076.7	6484.5	6768.7	6933.6
65°	1420.6	1970.6	2525.1	3075.0	3721.2	4371.9	5018.1	5664.2	6095.0	6516.6	6649.5
67.5°	1269.4	1736.8	2204.3	2671.7	3235.4	3799.1	4358.2	4921.8	5462.6	5870.5	6053.8
70°	1099.9	1466.5	1837.7	2204.3	2717.6	3230.8	3744.1	4257.3	4733.9	5183.1	5357.2
72.5°	957.8	1241.9	1530.6	1814.8	2181.4	2543.4	2910.0	3272.1	3835.7	4284.8	4454.4
75°	815.7	1021.9	1223.6	1429.8	1681.9	1933.9	2181.4	2433.4	2832.1	3235.4	3405.0
77.5°	627.8	765.3	898.2	1031.1	1205.3	1374.8	1549.0	1718.5	1998.1	2300.5	2387.6
80°	435.4	513.3	586.6	664.5	802.0	939.5	1076.9	1214.4	1397.7	1567.3	1700.2
82.5°	270.4	320.8	366.6	412.4	522.4	632.4	737.8	847.8	921.1	930.3	1063.2
85°	174.1	206.2	233.7	261.2	325.4	394.1	458.3	522.4	467.4	435.4	517.8
87.5°	68.7	87.1	100.8	114.6	110.0	105.4	100.8	96.2	82.5	73.3	91.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671810
 CATALOG NUMBER: CCP-SA-2E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671810

CATALOG NUMBER: CCP-SA-2E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6
2.5°	3533.3	3547.0	3560.8	3569.9	3583.7	3588.3	3592.8	3592.8	3597.4	3602.0	3611.2
5°	3702.8	3730.3	3757.8	3780.7	3808.2	3831.2	3849.5	3872.4	3890.7	3890.7	3886.1
7.5°	3560.8	3629.5	3698.3	3767.0	3835.7	3886.1	3932.0	3982.4	4028.2	4037.4	4046.5
10°	3372.9	3446.2	3514.9	3588.3	3657.0	3734.9	3808.2	3881.6	3959.5	3973.2	3991.5
12.5°	3198.7	3285.8	3372.9	3455.4	3542.4	3597.4	3652.4	3702.8	3757.8	3794.5	3831.2
15°	3194.2	3267.5	3340.8	3409.5	3482.9	3514.9	3547.0	3574.5	3606.6	3606.6	3611.2
17.5°	3299.6	3345.4	3391.2	3432.5	3478.3	3482.9	3492.0	3496.6	3501.2	3487.4	3473.7
20°	3505.8	3524.1	3542.4	3560.8	3579.1	3547.0	3519.5	3487.4	3455.4	3418.7	3386.6
22.5°	3808.2	3767.0	3725.7	3684.5	3643.3	3588.3	3528.7	3473.7	3414.1	3368.3	3322.5
25°	4092.4	4042.0	3991.5	3941.1	3890.7	3771.6	3652.4	3528.7	3409.5	3359.1	3308.7
27.5°	4472.7	4394.8	4316.9	4239.0	4161.1	4000.7	3840.3	3679.9	3519.5	3432.5	3350.0
30°	4564.4	4477.3	4390.2	4298.6	4211.5	4055.7	3904.5	3748.7	3592.8	3492.0	3395.8
32.5°	4697.3	4596.5	4495.6	4394.8	4294.0	4142.8	3991.5	3835.7	3684.5	3592.8	3496.6
35°	4917.3	4802.7	4688.1	4569.0	4454.4	4298.6	4147.4	3991.5	3835.7	3730.3	3629.5
37.5°	5105.1	4972.2	4839.3	4706.4	4573.6	4436.1	4294.0	4156.5	4014.5	3909.1	3808.2
40°	5316.0	5169.3	5022.7	4880.6	4733.9	4605.6	4477.3	4344.4	4216.1	4133.6	4051.1
42.5°	5499.3	5320.5	5146.4	4972.2	4793.5	4706.4	4624.0	4536.9	4449.8	4408.6	4362.7
45°	5627.6	5462.6	5293.0	5128.1	4963.1	4898.9	4834.8	4770.6	4706.4	4747.7	4788.9
47.5°	5682.6	5549.7	5421.4	5293.0	5160.1	5183.1	5206.0	5224.3	5247.2	5302.2	5361.8
50°	5733.0	5659.7	5581.7	5508.4	5430.5	5517.6	5600.1	5687.2	5774.2	5888.8	6003.4
52.5°	5833.8	5792.6	5755.9	5714.6	5673.4	5824.6	5975.9	6127.1	6278.3	6406.6	6535.0
55°	6136.3	6104.2	6072.1	6035.4	6003.4	6218.7	6429.6	6644.9	6860.3	6993.2	7126.1
57.5°	6553.3	6535.0	6512.0	6493.7	6470.8	6681.6	6887.8	7094.0	7304.8	7433.2	7566.1
60°	6869.5	6874.1	6874.1	6878.7	6878.7	7039.1	7199.4	7364.4	7524.8	7634.8	7749.4
62.5°	7039.1	7029.9	7020.7	7011.6	7002.4	7135.3	7268.2	7401.1	7534.0	7616.5	7699.0
65°	6855.7	6906.2	6956.6	7007.0	7057.4	7075.7	7089.5	7107.8	7121.5	7172.0	7222.4
67.5°	6241.7	6342.5	6438.7	6539.5	6635.8	6567.0	6502.9	6434.1	6365.4	6379.1	6388.3
70°	5558.8	5673.4	5792.6	5907.1	6021.7	5861.3	5700.9	5535.9	5375.5	5320.5	5265.5
72.5°	4688.1	4788.9	4894.3	4995.2	5096.0	4898.9	4706.4	4509.4	4312.3	4216.1	4119.9
75°	3583.7	3702.8	3826.6	3945.7	4064.9	3844.9	3620.3	3400.4	3175.8	3111.7	3052.1
77.5°	2612.1	2754.2	2896.3	3038.3	3180.4	2983.3	2786.3	2584.7	2387.6	2350.9	2314.3
80°	1901.8	2011.8	2117.2	2227.2	2332.6	2218.0	2103.5	1988.9	1874.3	1869.7	1865.2
82.5°	1283.2	1379.4	1471.1	1567.3	1658.9	1613.1	1571.9	1526.0	1480.2	1526.0	1576.5
85°	659.9	792.8	930.3	1063.2	1196.1	1182.3	1173.2	1159.4	1145.7	1205.3	1260.2
87.5°	132.9	247.5	362.0	472.0	586.6	559.1	531.6	499.5	472.0	490.4	504.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671810
 CATALOG NUMBER: CCP-SA-2E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671810

CATALOG NUMBER: CCP-SA-2E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6
2.5°	3615.8	3620.3	3620.3	3620.3	3620.3	3620.3	3611.2	3606.6	3597.4	3588.3	3574.5
5°	3886.1	3881.6	3863.2	3844.9	3822.0	3803.7	3789.9	3771.6	3757.8	3739.5	3712.0
7.5°	4055.7	4064.9	4032.8	4005.3	3973.2	3941.1	3909.1	3877.0	3844.9	3812.8	3748.7
10°	4005.3	4019.0	4000.7	3982.4	3959.5	3941.1	3904.5	3863.2	3826.6	3785.3	3707.4
12.5°	3863.2	3899.9	3890.7	3881.6	3872.4	3863.2	3840.3	3812.8	3789.9	3762.4	3675.3
15°	3611.2	3611.2	3615.8	3620.3	3620.3	3624.9	3629.5	3634.1	3638.7	3643.3	3592.8
17.5°	3460.0	3446.2	3446.2	3446.2	3446.2	3446.2	3464.5	3487.4	3505.8	3524.1	3510.4
20°	3350.0	3317.9	3313.3	3313.3	3308.7	3304.1	3336.2	3372.9	3405.0	3437.0	3455.4
22.5°	3276.6	3230.8	3226.2	3221.6	3217.1	3212.5	3253.7	3295.0	3336.2	3377.5	3441.6
25°	3258.3	3207.9	3212.5	3217.1	3217.1	3221.6	3253.7	3285.8	3317.9	3350.0	3460.0
27.5°	3262.9	3180.4	3185.0	3189.6	3189.6	3194.2	3244.6	3290.4	3340.8	3386.6	3524.1
30°	3295.0	3198.7	3189.6	3180.4	3171.2	3162.1	3230.8	3299.6	3368.3	3437.0	3542.4
32.5°	3405.0	3313.3	3290.4	3267.5	3244.6	3221.6	3304.1	3382.0	3464.5	3542.4	3629.5
35°	3524.1	3423.3	3414.1	3405.0	3391.2	3382.0	3455.4	3533.3	3606.6	3679.9	3757.8
37.5°	3702.8	3602.0	3592.8	3579.1	3569.9	3556.2	3638.7	3716.6	3799.1	3877.0	3945.7
40°	3968.6	3886.1	3881.6	3881.6	3877.0	3872.4	3936.6	4005.3	4069.5	4133.6	4179.4
42.5°	4321.5	4280.3	4294.0	4312.3	4326.1	4339.8	4390.2	4445.2	4495.6	4546.1	4532.3
45°	4830.2	4871.4	4876.0	4880.6	4885.2	4889.8	4903.5	4921.8	4935.6	4949.3	4894.3
47.5°	5416.8	5471.8	5499.3	5526.8	5549.7	5577.2	5558.8	5535.9	5517.6	5494.7	5357.2
50°	6113.3	6227.9	6223.3	6218.7	6209.6	6205.0	6168.3	6131.7	6090.4	6053.8	5852.1
52.5°	6663.3	6791.6	6814.5	6837.4	6860.3	6883.2	6814.5	6745.8	6672.4	6603.7	6351.6
55°	7254.4	7387.3	7391.9	7396.5	7396.5	7401.1	7304.8	7208.6	7107.8	7011.6	6750.3
57.5°	7694.4	7822.7	7808.9	7799.8	7786.0	7772.3	7657.7	7543.2	7428.6	7314.0	7052.8
60°	7859.4	7969.3	7941.8	7914.4	7882.3	7854.8	7767.7	7680.6	7589.0	7501.9	7249.9
62.5°	7781.5	7863.9	7822.7	7786.0	7744.8	7703.5	7593.6	7479.0	7369.0	7254.4	7071.1
65°	7268.2	7318.6	7263.6	7213.2	7162.8	7107.8	7016.1	6924.5	6828.2	6736.6	6612.9
67.5°	6402.1	6411.2	6406.6	6402.1	6397.5	6392.9	6260.0	6127.1	5989.6	5856.7	5847.5
70°	5215.1	5160.1	5169.3	5183.1	5192.2	5201.4	5100.6	5004.3	4903.5	4802.7	4848.5
72.5°	4023.6	3927.4	3950.3	3977.8	4000.7	4023.6	3941.1	3863.2	3780.7	3698.3	3762.4
75°	2987.9	2928.4	2951.3	2978.8	3001.7	3024.6	2992.5	2960.4	2923.8	2891.7	2951.3
77.5°	2277.6	2240.9	2245.5	2245.5	2250.1	2250.1	2254.7	2263.9	2268.4	2273.0	2337.2
80°	1856.0	1851.4	1846.8	1842.3	1833.1	1828.5	1874.3	1920.2	1966.0	2011.8	2043.9
82.5°	1622.3	1668.1	1640.6	1617.7	1590.2	1562.7	1604.0	1645.2	1686.4	1727.7	1713.9
85°	1319.8	1374.8	1324.4	1274.0	1219.0	1168.6	1205.3	1237.3	1274.0	1306.1	1287.7
87.5°	522.4	536.2	453.7	375.8	293.3	210.8	334.5	453.7	577.4	696.6	714.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671810
 CATALOG NUMBER: CCP-SA-2E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671810

CATALOG NUMBER: CCP-SA-2E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6	3299.6
2.5°	3560.8	3542.4	3528.7	3524.1	3514.9	3510.4	3501.2	3492.0	3478.3	3469.1	3455.4
5°	3679.9	3652.4	3620.3	3574.5	3533.3	3487.4	3441.6	3400.4	3359.1	3313.3	3272.1
7.5°	3684.5	3620.3	3556.2	3496.6	3432.5	3372.9	3308.7	3253.7	3194.2	3134.6	3079.6
10°	3634.1	3556.2	3478.3	3400.4	3327.1	3249.1	3171.2	3107.1	3038.3	2969.6	2905.4
12.5°	3592.8	3505.8	3418.7	3327.1	3240.0	3148.3	3056.7	2992.5	2928.4	2864.2	2800.0
15°	3542.4	3487.4	3437.0	3354.5	3272.1	3189.6	3107.1	3020.0	2937.5	2850.4	2763.4
17.5°	3501.2	3487.4	3473.7	3418.7	3363.7	3304.1	3249.1	3162.1	3075.0	2983.3	2896.3
20°	3478.3	3496.6	3514.9	3487.4	3460.0	3427.9	3400.4	3336.2	3272.1	3203.3	3139.2
22.5°	3505.8	3574.5	3638.7	3643.3	3652.4	3657.0	3661.6	3602.0	3542.4	3478.3	3418.7
25°	3569.9	3679.9	3789.9	3849.5	3909.1	3973.2	4032.8	3996.1	3959.5	3922.8	3886.1
27.5°	3657.0	3794.5	3932.0	4019.0	4101.5	4188.6	4275.7	4271.1	4266.5	4257.3	4252.8
30°	3643.3	3748.7	3854.1	3959.5	4064.9	4170.3	4275.7	4330.7	4381.1	4436.1	4491.1
32.5°	3721.2	3808.2	3899.9	4009.9	4119.9	4234.4	4344.4	4459.0	4569.0	4683.5	4798.1
35°	3840.3	3918.2	4000.7	4119.9	4243.6	4362.7	4486.5	4624.0	4766.0	4908.1	5045.6
37.5°	4019.0	4087.8	4161.1	4261.9	4367.3	4468.1	4573.6	4775.2	4976.8	5183.1	5384.7
40°	4225.3	4271.1	4316.9	4413.2	4509.4	4605.6	4701.9	4953.9	5206.0	5458.0	5710.1
42.5°	4523.1	4509.4	4495.6	4573.6	4656.0	4733.9	4816.4	5045.6	5274.7	5503.8	5733.0
45°	4839.3	4784.4	4729.4	4766.0	4807.3	4843.9	4885.2	5118.9	5352.6	5590.9	5824.6
47.5°	5219.7	5082.2	4944.8	4912.7	4880.6	4843.9	4811.9	5063.9	5316.0	5572.6	5824.6
50°	5650.5	5444.3	5242.6	5160.1	5073.1	4990.6	4903.5	5109.7	5320.5	5531.3	5737.6
52.5°	6099.6	5843.0	5590.9	5462.6	5334.3	5201.4	5073.1	5247.2	5425.9	5604.7	5778.8
55°	6484.5	6223.3	5957.5	5806.3	5655.1	5503.8	5352.6	5526.8	5700.9	5875.0	6049.2
57.5°	6791.6	6530.4	6269.2	6127.1	5980.4	5838.4	5691.7	5856.7	6026.3	6195.8	6360.8
60°	7002.4	6750.3	6498.3	6360.8	6223.3	6085.8	5948.4	6145.4	6342.5	6544.1	6741.2
62.5°	6892.4	6709.1	6525.8	6466.2	6406.6	6342.5	6282.9	6470.8	6654.1	6842.0	7029.9
65°	6489.1	6365.4	6241.7	6301.2	6365.4	6425.0	6489.1	6612.9	6736.6	6864.9	6988.6
67.5°	5833.8	5824.6	5810.9	5943.8	6076.7	6214.2	6347.1	6429.6	6507.5	6589.9	6672.4
70°	4894.3	4944.8	4990.6	5219.7	5448.8	5678.0	5907.1	5939.2	5971.3	6003.4	6035.4
72.5°	3831.2	3895.3	3964.0	4266.5	4564.4	4866.8	5169.3	5151.0	5132.6	5109.7	5091.4
75°	3015.4	3075.0	3139.2	3418.7	3698.3	3977.8	4257.3	4179.4	4106.1	4028.2	3950.3
77.5°	2405.9	2470.1	2538.8	2800.0	3061.3	3327.1	3588.3	3400.4	3212.5	3024.6	2836.7
80°	2071.4	2103.5	2131.0	2309.7	2483.8	2662.6	2841.3	2648.8	2451.8	2254.7	2062.2
82.5°	1700.2	1681.9	1668.1	1773.5	1878.9	1984.3	2089.7	1906.4	1723.1	1535.2	1351.9
85°	1269.4	1251.1	1232.8	1287.7	1342.7	1402.3	1457.3	1246.5	1035.7	820.3	609.5
87.5°	737.8	756.1	774.5	834.1	893.6	957.8	1017.4	802.0	586.6	366.6	151.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671810
 CATALOG NUMBER: CCP-SA-2E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671810
 CATALOG NUMBER: CCP-SA-2E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	3299.6	3299.6
2.5°	3427.9	3405.0
5°	3240.0	3207.9
7.5°	3033.8	2992.5
10°	2845.9	2790.9
12.5°	2726.7	2658.0
15°	2680.9	2598.4
17.5°	2818.4	2740.5
20°	3029.2	2923.8
22.5°	3285.8	3157.5
25°	3730.3	3574.5
27.5°	4092.4	3932.0
30°	4316.9	4142.8
32.5°	4564.4	4335.2
35°	4821.0	4601.0
37.5°	5132.6	4885.2
40°	5453.4	5196.8
42.5°	5563.4	5398.4
45°	5668.8	5513.0
47.5°	5691.7	5563.4
50°	5714.6	5696.3
52.5°	5778.8	5774.2
55°	6053.8	6058.4
57.5°	6392.9	6420.4
60°	6704.5	6672.4
62.5°	6864.9	6699.9
65°	6754.9	6525.8
67.5°	6425.0	6177.5
70°	5700.9	5366.4
72.5°	4798.1	4504.8
75°	3698.3	3450.8
77.5°	2630.5	2424.3
80°	1851.4	1645.2
82.5°	1186.9	1021.9
85°	536.2	467.4
87.5°	151.2	146.6
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P671810
CATALOG NUMBER: CCP-SA-2E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)