

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P671812

Luminaire Tested: **CCP-SA-1B-735-U-SLR**

Issue Date: 04/16/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P671812  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 04/16/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: CCP-SA-1B-735-U-SLR  
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @450mA w/ SLR distribution lens  
Light Source: (16) 3500K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2826.8 lumens  
Efficiency: N/A  
Efficacy: 117.8 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B1 - U0 - G1

Input Watts (W): 24  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

REPORT NUMBER: P671812  
 CATALOG NUMBER: CCP-SA-1B-735-U-SLR

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 4 fc  
 Type IV - Short - N/A

REPORT NUMBER: P671812  
CATALOG NUMBER: CCP-SA-1B-735-U-SLR

### Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral    - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P671812  
 CATALOG NUMBER: CCP-SA-1B-735-U-SLR


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	581.6	0.0	581.6
	% Fixture	20.6	0.0	20.6
<b>Street Side</b>	Lumens	2245.2	0.0	2245.2
	% Fixture	79.4	0.0	79.4
<b>Total</b>	Lumens	2826.8	0.0	2826.8
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	70.1	2.5
10°-20°	148.1	5.2
20°-30°	216.7	7.7
30°-40°	305.3	10.8
40°-50°	419.5	14.8
50°-60°	571.7	20.2
60°-70°	625.7	22.1
70°-80°	361.4	12.8
80°-90°	108.3	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2826.8	100.0
0°-180°	2826.8	100.0



REPORT NUMBER: P671812


CATALOG NUMBER: CCP-SA-1B-735-U-SLR

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	290.3	10.3			
FM (30°-60°)	1031.6	36.5			
FH (60°-80°)	831.2	29.4			G1/1800
FVH (80°-90°)	92.0	3.3			G1/100
BL (0°-30°)	144.6	5.1	B1/500		
BM (30°-60°)	264.9	9.4	B1/1000		
BH (60°-80°)	155.9	5.5	B1/500		G1/500
BVH (80°-90°)	16.3	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B1-U0-G1**

Type IV Short





REPORT NUMBER: P671812

CATALOG NUMBER: CCP-SA-1B-735-U-SLR

**CANDELA DISTRIBUTION (FULL):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7
2.5°	931.5	926.5	922.8	919.0	914.0	910.2	905.2	900.2	893.9	888.9	882.6
5°	877.6	862.6	847.5	838.8	828.7	820.0	809.9	798.6	787.4	774.8	763.5
7.5°	818.7	799.9	781.1	766.0	749.7	734.7	718.4	704.6	690.8	677.0	663.2
10°	763.5	746.0	728.4	709.6	689.6	670.8	650.7	631.9	613.1	594.3	575.5
12.5°	727.2	705.9	685.8	664.5	644.4	623.1	601.8	584.2	566.7	547.9	530.3
15°	710.9	690.8	672.0	650.7	629.4	608.1	586.8	566.7	547.9	527.8	507.8
17.5°	749.7	720.9	692.1	664.5	636.9	609.3	581.7	556.7	531.6	506.5	481.4
20°	799.9	763.5	728.4	694.6	659.5	625.6	590.5	555.4	520.3	485.2	450.1
22.5°	863.8	822.5	782.3	738.5	693.3	649.4	604.3	560.4	516.5	471.4	427.5
25°	977.9	929.0	880.1	817.4	753.5	690.8	626.9	569.2	512.8	455.1	397.4
27.5°	1075.7	1009.3	944.1	868.8	793.6	718.4	643.2	576.7	511.5	445.1	378.6
30°	1133.4	1068.2	1003.0	911.5	821.2	729.7	638.2	564.2	491.5	417.5	343.5
32.5°	1186.0	1113.3	1040.6	940.3	838.8	738.5	636.9	555.4	475.2	393.7	312.2
35°	1258.8	1178.5	1099.5	982.9	866.3	749.7	633.1	549.1	463.9	379.9	294.6
37.5°	1336.5	1237.5	1139.7	1010.5	881.4	752.3	623.1	540.4	457.6	374.9	292.1
40°	1421.8	1301.4	1182.3	1039.4	897.7	754.8	611.8	529.1	446.3	362.3	279.6
42.5°	1476.9	1346.5	1216.1	1061.9	909.0	754.8	600.5	519.1	437.6	354.8	273.3
45°	1508.3	1381.6	1256.3	1089.5	922.8	756.0	589.3	509.0	428.8	347.3	267.0
47.5°	1522.1	1404.2	1286.3	1110.8	936.6	761.0	585.5	504.0	421.3	339.8	257.0
50°	1558.4	1454.4	1350.3	1162.2	975.4	787.4	599.3	511.5	425.0	337.3	249.5
52.5°	1579.7	1490.7	1401.7	1208.6	1015.5	822.5	629.4	531.6	433.8	336.0	238.2
55°	1657.5	1572.2	1486.9	1281.3	1074.5	868.8	662.0	554.2	446.3	337.3	229.4
57.5°	1756.5	1666.2	1577.2	1355.3	1133.4	911.5	689.6	574.2	457.6	342.3	225.7
60°	1825.5	1737.7	1651.2	1415.5	1178.5	942.8	705.9	585.5	465.1	343.5	223.2
62.5°	1833.0	1720.1	1608.6	1379.1	1149.7	919.0	689.6	573.0	456.4	338.5	221.9
65°	1785.3	1653.7	1522.1	1302.6	1083.2	863.8	644.4	537.9	431.3	323.5	216.9
67.5°	1690.1	1535.8	1381.6	1181.0	980.4	779.8	579.2	487.7	397.4	305.9	214.4
70°	1468.1	1332.7	1198.6	1024.3	851.3	677.0	502.8	427.5	353.6	278.3	203.1
72.5°	1232.4	1105.8	980.4	838.8	698.3	556.7	415.0	358.6	302.2	244.5	188.1
75°	944.1	848.8	754.8	649.4	544.1	437.6	332.2	290.9	249.5	208.1	166.7
77.5°	663.2	611.8	561.7	482.7	403.7	324.7	245.7	218.2	190.6	163.0	135.4
80°	450.1	421.3	393.7	337.3	280.8	223.2	166.7	149.2	130.4	112.8	94.0
82.5°	279.6	278.3	275.8	237.0	198.1	159.2	120.4	105.3	91.5	76.5	61.4
85°	127.9	149.2	169.3	147.9	126.6	105.3	84.0	74.0	63.9	52.7	42.6
87.5°	40.1	48.9	56.4	53.9	50.2	47.6	43.9	37.6	31.3	25.1	18.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671812  
 CATALOG NUMBER: CCP-SA-1B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671812

CATALOG NUMBER: CCP-SA-1B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7
2.5°	877.6	873.9	868.8	863.8	857.6	852.6	846.3	840.0	838.8	836.3	835.0
5°	756.0	748.5	739.7	732.2	724.7	715.9	708.4	699.6	693.3	685.8	679.5
7.5°	649.4	636.9	623.1	609.3	596.8	584.2	570.5	557.9	551.7	545.4	539.1
10°	564.2	551.7	540.4	527.8	519.1	511.5	502.8	494.0	486.5	478.9	471.4
12.5°	521.6	512.8	504.0	495.2	485.2	476.4	466.4	456.4	447.6	440.1	431.3
15°	495.2	482.7	468.9	456.4	442.6	430.0	416.2	402.5	392.4	383.6	373.6
17.5°	463.9	445.1	427.5	408.7	393.7	378.6	362.3	347.3	336.0	323.5	312.2
20°	428.8	407.5	384.9	363.6	346.0	329.7	312.2	294.6	282.1	268.3	255.8
22.5°	398.7	371.1	342.3	313.4	294.6	275.8	255.8	237.0	225.7	213.1	201.9
25°	366.1	336.0	304.7	273.3	254.5	234.5	215.6	195.6	186.8	179.3	170.5
27.5°	348.5	318.5	287.1	257.0	239.5	220.7	203.1	184.3	178.0	170.5	164.2
30°	313.4	284.6	254.5	224.4	211.9	200.6	188.1	175.5	173.0	171.8	169.3
32.5°	282.1	252.0	221.9	191.8	180.5	169.3	158.0	146.7	145.4	142.9	141.7
35°	265.8	237.0	206.9	178.0	168.0	156.7	146.7	135.4	132.9	129.1	126.6
37.5°	262.0	231.9	200.6	170.5	160.5	150.5	139.2	129.1	126.6	124.1	121.6
40°	252.0	223.2	195.6	166.7	156.7	146.7	135.4	125.4	122.9	120.4	117.9
42.5°	244.5	216.9	188.1	159.2	150.5	141.7	131.6	122.9	120.4	117.9	114.1
45°	238.2	209.4	179.3	150.5	144.2	137.9	130.4	124.1	121.6	117.9	115.3
47.5°	228.2	200.6	171.8	142.9	136.7	131.6	125.4	119.1	116.6	114.1	111.6
50°	220.7	191.8	163.0	134.2	129.1	124.1	119.1	114.1	114.1	115.3	115.3
52.5°	210.6	183.0	155.5	127.9	122.9	117.9	112.8	107.8	109.1	110.3	111.6
55°	201.9	175.5	147.9	120.4	115.3	110.3	104.1	99.0	100.3	101.6	102.8
57.5°	198.1	170.5	142.9	115.3	110.3	104.1	99.0	92.8	92.8	92.8	92.8
60°	195.6	166.7	139.2	110.3	104.1	99.0	92.8	86.5	85.3	85.3	84.0
62.5°	194.3	165.5	137.9	109.1	101.6	95.3	87.8	80.2	79.0	77.7	76.5
65°	189.3	163.0	135.4	107.8	99.0	91.5	82.7	74.0	72.7	72.7	71.5
67.5°	188.1	160.5	134.2	106.6	97.8	87.8	79.0	69.0	67.7	66.4	65.2
70°	178.0	154.2	129.1	104.1	94.0	85.3	75.2	65.2	63.9	61.4	60.2
72.5°	165.5	144.2	121.6	99.0	89.0	79.0	69.0	58.9	57.7	56.4	53.9
75°	146.7	126.6	106.6	86.5	77.7	70.2	61.4	52.7	51.4	50.2	47.6
77.5°	120.4	104.1	89.0	72.7	66.4	60.2	53.9	47.6	46.4	45.1	42.6
80°	85.3	75.2	66.4	56.4	52.7	47.6	43.9	38.9	38.9	37.6	37.6
82.5°	56.4	51.4	46.4	41.4	38.9	36.4	33.9	31.3	31.3	30.1	30.1
85°	40.1	37.6	33.9	31.3	30.1	27.6	26.3	23.8	23.8	23.8	23.8
87.5°	18.8	18.8	17.6	17.6	16.3	16.3	15.0	13.8	13.8	13.8	13.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671812  
 CATALOG NUMBER: CCP-SA-1B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671812  
 CATALOG NUMBER: CCP-SA-1B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7
2.5°	832.5	828.7	825.0	820.0	816.2	811.2	804.9	799.9	793.6	793.6	792.4
5°	672.0	668.2	664.5	659.5	655.7	650.7	646.9	641.9	636.9	636.9	635.7
7.5°	532.8	525.3	517.8	509.0	501.5	496.5	491.5	485.2	480.2	476.4	472.7
10°	463.9	456.4	447.6	440.1	431.3	425.0	418.8	411.2	405.0	399.9	394.9
12.5°	422.5	413.7	405.0	396.2	387.4	378.6	371.1	362.3	353.6	347.3	341.0
15°	363.6	354.8	346.0	337.3	328.5	318.5	308.4	297.1	287.1	282.1	278.3
17.5°	299.6	290.9	280.8	272.1	262.0	254.5	247.0	239.5	231.9	226.9	223.2
20°	242.0	231.9	221.9	211.9	201.9	196.8	191.8	186.8	181.8	178.0	175.5
22.5°	189.3	183.0	178.0	171.8	165.5	161.7	159.2	155.5	151.7	151.7	151.7
25°	161.7	158.0	155.5	151.7	147.9	146.7	145.4	142.9	141.7	140.4	140.4
27.5°	156.7	153.0	149.2	145.4	141.7	140.4	139.2	136.7	135.4	135.4	135.4
30°	166.7	165.5	164.2	163.0	161.7	159.2	155.5	153.0	149.2	146.7	144.2
32.5°	139.2	137.9	137.9	136.7	135.4	137.9	139.2	141.7	142.9	144.2	145.4
35°	122.9	120.4	117.9	115.3	112.8	111.6	110.3	109.1	107.8	107.8	106.6
37.5°	119.1	116.6	114.1	111.6	109.1	107.8	106.6	105.3	104.1	104.1	102.8
40°	115.3	112.8	111.6	109.1	106.6	105.3	104.1	101.6	100.3	99.0	99.0
42.5°	111.6	110.3	107.8	106.6	104.1	102.8	101.6	99.0	97.8	96.5	95.3
45°	111.6	109.1	106.6	104.1	101.6	100.3	97.8	96.5	94.0	94.0	92.8
47.5°	109.1	106.6	104.1	101.6	99.0	97.8	95.3	94.0	91.5	90.3	89.0
50°	115.3	111.6	106.6	102.8	97.8	96.5	94.0	92.8	90.3	89.0	87.8
52.5°	112.8	109.1	104.1	100.3	95.3	92.8	91.5	89.0	86.5	85.3	84.0
55°	104.1	100.3	97.8	94.0	90.3	87.8	85.3	82.7	80.2	79.0	79.0
57.5°	92.8	91.5	90.3	89.0	87.8	85.3	82.7	79.0	76.5	75.2	74.0
60°	82.7	84.0	85.3	86.5	87.8	84.0	80.2	76.5	72.7	71.5	70.2
62.5°	75.2	77.7	80.2	81.5	84.0	80.2	76.5	72.7	69.0	67.7	66.4
65°	70.2	71.5	71.5	72.7	72.7	70.2	69.0	66.4	63.9	62.7	62.7
67.5°	63.9	63.9	63.9	62.7	62.7	61.4	61.4	60.2	58.9	57.7	57.7
70°	57.7	57.7	57.7	56.4	56.4	55.2	55.2	53.9	52.7	52.7	51.4
72.5°	52.7	52.7	51.4	51.4	50.2	50.2	50.2	48.9	48.9	47.6	47.6
75°	46.4	46.4	45.1	45.1	43.9	43.9	43.9	42.6	42.6	42.6	41.4
77.5°	41.4	41.4	40.1	40.1	38.9	38.9	38.9	37.6	37.6	36.4	36.4
80°	36.4	36.4	35.1	35.1	33.9	33.9	32.6	32.6	31.3	31.3	30.1
82.5°	28.8	28.8	28.8	28.8	28.8	27.6	27.6	26.3	25.1	25.1	23.8
85°	23.8	23.8	23.8	22.6	22.6	22.6	21.3	21.3	20.1	18.8	18.8
87.5°	13.8	13.8	13.8	12.5	12.5	12.5	12.5	12.5	12.5	12.5	11.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671812  
 CATALOG NUMBER: CCP-SA-1B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671812  
 CATALOG NUMBER: CCP-SA-1B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7
2.5°	792.4	791.1	786.1	781.1	786.1	791.1	791.1	791.1	789.9	789.9	789.9
5°	635.7	634.4	631.9	629.4	629.4	628.1	630.6	633.1	635.7	638.2	640.7
7.5°	467.6	463.9	460.1	456.4	458.9	460.1	463.9	466.4	470.2	472.7	478.9
10°	389.9	384.9	381.1	377.4	374.9	372.4	369.9	368.6	366.1	363.6	366.1
12.5°	333.5	327.2	321.0	313.4	312.2	310.9	308.4	305.9	303.4	300.9	299.6
15°	273.3	268.3	265.8	262.0	257.0	252.0	249.5	248.2	245.7	243.2	242.0
17.5°	218.2	213.1	209.4	205.6	204.4	201.9	201.9	201.9	201.9	201.9	201.9
20°	171.8	168.0	168.0	166.7	166.7	165.5	166.7	168.0	168.0	169.3	170.5
22.5°	150.5	150.5	149.2	147.9	149.2	149.2	150.5	151.7	153.0	154.2	155.5
25°	139.2	137.9	139.2	140.4	140.4	140.4	141.7	141.7	142.9	142.9	142.9
27.5°	134.2	134.2	135.4	135.4	136.7	136.7	136.7	135.4	135.4	134.2	134.2
30°	141.7	139.2	139.2	139.2	137.9	136.7	135.4	135.4	134.2	132.9	131.6
32.5°	146.7	147.9	146.7	144.2	142.9	140.4	139.2	136.7	135.4	132.9	130.4
35°	106.6	105.3	107.8	109.1	110.3	111.6	112.8	114.1	114.1	115.3	115.3
37.5°	102.8	101.6	101.6	100.3	100.3	100.3	100.3	100.3	99.0	99.0	100.3
40°	97.8	96.5	96.5	95.3	95.3	94.0	94.0	94.0	94.0	94.0	94.0
42.5°	94.0	92.8	92.8	92.8	92.8	91.5	91.5	90.3	90.3	89.0	89.0
45°	92.8	91.5	90.3	89.0	89.0	87.8	87.8	87.8	86.5	86.5	86.5
47.5°	87.8	86.5	86.5	85.3	85.3	84.0	84.0	84.0	82.7	82.7	82.7
50°	85.3	84.0	84.0	82.7	82.7	81.5	81.5	81.5	80.2	80.2	80.2
52.5°	81.5	80.2	80.2	80.2	79.0	77.7	77.7	77.7	76.5	76.5	76.5
55°	77.7	76.5	76.5	76.5	75.2	74.0	74.0	74.0	72.7	72.7	72.7
57.5°	72.7	71.5	71.5	70.2	70.2	70.2	70.2	70.2	69.0	69.0	69.0
60°	69.0	67.7	67.7	66.4	66.4	65.2	65.2	65.2	65.2	65.2	65.2
62.5°	65.2	63.9	62.7	61.4	62.7	62.7	62.7	62.7	61.4	61.4	61.4
65°	61.4	60.2	58.9	57.7	57.7	57.7	57.7	57.7	57.7	57.7	57.7
67.5°	56.4	55.2	53.9	52.7	53.9	53.9	53.9	53.9	53.9	53.9	53.9
70°	51.4	50.2	50.2	48.9	48.9	47.6	47.6	48.9	48.9	48.9	48.9
72.5°	46.4	45.1	45.1	43.9	43.9	43.9	43.9	43.9	43.9	43.9	43.9
75°	41.4	40.1	40.1	38.9	38.9	38.9	38.9	38.9	38.9	38.9	38.9
77.5°	35.1	33.9	33.9	33.9	33.9	33.9	33.9	35.1	35.1	35.1	35.1
80°	30.1	28.8	28.8	28.8	28.8	28.8	28.8	28.8	28.8	28.8	28.8
82.5°	23.8	22.6	22.6	22.6	22.6	22.6	22.6	22.6	22.6	22.6	22.6
85°	17.6	16.3	16.3	16.3	17.6	17.6	17.6	17.6	17.6	17.6	17.6
87.5°	11.3	10.0	10.0	10.0	11.3	11.3	11.3	11.3	10.0	10.0	10.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671812  
 CATALOG NUMBER: CCP-SA-1B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671812  
 CATALOG NUMBER: CCP-SA-1B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7
2.5°	789.9	789.9	789.9	788.6	787.4	786.1	784.8	788.6	791.1	794.9	797.4
5°	641.9	644.4	645.7	649.4	653.2	657.0	660.7	663.2	665.7	667.0	669.5
7.5°	483.9	490.2	495.2	500.2	505.3	509.0	514.0	517.8	521.6	525.3	529.1
10°	367.3	369.9	371.1	376.1	379.9	384.9	388.7	392.4	396.2	398.7	402.5
12.5°	298.4	295.9	294.6	294.6	294.6	294.6	294.6	297.1	299.6	302.2	304.7
15°	240.7	239.5	238.2	237.0	235.7	233.2	231.9	234.5	237.0	239.5	242.0
17.5°	201.9	201.9	201.9	200.6	199.3	198.1	196.8	198.1	199.3	199.3	200.6
20°	173.0	174.3	175.5	176.8	176.8	178.0	178.0	179.3	180.5	180.5	181.8
22.5°	155.5	156.7	156.7	156.7	158.0	158.0	158.0	159.2	160.5	161.7	163.0
25°	141.7	141.7	140.4	140.4	141.7	141.7	141.7	141.7	142.9	142.9	142.9
27.5°	134.2	132.9	132.9	132.9	132.9	131.6	131.6	131.6	131.6	131.6	131.6
30°	130.4	129.1	127.9	126.6	126.6	125.4	124.1	124.1	124.1	124.1	124.1
32.5°	129.1	126.6	124.1	122.9	122.9	121.6	120.4	119.1	119.1	117.9	116.6
35°	115.3	114.1	114.1	112.8	111.6	110.3	109.1	109.1	109.1	107.8	107.8
37.5°	100.3	101.6	101.6	101.6	102.8	102.8	102.8	102.8	104.1	104.1	104.1
40°	94.0	94.0	94.0	95.3	96.5	96.5	97.8	97.8	99.0	99.0	99.0
42.5°	89.0	87.8	87.8	89.0	89.0	90.3	90.3	91.5	92.8	92.8	94.0
45°	86.5	85.3	85.3	85.3	85.3	84.0	84.0	85.3	86.5	87.8	89.0
47.5°	81.5	81.5	80.2	80.2	80.2	80.2	80.2	80.2	81.5	81.5	81.5
50°	79.0	79.0	77.7	77.7	77.7	77.7	77.7	77.7	77.7	77.7	77.7
52.5°	76.5	75.2	75.2	75.2	75.2	74.0	74.0	74.0	74.0	74.0	74.0
55°	72.7	71.5	71.5	71.5	71.5	71.5	71.5	71.5	72.7	72.7	72.7
57.5°	69.0	67.7	67.7	67.7	69.0	69.0	69.0	69.0	70.2	70.2	70.2
60°	65.2	65.2	65.2	65.2	65.2	65.2	65.2	66.4	66.4	67.7	67.7
62.5°	61.4	61.4	61.4	61.4	62.7	62.7	62.7	62.7	63.9	63.9	63.9
65°	57.7	57.7	57.7	57.7	58.9	58.9	58.9	58.9	58.9	58.9	58.9
67.5°	53.9	53.9	53.9	53.9	53.9	53.9	53.9	55.2	55.2	56.4	56.4
70°	48.9	47.6	47.6	48.9	48.9	50.2	50.2	51.4	51.4	52.7	52.7
72.5°	43.9	43.9	43.9	43.9	43.9	43.9	43.9	45.1	46.4	46.4	47.6
75°	38.9	38.9	38.9	38.9	40.1	40.1	40.1	41.4	41.4	42.6	42.6
77.5°	35.1	33.9	33.9	33.9	35.1	35.1	35.1	36.4	36.4	37.6	37.6
80°	28.8	28.8	28.8	28.8	30.1	30.1	30.1	30.1	31.3	31.3	31.3
82.5°	23.8	23.8	23.8	23.8	23.8	23.8	23.8	23.8	25.1	25.1	25.1
85°	17.6	17.6	17.6	17.6	18.8	18.8	18.8	18.8	18.8	18.8	18.8
87.5°	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3	12.5	12.5	12.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671812  
 CATALOG NUMBER: CCP-SA-1B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671812  
 CATALOG NUMBER: CCP-SA-1B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7
2.5°	797.4	797.4	797.4	797.4	799.9	801.1	803.7	804.9	803.7	802.4	799.9
5°	670.8	672.0	672.0	673.3	673.3	673.3	673.3	673.3	675.8	678.3	680.8
7.5°	530.3	531.6	532.8	534.1	534.1	534.1	532.8	532.8	534.1	534.1	535.4
10°	406.2	411.2	415.0	418.8	416.2	412.5	410.0	406.2	406.2	406.2	405.0
12.5°	307.2	308.4	310.9	312.2	310.9	310.9	309.7	308.4	309.7	312.2	313.4
15°	243.2	243.2	244.5	244.5	245.7	247.0	247.0	248.2	250.8	252.0	254.5
17.5°	201.9	203.1	203.1	204.4	204.4	205.6	205.6	205.6	208.1	210.6	214.4
20°	181.8	181.8	181.8	181.8	181.8	180.5	180.5	179.3	180.5	183.0	184.3
22.5°	163.0	164.2	164.2	164.2	163.0	161.7	159.2	158.0	158.0	159.2	159.2
25°	142.9	141.7	141.7	140.4	140.4	141.7	141.7	141.7	142.9	142.9	144.2
27.5°	131.6	130.4	130.4	129.1	129.1	130.4	130.4	130.4	130.4	130.4	130.4
30°	122.9	122.9	121.6	120.4	121.6	121.6	122.9	122.9	124.1	124.1	125.4
32.5°	116.6	115.3	115.3	114.1	115.3	115.3	116.6	116.6	117.9	119.1	119.1
35°	107.8	107.8	107.8	107.8	107.8	107.8	106.6	106.6	106.6	106.6	106.6
37.5°	102.8	102.8	101.6	100.3	100.3	100.3	100.3	100.3	99.0	97.8	96.5
40°	99.0	97.8	97.8	96.5	95.3	95.3	94.0	92.8	92.8	91.5	91.5
42.5°	94.0	92.8	92.8	91.5	90.3	90.3	89.0	87.8	87.8	87.8	86.5
45°	87.8	87.8	86.5	85.3	85.3	85.3	84.0	84.0	84.0	84.0	82.7
47.5°	81.5	81.5	80.2	80.2	80.2	80.2	79.0	79.0	79.0	79.0	79.0
50°	77.7	77.7	77.7	77.7	77.7	77.7	76.5	76.5	76.5	76.5	76.5
52.5°	74.0	74.0	74.0	74.0	74.0	74.0	74.0	74.0	74.0	74.0	74.0
55°	72.7	72.7	72.7	72.7	72.7	72.7	71.5	71.5	71.5	72.7	72.7
57.5°	70.2	70.2	69.0	69.0	69.0	69.0	69.0	69.0	69.0	69.0	69.0
60°	67.7	67.7	67.7	67.7	67.7	67.7	67.7	67.7	67.7	67.7	67.7
62.5°	63.9	63.9	63.9	63.9	63.9	65.2	65.2	65.2	65.2	65.2	63.9
65°	58.9	60.2	60.2	60.2	60.2	60.2	60.2	60.2	60.2	60.2	60.2
67.5°	56.4	56.4	56.4	56.4	56.4	56.4	56.4	56.4	56.4	56.4	56.4
70°	52.7	52.7	51.4	51.4	51.4	52.7	52.7	52.7	52.7	52.7	52.7
72.5°	47.6	47.6	47.6	47.6	47.6	47.6	47.6	47.6	47.6	48.9	48.9
75°	42.6	42.6	42.6	42.6	42.6	42.6	42.6	42.6	42.6	42.6	42.6
77.5°	37.6	37.6	36.4	36.4	36.4	37.6	37.6	37.6	37.6	38.9	38.9
80°	31.3	31.3	31.3	31.3	31.3	31.3	31.3	31.3	31.3	32.6	32.6
82.5°	25.1	25.1	25.1	25.1	25.1	25.1	25.1	25.1	25.1	26.3	26.3
85°	18.8	20.1	20.1	20.1	20.1	20.1	20.1	20.1	20.1	21.3	21.3
87.5°	12.5	12.5	12.5	12.5	12.5	12.5	11.3	11.3	11.3	11.3	10.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671812  
 CATALOG NUMBER: CCP-SA-1B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671812  
 CATALOG NUMBER: CCP-SA-1B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7
2.5°	798.6	799.9	801.1	801.1	802.4	803.7	803.7	808.7	813.7	816.2	818.7
5°	683.3	682.0	682.0	680.8	679.5	683.3	687.1	694.6	702.1	703.4	705.9
7.5°	535.4	536.6	537.9	537.9	539.1	535.4	530.3	531.6	532.8	539.1	544.1
10°	405.0	406.2	407.5	407.5	408.7	407.5	405.0	408.7	412.5	417.5	423.8
12.5°	314.7	318.5	322.2	324.7	328.5	331.0	332.2	337.3	341.0	347.3	353.6
15°	257.0	259.5	262.0	264.5	267.0	269.6	272.1	277.1	282.1	289.6	297.1
17.5°	216.9	216.9	218.2	218.2	218.2	220.7	223.2	225.7	226.9	234.5	242.0
20°	185.6	184.3	183.0	181.8	180.5	183.0	184.3	185.6	186.8	191.8	195.6
22.5°	159.2	159.2	160.5	160.5	160.5	159.2	156.7	158.0	158.0	160.5	164.2
25°	144.2	144.2	144.2	142.9	142.9	144.2	145.4	145.4	144.2	145.4	146.7
27.5°	130.4	131.6	131.6	132.9	132.9	134.2	134.2	134.2	134.2	135.4	136.7
30°	125.4	125.4	126.6	126.6	126.6	127.9	129.1	129.1	129.1	130.4	132.9
32.5°	120.4	121.6	122.9	124.1	125.4	126.6	126.6	127.9	127.9	129.1	130.4
35°	106.6	105.3	105.3	104.1	102.8	102.8	102.8	102.8	101.6	102.8	102.8
37.5°	95.3	95.3	95.3	94.0	94.0	95.3	95.3	95.3	95.3	96.5	96.5
40°	90.3	90.3	90.3	90.3	90.3	90.3	90.3	91.5	91.5	92.8	94.0
42.5°	86.5	86.5	86.5	86.5	86.5	87.8	87.8	87.8	87.8	89.0	89.0
45°	82.7	82.7	82.7	82.7	82.7	82.7	82.7	84.0	84.0	85.3	86.5
47.5°	79.0	79.0	79.0	79.0	79.0	80.2	81.5	81.5	81.5	82.7	82.7
50°	76.5	76.5	76.5	76.5	76.5	77.7	77.7	79.0	79.0	80.2	81.5
52.5°	74.0	74.0	74.0	74.0	74.0	75.2	75.2	76.5	76.5	77.7	79.0
55°	72.7	72.7	72.7	71.5	71.5	72.7	72.7	74.0	74.0	75.2	75.2
57.5°	69.0	69.0	69.0	69.0	69.0	69.0	69.0	70.2	70.2	71.5	72.7
60°	67.7	67.7	66.4	66.4	65.2	66.4	66.4	67.7	67.7	69.0	69.0
62.5°	63.9	63.9	63.9	62.7	62.7	63.9	63.9	63.9	63.9	65.2	66.4
65°	60.2	60.2	60.2	58.9	58.9	60.2	60.2	60.2	60.2	61.4	62.7
67.5°	56.4	56.4	56.4	55.2	55.2	55.2	55.2	56.4	56.4	57.7	58.9
70°	52.7	52.7	52.7	51.4	51.4	51.4	50.2	51.4	52.7	53.9	53.9
72.5°	48.9	48.9	48.9	47.6	47.6	47.6	46.4	47.6	47.6	48.9	48.9
75°	42.6	42.6	42.6	42.6	42.6	42.6	41.4	41.4	41.4	42.6	42.6
77.5°	38.9	38.9	38.9	37.6	37.6	37.6	36.4	36.4	36.4	37.6	37.6
80°	32.6	32.6	32.6	31.3	31.3	31.3	30.1	30.1	30.1	31.3	31.3
82.5°	26.3	26.3	26.3	25.1	25.1	25.1	23.8	23.8	23.8	25.1	25.1
85°	21.3	21.3	21.3	21.3	21.3	21.3	20.1	20.1	20.1	21.3	22.6
87.5°	10.0	10.0	11.3	11.3	11.3	11.3	10.0	10.0	8.8	8.8	10.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671812  
 CATALOG NUMBER: CCP-SA-1B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671812  
 CATALOG NUMBER: CCP-SA-1B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7
2.5°	821.2	823.7	830.0	835.0	841.3	846.3	850.0	855.1	858.8	862.6	865.1
5°	707.1	708.4	714.6	720.9	725.9	732.2	741.0	749.7	758.5	767.3	773.6
7.5°	550.4	555.4	562.9	571.7	579.2	586.8	595.5	605.6	614.3	623.1	631.9
10°	428.8	433.8	441.3	448.8	455.1	462.6	472.7	482.7	492.7	502.8	512.8
12.5°	359.8	366.1	374.9	383.6	391.2	399.9	412.5	423.8	436.3	447.6	460.1
15°	303.4	310.9	322.2	334.8	346.0	357.3	369.9	382.4	393.7	406.2	418.8
17.5°	249.5	257.0	267.0	278.3	288.4	298.4	313.4	327.2	342.3	356.1	369.9
20°	200.6	204.4	214.4	224.4	234.5	244.5	255.8	267.0	278.3	289.6	307.2
22.5°	166.7	169.3	174.3	178.0	183.0	186.8	198.1	209.4	219.4	230.7	247.0
25°	146.7	147.9	151.7	154.2	158.0	160.5	168.0	174.3	181.8	188.1	203.1
27.5°	136.7	137.9	139.2	140.4	141.7	142.9	147.9	153.0	156.7	161.7	175.5
30°	134.2	135.4	139.2	141.7	145.4	147.9	150.5	153.0	155.5	158.0	166.7
32.5°	131.6	132.9	132.9	131.6	131.6	130.4	132.9	134.2	136.7	137.9	145.4
35°	104.1	104.1	105.3	106.6	107.8	109.1	112.8	115.3	119.1	121.6	127.9
37.5°	97.8	97.8	99.0	101.6	102.8	104.1	106.6	109.1	111.6	114.1	120.4
40°	94.0	95.3	96.5	97.8	99.0	100.3	102.8	104.1	106.6	107.8	112.8
42.5°	90.3	90.3	91.5	94.0	95.3	96.5	99.0	100.3	102.8	104.1	109.1
45°	87.8	89.0	90.3	91.5	91.5	92.8	95.3	97.8	99.0	101.6	106.6
47.5°	84.0	84.0	86.5	87.8	90.3	91.5	94.0	95.3	97.8	99.0	104.1
50°	81.5	82.7	85.3	86.5	89.0	90.3	94.0	96.5	100.3	102.8	105.3
52.5°	79.0	80.2	82.7	84.0	86.5	87.8	92.8	97.8	101.6	106.6	106.6
55°	76.5	76.5	79.0	82.7	85.3	87.8	90.3	94.0	96.5	99.0	99.0
57.5°	72.7	74.0	76.5	80.2	82.7	85.3	87.8	90.3	91.5	94.0	92.8
60°	70.2	70.2	74.0	77.7	81.5	85.3	85.3	85.3	84.0	84.0	84.0
62.5°	66.4	67.7	72.7	79.0	84.0	89.0	85.3	81.5	77.7	74.0	75.2
65°	63.9	65.2	67.7	71.5	74.0	76.5	74.0	72.7	70.2	67.7	69.0
67.5°	58.9	60.2	61.4	61.4	62.7	62.7	62.7	62.7	62.7	62.7	63.9
70°	55.2	55.2	55.2	56.4	56.4	56.4	56.4	56.4	56.4	56.4	57.7
72.5°	50.2	50.2	50.2	50.2	50.2	50.2	50.2	50.2	50.2	50.2	51.4
75°	43.9	43.9	43.9	43.9	43.9	43.9	43.9	43.9	43.9	43.9	45.1
77.5°	38.9	38.9	38.9	38.9	38.9	38.9	38.9	38.9	37.6	37.6	38.9
80°	32.6	32.6	32.6	32.6	31.3	31.3	31.3	31.3	31.3	31.3	32.6
82.5°	26.3	26.3	26.3	26.3	25.1	25.1	25.1	25.1	23.8	23.8	25.1
85°	23.8	25.1	25.1	26.3	26.3	26.3	25.1	23.8	22.6	21.3	21.3
87.5°	10.0	10.0	10.0	10.0	8.8	8.8	8.8	8.8	8.8	8.8	8.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671812  
 CATALOG NUMBER: CCP-SA-1B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671812  
 CATALOG NUMBER: CCP-SA-1B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7
2.5°	868.8	871.4	873.9	877.6	882.6	886.4	890.2	897.7	906.5	914.0	921.5
5°	779.8	786.1	792.4	799.9	807.4	813.7	821.2	836.3	851.3	865.1	880.1
7.5°	639.4	648.2	655.7	668.2	679.5	692.1	703.4	722.2	739.7	758.5	776.1
10°	522.8	532.8	542.9	559.2	576.7	593.0	609.3	624.4	640.7	655.7	670.8
12.5°	472.7	483.9	496.5	506.5	517.8	527.8	537.9	555.4	573.0	590.5	608.1
15°	431.3	443.8	456.4	468.9	480.2	492.7	504.0	519.1	535.4	550.4	565.4
17.5°	383.6	396.2	410.0	423.8	437.6	451.4	465.1	486.5	507.8	527.8	549.1
20°	323.5	341.0	357.3	376.1	394.9	413.7	432.5	455.1	477.7	499.0	521.6
22.5°	263.3	279.6	295.9	318.5	341.0	362.3	384.9	415.0	443.8	473.9	502.8
25°	219.4	234.5	249.5	274.6	298.4	323.5	347.3	383.6	418.8	455.1	490.2
27.5°	189.3	203.1	216.9	243.2	269.6	294.6	321.0	361.1	399.9	440.1	478.9
30°	175.5	184.3	193.1	218.2	243.2	267.0	292.1	331.0	369.9	408.7	447.6
32.5°	153.0	160.5	168.0	190.6	213.1	234.5	257.0	297.1	336.0	376.1	415.0
35°	135.4	141.7	147.9	169.3	189.3	210.6	230.7	270.8	310.9	351.1	391.2
37.5°	125.4	131.6	136.7	155.5	175.5	194.3	213.1	253.3	292.1	332.2	371.1
40°	117.9	121.6	126.6	145.4	163.0	181.8	199.3	235.7	273.3	309.7	346.0
42.5°	112.8	117.9	121.6	137.9	155.5	171.8	188.1	223.2	258.3	292.1	327.2
45°	111.6	116.6	121.6	135.4	149.2	161.7	175.5	209.4	243.2	277.1	310.9
47.5°	109.1	112.8	117.9	129.1	139.2	150.5	160.5	194.3	228.2	260.8	294.6
50°	107.8	109.1	111.6	121.6	131.6	141.7	151.7	185.6	219.4	253.3	287.1
52.5°	106.6	106.6	106.6	115.3	124.1	131.6	140.4	174.3	209.4	243.2	277.1
55°	99.0	97.8	97.8	106.6	114.1	122.9	130.4	164.2	198.1	230.7	264.5
57.5°	91.5	90.3	89.0	96.5	104.1	111.6	119.1	153.0	188.1	221.9	255.8
60°	84.0	82.7	82.7	90.3	96.5	104.1	110.3	145.4	179.3	214.4	248.2
62.5°	75.2	76.5	76.5	82.7	90.3	96.5	102.8	137.9	174.3	209.4	244.5
65°	69.0	70.2	70.2	77.7	85.3	92.8	100.3	134.2	169.3	203.1	237.0
67.5°	63.9	65.2	65.2	74.0	81.5	90.3	97.8	127.9	159.2	189.3	219.4
70°	58.9	58.9	60.2	69.0	77.7	86.5	95.3	121.6	147.9	173.0	199.3
72.5°	52.7	53.9	55.2	63.9	71.5	80.2	87.8	111.6	135.4	159.2	183.0
75°	46.4	47.6	48.9	56.4	63.9	71.5	79.0	101.6	122.9	145.4	166.7
77.5°	41.4	42.6	43.9	50.2	56.4	62.7	69.0	85.3	102.8	119.1	135.4
80°	33.9	33.9	35.1	40.1	45.1	48.9	53.9	65.2	76.5	86.5	97.8
82.5°	25.1	26.3	26.3	30.1	32.6	36.4	38.9	45.1	50.2	56.4	61.4
85°	21.3	20.1	20.1	22.6	23.8	26.3	27.6	31.3	33.9	37.6	40.1
87.5°	8.8	7.5	7.5	8.8	11.3	12.5	13.8	13.8	15.0	15.0	15.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671812  
 CATALOG NUMBER: CCP-SA-1B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671812

CATALOG NUMBER: CCP-SA-1B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7
2.5°	925.3	927.8	931.5	934.0	940.3	945.3	951.6	956.6	960.4	966.6	964.1
5°	891.4	902.7	914.0	925.3	934.0	942.8	950.3	959.1	969.1	988.0	993.0
7.5°	791.1	806.2	820.0	835.0	852.6	870.1	887.7	905.2	921.5	945.3	960.4
10°	692.1	713.4	733.4	754.8	771.1	787.4	802.4	818.7	841.3	865.1	892.7
12.5°	629.4	650.7	672.0	693.3	717.1	739.7	763.5	786.1	807.4	826.2	857.6
15°	588.0	611.8	634.4	657.0	685.8	713.4	742.2	769.8	801.1	826.2	847.5
17.5°	578.0	606.8	634.4	663.2	693.3	723.4	753.5	783.6	814.9	852.6	880.1
20°	560.4	599.3	638.2	677.0	715.9	753.5	792.4	830.0	871.4	916.5	929.0
22.5°	550.4	596.8	644.4	690.8	743.5	797.4	850.0	902.7	946.6	980.4	1018.0
25°	549.1	606.8	665.7	723.4	789.9	855.1	921.5	986.7	1043.1	1077.0	1107.1
27.5°	547.9	618.1	687.1	756.0	837.5	917.7	999.2	1079.5	1132.1	1181.0	1206.1
30°	532.8	616.8	702.1	786.1	877.6	969.1	1060.7	1152.2	1206.1	1240.0	1252.5
32.5°	514.0	613.1	712.1	811.2	915.2	1019.3	1122.1	1226.2	1268.8	1297.6	1287.6
35°	499.0	608.1	715.9	823.7	934.0	1045.6	1156.0	1266.3	1327.7	1367.8	1351.5
37.5°	485.2	599.3	713.4	827.5	956.6	1085.7	1214.9	1344.0	1402.9	1445.6	1426.8
40°	468.9	590.5	713.4	835.0	982.9	1129.6	1277.6	1424.3	1500.7	1537.1	1508.3
42.5°	455.1	581.7	709.6	836.3	994.2	1152.2	1310.2	1468.1	1553.4	1604.8	1568.4
45°	437.6	564.2	689.6	816.2	990.5	1164.7	1337.8	1512.0	1611.1	1651.2	1601.0
47.5°	418.8	544.1	668.2	792.4	977.9	1163.5	1349.0	1534.6	1626.1	1673.8	1627.4
50°	412.5	537.9	662.0	787.4	988.0	1189.8	1390.4	1591.0	1657.5	1696.3	1634.9
52.5°	411.2	544.1	678.3	811.2	1013.0	1213.6	1415.5	1616.1	1670.0	1711.4	1656.2
55°	407.5	551.7	694.6	837.5	1048.1	1260.0	1470.6	1681.3	1735.2	1765.3	1723.9
57.5°	411.2	566.7	720.9	876.4	1093.3	1310.2	1527.1	1744.0	1809.2	1830.5	1821.7
60°	413.7	579.2	743.5	909.0	1120.9	1332.7	1544.6	1756.5	1824.2	1876.9	1886.9
62.5°	407.5	570.5	732.2	895.2	1087.0	1278.8	1470.6	1662.5	1774.1	1851.8	1896.9
65°	388.7	539.1	690.8	841.3	1018.0	1196.1	1372.9	1549.6	1667.5	1782.8	1819.2
67.5°	347.3	475.2	603.1	730.9	885.1	1039.4	1192.3	1346.5	1494.5	1606.1	1656.2
70°	300.9	401.2	502.8	603.1	743.5	883.9	1024.3	1164.7	1295.1	1418.0	1465.6
72.5°	262.0	339.8	418.8	496.5	596.8	695.8	796.1	895.2	1049.4	1172.3	1218.6
75°	223.2	279.6	334.8	391.2	460.1	529.1	596.8	665.7	774.8	885.1	931.5
77.5°	171.8	209.4	245.7	282.1	329.7	376.1	423.8	470.2	546.6	629.4	653.2
80°	119.1	140.4	160.5	181.8	219.4	257.0	294.6	332.2	382.4	428.8	465.1
82.5°	74.0	87.8	100.3	112.8	142.9	173.0	201.9	231.9	252.0	254.5	290.9
85°	47.6	56.4	63.9	71.5	89.0	107.8	125.4	142.9	127.9	119.1	141.7
87.5°	18.8	23.8	27.6	31.3	30.1	28.8	27.6	26.3	22.6	20.1	25.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671812  
 CATALOG NUMBER: CCP-SA-1B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671812

CATALOG NUMBER: CCP-SA-1B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7
2.5°	966.6	970.4	974.2	976.7	980.4	981.7	982.9	982.9	984.2	985.4	988.0
5°	1013.0	1020.6	1028.1	1034.3	1041.9	1048.1	1053.2	1059.4	1064.4	1064.4	1063.2
7.5°	974.2	993.0	1011.8	1030.6	1049.4	1063.2	1075.7	1089.5	1102.0	1104.6	1107.1
10°	922.8	942.8	961.6	981.7	1000.5	1021.8	1041.9	1061.9	1083.2	1087.0	1092.0
12.5°	875.1	898.9	922.8	945.3	969.1	984.2	999.2	1013.0	1028.1	1038.1	1048.1
15°	873.9	893.9	914.0	932.8	952.9	961.6	970.4	977.9	986.7	986.7	988.0
17.5°	902.7	915.2	927.8	939.1	951.6	952.9	955.4	956.6	957.9	954.1	950.3
20°	959.1	964.1	969.1	974.2	979.2	970.4	962.9	954.1	945.3	935.3	926.5
22.5°	1041.9	1030.6	1019.3	1008.0	996.7	981.7	965.4	950.3	934.0	921.5	909.0
25°	1119.6	1105.8	1092.0	1078.2	1064.4	1031.8	999.2	965.4	932.8	919.0	905.2
27.5°	1223.7	1202.3	1181.0	1159.7	1138.4	1094.5	1050.6	1006.8	962.9	939.1	916.5
30°	1248.7	1224.9	1201.1	1176.0	1152.2	1109.6	1068.2	1025.6	982.9	955.4	929.0
32.5°	1285.1	1257.5	1229.9	1202.3	1174.8	1133.4	1092.0	1049.4	1008.0	982.9	956.6
35°	1345.3	1313.9	1282.6	1250.0	1218.6	1176.0	1134.6	1092.0	1049.4	1020.6	993.0
37.5°	1396.7	1360.3	1324.0	1287.6	1251.2	1213.6	1174.8	1137.2	1098.3	1069.4	1041.9
40°	1454.4	1414.2	1374.1	1335.2	1295.1	1260.0	1224.9	1188.6	1153.5	1130.9	1108.3
42.5°	1504.5	1455.6	1408.0	1360.3	1311.4	1287.6	1265.0	1241.2	1217.4	1206.1	1193.6
45°	1539.6	1494.5	1448.1	1402.9	1357.8	1340.3	1322.7	1305.2	1287.6	1298.9	1310.2
47.5°	1554.7	1518.3	1483.2	1448.1	1411.7	1418.0	1424.3	1429.3	1435.5	1450.6	1466.9
50°	1568.4	1548.4	1527.1	1507.0	1485.7	1509.5	1532.1	1555.9	1579.7	1611.1	1642.4
52.5°	1596.0	1584.7	1574.7	1563.4	1552.1	1593.5	1634.9	1676.3	1717.6	1752.7	1787.8
55°	1678.8	1670.0	1661.2	1651.2	1642.4	1701.3	1759.0	1817.9	1876.9	1913.2	1949.6
57.5°	1792.9	1787.8	1781.6	1776.6	1770.3	1828.0	1884.4	1940.8	1998.5	2033.6	2069.9
60°	1879.4	1880.6	1880.6	1881.9	1881.9	1925.8	1969.6	2014.8	2058.7	2088.7	2120.1
62.5°	1925.8	1923.3	1920.7	1918.2	1915.7	1952.1	1988.4	2024.8	2061.2	2083.7	2106.3
65°	1875.6	1889.4	1903.2	1917.0	1930.8	1935.8	1939.6	1944.6	1948.3	1962.1	1975.9
67.5°	1707.6	1735.2	1761.5	1789.1	1815.4	1796.6	1779.1	1760.3	1741.5	1745.2	1747.7
70°	1520.8	1552.1	1584.7	1616.1	1647.4	1603.5	1559.7	1514.5	1470.6	1455.6	1440.6
72.5°	1282.6	1310.2	1339.0	1366.6	1394.2	1340.3	1287.6	1233.7	1179.8	1153.5	1127.1
75°	980.4	1013.0	1046.9	1079.5	1112.1	1051.9	990.5	930.3	868.8	851.3	835.0
77.5°	714.6	753.5	792.4	831.2	870.1	816.2	762.3	707.1	653.2	643.2	633.1
80°	520.3	550.4	579.2	609.3	638.2	606.8	575.5	544.1	512.8	511.5	510.3
82.5°	351.1	377.4	402.5	428.8	453.9	441.3	430.0	417.5	405.0	417.5	431.3
85°	180.5	216.9	254.5	290.9	327.2	323.5	321.0	317.2	313.4	329.7	344.8
87.5°	36.4	67.7	99.0	129.1	160.5	153.0	145.4	136.7	129.1	134.2	137.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671812  
 CATALOG NUMBER: CCP-SA-1B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671812

CATALOG NUMBER: CCP-SA-1B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7
2.5°	989.2	990.5	990.5	990.5	990.5	990.5	988.0	986.7	984.2	981.7	977.9
5°	1063.2	1061.9	1056.9	1051.9	1045.6	1040.6	1036.9	1031.8	1028.1	1023.1	1015.5
7.5°	1109.6	1112.1	1103.3	1095.8	1087.0	1078.2	1069.4	1060.7	1051.9	1043.1	1025.6
10°	1095.8	1099.5	1094.5	1089.5	1083.2	1078.2	1068.2	1056.9	1046.9	1035.6	1014.3
12.5°	1056.9	1066.9	1064.4	1061.9	1059.4	1056.9	1050.6	1043.1	1036.9	1029.3	1005.5
15°	988.0	988.0	989.2	990.5	990.5	991.7	993.0	994.2	995.5	996.7	982.9
17.5°	946.6	942.8	942.8	942.8	942.8	942.8	947.8	954.1	959.1	964.1	960.4
20°	916.5	907.7	906.5	906.5	905.2	904.0	912.7	922.8	931.5	940.3	945.3
22.5°	896.4	883.9	882.6	881.4	880.1	878.9	890.2	901.4	912.7	924.0	941.6
25°	891.4	877.6	878.9	880.1	880.1	881.4	890.2	898.9	907.7	916.5	946.6
27.5°	892.7	870.1	871.4	872.6	872.6	873.9	887.7	900.2	914.0	926.5	964.1
30°	901.4	875.1	872.6	870.1	867.6	865.1	883.9	902.7	921.5	940.3	969.1
32.5°	931.5	906.5	900.2	893.9	887.7	881.4	904.0	925.3	947.8	969.1	993.0
35°	964.1	936.6	934.0	931.5	927.8	925.3	945.3	966.6	986.7	1006.8	1028.1
37.5°	1013.0	985.4	982.9	979.2	976.7	972.9	995.5	1016.8	1039.4	1060.7	1079.5
40°	1085.7	1063.2	1061.9	1061.9	1060.7	1059.4	1077.0	1095.8	1113.3	1130.9	1143.4
42.5°	1182.3	1171.0	1174.8	1179.8	1183.5	1187.3	1201.1	1216.1	1229.9	1243.7	1240.0
45°	1321.5	1332.7	1334.0	1335.2	1336.5	1337.8	1341.5	1346.5	1350.3	1354.1	1339.0
47.5°	1481.9	1497.0	1504.5	1512.0	1518.3	1525.8	1520.8	1514.5	1509.5	1503.2	1465.6
50°	1672.5	1703.8	1702.6	1701.3	1698.8	1697.6	1687.5	1677.5	1666.2	1656.2	1601.0
52.5°	1823.0	1858.1	1864.3	1870.6	1876.9	1883.1	1864.3	1845.5	1825.5	1806.7	1737.7
55°	1984.7	2021.0	2022.3	2023.6	2023.6	2024.8	1998.5	1972.1	1944.6	1918.2	1846.8
57.5°	2105.0	2140.2	2136.4	2133.9	2130.1	2126.4	2095.0	2063.7	2032.3	2001.0	1929.5
60°	2150.2	2180.3	2172.7	2165.2	2156.5	2148.9	2125.1	2101.3	2076.2	2052.4	1983.4
62.5°	2128.9	2151.4	2140.2	2130.1	2118.8	2107.6	2077.5	2046.1	2016.0	1984.7	1934.5
65°	1988.4	2002.2	1987.2	1973.4	1959.6	1944.6	1919.5	1894.4	1868.1	1843.0	1809.2
67.5°	1751.5	1754.0	1752.7	1751.5	1750.2	1749.0	1712.6	1676.3	1638.7	1602.3	1599.8
70°	1426.8	1411.7	1414.2	1418.0	1420.5	1423.0	1395.4	1369.1	1341.5	1313.9	1326.5
72.5°	1100.8	1074.5	1080.7	1088.3	1094.5	1100.8	1078.2	1056.9	1034.3	1011.8	1029.3
75°	817.4	801.1	807.4	814.9	821.2	827.5	818.7	809.9	799.9	791.1	807.4
77.5°	623.1	613.1	614.3	614.3	615.6	615.6	616.8	619.4	620.6	621.9	639.4
80°	507.8	506.5	505.3	504.0	501.5	500.2	512.8	525.3	537.9	550.4	559.2
82.5°	443.8	456.4	448.8	442.6	435.1	427.5	438.8	450.1	461.4	472.7	468.9
85°	361.1	376.1	362.3	348.5	333.5	319.7	329.7	338.5	348.5	357.3	352.3
87.5°	142.9	146.7	124.1	102.8	80.2	57.7	91.5	124.1	158.0	190.6	195.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671812  
 CATALOG NUMBER: CCP-SA-1B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671812

CATALOG NUMBER: CCP-SA-1B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7	902.7
2.5°	974.2	969.1	965.4	964.1	961.6	960.4	957.9	955.4	951.6	949.1	945.3
5°	1006.8	999.2	990.5	977.9	966.6	954.1	941.6	930.3	919.0	906.5	895.2
7.5°	1008.0	990.5	972.9	956.6	939.1	922.8	905.2	890.2	873.9	857.6	842.5
10°	994.2	972.9	951.6	930.3	910.2	888.9	867.6	850.0	831.2	812.4	794.9
12.5°	982.9	959.1	935.3	910.2	886.4	861.3	836.3	818.7	801.1	783.6	766.0
15°	969.1	954.1	940.3	917.7	895.2	872.6	850.0	826.2	803.7	779.8	756.0
17.5°	957.9	954.1	950.3	935.3	920.3	904.0	888.9	865.1	841.3	816.2	792.4
20°	951.6	956.6	961.6	954.1	946.6	937.8	930.3	912.7	895.2	876.4	858.8
22.5°	959.1	977.9	995.5	996.7	999.2	1000.5	1001.7	985.4	969.1	951.6	935.3
25°	976.7	1006.8	1036.9	1053.2	1069.4	1087.0	1103.3	1093.3	1083.2	1073.2	1063.2
27.5°	1000.5	1038.1	1075.7	1099.5	1122.1	1145.9	1169.7	1168.5	1167.2	1164.7	1163.5
30°	996.7	1025.6	1054.4	1083.2	1112.1	1140.9	1169.7	1184.8	1198.6	1213.6	1228.7
32.5°	1018.0	1041.9	1066.9	1097.0	1127.1	1158.5	1188.6	1219.9	1250.0	1281.3	1312.7
35°	1050.6	1072.0	1094.5	1127.1	1161.0	1193.6	1227.4	1265.0	1303.9	1342.8	1380.4
37.5°	1099.5	1118.3	1138.4	1166.0	1194.8	1222.4	1251.2	1306.4	1361.6	1418.0	1473.2
40°	1156.0	1168.5	1181.0	1207.4	1233.7	1260.0	1286.3	1355.3	1424.3	1493.2	1562.2
42.5°	1237.5	1233.7	1229.9	1251.2	1273.8	1295.1	1317.7	1380.4	1443.1	1505.8	1568.4
45°	1324.0	1308.9	1293.9	1303.9	1315.2	1325.2	1336.5	1400.4	1464.4	1529.6	1593.5
47.5°	1428.0	1390.4	1352.8	1344.0	1335.2	1325.2	1316.4	1385.4	1454.4	1524.6	1593.5
50°	1545.9	1489.5	1434.3	1411.7	1387.9	1365.3	1341.5	1397.9	1455.6	1513.3	1569.7
52.5°	1668.7	1598.5	1529.6	1494.5	1459.4	1423.0	1387.9	1435.5	1484.4	1533.3	1581.0
55°	1774.1	1702.6	1629.9	1588.5	1547.1	1505.8	1464.4	1512.0	1559.7	1607.3	1655.0
57.5°	1858.1	1786.6	1715.1	1676.3	1636.1	1597.3	1557.2	1602.3	1648.7	1695.1	1740.2
60°	1915.7	1846.8	1777.8	1740.2	1702.6	1665.0	1627.4	1681.3	1735.2	1790.4	1844.3
62.5°	1885.6	1835.5	1785.3	1769.0	1752.7	1735.2	1718.9	1770.3	1820.4	1871.8	1923.3
65°	1775.3	1741.5	1707.6	1723.9	1741.5	1757.8	1775.3	1809.2	1843.0	1878.1	1912.0
67.5°	1596.0	1593.5	1589.8	1626.1	1662.5	1700.1	1736.4	1759.0	1780.3	1802.9	1825.5
70°	1339.0	1352.8	1365.3	1428.0	1490.7	1553.4	1616.1	1624.9	1633.6	1642.4	1651.2
72.5°	1048.1	1065.7	1084.5	1167.2	1248.7	1331.5	1414.2	1409.2	1404.2	1397.9	1392.9
75°	825.0	841.3	858.8	935.3	1011.8	1088.3	1164.7	1143.4	1123.4	1102.0	1080.7
77.5°	658.2	675.8	694.6	766.0	837.5	910.2	981.7	930.3	878.9	827.5	776.1
80°	566.7	575.5	583.0	631.9	679.5	728.4	777.3	724.7	670.8	616.8	564.2
82.5°	465.1	460.1	456.4	485.2	514.0	542.9	571.7	521.6	471.4	420.0	369.9
85°	347.3	342.3	337.3	352.3	367.3	383.6	398.7	341.0	283.3	224.4	166.7
87.5°	201.9	206.9	211.9	228.2	244.5	262.0	278.3	219.4	160.5	100.3	41.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671812  
 CATALOG NUMBER: CCP-SA-1B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671812  
 CATALOG NUMBER: CCP-SA-1B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
0°	902.7	902.7
2.5°	937.8	931.5
5°	886.4	877.6
7.5°	830.0	818.7
10°	778.6	763.5
12.5°	746.0	727.2
15°	733.4	710.9
17.5°	771.1	749.7
20°	828.7	799.9
22.5°	898.9	863.8
25°	1020.6	977.9
27.5°	1119.6	1075.7
30°	1181.0	1133.4
32.5°	1248.7	1186.0
35°	1318.9	1258.8
37.5°	1404.2	1336.5
40°	1492.0	1421.8
42.5°	1522.1	1476.9
45°	1550.9	1508.3
47.5°	1557.2	1522.1
50°	1563.4	1558.4
52.5°	1581.0	1579.7
55°	1656.2	1657.5
57.5°	1749.0	1756.5
60°	1834.2	1825.5
62.5°	1878.1	1833.0
65°	1848.0	1785.3
67.5°	1757.8	1690.1
70°	1559.7	1468.1
72.5°	1312.7	1232.4
75°	1011.8	944.1
77.5°	719.7	663.2
80°	506.5	450.1
82.5°	324.7	279.6
85°	146.7	127.9
87.5°	41.4	40.1
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P671812  
CATALOG NUMBER: CCP-SA-1B-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)