

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P671813

Luminaire Tested: **CCP-SA-1C-735-U-SLR**

Issue Date: 04/16/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P671813  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 04/16/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: CCP-SA-1C-735-U-SLR  
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @615mA w/ SLR distribution lens  
Light Source: (16) 3500K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3700.7 lumens  
Efficiency: N/A  
Efficacy: 115.6 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B1 - U0 - G2

Input Watts (W): 32  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

REPORT NUMBER: P671813  
 CATALOG NUMBER: CCP-SA-1C-735-U-SLR

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 5.3 fc  
 Type IV - Short - N/A

REPORT NUMBER: P671813  
CATALOG NUMBER: CCP-SA-1C-735-U-SLR

### Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral    - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P671813

CATALOG NUMBER: CCP-SA-1C-735-U-SLR


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	761.4	0.0	761.4
	% Fixture	20.6	0.0	20.6
<b>Street Side</b>	Lumens	2939.2	0.0	2939.2
	% Fixture	79.4	0.0	79.4
<b>Total</b>	Lumens	3700.7	0.0	3700.7
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	91.8	2.5
10°-20°	193.9	5.2
20°-30°	283.7	7.7
30°-40°	399.6	10.8
40°-50°	549.1	14.8
50°-60°	748.5	20.2
60°-70°	819.2	22.1
70°-80°	473.1	12.8
80°-90°	141.8	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3700.7	100.0
0°-180°	3700.7	100.0



REPORT NUMBER: P671813


CATALOG NUMBER: CCP-SA-1C-735-U-SLR

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	380.1	10.3			
FM (30°-60°)	1350.5	36.5			
FH (60°-80°)	1088.2	29.4			G1/1800
FVH (80°-90°)	120.5	3.3			G2/225
BL (0°-30°)	189.3	5.1	B1/500		
BM (30°-60°)	346.7	9.4	B1/1000		
BH (60°-80°)	204.1	5.5	B1/500		G1/500
BVH (80°-90°)	21.4	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B1-U0-G2**

Type IV Short





REPORT NUMBER: P671813

CATALOG NUMBER: CCP-SA-1C-735-U-SLR

**CANDELA DISTRIBUTION (FULL):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8
2.5°	1219.5	1212.9	1208.0	1203.1	1196.5	1191.6	1185.0	1178.5	1170.3	1163.7	1155.5
5°	1148.9	1129.2	1109.5	1098.1	1084.9	1073.4	1060.3	1045.5	1030.8	1014.3	999.6
7.5°	1071.8	1047.2	1022.6	1002.9	981.5	961.8	940.5	922.4	904.4	886.3	868.3
10°	999.6	976.6	953.6	929.0	902.7	878.1	851.9	827.2	802.6	778.0	753.4
12.5°	952.0	924.1	897.8	869.9	843.6	815.7	787.8	764.9	741.9	717.3	694.3
15°	930.6	904.4	879.8	851.9	824.0	796.0	768.1	741.9	717.3	691.0	664.7
17.5°	981.5	943.8	906.0	869.9	833.8	797.7	761.6	728.8	695.9	663.1	630.3
20°	1047.2	999.6	953.6	909.3	863.3	819.0	773.1	727.1	681.2	635.2	589.2
22.5°	1130.9	1076.7	1024.2	966.7	907.7	850.2	791.1	733.7	676.2	617.1	559.7
25°	1280.2	1216.2	1152.2	1070.2	986.4	904.4	820.7	745.2	671.3	595.8	520.3
27.5°	1408.3	1321.3	1235.9	1137.4	1039.0	940.5	842.0	755.0	669.7	582.7	495.7
30°	1483.8	1398.4	1313.1	1193.3	1075.1	955.3	835.4	738.6	643.4	546.6	449.7
32.5°	1552.7	1457.5	1362.3	1231.0	1098.1	966.7	833.8	727.1	622.1	515.4	408.7
35°	1647.9	1542.9	1439.5	1286.8	1134.2	981.5	828.9	718.9	607.3	497.3	385.7
37.5°	1749.7	1620.0	1492.0	1322.9	1153.9	984.8	815.7	707.4	599.1	490.8	382.4
40°	1861.3	1703.7	1547.8	1360.7	1175.2	988.1	801.0	692.6	584.3	474.3	366.0
42.5°	1933.5	1762.8	1592.1	1390.2	1190.0	988.1	786.2	679.5	572.8	464.5	357.8
45°	1974.5	1808.8	1644.6	1426.3	1208.0	989.7	771.4	666.4	561.3	454.7	349.6
47.5°	1992.6	1838.3	1684.0	1454.2	1226.1	996.3	766.5	659.8	551.5	444.8	336.5
50°	2040.2	1904.0	1767.7	1521.5	1277.0	1030.8	784.6	669.7	556.4	441.5	326.6
52.5°	2068.1	1951.6	1835.0	1582.3	1329.5	1076.7	824.0	695.9	567.9	439.9	311.9
55°	2169.9	2058.2	1946.6	1677.4	1406.6	1137.4	866.6	725.5	584.3	441.5	300.4
57.5°	2299.5	2181.3	2064.8	1774.3	1483.8	1193.3	902.7	751.7	599.1	448.1	295.4
60°	2389.8	2274.9	2161.6	1853.1	1542.9	1234.3	924.1	766.5	608.9	449.7	292.2
62.5°	2399.6	2251.9	2105.8	1805.5	1505.1	1203.1	902.7	750.1	597.4	443.2	290.5
65°	2337.3	2164.9	1992.6	1705.4	1418.1	1130.9	843.6	704.1	564.6	423.5	284.0
67.5°	2212.5	2010.6	1808.8	1546.1	1283.5	1020.9	758.3	638.5	520.3	400.5	280.7
70°	1922.0	1744.7	1569.1	1341.0	1114.5	886.3	658.2	559.7	462.9	364.4	265.9
72.5°	1613.4	1447.7	1283.5	1098.1	914.2	728.8	543.3	469.4	395.6	320.1	246.2
75°	1235.9	1111.2	988.1	850.2	712.3	572.8	435.0	380.8	326.6	272.5	218.3
77.5°	868.3	801.0	735.3	631.9	528.5	425.1	321.7	285.6	249.5	213.4	177.3
80°	589.2	551.5	515.4	441.5	367.7	292.2	218.3	195.3	170.7	147.7	123.1
82.5°	366.0	364.4	361.1	310.2	259.3	208.5	157.6	137.9	119.8	100.1	80.4
85°	167.4	195.3	221.6	193.7	165.8	137.9	110.0	96.8	83.7	68.9	55.8
87.5°	52.5	64.0	73.9	70.6	65.7	62.4	57.4	49.2	41.0	32.8	24.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671813  
 CATALOG NUMBER: CCP-SA-1C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671813

CATALOG NUMBER: CCP-SA-1C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8
2.5°	1148.9	1144.0	1137.4	1130.9	1122.7	1116.1	1107.9	1099.7	1098.1	1094.8	1093.1
5°	989.7	979.9	968.4	958.5	948.7	937.2	927.4	915.9	907.7	897.8	889.6
7.5°	850.2	833.8	815.7	797.7	781.3	764.9	746.8	730.4	722.2	714.0	705.8
10°	738.6	722.2	707.4	691.0	679.5	669.7	658.2	646.7	636.8	627.0	617.1
12.5°	682.8	671.3	659.8	648.3	635.2	623.7	610.6	597.4	586.0	576.1	564.6
15°	648.3	631.9	613.9	597.4	579.4	563.0	544.9	526.9	513.7	502.2	489.1
17.5°	607.3	582.7	559.7	535.1	515.4	495.7	474.3	454.7	439.9	423.5	408.7
20°	561.3	533.4	503.9	476.0	453.0	431.7	408.7	385.7	369.3	351.2	334.8
22.5°	521.9	485.8	448.1	410.3	385.7	361.1	334.8	310.2	295.4	279.0	264.3
25°	479.3	439.9	398.8	357.8	333.2	306.9	282.3	256.0	244.6	234.7	223.2
27.5°	456.3	416.9	375.9	336.5	313.5	288.9	265.9	241.3	233.1	223.2	215.0
30°	410.3	372.6	333.2	293.8	277.4	262.6	246.2	229.8	226.5	224.9	221.6
32.5°	369.3	329.9	290.5	251.1	236.4	221.6	206.8	192.0	190.4	187.1	185.5
35°	348.0	310.2	270.8	233.1	219.9	205.2	192.0	177.3	174.0	169.1	165.8
37.5°	343.0	303.6	262.6	223.2	210.1	197.0	182.2	169.1	165.8	162.5	159.2
40°	329.9	292.2	256.0	218.3	205.2	192.0	177.3	164.1	160.9	157.6	154.3
42.5°	320.1	284.0	246.2	208.5	197.0	185.5	172.3	160.9	157.6	154.3	149.4
45°	311.9	274.1	234.7	197.0	188.8	180.5	170.7	162.5	159.2	154.3	151.0
47.5°	298.7	262.6	224.9	187.1	178.9	172.3	164.1	155.9	152.6	149.4	146.1
50°	288.9	251.1	213.4	175.6	169.1	162.5	155.9	149.4	149.4	151.0	151.0
52.5°	275.7	239.6	203.5	167.4	160.9	154.3	147.7	141.2	142.8	144.4	146.1
55°	264.3	229.8	193.7	157.6	151.0	144.4	136.2	129.7	131.3	132.9	134.6
57.5°	259.3	223.2	187.1	151.0	144.4	136.2	129.7	121.5	121.5	121.5	121.5
60°	256.0	218.3	182.2	144.4	136.2	129.7	121.5	113.3	111.6	111.6	110.0
62.5°	254.4	216.7	180.5	142.8	132.9	124.7	114.9	105.0	103.4	101.8	100.1
65°	247.8	213.4	177.3	141.2	129.7	119.8	108.3	96.8	95.2	95.2	93.6
67.5°	246.2	210.1	175.6	139.5	128.0	114.9	103.4	90.3	88.6	87.0	85.3
70°	233.1	201.9	169.1	136.2	123.1	111.6	98.5	85.3	83.7	80.4	78.8
72.5°	216.7	188.8	159.2	129.7	116.5	103.4	90.3	77.1	75.5	73.9	70.6
75°	192.0	165.8	139.5	113.3	101.8	91.9	80.4	68.9	67.3	65.7	62.4
77.5°	157.6	136.2	116.5	95.2	87.0	78.8	70.6	62.4	60.7	59.1	55.8
80°	111.6	98.5	87.0	73.9	68.9	62.4	57.4	50.9	50.9	49.2	49.2
82.5°	73.9	67.3	60.7	54.2	50.9	47.6	44.3	41.0	41.0	39.4	39.4
85°	52.5	49.2	44.3	41.0	39.4	36.1	34.5	31.2	31.2	31.2	31.2
87.5°	24.6	24.6	23.0	23.0	21.3	21.3	19.7	18.1	18.1	18.1	18.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671813  
 CATALOG NUMBER: CCP-SA-1C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671813  
 CATALOG NUMBER: CCP-SA-1C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8
2.5°	1089.8	1084.9	1080.0	1073.4	1068.5	1061.9	1053.7	1047.2	1039.0	1039.0	1037.3
5°	879.8	874.8	869.9	863.3	858.4	851.9	846.9	840.4	833.8	833.8	832.2
7.5°	697.6	687.7	677.9	666.4	656.5	650.0	643.4	635.2	628.6	623.7	618.8
10°	607.3	597.4	586.0	576.1	564.6	556.4	548.2	538.4	530.2	523.6	517.0
12.5°	553.1	541.6	530.2	518.7	507.2	495.7	485.8	474.3	462.9	454.7	446.4
15°	476.0	464.5	453.0	441.5	430.0	416.9	403.8	389.0	375.9	369.3	364.4
17.5°	392.3	380.8	367.7	356.2	343.0	333.2	323.3	313.5	303.6	297.1	292.2
20°	316.8	303.6	290.5	277.4	264.3	257.7	251.1	244.6	238.0	233.1	229.8
22.5°	247.8	239.6	233.1	224.9	216.7	211.7	208.5	203.5	198.6	198.6	198.6
25°	211.7	206.8	203.5	198.6	193.7	192.0	190.4	187.1	185.5	183.8	183.8
27.5°	205.2	200.2	195.3	190.4	185.5	183.8	182.2	178.9	177.3	177.3	177.3
30°	218.3	216.7	215.0	213.4	211.7	208.5	203.5	200.2	195.3	192.0	188.8
32.5°	182.2	180.5	180.5	178.9	177.3	180.5	182.2	185.5	187.1	188.8	190.4
35°	160.9	157.6	154.3	151.0	147.7	146.1	144.4	142.8	141.2	141.2	139.5
37.5°	155.9	152.6	149.4	146.1	142.8	141.2	139.5	137.9	136.2	136.2	134.6
40°	151.0	147.7	146.1	142.8	139.5	137.9	136.2	132.9	131.3	129.7	129.7
42.5°	146.1	144.4	141.2	139.5	136.2	134.6	132.9	129.7	128.0	126.4	124.7
45°	146.1	142.8	139.5	136.2	132.9	131.3	128.0	126.4	123.1	123.1	121.5
47.5°	142.8	139.5	136.2	132.9	129.7	128.0	124.7	123.1	119.8	118.2	116.5
50°	151.0	146.1	139.5	134.6	128.0	126.4	123.1	121.5	118.2	116.5	114.9
52.5°	147.7	142.8	136.2	131.3	124.7	121.5	119.8	116.5	113.3	111.6	110.0
55°	136.2	131.3	128.0	123.1	118.2	114.9	111.6	108.3	105.0	103.4	103.4
57.5°	121.5	119.8	118.2	116.5	114.9	111.6	108.3	103.4	100.1	98.5	96.8
60°	108.3	110.0	111.6	113.3	114.9	110.0	105.0	100.1	95.2	93.6	91.9
62.5°	98.5	101.8	105.0	106.7	110.0	105.0	100.1	95.2	90.3	88.6	87.0
65°	91.9	93.6	93.6	95.2	95.2	91.9	90.3	87.0	83.7	82.1	82.1
67.5°	83.7	83.7	83.7	82.1	82.1	80.4	80.4	78.8	77.1	75.5	75.5
70°	75.5	75.5	75.5	73.9	73.9	72.2	72.2	70.6	68.9	68.9	67.3
72.5°	68.9	68.9	67.3	67.3	65.7	65.7	65.7	64.0	64.0	62.4	62.4
75°	60.7	60.7	59.1	59.1	57.4	57.4	57.4	55.8	55.8	55.8	54.2
77.5°	54.2	54.2	52.5	52.5	50.9	50.9	50.9	49.2	49.2	47.6	47.6
80°	47.6	47.6	46.0	46.0	44.3	44.3	42.7	42.7	41.0	41.0	39.4
82.5°	37.8	37.8	37.8	37.8	37.8	36.1	36.1	34.5	32.8	32.8	31.2
85°	31.2	31.2	31.2	29.5	29.5	29.5	27.9	27.9	26.3	24.6	24.6
87.5°	18.1	18.1	18.1	16.4	16.4	16.4	16.4	16.4	16.4	16.4	14.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671813  
 CATALOG NUMBER: CCP-SA-1C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671813  
 CATALOG NUMBER: CCP-SA-1C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8
2.5°	1037.3	1035.7	1029.1	1022.6	1029.1	1035.7	1035.7	1035.7	1034.0	1034.0	1034.0
5°	832.2	830.5	827.2	824.0	824.0	822.3	825.6	828.9	832.2	835.4	838.7
7.5°	612.2	607.3	602.4	597.4	600.7	602.4	607.3	610.6	615.5	618.8	627.0
10°	510.5	503.9	499.0	494.0	490.8	487.5	484.2	482.6	479.3	476.0	479.3
12.5°	436.6	428.4	420.2	410.3	408.7	407.1	403.8	400.5	397.2	393.9	392.3
15°	357.8	351.2	348.0	343.0	336.5	329.9	326.6	325.0	321.7	318.4	316.8
17.5°	285.6	279.0	274.1	269.2	267.5	264.3	264.3	264.3	264.3	264.3	264.3
20°	224.9	219.9	219.9	218.3	218.3	216.7	218.3	219.9	219.9	221.6	223.2
22.5°	197.0	197.0	195.3	193.7	195.3	195.3	197.0	198.6	200.2	201.9	203.5
25°	182.2	180.5	182.2	183.8	183.8	183.8	185.5	185.5	187.1	187.1	187.1
27.5°	175.6	175.6	177.3	177.3	178.9	178.9	178.9	177.3	177.3	175.6	175.6
30°	185.5	182.2	182.2	182.2	180.5	178.9	177.3	177.3	175.6	174.0	172.3
32.5°	192.0	193.7	192.0	188.8	187.1	183.8	182.2	178.9	177.3	174.0	170.7
35°	139.5	137.9	141.2	142.8	144.4	146.1	147.7	149.4	149.4	151.0	151.0
37.5°	134.6	132.9	132.9	131.3	131.3	131.3	131.3	131.3	129.7	129.7	131.3
40°	128.0	126.4	126.4	124.7	124.7	123.1	123.1	123.1	123.1	123.1	123.1
42.5°	123.1	121.5	121.5	121.5	121.5	119.8	119.8	118.2	118.2	116.5	116.5
45°	121.5	119.8	118.2	116.5	116.5	114.9	114.9	114.9	113.3	113.3	113.3
47.5°	114.9	113.3	113.3	111.6	111.6	110.0	110.0	110.0	108.3	108.3	108.3
50°	111.6	110.0	110.0	108.3	108.3	106.7	106.7	106.7	105.0	105.0	105.0
52.5°	106.7	105.0	105.0	105.0	103.4	101.8	101.8	101.8	100.1	100.1	100.1
55°	101.8	100.1	100.1	100.1	98.5	96.8	96.8	96.8	95.2	95.2	95.2
57.5°	95.2	93.6	93.6	91.9	91.9	91.9	91.9	91.9	90.3	90.3	90.3
60°	90.3	88.6	88.6	87.0	87.0	85.3	85.3	85.3	85.3	85.3	85.3
62.5°	85.3	83.7	82.1	80.4	82.1	82.1	82.1	82.1	80.4	80.4	80.4
65°	80.4	78.8	77.1	75.5	75.5	75.5	75.5	75.5	75.5	75.5	75.5
67.5°	73.9	72.2	70.6	68.9	70.6	70.6	70.6	70.6	70.6	70.6	70.6
70°	67.3	65.7	65.7	64.0	64.0	62.4	62.4	64.0	64.0	64.0	64.0
72.5°	60.7	59.1	59.1	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4
75°	54.2	52.5	52.5	50.9	50.9	50.9	50.9	50.9	50.9	50.9	50.9
77.5°	46.0	44.3	44.3	44.3	44.3	44.3	44.3	46.0	46.0	46.0	46.0
80°	39.4	37.8	37.8	37.8	37.8	37.8	37.8	37.8	37.8	37.8	37.8
82.5°	31.2	29.5	29.5	29.5	29.5	29.5	29.5	29.5	29.5	29.5	29.5
85°	23.0	21.3	21.3	21.3	23.0	23.0	23.0	23.0	23.0	23.0	23.0
87.5°	14.8	13.1	13.1	13.1	14.8	14.8	14.8	14.8	13.1	13.1	13.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671813  
 CATALOG NUMBER: CCP-SA-1C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671813  
 CATALOG NUMBER: CCP-SA-1C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8
2.5°	1034.0	1034.0	1034.0	1032.4	1030.8	1029.1	1027.5	1032.4	1035.7	1040.6	1043.9
5°	840.4	843.6	845.3	850.2	855.1	860.1	865.0	868.3	871.6	873.2	876.5
7.5°	633.6	641.8	648.3	654.9	661.5	666.4	672.9	677.9	682.8	687.7	692.6
10°	480.9	484.2	485.8	492.4	497.3	503.9	508.8	513.7	518.7	521.9	526.9
12.5°	390.6	387.4	385.7	385.7	385.7	385.7	385.7	389.0	392.3	395.6	398.8
15°	315.1	313.5	311.9	310.2	308.6	305.3	303.6	306.9	310.2	313.5	316.8
17.5°	264.3	264.3	264.3	262.6	261.0	259.3	257.7	259.3	261.0	261.0	262.6
20°	226.5	228.1	229.8	231.4	231.4	233.1	233.1	234.7	236.4	236.4	238.0
22.5°	203.5	205.2	205.2	205.2	206.8	206.8	206.8	208.5	210.1	211.7	213.4
25°	185.5	185.5	183.8	183.8	185.5	185.5	185.5	185.5	187.1	187.1	187.1
27.5°	175.6	174.0	174.0	174.0	174.0	172.3	172.3	172.3	172.3	172.3	172.3
30°	170.7	169.1	167.4	165.8	165.8	164.1	162.5	162.5	162.5	162.5	162.5
32.5°	169.1	165.8	162.5	160.9	160.9	159.2	157.6	155.9	155.9	154.3	152.6
35°	151.0	149.4	149.4	147.7	146.1	144.4	142.8	142.8	142.8	141.2	141.2
37.5°	131.3	132.9	132.9	132.9	134.6	134.6	134.6	134.6	136.2	136.2	136.2
40°	123.1	123.1	123.1	124.7	126.4	126.4	128.0	128.0	129.7	129.7	129.7
42.5°	116.5	114.9	114.9	116.5	116.5	118.2	118.2	119.8	121.5	121.5	123.1
45°	113.3	111.6	111.6	111.6	111.6	110.0	110.0	111.6	113.3	114.9	116.5
47.5°	106.7	106.7	105.0	105.0	105.0	105.0	105.0	105.0	106.7	106.7	106.7
50°	103.4	103.4	101.8	101.8	101.8	101.8	101.8	101.8	101.8	101.8	101.8
52.5°	100.1	98.5	98.5	98.5	98.5	96.8	96.8	96.8	96.8	96.8	96.8
55°	95.2	93.6	93.6	93.6	93.6	93.6	93.6	93.6	95.2	95.2	95.2
57.5°	90.3	88.6	88.6	88.6	90.3	90.3	90.3	90.3	91.9	91.9	91.9
60°	85.3	85.3	85.3	85.3	85.3	85.3	85.3	87.0	87.0	88.6	88.6
62.5°	80.4	80.4	80.4	80.4	82.1	82.1	82.1	82.1	83.7	83.7	83.7
65°	75.5	75.5	75.5	75.5	77.1	77.1	77.1	77.1	77.1	77.1	77.1
67.5°	70.6	70.6	70.6	70.6	70.6	70.6	70.6	72.2	72.2	73.9	73.9
70°	64.0	62.4	62.4	64.0	64.0	65.7	65.7	67.3	67.3	68.9	68.9
72.5°	57.4	57.4	57.4	57.4	57.4	57.4	57.4	59.1	60.7	60.7	62.4
75°	50.9	50.9	50.9	50.9	52.5	52.5	52.5	54.2	54.2	55.8	55.8
77.5°	46.0	44.3	44.3	44.3	46.0	46.0	46.0	47.6	47.6	49.2	49.2
80°	37.8	37.8	37.8	37.8	39.4	39.4	39.4	39.4	41.0	41.0	41.0
82.5°	31.2	31.2	31.2	31.2	31.2	31.2	31.2	31.2	32.8	32.8	32.8
85°	23.0	23.0	23.0	23.0	24.6	24.6	24.6	24.6	24.6	24.6	24.6
87.5°	14.8	14.8	14.8	14.8	14.8	14.8	14.8	14.8	16.4	16.4	16.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671813  
 CATALOG NUMBER: CCP-SA-1C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671813  
 CATALOG NUMBER: CCP-SA-1C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8
2.5°	1043.9	1043.9	1043.9	1043.9	1047.2	1048.8	1052.1	1053.7	1052.1	1050.5	1047.2
5°	878.1	879.8	879.8	881.4	881.4	881.4	881.4	881.4	884.7	888.0	891.2
7.5°	694.3	695.9	697.6	699.2	699.2	699.2	697.6	697.6	699.2	699.2	700.9
10°	531.8	538.4	543.3	548.2	544.9	540.0	536.7	531.8	531.8	531.8	530.2
12.5°	402.1	403.8	407.1	408.7	407.1	407.1	405.4	403.8	405.4	408.7	410.3
15°	318.4	318.4	320.1	320.1	321.7	323.3	323.3	325.0	328.3	329.9	333.2
17.5°	264.3	265.9	265.9	267.5	267.5	269.2	269.2	269.2	272.5	275.7	280.7
20°	238.0	238.0	238.0	238.0	238.0	236.4	236.4	234.7	236.4	239.6	241.3
22.5°	213.4	215.0	215.0	215.0	213.4	211.7	208.5	206.8	206.8	208.5	208.5
25°	187.1	185.5	185.5	183.8	183.8	185.5	185.5	185.5	187.1	187.1	188.8
27.5°	172.3	170.7	170.7	169.1	169.1	170.7	170.7	170.7	170.7	170.7	170.7
30°	160.9	160.9	159.2	157.6	159.2	159.2	160.9	160.9	162.5	162.5	164.1
32.5°	152.6	151.0	151.0	149.4	151.0	151.0	152.6	152.6	154.3	155.9	155.9
35°	141.2	141.2	141.2	141.2	141.2	141.2	139.5	139.5	139.5	139.5	139.5
37.5°	134.6	134.6	132.9	131.3	131.3	131.3	131.3	131.3	129.7	128.0	126.4
40°	129.7	128.0	128.0	126.4	124.7	124.7	123.1	121.5	121.5	119.8	119.8
42.5°	123.1	121.5	121.5	119.8	118.2	118.2	116.5	114.9	114.9	114.9	113.3
45°	114.9	114.9	113.3	111.6	111.6	111.6	110.0	110.0	110.0	110.0	108.3
47.5°	106.7	106.7	105.0	105.0	105.0	105.0	103.4	103.4	103.4	103.4	103.4
50°	101.8	101.8	101.8	101.8	101.8	101.8	100.1	100.1	100.1	100.1	100.1
52.5°	96.8	96.8	96.8	96.8	96.8	96.8	96.8	96.8	96.8	96.8	96.8
55°	95.2	95.2	95.2	95.2	95.2	95.2	93.6	93.6	93.6	95.2	95.2
57.5°	91.9	91.9	90.3	90.3	90.3	90.3	90.3	90.3	90.3	90.3	90.3
60°	88.6	88.6	88.6	88.6	88.6	88.6	88.6	88.6	88.6	88.6	88.6
62.5°	83.7	83.7	83.7	83.7	83.7	85.3	85.3	85.3	85.3	85.3	83.7
65°	77.1	78.8	78.8	78.8	78.8	78.8	78.8	78.8	78.8	78.8	78.8
67.5°	73.9	73.9	73.9	73.9	73.9	73.9	73.9	73.9	73.9	73.9	73.9
70°	68.9	68.9	67.3	67.3	67.3	68.9	68.9	68.9	68.9	68.9	68.9
72.5°	62.4	62.4	62.4	62.4	62.4	62.4	62.4	62.4	62.4	64.0	64.0
75°	55.8	55.8	55.8	55.8	55.8	55.8	55.8	55.8	55.8	55.8	55.8
77.5°	49.2	49.2	47.6	47.6	47.6	49.2	49.2	49.2	49.2	50.9	50.9
80°	41.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0	42.7	42.7
82.5°	32.8	32.8	32.8	32.8	32.8	32.8	32.8	32.8	32.8	34.5	34.5
85°	24.6	26.3	26.3	26.3	26.3	26.3	26.3	26.3	26.3	27.9	27.9
87.5°	16.4	16.4	16.4	16.4	16.4	16.4	14.8	14.8	14.8	14.8	13.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671813  
 CATALOG NUMBER: CCP-SA-1C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671813  
 CATALOG NUMBER: CCP-SA-1C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8
2.5°	1045.5	1047.2	1048.8	1048.8	1050.5	1052.1	1052.1	1058.7	1065.2	1068.5	1071.8
5°	894.5	892.9	892.9	891.2	889.6	894.5	899.5	909.3	919.2	920.8	924.1
7.5°	700.9	702.5	704.1	704.1	705.8	700.9	694.3	695.9	697.6	705.8	712.3
10°	530.2	531.8	533.4	533.4	535.1	533.4	530.2	535.1	540.0	546.6	554.8
12.5°	412.0	416.9	421.8	425.1	430.0	433.3	435.0	441.5	446.4	454.7	462.9
15°	336.5	339.8	343.0	346.3	349.6	352.9	356.2	362.7	369.3	379.1	389.0
17.5°	284.0	284.0	285.6	285.6	285.6	288.9	292.2	295.4	297.1	306.9	316.8
20°	242.9	241.3	239.6	238.0	236.4	239.6	241.3	242.9	244.6	251.1	256.0
22.5°	208.5	208.5	210.1	210.1	210.1	208.5	205.2	206.8	206.8	210.1	215.0
25°	188.8	188.8	188.8	187.1	187.1	188.8	190.4	190.4	188.8	190.4	192.0
27.5°	170.7	172.3	172.3	174.0	174.0	175.6	175.6	175.6	175.6	177.3	178.9
30°	164.1	164.1	165.8	165.8	165.8	167.4	169.1	169.1	169.1	170.7	174.0
32.5°	157.6	159.2	160.9	162.5	164.1	165.8	165.8	167.4	167.4	169.1	170.7
35°	139.5	137.9	137.9	136.2	134.6	134.6	134.6	134.6	132.9	134.6	134.6
37.5°	124.7	124.7	124.7	123.1	123.1	124.7	124.7	124.7	124.7	126.4	126.4
40°	118.2	118.2	118.2	118.2	118.2	118.2	118.2	119.8	119.8	121.5	123.1
42.5°	113.3	113.3	113.3	113.3	113.3	114.9	114.9	114.9	114.9	116.5	116.5
45°	108.3	108.3	108.3	108.3	108.3	108.3	108.3	110.0	110.0	111.6	113.3
47.5°	103.4	103.4	103.4	103.4	103.4	105.0	106.7	106.7	106.7	108.3	108.3
50°	100.1	100.1	100.1	100.1	100.1	101.8	101.8	103.4	103.4	105.0	106.7
52.5°	96.8	96.8	96.8	96.8	96.8	98.5	98.5	100.1	100.1	101.8	103.4
55°	95.2	95.2	95.2	93.6	93.6	95.2	95.2	96.8	96.8	98.5	98.5
57.5°	90.3	90.3	90.3	90.3	90.3	90.3	90.3	91.9	91.9	93.6	95.2
60°	88.6	88.6	87.0	87.0	85.3	87.0	87.0	88.6	88.6	90.3	90.3
62.5°	83.7	83.7	83.7	82.1	82.1	83.7	83.7	83.7	83.7	85.3	87.0
65°	78.8	78.8	78.8	77.1	77.1	78.8	78.8	78.8	78.8	80.4	82.1
67.5°	73.9	73.9	73.9	72.2	72.2	72.2	72.2	73.9	73.9	75.5	77.1
70°	68.9	68.9	68.9	67.3	67.3	67.3	65.7	67.3	68.9	70.6	70.6
72.5°	64.0	64.0	64.0	62.4	62.4	62.4	60.7	62.4	62.4	64.0	64.0
75°	55.8	55.8	55.8	55.8	55.8	55.8	54.2	54.2	54.2	55.8	55.8
77.5°	50.9	50.9	50.9	49.2	49.2	49.2	47.6	47.6	47.6	49.2	49.2
80°	42.7	42.7	42.7	41.0	41.0	41.0	39.4	39.4	39.4	41.0	41.0
82.5°	34.5	34.5	34.5	32.8	32.8	32.8	31.2	31.2	31.2	32.8	32.8
85°	27.9	27.9	27.9	27.9	27.9	27.9	26.3	26.3	26.3	27.9	29.5
87.5°	13.1	13.1	14.8	14.8	14.8	14.8	13.1	13.1	11.5	11.5	13.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671813  
 CATALOG NUMBER: CCP-SA-1C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671813  
 CATALOG NUMBER: CCP-SA-1C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8
2.5°	1075.1	1078.4	1086.6	1093.1	1101.3	1107.9	1112.8	1119.4	1124.3	1129.2	1132.5
5°	925.7	927.4	935.6	943.8	950.3	958.5	970.0	981.5	993.0	1004.5	1012.7
7.5°	720.5	727.1	737.0	748.5	758.3	768.1	779.6	792.8	804.3	815.7	827.2
10°	561.3	567.9	577.8	587.6	595.8	605.7	618.8	631.9	645.0	658.2	671.3
12.5°	471.1	479.3	490.8	502.2	512.1	523.6	540.0	554.8	571.2	586.0	602.4
15°	397.2	407.1	421.8	438.2	453.0	467.8	484.2	500.6	515.4	531.8	548.2
17.5°	326.6	336.5	349.6	364.4	377.5	390.6	410.3	428.4	448.1	466.1	484.2
20°	262.6	267.5	280.7	293.8	306.9	320.1	334.8	349.6	364.4	379.1	402.1
22.5°	218.3	221.6	228.1	233.1	239.6	244.6	259.3	274.1	287.2	302.0	323.3
25°	192.0	193.7	198.6	201.9	206.8	210.1	219.9	228.1	238.0	246.2	265.9
27.5°	178.9	180.5	182.2	183.8	185.5	187.1	193.7	200.2	205.2	211.7	229.8
30°	175.6	177.3	182.2	185.5	190.4	193.7	197.0	200.2	203.5	206.8	218.3
32.5°	172.3	174.0	174.0	172.3	172.3	170.7	174.0	175.6	178.9	180.5	190.4
35°	136.2	136.2	137.9	139.5	141.2	142.8	147.7	151.0	155.9	159.2	167.4
37.5°	128.0	128.0	129.7	132.9	134.6	136.2	139.5	142.8	146.1	149.4	157.6
40°	123.1	124.7	126.4	128.0	129.7	131.3	134.6	136.2	139.5	141.2	147.7
42.5°	118.2	118.2	119.8	123.1	124.7	126.4	129.7	131.3	134.6	136.2	142.8
45°	114.9	116.5	118.2	119.8	119.8	121.5	124.7	128.0	129.7	132.9	139.5
47.5°	110.0	110.0	113.3	114.9	118.2	119.8	123.1	124.7	128.0	129.7	136.2
50°	106.7	108.3	111.6	113.3	116.5	118.2	123.1	126.4	131.3	134.6	137.9
52.5°	103.4	105.0	108.3	110.0	113.3	114.9	121.5	128.0	132.9	139.5	139.5
55°	100.1	100.1	103.4	108.3	111.6	114.9	118.2	123.1	126.4	129.7	129.7
57.5°	95.2	96.8	100.1	105.0	108.3	111.6	114.9	118.2	119.8	123.1	121.5
60°	91.9	91.9	96.8	101.8	106.7	111.6	111.6	111.6	110.0	110.0	110.0
62.5°	87.0	88.6	95.2	103.4	110.0	116.5	111.6	106.7	101.8	96.8	98.5
65°	83.7	85.3	88.6	93.6	96.8	100.1	96.8	95.2	91.9	88.6	90.3
67.5°	77.1	78.8	80.4	80.4	82.1	82.1	82.1	82.1	82.1	82.1	83.7
70°	72.2	72.2	72.2	73.9	73.9	73.9	73.9	73.9	73.9	73.9	75.5
72.5°	65.7	65.7	65.7	65.7	65.7	65.7	65.7	65.7	65.7	65.7	67.3
75°	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4	59.1
77.5°	50.9	50.9	50.9	50.9	50.9	50.9	50.9	50.9	49.2	49.2	50.9
80°	42.7	42.7	42.7	42.7	41.0	41.0	41.0	41.0	41.0	41.0	42.7
82.5°	34.5	34.5	34.5	34.5	32.8	32.8	32.8	32.8	31.2	31.2	32.8
85°	31.2	32.8	32.8	34.5	34.5	34.5	32.8	31.2	29.5	27.9	27.9
87.5°	13.1	13.1	13.1	13.1	11.5	11.5	11.5	11.5	11.5	11.5	11.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671813  
 CATALOG NUMBER: CCP-SA-1C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671813  
 CATALOG NUMBER: CCP-SA-1C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8
2.5°	1137.4	1140.7	1144.0	1148.9	1155.5	1160.4	1165.4	1175.2	1186.7	1196.5	1206.4
5°	1020.9	1029.1	1037.3	1047.2	1057.0	1065.2	1075.1	1094.8	1114.5	1132.5	1152.2
7.5°	837.1	848.6	858.4	874.8	889.6	906.0	920.8	945.4	968.4	993.0	1016.0
10°	684.4	697.6	710.7	732.0	755.0	776.4	797.7	817.4	838.7	858.4	878.1
12.5°	618.8	633.6	650.0	663.1	677.9	691.0	704.1	727.1	750.1	773.1	796.0
15°	564.6	581.0	597.4	613.9	628.6	645.0	659.8	679.5	700.9	720.5	740.2
17.5°	502.2	518.7	536.7	554.8	572.8	590.9	608.9	636.8	664.7	691.0	718.9
20°	423.5	446.4	467.8	492.4	517.0	541.6	566.3	595.8	625.4	653.3	682.8
22.5°	344.7	366.0	387.4	416.9	446.4	474.3	503.9	543.3	581.0	620.4	658.2
25°	287.2	306.9	326.6	359.5	390.6	423.5	454.7	502.2	548.2	595.8	641.8
27.5°	247.8	265.9	284.0	318.4	352.9	385.7	420.2	472.7	523.6	576.1	627.0
30°	229.8	241.3	252.8	285.6	318.4	349.6	382.4	433.3	484.2	535.1	586.0
32.5°	200.2	210.1	219.9	249.5	279.0	306.9	336.5	389.0	439.9	492.4	543.3
35°	177.3	185.5	193.7	221.6	247.8	275.7	302.0	354.5	407.1	459.6	512.1
37.5°	164.1	172.3	178.9	203.5	229.8	254.4	279.0	331.6	382.4	435.0	485.8
40°	154.3	159.2	165.8	190.4	213.4	238.0	261.0	308.6	357.8	405.4	453.0
42.5°	147.7	154.3	159.2	180.5	203.5	224.9	246.2	292.2	338.1	382.4	428.4
45°	146.1	152.6	159.2	177.3	195.3	211.7	229.8	274.1	318.4	362.7	407.1
47.5°	142.8	147.7	154.3	169.1	182.2	197.0	210.1	254.4	298.7	341.4	385.7
50°	141.2	142.8	146.1	159.2	172.3	185.5	198.6	242.9	287.2	331.6	375.9
52.5°	139.5	139.5	139.5	151.0	162.5	172.3	183.8	228.1	274.1	318.4	362.7
55°	129.7	128.0	128.0	139.5	149.4	160.9	170.7	215.0	259.3	302.0	346.3
57.5°	119.8	118.2	116.5	126.4	136.2	146.1	155.9	200.2	246.2	290.5	334.8
60°	110.0	108.3	108.3	118.2	126.4	136.2	144.4	190.4	234.7	280.7	325.0
62.5°	98.5	100.1	100.1	108.3	118.2	126.4	134.6	180.5	228.1	274.1	320.1
65°	90.3	91.9	91.9	101.8	111.6	121.5	131.3	175.6	221.6	265.9	310.2
67.5°	83.7	85.3	85.3	96.8	106.7	118.2	128.0	167.4	208.5	247.8	287.2
70°	77.1	77.1	78.8	90.3	101.8	113.3	124.7	159.2	193.7	226.5	261.0
72.5°	68.9	70.6	72.2	83.7	93.6	105.0	114.9	146.1	177.3	208.5	239.6
75°	60.7	62.4	64.0	73.9	83.7	93.6	103.4	132.9	160.9	190.4	218.3
77.5°	54.2	55.8	57.4	65.7	73.9	82.1	90.3	111.6	134.6	155.9	177.3
80°	44.3	44.3	46.0	52.5	59.1	64.0	70.6	85.3	100.1	113.3	128.0
82.5°	32.8	34.5	34.5	39.4	42.7	47.6	50.9	59.1	65.7	73.9	80.4
85°	27.9	26.3	26.3	29.5	31.2	34.5	36.1	41.0	44.3	49.2	52.5
87.5°	11.5	9.8	9.8	11.5	14.8	16.4	18.1	18.1	19.7	19.7	19.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671813  
 CATALOG NUMBER: CCP-SA-1C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671813

CATALOG NUMBER: CCP-SA-1C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8
2.5°	1211.3	1214.6	1219.5	1222.8	1231.0	1237.6	1245.8	1252.3	1257.3	1265.5	1262.2
5°	1167.0	1181.8	1196.5	1211.3	1222.8	1234.3	1244.1	1255.6	1268.8	1293.4	1299.9
7.5°	1035.7	1055.4	1073.4	1093.1	1116.1	1139.1	1162.1	1185.0	1206.4	1237.6	1257.3
10°	906.0	933.9	960.2	988.1	1009.4	1030.8	1050.5	1071.8	1101.3	1132.5	1168.6
12.5°	824.0	851.9	879.8	907.7	938.8	968.4	999.6	1029.1	1057.0	1081.6	1122.7
15°	769.8	801.0	830.5	860.1	897.8	933.9	971.7	1007.8	1048.8	1081.6	1109.5
17.5°	756.7	794.4	830.5	868.3	907.7	947.1	986.4	1025.8	1066.9	1116.1	1152.2
20°	733.7	784.6	835.4	886.3	937.2	986.4	1037.3	1086.6	1140.7	1199.8	1216.2
22.5°	720.5	781.3	843.6	904.4	973.3	1043.9	1112.8	1181.8	1239.2	1283.5	1332.8
25°	718.9	794.4	871.6	947.1	1034.0	1119.4	1206.4	1291.7	1365.6	1409.9	1449.3
27.5°	717.3	809.2	899.5	989.7	1096.4	1201.5	1308.1	1413.2	1482.1	1546.1	1579.0
30°	697.6	807.5	919.2	1029.1	1148.9	1268.8	1388.6	1508.4	1579.0	1623.3	1639.7
32.5°	672.9	802.6	932.3	1061.9	1198.2	1334.4	1469.0	1605.2	1661.0	1698.8	1685.7
35°	653.3	796.0	937.2	1078.4	1222.8	1368.9	1513.3	1657.8	1738.2	1790.7	1769.4
37.5°	635.2	784.6	933.9	1083.3	1252.3	1421.4	1590.5	1759.5	1836.7	1892.5	1867.8
40°	613.9	773.1	933.9	1093.1	1286.8	1478.8	1672.5	1864.6	1964.7	2012.3	1974.5
42.5°	595.8	761.6	929.0	1094.8	1301.6	1508.4	1715.2	1922.0	2033.6	2100.9	2053.3
45°	572.8	738.6	902.7	1068.5	1296.7	1524.8	1751.3	1979.5	2109.1	2161.6	2096.0
47.5°	548.2	712.3	874.8	1037.3	1280.2	1523.2	1766.1	2009.0	2128.8	2191.2	2130.5
50°	540.0	704.1	866.6	1030.8	1293.4	1557.6	1820.2	2082.9	2169.9	2220.7	2140.3
52.5°	538.4	712.3	888.0	1061.9	1326.2	1588.8	1853.1	2115.7	2186.3	2240.4	2168.2
55°	533.4	722.2	909.3	1096.4	1372.2	1649.5	1925.3	2201.0	2271.6	2311.0	2256.8
57.5°	538.4	741.9	943.8	1147.3	1431.2	1715.2	1999.2	2283.1	2368.5	2396.4	2384.9
60°	541.6	758.3	973.3	1190.0	1467.4	1744.7	2022.1	2299.5	2388.1	2457.1	2470.2
62.5°	533.4	746.8	958.5	1171.9	1423.0	1674.2	1925.3	2176.4	2322.5	2424.3	2483.3
65°	508.8	705.8	904.4	1101.3	1332.8	1565.8	1797.3	2028.7	2183.0	2334.0	2381.6
67.5°	454.7	622.1	789.5	956.9	1158.8	1360.7	1560.9	1762.8	1956.5	2102.6	2168.2
70°	393.9	525.2	658.2	789.5	973.3	1157.1	1341.0	1524.8	1695.5	1856.4	1918.7
72.5°	343.0	444.8	548.2	650.0	781.3	910.9	1042.3	1171.9	1373.8	1534.7	1595.4
75°	292.2	366.0	438.2	512.1	602.4	692.6	781.3	871.6	1014.3	1158.8	1219.5
77.5°	224.9	274.1	321.7	369.3	431.7	492.4	554.8	615.5	715.6	824.0	855.1
80°	155.9	183.8	210.1	238.0	287.2	336.5	385.7	435.0	500.6	561.3	608.9
82.5°	96.8	114.9	131.3	147.7	187.1	226.5	264.3	303.6	329.9	333.2	380.8
85°	62.4	73.9	83.7	93.6	116.5	141.2	164.1	187.1	167.4	155.9	185.5
87.5°	24.6	31.2	36.1	41.0	39.4	37.8	36.1	34.5	29.5	26.3	32.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671813  
 CATALOG NUMBER: CCP-SA-1C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671813

CATALOG NUMBER: CCP-SA-1C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8
2.5°	1265.5	1270.4	1275.3	1278.6	1283.5	1285.2	1286.8	1286.8	1288.5	1290.1	1293.4
5°	1326.2	1336.1	1345.9	1354.1	1364.0	1372.2	1378.7	1386.9	1393.5	1393.5	1391.9
7.5°	1275.3	1299.9	1324.6	1349.2	1373.8	1391.9	1408.3	1426.3	1442.7	1446.0	1449.3
10°	1208.0	1234.3	1258.9	1285.2	1309.8	1337.7	1364.0	1390.2	1418.1	1423.0	1429.6
12.5°	1145.7	1176.8	1208.0	1237.6	1268.8	1288.5	1308.1	1326.2	1345.9	1359.0	1372.2
15°	1144.0	1170.3	1196.5	1221.2	1247.4	1258.9	1270.4	1280.2	1291.7	1291.7	1293.4
17.5°	1181.8	1198.2	1214.6	1229.4	1245.8	1247.4	1250.7	1252.3	1254.0	1249.1	1244.1
20°	1255.6	1262.2	1268.8	1275.3	1281.9	1270.4	1260.5	1249.1	1237.6	1224.4	1212.9
22.5°	1364.0	1349.2	1334.4	1319.6	1304.9	1285.2	1263.8	1244.1	1222.8	1206.4	1190.0
25°	1465.7	1447.7	1429.6	1411.6	1393.5	1350.8	1308.1	1263.8	1221.2	1203.1	1185.0
27.5°	1601.9	1574.0	1546.1	1518.2	1490.3	1432.9	1375.4	1318.0	1260.5	1229.4	1199.8
30°	1634.8	1603.6	1572.4	1539.6	1508.4	1452.6	1398.4	1342.6	1286.8	1250.7	1216.2
32.5°	1682.4	1646.3	1610.2	1574.0	1537.9	1483.8	1429.6	1373.8	1319.6	1286.8	1252.3
35°	1761.2	1720.1	1679.1	1636.4	1595.4	1539.6	1485.4	1429.6	1373.8	1336.1	1299.9
37.5°	1828.5	1780.9	1733.3	1685.7	1638.1	1588.8	1537.9	1488.7	1437.8	1400.1	1364.0
40°	1904.0	1851.4	1798.9	1748.0	1695.5	1649.5	1603.6	1556.0	1510.0	1480.5	1450.9
42.5°	1969.6	1905.6	1843.2	1780.9	1716.8	1685.7	1656.1	1624.9	1593.7	1579.0	1562.6
45°	2015.6	1956.5	1895.7	1836.7	1777.6	1754.6	1731.6	1708.6	1685.7	1700.4	1715.2
47.5°	2035.3	1987.7	1941.7	1895.7	1848.1	1856.4	1864.6	1871.1	1879.3	1899.0	1920.4
50°	2053.3	2027.1	1999.2	1972.9	1945.0	1976.2	2005.7	2036.9	2068.1	2109.1	2150.2
52.5°	2089.4	2074.7	2061.5	2046.8	2032.0	2086.1	2140.3	2194.5	2248.6	2294.6	2340.5
55°	2197.8	2186.3	2174.8	2161.6	2150.2	2227.3	2302.8	2379.9	2457.1	2504.7	2552.3
57.5°	2347.1	2340.5	2332.3	2325.8	2317.6	2393.1	2466.9	2540.8	2616.3	2662.3	2709.9
60°	2460.4	2462.0	2462.0	2463.7	2463.7	2521.1	2578.5	2637.6	2695.1	2734.5	2775.5
62.5°	2521.1	2517.8	2514.5	2511.2	2508.0	2555.6	2603.2	2650.8	2698.4	2727.9	2757.5
65°	2455.4	2473.5	2491.6	2509.6	2527.7	2534.2	2539.2	2545.7	2550.6	2568.7	2586.8
67.5°	2235.5	2271.6	2306.1	2342.2	2376.7	2352.0	2329.1	2304.4	2279.8	2284.7	2288.0
70°	1990.9	2032.0	2074.7	2115.7	2156.7	2099.3	2041.8	1982.7	1925.3	1905.6	1885.9
72.5°	1679.1	1715.2	1753.0	1789.1	1825.2	1754.6	1685.7	1615.1	1544.5	1510.0	1475.6
75°	1283.5	1326.2	1370.5	1413.2	1455.9	1377.1	1296.7	1217.9	1137.4	1114.5	1093.1
77.5°	935.6	986.4	1037.3	1088.2	1139.1	1068.5	997.9	925.7	855.1	842.0	828.9
80°	681.2	720.5	758.3	797.7	835.4	794.4	753.4	712.3	671.3	669.7	668.0
82.5°	459.6	494.0	526.9	561.3	594.2	577.8	563.0	546.6	530.2	546.6	564.6
85°	236.4	284.0	333.2	380.8	428.4	423.5	420.2	415.3	410.3	431.7	451.4
87.5°	47.6	88.6	129.7	169.1	210.1	200.2	190.4	178.9	169.1	175.6	180.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671813  
 CATALOG NUMBER: CCP-SA-1C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671813

CATALOG NUMBER: CCP-SA-1C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8
2.5°	1295.0	1296.7	1296.7	1296.7	1296.7	1296.7	1293.4	1291.7	1288.5	1285.2	1280.2
5°	1391.9	1390.2	1383.6	1377.1	1368.9	1362.3	1357.4	1350.8	1345.9	1339.3	1329.5
7.5°	1452.6	1455.9	1444.4	1434.5	1423.0	1411.6	1400.1	1388.6	1377.1	1365.6	1342.6
10°	1434.5	1439.5	1432.9	1426.3	1418.1	1411.6	1398.4	1383.6	1370.5	1355.7	1327.8
12.5°	1383.6	1396.8	1393.5	1390.2	1386.9	1383.6	1375.4	1365.6	1357.4	1347.5	1316.4
15°	1293.4	1293.4	1295.0	1296.7	1296.7	1298.3	1299.9	1301.6	1303.2	1304.9	1286.8
17.5°	1239.2	1234.3	1234.3	1234.3	1234.3	1234.3	1240.9	1249.1	1255.6	1262.2	1257.3
20°	1199.8	1188.3	1186.7	1186.7	1185.0	1183.4	1194.9	1208.0	1219.5	1231.0	1237.6
22.5°	1173.6	1157.1	1155.5	1153.9	1152.2	1150.6	1165.4	1180.1	1194.9	1209.7	1232.6
25°	1167.0	1148.9	1150.6	1152.2	1152.2	1153.9	1165.4	1176.8	1188.3	1199.8	1239.2
27.5°	1168.6	1139.1	1140.7	1142.4	1142.4	1144.0	1162.1	1178.5	1196.5	1212.9	1262.2
30°	1180.1	1145.7	1142.4	1139.1	1135.8	1132.5	1157.1	1181.8	1206.4	1231.0	1268.8
32.5°	1219.5	1186.7	1178.5	1170.3	1162.1	1153.9	1183.4	1211.3	1240.9	1268.8	1299.9
35°	1262.2	1226.1	1222.8	1219.5	1214.6	1211.3	1237.6	1265.5	1291.7	1318.0	1345.9
37.5°	1326.2	1290.1	1286.8	1281.9	1278.6	1273.7	1303.2	1331.1	1360.7	1388.6	1413.2
40°	1421.4	1391.9	1390.2	1390.2	1388.6	1386.9	1409.9	1434.5	1457.5	1480.5	1496.9
42.5°	1547.8	1533.0	1537.9	1544.5	1549.4	1554.3	1572.4	1592.1	1610.2	1628.2	1623.3
45°	1730.0	1744.7	1746.4	1748.0	1749.7	1751.3	1756.2	1762.8	1767.7	1772.6	1753.0
47.5°	1940.1	1959.8	1969.6	1979.5	1987.7	1997.5	1990.9	1982.7	1976.2	1968.0	1918.7
50°	2189.5	2230.6	2228.9	2227.3	2224.0	2222.4	2209.2	2196.1	2181.3	2168.2	2096.0
52.5°	2386.5	2432.5	2440.7	2448.9	2457.1	2465.3	2440.7	2416.1	2389.8	2365.2	2274.9
55°	2598.2	2645.8	2647.5	2649.1	2649.1	2650.8	2616.3	2581.8	2545.7	2511.2	2417.7
57.5°	2755.8	2801.8	2796.8	2793.6	2788.6	2783.7	2742.7	2701.6	2660.6	2619.6	2526.0
60°	2814.9	2854.3	2844.4	2834.6	2823.1	2813.3	2782.1	2750.9	2718.1	2686.9	2596.6
62.5°	2787.0	2816.5	2801.8	2788.6	2773.9	2759.1	2719.7	2678.7	2639.3	2598.2	2532.6
65°	2603.2	2621.2	2601.5	2583.5	2565.4	2545.7	2512.9	2480.1	2445.6	2412.8	2368.5
67.5°	2293.0	2296.2	2294.6	2293.0	2291.3	2289.7	2242.1	2194.5	2145.2	2097.6	2094.3
70°	1867.8	1848.1	1851.4	1856.4	1859.6	1862.9	1826.8	1792.3	1756.2	1720.1	1736.5
72.5°	1441.1	1406.6	1414.8	1424.7	1432.9	1441.1	1411.6	1383.6	1354.1	1324.6	1347.5
75°	1070.2	1048.8	1057.0	1066.9	1075.1	1083.3	1071.8	1060.3	1047.2	1035.7	1057.0
77.5°	815.7	802.6	804.3	804.3	805.9	805.9	807.5	810.8	812.5	814.1	837.1
80°	664.7	663.1	661.5	659.8	656.5	654.9	671.3	687.7	704.1	720.5	732.0
82.5°	581.0	597.4	587.6	579.4	569.5	559.7	574.5	589.2	604.0	618.8	613.9
85°	472.7	492.4	474.3	456.3	436.6	418.5	431.7	443.2	456.3	467.8	461.2
87.5°	187.1	192.0	162.5	134.6	105.0	75.5	119.8	162.5	206.8	249.5	256.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671813  
 CATALOG NUMBER: CCP-SA-1C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671813

CATALOG NUMBER: CCP-SA-1C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8	1181.8
2.5°	1275.3	1268.8	1263.8	1262.2	1258.9	1257.3	1254.0	1250.7	1245.8	1242.5	1237.6
5°	1318.0	1308.1	1296.7	1280.2	1265.5	1249.1	1232.6	1217.9	1203.1	1186.7	1171.9
7.5°	1319.6	1296.7	1273.7	1252.3	1229.4	1208.0	1185.0	1165.4	1144.0	1122.7	1103.0
10°	1301.6	1273.7	1245.8	1217.9	1191.6	1163.7	1135.8	1112.8	1088.2	1063.6	1040.6
12.5°	1286.8	1255.6	1224.4	1191.6	1160.4	1127.6	1094.8	1071.8	1048.8	1025.8	1002.9
15°	1268.8	1249.1	1231.0	1201.5	1171.9	1142.4	1112.8	1081.6	1052.1	1020.9	989.7
17.5°	1254.0	1249.1	1244.1	1224.4	1204.7	1183.4	1163.7	1132.5	1101.3	1068.5	1037.3
20°	1245.8	1252.3	1258.9	1249.1	1239.2	1227.7	1217.9	1194.9	1171.9	1147.3	1124.3
22.5°	1255.6	1280.2	1303.2	1304.9	1308.1	1309.8	1311.4	1290.1	1268.8	1245.8	1224.4
25°	1278.6	1318.0	1357.4	1378.7	1400.1	1423.0	1444.4	1431.2	1418.1	1405.0	1391.9
27.5°	1309.8	1359.0	1408.3	1439.5	1469.0	1500.2	1531.4	1529.7	1528.1	1524.8	1523.2
30°	1304.9	1342.6	1380.4	1418.1	1455.9	1493.6	1531.4	1551.1	1569.1	1588.8	1608.5
32.5°	1332.8	1364.0	1396.8	1436.2	1475.6	1516.6	1556.0	1597.0	1636.4	1677.4	1718.5
35°	1375.4	1403.3	1432.9	1475.6	1519.9	1562.6	1606.9	1656.1	1707.0	1757.9	1807.1
37.5°	1439.5	1464.1	1490.3	1526.4	1564.2	1600.3	1638.1	1710.3	1782.5	1856.4	1928.6
40°	1513.3	1529.7	1546.1	1580.6	1615.1	1649.5	1684.0	1774.3	1864.6	1954.8	2045.1
42.5°	1620.0	1615.1	1610.2	1638.1	1667.6	1695.5	1725.0	1807.1	1889.2	1971.2	2053.3
45°	1733.3	1713.6	1693.9	1707.0	1721.8	1734.9	1749.7	1833.4	1917.1	2002.4	2086.1
47.5°	1869.5	1820.2	1771.0	1759.5	1748.0	1734.9	1723.4	1813.7	1904.0	1995.9	2086.1
50°	2023.8	1949.9	1877.7	1848.1	1817.0	1787.4	1756.2	1830.1	1905.6	1981.1	2055.0
52.5°	2184.6	2092.7	2002.4	1956.5	1910.5	1862.9	1817.0	1879.3	1943.3	2007.4	2069.7
55°	2322.5	2228.9	2133.7	2079.6	2025.4	1971.2	1917.1	1979.5	2041.8	2104.2	2166.6
57.5°	2432.5	2338.9	2245.4	2194.5	2141.9	2091.1	2038.5	2097.6	2158.4	2219.1	2278.2
60°	2508.0	2417.7	2327.4	2278.2	2228.9	2179.7	2130.5	2201.0	2271.6	2343.8	2414.4
62.5°	2468.6	2402.9	2337.3	2315.9	2294.6	2271.6	2250.3	2317.6	2383.2	2450.5	2517.8
65°	2324.1	2279.8	2235.5	2256.8	2279.8	2301.2	2324.1	2368.5	2412.8	2458.7	2503.0
67.5°	2089.4	2086.1	2081.2	2128.8	2176.4	2225.7	2273.3	2302.8	2330.7	2360.2	2389.8
70°	1753.0	1771.0	1787.4	1869.5	1951.6	2033.6	2115.7	2127.2	2138.7	2150.2	2161.6
72.5°	1372.2	1395.1	1419.8	1528.1	1634.8	1743.1	1851.4	1844.9	1838.3	1830.1	1823.5
75°	1080.0	1101.3	1124.3	1224.4	1324.6	1424.7	1524.8	1496.9	1470.6	1442.7	1414.8
77.5°	861.7	884.7	909.3	1002.9	1096.4	1191.6	1285.2	1217.9	1150.6	1083.3	1016.0
80°	741.9	753.4	763.2	827.2	889.6	953.6	1017.6	948.7	878.1	807.5	738.6
82.5°	608.9	602.4	597.4	635.2	672.9	710.7	748.5	682.8	617.1	549.8	484.2
85°	454.7	448.1	441.5	461.2	480.9	502.2	521.9	446.4	370.9	293.8	218.3
87.5°	264.3	270.8	277.4	298.7	320.1	343.0	364.4	287.2	210.1	131.3	54.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671813  
 CATALOG NUMBER: CCP-SA-1C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671813  
 CATALOG NUMBER: CCP-SA-1C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
0°	1181.8	1181.8
2.5°	1227.7	1219.5
5°	1160.4	1148.9
7.5°	1086.6	1071.8
10°	1019.3	999.6
12.5°	976.6	952.0
15°	960.2	930.6
17.5°	1009.4	981.5
20°	1084.9	1047.2
22.5°	1176.8	1130.9
25°	1336.1	1280.2
27.5°	1465.7	1408.3
30°	1546.1	1483.8
32.5°	1634.8	1552.7
35°	1726.7	1647.9
37.5°	1838.3	1749.7
40°	1953.2	1861.3
42.5°	1992.6	1933.5
45°	2030.3	1974.5
47.5°	2038.5	1992.6
50°	2046.8	2040.2
52.5°	2069.7	2068.1
55°	2168.2	2169.9
57.5°	2289.7	2299.5
60°	2401.3	2389.8
62.5°	2458.7	2399.6
65°	2419.3	2337.3
67.5°	2301.2	2212.5
70°	2041.8	1922.0
72.5°	1718.5	1613.4
75°	1324.6	1235.9
77.5°	942.1	868.3
80°	663.1	589.2
82.5°	425.1	366.0
85°	192.0	167.4
87.5°	54.2	52.5
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P671813  
CATALOG NUMBER: CCP-SA-1C-735-U-SLR

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)