

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P671843

Luminaire Tested: **CCP-SA-2E-750-U-SLR**

Issue Date: 04/16/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P671843  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 04/16/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: CCP-SA-2E-750-U-SLR  
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @1050mA w/ SLR distribution lens  
Light Source: (32) 5000K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 11606.7 lumens  
Efficiency: N/A  
Efficacy: 108.9 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B2 - U0 - G3

Input Watts (W): 106.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

REPORT NUMBER: P671843  
 CATALOG NUMBER: CCP-SA-2E-750-U-SLR

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 16.5 fc  
 Type IV - Short - N/A

REPORT NUMBER: P671843  
CATALOG NUMBER: CCP-SA-2E-750-U-SLR

### Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral    - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P671843  
 CATALOG NUMBER: CCP-SA-2E-750-U-SLR


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	2388.2	0.0	2388.2
	% Fixture	20.6	0.0	20.6
<b>Street Side</b>	Lumens	9218.6	0.0	9218.6
	% Fixture	79.4	0.0	79.4
<b>Total</b>	Lumens	11606.7	0.0	11606.7
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	288.0	2.5
10°-20°	608.1	5.2
20°-30°	889.7	7.7
30°-40°	1253.4	10.8
40°-50°	1722.3	14.8
50°-60°	2347.5	20.2
60°-70°	2569.3	22.1
70°-80°	1483.8	12.8
80°-90°	444.8	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	11606.7	100.0
0°-180°	11606.7	100.0




REPORT NUMBER: P671843  
 CATALOG NUMBER: CCP-SA-2E-750-U-SLR

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1192.0	10.3			
FM (30°-60°)	4235.7	36.5			
FH (60°-80°)	3413.1	29.4			G2/5000
FVH (80°-90°)	377.8	3.3			G3/500
BL (0°-30°)	593.7	5.1	B2/1000		
BM (30°-60°)	1087.5	9.4	B2/2500		
BH (60°-80°)	640.0	5.5	B2/1000		G2/1000
BVH (80°-90°)	67.0	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B2-U0-G3**

Type IV Short





REPORT NUMBER: P671843

CATALOG NUMBER: CCP-SA-2E-750-U-SLR

**CANDELA DISTRIBUTION (FULL):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5
2.5°	3824.9	3804.3	3788.8	3773.4	3752.8	3737.4	3716.8	3696.2	3670.4	3649.8	3624.1
5°	3603.5	3541.7	3480.0	3443.9	3402.7	3366.7	3325.5	3279.2	3232.9	3181.4	3135.1
7.5°	3361.6	3284.3	3207.1	3145.4	3078.4	3016.7	2949.7	2893.1	2836.5	2779.9	2723.2
10°	3135.1	3063.0	2990.9	2913.7	2831.3	2754.1	2671.8	2594.5	2517.3	2440.1	2362.9
12.5°	2985.8	2898.3	2815.9	2728.4	2646.0	2558.5	2471.0	2398.9	2326.8	2249.6	2177.6
15°	2918.8	2836.5	2759.3	2671.8	2584.2	2496.7	2409.2	2326.8	2249.6	2167.3	2084.9
17.5°	3078.4	2960.0	2841.6	2728.4	2615.1	2501.9	2388.6	2285.7	2182.7	2079.7	1976.8
20°	3284.3	3135.1	2990.9	2851.9	2707.8	2568.8	2424.7	2280.5	2136.4	1992.2	1848.1
22.5°	3546.9	3377.0	3212.3	3032.1	2846.8	2666.6	2481.3	2301.1	2120.9	1935.6	1755.4
25°	4015.3	3814.6	3613.8	3356.4	3093.9	2836.5	2573.9	2337.1	2105.5	1868.7	1631.9
27.5°	4416.9	4144.0	3876.4	3567.5	3258.6	2949.7	2640.9	2368.0	2100.3	1827.5	1554.7
30°	4653.7	4386.0	4118.3	3742.5	3371.9	2996.1	2620.3	2316.5	2018.0	1714.2	1410.5
32.5°	4869.9	4571.3	4272.7	3860.9	3443.9	3032.1	2615.1	2280.5	1951.0	1616.4	1281.8
35°	5168.5	4839.0	4514.7	4035.9	3557.2	3078.4	2599.7	2254.8	1904.7	1559.8	1209.8
37.5°	5487.6	5081.0	4679.4	4149.2	3619.0	3088.7	2558.5	2218.7	1879.0	1539.2	1199.5
40°	5837.7	5343.5	4854.5	4267.6	3685.9	3099.0	2512.2	2172.4	1832.6	1487.7	1148.0
42.5°	6064.2	5528.8	4993.4	4360.3	3732.2	3099.0	2465.8	2131.2	1796.6	1456.9	1122.2
45°	6192.9	5673.0	5158.2	4473.5	3788.8	3104.2	2419.5	2090.0	1760.6	1426.0	1096.5
47.5°	6249.5	5765.6	5281.7	4561.0	3845.5	3124.8	2404.1	2069.4	1729.7	1395.1	1055.3
50°	6398.8	5971.5	5544.3	4772.1	4005.1	3232.9	2460.7	2100.3	1745.1	1384.8	1024.4
52.5°	6486.3	6120.8	5755.3	4962.6	4169.8	3377.0	2584.2	2182.7	1781.2	1379.6	978.1
55°	6805.5	6455.4	6105.4	5261.1	4411.7	3567.5	2718.1	2275.4	1832.6	1384.8	942.1
57.5°	7212.2	6841.5	6476.0	5564.9	4653.7	3742.5	2831.3	2357.7	1879.0	1405.4	926.6
60°	7495.3	7135.0	6779.8	5812.0	4839.0	3871.2	2898.3	2404.1	1909.9	1410.5	916.3
62.5°	7526.2	7062.9	6604.7	5662.7	4720.6	3773.4	2831.3	2352.6	1873.8	1389.9	911.2
65°	7330.6	6790.1	6249.5	5348.6	4447.8	3546.9	2646.0	2208.4	1770.9	1328.2	890.6
67.5°	6939.3	6306.2	5673.0	4849.3	4025.6	3202.0	2378.3	2002.5	1631.9	1256.1	880.3
70°	6028.2	5472.2	4921.4	4205.8	3495.4	2779.9	2064.3	1755.4	1451.7	1142.8	834.0
72.5°	5060.4	4540.4	4025.6	3443.9	2867.4	2285.7	1703.9	1472.3	1240.6	1003.8	772.2
75°	3876.4	3485.1	3099.0	2666.6	2234.2	1796.6	1364.2	1194.3	1024.4	854.5	684.7
77.5°	2723.2	2512.2	2306.3	1981.9	1657.6	1333.3	1009.0	895.7	782.5	669.2	556.0
80°	1848.1	1729.7	1616.4	1384.8	1153.1	916.3	684.7	612.6	535.4	463.3	386.1
82.5°	1148.0	1142.8	1132.5	972.9	813.4	653.8	494.2	432.4	375.8	314.0	252.2
85°	525.1	612.6	695.0	607.4	519.9	432.4	344.9	303.7	262.5	216.2	175.0
87.5°	164.7	200.8	231.7	221.4	205.9	195.6	180.2	154.4	128.7	103.0	77.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671843  
 CATALOG NUMBER: CCP-SA-2E-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671843

CATALOG NUMBER: CCP-SA-2E-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5
2.5°	3603.5	3588.1	3567.5	3546.9	3521.2	3500.6	3474.8	3449.1	3443.9	3433.6	3428.5
5°	3104.2	3073.3	3037.2	3006.4	2975.5	2939.4	2908.6	2872.5	2846.8	2815.9	2790.2
7.5°	2666.6	2615.1	2558.5	2501.9	2450.4	2398.9	2342.3	2290.8	2265.1	2239.3	2213.6
10°	2316.5	2265.1	2218.7	2167.3	2131.2	2100.3	2064.3	2028.3	1997.4	1966.5	1935.6
12.5°	2141.5	2105.5	2069.4	2033.4	1992.2	1956.2	1915.0	1873.8	1837.8	1806.9	1770.9
15°	2033.4	1981.9	1925.3	1873.8	1817.2	1765.7	1709.1	1652.5	1611.3	1575.3	1534.1
17.5°	1904.7	1827.5	1755.4	1678.2	1616.4	1554.7	1487.7	1426.0	1379.6	1328.2	1281.8
20°	1760.6	1673.1	1580.4	1492.9	1420.8	1353.9	1281.8	1209.8	1158.3	1101.6	1050.2
22.5°	1637.0	1523.8	1405.4	1287.0	1209.8	1132.5	1050.2	972.9	926.6	875.1	828.8
25°	1503.2	1379.6	1250.9	1122.2	1045.0	962.7	885.4	803.1	767.0	736.1	700.1
27.5°	1431.1	1307.6	1178.9	1055.3	983.2	906.0	834.0	756.7	731.0	700.1	674.4
30°	1287.0	1168.6	1045.0	921.5	870.0	823.7	772.2	720.7	710.4	705.3	695.0
32.5°	1158.3	1034.7	911.2	787.6	741.3	695.0	648.6	602.3	597.2	586.9	581.7
35°	1091.4	972.9	849.4	731.0	689.8	643.5	602.3	556.0	545.7	530.2	519.9
37.5°	1075.9	952.4	823.7	700.1	658.9	617.7	571.4	530.2	519.9	509.6	499.3
40°	1034.7	916.3	803.1	684.7	643.5	602.3	556.0	514.8	504.5	494.2	483.9
42.5°	1003.8	890.6	772.2	653.8	617.7	581.7	540.5	504.5	494.2	483.9	468.5
45°	978.1	859.7	736.1	617.7	592.0	566.3	535.4	509.6	499.3	483.9	473.6
47.5°	936.9	823.7	705.3	586.9	561.1	540.5	514.8	489.0	478.8	468.5	458.2
50°	906.0	787.6	669.2	550.8	530.2	509.6	489.0	468.5	468.5	473.6	473.6
52.5°	864.8	751.6	638.3	525.1	504.5	483.9	463.3	442.7	447.9	453.0	458.2
55°	828.8	720.7	607.4	494.2	473.6	453.0	427.3	406.7	411.8	417.0	422.1
57.5°	813.4	700.1	586.9	473.6	453.0	427.3	406.7	380.9	380.9	380.9	380.9
60°	803.1	684.7	571.4	453.0	427.3	406.7	380.9	355.2	350.1	350.1	344.9
62.5°	797.9	679.5	566.3	447.9	417.0	391.2	360.4	329.5	324.3	319.2	314.0
65°	777.3	669.2	556.0	442.7	406.7	375.8	339.8	303.7	298.6	298.6	293.4
67.5°	772.2	658.9	550.8	437.6	401.5	360.4	324.3	283.1	278.0	272.8	267.7
70°	731.0	633.2	530.2	427.3	386.1	350.1	308.9	267.7	262.5	252.2	247.1
72.5°	679.5	592.0	499.3	406.7	365.5	324.3	283.1	242.0	236.8	231.7	221.4
75°	602.3	519.9	437.6	355.2	319.2	288.3	252.2	216.2	211.1	205.9	195.6
77.5°	494.2	427.3	365.5	298.6	272.8	247.1	221.4	195.6	190.5	185.3	175.0
80°	350.1	308.9	272.8	231.7	216.2	195.6	180.2	159.6	159.6	154.4	154.4
82.5°	231.7	211.1	190.5	169.9	159.6	149.3	139.0	128.7	128.7	123.5	123.5
85°	164.7	154.4	139.0	128.7	123.5	113.3	108.1	97.8	97.8	97.8	97.8
87.5°	77.2	77.2	72.1	72.1	66.9	66.9	61.8	56.6	56.6	56.6	56.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671843  
 CATALOG NUMBER: CCP-SA-2E-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671843

CATALOG NUMBER: CCP-SA-2E-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5
2.5°	3418.2	3402.7	3387.3	3366.7	3351.3	3330.7	3304.9	3284.3	3258.6	3258.6	3253.5
5°	2759.3	2743.8	2728.4	2707.8	2692.3	2671.8	2656.3	2635.7	2615.1	2615.1	2610.0
7.5°	2187.8	2157.0	2126.1	2090.0	2059.2	2038.6	2018.0	1992.2	1971.6	1956.2	1940.8
10°	1904.7	1873.8	1837.8	1806.9	1770.9	1745.1	1719.4	1688.5	1662.8	1642.2	1621.6
12.5°	1734.8	1698.8	1662.8	1626.7	1590.7	1554.7	1523.8	1487.7	1451.7	1426.0	1400.2
15°	1492.9	1456.9	1420.8	1384.8	1348.7	1307.6	1266.4	1220.0	1178.9	1158.3	1142.8
17.5°	1230.3	1194.3	1153.1	1117.1	1075.9	1045.0	1014.1	983.2	952.4	931.8	916.3
20°	993.5	952.4	911.2	870.0	828.8	808.2	787.6	767.0	746.4	731.0	720.7
22.5°	777.3	751.6	731.0	705.3	679.5	664.1	653.8	638.3	622.9	622.9	622.9
25°	664.1	648.6	638.3	622.9	607.4	602.3	597.2	586.9	581.7	576.6	576.6
27.5°	643.5	628.0	612.6	597.2	581.7	576.6	571.4	561.1	556.0	556.0	556.0
30°	684.7	679.5	674.4	669.2	664.1	653.8	638.3	628.0	612.6	602.3	592.0
32.5°	571.4	566.3	566.3	561.1	556.0	566.3	571.4	581.7	586.9	592.0	597.2
35°	504.5	494.2	483.9	473.6	463.3	458.2	453.0	447.9	442.7	442.7	437.6
37.5°	489.0	478.8	468.5	458.2	447.9	442.7	437.6	432.4	427.3	427.3	422.1
40°	473.6	463.3	458.2	447.9	437.6	432.4	427.3	417.0	411.8	406.7	406.7
42.5°	458.2	453.0	442.7	437.6	427.3	422.1	417.0	406.7	401.5	396.4	391.2
45°	458.2	447.9	437.6	427.3	417.0	411.8	401.5	396.4	386.1	386.1	380.9
47.5°	447.9	437.6	427.3	417.0	406.7	401.5	391.2	386.1	375.8	370.6	365.5
50°	473.6	458.2	437.6	422.1	401.5	396.4	386.1	380.9	370.6	365.5	360.4
52.5°	463.3	447.9	427.3	411.8	391.2	380.9	375.8	365.5	355.2	350.1	344.9
55°	427.3	411.8	401.5	386.1	370.6	360.4	350.1	339.8	329.5	324.3	324.3
57.5°	380.9	375.8	370.6	365.5	360.4	350.1	339.8	324.3	314.0	308.9	303.7
60°	339.8	344.9	350.1	355.2	360.4	344.9	329.5	314.0	298.6	293.4	288.3
62.5°	308.9	319.2	329.5	334.6	344.9	329.5	314.0	298.6	283.1	278.0	272.8
65°	288.3	293.4	293.4	298.6	298.6	288.3	283.1	272.8	262.5	257.4	257.4
67.5°	262.5	262.5	262.5	257.4	257.4	252.2	252.2	247.1	242.0	236.8	236.8
70°	236.8	236.8	236.8	231.7	231.7	226.5	226.5	221.4	216.2	216.2	211.1
72.5°	216.2	216.2	211.1	211.1	205.9	205.9	205.9	200.8	200.8	195.6	195.6
75°	190.5	190.5	185.3	185.3	180.2	180.2	180.2	175.0	175.0	175.0	169.9
77.5°	169.9	169.9	164.7	164.7	159.6	159.6	159.6	154.4	154.4	149.3	149.3
80°	149.3	149.3	144.1	144.1	139.0	139.0	133.8	133.8	128.7	128.7	123.5
82.5°	118.4	118.4	118.4	118.4	118.4	113.3	113.3	108.1	103.0	103.0	97.8
85°	97.8	97.8	97.8	92.7	92.7	92.7	87.5	87.5	82.4	77.2	77.2
87.5°	56.6	56.6	56.6	51.5	51.5	51.5	51.5	51.5	51.5	51.5	46.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671843  
 CATALOG NUMBER: CCP-SA-2E-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671843

CATALOG NUMBER: CCP-SA-2E-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5
2.5°	3253.5	3248.3	3227.7	3207.1	3227.7	3248.3	3248.3	3248.3	3243.2	3243.2	3243.2
5°	2610.0	2604.8	2594.5	2584.2	2584.2	2579.1	2589.4	2599.7	2610.0	2620.3	2630.6
7.5°	1920.2	1904.7	1889.3	1873.8	1884.1	1889.3	1904.7	1915.0	1930.5	1940.8	1966.5
10°	1601.0	1580.4	1565.0	1549.5	1539.2	1528.9	1518.6	1513.5	1503.2	1492.9	1503.2
12.5°	1369.3	1343.6	1317.9	1287.0	1281.8	1276.7	1266.4	1256.1	1245.8	1235.5	1230.3
15°	1122.2	1101.6	1091.4	1075.9	1055.3	1034.7	1024.4	1019.3	1009.0	998.7	993.5
17.5°	895.7	875.1	859.7	844.3	839.1	828.8	828.8	828.8	828.8	828.8	828.8
20°	705.3	689.8	689.8	684.7	684.7	679.5	684.7	689.8	689.8	695.0	700.1
22.5°	617.7	617.7	612.6	607.4	612.6	612.6	617.7	622.9	628.0	633.2	638.3
25°	571.4	566.3	571.4	576.6	576.6	576.6	581.7	581.7	586.9	586.9	586.9
27.5°	550.8	550.8	556.0	556.0	561.1	561.1	561.1	556.0	556.0	550.8	550.8
30°	581.7	571.4	571.4	571.4	566.3	561.1	556.0	556.0	550.8	545.7	540.5
32.5°	602.3	607.4	602.3	592.0	586.9	576.6	571.4	561.1	556.0	545.7	535.4
35°	437.6	432.4	442.7	447.9	453.0	458.2	463.3	468.5	468.5	473.6	473.6
37.5°	422.1	417.0	417.0	411.8	411.8	411.8	411.8	411.8	406.7	406.7	411.8
40°	401.5	396.4	396.4	391.2	391.2	386.1	386.1	386.1	386.1	386.1	386.1
42.5°	386.1	380.9	380.9	380.9	380.9	375.8	375.8	370.6	370.6	365.5	365.5
45°	380.9	375.8	370.6	365.5	365.5	360.4	360.4	360.4	355.2	355.2	355.2
47.5°	360.4	355.2	355.2	350.1	350.1	344.9	344.9	344.9	339.8	339.8	339.8
50°	350.1	344.9	344.9	339.8	339.8	334.6	334.6	334.6	329.5	329.5	329.5
52.5°	334.6	329.5	329.5	329.5	324.3	319.2	319.2	319.2	314.0	314.0	314.0
55°	319.2	314.0	314.0	314.0	308.9	303.7	303.7	303.7	298.6	298.6	298.6
57.5°	298.6	293.4	293.4	288.3	288.3	288.3	288.3	288.3	283.1	283.1	283.1
60°	283.1	278.0	278.0	272.8	272.8	267.7	267.7	267.7	267.7	267.7	267.7
62.5°	267.7	262.5	257.4	252.2	257.4	257.4	257.4	257.4	252.2	252.2	252.2
65°	252.2	247.1	242.0	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8
67.5°	231.7	226.5	221.4	216.2	221.4	221.4	221.4	221.4	221.4	221.4	221.4
70°	211.1	205.9	205.9	200.8	200.8	195.6	195.6	200.8	200.8	200.8	200.8
72.5°	190.5	185.3	185.3	180.2	180.2	180.2	180.2	180.2	180.2	180.2	180.2
75°	169.9	164.7	164.7	159.6	159.6	159.6	159.6	159.6	159.6	159.6	159.6
77.5°	144.1	139.0	139.0	139.0	139.0	139.0	139.0	144.1	144.1	144.1	144.1
80°	123.5	118.4	118.4	118.4	118.4	118.4	118.4	118.4	118.4	118.4	118.4
82.5°	97.8	92.7	92.7	92.7	92.7	92.7	92.7	92.7	92.7	92.7	92.7
85°	72.1	66.9	66.9	66.9	72.1	72.1	72.1	72.1	72.1	72.1	72.1
87.5°	46.3	41.2	41.2	41.2	46.3	46.3	46.3	46.3	41.2	41.2	41.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671843  
 CATALOG NUMBER: CCP-SA-2E-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671843

CATALOG NUMBER: CCP-SA-2E-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5
2.5°	3243.2	3243.2	3243.2	3238.0	3232.9	3227.7	3222.6	3238.0	3248.3	3263.8	3274.1
5°	2635.7	2646.0	2651.2	2666.6	2682.0	2697.5	2712.9	2723.2	2733.5	2738.7	2749.0
7.5°	1987.1	2012.8	2033.4	2054.0	2074.6	2090.0	2110.6	2126.1	2141.5	2157.0	2172.4
10°	1508.3	1518.6	1523.8	1544.4	1559.8	1580.4	1595.8	1611.3	1626.7	1637.0	1652.5
12.5°	1225.2	1214.9	1209.8	1209.8	1209.8	1209.8	1209.8	1220.0	1230.3	1240.6	1250.9
15°	988.4	983.2	978.1	972.9	967.8	957.5	952.4	962.7	972.9	983.2	993.5
17.5°	828.8	828.8	828.8	823.7	818.5	813.4	808.2	813.4	818.5	818.5	823.7
20°	710.4	715.6	720.7	725.9	725.9	731.0	731.0	736.1	741.3	741.3	746.4
22.5°	638.3	643.5	643.5	643.5	648.6	648.6	648.6	653.8	658.9	664.1	669.2
25°	581.7	581.7	576.6	576.6	581.7	581.7	581.7	581.7	586.9	586.9	586.9
27.5°	550.8	545.7	545.7	545.7	545.7	540.5	540.5	540.5	540.5	540.5	540.5
30°	535.4	530.2	525.1	519.9	519.9	514.8	509.6	509.6	509.6	509.6	509.6
32.5°	530.2	519.9	509.6	504.5	504.5	499.3	494.2	489.0	489.0	483.9	478.8
35°	473.6	468.5	468.5	463.3	458.2	453.0	447.9	447.9	447.9	442.7	442.7
37.5°	411.8	417.0	417.0	417.0	422.1	422.1	422.1	422.1	427.3	427.3	427.3
40°	386.1	386.1	386.1	391.2	396.4	396.4	401.5	401.5	406.7	406.7	406.7
42.5°	365.5	360.4	360.4	365.5	365.5	370.6	370.6	375.8	380.9	380.9	386.1
45°	355.2	350.1	350.1	350.1	350.1	344.9	344.9	350.1	355.2	360.4	365.5
47.5°	334.6	334.6	329.5	329.5	329.5	329.5	329.5	329.5	334.6	334.6	334.6
50°	324.3	324.3	319.2	319.2	319.2	319.2	319.2	319.2	319.2	319.2	319.2
52.5°	314.0	308.9	308.9	308.9	308.9	303.7	303.7	303.7	303.7	303.7	303.7
55°	298.6	293.4	293.4	293.4	293.4	293.4	293.4	293.4	298.6	298.6	298.6
57.5°	283.1	278.0	278.0	278.0	283.1	283.1	283.1	283.1	288.3	288.3	288.3
60°	267.7	267.7	267.7	267.7	267.7	267.7	267.7	272.8	272.8	278.0	278.0
62.5°	252.2	252.2	252.2	252.2	257.4	257.4	257.4	257.4	262.5	262.5	262.5
65°	236.8	236.8	236.8	236.8	242.0	242.0	242.0	242.0	242.0	242.0	242.0
67.5°	221.4	221.4	221.4	221.4	221.4	221.4	221.4	226.5	226.5	231.7	231.7
70°	200.8	195.6	195.6	200.8	200.8	205.9	205.9	211.1	211.1	216.2	216.2
72.5°	180.2	180.2	180.2	180.2	180.2	180.2	180.2	185.3	190.5	190.5	195.6
75°	159.6	159.6	159.6	159.6	164.7	164.7	164.7	169.9	169.9	175.0	175.0
77.5°	144.1	139.0	139.0	139.0	144.1	144.1	144.1	149.3	149.3	154.4	154.4
80°	118.4	118.4	118.4	118.4	123.5	123.5	123.5	123.5	128.7	128.7	128.7
82.5°	97.8	97.8	97.8	97.8	97.8	97.8	97.8	97.8	103.0	103.0	103.0
85°	72.1	72.1	72.1	72.1	77.2	77.2	77.2	77.2	77.2	77.2	77.2
87.5°	46.3	46.3	46.3	46.3	46.3	46.3	46.3	46.3	51.5	51.5	51.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671843  
 CATALOG NUMBER: CCP-SA-2E-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671843

CATALOG NUMBER: CCP-SA-2E-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5
2.5°	3274.1	3274.1	3274.1	3274.1	3284.3	3289.5	3299.8	3304.9	3299.8	3294.6	3284.3
5°	2754.1	2759.3	2759.3	2764.4	2764.4	2764.4	2764.4	2764.4	2774.7	2785.0	2795.3
7.5°	2177.6	2182.7	2187.8	2193.0	2193.0	2193.0	2187.8	2187.8	2193.0	2193.0	2198.1
10°	1667.9	1688.5	1703.9	1719.4	1709.1	1693.7	1683.4	1667.9	1667.9	1667.9	1662.8
12.5°	1261.2	1266.4	1276.7	1281.8	1276.7	1276.7	1271.5	1266.4	1271.5	1281.8	1287.0
15°	998.7	998.7	1003.8	1003.8	1009.0	1014.1	1014.1	1019.3	1029.6	1034.7	1045.0
17.5°	828.8	834.0	834.0	839.1	839.1	844.3	844.3	844.3	854.5	864.8	880.3
20°	746.4	746.4	746.4	746.4	746.4	741.3	741.3	736.1	741.3	751.6	756.7
22.5°	669.2	674.4	674.4	674.4	669.2	664.1	653.8	648.6	648.6	653.8	653.8
25°	586.9	581.7	581.7	576.6	576.6	581.7	581.7	581.7	586.9	586.9	592.0
27.5°	540.5	535.4	535.4	530.2	530.2	535.4	535.4	535.4	535.4	535.4	535.4
30°	504.5	504.5	499.3	494.2	499.3	499.3	504.5	504.5	509.6	509.6	514.8
32.5°	478.8	473.6	473.6	468.5	473.6	473.6	478.8	478.8	483.9	489.0	489.0
35°	442.7	442.7	442.7	442.7	442.7	442.7	437.6	437.6	437.6	437.6	437.6
37.5°	422.1	422.1	417.0	411.8	411.8	411.8	411.8	411.8	406.7	401.5	396.4
40°	406.7	401.5	401.5	396.4	391.2	391.2	386.1	380.9	380.9	375.8	375.8
42.5°	386.1	380.9	380.9	375.8	370.6	370.6	365.5	360.4	360.4	360.4	355.2
45°	360.4	360.4	355.2	350.1	350.1	350.1	344.9	344.9	344.9	344.9	339.8
47.5°	334.6	334.6	329.5	329.5	329.5	329.5	324.3	324.3	324.3	324.3	324.3
50°	319.2	319.2	319.2	319.2	319.2	319.2	314.0	314.0	314.0	314.0	314.0
52.5°	303.7	303.7	303.7	303.7	303.7	303.7	303.7	303.7	303.7	303.7	303.7
55°	298.6	298.6	298.6	298.6	298.6	298.6	293.4	293.4	293.4	298.6	298.6
57.5°	288.3	288.3	283.1	283.1	283.1	283.1	283.1	283.1	283.1	283.1	283.1
60°	278.0	278.0	278.0	278.0	278.0	278.0	278.0	278.0	278.0	278.0	278.0
62.5°	262.5	262.5	262.5	262.5	262.5	267.7	267.7	267.7	267.7	267.7	262.5
65°	242.0	247.1	247.1	247.1	247.1	247.1	247.1	247.1	247.1	247.1	247.1
67.5°	231.7	231.7	231.7	231.7	231.7	231.7	231.7	231.7	231.7	231.7	231.7
70°	216.2	216.2	211.1	211.1	211.1	216.2	216.2	216.2	216.2	216.2	216.2
72.5°	195.6	195.6	195.6	195.6	195.6	195.6	195.6	195.6	195.6	200.8	200.8
75°	175.0	175.0	175.0	175.0	175.0	175.0	175.0	175.0	175.0	175.0	175.0
77.5°	154.4	154.4	149.3	149.3	149.3	154.4	154.4	154.4	154.4	159.6	159.6
80°	128.7	128.7	128.7	128.7	128.7	128.7	128.7	128.7	128.7	133.8	133.8
82.5°	103.0	103.0	103.0	103.0	103.0	103.0	103.0	103.0	103.0	108.1	108.1
85°	77.2	82.4	82.4	82.4	82.4	82.4	82.4	82.4	82.4	87.5	87.5
87.5°	51.5	51.5	51.5	51.5	51.5	51.5	46.3	46.3	46.3	46.3	41.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671843  
 CATALOG NUMBER: CCP-SA-2E-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671843

CATALOG NUMBER: CCP-SA-2E-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5
2.5°	3279.2	3284.3	3289.5	3289.5	3294.6	3299.8	3299.8	3320.4	3341.0	3351.3	3361.6
5°	2805.6	2800.4	2800.4	2795.3	2790.2	2805.6	2821.0	2851.9	2882.8	2888.0	2898.3
7.5°	2198.1	2203.3	2208.4	2208.4	2213.6	2198.1	2177.6	2182.7	2187.8	2213.6	2234.2
10°	1662.8	1667.9	1673.1	1673.1	1678.2	1673.1	1662.8	1678.2	1693.7	1714.2	1740.0
12.5°	1292.1	1307.6	1323.0	1333.3	1348.7	1359.0	1364.2	1384.8	1400.2	1426.0	1451.7
15°	1055.3	1065.6	1075.9	1086.2	1096.5	1106.8	1117.1	1137.7	1158.3	1189.2	1220.0
17.5°	890.6	890.6	895.7	895.7	895.7	906.0	916.3	926.6	931.8	962.7	993.5
20°	761.9	756.7	751.6	746.4	741.3	751.6	756.7	761.9	767.0	787.6	803.1
22.5°	653.8	653.8	658.9	658.9	658.9	653.8	643.5	648.6	648.6	658.9	674.4
25°	592.0	592.0	592.0	586.9	586.9	592.0	597.2	597.2	592.0	597.2	602.3
27.5°	535.4	540.5	540.5	545.7	545.7	550.8	550.8	550.8	550.8	556.0	561.1
30°	514.8	514.8	519.9	519.9	519.9	525.1	530.2	530.2	530.2	535.4	545.7
32.5°	494.2	499.3	504.5	509.6	514.8	519.9	519.9	525.1	525.1	530.2	535.4
35°	437.6	432.4	432.4	427.3	422.1	422.1	422.1	422.1	417.0	422.1	422.1
37.5°	391.2	391.2	391.2	386.1	386.1	391.2	391.2	391.2	391.2	396.4	396.4
40°	370.6	370.6	370.6	370.6	370.6	370.6	370.6	375.8	375.8	380.9	386.1
42.5°	355.2	355.2	355.2	355.2	355.2	360.4	360.4	360.4	360.4	365.5	365.5
45°	339.8	339.8	339.8	339.8	339.8	339.8	339.8	344.9	344.9	350.1	355.2
47.5°	324.3	324.3	324.3	324.3	324.3	329.5	334.6	334.6	334.6	339.8	339.8
50°	314.0	314.0	314.0	314.0	314.0	319.2	319.2	324.3	324.3	329.5	334.6
52.5°	303.7	303.7	303.7	303.7	303.7	308.9	308.9	314.0	314.0	319.2	324.3
55°	298.6	298.6	298.6	293.4	293.4	298.6	298.6	303.7	303.7	308.9	308.9
57.5°	283.1	283.1	283.1	283.1	283.1	283.1	283.1	288.3	288.3	293.4	298.6
60°	278.0	278.0	272.8	272.8	267.7	272.8	272.8	278.0	278.0	283.1	283.1
62.5°	262.5	262.5	262.5	257.4	257.4	262.5	262.5	262.5	262.5	267.7	272.8
65°	247.1	247.1	247.1	242.0	242.0	247.1	247.1	247.1	247.1	252.2	257.4
67.5°	231.7	231.7	231.7	226.5	226.5	226.5	226.5	231.7	231.7	236.8	242.0
70°	216.2	216.2	216.2	211.1	211.1	211.1	205.9	211.1	216.2	221.4	221.4
72.5°	200.8	200.8	200.8	195.6	195.6	195.6	190.5	195.6	195.6	200.8	200.8
75°	175.0	175.0	175.0	175.0	175.0	175.0	169.9	169.9	169.9	175.0	175.0
77.5°	159.6	159.6	159.6	154.4	154.4	154.4	149.3	149.3	149.3	154.4	154.4
80°	133.8	133.8	133.8	128.7	128.7	128.7	123.5	123.5	123.5	128.7	128.7
82.5°	108.1	108.1	108.1	103.0	103.0	103.0	97.8	97.8	97.8	103.0	103.0
85°	87.5	87.5	87.5	87.5	87.5	87.5	82.4	82.4	82.4	87.5	92.7
87.5°	41.2	41.2	46.3	46.3	46.3	46.3	41.2	41.2	36.0	36.0	41.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671843  
 CATALOG NUMBER: CCP-SA-2E-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671843

CATALOG NUMBER: CCP-SA-2E-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5
2.5°	3371.9	3382.2	3407.9	3428.5	3454.2	3474.8	3490.3	3510.9	3526.3	3541.7	3552.0
5°	2903.4	2908.6	2934.3	2960.0	2980.6	3006.4	3042.4	3078.4	3114.5	3150.5	3176.2
7.5°	2259.9	2280.5	2311.4	2347.4	2378.3	2409.2	2445.2	2486.4	2522.5	2558.5	2594.5
10°	1760.6	1781.2	1812.1	1842.9	1868.7	1899.6	1940.8	1981.9	2023.1	2064.3	2105.5
12.5°	1477.4	1503.2	1539.2	1575.3	1606.1	1642.2	1693.7	1740.0	1791.5	1837.8	1889.3
15°	1245.8	1276.7	1323.0	1374.5	1420.8	1467.1	1518.6	1570.1	1616.4	1667.9	1719.4
17.5°	1024.4	1055.3	1096.5	1142.8	1184.0	1225.2	1287.0	1343.6	1405.4	1462.0	1518.6
20°	823.7	839.1	880.3	921.5	962.7	1003.8	1050.2	1096.5	1142.8	1189.2	1261.2
22.5°	684.7	695.0	715.6	731.0	751.6	767.0	813.4	859.7	900.9	947.2	1014.1
25°	602.3	607.4	622.9	633.2	648.6	658.9	689.8	715.6	746.4	772.2	834.0
27.5°	561.1	566.3	571.4	576.6	581.7	586.9	607.4	628.0	643.5	664.1	720.7
30°	550.8	556.0	571.4	581.7	597.2	607.4	617.7	628.0	638.3	648.6	684.7
32.5°	540.5	545.7	545.7	540.5	540.5	535.4	545.7	550.8	561.1	566.3	597.2
35°	427.3	427.3	432.4	437.6	442.7	447.9	463.3	473.6	489.0	499.3	525.1
37.5°	401.5	401.5	406.7	417.0	422.1	427.3	437.6	447.9	458.2	468.5	494.2
40°	386.1	391.2	396.4	401.5	406.7	411.8	422.1	427.3	437.6	442.7	463.3
42.5°	370.6	370.6	375.8	386.1	391.2	396.4	406.7	411.8	422.1	427.3	447.9
45°	360.4	365.5	370.6	375.8	375.8	380.9	391.2	401.5	406.7	417.0	437.6
47.5°	344.9	344.9	355.2	360.4	370.6	375.8	386.1	391.2	401.5	406.7	427.3
50°	334.6	339.8	350.1	355.2	365.5	370.6	386.1	396.4	411.8	422.1	432.4
52.5°	324.3	329.5	339.8	344.9	355.2	360.4	380.9	401.5	417.0	437.6	437.6
55°	314.0	314.0	324.3	339.8	350.1	360.4	370.6	386.1	396.4	406.7	406.7
57.5°	298.6	303.7	314.0	329.5	339.8	350.1	360.4	370.6	375.8	386.1	380.9
60°	288.3	288.3	303.7	319.2	334.6	350.1	350.1	350.1	344.9	344.9	344.9
62.5°	272.8	278.0	298.6	324.3	344.9	365.5	350.1	334.6	319.2	303.7	308.9
65°	262.5	267.7	278.0	293.4	303.7	314.0	303.7	298.6	288.3	278.0	283.1
67.5°	242.0	247.1	252.2	252.2	257.4	257.4	257.4	257.4	257.4	257.4	262.5
70°	226.5	226.5	226.5	231.7	231.7	231.7	231.7	231.7	231.7	231.7	236.8
72.5°	205.9	205.9	205.9	205.9	205.9	205.9	205.9	205.9	205.9	205.9	211.1
75°	180.2	180.2	180.2	180.2	180.2	180.2	180.2	180.2	180.2	180.2	185.3
77.5°	159.6	159.6	159.6	159.6	159.6	159.6	159.6	159.6	154.4	154.4	159.6
80°	133.8	133.8	133.8	133.8	128.7	128.7	128.7	128.7	128.7	128.7	133.8
82.5°	108.1	108.1	108.1	108.1	103.0	103.0	103.0	103.0	97.8	97.8	103.0
85°	97.8	103.0	103.0	108.1	108.1	108.1	103.0	97.8	92.7	87.5	87.5
87.5°	41.2	41.2	41.2	41.2	36.0	36.0	36.0	36.0	36.0	36.0	36.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671843  
 CATALOG NUMBER: CCP-SA-2E-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671843

CATALOG NUMBER: CCP-SA-2E-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5
2.5°	3567.5	3577.8	3588.1	3603.5	3624.1	3639.6	3655.0	3685.9	3721.9	3752.8	3783.7
5°	3202.0	3227.7	3253.5	3284.3	3315.2	3341.0	3371.9	3433.6	3495.4	3552.0	3613.8
7.5°	2625.4	2661.5	2692.3	2743.8	2790.2	2841.6	2888.0	2965.2	3037.2	3114.5	3186.5
10°	2146.7	2187.8	2229.0	2296.0	2368.0	2434.9	2501.9	2563.6	2630.6	2692.3	2754.1
12.5°	1940.8	1987.1	2038.6	2079.7	2126.1	2167.3	2208.4	2280.5	2352.6	2424.7	2496.7
15°	1770.9	1822.3	1873.8	1925.3	1971.6	2023.1	2069.4	2131.2	2198.1	2259.9	2321.7
17.5°	1575.3	1626.7	1683.4	1740.0	1796.6	1853.2	1909.9	1997.4	2084.9	2167.3	2254.8
20°	1328.2	1400.2	1467.1	1544.4	1621.6	1698.8	1776.0	1868.7	1961.3	2048.9	2141.5
22.5°	1081.1	1148.0	1214.9	1307.6	1400.2	1487.7	1580.4	1703.9	1822.3	1945.9	2064.3
25°	900.9	962.7	1024.4	1127.4	1225.2	1328.2	1426.0	1575.3	1719.4	1868.7	2012.8
27.5°	777.3	834.0	890.6	998.7	1106.8	1209.8	1317.9	1482.6	1642.2	1806.9	1966.5
30°	720.7	756.7	792.8	895.7	998.7	1096.5	1199.5	1359.0	1518.6	1678.2	1837.8
32.5°	628.0	658.9	689.8	782.5	875.1	962.7	1055.3	1220.0	1379.6	1544.4	1703.9
35°	556.0	581.7	607.4	695.0	777.3	864.8	947.2	1111.9	1276.7	1441.4	1606.1
37.5°	514.8	540.5	561.1	638.3	720.7	797.9	875.1	1039.9	1199.5	1364.2	1523.8
40°	483.9	499.3	519.9	597.2	669.2	746.4	818.5	967.8	1122.2	1271.5	1420.8
42.5°	463.3	483.9	499.3	566.3	638.3	705.3	772.2	916.3	1060.5	1199.5	1343.6
45°	458.2	478.8	499.3	556.0	612.6	664.1	720.7	859.7	998.7	1137.7	1276.7
47.5°	447.9	463.3	483.9	530.2	571.4	617.7	658.9	797.9	936.9	1070.8	1209.8
50°	442.7	447.9	458.2	499.3	540.5	581.7	622.9	761.9	900.9	1039.9	1178.9
52.5°	437.6	437.6	437.6	473.6	509.6	540.5	576.6	715.6	859.7	998.7	1137.7
55°	406.7	401.5	401.5	437.6	468.5	504.5	535.4	674.4	813.4	947.2	1086.2
57.5°	375.8	370.6	365.5	396.4	427.3	458.2	489.0	628.0	772.2	911.2	1050.2
60°	344.9	339.8	339.8	370.6	396.4	427.3	453.0	597.2	736.1	880.3	1019.3
62.5°	308.9	314.0	314.0	339.8	370.6	396.4	422.1	566.3	715.6	859.7	1003.8
65°	283.1	288.3	288.3	319.2	350.1	380.9	411.8	550.8	695.0	834.0	972.9
67.5°	262.5	267.7	267.7	303.7	334.6	370.6	401.5	525.1	653.8	777.3	900.9
70°	242.0	242.0	247.1	283.1	319.2	355.2	391.2	499.3	607.4	710.4	818.5
72.5°	216.2	221.4	226.5	262.5	293.4	329.5	360.4	458.2	556.0	653.8	751.6
75°	190.5	195.6	200.8	231.7	262.5	293.4	324.3	417.0	504.5	597.2	684.7
77.5°	169.9	175.0	180.2	205.9	231.7	257.4	283.1	350.1	422.1	489.0	556.0
80°	139.0	139.0	144.1	164.7	185.3	200.8	221.4	267.7	314.0	355.2	401.5
82.5°	103.0	108.1	108.1	123.5	133.8	149.3	159.6	185.3	205.9	231.7	252.2
85°	87.5	82.4	82.4	92.7	97.8	108.1	113.3	128.7	139.0	154.4	164.7
87.5°	36.0	30.9	30.9	36.0	46.3	51.5	56.6	56.6	61.8	61.8	61.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671843  
 CATALOG NUMBER: CCP-SA-2E-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671843

CATALOG NUMBER: CCP-SA-2E-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5
2.5°	3799.1	3809.4	3824.9	3835.2	3860.9	3881.5	3907.2	3927.8	3943.3	3969.0	3958.7
5°	3660.1	3706.5	3752.8	3799.1	3835.2	3871.2	3902.1	3938.1	3979.3	4056.5	4077.1
7.5°	3248.3	3310.1	3366.7	3428.5	3500.6	3572.6	3644.7	3716.8	3783.7	3881.5	3943.3
10°	2841.6	2929.1	3011.5	3099.0	3165.9	3232.9	3294.6	3361.6	3454.2	3552.0	3665.3
12.5°	2584.2	2671.8	2759.3	2846.8	2944.6	3037.2	3135.1	3227.7	3315.2	3392.5	3521.2
15°	2414.4	2512.2	2604.8	2697.5	2815.9	2929.1	3047.5	3160.8	3289.5	3392.5	3480.0
17.5°	2373.2	2491.6	2604.8	2723.2	2846.8	2970.3	3093.9	3217.4	3346.1	3500.6	3613.8
20°	2301.1	2460.7	2620.3	2779.9	2939.4	3093.9	3253.5	3407.9	3577.8	3763.1	3814.6
22.5°	2259.9	2450.4	2646.0	2836.5	3052.7	3274.1	3490.3	3706.5	3886.7	4025.6	4180.1
25°	2254.8	2491.6	2733.5	2970.3	3243.2	3510.9	3783.7	4051.4	4283.0	4422.0	4545.6
27.5°	2249.6	2537.9	2821.0	3104.2	3438.8	3768.2	4102.9	4432.3	4648.5	4849.3	4952.3
30°	2187.8	2532.8	2882.8	3227.7	3603.5	3979.3	4355.1	4730.9	4952.3	5091.3	5142.7
32.5°	2110.6	2517.3	2924.0	3330.7	3758.0	4185.2	4607.4	5034.6	5209.7	5328.1	5286.9
35°	2048.9	2496.7	2939.4	3382.2	3835.2	4293.3	4746.3	5199.4	5451.6	5616.3	5549.4
37.5°	1992.2	2460.7	2929.1	3397.6	3927.8	4458.1	4988.3	5518.5	5760.5	5935.5	5858.3
40°	1925.3	2424.7	2929.1	3428.5	4035.9	4638.2	5245.7	5848.0	6162.0	6311.3	6192.9
42.5°	1868.7	2388.6	2913.7	3433.6	4082.3	4730.9	5379.5	6028.2	6378.2	6589.3	6440.0
45°	1796.6	2316.5	2831.3	3351.3	4066.8	4782.4	5492.8	6208.3	6615.0	6779.8	6573.8
47.5°	1719.4	2234.2	2743.8	3253.5	4015.3	4777.2	5539.1	6301.0	6676.8	6872.4	6681.9
50°	1693.7	2208.4	2718.1	3232.9	4056.5	4885.3	5709.0	6532.7	6805.5	6965.1	6712.8
52.5°	1688.5	2234.2	2785.0	3330.7	4159.5	4983.1	5812.0	6635.6	6857.0	7026.9	6800.4
55°	1673.1	2265.1	2851.9	3438.8	4303.6	5173.6	6038.5	6903.3	7124.7	7248.2	7078.3
57.5°	1688.5	2326.8	2960.0	3598.4	4489.0	5379.5	6270.1	7160.7	7428.4	7515.9	7479.9
60°	1698.8	2378.3	3052.7	3732.2	4602.2	5472.2	6342.2	7212.2	7490.2	7706.4	7747.6
62.5°	1673.1	2342.3	3006.4	3675.6	4463.2	5250.8	6038.5	6826.1	7284.3	7603.4	7788.7
65°	1595.8	2213.6	2836.5	3454.2	4180.1	4911.1	5636.9	6362.8	6846.7	7320.3	7469.6
67.5°	1426.0	1951.0	2476.1	3001.2	3634.4	4267.6	4895.6	5528.8	6136.3	6594.4	6800.4
70°	1235.5	1647.3	2064.3	2476.1	3052.7	3629.3	4205.8	4782.4	5317.8	5822.3	6017.9
72.5°	1075.9	1395.1	1719.4	2038.6	2450.4	2857.1	3268.9	3675.6	4308.8	4813.3	5003.7
75°	916.3	1148.0	1374.5	1606.1	1889.3	2172.4	2450.4	2733.5	3181.4	3634.4	3824.9
77.5°	705.3	859.7	1009.0	1158.3	1353.9	1544.4	1740.0	1930.5	2244.5	2584.2	2682.0
80°	489.0	576.6	658.9	746.4	900.9	1055.3	1209.8	1364.2	1570.1	1760.6	1909.9
82.5°	303.7	360.4	411.8	463.3	586.9	710.4	828.8	952.4	1034.7	1045.0	1194.3
85°	195.6	231.7	262.5	293.4	365.5	442.7	514.8	586.9	625.1	489.0	581.7
87.5°	77.2	97.8	113.3	128.7	123.5	118.4	113.3	108.1	92.7	82.4	103.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671843  
 CATALOG NUMBER: CCP-SA-2E-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671843

CATALOG NUMBER: CCP-SA-2E-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5
2.5°	3969.0	3984.5	3999.9	4010.2	4025.6	4030.8	4035.9	4035.9	4041.1	4046.2	4056.5
5°	4159.5	4190.4	4221.3	4247.0	4277.9	4303.6	4324.2	4350.0	4370.6	4370.6	4365.4
7.5°	3999.9	4077.1	4154.3	4231.6	4308.8	4365.4	4416.9	4473.5	4525.0	4535.3	4545.6
10°	3788.8	3871.2	3948.4	4030.8	4108.0	4195.5	4277.9	4360.3	4447.8	4463.2	4483.8
12.5°	3593.2	3691.0	3788.8	3881.5	3979.3	4041.1	4102.9	4159.5	4221.3	4262.4	4303.6
15°	3588.1	3670.4	3752.8	3830.0	3912.4	3948.4	3984.5	4015.3	4051.4	4051.4	4056.5
17.5°	3706.5	3758.0	3809.4	3855.8	3907.2	3912.4	3922.7	3927.8	3933.0	3917.5	3902.1
20°	3938.1	3958.7	3979.3	3999.9	4020.5	3984.5	3953.6	3917.5	3881.5	3840.3	3804.3
22.5°	4277.9	4231.6	4185.2	4138.9	4092.6	4030.8	3963.9	3902.1	3835.2	3783.7	3732.2
25°	4597.1	4540.4	4483.8	4427.2	4370.6	4236.7	4102.9	3963.9	3830.0	3773.4	3716.8
27.5°	5024.3	4936.8	4849.3	4761.8	4674.3	4494.1	4313.9	4133.7	3953.6	3855.8	3763.1
30°	5127.3	5029.5	4931.7	4828.7	4730.9	4555.9	4386.0	4211.0	4035.9	3922.7	3814.6
32.5°	5276.6	5163.3	5050.1	4936.8	4823.6	4653.7	4483.8	4308.8	4138.9	4035.9	3927.8
35°	5523.7	5395.0	5266.3	5132.4	5003.7	4828.7	4658.8	4483.8	4308.8	4190.4	4077.1
37.5°	5734.7	5585.5	5436.2	5286.9	5137.6	4983.1	4823.6	4669.1	4509.5	4391.1	4277.9
40°	5971.5	5806.8	5642.1	5482.5	5317.8	5173.6	5029.5	4880.2	4736.1	4643.4	4550.7
42.5°	6177.5	5976.7	5781.1	5585.5	5384.7	5286.9	5194.2	5096.4	4998.6	4952.3	4900.8
45°	6321.6	6136.3	5945.8	5760.5	5575.2	5503.1	5431.0	5358.9	5286.9	5333.2	5379.5
47.5°	6383.4	6234.1	6089.9	5945.8	5796.5	5822.3	5848.0	5868.6	5894.3	5956.1	6023.0
50°	6440.0	6357.6	6270.1	6187.8	6100.2	6198.0	6290.7	6388.5	6486.3	6615.0	6743.7
52.5°	6553.3	6506.9	6465.7	6419.4	6373.1	6543.0	6712.8	6882.7	7052.6	7196.7	7340.9
55°	6893.0	6857.0	6820.9	6779.8	6743.7	6985.7	7222.5	7464.4	7706.4	7855.7	8005.0
57.5°	7361.5	7340.9	7315.1	7294.5	7268.8	7505.6	7737.3	7968.9	8205.7	8349.9	8499.2
60°	7716.7	7721.8	7721.8	7727.0	7727.0	7907.1	8087.3	8272.6	8452.8	8576.4	8705.1
62.5°	7907.1	7896.8	7886.6	7876.3	7866.0	8015.3	8164.5	8313.8	8463.1	8555.8	8648.4
65°	7701.2	7757.9	7814.5	7871.1	7927.7	7948.3	7963.8	7984.4	7999.8	8056.4	8113.1
67.5°	7011.4	7124.7	7232.8	7346.0	7454.1	7376.9	7304.8	7227.6	7150.4	7165.9	7176.1
70°	6244.4	6373.1	6506.9	6635.6	6764.3	6584.1	6404.0	6218.6	6038.5	5976.7	5914.9
72.5°	5266.3	5379.5	5497.9	5611.2	5724.4	5503.1	5286.9	5065.5	4844.2	4736.1	4627.9
75°	4025.6	4159.5	4298.5	4432.3	4566.2	4319.1	4066.8	3819.7	3567.5	3495.4	3428.5
77.5°	2934.3	3093.9	3253.5	3413.0	3572.6	3351.3	3129.9	2903.4	2682.0	2640.9	2599.7
80°	2136.4	2259.9	2378.3	2501.9	2620.3	2491.6	2362.9	2234.2	2105.5	2100.3	2095.2
82.5°	1441.4	1549.5	1652.5	1760.6	1863.5	1812.1	1765.7	1714.2	1662.8	1714.2	1770.9
85°	741.3	890.6	1045.0	1194.3	1343.6	1328.2	1317.9	1302.4	1287.0	1353.9	1415.7
87.5°	149.3	278.0	406.7	530.2	658.9	628.0	597.2	561.1	530.2	550.8	566.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671843  
 CATALOG NUMBER: CCP-SA-2E-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671843

CATALOG NUMBER: CCP-SA-2E-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5
2.5°	4061.7	4066.8	4066.8	4066.8	4066.8	4066.8	4056.5	4051.4	4041.1	4030.8	4015.3
5°	4365.4	4360.3	4339.7	4319.1	4293.3	4272.7	4257.3	4236.7	4221.3	4200.7	4169.8
7.5°	4555.9	4566.2	4530.1	4499.2	4463.2	4427.2	4391.1	4355.1	4319.1	4283.0	4211.0
10°	4499.2	4514.7	4494.1	4473.5	4447.8	4427.2	4386.0	4339.7	4298.5	4252.1	4164.6
12.5°	4339.7	4380.8	4370.6	4360.3	4350.0	4339.7	4313.9	4283.0	4257.3	4226.4	4128.6
15°	4056.5	4056.5	4061.7	4066.8	4066.8	4072.0	4077.1	4082.3	4087.4	4092.6	4035.9
17.5°	3886.7	3871.2	3871.2	3871.2	3871.2	3871.2	3891.8	3917.5	3938.1	3958.7	3943.3
20°	3763.1	3727.1	3721.9	3721.9	3716.8	3711.6	3747.7	3788.8	3824.9	3860.9	3881.5
22.5°	3680.7	3629.3	3624.1	3619.0	3613.8	3608.7	3655.0	3701.3	3747.7	3794.0	3866.1
25°	3660.1	3603.5	3608.7	3613.8	3613.8	3619.0	3655.0	3691.0	3727.1	3763.1	3886.7
27.5°	3665.3	3572.6	3577.8	3582.9	3582.9	3588.1	3644.7	3696.2	3752.8	3804.3	3958.7
30°	3701.3	3593.2	3582.9	3572.6	3562.3	3552.0	3629.3	3706.5	3783.7	3860.9	3979.3
32.5°	3824.9	3721.9	3696.2	3670.4	3644.7	3619.0	3711.6	3799.1	3891.8	3979.3	4077.1
35°	3958.7	3845.5	3835.2	3824.9	3809.4	3799.1	3881.5	3969.0	4051.4	4133.7	4221.3
37.5°	4159.5	4046.2	4035.9	4020.5	4010.2	3994.8	4087.4	4174.9	4267.6	4355.1	4432.3
40°	4458.1	4365.4	4360.3	4360.3	4355.1	4350.0	4422.0	4499.2	4571.3	4643.4	4694.9
42.5°	4854.5	4808.1	4823.6	4844.2	4859.6	4875.0	4931.7	4993.4	5050.1	5106.7	5091.3
45°	5425.9	5472.2	5477.3	5482.5	5487.6	5492.8	5508.2	5528.8	5544.3	5559.7	5497.9
47.5°	6084.8	6146.6	6177.5	6208.3	6234.1	6265.0	6244.4	6218.6	6198.0	6172.3	6017.9
50°	6867.3	6996.0	6990.8	6985.7	6975.4	6970.2	6929.0	6887.9	6841.5	6800.4	6573.8
52.5°	7485.0	7629.2	7654.9	7680.6	7706.4	7732.1	7654.9	7577.7	7495.3	7418.1	7135.0
55°	8149.1	8298.4	8303.5	8308.7	8308.7	8313.8	8205.7	8097.6	7984.4	7876.3	7582.8
57.5°	8643.3	8787.4	8772.0	8761.7	8746.2	8730.8	8602.1	8473.4	8344.7	8216.0	7922.6
60°	8828.6	8952.2	8921.3	8890.4	8854.4	8823.5	8725.7	8627.8	8524.9	8427.1	8143.9
62.5°	8741.1	8833.8	8787.4	8746.2	8699.9	8653.6	8530.0	8401.3	8277.8	8149.1	7943.2
65°	8164.5	8221.2	8159.4	8102.8	8046.1	7984.4	7881.4	7778.4	7670.3	7567.4	7428.4
67.5°	7191.6	7201.9	7196.7	7191.6	7186.4	7181.3	7032.0	6882.7	6728.3	6579.0	6568.7
70°	5858.3	5796.5	5806.8	5822.3	5832.5	5842.8	5729.6	5621.5	5508.2	5395.0	5446.5
72.5°	4519.8	4411.7	4437.5	4468.4	4494.1	4519.8	4427.2	4339.7	4247.0	4154.3	4226.4
75°	3356.4	3289.5	3315.2	3346.1	3371.9	3397.6	3361.6	3325.5	3284.3	3248.3	3315.2
77.5°	2558.5	2517.3	2522.5	2522.5	2527.6	2527.6	2532.8	2543.1	2548.2	2553.3	2625.4
80°	2084.9	2079.7	2074.6	2069.4	2059.2	2054.0	2105.5	2157.0	2208.4	2259.9	2296.0
82.5°	1822.3	1873.8	1842.9	1817.2	1786.3	1755.4	1801.8	1848.1	1894.4	1940.8	1925.3
85°	1482.6	1544.4	1487.7	1431.1	1369.3	1312.7	1353.9	1389.9	1431.1	1467.1	1446.6
87.5°	586.9	602.3	509.6	422.1	329.5	236.8	375.8	509.6	648.6	782.5	803.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671843  
 CATALOG NUMBER: CCP-SA-2E-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671843

CATALOG NUMBER: CCP-SA-2E-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5	3706.5
2.5°	3999.9	3979.3	3963.9	3958.7	3948.4	3943.3	3933.0	3922.7	3907.2	3896.9	3881.5
5°	4133.7	4102.9	4066.8	4015.3	3969.0	3917.5	3866.1	3819.7	3773.4	3721.9	3675.6
7.5°	4138.9	4066.8	3994.8	3927.8	3855.8	3788.8	3716.8	3655.0	3588.1	3521.2	3459.4
10°	4082.3	3994.8	3907.2	3819.7	3737.4	3649.8	3562.3	3490.3	3413.0	3335.8	3263.8
12.5°	4035.9	3938.1	3840.3	3737.4	3639.6	3536.6	3433.6	3361.6	3289.5	3217.4	3145.4
15°	3979.3	3917.5	3860.9	3768.2	3675.6	3582.9	3490.3	3392.5	3299.8	3202.0	3104.2
17.5°	3933.0	3917.5	3902.1	3840.3	3778.5	3711.6	3649.8	3552.0	3454.2	3351.3	3253.5
20°	3907.2	3927.8	3948.4	3917.5	3886.7	3850.6	3819.7	3747.7	3675.6	3598.4	3526.3
22.5°	3938.1	4015.3	4087.4	4092.6	4102.9	4108.0	4113.2	4046.2	3979.3	3907.2	3840.3
25°	4010.2	4133.7	4257.3	4324.2	4391.1	4463.2	4530.1	4489.0	4447.8	4406.6	4365.4
27.5°	4108.0	4262.4	4416.9	4514.7	4607.4	4705.2	4803.0	4797.8	4792.7	4782.4	4777.2
30°	4092.6	4211.0	4329.4	4447.8	4566.2	4684.6	4803.0	4864.7	4921.4	4983.1	5044.9
32.5°	4180.1	4277.9	4380.8	4504.4	4627.9	4756.6	4880.2	5008.9	5132.4	5261.1	5389.8
35°	4313.9	4401.4	4494.1	4627.9	4766.9	4900.8	5039.8	5194.2	5353.8	5513.4	5667.8
37.5°	4514.7	4591.9	4674.3	4787.5	4905.9	5019.2	5137.6	5364.1	5590.6	5822.3	6048.8
40°	4746.3	4797.8	4849.3	4957.4	5065.5	5173.6	5281.7	5564.9	5848.0	6131.1	6414.3
42.5°	5081.0	5065.5	5050.1	5137.6	5230.2	5317.8	5410.4	5667.8	5925.2	6182.6	6440.0
45°	5436.2	5374.4	5312.6	5353.8	5400.1	5441.3	5487.6	5750.2	6012.7	6280.4	6543.0
47.5°	5863.4	5709.0	5554.6	5518.5	5482.5	5441.3	5405.3	5688.4	5971.5	6259.8	6543.0
50°	6347.3	6115.7	5889.2	5796.5	5698.7	5606.0	5508.2	5739.9	5976.7	6213.5	6445.1
52.5°	6851.8	6563.5	6280.4	6136.3	5992.1	5842.8	5698.7	5894.3	6095.1	6295.9	6491.5
55°	7284.3	6990.8	6692.2	6522.4	6352.5	6182.6	6012.7	6208.3	6404.0	6599.6	6795.2
57.5°	7629.2	7335.7	7042.3	6882.7	6718.0	6558.4	6393.7	6579.0	6769.5	6959.9	7145.3
60°	7866.0	7582.8	7299.7	7145.3	6990.8	6836.4	6681.9	6903.3	7124.7	7351.2	7572.5
62.5°	7742.4	7536.5	7330.6	7263.7	7196.7	7124.7	7057.7	7268.8	7474.7	7685.8	7896.8
65°	7289.4	7150.4	7011.4	7078.3	7150.4	7217.3	7289.4	7428.4	7567.4	7711.5	7850.5
67.5°	6553.3	6543.0	6527.5	6676.8	6826.1	6980.5	7129.8	7222.5	7310.0	7402.7	7495.3
70°	5497.9	5554.6	5606.0	5863.4	6120.8	6378.2	6635.6	6671.7	6707.7	6743.7	6779.8
72.5°	4303.6	4375.7	4452.9	4792.7	5127.3	5467.0	5806.8	5786.2	5765.6	5739.9	5719.3
75°	3387.3	3454.2	3526.3	3840.3	4154.3	4468.4	4782.4	4694.9	4612.5	4525.0	4437.5
77.5°	2702.6	2774.7	2851.9	3145.4	3438.8	3737.4	4030.8	3819.7	3608.7	3397.6	3186.5
80°	2326.8	2362.9	2393.8	2594.5	2790.2	2990.9	3191.7	2975.5	2754.1	2532.8	2316.5
82.5°	1909.9	1889.3	1873.8	1992.2	2110.6	2229.0	2347.4	2141.5	1935.6	1724.5	1518.6
85°	1426.0	1405.4	1384.8	1446.6	1508.3	1575.3	1637.0	1400.2	1163.4	921.5	684.7
87.5°	828.8	849.4	870.0	936.9	1003.8	1075.9	1142.8	900.9	658.9	411.8	169.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671843  
 CATALOG NUMBER: CCP-SA-2E-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671843  
 CATALOG NUMBER: CCP-SA-2E-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
0°	3706.5	3706.5
2.5°	3850.6	3824.9
5°	3639.6	3603.5
7.5°	3407.9	3361.6
10°	3196.8	3135.1
12.5°	3063.0	2985.8
15°	3011.5	2918.8
17.5°	3165.9	3078.4
20°	3402.7	3284.3
22.5°	3691.0	3546.9
25°	4190.4	4015.3
27.5°	4597.1	4416.9
30°	4849.3	4653.7
32.5°	5127.3	4869.9
35°	5415.6	5168.5
37.5°	5765.6	5487.6
40°	6126.0	5837.7
42.5°	6249.5	6064.2
45°	6367.9	6192.9
47.5°	6393.7	6249.5
50°	6419.4	6398.8
52.5°	6491.5	6486.3
55°	6800.4	6805.5
57.5°	7181.3	7212.2
60°	7531.3	7495.3
62.5°	7711.5	7526.2
65°	7588.0	7330.6
67.5°	7217.3	6939.3
70°	6404.0	6028.2
72.5°	5389.8	5060.4
75°	4154.3	3876.4
77.5°	2954.9	2723.2
80°	2079.7	1848.1
82.5°	1333.3	1148.0
85°	602.3	525.1
87.5°	169.9	164.7
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P671843  
CATALOG NUMBER: CCP-SA-2E-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)