

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P671845

Luminaire Tested: **CCP-SA-1B-760-U-SLR**

Issue Date: 04/16/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P671845  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 04/16/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: CCP-SA-1B-760-U-SLR  
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @450mA w/ SLR distribution lens  
Light Source: (16) 5700K CCT, 70 CRI LEDs  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2931.6 lumens  
Efficiency: N/A  
Efficacy: 122.2 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B1 - U0 - G1

Input Watts (W): 24  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

REPORT NUMBER: P671845  
 CATALOG NUMBER: CCP-SA-1B-760-U-SLR

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 4.2 fc  
 Type IV - Short - N/A

REPORT NUMBER: P671845  
CATALOG NUMBER: CCP-SA-1B-760-U-SLR

### Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral    - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P671845  
 CATALOG NUMBER: CCP-SA-1B-760-U-SLR


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	603.2	0.0	603.2
	% Fixture	20.6	0.0	20.6
<b>Street Side</b>	Lumens	2328.4	0.0	2328.4
	% Fixture	79.4	0.0	79.4
<b>Total</b>	Lumens	2931.6	0.0	2931.6
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	72.7	2.5
10°-20°	153.6	5.2
20°-30°	224.7	7.7
30°-40°	316.6	10.8
40°-50°	435.0	14.8
50°-60°	592.9	20.2
60°-70°	649.0	22.1
70°-80°	374.8	12.8
80°-90°	112.3	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2931.6	100.0
0°-180°	2931.6	100.0



REPORT NUMBER: P671845


CATALOG NUMBER: CCP-SA-1B-760-U-SLR

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	301.1	10.3			
FM (30°-60°)	1069.9	36.5			
FH (60°-80°)	862.1	29.4			G1/1800
FVH (80°-90°)	95.4	3.3			G1/100
BL (0°-30°)	150.0	5.1	B1/500		
BM (30°-60°)	274.7	9.4	B1/1000		
BH (60°-80°)	161.6	5.5	B1/500		G1/500
BVH (80°-90°)	16.9	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B1-U0-G1**

Type IV Short





REPORT NUMBER: P671845

CATALOG NUMBER: CCP-SA-1B-760-U-SLR

**CANDELA DISTRIBUTION (FULL):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2
2.5°	966.1	960.9	957.0	953.1	947.9	944.0	938.8	933.6	927.1	921.9	915.4
5°	910.2	894.6	879.0	869.9	859.5	850.4	840.0	828.3	816.6	803.6	791.9
7.5°	849.1	829.6	810.1	794.5	777.6	762.0	745.1	730.8	716.5	702.1	687.8
10°	791.9	773.7	755.5	736.0	715.2	695.6	674.8	655.3	635.8	616.3	596.8
12.5°	754.2	732.1	711.3	689.1	668.3	646.2	624.1	605.9	587.7	568.2	550.0
15°	737.3	716.5	696.9	674.8	652.7	630.6	608.5	587.7	568.2	547.4	526.6
17.5°	777.6	747.7	717.8	689.1	660.5	631.9	603.3	577.3	551.3	525.3	499.3
20°	829.6	791.9	755.5	720.4	683.9	648.8	612.4	576.0	539.6	503.2	466.8
22.5°	895.9	853.0	811.4	765.9	719.1	673.5	626.7	581.2	535.7	488.9	443.4
25°	1014.2	963.5	912.8	847.8	781.5	716.5	650.1	590.3	531.8	472.0	412.2
27.5°	1115.6	1046.7	979.1	901.1	823.1	745.1	667.0	598.1	530.5	461.6	392.7
30°	1175.4	1107.8	1040.2	945.3	851.7	756.8	661.8	585.1	509.7	433.0	356.3
32.5°	1230.1	1154.6	1079.2	975.2	869.9	765.9	660.5	576.0	492.8	408.3	323.8
35°	1305.5	1222.3	1140.3	1019.4	898.5	777.6	656.6	569.5	481.1	394.0	305.6
37.5°	1386.1	1283.4	1181.9	1048.0	914.1	780.2	646.2	560.4	474.6	388.8	303.0
40°	1474.5	1349.7	1226.2	1077.9	931.0	782.8	634.5	548.7	462.9	375.8	290.0
42.5°	1531.7	1396.5	1261.3	1101.3	942.7	782.8	622.8	538.3	453.8	368.0	283.5
45°	1564.2	1432.9	1302.9	1129.9	957.0	784.1	611.1	527.9	444.7	360.2	277.0
47.5°	1578.5	1456.3	1334.1	1152.0	971.3	789.3	607.2	522.7	436.9	352.4	266.6
50°	1616.2	1508.3	1400.4	1205.4	1011.6	816.6	621.5	530.5	440.8	349.8	258.8
52.5°	1638.3	1546.0	1453.7	1253.5	1053.2	853.0	652.7	551.3	449.9	348.5	247.1
55°	1719.0	1630.5	1542.1	1328.9	1114.3	901.1	686.5	574.7	462.9	349.8	238.0
57.5°	1821.7	1728.1	1635.7	1405.6	1175.4	945.3	715.2	595.5	474.6	355.0	234.0
60°	1893.2	1802.2	1712.5	1468.0	1222.3	977.8	732.1	607.2	482.4	356.3	231.4
62.5°	1901.0	1784.0	1668.3	1430.3	1192.4	953.1	715.2	594.2	473.3	351.1	230.1
65°	1851.6	1715.1	1578.5	1351.0	1123.4	895.9	668.3	557.8	447.3	335.5	224.9
67.5°	1752.8	1592.8	1432.9	1224.9	1016.8	808.8	600.7	505.8	412.2	317.3	222.3
70°	1522.6	1382.2	1243.1	1062.3	882.9	702.1	521.4	443.4	366.7	288.7	210.6
72.5°	1278.2	1146.8	1016.8	869.9	724.3	577.3	430.4	371.9	313.4	253.6	195.0
75°	979.1	880.3	782.8	673.5	564.3	453.8	344.6	301.7	258.8	215.8	172.9
77.5°	687.8	634.5	582.5	500.6	418.7	336.8	254.9	226.2	197.6	169.0	140.4
80°	466.8	436.9	408.3	349.8	291.3	231.4	172.9	154.7	135.2	117.0	97.5
82.5°	290.0	288.7	286.1	245.8	205.4	165.1	124.8	109.2	94.9	79.3	63.7
85°	132.6	154.7	175.5	153.4	131.3	109.2	87.1	76.7	66.3	54.6	44.2
87.5°	41.6	50.7	58.5	55.9	52.0	49.4	45.5	39.0	32.5	26.0	19.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671845  
 CATALOG NUMBER: CCP-SA-1B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671845  
 CATALOG NUMBER: CCP-SA-1B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2
2.5°	910.2	906.3	901.1	895.9	889.4	884.2	877.7	871.2	869.9	867.3	866.0
5°	784.1	776.3	767.2	759.4	751.6	742.5	734.7	725.6	719.1	711.3	704.7
7.5°	673.5	660.5	646.2	631.9	618.9	605.9	591.6	578.6	572.1	565.6	559.1
10°	585.1	572.1	560.4	547.4	538.3	530.5	521.4	512.3	504.5	496.7	488.9
12.5°	540.9	531.8	522.7	513.6	503.2	494.1	483.7	473.3	464.2	456.4	447.3
15°	513.6	500.6	486.3	473.3	459.0	446.0	431.7	417.4	407.0	397.9	387.5
17.5°	481.1	461.6	443.4	423.9	408.3	392.7	375.8	360.2	348.5	335.5	323.8
20°	444.7	422.6	399.2	377.1	358.9	342.0	323.8	305.6	292.6	278.3	265.3
22.5°	413.5	384.9	355.0	325.1	305.6	286.1	265.3	245.8	234.0	221.0	209.3
25°	379.7	348.5	316.0	283.5	264.0	243.2	223.6	202.8	193.7	185.9	176.8
27.5°	361.5	330.3	297.8	266.6	248.4	228.8	210.6	191.1	184.6	176.8	170.3
30°	325.1	295.2	264.0	232.7	219.7	208.0	195.0	182.0	179.4	178.1	175.5
32.5°	292.6	261.4	230.1	198.9	187.2	175.5	163.8	152.1	150.8	148.2	146.9
35°	275.7	245.8	214.5	184.6	174.2	162.5	152.1	140.4	137.8	133.9	131.3
37.5°	271.8	240.6	208.0	176.8	166.4	156.0	144.3	133.9	131.3	128.7	126.1
40°	261.4	231.4	202.8	172.9	162.5	152.1	140.4	130.0	127.4	124.8	122.2
42.5°	253.6	224.9	195.0	165.1	156.0	146.9	136.5	127.4	124.8	122.2	118.3
45°	247.1	217.1	185.9	156.0	149.5	143.0	135.2	128.7	126.1	122.2	119.6
47.5°	236.7	208.0	178.1	148.2	141.7	136.5	130.0	123.5	120.9	118.3	115.7
50°	228.8	198.9	169.0	139.1	133.9	128.7	123.5	118.3	118.3	119.6	119.6
52.5°	218.4	189.8	161.2	132.6	127.4	122.2	117.0	111.8	113.1	114.4	115.7
55°	209.3	182.0	153.4	124.8	119.6	114.4	107.9	102.7	104.0	105.3	106.6
57.5°	205.4	176.8	148.2	119.6	114.4	107.9	102.7	96.2	96.2	96.2	96.2
60°	202.8	172.9	144.3	114.4	107.9	102.7	96.2	89.7	88.4	88.4	87.1
62.5°	201.5	171.6	143.0	113.1	105.3	98.8	91.0	83.2	81.9	80.6	79.3
65°	196.3	169.0	140.4	111.8	102.7	94.9	85.8	76.7	75.4	75.4	74.1
67.5°	195.0	166.4	139.1	110.5	101.4	91.0	81.9	71.5	70.2	68.9	67.6
70°	184.6	159.9	133.9	107.9	97.5	88.4	78.0	67.6	66.3	63.7	62.4
72.5°	171.6	149.5	126.1	102.7	92.3	81.9	71.5	61.1	59.8	58.5	55.9
75°	152.1	131.3	110.5	89.7	80.6	72.8	63.7	54.6	53.3	52.0	49.4
77.5°	124.8	107.9	92.3	75.4	68.9	62.4	55.9	49.4	48.1	46.8	44.2
80°	88.4	78.0	68.9	58.5	54.6	49.4	45.5	40.3	40.3	39.0	39.0
82.5°	58.5	53.3	48.1	42.9	40.3	37.7	35.1	32.5	32.5	31.2	31.2
85°	41.6	39.0	35.1	32.5	31.2	28.6	27.3	24.7	24.7	24.7	24.7
87.5°	19.5	19.5	18.2	18.2	16.9	16.9	15.6	14.3	14.3	14.3	14.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671845  
 CATALOG NUMBER: CCP-SA-1B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671845  
 CATALOG NUMBER: CCP-SA-1B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2
2.5°	863.4	859.5	855.6	850.4	846.5	841.3	834.8	829.6	823.1	823.1	821.8
5°	696.9	693.0	689.1	683.9	680.0	674.8	670.9	665.7	660.5	660.5	659.2
7.5°	552.6	544.8	537.0	527.9	520.1	514.9	509.7	503.2	498.0	494.1	490.2
10°	481.1	473.3	464.2	456.4	447.3	440.8	434.3	426.5	420.0	414.8	409.6
12.5°	438.2	429.1	420.0	410.9	401.8	392.7	384.9	375.8	366.7	360.2	353.7
15°	377.1	368.0	358.9	349.8	340.7	330.3	319.9	308.2	297.8	292.6	288.7
17.5°	310.8	301.7	291.3	282.2	271.8	264.0	256.2	248.4	240.6	235.3	231.4
20°	251.0	240.6	230.1	219.7	209.3	204.1	198.9	193.7	188.5	184.6	182.0
22.5°	196.3	189.8	184.6	178.1	171.6	167.7	165.1	161.2	157.3	157.3	157.3
25°	167.7	163.8	161.2	157.3	153.4	152.1	150.8	148.2	146.9	145.6	145.6
27.5°	162.5	158.6	154.7	150.8	146.9	145.6	144.3	141.7	140.4	140.4	140.4
30°	172.9	171.6	170.3	169.0	167.7	165.1	161.2	158.6	154.7	152.1	149.5
32.5°	144.3	143.0	143.0	141.7	140.4	143.0	144.3	146.9	148.2	149.5	150.8
35°	127.4	124.8	122.2	119.6	117.0	115.7	114.4	113.1	111.8	111.8	110.5
37.5°	123.5	120.9	118.3	115.7	113.1	111.8	110.5	109.2	107.9	107.9	106.6
40°	119.6	117.0	115.7	113.1	110.5	109.2	107.9	105.3	104.0	102.7	102.7
42.5°	115.7	114.4	111.8	110.5	107.9	106.6	105.3	102.7	101.4	100.1	98.8
45°	115.7	113.1	110.5	107.9	105.3	104.0	101.4	100.1	97.5	97.5	96.2
47.5°	113.1	110.5	107.9	105.3	102.7	101.4	98.8	97.5	94.9	93.6	92.3
50°	119.6	115.7	110.5	106.6	101.4	100.1	97.5	96.2	93.6	92.3	91.0
52.5°	117.0	113.1	107.9	104.0	98.8	96.2	94.9	92.3	89.7	88.4	87.1
55°	107.9	104.0	101.4	97.5	93.6	91.0	88.4	85.8	83.2	81.9	81.9
57.5°	96.2	94.9	93.6	92.3	91.0	88.4	85.8	81.9	79.3	78.0	76.7
60°	85.8	87.1	88.4	89.7	91.0	87.1	83.2	79.3	75.4	74.1	72.8
62.5°	78.0	80.6	83.2	84.5	87.1	83.2	79.3	75.4	71.5	70.2	68.9
65°	72.8	74.1	74.1	75.4	75.4	72.8	71.5	68.9	66.3	65.0	65.0
67.5°	66.3	66.3	66.3	65.0	65.0	63.7	63.7	62.4	61.1	59.8	59.8
70°	59.8	59.8	59.8	58.5	58.5	57.2	57.2	55.9	54.6	54.6	53.3
72.5°	54.6	54.6	53.3	53.3	52.0	52.0	52.0	50.7	50.7	49.4	49.4
75°	48.1	48.1	46.8	46.8	45.5	45.5	45.5	44.2	44.2	44.2	42.9
77.5°	42.9	42.9	41.6	41.6	40.3	40.3	40.3	39.0	39.0	37.7	37.7
80°	37.7	37.7	36.4	36.4	35.1	35.1	33.8	33.8	32.5	32.5	31.2
82.5°	29.9	29.9	29.9	29.9	29.9	28.6	28.6	27.3	26.0	26.0	24.7
85°	24.7	24.7	24.7	23.4	23.4	23.4	22.1	22.1	20.8	19.5	19.5
87.5°	14.3	14.3	14.3	13.0	13.0	13.0	13.0	13.0	13.0	13.0	11.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671845  
 CATALOG NUMBER: CCP-SA-1B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671845  
 CATALOG NUMBER: CCP-SA-1B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2
2.5°	821.8	820.5	815.3	810.1	815.3	820.5	820.5	820.5	819.2	819.2	819.2
5°	659.2	657.9	655.3	652.7	652.7	651.4	654.0	656.6	659.2	661.8	664.4
7.5°	485.0	481.1	477.2	473.3	475.9	477.2	481.1	483.7	487.6	490.2	496.7
10°	404.4	399.2	395.3	391.4	388.8	386.2	383.6	382.3	379.7	377.1	379.7
12.5°	345.9	339.4	332.9	325.1	323.8	322.5	319.9	317.3	314.7	312.1	310.8
15°	283.5	278.3	275.7	271.8	266.6	261.4	258.8	257.5	254.9	252.3	251.0
17.5°	226.2	221.0	217.1	213.2	211.9	209.3	209.3	209.3	209.3	209.3	209.3
20°	178.1	174.2	174.2	172.9	172.9	171.6	172.9	174.2	174.2	175.5	176.8
22.5°	156.0	156.0	154.7	153.4	154.7	154.7	156.0	157.3	158.6	159.9	161.2
25°	144.3	143.0	144.3	145.6	145.6	145.6	146.9	146.9	148.2	148.2	148.2
27.5°	139.1	139.1	140.4	140.4	141.7	141.7	141.7	140.4	140.4	139.1	139.1
30°	146.9	144.3	144.3	144.3	143.0	141.7	140.4	140.4	139.1	137.8	136.5
32.5°	152.1	153.4	152.1	149.5	148.2	145.6	144.3	141.7	140.4	137.8	135.2
35°	110.5	109.2	111.8	113.1	114.4	115.7	117.0	118.3	118.3	119.6	119.6
37.5°	106.6	105.3	105.3	104.0	104.0	104.0	104.0	104.0	102.7	102.7	104.0
40°	101.4	100.1	100.1	98.8	98.8	97.5	97.5	97.5	97.5	97.5	97.5
42.5°	97.5	96.2	96.2	96.2	96.2	94.9	94.9	93.6	93.6	92.3	92.3
45°	96.2	94.9	93.6	92.3	92.3	91.0	91.0	91.0	89.7	89.7	89.7
47.5°	91.0	89.7	89.7	88.4	88.4	87.1	87.1	87.1	85.8	85.8	85.8
50°	88.4	87.1	87.1	85.8	85.8	84.5	84.5	84.5	83.2	83.2	83.2
52.5°	84.5	83.2	83.2	83.2	81.9	80.6	80.6	80.6	79.3	79.3	79.3
55°	80.6	79.3	79.3	79.3	78.0	76.7	76.7	76.7	75.4	75.4	75.4
57.5°	75.4	74.1	74.1	72.8	72.8	72.8	72.8	72.8	71.5	71.5	71.5
60°	71.5	70.2	70.2	68.9	68.9	67.6	67.6	67.6	67.6	67.6	67.6
62.5°	67.6	66.3	65.0	63.7	65.0	65.0	65.0	65.0	63.7	63.7	63.7
65°	63.7	62.4	61.1	59.8	59.8	59.8	59.8	59.8	59.8	59.8	59.8
67.5°	58.5	57.2	55.9	54.6	55.9	55.9	55.9	55.9	55.9	55.9	55.9
70°	53.3	52.0	52.0	50.7	50.7	49.4	49.4	50.7	50.7	50.7	50.7
72.5°	48.1	46.8	46.8	45.5	45.5	45.5	45.5	45.5	45.5	45.5	45.5
75°	42.9	41.6	41.6	40.3	40.3	40.3	40.3	40.3	40.3	40.3	40.3
77.5°	36.4	35.1	35.1	35.1	35.1	35.1	35.1	36.4	36.4	36.4	36.4
80°	31.2	29.9	29.9	29.9	29.9	29.9	29.9	29.9	29.9	29.9	29.9
82.5°	24.7	23.4	23.4	23.4	23.4	23.4	23.4	23.4	23.4	23.4	23.4
85°	18.2	16.9	16.9	16.9	18.2	18.2	18.2	18.2	18.2	18.2	18.2
87.5°	11.7	10.4	10.4	10.4	11.7	11.7	11.7	11.7	10.4	10.4	10.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671845  
 CATALOG NUMBER: CCP-SA-1B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671845  
 CATALOG NUMBER: CCP-SA-1B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2
2.5°	819.2	819.2	819.2	817.9	816.6	815.3	814.0	817.9	820.5	824.4	827.0
5°	665.7	668.3	669.6	673.5	677.4	681.3	685.2	687.8	690.4	691.7	694.3
7.5°	501.9	508.4	513.6	518.8	524.0	527.9	533.1	537.0	540.9	544.8	548.7
10°	381.0	383.6	384.9	390.1	394.0	399.2	403.1	407.0	410.9	413.5	417.4
12.5°	309.5	306.9	305.6	305.6	305.6	305.6	305.6	308.2	310.8	313.4	316.0
15°	249.7	248.4	247.1	245.8	244.5	241.9	240.6	243.2	245.8	248.4	251.0
17.5°	209.3	209.3	209.3	208.0	206.7	205.4	204.1	205.4	206.7	206.7	208.0
20°	179.4	180.7	182.0	183.3	183.3	184.6	184.6	185.9	187.2	187.2	188.5
22.5°	161.2	162.5	162.5	162.5	163.8	163.8	163.8	165.1	166.4	167.7	169.0
25°	146.9	146.9	145.6	145.6	146.9	146.9	146.9	146.9	148.2	148.2	148.2
27.5°	139.1	137.8	137.8	137.8	137.8	136.5	136.5	136.5	136.5	136.5	136.5
30°	135.2	133.9	132.6	131.3	131.3	130.0	128.7	128.7	128.7	128.7	128.7
32.5°	133.9	131.3	128.7	127.4	127.4	126.1	124.8	123.5	123.5	122.2	120.9
35°	119.6	118.3	118.3	117.0	115.7	114.4	113.1	113.1	113.1	111.8	111.8
37.5°	104.0	105.3	105.3	105.3	106.6	106.6	106.6	106.6	107.9	107.9	107.9
40°	97.5	97.5	97.5	98.8	100.1	100.1	101.4	101.4	102.7	102.7	102.7
42.5°	92.3	91.0	91.0	92.3	92.3	93.6	93.6	94.9	96.2	96.2	97.5
45°	89.7	88.4	88.4	88.4	88.4	87.1	87.1	88.4	89.7	91.0	92.3
47.5°	84.5	84.5	83.2	83.2	83.2	83.2	83.2	83.2	84.5	84.5	84.5
50°	81.9	81.9	80.6	80.6	80.6	80.6	80.6	80.6	80.6	80.6	80.6
52.5°	79.3	78.0	78.0	78.0	78.0	76.7	76.7	76.7	76.7	76.7	76.7
55°	75.4	74.1	74.1	74.1	74.1	74.1	74.1	74.1	75.4	75.4	75.4
57.5°	71.5	70.2	70.2	70.2	71.5	71.5	71.5	71.5	72.8	72.8	72.8
60°	67.6	67.6	67.6	67.6	67.6	67.6	67.6	68.9	68.9	70.2	70.2
62.5°	63.7	63.7	63.7	63.7	65.0	65.0	65.0	65.0	66.3	66.3	66.3
65°	59.8	59.8	59.8	59.8	61.1	61.1	61.1	61.1	61.1	61.1	61.1
67.5°	55.9	55.9	55.9	55.9	55.9	55.9	55.9	57.2	57.2	58.5	58.5
70°	50.7	49.4	49.4	50.7	50.7	52.0	52.0	53.3	53.3	54.6	54.6
72.5°	45.5	45.5	45.5	45.5	45.5	45.5	45.5	46.8	48.1	48.1	49.4
75°	40.3	40.3	40.3	40.3	41.6	41.6	41.6	42.9	42.9	44.2	44.2
77.5°	36.4	35.1	35.1	35.1	36.4	36.4	36.4	37.7	37.7	39.0	39.0
80°	29.9	29.9	29.9	29.9	31.2	31.2	31.2	31.2	32.5	32.5	32.5
82.5°	24.7	24.7	24.7	24.7	24.7	24.7	24.7	24.7	26.0	26.0	26.0
85°	18.2	18.2	18.2	18.2	19.5	19.5	19.5	19.5	19.5	19.5	19.5
87.5°	11.7	11.7	11.7	11.7	11.7	11.7	11.7	11.7	13.0	13.0	13.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671845  
 CATALOG NUMBER: CCP-SA-1B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671845  
 CATALOG NUMBER: CCP-SA-1B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2
2.5°	827.0	827.0	827.0	827.0	829.6	830.9	833.5	834.8	833.5	832.2	829.6
5°	695.6	696.9	696.9	698.2	698.2	698.2	698.2	698.2	700.8	703.4	706.0
7.5°	550.0	551.3	552.6	553.9	553.9	553.9	552.6	552.6	553.9	553.9	555.2
10°	421.3	426.5	430.4	434.3	431.7	427.8	425.2	421.3	421.3	421.3	420.0
12.5°	318.6	319.9	322.5	323.8	322.5	322.5	321.2	319.9	321.2	323.8	325.1
15°	252.3	252.3	253.6	253.6	254.9	256.2	256.2	257.5	260.1	261.4	264.0
17.5°	209.3	210.6	210.6	211.9	211.9	213.2	213.2	213.2	215.8	218.4	222.3
20°	188.5	188.5	188.5	188.5	188.5	187.2	187.2	185.9	187.2	189.8	191.1
22.5°	169.0	170.3	170.3	170.3	169.0	167.7	165.1	163.8	163.8	165.1	165.1
25°	148.2	146.9	146.9	145.6	145.6	146.9	146.9	146.9	148.2	148.2	149.5
27.5°	136.5	135.2	135.2	133.9	133.9	135.2	135.2	135.2	135.2	135.2	135.2
30°	127.4	127.4	126.1	124.8	126.1	126.1	127.4	127.4	128.7	128.7	130.0
32.5°	120.9	119.6	119.6	118.3	119.6	119.6	120.9	120.9	122.2	123.5	123.5
35°	111.8	111.8	111.8	111.8	111.8	111.8	110.5	110.5	110.5	110.5	110.5
37.5°	106.6	106.6	105.3	104.0	104.0	104.0	104.0	104.0	102.7	101.4	100.1
40°	102.7	101.4	101.4	100.1	98.8	98.8	97.5	96.2	96.2	94.9	94.9
42.5°	97.5	96.2	96.2	94.9	93.6	93.6	92.3	91.0	91.0	91.0	89.7
45°	91.0	91.0	89.7	88.4	88.4	88.4	87.1	87.1	87.1	87.1	85.8
47.5°	84.5	84.5	83.2	83.2	83.2	83.2	81.9	81.9	81.9	81.9	81.9
50°	80.6	80.6	80.6	80.6	80.6	80.6	79.3	79.3	79.3	79.3	79.3
52.5°	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7
55°	75.4	75.4	75.4	75.4	75.4	75.4	74.1	74.1	74.1	75.4	75.4
57.5°	72.8	72.8	71.5	71.5	71.5	71.5	71.5	71.5	71.5	71.5	71.5
60°	70.2	70.2	70.2	70.2	70.2	70.2	70.2	70.2	70.2	70.2	70.2
62.5°	66.3	66.3	66.3	66.3	66.3	67.6	67.6	67.6	67.6	67.6	66.3
65°	61.1	62.4	62.4	62.4	62.4	62.4	62.4	62.4	62.4	62.4	62.4
67.5°	58.5	58.5	58.5	58.5	58.5	58.5	58.5	58.5	58.5	58.5	58.5
70°	54.6	54.6	53.3	53.3	53.3	54.6	54.6	54.6	54.6	54.6	54.6
72.5°	49.4	49.4	49.4	49.4	49.4	49.4	49.4	49.4	49.4	50.7	50.7
75°	44.2	44.2	44.2	44.2	44.2	44.2	44.2	44.2	44.2	44.2	44.2
77.5°	39.0	39.0	37.7	37.7	37.7	39.0	39.0	39.0	39.0	40.3	40.3
80°	32.5	32.5	32.5	32.5	32.5	32.5	32.5	32.5	32.5	33.8	33.8
82.5°	26.0	26.0	26.0	26.0	26.0	26.0	26.0	26.0	26.0	27.3	27.3
85°	19.5	20.8	20.8	20.8	20.8	20.8	20.8	20.8	20.8	22.1	22.1
87.5°	13.0	13.0	13.0	13.0	13.0	13.0	11.7	11.7	11.7	11.7	10.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671845  
 CATALOG NUMBER: CCP-SA-1B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671845  
 CATALOG NUMBER: CCP-SA-1B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2
2.5°	828.3	829.6	830.9	830.9	832.2	833.5	833.5	838.7	843.9	846.5	849.1
5°	708.6	707.3	707.3	706.0	704.7	708.6	712.6	720.4	728.2	729.5	732.1
7.5°	555.2	556.5	557.8	557.8	559.1	555.2	550.0	551.3	552.6	559.1	564.3
10°	420.0	421.3	422.6	422.6	423.9	422.6	420.0	423.9	427.8	433.0	439.5
12.5°	326.4	330.3	334.2	336.8	340.7	343.3	344.6	349.8	353.7	360.2	366.7
15°	266.6	269.2	271.8	274.4	277.0	279.6	282.2	287.4	292.6	300.4	308.2
17.5°	224.9	224.9	226.2	226.2	226.2	228.8	231.4	234.0	235.3	243.2	251.0
20°	192.4	191.1	189.8	188.5	187.2	189.8	191.1	192.4	193.7	198.9	202.8
22.5°	165.1	165.1	166.4	166.4	166.4	165.1	162.5	163.8	163.8	166.4	170.3
25°	149.5	149.5	149.5	148.2	148.2	149.5	150.8	150.8	149.5	150.8	152.1
27.5°	135.2	136.5	136.5	137.8	137.8	139.1	139.1	139.1	139.1	140.4	141.7
30°	130.0	130.0	131.3	131.3	131.3	132.6	133.9	133.9	133.9	135.2	137.8
32.5°	124.8	126.1	127.4	128.7	130.0	131.3	131.3	132.6	132.6	133.9	135.2
35°	110.5	109.2	109.2	107.9	106.6	106.6	106.6	106.6	105.3	106.6	106.6
37.5°	98.8	98.8	98.8	97.5	97.5	98.8	98.8	98.8	98.8	100.1	100.1
40°	93.6	93.6	93.6	93.6	93.6	93.6	93.6	94.9	94.9	96.2	97.5
42.5°	89.7	89.7	89.7	89.7	89.7	91.0	91.0	91.0	91.0	92.3	92.3
45°	85.8	85.8	85.8	85.8	85.8	85.8	85.8	87.1	87.1	88.4	89.7
47.5°	81.9	81.9	81.9	81.9	81.9	83.2	84.5	84.5	84.5	85.8	85.8
50°	79.3	79.3	79.3	79.3	79.3	80.6	80.6	81.9	81.9	83.2	84.5
52.5°	76.7	76.7	76.7	76.7	76.7	78.0	78.0	79.3	79.3	80.6	81.9
55°	75.4	75.4	75.4	74.1	74.1	75.4	75.4	76.7	76.7	78.0	78.0
57.5°	71.5	71.5	71.5	71.5	71.5	71.5	71.5	72.8	72.8	74.1	75.4
60°	70.2	70.2	68.9	68.9	67.6	68.9	68.9	70.2	70.2	71.5	71.5
62.5°	66.3	66.3	66.3	65.0	65.0	66.3	66.3	66.3	66.3	67.6	68.9
65°	62.4	62.4	62.4	61.1	61.1	62.4	62.4	62.4	62.4	63.7	65.0
67.5°	58.5	58.5	58.5	57.2	57.2	57.2	57.2	58.5	58.5	59.8	61.1
70°	54.6	54.6	54.6	53.3	53.3	53.3	52.0	53.3	54.6	55.9	55.9
72.5°	50.7	50.7	50.7	49.4	49.4	49.4	48.1	49.4	49.4	50.7	50.7
75°	44.2	44.2	44.2	44.2	44.2	44.2	42.9	42.9	42.9	44.2	44.2
77.5°	40.3	40.3	40.3	39.0	39.0	39.0	37.7	37.7	37.7	39.0	39.0
80°	33.8	33.8	33.8	32.5	32.5	32.5	31.2	31.2	31.2	32.5	32.5
82.5°	27.3	27.3	27.3	26.0	26.0	26.0	24.7	24.7	24.7	26.0	26.0
85°	22.1	22.1	22.1	22.1	22.1	22.1	20.8	20.8	20.8	22.1	23.4
87.5°	10.4	10.4	11.7	11.7	11.7	11.7	10.4	10.4	9.1	9.1	10.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671845  
 CATALOG NUMBER: CCP-SA-1B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671845  
 CATALOG NUMBER: CCP-SA-1B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2
2.5°	851.7	854.3	860.8	866.0	872.5	877.7	881.6	886.8	890.7	894.6	897.2
5°	733.4	734.7	741.2	747.7	752.9	759.4	768.5	777.6	786.7	795.8	802.3
7.5°	570.8	576.0	583.8	592.9	600.7	608.5	617.6	628.0	637.1	646.2	655.3
10°	444.7	449.9	457.7	465.5	472.0	479.8	490.2	500.6	511.0	521.4	531.8
12.5°	373.2	379.7	388.8	397.9	405.7	414.8	427.8	439.5	452.5	464.2	477.2
15°	314.7	322.5	334.2	347.2	358.9	370.6	383.6	396.6	408.3	421.3	434.3
17.5°	258.8	266.6	277.0	288.7	299.1	309.5	325.1	339.4	355.0	369.3	383.6
20°	208.0	211.9	222.3	232.7	243.2	253.6	265.3	277.0	288.7	300.4	318.6
22.5°	172.9	175.5	180.7	184.6	189.8	193.7	205.4	217.1	227.5	239.3	256.2
25°	152.1	153.4	157.3	159.9	163.8	166.4	174.2	180.7	188.5	195.0	210.6
27.5°	141.7	143.0	144.3	145.6	146.9	148.2	153.4	158.6	162.5	167.7	182.0
30°	139.1	140.4	144.3	146.9	150.8	153.4	156.0	158.6	161.2	163.8	172.9
32.5°	136.5	137.8	137.8	136.5	136.5	135.2	137.8	139.1	141.7	143.0	150.8
35°	107.9	107.9	109.2	110.5	111.8	113.1	117.0	119.6	123.5	126.1	132.6
37.5°	101.4	101.4	102.7	105.3	106.6	107.9	110.5	113.1	115.7	118.3	124.8
40°	97.5	98.8	100.1	101.4	102.7	104.0	106.6	107.9	110.5	111.8	117.0
42.5°	93.6	93.6	94.9	97.5	98.8	100.1	102.7	104.0	106.6	107.9	113.1
45°	91.0	92.3	93.6	94.9	94.9	96.2	98.8	101.4	102.7	105.3	110.5
47.5°	87.1	87.1	89.7	91.0	93.6	94.9	97.5	98.8	101.4	102.7	107.9
50°	84.5	85.8	88.4	89.7	92.3	93.6	97.5	100.1	104.0	106.6	109.2
52.5°	81.9	83.2	85.8	87.1	89.7	91.0	96.2	101.4	105.3	110.5	110.5
55°	79.3	79.3	81.9	85.8	88.4	91.0	93.6	97.5	100.1	102.7	102.7
57.5°	75.4	76.7	79.3	83.2	85.8	88.4	91.0	93.6	94.9	97.5	96.2
60°	72.8	72.8	76.7	80.6	84.5	88.4	88.4	88.4	87.1	87.1	87.1
62.5°	68.9	70.2	75.4	81.9	87.1	92.3	88.4	84.5	80.6	76.7	78.0
65°	66.3	67.6	70.2	74.1	76.7	79.3	76.7	75.4	72.8	70.2	71.5
67.5°	61.1	62.4	63.7	63.7	65.0	65.0	65.0	65.0	65.0	65.0	66.3
70°	57.2	57.2	57.2	58.5	58.5	58.5	58.5	58.5	58.5	58.5	59.8
72.5°	52.0	52.0	52.0	52.0	52.0	52.0	52.0	52.0	52.0	52.0	53.3
75°	45.5	45.5	45.5	45.5	45.5	45.5	45.5	45.5	45.5	45.5	46.8
77.5°	40.3	40.3	40.3	40.3	40.3	40.3	40.3	40.3	39.0	39.0	40.3
80°	33.8	33.8	33.8	33.8	32.5	32.5	32.5	32.5	32.5	32.5	33.8
82.5°	27.3	27.3	27.3	27.3	26.0	26.0	26.0	26.0	24.7	24.7	26.0
85°	24.7	26.0	26.0	27.3	27.3	27.3	26.0	24.7	23.4	22.1	22.1
87.5°	10.4	10.4	10.4	10.4	9.1	9.1	9.1	9.1	9.1	9.1	9.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671845  
 CATALOG NUMBER: CCP-SA-1B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671845  
 CATALOG NUMBER: CCP-SA-1B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2
2.5°	901.1	903.7	906.3	910.2	915.4	919.3	923.2	931.0	940.1	947.9	955.7
5°	808.8	815.3	821.8	829.6	837.4	843.9	851.7	867.3	882.9	897.2	912.8
7.5°	663.1	672.2	680.0	693.0	704.7	717.8	729.5	749.0	767.2	786.7	804.9
10°	542.2	552.6	563.0	579.9	598.1	615.0	631.9	647.5	664.4	680.0	695.6
12.5°	490.2	501.9	514.9	525.3	537.0	547.4	557.8	576.0	594.2	612.4	630.6
15°	447.3	460.3	473.3	486.3	498.0	511.0	522.7	538.3	555.2	570.8	586.4
17.5°	397.9	410.9	425.2	439.5	453.8	468.1	482.4	504.5	526.6	547.4	569.5
20°	335.5	353.7	370.6	390.1	409.6	429.1	448.6	472.0	495.4	517.5	540.9
22.5°	273.1	290.0	306.9	330.3	353.7	375.8	399.2	430.4	460.3	491.5	521.4
25°	227.5	243.2	258.8	284.8	309.5	335.5	360.2	397.9	434.3	472.0	508.4
27.5°	196.3	210.6	224.9	252.3	279.6	305.6	332.9	374.5	414.8	456.4	496.7
30°	182.0	191.1	200.2	226.2	252.3	277.0	303.0	343.3	383.6	423.9	464.2
32.5°	158.6	166.4	174.2	197.6	221.0	243.2	266.6	308.2	348.5	390.1	430.4
35°	140.4	146.9	153.4	175.5	196.3	218.4	239.3	280.9	322.5	364.1	405.7
37.5°	130.0	136.5	141.7	161.2	182.0	201.5	221.0	262.7	303.0	344.6	384.9
40°	122.2	126.1	131.3	150.8	169.0	188.5	206.7	244.5	283.5	321.2	358.9
42.5°	117.0	122.2	126.1	143.0	161.2	178.1	195.0	231.4	267.9	303.0	339.4
45°	115.7	120.9	126.1	140.4	154.7	167.7	182.0	217.1	252.3	287.4	322.5
47.5°	113.1	117.0	122.2	133.9	144.3	156.0	166.4	201.5	236.7	270.5	305.6
50°	111.8	113.1	115.7	126.1	136.5	146.9	157.3	192.4	227.5	262.7	297.8
52.5°	110.5	110.5	110.5	119.6	128.7	136.5	145.6	180.7	217.1	252.3	287.4
55°	102.7	101.4	101.4	110.5	118.3	127.4	135.2	170.3	205.4	239.3	274.4
57.5°	94.9	93.6	92.3	100.1	107.9	115.7	123.5	158.6	195.0	230.1	265.3
60°	87.1	85.8	85.8	93.6	100.1	107.9	114.4	150.8	185.9	222.3	257.5
62.5°	78.0	79.3	79.3	85.8	93.6	100.1	106.6	143.0	180.7	217.1	253.6
65°	71.5	72.8	72.8	80.6	88.4	96.2	104.0	139.1	175.5	210.6	245.8
67.5°	66.3	67.6	67.6	76.7	84.5	93.6	101.4	132.6	165.1	196.3	227.5
70°	61.1	61.1	62.4	71.5	80.6	89.7	98.8	126.1	153.4	179.4	206.7
72.5°	54.6	55.9	57.2	66.3	74.1	83.2	91.0	115.7	140.4	165.1	189.8
75°	48.1	49.4	50.7	58.5	66.3	74.1	81.9	105.3	127.4	150.8	172.9
77.5°	42.9	44.2	45.5	52.0	58.5	65.0	71.5	88.4	106.6	123.5	140.4
80°	35.1	35.1	36.4	41.6	46.8	50.7	55.9	67.6	79.3	89.7	101.4
82.5°	26.0	27.3	27.3	31.2	33.8	37.7	40.3	46.8	52.0	58.5	63.7
85°	22.1	20.8	20.8	23.4	24.7	27.3	28.6	32.5	35.1	39.0	41.6
87.5°	9.1	7.8	7.8	9.1	11.7	13.0	14.3	14.3	15.6	15.6	15.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671845  
 CATALOG NUMBER: CCP-SA-1B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671845

CATALOG NUMBER: CCP-SA-1B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2
2.5°	959.6	962.2	966.1	968.7	975.2	980.4	986.9	992.1	996.0	1002.5	999.9
5°	924.5	936.2	947.9	959.6	968.7	977.8	985.6	994.7	1005.1	1024.6	1029.8
7.5°	820.5	836.1	850.4	866.0	884.2	902.4	920.6	938.8	955.7	980.4	996.0
10°	717.8	739.9	760.7	782.8	799.7	816.6	832.2	849.1	872.5	897.2	925.8
12.5°	652.7	674.8	696.9	719.1	743.8	767.2	791.9	815.3	837.4	856.9	889.4
15°	609.8	634.5	657.9	681.3	711.3	739.9	769.8	798.4	830.9	856.9	879.0
17.5°	599.4	629.3	657.9	687.8	719.1	750.3	781.5	812.7	845.2	884.2	912.8
20°	581.2	621.5	661.8	702.1	742.5	781.5	821.8	860.8	903.7	950.5	963.5
22.5°	570.8	618.9	668.3	716.5	771.1	827.0	881.6	936.2	981.7	1016.8	1055.8
25°	569.5	629.3	690.4	750.3	819.2	886.8	955.7	1023.3	1081.8	1116.9	1148.1
27.5°	568.2	641.0	712.6	784.1	868.6	951.8	1036.3	1119.5	1174.1	1224.9	1250.9
30°	552.6	639.7	728.2	815.3	910.2	1005.1	1100.0	1195.0	1250.9	1286.0	1299.0
32.5°	533.1	635.8	738.6	841.3	949.2	1057.1	1163.7	1271.7	1315.9	1345.8	1335.4
35°	517.5	630.6	742.5	854.3	968.7	1084.4	1198.9	1313.3	1377.0	1418.6	1401.7
37.5°	503.2	621.5	739.9	858.2	992.1	1126.0	1260.0	1393.9	1455.0	1499.2	1479.7
40°	486.3	612.4	739.9	866.0	1019.4	1171.5	1325.0	1477.1	1556.4	1594.1	1564.2
42.5°	472.0	603.3	736.0	867.3	1031.1	1195.0	1358.8	1522.6	1611.0	1664.4	1626.6
45°	453.8	585.1	715.2	846.5	1027.2	1208.0	1387.4	1568.1	1670.9	1712.5	1660.5
47.5°	434.3	564.3	693.0	821.8	1014.2	1206.7	1399.1	1591.5	1686.5	1735.9	1687.8
50°	427.8	557.8	686.5	816.6	1024.6	1234.0	1442.0	1650.0	1719.0	1759.3	1695.6
52.5°	426.5	564.3	703.4	841.3	1050.6	1258.7	1468.0	1676.1	1732.0	1774.9	1717.7
55°	422.6	572.1	720.4	868.6	1087.0	1306.8	1525.2	1743.7	1799.6	1830.8	1787.9
57.5°	426.5	587.7	747.7	908.9	1133.8	1358.8	1583.7	1808.7	1876.3	1898.4	1889.3
60°	429.1	600.7	771.1	942.7	1162.4	1382.2	1601.9	1821.7	1891.9	1946.5	1956.9
62.5°	422.6	591.6	759.4	928.4	1127.3	1326.3	1525.2	1724.2	1839.9	1920.5	1967.3
65°	403.1	559.1	716.5	872.5	1055.8	1240.5	1423.8	1607.1	1729.4	1849.0	1886.7
67.5°	360.2	492.8	625.4	758.1	918.0	1077.9	1236.6	1396.5	1549.9	1665.7	1717.7
70°	312.1	416.1	521.4	625.4	771.1	916.7	1062.3	1208.0	1343.2	1470.6	1520.0
72.5°	271.8	352.4	434.3	514.9	618.9	721.7	825.7	928.4	1088.3	1215.8	1263.9
75°	231.4	290.0	347.2	405.7	477.2	548.7	618.9	690.4	803.6	918.0	966.1
77.5°	178.1	217.1	254.9	292.6	342.0	390.1	439.5	487.6	566.9	652.7	677.4
80°	123.5	145.6	166.4	188.5	227.5	266.6	305.6	344.6	396.6	444.7	482.4
82.5°	76.7	91.0	104.0	117.0	148.2	179.4	209.3	240.6	261.4	264.0	301.7
85°	49.4	58.5	66.3	74.1	92.3	111.8	130.0	148.2	132.6	123.5	146.9
87.5°	19.5	24.7	28.6	32.5	31.2	29.9	28.6	27.3	23.4	20.8	26.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671845  
 CATALOG NUMBER: CCP-SA-1B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671845

CATALOG NUMBER: CCP-SA-1B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2
2.5°	1002.5	1006.4	1010.3	1012.9	1016.8	1018.1	1019.4	1019.4	1020.7	1022.0	1024.6
5°	1050.6	1058.4	1066.2	1072.7	1080.5	1087.0	1092.2	1098.7	1103.9	1103.9	1102.6
7.5°	1010.3	1029.8	1049.3	1068.8	1088.3	1102.6	1115.6	1129.9	1142.9	1145.5	1148.1
10°	957.0	977.8	997.3	1018.1	1037.6	1059.7	1080.5	1101.3	1123.4	1127.3	1132.5
12.5°	907.6	932.3	957.0	980.4	1005.1	1020.7	1036.3	1050.6	1066.2	1076.6	1087.0
15°	906.3	927.1	947.9	967.4	988.2	997.3	1006.4	1014.2	1023.3	1023.3	1024.6
17.5°	936.2	949.2	962.2	973.9	986.9	988.2	990.8	992.1	993.4	989.5	985.6
20°	994.7	999.9	1005.1	1010.3	1015.5	1006.4	998.6	989.5	980.4	970.0	960.9
22.5°	1080.5	1068.8	1057.1	1045.4	1033.7	1018.1	1001.2	985.6	968.7	955.7	942.7
25°	1161.1	1146.8	1132.5	1118.2	1103.9	1070.1	1036.3	1001.2	967.4	953.1	938.8
27.5°	1269.1	1247.0	1224.9	1202.8	1180.6	1135.1	1089.6	1044.1	998.6	973.9	950.5
30°	1295.1	1270.4	1245.7	1219.7	1195.0	1150.7	1107.8	1063.6	1019.4	990.8	963.5
32.5°	1332.8	1304.2	1275.6	1247.0	1218.4	1175.4	1132.5	1088.3	1045.4	1019.4	992.1
35°	1395.2	1362.7	1330.2	1296.4	1263.9	1219.7	1176.7	1132.5	1088.3	1058.4	1029.8
37.5°	1448.5	1410.8	1373.1	1335.4	1297.7	1258.7	1218.4	1179.3	1139.0	1109.1	1080.5
40°	1508.3	1466.7	1425.1	1384.8	1343.2	1306.8	1270.4	1232.7	1196.3	1172.8	1149.4
42.5°	1560.3	1509.6	1460.2	1410.8	1360.1	1335.4	1312.0	1287.3	1262.6	1250.9	1237.9
45°	1596.7	1549.9	1501.8	1455.0	1408.2	1390.0	1371.8	1353.6	1335.4	1347.1	1358.8
47.5°	1612.3	1574.6	1538.2	1501.8	1464.1	1470.6	1477.1	1482.3	1488.8	1504.4	1521.3
50°	1626.6	1605.8	1583.7	1562.9	1540.8	1565.5	1588.9	1613.6	1638.3	1670.9	1703.4
52.5°	1655.3	1643.5	1633.1	1621.4	1609.7	1652.6	1695.6	1738.5	1781.4	1817.8	1854.2
55°	1741.1	1732.0	1722.9	1712.5	1703.4	1764.5	1824.3	1885.4	1946.5	1984.2	2021.9
57.5°	1859.4	1854.2	1847.7	1842.5	1836.0	1895.8	1954.3	2012.8	2072.6	2109.0	2146.8
60°	1949.1	1950.4	1950.4	1951.7	1951.7	1997.2	2042.7	2089.5	2135.1	2166.3	2198.8
62.5°	1997.2	1994.6	1992.0	1989.4	1986.8	2024.5	2062.2	2099.9	2137.7	2161.1	2184.5
65°	1945.2	1959.5	1973.8	1988.1	2002.4	2007.6	2011.5	2016.7	2020.6	2034.9	2049.2
67.5°	1771.0	1799.6	1826.9	1855.5	1882.8	1863.3	1845.1	1825.6	1806.1	1810.0	1812.6
70°	1577.2	1609.7	1643.5	1676.1	1708.6	1663.1	1617.5	1570.7	1525.2	1509.6	1494.0
72.5°	1330.2	1358.8	1388.7	1417.3	1445.9	1390.0	1335.4	1279.5	1223.6	1196.3	1168.9
75°	1016.8	1050.6	1085.7	1119.5	1153.3	1090.9	1027.2	964.8	901.1	882.9	866.0
77.5°	741.2	781.5	821.8	862.1	902.4	846.5	790.6	733.4	677.4	667.0	656.6
80°	539.6	570.8	600.7	631.9	661.8	629.3	596.8	564.3	531.8	530.5	529.2
82.5°	364.1	391.4	417.4	444.7	470.7	457.7	446.0	433.0	420.0	433.0	447.3
85°	187.2	224.9	264.0	301.7	339.4	335.5	332.9	329.0	325.1	342.0	357.6
87.5°	37.7	70.2	102.7	133.9	166.4	158.6	150.8	141.7	133.9	139.1	143.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671845  
 CATALOG NUMBER: CCP-SA-1B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671845

CATALOG NUMBER: CCP-SA-1B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2
2.5°	1025.9	1027.2	1027.2	1027.2	1027.2	1027.2	1024.6	1023.3	1020.7	1018.1	1014.2
5°	1102.6	1101.3	1096.1	1090.9	1084.4	1079.2	1075.3	1070.1	1066.2	1061.0	1053.2
7.5°	1150.7	1153.3	1144.2	1136.4	1127.3	1118.2	1109.1	1100.0	1090.9	1081.8	1063.6
10°	1136.4	1140.3	1135.1	1129.9	1123.4	1118.2	1107.8	1096.1	1085.7	1074.0	1051.9
12.5°	1096.1	1106.5	1103.9	1101.3	1098.7	1096.1	1089.6	1081.8	1075.3	1067.5	1042.8
15°	1024.6	1024.6	1025.9	1027.2	1027.2	1028.5	1029.8	1031.1	1032.4	1033.7	1019.4
17.5°	981.7	977.8	977.8	977.8	977.8	977.8	983.0	989.5	994.7	999.9	996.0
20°	950.5	941.4	940.1	940.1	938.8	937.5	946.6	957.0	966.1	975.2	980.4
22.5°	929.7	916.7	915.4	914.1	912.8	911.5	923.2	934.9	946.6	958.3	976.5
25°	924.5	910.2	911.5	912.8	912.8	914.1	923.2	932.3	941.4	950.5	981.7
27.5°	925.8	902.4	903.7	905.0	905.0	906.3	920.6	933.6	947.9	960.9	999.9
30°	934.9	907.6	905.0	902.4	899.8	897.2	916.7	936.2	955.7	975.2	1005.1
32.5°	966.1	940.1	933.6	927.1	920.6	914.1	937.5	959.6	983.0	1005.1	1029.8
35°	999.9	971.3	968.7	966.1	962.2	959.6	980.4	1002.5	1023.3	1044.1	1066.2
37.5°	1050.6	1022.0	1019.4	1015.5	1012.9	1009.0	1032.4	1054.5	1077.9	1100.0	1119.5
40°	1126.0	1102.6	1101.3	1101.3	1100.0	1098.7	1116.9	1136.4	1154.6	1172.8	1185.9
42.5°	1226.2	1214.5	1218.4	1223.6	1227.5	1231.4	1245.7	1261.3	1275.6	1289.9	1286.0
45°	1370.5	1382.2	1383.5	1384.8	1386.1	1387.4	1391.3	1396.5	1400.4	1404.3	1388.7
47.5°	1536.9	1552.5	1560.3	1568.1	1574.6	1582.4	1577.2	1570.7	1565.5	1559.0	1520.0
50°	1734.6	1767.1	1765.8	1764.5	1761.9	1760.6	1750.2	1739.8	1728.1	1717.7	1660.5
52.5°	1890.6	1927.0	1933.5	1940.0	1946.5	1953.0	1933.5	1914.0	1893.2	1873.7	1802.2
55°	2058.3	2096.0	2097.3	2098.6	2098.6	2099.9	2072.6	2045.3	2016.7	1989.4	1915.3
57.5°	2183.2	2219.6	2215.7	2213.1	2209.2	2205.3	2172.8	2140.3	2107.7	2075.2	2001.1
60°	2230.0	2261.2	2253.4	2245.6	2236.5	2228.7	2204.0	2179.3	2153.3	2128.6	2057.0
62.5°	2207.9	2231.3	2219.6	2209.2	2197.5	2185.8	2154.6	2122.0	2090.8	2058.3	2006.3
65°	2062.2	2076.5	2060.9	2046.6	2032.3	2016.7	1990.7	1964.7	1937.4	1911.4	1876.3
67.5°	1816.5	1819.1	1817.8	1816.5	1815.2	1813.9	1776.2	1738.5	1699.5	1661.8	1659.2
70°	1479.7	1464.1	1466.7	1470.6	1473.2	1475.8	1447.2	1419.9	1391.3	1362.7	1375.7
72.5°	1141.6	1114.3	1120.8	1128.6	1135.1	1141.6	1118.2	1096.1	1072.7	1049.3	1067.5
75°	847.8	830.9	837.4	845.2	851.7	858.2	849.1	840.0	829.6	820.5	837.4
77.5°	646.2	635.8	637.1	637.1	638.4	638.4	639.7	642.3	643.6	644.9	663.1
80°	526.6	525.3	524.0	522.7	520.1	518.8	531.8	544.8	557.8	570.8	579.9
82.5°	460.3	473.3	465.5	459.0	451.2	443.4	455.1	466.8	478.5	490.2	486.3
85°	374.5	390.1	375.8	361.5	345.9	331.6	342.0	351.1	361.5	370.6	365.4
87.5°	148.2	152.1	128.7	106.6	83.2	59.8	94.9	128.7	163.8	197.6	202.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671845  
 CATALOG NUMBER: CCP-SA-1B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671845

CATALOG NUMBER: CCP-SA-1B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2	936.2
2.5°	1010.3	1005.1	1001.2	999.9	997.3	996.0	993.4	990.8	986.9	984.3	980.4
5°	1044.1	1036.3	1027.2	1014.2	1002.5	989.5	976.5	964.8	953.1	940.1	928.4
7.5°	1045.4	1027.2	1009.0	992.1	973.9	957.0	938.8	923.2	906.3	889.4	873.8
10°	1031.1	1009.0	986.9	964.8	944.0	921.9	899.8	881.6	862.1	842.6	824.4
12.5°	1019.4	994.7	970.0	944.0	919.3	893.3	867.3	849.1	830.9	812.7	794.5
15°	1005.1	989.5	975.2	951.8	928.4	905.0	881.6	856.9	833.5	808.8	784.1
17.5°	993.4	989.5	985.6	970.0	954.4	937.5	921.9	897.2	872.5	846.5	821.8
20°	986.9	992.1	997.3	989.5	981.7	972.6	964.8	946.6	928.4	908.9	890.7
22.5°	994.7	1014.2	1032.4	1033.7	1036.3	1037.6	1038.9	1022.0	1005.1	986.9	970.0
25°	1012.9	1044.1	1075.3	1092.2	1109.1	1127.3	1144.2	1133.8	1123.4	1113.0	1102.6
27.5°	1037.6	1076.6	1115.6	1140.3	1163.7	1188.5	1213.2	1211.9	1210.6	1208.0	1206.7
30°	1033.7	1063.6	1093.5	1123.4	1153.3	1183.3	1213.2	1228.8	1243.1	1258.7	1274.3
32.5°	1055.8	1080.5	1106.5	1137.7	1168.9	1201.5	1232.7	1265.2	1296.4	1328.9	1361.4
35°	1089.6	1111.7	1135.1	1168.9	1204.1	1237.9	1273.0	1312.0	1352.3	1392.6	1431.6
37.5°	1140.3	1159.8	1180.6	1209.3	1239.2	1267.8	1297.7	1354.9	1412.1	1470.6	1527.8
40°	1198.9	1211.9	1224.9	1252.2	1279.5	1306.8	1334.1	1405.6	1477.1	1548.6	1620.1
42.5°	1283.4	1279.5	1275.6	1297.7	1321.1	1343.2	1366.6	1431.6	1496.6	1561.6	1626.6
45°	1373.1	1357.5	1341.9	1352.3	1364.0	1374.4	1386.1	1452.4	1518.7	1586.3	1652.6
47.5°	1481.0	1442.0	1403.0	1393.9	1384.8	1374.4	1365.3	1436.8	1508.3	1581.1	1652.6
50°	1603.2	1544.7	1487.5	1464.1	1439.4	1416.0	1391.3	1449.8	1509.6	1569.4	1627.9
52.5°	1730.7	1657.9	1586.3	1549.9	1513.5	1475.8	1439.4	1488.8	1539.5	1590.2	1639.6
55°	1839.9	1765.8	1690.4	1647.4	1604.5	1561.6	1518.7	1568.1	1617.5	1667.0	1716.4
57.5°	1927.0	1852.9	1778.8	1738.5	1696.9	1656.6	1614.9	1661.8	1709.9	1758.0	1804.8
60°	1986.8	1915.3	1843.8	1804.8	1765.8	1726.8	1687.8	1743.7	1799.6	1856.8	1912.7
62.5°	1955.6	1903.6	1851.6	1834.7	1817.8	1799.6	1782.7	1836.0	1888.0	1941.3	1994.6
65°	1841.2	1806.1	1771.0	1787.9	1806.1	1823.0	1841.2	1876.3	1911.4	1947.8	1982.9
67.5°	1655.3	1652.6	1648.7	1686.5	1724.2	1763.2	1800.9	1824.3	1846.4	1869.8	1893.2
70°	1388.7	1403.0	1416.0	1481.0	1546.0	1611.0	1676.1	1685.2	1694.3	1703.4	1712.5
72.5°	1087.0	1105.2	1124.7	1210.6	1295.1	1380.9	1466.7	1461.5	1456.3	1449.8	1444.6
75°	855.6	872.5	890.7	970.0	1049.3	1128.6	1208.0	1185.9	1165.0	1142.9	1120.8
77.5°	682.6	700.8	720.4	794.5	868.6	944.0	1018.1	964.8	911.5	858.2	804.9
80°	587.7	596.8	604.6	655.3	704.7	755.5	806.2	751.6	695.6	639.7	585.1
82.5°	482.4	477.2	473.3	503.2	533.1	563.0	592.9	540.9	488.9	435.6	383.6
85°	360.2	355.0	349.8	365.4	381.0	397.9	413.5	353.7	293.9	232.7	172.9
87.5°	209.3	214.5	219.7	236.7	253.6	271.8	288.7	227.5	166.4	104.0	42.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671845  
 CATALOG NUMBER: CCP-SA-1B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P671845  
CATALOG NUMBER: CCP-SA-1B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
0°	936.2	936.2
2.5°	972.6	966.1
5°	919.3	910.2
7.5°	860.8	849.1
10°	807.5	791.9
12.5°	773.7	754.2
15°	760.7	737.3
17.5°	799.7	777.6
20°	859.5	829.6
22.5°	932.3	895.9
25°	1058.4	1014.2
27.5°	1161.1	1115.6
30°	1224.9	1175.4
32.5°	1295.1	1230.1
35°	1367.9	1305.5
37.5°	1456.3	1386.1
40°	1547.3	1474.5
42.5°	1578.5	1531.7
45°	1608.4	1564.2
47.5°	1614.9	1578.5
50°	1621.4	1616.2
52.5°	1639.6	1638.3
55°	1717.7	1719.0
57.5°	1813.9	1821.7
60°	1902.3	1893.2
62.5°	1947.8	1901.0
65°	1916.6	1851.6
67.5°	1823.0	1752.8
70°	1617.5	1522.6
72.5°	1361.4	1278.2
75°	1049.3	979.1
77.5°	746.4	687.8
80°	525.3	466.8
82.5°	336.8	290.0
85°	152.1	132.6
87.5°	42.9	41.6
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P671845  
CATALOG NUMBER: CCP-SA-1B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)