

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P671857

Luminaire Tested: **CCP-SA-1C-827-U-SLR**

Issue Date: 04/16/2023



Test Information

Test Method: LM-79-08
Report Number: P671857
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/16/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCP-SA-1C-827-U-SLR
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @615mA w/ SLR distribution lens
Light Source: (16) 2700K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2758.1 lumens
Efficiency: N/A
Efficacy: 86.2 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G1


Input Watts (W): 32
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



REPORT NUMBER: P671857
 CATALOG NUMBER: CCP-SA-1C-827-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 3.9 fc
 Type IV - Short - N/A

REPORT NUMBER: P671857
CATALOG NUMBER: CCP-SA-1C-827-U-SLR

Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P671857
 CATALOG NUMBER: CCP-SA-1C-827-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	567.5	0.0	567.5
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	2190.6	0.0	2190.6
	% Fixture	79.4	0.0	79.4
Total	Lumens	2758.1	0.0	2758.1
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.4	2.5
10°-20°	144.5	5.2
20°-30°	211.4	7.7
30°-40°	297.8	10.8
40°-50°	409.3	14.8
50°-60°	557.8	20.2
60°-70°	610.6	22.1
70°-80°	352.6	12.8
80°-90°	105.7	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2758.1	100.0
0°-180°	2758.1	100.0



REPORT NUMBER: P671857


CATALOG NUMBER: CCP-SA-1C-827-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	283.3	10.3			
FM	(30°-60°)	1006.5	36.5			
FH	(60°-80°)	811.1	29.4			G1/1800
FVH	(80°-90°)	89.8	3.3			G1/100
BL	(0°-30°)	141.1	5.1	B1/500		
BM	(30°-60°)	258.4	9.4	B1/1000		
BH	(60°-80°)	152.1	5.5	B1/500		G1/500
BVH	(80°-90°)	15.9	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type IV Short





REPORT NUMBER: P671857
 CATALOG NUMBER: CCP-SA-1C-827-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8
2.5°	908.9	904.0	900.4	896.7	891.8	888.1	883.2	878.3	872.2	867.3	861.2
5°	856.3	841.6	827.0	818.4	808.6	800.0	790.3	779.2	768.2	756.0	745.0
7.5°	798.8	780.5	762.1	747.4	731.5	716.9	701.0	687.5	674.0	660.6	647.1
10°	745.0	727.9	710.7	692.4	672.8	654.5	634.9	616.5	598.2	579.8	561.5
12.5°	709.5	688.7	669.1	648.4	628.8	608.0	587.2	570.1	552.9	534.6	517.5
15°	693.6	674.0	655.7	634.9	614.1	593.3	572.5	552.9	534.6	515.0	495.4
17.5°	731.5	703.4	675.3	648.4	621.4	594.5	567.6	543.1	518.7	494.2	469.8
20°	780.5	745.0	710.7	677.7	643.5	610.4	576.2	541.9	507.7	473.4	439.2
22.5°	842.9	802.5	763.3	720.5	676.5	633.7	589.6	546.8	504.0	460.0	417.1
25°	954.2	906.5	858.8	797.6	735.2	674.0	611.7	555.4	500.3	444.1	387.8
27.5°	1049.6	984.8	921.2	847.8	774.4	701.0	627.6	562.7	499.1	434.3	369.4
30°	1105.9	1042.3	978.6	889.3	801.3	712.0	622.7	550.5	479.5	407.4	335.2
32.5°	1157.2	1086.3	1015.3	917.5	818.4	720.5	621.4	541.9	463.6	384.1	304.6
35°	1228.2	1149.9	1072.8	959.1	845.3	731.5	617.8	535.8	452.6	370.7	287.5
37.5°	1304.0	1207.4	1112.0	986.0	860.0	734.0	608.0	527.2	446.5	365.8	285.0
40°	1387.2	1269.8	1153.6	1014.1	875.9	736.4	597.0	516.2	435.5	353.5	272.8
42.5°	1441.1	1313.8	1186.6	1036.1	886.9	736.4	586.0	506.4	426.9	346.2	266.7
45°	1471.6	1348.1	1225.8	1063.1	900.4	737.7	575.0	496.7	418.4	338.9	260.6
47.5°	1485.1	1370.1	1255.1	1083.9	913.8	742.5	571.3	491.8	411.0	331.5	250.8
50°	1520.6	1419.0	1317.5	1134.0	951.7	768.2	584.7	499.1	414.7	329.1	243.4
52.5°	1541.4	1454.5	1367.7	1179.3	990.9	802.5	614.1	518.7	423.3	327.8	232.4
55°	1617.2	1534.0	1450.8	1250.2	1048.4	847.8	645.9	540.7	435.5	329.1	223.9
57.5°	1713.9	1625.8	1538.9	1322.4	1105.9	889.3	672.8	560.3	446.5	334.0	220.2
60°	1781.1	1695.5	1611.1	1381.1	1149.9	919.9	688.7	571.3	453.8	335.2	217.7
62.5°	1788.5	1678.4	1569.5	1345.6	1121.8	896.7	672.8	559.1	445.3	330.3	216.5
65°	1742.0	1613.5	1485.1	1271.0	1056.9	842.9	628.8	524.8	420.8	315.6	211.6
67.5°	1649.0	1498.6	1348.1	1152.4	956.6	760.9	565.2	475.9	387.8	298.5	209.2
70°	1432.5	1300.4	1169.5	999.4	830.6	660.6	490.5	417.1	345.0	271.6	198.2
72.5°	1202.5	1079.0	956.6	818.4	681.4	543.1	404.9	349.9	294.8	238.5	183.5
75°	921.2	828.2	736.4	633.7	530.9	426.9	324.2	283.8	243.4	203.1	162.7
77.5°	647.1	597.0	548.0	471.0	393.9	316.8	239.8	212.9	185.9	159.0	132.1
80°	439.2	411.0	384.1	329.1	274.0	217.7	162.7	145.6	127.2	110.1	91.7
82.5°	272.8	271.6	269.1	231.2	193.3	155.4	117.4	102.8	89.3	74.6	59.9
85°	124.8	145.6	165.1	144.4	123.6	102.8	82.0	72.2	62.4	51.4	41.6
87.5°	39.1	47.7	55.0	52.6	48.9	46.5	42.8	36.7	30.6	24.5	18.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671857
 CATALOG NUMBER: CCP-SA-1C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671857

CATALOG NUMBER: CCP-SA-1C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8
2.5°	856.3	852.6	847.8	842.9	836.7	831.8	825.7	819.6	818.4	815.9	814.7
5°	737.7	730.3	721.8	714.4	707.1	698.5	691.2	682.6	676.5	669.1	663.0
7.5°	633.7	621.4	608.0	594.5	582.3	570.1	556.6	544.4	538.3	532.1	526.0
10°	550.5	538.3	527.2	515.0	506.4	499.1	490.5	482.0	474.6	467.3	460.0
12.5°	508.9	500.3	491.8	483.2	473.4	464.9	455.1	445.3	436.7	429.4	420.8
15°	483.2	471.0	457.5	445.3	431.8	419.6	406.1	392.7	382.9	374.3	364.5
17.5°	452.6	434.3	417.1	398.8	384.1	369.4	353.5	338.9	327.8	315.6	304.6
20°	418.4	397.6	375.6	354.8	337.6	321.7	304.6	287.5	275.2	261.8	249.6
22.5°	389.0	362.1	334.0	305.8	287.5	269.1	249.6	231.2	220.2	208.0	197.0
25°	357.2	327.8	297.3	266.7	248.3	228.8	210.4	190.8	182.3	174.9	166.4
27.5°	340.1	310.7	280.1	250.8	233.7	215.3	198.2	179.8	173.7	166.4	160.3
30°	305.8	277.7	248.3	219.0	206.7	195.7	183.5	171.3	168.8	167.6	165.1
32.5°	275.2	245.9	216.5	187.2	176.2	165.1	154.1	143.1	141.9	139.5	138.2
35°	259.3	231.2	201.8	173.7	163.9	152.9	143.1	132.1	129.7	126.0	123.6
37.5°	255.7	226.3	195.7	166.4	156.6	146.8	135.8	126.0	123.6	121.1	118.7
40°	245.9	217.7	190.8	162.7	152.9	143.1	132.1	122.3	119.9	117.4	115.0
42.5°	238.5	211.6	183.5	155.4	146.8	138.2	128.4	119.9	117.4	115.0	111.3
45°	232.4	204.3	174.9	146.8	140.7	134.6	127.2	121.1	118.7	115.0	112.5
47.5°	222.6	195.7	167.6	139.5	133.3	128.4	122.3	116.2	113.8	111.3	108.9
50°	215.3	187.2	159.0	130.9	126.0	121.1	116.2	111.3	111.3	111.3	112.5
52.5°	205.5	178.6	151.7	124.8	119.9	115.0	110.1	105.2	106.4	107.7	108.9
55°	197.0	171.3	144.4	117.4	112.5	107.7	101.5	96.6	97.9	99.1	100.3
57.5°	193.3	166.4	139.5	112.5	107.7	101.5	96.6	90.5	90.5	90.5	90.5
60°	190.8	162.7	135.8	107.7	101.5	96.6	90.5	84.4	83.2	83.2	82.0
62.5°	189.6	161.5	134.6	106.4	99.1	93.0	85.6	78.3	77.1	75.8	74.6
65°	184.7	159.0	132.1	105.2	96.6	89.3	80.7	72.2	71.0	71.0	69.7
67.5°	183.5	156.6	130.9	104.0	95.4	85.6	77.1	67.3	66.1	64.8	63.6
70°	173.7	150.5	126.0	101.5	91.7	83.2	73.4	63.6	62.4	59.9	58.7
72.5°	161.5	140.7	118.7	96.6	86.9	77.1	67.3	57.5	56.3	55.0	52.6
75°	143.1	123.6	104.0	84.4	75.8	68.5	59.9	51.4	50.2	48.9	46.5
77.5°	117.4	101.5	86.9	71.0	64.8	58.7	52.6	46.5	45.3	44.0	41.6
80°	83.2	73.4	64.8	55.0	51.4	46.5	42.8	37.9	37.9	36.7	36.7
82.5°	55.0	50.2	45.3	40.4	37.9	35.5	33.0	30.6	30.6	29.4	29.4
85°	39.1	36.7	33.0	30.6	29.4	26.9	25.7	23.2	23.2	23.2	23.2
87.5°	18.3	18.3	17.1	17.1	15.9	15.9	14.7	13.5	13.5	13.5	13.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671857
 CATALOG NUMBER: CCP-SA-1C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671857
 CATALOG NUMBER: CCP-SA-1C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8
2.5°	812.3	808.6	804.9	800.0	796.4	791.5	785.4	780.5	774.4	774.4	773.1
5°	655.7	652.0	648.4	643.5	639.8	634.9	631.2	626.3	621.4	621.4	620.2
7.5°	519.9	512.6	505.2	496.7	489.3	484.4	479.5	473.4	468.5	464.9	461.2
10°	452.6	445.3	436.7	429.4	420.8	414.7	408.6	401.2	395.1	390.2	385.3
12.5°	412.3	403.7	395.1	386.6	378.0	369.4	362.1	353.5	345.0	338.9	332.7
15°	354.8	346.2	337.6	329.1	320.5	310.7	300.9	289.9	280.1	275.2	271.6
17.5°	292.4	283.8	274.0	265.5	255.7	248.3	241.0	233.7	226.3	221.4	217.7
20°	236.1	226.3	216.5	206.7	197.0	192.1	187.2	182.3	177.4	173.7	171.3
22.5°	184.7	178.6	173.7	167.6	161.5	157.8	155.4	151.7	148.0	148.0	148.0
25°	157.8	154.1	151.7	148.0	144.4	143.1	141.9	139.5	138.2	137.0	137.0
27.5°	152.9	149.2	145.6	141.9	138.2	137.0	135.8	133.3	132.1	132.1	132.1
30°	162.7	161.5	160.3	159.0	157.8	155.4	151.7	149.2	145.6	143.1	140.7
32.5°	135.8	134.6	134.6	133.3	132.1	134.6	135.8	138.2	139.5	140.7	141.9
35°	119.9	117.4	115.0	112.5	110.1	108.9	107.7	106.4	105.2	105.2	104.0
37.5°	116.2	113.8	111.3	108.9	106.4	105.2	104.0	102.8	101.5	101.5	100.3
40°	112.5	110.1	108.9	106.4	104.0	102.8	101.5	99.1	97.9	96.6	96.6
42.5°	108.9	107.7	105.2	104.0	101.5	100.3	99.1	96.6	95.4	94.2	93.0
45°	108.9	106.4	104.0	101.5	99.1	97.9	95.4	94.2	91.7	91.7	90.5
47.5°	106.4	104.0	101.5	99.1	96.6	95.4	93.0	91.7	89.3	88.1	86.9
50°	112.5	108.9	104.0	100.3	95.4	94.2	91.7	90.5	88.1	86.9	85.6
52.5°	110.1	106.4	101.5	97.9	93.0	90.5	89.3	86.9	84.4	83.2	82.0
55°	101.5	97.9	95.4	91.7	88.1	85.6	83.2	80.7	78.3	77.1	77.1
57.5°	90.5	89.3	88.1	86.9	85.6	83.2	80.7	77.1	74.6	73.4	72.2
60°	80.7	82.0	83.2	84.4	85.6	82.0	78.3	74.6	71.0	69.7	68.5
62.5°	73.4	75.8	78.3	79.5	82.0	78.3	74.6	71.0	67.3	66.1	64.8
65°	68.5	69.7	69.7	71.0	71.0	68.5	67.3	64.8	62.4	61.2	61.2
67.5°	62.4	62.4	62.4	61.2	61.2	59.9	59.9	58.7	57.5	56.3	56.3
70°	56.3	56.3	56.3	55.0	55.0	53.8	53.8	52.6	51.4	51.4	50.2
72.5°	51.4	51.4	50.2	50.2	48.9	48.9	48.9	47.7	47.7	46.5	46.5
75°	45.3	45.3	44.0	44.0	42.8	42.8	42.8	41.6	41.6	41.6	40.4
77.5°	40.4	40.4	39.1	39.1	37.9	37.9	37.9	36.7	36.7	35.5	35.5
80°	35.5	35.5	34.3	34.3	33.0	33.0	31.8	31.8	30.6	30.6	29.4
82.5°	28.1	28.1	28.1	28.1	28.1	26.9	26.9	25.7	24.5	24.5	23.2
85°	23.2	23.2	23.2	22.0	22.0	22.0	20.8	20.8	19.6	18.3	18.3
87.5°	13.5	13.5	13.5	12.2	12.2	12.2	12.2	12.2	12.2	12.2	11.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671857
 CATALOG NUMBER: CCP-SA-1C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671857
 CATALOG NUMBER: CCP-SA-1C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8
2.5°	773.1	771.9	767.0	762.1	767.0	771.9	771.9	771.9	770.7	770.7	770.7
5°	620.2	619.0	616.5	614.1	614.1	612.9	615.3	617.8	620.2	622.7	625.1
7.5°	456.3	452.6	449.0	445.3	447.7	449.0	452.6	455.1	458.7	461.2	467.3
10°	380.4	375.6	371.9	368.2	365.8	363.3	360.9	359.7	357.2	354.8	357.2
12.5°	325.4	319.3	313.2	305.8	304.6	303.4	300.9	298.5	296.0	293.6	292.4
15°	266.7	261.8	259.3	255.7	250.8	245.9	243.4	242.2	239.8	237.3	236.1
17.5°	212.9	208.0	204.3	200.6	199.4	197.0	197.0	197.0	197.0	197.0	197.0
20°	167.6	163.9	163.9	162.7	162.7	161.5	162.7	163.9	163.9	165.1	166.4
22.5°	146.8	146.8	145.6	144.4	145.6	145.6	146.8	148.0	149.2	150.5	151.7
25°	135.8	134.6	135.8	137.0	137.0	137.0	138.2	138.2	139.5	139.5	139.5
27.5°	130.9	130.9	132.1	132.1	133.3	133.3	133.3	132.1	132.1	130.9	130.9
30°	138.2	135.8	135.8	135.8	134.6	133.3	132.1	132.1	130.9	129.7	128.4
32.5°	143.1	144.4	143.1	140.7	139.5	137.0	135.8	133.3	132.1	129.7	127.2
35°	104.0	102.8	105.2	106.4	107.7	108.9	110.1	111.3	111.3	112.5	112.5
37.5°	100.3	99.1	99.1	97.9	97.9	97.9	97.9	97.9	96.6	96.6	97.9
40°	95.4	94.2	94.2	93.0	93.0	91.7	91.7	91.7	91.7	91.7	91.7
42.5°	91.7	90.5	90.5	90.5	90.5	89.3	89.3	88.1	88.1	86.9	86.9
45°	90.5	89.3	88.1	86.9	86.9	85.6	85.6	85.6	84.4	84.4	84.4
47.5°	85.6	84.4	84.4	83.2	83.2	82.0	82.0	82.0	80.7	80.7	80.7
50°	83.2	82.0	82.0	80.7	80.7	79.5	79.5	79.5	78.3	78.3	78.3
52.5°	79.5	78.3	78.3	78.3	77.1	75.8	75.8	75.8	74.6	74.6	74.6
55°	75.8	74.6	74.6	74.6	73.4	72.2	72.2	72.2	71.0	71.0	71.0
57.5°	71.0	69.7	69.7	68.5	68.5	68.5	68.5	68.5	67.3	67.3	67.3
60°	67.3	66.1	66.1	64.8	64.8	63.6	63.6	63.6	63.6	63.6	63.6
62.5°	63.6	62.4	61.2	59.9	61.2	61.2	61.2	61.2	59.9	59.9	59.9
65°	59.9	58.7	57.5	56.3	56.3	56.3	56.3	56.3	56.3	56.3	56.3
67.5°	55.0	53.8	52.6	51.4	52.6	52.6	52.6	52.6	52.6	52.6	52.6
70°	50.2	48.9	48.9	47.7	47.7	46.5	46.5	47.7	47.7	47.7	47.7
72.5°	45.3	44.0	44.0	42.8	42.8	42.8	42.8	42.8	42.8	42.8	42.8
75°	40.4	39.1	39.1	37.9	37.9	37.9	37.9	37.9	37.9	37.9	37.9
77.5°	34.3	33.0	33.0	33.0	33.0	33.0	33.0	34.3	34.3	34.3	34.3
80°	29.4	28.1	28.1	28.1	28.1	28.1	28.1	28.1	28.1	28.1	28.1
82.5°	23.2	22.0	22.0	22.0	22.0	22.0	22.0	22.0	22.0	22.0	22.0
85°	17.1	15.9	15.9	15.9	17.1	17.1	17.1	17.1	17.1	17.1	17.1
87.5°	11.0	9.8	9.8	9.8	11.0	11.0	11.0	11.0	9.8	9.8	9.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671857
 CATALOG NUMBER: CCP-SA-1C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671857
 CATALOG NUMBER: CCP-SA-1C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8
2.5°	770.7	770.7	770.7	769.5	768.2	767.0	765.8	769.5	771.9	775.6	778.0
5°	626.3	628.8	630.0	633.7	637.3	641.0	644.7	647.1	649.6	650.8	653.2
7.5°	472.2	478.3	483.2	488.1	493.0	496.7	501.6	505.2	508.9	512.6	516.2
10°	358.4	360.9	362.1	367.0	370.7	375.6	379.2	382.9	386.6	389.0	392.7
12.5°	291.1	288.7	287.5	287.5	287.5	287.5	287.5	289.9	292.4	294.8	297.3
15°	234.9	233.7	232.4	231.2	230.0	227.5	226.3	228.8	231.2	233.7	236.1
17.5°	197.0	197.0	197.0	195.7	194.5	193.3	192.1	193.3	194.5	194.5	195.7
20°	168.8	170.0	171.3	172.5	172.5	173.7	173.7	174.9	176.2	176.2	177.4
22.5°	151.7	152.9	152.9	152.9	154.1	154.1	154.1	155.4	156.6	157.8	159.0
25°	138.2	138.2	137.0	137.0	138.2	138.2	138.2	138.2	139.5	139.5	139.5
27.5°	130.9	129.7	129.7	129.7	129.7	128.4	128.4	128.4	128.4	128.4	128.4
30°	127.2	126.0	124.8	123.6	123.6	122.3	121.1	121.1	121.1	121.1	121.1
32.5°	126.0	123.6	121.1	119.9	119.9	118.7	117.4	116.2	116.2	115.0	113.8
35°	112.5	111.3	111.3	110.1	108.9	107.7	106.4	106.4	106.4	105.2	105.2
37.5°	97.9	99.1	99.1	99.1	100.3	100.3	100.3	100.3	101.5	101.5	101.5
40°	91.7	91.7	91.7	93.0	94.2	94.2	95.4	95.4	96.6	96.6	96.6
42.5°	86.9	85.6	85.6	86.9	86.9	88.1	88.1	89.3	90.5	90.5	91.7
45°	84.4	83.2	83.2	83.2	83.2	82.0	82.0	83.2	84.4	85.6	86.9
47.5°	79.5	79.5	78.3	78.3	78.3	78.3	78.3	78.3	79.5	79.5	79.5
50°	77.1	77.1	75.8	75.8	75.8	75.8	75.8	75.8	75.8	75.8	75.8
52.5°	74.6	73.4	73.4	73.4	73.4	72.2	72.2	72.2	72.2	72.2	72.2
55°	71.0	69.7	69.7	69.7	69.7	69.7	69.7	69.7	71.0	71.0	71.0
57.5°	67.3	66.1	66.1	66.1	67.3	67.3	67.3	67.3	68.5	68.5	68.5
60°	63.6	63.6	63.6	63.6	63.6	63.6	63.6	64.8	64.8	66.1	66.1
62.5°	59.9	59.9	59.9	59.9	61.2	61.2	61.2	61.2	62.4	62.4	62.4
65°	56.3	56.3	56.3	56.3	57.5	57.5	57.5	57.5	57.5	57.5	57.5
67.5°	52.6	52.6	52.6	52.6	52.6	52.6	52.6	53.8	53.8	55.0	55.0
70°	47.7	46.5	46.5	47.7	47.7	48.9	48.9	50.2	50.2	51.4	51.4
72.5°	42.8	42.8	42.8	42.8	42.8	42.8	42.8	44.0	45.3	45.3	46.5
75°	37.9	37.9	37.9	37.9	39.1	39.1	39.1	40.4	40.4	41.6	41.6
77.5°	34.3	33.0	33.0	33.0	34.3	34.3	34.3	35.5	35.5	36.7	36.7
80°	28.1	28.1	28.1	28.1	29.4	29.4	29.4	29.4	30.6	30.6	30.6
82.5°	23.2	23.2	23.2	23.2	23.2	23.2	23.2	23.2	24.5	24.5	24.5
85°	17.1	17.1	17.1	17.1	18.3	18.3	18.3	18.3	18.3	18.3	18.3
87.5°	11.0	11.0	11.0	11.0	11.0	11.0	11.0	11.0	12.2	12.2	12.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671857
 CATALOG NUMBER: CCP-SA-1C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671857
 CATALOG NUMBER: CCP-SA-1C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8
2.5°	778.0	778.0	778.0	778.0	780.5	781.7	784.1	785.4	784.1	782.9	780.5
5°	654.5	655.7	655.7	656.9	656.9	656.9	656.9	656.9	659.4	661.8	664.3
7.5°	517.5	518.7	519.9	521.1	521.1	521.1	519.9	519.9	521.1	521.1	522.4
10°	396.4	401.2	404.9	408.6	406.1	402.5	400.0	396.4	396.4	396.4	395.1
12.5°	299.7	300.9	303.4	304.6	303.4	303.4	302.2	300.9	302.2	304.6	305.8
15°	237.3	237.3	238.5	238.5	239.8	241.0	241.0	242.2	244.7	245.9	248.3
17.5°	197.0	198.2	198.2	199.4	199.4	200.6	200.6	200.6	203.1	205.5	209.2
20°	177.4	177.4	177.4	177.4	177.4	176.2	176.2	174.9	176.2	178.6	179.8
22.5°	159.0	160.3	160.3	160.3	159.0	157.8	155.4	154.1	154.1	155.4	155.4
25°	139.5	138.2	138.2	137.0	137.0	138.2	138.2	138.2	139.5	139.5	140.7
27.5°	128.4	127.2	127.2	126.0	126.0	127.2	127.2	127.2	127.2	127.2	127.2
30°	119.9	119.9	118.7	117.4	118.7	118.7	119.9	119.9	121.1	121.1	122.3
32.5°	113.8	112.5	112.5	111.3	112.5	112.5	113.8	113.8	115.0	116.2	116.2
35°	105.2	105.2	105.2	105.2	105.2	105.2	104.0	104.0	104.0	104.0	104.0
37.5°	100.3	100.3	99.1	97.9	97.9	97.9	97.9	97.9	96.6	95.4	94.2
40°	96.6	95.4	95.4	94.2	93.0	93.0	91.7	90.5	90.5	89.3	89.3
42.5°	91.7	90.5	90.5	89.3	88.1	88.1	86.9	85.6	85.6	85.6	84.4
45°	85.6	85.6	84.4	83.2	83.2	83.2	82.0	82.0	82.0	82.0	80.7
47.5°	79.5	79.5	78.3	78.3	78.3	78.3	77.1	77.1	77.1	77.1	77.1
50°	75.8	75.8	75.8	75.8	75.8	75.8	74.6	74.6	74.6	74.6	74.6
52.5°	72.2	72.2	72.2	72.2	72.2	72.2	72.2	72.2	72.2	72.2	72.2
55°	71.0	71.0	71.0	71.0	71.0	71.0	69.7	69.7	69.7	71.0	71.0
57.5°	68.5	68.5	67.3	67.3	67.3	67.3	67.3	67.3	67.3	67.3	67.3
60°	66.1	66.1	66.1	66.1	66.1	66.1	66.1	66.1	66.1	66.1	66.1
62.5°	62.4	62.4	62.4	62.4	62.4	63.6	63.6	63.6	63.6	63.6	62.4
65°	57.5	58.7	58.7	58.7	58.7	58.7	58.7	58.7	58.7	58.7	58.7
67.5°	55.0	55.0	55.0	55.0	55.0	55.0	55.0	55.0	55.0	55.0	55.0
70°	51.4	51.4	50.2	50.2	50.2	51.4	51.4	51.4	51.4	51.4	51.4
72.5°	46.5	46.5	46.5	46.5	46.5	46.5	46.5	46.5	46.5	47.7	47.7
75°	41.6	41.6	41.6	41.6	41.6	41.6	41.6	41.6	41.6	41.6	41.6
77.5°	36.7	36.7	35.5	35.5	35.5	36.7	36.7	36.7	36.7	37.9	37.9
80°	30.6	30.6	30.6	30.6	30.6	30.6	30.6	30.6	30.6	31.8	31.8
82.5°	24.5	24.5	24.5	24.5	24.5	24.5	24.5	24.5	24.5	25.7	25.7
85°	18.3	19.6	19.6	19.6	19.6	19.6	19.6	19.6	19.6	20.8	20.8
87.5°	12.2	12.2	12.2	12.2	12.2	12.2	11.0	11.0	11.0	11.0	9.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671857
 CATALOG NUMBER: CCP-SA-1C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671857
 CATALOG NUMBER: CCP-SA-1C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8
2.5°	779.2	780.5	781.7	781.7	782.9	784.1	784.1	789.0	793.9	796.4	798.8
5°	666.7	665.5	665.5	664.3	663.0	666.7	670.4	677.7	685.1	686.3	688.7
7.5°	522.4	523.6	524.8	524.8	526.0	522.4	517.5	518.7	519.9	526.0	530.9
10°	395.1	396.4	397.6	397.6	398.8	397.6	395.1	398.8	402.5	407.4	413.5
12.5°	307.1	310.7	314.4	316.8	320.5	323.0	324.2	329.1	332.7	338.9	345.0
15°	250.8	253.2	255.7	258.1	260.6	263.0	265.5	270.4	275.2	282.6	289.9
17.5°	211.6	211.6	212.9	212.9	212.9	215.3	217.7	220.2	221.4	228.8	236.1
20°	181.0	179.8	178.6	177.4	176.2	178.6	179.8	181.0	182.3	187.2	190.8
22.5°	155.4	155.4	156.6	156.6	156.6	155.4	152.9	154.1	154.1	156.6	160.3
25°	140.7	140.7	140.7	139.5	139.5	140.7	141.9	141.9	140.7	141.9	143.1
27.5°	127.2	128.4	128.4	129.7	129.7	130.9	130.9	130.9	130.9	132.1	133.3
30°	122.3	122.3	123.6	123.6	123.6	124.8	126.0	126.0	126.0	127.2	129.7
32.5°	117.4	118.7	119.9	121.1	122.3	123.6	123.6	124.8	124.8	126.0	127.2
35°	104.0	102.8	102.8	101.5	100.3	100.3	100.3	100.3	99.1	100.3	100.3
37.5°	93.0	93.0	93.0	91.7	91.7	93.0	93.0	93.0	93.0	94.2	94.2
40°	88.1	88.1	88.1	88.1	88.1	88.1	88.1	89.3	89.3	90.5	91.7
42.5°	84.4	84.4	84.4	84.4	84.4	85.6	85.6	85.6	85.6	86.9	86.9
45°	80.7	80.7	80.7	80.7	80.7	80.7	80.7	82.0	82.0	83.2	84.4
47.5°	77.1	77.1	77.1	77.1	77.1	78.3	79.5	79.5	79.5	80.7	80.7
50°	74.6	74.6	74.6	74.6	74.6	75.8	75.8	77.1	77.1	78.3	79.5
52.5°	72.2	72.2	72.2	72.2	72.2	73.4	73.4	74.6	74.6	75.8	77.1
55°	71.0	71.0	71.0	69.7	69.7	71.0	71.0	72.2	72.2	73.4	73.4
57.5°	67.3	67.3	67.3	67.3	67.3	67.3	67.3	68.5	68.5	69.7	71.0
60°	66.1	66.1	64.8	64.8	63.6	64.8	64.8	66.1	66.1	67.3	67.3
62.5°	62.4	62.4	62.4	61.2	61.2	62.4	62.4	62.4	62.4	63.6	64.8
65°	58.7	58.7	58.7	57.5	57.5	58.7	58.7	58.7	58.7	59.9	61.2
67.5°	55.0	55.0	55.0	53.8	53.8	53.8	53.8	55.0	55.0	56.3	57.5
70°	51.4	51.4	51.4	50.2	50.2	50.2	48.9	50.2	51.4	52.6	52.6
72.5°	47.7	47.7	47.7	46.5	46.5	46.5	45.3	46.5	46.5	47.7	47.7
75°	41.6	41.6	41.6	41.6	41.6	41.6	40.4	40.4	40.4	41.6	41.6
77.5°	37.9	37.9	37.9	36.7	36.7	36.7	35.5	35.5	35.5	36.7	36.7
80°	31.8	31.8	31.8	30.6	30.6	30.6	29.4	29.4	29.4	30.6	30.6
82.5°	25.7	25.7	25.7	24.5	24.5	24.5	23.2	23.2	23.2	24.5	24.5
85°	20.8	20.8	20.8	20.8	20.8	20.8	19.6	19.6	19.6	20.8	22.0
87.5°	9.8	9.8	11.0	11.0	11.0	11.0	9.8	9.8	8.6	8.6	9.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671857
 CATALOG NUMBER: CCP-SA-1C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671857
 CATALOG NUMBER: CCP-SA-1C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8
2.5°	801.3	803.7	809.8	814.7	820.8	825.7	829.4	834.3	838.0	841.6	844.1
5°	689.9	691.2	697.3	703.4	708.3	714.4	723.0	731.5	740.1	748.7	754.8
7.5°	537.0	541.9	549.3	557.8	565.2	572.5	581.1	590.9	599.4	608.0	616.5
10°	418.4	423.3	430.6	437.9	444.1	451.4	461.2	471.0	480.8	490.5	500.3
12.5°	351.1	357.2	365.8	374.3	381.7	390.2	402.5	413.5	425.7	436.7	449.0
15°	296.0	303.4	314.4	326.6	337.6	348.6	360.9	373.1	384.1	396.4	408.6
17.5°	243.4	250.8	260.6	271.6	281.4	291.1	305.8	319.3	334.0	347.4	360.9
20°	195.7	199.4	209.2	219.0	228.8	238.5	249.6	260.6	271.6	282.6	299.7
22.5°	162.7	165.1	170.0	173.7	178.6	182.3	193.3	204.3	214.1	225.1	241.0
25°	143.1	144.4	148.0	150.5	154.1	156.6	163.9	170.0	177.4	183.5	198.2
27.5°	133.3	134.6	135.8	137.0	138.2	139.5	144.4	149.2	152.9	157.8	171.3
30°	130.9	132.1	135.8	138.2	141.9	144.4	146.8	149.2	151.7	154.1	162.7
32.5°	128.4	129.7	129.7	128.4	128.4	127.2	129.7	130.9	133.3	134.6	141.9
35°	101.5	101.5	102.8	104.0	105.2	106.4	110.1	112.5	116.2	118.7	124.8
37.5°	95.4	95.4	96.6	99.1	100.3	101.5	104.0	106.4	108.9	111.3	117.4
40°	91.7	93.0	94.2	95.4	96.6	97.9	100.3	101.5	104.0	105.2	110.1
42.5°	88.1	88.1	89.3	91.7	93.0	94.2	96.6	97.9	100.3	101.5	106.4
45°	85.6	86.9	88.1	89.3	89.3	90.5	93.0	95.4	96.6	99.1	104.0
47.5°	82.0	82.0	84.4	85.6	88.1	89.3	91.7	93.0	95.4	96.6	101.5
50°	79.5	80.7	83.2	84.4	86.9	88.1	91.7	94.2	97.9	100.3	102.8
52.5°	77.1	78.3	80.7	82.0	84.4	85.6	90.5	95.4	99.1	104.0	104.0
55°	74.6	74.6	77.1	80.7	83.2	85.6	88.1	91.7	94.2	96.6	96.6
57.5°	71.0	72.2	74.6	78.3	80.7	83.2	85.6	88.1	89.3	91.7	90.5
60°	68.5	68.5	72.2	75.8	79.5	83.2	83.2	83.2	82.0	82.0	82.0
62.5°	64.8	66.1	71.0	77.1	82.0	86.9	83.2	79.5	75.8	72.2	73.4
65°	62.4	63.6	66.1	69.7	72.2	74.6	72.2	71.0	68.5	66.1	67.3
67.5°	57.5	58.7	59.9	59.9	61.2	61.2	61.2	61.2	61.2	61.2	62.4
70°	53.8	53.8	53.8	55.0	55.0	55.0	55.0	55.0	55.0	55.0	56.3
72.5°	48.9	48.9	48.9	48.9	48.9	48.9	48.9	48.9	48.9	48.9	50.2
75°	42.8	42.8	42.8	42.8	42.8	42.8	42.8	42.8	42.8	42.8	44.0
77.5°	37.9	37.9	37.9	37.9	37.9	37.9	37.9	37.9	36.7	36.7	37.9
80°	31.8	31.8	31.8	31.8	30.6	30.6	30.6	30.6	30.6	30.6	31.8
82.5°	25.7	25.7	25.7	25.7	24.5	24.5	24.5	24.5	23.2	23.2	24.5
85°	23.2	24.5	24.5	25.7	25.7	25.7	24.5	23.2	22.0	20.8	20.8
87.5°	9.8	9.8	9.8	9.8	8.6	8.6	8.6	8.6	8.6	8.6	8.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671857
 CATALOG NUMBER: CCP-SA-1C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671857
 CATALOG NUMBER: CCP-SA-1C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8
2.5°	847.8	850.2	852.6	856.3	861.2	864.9	868.5	875.9	884.5	891.8	899.1
5°	760.9	767.0	773.1	780.5	787.8	793.9	801.3	815.9	830.6	844.1	858.8
7.5°	623.9	632.5	639.8	652.0	663.0	675.3	686.3	704.6	721.8	740.1	757.2
10°	510.1	519.9	529.7	545.6	562.7	578.6	594.5	609.2	625.1	639.8	654.5
12.5°	461.2	472.2	484.4	494.2	505.2	515.0	524.8	541.9	559.1	576.2	593.3
15°	420.8	433.1	445.3	457.5	468.5	480.8	491.8	506.4	522.4	537.0	551.7
17.5°	374.3	386.6	400.0	413.5	426.9	440.4	453.8	474.6	495.4	515.0	535.8
20°	315.6	332.7	348.6	367.0	385.3	403.7	422.0	444.1	466.1	486.9	508.9
22.5°	256.9	272.8	288.7	310.7	332.7	353.5	375.6	404.9	433.1	462.4	490.5
25°	214.1	228.8	243.4	267.9	291.1	315.6	338.9	374.3	408.6	444.1	478.3
27.5°	184.7	198.2	211.6	237.3	263.0	287.5	313.2	352.3	390.2	429.4	467.3
30°	171.3	179.8	188.4	212.9	237.3	260.6	285.0	323.0	360.9	398.8	436.7
32.5°	149.2	156.6	163.9	185.9	208.0	228.8	250.8	289.9	327.8	367.0	404.9
35°	132.1	138.2	144.4	165.1	184.7	205.5	225.1	264.2	303.4	342.5	381.7
37.5°	122.3	128.4	133.3	151.7	171.3	189.6	208.0	247.1	285.0	324.2	362.1
40°	115.0	118.7	123.6	141.9	159.0	177.4	194.5	230.0	266.7	302.2	337.6
42.5°	110.1	115.0	118.7	134.6	151.7	167.6	183.5	217.7	252.0	285.0	319.3
45°	108.9	113.8	118.7	132.1	145.6	157.8	171.3	204.3	237.3	270.4	303.4
47.5°	106.4	110.1	115.0	126.0	135.8	146.8	156.6	189.6	222.6	254.4	287.5
50°	105.2	106.4	108.9	118.7	128.4	138.2	148.0	181.0	214.1	247.1	280.1
52.5°	104.0	104.0	104.0	112.5	121.1	128.4	137.0	170.0	204.3	237.3	270.4
55°	96.6	95.4	95.4	104.0	111.3	119.9	127.2	160.3	193.3	225.1	258.1
57.5°	89.3	88.1	86.9	94.2	101.5	108.9	116.2	149.2	183.5	216.5	249.6
60°	82.0	80.7	80.7	88.1	94.2	101.5	107.7	141.9	174.9	209.2	242.2
62.5°	73.4	74.6	74.6	80.7	88.1	94.2	100.3	134.6	170.0	204.3	238.5
65°	67.3	68.5	68.5	75.8	83.2	90.5	97.9	130.9	165.1	198.2	231.2
67.5°	62.4	63.6	63.6	72.2	79.5	88.1	95.4	124.8	155.4	184.7	214.1
70°	57.5	57.5	58.7	67.3	75.8	84.4	93.0	118.7	144.4	168.8	194.5
72.5°	51.4	52.6	53.8	62.4	69.7	78.3	85.6	108.9	132.1	155.4	178.6
75°	45.3	46.5	47.7	55.0	62.4	69.7	77.1	99.1	119.9	141.9	162.7
77.5°	40.4	41.6	42.8	48.9	55.0	61.2	67.3	83.2	100.3	116.2	132.1
80°	33.0	33.0	34.3	39.1	44.0	47.7	52.6	63.6	74.6	84.4	95.4
82.5°	24.5	25.7	25.7	29.4	31.8	35.5	37.9	44.0	48.9	55.0	59.9
85°	20.8	19.6	19.6	22.0	23.2	25.7	26.9	30.6	33.0	36.7	39.1
87.5°	8.6	7.3	7.3	8.6	11.0	12.2	13.5	13.5	14.7	14.7	14.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671857
 CATALOG NUMBER: CCP-SA-1C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671857
 CATALOG NUMBER: CCP-SA-1C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8
2.5°	902.8	905.2	908.9	911.4	917.5	922.4	928.5	933.4	937.1	943.2	940.7
5°	869.8	880.8	891.8	902.8	911.4	919.9	927.3	935.8	945.6	964.0	968.9
7.5°	771.9	786.6	800.0	814.7	831.8	849.0	866.1	883.2	899.1	922.4	937.1
10°	675.3	696.1	715.6	736.4	752.3	768.2	782.9	798.8	820.8	844.1	871.0
12.5°	614.1	634.9	655.7	676.5	699.7	721.8	745.0	767.0	787.8	806.2	836.7
15°	573.7	597.0	619.0	641.0	669.1	696.1	724.2	751.1	781.7	806.2	827.0
17.5°	563.9	592.1	619.0	647.1	676.5	705.8	735.2	764.6	795.2	831.8	858.8
20°	546.8	584.7	622.7	660.6	698.5	735.2	773.1	809.8	850.2	894.2	906.5
22.5°	537.0	582.3	628.8	674.0	725.4	778.0	829.4	880.8	923.6	956.6	993.3
25°	535.8	592.1	649.6	705.8	770.7	834.3	899.1	962.7	1017.8	1050.8	1080.2
27.5°	534.6	603.1	670.4	737.7	817.2	895.5	975.0	1053.3	1104.6	1152.4	1176.8
30°	519.9	601.9	685.1	767.0	856.3	945.6	1034.9	1124.2	1176.8	1209.9	1222.1
32.5°	501.6	598.2	694.8	791.5	893.0	994.5	1094.9	1196.4	1238.0	1266.1	1256.3
35°	486.9	593.3	698.5	803.7	911.4	1020.2	1127.9	1235.5	1295.5	1334.6	1318.7
37.5°	473.4	584.7	696.1	807.4	933.4	1059.4	1185.4	1311.4	1368.9	1410.5	1392.1
40°	457.5	576.2	696.1	814.7	959.1	1102.2	1246.6	1389.7	1464.3	1499.8	1471.6
42.5°	444.1	567.6	692.4	815.9	970.1	1124.2	1278.4	1432.5	1515.7	1565.8	1530.4
45°	426.9	550.5	672.8	796.4	966.4	1136.5	1305.3	1475.3	1572.0	1611.1	1562.2
47.5°	408.6	530.9	652.0	773.1	954.2	1135.2	1316.3	1497.3	1586.6	1633.1	1587.9
50°	402.5	524.8	645.9	768.2	964.0	1160.9	1356.6	1552.4	1617.2	1655.1	1595.2
52.5°	401.2	530.9	661.8	791.5	988.4	1184.2	1381.1	1576.8	1629.4	1669.8	1616.0
55°	397.6	538.3	677.7	817.2	1022.7	1229.4	1434.9	1640.5	1693.1	1722.4	1682.0
57.5°	401.2	552.9	703.4	855.1	1066.7	1278.4	1490.0	1701.6	1765.2	1786.0	1777.5
60°	403.7	565.2	725.4	886.9	1093.6	1300.4	1507.1	1713.9	1779.9	1831.3	1841.1
62.5°	397.6	556.6	714.4	873.4	1060.6	1247.8	1434.9	1622.1	1731.0	1806.8	1850.9
65°	379.2	526.0	674.0	820.8	993.3	1167.0	1339.5	1512.0	1627.0	1739.5	1775.0
67.5°	338.9	463.6	588.4	713.2	863.7	1014.1	1163.4	1313.8	1458.2	1567.1	1616.0
70°	293.6	391.5	490.5	588.4	725.4	862.4	999.4	1136.5	1263.7	1383.6	1430.0
72.5°	255.7	331.5	408.6	484.4	582.3	678.9	776.8	873.4	1023.9	1143.8	1189.1
75°	217.7	272.8	326.6	381.7	449.0	516.2	582.3	649.6	756.0	863.7	908.9
77.5°	167.6	204.3	239.8	275.2	321.7	367.0	413.5	458.7	533.4	614.1	637.3
80°	116.2	137.0	156.6	177.4	214.1	250.8	287.5	324.2	373.1	418.4	453.8
82.5°	72.2	85.6	97.9	110.1	139.5	168.8	197.0	226.3	245.9	248.3	283.8
85°	46.5	55.0	62.4	69.7	86.9	105.2	122.3	139.5	124.8	116.2	138.2
87.5°	18.3	23.2	26.9	30.6	29.4	28.1	26.9	25.7	22.0	19.6	24.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671857
 CATALOG NUMBER: CCP-SA-1C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671857

CATALOG NUMBER: CCP-SA-1C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8
2.5°	943.2	946.8	950.5	953.0	956.6	957.9	959.1	959.1	960.3	961.5	964.0
5°	988.4	995.8	1003.1	1009.2	1016.6	1022.7	1027.6	1033.7	1038.6	1038.6	1037.4
7.5°	950.5	968.9	987.2	1005.6	1023.9	1037.4	1049.6	1063.1	1075.3	1077.7	1080.2
10°	900.4	919.9	938.3	957.9	976.2	997.0	1016.6	1036.1	1056.9	1060.6	1065.5
12.5°	853.9	877.1	900.4	922.4	945.6	960.3	975.0	988.4	1003.1	1012.9	1022.7
15°	852.6	872.2	891.8	910.1	929.7	938.3	946.8	954.2	962.7	962.7	964.0
17.5°	880.8	893.0	905.2	916.3	928.5	929.7	932.2	933.4	934.6	930.9	927.3
20°	935.8	940.7	945.6	950.5	955.4	946.8	939.5	930.9	922.4	912.6	904.0
22.5°	1016.6	1005.6	994.5	983.5	972.5	957.9	941.9	927.3	911.4	899.1	886.9
25°	1092.4	1079.0	1065.5	1052.0	1038.6	1006.8	975.0	941.9	910.1	896.7	883.2
27.5°	1193.9	1173.2	1152.4	1131.6	1110.8	1067.9	1025.1	982.3	939.5	916.3	894.2
30°	1218.4	1195.2	1171.9	1147.5	1124.2	1082.6	1042.3	1000.7	959.1	932.2	906.5
32.5°	1253.9	1227.0	1200.1	1173.2	1146.2	1105.9	1065.5	1023.9	983.5	959.1	933.4
35°	1312.6	1282.0	1251.4	1219.6	1189.1	1147.5	1107.1	1065.5	1023.9	995.8	968.9
37.5°	1362.8	1327.3	1291.8	1256.3	1220.9	1184.2	1146.2	1109.5	1071.6	1043.5	1016.6
40°	1419.0	1379.9	1340.7	1302.8	1263.7	1229.4	1195.2	1159.7	1125.4	1103.4	1081.4
42.5°	1468.0	1420.3	1373.8	1327.3	1279.6	1256.3	1234.3	1211.1	1187.8	1176.8	1164.6
45°	1502.2	1458.2	1412.9	1368.9	1324.8	1307.7	1290.6	1273.5	1256.3	1267.3	1278.4
47.5°	1516.9	1481.4	1447.2	1412.9	1377.4	1383.6	1389.7	1394.6	1400.7	1415.4	1431.3
50°	1530.4	1510.8	1490.0	1470.4	1449.6	1472.9	1494.9	1518.1	1541.4	1572.0	1602.5
52.5°	1557.3	1546.3	1536.5	1525.5	1514.5	1554.8	1595.2	1635.6	1675.9	1710.2	1744.4
55°	1638.0	1629.4	1620.9	1611.1	1602.5	1660.0	1716.3	1773.8	1831.3	1866.8	1902.2
57.5°	1749.3	1744.4	1738.3	1733.4	1727.3	1783.6	1838.6	1893.7	1950.0	1984.2	2019.7
60°	1833.7	1835.0	1835.0	1836.2	1836.2	1879.0	1921.8	1965.9	2008.7	2038.0	2068.6
62.5°	1879.0	1876.6	1874.1	1871.7	1869.2	1904.7	1940.2	1975.6	2011.1	2033.1	2055.2
65°	1830.1	1843.5	1857.0	1870.4	1883.9	1888.8	1892.5	1897.4	1901.0	1914.5	1927.9
67.5°	1666.1	1693.1	1718.7	1745.7	1771.3	1753.0	1735.9	1717.5	1699.2	1702.8	1705.3
70°	1483.9	1514.5	1546.3	1576.8	1607.4	1564.6	1521.8	1477.8	1434.9	1420.3	1405.6
72.5°	1251.4	1278.4	1306.5	1333.4	1360.3	1307.7	1256.3	1203.7	1151.1	1125.4	1099.8
75°	956.6	988.4	1021.5	1053.3	1085.1	1026.4	966.4	907.7	847.8	830.6	814.7
77.5°	697.3	735.2	773.1	811.1	849.0	796.4	743.8	689.9	637.3	627.6	617.8
80°	507.7	537.0	565.2	594.5	622.7	592.1	561.5	530.9	500.3	499.1	497.9
82.5°	342.5	368.2	392.7	418.4	442.8	430.6	419.6	407.4	395.1	407.4	420.8
85°	176.2	211.6	248.3	283.8	319.3	315.6	313.2	309.5	305.8	321.7	336.4
87.5°	35.5	66.1	96.6	126.0	156.6	149.2	141.9	133.3	126.0	130.9	134.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671857
 CATALOG NUMBER: CCP-SA-1C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671857

CATALOG NUMBER: CCP-SA-1C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8
2.5°	965.2	966.4	966.4	966.4	966.4	966.4	964.0	962.7	960.3	957.9	954.2
5°	1037.4	1036.1	1031.2	1026.4	1020.2	1015.3	1011.7	1006.8	1003.1	998.2	990.9
7.5°	1082.6	1085.1	1076.5	1069.2	1060.6	1052.0	1043.5	1034.9	1026.4	1017.8	1000.7
10°	1069.2	1072.8	1067.9	1063.1	1056.9	1052.0	1042.3	1031.2	1021.5	1010.5	989.7
12.5°	1031.2	1041.0	1038.6	1036.1	1033.7	1031.2	1025.1	1017.8	1011.7	1004.3	981.1
15°	964.0	964.0	965.2	966.4	966.4	967.6	968.9	970.1	971.3	972.5	959.1
17.5°	923.6	919.9	919.9	919.9	919.9	919.9	924.8	930.9	935.8	940.7	937.1
20°	894.2	885.7	884.5	884.5	883.2	882.0	890.6	900.4	908.9	917.5	922.4
22.5°	874.7	862.4	861.2	860.0	858.8	857.5	868.5	879.6	890.6	901.6	918.7
25°	869.8	856.3	857.5	858.8	858.8	860.0	868.5	877.1	885.7	894.2	923.6
27.5°	871.0	849.0	850.2	851.4	851.4	852.6	866.1	878.3	891.8	904.0	940.7
30°	879.6	853.9	851.4	849.0	846.5	844.1	862.4	880.8	899.1	917.5	945.6
32.5°	908.9	884.5	878.3	872.2	866.1	860.0	882.0	902.8	924.8	945.6	968.9
35°	940.7	913.8	911.4	908.9	905.2	902.8	922.4	943.2	962.7	982.3	1003.1
37.5°	988.4	961.5	959.1	955.4	953.0	949.3	971.3	992.1	1014.1	1034.9	1053.3
40°	1059.4	1037.4	1036.1	1036.1	1034.9	1033.7	1050.8	1069.2	1086.3	1103.4	1115.7
42.5°	1153.6	1142.6	1146.2	1151.1	1154.8	1158.5	1171.9	1186.6	1200.1	1213.5	1209.9
45°	1289.4	1300.4	1301.6	1302.8	1304.0	1305.3	1308.9	1313.8	1317.5	1321.2	1306.5
47.5°	1445.9	1460.6	1468.0	1475.3	1481.4	1488.8	1483.9	1477.8	1472.9	1466.7	1430.0
50°	1631.9	1662.5	1661.3	1660.0	1657.6	1656.4	1646.6	1636.8	1625.8	1616.0	1562.2
52.5°	1778.7	1812.9	1819.1	1825.2	1831.3	1837.4	1819.1	1800.7	1781.1	1762.8	1695.5
55°	1936.5	1972.0	1973.2	1974.4	1974.4	1975.6	1950.0	1924.3	1897.4	1871.7	1801.9
57.5°	2053.9	2088.2	2084.5	2082.1	2078.4	2074.7	2044.1	2013.6	1983.0	1952.4	1882.7
60°	2098.0	2127.3	2120.0	2112.7	2104.1	2096.7	2073.5	2050.3	2025.8	2002.6	1935.3
62.5°	2077.2	2099.2	2088.2	2078.4	2067.4	2056.4	2027.0	1996.4	1967.1	1936.5	1887.6
65°	1940.2	1953.6	1938.9	1925.5	1912.0	1897.4	1872.9	1848.4	1822.7	1798.3	1765.2
67.5°	1709.0	1711.4	1710.2	1709.0	1707.7	1706.5	1671.0	1635.6	1598.9	1563.4	1560.9
70°	1392.1	1377.4	1379.9	1383.6	1386.0	1388.5	1361.5	1335.9	1308.9	1282.0	1294.3
72.5°	1074.1	1048.4	1054.5	1061.8	1067.9	1074.1	1052.0	1031.2	1009.2	987.2	1004.3
75°	797.6	781.7	787.8	795.2	801.3	807.4	798.8	790.3	780.5	771.9	787.8
77.5°	608.0	598.2	599.4	599.4	600.6	600.6	601.9	604.3	605.5	606.8	623.9
80°	495.4	494.2	493.0	491.8	489.3	488.1	500.3	512.6	524.8	537.0	545.6
82.5°	433.1	445.3	437.9	431.8	424.5	417.1	428.2	439.2	450.2	461.2	457.5
85°	352.3	367.0	353.5	340.1	325.4	311.9	321.7	330.3	340.1	348.6	343.7
87.5°	139.5	143.1	121.1	100.3	78.3	56.3	89.3	121.1	154.1	185.9	190.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671857
 CATALOG NUMBER: CCP-SA-1C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671857

CATALOG NUMBER: CCP-SA-1C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8	880.8
2.5°	950.5	945.6	941.9	940.7	938.3	937.1	934.6	932.2	928.5	926.0	922.4
5°	982.3	975.0	966.4	954.2	943.2	930.9	918.7	907.7	896.7	884.5	873.4
7.5°	983.5	966.4	949.3	933.4	916.3	900.4	883.2	868.5	852.6	836.7	822.1
10°	970.1	949.3	928.5	907.7	888.1	867.3	846.5	829.4	811.1	792.7	775.6
12.5°	959.1	935.8	912.6	888.1	864.9	840.4	815.9	798.8	781.7	764.6	747.4
15°	945.6	930.9	917.5	895.5	873.4	851.4	829.4	806.2	784.1	760.9	737.7
17.5°	934.6	930.9	927.3	912.6	897.9	882.0	867.3	844.1	820.8	796.4	773.1
20°	928.5	933.4	938.3	930.9	923.6	915.0	907.7	890.6	873.4	855.1	838.0
22.5°	935.8	954.2	971.3	972.5	975.0	976.2	977.4	961.5	945.6	928.5	912.6
25°	953.0	982.3	1011.7	1027.6	1043.5	1060.6	1076.5	1066.7	1056.9	1047.2	1037.4
27.5°	976.2	1012.9	1049.6	1072.8	1094.9	1118.1	1141.3	1140.1	1138.9	1136.5	1135.2
30°	972.5	1000.7	1028.8	1056.9	1085.1	1113.2	1141.3	1156.0	1169.5	1184.2	1198.8
32.5°	993.3	1016.6	1041.0	1070.4	1099.8	1130.3	1159.7	1190.3	1219.6	1250.2	1280.8
35°	1025.1	1045.9	1067.9	1099.8	1132.8	1164.6	1197.6	1234.3	1272.2	1310.2	1346.9
37.5°	1072.8	1091.2	1110.8	1137.7	1165.8	1192.7	1220.9	1274.7	1328.5	1383.6	1437.4
40°	1127.9	1140.1	1152.4	1178.0	1203.7	1229.4	1255.1	1322.4	1389.7	1457.0	1524.2
42.5°	1207.4	1203.7	1200.1	1220.9	1242.9	1263.7	1285.7	1346.9	1408.0	1469.2	1530.4
45°	1291.8	1277.1	1262.5	1272.2	1283.2	1293.0	1304.0	1366.4	1428.8	1492.4	1554.8
47.5°	1393.3	1356.6	1319.9	1311.4	1302.8	1293.0	1284.5	1351.8	1419.0	1487.5	1554.8
50°	1508.3	1453.3	1399.5	1377.4	1354.2	1332.2	1308.9	1364.0	1420.3	1476.5	1531.6
52.5°	1628.2	1559.7	1492.4	1458.2	1423.9	1388.5	1354.2	1400.7	1448.4	1496.1	1542.6
55°	1731.0	1661.3	1590.3	1549.9	1509.6	1469.2	1428.8	1475.3	1521.8	1568.3	1614.8
57.5°	1812.9	1743.2	1673.5	1635.6	1596.4	1558.5	1519.3	1563.4	1608.6	1653.9	1698.0
60°	1869.2	1801.9	1734.7	1698.0	1661.3	1624.6	1587.9	1640.5	1693.1	1746.9	1799.5
62.5°	1839.9	1790.9	1742.0	1726.1	1710.2	1693.1	1677.2	1727.3	1776.2	1826.4	1876.6
65°	1732.2	1699.2	1666.1	1682.0	1699.2	1715.1	1732.2	1765.2	1798.3	1832.5	1865.5
67.5°	1557.3	1554.8	1551.2	1586.6	1622.1	1658.8	1694.3	1716.3	1737.1	1759.1	1781.1
70°	1306.5	1319.9	1332.2	1393.3	1454.5	1515.7	1576.8	1585.4	1594.0	1602.5	1611.1
72.5°	1022.7	1039.8	1058.2	1138.9	1218.4	1299.2	1379.9	1375.0	1370.1	1364.0	1359.1
75°	804.9	820.8	838.0	912.6	987.2	1061.8	1136.5	1115.7	1096.1	1075.3	1054.5
77.5°	642.2	659.4	677.7	747.4	817.2	888.1	957.9	907.7	857.5	807.4	757.2
80°	552.9	561.5	568.8	616.5	663.0	710.7	758.5	707.1	654.5	601.9	550.5
82.5°	453.8	449.0	445.3	473.4	501.6	529.7	557.8	508.9	460.0	409.8	360.9
85°	338.9	334.0	329.1	343.7	358.4	374.3	389.0	332.7	276.5	219.0	162.7
87.5°	197.0	201.8	206.7	222.6	238.5	255.7	271.6	214.1	156.6	97.9	40.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671857
 CATALOG NUMBER: CCP-SA-1C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671857
CATALOG NUMBER: CCP-SA-1C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	880.8	880.8
2.5°	915.0	908.9
5°	864.9	856.3
7.5°	809.8	798.8
10°	759.7	745.0
12.5°	727.9	709.5
15°	715.6	693.6
17.5°	752.3	731.5
20°	808.6	780.5
22.5°	877.1	842.9
25°	995.8	954.2
27.5°	1092.4	1049.6
30°	1152.4	1105.9
32.5°	1218.4	1157.2
35°	1286.9	1228.2
37.5°	1370.1	1304.0
40°	1455.7	1387.2
42.5°	1485.1	1441.1
45°	1513.2	1471.6
47.5°	1519.3	1485.1
50°	1525.5	1520.6
52.5°	1542.6	1541.4
55°	1616.0	1617.2
57.5°	1706.5	1713.9
60°	1789.7	1781.1
62.5°	1832.5	1788.5
65°	1803.2	1742.0
67.5°	1715.1	1649.0
70°	1521.8	1432.5
72.5°	1280.8	1202.5
75°	987.2	921.2
77.5°	702.2	647.1
80°	494.2	439.2
82.5°	316.8	272.8
85°	143.1	124.8
87.5°	40.4	39.1
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P671857
CATALOG NUMBER: CCP-SA-1C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)