

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P671895

Luminaire Tested: **CCP-SA-2B-840-U-SLR**

Issue Date: 04/16/2023



Test Information

Test Method: LM-79-08
Report Number: P671895
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/16/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCP-SA-2B-840-U-SLR
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @450mA w/ SLR distribution lens
Light Source: (32) 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4886.5 lumens
Efficiency: N/A
Efficacy: 106.2 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2

Input Watts (W): 46
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P671895
 CATALOG NUMBER: CCP-SA-2B-840-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 6.9 fc
 Type IV - Short - N/A

REPORT NUMBER: P671895
CATALOG NUMBER: CCP-SA-2B-840-U-SLR

Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P671895

CATALOG NUMBER: CCP-SA-2B-840-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1005.4	0.0	1005.4
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	3881.0	0.0	3881.0
	% Fixture	79.4	0.0	79.4
Total	Lumens	4886.5	0.0	4886.5
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.3	2.5
10°-20°	256.0	5.2
20°-30°	374.5	7.7
30°-40°	527.7	10.8
40°-50°	725.1	14.8
50°-60°	988.3	20.2
60°-70°	1081.7	22.1
70°-80°	624.7	12.8
80°-90°	187.2	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4886.5	100.0
0°-180°	4886.5	100.0



REPORT NUMBER: P671895


CATALOG NUMBER: CCP-SA-2B-840-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	501.9	10.3			
FM (30°-60°)	1783.2	36.5			
FH (60°-80°)	1436.9	29.4			G1/1800
FVH (80°-90°)	159.1	3.3			G2/225
BL (0°-30°)	250.0	5.1	B1/500		
BM (30°-60°)	457.8	9.4	B1/1000		
BH (60°-80°)	269.4	5.5	B1/500		G1/500
BVH (80°-90°)	28.2	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P671895

CATALOG NUMBER: CCP-SA-2B-840-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4
2.5°	1610.3	1601.6	1595.1	1588.6	1579.9	1573.4	1564.8	1556.1	1545.3	1536.6	1525.8
5°	1517.1	1491.1	1465.1	1449.9	1432.6	1417.4	1400.1	1380.6	1361.0	1339.4	1319.9
7.5°	1415.2	1382.7	1350.2	1324.2	1296.0	1270.0	1241.8	1218.0	1194.2	1170.3	1146.5
10°	1319.9	1289.5	1259.2	1226.7	1192.0	1159.5	1124.8	1092.3	1059.8	1027.3	994.8
12.5°	1257.0	1220.2	1185.5	1148.7	1114.0	1077.1	1040.3	1010.0	979.6	947.1	916.8
15°	1228.8	1194.2	1161.7	1124.8	1088.0	1051.1	1014.3	979.6	947.1	912.4	877.7
17.5°	1296.0	1246.2	1196.3	1148.7	1101.0	1053.3	1005.6	962.3	918.9	875.6	832.2
20°	1382.7	1319.9	1259.2	1200.7	1140.0	1081.5	1020.8	960.1	899.4	838.7	778.1
22.5°	1493.3	1421.7	1352.4	1276.5	1198.5	1122.6	1044.6	968.8	892.9	814.9	739.0
25°	1690.5	1606.0	1521.4	1413.1	1302.5	1194.2	1083.6	983.9	886.4	786.7	687.0
27.5°	1859.5	1744.7	1632.0	1501.9	1371.9	1241.8	1111.8	996.9	884.2	769.4	654.5
30°	1959.2	1846.5	1733.8	1575.6	1419.6	1261.4	1103.1	975.3	849.6	721.7	593.8
32.5°	2050.2	1924.5	1798.8	1625.5	1449.9	1276.5	1101.0	960.1	821.4	680.5	539.7
35°	2175.9	2037.2	1900.7	1699.1	1497.6	1296.0	1094.5	949.3	801.9	656.7	509.3
37.5°	2310.3	2139.1	1970.1	1746.8	1523.6	1300.4	1077.1	934.1	791.1	648.0	505.0
40°	2457.7	2249.6	2043.7	1796.7	1551.8	1304.7	1057.6	914.6	771.6	626.3	483.3
42.5°	2553.1	2327.7	2102.3	1835.7	1571.3	1304.7	1038.1	897.3	756.4	613.3	472.5
45°	2607.2	2388.3	2171.6	1883.4	1595.1	1306.9	1018.6	879.9	741.2	600.3	461.6
47.5°	2631.1	2427.3	2223.6	1920.2	1619.0	1315.5	1012.1	871.2	728.2	587.3	444.3
50°	2693.9	2514.0	2334.2	2009.1	1686.1	1361.0	1036.0	884.2	734.7	583.0	431.3
52.5°	2730.8	2576.9	2423.0	2089.3	1755.5	1421.7	1088.0	918.9	749.9	580.8	411.8
55°	2865.1	2717.8	2570.4	2215.0	1857.4	1501.9	1144.3	957.9	771.6	583.0	396.6
57.5°	3036.4	2880.3	2726.4	2342.8	1959.2	1575.6	1192.0	992.6	791.1	591.7	390.1
60°	3155.6	3003.8	2854.3	2446.9	2037.2	1629.8	1220.2	1012.1	804.1	593.8	385.8
62.5°	3168.6	2973.5	2780.6	2384.0	1987.4	1588.6	1192.0	990.4	788.9	585.2	383.6
65°	3086.2	2858.6	2631.1	2251.8	1872.5	1493.3	1114.0	929.8	745.5	559.2	374.9
67.5°	2921.5	2654.9	2388.3	2041.6	1694.8	1348.0	1001.3	843.1	687.0	528.8	370.6
70°	2537.9	2303.8	2071.9	1770.7	1471.6	1170.3	869.1	739.0	611.2	481.1	351.1
72.5°	2130.4	1911.5	1694.8	1449.9	1207.2	962.3	717.4	619.8	522.3	422.6	325.1
75°	1632.0	1467.2	1304.7	1122.6	940.6	756.4	574.3	502.8	431.3	359.8	288.2
77.5°	1146.5	1057.6	970.9	834.4	697.9	561.3	424.8	377.1	329.4	281.7	234.1
80°	778.1	728.2	680.5	583.0	485.5	385.8	288.2	257.9	225.4	195.1	162.5
82.5°	483.3	481.1	476.8	409.6	342.4	275.2	208.1	182.1	158.2	132.2	106.2
85°	221.1	257.9	292.6	255.7	218.9	182.1	145.2	127.9	110.5	91.0	73.7
87.5°	69.4	84.5	97.5	93.2	86.7	82.4	75.9	65.0	54.2	43.3	32.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671895
 CATALOG NUMBER: CCP-SA-2B-840-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671895

CATALOG NUMBER: CCP-SA-2B-840-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4
2.5°	1517.1	1510.6	1501.9	1493.3	1482.4	1473.7	1462.9	1452.1	1449.9	1445.6	1443.4
5°	1306.9	1293.9	1278.7	1265.7	1252.7	1237.5	1224.5	1209.3	1198.5	1185.5	1174.7
7.5°	1122.6	1101.0	1077.1	1053.3	1031.6	1010.0	986.1	964.4	953.6	942.8	931.9
10°	975.3	953.6	934.1	912.4	897.3	884.2	869.1	853.9	840.9	827.9	814.9
12.5°	901.6	886.4	871.2	856.1	838.7	823.6	806.2	788.9	773.7	760.7	745.5
15°	856.1	834.4	810.6	788.9	765.0	743.4	719.5	695.7	678.4	663.2	645.8
17.5°	801.9	769.4	739.0	706.5	680.5	654.5	626.3	600.3	580.8	559.2	539.7
20°	741.2	704.4	665.4	628.5	598.2	570.0	539.7	509.3	487.6	463.8	442.1
22.5°	689.2	641.5	591.7	541.8	509.3	476.8	442.1	409.6	390.1	368.4	348.9
25°	632.8	580.8	526.6	472.5	440.0	405.3	372.8	338.1	322.9	309.9	294.7
27.5°	602.5	550.5	496.3	444.3	413.9	381.4	351.1	318.6	307.8	294.7	283.9
30°	541.8	492.0	440.0	387.9	366.3	346.8	325.1	303.4	299.1	296.9	292.6
32.5°	487.6	435.6	383.6	331.6	312.1	292.6	273.1	253.6	251.4	247.1	244.9
35°	459.5	409.6	357.6	307.8	290.4	270.9	253.6	234.1	229.7	223.2	218.9
37.5°	453.0	400.9	346.8	294.7	277.4	260.1	240.6	223.2	218.9	214.6	210.2
40°	435.6	385.8	338.1	288.2	270.9	253.6	234.1	216.7	212.4	208.1	203.7
42.5°	422.6	374.9	325.1	275.2	260.1	244.9	227.6	212.4	208.1	203.7	197.2
45°	411.8	361.9	309.9	260.1	249.2	238.4	225.4	214.6	210.2	203.7	199.4
47.5°	394.4	346.8	296.9	247.1	236.2	227.6	216.7	205.9	201.6	197.2	192.9
50°	381.4	331.6	281.7	231.9	223.2	214.6	205.9	197.2	197.2	199.4	199.4
52.5°	364.1	316.4	268.7	221.1	212.4	203.7	195.1	186.4	188.6	190.7	192.9
55°	348.9	303.4	255.7	208.1	199.4	190.7	179.9	171.2	173.4	175.5	177.7
57.5°	342.4	294.7	247.1	199.4	190.7	179.9	171.2	160.4	160.4	160.4	160.4
60°	338.1	288.2	240.6	190.7	179.9	171.2	160.4	149.5	147.4	147.4	145.2
62.5°	335.9	286.1	238.4	188.6	175.5	164.7	151.7	138.7	136.5	134.4	132.2
65°	327.3	281.7	234.1	186.4	171.2	158.2	143.0	127.9	125.7	125.7	123.5
67.5°	325.1	277.4	231.9	184.2	169.0	151.7	136.5	119.2	117.0	114.9	112.7
70°	307.8	266.6	223.2	179.9	162.5	147.4	130.0	112.7	110.5	106.2	104.0
72.5°	286.1	249.2	210.2	171.2	153.9	136.5	119.2	101.9	99.7	97.5	93.2
75°	253.6	218.9	184.2	149.5	134.4	121.4	106.2	91.0	88.9	86.7	82.4
77.5°	208.1	179.9	153.9	125.7	114.9	104.0	93.2	82.4	80.2	78.0	73.7
80°	147.4	130.0	114.9	97.5	91.0	82.4	75.9	67.2	67.2	65.0	65.0
82.5°	97.5	88.9	80.2	71.5	67.2	62.9	58.5	54.2	54.2	52.0	52.0
85°	69.4	65.0	58.5	54.2	52.0	47.7	45.5	41.2	41.2	41.2	41.2
87.5°	32.5	32.5	30.3	30.3	28.2	28.2	26.0	23.8	23.8	23.8	23.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671895
 CATALOG NUMBER: CCP-SA-2B-840-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671895

CATALOG NUMBER: CCP-SA-2B-840-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4
2.5°	1439.1	1432.6	1426.1	1417.4	1410.9	1402.2	1391.4	1382.7	1371.9	1371.9	1369.7
5°	1161.7	1155.2	1148.7	1140.0	1133.5	1124.8	1118.3	1109.6	1101.0	1101.0	1098.8
7.5°	921.1	908.1	895.1	879.9	866.9	858.2	849.6	838.7	830.1	823.6	817.1
10°	801.9	788.9	773.7	760.7	745.5	734.7	723.9	710.9	700.0	691.4	682.7
12.5°	730.4	715.2	700.0	684.9	669.7	654.5	641.5	626.3	611.2	600.3	589.5
15°	628.5	613.3	598.2	583.0	567.8	550.5	533.1	513.6	496.3	487.6	481.1
17.5°	518.0	502.8	485.5	470.3	453.0	440.0	427.0	413.9	400.9	392.3	385.8
20°	418.3	400.9	383.6	366.3	348.9	340.3	331.6	322.9	314.3	307.8	303.4
22.5°	327.3	316.4	307.8	296.9	286.1	279.6	275.2	268.7	262.2	262.2	262.2
25°	279.6	273.1	268.7	262.2	255.7	253.6	251.4	247.1	244.9	242.7	242.7
27.5°	270.9	264.4	257.9	251.4	244.9	242.7	240.6	236.2	234.1	234.1	234.1
30°	288.2	286.1	283.9	281.7	279.6	275.2	268.7	264.4	257.9	253.6	249.2
32.5°	240.6	238.4	238.4	236.2	234.1	238.4	240.6	244.9	247.1	249.2	251.4
35°	212.4	208.1	203.7	199.4	195.1	192.9	190.7	188.6	186.4	186.4	184.2
37.5°	205.9	201.6	197.2	192.9	188.6	186.4	184.2	182.1	179.9	179.9	177.7
40°	199.4	195.1	192.9	188.6	184.2	182.1	179.9	175.5	173.4	171.2	171.2
42.5°	192.9	190.7	186.4	184.2	179.9	177.7	175.5	171.2	169.0	166.9	164.7
45°	192.9	188.6	184.2	179.9	175.5	173.4	169.0	166.9	162.5	162.5	160.4
47.5°	188.6	184.2	179.9	175.5	171.2	169.0	164.7	162.5	158.2	156.0	153.9
50°	199.4	192.9	184.2	177.7	169.0	166.9	162.5	160.4	156.0	153.9	151.7
52.5°	195.1	188.6	179.9	173.4	164.7	160.4	158.2	153.9	149.5	147.4	145.2
55°	179.9	173.4	169.0	162.5	156.0	151.7	147.4	143.0	138.7	136.5	136.5
57.5°	160.4	158.2	156.0	153.9	151.7	147.4	143.0	136.5	132.2	130.0	127.9
60°	143.0	145.2	147.4	149.5	151.7	145.2	138.7	132.2	125.7	123.5	121.4
62.5°	130.0	134.4	138.7	140.9	145.2	138.7	132.2	125.7	119.2	117.0	114.9
65°	121.4	123.5	123.5	125.7	125.7	121.4	119.2	114.9	110.5	108.4	108.4
67.5°	110.5	110.5	110.5	108.4	108.4	106.2	106.2	104.0	101.9	99.7	99.7
70°	99.7	99.7	99.7	97.5	97.5	95.4	95.4	93.2	91.0	91.0	88.9
72.5°	91.0	91.0	88.9	88.9	86.7	86.7	86.7	84.5	84.5	82.4	82.4
75°	80.2	80.2	78.0	78.0	75.9	75.9	75.9	73.7	73.7	73.7	71.5
77.5°	71.5	71.5	69.4	69.4	67.2	67.2	67.2	65.0	65.0	62.9	62.9
80°	62.9	62.9	60.7	60.7	58.5	58.5	56.3	56.3	54.2	54.2	52.0
82.5°	49.8	49.8	49.8	49.8	49.8	47.7	47.7	45.5	43.3	43.3	41.2
85°	41.2	41.2	41.2	39.0	39.0	39.0	36.8	36.8	34.7	32.5	32.5
87.5°	23.8	23.8	23.8	21.7	21.7	21.7	21.7	21.7	21.7	21.7	19.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671895
 CATALOG NUMBER: CCP-SA-2B-840-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671895
 CATALOG NUMBER: CCP-SA-2B-840-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4
2.5°	1369.7	1367.6	1358.9	1350.2	1358.9	1367.6	1367.6	1367.6	1365.4	1365.4	1365.4
5°	1098.8	1096.6	1092.3	1088.0	1088.0	1085.8	1090.1	1094.5	1098.8	1103.1	1107.5
7.5°	808.4	801.9	795.4	788.9	793.2	795.4	801.9	806.2	812.7	817.1	827.9
10°	674.0	665.4	658.9	652.4	648.0	643.7	639.3	637.2	632.8	628.5	632.8
12.5°	576.5	565.7	554.8	541.8	539.7	537.5	533.1	528.8	524.5	520.1	518.0
15°	472.5	463.8	459.5	453.0	444.3	435.6	431.3	429.1	424.8	420.5	418.3
17.5°	377.1	368.4	361.9	355.4	353.3	348.9	348.9	348.9	348.9	348.9	348.9
20°	296.9	290.4	290.4	288.2	288.2	286.1	288.2	290.4	290.4	292.6	294.7
22.5°	260.1	260.1	257.9	255.7	257.9	257.9	260.1	262.2	264.4	266.6	268.7
25°	240.6	238.4	240.6	242.7	242.7	242.7	244.9	244.9	247.1	247.1	247.1
27.5°	231.9	231.9	234.1	234.1	236.2	236.2	236.2	234.1	234.1	231.9	231.9
30°	244.9	240.6	240.6	240.6	238.4	236.2	234.1	234.1	231.9	229.7	227.6
32.5°	253.6	255.7	253.6	249.2	247.1	242.7	240.6	236.2	234.1	229.7	225.4
35°	184.2	182.1	186.4	188.6	190.7	192.9	195.1	197.2	197.2	199.4	199.4
37.5°	177.7	175.5	175.5	173.4	173.4	173.4	173.4	173.4	171.2	171.2	173.4
40°	169.0	166.9	166.9	164.7	164.7	162.5	162.5	162.5	162.5	162.5	162.5
42.5°	162.5	160.4	160.4	160.4	160.4	158.2	158.2	156.0	156.0	153.9	153.9
45°	160.4	158.2	156.0	153.9	153.9	151.7	151.7	151.7	149.5	149.5	149.5
47.5°	151.7	149.5	149.5	147.4	147.4	145.2	145.2	145.2	143.0	143.0	143.0
50°	147.4	145.2	145.2	143.0	143.0	140.9	140.9	140.9	138.7	138.7	138.7
52.5°	140.9	138.7	138.7	138.7	136.5	134.4	134.4	134.4	132.2	132.2	132.2
55°	134.4	132.2	132.2	132.2	130.0	127.9	127.9	127.9	125.7	125.7	125.7
57.5°	125.7	123.5	123.5	121.4	121.4	121.4	121.4	121.4	119.2	119.2	119.2
60°	119.2	117.0	117.0	114.9	114.9	112.7	112.7	112.7	112.7	112.7	112.7
62.5°	112.7	110.5	108.4	106.2	108.4	108.4	108.4	108.4	106.2	106.2	106.2
65°	106.2	104.0	101.9	99.7	99.7	99.7	99.7	99.7	99.7	99.7	99.7
67.5°	97.5	95.4	93.2	91.0	93.2	93.2	93.2	93.2	93.2	93.2	93.2
70°	88.9	86.7	86.7	84.5	84.5	82.4	82.4	84.5	84.5	84.5	84.5
72.5°	80.2	78.0	78.0	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9
75°	71.5	69.4	69.4	67.2	67.2	67.2	67.2	67.2	67.2	67.2	67.2
77.5°	60.7	58.5	58.5	58.5	58.5	58.5	58.5	60.7	60.7	60.7	60.7
80°	52.0	49.8	49.8	49.8	49.8	49.8	49.8	49.8	49.8	49.8	49.8
82.5°	41.2	39.0	39.0	39.0	39.0	39.0	39.0	39.0	39.0	39.0	39.0
85°	30.3	28.2	28.2	28.2	30.3	30.3	30.3	30.3	30.3	30.3	30.3
87.5°	19.5	17.3	17.3	17.3	19.5	19.5	19.5	19.5	17.3	17.3	17.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671895
 CATALOG NUMBER: CCP-SA-2B-840-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671895

CATALOG NUMBER: CCP-SA-2B-840-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4
2.5°	1365.4	1365.4	1365.4	1363.2	1361.0	1358.9	1356.7	1363.2	1367.6	1374.1	1378.4
5°	1109.6	1114.0	1116.1	1122.6	1129.2	1135.7	1142.2	1146.5	1150.8	1153.0	1157.3
7.5°	836.6	847.4	856.1	864.7	873.4	879.9	888.6	895.1	901.6	908.1	914.6
10°	635.0	639.3	641.5	650.2	656.7	665.4	671.9	678.4	684.9	689.2	695.7
12.5°	515.8	511.5	509.3	509.3	509.3	509.3	509.3	513.6	518.0	522.3	526.6
15°	416.1	413.9	411.8	409.6	407.4	403.1	400.9	405.3	409.6	413.9	418.3
17.5°	348.9	348.9	348.9	346.8	344.6	342.4	340.3	342.4	344.6	344.6	346.8
20°	299.1	301.3	303.4	305.6	305.6	307.8	307.8	309.9	312.1	312.1	314.3
22.5°	268.7	270.9	270.9	270.9	273.1	273.1	273.1	275.2	277.4	279.6	281.7
25°	244.9	244.9	242.7	242.7	244.9	244.9	244.9	244.9	247.1	247.1	247.1
27.5°	231.9	229.7	229.7	229.7	229.7	227.6	227.6	227.6	227.6	227.6	227.6
30°	225.4	223.2	221.1	218.9	218.9	216.7	214.6	214.6	214.6	214.6	214.6
32.5°	223.2	218.9	214.6	212.4	212.4	210.2	208.1	205.9	205.9	203.7	201.6
35°	199.4	197.2	197.2	195.1	192.9	190.7	188.6	188.6	188.6	186.4	186.4
37.5°	173.4	175.5	175.5	175.5	177.7	177.7	177.7	177.7	179.9	179.9	179.9
40°	162.5	162.5	162.5	164.7	166.9	166.9	169.0	169.0	171.2	171.2	171.2
42.5°	153.9	151.7	151.7	153.9	153.9	156.0	156.0	158.2	160.4	160.4	162.5
45°	149.5	147.4	147.4	147.4	147.4	145.2	145.2	147.4	149.5	151.7	153.9
47.5°	140.9	140.9	138.7	138.7	138.7	138.7	138.7	138.7	140.9	140.9	140.9
50°	136.5	136.5	134.4	134.4	134.4	134.4	134.4	134.4	134.4	134.4	134.4
52.5°	132.2	130.0	130.0	130.0	130.0	127.9	127.9	127.9	127.9	127.9	127.9
55°	125.7	123.5	123.5	123.5	123.5	123.5	123.5	123.5	125.7	125.7	125.7
57.5°	119.2	117.0	117.0	117.0	119.2	119.2	119.2	119.2	121.4	121.4	121.4
60°	112.7	112.7	112.7	112.7	112.7	112.7	112.7	114.9	114.9	117.0	117.0
62.5°	106.2	106.2	106.2	106.2	108.4	108.4	108.4	108.4	110.5	110.5	110.5
65°	99.7	99.7	99.7	99.7	101.9	101.9	101.9	101.9	101.9	101.9	101.9
67.5°	93.2	93.2	93.2	93.2	93.2	93.2	93.2	95.4	95.4	97.5	97.5
70°	84.5	82.4	82.4	84.5	84.5	86.7	86.7	88.9	88.9	91.0	91.0
72.5°	75.9	75.9	75.9	75.9	75.9	75.9	75.9	78.0	80.2	80.2	82.4
75°	67.2	67.2	67.2	67.2	69.4	69.4	69.4	71.5	71.5	73.7	73.7
77.5°	60.7	58.5	58.5	58.5	60.7	60.7	60.7	62.9	62.9	65.0	65.0
80°	49.8	49.8	49.8	49.8	52.0	52.0	52.0	52.0	54.2	54.2	54.2
82.5°	41.2	41.2	41.2	41.2	41.2	41.2	41.2	41.2	43.3	43.3	43.3
85°	30.3	30.3	30.3	30.3	32.5	32.5	32.5	32.5	32.5	32.5	32.5
87.5°	19.5	19.5	19.5	19.5	19.5	19.5	19.5	19.5	21.7	21.7	21.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671895
 CATALOG NUMBER: CCP-SA-2B-840-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671895

CATALOG NUMBER: CCP-SA-2B-840-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4
2.5°	1378.4	1378.4	1378.4	1378.4	1382.7	1384.9	1389.2	1391.4	1389.2	1387.1	1382.7
5°	1159.5	1161.7	1161.7	1163.8	1163.8	1163.8	1163.8	1163.8	1168.2	1172.5	1176.8
7.5°	916.8	918.9	921.1	923.3	923.3	923.3	921.1	921.1	923.3	923.3	925.4
10°	702.2	710.9	717.4	723.9	719.5	713.0	708.7	702.2	702.2	702.2	700.0
12.5°	531.0	533.1	537.5	539.7	537.5	537.5	535.3	533.1	535.3	539.7	541.8
15°	420.5	420.5	422.6	422.6	424.8	427.0	427.0	429.1	433.5	435.6	440.0
17.5°	348.9	351.1	351.1	353.3	353.3	355.4	355.4	355.4	359.8	364.1	370.6
20°	314.3	314.3	314.3	314.3	314.3	312.1	312.1	309.9	312.1	316.4	318.6
22.5°	281.7	283.9	283.9	283.9	281.7	279.6	275.2	273.1	273.1	275.2	275.2
25°	247.1	244.9	244.9	242.7	242.7	244.9	244.9	244.9	247.1	247.1	249.2
27.5°	227.6	225.4	225.4	223.2	223.2	225.4	225.4	225.4	225.4	225.4	225.4
30°	212.4	212.4	210.2	208.1	210.2	210.2	212.4	212.4	214.6	214.6	216.7
32.5°	201.6	199.4	199.4	197.2	199.4	199.4	201.6	201.6	203.7	205.9	205.9
35°	186.4	186.4	186.4	186.4	186.4	186.4	184.2	184.2	184.2	184.2	184.2
37.5°	177.7	177.7	175.5	173.4	173.4	173.4	173.4	173.4	171.2	169.0	166.9
40°	171.2	169.0	169.0	166.9	164.7	164.7	162.5	160.4	160.4	158.2	158.2
42.5°	162.5	160.4	160.4	158.2	156.0	156.0	153.9	151.7	151.7	151.7	149.5
45°	151.7	151.7	149.5	147.4	147.4	147.4	145.2	145.2	145.2	145.2	143.0
47.5°	140.9	140.9	138.7	138.7	138.7	138.7	136.5	136.5	136.5	136.5	136.5
50°	134.4	134.4	134.4	134.4	134.4	134.4	132.2	132.2	132.2	132.2	132.2
52.5°	127.9	127.9	127.9	127.9	127.9	127.9	127.9	127.9	127.9	127.9	127.9
55°	125.7	125.7	125.7	125.7	125.7	125.7	123.5	123.5	123.5	125.7	125.7
57.5°	121.4	121.4	119.2	119.2	119.2	119.2	119.2	119.2	119.2	119.2	119.2
60°	117.0	117.0	117.0	117.0	117.0	117.0	117.0	117.0	117.0	117.0	117.0
62.5°	110.5	110.5	110.5	110.5	110.5	112.7	112.7	112.7	112.7	112.7	110.5
65°	101.9	104.0	104.0	104.0	104.0	104.0	104.0	104.0	104.0	104.0	104.0
67.5°	97.5	97.5	97.5	97.5	97.5	97.5	97.5	97.5	97.5	97.5	97.5
70°	91.0	91.0	88.9	88.9	88.9	91.0	91.0	91.0	91.0	91.0	91.0
72.5°	82.4	82.4	82.4	82.4	82.4	82.4	82.4	82.4	82.4	84.5	84.5
75°	73.7	73.7	73.7	73.7	73.7	73.7	73.7	73.7	73.7	73.7	73.7
77.5°	65.0	65.0	62.9	62.9	62.9	65.0	65.0	65.0	65.0	67.2	67.2
80°	54.2	54.2	54.2	54.2	54.2	54.2	54.2	54.2	54.2	56.3	56.3
82.5°	43.3	43.3	43.3	43.3	43.3	43.3	43.3	43.3	43.3	45.5	45.5
85°	32.5	34.7	34.7	34.7	34.7	34.7	34.7	34.7	34.7	36.8	36.8
87.5°	21.7	21.7	21.7	21.7	21.7	21.7	19.5	19.5	19.5	19.5	17.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671895
 CATALOG NUMBER: CCP-SA-2B-840-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671895
 CATALOG NUMBER: CCP-SA-2B-840-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4
2.5°	1380.6	1382.7	1384.9	1384.9	1387.1	1389.2	1389.2	1397.9	1406.6	1410.9	1415.2
5°	1181.2	1179.0	1179.0	1176.8	1174.7	1181.2	1187.7	1200.7	1213.7	1215.8	1220.2
7.5°	925.4	927.6	929.8	929.8	931.9	925.4	916.8	918.9	921.1	931.9	940.6
10°	700.0	702.2	704.4	704.4	706.5	704.4	700.0	706.5	713.0	721.7	732.5
12.5°	544.0	550.5	557.0	561.3	567.8	572.2	574.3	583.0	589.5	600.3	611.2
15°	444.3	448.6	453.0	457.3	461.6	466.0	470.3	479.0	487.6	500.6	513.6
17.5°	374.9	374.9	377.1	377.1	377.1	381.4	385.8	390.1	392.3	405.3	418.3
20°	320.8	318.6	316.4	314.3	312.1	316.4	318.6	320.8	322.9	331.6	338.1
22.5°	275.2	275.2	277.4	277.4	277.4	275.2	270.9	273.1	273.1	277.4	283.9
25°	249.2	249.2	249.2	247.1	247.1	249.2	251.4	251.4	249.2	251.4	253.6
27.5°	225.4	227.6	227.6	229.7	229.7	231.9	231.9	231.9	231.9	234.1	236.2
30°	216.7	216.7	218.9	218.9	218.9	221.1	223.2	223.2	223.2	225.4	229.7
32.5°	208.1	210.2	212.4	214.6	216.7	218.9	218.9	221.1	221.1	223.2	225.4
35°	184.2	182.1	182.1	179.9	177.7	177.7	177.7	177.7	175.5	177.7	177.7
37.5°	164.7	164.7	164.7	162.5	162.5	164.7	164.7	164.7	164.7	166.9	166.9
40°	156.0	156.0	156.0	156.0	156.0	156.0	156.0	158.2	158.2	160.4	162.5
42.5°	149.5	149.5	149.5	149.5	149.5	151.7	151.7	151.7	151.7	153.9	153.9
45°	143.0	143.0	143.0	143.0	143.0	143.0	143.0	145.2	145.2	147.4	149.5
47.5°	136.5	136.5	136.5	136.5	136.5	138.7	140.9	140.9	140.9	143.0	143.0
50°	132.2	132.2	132.2	132.2	132.2	134.4	134.4	136.5	136.5	138.7	140.9
52.5°	127.9	127.9	127.9	127.9	127.9	130.0	130.0	132.2	132.2	134.4	136.5
55°	125.7	125.7	125.7	123.5	123.5	125.7	125.7	127.9	127.9	130.0	130.0
57.5°	119.2	119.2	119.2	119.2	119.2	119.2	119.2	121.4	121.4	123.5	125.7
60°	117.0	117.0	114.9	114.9	112.7	114.9	114.9	117.0	117.0	119.2	119.2
62.5°	110.5	110.5	110.5	108.4	108.4	110.5	110.5	110.5	110.5	112.7	114.9
65°	104.0	104.0	104.0	101.9	101.9	104.0	104.0	104.0	104.0	106.2	108.4
67.5°	97.5	97.5	97.5	95.4	95.4	95.4	95.4	97.5	97.5	99.7	101.9
70°	91.0	91.0	91.0	88.9	88.9	88.9	86.7	88.9	91.0	93.2	93.2
72.5°	84.5	84.5	84.5	82.4	82.4	82.4	80.2	82.4	82.4	84.5	84.5
75°	73.7	73.7	73.7	73.7	73.7	73.7	71.5	71.5	71.5	73.7	73.7
77.5°	67.2	67.2	67.2	65.0	65.0	65.0	62.9	62.9	62.9	65.0	65.0
80°	56.3	56.3	56.3	54.2	54.2	54.2	52.0	52.0	52.0	54.2	54.2
82.5°	45.5	45.5	45.5	43.3	43.3	43.3	41.2	41.2	41.2	43.3	43.3
85°	36.8	36.8	36.8	36.8	36.8	36.8	34.7	34.7	34.7	36.8	39.0
87.5°	17.3	17.3	19.5	19.5	19.5	19.5	17.3	17.3	15.2	15.2	17.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671895
 CATALOG NUMBER: CCP-SA-2B-840-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671895
 CATALOG NUMBER: CCP-SA-2B-840-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4
2.5°	1419.6	1423.9	1434.7	1443.4	1454.2	1462.9	1469.4	1478.1	1484.6	1491.1	1495.4
5°	1222.3	1224.5	1235.3	1246.2	1254.9	1265.7	1280.9	1296.0	1311.2	1326.4	1337.2
7.5°	951.4	960.1	973.1	988.3	1001.3	1014.3	1029.5	1046.8	1062.0	1077.1	1092.3
10°	741.2	749.9	762.9	775.9	786.7	799.7	817.1	834.4	851.7	869.1	886.4
12.5°	622.0	632.8	648.0	663.2	676.2	691.4	713.0	732.5	754.2	773.7	795.4
15°	524.5	537.5	557.0	578.7	598.2	617.7	639.3	661.0	680.5	702.2	723.9
17.5°	431.3	444.3	461.6	481.1	498.5	515.8	541.8	565.7	591.7	615.5	639.3
20°	346.8	353.3	370.6	387.9	405.3	422.6	442.1	461.6	481.1	500.6	531.0
22.5°	288.2	292.6	301.3	307.8	316.4	322.9	342.4	361.9	379.3	398.8	427.0
25°	253.6	255.7	262.2	266.6	273.1	277.4	290.4	301.3	314.3	325.1	351.1
27.5°	236.2	238.4	240.6	242.7	244.9	247.1	255.7	264.4	270.9	279.6	303.4
30°	231.9	234.1	240.6	244.9	251.4	255.7	260.1	264.4	268.7	273.1	288.2
32.5°	227.6	229.7	229.7	227.6	227.6	225.4	229.7	231.9	236.2	238.4	251.4
35°	179.9	179.9	182.1	184.2	186.4	188.6	195.1	199.4	205.9	210.2	221.1
37.5°	169.0	169.0	171.2	175.5	177.7	179.9	184.2	188.6	192.9	197.2	208.1
40°	162.5	164.7	166.9	169.0	171.2	173.4	177.7	179.9	184.2	186.4	195.1
42.5°	156.0	156.0	158.2	162.5	164.7	166.9	171.2	173.4	177.7	179.9	188.6
45°	151.7	153.9	156.0	158.2	158.2	160.4	164.7	169.0	171.2	175.5	184.2
47.5°	145.2	145.2	149.5	151.7	156.0	158.2	162.5	164.7	169.0	171.2	179.9
50°	140.9	143.0	147.4	149.5	153.9	156.0	162.5	166.9	173.4	177.7	182.1
52.5°	136.5	138.7	143.0	145.2	149.5	151.7	160.4	169.0	175.5	184.2	184.2
55°	132.2	132.2	136.5	143.0	147.4	151.7	156.0	162.5	166.9	171.2	171.2
57.5°	125.7	127.9	132.2	138.7	143.0	147.4	151.7	156.0	158.2	162.5	160.4
60°	121.4	121.4	127.9	134.4	140.9	147.4	147.4	147.4	145.2	145.2	145.2
62.5°	114.9	117.0	125.7	136.5	145.2	153.9	147.4	140.9	134.4	127.9	130.0
65°	110.5	112.7	117.0	123.5	127.9	132.2	127.9	125.7	121.4	117.0	119.2
67.5°	101.9	104.0	106.2	106.2	108.4	108.4	108.4	108.4	108.4	108.4	110.5
70°	95.4	95.4	95.4	97.5	97.5	97.5	97.5	97.5	97.5	97.5	99.7
72.5°	86.7	86.7	86.7	86.7	86.7	86.7	86.7	86.7	86.7	86.7	88.9
75°	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9	75.9	78.0
77.5°	67.2	67.2	67.2	67.2	67.2	67.2	67.2	67.2	65.0	65.0	67.2
80°	56.3	56.3	56.3	56.3	54.2	54.2	54.2	54.2	54.2	54.2	56.3
82.5°	45.5	45.5	45.5	45.5	43.3	43.3	43.3	43.3	41.2	41.2	43.3
85°	41.2	43.3	43.3	45.5	45.5	45.5	43.3	41.2	39.0	36.8	36.8
87.5°	17.3	17.3	17.3	17.3	15.2	15.2	15.2	15.2	15.2	15.2	15.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671895
 CATALOG NUMBER: CCP-SA-2B-840-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671895

CATALOG NUMBER: CCP-SA-2B-840-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4
2.5°	1501.9	1506.3	1510.6	1517.1	1525.8	1532.3	1538.8	1551.8	1566.9	1579.9	1592.9
5°	1348.0	1358.9	1369.7	1382.7	1395.7	1406.6	1419.6	1445.6	1471.6	1495.4	1521.4
7.5°	1105.3	1120.5	1133.5	1155.2	1174.7	1196.3	1215.8	1248.4	1278.7	1311.2	1341.5
10°	903.8	921.1	938.4	966.6	996.9	1025.1	1053.3	1079.3	1107.5	1133.5	1159.5
12.5°	817.1	836.6	858.2	875.6	895.1	912.4	929.8	960.1	990.4	1020.8	1051.1
15°	745.5	767.2	788.9	810.6	830.1	851.7	871.2	897.3	925.4	951.4	977.4
17.5°	663.2	684.9	708.7	732.5	756.4	780.2	804.1	840.9	877.7	912.4	949.3
20°	559.2	589.5	617.7	650.2	682.7	715.2	747.7	786.7	825.7	862.6	901.6
22.5°	455.1	483.3	511.5	550.5	589.5	626.3	665.4	717.4	767.2	819.2	869.1
25°	379.3	405.3	431.3	474.6	515.8	559.2	600.3	663.2	723.9	786.7	847.4
27.5°	327.3	351.1	374.9	420.5	466.0	509.3	554.8	624.2	691.4	760.7	827.9
30°	303.4	318.6	333.8	377.1	420.5	461.6	505.0	572.2	639.3	706.5	773.7
32.5°	264.4	277.4	290.4	329.4	368.4	405.3	444.3	513.6	580.8	650.2	717.4
35°	234.1	244.9	255.7	292.6	327.3	364.1	398.8	468.1	537.5	606.8	676.2
37.5°	216.7	227.6	236.2	268.7	303.4	335.9	368.4	437.8	505.0	574.3	641.5
40°	203.7	210.2	218.9	251.4	281.7	314.3	344.6	407.4	472.5	535.3	598.2
42.5°	195.1	203.7	210.2	238.4	268.7	296.9	325.1	385.8	446.5	505.0	565.7
45°	192.9	201.6	210.2	234.1	257.9	279.6	303.4	361.9	420.5	479.0	537.5
47.5°	188.6	195.1	203.7	223.2	240.6	260.1	277.4	335.9	394.4	450.8	509.3
50°	186.4	188.6	192.9	210.2	227.6	244.9	262.2	320.8	379.3	437.8	496.3
52.5°	184.2	184.2	184.2	199.4	214.6	227.6	242.7	301.3	361.9	420.5	479.0
55°	171.2	169.0	169.0	184.2	197.2	212.4	225.4	283.9	342.4	398.8	457.3
57.5°	158.2	156.0	153.9	166.9	179.9	192.9	205.9	264.4	325.1	383.6	442.1
60°	145.2	143.0	143.0	156.0	166.9	179.9	190.7	251.4	309.9	370.6	429.1
62.5°	130.0	132.2	132.2	143.0	156.0	166.9	177.7	238.4	301.3	361.9	422.6
65°	119.2	121.4	121.4	134.4	147.4	160.4	173.4	231.9	292.6	351.1	409.6
67.5°	110.5	112.7	112.7	127.9	140.9	156.0	169.0	221.1	275.2	327.3	379.3
70°	101.9	101.9	104.0	119.2	134.4	149.5	164.7	210.2	255.7	299.1	344.6
72.5°	91.0	93.2	95.4	110.5	123.5	138.7	151.7	192.9	234.1	275.2	316.4
75°	80.2	82.4	84.5	97.5	110.5	123.5	136.5	175.5	212.4	251.4	288.2
77.5°	71.5	73.7	75.9	86.7	97.5	108.4	119.2	147.4	177.7	205.9	234.1
80°	58.5	58.5	60.7	69.4	78.0	84.5	93.2	112.7	132.2	149.5	169.0
82.5°	43.3	45.5	45.5	52.0	56.3	62.9	67.2	78.0	86.7	97.5	106.2
85°	36.8	34.7	34.7	39.0	41.2	45.5	47.7	54.2	58.5	65.0	69.4
87.5°	15.2	13.0	13.0	15.2	19.5	21.7	23.8	23.8	26.0	26.0	26.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671895
 CATALOG NUMBER: CCP-SA-2B-840-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671895

CATALOG NUMBER: CCP-SA-2B-840-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4
2.5°	1599.4	1603.8	1610.3	1614.6	1625.5	1634.1	1645.0	1653.6	1660.1	1671.0	1666.6
5°	1540.9	1560.4	1579.9	1599.4	1614.6	1629.8	1642.8	1658.0	1675.3	1707.8	1716.5
7.5°	1367.6	1393.6	1417.4	1443.4	1473.7	1504.1	1534.4	1564.8	1592.9	1634.1	1660.1
10°	1196.3	1233.2	1267.9	1304.7	1332.9	1361.0	1387.1	1415.2	1454.2	1495.4	1543.1
12.5°	1088.0	1124.8	1161.7	1198.5	1239.7	1278.7	1319.9	1358.9	1395.7	1428.2	1482.4
15°	1016.5	1057.6	1096.6	1135.7	1185.5	1233.2	1283.0	1330.7	1384.9	1428.2	1465.1
17.5°	999.1	1049.0	1096.6	1146.5	1198.5	1250.5	1302.5	1354.5	1408.7	1473.7	1521.4
20°	968.8	1036.0	1103.1	1170.3	1237.5	1302.5	1369.7	1434.7	1506.3	1584.3	1606.0
22.5°	951.4	1031.6	1114.0	1194.2	1285.2	1378.4	1469.4	1560.4	1636.3	1694.8	1759.8
25°	949.3	1049.0	1150.8	1250.5	1365.4	1478.1	1592.9	1705.6	1803.2	1861.7	1913.7
27.5°	947.1	1068.5	1187.7	1306.9	1447.7	1586.4	1727.3	1866.0	1957.1	2041.6	2084.9
30°	921.1	1066.3	1213.7	1358.9	1517.1	1675.3	1833.5	1991.7	2084.9	2143.4	2165.1
32.5°	888.6	1059.8	1231.0	1402.2	1582.1	1762.0	1939.7	2119.6	2193.3	2243.1	2225.8
35°	862.6	1051.1	1237.5	1423.9	1614.6	1807.5	1998.2	2188.9	2295.1	2364.5	2336.3
37.5°	838.7	1036.0	1233.2	1430.4	1653.6	1876.9	2100.1	2323.3	2425.2	2498.9	2466.4
40°	810.6	1020.8	1233.2	1443.4	1699.1	1952.7	2208.5	2462.0	2594.2	2657.1	2607.2
42.5°	786.7	1005.6	1226.7	1445.6	1718.7	1991.7	2264.8	2537.9	2685.3	2774.1	2711.3
45°	756.4	975.3	1192.0	1410.9	1712.1	2013.4	2312.5	2613.7	2785.0	2854.3	2767.6
47.5°	723.9	940.6	1155.2	1369.7	1690.5	2011.2	2332.0	2652.7	2811.0	2893.3	2813.1
50°	713.0	929.8	1144.3	1361.0	1707.8	2056.7	2403.5	2750.3	2865.1	2932.3	2826.1
52.5°	710.9	940.6	1172.5	1402.2	1751.2	2097.9	2446.9	2793.6	2886.8	2958.3	2863.0
55°	704.4	953.6	1200.7	1447.7	1811.8	2178.1	2542.2	2906.3	2999.5	3051.5	2980.0
57.5°	710.9	979.6	1246.2	1514.9	1889.9	2264.8	2639.7	3014.7	3127.4	3164.2	3149.1
60°	715.2	1001.3	1285.2	1571.3	1937.5	2303.8	2670.1	3036.4	3153.4	3244.4	3261.8
62.5°	704.4	986.1	1265.7	1547.4	1879.0	2210.6	2542.2	2873.8	3066.7	3201.1	3279.1
65°	671.9	931.9	1194.2	1454.2	1759.8	2067.6	2373.2	2678.8	2882.5	3081.9	3144.7
67.5°	600.3	821.4	1042.5	1263.5	1530.1	1796.7	2061.1	2327.7	2583.4	2776.3	2863.0
70°	520.1	693.5	869.1	1042.5	1285.2	1527.9	1770.7	2013.4	2238.8	2451.2	2533.5
72.5°	453.0	587.3	723.9	858.2	1031.6	1202.8	1376.2	1547.4	1814.0	2026.4	2106.6
75°	385.8	483.3	578.7	676.2	795.4	914.6	1031.6	1150.8	1339.4	1530.1	1610.3
77.5°	296.9	361.9	424.8	487.6	570.0	650.2	732.5	812.7	944.9	1088.0	1129.2
80°	205.9	242.7	277.4	314.3	379.3	444.3	509.3	574.3	661.0	741.2	804.1
82.5°	127.9	151.7	173.4	195.1	247.1	299.1	348.9	400.9	435.6	440.0	502.8
85°	82.4	97.5	110.5	123.5	153.9	186.4	216.7	247.1	221.1	205.9	244.9
87.5°	32.5	41.2	47.7	54.2	52.0	49.8	47.7	45.5	39.0	34.7	43.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671895
 CATALOG NUMBER: CCP-SA-2B-840-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671895

CATALOG NUMBER: CCP-SA-2B-840-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4
2.5°	1671.0	1677.5	1684.0	1688.3	1694.8	1697.0	1699.1	1699.1	1701.3	1703.5	1707.8
5°	1751.2	1764.2	1777.2	1788.0	1801.0	1811.8	1820.5	1831.3	1840.0	1840.0	1837.9
7.5°	1684.0	1716.5	1749.0	1781.5	1814.0	1837.9	1859.5	1883.4	1905.0	1909.4	1913.7
10°	1595.1	1629.8	1662.3	1697.0	1729.5	1766.3	1801.0	1835.7	1872.5	1879.0	1887.7
12.5°	1512.8	1553.9	1595.1	1634.1	1675.3	1701.3	1727.3	1751.2	1777.2	1794.5	1811.8
15°	1510.6	1545.3	1579.9	1612.5	1647.1	1662.3	1677.5	1690.5	1705.6	1705.6	1707.8
17.5°	1560.4	1582.1	1603.8	1623.3	1645.0	1647.1	1651.5	1653.6	1655.8	1649.3	1642.8
20°	1658.0	1666.6	1675.3	1684.0	1692.6	1677.5	1664.5	1649.3	1634.1	1616.8	1601.6
22.5°	1801.0	1781.5	1762.0	1742.5	1723.0	1697.0	1668.8	1642.8	1614.6	1592.9	1571.3
25°	1935.4	1911.5	1887.7	1863.9	1840.0	1783.7	1727.3	1668.8	1612.5	1588.6	1564.8
27.5°	2115.3	2078.4	2041.6	2004.7	1967.9	1892.0	1816.2	1740.3	1664.5	1623.3	1584.3
30°	2158.6	2117.4	2076.3	2032.9	1991.7	1918.0	1846.5	1772.8	1699.1	1651.5	1606.0
32.5°	2221.5	2173.8	2126.1	2078.4	2030.7	1959.2	1887.7	1814.0	1742.5	1699.1	1653.6
35°	2325.5	2271.3	2217.1	2160.8	2106.6	2032.9	1961.4	1887.7	1814.0	1764.2	1716.5
37.5°	2414.3	2351.5	2288.6	2225.8	2162.9	2097.9	2030.7	1965.7	1898.5	1848.7	1801.0
40°	2514.0	2444.7	2375.3	2308.1	2238.8	2178.1	2117.4	2054.6	1993.9	1954.9	1915.9
42.5°	2600.7	2516.2	2433.9	2351.5	2267.0	2225.8	2186.8	2145.6	2104.4	2084.9	2063.2
45°	2661.4	2583.4	2503.2	2425.2	2347.2	2316.8	2286.5	2256.1	2225.8	2245.3	2264.8
47.5°	2687.4	2624.6	2563.9	2503.2	2440.4	2451.2	2462.0	2470.7	2481.5	2507.5	2535.7
50°	2711.3	2676.6	2639.7	2605.1	2568.2	2609.4	2648.4	2689.6	2730.8	2785.0	2839.1
52.5°	2758.9	2739.4	2722.1	2702.6	2683.1	2754.6	2826.1	2897.6	2969.2	3029.9	3090.5
55°	2902.0	2886.8	2871.6	2854.3	2839.1	2941.0	3040.7	3142.6	3244.4	3307.3	3370.1
57.5°	3099.2	3090.5	3079.7	3071.0	3060.2	3159.9	3257.4	3354.9	3454.6	3515.3	3578.2
60°	3248.7	3250.9	3250.9	3253.1	3253.1	3328.9	3404.8	3482.8	3558.7	3610.7	3664.9
62.5°	3328.9	3324.6	3320.3	3315.9	3311.6	3374.4	3437.3	3500.2	3563.0	3602.0	3641.0
65°	3242.2	3266.1	3289.9	3313.8	3337.6	3346.3	3352.8	3361.4	3367.9	3391.8	3415.6
67.5°	2951.8	2999.5	3045.0	3092.7	3138.2	3105.7	3075.4	3042.9	3010.3	3016.8	3021.2
70°	2628.9	2683.1	2739.4	2793.6	2847.8	2771.9	2696.1	2618.1	2542.2	2516.2	2490.2
72.5°	2217.1	2264.8	2314.7	2362.3	2410.0	2316.8	2225.8	2132.6	2039.4	1993.9	1948.4
75°	1694.8	1751.2	1809.7	1866.0	1922.4	1818.3	1712.1	1608.1	1501.9	1471.6	1443.4
77.5°	1235.3	1302.5	1369.7	1436.9	1504.1	1410.9	1317.7	1222.3	1129.2	1111.8	1094.5
80°	899.4	951.4	1001.3	1053.3	1103.1	1049.0	994.8	940.6	886.4	884.2	882.1
82.5°	606.8	652.4	695.7	741.2	784.6	762.9	743.4	721.7	700.0	721.7	745.5
85°	312.1	374.9	440.0	502.8	565.7	559.2	554.8	548.3	541.8	570.0	596.0
87.5°	62.9	117.0	171.2	223.2	277.4	264.4	251.4	236.2	223.2	231.9	238.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671895
 CATALOG NUMBER: CCP-SA-2B-840-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671895

CATALOG NUMBER: CCP-SA-2B-840-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4
2.5°	1710.0	1712.1	1712.1	1712.1	1712.1	1712.1	1707.8	1705.6	1701.3	1697.0	1690.5
5°	1837.9	1835.7	1827.0	1818.3	1807.5	1798.8	1792.3	1783.7	1777.2	1768.5	1755.5
7.5°	1918.0	1922.4	1907.2	1894.2	1879.0	1863.9	1848.7	1833.5	1818.3	1803.2	1772.8
10°	1894.2	1900.7	1892.0	1883.4	1872.5	1863.9	1846.5	1827.0	1809.7	1790.2	1753.3
12.5°	1827.0	1844.4	1840.0	1835.7	1831.3	1827.0	1816.2	1803.2	1792.3	1779.3	1738.2
15°	1707.8	1707.8	1710.0	1712.1	1712.1	1714.3	1716.5	1718.7	1720.8	1723.0	1699.1
17.5°	1636.3	1629.8	1629.8	1629.8	1629.8	1629.8	1638.5	1649.3	1658.0	1666.6	1660.1
20°	1584.3	1569.1	1566.9	1566.9	1564.8	1562.6	1577.8	1595.1	1610.3	1625.5	1634.1
22.5°	1549.6	1527.9	1525.8	1523.6	1521.4	1519.3	1538.8	1558.3	1577.8	1597.3	1627.6
25°	1540.9	1517.1	1519.3	1521.4	1521.4	1523.6	1538.8	1553.9	1569.1	1584.3	1636.3
27.5°	1543.1	1504.1	1506.3	1508.4	1508.4	1510.6	1534.4	1556.1	1579.9	1601.6	1666.6
30°	1558.3	1512.8	1508.4	1504.1	1499.8	1495.4	1527.9	1560.4	1592.9	1625.5	1675.3
32.5°	1610.3	1566.9	1556.1	1545.3	1534.4	1523.6	1562.6	1599.4	1638.5	1675.3	1716.5
35°	1666.6	1619.0	1614.6	1610.3	1603.8	1599.4	1634.1	1671.0	1705.6	1740.3	1777.2
37.5°	1751.2	1703.5	1699.1	1692.6	1688.3	1681.8	1720.8	1757.7	1796.7	1833.5	1866.0
40°	1876.9	1837.9	1835.7	1835.7	1833.5	1831.3	1861.7	1894.2	1924.5	1954.9	1976.6
42.5°	2043.7	2024.2	2030.7	2039.4	2045.9	2052.4	2076.3	2102.3	2126.1	2149.9	2143.4
45°	2284.3	2303.8	2306.0	2308.1	2310.3	2312.5	2319.0	2327.7	2334.2	2340.7	2314.7
47.5°	2561.7	2587.7	2600.7	2613.7	2624.6	2637.6	2628.9	2618.1	2609.4	2598.6	2533.5
50°	2891.1	2945.3	2943.2	2941.0	2936.7	2934.5	2917.2	2899.8	2880.3	2863.0	2767.6
52.5°	3151.2	3211.9	3222.7	3233.6	3244.4	3255.2	3222.7	3190.2	3155.6	3123.0	3003.8
55°	3430.8	3493.6	3495.8	3498.0	3498.0	3500.2	3454.6	3409.1	3361.4	3315.9	3192.4
57.5°	3638.9	3699.5	3693.0	3688.7	3682.2	3675.7	3621.5	3567.3	3513.2	3459.0	3335.4
60°	3716.9	3768.9	3755.9	3742.9	3727.7	3714.7	3673.5	3632.4	3589.0	3547.8	3428.6
62.5°	3680.0	3719.0	3699.5	3682.2	3662.7	3643.2	3591.2	3537.0	3485.0	3430.8	3344.1
65°	3437.3	3461.1	3435.1	3411.3	3387.5	3361.4	3318.1	3274.8	3229.2	3185.9	3127.4
67.5°	3027.7	3032.0	3029.9	3027.7	3025.5	3023.4	2960.5	2897.6	2832.6	2769.8	2765.4
70°	2466.4	2440.4	2444.7	2451.2	2455.5	2459.9	2412.2	2366.7	2319.0	2271.3	2293.0
72.5°	1902.9	1857.4	1868.2	1881.2	1892.0	1902.9	1863.9	1827.0	1788.0	1749.0	1779.3
75°	1413.1	1384.9	1395.7	1408.7	1419.6	1430.4	1415.2	1400.1	1382.7	1367.6	1395.7
77.5°	1077.1	1059.8	1062.0	1062.0	1064.1	1064.1	1066.3	1070.6	1072.8	1075.0	1105.3
80°	877.7	875.6	873.4	871.2	866.9	864.7	886.4	908.1	929.8	951.4	966.6
82.5°	767.2	788.9	775.9	765.0	752.0	739.0	758.5	778.1	797.6	817.1	810.6
85°	624.2	650.2	626.3	602.5	576.5	552.7	570.0	585.2	602.5	617.7	609.0
87.5°	247.1	253.6	214.6	177.7	138.7	99.7	158.2	214.6	273.1	329.4	338.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671895
 CATALOG NUMBER: CCP-SA-2B-840-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671895

CATALOG NUMBER: CCP-SA-2B-840-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4	1560.4
2.5°	1684.0	1675.3	1668.8	1666.6	1662.3	1660.1	1655.8	1651.5	1645.0	1640.6	1634.1
5°	1740.3	1727.3	1712.1	1690.5	1671.0	1649.3	1627.6	1608.1	1588.6	1566.9	1547.4
7.5°	1742.5	1712.1	1681.8	1653.6	1623.3	1595.1	1564.8	1538.8	1510.6	1482.4	1456.4
10°	1718.7	1681.8	1645.0	1608.1	1573.4	1536.6	1499.8	1469.4	1436.9	1404.4	1374.1
12.5°	1699.1	1658.0	1616.8	1573.4	1532.3	1488.9	1445.6	1415.2	1384.9	1354.5	1324.2
15°	1675.3	1649.3	1625.5	1586.4	1547.4	1508.4	1469.4	1428.2	1389.2	1348.0	1306.9
17.5°	1655.8	1649.3	1642.8	1616.8	1590.8	1562.6	1536.6	1495.4	1454.2	1410.9	1369.7
20°	1645.0	1653.6	1662.3	1649.3	1636.3	1621.1	1608.1	1577.8	1547.4	1514.9	1484.6
22.5°	1658.0	1690.5	1720.8	1723.0	1727.3	1729.5	1731.7	1703.5	1675.3	1645.0	1616.8
25°	1688.3	1740.3	1792.3	1820.5	1848.7	1879.0	1907.2	1889.9	1872.5	1855.2	1837.9
27.5°	1729.5	1794.5	1859.5	1900.7	1939.7	1980.9	2022.1	2019.9	2017.7	2013.4	2011.2
30°	1723.0	1772.8	1822.7	1872.5	1922.4	1972.2	2022.1	2048.1	2071.9	2097.9	2123.9
32.5°	1759.8	1801.0	1844.4	1896.4	1948.4	2002.6	2054.6	2108.8	2160.8	2215.0	2269.1
35°	1816.2	1853.0	1892.0	1948.4	2006.9	2063.2	2121.8	2186.8	2254.0	2321.2	2386.2
37.5°	1900.7	1933.2	1967.9	2015.6	2065.4	2113.1	2162.9	2258.3	2353.7	2451.2	2546.5
40°	1998.2	2019.9	2041.6	2087.1	2132.6	2178.1	2223.6	2342.8	2462.0	2581.2	2700.4
42.5°	2139.1	2132.6	2126.1	2162.9	2202.0	2238.8	2277.8	2386.2	2494.5	2602.9	2711.3
45°	2288.6	2262.6	2236.6	2254.0	2273.5	2290.8	2310.3	2420.8	2531.4	2644.1	2754.6
47.5°	2468.5	2403.5	2338.5	2323.3	2308.1	2290.8	2275.6	2394.8	2514.0	2635.4	2754.6
50°	2672.3	2574.7	2479.4	2440.4	2399.2	2360.2	2319.0	2416.5	2516.2	2615.9	2713.4
52.5°	2884.6	2763.3	2644.1	2583.4	2522.7	2459.9	2399.2	2481.5	2566.1	2650.6	2732.9
55°	3066.7	2943.2	2817.5	2745.9	2674.4	2602.9	2531.4	2613.7	2696.1	2778.4	2860.8
57.5°	3211.9	3088.4	2964.8	2897.6	2828.3	2761.1	2691.8	2769.8	2850.0	2930.2	3008.2
60°	3311.6	3192.4	3073.2	3008.2	2943.2	2878.1	2813.1	2906.3	2999.5	3094.9	3188.1
62.5°	3259.6	3172.9	3086.2	3058.0	3029.9	2999.5	2971.3	3060.2	3146.9	3235.7	3324.6
65°	3068.9	3010.3	2951.8	2980.0	3010.3	3038.5	3068.9	3127.4	3185.9	3246.6	3305.1
67.5°	2758.9	2754.6	2748.1	2811.0	2873.8	2938.8	3001.7	3040.7	3077.5	3116.5	3155.6
70°	2314.7	2338.5	2360.2	2468.5	2576.9	2685.3	2793.6	2808.8	2824.0	2839.1	2854.3
72.5°	1811.8	1842.2	1874.7	2017.7	2158.6	2301.6	2444.7	2436.0	2427.3	2416.5	2407.8
75°	1426.1	1454.2	1484.6	1616.8	1749.0	1881.2	2013.4	1976.6	1941.9	1905.0	1868.2
77.5°	1137.8	1168.2	1200.7	1324.2	1447.7	1573.4	1697.0	1608.1	1519.3	1430.4	1341.5
80°	979.6	994.8	1007.8	1092.3	1174.7	1259.2	1343.7	1252.7	1159.5	1066.3	975.3
82.5°	804.1	795.4	788.9	838.7	888.6	938.4	988.3	901.6	814.9	726.0	639.3
85°	600.3	591.7	583.0	609.0	635.0	663.2	689.2	589.5	489.8	387.9	288.2
87.5°	348.9	357.6	366.3	394.4	422.6	453.0	481.1	379.3	277.4	173.4	71.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671895
 CATALOG NUMBER: CCP-SA-2B-840-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671895
CATALOG NUMBER: CCP-SA-2B-840-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1560.4	1560.4
2.5°	1621.1	1610.3
5°	1532.3	1517.1
7.5°	1434.7	1415.2
10°	1345.9	1319.9
12.5°	1289.5	1257.0
15°	1267.9	1228.8
17.5°	1332.9	1296.0
20°	1432.6	1382.7
22.5°	1553.9	1493.3
25°	1764.2	1690.5
27.5°	1935.4	1859.5
30°	2041.6	1959.2
32.5°	2158.6	2050.2
35°	2280.0	2175.9
37.5°	2427.3	2310.3
40°	2579.1	2457.7
42.5°	2631.1	2553.1
45°	2680.9	2607.2
47.5°	2691.8	2631.1
50°	2702.6	2693.9
52.5°	2732.9	2730.8
55°	2863.0	2865.1
57.5°	3023.4	3036.4
60°	3170.7	3155.6
62.5°	3246.6	3168.6
65°	3194.6	3086.2
67.5°	3038.5	2921.5
70°	2696.1	2537.9
72.5°	2269.1	2130.4
75°	1749.0	1632.0
77.5°	1244.0	1146.5
80°	875.6	778.1
82.5°	561.3	483.3
85°	253.6	221.1
87.5°	71.5	69.4
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P671895
CATALOG NUMBER: CCP-SA-2B-840-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)