

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P675959

Luminaire Tested: **CCW-SA-2A-727-U-SLR**

Issue Date: 04/25/2023



Test Information

Test Method: LM-79-08
Report Number: P675959
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-2A-727-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @350mA w/
SLR distribution lens
Light Source: (32) 2700K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3797.4 lumens
Efficiency: N/A
Efficacy: 104.9 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2

Input Watts (W): 36.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P675959
 CATALOG NUMBER: CCW-SA-2A-727-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 5.4 fc
 Type IV - Short - N/A

REPORT NUMBER: P675959
CATALOG NUMBER: CCW-SA-2A-727-U-SLR

Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P675959

CATALOG NUMBER: CCW-SA-2A-727-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	781.3	0.0	781.3
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	3016.1	0.0	3016.1
	% Fixture	79.4	0.0	79.4
Total	Lumens	3797.4	0.0	3797.4
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.2	2.5
10°-20°	198.9	5.2
20°-30°	291.1	7.7
30°-40°	410.1	10.8
40°-50°	563.5	14.8
50°-60°	768.0	20.2
60°-70°	840.6	22.1
70°-80°	485.5	12.8
80°-90°	145.5	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3797.4	100.0
0°-180°	3797.4	100.0




REPORT NUMBER: P675959
 CATALOG NUMBER: CCW-SA-2A-727-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	390.0	10.3			
FM (30°-60°)	1385.8	36.5			
FH (60°-80°)	1116.7	29.4			G1/1800
FVH (80°-90°)	123.6	3.3			G2/225
BL (0°-30°)	194.2	5.1	B1/500		
BM (30°-60°)	355.8	9.4	B1/1000		
BH (60°-80°)	209.4	5.5	B1/500		G1/500
BVH (80°-90°)	21.9	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P675959

CATALOG NUMBER: CCW-SA-2A-727-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7
2.5°	1251.4	1244.7	1239.6	1234.6	1227.8	1222.8	1216.0	1209.3	1200.9	1194.1	1185.7
5°	1179.0	1158.8	1138.6	1126.8	1113.3	1101.5	1088.0	1072.9	1057.7	1040.9	1025.7
7.5°	1099.8	1074.6	1049.3	1029.1	1007.2	987.0	965.1	946.6	928.0	909.5	891.0
10°	1025.7	1002.1	978.6	953.3	926.3	901.1	874.1	848.9	823.6	798.3	773.1
12.5°	976.9	948.2	921.3	892.7	865.7	837.1	808.4	784.9	761.3	736.0	712.4
15°	955.0	928.0	902.8	874.1	845.5	816.9	788.2	761.3	736.0	709.1	682.1
17.5°	1007.2	968.4	929.7	892.7	855.6	818.5	781.5	747.8	714.1	680.4	646.8
20°	1074.6	1025.7	978.6	933.1	885.9	840.4	793.3	746.1	699.0	651.8	604.6
22.5°	1160.5	1104.9	1051.0	992.0	931.4	872.4	811.8	752.9	693.9	633.3	574.3
25°	1313.7	1248.0	1182.3	1098.1	1012.2	928.0	842.1	764.7	688.9	611.4	533.9
27.5°	1445.1	1355.8	1268.2	1167.2	1066.1	965.1	864.0	774.8	687.2	597.9	508.6
30°	1522.6	1435.0	1347.4	1224.5	1103.2	980.2	857.3	757.9	660.2	560.9	461.5
32.5°	1593.3	1495.6	1397.9	1263.2	1126.8	992.0	855.6	746.1	638.3	528.9	419.4
35°	1691.0	1583.2	1477.1	1320.5	1163.8	1007.2	850.5	737.7	623.2	510.3	395.8
37.5°	1795.4	1662.4	1531.0	1357.5	1184.0	1010.6	837.1	725.9	614.8	503.6	392.4
40°	1909.9	1748.3	1588.3	1396.2	1205.9	1013.9	821.9	710.8	599.6	486.8	375.6
42.5°	1984.1	1808.9	1633.7	1426.6	1221.1	1013.9	806.8	697.3	587.8	476.6	367.2
45°	2026.2	1856.1	1687.6	1463.6	1239.6	1015.6	791.6	683.8	576.0	466.5	358.7
47.5°	2044.7	1886.4	1728.0	1492.3	1258.1	1022.3	786.5	677.1	565.9	456.4	345.3
50°	2093.5	1953.7	1813.9	1561.3	1310.4	1057.7	805.1	687.2	571.0	453.1	335.2
52.5°	2122.2	2002.6	1883.0	1623.6	1364.2	1104.9	845.5	714.1	582.8	451.4	320.0
55°	2226.6	2112.1	1997.5	1721.3	1443.4	1167.2	889.3	744.4	599.6	453.1	308.2
57.5°	2359.6	2238.4	2118.8	1820.7	1522.6	1224.5	926.3	771.4	614.8	459.8	303.2
60°	2452.3	2334.4	2218.2	1901.5	1583.2	1266.6	948.2	786.5	624.9	461.5	299.8
62.5°	2462.4	2310.8	2160.9	1852.7	1544.5	1234.6	926.3	769.7	613.1	454.7	298.1
65°	2398.4	2221.5	2044.7	1749.9	1455.2	1160.5	865.7	722.5	579.4	434.5	291.4
67.5°	2270.4	2063.2	1856.1	1586.6	1317.1	1047.6	778.1	655.2	533.9	411.0	288.0
70°	1972.3	1790.4	1610.1	1376.0	1143.6	909.5	675.4	574.3	475.0	373.9	272.8
72.5°	1655.6	1485.5	1317.1	1126.8	938.1	747.8	557.5	481.7	405.9	328.4	252.6
75°	1268.2	1140.2	1013.9	872.4	731.0	587.8	446.3	390.7	335.2	279.6	224.0
77.5°	891.0	821.9	754.5	648.4	542.3	436.2	330.1	293.1	256.0	219.0	181.9
80°	604.6	565.9	528.9	453.1	377.3	299.8	224.0	200.4	175.2	151.6	126.3
82.5°	375.6	373.9	370.5	318.3	266.1	213.9	161.7	141.5	123.0	102.7	82.5
85°	171.8	200.4	227.4	198.7	170.1	141.5	112.8	99.4	85.9	70.7	57.3
87.5°	53.9	65.7	75.8	72.4	67.4	64.0	58.9	50.5	42.1	33.7	25.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675959
 CATALOG NUMBER: CCW-SA-2A-727-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675959

CATALOG NUMBER: CCW-SA-2A-727-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7
2.5°	1179.0	1173.9	1167.2	1160.5	1152.0	1145.3	1136.9	1128.5	1126.8	1123.4	1121.7
5°	1015.6	1005.5	993.7	983.6	973.5	961.7	951.6	939.8	931.4	921.3	912.9
7.5°	872.4	855.6	837.1	818.5	801.7	784.9	766.3	749.5	741.1	732.7	724.2
10°	757.9	741.1	725.9	709.1	697.3	687.2	675.4	663.6	653.5	643.4	633.3
12.5°	700.7	688.9	677.1	665.3	651.8	640.0	626.5	613.1	601.3	591.2	579.4
15°	665.3	648.4	629.9	613.1	594.5	577.7	559.2	540.6	527.2	515.4	501.9
17.5°	623.2	597.9	574.3	549.1	528.9	508.6	486.8	466.5	451.4	434.5	419.4
20°	576.0	547.4	517.1	488.4	464.9	443.0	419.4	395.8	379.0	360.4	343.6
22.5°	535.6	498.5	459.8	421.1	395.8	370.5	343.6	318.3	303.2	286.3	271.2
25°	491.8	451.4	409.3	367.2	341.9	315.0	289.7	262.7	251.0	240.8	229.1
27.5°	468.2	427.8	385.7	345.3	321.7	296.4	272.8	247.6	239.2	229.1	220.6
30°	421.1	382.3	341.9	301.5	284.6	269.5	252.6	235.8	232.4	230.7	227.4
32.5°	379.0	338.5	298.1	257.7	242.5	227.4	212.2	197.1	195.4	192.0	190.3
35°	357.1	318.3	277.9	239.2	225.7	210.5	197.1	181.9	178.5	173.5	170.1
37.5°	352.0	311.6	269.5	229.1	215.6	202.1	187.0	173.5	170.1	166.7	163.4
40°	338.5	299.8	262.7	224.0	210.5	197.1	181.9	168.4	165.1	161.7	158.3
42.5°	328.4	291.4	252.6	213.9	202.1	190.3	176.8	165.1	161.7	158.3	153.3
45°	320.0	281.3	240.8	202.1	193.7	185.3	175.2	166.7	163.4	158.3	155.0
47.5°	306.5	269.5	230.7	192.0	183.6	176.8	168.4	160.0	156.6	153.3	149.9
50°	296.4	257.7	219.0	180.2	173.5	166.7	160.0	153.3	153.3	155.0	155.0
52.5°	283.0	245.9	208.8	171.8	165.1	158.3	151.6	144.8	146.5	148.2	149.9
55°	271.2	235.8	198.7	161.7	155.0	148.2	139.8	133.1	134.7	136.4	138.1
57.5°	266.1	229.1	192.0	155.0	148.2	139.8	133.1	124.6	124.6	124.6	124.6
60°	262.7	224.0	187.0	148.2	139.8	133.1	124.6	116.2	114.5	114.5	112.8
62.5°	261.1	222.3	185.3	146.5	136.4	128.0	117.9	107.8	106.1	104.4	102.7
65°	254.3	219.0	181.9	144.8	133.1	123.0	111.2	99.4	97.7	97.7	96.0
67.5°	252.6	215.6	180.2	143.2	131.4	117.9	106.1	92.6	90.9	89.3	87.6
70°	239.2	207.2	173.5	139.8	126.3	114.5	101.1	87.6	85.9	82.5	80.8
72.5°	222.3	193.7	163.4	133.1	119.6	106.1	92.6	79.2	77.5	75.8	72.4
75°	197.1	170.1	143.2	116.2	104.4	94.3	82.5	70.7	69.1	67.4	64.0
77.5°	161.7	139.8	119.6	97.7	89.3	80.8	72.4	64.0	62.3	60.6	57.3
80°	114.5	101.1	89.3	75.8	70.7	64.0	58.9	52.2	52.2	50.5	50.5
82.5°	75.8	69.1	62.3	55.6	52.2	48.8	45.5	42.1	42.1	40.4	40.4
85°	53.9	50.5	45.5	42.1	40.4	37.1	35.4	32.0	32.0	32.0	32.0
87.5°	25.3	25.3	23.6	23.6	21.9	21.9	20.2	18.5	18.5	18.5	18.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675959
 CATALOG NUMBER: CCW-SA-2A-727-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675959

CATALOG NUMBER: CCW-SA-2A-727-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7
2.5°	1118.3	1113.3	1108.2	1101.5	1096.5	1089.7	1081.3	1074.6	1066.1	1066.1	1064.5
5°	902.8	897.7	892.7	885.9	880.9	874.1	869.1	862.3	855.6	855.6	853.9
7.5°	715.8	705.7	695.6	683.8	673.7	667.0	660.2	651.8	645.1	640.0	635.0
10°	623.2	613.1	601.3	591.2	579.4	571.0	562.5	552.4	544.0	537.3	530.5
12.5°	567.6	555.8	544.0	532.2	520.4	508.6	498.5	486.8	475.0	466.5	458.1
15°	488.4	476.6	464.9	453.1	441.3	427.8	414.3	399.2	385.7	379.0	373.9
17.5°	402.5	390.7	377.3	365.5	352.0	341.9	331.8	321.7	311.6	304.9	299.8
20°	325.1	311.6	298.1	284.6	271.2	264.4	257.7	251.0	244.2	239.2	235.8
22.5°	254.3	245.9	239.2	230.7	222.3	217.3	213.9	208.8	203.8	203.8	203.8
25°	217.3	212.2	208.8	203.8	198.7	197.1	195.4	192.0	190.3	188.6	188.6
27.5°	210.5	205.5	200.4	195.4	190.3	188.6	187.0	183.6	181.9	181.9	181.9
30°	224.0	222.3	220.6	219.0	217.3	213.9	208.8	205.5	200.4	197.1	193.7
32.5°	187.0	185.3	185.3	183.6	181.9	185.3	187.0	190.3	192.0	193.7	195.4
35°	165.1	161.7	158.3	155.0	151.6	149.9	148.2	146.5	144.8	144.8	143.2
37.5°	160.0	156.6	153.3	149.9	146.5	144.8	143.2	141.5	139.8	139.8	138.1
40°	155.0	151.6	149.9	146.5	143.2	141.5	139.8	136.4	134.7	133.1	133.1
42.5°	149.9	148.2	144.8	143.2	139.8	138.1	136.4	133.1	131.4	129.7	128.0
45°	149.9	146.5	143.2	139.8	136.4	134.7	131.4	129.7	126.3	126.3	124.6
47.5°	146.5	143.2	139.8	136.4	133.1	131.4	128.0	126.3	123.0	121.3	119.6
50°	155.0	149.9	143.2	138.1	131.4	129.7	126.3	124.6	121.3	119.6	117.9
52.5°	151.6	146.5	139.8	134.7	128.0	124.6	123.0	119.6	116.2	114.5	112.8
55°	139.8	134.7	131.4	126.3	121.3	117.9	114.5	111.2	107.8	106.1	106.1
57.5°	124.6	123.0	121.3	119.6	117.9	114.5	111.2	106.1	102.7	101.1	99.4
60°	111.2	112.8	114.5	116.2	117.9	112.8	107.8	102.7	97.7	96.0	94.3
62.5°	101.1	104.4	107.8	109.5	112.8	107.8	102.7	97.7	92.6	90.9	89.3
65°	94.3	96.0	96.0	97.7	97.7	94.3	92.6	89.3	85.9	84.2	84.2
67.5°	85.9	85.9	85.9	84.2	84.2	82.5	82.5	80.8	79.2	77.5	77.5
70°	77.5	77.5	77.5	75.8	75.8	74.1	74.1	72.4	70.7	70.7	69.1
72.5°	70.7	70.7	69.1	69.1	67.4	67.4	67.4	65.7	65.7	64.0	64.0
75°	62.3	62.3	60.6	60.6	58.9	58.9	58.9	57.3	57.3	57.3	55.6
77.5°	55.6	55.6	53.9	53.9	52.2	52.2	52.2	50.5	50.5	48.8	48.8
80°	48.8	48.8	47.2	47.2	45.5	45.5	43.8	43.8	42.1	42.1	40.4
82.5°	38.7	38.7	38.7	38.7	38.7	37.1	37.1	35.4	33.7	33.7	32.0
85°	32.0	32.0	32.0	30.3	30.3	30.3	28.6	28.6	26.9	25.3	25.3
87.5°	18.5	18.5	18.5	16.8	16.8	16.8	16.8	16.8	16.8	16.8	15.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675959
 CATALOG NUMBER: CCW-SA-2A-727-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675959
 CATALOG NUMBER: CCW-SA-2A-727-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7
2.5°	1064.5	1062.8	1056.0	1049.3	1056.0	1062.8	1062.8	1062.8	1061.1	1061.1	1061.1
5°	853.9	852.2	848.9	845.5	845.5	843.8	847.2	850.5	853.9	857.3	860.7
7.5°	628.2	623.2	618.1	613.1	616.4	618.1	623.2	626.5	631.6	635.0	643.4
10°	523.8	517.1	512.0	507.0	503.6	500.2	496.9	495.2	491.8	488.4	491.8
12.5°	448.0	439.6	431.2	421.1	419.4	417.7	414.3	411.0	407.6	404.2	402.5
15°	367.2	360.4	357.1	352.0	345.3	338.5	335.2	333.5	330.1	326.7	325.1
17.5°	293.1	286.3	281.3	276.2	274.5	271.2	271.2	271.2	271.2	271.2	271.2
20°	230.7	225.7	225.7	224.0	224.0	222.3	224.0	225.7	225.7	227.4	229.1
22.5°	202.1	202.1	200.4	198.7	200.4	200.4	202.1	203.8	205.5	207.2	208.8
25°	187.0	185.3	187.0	188.6	188.6	188.6	190.3	190.3	192.0	192.0	192.0
27.5°	180.2	180.2	181.9	181.9	183.6	183.6	183.6	181.9	181.9	180.2	180.2
30°	190.3	187.0	187.0	187.0	185.3	183.6	181.9	181.9	180.2	178.5	176.8
32.5°	197.1	198.7	197.1	193.7	192.0	188.6	187.0	183.6	181.9	178.5	175.2
35°	143.2	141.5	144.8	146.5	148.2	149.9	151.6	153.3	153.3	155.0	155.0
37.5°	138.1	136.4	136.4	134.7	134.7	134.7	134.7	134.7	133.1	133.1	134.7
40°	131.4	129.7	129.7	128.0	128.0	126.3	126.3	126.3	126.3	126.3	126.3
42.5°	126.3	124.6	124.6	124.6	124.6	123.0	123.0	121.3	121.3	119.6	119.6
45°	124.6	123.0	121.3	119.6	119.6	117.9	117.9	117.9	116.2	116.2	116.2
47.5°	117.9	116.2	116.2	114.5	114.5	112.8	112.8	112.8	111.2	111.2	111.2
50°	114.5	112.8	112.8	111.2	111.2	109.5	109.5	109.5	107.8	107.8	107.8
52.5°	109.5	107.8	107.8	107.8	106.1	104.4	104.4	104.4	102.7	102.7	102.7
55°	104.4	102.7	102.7	102.7	101.1	99.4	99.4	99.4	97.7	97.7	97.7
57.5°	97.7	96.0	96.0	94.3	94.3	94.3	94.3	94.3	92.6	92.6	92.6
60°	92.6	90.9	90.9	89.3	89.3	87.6	87.6	87.6	87.6	87.6	87.6
62.5°	87.6	85.9	84.2	82.5	84.2	84.2	84.2	84.2	82.5	82.5	82.5
65°	82.5	80.8	79.2	77.5	77.5	77.5	77.5	77.5	77.5	77.5	77.5
67.5°	75.8	74.1	72.4	70.7	72.4	72.4	72.4	72.4	72.4	72.4	72.4
70°	69.1	67.4	67.4	65.7	65.7	64.0	64.0	65.7	65.7	65.7	65.7
72.5°	62.3	60.6	60.6	58.9	58.9	58.9	58.9	58.9	58.9	58.9	58.9
75°	55.6	53.9	53.9	52.2	52.2	52.2	52.2	52.2	52.2	52.2	52.2
77.5°	47.2	45.5	45.5	45.5	45.5	45.5	45.5	47.2	47.2	47.2	47.2
80°	40.4	38.7	38.7	38.7	38.7	38.7	38.7	38.7	38.7	38.7	38.7
82.5°	32.0	30.3	30.3	30.3	30.3	30.3	30.3	30.3	30.3	30.3	30.3
85°	23.6	21.9	21.9	21.9	23.6	23.6	23.6	23.6	23.6	23.6	23.6
87.5°	15.2	13.5	13.5	13.5	15.2	15.2	15.2	15.2	13.5	13.5	13.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675959
 CATALOG NUMBER: CCW-SA-2A-727-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675959
 CATALOG NUMBER: CCW-SA-2A-727-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7
2.5°	1061.1	1061.1	1061.1	1059.4	1057.7	1056.0	1054.3	1059.4	1062.8	1067.8	1071.2
5°	862.3	865.7	867.4	872.4	877.5	882.6	887.6	891.0	894.3	896.0	899.4
7.5°	650.1	658.5	665.3	672.0	678.8	683.8	690.5	695.6	700.7	705.7	710.8
10°	493.5	496.9	498.5	505.3	510.3	517.1	522.1	527.2	532.2	535.6	540.6
12.5°	400.9	397.5	395.8	395.8	395.8	395.8	395.8	399.2	402.5	405.9	409.3
15°	323.4	321.7	320.0	318.3	316.6	313.3	311.6	315.0	318.3	321.7	325.1
17.5°	271.2	271.2	271.2	269.5	267.8	266.1	264.4	266.1	267.8	267.8	269.5
20°	232.4	234.1	235.8	237.5	237.5	239.2	239.2	240.8	242.5	242.5	244.2
22.5°	208.8	210.5	210.5	210.5	212.2	212.2	212.2	213.9	215.6	217.3	219.0
25°	190.3	190.3	188.6	188.6	190.3	190.3	190.3	190.3	192.0	192.0	192.0
27.5°	180.2	178.5	178.5	178.5	178.5	176.8	176.8	176.8	176.8	176.8	176.8
30°	175.2	173.5	171.8	170.1	170.1	168.4	166.7	166.7	166.7	166.7	166.7
32.5°	173.5	170.1	166.7	165.1	165.1	163.4	161.7	160.0	160.0	158.3	156.6
35°	155.0	153.3	153.3	151.6	149.9	148.2	146.5	146.5	146.5	144.8	144.8
37.5°	134.7	136.4	136.4	136.4	138.1	138.1	138.1	138.1	139.8	139.8	139.8
40°	126.3	126.3	126.3	128.0	129.7	129.7	131.4	131.4	133.1	133.1	133.1
42.5°	119.6	117.9	117.9	119.6	119.6	121.3	121.3	123.0	124.6	124.6	126.3
45°	116.2	114.5	114.5	114.5	114.5	112.8	112.8	114.5	116.2	117.9	119.6
47.5°	109.5	109.5	107.8	107.8	107.8	107.8	107.8	107.8	109.5	109.5	109.5
50°	106.1	106.1	104.4	104.4	104.4	104.4	104.4	104.4	104.4	104.4	104.4
52.5°	102.7	101.1	101.1	101.1	101.1	99.4	99.4	99.4	99.4	99.4	99.4
55°	97.7	96.0	96.0	96.0	96.0	96.0	96.0	96.0	97.7	97.7	97.7
57.5°	92.6	90.9	90.9	90.9	92.6	92.6	92.6	92.6	94.3	94.3	94.3
60°	87.6	87.6	87.6	87.6	87.6	87.6	87.6	89.3	89.3	90.9	90.9
62.5°	82.5	82.5	82.5	82.5	84.2	84.2	84.2	84.2	85.9	85.9	85.9
65°	77.5	77.5	77.5	77.5	79.2	79.2	79.2	79.2	79.2	79.2	79.2
67.5°	72.4	72.4	72.4	72.4	72.4	72.4	72.4	74.1	74.1	75.8	75.8
70°	65.7	64.0	64.0	65.7	65.7	67.4	67.4	69.1	69.1	70.7	70.7
72.5°	58.9	58.9	58.9	58.9	58.9	58.9	58.9	60.6	62.3	62.3	64.0
75°	52.2	52.2	52.2	52.2	53.9	53.9	53.9	55.6	55.6	57.3	57.3
77.5°	47.2	45.5	45.5	45.5	47.2	47.2	47.2	48.8	48.8	50.5	50.5
80°	38.7	38.7	38.7	38.7	40.4	40.4	40.4	40.4	42.1	42.1	42.1
82.5°	32.0	32.0	32.0	32.0	32.0	32.0	32.0	32.0	33.7	33.7	33.7
85°	23.6	23.6	23.6	23.6	25.3	25.3	25.3	25.3	25.3	25.3	25.3
87.5°	15.2	15.2	15.2	15.2	15.2	15.2	15.2	15.2	16.8	16.8	16.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675959
 CATALOG NUMBER: CCW-SA-2A-727-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675959

CATALOG NUMBER: CCW-SA-2A-727-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7
2.5°	1071.2	1071.2	1071.2	1071.2	1074.6	1076.2	1079.6	1081.3	1079.6	1077.9	1074.6
5°	901.1	902.8	902.8	904.4	904.4	904.4	904.4	904.4	907.8	911.2	914.6
7.5°	712.4	714.1	715.8	717.5	717.5	717.5	715.8	715.8	717.5	717.5	719.2
10°	545.7	552.4	557.5	562.5	559.2	554.1	550.8	545.7	545.7	545.7	544.0
12.5°	412.6	414.3	417.7	419.4	417.7	417.7	416.0	414.3	416.0	419.4	421.1
15°	326.7	326.7	328.4	328.4	330.1	331.8	331.8	333.5	336.9	338.5	341.9
17.5°	271.2	272.8	272.8	274.5	274.5	276.2	276.2	276.2	279.6	283.0	288.0
20°	244.2	244.2	244.2	244.2	244.2	242.5	242.5	240.8	242.5	245.9	247.6
22.5°	219.0	220.6	220.6	220.6	219.0	217.3	213.9	212.2	212.2	213.9	213.9
25°	192.0	190.3	190.3	188.6	188.6	190.3	190.3	190.3	192.0	192.0	193.7
27.5°	176.8	175.2	175.2	173.5	173.5	175.2	175.2	175.2	175.2	175.2	175.2
30°	165.1	165.1	163.4	161.7	163.4	163.4	165.1	165.1	166.7	166.7	168.4
32.5°	156.6	155.0	155.0	153.3	155.0	155.0	156.6	156.6	158.3	160.0	160.0
35°	144.8	144.8	144.8	144.8	144.8	144.8	143.2	143.2	143.2	143.2	143.2
37.5°	138.1	138.1	136.4	134.7	134.7	134.7	134.7	134.7	133.1	131.4	129.7
40°	133.1	131.4	131.4	129.7	128.0	128.0	126.3	124.6	124.6	123.0	123.0
42.5°	126.3	124.6	124.6	123.0	121.3	121.3	119.6	117.9	117.9	117.9	116.2
45°	117.9	117.9	116.2	114.5	114.5	114.5	112.8	112.8	112.8	112.8	111.2
47.5°	109.5	109.5	107.8	107.8	107.8	107.8	106.1	106.1	106.1	106.1	106.1
50°	104.4	104.4	104.4	104.4	104.4	104.4	102.7	102.7	102.7	102.7	102.7
52.5°	99.4	99.4	99.4	99.4	99.4	99.4	99.4	99.4	99.4	99.4	99.4
55°	97.7	97.7	97.7	97.7	97.7	97.7	96.0	96.0	96.0	97.7	97.7
57.5°	94.3	94.3	92.6	92.6	92.6	92.6	92.6	92.6	92.6	92.6	92.6
60°	90.9	90.9	90.9	90.9	90.9	90.9	90.9	90.9	90.9	90.9	90.9
62.5°	85.9	85.9	85.9	85.9	85.9	87.6	87.6	87.6	87.6	87.6	85.9
65°	79.2	80.8	80.8	80.8	80.8	80.8	80.8	80.8	80.8	80.8	80.8
67.5°	75.8	75.8	75.8	75.8	75.8	75.8	75.8	75.8	75.8	75.8	75.8
70°	70.7	70.7	69.1	69.1	69.1	70.7	70.7	70.7	70.7	70.7	70.7
72.5°	64.0	64.0	64.0	64.0	64.0	64.0	64.0	64.0	64.0	65.7	65.7
75°	57.3	57.3	57.3	57.3	57.3	57.3	57.3	57.3	57.3	57.3	57.3
77.5°	50.5	50.5	48.8	48.8	48.8	50.5	50.5	50.5	50.5	52.2	52.2
80°	42.1	42.1	42.1	42.1	42.1	42.1	42.1	42.1	42.1	43.8	43.8
82.5°	33.7	33.7	33.7	33.7	33.7	33.7	33.7	33.7	33.7	35.4	35.4
85°	25.3	26.9	26.9	26.9	26.9	26.9	26.9	26.9	26.9	28.6	28.6
87.5°	16.8	16.8	16.8	16.8	16.8	16.8	15.2	15.2	15.2	15.2	13.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675959
 CATALOG NUMBER: CCW-SA-2A-727-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675959
 CATALOG NUMBER: CCW-SA-2A-727-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7
2.5°	1072.9	1074.6	1076.2	1076.2	1077.9	1079.6	1079.6	1086.3	1093.1	1096.5	1099.8
5°	917.9	916.2	916.2	914.6	912.9	917.9	923.0	933.1	943.2	944.9	948.2
7.5°	719.2	720.9	722.5	722.5	724.2	719.2	712.4	714.1	715.8	724.2	731.0
10°	544.0	545.7	547.4	547.4	549.1	547.4	544.0	549.1	554.1	560.9	569.3
12.5°	422.7	427.8	432.9	436.2	441.3	444.6	446.3	453.1	458.1	466.5	475.0
15°	345.3	348.6	352.0	355.4	358.7	362.1	365.5	372.2	379.0	389.1	399.2
17.5°	291.4	291.4	293.1	293.1	293.1	296.4	299.8	303.2	304.9	315.0	325.1
20°	249.3	247.6	245.9	244.2	242.5	245.9	247.6	249.3	251.0	257.7	262.7
22.5°	213.9	213.9	215.6	215.6	215.6	213.9	210.5	212.2	212.2	215.6	220.6
25°	193.7	193.7	193.7	192.0	192.0	193.7	195.4	195.4	193.7	195.4	197.1
27.5°	175.2	176.8	176.8	178.5	178.5	180.2	180.2	180.2	180.2	181.9	183.6
30°	168.4	168.4	170.1	170.1	170.1	171.8	173.5	173.5	173.5	175.2	178.5
32.5°	161.7	163.4	165.1	166.7	168.4	170.1	170.1	171.8	171.8	173.5	175.2
35°	143.2	141.5	141.5	139.8	138.1	138.1	138.1	138.1	136.4	138.1	138.1
37.5°	128.0	128.0	128.0	126.3	126.3	128.0	128.0	128.0	128.0	129.7	129.7
40°	121.3	121.3	121.3	121.3	121.3	121.3	121.3	123.0	123.0	124.6	126.3
42.5°	116.2	116.2	116.2	116.2	116.2	117.9	117.9	117.9	117.9	119.6	119.6
45°	111.2	111.2	111.2	111.2	111.2	111.2	111.2	112.8	112.8	114.5	116.2
47.5°	106.1	106.1	106.1	106.1	106.1	107.8	109.5	109.5	109.5	111.2	111.2
50°	102.7	102.7	102.7	102.7	102.7	104.4	104.4	106.1	106.1	107.8	109.5
52.5°	99.4	99.4	99.4	99.4	99.4	101.1	101.1	102.7	102.7	104.4	106.1
55°	97.7	97.7	97.7	96.0	96.0	97.7	97.7	99.4	99.4	101.1	101.1
57.5°	92.6	92.6	92.6	92.6	92.6	92.6	92.6	94.3	94.3	96.0	97.7
60°	90.9	90.9	89.3	89.3	87.6	89.3	89.3	90.9	90.9	92.6	92.6
62.5°	85.9	85.9	85.9	84.2	84.2	85.9	85.9	85.9	85.9	87.6	89.3
65°	80.8	80.8	80.8	79.2	79.2	80.8	80.8	80.8	80.8	82.5	84.2
67.5°	75.8	75.8	75.8	74.1	74.1	74.1	74.1	75.8	75.8	77.5	79.2
70°	70.7	70.7	70.7	69.1	69.1	69.1	67.4	69.1	70.7	72.4	72.4
72.5°	65.7	65.7	65.7	64.0	64.0	64.0	62.3	64.0	64.0	65.7	65.7
75°	57.3	57.3	57.3	57.3	57.3	57.3	55.6	55.6	55.6	57.3	57.3
77.5°	52.2	52.2	52.2	50.5	50.5	50.5	48.8	48.8	48.8	50.5	50.5
80°	43.8	43.8	43.8	42.1	42.1	42.1	40.4	40.4	40.4	42.1	42.1
82.5°	35.4	35.4	35.4	33.7	33.7	33.7	32.0	32.0	32.0	33.7	33.7
85°	28.6	28.6	28.6	28.6	28.6	28.6	26.9	26.9	26.9	28.6	30.3
87.5°	13.5	13.5	15.2	15.2	15.2	15.2	13.5	13.5	11.8	11.8	13.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675959
 CATALOG NUMBER: CCW-SA-2A-727-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675959
 CATALOG NUMBER: CCW-SA-2A-727-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7
2.5°	1103.2	1106.6	1115.0	1121.7	1130.1	1136.9	1141.9	1148.7	1153.7	1158.8	1162.1
5°	949.9	951.6	960.0	968.4	975.2	983.6	995.4	1007.2	1019.0	1030.8	1039.2
7.5°	739.4	746.1	756.2	768.0	778.1	788.2	800.0	813.5	825.3	837.1	848.9
10°	576.0	582.8	592.9	603.0	611.4	621.5	635.0	648.4	661.9	675.4	688.9
12.5°	483.4	491.8	503.6	515.4	525.5	537.3	554.1	569.3	586.1	601.3	618.1
15°	407.6	417.7	432.9	449.7	464.9	480.0	496.9	513.7	528.9	545.7	562.5
17.5°	335.2	345.3	358.7	373.9	387.4	400.9	421.1	439.6	459.8	478.3	496.9
20°	269.5	274.5	288.0	301.5	315.0	328.4	343.6	358.7	373.9	389.1	412.6
22.5°	224.0	227.4	234.1	239.2	245.9	251.0	266.1	281.3	294.7	309.9	331.8
25°	197.1	198.7	203.8	207.2	212.2	215.6	225.7	234.1	244.2	252.6	272.8
27.5°	183.6	185.3	187.0	188.6	190.3	192.0	198.7	205.5	210.5	217.3	235.8
30°	180.2	181.9	187.0	190.3	195.4	198.7	202.1	205.5	208.8	212.2	224.0
32.5°	176.8	178.5	178.5	176.8	176.8	175.2	178.5	180.2	183.6	185.3	195.4
35°	139.8	139.8	141.5	143.2	144.8	146.5	151.6	155.0	160.0	163.4	171.8
37.5°	131.4	131.4	133.1	136.4	138.1	139.8	143.2	146.5	149.9	153.3	161.7
40°	126.3	128.0	129.7	131.4	133.1	134.7	138.1	139.8	143.2	144.8	151.6
42.5°	121.3	121.3	123.0	126.3	128.0	129.7	133.1	134.7	138.1	139.8	146.5
45°	117.9	119.6	121.3	123.0	123.0	124.6	128.0	131.4	133.1	136.4	143.2
47.5°	112.8	112.8	116.2	117.9	121.3	123.0	126.3	128.0	131.4	133.1	139.8
50°	109.5	111.2	114.5	116.2	119.6	121.3	126.3	129.7	134.7	138.1	141.5
52.5°	106.1	107.8	111.2	112.8	116.2	117.9	124.6	131.4	136.4	143.2	143.2
55°	102.7	102.7	106.1	111.2	114.5	117.9	121.3	126.3	129.7	133.1	133.1
57.5°	97.7	99.4	102.7	107.8	111.2	114.5	117.9	121.3	123.0	126.3	124.6
60°	94.3	94.3	99.4	104.4	109.5	114.5	114.5	114.5	112.8	112.8	112.8
62.5°	89.3	90.9	97.7	106.1	112.8	119.6	114.5	109.5	104.4	99.4	101.1
65°	85.9	87.6	90.9	96.0	99.4	102.7	99.4	97.7	94.3	90.9	92.6
67.5°	79.2	80.8	82.5	82.5	84.2	84.2	84.2	84.2	84.2	84.2	85.9
70°	74.1	74.1	74.1	75.8	75.8	75.8	75.8	75.8	75.8	75.8	77.5
72.5°	67.4	67.4	67.4	67.4	67.4	67.4	67.4	67.4	67.4	67.4	69.1
75°	58.9	58.9	58.9	58.9	58.9	58.9	58.9	58.9	58.9	58.9	60.6
77.5°	52.2	52.2	52.2	52.2	52.2	52.2	52.2	52.2	50.5	50.5	52.2
80°	43.8	43.8	43.8	43.8	42.1	42.1	42.1	42.1	42.1	42.1	43.8
82.5°	35.4	35.4	35.4	35.4	33.7	33.7	33.7	33.7	32.0	32.0	33.7
85°	32.0	33.7	33.7	35.4	35.4	35.4	33.7	32.0	30.3	28.6	28.6
87.5°	13.5	13.5	13.5	13.5	11.8	11.8	11.8	11.8	11.8	11.8	11.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675959
 CATALOG NUMBER: CCW-SA-2A-727-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675959
 CATALOG NUMBER: CCW-SA-2A-727-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7
2.5°	1167.2	1170.6	1173.9	1179.0	1185.7	1190.8	1195.8	1205.9	1217.7	1227.8	1237.9
5°	1047.6	1056.0	1064.5	1074.6	1084.7	1093.1	1103.2	1123.4	1143.6	1162.1	1182.3
7.5°	859.0	870.8	880.9	897.7	912.9	929.7	944.9	970.1	993.7	1019.0	1042.6
10°	702.3	715.8	729.3	751.2	774.8	796.7	818.5	838.8	860.7	880.9	901.1
12.5°	635.0	650.1	667.0	680.4	695.6	709.1	722.5	746.1	769.7	793.3	816.9
15°	579.4	596.2	613.1	629.9	645.1	661.9	677.1	697.3	719.2	739.4	759.6
17.5°	515.4	532.2	550.8	569.3	587.8	606.3	624.9	653.5	682.1	709.1	737.7
20°	434.5	458.1	480.0	505.3	530.5	555.8	581.1	611.4	641.7	670.3	700.7
22.5°	353.7	375.6	397.5	427.8	458.1	486.8	517.1	557.5	596.2	636.6	675.4
25°	294.7	315.0	335.2	368.9	400.9	434.5	466.5	515.4	562.5	611.4	658.5
27.5°	254.3	272.8	291.4	326.7	362.1	395.8	431.2	485.1	537.3	591.2	643.4
30°	235.8	247.6	259.4	293.1	326.7	358.7	392.4	444.6	496.9	549.1	601.3
32.5°	205.5	215.6	225.7	256.0	286.3	315.0	345.3	399.2	451.4	505.3	557.5
35°	181.9	190.3	198.7	227.4	254.3	283.0	309.9	363.8	417.7	471.6	525.5
37.5°	168.4	176.8	183.6	208.8	235.8	261.1	286.3	340.2	392.4	446.3	498.5
40°	158.3	163.4	170.1	195.4	219.0	244.2	267.8	316.6	367.2	416.0	464.9
42.5°	151.6	158.3	163.4	185.3	208.8	230.7	252.6	299.8	347.0	392.4	439.6
45°	149.9	156.6	163.4	181.9	200.4	217.3	235.8	281.3	326.7	372.2	417.7
47.5°	146.5	151.6	158.3	173.5	187.0	202.1	215.6	261.1	306.5	350.3	395.8
50°	144.8	146.5	149.9	163.4	176.8	190.3	203.8	249.3	294.7	340.2	385.7
52.5°	143.2	143.2	143.2	155.0	166.7	176.8	188.6	234.1	281.3	326.7	372.2
55°	133.1	131.4	131.4	143.2	153.3	165.1	175.2	220.6	266.1	309.9	355.4
57.5°	123.0	121.3	119.6	129.7	139.8	149.9	160.0	205.5	252.6	298.1	343.6
60°	112.8	111.2	111.2	121.3	129.7	139.8	148.2	195.4	240.8	288.0	333.5
62.5°	101.1	102.7	102.7	111.2	121.3	129.7	138.1	185.3	234.1	281.3	328.4
65°	92.6	94.3	94.3	104.4	114.5	124.6	134.7	180.2	227.4	272.8	318.3
67.5°	85.9	87.6	87.6	99.4	109.5	121.3	131.4	171.8	213.9	254.3	294.7
70°	79.2	79.2	80.8	92.6	104.4	116.2	128.0	163.4	198.7	232.4	267.8
72.5°	70.7	72.4	74.1	85.9	96.0	107.8	117.9	149.9	181.9	213.9	245.9
75°	62.3	64.0	65.7	75.8	85.9	96.0	106.1	136.4	165.1	195.4	224.0
77.5°	55.6	57.3	58.9	67.4	75.8	84.2	92.6	114.5	138.1	160.0	181.9
80°	45.5	45.5	47.2	53.9	60.6	65.7	72.4	87.6	102.7	116.2	131.4
82.5°	33.7	35.4	35.4	40.4	43.8	48.8	52.2	60.6	67.4	75.8	82.5
85°	28.6	26.9	26.9	30.3	32.0	35.4	37.1	42.1	45.5	50.5	53.9
87.5°	11.8	10.1	10.1	11.8	15.2	16.8	18.5	18.5	20.2	20.2	20.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675959
 CATALOG NUMBER: CCW-SA-2A-727-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675959

CATALOG NUMBER: CCW-SA-2A-727-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7
2.5°	1243.0	1246.4	1251.4	1254.8	1263.2	1269.9	1278.4	1285.1	1290.1	1298.6	1295.2
5°	1197.5	1212.7	1227.8	1243.0	1254.8	1266.6	1276.7	1288.5	1301.9	1327.2	1333.9
7.5°	1062.8	1083.0	1101.5	1121.7	1145.3	1168.9	1192.5	1216.0	1237.9	1269.9	1290.1
10°	929.7	958.3	985.3	1013.9	1035.8	1057.7	1077.9	1099.8	1130.1	1162.1	1199.2
12.5°	845.5	874.1	902.8	931.4	963.4	993.7	1025.7	1056.0	1084.7	1109.9	1152.0
15°	789.9	821.9	852.2	882.6	921.3	958.3	997.1	1034.1	1076.2	1109.9	1138.6
17.5°	776.4	815.2	852.2	891.0	931.4	971.8	1012.2	1052.7	1094.8	1145.3	1182.3
20°	752.9	805.1	857.3	909.5	961.7	1012.2	1064.5	1115.0	1170.6	1231.2	1248.0
22.5°	739.4	801.7	865.7	928.0	998.8	1071.2	1141.9	1212.7	1271.6	1317.1	1367.6
25°	737.7	815.2	894.3	971.8	1061.1	1148.7	1237.9	1325.5	1401.3	1446.8	1487.2
27.5°	736.0	830.3	923.0	1015.6	1125.1	1232.9	1342.4	1450.1	1520.9	1586.6	1620.3
30°	715.8	828.7	943.2	1056.0	1179.0	1301.9	1424.9	1547.8	1620.3	1665.7	1682.6
32.5°	690.5	823.6	956.7	1089.7	1229.5	1369.3	1507.4	1647.2	1704.5	1743.2	1729.7
35°	670.3	816.9	961.7	1106.6	1254.8	1404.7	1552.9	1701.1	1783.6	1837.5	1815.6
37.5°	651.8	805.1	958.3	1111.6	1285.1	1458.6	1632.0	1805.5	1884.7	1941.9	1916.7
40°	629.9	793.3	958.3	1121.7	1320.5	1517.5	1716.3	1913.3	2016.1	2064.9	2026.2
42.5°	611.4	781.5	953.3	1123.4	1335.6	1547.8	1760.0	1972.3	2086.8	2155.8	2107.0
45°	587.8	757.9	926.3	1096.5	1330.6	1564.7	1797.1	2031.2	2164.3	2218.2	2150.8
47.5°	562.5	731.0	897.7	1064.5	1313.7	1563.0	1812.3	2061.5	2184.5	2248.5	2186.2
50°	554.1	722.5	889.3	1057.7	1327.2	1598.4	1867.8	2137.3	2226.6	2278.8	2196.3
52.5°	552.4	731.0	911.2	1089.7	1360.9	1630.4	1901.5	2171.0	2243.4	2299.0	2224.9
55°	547.4	741.1	933.1	1125.1	1408.0	1692.7	1975.6	2258.6	2331.0	2371.4	2315.9
57.5°	552.4	761.3	968.4	1177.3	1468.7	1760.0	2051.4	2342.8	2430.4	2459.0	2447.2
60°	555.8	778.1	998.8	1221.1	1505.7	1790.4	2075.0	2359.6	2450.6	2521.3	2534.8
62.5°	547.4	766.3	983.6	1202.6	1460.3	1717.9	1975.6	2233.3	2383.2	2487.6	2548.3
65°	522.1	724.2	928.0	1130.1	1367.6	1606.8	1844.3	2081.7	2240.1	2395.0	2443.9
67.5°	466.5	638.3	810.1	981.9	1189.1	1396.2	1601.7	1808.9	2007.6	2157.5	2224.9
70°	404.2	539.0	675.4	810.1	998.8	1187.4	1376.0	1564.7	1739.8	1904.9	1968.9
72.5°	352.0	456.4	562.5	667.0	801.7	934.8	1069.5	1202.6	1409.7	1574.8	1637.1
75°	299.8	375.6	449.7	525.5	618.1	710.8	801.7	894.3	1040.9	1189.1	1251.4
77.5°	230.7	281.3	330.1	379.0	443.0	505.3	569.3	631.6	734.3	845.5	877.5
80°	160.0	188.6	215.6	244.2	294.7	345.3	395.8	446.3	513.7	576.0	624.9
82.5°	99.4	117.9	134.7	151.6	192.0	232.4	271.2	311.6	338.5	341.9	390.7
85°	64.0	75.8	85.9	96.0	119.6	144.8	168.4	192.0	171.8	160.0	190.3
87.5°	25.3	32.0	37.1	42.1	40.4	38.7	37.1	35.4	30.3	26.9	33.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675959
 CATALOG NUMBER: CCW-SA-2A-727-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675959

CATALOG NUMBER: CCW-SA-2A-727-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7
2.5°	1298.6	1303.6	1308.7	1312.0	1317.1	1318.8	1320.5	1320.5	1322.1	1323.8	1327.2
5°	1360.9	1371.0	1381.1	1389.5	1399.6	1408.0	1414.8	1423.2	1429.9	1429.9	1428.3
7.5°	1308.7	1333.9	1359.2	1384.5	1409.7	1428.3	1445.1	1463.6	1480.5	1483.8	1487.2
10°	1239.6	1266.6	1291.8	1318.8	1344.0	1372.7	1399.6	1426.6	1455.2	1460.3	1467.0
12.5°	1175.6	1207.6	1239.6	1269.9	1301.9	1322.1	1342.4	1360.9	1381.1	1394.6	1408.0
15°	1173.9	1200.9	1227.8	1253.1	1280.0	1291.8	1303.6	1313.7	1325.5	1325.5	1327.2
17.5°	1212.7	1229.5	1246.4	1261.5	1278.4	1280.0	1283.4	1285.1	1286.8	1281.7	1276.7
20°	1288.5	1295.2	1301.9	1308.7	1315.4	1303.6	1293.5	1281.7	1269.9	1256.5	1244.7
22.5°	1399.6	1384.5	1369.3	1354.1	1339.0	1318.8	1296.9	1276.7	1254.8	1237.9	1221.1
25°	1504.0	1485.5	1467.0	1448.5	1429.9	1386.1	1342.4	1296.9	1253.1	1234.6	1216.0
27.5°	1643.8	1615.2	1586.6	1557.9	1529.3	1470.4	1411.4	1352.5	1293.5	1261.5	1231.2
30°	1677.5	1645.5	1613.5	1579.8	1547.8	1490.6	1435.0	1377.7	1320.5	1283.4	1248.0
32.5°	1726.4	1689.3	1652.3	1615.2	1578.1	1522.6	1467.0	1409.7	1354.1	1320.5	1285.1
35°	1807.2	1765.1	1723.0	1679.2	1637.1	1579.8	1524.3	1467.0	1409.7	1371.0	1333.9
37.5°	1876.3	1827.4	1778.6	1729.7	1680.9	1630.4	1578.1	1527.6	1475.4	1436.7	1399.6
40°	1953.7	1899.8	1845.9	1793.7	1739.8	1692.7	1645.5	1596.7	1549.5	1519.2	1488.9
42.5°	2021.1	1955.4	1891.4	1827.4	1761.7	1729.7	1699.4	1667.4	1635.4	1620.3	1603.4
45°	2068.3	2007.6	1945.3	1884.7	1824.1	1800.5	1776.9	1753.3	1729.7	1744.9	1760.0
47.5°	2088.5	2039.6	1992.5	1945.3	1896.5	1904.9	1913.3	1920.1	1928.5	1948.7	1970.6
50°	2107.0	2080.1	2051.4	2024.5	1995.8	2027.8	2058.2	2090.2	2122.2	2164.3	2206.4
52.5°	2144.1	2128.9	2115.4	2100.3	2085.1	2140.7	2196.3	2251.9	2307.4	2354.6	2401.8
55°	2255.2	2243.4	2231.6	2218.2	2206.4	2285.5	2363.0	2442.2	2521.3	2570.2	2619.0
57.5°	2408.5	2401.8	2393.3	2386.6	2378.2	2455.6	2531.4	2607.2	2684.7	2731.9	2780.7
60°	2524.7	2526.4	2526.4	2528.1	2528.1	2587.0	2646.0	2706.6	2765.6	2806.0	2848.1
62.5°	2587.0	2583.7	2580.3	2576.9	2573.5	2622.4	2671.2	2720.1	2768.9	2799.2	2829.6
65°	2519.6	2538.2	2556.7	2575.2	2593.8	2600.5	2605.5	2612.3	2617.3	2635.9	2654.4
67.5°	2294.0	2331.0	2366.4	2403.4	2438.8	2413.5	2390.0	2364.7	2339.4	2344.5	2347.9
70°	2043.0	2085.1	2128.9	2171.0	2213.1	2154.2	2095.2	2034.6	1975.6	1955.4	1935.2
72.5°	1723.0	1760.0	1798.8	1835.8	1872.9	1800.5	1729.7	1657.3	1584.9	1549.5	1514.1
75°	1317.1	1360.9	1406.4	1450.1	1493.9	1413.1	1330.6	1249.7	1167.2	1143.6	1121.7
77.5°	960.0	1012.2	1064.5	1116.7	1168.9	1096.5	1024.0	949.9	877.5	864.0	850.5
80°	699.0	739.4	778.1	818.5	857.3	815.2	773.1	731.0	688.9	687.2	685.5
82.5°	471.6	507.0	540.6	576.0	609.7	592.9	577.7	560.9	544.0	560.9	579.4
85°	242.5	291.4	341.9	390.7	439.6	434.5	431.2	426.1	421.1	443.0	463.2
87.5°	48.8	90.9	133.1	173.5	215.6	205.5	195.4	183.6	173.5	180.2	185.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675959
 CATALOG NUMBER: CCW-SA-2A-727-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675959

CATALOG NUMBER: CCW-SA-2A-727-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7
2.5°	1328.9	1330.6	1330.6	1330.6	1330.6	1330.6	1327.2	1325.5	1322.1	1318.8	1313.7
5°	1428.3	1426.6	1419.8	1413.1	1404.7	1397.9	1392.9	1386.1	1381.1	1374.4	1364.2
7.5°	1490.6	1493.9	1482.1	1472.0	1460.3	1448.5	1436.7	1424.9	1413.1	1401.3	1377.7
10°	1472.0	1477.1	1470.4	1463.6	1455.2	1448.5	1435.0	1419.8	1406.4	1391.2	1362.6
12.5°	1419.8	1433.3	1429.9	1426.6	1423.2	1419.8	1411.4	1401.3	1392.9	1382.8	1350.8
15°	1327.2	1327.2	1328.9	1330.6	1330.6	1332.2	1333.9	1335.6	1337.3	1339.0	1320.5
17.5°	1271.6	1266.6	1266.6	1266.6	1266.6	1266.6	1273.3	1281.7	1288.5	1295.2	1290.1
20°	1231.2	1219.4	1217.7	1217.7	1216.0	1214.3	1226.1	1239.6	1251.4	1263.2	1269.9
22.5°	1204.2	1187.4	1185.7	1184.0	1182.3	1180.7	1195.8	1211.0	1226.1	1241.3	1264.9
25°	1197.5	1179.0	1180.7	1182.3	1182.3	1184.0	1195.8	1207.6	1219.4	1231.2	1271.6
27.5°	1199.2	1168.9	1170.6	1172.2	1172.2	1173.9	1192.5	1209.3	1227.8	1244.7	1295.2
30°	1211.0	1175.6	1172.2	1168.9	1165.5	1162.1	1187.4	1212.7	1237.9	1263.2	1301.9
32.5°	1251.4	1217.7	1209.3	1200.9	1192.5	1184.0	1214.3	1243.0	1273.3	1301.9	1333.9
35°	1295.2	1258.1	1254.8	1251.4	1246.4	1243.0	1269.9	1298.6	1325.5	1352.5	1381.1
37.5°	1360.9	1323.8	1320.5	1315.4	1312.0	1307.0	1337.3	1365.9	1396.2	1424.9	1450.1
40°	1458.6	1428.3	1426.6	1426.6	1424.9	1423.2	1446.8	1472.0	1495.6	1519.2	1536.0
42.5°	1588.3	1573.1	1578.1	1584.9	1589.9	1595.0	1613.5	1633.7	1652.3	1670.8	1665.7
45°	1775.2	1790.4	1792.0	1793.7	1795.4	1797.1	1802.2	1808.9	1813.9	1819.0	1798.8
47.5°	1990.8	2011.0	2021.1	2031.2	2039.6	2049.7	2043.0	2034.6	2027.8	2019.4	1968.9
50°	2246.8	2288.9	2287.2	2285.5	2282.2	2280.5	2267.0	2253.5	2238.4	2224.9	2150.8
52.5°	2448.9	2496.1	2504.5	2512.9	2521.3	2529.8	2504.5	2479.2	2452.3	2427.0	2334.4
55°	2666.2	2715.0	2716.7	2718.4	2718.4	2720.1	2684.7	2649.3	2612.3	2576.9	2480.9
57.5°	2827.9	2875.0	2870.0	2866.6	2861.6	2856.5	2814.4	2772.3	2730.2	2688.1	2592.1
60°	2888.5	2928.9	2918.8	2908.7	2896.9	2886.8	2854.8	2822.8	2789.1	2757.1	2664.5
62.5°	2859.9	2890.2	2875.0	2861.6	2846.4	2831.2	2790.8	2748.7	2708.3	2666.2	2598.8
65°	2671.2	2689.8	2669.5	2651.0	2632.5	2612.3	2578.6	2544.9	2509.5	2475.9	2430.4
67.5°	2352.9	2356.3	2354.6	2352.9	2351.2	2349.5	2300.7	2251.9	2201.3	2152.5	2149.1
70°	1916.7	1896.5	1899.8	1904.9	1908.3	1911.6	1874.6	1839.2	1802.2	1765.1	1781.9
72.5°	1478.8	1443.4	1451.8	1461.9	1470.4	1478.8	1448.5	1419.8	1389.5	1359.2	1382.8
75°	1098.1	1076.2	1084.7	1094.8	1103.2	1111.6	1099.8	1088.0	1074.6	1062.8	1084.7
77.5°	837.1	823.6	825.3	825.3	827.0	827.0	828.7	832.0	833.7	835.4	859.0
80°	682.1	680.4	678.8	677.1	673.7	672.0	688.9	705.7	722.5	739.4	751.2
82.5°	596.2	613.1	603.0	594.5	584.4	574.3	589.5	604.6	619.8	635.0	629.9
85°	485.1	505.3	486.8	468.2	448.0	429.5	443.0	454.7	468.2	480.0	473.3
87.5°	192.0	197.1	166.7	138.1	107.8	77.5	123.0	166.7	212.2	256.0	262.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675959
 CATALOG NUMBER: CCW-SA-2A-727-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675959

CATALOG NUMBER: CCW-SA-2A-727-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7	1212.7
2.5°	1308.7	1301.9	1296.9	1295.2	1291.8	1290.1	1286.8	1283.4	1278.4	1275.0	1269.9
5°	1352.5	1342.4	1330.6	1313.7	1298.6	1281.7	1264.9	1249.7	1234.6	1217.7	1202.6
7.5°	1354.1	1330.6	1307.0	1285.1	1261.5	1239.6	1216.0	1195.8	1173.9	1152.0	1131.8
10°	1335.6	1307.0	1278.4	1249.7	1222.8	1194.1	1165.5	1141.9	1116.7	1091.4	1067.8
12.5°	1320.5	1288.5	1256.5	1222.8	1190.8	1157.1	1123.4	1099.8	1076.2	1052.7	1029.1
15°	1301.9	1281.7	1263.2	1232.9	1202.6	1172.2	1141.9	1109.9	1079.6	1047.6	1015.6
17.5°	1286.8	1281.7	1276.7	1256.5	1236.2	1214.3	1194.1	1162.1	1130.1	1096.5	1064.5
20°	1278.4	1285.1	1291.8	1281.7	1271.6	1259.8	1249.7	1226.1	1202.6	1177.3	1153.7
22.5°	1288.5	1313.7	1337.3	1339.0	1342.4	1344.0	1345.7	1323.8	1301.9	1278.4	1256.5
25°	1312.0	1352.5	1392.9	1414.8	1436.7	1460.3	1482.1	1468.7	1455.2	1441.7	1428.3
27.5°	1344.0	1394.6	1445.1	1477.1	1507.4	1539.4	1571.4	1569.7	1568.0	1564.7	1563.0
30°	1339.0	1377.7	1416.5	1455.2	1493.9	1532.7	1571.4	1591.6	1610.1	1630.4	1650.6
32.5°	1367.6	1399.6	1433.3	1473.7	1514.1	1556.3	1596.7	1638.8	1679.2	1721.3	1763.4
35°	1411.4	1440.0	1470.4	1514.1	1559.6	1603.4	1648.9	1699.4	1751.6	1803.8	1854.4
37.5°	1477.1	1502.4	1529.3	1566.4	1605.1	1642.2	1680.9	1755.0	1829.1	1904.9	1979.0
40°	1552.9	1569.7	1586.6	1621.9	1657.3	1692.7	1728.0	1820.7	1913.3	2006.0	2098.6
42.5°	1662.4	1657.3	1652.3	1680.9	1711.2	1739.8	1770.2	1854.4	1938.6	2022.8	2107.0
45°	1778.6	1758.4	1738.2	1751.6	1766.8	1780.3	1795.4	1881.3	1967.2	2054.8	2140.7
47.5°	1918.4	1867.8	1817.3	1805.5	1793.7	1780.3	1768.5	1861.1	1953.7	2048.1	2140.7
50°	2076.7	2000.9	1926.8	1896.5	1864.5	1834.2	1802.2	1877.9	1955.4	2032.9	2108.7
52.5°	2241.7	2147.4	2054.8	2007.6	1960.5	1911.6	1864.5	1928.5	1994.2	2059.8	2123.8
55°	2383.2	2287.2	2189.5	2134.0	2078.4	2022.8	1967.2	2031.2	2095.2	2159.2	2223.2
57.5°	2496.1	2400.1	2304.1	2251.9	2198.0	2145.7	2091.8	2152.5	2214.8	2277.1	2337.7
60°	2573.5	2480.9	2388.3	2337.7	2287.2	2236.7	2186.2	2258.6	2331.0	2405.1	2477.5
62.5°	2533.1	2465.8	2398.4	2376.5	2354.6	2331.0	2309.1	2378.2	2445.5	2514.6	2583.7
65°	2384.9	2339.4	2294.0	2315.9	2339.4	2361.3	2384.9	2430.4	2475.9	2523.0	2568.5
67.5°	2144.1	2140.7	2135.6	2184.5	2233.3	2283.9	2332.7	2363.0	2391.6	2422.0	2452.3
70°	1798.8	1817.3	1834.2	1918.4	2002.6	2086.8	2171.0	2182.8	2194.6	2206.4	2218.2
72.5°	1408.0	1431.6	1456.9	1568.0	1677.5	1788.7	1899.8	1893.1	1886.4	1877.9	1871.2
75°	1108.2	1130.1	1153.7	1256.5	1359.2	1461.9	1564.7	1536.0	1509.1	1480.5	1451.8
77.5°	884.2	907.8	933.1	1029.1	1125.1	1222.8	1318.8	1249.7	1180.7	1111.6	1042.6
80°	761.3	773.1	783.2	848.9	912.9	978.6	1044.2	973.5	901.1	828.7	757.9
82.5°	624.9	618.1	613.1	651.8	690.5	729.3	768.0	700.7	633.3	564.2	496.9
85°	466.5	459.8	453.1	473.3	493.5	515.4	535.6	458.1	380.6	301.5	224.0
87.5°	271.2	277.9	284.6	306.5	328.4	352.0	373.9	294.7	215.6	134.7	55.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675959
 CATALOG NUMBER: CCW-SA-2A-727-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675959
 CATALOG NUMBER: CCW-SA-2A-727-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1212.7	1212.7
2.5°	1259.8	1251.4
5°	1190.8	1179.0
7.5°	1115.0	1099.8
10°	1045.9	1025.7
12.5°	1002.1	976.9
15°	985.3	955.0
17.5°	1035.8	1007.2
20°	1113.3	1074.6
22.5°	1207.6	1160.5
25°	1371.0	1313.7
27.5°	1504.0	1445.1
30°	1586.6	1522.6
32.5°	1677.5	1593.3
35°	1771.8	1691.0
37.5°	1886.4	1795.4
40°	2004.3	1909.9
42.5°	2044.7	1984.1
45°	2083.4	2026.2
47.5°	2091.8	2044.7
50°	2100.3	2093.5
52.5°	2123.8	2122.2
55°	2224.9	2226.6
57.5°	2349.5	2359.6
60°	2464.1	2452.3
62.5°	2523.0	2462.4
65°	2482.6	2398.4
67.5°	2361.3	2270.4
70°	2095.2	1972.3
72.5°	1763.4	1655.6
75°	1359.2	1268.2
77.5°	966.8	891.0
80°	680.4	604.6
82.5°	436.2	375.6
85°	197.1	171.8
87.5°	55.6	53.9
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P675959
CATALOG NUMBER: CCW-SA-2A-727-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)