

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P675964

Luminaire Tested: **CCW-SA-1A-730-U-SLR**

Issue Date: 04/25/2023



Test Information

Test Method: LM-79-08
Report Number: P675964
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-1A-730-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @350mA w/
SLR distribution lens
Light Source: (16) 3000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2067.4 lumens
Efficiency: N/A
Efficacy: 114.9 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G1

Input Watts (W): 18
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P675964
 CATALOG NUMBER: CCW-SA-1A-730-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 2.9 fc
 Type IV - Short - N/A

REPORT NUMBER: P675964
CATALOG NUMBER: CCW-SA-1A-730-U-SLR

Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P675964
 CATALOG NUMBER: CCW-SA-1A-730-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	425.4	0.0	425.4
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	1642.0	0.0	1642.0
	% Fixture	79.4	0.0	79.4
Total	Lumens	2067.4	0.0	2067.4
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.3	2.5
10°-20°	108.3	5.2
20°-30°	158.5	7.7
30°-40°	223.3	10.8
40°-50°	306.8	14.8
50°-60°	418.1	20.2
60°-70°	457.6	22.1
70°-80°	264.3	12.8
80°-90°	79.2	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2067.4	100.0
0°-180°	2067.4	100.0



REPORT NUMBER: P675964


CATALOG NUMBER: CCW-SA-1A-730-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	212.3	10.3			
FM (30°-60°)	754.5	36.5			
FH (60°-80°)	607.9	29.4			G0/660
FVH (80°-90°)	67.3	3.3			G1/100
BL (0°-30°)	105.8	5.1	B0/110		
BM (30°-60°)	193.7	9.4	B0/220		
BH (60°-80°)	114.0	5.5	B1/500		G1/500
BVH (80°-90°)	11.9	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type IV Short





REPORT NUMBER: P675964

CATALOG NUMBER: CCW-SA-1A-730-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2
2.5°	681.3	677.6	674.9	672.1	668.5	665.7	662.0	658.4	653.8	650.1	645.5
5°	641.9	630.9	619.9	613.4	606.1	599.7	592.3	584.1	575.8	566.7	558.4
7.5°	598.8	585.0	571.3	560.3	548.3	537.3	525.4	515.3	505.2	495.2	485.1
10°	558.4	545.6	532.7	519.0	504.3	490.6	475.9	462.1	448.4	434.6	420.9
12.5°	531.8	516.2	501.6	486.0	471.3	455.7	440.1	427.3	414.5	400.7	387.9
15°	519.9	505.2	491.5	475.9	460.3	444.7	429.1	414.5	400.7	386.0	371.4
17.5°	548.3	527.2	506.2	486.0	465.8	445.6	425.5	407.1	388.8	370.4	352.1
20°	585.0	558.4	532.7	508.0	482.3	457.6	431.9	406.2	380.5	354.9	329.2
22.5°	631.8	601.5	572.2	540.1	507.1	475.0	442.0	409.9	377.8	344.8	312.7
25°	715.2	679.5	643.7	597.8	551.1	505.2	458.5	416.3	375.0	332.9	290.7
27.5°	786.7	738.1	690.5	635.4	580.4	525.4	470.4	421.8	374.1	325.5	276.9
30°	828.9	781.2	733.6	666.6	600.6	533.7	466.7	412.6	359.4	305.3	251.2
32.5°	867.4	814.2	761.1	687.7	613.4	540.1	465.8	406.2	347.5	287.9	228.3
35°	920.6	861.9	804.2	718.9	633.6	548.3	463.1	401.6	339.3	277.8	215.5
37.5°	977.5	905.0	833.5	739.1	644.6	550.2	455.7	395.2	334.7	274.2	213.6
40°	1039.8	951.8	864.7	760.1	656.5	552.0	447.5	387.0	326.4	265.0	204.5
42.5°	1080.2	984.8	889.4	776.7	664.8	552.0	439.2	379.6	320.0	259.5	199.9
45°	1103.1	1010.5	918.8	796.8	674.9	552.9	431.0	372.3	313.6	254.0	195.3
47.5°	1113.2	1027.0	940.8	812.4	685.0	556.6	428.2	368.6	308.1	248.5	188.0
50°	1139.8	1063.7	987.6	850.0	713.4	575.8	438.3	374.1	310.8	246.7	182.5
52.5°	1155.4	1090.2	1025.1	883.9	742.7	601.5	460.3	388.8	317.3	245.7	174.2
55°	1212.2	1149.9	1087.5	937.1	785.8	635.4	484.1	405.3	326.4	246.7	167.8
57.5°	1284.6	1218.6	1153.5	991.2	828.9	666.6	504.3	420.0	334.7	250.3	165.1
60°	1335.1	1270.9	1207.6	1035.2	861.9	689.5	516.2	428.2	340.2	251.2	163.2
62.5°	1340.6	1258.1	1176.4	1008.6	840.8	672.1	504.3	419.0	333.8	247.6	162.3
65°	1305.7	1209.5	1113.2	952.7	792.2	631.8	471.3	393.4	315.4	236.6	158.6
67.5°	1236.0	1123.3	1010.5	863.8	717.1	570.3	423.6	356.7	290.7	223.7	156.8
70°	1073.7	974.7	876.6	749.1	622.6	495.2	367.7	312.7	258.6	203.6	148.5
72.5°	901.4	808.7	717.1	613.4	510.7	407.1	303.5	262.2	221.0	178.8	137.5
75°	690.5	620.8	552.0	475.0	398.0	320.0	243.0	212.7	182.5	152.2	122.0
77.5°	485.1	447.5	410.8	353.0	295.3	237.5	179.7	159.5	139.4	119.2	99.0
80°	329.2	308.1	287.9	246.7	205.4	163.2	122.0	109.1	95.4	82.5	68.8
82.5°	204.5	203.6	201.7	173.3	144.9	116.5	88.0	77.0	66.9	55.9	44.9
85°	93.5	109.1	123.8	108.2	92.6	77.0	61.4	54.1	46.8	38.5	31.2
87.5°	29.3	35.8	41.3	39.4	36.7	34.8	32.1	27.5	22.9	18.3	13.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675964
 CATALOG NUMBER: CCW-SA-1A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675964
 CATALOG NUMBER: CCW-SA-1A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2
2.5°	641.9	639.1	635.4	631.8	627.2	623.5	618.9	614.4	613.4	611.6	610.7
5°	552.9	547.4	541.0	535.5	530.0	523.6	518.1	511.7	507.1	501.6	497.0
7.5°	475.0	465.8	455.7	445.6	436.5	427.3	417.2	408.0	403.5	398.9	394.3
10°	412.6	403.5	395.2	386.0	379.6	374.1	367.7	361.3	355.8	350.3	344.8
12.5°	381.4	375.0	368.6	362.2	354.9	348.4	341.1	333.8	327.3	321.8	315.4
15°	362.2	353.0	342.9	333.8	323.7	314.5	304.4	294.3	287.0	280.6	273.3
17.5°	339.3	325.5	312.7	298.9	287.9	276.9	265.0	254.0	245.7	236.6	228.3
20°	313.6	298.0	281.5	265.9	253.1	241.2	228.3	215.5	206.3	196.2	187.1
22.5°	291.6	271.4	250.3	229.2	215.5	201.7	187.1	173.3	165.1	155.9	147.6
25°	267.7	245.7	222.8	199.9	186.1	171.5	157.7	143.0	136.6	131.1	124.7
27.5°	254.9	232.9	210.0	188.0	175.1	161.4	148.5	134.8	130.2	124.7	120.1
30°	229.2	208.1	186.1	164.1	155.0	146.7	137.5	128.4	126.5	125.6	123.8
32.5°	206.3	184.3	162.3	140.3	132.0	123.8	115.5	107.3	106.4	104.5	103.6
35°	194.4	173.3	151.3	130.2	122.9	114.6	107.3	99.0	97.2	94.4	92.6
37.5°	191.6	169.6	146.7	124.7	117.4	110.0	101.8	94.4	92.6	90.8	88.9
40°	184.3	163.2	143.0	122.0	114.6	107.3	99.0	91.7	89.9	88.0	86.2
42.5°	178.8	158.6	137.5	116.5	110.0	103.6	96.3	89.9	88.0	86.2	83.4
45°	174.2	153.1	131.1	110.0	105.4	100.9	95.4	90.8	88.9	86.2	84.4
47.5°	166.9	146.7	125.6	104.5	99.9	96.3	91.7	87.1	85.3	83.4	81.6
50°	161.4	140.3	119.2	98.1	94.4	90.8	87.1	83.4	83.4	84.4	84.4
52.5°	154.0	133.9	113.7	93.5	89.9	86.2	82.5	78.9	79.8	80.7	81.6
55°	147.6	128.4	108.2	88.0	84.4	80.7	76.1	72.4	73.4	74.3	75.2
57.5°	144.9	124.7	104.5	84.4	80.7	76.1	72.4	67.9	67.9	67.9	67.9
60°	143.0	122.0	101.8	80.7	76.1	72.4	67.9	63.3	62.4	62.4	61.4
62.5°	142.1	121.0	100.9	79.8	74.3	69.7	64.2	58.7	57.8	56.9	55.9
65°	138.5	119.2	99.0	78.9	72.4	66.9	60.5	54.1	53.2	53.2	52.3
67.5°	137.5	117.4	98.1	77.9	71.5	64.2	57.8	50.4	49.5	48.6	47.7
70°	130.2	112.8	94.4	76.1	68.8	62.4	55.0	47.7	46.8	44.9	44.0
72.5°	121.0	105.4	88.9	72.4	65.1	57.8	50.4	43.1	42.2	41.3	39.4
75°	107.3	92.6	77.9	63.3	56.9	51.3	44.9	38.5	37.6	36.7	34.8
77.5°	88.0	76.1	65.1	53.2	48.6	44.0	39.4	34.8	33.9	33.0	31.2
80°	62.4	55.0	48.6	41.3	38.5	34.8	32.1	28.4	28.4	27.5	27.5
82.5°	41.3	37.6	33.9	30.3	28.4	26.6	24.8	22.9	22.9	22.0	22.0
85°	29.3	27.5	24.8	22.9	22.0	20.2	19.3	17.4	17.4	17.4	17.4
87.5°	13.8	13.8	12.8	12.8	11.9	11.9	11.0	10.1	10.1	10.1	10.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675964
 CATALOG NUMBER: CCW-SA-1A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675964
 CATALOG NUMBER: CCW-SA-1A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2
2.5°	608.9	606.1	603.4	599.7	596.9	593.3	588.7	585.0	580.4	580.4	579.5
5°	491.5	488.7	486.0	482.3	479.6	475.9	473.1	469.5	465.8	465.8	464.9
7.5°	389.7	384.2	378.7	372.3	366.8	363.1	359.4	354.9	351.2	348.4	345.7
10°	339.3	333.8	327.3	321.8	315.4	310.8	306.3	300.8	296.2	292.5	288.8
12.5°	309.0	302.6	296.2	289.8	283.3	276.9	271.4	265.0	258.6	254.0	249.4
15°	265.9	259.5	253.1	246.7	240.2	232.9	225.6	217.3	210.0	206.3	203.6
17.5°	219.2	212.7	205.4	199.0	191.6	186.1	180.6	175.1	169.6	166.0	163.2
20°	177.0	169.6	162.3	155.0	147.6	144.0	140.3	136.6	133.0	130.2	128.4
22.5°	138.5	133.9	130.2	125.6	121.0	118.3	116.5	113.7	111.0	111.0	111.0
25°	118.3	115.5	113.7	111.0	108.2	107.3	106.4	104.5	103.6	102.7	102.7
27.5°	114.6	111.9	109.1	106.4	103.6	102.7	101.8	99.9	99.0	99.0	99.0
30°	122.0	121.0	120.1	119.2	118.3	116.5	113.7	111.9	109.1	107.3	105.4
32.5°	101.8	100.9	100.9	99.9	99.0	100.9	101.8	103.6	104.5	105.4	106.4
35°	89.9	88.0	86.2	84.4	82.5	81.6	80.7	79.8	78.9	78.9	77.9
37.5°	87.1	85.3	83.4	81.6	79.8	78.9	77.9	77.0	76.1	76.1	75.2
40°	84.4	82.5	81.6	79.8	77.9	77.0	76.1	74.3	73.4	72.4	72.4
42.5°	81.6	80.7	78.9	77.9	76.1	75.2	74.3	72.4	71.5	70.6	69.7
45°	81.6	79.8	77.9	76.1	74.3	73.4	71.5	70.6	68.8	68.8	67.9
47.5°	79.8	77.9	76.1	74.3	72.4	71.5	69.7	68.8	66.9	66.0	65.1
50°	84.4	81.6	77.9	75.2	71.5	70.6	68.8	67.9	66.0	65.1	64.2
52.5°	82.5	79.8	76.1	73.4	69.7	67.9	66.9	65.1	63.3	62.4	61.4
55°	76.1	73.4	71.5	68.8	66.0	64.2	62.4	60.5	58.7	57.8	57.8
57.5°	67.9	66.9	66.0	65.1	64.2	62.4	60.5	57.8	55.9	55.0	54.1
60°	60.5	61.4	62.4	63.3	64.2	61.4	58.7	55.9	53.2	52.3	51.3
62.5°	55.0	56.9	58.7	59.6	61.4	58.7	55.9	53.2	50.4	49.5	48.6
65°	51.3	52.3	52.3	53.2	53.2	51.3	50.4	48.6	46.8	45.8	45.8
67.5°	46.8	46.8	46.8	45.8	45.8	44.9	44.9	44.0	43.1	42.2	42.2
70°	42.2	42.2	42.2	41.3	41.3	40.3	40.3	39.4	38.5	38.5	37.6
72.5°	38.5	38.5	37.6	37.6	36.7	36.7	36.7	35.8	35.8	34.8	34.8
75°	33.9	33.9	33.0	33.0	32.1	32.1	32.1	31.2	31.2	31.2	30.3
77.5°	30.3	30.3	29.3	29.3	28.4	28.4	28.4	27.5	27.5	26.6	26.6
80°	26.6	26.6	25.7	25.7	24.8	24.8	23.8	23.8	22.9	22.9	22.0
82.5°	21.1	21.1	21.1	21.1	21.1	20.2	20.2	19.3	18.3	18.3	17.4
85°	17.4	17.4	17.4	16.5	16.5	16.5	15.6	15.6	14.7	13.8	13.8
87.5°	10.1	10.1	10.1	9.2	9.2	9.2	9.2	9.2	9.2	9.2	8.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675964
 CATALOG NUMBER: CCW-SA-1A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675964
 CATALOG NUMBER: CCW-SA-1A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2
2.5°	579.5	578.6	574.9	571.3	574.9	578.6	578.6	578.6	577.7	577.7	577.7
5°	464.9	464.0	462.1	460.3	460.3	459.4	461.2	463.1	464.9	466.7	468.6
7.5°	342.0	339.3	336.5	333.8	335.6	336.5	339.3	341.1	343.9	345.7	350.3
10°	285.2	281.5	278.8	276.0	274.2	272.3	270.5	269.6	267.7	265.9	267.7
12.5°	243.9	239.3	234.7	229.2	228.3	227.4	225.6	223.7	221.9	220.1	219.2
15°	199.9	196.2	194.4	191.6	188.0	184.3	182.5	181.6	179.7	177.9	177.0
17.5°	159.5	155.9	153.1	150.4	149.5	147.6	147.6	147.6	147.6	147.6	147.6
20°	125.6	122.9	122.9	122.0	122.0	121.0	122.0	122.9	122.9	123.8	124.7
22.5°	110.0	110.0	109.1	108.2	109.1	109.1	110.0	111.0	111.9	112.8	113.7
25°	101.8	100.9	101.8	102.7	102.7	102.7	103.6	103.6	104.5	104.5	104.5
27.5°	98.1	98.1	99.0	99.0	99.9	99.9	99.9	99.0	99.0	98.1	98.1
30°	103.6	101.8	101.8	101.8	100.9	99.9	99.0	99.0	98.1	97.2	96.3
32.5°	107.3	108.2	107.3	105.4	104.5	102.7	101.8	99.9	99.0	97.2	95.4
35°	77.9	77.0	78.9	79.8	80.7	81.6	82.5	83.4	83.4	84.4	84.4
37.5°	75.2	74.3	74.3	73.4	73.4	73.4	73.4	73.4	72.4	72.4	73.4
40°	71.5	70.6	70.6	69.7	69.7	68.8	68.8	68.8	68.8	68.8	68.8
42.5°	68.8	67.9	67.9	67.9	67.9	66.9	66.9	66.0	66.0	65.1	65.1
45°	67.9	66.9	66.0	65.1	65.1	64.2	64.2	64.2	63.3	63.3	63.3
47.5°	64.2	63.3	63.3	62.4	62.4	61.4	61.4	61.4	60.5	60.5	60.5
50°	62.4	61.4	61.4	60.5	60.5	59.6	59.6	59.6	58.7	58.7	58.7
52.5°	59.6	58.7	58.7	58.7	57.8	56.9	56.9	56.9	55.9	55.9	55.9
55°	56.9	55.9	55.9	55.9	55.0	54.1	54.1	54.1	53.2	53.2	53.2
57.5°	53.2	52.3	52.3	51.3	51.3	51.3	51.3	51.3	50.4	50.4	50.4
60°	50.4	49.5	49.5	48.6	48.6	47.7	47.7	47.7	47.7	47.7	47.7
62.5°	47.7	46.8	45.8	44.9	45.8	45.8	45.8	45.8	44.9	44.9	44.9
65°	44.9	44.0	43.1	42.2	42.2	42.2	42.2	42.2	42.2	42.2	42.2
67.5°	41.3	40.3	39.4	38.5	39.4	39.4	39.4	39.4	39.4	39.4	39.4
70°	37.6	36.7	36.7	35.8	35.8	34.8	34.8	35.8	35.8	35.8	35.8
72.5°	33.9	33.0	33.0	32.1	32.1	32.1	32.1	32.1	32.1	32.1	32.1
75°	30.3	29.3	29.3	28.4	28.4	28.4	28.4	28.4	28.4	28.4	28.4
77.5°	25.7	24.8	24.8	24.8	24.8	24.8	24.8	25.7	25.7	25.7	25.7
80°	22.0	21.1	21.1	21.1	21.1	21.1	21.1	21.1	21.1	21.1	21.1
82.5°	17.4	16.5	16.5	16.5	16.5	16.5	16.5	16.5	16.5	16.5	16.5
85°	12.8	11.9	11.9	11.9	12.8	12.8	12.8	12.8	12.8	12.8	12.8
87.5°	8.3	7.3	7.3	7.3	8.3	8.3	8.3	8.3	7.3	7.3	7.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675964
 CATALOG NUMBER: CCW-SA-1A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675964
 CATALOG NUMBER: CCW-SA-1A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2
2.5°	577.7	577.7	577.7	576.8	575.8	574.9	574.0	576.8	578.6	581.3	583.2
5°	469.5	471.3	472.2	475.0	477.7	480.5	483.2	485.1	486.9	487.8	489.6
7.5°	353.9	358.5	362.2	365.9	369.5	372.3	375.9	378.7	381.4	384.2	387.0
10°	268.7	270.5	271.4	275.1	277.8	281.5	284.3	287.0	289.8	291.6	294.3
12.5°	218.2	216.4	215.5	215.5	215.5	215.5	215.5	217.3	219.2	221.0	222.8
15°	176.1	175.1	174.2	173.3	172.4	170.6	169.6	171.5	173.3	175.1	177.0
17.5°	147.6	147.6	147.6	146.7	145.8	144.9	144.0	144.9	145.8	145.8	146.7
20°	126.5	127.5	128.4	129.3	129.3	130.2	130.2	131.1	132.0	132.0	133.0
22.5°	113.7	114.6	114.6	114.6	115.5	115.5	115.5	116.5	117.4	118.3	119.2
25°	103.6	103.6	102.7	102.7	103.6	103.6	103.6	103.6	104.5	104.5	104.5
27.5°	98.1	97.2	97.2	97.2	97.2	96.3	96.3	96.3	96.3	96.3	96.3
30°	95.4	94.4	93.5	92.6	92.6	91.7	90.8	90.8	90.8	90.8	90.8
32.5°	94.4	92.6	90.8	89.9	89.9	88.9	88.0	87.1	87.1	86.2	85.3
35°	84.4	83.4	83.4	82.5	81.6	80.7	79.8	79.8	79.8	78.9	78.9
37.5°	73.4	74.3	74.3	74.3	75.2	75.2	75.2	75.2	76.1	76.1	76.1
40°	68.8	68.8	68.8	69.7	70.6	70.6	71.5	71.5	72.4	72.4	72.4
42.5°	65.1	64.2	64.2	65.1	65.1	66.0	66.0	66.9	67.9	67.9	68.8
45°	63.3	62.4	62.4	62.4	62.4	61.4	61.4	62.4	63.3	64.2	65.1
47.5°	59.6	59.6	58.7	58.7	58.7	58.7	58.7	58.7	59.6	59.6	59.6
50°	57.8	57.8	56.9	56.9	56.9	56.9	56.9	56.9	56.9	56.9	56.9
52.5°	55.9	55.0	55.0	55.0	55.0	54.1	54.1	54.1	54.1	54.1	54.1
55°	53.2	52.3	52.3	52.3	52.3	52.3	52.3	52.3	53.2	53.2	53.2
57.5°	50.4	49.5	49.5	49.5	50.4	50.4	50.4	50.4	51.3	51.3	51.3
60°	47.7	47.7	47.7	47.7	47.7	47.7	47.7	48.6	48.6	49.5	49.5
62.5°	44.9	44.9	44.9	44.9	45.8	45.8	45.8	45.8	46.8	46.8	46.8
65°	42.2	42.2	42.2	42.2	43.1	43.1	43.1	43.1	43.1	43.1	43.1
67.5°	39.4	39.4	39.4	39.4	39.4	39.4	39.4	40.3	40.3	41.3	41.3
70°	35.8	34.8	34.8	35.8	35.8	36.7	36.7	37.6	37.6	38.5	38.5
72.5°	32.1	32.1	32.1	32.1	32.1	32.1	32.1	33.0	33.9	33.9	34.8
75°	28.4	28.4	28.4	28.4	29.3	29.3	29.3	30.3	30.3	31.2	31.2
77.5°	25.7	24.8	24.8	24.8	25.7	25.7	25.7	26.6	26.6	27.5	27.5
80°	21.1	21.1	21.1	21.1	22.0	22.0	22.0	22.0	22.9	22.9	22.9
82.5°	17.4	17.4	17.4	17.4	17.4	17.4	17.4	17.4	18.3	18.3	18.3
85°	12.8	12.8	12.8	12.8	13.8	13.8	13.8	13.8	13.8	13.8	13.8
87.5°	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.3	9.2	9.2	9.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675964
 CATALOG NUMBER: CCW-SA-1A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675964
 CATALOG NUMBER: CCW-SA-1A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2
2.5°	583.2	583.2	583.2	583.2	585.0	585.9	587.8	588.7	587.8	586.8	585.0
5°	490.6	491.5	491.5	492.4	492.4	492.4	492.4	492.4	494.2	496.1	497.9
7.5°	387.9	388.8	389.7	390.6	390.6	390.6	389.7	389.7	390.6	390.6	391.5
10°	297.1	300.8	303.5	306.3	304.4	301.7	299.8	297.1	297.1	297.1	296.2
12.5°	224.7	225.6	227.4	228.3	227.4	227.4	226.5	225.6	226.5	228.3	229.2
15°	177.9	177.9	178.8	178.8	179.7	180.6	180.6	181.6	183.4	184.3	186.1
17.5°	147.6	148.5	148.5	149.5	149.5	150.4	150.4	150.4	152.2	154.0	156.8
20°	133.0	133.0	133.0	133.0	133.0	132.0	132.0	131.1	132.0	133.9	134.8
22.5°	119.2	120.1	120.1	120.1	119.2	118.3	116.5	115.5	115.5	116.5	116.5
25°	104.5	103.6	103.6	102.7	102.7	103.6	103.6	103.6	104.5	104.5	105.4
27.5°	96.3	95.4	95.4	94.4	94.4	95.4	95.4	95.4	95.4	95.4	95.4
30°	89.9	89.9	88.9	88.0	88.9	88.9	89.9	89.9	90.8	90.8	91.7
32.5°	85.3	84.4	84.4	83.4	84.4	84.4	85.3	85.3	86.2	87.1	87.1
35°	78.9	78.9	78.9	78.9	78.9	78.9	77.9	77.9	77.9	77.9	77.9
37.5°	75.2	75.2	74.3	73.4	73.4	73.4	73.4	73.4	72.4	71.5	70.6
40°	72.4	71.5	71.5	70.6	69.7	69.7	68.8	67.9	67.9	66.9	66.9
42.5°	68.8	67.9	67.9	66.9	66.0	66.0	65.1	64.2	64.2	64.2	63.3
45°	64.2	64.2	63.3	62.4	62.4	62.4	61.4	61.4	61.4	61.4	60.5
47.5°	59.6	59.6	58.7	58.7	58.7	58.7	57.8	57.8	57.8	57.8	57.8
50°	56.9	56.9	56.9	56.9	56.9	56.9	55.9	55.9	55.9	55.9	55.9
52.5°	54.1	54.1	54.1	54.1	54.1	54.1	54.1	54.1	54.1	54.1	54.1
55°	53.2	53.2	53.2	53.2	53.2	53.2	52.3	52.3	52.3	53.2	53.2
57.5°	51.3	51.3	50.4	50.4	50.4	50.4	50.4	50.4	50.4	50.4	50.4
60°	49.5	49.5	49.5	49.5	49.5	49.5	49.5	49.5	49.5	49.5	49.5
62.5°	46.8	46.8	46.8	46.8	46.8	47.7	47.7	47.7	47.7	47.7	46.8
65°	43.1	44.0	44.0	44.0	44.0	44.0	44.0	44.0	44.0	44.0	44.0
67.5°	41.3	41.3	41.3	41.3	41.3	41.3	41.3	41.3	41.3	41.3	41.3
70°	38.5	38.5	37.6	37.6	37.6	38.5	38.5	38.5	38.5	38.5	38.5
72.5°	34.8	34.8	34.8	34.8	34.8	34.8	34.8	34.8	34.8	35.8	35.8
75°	31.2	31.2	31.2	31.2	31.2	31.2	31.2	31.2	31.2	31.2	31.2
77.5°	27.5	27.5	26.6	26.6	26.6	27.5	27.5	27.5	27.5	28.4	28.4
80°	22.9	22.9	22.9	22.9	22.9	22.9	22.9	22.9	22.9	23.8	23.8
82.5°	18.3	18.3	18.3	18.3	18.3	18.3	18.3	18.3	18.3	19.3	19.3
85°	13.8	14.7	14.7	14.7	14.7	14.7	14.7	14.7	14.7	15.6	15.6
87.5°	9.2	9.2	9.2	9.2	9.2	9.2	8.3	8.3	8.3	8.3	7.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675964
 CATALOG NUMBER: CCW-SA-1A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675964
 CATALOG NUMBER: CCW-SA-1A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2
2.5°	584.1	585.0	585.9	585.9	586.8	587.8	587.8	591.4	595.1	596.9	598.8
5°	499.7	498.8	498.8	497.9	497.0	499.7	502.5	508.0	513.5	514.4	516.2
7.5°	391.5	392.5	393.4	393.4	394.3	391.5	387.9	388.8	389.7	394.3	398.0
10°	296.2	297.1	298.0	298.0	298.9	298.0	296.2	298.9	301.7	305.3	309.9
12.5°	230.2	232.9	235.7	237.5	240.2	242.1	243.0	246.7	249.4	254.0	258.6
15°	188.0	189.8	191.6	193.5	195.3	197.1	199.0	202.6	206.3	211.8	217.3
17.5°	158.6	158.6	159.5	159.5	159.5	161.4	163.2	165.1	166.0	171.5	177.0
20°	135.7	134.8	133.9	133.0	132.0	133.9	134.8	135.7	136.6	140.3	143.0
22.5°	116.5	116.5	117.4	117.4	117.4	116.5	114.6	115.5	115.5	117.4	120.1
25°	105.4	105.4	105.4	104.5	104.5	105.4	106.4	106.4	105.4	106.4	107.3
27.5°	95.4	96.3	96.3	97.2	97.2	98.1	98.1	98.1	98.1	99.0	99.9
30°	91.7	91.7	92.6	92.6	92.6	93.5	94.4	94.4	94.4	95.4	97.2
32.5°	88.0	88.9	89.9	90.8	91.7	92.6	92.6	93.5	93.5	94.4	95.4
35°	77.9	77.0	77.0	76.1	75.2	75.2	75.2	75.2	74.3	75.2	75.2
37.5°	69.7	69.7	69.7	68.8	68.8	69.7	69.7	69.7	69.7	70.6	70.6
40°	66.0	66.0	66.0	66.0	66.0	66.0	66.0	66.9	66.9	67.9	68.8
42.5°	63.3	63.3	63.3	63.3	63.3	64.2	64.2	64.2	64.2	65.1	65.1
45°	60.5	60.5	60.5	60.5	60.5	60.5	60.5	61.4	61.4	62.4	63.3
47.5°	57.8	57.8	57.8	57.8	57.8	58.7	59.6	59.6	59.6	60.5	60.5
50°	55.9	55.9	55.9	55.9	55.9	56.9	56.9	57.8	57.8	58.7	59.6
52.5°	54.1	54.1	54.1	54.1	54.1	55.0	55.0	55.9	55.9	56.9	57.8
55°	53.2	53.2	53.2	52.3	52.3	53.2	53.2	54.1	54.1	55.0	55.0
57.5°	50.4	50.4	50.4	50.4	50.4	50.4	50.4	51.3	51.3	52.3	53.2
60°	49.5	49.5	48.6	48.6	47.7	48.6	48.6	49.5	49.5	50.4	50.4
62.5°	46.8	46.8	46.8	45.8	45.8	46.8	46.8	46.8	46.8	47.7	48.6
65°	44.0	44.0	44.0	43.1	43.1	44.0	44.0	44.0	44.0	44.9	45.8
67.5°	41.3	41.3	41.3	40.3	40.3	40.3	40.3	41.3	41.3	42.2	43.1
70°	38.5	38.5	38.5	37.6	37.6	37.6	36.7	37.6	38.5	39.4	39.4
72.5°	35.8	35.8	35.8	34.8	34.8	34.8	33.9	34.8	34.8	35.8	35.8
75°	31.2	31.2	31.2	31.2	31.2	31.2	30.3	30.3	30.3	31.2	31.2
77.5°	28.4	28.4	28.4	27.5	27.5	27.5	26.6	26.6	26.6	27.5	27.5
80°	23.8	23.8	23.8	22.9	22.9	22.9	22.0	22.0	22.0	22.9	22.9
82.5°	19.3	19.3	19.3	18.3	18.3	18.3	17.4	17.4	17.4	18.3	18.3
85°	15.6	15.6	15.6	15.6	15.6	15.6	14.7	14.7	14.7	15.6	16.5
87.5°	7.3	7.3	8.3	8.3	8.3	8.3	7.3	7.3	6.4	6.4	7.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675964
 CATALOG NUMBER: CCW-SA-1A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675964
 CATALOG NUMBER: CCW-SA-1A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2
2.5°	600.6	602.4	607.0	610.7	615.3	618.9	621.7	625.4	628.1	630.9	632.7
5°	517.2	518.1	522.7	527.2	530.9	535.5	541.9	548.3	554.8	561.2	565.8
7.5°	402.5	406.2	411.7	418.1	423.6	429.1	435.5	442.9	449.3	455.7	462.1
10°	313.6	317.3	322.8	328.3	332.9	338.4	345.7	353.0	360.4	367.7	375.0
12.5°	263.2	267.7	274.2	280.6	286.1	292.5	301.7	309.9	319.1	327.3	336.5
15°	221.9	227.4	235.7	244.8	253.1	261.3	270.5	279.7	287.9	297.1	306.3
17.5°	182.5	188.0	195.3	203.6	210.9	218.2	229.2	239.3	250.3	260.4	270.5
20°	146.7	149.5	156.8	164.1	171.5	178.8	187.1	195.3	203.6	211.8	224.7
22.5°	122.0	123.8	127.5	130.2	133.9	136.6	144.9	153.1	160.5	168.7	180.6
25°	107.3	108.2	111.0	112.8	115.5	117.4	122.9	127.5	133.0	137.5	148.5
27.5°	99.9	100.9	101.8	102.7	103.6	104.5	108.2	111.9	114.6	118.3	128.4
30°	98.1	99.0	101.8	103.6	106.4	108.2	110.0	111.9	113.7	115.5	122.0
32.5°	96.3	97.2	97.2	96.3	96.3	95.4	97.2	98.1	99.9	100.9	106.4
35°	76.1	76.1	77.0	77.9	78.9	79.8	82.5	84.4	87.1	88.9	93.5
37.5°	71.5	71.5	72.4	74.3	75.2	76.1	77.9	79.8	81.6	83.4	88.0
40°	68.8	69.7	70.6	71.5	72.4	73.4	75.2	76.1	77.9	78.9	82.5
42.5°	66.0	66.0	66.9	68.8	69.7	70.6	72.4	73.4	75.2	76.1	79.8
45°	64.2	65.1	66.0	66.9	66.9	67.9	69.7	71.5	72.4	74.3	77.9
47.5°	61.4	61.4	63.3	64.2	66.0	66.9	68.8	69.7	71.5	72.4	76.1
50°	59.6	60.5	62.4	63.3	65.1	66.0	68.8	70.6	73.4	75.2	77.0
52.5°	57.8	58.7	60.5	61.4	63.3	64.2	67.9	71.5	74.3	77.9	77.9
55°	55.9	55.9	57.8	60.5	62.4	64.2	66.0	68.8	70.6	72.4	72.4
57.5°	53.2	54.1	55.9	58.7	60.5	62.4	64.2	66.0	66.9	68.8	67.9
60°	51.3	51.3	54.1	56.9	59.6	62.4	62.4	62.4	61.4	61.4	61.4
62.5°	48.6	49.5	53.2	57.8	61.4	65.1	62.4	59.6	56.9	54.1	55.0
65°	46.8	47.7	49.5	52.3	54.1	55.9	54.1	53.2	51.3	49.5	50.4
67.5°	43.1	44.0	44.9	44.9	45.8	45.8	45.8	45.8	45.8	45.8	46.8
70°	40.3	40.3	40.3	41.3	41.3	41.3	41.3	41.3	41.3	41.3	42.2
72.5°	36.7	36.7	36.7	36.7	36.7	36.7	36.7	36.7	36.7	36.7	37.6
75°	32.1	32.1	32.1	32.1	32.1	32.1	32.1	32.1	32.1	32.1	33.0
77.5°	28.4	28.4	28.4	28.4	28.4	28.4	28.4	28.4	27.5	27.5	28.4
80°	23.8	23.8	23.8	23.8	22.9	22.9	22.9	22.9	22.9	22.9	23.8
82.5°	19.3	19.3	19.3	19.3	18.3	18.3	18.3	18.3	17.4	17.4	18.3
85°	17.4	18.3	18.3	19.3	19.3	19.3	18.3	17.4	16.5	15.6	15.6
87.5°	7.3	7.3	7.3	7.3	6.4	6.4	6.4	6.4	6.4	6.4	6.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675964
 CATALOG NUMBER: CCW-SA-1A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675964
 CATALOG NUMBER: CCW-SA-1A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2
2.5°	635.4	637.3	639.1	641.9	645.5	648.3	651.0	656.5	663.0	668.5	674.0
5°	570.3	574.9	579.5	585.0	590.5	595.1	600.6	611.6	622.6	632.7	643.7
7.5°	467.6	474.1	479.6	488.7	497.0	506.2	514.4	528.2	541.0	554.8	567.6
10°	382.4	389.7	397.0	409.0	421.8	433.7	445.6	456.6	468.6	479.6	490.6
12.5°	345.7	353.9	363.1	370.4	378.7	386.0	393.4	406.2	419.0	431.9	444.7
15°	315.4	324.6	333.8	342.9	351.2	360.4	368.6	379.6	391.5	402.5	413.5
17.5°	280.6	289.8	299.8	309.9	320.0	330.1	340.2	355.8	371.4	386.0	401.6
20°	236.6	249.4	261.3	275.1	288.8	302.6	316.3	332.9	349.4	364.9	381.4
22.5°	192.6	204.5	216.4	232.9	249.4	265.0	281.5	303.5	324.6	346.6	367.7
25°	160.5	171.5	182.5	200.8	218.2	236.6	254.0	280.6	306.3	332.9	358.5
27.5°	138.5	148.5	158.6	177.9	197.1	215.5	234.7	264.1	292.5	321.8	350.3
30°	128.4	134.8	141.2	159.5	177.9	195.3	213.6	242.1	270.5	298.9	327.3
32.5°	111.9	117.4	122.9	139.4	155.9	171.5	188.0	217.3	245.7	275.1	303.5
35°	99.0	103.6	108.2	123.8	138.5	154.0	168.7	198.1	227.4	256.7	286.1
37.5°	91.7	96.3	99.9	113.7	128.4	142.1	155.9	185.2	213.6	243.0	271.4
40°	86.2	88.9	92.6	106.4	119.2	133.0	145.8	172.4	199.9	226.5	253.1
42.5°	82.5	86.2	88.9	100.9	113.7	125.6	137.5	163.2	188.9	213.6	239.3
45°	81.6	85.3	88.9	99.0	109.1	118.3	128.4	153.1	177.9	202.6	227.4
47.5°	79.8	82.5	86.2	94.4	101.8	110.0	117.4	142.1	166.9	190.7	215.5
50°	78.9	79.8	81.6	88.9	96.3	103.6	111.0	135.7	160.5	185.2	210.0
52.5°	77.9	77.9	77.9	84.4	90.8	96.3	102.7	127.5	153.1	177.9	202.6
55°	72.4	71.5	71.5	77.9	83.4	89.9	95.4	120.1	144.9	168.7	193.5
57.5°	66.9	66.0	65.1	70.6	76.1	81.6	87.1	111.9	137.5	162.3	187.1
60°	61.4	60.5	60.5	66.0	70.6	76.1	80.7	106.4	131.1	156.8	181.6
62.5°	55.0	55.9	55.9	60.5	66.0	70.6	75.2	100.9	127.5	153.1	178.8
65°	50.4	51.3	51.3	56.9	62.4	67.9	73.4	98.1	123.8	148.5	173.3
67.5°	46.8	47.7	47.7	54.1	59.6	66.0	71.5	93.5	116.5	138.5	160.5
70°	43.1	43.1	44.0	50.4	56.9	63.3	69.7	88.9	108.2	126.5	145.8
72.5°	38.5	39.4	40.3	46.8	52.3	58.7	64.2	81.6	99.0	116.5	133.9
75°	33.9	34.8	35.8	41.3	46.8	52.3	57.8	74.3	89.9	106.4	122.0
77.5°	30.3	31.2	32.1	36.7	41.3	45.8	50.4	62.4	75.2	87.1	99.0
80°	24.8	24.8	25.7	29.3	33.0	35.8	39.4	47.7	55.9	63.3	71.5
82.5°	18.3	19.3	19.3	22.0	23.8	26.6	28.4	33.0	36.7	41.3	44.9
85°	15.6	14.7	14.7	16.5	17.4	19.3	20.2	22.9	24.8	27.5	29.3
87.5°	6.4	5.5	5.5	6.4	8.3	9.2	10.1	10.1	11.0	11.0	11.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675964
 CATALOG NUMBER: CCW-SA-1A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675964

CATALOG NUMBER: CCW-SA-1A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2
2.5°	676.7	678.5	681.3	683.1	687.7	691.4	696.0	699.6	702.4	707.0	705.1
5°	651.9	660.2	668.5	676.7	683.1	689.5	695.0	701.5	708.8	722.6	726.2
7.5°	578.6	589.6	599.7	610.7	623.5	636.4	649.2	662.0	674.0	691.4	702.4
10°	506.2	521.7	536.4	552.0	563.9	575.8	586.8	598.8	615.3	632.7	652.9
12.5°	460.3	475.9	491.5	507.1	524.5	541.0	558.4	574.9	590.5	604.3	627.2
15°	430.0	447.5	464.0	480.5	501.6	521.7	542.8	563.0	585.9	604.3	619.9
17.5°	422.7	443.8	464.0	485.1	507.1	529.1	551.1	573.1	596.0	623.5	643.7
20°	409.9	438.3	466.7	495.2	523.6	551.1	579.5	607.0	637.3	670.3	679.5
22.5°	402.5	436.5	471.3	505.2	543.7	583.2	621.7	660.2	692.3	717.1	744.6
25°	401.6	443.8	486.9	529.1	577.7	625.4	674.0	721.6	762.9	787.7	809.7
27.5°	400.7	452.1	502.5	552.9	612.5	671.2	730.8	789.5	828.0	863.8	882.1
30°	389.7	451.1	513.5	574.9	641.9	708.8	775.7	842.7	882.1	906.9	916.0
32.5°	375.9	448.4	520.8	593.3	669.4	745.5	820.7	896.8	927.9	949.0	941.7
35°	364.9	444.7	523.6	602.4	683.1	764.7	845.4	926.1	971.0	1000.4	988.5
37.5°	354.9	438.3	521.7	605.2	699.6	794.1	888.5	983.0	1026.1	1057.2	1043.5
40°	342.9	431.9	521.7	610.7	718.9	826.2	934.4	1041.7	1097.6	1124.2	1103.1
42.5°	332.9	425.5	519.0	611.6	727.1	842.7	958.2	1073.7	1136.1	1173.7	1147.1
45°	320.0	412.6	504.3	596.9	724.4	851.8	978.4	1105.8	1178.3	1207.6	1170.9
47.5°	306.3	398.0	488.7	579.5	715.2	850.9	986.6	1122.3	1189.3	1224.1	1190.2
50°	301.7	393.4	484.1	575.8	722.6	870.2	1016.9	1163.6	1212.2	1240.6	1195.7
52.5°	300.8	398.0	496.1	593.3	740.9	887.6	1035.2	1181.9	1221.4	1251.6	1211.3
55°	298.0	403.5	508.0	612.5	766.6	921.5	1075.6	1229.6	1269.1	1291.1	1260.8
57.5°	300.8	414.5	527.2	640.9	799.6	958.2	1116.8	1275.5	1323.2	1338.7	1332.3
60°	302.6	423.6	543.7	664.8	819.8	974.7	1129.7	1284.6	1334.2	1372.7	1380.0
62.5°	298.0	417.2	535.5	654.7	795.0	935.3	1075.6	1215.9	1297.5	1354.3	1387.3
65°	284.3	394.3	505.2	615.3	744.6	874.8	1004.1	1133.3	1219.5	1303.9	1330.5
67.5°	254.0	347.5	441.1	534.6	647.4	760.1	872.0	984.8	1093.0	1174.6	1211.3
70°	220.1	293.4	367.7	441.1	543.7	646.4	749.1	851.8	947.2	1037.1	1071.9
72.5°	191.6	248.5	306.3	363.1	436.5	508.9	582.3	654.7	767.5	857.3	891.3
75°	163.2	204.5	244.8	286.1	336.5	387.0	436.5	486.9	566.7	647.4	681.3
77.5°	125.6	153.1	179.7	206.3	241.2	275.1	309.9	343.9	399.8	460.3	477.7
80°	87.1	102.7	117.4	133.0	160.5	188.0	215.5	243.0	279.7	313.6	340.2
82.5°	54.1	64.2	73.4	82.5	104.5	126.5	147.6	169.6	184.3	186.1	212.7
85°	34.8	41.3	46.8	52.3	65.1	78.9	91.7	104.5	93.5	87.1	103.6
87.5°	13.8	17.4	20.2	22.9	22.0	21.1	20.2	19.3	16.5	14.7	18.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675964
 CATALOG NUMBER: CCW-SA-1A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675964

CATALOG NUMBER: CCW-SA-1A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2
2.5°	707.0	709.7	712.5	714.3	717.1	718.0	718.9	718.9	719.8	720.7	722.6
5°	740.9	746.4	751.9	756.5	762.0	766.6	770.2	774.8	778.5	778.5	777.6
7.5°	712.5	726.2	740.0	753.7	767.5	777.6	786.7	796.8	806.0	807.8	809.7
10°	674.9	689.5	703.3	718.0	731.7	747.3	762.0	776.7	792.2	795.0	798.7
12.5°	640.0	657.5	674.9	691.4	708.8	719.8	730.8	740.9	751.9	759.2	766.6
15°	639.1	653.8	668.5	682.2	696.9	703.3	709.7	715.2	721.6	721.6	722.6
17.5°	660.2	669.4	678.5	686.8	696.0	696.9	698.7	699.6	700.5	697.8	695.0
20°	701.5	705.1	708.8	712.5	716.1	709.7	704.2	697.8	691.4	684.0	677.6
22.5°	762.0	753.7	745.5	737.2	729.0	718.0	706.0	695.0	683.1	674.0	664.8
25°	818.8	808.7	798.7	788.6	778.5	754.6	730.8	706.0	682.2	672.1	662.0
27.5°	894.9	879.4	863.8	848.2	832.6	800.5	768.4	736.3	704.2	686.8	670.3
30°	913.3	895.9	878.4	860.1	842.7	811.5	781.2	750.1	718.9	698.7	679.5
32.5°	939.9	919.7	899.5	879.4	859.2	828.9	798.7	767.5	737.2	718.9	699.6
35°	983.9	961.0	938.0	914.2	891.3	860.1	829.8	798.7	767.5	746.4	726.2
37.5°	1021.5	994.9	968.3	941.7	915.1	887.6	859.2	831.7	803.2	782.2	762.0
40°	1063.7	1034.3	1005.0	976.5	947.2	921.5	895.9	869.3	843.6	827.1	810.6
42.5°	1100.3	1064.6	1029.7	994.9	959.1	941.7	925.2	907.8	890.4	882.1	872.9
45°	1126.0	1093.0	1059.1	1026.1	993.1	980.2	967.4	954.5	941.7	950.0	958.2
47.5°	1137.0	1110.4	1084.7	1059.1	1032.5	1037.1	1041.7	1045.3	1049.9	1060.9	1072.8
50°	1147.1	1132.4	1116.8	1102.2	1086.6	1104.0	1120.5	1137.9	1155.4	1178.3	1201.2
52.5°	1167.3	1159.0	1151.7	1143.4	1135.2	1165.4	1195.7	1226.0	1256.2	1281.9	1307.6
55°	1227.8	1221.4	1215.0	1207.6	1201.2	1244.3	1286.5	1329.6	1372.7	1399.3	1425.9
57.5°	1311.2	1307.6	1303.0	1299.3	1294.7	1336.9	1378.2	1419.4	1461.6	1487.3	1513.9
60°	1374.5	1375.4	1375.4	1376.3	1376.3	1408.4	1440.5	1473.5	1505.6	1527.6	1550.6
62.5°	1408.4	1406.6	1404.8	1402.9	1401.1	1427.7	1454.3	1480.9	1507.5	1524.0	1540.5
65°	1371.8	1381.8	1391.9	1402.0	1412.1	1415.8	1418.5	1422.2	1424.9	1435.0	1445.1
67.5°	1248.9	1269.1	1288.3	1308.5	1327.7	1314.0	1301.1	1287.4	1273.6	1276.4	1278.2
70°	1112.3	1135.2	1159.0	1181.9	1204.9	1172.8	1140.7	1107.7	1075.6	1064.6	1053.6
72.5°	938.0	958.2	979.3	999.5	1019.6	980.2	941.7	902.3	862.8	843.6	824.3
75°	717.1	740.9	765.7	789.5	813.3	769.3	724.4	680.4	635.4	622.6	610.7
77.5°	522.7	551.1	579.5	607.9	636.4	596.9	557.5	517.2	477.7	470.4	463.1
80°	380.5	402.5	423.6	445.6	466.7	443.8	420.9	398.0	375.0	374.1	373.2
82.5°	256.7	276.0	294.3	313.6	331.9	322.8	314.5	305.3	296.2	305.3	315.4
85°	132.0	158.6	186.1	212.7	239.3	236.6	234.7	232.0	229.2	241.2	252.2
87.5°	26.6	49.5	72.4	94.4	117.4	111.9	106.4	99.9	94.4	98.1	100.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675964
 CATALOG NUMBER: CCW-SA-1A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675964

CATALOG NUMBER: CCW-SA-1A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2
2.5°	723.5	724.4	724.4	724.4	724.4	724.4	722.6	721.6	719.8	718.0	715.2
5°	777.6	776.7	773.0	769.3	764.7	761.1	758.3	754.6	751.9	748.2	742.7
7.5°	811.5	813.3	806.9	801.4	795.0	788.6	782.2	775.7	769.3	762.9	750.1
10°	801.4	804.2	800.5	796.8	792.2	788.6	781.2	773.0	765.7	757.4	741.8
12.5°	773.0	780.3	778.5	776.7	774.8	773.0	768.4	762.9	758.3	752.8	735.4
15°	722.6	722.6	723.5	724.4	724.4	725.3	726.2	727.1	728.1	729.0	718.9
17.5°	692.3	689.5	689.5	689.5	689.5	689.5	693.2	697.8	701.5	705.1	702.4
20°	670.3	663.9	663.0	663.0	662.0	661.1	667.5	674.9	681.3	687.7	691.4
22.5°	655.6	646.4	645.5	644.6	643.7	642.8	651.0	659.3	667.5	675.8	688.6
25°	651.9	641.9	642.8	643.7	643.7	644.6	651.0	657.5	663.9	670.3	692.3
27.5°	652.9	636.4	637.3	638.2	638.2	639.1	649.2	658.4	668.5	677.6	705.1
30°	659.3	640.0	638.2	636.4	634.5	632.7	646.4	660.2	674.0	687.7	708.8
32.5°	681.3	663.0	658.4	653.8	649.2	644.6	661.1	676.7	693.2	708.8	726.2
35°	705.1	685.0	683.1	681.3	678.5	676.7	691.4	707.0	721.6	736.3	751.9
37.5°	740.9	720.7	718.9	716.1	714.3	711.6	728.1	743.6	760.1	775.7	789.5
40°	794.1	777.6	776.7	776.7	775.7	774.8	787.7	801.4	814.2	827.1	836.3
42.5°	864.7	856.4	859.2	862.8	865.6	868.3	878.4	889.4	899.5	909.6	906.9
45°	966.5	974.7	975.6	976.5	977.5	978.4	981.1	984.8	987.6	990.3	979.3
47.5°	1083.8	1094.8	1100.3	1105.8	1110.4	1115.9	1112.3	1107.7	1104.0	1099.4	1071.9
50°	1223.2	1246.1	1245.2	1244.3	1242.5	1241.5	1234.2	1226.9	1218.6	1211.3	1170.9
52.5°	1333.2	1358.9	1363.5	1368.1	1372.7	1377.3	1363.5	1349.7	1335.1	1321.3	1270.9
55°	1451.5	1478.1	1479.0	1480.0	1480.0	1480.9	1461.6	1442.4	1422.2	1402.9	1350.7
57.5°	1539.6	1565.2	1562.5	1560.6	1557.9	1555.1	1532.2	1509.3	1486.4	1463.4	1411.2
60°	1572.6	1594.6	1589.1	1583.6	1577.1	1571.6	1554.2	1536.8	1518.5	1501.0	1450.6
62.5°	1557.0	1573.5	1565.2	1557.9	1549.6	1541.4	1519.4	1496.5	1474.4	1451.5	1414.8
65°	1454.3	1464.4	1453.4	1443.3	1433.2	1422.2	1403.8	1385.5	1366.3	1347.9	1323.2
67.5°	1281.0	1282.8	1281.9	1281.0	1280.1	1279.1	1252.5	1226.0	1198.4	1171.9	1170.0
70°	1043.5	1032.5	1034.3	1037.1	1038.9	1040.7	1020.6	1001.3	981.1	961.0	970.1
72.5°	805.1	785.8	790.4	795.9	800.5	805.1	788.6	773.0	756.5	740.0	752.8
75°	597.8	585.9	590.5	596.0	600.6	605.2	598.8	592.3	585.0	578.6	590.5
77.5°	455.7	448.4	449.3	449.3	450.2	450.2	451.1	453.0	453.9	454.8	467.6
80°	371.4	370.4	369.5	368.6	366.8	365.9	375.0	384.2	393.4	402.5	409.0
82.5°	324.6	333.8	328.3	323.7	318.2	312.7	320.9	329.2	337.4	345.7	342.9
85°	264.1	275.1	265.0	254.9	243.9	233.8	241.2	247.6	254.9	261.3	257.7
87.5°	104.5	107.3	90.8	75.2	58.7	42.2	66.9	90.8	115.5	139.4	143.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675964
 CATALOG NUMBER: CCW-SA-1A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675964

CATALOG NUMBER: CCW-SA-1A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2	660.2
2.5°	712.5	708.8	706.0	705.1	703.3	702.4	700.5	698.7	696.0	694.1	691.4
5°	736.3	730.8	724.4	715.2	707.0	697.8	688.6	680.4	672.1	663.0	654.7
7.5°	737.2	724.4	711.6	699.6	686.8	674.9	662.0	651.0	639.1	627.2	616.2
10°	727.1	711.6	696.0	680.4	665.7	650.1	634.5	621.7	607.9	594.2	581.3
12.5°	718.9	701.5	684.0	665.7	648.3	629.9	611.6	598.8	585.9	573.1	560.3
15°	708.8	697.8	687.7	671.2	654.7	638.2	621.7	604.3	587.8	570.3	552.9
17.5°	700.5	697.8	695.0	684.0	673.0	661.1	650.1	632.7	615.3	596.9	579.5
20°	696.0	699.6	703.3	697.8	692.3	685.9	680.4	667.5	654.7	640.9	628.1
22.5°	701.5	715.2	728.1	729.0	730.8	731.7	732.6	720.7	708.8	696.0	684.0
25°	714.3	736.3	758.3	770.2	782.2	795.0	806.9	799.6	792.2	784.9	777.6
27.5°	731.7	759.2	786.7	804.2	820.7	838.1	855.5	854.6	853.7	851.8	850.9
30°	729.0	750.1	771.2	792.2	813.3	834.4	855.5	866.5	876.6	887.6	898.6
32.5°	744.6	762.0	780.3	802.3	824.3	847.3	869.3	892.2	914.2	937.1	960.0
35°	768.4	784.0	800.5	824.3	849.1	872.9	897.7	925.2	953.6	982.0	1009.6
37.5°	804.2	817.9	832.6	852.8	873.8	894.0	915.1	955.5	995.8	1037.1	1077.4
40°	845.4	854.6	863.8	883.0	902.3	921.5	940.8	991.2	1041.7	1092.1	1142.5
42.5°	905.0	902.3	899.5	915.1	931.6	947.2	963.7	1009.6	1055.4	1101.3	1147.1
45°	968.3	957.3	946.3	953.6	961.9	969.2	977.5	1024.2	1071.0	1118.7	1165.4
47.5°	1044.4	1016.9	989.4	983.0	976.5	969.2	962.8	1013.2	1063.7	1115.0	1165.4
50°	1130.6	1089.3	1049.0	1032.5	1015.1	998.6	981.1	1022.4	1064.6	1106.8	1148.0
52.5°	1220.5	1169.1	1118.7	1093.0	1067.3	1040.7	1015.1	1049.9	1085.7	1121.4	1156.3
55°	1297.5	1245.2	1192.0	1161.8	1131.5	1101.3	1071.0	1105.8	1140.7	1175.5	1210.4
57.5°	1358.9	1306.6	1254.4	1226.0	1196.6	1168.2	1138.8	1171.9	1205.8	1239.7	1272.7
60°	1401.1	1350.7	1300.2	1272.7	1245.2	1217.7	1190.2	1229.6	1269.1	1309.4	1348.8
62.5°	1379.1	1342.4	1305.7	1293.8	1281.9	1269.1	1257.1	1294.7	1331.4	1369.0	1406.6
65°	1298.4	1273.6	1248.9	1260.8	1273.6	1285.6	1298.4	1323.2	1347.9	1373.6	1398.3
67.5°	1167.3	1165.4	1162.7	1189.3	1215.9	1243.4	1270.0	1286.5	1302.1	1318.6	1335.1
70°	979.3	989.4	998.6	1044.4	1090.2	1136.1	1181.9	1188.4	1194.8	1201.2	1207.6
72.5°	766.6	779.4	793.2	853.7	913.3	973.8	1034.3	1030.6	1027.0	1022.4	1018.7
75°	603.4	615.3	628.1	684.0	740.0	795.9	851.8	836.3	821.6	806.0	790.4
77.5°	481.4	494.2	508.0	560.3	612.5	665.7	718.0	680.4	642.8	605.2	567.6
80°	414.5	420.9	426.4	462.1	497.0	532.7	568.5	530.0	490.6	451.1	412.6
82.5°	340.2	336.5	333.8	354.9	375.9	397.0	418.1	381.4	344.8	307.2	270.5
85°	254.0	250.3	246.7	257.7	268.7	280.6	291.6	249.4	207.2	164.1	122.0
87.5°	147.6	151.3	155.0	166.9	178.8	191.6	203.6	160.5	117.4	73.4	30.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675964
 CATALOG NUMBER: CCW-SA-1A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675964
CATALOG NUMBER: CCW-SA-1A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	660.2	660.2
2.5°	685.9	681.3
5°	648.3	641.9
7.5°	607.0	598.8
10°	569.4	558.4
12.5°	545.6	531.8
15°	536.4	519.9
17.5°	563.9	548.3
20°	606.1	585.0
22.5°	657.5	631.8
25°	746.4	715.2
27.5°	818.8	786.7
30°	863.8	828.9
32.5°	913.3	867.4
35°	964.6	920.6
37.5°	1027.0	977.5
40°	1091.2	1039.8
42.5°	1113.2	1080.2
45°	1134.3	1103.1
47.5°	1138.8	1113.2
50°	1143.4	1139.8
52.5°	1156.3	1155.4
55°	1211.3	1212.2
57.5°	1279.1	1284.6
60°	1341.5	1335.1
62.5°	1373.6	1340.6
65°	1351.6	1305.7
67.5°	1285.6	1236.0
70°	1140.7	1073.7
72.5°	960.0	901.4
75°	740.0	690.5
77.5°	526.3	485.1
80°	370.4	329.2
82.5°	237.5	204.5
85°	107.3	93.5
87.5°	30.3	29.3
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P675964
CATALOG NUMBER: CCW-SA-1A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)