

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P675979

Luminaire Tested: **CCW-SA-1E-735-U-SLR**

Issue Date: 04/25/2023



Test Information

Test Method: LM-79-08
Report Number: P675979
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-1E-735-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @1050mA w/
SLR distribution lens
Light Source: (16) 3500K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5596.1 lumens
Efficiency: N/A
Efficacy: 99.8 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 56.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



REPORT NUMBER: P675979
 CATALOG NUMBER: CCW-SA-1E-735-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 7.9 fc
 Type IV - Short - N/A

REPORT NUMBER: P675979
CATALOG NUMBER: CCW-SA-1E-735-U-SLR

Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P675979
 CATALOG NUMBER: CCW-SA-1E-735-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1151.4	0.0	1151.4
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	4444.7	0.0	4444.7
	% Fixture	79.4	0.0	79.4
Total	Lumens	5596.1	0.0	5596.1
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.9	2.5
10°-20°	293.2	5.2
20°-30°	428.9	7.7
30°-40°	604.3	10.8
40°-50°	830.4	14.8
50°-60°	1131.8	20.2
60°-70°	1238.8	22.1
70°-80°	715.4	12.8
80°-90°	214.4	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5596.1	100.0
0°-180°	5596.1	100.0




REPORT NUMBER: P675979
 CATALOG NUMBER: CCW-SA-1E-735-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	574.7	10.3			
FM (30°-60°)	2042.2	36.5			
FH (60°-80°)	1645.6	29.4			G1/1800
FVH (80°-90°)	182.2	3.3			G2/225
BL (0°-30°)	286.3	5.1	B1/500		
BM (30°-60°)	524.3	9.4	B1/1000		
BH (60°-80°)	308.6	5.5	B1/500		G1/500
BVH (80°-90°)	32.3	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2
 Type IV Short





REPORT NUMBER: P675979

CATALOG NUMBER: CCW-SA-1E-735-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1
2.5°	1844.1	1834.2	1826.8	1819.3	1809.4	1802.0	1792.0	1782.1	1769.7	1759.8	1747.3
5°	1737.4	1707.6	1677.8	1660.5	1640.6	1623.2	1603.4	1581.1	1558.7	1533.9	1511.6
7.5°	1620.8	1583.5	1546.3	1516.5	1484.3	1454.5	1422.2	1394.9	1367.6	1340.3	1313.0
10°	1511.6	1476.8	1442.1	1404.8	1365.1	1327.9	1288.2	1250.9	1213.7	1176.5	1139.2
12.5°	1439.6	1397.4	1357.7	1315.5	1275.8	1233.6	1191.4	1156.6	1121.9	1084.6	1049.9
15°	1407.3	1367.6	1330.4	1288.2	1246.0	1203.8	1161.6	1121.9	1084.6	1044.9	1005.2
17.5°	1484.3	1427.2	1370.1	1315.5	1260.9	1206.3	1151.7	1102.0	1052.4	1002.7	953.1
20°	1583.5	1511.6	1442.1	1375.0	1305.5	1238.5	1169.0	1099.5	1030.0	960.5	891.0
22.5°	1710.1	1628.2	1548.8	1461.9	1372.6	1285.7	1196.3	1109.5	1022.6	933.2	846.4
25°	1936.0	1839.2	1742.4	1618.3	1491.7	1367.6	1241.0	1126.8	1015.1	901.0	786.8
27.5°	2129.6	1998.0	1869.0	1720.0	1571.1	1422.2	1273.3	1141.7	1012.7	881.1	749.6
30°	2243.8	2114.7	1985.6	1804.4	1625.7	1444.5	1263.4	1116.9	973.0	826.5	680.1
32.5°	2348.0	2204.0	2060.1	1861.5	1660.5	1461.9	1260.9	1099.5	940.7	779.4	618.0
35°	2492.0	2333.1	2176.7	1945.9	1715.1	1484.3	1253.4	1087.1	918.3	752.1	583.3
37.5°	2645.8	2449.8	2256.2	2000.5	1744.9	1489.2	1233.6	1069.8	905.9	742.1	578.3
40°	2814.6	2576.3	2340.5	2057.6	1777.1	1494.2	1211.2	1047.4	883.6	717.3	553.5
42.5°	2923.8	2665.7	2407.6	2102.3	1799.5	1494.2	1188.9	1027.6	866.2	702.4	541.1
45°	2985.9	2735.2	2487.0	2156.9	1826.8	1496.7	1166.6	1007.7	848.9	687.5	528.7
47.5°	3013.2	2779.9	2546.6	2199.1	1854.1	1506.6	1159.1	997.8	834.0	672.6	508.8
50°	3085.2	2879.1	2673.1	2300.8	1931.0	1558.7	1186.4	1012.7	841.4	667.7	493.9
52.5°	3127.4	2951.1	2774.9	2392.7	2010.4	1628.2	1246.0	1052.4	858.8	665.2	471.6
55°	3281.2	3112.5	2943.7	2536.6	2127.1	1720.0	1310.5	1097.1	883.6	667.7	454.2
57.5°	3477.3	3298.6	3122.4	2683.1	2243.8	1804.4	1365.1	1136.8	905.9	677.6	446.8
60°	3613.8	3440.1	3268.8	2802.2	2333.1	1866.5	1397.4	1159.1	920.8	680.1	441.8
62.5°	3628.7	3405.3	3184.4	2730.2	2276.0	1819.3	1365.1	1134.3	903.5	670.1	439.3
65°	3534.4	3273.8	3013.2	2578.8	2144.5	1710.1	1275.8	1064.8	853.8	640.4	429.4
67.5°	3345.8	3040.5	2735.2	2338.1	1940.9	1543.8	1146.7	965.5	786.8	605.6	424.4
70°	2906.5	2638.4	2372.8	2027.8	1685.3	1340.3	995.3	846.4	699.9	551.0	402.1
72.5°	2439.8	2189.1	1940.9	1660.5	1382.5	1102.0	821.6	709.9	598.2	484.0	372.3
75°	1869.0	1680.3	1494.2	1285.7	1077.2	866.2	657.7	575.8	493.9	412.0	330.1
77.5°	1313.0	1211.2	1111.9	955.6	799.2	642.8	486.5	431.9	377.3	322.7	268.1
80°	891.0	834.0	779.4	667.7	556.0	441.8	330.1	295.4	258.1	223.4	186.2
82.5°	553.5	551.0	546.0	469.1	392.2	315.2	238.3	208.5	181.2	151.4	121.6
85°	253.2	295.4	335.1	292.9	250.7	208.5	166.3	146.4	126.6	104.2	84.4
87.5°	79.4	96.8	111.7	106.7	99.3	94.3	86.9	74.5	62.1	49.6	37.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675979
 CATALOG NUMBER: CCW-SA-1E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675979

CATALOG NUMBER: CCW-SA-1E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1
2.5°	1737.4	1730.0	1720.0	1710.1	1697.7	1687.8	1675.4	1663.0	1660.5	1655.5	1653.0
5°	1496.7	1481.8	1464.4	1449.5	1434.6	1417.2	1402.3	1385.0	1372.6	1357.7	1345.3
7.5°	1285.7	1260.9	1233.6	1206.3	1181.4	1156.6	1129.3	1104.5	1092.1	1079.7	1067.3
10°	1116.9	1092.1	1069.8	1044.9	1027.6	1012.7	995.3	977.9	963.0	948.1	933.2
12.5°	1032.5	1015.1	997.8	980.4	960.5	943.2	923.3	903.5	886.1	871.2	853.8
15°	980.4	955.6	928.3	903.5	876.2	851.3	824.0	796.7	776.9	759.5	739.6
17.5°	918.3	881.1	846.4	809.1	779.4	749.6	717.3	687.5	665.2	640.4	618.0
20°	848.9	806.7	762.0	719.8	685.0	652.8	618.0	583.3	558.5	531.2	506.3
22.5°	789.3	734.7	677.6	620.5	583.3	546.0	506.3	469.1	446.8	421.9	399.6
25°	724.8	665.2	603.1	541.1	503.9	464.1	426.9	387.2	369.8	354.9	337.6
27.5°	690.0	630.4	568.4	508.8	474.1	436.8	402.1	364.9	352.4	337.6	325.1
30°	620.5	563.4	503.9	444.3	419.5	397.1	372.3	347.5	342.5	340.0	335.1
32.5°	558.5	498.9	439.3	379.7	357.4	335.1	312.7	290.4	287.9	283.0	280.5
35°	526.2	469.1	409.5	352.4	332.6	310.3	290.4	268.1	263.1	255.6	250.7
37.5°	518.7	459.2	397.1	337.6	317.7	297.8	275.5	255.6	250.7	245.7	240.8
40°	498.9	441.8	387.2	330.1	310.3	290.4	268.1	248.2	243.2	238.3	233.3
42.5°	484.0	429.4	372.3	315.2	297.8	280.5	260.6	243.2	238.3	233.3	225.9
45°	471.6	414.5	354.9	297.8	285.4	273.0	258.1	245.7	240.8	233.3	228.3
47.5°	451.7	397.1	340.0	283.0	270.5	260.6	248.2	235.8	230.8	225.9	220.9
50°	436.8	379.7	322.7	265.6	255.6	245.7	235.8	225.9	225.9	228.3	228.3
52.5°	417.0	362.4	307.8	253.2	243.2	233.3	223.4	213.5	215.9	218.4	220.9
55°	399.6	347.5	292.9	238.3	228.3	218.4	206.0	196.1	198.6	201.0	203.5
57.5°	392.2	337.6	283.0	228.3	218.4	206.0	196.1	183.7	183.7	183.7	183.7
60°	387.2	330.1	275.5	218.4	206.0	196.1	183.7	171.3	168.8	168.8	166.3
62.5°	384.7	327.6	273.0	215.9	201.0	188.6	173.7	158.8	156.4	153.9	151.4
65°	374.8	322.7	268.1	213.5	196.1	181.2	163.8	146.4	144.0	144.0	141.5
67.5°	372.3	317.7	265.6	211.0	193.6	173.7	156.4	136.5	134.0	131.5	129.1
70°	352.4	305.3	255.6	206.0	186.2	168.8	148.9	129.1	126.6	121.6	119.1
72.5°	327.6	285.4	240.8	196.1	176.2	156.4	136.5	116.7	114.2	111.7	106.7
75°	290.4	250.7	211.0	171.3	153.9	139.0	121.6	104.2	101.8	99.3	94.3
77.5°	238.3	206.0	176.2	144.0	131.5	119.1	106.7	94.3	91.8	89.4	84.4
80°	168.8	148.9	131.5	111.7	104.2	94.3	86.9	76.9	76.9	74.5	74.5
82.5°	111.7	101.8	91.8	81.9	76.9	72.0	67.0	62.1	62.1	59.6	59.6
85°	79.4	74.5	67.0	62.1	59.6	54.6	52.1	47.2	47.2	47.2	47.2
87.5°	37.2	37.2	34.7	34.7	32.3	32.3	29.8	27.3	27.3	27.3	27.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675979
 CATALOG NUMBER: CCW-SA-1E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675979
 CATALOG NUMBER: CCW-SA-1E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1
2.5°	1648.1	1640.6	1633.2	1623.2	1615.8	1605.9	1593.5	1583.5	1571.1	1571.1	1568.6
5°	1330.4	1322.9	1315.5	1305.5	1298.1	1288.2	1280.7	1270.8	1260.9	1260.9	1258.4
7.5°	1054.9	1040.0	1025.1	1007.7	992.8	982.9	973.0	960.5	950.6	943.2	935.7
10°	918.3	903.5	886.1	871.2	853.8	841.4	829.0	814.1	801.7	791.8	781.8
12.5°	836.4	819.1	801.7	784.3	766.9	749.6	734.7	717.3	699.9	687.5	675.1
15°	719.8	702.4	685.0	667.7	650.3	630.4	610.6	588.2	568.4	558.5	551.0
17.5°	593.2	575.8	556.0	538.6	518.7	503.9	489.0	474.1	459.2	449.2	441.8
20°	479.0	459.2	439.3	419.5	399.6	389.7	379.7	369.8	359.9	352.4	347.5
22.5°	374.8	362.4	352.4	340.0	327.6	320.2	315.2	307.8	300.3	300.3	300.3
25°	320.2	312.7	307.8	300.3	292.9	290.4	287.9	283.0	280.5	278.0	278.0
27.5°	310.3	302.8	295.4	287.9	280.5	278.0	275.5	270.5	268.1	268.1	268.1
30°	330.1	327.6	325.1	322.7	320.2	315.2	307.8	302.8	295.4	290.4	285.4
32.5°	275.5	273.0	273.0	270.5	268.1	273.0	275.5	280.5	283.0	285.4	287.9
35°	243.2	238.3	233.3	228.3	223.4	220.9	218.4	215.9	213.5	213.5	211.0
37.5°	235.8	230.8	225.9	220.9	215.9	213.5	211.0	208.5	206.0	206.0	203.5
40°	228.3	223.4	220.9	215.9	211.0	208.5	206.0	201.0	198.6	196.1	196.1
42.5°	220.9	218.4	213.5	211.0	206.0	203.5	201.0	196.1	193.6	191.1	188.6
45°	220.9	215.9	211.0	206.0	201.0	198.6	193.6	191.1	186.2	186.2	183.7
47.5°	215.9	211.0	206.0	201.0	196.1	193.6	188.6	186.2	181.2	178.7	176.2
50°	228.3	220.9	211.0	203.5	193.6	191.1	186.2	183.7	178.7	176.2	173.7
52.5°	223.4	215.9	206.0	198.6	188.6	183.7	181.2	176.2	171.3	168.8	166.3
55°	206.0	198.6	193.6	186.2	178.7	173.7	168.8	163.8	158.8	156.4	156.4
57.5°	183.7	181.2	178.7	176.2	173.7	168.8	163.8	156.4	151.4	148.9	146.4
60°	163.8	166.3	168.8	171.3	173.7	166.3	158.8	151.4	144.0	141.5	139.0
62.5°	148.9	153.9	158.8	161.3	166.3	158.8	151.4	144.0	136.5	134.0	131.5
65°	139.0	141.5	141.5	144.0	144.0	139.0	136.5	131.5	126.6	124.1	124.1
67.5°	126.6	126.6	126.6	124.1	124.1	121.6	121.6	119.1	116.7	114.2	114.2
70°	114.2	114.2	114.2	111.7	111.7	109.2	109.2	106.7	104.2	104.2	101.8
72.5°	104.2	104.2	101.8	101.8	99.3	99.3	99.3	96.8	96.8	94.3	94.3
75°	91.8	91.8	89.4	89.4	86.9	86.9	86.9	84.4	84.4	84.4	81.9
77.5°	81.9	81.9	79.4	79.4	76.9	76.9	76.9	74.5	74.5	72.0	72.0
80°	72.0	72.0	69.5	69.5	67.0	67.0	64.5	64.5	62.1	62.1	59.6
82.5°	57.1	57.1	57.1	57.1	57.1	54.6	54.6	52.1	49.6	49.6	47.2
85°	47.2	47.2	47.2	44.7	44.7	44.7	42.2	42.2	39.7	37.2	37.2
87.5°	27.3	27.3	27.3	24.8	24.8	24.8	24.8	24.8	24.8	24.8	22.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675979
 CATALOG NUMBER: CCW-SA-1E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675979

CATALOG NUMBER: CCW-SA-1E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1
2.5°	1568.6	1566.2	1556.2	1546.3	1556.2	1566.2	1566.2	1566.2	1563.7	1563.7	1563.7
5°	1258.4	1255.9	1250.9	1246.0	1246.0	1243.5	1248.5	1253.4	1258.4	1263.4	1268.3
7.5°	925.8	918.3	910.9	903.5	908.4	910.9	918.3	923.3	930.8	935.7	948.1
10°	771.9	762.0	754.5	747.1	742.1	737.2	732.2	729.7	724.8	719.8	724.8
12.5°	660.2	647.8	635.4	620.5	618.0	615.5	610.6	605.6	600.7	595.7	593.2
15°	541.1	531.2	526.2	518.7	508.8	498.9	493.9	491.4	486.5	481.5	479.0
17.5°	431.9	421.9	414.5	407.1	404.6	399.6	399.6	399.6	399.6	399.6	399.6
20°	340.0	332.6	332.6	330.1	330.1	327.6	330.1	332.6	332.6	335.1	337.6
22.5°	297.8	297.8	295.4	292.9	295.4	295.4	297.8	300.3	302.8	305.3	307.8
25°	275.5	273.0	275.5	278.0	278.0	278.0	280.5	280.5	283.0	283.0	283.0
27.5°	265.6	265.6	268.1	268.1	270.5	270.5	270.5	268.1	268.1	265.6	265.6
30°	280.5	275.5	275.5	275.5	273.0	270.5	268.1	268.1	265.6	263.1	260.6
32.5°	290.4	292.9	290.4	285.4	283.0	278.0	275.5	270.5	268.1	263.1	258.1
35°	211.0	208.5	213.5	215.9	218.4	220.9	223.4	225.9	225.9	228.3	228.3
37.5°	203.5	201.0	201.0	198.6	198.6	198.6	198.6	198.6	196.1	196.1	198.6
40°	193.6	191.1	191.1	188.6	188.6	186.2	186.2	186.2	186.2	186.2	186.2
42.5°	186.2	183.7	183.7	183.7	183.7	181.2	181.2	178.7	178.7	176.2	176.2
45°	183.7	181.2	178.7	176.2	176.2	173.7	173.7	173.7	171.3	171.3	171.3
47.5°	173.7	171.3	171.3	168.8	168.8	166.3	166.3	166.3	163.8	163.8	163.8
50°	168.8	166.3	166.3	163.8	163.8	161.3	161.3	161.3	158.8	158.8	158.8
52.5°	161.3	158.8	158.8	158.8	156.4	153.9	153.9	153.9	151.4	151.4	151.4
55°	153.9	151.4	151.4	151.4	148.9	146.4	146.4	146.4	144.0	144.0	144.0
57.5°	144.0	141.5	141.5	139.0	139.0	139.0	139.0	139.0	136.5	136.5	136.5
60°	136.5	134.0	134.0	131.5	131.5	129.1	129.1	129.1	129.1	129.1	129.1
62.5°	129.1	126.6	124.1	121.6	124.1	124.1	124.1	124.1	121.6	121.6	121.6
65°	121.6	119.1	116.7	114.2	114.2	114.2	114.2	114.2	114.2	114.2	114.2
67.5°	111.7	109.2	106.7	104.2	106.7	106.7	106.7	106.7	106.7	106.7	106.7
70°	101.8	99.3	99.3	96.8	96.8	94.3	94.3	96.8	96.8	96.8	96.8
72.5°	91.8	89.4	89.4	86.9	86.9	86.9	86.9	86.9	86.9	86.9	86.9
75°	81.9	79.4	79.4	76.9	76.9	76.9	76.9	76.9	76.9	76.9	76.9
77.5°	69.5	67.0	67.0	67.0	67.0	67.0	67.0	69.5	69.5	69.5	69.5
80°	59.6	57.1	57.1	57.1	57.1	57.1	57.1	57.1	57.1	57.1	57.1
82.5°	47.2	44.7	44.7	44.7	44.7	44.7	44.7	44.7	44.7	44.7	44.7
85°	34.7	32.3	32.3	32.3	34.7	34.7	34.7	34.7	34.7	34.7	34.7
87.5°	22.3	19.9	19.9	19.9	22.3	22.3	22.3	22.3	19.9	19.9	19.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675979
 CATALOG NUMBER: CCW-SA-1E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675979
 CATALOG NUMBER: CCW-SA-1E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1
2.5°	1563.7	1563.7	1563.7	1561.2	1558.7	1556.2	1553.7	1561.2	1566.2	1573.6	1578.6
5°	1270.8	1275.8	1278.2	1285.7	1293.1	1300.6	1308.0	1313.0	1318.0	1320.4	1325.4
7.5°	958.1	970.5	980.4	990.3	1000.3	1007.7	1017.6	1025.1	1032.5	1040.0	1047.4
10°	727.2	732.2	734.7	744.6	752.1	762.0	769.4	776.9	784.3	789.3	796.7
12.5°	590.7	585.8	583.3	583.3	583.3	583.3	583.3	588.2	593.2	598.2	603.1
15°	476.5	474.1	471.6	469.1	466.6	461.7	459.2	464.1	469.1	474.1	479.0
17.5°	399.6	399.6	399.6	397.1	394.6	392.2	389.7	392.2	394.6	394.6	397.1
20°	342.5	345.0	347.5	350.0	350.0	352.4	352.4	354.9	357.4	357.4	359.9
22.5°	307.8	310.3	310.3	310.3	312.7	312.7	312.7	315.2	317.7	320.2	322.7
25°	280.5	280.5	278.0	278.0	280.5	280.5	280.5	280.5	283.0	283.0	283.0
27.5°	265.6	263.1	263.1	263.1	263.1	260.6	260.6	260.6	260.6	260.6	260.6
30°	258.1	255.6	253.2	250.7	250.7	248.2	245.7	245.7	245.7	245.7	245.7
32.5°	255.6	250.7	245.7	243.2	243.2	240.8	238.3	235.8	235.8	233.3	230.8
35°	228.3	225.9	225.9	223.4	220.9	218.4	215.9	215.9	215.9	213.5	213.5
37.5°	198.6	201.0	201.0	201.0	203.5	203.5	203.5	203.5	206.0	206.0	206.0
40°	186.2	186.2	186.2	188.6	191.1	191.1	193.6	193.6	196.1	196.1	196.1
42.5°	176.2	173.7	173.7	176.2	176.2	178.7	178.7	181.2	183.7	183.7	186.2
45°	171.3	168.8	168.8	168.8	168.8	166.3	166.3	168.8	171.3	173.7	176.2
47.5°	161.3	161.3	158.8	158.8	158.8	158.8	158.8	158.8	161.3	161.3	161.3
50°	156.4	156.4	153.9	153.9	153.9	153.9	153.9	153.9	153.9	153.9	153.9
52.5°	151.4	148.9	148.9	148.9	148.9	146.4	146.4	146.4	146.4	146.4	146.4
55°	144.0	141.5	141.5	141.5	141.5	141.5	141.5	141.5	144.0	144.0	144.0
57.5°	136.5	134.0	134.0	134.0	136.5	136.5	136.5	136.5	139.0	139.0	139.0
60°	129.1	129.1	129.1	129.1	129.1	129.1	129.1	131.5	131.5	134.0	134.0
62.5°	121.6	121.6	121.6	121.6	124.1	124.1	124.1	124.1	126.6	126.6	126.6
65°	114.2	114.2	114.2	114.2	116.7	116.7	116.7	116.7	116.7	116.7	116.7
67.5°	106.7	106.7	106.7	106.7	106.7	106.7	106.7	109.2	109.2	111.7	111.7
70°	96.8	94.3	94.3	96.8	96.8	99.3	99.3	101.8	101.8	104.2	104.2
72.5°	86.9	86.9	86.9	86.9	86.9	86.9	86.9	89.4	91.8	91.8	94.3
75°	76.9	76.9	76.9	76.9	79.4	79.4	79.4	81.9	81.9	84.4	84.4
77.5°	69.5	67.0	67.0	67.0	69.5	69.5	69.5	72.0	72.0	74.5	74.5
80°	57.1	57.1	57.1	57.1	59.6	59.6	59.6	59.6	62.1	62.1	62.1
82.5°	47.2	47.2	47.2	47.2	47.2	47.2	47.2	47.2	49.6	49.6	49.6
85°	34.7	34.7	34.7	34.7	37.2	37.2	37.2	37.2	37.2	37.2	37.2
87.5°	22.3	22.3	22.3	22.3	22.3	22.3	22.3	22.3	24.8	24.8	24.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675979
 CATALOG NUMBER: CCW-SA-1E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675979

CATALOG NUMBER: CCW-SA-1E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1
2.5°	1578.6	1578.6	1578.6	1578.6	1583.5	1586.0	1591.0	1593.5	1591.0	1588.5	1583.5
5°	1327.9	1330.4	1330.4	1332.8	1332.8	1332.8	1332.8	1332.8	1337.8	1342.8	1347.7
7.5°	1049.9	1052.4	1054.9	1057.3	1057.3	1057.3	1054.9	1054.9	1057.3	1057.3	1059.8
10°	804.2	814.1	821.6	829.0	824.0	816.6	811.6	804.2	804.2	804.2	801.7
12.5°	608.1	610.6	615.5	618.0	615.5	615.5	613.1	610.6	613.1	618.0	620.5
15°	481.5	481.5	484.0	484.0	486.5	489.0	489.0	491.4	496.4	498.9	503.9
17.5°	399.6	402.1	402.1	404.6	404.6	407.1	407.1	407.1	412.0	417.0	424.4
20°	359.9	359.9	359.9	359.9	359.9	357.4	357.4	354.9	357.4	362.4	364.9
22.5°	322.7	325.1	325.1	325.1	322.7	320.2	315.2	312.7	312.7	315.2	315.2
25°	283.0	280.5	280.5	278.0	278.0	280.5	280.5	280.5	283.0	283.0	285.4
27.5°	260.6	258.1	258.1	255.6	255.6	258.1	258.1	258.1	258.1	258.1	258.1
30°	243.2	243.2	240.8	238.3	240.8	240.8	243.2	243.2	245.7	245.7	248.2
32.5°	230.8	228.3	228.3	225.9	228.3	228.3	230.8	230.8	233.3	235.8	235.8
35°	213.5	213.5	213.5	213.5	213.5	213.5	211.0	211.0	211.0	211.0	211.0
37.5°	203.5	203.5	201.0	198.6	198.6	198.6	198.6	198.6	196.1	193.6	191.1
40°	196.1	193.6	193.6	191.1	188.6	188.6	186.2	183.7	183.7	181.2	181.2
42.5°	186.2	183.7	183.7	181.2	178.7	178.7	176.2	173.7	173.7	173.7	171.3
45°	173.7	173.7	171.3	168.8	168.8	168.8	166.3	166.3	166.3	166.3	163.8
47.5°	161.3	161.3	158.8	158.8	158.8	158.8	156.4	156.4	156.4	156.4	156.4
50°	153.9	153.9	153.9	153.9	153.9	153.9	151.4	151.4	151.4	151.4	151.4
52.5°	146.4	146.4	146.4	146.4	146.4	146.4	146.4	146.4	146.4	146.4	146.4
55°	144.0	144.0	144.0	144.0	144.0	144.0	141.5	141.5	141.5	144.0	144.0
57.5°	139.0	139.0	136.5	136.5	136.5	136.5	136.5	136.5	136.5	136.5	136.5
60°	134.0	134.0	134.0	134.0	134.0	134.0	134.0	134.0	134.0	134.0	134.0
62.5°	126.6	126.6	126.6	126.6	126.6	129.1	129.1	129.1	129.1	129.1	126.6
65°	116.7	119.1	119.1	119.1	119.1	119.1	119.1	119.1	119.1	119.1	119.1
67.5°	111.7	111.7	111.7	111.7	111.7	111.7	111.7	111.7	111.7	111.7	111.7
70°	104.2	104.2	101.8	101.8	101.8	104.2	104.2	104.2	104.2	104.2	104.2
72.5°	94.3	94.3	94.3	94.3	94.3	94.3	94.3	94.3	94.3	96.8	96.8
75°	84.4	84.4	84.4	84.4	84.4	84.4	84.4	84.4	84.4	84.4	84.4
77.5°	74.5	74.5	72.0	72.0	72.0	74.5	74.5	74.5	74.5	76.9	76.9
80°	62.1	62.1	62.1	62.1	62.1	62.1	62.1	62.1	62.1	64.5	64.5
82.5°	49.6	49.6	49.6	49.6	49.6	49.6	49.6	49.6	49.6	52.1	52.1
85°	37.2	39.7	39.7	39.7	39.7	39.7	39.7	39.7	39.7	42.2	42.2
87.5°	24.8	24.8	24.8	24.8	24.8	24.8	22.3	22.3	22.3	22.3	19.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675979
 CATALOG NUMBER: CCW-SA-1E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675979
 CATALOG NUMBER: CCW-SA-1E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1
2.5°	1581.1	1583.5	1586.0	1586.0	1588.5	1591.0	1591.0	1600.9	1610.8	1615.8	1620.8
5°	1352.7	1350.2	1350.2	1347.7	1345.3	1352.7	1360.1	1375.0	1389.9	1392.4	1397.4
7.5°	1059.8	1062.3	1064.8	1064.8	1067.3	1059.8	1049.9	1052.4	1054.9	1067.3	1077.2
10°	801.7	804.2	806.7	806.7	809.1	806.7	801.7	809.1	816.6	826.5	838.9
12.5°	623.0	630.4	637.9	642.8	650.3	655.3	657.7	667.7	675.1	687.5	699.9
15°	508.8	513.8	518.7	523.7	528.7	533.6	538.6	548.5	558.5	573.3	588.2
17.5°	429.4	429.4	431.9	431.9	431.9	436.8	441.8	446.8	449.2	464.1	479.0
20°	367.3	364.9	362.4	359.9	357.4	362.4	364.9	367.3	369.8	379.7	387.2
22.5°	315.2	315.2	317.7	317.7	317.7	315.2	310.3	312.7	312.7	317.7	325.1
25°	285.4	285.4	285.4	283.0	283.0	285.4	287.9	287.9	285.4	287.9	290.4
27.5°	258.1	260.6	260.6	263.1	263.1	265.6	265.6	265.6	265.6	268.1	270.5
30°	248.2	248.2	250.7	250.7	250.7	253.2	255.6	255.6	255.6	258.1	263.1
32.5°	238.3	240.8	243.2	245.7	248.2	250.7	250.7	253.2	253.2	255.6	258.1
35°	211.0	208.5	208.5	206.0	203.5	203.5	203.5	203.5	201.0	203.5	203.5
37.5°	188.6	188.6	188.6	186.2	186.2	188.6	188.6	188.6	188.6	191.1	191.1
40°	178.7	178.7	178.7	178.7	178.7	178.7	178.7	181.2	181.2	183.7	186.2
42.5°	171.3	171.3	171.3	171.3	171.3	173.7	173.7	173.7	173.7	176.2	176.2
45°	163.8	163.8	163.8	163.8	163.8	163.8	163.8	166.3	166.3	168.8	171.3
47.5°	156.4	156.4	156.4	156.4	156.4	158.8	161.3	161.3	161.3	163.8	163.8
50°	151.4	151.4	151.4	151.4	151.4	153.9	153.9	156.4	156.4	158.8	161.3
52.5°	146.4	146.4	146.4	146.4	146.4	148.9	148.9	151.4	151.4	153.9	156.4
55°	144.0	144.0	144.0	141.5	141.5	144.0	144.0	146.4	146.4	148.9	148.9
57.5°	136.5	136.5	136.5	136.5	136.5	136.5	136.5	139.0	139.0	141.5	144.0
60°	134.0	134.0	131.5	131.5	129.1	131.5	131.5	134.0	134.0	136.5	136.5
62.5°	126.6	126.6	126.6	124.1	124.1	126.6	126.6	126.6	126.6	129.1	131.5
65°	119.1	119.1	119.1	116.7	116.7	119.1	119.1	119.1	119.1	121.6	124.1
67.5°	111.7	111.7	111.7	109.2	109.2	109.2	109.2	111.7	111.7	114.2	116.7
70°	104.2	104.2	104.2	101.8	101.8	101.8	99.3	101.8	104.2	106.7	106.7
72.5°	96.8	96.8	96.8	94.3	94.3	94.3	91.8	94.3	94.3	96.8	96.8
75°	84.4	84.4	84.4	84.4	84.4	84.4	81.9	81.9	81.9	84.4	84.4
77.5°	76.9	76.9	76.9	74.5	74.5	74.5	72.0	72.0	72.0	74.5	74.5
80°	64.5	64.5	64.5	62.1	62.1	62.1	59.6	59.6	59.6	62.1	62.1
82.5°	52.1	52.1	52.1	49.6	49.6	49.6	47.2	47.2	47.2	49.6	49.6
85°	42.2	42.2	42.2	42.2	42.2	42.2	39.7	39.7	39.7	42.2	44.7
87.5°	19.9	19.9	22.3	22.3	22.3	22.3	19.9	19.9	17.4	17.4	19.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675979
 CATALOG NUMBER: CCW-SA-1E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675979
 CATALOG NUMBER: CCW-SA-1E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1
2.5°	1625.7	1630.7	1643.1	1653.0	1665.4	1675.4	1682.8	1692.7	1700.2	1707.6	1712.6
5°	1399.9	1402.3	1414.8	1427.2	1437.1	1449.5	1466.9	1484.3	1501.6	1519.0	1531.4
7.5°	1089.6	1099.5	1114.4	1131.8	1146.7	1161.6	1179.0	1198.8	1216.2	1233.6	1250.9
10°	848.9	858.8	873.7	888.6	901.0	915.9	935.7	955.6	975.4	995.3	1015.1
12.5°	712.3	724.8	742.1	759.5	774.4	791.8	816.6	838.9	863.7	886.1	910.9
15°	600.7	615.5	637.9	662.7	685.0	707.4	732.2	757.0	779.4	804.2	829.0
17.5°	493.9	508.8	528.7	551.0	570.9	590.7	620.5	647.8	677.6	704.9	732.2
20°	397.1	404.6	424.4	444.3	464.1	484.0	506.3	528.7	551.0	573.3	608.1
22.5°	330.1	335.1	345.0	352.4	362.4	369.8	392.2	414.5	434.4	456.7	489.0
25°	290.4	292.9	300.3	305.3	312.7	317.7	332.6	345.0	359.9	372.3	402.1
27.5°	270.5	273.0	275.5	278.0	280.5	283.0	292.9	302.8	310.3	320.2	347.5
30°	265.6	268.1	275.5	280.5	287.9	292.9	297.8	302.8	307.8	312.7	330.1
32.5°	260.6	263.1	263.1	260.6	260.6	258.1	263.1	265.6	270.5	273.0	287.9
35°	206.0	206.0	208.5	211.0	213.5	215.9	223.4	228.3	235.8	240.8	253.2
37.5°	193.6	193.6	196.1	201.0	203.5	206.0	211.0	215.9	220.9	225.9	238.3
40°	186.2	188.6	191.1	193.6	196.1	198.6	203.5	206.0	211.0	213.5	223.4
42.5°	178.7	178.7	181.2	186.2	188.6	191.1	196.1	198.6	203.5	206.0	215.9
45°	173.7	176.2	178.7	181.2	181.2	183.7	188.6	193.6	196.1	201.0	211.0
47.5°	166.3	166.3	171.3	173.7	178.7	181.2	186.2	188.6	193.6	196.1	206.0
50°	161.3	163.8	168.8	171.3	176.2	178.7	186.2	191.1	198.6	203.5	208.5
52.5°	156.4	158.8	163.8	166.3	171.3	173.7	183.7	193.6	201.0	211.0	211.0
55°	151.4	151.4	156.4	163.8	168.8	173.7	178.7	186.2	191.1	196.1	196.1
57.5°	144.0	146.4	151.4	158.8	163.8	168.8	173.7	178.7	181.2	186.2	183.7
60°	139.0	139.0	146.4	153.9	161.3	168.8	168.8	168.8	166.3	166.3	166.3
62.5°	131.5	134.0	144.0	156.4	166.3	176.2	168.8	161.3	153.9	146.4	148.9
65°	126.6	129.1	134.0	141.5	146.4	151.4	146.4	144.0	139.0	134.0	136.5
67.5°	116.7	119.1	121.6	121.6	124.1	124.1	124.1	124.1	124.1	124.1	126.6
70°	109.2	109.2	109.2	111.7	111.7	111.7	111.7	111.7	111.7	111.7	114.2
72.5°	99.3	99.3	99.3	99.3	99.3	99.3	99.3	99.3	99.3	99.3	101.8
75°	86.9	86.9	86.9	86.9	86.9	86.9	86.9	86.9	86.9	86.9	89.4
77.5°	76.9	76.9	76.9	76.9	76.9	76.9	76.9	76.9	74.5	74.5	76.9
80°	64.5	64.5	64.5	64.5	62.1	62.1	62.1	62.1	62.1	62.1	64.5
82.5°	52.1	52.1	52.1	52.1	49.6	49.6	49.6	49.6	47.2	47.2	49.6
85°	47.2	49.6	49.6	52.1	52.1	52.1	49.6	47.2	44.7	42.2	42.2
87.5°	19.9	19.9	19.9	19.9	17.4	17.4	17.4	17.4	17.4	17.4	17.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675979
 CATALOG NUMBER: CCW-SA-1E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675979

CATALOG NUMBER: CCW-SA-1E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1
2.5°	1720.0	1725.0	1730.0	1737.4	1747.3	1754.8	1762.2	1777.1	1794.5	1809.4	1824.3
5°	1543.8	1556.2	1568.6	1583.5	1598.4	1610.8	1625.7	1655.5	1685.3	1712.6	1742.4
7.5°	1265.8	1283.2	1298.1	1322.9	1345.3	1370.1	1392.4	1429.6	1464.4	1501.6	1536.4
10°	1035.0	1054.9	1074.7	1107.0	1141.7	1174.0	1206.3	1236.0	1268.3	1298.1	1327.9
12.5°	935.7	958.1	982.9	1002.7	1025.1	1044.9	1064.8	1099.5	1134.3	1169.0	1203.8
15°	853.8	878.6	903.5	928.3	950.6	975.4	997.8	1027.6	1059.8	1089.6	1119.4
17.5°	759.5	784.3	811.6	838.9	866.2	893.5	920.8	963.0	1005.2	1044.9	1087.1
20°	640.4	675.1	707.4	744.6	781.8	819.1	856.3	901.0	945.7	987.8	1032.5
22.5°	521.2	553.5	585.8	630.4	675.1	717.3	762.0	821.6	878.6	938.2	995.3
25°	434.4	464.1	493.9	543.6	590.7	640.4	687.5	759.5	829.0	901.0	970.5
27.5°	374.8	402.1	429.4	481.5	533.6	583.3	635.4	714.8	791.8	871.2	948.1
30°	347.5	364.9	382.2	431.9	481.5	528.7	578.3	655.3	732.2	809.1	886.1
32.5°	302.8	317.7	332.6	377.3	421.9	464.1	508.8	588.2	665.2	744.6	821.6
35°	268.1	280.5	292.9	335.1	374.8	417.0	456.7	536.1	615.5	695.0	774.4
37.5°	248.2	260.6	270.5	307.8	347.5	384.7	421.9	501.4	578.3	657.7	734.7
40°	233.3	240.8	250.7	287.9	322.7	359.9	394.6	466.6	541.1	613.1	685.0
42.5°	223.4	233.3	240.8	273.0	307.8	340.0	372.3	441.8	511.3	578.3	647.8
45°	220.9	230.8	240.8	268.1	295.4	320.2	347.5	414.5	481.5	548.5	615.5
47.5°	215.9	223.4	233.3	255.6	275.5	297.8	317.7	384.7	451.7	516.3	583.3
50°	213.5	215.9	220.9	240.8	260.6	280.5	300.3	367.3	434.4	501.4	568.4
52.5°	211.0	211.0	211.0	228.3	245.7	260.6	278.0	345.0	414.5	481.5	548.5
55°	196.1	193.6	193.6	211.0	225.9	243.2	258.1	325.1	392.2	456.7	523.7
57.5°	181.2	178.7	176.2	191.1	206.0	220.9	235.8	302.8	372.3	439.3	506.3
60°	166.3	163.8	163.8	178.7	191.1	206.0	218.4	287.9	354.9	424.4	491.4
62.5°	148.9	151.4	151.4	163.8	178.7	191.1	203.5	273.0	345.0	414.5	484.0
65°	136.5	139.0	139.0	153.9	168.8	183.7	198.6	265.6	335.1	402.1	469.1
67.5°	126.6	129.1	129.1	146.4	161.3	178.7	193.6	253.2	315.2	374.8	434.4
70°	116.7	116.7	119.1	136.5	153.9	171.3	188.6	240.8	292.9	342.5	394.6
72.5°	104.2	106.7	109.2	126.6	141.5	158.8	173.7	220.9	268.1	315.2	362.4
75°	91.8	94.3	96.8	111.7	126.6	141.5	156.4	201.0	243.2	287.9	330.1
77.5°	81.9	84.4	86.9	99.3	111.7	124.1	136.5	168.8	203.5	235.8	268.1
80°	67.0	67.0	69.5	79.4	89.4	96.8	106.7	129.1	151.4	171.3	193.6
82.5°	49.6	52.1	52.1	59.6	64.5	72.0	76.9	89.4	99.3	111.7	121.6
85°	42.2	39.7	39.7	44.7	47.2	52.1	54.6	62.1	67.0	74.5	79.4
87.5°	17.4	14.9	14.9	17.4	22.3	24.8	27.3	27.3	29.8	29.8	29.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675979
 CATALOG NUMBER: CCW-SA-1E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675979

CATALOG NUMBER: CCW-SA-1E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1
2.5°	1831.7	1836.7	1844.1	1849.1	1861.5	1871.4	1883.9	1893.8	1901.2	1913.6	1908.7
5°	1764.7	1787.1	1809.4	1831.7	1849.1	1866.5	1881.4	1898.7	1918.6	1955.8	1965.8
7.5°	1566.2	1595.9	1623.2	1653.0	1687.8	1722.5	1757.3	1792.0	1824.3	1871.4	1901.2
10°	1370.1	1412.3	1452.0	1494.2	1526.4	1558.7	1588.5	1620.8	1665.4	1712.6	1767.2
12.5°	1246.0	1288.2	1330.4	1372.6	1419.7	1464.4	1511.6	1556.2	1598.4	1635.7	1697.7
15°	1164.1	1211.2	1255.9	1300.6	1357.7	1412.3	1469.4	1524.0	1586.0	1635.7	1677.8
17.5°	1144.2	1201.3	1255.9	1313.0	1372.6	1432.1	1491.7	1551.3	1613.3	1687.8	1742.4
20°	1109.5	1186.4	1263.4	1340.3	1417.2	1491.7	1568.6	1643.1	1725.0	1814.4	1839.2
22.5°	1089.6	1181.4	1275.8	1367.6	1471.8	1578.6	1682.8	1787.1	1873.9	1940.9	2015.4
25°	1087.1	1201.3	1318.0	1432.1	1563.7	1692.7	1824.3	1953.4	2065.0	2132.1	2191.6
27.5°	1084.6	1223.6	1360.1	1496.7	1658.0	1816.8	1978.2	2137.0	2241.3	2338.1	2387.7
30°	1054.9	1221.2	1389.9	1556.2	1737.4	1918.6	2099.8	2281.0	2387.7	2454.7	2479.5
32.5°	1017.6	1213.7	1409.8	1605.9	1811.9	2017.9	2221.4	2427.4	2511.8	2568.9	2549.0
35°	987.8	1203.8	1417.2	1630.7	1849.1	2070.0	2288.4	2506.8	2628.5	2707.9	2675.6
37.5°	960.5	1186.4	1412.3	1638.1	1893.8	2149.4	2405.1	2660.7	2777.4	2861.8	2824.5
40°	928.3	1169.0	1412.3	1653.0	1945.9	2236.3	2529.2	2819.6	2971.0	3043.0	2985.9
42.5°	901.0	1151.7	1404.8	1655.5	1968.2	2281.0	2593.7	2906.5	3075.2	3177.0	3105.0
45°	866.2	1116.9	1365.1	1615.8	1960.8	2305.8	2648.3	2993.3	3189.4	3268.8	3169.5
47.5°	829.0	1077.2	1322.9	1568.6	1936.0	2303.3	2670.7	3038.0	3219.2	3313.5	3221.7
50°	816.6	1064.8	1310.5	1558.7	1955.8	2355.4	2752.6	3149.7	3281.2	3358.2	3236.6
52.5°	814.1	1077.2	1342.8	1605.9	2005.5	2402.6	2802.2	3199.3	3306.1	3388.0	3278.8
55°	806.7	1092.1	1375.0	1658.0	2075.0	2494.4	2911.4	3328.4	3435.1	3494.7	3412.8
57.5°	814.1	1121.9	1427.2	1734.9	2164.3	2593.7	3023.1	3452.5	3581.6	3623.8	3606.4
60°	819.1	1146.7	1471.8	1799.5	2218.9	2638.4	3057.9	3477.3	3611.3	3715.6	3735.4
62.5°	806.7	1129.3	1449.5	1772.2	2151.9	2531.7	2911.4	3291.2	3512.1	3666.0	3755.3
65°	769.4	1067.3	1367.6	1665.4	2015.4	2367.9	2717.8	3067.8	3301.1	3529.4	3601.4
67.5°	687.5	940.7	1193.9	1447.0	1752.3	2057.6	2360.4	2665.7	2958.6	3179.5	3278.8
70°	595.7	794.2	995.3	1193.9	1471.8	1749.8	2027.8	2305.8	2563.9	2807.2	2901.5
72.5°	518.7	672.6	829.0	982.9	1181.4	1377.5	1576.1	1772.2	2077.5	2320.7	2412.5
75°	441.8	553.5	662.7	774.4	910.9	1047.4	1181.4	1318.0	1533.9	1752.3	1844.1
77.5°	340.0	414.5	486.5	558.5	652.8	744.6	838.9	930.8	1082.2	1246.0	1293.1
80°	235.8	278.0	317.7	359.9	434.4	508.8	583.3	657.7	757.0	848.9	920.8
82.5°	146.4	173.7	198.6	223.4	283.0	342.5	399.6	459.2	498.9	503.9	575.8
85°	94.3	111.7	126.6	141.5	176.2	213.5	248.2	283.0	253.2	235.8	280.5
87.5°	37.2	47.2	54.6	62.1	59.6	57.1	54.6	52.1	44.7	39.7	49.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675979
 CATALOG NUMBER: CCW-SA-1E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675979

CATALOG NUMBER: CCW-SA-1E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1
2.5°	1913.6	1921.1	1928.5	1933.5	1940.9	1943.4	1945.9	1945.9	1948.4	1950.9	1955.8
5°	2005.5	2020.4	2035.3	2047.7	2062.6	2075.0	2084.9	2097.3	2107.2	2107.2	2104.8
7.5°	1928.5	1965.8	2003.0	2040.2	2077.5	2104.8	2129.6	2156.9	2181.7	2186.7	2191.6
10°	1826.8	1866.5	1903.7	1943.4	1980.7	2022.9	2062.6	2102.3	2144.5	2151.9	2161.8
12.5°	1732.5	1779.6	1826.8	1871.4	1918.6	1948.4	1978.2	2005.5	2035.3	2055.1	2075.0
15°	1730.0	1769.7	1809.4	1846.6	1886.3	1903.7	1921.1	1936.0	1953.4	1953.4	1955.8
17.5°	1787.1	1811.9	1836.7	1859.0	1883.9	1886.3	1891.3	1893.8	1896.3	1888.8	1881.4
20°	1898.7	1908.7	1918.6	1928.5	1938.5	1921.1	1906.2	1888.8	1871.4	1851.6	1834.2
22.5°	2062.6	2040.2	2017.9	1995.5	1973.2	1943.4	1911.2	1881.4	1849.1	1824.3	1799.5
25°	2216.4	2189.1	2161.8	2134.5	2107.2	2042.7	1978.2	1911.2	1846.6	1819.3	1792.0
27.5°	2422.5	2380.3	2338.1	2295.9	2253.7	2166.8	2079.9	1993.1	1906.2	1859.0	1814.4
30°	2472.1	2424.9	2377.8	2328.1	2281.0	2196.6	2114.7	2030.3	1945.9	1891.3	1839.2
32.5°	2544.1	2489.5	2434.9	2380.3	2325.7	2243.8	2161.8	2077.5	1995.5	1945.9	1893.8
35°	2663.2	2601.2	2539.1	2474.6	2412.5	2328.1	2246.2	2161.8	2077.5	2020.4	1965.8
37.5°	2765.0	2693.0	2621.0	2549.0	2477.1	2402.6	2325.7	2251.2	2174.3	2117.2	2062.6
40°	2879.1	2799.7	2720.3	2643.4	2563.9	2494.4	2424.9	2353.0	2283.5	2238.8	2194.1
42.5°	2978.4	2881.6	2787.3	2693.0	2596.2	2549.0	2504.4	2457.2	2410.0	2387.7	2362.9
45°	3047.9	2958.6	2866.7	2777.4	2688.0	2653.3	2618.5	2583.8	2549.0	2571.4	2593.7
47.5°	3077.7	3005.7	2936.2	2866.7	2794.8	2807.2	2819.6	2829.5	2841.9	2871.7	2904.0
50°	3105.0	3065.3	3023.1	2983.4	2941.2	2988.4	3033.0	3080.2	3127.4	3189.4	3251.5
52.5°	3159.6	3137.3	3117.4	3095.1	3072.7	3154.7	3236.6	3318.5	3400.4	3469.9	3539.4
55°	3323.4	3306.1	3288.7	3268.8	3251.5	3368.1	3482.3	3598.9	3715.6	3787.6	3859.5
57.5°	3549.3	3539.4	3527.0	3517.0	3504.6	3618.8	3730.5	3842.2	3956.3	4025.8	4097.8
60°	3720.6	3723.0	3723.0	3725.5	3725.5	3812.4	3899.3	3988.6	4075.5	4135.1	4197.1
62.5°	3812.4	3807.4	3802.5	3797.5	3792.5	3864.5	3936.5	4008.5	4080.4	4125.1	4169.8
65°	3713.1	3740.4	3767.7	3795.0	3822.3	3832.2	3839.7	3849.6	3857.1	3884.4	3911.7
67.5°	3380.5	3435.1	3487.2	3541.9	3594.0	3556.7	3522.0	3484.8	3447.5	3455.0	3459.9
70°	3010.7	3072.7	3137.3	3199.3	3261.4	3174.5	3087.6	2998.3	2911.4	2881.6	2851.8
72.5°	2539.1	2593.7	2650.8	2705.4	2760.0	2653.3	2549.0	2442.3	2335.6	2283.5	2231.3
75°	1940.9	2005.5	2072.5	2137.0	2201.6	2082.4	1960.8	1841.7	1720.0	1685.3	1653.0
77.5°	1414.8	1491.7	1568.6	1645.6	1722.5	1615.8	1509.1	1399.9	1293.1	1273.3	1253.4
80°	1030.0	1089.6	1146.7	1206.3	1263.4	1201.3	1139.2	1077.2	1015.1	1012.7	1010.2
82.5°	695.0	747.1	796.7	848.9	898.5	873.7	851.3	826.5	801.7	826.5	853.8
85°	357.4	429.4	503.9	575.8	647.8	640.4	635.4	628.0	620.5	652.8	682.6
87.5°	72.0	134.0	196.1	255.6	317.7	302.8	287.9	270.5	255.6	265.6	273.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675979
 CATALOG NUMBER: CCW-SA-1E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675979

CATALOG NUMBER: CCW-SA-1E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1
2.5°	1958.3	1960.8	1960.8	1960.8	1960.8	1960.8	1955.8	1953.4	1948.4	1943.4	1936.0
5°	2104.8	2102.3	2092.3	2082.4	2070.0	2060.1	2052.6	2042.7	2035.3	2025.3	2010.4
7.5°	2196.6	2201.6	2184.2	2169.3	2151.9	2134.5	2117.2	2099.8	2082.4	2065.0	2030.3
10°	2169.3	2176.7	2166.8	2156.9	2144.5	2134.5	2114.7	2092.3	2072.5	2050.2	2008.0
12.5°	2092.3	2112.2	2107.2	2102.3	2097.3	2092.3	2079.9	2065.0	2052.6	2037.7	1990.6
15°	1955.8	1955.8	1958.3	1960.8	1960.8	1963.3	1965.8	1968.2	1970.7	1973.2	1945.9
17.5°	1873.9	1866.5	1866.5	1866.5	1866.5	1866.5	1876.4	1888.8	1898.7	1908.7	1901.2
20°	1814.4	1797.0	1794.5	1794.5	1792.0	1789.5	1806.9	1826.8	1844.1	1861.5	1871.4
22.5°	1774.6	1749.8	1747.3	1744.9	1742.4	1739.9	1762.2	1784.6	1806.9	1829.3	1864.0
25°	1764.7	1737.4	1739.9	1742.4	1742.4	1744.9	1762.2	1779.6	1797.0	1814.4	1873.9
27.5°	1767.2	1722.5	1725.0	1727.5	1727.5	1730.0	1757.3	1782.1	1809.4	1834.2	1908.7
30°	1784.6	1732.5	1727.5	1722.5	1717.6	1712.6	1749.8	1787.1	1824.3	1861.5	1918.6
32.5°	1844.1	1794.5	1782.1	1769.7	1757.3	1744.9	1789.5	1831.7	1876.4	1918.6	1965.8
35°	1908.7	1854.1	1849.1	1844.1	1836.7	1831.7	1871.4	1913.6	1953.4	1993.1	2035.3
37.5°	2005.5	1950.9	1945.9	1938.5	1933.5	1926.1	1970.7	2012.9	2057.6	2099.8	2137.0
40°	2149.4	2104.8	2102.3	2102.3	2099.8	2097.3	2132.1	2169.3	2204.0	2238.8	2263.6
42.5°	2340.5	2318.2	2325.7	2335.6	2343.0	2350.5	2377.8	2407.6	2434.9	2462.2	2454.7
45°	2616.1	2638.4	2640.9	2643.4	2645.8	2648.3	2655.8	2665.7	2673.1	2680.6	2650.8
47.5°	2933.8	2963.5	2978.4	2993.3	3005.7	3020.6	3010.7	2998.3	2988.4	2975.9	2901.5
50°	3311.0	3373.1	3370.6	3368.1	3363.1	3360.7	3340.8	3320.9	3298.6	3278.8	3169.5
52.5°	3608.9	3678.4	3690.8	3703.2	3715.6	3728.0	3690.8	3653.5	3613.8	3576.6	3440.1
55°	3929.0	4001.0	4003.5	4006.0	4006.0	4008.5	3956.3	3904.2	3849.6	3797.5	3656.0
57.5°	4167.3	4236.8	4229.4	4224.4	4217.0	4209.5	4147.5	4085.4	4023.4	3961.3	3819.8
60°	4256.7	4316.2	4301.3	4286.5	4269.1	4254.2	4207.0	4159.9	4110.2	4063.1	3926.6
62.5°	4214.5	4259.2	4236.8	4217.0	4194.6	4172.3	4112.7	4050.7	3991.1	3929.0	3829.8
65°	3936.5	3963.8	3934.0	3906.7	3879.4	3849.6	3800.0	3750.3	3698.2	3648.6	3581.6
67.5°	3467.4	3472.4	3469.9	3467.4	3464.9	3462.4	3390.4	3318.5	3244.0	3172.0	3167.1
70°	2824.5	2794.8	2799.7	2807.2	2812.1	2817.1	2762.5	2710.4	2655.8	2601.2	2626.0
72.5°	2179.2	2127.1	2139.5	2154.4	2166.8	2179.2	2134.5	2092.3	2047.7	2003.0	2037.7
75°	1618.3	1586.0	1598.4	1613.3	1625.7	1638.1	1620.8	1603.4	1583.5	1566.2	1598.4
77.5°	1233.6	1213.7	1216.2	1216.2	1218.7	1218.7	1221.2	1226.1	1228.6	1231.1	1265.8
80°	1005.2	1002.7	1000.3	997.8	992.8	990.3	1015.1	1040.0	1064.8	1089.6	1107.0
82.5°	878.6	903.5	888.6	876.2	861.3	846.4	868.7	891.0	913.4	935.7	928.3
85°	714.8	744.6	717.3	690.0	660.2	632.9	652.8	670.1	690.0	707.4	697.4
87.5°	283.0	290.4	245.7	203.5	158.8	114.2	181.2	245.7	312.7	377.3	387.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675979
 CATALOG NUMBER: CCW-SA-1E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675979

CATALOG NUMBER: CCW-SA-1E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1	1787.1
2.5°	1928.5	1918.6	1911.2	1908.7	1903.7	1901.2	1896.3	1891.3	1883.9	1878.9	1871.4
5°	1993.1	1978.2	1960.8	1936.0	1913.6	1888.8	1864.0	1841.7	1819.3	1794.5	1772.2
7.5°	1995.5	1960.8	1926.1	1893.8	1859.0	1826.8	1792.0	1762.2	1730.0	1697.7	1667.9
10°	1968.2	1926.1	1883.9	1841.7	1802.0	1759.8	1717.6	1682.8	1645.6	1608.4	1573.6
12.5°	1945.9	1898.7	1851.6	1802.0	1754.8	1705.2	1655.5	1620.8	1586.0	1551.3	1516.5
15°	1918.6	1888.8	1861.5	1816.8	1772.2	1727.5	1682.8	1635.7	1591.0	1543.8	1496.7
17.5°	1896.3	1888.8	1881.4	1851.6	1821.8	1789.5	1759.8	1712.6	1665.4	1615.8	1568.6
20°	1883.9	1893.8	1903.7	1888.8	1873.9	1856.6	1841.7	1806.9	1772.2	1734.9	1700.2
22.5°	1898.7	1936.0	1970.7	1973.2	1978.2	1980.7	1983.1	1950.9	1918.6	1883.9	1851.6
25°	1933.5	1993.1	2052.6	2084.9	2117.2	2151.9	2184.2	2164.3	2144.5	2124.6	2104.8
27.5°	1980.7	2055.1	2129.6	2176.7	2221.4	2268.6	2315.7	2313.2	2310.8	2305.8	2303.3
30°	1973.2	2030.3	2087.4	2144.5	2201.6	2258.6	2315.7	2345.5	2372.8	2402.6	2432.4
32.5°	2015.4	2062.6	2112.2	2171.8	2231.3	2293.4	2353.0	2415.0	2474.6	2536.6	2598.7
35°	2079.9	2122.1	2166.8	2231.3	2298.4	2362.9	2429.9	2504.4	2581.3	2658.2	2732.7
37.5°	2176.7	2214.0	2253.7	2308.3	2365.4	2420.0	2477.1	2586.3	2695.5	2807.2	2916.4
40°	2288.4	2313.2	2338.1	2390.2	2442.3	2494.4	2546.6	2683.1	2819.6	2956.1	3092.6
42.5°	2449.8	2442.3	2434.9	2477.1	2521.7	2563.9	2608.6	2732.7	2856.8	2980.9	3105.0
45°	2621.0	2591.2	2561.5	2581.3	2603.6	2623.5	2645.8	2772.4	2899.0	3028.1	3154.7
47.5°	2827.0	2752.6	2678.1	2660.7	2643.4	2623.5	2606.1	2742.6	2879.1	3018.1	3154.7
50°	3060.3	2948.6	2839.4	2794.8	2747.6	2702.9	2655.8	2767.5	2881.6	2995.8	3107.5
52.5°	3303.6	3164.6	3028.1	2958.6	2889.1	2817.1	2747.6	2841.9	2938.7	3035.5	3129.8
55°	3512.1	3370.6	3226.6	3144.7	3062.8	2980.9	2899.0	2993.3	3087.6	3182.0	3276.3
57.5°	3678.4	3536.9	3395.4	3318.5	3239.0	3162.1	3082.7	3172.0	3263.9	3355.7	3445.1
60°	3792.5	3656.0	3519.5	3445.1	3370.6	3296.1	3221.7	3328.4	3435.1	3544.3	3651.1
62.5°	3733.0	3633.7	3534.4	3502.1	3469.9	3435.1	3402.9	3504.6	3603.9	3705.7	3807.4
65°	3514.5	3447.5	3380.5	3412.8	3447.5	3479.8	3514.5	3581.6	3648.6	3718.1	3785.1
67.5°	3159.6	3154.7	3147.2	3219.2	3291.2	3365.6	3437.6	3482.3	3524.5	3569.2	3613.8
70°	2650.8	2678.1	2702.9	2827.0	2951.1	3075.2	3199.3	3216.7	3234.1	3251.5	3268.8
72.5°	2075.0	2109.7	2147.0	2310.8	2472.1	2635.9	2799.7	2789.8	2779.9	2767.5	2757.5
75°	1633.2	1665.4	1700.2	1851.6	2003.0	2154.4	2305.8	2263.6	2223.9	2181.7	2139.5
77.5°	1303.1	1337.8	1375.0	1516.5	1658.0	1802.0	1943.4	1841.7	1739.9	1638.1	1536.4
80°	1121.9	1139.2	1154.1	1250.9	1345.3	1442.1	1538.9	1434.6	1327.9	1221.2	1116.9
82.5°	920.8	910.9	903.5	960.5	1017.6	1074.7	1131.8	1032.5	933.2	831.5	732.2
85°	687.5	677.6	667.7	697.4	727.2	759.5	789.3	675.1	560.9	444.3	330.1
87.5°	399.6	409.5	419.5	451.7	484.0	518.7	551.0	434.4	317.7	198.6	81.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675979
 CATALOG NUMBER: CCW-SA-1E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675979
 CATALOG NUMBER: CCW-SA-1E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1787.1	1787.1
2.5°	1856.6	1844.1
5°	1754.8	1737.4
7.5°	1643.1	1620.8
10°	1541.3	1511.6
12.5°	1476.8	1439.6
15°	1452.0	1407.3
17.5°	1526.4	1484.3
20°	1640.6	1583.5
22.5°	1779.6	1710.1
25°	2020.4	1936.0
27.5°	2216.4	2129.6
30°	2338.1	2243.8
32.5°	2472.1	2348.0
35°	2611.1	2492.0
37.5°	2779.9	2645.8
40°	2953.6	2814.6
42.5°	3013.2	2923.8
45°	3070.3	2985.9
47.5°	3082.7	3013.2
50°	3095.1	3085.2
52.5°	3129.8	3127.4
55°	3278.8	3281.2
57.5°	3462.4	3477.3
60°	3631.2	3613.8
62.5°	3718.1	3628.7
65°	3658.5	3534.4
67.5°	3479.8	3345.8
70°	3087.6	2906.5
72.5°	2598.7	2439.8
75°	2003.0	1869.0
77.5°	1424.7	1313.0
80°	1002.7	891.0
82.5°	642.8	553.5
85°	290.4	253.2
87.5°	81.9	79.4
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P675979
CATALOG NUMBER: CCW-SA-1E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)