

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P675985

Luminaire Tested: **CCW-SA-2E-735-U-SLR**

Issue Date: 04/25/2023



Test Information

Test Method: LM-79-08
Report Number: P675985
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-2E-735-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @1050mA w/
SLR distribution lens
Light Source: (32) 3500K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11191.4 lumens
Efficiency: N/A
Efficacy: 105.0 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B2 - U0 - G3

Input Watts (W): 106.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P675985
 CATALOG NUMBER: CCW-SA-2E-735-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 15.9 fc
 Type IV - Short - N/A

REPORT NUMBER: P675985
CATALOG NUMBER: CCW-SA-2E-735-U-SLR

Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P675985

CATALOG NUMBER: CCW-SA-2E-735-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2302.7	0.0	2302.7
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	8888.7	0.0	8888.7
	% Fixture	79.4	0.0	79.4
Total	Lumens	11191.4	0.0	11191.4
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	277.7	2.5
10°-20°	586.3	5.2
20°-30°	857.8	7.7
30°-40°	1208.5	10.8
40°-50°	1660.7	14.8
50°-60°	2263.5	20.2
60°-70°	2477.4	22.1
70°-80°	1430.7	12.8
80°-90°	428.9	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	11191.4	100.0
0°-180°	11191.4	100.0



REPORT NUMBER: P675985


CATALOG NUMBER: CCW-SA-2E-735-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1149.4	10.3			
FM (30°-60°)	4084.1	36.5			
FH (60°-80°)	3291.0	29.4			G2/5000
FVH (80°-90°)	364.3	3.3			G3/500
BL (0°-30°)	572.5	5.1	B2/1000		
BM (30°-60°)	1048.6	9.4	B2/2500		
BH (60°-80°)	617.1	5.5	B2/1000		G2/1000
BVH (80°-90°)	64.6	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G3

Type IV Short





REPORT NUMBER: P675985

CATALOG NUMBER: CCW-SA-2E-735-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9
2.5°	3688.0	3668.2	3653.3	3638.4	3618.5	3603.6	3583.8	3563.9	3539.1	3519.3	3494.4
5°	3474.6	3415.0	3355.5	3320.7	3281.0	3246.3	3206.5	3161.9	3117.2	3067.6	3022.9
7.5°	3241.3	3166.8	3092.4	3032.8	2968.3	2908.7	2844.2	2789.6	2735.0	2680.4	2625.8
10°	3022.9	2953.4	2883.9	2809.4	2730.0	2655.6	2576.2	2501.7	2427.2	2352.8	2278.3
12.5°	2878.9	2794.6	2715.1	2630.8	2551.3	2467.0	2382.6	2313.1	2243.6	2169.1	2099.6
15°	2814.4	2735.0	2660.5	2576.2	2491.8	2407.4	2323.0	2243.6	2169.1	2089.7	2010.3
17.5°	2968.3	2854.1	2740.0	2630.8	2521.6	2412.4	2303.2	2203.9	2104.6	2005.3	1906.1
20°	3166.8	3022.9	2883.9	2749.9	2610.9	2476.9	2337.9	2198.9	2059.9	1920.9	1782.0
22.5°	3420.0	3256.2	3097.3	2923.6	2744.9	2571.2	2392.5	2218.8	2045.0	1866.3	1692.6
25°	3871.7	3678.1	3484.5	3236.3	2983.2	2735.0	2481.8	2253.5	2030.1	1801.8	1573.5
27.5°	4258.8	3995.8	3737.7	3439.8	3142.0	2844.2	2546.4	2283.3	2025.2	1762.1	1499.0
30°	4487.2	4229.1	3970.9	3608.6	3251.2	2888.9	2526.5	2233.7	1945.8	1652.9	1360.1
32.5°	4695.6	4407.8	4119.9	3722.8	3320.7	2923.6	2521.6	2198.9	1881.2	1558.6	1236.0
35°	4983.5	4665.9	4353.2	3891.5	3429.9	2968.3	2506.7	2174.1	1836.6	1504.0	1166.5
37.5°	5291.3	4899.2	4512.0	4000.7	3489.5	2978.2	2467.0	2139.3	1811.7	1484.1	1156.5
40°	5628.8	5152.3	4680.8	4114.9	3554.0	2988.1	2422.3	2094.7	1767.1	1434.5	1106.9
42.5°	5847.2	5331.0	4814.8	4204.2	3598.7	2988.1	2377.6	2055.0	1732.3	1404.7	1082.1
45°	5971.3	5470.0	4973.6	4313.4	3653.3	2993.1	2332.9	2015.3	1697.6	1374.9	1057.3
47.5°	6025.9	5559.3	5092.7	4397.8	3707.9	3013.0	2318.0	1995.4	1667.8	1345.2	1017.6
50°	6169.9	5757.9	5345.9	4601.3	3861.7	3117.2	2372.6	2025.2	1682.7	1335.2	987.8
52.5°	6254.2	5901.8	5549.4	4785.0	4020.6	3256.2	2491.8	2104.6	1717.4	1330.3	943.1
55°	6562.0	6224.5	5886.9	5072.9	4253.9	3439.8	2620.8	2193.9	1767.1	1335.2	908.4
57.5°	6954.1	6596.7	6244.3	5365.7	4487.2	3608.6	2730.0	2273.4	1811.7	1355.1	893.5
60°	7227.1	6879.7	6537.2	5604.0	4665.9	3732.7	2794.6	2318.0	1841.5	1360.1	883.5
62.5°	7256.9	6810.2	6368.4	5460.1	4551.7	3638.4	2730.0	2268.4	1806.8	1340.2	878.6
65°	7068.3	6547.1	6025.9	5157.3	4288.6	3420.0	2551.3	2129.4	1707.5	1280.6	858.7
67.5°	6691.0	6080.5	5470.0	4675.8	3881.6	3087.4	2293.2	1930.9	1573.5	1211.1	848.8
70°	5812.5	5276.4	4745.3	4055.3	3370.3	2680.4	1990.4	1692.6	1399.8	1101.9	804.1
72.5°	4879.3	4378.0	3881.6	3320.7	2764.8	2203.9	1643.0	1419.6	1196.2	967.9	744.6
75°	3737.7	3360.4	2988.1	2571.2	2154.2	1732.3	1315.4	1151.6	987.8	824.0	660.2
77.5°	2625.8	2422.3	2223.7	1911.0	1598.3	1285.6	972.9	863.7	754.5	645.3	536.1
80°	1782.0	1667.8	1558.6	1335.2	1111.9	883.5	660.2	590.7	516.2	446.7	372.3
82.5°	1106.9	1101.9	1092.0	938.1	784.3	630.4	476.5	416.9	362.3	302.8	243.2
85°	506.3	590.7	670.1	585.7	501.3	416.9	332.6	292.9	253.1	208.5	168.8
87.5°	158.8	193.6	223.4	213.4	198.5	188.6	173.7	148.9	124.1	99.3	74.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675985
 CATALOG NUMBER: CCW-SA-2E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675985

CATALOG NUMBER: CCW-SA-2E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9
2.5°	3474.6	3459.7	3439.8	3420.0	3395.2	3375.3	3350.5	3325.7	3320.7	3310.8	3305.8
5°	2993.1	2963.3	2928.6	2898.8	2869.0	2834.3	2804.5	2769.7	2744.9	2715.1	2690.3
7.5°	2571.2	2521.6	2467.0	2412.4	2362.7	2313.1	2258.5	2208.8	2184.0	2159.2	2134.4
10°	2233.7	2184.0	2139.3	2089.7	2055.0	2025.2	1990.4	1955.7	1925.9	1896.1	1866.3
12.5°	2064.9	2030.1	1995.4	1960.7	1920.9	1886.2	1846.5	1806.8	1772.0	1742.3	1707.5
15°	1960.7	1911.0	1856.4	1806.8	1752.2	1702.5	1647.9	1593.3	1553.6	1518.9	1479.2
17.5°	1836.6	1762.1	1692.6	1618.2	1558.6	1499.0	1434.5	1374.9	1330.3	1280.6	1236.0
20°	1697.6	1613.2	1523.9	1439.5	1370.0	1305.4	1236.0	1166.5	1116.8	1062.2	1012.6
22.5°	1578.5	1469.3	1355.1	1240.9	1166.5	1092.0	1012.6	938.1	893.5	843.8	799.2
25°	1449.4	1330.3	1206.2	1082.1	1007.6	928.2	853.8	774.3	739.6	709.8	675.1
27.5°	1379.9	1260.8	1136.7	1017.6	948.1	873.6	804.1	729.7	704.8	675.1	650.2
30°	1240.9	1126.8	1007.6	888.5	838.9	794.2	744.6	694.9	685.0	680.0	670.1
32.5°	1116.8	997.7	878.6	759.4	714.8	670.1	625.4	580.8	575.8	565.9	560.9
35°	1052.3	938.1	819.0	704.8	665.1	620.5	580.8	536.1	526.2	511.3	501.3
37.5°	1037.4	918.3	794.2	675.1	635.4	595.6	551.0	511.3	501.3	491.4	481.5
40°	997.7	883.5	774.3	660.2	620.5	580.8	536.1	496.4	486.4	476.5	466.6
42.5°	967.9	858.7	744.6	630.4	595.6	560.9	521.2	486.4	476.5	466.6	451.7
45°	943.1	828.9	709.8	595.6	570.8	546.0	516.2	491.4	481.5	466.6	456.7
47.5°	903.4	794.2	680.0	565.9	541.0	521.2	496.4	471.6	461.6	451.7	441.8
50°	873.6	759.4	645.3	531.1	511.3	491.4	471.6	451.7	451.7	456.7	456.7
52.5°	833.9	724.7	615.5	506.3	486.4	466.6	446.7	426.9	431.8	436.8	441.8
55°	799.2	694.9	585.7	476.5	456.7	436.8	412.0	392.1	397.1	402.1	407.0
57.5°	784.3	675.1	565.9	456.7	436.8	412.0	392.1	367.3	367.3	367.3	367.3
60°	774.3	660.2	551.0	436.8	412.0	392.1	367.3	342.5	337.5	337.5	332.6
62.5°	769.4	655.2	546.0	431.8	402.1	377.2	347.5	317.7	312.7	307.7	302.8
65°	749.5	645.3	536.1	426.9	392.1	362.3	327.6	292.9	287.9	287.9	282.9
67.5°	744.6	635.4	531.1	421.9	387.2	347.5	312.7	273.0	268.0	263.1	258.1
70°	704.8	610.5	511.3	412.0	372.3	337.5	297.8	258.1	253.1	243.2	238.3
72.5°	655.2	570.8	481.5	392.1	352.4	312.7	273.0	233.3	228.3	223.4	213.4
75°	580.8	501.3	421.9	342.5	307.7	278.0	243.2	208.5	203.5	198.5	188.6
77.5°	476.5	412.0	352.4	287.9	263.1	238.3	213.4	188.6	183.7	178.7	168.8
80°	337.5	297.8	263.1	223.4	208.5	188.6	173.7	153.9	153.9	148.9	148.9
82.5°	223.4	203.5	183.7	163.8	153.9	143.9	134.0	124.1	124.1	119.1	119.1
85°	158.8	148.9	134.0	124.1	119.1	109.2	104.2	94.3	94.3	94.3	94.3
87.5°	74.5	74.5	69.5	69.5	64.5	64.5	59.6	54.6	54.6	54.6	54.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675985
 CATALOG NUMBER: CCW-SA-2E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675985

CATALOG NUMBER: CCW-SA-2E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9
2.5°	3295.9	3281.0	3266.1	3246.3	3231.4	3211.5	3186.7	3166.8	3142.0	3142.0	3137.0
5°	2660.5	2645.6	2630.8	2610.9	2596.0	2576.2	2561.3	2541.4	2521.6	2521.6	2516.6
7.5°	2109.6	2079.8	2050.0	2015.3	1985.5	1965.6	1945.8	1920.9	1901.1	1886.2	1871.3
10°	1836.6	1806.8	1772.0	1742.3	1707.5	1682.7	1657.9	1628.1	1603.3	1583.4	1563.6
12.5°	1672.8	1638.0	1603.3	1568.5	1533.8	1499.0	1469.3	1434.5	1399.8	1374.9	1350.1
15°	1439.5	1404.7	1370.0	1335.2	1300.5	1260.8	1221.1	1176.4	1136.7	1116.8	1101.9
17.5°	1186.3	1151.6	1111.9	1077.1	1037.4	1007.6	977.8	948.1	918.3	898.4	883.5
20°	958.0	918.3	878.6	838.9	799.2	779.3	759.4	739.6	719.7	704.8	694.9
22.5°	749.5	724.7	704.8	680.0	655.2	640.3	630.4	615.5	600.6	600.6	600.6
25°	640.3	625.4	615.5	600.6	585.7	580.8	575.8	565.9	560.9	555.9	555.9
27.5°	620.5	605.6	590.7	575.8	560.9	555.9	551.0	541.0	536.1	536.1	536.1
30°	660.2	655.2	650.2	645.3	640.3	630.4	615.5	605.6	590.7	580.8	570.8
32.5°	551.0	546.0	546.0	541.0	536.1	546.0	551.0	560.9	565.9	570.8	575.8
35°	486.4	476.5	466.6	456.7	446.7	441.8	436.8	431.8	426.9	426.9	421.9
37.5°	471.6	461.6	451.7	441.8	431.8	426.9	421.9	416.9	412.0	412.0	407.0
40°	456.7	446.7	441.8	431.8	421.9	416.9	412.0	402.1	397.1	392.1	392.1
42.5°	441.8	436.8	426.9	421.9	412.0	407.0	402.1	392.1	387.2	382.2	377.2
45°	441.8	431.8	421.9	412.0	402.1	397.1	387.2	382.2	372.3	372.3	367.3
47.5°	431.8	421.9	412.0	402.1	392.1	387.2	377.2	372.3	362.3	357.4	352.4
50°	456.7	441.8	421.9	407.0	387.2	382.2	372.3	367.3	357.4	352.4	347.5
52.5°	446.7	431.8	412.0	397.1	377.2	367.3	362.3	352.4	342.5	337.5	332.6
55°	412.0	397.1	387.2	372.3	357.4	347.5	337.5	327.6	317.7	312.7	312.7
57.5°	367.3	362.3	357.4	352.4	347.5	337.5	327.6	312.7	302.8	297.8	292.9
60°	327.6	332.6	337.5	342.5	347.5	332.6	317.7	302.8	287.9	282.9	278.0
62.5°	297.8	307.7	317.7	322.6	332.6	317.7	302.8	287.9	273.0	268.0	263.1
65°	278.0	282.9	282.9	287.9	287.9	278.0	273.0	263.1	253.1	248.2	248.2
67.5°	253.1	253.1	253.1	248.2	248.2	243.2	243.2	238.3	233.3	228.3	228.3
70°	228.3	228.3	228.3	223.4	223.4	218.4	218.4	213.4	208.5	208.5	203.5
72.5°	208.5	208.5	203.5	203.5	198.5	198.5	198.5	193.6	193.6	188.6	188.6
75°	183.7	183.7	178.7	178.7	173.7	173.7	173.7	168.8	168.8	168.8	163.8
77.5°	163.8	163.8	158.8	158.8	153.9	153.9	153.9	148.9	148.9	143.9	143.9
80°	143.9	143.9	139.0	139.0	134.0	134.0	129.1	129.1	124.1	124.1	119.1
82.5°	114.2	114.2	114.2	114.2	114.2	109.2	109.2	104.2	99.3	99.3	94.3
85°	94.3	94.3	94.3	89.3	89.3	89.3	84.4	84.4	79.4	74.5	74.5
87.5°	54.6	54.6	54.6	49.6	49.6	49.6	49.6	49.6	49.6	49.6	44.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675985
 CATALOG NUMBER: CCW-SA-2E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675985

CATALOG NUMBER: CCW-SA-2E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9
2.5°	3137.0	3132.1	3112.2	3092.4	3112.2	3132.1	3132.1	3132.1	3127.1	3127.1	3127.1
5°	2516.6	2511.6	2501.7	2491.8	2491.8	2486.8	2496.7	2506.7	2516.6	2526.5	2536.4
7.5°	1851.5	1836.6	1821.7	1806.8	1816.7	1821.7	1836.6	1846.5	1861.4	1871.3	1896.1
10°	1543.7	1523.9	1509.0	1494.1	1484.1	1474.2	1464.3	1459.3	1449.4	1439.5	1449.4
12.5°	1320.3	1295.5	1270.7	1240.9	1236.0	1231.0	1221.1	1211.1	1201.2	1191.3	1186.3
15°	1082.1	1062.2	1052.3	1037.4	1017.6	997.7	987.8	982.8	972.9	963.0	958.0
17.5°	863.7	843.8	828.9	814.0	809.1	799.2	799.2	799.2	799.2	799.2	799.2
20°	680.0	665.1	665.1	660.2	660.2	655.2	660.2	665.1	665.1	670.1	675.1
22.5°	595.6	595.6	590.7	585.7	590.7	590.7	595.6	600.6	605.6	610.5	615.5
25°	551.0	546.0	551.0	555.9	555.9	555.9	560.9	560.9	565.9	565.9	565.9
27.5°	531.1	531.1	536.1	536.1	541.0	541.0	541.0	536.1	536.1	531.1	531.1
30°	560.9	551.0	551.0	551.0	546.0	541.0	536.1	536.1	531.1	526.2	521.2
32.5°	580.8	585.7	580.8	570.8	565.9	555.9	551.0	541.0	536.1	526.2	516.2
35°	421.9	416.9	426.9	431.8	436.8	441.8	446.7	451.7	451.7	456.7	456.7
37.5°	407.0	402.1	402.1	397.1	397.1	397.1	397.1	397.1	392.1	392.1	397.1
40°	387.2	382.2	382.2	377.2	377.2	372.3	372.3	372.3	372.3	372.3	372.3
42.5°	372.3	367.3	367.3	367.3	367.3	362.3	362.3	357.4	357.4	352.4	352.4
45°	367.3	362.3	357.4	352.4	352.4	347.5	347.5	347.5	342.5	342.5	342.5
47.5°	347.5	342.5	342.5	337.5	337.5	332.6	332.6	332.6	327.6	327.6	327.6
50°	337.5	332.6	332.6	327.6	327.6	322.6	322.6	322.6	317.7	317.7	317.7
52.5°	322.6	317.7	317.7	317.7	312.7	307.7	307.7	307.7	302.8	302.8	302.8
55°	307.7	302.8	302.8	302.8	297.8	292.9	292.9	292.9	287.9	287.9	287.9
57.5°	287.9	282.9	282.9	278.0	278.0	278.0	278.0	278.0	273.0	273.0	273.0
60°	273.0	268.0	268.0	263.1	263.1	258.1	258.1	258.1	258.1	258.1	258.1
62.5°	258.1	253.1	248.2	243.2	248.2	248.2	248.2	248.2	243.2	243.2	243.2
65°	243.2	238.3	233.3	228.3	228.3	228.3	228.3	228.3	228.3	228.3	228.3
67.5°	223.4	218.4	213.4	208.5	213.4	213.4	213.4	213.4	213.4	213.4	213.4
70°	203.5	198.5	198.5	193.6	193.6	188.6	188.6	193.6	193.6	193.6	193.6
72.5°	183.7	178.7	178.7	173.7	173.7	173.7	173.7	173.7	173.7	173.7	173.7
75°	163.8	158.8	158.8	153.9	153.9	153.9	153.9	153.9	153.9	153.9	153.9
77.5°	139.0	134.0	134.0	134.0	134.0	134.0	134.0	139.0	139.0	139.0	139.0
80°	119.1	114.2	114.2	114.2	114.2	114.2	114.2	114.2	114.2	114.2	114.2
82.5°	94.3	89.3	89.3	89.3	89.3	89.3	89.3	89.3	89.3	89.3	89.3
85°	69.5	64.5	64.5	64.5	69.5	69.5	69.5	69.5	69.5	69.5	69.5
87.5°	44.7	39.7	39.7	39.7	44.7	44.7	44.7	44.7	39.7	39.7	39.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675985
 CATALOG NUMBER: CCW-SA-2E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675985

CATALOG NUMBER: CCW-SA-2E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9
2.5°	3127.1	3127.1	3127.1	3122.2	3117.2	3112.2	3107.3	3122.2	3132.1	3147.0	3156.9
5°	2541.4	2551.3	2556.3	2571.2	2586.1	2601.0	2615.9	2625.8	2635.7	2640.7	2650.6
7.5°	1916.0	1940.8	1960.7	1980.5	2000.4	2015.3	2035.1	2050.0	2064.9	2079.8	2094.7
10°	1454.4	1464.3	1469.3	1489.1	1504.0	1523.9	1538.7	1553.6	1568.5	1578.5	1593.3
12.5°	1181.4	1171.4	1166.5	1166.5	1166.5	1166.5	1166.5	1176.4	1186.3	1196.2	1206.2
15°	953.0	948.1	943.1	938.1	933.2	923.2	918.3	928.2	938.1	948.1	958.0
17.5°	799.2	799.2	799.2	794.2	789.2	784.3	779.3	784.3	789.2	789.2	794.2
20°	685.0	690.0	694.9	699.9	699.9	704.8	704.8	709.8	714.8	714.8	719.7
22.5°	615.5	620.5	620.5	620.5	625.4	625.4	625.4	630.4	635.4	640.3	645.3
25°	560.9	560.9	555.9	555.9	560.9	560.9	560.9	560.9	565.9	565.9	565.9
27.5°	531.1	526.2	526.2	526.2	526.2	521.2	521.2	521.2	521.2	521.2	521.2
30°	516.2	511.3	506.3	501.3	501.3	496.4	491.4	491.4	491.4	491.4	491.4
32.5°	511.3	501.3	491.4	486.4	486.4	481.5	476.5	471.6	471.6	466.6	461.6
35°	456.7	451.7	451.7	446.7	441.8	436.8	431.8	431.8	431.8	426.9	426.9
37.5°	397.1	402.1	402.1	402.1	407.0	407.0	407.0	407.0	412.0	412.0	412.0
40°	372.3	372.3	372.3	377.2	382.2	382.2	387.2	387.2	392.1	392.1	392.1
42.5°	352.4	347.5	347.5	352.4	352.4	357.4	357.4	362.3	367.3	367.3	372.3
45°	342.5	337.5	337.5	337.5	337.5	332.6	332.6	337.5	342.5	347.5	352.4
47.5°	322.6	322.6	317.7	317.7	317.7	317.7	317.7	317.7	322.6	322.6	322.6
50°	312.7	312.7	307.7	307.7	307.7	307.7	307.7	307.7	307.7	307.7	307.7
52.5°	302.8	297.8	297.8	297.8	297.8	292.9	292.9	292.9	292.9	292.9	292.9
55°	287.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	287.9	287.9	287.9
57.5°	273.0	268.0	268.0	268.0	273.0	273.0	273.0	273.0	278.0	278.0	278.0
60°	258.1	258.1	258.1	258.1	258.1	258.1	258.1	263.1	263.1	268.0	268.0
62.5°	243.2	243.2	243.2	243.2	248.2	248.2	248.2	248.2	253.1	253.1	253.1
65°	228.3	228.3	228.3	228.3	233.3	233.3	233.3	233.3	233.3	233.3	233.3
67.5°	213.4	213.4	213.4	213.4	213.4	213.4	213.4	218.4	218.4	223.4	223.4
70°	193.6	188.6	188.6	193.6	193.6	198.5	198.5	203.5	203.5	208.5	208.5
72.5°	173.7	173.7	173.7	173.7	173.7	173.7	173.7	178.7	183.7	183.7	188.6
75°	153.9	153.9	153.9	153.9	158.8	158.8	158.8	163.8	163.8	168.8	168.8
77.5°	139.0	134.0	134.0	134.0	139.0	139.0	139.0	143.9	143.9	148.9	148.9
80°	114.2	114.2	114.2	114.2	119.1	119.1	119.1	119.1	124.1	124.1	124.1
82.5°	94.3	94.3	94.3	94.3	94.3	94.3	94.3	94.3	99.3	99.3	99.3
85°	69.5	69.5	69.5	69.5	74.5	74.5	74.5	74.5	74.5	74.5	74.5
87.5°	44.7	44.7	44.7	44.7	44.7	44.7	44.7	44.7	49.6	49.6	49.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675985
 CATALOG NUMBER: CCW-SA-2E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675985
 CATALOG NUMBER: CCW-SA-2E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9
2.5°	3156.9	3156.9	3156.9	3156.9	3166.8	3171.8	3181.7	3186.7	3181.7	3176.8	3166.8
5°	2655.6	2660.5	2660.5	2665.5	2665.5	2665.5	2665.5	2665.5	2675.4	2685.4	2695.3
7.5°	2099.6	2104.6	2109.6	2114.5	2114.5	2114.5	2109.6	2109.6	2114.5	2114.5	2119.5
10°	1608.2	1628.1	1643.0	1657.9	1647.9	1633.1	1623.1	1608.2	1608.2	1608.2	1603.3
12.5°	1216.1	1221.1	1231.0	1236.0	1231.0	1231.0	1226.0	1221.1	1226.0	1236.0	1240.9
15°	963.0	963.0	967.9	967.9	972.9	977.8	977.8	982.8	992.7	997.7	1007.6
17.5°	799.2	804.1	804.1	809.1	809.1	814.0	814.0	814.0	824.0	833.9	848.8
20°	719.7	719.7	719.7	719.7	719.7	714.8	714.8	709.8	714.8	724.7	729.7
22.5°	645.3	650.2	650.2	650.2	645.3	640.3	630.4	625.4	625.4	630.4	630.4
25°	565.9	560.9	560.9	555.9	555.9	560.9	560.9	560.9	565.9	565.9	570.8
27.5°	521.2	516.2	516.2	511.3	511.3	516.2	516.2	516.2	516.2	516.2	516.2
30°	486.4	486.4	481.5	476.5	481.5	481.5	486.4	486.4	491.4	491.4	496.4
32.5°	461.6	456.7	456.7	451.7	456.7	456.7	461.6	461.6	466.6	471.6	471.6
35°	426.9	426.9	426.9	426.9	426.9	426.9	421.9	421.9	421.9	421.9	421.9
37.5°	407.0	407.0	402.1	397.1	397.1	397.1	397.1	397.1	392.1	387.2	382.2
40°	392.1	387.2	387.2	382.2	377.2	377.2	372.3	367.3	367.3	362.3	362.3
42.5°	372.3	367.3	367.3	362.3	357.4	357.4	352.4	347.5	347.5	347.5	342.5
45°	347.5	347.5	342.5	337.5	337.5	337.5	332.6	332.6	332.6	332.6	327.6
47.5°	322.6	322.6	317.7	317.7	317.7	317.7	312.7	312.7	312.7	312.7	312.7
50°	307.7	307.7	307.7	307.7	307.7	307.7	302.8	302.8	302.8	302.8	302.8
52.5°	292.9	292.9	292.9	292.9	292.9	292.9	292.9	292.9	292.9	292.9	292.9
55°	287.9	287.9	287.9	287.9	287.9	287.9	282.9	282.9	282.9	287.9	287.9
57.5°	278.0	278.0	273.0	273.0	273.0	273.0	273.0	273.0	273.0	273.0	273.0
60°	268.0	268.0	268.0	268.0	268.0	268.0	268.0	268.0	268.0	268.0	268.0
62.5°	253.1	253.1	253.1	253.1	253.1	258.1	258.1	258.1	258.1	258.1	253.1
65°	233.3	238.3	238.3	238.3	238.3	238.3	238.3	238.3	238.3	238.3	238.3
67.5°	223.4	223.4	223.4	223.4	223.4	223.4	223.4	223.4	223.4	223.4	223.4
70°	208.5	208.5	203.5	203.5	203.5	208.5	208.5	208.5	208.5	208.5	208.5
72.5°	188.6	188.6	188.6	188.6	188.6	188.6	188.6	188.6	188.6	193.6	193.6
75°	168.8	168.8	168.8	168.8	168.8	168.8	168.8	168.8	168.8	168.8	168.8
77.5°	148.9	148.9	143.9	143.9	143.9	148.9	148.9	148.9	148.9	153.9	153.9
80°	124.1	124.1	124.1	124.1	124.1	124.1	124.1	124.1	124.1	129.1	129.1
82.5°	99.3	99.3	99.3	99.3	99.3	99.3	99.3	99.3	99.3	104.2	104.2
85°	74.5	79.4	79.4	79.4	79.4	79.4	79.4	79.4	79.4	84.4	84.4
87.5°	49.6	49.6	49.6	49.6	49.6	49.6	44.7	44.7	44.7	44.7	39.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675985
 CATALOG NUMBER: CCW-SA-2E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675985

CATALOG NUMBER: CCW-SA-2E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9
2.5°	3161.9	3166.8	3171.8	3171.8	3176.8	3181.7	3181.7	3201.6	3221.4	3231.4	3241.3
5°	2705.2	2700.2	2700.2	2695.3	2690.3	2705.2	2720.1	2749.9	2779.7	2784.6	2794.6
7.5°	2119.5	2124.5	2129.4	2129.4	2134.4	2119.5	2099.6	2104.6	2109.6	2134.4	2154.2
10°	1603.3	1608.2	1613.2	1613.2	1618.2	1613.2	1603.3	1618.2	1633.1	1652.9	1677.7
12.5°	1245.9	1260.8	1275.7	1285.6	1300.5	1310.4	1315.4	1335.2	1350.1	1374.9	1399.8
15°	1017.6	1027.5	1037.4	1047.3	1057.3	1067.2	1077.1	1097.0	1116.8	1146.6	1176.4
17.5°	858.7	858.7	863.7	863.7	863.7	873.6	883.5	893.5	898.4	928.2	958.0
20°	734.6	729.7	724.7	719.7	714.8	724.7	729.7	734.6	739.6	759.4	774.3
22.5°	630.4	630.4	635.4	635.4	635.4	630.4	620.5	625.4	625.4	635.4	650.2
25°	570.8	570.8	570.8	565.9	565.9	570.8	575.8	575.8	570.8	575.8	580.8
27.5°	516.2	521.2	521.2	526.2	526.2	531.1	531.1	531.1	531.1	536.1	541.0
30°	496.4	496.4	501.3	501.3	501.3	506.3	511.3	511.3	511.3	516.2	526.2
32.5°	476.5	481.5	486.4	491.4	496.4	501.3	501.3	506.3	506.3	511.3	516.2
35°	421.9	416.9	416.9	412.0	407.0	407.0	407.0	407.0	402.1	407.0	407.0
37.5°	377.2	377.2	377.2	372.3	372.3	377.2	377.2	377.2	377.2	382.2	382.2
40°	357.4	357.4	357.4	357.4	357.4	357.4	357.4	362.3	362.3	367.3	372.3
42.5°	342.5	342.5	342.5	342.5	342.5	347.5	347.5	347.5	347.5	352.4	352.4
45°	327.6	327.6	327.6	327.6	327.6	327.6	327.6	332.6	332.6	337.5	342.5
47.5°	312.7	312.7	312.7	312.7	312.7	317.7	322.6	322.6	322.6	327.6	327.6
50°	302.8	302.8	302.8	302.8	302.8	307.7	307.7	312.7	312.7	317.7	322.6
52.5°	292.9	292.9	292.9	292.9	292.9	297.8	297.8	302.8	302.8	307.7	312.7
55°	287.9	287.9	287.9	282.9	282.9	287.9	287.9	292.9	292.9	297.8	297.8
57.5°	273.0	273.0	273.0	273.0	273.0	273.0	273.0	278.0	278.0	282.9	287.9
60°	268.0	268.0	263.1	263.1	258.1	263.1	263.1	268.0	268.0	273.0	273.0
62.5°	253.1	253.1	253.1	248.2	248.2	253.1	253.1	253.1	253.1	258.1	263.1
65°	238.3	238.3	238.3	233.3	233.3	238.3	238.3	238.3	238.3	243.2	248.2
67.5°	223.4	223.4	223.4	218.4	218.4	218.4	218.4	223.4	223.4	228.3	233.3
70°	208.5	208.5	208.5	203.5	203.5	203.5	198.5	203.5	208.5	213.4	213.4
72.5°	193.6	193.6	193.6	188.6	188.6	188.6	183.7	188.6	188.6	193.6	193.6
75°	168.8	168.8	168.8	168.8	168.8	168.8	163.8	163.8	163.8	168.8	168.8
77.5°	153.9	153.9	153.9	148.9	148.9	148.9	143.9	143.9	143.9	148.9	148.9
80°	129.1	129.1	129.1	124.1	124.1	124.1	119.1	119.1	119.1	124.1	124.1
82.5°	104.2	104.2	104.2	99.3	99.3	99.3	94.3	94.3	94.3	99.3	99.3
85°	84.4	84.4	84.4	84.4	84.4	84.4	79.4	79.4	79.4	84.4	89.3
87.5°	39.7	39.7	44.7	44.7	44.7	44.7	39.7	39.7	34.7	34.7	39.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675985
 CATALOG NUMBER: CCW-SA-2E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675985

CATALOG NUMBER: CCW-SA-2E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9
2.5°	3251.2	3261.1	3286.0	3305.8	3330.6	3350.5	3365.4	3385.2	3400.1	3415.0	3424.9
5°	2799.5	2804.5	2829.3	2854.1	2874.0	2898.8	2933.5	2968.3	3003.0	3037.8	3062.6
7.5°	2179.1	2198.9	2228.7	2263.4	2293.2	2323.0	2357.8	2397.5	2432.2	2467.0	2501.7
10°	1697.6	1717.4	1747.2	1777.0	1801.8	1831.6	1871.3	1911.0	1950.7	1990.4	2030.1
12.5°	1424.6	1449.4	1484.1	1518.9	1548.7	1583.4	1633.1	1677.7	1727.4	1772.0	1821.7
15°	1201.2	1231.0	1275.7	1325.3	1370.0	1414.7	1464.3	1513.9	1558.6	1608.2	1657.9
17.5°	987.8	1017.6	1057.3	1101.9	1141.6	1181.4	1240.9	1295.5	1355.1	1409.7	1464.3
20°	794.2	809.1	848.8	888.5	928.2	967.9	1012.6	1057.3	1101.9	1146.6	1216.1
22.5°	660.2	670.1	690.0	704.8	724.7	739.6	784.3	828.9	868.6	913.3	977.8
25°	580.8	585.7	600.6	610.5	625.4	635.4	665.1	690.0	719.7	744.6	804.1
27.5°	541.0	546.0	551.0	555.9	560.9	565.9	585.7	605.6	620.5	640.3	694.9
30°	531.1	536.1	551.0	560.9	575.8	585.7	595.6	605.6	615.5	625.4	660.2
32.5°	521.2	526.2	526.2	521.2	521.2	516.2	526.2	531.1	541.0	546.0	575.8
35°	412.0	412.0	416.9	421.9	426.9	431.8	446.7	456.7	471.6	481.5	506.3
37.5°	387.2	387.2	392.1	402.1	407.0	412.0	421.9	431.8	441.8	451.7	476.5
40°	372.3	377.2	382.2	387.2	392.1	397.1	407.0	412.0	421.9	426.9	446.7
42.5°	357.4	357.4	362.3	372.3	377.2	382.2	392.1	397.1	407.0	412.0	431.8
45°	347.5	352.4	357.4	362.3	362.3	367.3	377.2	387.2	392.1	402.1	421.9
47.5°	332.6	332.6	342.5	347.5	357.4	362.3	372.3	377.2	387.2	392.1	412.0
50°	322.6	327.6	337.5	342.5	352.4	357.4	372.3	382.2	397.1	407.0	416.9
52.5°	312.7	317.7	327.6	332.6	342.5	347.5	367.3	387.2	402.1	421.9	421.9
55°	302.8	302.8	312.7	327.6	337.5	347.5	357.4	372.3	382.2	392.1	392.1
57.5°	287.9	292.9	302.8	317.7	327.6	337.5	347.5	357.4	362.3	372.3	367.3
60°	278.0	278.0	292.9	307.7	322.6	337.5	337.5	337.5	332.6	332.6	332.6
62.5°	263.1	268.0	287.9	312.7	332.6	352.4	337.5	322.6	307.7	292.9	297.8
65°	253.1	258.1	268.0	282.9	292.9	302.8	292.9	287.9	278.0	268.0	273.0
67.5°	233.3	238.3	243.2	243.2	248.2	248.2	248.2	248.2	248.2	248.2	253.1
70°	218.4	218.4	218.4	223.4	223.4	223.4	223.4	223.4	223.4	223.4	228.3
72.5°	198.5	198.5	198.5	198.5	198.5	198.5	198.5	198.5	198.5	198.5	203.5
75°	173.7	173.7	173.7	173.7	173.7	173.7	173.7	173.7	173.7	173.7	178.7
77.5°	153.9	153.9	153.9	153.9	153.9	153.9	153.9	153.9	148.9	148.9	153.9
80°	129.1	129.1	129.1	129.1	124.1	124.1	124.1	124.1	124.1	124.1	129.1
82.5°	104.2	104.2	104.2	104.2	99.3	99.3	99.3	99.3	94.3	94.3	99.3
85°	94.3	99.3	99.3	104.2	104.2	104.2	99.3	94.3	89.3	84.4	84.4
87.5°	39.7	39.7	39.7	39.7	34.7	34.7	34.7	34.7	34.7	34.7	34.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675985
 CATALOG NUMBER: CCW-SA-2E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675985

CATALOG NUMBER: CCW-SA-2E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9
2.5°	3439.8	3449.8	3459.7	3474.6	3494.4	3509.3	3524.2	3554.0	3588.7	3618.5	3648.3
5°	3087.4	3112.2	3137.0	3166.8	3196.6	3221.4	3251.2	3310.8	3370.3	3424.9	3484.5
7.5°	2531.5	2566.2	2596.0	2645.6	2690.3	2740.0	2784.6	2859.1	2928.6	3003.0	3072.5
10°	2069.9	2109.6	2149.3	2213.8	2283.3	2347.8	2412.4	2471.9	2536.4	2596.0	2655.6
12.5°	1871.3	1916.0	1965.6	2005.3	2050.0	2089.7	2129.4	2198.9	2268.4	2337.9	2407.4
15°	1707.5	1757.1	1806.8	1856.4	1901.1	1950.7	1995.4	2055.0	2119.5	2179.1	2238.6
17.5°	1518.9	1568.5	1623.1	1677.7	1732.3	1786.9	1841.5	1925.9	2010.3	2089.7	2174.1
20°	1280.6	1350.1	1414.7	1489.1	1563.6	1638.0	1712.5	1801.8	1891.2	1975.5	2064.9
22.5°	1042.4	1106.9	1171.4	1260.8	1350.1	1434.5	1523.9	1643.0	1757.1	1876.3	1990.4
25°	868.6	928.2	987.8	1087.0	1181.4	1280.6	1374.9	1518.9	1657.9	1801.8	1940.8
27.5°	749.5	804.1	858.7	963.0	1067.2	1166.5	1270.7	1429.5	1583.4	1742.3	1896.1
30°	694.9	729.7	764.4	863.7	963.0	1057.3	1156.5	1310.4	1464.3	1618.2	1772.0
32.5°	605.6	635.4	665.1	754.5	843.8	928.2	1017.6	1176.4	1330.3	1489.1	1643.0
35°	536.1	560.9	585.7	670.1	749.5	833.9	913.3	1072.2	1231.0	1389.8	1548.7
37.5°	496.4	521.2	541.0	615.5	694.9	769.4	843.8	1002.7	1156.5	1315.4	1469.3
40°	466.6	481.5	501.3	575.8	645.3	719.7	789.2	933.2	1082.1	1226.0	1370.0
42.5°	446.7	466.6	481.5	546.0	615.5	680.0	744.6	883.5	1022.5	1156.5	1295.5
45°	441.8	461.6	481.5	536.1	590.7	640.3	694.9	828.9	963.0	1097.0	1231.0
47.5°	431.8	446.7	466.6	511.3	551.0	595.6	635.4	769.4	903.4	1032.4	1166.5
50°	426.9	431.8	441.8	481.5	521.2	560.9	600.6	734.6	868.6	1002.7	1136.7
52.5°	421.9	421.9	421.9	456.7	491.4	521.2	555.9	690.0	828.9	963.0	1097.0
55°	392.1	387.2	387.2	421.9	451.7	486.4	516.2	650.2	784.3	913.3	1047.3
57.5°	362.3	357.4	352.4	382.2	412.0	441.8	471.6	605.6	744.6	878.6	1012.6
60°	332.6	327.6	327.6	357.4	382.2	412.0	436.8	575.8	709.8	848.8	982.8
62.5°	297.8	302.8	302.8	327.6	357.4	382.2	407.0	546.0	690.0	828.9	967.9
65°	273.0	278.0	278.0	307.7	337.5	367.3	397.1	531.1	670.1	804.1	938.1
67.5°	253.1	258.1	258.1	292.9	322.6	357.4	387.2	506.3	630.4	749.5	868.6
70°	233.3	233.3	238.3	273.0	307.7	342.5	377.2	481.5	585.7	685.0	789.2
72.5°	208.5	213.4	218.4	253.1	282.9	317.7	347.5	441.8	536.1	630.4	724.7
75°	183.7	188.6	193.6	223.4	253.1	282.9	312.7	402.1	486.4	575.8	660.2
77.5°	163.8	168.8	173.7	198.5	223.4	248.2	273.0	337.5	407.0	471.6	536.1
80°	134.0	134.0	139.0	158.8	178.7	193.6	213.4	258.1	302.8	342.5	387.2
82.5°	99.3	104.2	104.2	119.1	129.1	143.9	153.9	178.7	198.5	223.4	243.2
85°	84.4	79.4	79.4	89.3	94.3	104.2	109.2	124.1	134.0	148.9	158.8
87.5°	34.7	29.8	29.8	34.7	44.7	49.6	54.6	54.6	59.6	59.6	59.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675985
 CATALOG NUMBER: CCW-SA-2E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675985

CATALOG NUMBER: CCW-SA-2E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9
2.5°	3663.2	3673.1	3688.0	3697.9	3722.8	3742.6	3767.4	3787.3	3802.2	3827.0	3817.1
5°	3529.2	3573.9	3618.5	3663.2	3697.9	3732.7	3762.5	3797.2	3836.9	3911.4	3931.2
7.5°	3132.1	3191.7	3246.3	3305.8	3375.3	3444.8	3514.3	3583.8	3648.3	3742.6	3802.2
10°	2740.0	2824.3	2903.8	2988.1	3052.7	3117.2	3176.8	3241.3	3330.6	3424.9	3534.1
12.5°	2491.8	2576.2	2660.5	2744.9	2839.2	2928.6	3022.9	3112.2	3196.6	3271.1	3395.2
15°	2328.0	2422.3	2511.6	2601.0	2715.1	2824.3	2938.5	3047.7	3171.8	3271.1	3355.5
17.5°	2288.3	2402.4	2511.6	2625.8	2744.9	2864.0	2983.2	3102.3	3226.4	3375.3	3484.5
20°	2218.8	2372.6	2526.5	2680.4	2834.3	2983.2	3137.0	3286.0	3449.8	3628.5	3678.1
22.5°	2179.1	2362.7	2551.3	2735.0	2943.5	3156.9	3365.4	3573.9	3747.6	3881.6	4030.5
25°	2174.1	2402.4	2635.7	2864.0	3127.1	3385.2	3648.3	3906.4	4129.8	4263.8	4382.9
27.5°	2169.1	2447.1	2720.1	2993.1	3315.7	3633.4	3956.1	4273.7	4482.2	4675.8	4775.1
30°	2109.6	2442.1	2779.7	3112.2	3474.6	3836.9	4199.3	4561.6	4775.1	4909.1	4958.7
32.5°	2035.1	2427.2	2819.4	3211.5	3623.5	4035.5	4442.5	4854.5	5023.3	5137.4	5097.7
35°	1975.5	2407.4	2834.3	3261.1	3697.9	4139.7	4576.5	5013.3	5256.5	5415.4	5350.9
37.5°	1920.9	2372.6	2824.3	3276.0	3787.3	4298.6	4809.8	5321.1	5554.4	5723.1	5648.7
40°	1856.4	2337.9	2824.3	3305.8	3891.5	4472.3	5058.0	5638.7	5941.5	6085.5	5971.3
42.5°	1801.8	2303.2	2809.4	3310.8	3936.2	4561.6	5187.1	5812.5	6150.0	6353.5	6209.6
45°	1732.3	2233.7	2730.0	3231.4	3921.3	4611.3	5296.3	5986.2	6378.3	6537.2	6338.6
47.5°	1657.9	2154.2	2645.6	3137.0	3871.7	4606.3	5340.9	6075.6	6437.9	6626.5	6442.9
50°	1633.1	2129.4	2620.8	3117.2	3911.4	4710.5	5504.7	6298.9	6562.0	6715.9	6472.6
52.5°	1628.1	2154.2	2685.4	3211.5	4010.7	4804.8	5604.0	6398.2	6611.6	6775.4	6557.0
55°	1613.2	2184.0	2749.9	3315.7	4149.6	4988.5	5822.4	6656.3	6869.7	6988.9	6825.1
57.5°	1628.1	2243.6	2854.1	3469.6	4328.3	5187.1	6045.8	6904.5	7162.6	7247.0	7212.2
60°	1638.0	2293.2	2943.5	3598.7	4437.5	5276.4	6115.3	6954.1	7222.2	7430.6	7470.3
62.5°	1613.2	2258.5	2898.8	3544.1	4303.5	5063.0	5822.4	6581.8	7023.6	7331.4	7510.1
65°	1538.7	2134.4	2735.0	3330.6	4030.5	4735.4	5435.2	6135.1	6601.7	7058.4	7202.3
67.5°	1374.9	1881.2	2387.5	2893.8	3504.4	4114.9	4720.5	5331.0	5916.7	6358.5	6557.0
70°	1191.3	1588.4	1990.4	2387.5	2943.5	3499.4	4055.3	4611.3	5127.5	5613.9	5802.5
72.5°	1037.4	1345.2	1657.9	1965.6	2362.7	2754.8	3151.9	3544.1	4154.6	4641.0	4824.7
75°	883.5	1106.9	1325.3	1548.7	1821.7	2094.7	2362.7	2635.7	3067.6	3504.4	3688.0
77.5°	680.0	828.9	972.9	1116.8	1305.4	1489.1	1677.7	1861.4	2164.2	2491.8	2586.1
80°	471.6	555.9	635.4	719.7	868.6	1017.6	1166.5	1315.4	1513.9	1697.6	1841.5
82.5°	292.9	347.5	397.1	446.7	565.9	685.0	799.2	918.3	997.7	1007.6	1151.6
85°	188.6	223.4	253.1	282.9	352.4	426.9	496.4	565.9	506.3	471.6	560.9
87.5°	74.5	94.3	109.2	124.1	119.1	114.2	109.2	104.2	89.3	79.4	99.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675985
 CATALOG NUMBER: CCW-SA-2E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675985

CATALOG NUMBER: CCW-SA-2E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9
2.5°	3827.0	3841.9	3856.8	3866.7	3881.6	3886.6	3891.5	3891.5	3896.5	3901.5	3911.4
5°	4010.7	4040.4	4070.2	4095.0	4124.8	4149.6	4169.5	4194.3	4214.2	4214.2	4209.2
7.5°	3856.8	3931.2	4005.7	4080.2	4154.6	4209.2	4258.8	4313.4	4363.1	4373.0	4382.9
10°	3653.3	3732.7	3807.1	3886.6	3961.0	4045.4	4124.8	4204.2	4288.6	4303.5	4323.4
12.5°	3464.7	3559.0	3653.3	3742.6	3836.9	3896.5	3956.1	4010.7	4070.2	4109.9	4149.6
15°	3459.7	3539.1	3618.5	3693.0	3772.4	3807.1	3841.9	3871.7	3906.4	3906.4	3911.4
17.5°	3573.9	3623.5	3673.1	3717.8	3767.4	3772.4	3782.3	3787.3	3792.3	3777.4	3762.5
20°	3797.2	3817.1	3836.9	3856.8	3876.6	3841.9	3812.1	3777.4	3742.6	3702.9	3668.2
22.5°	4124.8	4080.2	4035.5	3990.8	3946.1	3886.6	3822.0	3762.5	3697.9	3648.3	3598.7
25°	4432.6	4378.0	4323.4	4268.8	4214.2	4085.1	3956.1	3822.0	3693.0	3638.4	3583.8
27.5°	4844.6	4760.2	4675.8	4591.4	4507.0	4333.3	4159.6	3985.8	3812.1	3717.8	3628.5
30°	4943.8	4849.5	4755.2	4655.9	4561.6	4392.9	4229.1	4060.3	3891.5	3782.3	3678.1
32.5°	5087.8	4978.6	4869.4	4760.2	4651.0	4487.2	4323.4	4154.6	3990.8	3891.5	3787.3
35°	5326.0	5201.9	5077.9	4948.8	4824.7	4655.9	4492.1	4323.4	4154.6	4040.4	3931.2
37.5°	5529.5	5385.6	5241.7	5097.7	4953.8	4804.8	4651.0	4502.1	4348.2	4234.0	4124.8
40°	5757.9	5599.0	5440.2	5286.3	5127.5	4988.5	4849.5	4705.6	4566.6	4477.2	4387.9
42.5°	5956.4	5762.8	5574.2	5385.6	5192.0	5097.7	5008.4	4914.0	4819.7	4775.1	4725.4
45°	6095.4	5916.7	5733.1	5554.4	5375.7	5306.2	5236.7	5167.2	5097.7	5142.4	5187.1
47.5°	6155.0	6011.0	5872.0	5733.1	5589.1	5613.9	5638.7	5658.6	5683.4	5743.0	5807.5
50°	6209.6	6130.2	6045.8	5966.4	5882.0	5976.3	6065.6	6159.9	6254.2	6378.3	6502.4
52.5°	6318.8	6274.1	6234.4	6189.7	6145.0	6308.8	6472.6	6636.4	6800.3	6939.2	7078.2
55°	6646.4	6611.6	6576.9	6537.2	6502.4	6735.7	6964.1	7197.3	7430.6	7574.6	7718.5
57.5°	7098.1	7078.2	7053.4	7033.5	7008.7	7237.1	7460.4	7683.8	7912.1	8051.1	8195.0
60°	7440.6	7445.5	7445.5	7450.5	7450.5	7624.2	7798.0	7976.6	8150.4	8269.5	8393.6
62.5°	7624.2	7614.3	7604.4	7594.4	7584.5	7728.5	7872.4	8016.4	8160.3	8249.6	8339.0
65°	7425.7	7480.3	7534.9	7589.5	7644.1	7663.9	7678.8	7698.7	7713.6	7768.2	7822.8
67.5°	6760.5	6869.7	6974.0	7083.2	7187.4	7113.0	7043.5	6969.0	6894.6	6909.5	6919.4
70°	6021.0	6145.0	6274.1	6398.2	6522.3	6348.6	6174.8	5996.1	5822.4	5762.8	5703.3
72.5°	5077.9	5187.1	5301.2	5410.4	5519.6	5306.2	5097.7	4884.3	4670.8	4566.6	4462.4
75°	3881.6	4010.7	4144.7	4273.7	4402.8	4164.5	3921.3	3683.1	3439.8	3370.3	3305.8
77.5°	2829.3	2983.2	3137.0	3290.9	3444.8	3231.4	3017.9	2799.5	2586.1	2546.4	2506.7
80°	2059.9	2179.1	2293.2	2412.4	2526.5	2402.4	2278.3	2154.2	2030.1	2025.2	2020.2
82.5°	1389.8	1494.1	1593.3	1697.6	1796.9	1747.2	1702.5	1652.9	1603.3	1652.9	1707.5
85°	714.8	858.7	1007.6	1151.6	1295.5	1280.6	1270.7	1255.8	1240.9	1305.4	1365.0
87.5°	143.9	268.0	392.1	511.3	635.4	605.6	575.8	541.0	511.3	531.1	546.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675985
 CATALOG NUMBER: CCW-SA-2E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675985

CATALOG NUMBER: CCW-SA-2E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9
2.5°	3916.3	3921.3	3921.3	3921.3	3921.3	3921.3	3911.4	3906.4	3896.5	3886.6	3871.7
5°	4209.2	4204.2	4184.4	4164.5	4139.7	4119.9	4105.0	4085.1	4070.2	4050.4	4020.6
7.5°	4392.9	4402.8	4368.0	4338.3	4303.5	4268.8	4234.0	4199.3	4164.5	4129.8	4060.3
10°	4338.3	4353.2	4333.3	4313.4	4288.6	4268.8	4229.1	4184.4	4144.7	4100.0	4015.6
12.5°	4184.4	4224.1	4214.2	4204.2	4194.3	4184.4	4159.6	4129.8	4105.0	4075.2	3980.9
15°	3911.4	3911.4	3916.3	3921.3	3921.3	3926.3	3931.2	3936.2	3941.2	3946.1	3891.5
17.5°	3747.6	3732.7	3732.7	3732.7	3732.7	3732.7	3752.5	3777.4	3797.2	3817.1	3802.2
20°	3628.5	3593.7	3588.7	3588.7	3583.8	3578.8	3613.6	3653.3	3688.0	3722.8	3742.6
22.5°	3549.0	3499.4	3494.4	3489.5	3484.5	3479.5	3524.2	3568.9	3613.6	3658.2	3727.7
25°	3529.2	3474.6	3479.5	3484.5	3484.5	3489.5	3524.2	3559.0	3593.7	3628.5	3747.6
27.5°	3534.1	3444.8	3449.8	3454.7	3454.7	3459.7	3514.3	3563.9	3618.5	3668.2	3817.1
30°	3568.9	3464.7	3454.7	3444.8	3434.9	3424.9	3499.4	3573.9	3648.3	3722.8	3836.9
32.5°	3688.0	3588.7	3563.9	3539.1	3514.3	3489.5	3578.8	3663.2	3752.5	3836.9	3931.2
35°	3817.1	3707.9	3697.9	3688.0	3673.1	3663.2	3742.6	3827.0	3906.4	3985.8	4070.2
37.5°	4010.7	3901.5	3891.5	3876.6	3866.7	3851.8	3941.2	4025.5	4114.9	4199.3	4273.7
40°	4298.6	4209.2	4204.2	4204.2	4199.3	4194.3	4263.8	4338.3	4407.8	4477.2	4526.9
42.5°	4680.8	4636.1	4651.0	4670.8	4685.7	4700.6	4755.2	4814.8	4869.4	4924.0	4909.1
45°	5231.7	5276.4	5281.4	5286.3	5291.3	5296.3	5311.1	5331.0	5345.9	5360.8	5301.2
47.5°	5867.1	5926.6	5956.4	5986.2	6011.0	6040.8	6021.0	5996.1	5976.3	5951.5	5802.5
50°	6621.6	6745.7	6740.7	6735.7	6725.8	6720.8	6681.1	6641.4	6596.7	6557.0	6338.6
52.5°	7217.2	7356.2	7381.0	7405.8	7430.6	7455.5	7381.0	7306.5	7227.1	7152.7	6879.7
55°	7857.5	8001.5	8006.4	8011.4	8011.4	8016.4	7912.1	7807.9	7698.7	7594.4	7311.5
57.5°	8334.0	8473.0	8458.1	8448.2	8433.3	8418.4	8294.3	8170.2	8046.1	7922.0	7639.1
60°	8512.7	8631.9	8602.1	8572.3	8537.5	8507.8	8413.4	8319.1	8219.9	8125.6	7852.6
62.5°	8428.3	8517.7	8473.0	8433.3	8388.6	8344.0	8224.8	8100.7	7981.6	7857.5	7659.0
65°	7872.4	7927.0	7867.4	7812.8	7758.2	7698.7	7599.4	7500.1	7395.9	7296.6	7162.6
67.5°	6934.3	6944.2	6939.2	6934.3	6929.3	6924.3	6780.4	6636.4	6487.5	6343.6	6333.7
70°	5648.7	5589.1	5599.0	5613.9	5623.9	5633.8	5524.6	5420.3	5311.1	5201.9	5251.6
72.5°	4358.1	4253.9	4278.7	4308.5	4333.3	4358.1	4268.8	4184.4	4095.0	4005.7	4075.2
75°	3236.3	3171.8	3196.6	3226.4	3251.2	3276.0	3241.3	3206.5	3166.8	3132.1	3196.6
77.5°	2467.0	2427.2	2432.2	2432.2	2437.2	2437.2	2442.1	2452.1	2457.0	2462.0	2531.5
80°	2010.3	2005.3	2000.4	1995.4	1985.5	1980.5	2030.1	2079.8	2129.4	2179.1	2213.8
82.5°	1757.1	1806.8	1777.0	1752.2	1722.4	1692.6	1737.3	1782.0	1826.6	1871.3	1856.4
85°	1429.5	1489.1	1434.5	1379.9	1320.3	1265.7	1305.4	1340.2	1379.9	1414.7	1394.8
87.5°	565.9	580.8	491.4	407.0	317.7	228.3	362.3	491.4	625.4	754.5	774.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675985
 CATALOG NUMBER: CCW-SA-2E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675985

CATALOG NUMBER: CCW-SA-2E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9	3573.9
2.5°	3856.8	3836.9	3822.0	3817.1	3807.1	3802.2	3792.3	3782.3	3767.4	3757.5	3742.6
5°	3985.8	3956.1	3921.3	3871.7	3827.0	3777.4	3727.7	3683.1	3638.4	3588.7	3544.1
7.5°	3990.8	3921.3	3851.8	3787.3	3717.8	3653.3	3583.8	3524.2	3459.7	3395.2	3335.6
10°	3936.2	3851.8	3767.4	3683.1	3603.6	3519.3	3434.9	3365.4	3290.9	3216.5	3147.0
12.5°	3891.5	3797.2	3702.9	3603.6	3509.3	3410.1	3310.8	3241.3	3171.8	3102.3	3032.8
15°	3836.9	3777.4	3722.8	3633.4	3544.1	3454.7	3365.4	3271.1	3181.7	3087.4	2993.1
17.5°	3792.3	3777.4	3762.5	3702.9	3643.3	3578.8	3519.3	3424.9	3330.6	3231.4	3137.0
20°	3767.4	3787.3	3807.1	3777.4	3747.6	3712.8	3683.1	3613.6	3544.1	3469.6	3400.1
22.5°	3797.2	3871.7	3941.2	3946.1	3956.1	3961.0	3966.0	3901.5	3836.9	3767.4	3702.9
25°	3866.7	3985.8	4105.0	4169.5	4234.0	4303.5	4368.0	4328.3	4288.6	4248.9	4209.2
27.5°	3961.0	4109.9	4258.8	4353.2	4442.5	4536.8	4631.1	4626.2	4621.2	4611.3	4606.3
30°	3946.1	4060.3	4174.5	4288.6	4402.8	4517.0	4631.1	4690.7	4745.3	4804.8	4864.4
32.5°	4030.5	4124.8	4224.1	4343.2	4462.4	4586.4	4705.6	4829.7	4948.8	5072.9	5197.0
35°	4159.6	4244.0	4333.3	4462.4	4596.4	4725.4	4859.4	5008.4	5162.2	5316.1	5465.0
37.5°	4353.2	4427.6	4507.0	4616.2	4730.4	4839.6	4953.8	5172.2	5390.6	5613.9	5832.3
40°	4576.5	4626.2	4675.8	4780.0	4884.3	4988.5	5092.7	5365.7	5638.7	5911.8	6184.8
42.5°	4899.2	4884.3	4869.4	4953.8	5043.1	5127.5	5216.8	5465.0	5713.2	5961.4	6209.6
45°	5241.7	5182.1	5122.5	5162.2	5206.9	5246.6	5291.3	5544.4	5797.6	6055.7	6308.8
47.5°	5653.6	5504.7	5355.8	5321.1	5286.3	5246.6	5211.9	5484.9	5757.9	6035.8	6308.8
50°	6120.2	5896.9	5678.5	5589.1	5494.8	5405.5	5311.1	5534.5	5762.8	5991.2	6214.5
52.5°	6606.7	6328.7	6055.7	5916.7	5777.7	5633.8	5494.8	5683.4	5877.0	6070.6	6259.2
55°	7023.6	6740.7	6452.8	6289.0	6125.2	5961.4	5797.6	5986.2	6174.8	6363.4	6552.1
57.5°	7356.2	7073.3	6790.3	6636.4	6477.6	6323.7	6164.9	6343.6	6527.2	6710.9	6889.6
60°	7584.5	7311.5	7038.5	6889.6	6740.7	6591.8	6442.9	6656.3	6869.7	7088.1	7301.6
62.5°	7465.4	7266.8	7068.3	7003.8	6939.2	6869.7	6805.2	7008.7	7207.3	7410.8	7614.3
65°	7028.6	6894.6	6760.5	6825.1	6894.6	6959.1	7028.6	7162.6	7296.6	7435.6	7569.6
67.5°	6318.8	6308.8	6294.0	6437.9	6581.8	6730.8	6874.7	6964.1	7048.4	7137.8	7227.1
70°	5301.2	5355.8	5405.5	5653.6	5901.8	6150.0	6398.2	6432.9	6467.7	6502.4	6537.2
72.5°	4149.6	4219.1	4293.6	4621.2	4943.8	5271.4	5599.0	5579.2	5559.3	5534.5	5514.7
75°	3266.1	3330.6	3400.1	3702.9	4005.7	4308.5	4611.3	4526.9	4447.5	4363.1	4278.7
77.5°	2605.9	2675.4	2749.9	3032.8	3315.7	3603.6	3886.6	3683.1	3479.5	3276.0	3072.5
80°	2243.6	2278.3	2308.1	2501.7	2690.3	2883.9	3077.5	2869.0	2655.6	2442.1	2233.7
82.5°	1841.5	1821.7	1806.8	1920.9	2035.1	2149.3	2263.4	2064.9	1866.3	1662.8	1464.3
85°	1374.9	1355.1	1335.2	1394.8	1454.4	1518.9	1578.5	1350.1	1121.8	888.5	660.2
87.5°	799.2	819.0	838.9	903.4	967.9	1037.4	1101.9	868.6	635.4	397.1	163.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675985
 CATALOG NUMBER: CCW-SA-2E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675985
CATALOG NUMBER: CCW-SA-2E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	3573.9	3573.9
2.5°	3712.8	3688.0
5°	3509.3	3474.6
7.5°	3286.0	3241.3
10°	3082.4	3022.9
12.5°	2953.4	2878.9
15°	2903.8	2814.4
17.5°	3052.7	2968.3
20°	3281.0	3166.8
22.5°	3559.0	3420.0
25°	4040.4	3871.7
27.5°	4432.6	4258.8
30°	4675.8	4487.2
32.5°	4943.8	4695.6
35°	5221.8	4983.5
37.5°	5559.3	5291.3
40°	5906.8	5628.8
42.5°	6025.9	5847.2
45°	6140.1	5971.3
47.5°	6164.9	6025.9
50°	6189.7	6169.9
52.5°	6259.2	6254.2
55°	6557.0	6562.0
57.5°	6924.3	6954.1
60°	7261.9	7227.1
62.5°	7435.6	7256.9
65°	7316.5	7068.3
67.5°	6959.1	6691.0
70°	6174.8	5812.5
72.5°	5197.0	4879.3
75°	4005.7	3737.7
77.5°	2849.2	2625.8
80°	2005.3	1782.0
82.5°	1285.6	1106.9
85°	580.8	506.3
87.5°	163.8	158.8
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P675985
CATALOG NUMBER: CCW-SA-2E-735-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)