

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P675989

Luminaire Tested: **CCW-SA-1D-740-U-SLR**

Issue Date: 04/25/2023



Test Information

Test Method: LM-79-08
Report Number: P675989
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-1D-740-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @800mA w/
SLR distribution lens
Light Source: (16) 4000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4628.1 lumens
Efficiency: N/A
Efficacy: 105.2 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2

Input Watts (W): 44
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P675989
 CATALOG NUMBER: CCW-SA-1D-740-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 6.6 fc
 Type IV - Short - N/A

REPORT NUMBER: P675989
CATALOG NUMBER: CCW-SA-1D-740-U-SLR

Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P675989
 CATALOG NUMBER: CCW-SA-1D-740-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	952.3	0.0	952.3
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	3675.8	0.0	3675.8
	% Fixture	79.4	0.0	79.4
Total	Lumens	4628.1	0.0	4628.1
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.8	2.5
10°-20°	242.5	5.2
20°-30°	354.7	7.7
30°-40°	499.8	10.8
40°-50°	686.7	14.8
50°-60°	936.0	20.2
60°-70°	1024.5	22.1
70°-80°	591.6	12.8
80°-90°	177.3	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4628.1	100.0
0°-180°	4628.1	100.0




REPORT NUMBER: P675989
 CATALOG NUMBER: CCW-SA-1D-740-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	475.3	10.3			
FM (30°-60°)	1688.9	36.5			
FH (60°-80°)	1360.9	29.4			G1/1800
FVH (80°-90°)	150.6	3.3			G2/225
BL (0°-30°)	236.7	5.1	B1/500		
BM (30°-60°)	433.6	9.4	B1/1000		
BH (60°-80°)	255.2	5.5	B1/500		G1/500
BVH (80°-90°)	26.7	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P675989

CATALOG NUMBER: CCW-SA-1D-740-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9
2.5°	1525.1	1516.9	1510.8	1504.6	1496.4	1490.2	1482.0	1473.8	1463.6	1455.4	1445.1
5°	1436.9	1412.2	1387.6	1373.2	1356.8	1342.5	1326.0	1307.6	1289.1	1268.6	1250.1
7.5°	1340.4	1309.6	1278.8	1254.2	1227.5	1202.9	1176.2	1153.6	1131.0	1108.4	1085.9
10°	1250.1	1221.3	1192.6	1161.8	1129.0	1098.2	1065.3	1034.6	1003.8	973.0	942.2
12.5°	1190.6	1155.7	1122.8	1087.9	1055.1	1020.2	985.3	956.6	927.8	897.0	868.3
15°	1163.9	1131.0	1100.2	1065.3	1030.4	995.6	960.7	927.8	897.0	864.2	831.3
17.5°	1227.5	1180.3	1133.1	1087.9	1042.8	997.6	952.4	911.4	870.3	829.3	788.2
20°	1309.6	1250.1	1192.6	1137.2	1079.7	1024.3	966.8	909.3	851.9	794.4	736.9
22.5°	1414.3	1346.6	1280.9	1209.0	1135.1	1063.3	989.4	917.5	845.7	771.8	700.0
25°	1601.1	1521.0	1441.0	1338.3	1233.7	1131.0	1026.3	931.9	839.5	745.1	650.7
27.5°	1761.2	1652.4	1545.7	1422.5	1299.3	1176.2	1053.0	944.2	837.5	728.7	619.9
30°	1855.6	1748.9	1642.1	1492.3	1344.5	1194.7	1044.8	923.7	804.7	683.5	562.4
32.5°	1941.8	1822.8	1703.7	1539.5	1373.2	1209.0	1042.8	909.3	778.0	644.5	511.1
35°	2060.9	1929.5	1800.2	1609.3	1418.4	1227.5	1036.6	899.1	759.5	622.0	482.4
37.5°	2188.2	2026.0	1865.9	1654.5	1443.0	1231.6	1020.2	884.7	749.2	613.8	478.3
40°	2327.7	2130.7	1935.7	1701.7	1469.7	1235.7	1001.7	866.2	730.8	593.2	457.7
42.5°	2418.1	2204.6	1991.1	1738.6	1488.2	1235.7	983.2	849.8	716.4	580.9	447.5
45°	2469.4	2262.1	2056.8	1783.8	1510.8	1237.8	964.8	833.4	702.0	568.6	437.2
47.5°	2492.0	2299.0	2106.1	1818.7	1533.4	1246.0	958.6	825.2	689.7	556.3	420.8
50°	2551.5	2381.1	2210.7	1902.8	1597.0	1289.1	981.2	837.5	695.9	552.2	408.5
52.5°	2586.4	2440.6	2294.9	1978.8	1662.7	1346.6	1030.4	870.3	710.2	550.1	390.0
55°	2713.6	2574.1	2434.5	2097.8	1759.1	1422.5	1083.8	907.3	730.8	552.2	375.6
57.5°	2875.8	2728.0	2582.3	2219.0	1855.6	1492.3	1129.0	940.1	749.2	560.4	369.5
60°	2988.7	2845.0	2703.4	2317.5	1929.5	1543.6	1155.7	958.6	761.5	562.4	365.4
62.5°	3001.0	2816.3	2633.6	2258.0	1882.3	1504.6	1129.0	938.1	747.2	554.2	363.3
65°	2923.0	2707.5	2492.0	2132.7	1773.5	1414.3	1055.1	880.6	706.1	529.6	355.1
67.5°	2767.0	2514.5	2262.1	1933.6	1605.2	1276.8	948.3	798.5	650.7	500.9	351.0
70°	2403.7	2182.0	1962.4	1677.0	1393.8	1108.4	823.1	700.0	578.9	455.7	332.5
72.5°	2017.8	1810.5	1605.2	1373.2	1143.3	911.4	679.4	587.1	494.7	400.3	307.9
75°	1545.7	1389.7	1235.7	1063.3	890.9	716.4	544.0	476.2	408.5	340.7	273.0
77.5°	1085.9	1001.7	919.6	790.3	661.0	531.6	402.3	357.2	312.0	266.8	221.7
80°	736.9	689.7	644.5	552.2	459.8	365.4	273.0	244.3	213.5	184.7	154.0
82.5°	457.7	455.7	451.6	388.0	324.3	260.7	197.1	172.4	149.8	125.2	100.6
85°	209.4	244.3	277.1	242.2	207.3	172.4	137.5	121.1	104.7	86.2	69.8
87.5°	65.7	80.1	92.4	88.3	82.1	78.0	71.8	61.6	51.3	41.1	30.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675989
 CATALOG NUMBER: CCW-SA-1D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675989

CATALOG NUMBER: CCW-SA-1D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9
2.5°	1436.9	1430.7	1422.5	1414.3	1404.0	1395.8	1385.6	1375.3	1373.2	1369.1	1367.1
5°	1237.8	1225.5	1211.1	1198.8	1186.5	1172.1	1159.8	1145.4	1135.1	1122.8	1112.6
7.5°	1063.3	1042.8	1020.2	997.6	977.1	956.6	934.0	913.4	903.2	892.9	882.7
10°	923.7	903.2	884.7	864.2	849.8	837.5	823.1	808.8	796.4	784.1	771.8
12.5°	853.9	839.5	825.2	810.8	794.4	780.0	763.6	747.2	732.8	720.5	706.1
15°	810.8	790.3	767.7	747.2	724.6	704.1	681.5	658.9	642.5	628.1	611.7
17.5°	759.5	728.7	700.0	669.2	644.5	619.9	593.2	568.6	550.1	529.6	511.1
20°	702.0	667.1	630.2	595.3	566.5	539.9	511.1	482.4	461.9	439.3	418.7
22.5°	652.8	607.6	560.4	513.2	482.4	451.6	418.7	388.0	369.5	349.0	330.5
25°	599.4	550.1	498.8	447.5	416.7	383.9	353.1	320.2	305.8	293.5	279.2
27.5°	570.6	521.4	470.1	420.8	392.1	361.3	332.5	301.7	291.5	279.2	268.9
30°	513.2	466.0	416.7	367.4	346.9	328.4	307.9	287.4	283.3	281.2	277.1
32.5°	461.9	412.6	363.3	314.1	295.6	277.1	258.6	240.2	238.1	234.0	232.0
35°	435.2	388.0	338.7	291.5	275.1	256.6	240.2	221.7	217.6	211.4	207.3
37.5°	429.0	379.7	328.4	279.2	262.7	246.3	227.8	211.4	207.3	203.2	199.1
40°	412.6	365.4	320.2	273.0	256.6	240.2	221.7	205.3	201.2	197.1	193.0
42.5°	400.3	355.1	307.9	260.7	246.3	232.0	215.5	201.2	197.1	193.0	186.8
45°	390.0	342.8	293.5	246.3	236.1	225.8	213.5	203.2	199.1	193.0	188.8
47.5°	373.6	328.4	281.2	234.0	223.7	215.5	205.3	195.0	190.9	186.8	182.7
50°	361.3	314.1	266.8	219.6	211.4	203.2	195.0	186.8	186.8	188.8	188.8
52.5°	344.9	299.7	254.5	209.4	201.2	193.0	184.7	176.5	178.6	180.6	182.7
55°	330.5	287.4	242.2	197.1	188.8	180.6	170.4	162.2	164.2	166.3	168.3
57.5°	324.3	279.2	234.0	188.8	180.6	170.4	162.2	151.9	151.9	151.9	151.9
60°	320.2	273.0	227.8	180.6	170.4	162.2	151.9	141.6	139.6	139.6	137.5
62.5°	318.2	271.0	225.8	178.6	166.3	156.0	143.7	131.4	129.3	127.3	125.2
65°	310.0	266.8	221.7	176.5	162.2	149.8	135.5	121.1	119.1	119.1	117.0
67.5°	307.9	262.7	219.6	174.5	160.1	143.7	129.3	112.9	110.8	108.8	106.7
70°	291.5	252.5	211.4	170.4	154.0	139.6	123.2	106.7	104.7	100.6	98.5
72.5°	271.0	236.1	199.1	162.2	145.7	129.3	112.9	96.5	94.4	92.4	88.3
75°	240.2	207.3	174.5	141.6	127.3	115.0	100.6	86.2	84.2	82.1	78.0
77.5°	197.1	170.4	145.7	119.1	108.8	98.5	88.3	78.0	75.9	73.9	69.8
80°	139.6	123.2	108.8	92.4	86.2	78.0	71.8	63.6	63.6	61.6	61.6
82.5°	92.4	84.2	75.9	67.7	63.6	59.5	55.4	51.3	51.3	49.3	49.3
85°	65.7	61.6	55.4	51.3	49.3	45.2	43.1	39.0	39.0	39.0	39.0
87.5°	30.8	30.8	28.7	28.7	26.7	26.7	24.6	22.6	22.6	22.6	22.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675989
 CATALOG NUMBER: CCW-SA-1D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675989

CATALOG NUMBER: CCW-SA-1D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9
2.5°	1363.0	1356.8	1350.7	1342.5	1336.3	1328.1	1317.8	1309.6	1299.3	1299.3	1297.3
5°	1100.2	1094.1	1087.9	1079.7	1073.6	1065.3	1059.2	1051.0	1042.8	1042.8	1040.7
7.5°	872.4	860.1	847.8	833.4	821.1	812.9	804.7	794.4	786.2	780.0	773.9
10°	759.5	747.2	732.8	720.5	706.1	695.9	685.6	673.3	663.0	654.8	646.6
12.5°	691.8	677.4	663.0	648.6	634.3	619.9	607.6	593.2	578.9	568.6	558.3
15°	595.3	580.9	566.5	552.2	537.8	521.4	505.0	486.5	470.1	461.9	455.7
17.5°	490.6	476.2	459.8	445.4	429.0	416.7	404.4	392.1	379.7	371.5	365.4
20°	396.2	379.7	363.3	346.9	330.5	322.3	314.1	305.8	297.6	291.5	287.4
22.5°	310.0	299.7	291.5	281.2	271.0	264.8	260.7	254.5	248.4	248.4	248.4
25°	264.8	258.6	254.5	248.4	242.2	240.2	238.1	234.0	232.0	229.9	229.9
27.5°	256.6	250.4	244.3	238.1	232.0	229.9	227.8	223.7	221.7	221.7	221.7
30°	273.0	271.0	268.9	266.8	264.8	260.7	254.5	250.4	244.3	240.2	236.1
32.5°	227.8	225.8	225.8	223.7	221.7	225.8	227.8	232.0	234.0	236.1	238.1
35°	201.2	197.1	193.0	188.8	184.7	182.7	180.6	178.6	176.5	176.5	174.5
37.5°	195.0	190.9	186.8	182.7	178.6	176.5	174.5	172.4	170.4	170.4	168.3
40°	188.8	184.7	182.7	178.6	174.5	172.4	170.4	166.3	164.2	162.2	162.2
42.5°	182.7	180.6	176.5	174.5	170.4	168.3	166.3	162.2	160.1	158.1	156.0
45°	182.7	178.6	174.5	170.4	166.3	164.2	160.1	158.1	154.0	154.0	151.9
47.5°	178.6	174.5	170.4	166.3	162.2	160.1	156.0	154.0	149.8	147.8	145.7
50°	188.8	182.7	174.5	168.3	160.1	158.1	154.0	151.9	147.8	145.7	143.7
52.5°	184.7	178.6	170.4	164.2	156.0	151.9	149.8	145.7	141.6	139.6	137.5
55°	170.4	164.2	160.1	154.0	147.8	143.7	139.6	135.5	131.4	129.3	129.3
57.5°	151.9	149.8	147.8	145.7	143.7	139.6	135.5	129.3	125.2	123.2	121.1
60°	135.5	137.5	139.6	141.6	143.7	137.5	131.4	125.2	119.1	117.0	115.0
62.5°	123.2	127.3	131.4	133.4	137.5	131.4	125.2	119.1	112.9	110.8	108.8
65°	115.0	117.0	117.0	119.1	119.1	115.0	112.9	108.8	104.7	102.6	102.6
67.5°	104.7	104.7	104.7	102.6	102.6	100.6	100.6	98.5	96.5	94.4	94.4
70°	94.4	94.4	94.4	92.4	92.4	90.3	90.3	88.3	86.2	86.2	84.2
72.5°	86.2	86.2	84.2	84.2	82.1	82.1	82.1	80.1	80.1	78.0	78.0
75°	75.9	75.9	73.9	73.9	71.8	71.8	71.8	69.8	69.8	69.8	67.7
77.5°	67.7	67.7	65.7	65.7	63.6	63.6	63.6	61.6	61.6	59.5	59.5
80°	59.5	59.5	57.5	57.5	55.4	55.4	53.4	53.4	51.3	51.3	49.3
82.5°	47.2	47.2	47.2	47.2	47.2	45.2	45.2	43.1	41.1	41.1	39.0
85°	39.0	39.0	39.0	36.9	36.9	36.9	34.9	34.9	32.8	30.8	30.8
87.5°	22.6	22.6	22.6	20.5	20.5	20.5	20.5	20.5	20.5	20.5	18.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675989
 CATALOG NUMBER: CCW-SA-1D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675989
 CATALOG NUMBER: CCW-SA-1D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9
2.5°	1297.3	1295.2	1287.0	1278.8	1287.0	1295.2	1295.2	1295.2	1293.2	1293.2	1293.2
5°	1040.7	1038.7	1034.6	1030.4	1030.4	1028.4	1032.5	1036.6	1040.7	1044.8	1048.9
7.5°	765.7	759.5	753.3	747.2	751.3	753.3	759.5	763.6	769.8	773.9	784.1
10°	638.4	630.2	624.0	617.9	613.8	609.6	605.5	603.5	599.4	595.3	599.4
12.5°	546.0	535.8	525.5	513.2	511.1	509.1	505.0	500.9	496.7	492.6	490.6
15°	447.5	439.3	435.2	429.0	420.8	412.6	408.5	406.4	402.3	398.2	396.2
17.5°	357.2	349.0	342.8	336.6	334.6	330.5	330.5	330.5	330.5	330.5	330.5
20°	281.2	275.1	275.1	273.0	273.0	271.0	273.0	275.1	275.1	277.1	279.2
22.5°	246.3	246.3	244.3	242.2	244.3	244.3	246.3	248.4	250.4	252.5	254.5
25°	227.8	225.8	227.8	229.9	229.9	229.9	232.0	232.0	234.0	234.0	234.0
27.5°	219.6	219.6	221.7	221.7	223.7	223.7	223.7	221.7	221.7	219.6	219.6
30°	232.0	227.8	227.8	227.8	225.8	223.7	221.7	221.7	219.6	217.6	215.5
32.5°	240.2	242.2	240.2	236.1	234.0	229.9	227.8	223.7	221.7	217.6	213.5
35°	174.5	172.4	176.5	178.6	180.6	182.7	184.7	186.8	186.8	188.8	188.8
37.5°	168.3	166.3	166.3	164.2	164.2	164.2	164.2	164.2	162.2	162.2	164.2
40°	160.1	158.1	158.1	156.0	156.0	154.0	154.0	154.0	154.0	154.0	154.0
42.5°	154.0	151.9	151.9	151.9	151.9	149.8	149.8	147.8	147.8	145.7	145.7
45°	151.9	149.8	147.8	145.7	145.7	143.7	143.7	143.7	141.6	141.6	141.6
47.5°	143.7	141.6	141.6	139.6	139.6	137.5	137.5	137.5	135.5	135.5	135.5
50°	139.6	137.5	137.5	135.5	135.5	133.4	133.4	133.4	131.4	131.4	131.4
52.5°	133.4	131.4	131.4	131.4	129.3	127.3	127.3	127.3	125.2	125.2	125.2
55°	127.3	125.2	125.2	125.2	123.2	121.1	121.1	121.1	119.1	119.1	119.1
57.5°	119.1	117.0	117.0	115.0	115.0	115.0	115.0	115.0	112.9	112.9	112.9
60°	112.9	110.8	110.8	108.8	108.8	106.7	106.7	106.7	106.7	106.7	106.7
62.5°	106.7	104.7	102.6	100.6	102.6	102.6	102.6	102.6	100.6	100.6	100.6
65°	100.6	98.5	96.5	94.4	94.4	94.4	94.4	94.4	94.4	94.4	94.4
67.5°	92.4	90.3	88.3	86.2	88.3	88.3	88.3	88.3	88.3	88.3	88.3
70°	84.2	82.1	82.1	80.1	80.1	78.0	78.0	80.1	80.1	80.1	80.1
72.5°	75.9	73.9	73.9	71.8	71.8	71.8	71.8	71.8	71.8	71.8	71.8
75°	67.7	65.7	65.7	63.6	63.6	63.6	63.6	63.6	63.6	63.6	63.6
77.5°	57.5	55.4	55.4	55.4	55.4	55.4	55.4	57.5	57.5	57.5	57.5
80°	49.3	47.2	47.2	47.2	47.2	47.2	47.2	47.2	47.2	47.2	47.2
82.5°	39.0	36.9	36.9	36.9	36.9	36.9	36.9	36.9	36.9	36.9	36.9
85°	28.7	26.7	26.7	26.7	28.7	28.7	28.7	28.7	28.7	28.7	28.7
87.5°	18.5	16.4	16.4	16.4	18.5	18.5	18.5	18.5	16.4	16.4	16.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675989
 CATALOG NUMBER: CCW-SA-1D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675989

CATALOG NUMBER: CCW-SA-1D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9
2.5°	1293.2	1293.2	1293.2	1291.1	1289.1	1287.0	1285.0	1291.1	1295.2	1301.4	1305.5
5°	1051.0	1055.1	1057.1	1063.3	1069.4	1075.6	1081.8	1085.9	1090.0	1092.0	1096.1
7.5°	792.3	802.6	810.8	819.0	827.2	833.4	841.6	847.8	853.9	860.1	866.2
10°	601.4	605.5	607.6	615.8	622.0	630.2	636.3	642.5	648.6	652.8	658.9
12.5°	488.5	484.4	482.4	482.4	482.4	482.4	482.4	486.5	490.6	494.7	498.8
15°	394.1	392.1	390.0	388.0	385.9	381.8	379.7	383.9	388.0	392.1	396.2
17.5°	330.5	330.5	330.5	328.4	326.4	324.3	322.3	324.3	326.4	326.4	328.4
20°	283.3	285.3	287.4	289.4	289.4	291.5	291.5	293.5	295.6	295.6	297.6
22.5°	254.5	256.6	256.6	256.6	258.6	258.6	258.6	260.7	262.7	264.8	266.8
25°	232.0	232.0	229.9	229.9	232.0	232.0	232.0	232.0	234.0	234.0	234.0
27.5°	219.6	217.6	217.6	217.6	217.6	215.5	215.5	215.5	215.5	215.5	215.5
30°	213.5	211.4	209.4	207.3	207.3	205.3	203.2	203.2	203.2	203.2	203.2
32.5°	211.4	207.3	203.2	201.2	201.2	199.1	197.1	195.0	195.0	193.0	190.9
35°	188.8	186.8	186.8	184.7	182.7	180.6	178.6	178.6	178.6	176.5	176.5
37.5°	164.2	166.3	166.3	166.3	168.3	168.3	168.3	168.3	170.4	170.4	170.4
40°	154.0	154.0	154.0	156.0	158.1	158.1	160.1	160.1	162.2	162.2	162.2
42.5°	145.7	143.7	143.7	145.7	145.7	147.8	147.8	149.8	151.9	151.9	154.0
45°	141.6	139.6	139.6	139.6	139.6	137.5	137.5	139.6	141.6	143.7	145.7
47.5°	133.4	133.4	131.4	131.4	131.4	131.4	131.4	131.4	133.4	133.4	133.4
50°	129.3	129.3	127.3	127.3	127.3	127.3	127.3	127.3	127.3	127.3	127.3
52.5°	125.2	123.2	123.2	123.2	123.2	121.1	121.1	121.1	121.1	121.1	121.1
55°	119.1	117.0	117.0	117.0	117.0	117.0	117.0	117.0	119.1	119.1	119.1
57.5°	112.9	110.8	110.8	110.8	112.9	112.9	112.9	112.9	115.0	115.0	115.0
60°	106.7	106.7	106.7	106.7	106.7	106.7	106.7	108.8	108.8	110.8	110.8
62.5°	100.6	100.6	100.6	100.6	102.6	102.6	102.6	102.6	104.7	104.7	104.7
65°	94.4	94.4	94.4	94.4	96.5	96.5	96.5	96.5	96.5	96.5	96.5
67.5°	88.3	88.3	88.3	88.3	88.3	88.3	88.3	90.3	90.3	92.4	92.4
70°	80.1	78.0	78.0	80.1	80.1	82.1	82.1	84.2	84.2	86.2	86.2
72.5°	71.8	71.8	71.8	71.8	71.8	71.8	71.8	73.9	75.9	75.9	78.0
75°	63.6	63.6	63.6	63.6	65.7	65.7	65.7	67.7	67.7	69.8	69.8
77.5°	57.5	55.4	55.4	55.4	57.5	57.5	57.5	59.5	59.5	61.6	61.6
80°	47.2	47.2	47.2	47.2	49.3	49.3	49.3	49.3	51.3	51.3	51.3
82.5°	39.0	39.0	39.0	39.0	39.0	39.0	39.0	39.0	41.1	41.1	41.1
85°	28.7	28.7	28.7	28.7	30.8	30.8	30.8	30.8	30.8	30.8	30.8
87.5°	18.5	18.5	18.5	18.5	18.5	18.5	18.5	18.5	20.5	20.5	20.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675989
 CATALOG NUMBER: CCW-SA-1D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675989
 CATALOG NUMBER: CCW-SA-1D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9
2.5°	1305.5	1305.5	1305.5	1305.5	1309.6	1311.7	1315.8	1317.8	1315.8	1313.7	1309.6
5°	1098.2	1100.2	1100.2	1102.3	1102.3	1102.3	1102.3	1102.3	1106.4	1110.5	1114.6
7.5°	868.3	870.3	872.4	874.4	874.4	874.4	872.4	872.4	874.4	874.4	876.5
10°	665.1	673.3	679.4	685.6	681.5	675.3	671.2	665.1	665.1	665.1	663.0
12.5°	502.9	505.0	509.1	511.1	509.1	509.1	507.0	505.0	507.0	511.1	513.2
15°	398.2	398.2	400.3	400.3	402.3	404.4	404.4	406.4	410.5	412.6	416.7
17.5°	330.5	332.5	332.5	334.6	334.6	336.6	336.6	336.6	340.7	344.9	351.0
20°	297.6	297.6	297.6	297.6	297.6	295.6	295.6	293.5	295.6	299.7	301.7
22.5°	266.8	268.9	268.9	268.9	266.8	264.8	260.7	258.6	258.6	260.7	260.7
25°	234.0	232.0	232.0	229.9	229.9	232.0	232.0	232.0	234.0	234.0	236.1
27.5°	215.5	213.5	213.5	211.4	211.4	213.5	213.5	213.5	213.5	213.5	213.5
30°	201.2	201.2	199.1	197.1	199.1	199.1	201.2	201.2	203.2	203.2	205.3
32.5°	190.9	188.8	188.8	186.8	188.8	188.8	190.9	190.9	193.0	195.0	195.0
35°	176.5	176.5	176.5	176.5	176.5	176.5	174.5	174.5	174.5	174.5	174.5
37.5°	168.3	168.3	166.3	164.2	164.2	164.2	164.2	164.2	162.2	160.1	158.1
40°	162.2	160.1	160.1	158.1	156.0	156.0	154.0	151.9	151.9	149.8	149.8
42.5°	154.0	151.9	151.9	149.8	147.8	147.8	145.7	143.7	143.7	143.7	141.6
45°	143.7	143.7	141.6	139.6	139.6	139.6	137.5	137.5	137.5	137.5	135.5
47.5°	133.4	133.4	131.4	131.4	131.4	131.4	129.3	129.3	129.3	129.3	129.3
50°	127.3	127.3	127.3	127.3	127.3	127.3	125.2	125.2	125.2	125.2	125.2
52.5°	121.1	121.1	121.1	121.1	121.1	121.1	121.1	121.1	121.1	121.1	121.1
55°	119.1	119.1	119.1	119.1	119.1	119.1	117.0	117.0	117.0	119.1	119.1
57.5°	115.0	115.0	112.9	112.9	112.9	112.9	112.9	112.9	112.9	112.9	112.9
60°	110.8	110.8	110.8	110.8	110.8	110.8	110.8	110.8	110.8	110.8	110.8
62.5°	104.7	104.7	104.7	104.7	104.7	106.7	106.7	106.7	106.7	106.7	104.7
65°	96.5	98.5	98.5	98.5	98.5	98.5	98.5	98.5	98.5	98.5	98.5
67.5°	92.4	92.4	92.4	92.4	92.4	92.4	92.4	92.4	92.4	92.4	92.4
70°	86.2	86.2	84.2	84.2	84.2	86.2	86.2	86.2	86.2	86.2	86.2
72.5°	78.0	78.0	78.0	78.0	78.0	78.0	78.0	78.0	78.0	80.1	80.1
75°	69.8	69.8	69.8	69.8	69.8	69.8	69.8	69.8	69.8	69.8	69.8
77.5°	61.6	61.6	59.5	59.5	59.5	61.6	61.6	61.6	61.6	63.6	63.6
80°	51.3	51.3	51.3	51.3	51.3	51.3	51.3	51.3	51.3	53.4	53.4
82.5°	41.1	41.1	41.1	41.1	41.1	41.1	41.1	41.1	41.1	43.1	43.1
85°	30.8	32.8	32.8	32.8	32.8	32.8	32.8	32.8	32.8	34.9	34.9
87.5°	20.5	20.5	20.5	20.5	20.5	20.5	18.5	18.5	18.5	18.5	16.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675989
 CATALOG NUMBER: CCW-SA-1D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675989
 CATALOG NUMBER: CCW-SA-1D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9
2.5°	1307.6	1309.6	1311.7	1311.7	1313.7	1315.8	1315.8	1324.0	1332.2	1336.3	1340.4
5°	1118.7	1116.7	1116.7	1114.6	1112.6	1118.7	1124.9	1137.2	1149.5	1151.6	1155.7
7.5°	876.5	878.5	880.6	880.6	882.7	876.5	868.3	870.3	872.4	882.7	890.9
10°	663.0	665.1	667.1	667.1	669.2	667.1	663.0	669.2	675.3	683.5	693.8
12.5°	515.2	521.4	527.5	531.6	537.8	541.9	544.0	552.2	558.3	568.6	578.9
15°	420.8	424.9	429.0	433.1	437.2	441.3	445.4	453.6	461.9	474.2	486.5
17.5°	355.1	355.1	357.2	357.2	357.2	361.3	365.4	369.5	371.5	383.9	396.2
20°	303.8	301.7	299.7	297.6	295.6	299.7	301.7	303.8	305.8	314.1	320.2
22.5°	260.7	260.7	262.7	262.7	262.7	260.7	256.6	258.6	258.6	262.7	268.9
25°	236.1	236.1	236.1	234.0	234.0	236.1	238.1	238.1	236.1	238.1	240.2
27.5°	213.5	215.5	215.5	217.6	217.6	219.6	219.6	219.6	219.6	221.7	223.7
30°	205.3	205.3	207.3	207.3	207.3	209.4	211.4	211.4	211.4	213.5	217.6
32.5°	197.1	199.1	201.2	203.2	205.3	207.3	207.3	209.4	209.4	211.4	213.5
35°	174.5	172.4	172.4	170.4	168.3	168.3	168.3	168.3	166.3	168.3	168.3
37.5°	156.0	156.0	156.0	154.0	154.0	156.0	156.0	156.0	156.0	158.1	158.1
40°	147.8	147.8	147.8	147.8	147.8	147.8	147.8	149.8	149.8	151.9	154.0
42.5°	141.6	141.6	141.6	141.6	141.6	143.7	143.7	143.7	143.7	145.7	145.7
45°	135.5	135.5	135.5	135.5	135.5	135.5	135.5	137.5	137.5	139.6	141.6
47.5°	129.3	129.3	129.3	129.3	129.3	131.4	133.4	133.4	133.4	135.5	135.5
50°	125.2	125.2	125.2	125.2	125.2	127.3	127.3	129.3	129.3	131.4	133.4
52.5°	121.1	121.1	121.1	121.1	121.1	123.2	123.2	125.2	125.2	127.3	129.3
55°	119.1	119.1	119.1	117.0	117.0	119.1	119.1	121.1	121.1	123.2	123.2
57.5°	112.9	112.9	112.9	112.9	112.9	112.9	112.9	115.0	115.0	117.0	119.1
60°	110.8	110.8	108.8	108.8	106.7	108.8	108.8	110.8	110.8	112.9	112.9
62.5°	104.7	104.7	104.7	102.6	102.6	104.7	104.7	104.7	104.7	106.7	108.8
65°	98.5	98.5	98.5	96.5	96.5	98.5	98.5	98.5	98.5	100.6	102.6
67.5°	92.4	92.4	92.4	90.3	90.3	90.3	90.3	92.4	92.4	94.4	96.5
70°	86.2	86.2	86.2	84.2	84.2	84.2	82.1	84.2	86.2	88.3	88.3
72.5°	80.1	80.1	80.1	78.0	78.0	78.0	75.9	78.0	78.0	80.1	80.1
75°	69.8	69.8	69.8	69.8	69.8	69.8	67.7	67.7	67.7	69.8	69.8
77.5°	63.6	63.6	63.6	61.6	61.6	61.6	59.5	59.5	59.5	61.6	61.6
80°	53.4	53.4	53.4	51.3	51.3	51.3	49.3	49.3	49.3	51.3	51.3
82.5°	43.1	43.1	43.1	41.1	41.1	41.1	39.0	39.0	39.0	41.1	41.1
85°	34.9	34.9	34.9	34.9	34.9	34.9	32.8	32.8	32.8	34.9	36.9
87.5°	16.4	16.4	18.5	18.5	18.5	18.5	16.4	16.4	14.4	14.4	16.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675989
 CATALOG NUMBER: CCW-SA-1D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675989

CATALOG NUMBER: CCW-SA-1D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9
2.5°	1344.5	1348.6	1358.9	1367.1	1377.4	1385.6	1391.7	1399.9	1406.1	1412.2	1416.4
5°	1157.7	1159.8	1170.0	1180.3	1188.5	1198.8	1213.1	1227.5	1241.9	1256.2	1266.5
7.5°	901.1	909.3	921.7	936.0	948.3	960.7	975.0	991.4	1005.8	1020.2	1034.6
10°	702.0	710.2	722.5	734.9	745.1	757.4	773.9	790.3	806.7	823.1	839.5
12.5°	589.1	599.4	613.8	628.1	640.4	654.8	675.3	693.8	714.3	732.8	753.3
15°	496.7	509.1	527.5	548.1	566.5	585.0	605.5	626.1	644.5	665.1	685.6
17.5°	408.5	420.8	437.2	455.7	472.1	488.5	513.2	535.8	560.4	583.0	605.5
20°	328.4	334.6	351.0	367.4	383.9	400.3	418.7	437.2	455.7	474.2	502.9
22.5°	273.0	277.1	285.3	291.5	299.7	305.8	324.3	342.8	359.2	377.7	404.4
25°	240.2	242.2	248.4	252.5	258.6	262.7	275.1	285.3	297.6	307.9	332.5
27.5°	223.7	225.8	227.8	229.9	232.0	234.0	242.2	250.4	256.6	264.8	287.4
30°	219.6	221.7	227.8	232.0	238.1	242.2	246.3	250.4	254.5	258.6	273.0
32.5°	215.5	217.6	217.6	215.5	215.5	213.5	217.6	219.6	223.7	225.8	238.1
35°	170.4	170.4	172.4	174.5	176.5	178.6	184.7	188.8	195.0	199.1	209.4
37.5°	160.1	160.1	162.2	166.3	168.3	170.4	174.5	178.6	182.7	186.8	197.1
40°	154.0	156.0	158.1	160.1	162.2	164.2	168.3	170.4	174.5	176.5	184.7
42.5°	147.8	147.8	149.8	154.0	156.0	158.1	162.2	164.2	168.3	170.4	178.6
45°	143.7	145.7	147.8	149.8	149.8	151.9	156.0	160.1	162.2	166.3	174.5
47.5°	137.5	137.5	141.6	143.7	147.8	149.8	154.0	156.0	160.1	162.2	170.4
50°	133.4	135.5	139.6	141.6	145.7	147.8	154.0	158.1	164.2	168.3	172.4
52.5°	129.3	131.4	135.5	137.5	141.6	143.7	151.9	160.1	166.3	174.5	174.5
55°	125.2	125.2	129.3	135.5	139.6	143.7	147.8	154.0	158.1	162.2	162.2
57.5°	119.1	121.1	125.2	131.4	135.5	139.6	143.7	147.8	149.8	154.0	151.9
60°	115.0	115.0	121.1	127.3	133.4	139.6	139.6	139.6	137.5	137.5	137.5
62.5°	108.8	110.8	119.1	129.3	137.5	145.7	139.6	133.4	127.3	121.1	123.2
65°	104.7	106.7	110.8	117.0	121.1	125.2	121.1	119.1	115.0	110.8	112.9
67.5°	96.5	98.5	100.6	100.6	102.6	102.6	102.6	102.6	102.6	102.6	104.7
70°	90.3	90.3	90.3	92.4	92.4	92.4	92.4	92.4	92.4	92.4	94.4
72.5°	82.1	82.1	82.1	82.1	82.1	82.1	82.1	82.1	82.1	82.1	84.2
75°	71.8	71.8	71.8	71.8	71.8	71.8	71.8	71.8	71.8	71.8	73.9
77.5°	63.6	63.6	63.6	63.6	63.6	63.6	63.6	63.6	61.6	61.6	63.6
80°	53.4	53.4	53.4	53.4	51.3	51.3	51.3	51.3	51.3	51.3	53.4
82.5°	43.1	43.1	43.1	43.1	41.1	41.1	41.1	41.1	39.0	39.0	41.1
85°	39.0	41.1	41.1	43.1	43.1	43.1	41.1	39.0	36.9	34.9	34.9
87.5°	16.4	16.4	16.4	16.4	14.4	14.4	14.4	14.4	14.4	14.4	14.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675989
 CATALOG NUMBER: CCW-SA-1D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675989

CATALOG NUMBER: CCW-SA-1D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9
2.5°	1422.5	1426.6	1430.7	1436.9	1445.1	1451.2	1457.4	1469.7	1484.1	1496.4	1508.7
5°	1276.8	1287.0	1297.3	1309.6	1321.9	1332.2	1344.5	1369.1	1393.8	1416.4	1441.0
7.5°	1046.9	1061.2	1073.6	1094.1	1112.6	1133.1	1151.6	1182.3	1211.1	1241.9	1270.6
10°	856.0	872.4	888.8	915.5	944.2	970.9	997.6	1022.2	1048.9	1073.6	1098.2
12.5°	773.9	792.3	812.9	829.3	847.8	864.2	880.6	909.3	938.1	966.8	995.6
15°	706.1	726.6	747.2	767.7	786.2	806.7	825.2	849.8	876.5	901.1	925.8
17.5°	628.1	648.6	671.2	693.8	716.4	739.0	761.5	796.4	831.3	864.2	899.1
20°	529.6	558.3	585.0	615.8	646.6	677.4	708.2	745.1	782.1	817.0	853.9
22.5°	431.1	457.7	484.4	521.4	558.3	593.2	630.2	679.4	726.6	775.9	823.1
25°	359.2	383.9	408.5	449.5	488.5	529.6	568.6	628.1	685.6	745.1	802.6
27.5°	310.0	332.5	355.1	398.2	441.3	482.4	525.5	591.2	654.8	720.5	784.1
30°	287.4	301.7	316.1	357.2	398.2	437.2	478.3	541.9	605.5	669.2	732.8
32.5°	250.4	262.7	275.1	312.0	349.0	383.9	420.8	486.5	550.1	615.8	679.4
35°	221.7	232.0	242.2	277.1	310.0	344.9	377.7	443.4	509.1	574.8	640.4
37.5°	205.3	215.5	223.7	254.5	287.4	318.2	349.0	414.6	478.3	544.0	607.6
40°	193.0	199.1	207.3	238.1	266.8	297.6	326.4	385.9	447.5	507.0	566.5
42.5°	184.7	193.0	199.1	225.8	254.5	281.2	307.9	365.4	422.9	478.3	535.8
45°	182.7	190.9	199.1	221.7	244.3	264.8	287.4	342.8	398.2	453.6	509.1
47.5°	178.6	184.7	193.0	211.4	227.8	246.3	262.7	318.2	373.6	427.0	482.4
50°	176.5	178.6	182.7	199.1	215.5	232.0	248.4	303.8	359.2	414.6	470.1
52.5°	174.5	174.5	174.5	188.8	203.2	215.5	229.9	285.3	342.8	398.2	453.6
55°	162.2	160.1	160.1	174.5	186.8	201.2	213.5	268.9	324.3	377.7	433.1
57.5°	149.8	147.8	145.7	158.1	170.4	182.7	195.0	250.4	307.9	363.3	418.7
60°	137.5	135.5	135.5	147.8	158.1	170.4	180.6	238.1	293.5	351.0	406.4
62.5°	123.2	125.2	125.2	135.5	147.8	158.1	168.3	225.8	285.3	342.8	400.3
65°	112.9	115.0	115.0	127.3	139.6	151.9	164.2	219.6	277.1	332.5	388.0
67.5°	104.7	106.7	106.7	121.1	133.4	147.8	160.1	209.4	260.7	310.0	359.2
70°	96.5	96.5	98.5	112.9	127.3	141.6	156.0	199.1	242.2	283.3	326.4
72.5°	86.2	88.3	90.3	104.7	117.0	131.4	143.7	182.7	221.7	260.7	299.7
75°	75.9	78.0	80.1	92.4	104.7	117.0	129.3	166.3	201.2	238.1	273.0
77.5°	67.7	69.8	71.8	82.1	92.4	102.6	112.9	139.6	168.3	195.0	221.7
80°	55.4	55.4	57.5	65.7	73.9	80.1	88.3	106.7	125.2	141.6	160.1
82.5°	41.1	43.1	43.1	49.3	53.4	59.5	63.6	73.9	82.1	92.4	100.6
85°	34.9	32.8	32.8	36.9	39.0	43.1	45.2	51.3	55.4	61.6	65.7
87.5°	14.4	12.3	12.3	14.4	18.5	20.5	22.6	22.6	24.6	24.6	24.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675989
 CATALOG NUMBER: CCW-SA-1D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675989

CATALOG NUMBER: CCW-SA-1D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9
2.5°	1514.9	1519.0	1525.1	1529.2	1539.5	1547.7	1558.0	1566.2	1572.4	1582.6	1578.5
5°	1459.5	1477.9	1496.4	1514.9	1529.2	1543.6	1555.9	1570.3	1586.7	1617.5	1625.7
7.5°	1295.2	1319.9	1342.5	1367.1	1395.8	1424.6	1453.3	1482.0	1508.7	1547.7	1572.4
10°	1133.1	1168.0	1200.8	1235.7	1262.4	1289.1	1313.7	1340.4	1377.4	1416.4	1461.5
12.5°	1030.4	1065.3	1100.2	1135.1	1174.1	1211.1	1250.1	1287.0	1321.9	1352.7	1404.0
15°	962.7	1001.7	1038.7	1075.6	1122.8	1168.0	1215.2	1260.3	1311.7	1352.7	1387.6
17.5°	946.3	993.5	1038.7	1085.9	1135.1	1184.4	1233.7	1282.9	1334.2	1395.8	1441.0
20°	917.5	981.2	1044.8	1108.4	1172.1	1233.7	1297.3	1358.9	1426.6	1500.5	1521.0
22.5°	901.1	977.1	1055.1	1131.0	1217.2	1305.5	1391.7	1477.9	1549.8	1605.2	1666.8
25°	899.1	993.5	1090.0	1184.4	1293.2	1399.9	1508.7	1615.5	1707.8	1763.3	1812.5
27.5°	897.0	1012.0	1124.9	1237.8	1371.2	1502.6	1636.0	1767.4	1853.6	1933.6	1974.7
30°	872.4	1009.9	1149.5	1287.0	1436.9	1586.7	1736.6	1886.4	1974.7	2030.1	2050.6
32.5°	841.6	1003.8	1165.9	1328.1	1498.5	1668.8	1837.2	2007.5	2077.3	2124.5	2108.1
35°	817.0	995.6	1172.1	1348.6	1529.2	1711.9	1892.6	2073.2	2173.8	2239.5	2212.8
37.5°	794.4	981.2	1168.0	1354.8	1566.2	1777.6	1989.0	2200.5	2297.0	2366.7	2336.0
40°	767.7	966.8	1168.0	1367.1	1609.3	1849.5	2091.7	2331.8	2457.1	2516.6	2469.4
42.5°	745.1	952.4	1161.8	1369.1	1627.8	1886.4	2145.1	2403.7	2543.3	2627.4	2567.9
45°	716.4	923.7	1129.0	1336.3	1621.6	1906.9	2190.2	2475.5	2637.7	2703.4	2621.3
47.5°	685.6	890.9	1094.1	1297.3	1601.1	1904.9	2208.7	2512.5	2662.3	2740.3	2664.4
50°	675.3	880.6	1083.8	1289.1	1617.5	1948.0	2276.4	2604.9	2713.6	2777.3	2676.7
52.5°	673.3	890.9	1110.5	1328.1	1658.6	1987.0	2317.5	2645.9	2734.2	2801.9	2711.6
55°	667.1	903.2	1137.2	1371.2	1716.0	2062.9	2407.8	2752.6	2840.9	2890.2	2822.4
57.5°	673.3	927.8	1180.3	1434.8	1789.9	2145.1	2500.2	2855.3	2962.0	2996.9	2982.5
60°	677.4	948.3	1217.2	1488.2	1835.1	2182.0	2528.9	2875.8	2986.7	3072.9	3089.3
62.5°	667.1	934.0	1198.8	1465.6	1779.7	2093.7	2407.8	2721.9	2904.5	3031.8	3105.7
65°	636.3	882.7	1131.0	1377.4	1666.8	1958.3	2247.7	2537.1	2730.1	2918.9	2978.4
67.5°	568.6	778.0	987.3	1196.7	1449.2	1701.7	1952.1	2204.6	2446.8	2629.5	2711.6
70°	492.6	656.9	823.1	987.3	1217.2	1447.1	1677.0	1906.9	2120.4	2321.6	2399.6
72.5°	429.0	556.3	685.6	812.9	977.1	1139.2	1303.5	1465.6	1718.1	1919.3	1995.2
75°	365.4	457.7	548.1	640.4	753.3	866.2	977.1	1090.0	1268.6	1449.2	1525.1
77.5°	281.2	342.8	402.3	461.9	539.9	615.8	693.8	769.8	895.0	1030.4	1069.4
80°	195.0	229.9	262.7	297.6	359.2	420.8	482.4	544.0	626.1	702.0	761.5
82.5°	121.1	143.7	164.2	184.7	234.0	283.3	330.5	379.7	412.6	416.7	476.2
85°	78.0	92.4	104.7	117.0	145.7	176.5	205.3	234.0	209.4	195.0	232.0
87.5°	30.8	39.0	45.2	51.3	49.3	47.2	45.2	43.1	36.9	32.8	41.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675989
 CATALOG NUMBER: CCW-SA-1D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675989

CATALOG NUMBER: CCW-SA-1D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9
2.5°	1582.6	1588.8	1594.9	1599.0	1605.2	1607.3	1609.3	1609.3	1611.4	1613.4	1617.5
5°	1658.6	1670.9	1683.2	1693.5	1705.8	1716.0	1724.3	1734.5	1742.7	1742.7	1740.7
7.5°	1594.9	1625.7	1656.5	1687.3	1718.1	1740.7	1761.2	1783.8	1804.3	1808.4	1812.5
10°	1510.8	1543.6	1574.4	1607.3	1638.0	1672.9	1705.8	1738.6	1773.5	1779.7	1787.9
12.5°	1432.8	1471.8	1510.8	1547.7	1586.7	1611.4	1636.0	1658.6	1683.2	1699.6	1716.0
15°	1430.7	1463.6	1496.4	1527.2	1560.0	1574.4	1588.8	1601.1	1615.5	1615.5	1617.5
17.5°	1477.9	1498.5	1519.0	1537.5	1558.0	1560.0	1564.1	1566.2	1568.2	1562.1	1555.9
20°	1570.3	1578.5	1586.7	1594.9	1603.1	1588.8	1576.5	1562.1	1547.7	1531.3	1516.9
22.5°	1705.8	1687.3	1668.8	1650.4	1631.9	1607.3	1580.6	1555.9	1529.2	1508.7	1488.2
25°	1833.0	1810.5	1787.9	1765.3	1742.7	1689.4	1636.0	1580.6	1527.2	1504.6	1482.0
27.5°	2003.4	1968.5	1933.6	1898.7	1863.8	1792.0	1720.1	1648.3	1576.5	1537.5	1500.5
30°	2044.5	2005.5	1966.5	1925.4	1886.4	1816.6	1748.9	1679.1	1609.3	1564.1	1521.0
32.5°	2104.0	2058.8	2013.7	1968.5	1923.4	1855.6	1787.9	1718.1	1650.4	1609.3	1566.2
35°	2202.5	2151.2	2099.9	2046.5	1995.2	1925.4	1857.7	1787.9	1718.1	1670.9	1625.7
37.5°	2286.7	2227.2	2167.6	2108.1	2048.6	1987.0	1923.4	1861.8	1798.2	1750.9	1705.8
40°	2381.1	2315.4	2249.7	2186.1	2120.4	2062.9	2005.5	1945.9	1888.5	1851.5	1814.6
42.5°	2463.2	2383.2	2305.2	2227.2	2147.1	2108.1	2071.2	2032.2	1993.2	1974.7	1954.2
45°	2520.7	2446.8	2370.8	2297.0	2223.1	2194.3	2165.6	2136.8	2108.1	2126.6	2145.1
47.5°	2545.3	2485.8	2428.3	2370.8	2311.3	2321.6	2331.8	2340.1	2350.3	2375.0	2401.6
50°	2567.9	2535.1	2500.2	2467.3	2432.4	2471.4	2508.4	2547.4	2586.4	2637.7	2689.0
52.5°	2613.1	2594.6	2578.2	2559.7	2541.2	2609.0	2676.7	2744.4	2812.2	2869.7	2927.1
55°	2748.5	2734.2	2719.8	2703.4	2689.0	2785.5	2879.9	2976.4	3072.9	3132.4	3191.9
57.5°	2935.3	2927.1	2916.9	2908.7	2898.4	2992.8	3085.2	3177.6	3272.0	3329.5	3389.0
60°	3077.0	3079.0	3079.0	3081.1	3081.1	3152.9	3224.8	3298.7	3370.5	3419.8	3471.1
62.5°	3152.9	3148.8	3144.7	3140.6	3136.5	3196.0	3255.6	3315.1	3374.6	3411.6	3448.5
65°	3070.8	3093.4	3116.0	3138.6	3161.1	3169.3	3175.5	3183.7	3189.9	3212.4	3235.0
67.5°	2795.8	2840.9	2884.0	2929.2	2972.3	2941.5	2912.8	2882.0	2851.2	2857.3	2861.4
70°	2489.9	2541.2	2594.6	2645.9	2697.2	2625.4	2553.5	2479.6	2407.8	2383.2	2358.5
72.5°	2099.9	2145.1	2192.3	2237.4	2282.6	2194.3	2108.1	2019.8	1931.6	1888.5	1845.4
75°	1605.2	1658.6	1714.0	1767.4	1820.7	1722.2	1621.6	1523.1	1422.5	1393.8	1367.1
77.5°	1170.0	1233.7	1297.3	1360.9	1424.6	1336.3	1248.0	1157.7	1069.4	1053.0	1036.6
80°	851.9	901.1	948.3	997.6	1044.8	993.5	942.2	890.9	839.5	837.5	835.4
82.5°	574.8	617.9	658.9	702.0	743.1	722.5	704.1	683.5	663.0	683.5	706.1
85°	295.6	355.1	416.7	476.2	535.8	529.6	525.5	519.3	513.2	539.9	564.5
87.5°	59.5	110.8	162.2	211.4	262.7	250.4	238.1	223.7	211.4	219.6	225.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675989
 CATALOG NUMBER: CCW-SA-1D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675989

CATALOG NUMBER: CCW-SA-1D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9
2.5°	1619.6	1621.6	1621.6	1621.6	1621.6	1621.6	1617.5	1615.5	1611.4	1607.3	1601.1
5°	1740.7	1738.6	1730.4	1722.2	1711.9	1703.7	1697.6	1689.4	1683.2	1675.0	1662.7
7.5°	1816.6	1820.7	1806.4	1794.0	1779.7	1765.3	1750.9	1736.6	1722.2	1707.8	1679.1
10°	1794.0	1800.2	1792.0	1783.8	1773.5	1765.3	1748.9	1730.4	1714.0	1695.5	1660.6
12.5°	1730.4	1746.8	1742.7	1738.6	1734.5	1730.4	1720.1	1707.8	1697.6	1685.3	1646.3
15°	1617.5	1617.5	1619.6	1621.6	1621.6	1623.7	1625.7	1627.8	1629.8	1631.9	1609.3
17.5°	1549.8	1543.6	1543.6	1543.6	1543.6	1543.6	1551.8	1562.1	1570.3	1578.5	1572.4
20°	1500.5	1486.1	1484.1	1484.1	1482.0	1480.0	1494.4	1510.8	1525.1	1539.5	1547.7
22.5°	1467.7	1447.1	1445.1	1443.0	1441.0	1438.9	1457.4	1475.9	1494.4	1512.8	1541.6
25°	1459.5	1436.9	1438.9	1441.0	1441.0	1443.0	1457.4	1471.8	1486.1	1500.5	1549.8
27.5°	1461.5	1424.6	1426.6	1428.7	1428.7	1430.7	1453.3	1473.8	1496.4	1516.9	1578.5
30°	1475.9	1432.8	1428.7	1424.6	1420.5	1416.4	1447.1	1477.9	1508.7	1539.5	1586.7
32.5°	1525.1	1484.1	1473.8	1463.6	1453.3	1443.0	1480.0	1514.9	1551.8	1586.7	1625.7
35°	1578.5	1533.4	1529.2	1525.1	1519.0	1514.9	1547.7	1582.6	1615.5	1648.3	1683.2
37.5°	1658.6	1613.4	1609.3	1603.1	1599.0	1592.9	1629.8	1664.7	1701.7	1736.6	1767.4
40°	1777.6	1740.7	1738.6	1738.6	1736.6	1734.5	1763.3	1794.0	1822.8	1851.5	1872.0
42.5°	1935.7	1917.2	1923.4	1931.6	1937.7	1943.9	1966.5	1991.1	2013.7	2036.3	2030.1
45°	2163.5	2182.0	2184.1	2186.1	2188.2	2190.2	2196.4	2204.6	2210.7	2216.9	2192.3
47.5°	2426.3	2450.9	2463.2	2475.5	2485.8	2498.1	2489.9	2479.6	2471.4	2461.2	2399.6
50°	2738.3	2789.6	2787.5	2785.5	2781.4	2779.3	2762.9	2746.5	2728.0	2711.6	2621.3
52.5°	2984.6	3042.1	3052.3	3062.6	3072.9	3083.1	3052.3	3021.5	2988.7	2957.9	2845.0
55°	3249.4	3308.9	3311.0	3313.0	3313.0	3315.1	3272.0	3228.9	3183.7	3140.6	3023.6
57.5°	3446.5	3503.9	3497.8	3493.7	3487.5	3481.4	3430.0	3378.7	3327.4	3276.1	3159.1
60°	3520.4	3569.6	3557.3	3545.0	3530.6	3518.3	3479.3	3440.3	3399.2	3360.2	3247.3
62.5°	3485.5	3522.4	3503.9	3487.5	3469.0	3450.6	3401.3	3350.0	3300.7	3249.4	3167.3
65°	3255.6	3278.1	3253.5	3230.9	3208.3	3183.7	3142.7	3101.6	3058.5	3017.4	2962.0
67.5°	2867.6	2871.7	2869.7	2867.6	2865.5	2863.5	2804.0	2744.4	2682.9	2623.3	2619.2
70°	2336.0	2311.3	2315.4	2321.6	2325.7	2329.8	2284.6	2241.5	2196.4	2151.2	2171.7
72.5°	1802.3	1759.1	1769.4	1781.7	1792.0	1802.3	1765.3	1730.4	1693.5	1656.5	1685.3
75°	1338.3	1311.7	1321.9	1334.2	1344.5	1354.8	1340.4	1326.0	1309.6	1295.2	1321.9
77.5°	1020.2	1003.8	1005.8	1005.8	1007.9	1007.9	1009.9	1014.0	1016.1	1018.1	1046.9
80°	831.3	829.3	827.2	825.2	821.1	819.0	839.5	860.1	880.6	901.1	915.5
82.5°	726.6	747.2	734.9	724.6	712.3	700.0	718.4	736.9	755.4	773.9	767.7
85°	591.2	615.8	593.2	570.6	546.0	523.4	539.9	554.2	570.6	585.0	576.8
87.5°	234.0	240.2	203.2	168.3	131.4	94.4	149.8	203.2	258.6	312.0	320.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675989
 CATALOG NUMBER: CCW-SA-1D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675989

CATALOG NUMBER: CCW-SA-1D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9	1477.9
2.5°	1594.9	1586.7	1580.6	1578.5	1574.4	1572.4	1568.2	1564.1	1558.0	1553.9	1547.7
5°	1648.3	1636.0	1621.6	1601.1	1582.6	1562.1	1541.6	1523.1	1504.6	1484.1	1465.6
7.5°	1650.4	1621.6	1592.9	1566.2	1537.5	1510.8	1482.0	1457.4	1430.7	1404.0	1379.4
10°	1627.8	1592.9	1558.0	1523.1	1490.2	1455.4	1420.5	1391.7	1360.9	1330.1	1301.4
12.5°	1609.3	1570.3	1531.3	1490.2	1451.2	1410.2	1369.1	1340.4	1311.7	1282.9	1254.2
15°	1586.7	1562.1	1539.5	1502.6	1465.6	1428.7	1391.7	1352.7	1315.8	1276.8	1237.8
17.5°	1568.2	1562.1	1555.9	1531.3	1506.7	1480.0	1455.4	1416.4	1377.4	1336.3	1297.3
20°	1558.0	1566.2	1574.4	1562.1	1549.8	1535.4	1523.1	1494.4	1465.6	1434.8	1406.1
22.5°	1570.3	1601.1	1629.8	1631.9	1636.0	1638.0	1640.1	1613.4	1586.7	1558.0	1531.3
25°	1599.0	1648.3	1697.6	1724.3	1750.9	1779.7	1806.4	1789.9	1773.5	1757.1	1740.7
27.5°	1638.0	1699.6	1761.2	1800.2	1837.2	1876.2	1915.2	1913.1	1911.0	1906.9	1904.9
30°	1631.9	1679.1	1726.3	1773.5	1820.7	1867.9	1915.2	1939.8	1962.4	1987.0	2011.6
32.5°	1666.8	1705.8	1746.8	1796.1	1845.4	1896.7	1945.9	1997.3	2046.5	2097.8	2149.2
35°	1720.1	1755.0	1792.0	1845.4	1900.8	1954.2	2009.6	2071.2	2134.8	2198.4	2260.0
37.5°	1800.2	1831.0	1863.8	1909.0	1956.2	2001.4	2048.6	2138.9	2229.2	2321.6	2411.9
40°	1892.6	1913.1	1933.6	1976.7	2019.8	2062.9	2106.1	2219.0	2331.8	2444.7	2557.6
42.5°	2026.0	2019.8	2013.7	2048.6	2085.5	2120.4	2157.4	2260.0	2362.6	2465.3	2567.9
45°	2167.6	2143.0	2118.4	2134.8	2153.3	2169.7	2188.2	2292.8	2397.5	2504.3	2609.0
47.5°	2338.0	2276.4	2214.8	2200.5	2186.1	2169.7	2155.3	2268.2	2381.1	2496.1	2609.0
50°	2531.0	2438.6	2348.3	2311.3	2272.3	2235.4	2196.4	2288.7	2383.2	2477.6	2570.0
52.5°	2732.1	2617.2	2504.3	2446.8	2389.3	2329.8	2272.3	2350.3	2430.4	2510.4	2588.4
55°	2904.5	2787.5	2668.5	2600.7	2533.0	2465.3	2397.5	2475.5	2553.5	2631.5	2709.5
57.5°	3042.1	2925.1	2808.1	2744.4	2678.8	2615.1	2549.4	2623.3	2699.3	2775.2	2849.1
60°	3136.5	3023.6	2910.7	2849.1	2787.5	2726.0	2664.4	2752.6	2840.9	2931.2	3019.5
62.5°	3087.2	3005.1	2923.0	2896.3	2869.7	2840.9	2814.2	2898.4	2980.5	3064.7	3148.8
65°	2906.6	2851.2	2795.8	2822.4	2851.2	2877.9	2906.6	2962.0	3017.4	3074.9	3130.3
67.5°	2613.1	2609.0	2602.8	2662.3	2721.9	2783.4	2843.0	2879.9	2914.8	2951.8	2988.7
70°	2192.3	2214.8	2235.4	2338.0	2440.6	2543.3	2645.9	2660.3	2674.6	2689.0	2703.4
72.5°	1716.0	1744.8	1775.6	1911.0	2044.5	2179.9	2315.4	2307.2	2299.0	2288.7	2280.5
75°	1350.7	1377.4	1406.1	1531.3	1656.5	1781.7	1906.9	1872.0	1839.2	1804.3	1769.4
77.5°	1077.7	1106.4	1137.2	1254.2	1371.2	1490.2	1607.3	1523.1	1438.9	1354.8	1270.6
80°	927.8	942.2	954.5	1034.6	1112.6	1192.6	1272.7	1186.5	1098.2	1009.9	923.7
82.5°	761.5	753.3	747.2	794.4	841.6	888.8	936.0	853.9	771.8	687.6	605.5
85°	568.6	560.4	552.2	576.8	601.4	628.1	652.8	558.3	463.9	367.4	273.0
87.5°	330.5	338.7	346.9	373.6	400.3	429.0	455.7	359.2	262.7	164.2	67.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675989
 CATALOG NUMBER: CCW-SA-1D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675989
CATALOG NUMBER: CCW-SA-1D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1477.9	1477.9
2.5°	1535.4	1525.1
5°	1451.2	1436.9
7.5°	1358.9	1340.4
10°	1274.7	1250.1
12.5°	1221.3	1190.6
15°	1200.8	1163.9
17.5°	1262.4	1227.5
20°	1356.8	1309.6
22.5°	1471.8	1414.3
25°	1670.9	1601.1
27.5°	1833.0	1761.2
30°	1933.6	1855.6
32.5°	2044.5	1941.8
35°	2159.4	2060.9
37.5°	2299.0	2188.2
40°	2442.7	2327.7
42.5°	2492.0	2418.1
45°	2539.2	2469.4
47.5°	2549.4	2492.0
50°	2559.7	2551.5
52.5°	2588.4	2586.4
55°	2711.6	2713.6
57.5°	2863.5	2875.8
60°	3003.1	2988.7
62.5°	3074.9	3001.0
65°	3025.7	2923.0
67.5°	2877.9	2767.0
70°	2553.5	2403.7
72.5°	2149.2	2017.8
75°	1656.5	1545.7
77.5°	1178.2	1085.9
80°	829.3	736.9
82.5°	531.6	457.7
85°	240.2	209.4
87.5°	67.7	65.7
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P675989
CATALOG NUMBER: CCW-SA-1D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)