

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P676020

Luminaire Tested: **CCW-SA-1B-827-U-SLR**

Issue Date: 04/25/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P676020  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 04/25/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: CCW-SA-1B-827-U-SLR  
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @450mA w/  
SLR distribution lens  
Light Source: (16) 2700K CCT, 80 CRI LEDs  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2106.8 lumens  
Efficiency: N/A  
Efficacy: 87.8 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B1 - U0 - G1


Input Watts (W): 24  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



REPORT NUMBER: P676020  
 CATALOG NUMBER: CCW-SA-1B-827-U-SLR

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 3 fc  
 Type IV - Short - N/A

REPORT NUMBER: P676020  
CATALOG NUMBER: CCW-SA-1B-827-U-SLR

### Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral    - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P676020  
 CATALOG NUMBER: CCW-SA-1B-827-U-SLR


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	433.5	0.0	433.5
	% Fixture	20.6	0.0	20.6
<b>Street Side</b>	Lumens	1673.3	0.0	1673.3
	% Fixture	79.4	0.0	79.4
<b>Total</b>	Lumens	2106.8	0.0	2106.8
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	52.3	2.5
10°-20°	110.4	5.2
20°-30°	161.5	7.7
30°-40°	227.5	10.8
40°-50°	312.6	14.8
50°-60°	426.1	20.2
60°-70°	466.4	22.1
70°-80°	269.3	12.8
80°-90°	80.7	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2106.8	100.0
0°-180°	2106.8	100.0




REPORT NUMBER: P676020  
 CATALOG NUMBER: CCW-SA-1B-827-U-SLR

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	216.4	10.3			
FM (30°-60°)	768.8	36.5			
FH (60°-80°)	619.5	29.4			G0/660
FVH (80°-90°)	68.6	3.3			G1/100
BL (0°-30°)	107.8	5.1	B0/110		
BM (30°-60°)	197.4	9.4	B0/220		
BH (60°-80°)	116.2	5.5	B1/500		G1/500
BVH (80°-90°)	12.2	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B1-U0-G1**

Type IV Short





REPORT NUMBER: P676020

CATALOG NUMBER: CCW-SA-1B-827-U-SLR

**CANDELA DISTRIBUTION (FULL):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8
2.5°	694.3	690.5	687.7	684.9	681.2	678.4	674.7	670.9	666.3	662.5	657.8
5°	654.1	642.9	631.7	625.1	617.7	611.1	603.6	595.2	586.8	577.5	569.1
7.5°	610.2	596.2	582.2	570.9	558.8	547.6	535.4	525.2	514.9	504.6	494.3
10°	569.1	556.0	542.9	528.9	513.9	499.9	485.0	471.0	456.9	442.9	428.9
12.5°	542.0	526.1	511.1	495.2	480.3	464.4	448.5	435.4	422.4	408.3	395.3
15°	529.8	514.9	500.9	485.0	469.1	453.2	437.3	422.4	408.3	393.4	378.4
17.5°	558.8	537.3	515.8	495.2	474.7	454.1	433.6	414.9	396.2	377.5	358.8
20°	596.2	569.1	542.9	517.7	491.5	466.3	440.1	414.0	387.8	361.6	335.5
22.5°	643.8	613.0	583.1	550.4	516.7	484.0	450.4	417.7	385.0	351.3	318.6
25°	728.9	692.4	656.0	609.3	561.6	514.9	467.2	424.2	382.2	339.2	296.2
27.5°	801.7	752.2	703.6	647.6	591.5	535.4	479.4	429.8	381.2	331.7	282.2
30°	844.7	796.1	747.5	679.3	612.1	543.8	475.6	420.5	366.3	311.2	256.0
32.5°	884.0	829.8	775.6	700.8	625.1	550.4	474.7	414.0	354.2	293.4	232.7
35°	938.2	878.4	819.5	732.6	645.7	558.8	471.9	409.3	345.7	283.1	219.6
37.5°	996.1	922.3	849.4	753.2	656.9	560.7	464.4	402.7	341.1	279.4	217.7
40°	1059.6	969.9	881.2	774.6	669.1	562.5	456.0	394.3	332.7	270.1	208.4
42.5°	1100.8	1003.6	906.4	791.5	677.5	562.5	447.6	386.9	326.1	264.4	203.7
45°	1124.1	1029.7	936.3	812.0	687.7	563.5	439.2	379.4	319.6	258.8	199.0
47.5°	1134.4	1046.6	958.7	827.9	698.0	567.2	436.4	375.6	314.0	253.2	191.6
50°	1161.5	1083.9	1006.4	866.2	727.0	586.8	446.7	381.2	316.8	251.4	186.0
52.5°	1177.4	1111.0	1044.7	900.8	756.9	613.0	469.1	396.2	323.3	250.4	177.5
55°	1235.3	1171.8	1108.2	955.0	800.8	647.6	493.4	413.0	332.7	251.4	171.0
57.5°	1309.1	1241.9	1175.5	1010.1	844.7	679.3	513.9	428.0	341.1	255.1	168.2
60°	1360.5	1295.1	1230.6	1055.0	878.4	702.7	526.1	436.4	346.7	256.0	166.3
62.5°	1366.1	1282.0	1198.9	1027.9	856.9	684.9	513.9	427.0	340.1	252.3	165.4
65°	1330.6	1232.5	1134.4	970.9	807.4	643.8	480.3	400.9	321.4	241.1	161.7
67.5°	1259.6	1144.7	1029.7	880.2	730.7	581.2	431.7	363.5	296.2	228.0	159.8
70°	1094.2	993.3	893.3	763.4	634.5	504.6	374.7	318.6	263.5	207.4	151.4
72.5°	918.5	824.2	730.7	625.1	520.5	414.9	309.3	267.2	225.2	182.2	140.2
75°	703.6	632.6	562.5	484.0	405.5	326.1	247.6	216.8	186.0	155.1	124.3
77.5°	494.3	456.0	418.6	359.8	300.9	242.0	183.1	162.6	142.0	121.5	100.9
80°	335.5	314.0	293.4	251.4	209.3	166.3	124.3	111.2	97.2	84.1	70.1
82.5°	208.4	207.4	205.6	176.6	147.6	118.7	89.7	78.5	68.2	57.0	45.8
85°	95.3	111.2	126.1	110.3	94.4	78.5	62.6	55.1	47.7	39.2	31.8
87.5°	29.9	36.4	42.0	40.2	37.4	35.5	32.7	28.0	23.4	18.7	14.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676020  
 CATALOG NUMBER: CCW-SA-1B-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P676020  
 CATALOG NUMBER: CCW-SA-1B-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8
2.5°	654.1	651.3	647.6	643.8	639.2	635.4	630.7	626.1	625.1	623.3	622.3
5°	563.5	557.9	551.3	545.7	540.1	533.6	528.0	521.4	516.7	511.1	506.5
7.5°	484.0	474.7	464.4	454.1	444.8	435.4	425.2	415.8	411.2	406.5	401.8
10°	420.5	411.2	402.7	393.4	386.9	381.2	374.7	368.2	362.6	357.0	351.3
12.5°	388.7	382.2	375.6	369.1	361.6	355.1	347.6	340.1	333.6	328.0	321.4
15°	369.1	359.8	349.5	340.1	329.9	320.5	310.2	300.0	292.5	285.9	278.5
17.5°	345.7	331.7	318.6	304.6	293.4	282.2	270.1	258.8	250.4	241.1	232.7
20°	319.6	303.7	286.9	271.0	257.9	245.8	232.7	219.6	210.2	200.0	190.6
22.5°	297.1	276.6	255.1	233.6	219.6	205.6	190.6	176.6	168.2	158.9	150.4
25°	272.9	250.4	227.1	203.7	189.7	174.7	160.7	145.8	139.2	133.6	127.1
27.5°	259.8	237.3	214.0	191.6	178.5	164.5	151.4	137.4	132.7	127.1	122.4
30°	233.6	212.1	189.7	167.3	157.9	149.5	140.2	130.8	129.0	128.0	126.1
32.5°	210.2	187.8	165.4	143.0	134.6	126.1	117.7	109.3	108.4	106.5	105.6
35°	198.1	176.6	154.2	132.7	125.2	116.8	109.3	100.9	99.0	96.2	94.4
37.5°	195.3	172.9	149.5	127.1	119.6	112.1	103.7	96.2	94.4	92.5	90.6
40°	187.8	166.3	145.8	124.3	116.8	109.3	100.9	93.4	91.6	89.7	87.8
42.5°	182.2	161.7	140.2	118.7	112.1	105.6	98.1	91.6	89.7	87.8	85.0
45°	177.5	156.1	133.6	112.1	107.5	102.8	97.2	92.5	90.6	87.8	86.0
47.5°	170.1	149.5	128.0	106.5	101.9	98.1	93.4	88.8	86.9	85.0	83.2
50°	164.5	143.0	121.5	100.0	96.2	92.5	88.8	85.0	85.0	86.0	86.0
52.5°	157.0	136.4	115.9	95.3	91.6	87.8	84.1	80.4	81.3	82.2	83.2
55°	150.4	130.8	110.3	89.7	86.0	82.2	77.6	73.8	74.8	75.7	76.6
57.5°	147.6	127.1	106.5	86.0	82.2	77.6	73.8	69.1	69.1	69.1	69.1
60°	145.8	124.3	103.7	82.2	77.6	73.8	69.1	64.5	63.5	63.5	62.6
62.5°	144.8	123.3	102.8	81.3	75.7	71.0	65.4	59.8	58.9	57.9	57.0
65°	141.1	121.5	100.9	80.4	73.8	68.2	61.7	55.1	54.2	54.2	53.3
67.5°	140.2	119.6	100.0	79.4	72.9	65.4	58.9	51.4	50.5	49.5	48.6
70°	132.7	114.9	96.2	77.6	70.1	63.5	56.1	48.6	47.7	45.8	44.9
72.5°	123.3	107.5	90.6	73.8	66.3	58.9	51.4	43.9	43.0	42.0	40.2
75°	109.3	94.4	79.4	64.5	57.9	52.3	45.8	39.2	38.3	37.4	35.5
77.5°	89.7	77.6	66.3	54.2	49.5	44.9	40.2	35.5	34.6	33.6	31.8
80°	63.5	56.1	49.5	42.0	39.2	35.5	32.7	29.0	29.0	28.0	28.0
82.5°	42.0	38.3	34.6	30.8	29.0	27.1	25.2	23.4	23.4	22.4	22.4
85°	29.9	28.0	25.2	23.4	22.4	20.6	19.6	17.8	17.8	17.8	17.8
87.5°	14.0	14.0	13.1	13.1	12.1	12.1	11.2	10.3	10.3	10.3	10.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676020  
 CATALOG NUMBER: CCW-SA-1B-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676020  
 CATALOG NUMBER: CCW-SA-1B-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8
2.5°	620.5	617.7	614.9	611.1	608.3	604.6	599.9	596.2	591.5	591.5	590.6
5°	500.9	498.1	495.2	491.5	488.7	485.0	482.2	478.4	474.7	474.7	473.8
7.5°	397.1	391.5	385.9	379.4	373.8	370.0	366.3	361.6	357.9	355.1	352.3
10°	345.7	340.1	333.6	328.0	321.4	316.8	312.1	306.5	301.8	298.1	294.3
12.5°	314.9	308.4	301.8	295.3	288.7	282.2	276.6	270.1	263.5	258.8	254.2
15°	271.0	264.4	257.9	251.4	244.8	237.3	229.9	221.5	214.0	210.2	207.4
17.5°	223.3	216.8	209.3	202.8	195.3	189.7	184.1	178.5	172.9	169.1	166.3
20°	180.3	172.9	165.4	157.9	150.4	146.7	143.0	139.2	135.5	132.7	130.8
22.5°	141.1	136.4	132.7	128.0	123.3	120.5	118.7	115.9	113.1	113.1	113.1
25°	120.5	117.7	115.9	113.1	110.3	109.3	108.4	106.5	105.6	104.7	104.7
27.5°	116.8	114.0	111.2	108.4	105.6	104.7	103.7	101.9	100.9	100.9	100.9
30°	124.3	123.3	122.4	121.5	120.5	118.7	115.9	114.0	111.2	109.3	107.5
32.5°	103.7	102.8	102.8	101.9	100.9	102.8	103.7	105.6	106.5	107.5	108.4
35°	91.6	89.7	87.8	86.0	84.1	83.2	82.2	81.3	80.4	80.4	79.4
37.5°	88.8	86.9	85.0	83.2	81.3	80.4	79.4	78.5	77.6	77.6	76.6
40°	86.0	84.1	83.2	81.3	79.4	78.5	77.6	75.7	74.8	73.8	73.8
42.5°	83.2	82.2	80.4	79.4	77.6	76.6	75.7	73.8	72.9	72.0	71.0
45°	83.2	81.3	79.4	77.6	75.7	74.8	72.9	72.0	70.1	70.1	69.1
47.5°	81.3	79.4	77.6	75.7	73.8	72.9	71.0	70.1	68.2	67.3	66.3
50°	86.0	83.2	79.4	76.6	72.9	72.0	70.1	69.1	67.3	66.3	65.4
52.5°	84.1	81.3	77.6	74.8	71.0	69.1	68.2	66.3	64.5	63.5	62.6
55°	77.6	74.8	72.9	70.1	67.3	65.4	63.5	61.7	59.8	58.9	58.9
57.5°	69.1	68.2	67.3	66.3	65.4	63.5	61.7	58.9	57.0	56.1	55.1
60°	61.7	62.6	63.5	64.5	65.4	62.6	59.8	57.0	54.2	53.3	52.3
62.5°	56.1	57.9	59.8	60.7	62.6	59.8	57.0	54.2	51.4	50.5	49.5
65°	52.3	53.3	53.3	54.2	54.2	52.3	51.4	49.5	47.7	46.7	46.7
67.5°	47.7	47.7	47.7	46.7	46.7	45.8	45.8	44.9	43.9	43.0	43.0
70°	43.0	43.0	43.0	42.0	42.0	41.1	41.1	40.2	39.2	39.2	38.3
72.5°	39.2	39.2	38.3	38.3	37.4	37.4	37.4	36.4	36.4	35.5	35.5
75°	34.6	34.6	33.6	33.6	32.7	32.7	32.7	31.8	31.8	31.8	30.8
77.5°	30.8	30.8	29.9	29.9	29.0	29.0	29.0	28.0	28.0	27.1	27.1
80°	27.1	27.1	26.2	26.2	25.2	25.2	24.3	24.3	23.4	23.4	22.4
82.5°	21.5	21.5	21.5	21.5	21.5	20.6	20.6	19.6	18.7	18.7	17.8
85°	17.8	17.8	17.8	16.8	16.8	16.8	15.9	15.9	15.0	14.0	14.0
87.5°	10.3	10.3	10.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	8.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676020  
 CATALOG NUMBER: CCW-SA-1B-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676020  
 CATALOG NUMBER: CCW-SA-1B-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8
2.5°	590.6	589.6	585.9	582.2	585.9	589.6	589.6	589.6	588.7	588.7	588.7
5°	473.8	472.8	471.0	469.1	469.1	468.2	470.0	471.9	473.8	475.6	477.5
7.5°	348.5	345.7	342.9	340.1	342.0	342.9	345.7	347.6	350.4	352.3	357.0
10°	290.6	286.9	284.1	281.3	279.4	277.5	275.7	274.7	272.9	271.0	272.9
12.5°	248.6	243.9	239.2	233.6	232.7	231.7	229.9	228.0	226.1	224.3	223.3
15°	203.7	200.0	198.1	195.3	191.6	187.8	186.0	185.0	183.1	181.3	180.3
17.5°	162.6	158.9	156.1	153.2	152.3	150.4	150.4	150.4	150.4	150.4	150.4
20°	128.0	125.2	125.2	124.3	124.3	123.3	124.3	125.2	125.2	126.1	127.1
22.5°	112.1	112.1	111.2	110.3	111.2	111.2	112.1	113.1	114.0	114.9	115.9
25°	103.7	102.8	103.7	104.7	104.7	104.7	105.6	105.6	106.5	106.5	106.5
27.5°	100.0	100.0	100.9	100.9	101.9	101.9	101.9	100.9	100.9	100.0	100.0
30°	105.6	103.7	103.7	103.7	102.8	101.9	100.9	100.9	100.0	99.0	98.1
32.5°	109.3	110.3	109.3	107.5	106.5	104.7	103.7	101.9	100.9	99.0	97.2
35°	79.4	78.5	80.4	81.3	82.2	83.2	84.1	85.0	85.0	86.0	86.0
37.5°	76.6	75.7	75.7	74.8	74.8	74.8	74.8	74.8	73.8	73.8	74.8
40°	72.9	72.0	72.0	71.0	71.0	70.1	70.1	70.1	70.1	70.1	70.1
42.5°	70.1	69.1	69.1	69.1	69.1	68.2	68.2	67.3	67.3	66.3	66.3
45°	69.1	68.2	67.3	66.3	66.3	65.4	65.4	65.4	64.5	64.5	64.5
47.5°	65.4	64.5	64.5	63.5	63.5	62.6	62.6	62.6	61.7	61.7	61.7
50°	63.5	62.6	62.6	61.7	61.7	60.7	60.7	60.7	59.8	59.8	59.8
52.5°	60.7	59.8	59.8	59.8	58.9	57.9	57.9	57.9	57.0	57.0	57.0
55°	57.9	57.0	57.0	57.0	56.1	55.1	55.1	55.1	54.2	54.2	54.2
57.5°	54.2	53.3	53.3	52.3	52.3	52.3	52.3	52.3	51.4	51.4	51.4
60°	51.4	50.5	50.5	49.5	49.5	48.6	48.6	48.6	48.6	48.6	48.6
62.5°	48.6	47.7	46.7	45.8	46.7	46.7	46.7	46.7	45.8	45.8	45.8
65°	45.8	44.9	43.9	43.0	43.0	43.0	43.0	43.0	43.0	43.0	43.0
67.5°	42.0	41.1	40.2	39.2	40.2	40.2	40.2	40.2	40.2	40.2	40.2
70°	38.3	37.4	37.4	36.4	36.4	35.5	35.5	36.4	36.4	36.4	36.4
72.5°	34.6	33.6	33.6	32.7	32.7	32.7	32.7	32.7	32.7	32.7	32.7
75°	30.8	29.9	29.9	29.0	29.0	29.0	29.0	29.0	29.0	29.0	29.0
77.5°	26.2	25.2	25.2	25.2	25.2	25.2	25.2	26.2	26.2	26.2	26.2
80°	22.4	21.5	21.5	21.5	21.5	21.5	21.5	21.5	21.5	21.5	21.5
82.5°	17.8	16.8	16.8	16.8	16.8	16.8	16.8	16.8	16.8	16.8	16.8
85°	13.1	12.1	12.1	12.1	13.1	13.1	13.1	13.1	13.1	13.1	13.1
87.5°	8.4	7.5	7.5	7.5	8.4	8.4	8.4	8.4	7.5	7.5	7.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676020  
 CATALOG NUMBER: CCW-SA-1B-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676020  
 CATALOG NUMBER: CCW-SA-1B-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8
2.5°	588.7	588.7	588.7	587.8	586.8	585.9	585.0	587.8	589.6	592.4	594.3
5°	478.4	480.3	481.2	484.0	486.8	489.6	492.4	494.3	496.2	497.1	499.0
7.5°	360.7	365.4	369.1	372.8	376.6	379.4	383.1	385.9	388.7	391.5	394.3
10°	273.8	275.7	276.6	280.3	283.1	286.9	289.7	292.5	295.3	297.1	300.0
12.5°	222.4	220.5	219.6	219.6	219.6	219.6	219.6	221.5	223.3	225.2	227.1
15°	179.4	178.5	177.5	176.6	175.7	173.8	172.9	174.7	176.6	178.5	180.3
17.5°	150.4	150.4	150.4	149.5	148.6	147.6	146.7	147.6	148.6	148.6	149.5
20°	129.0	129.9	130.8	131.8	131.8	132.7	132.7	133.6	134.6	134.6	135.5
22.5°	115.9	116.8	116.8	116.8	117.7	117.7	117.7	118.7	119.6	120.5	121.5
25°	105.6	105.6	104.7	104.7	105.6	105.6	105.6	105.6	106.5	106.5	106.5
27.5°	100.0	99.0	99.0	99.0	99.0	98.1	98.1	98.1	98.1	98.1	98.1
30°	97.2	96.2	95.3	94.4	94.4	93.4	92.5	92.5	92.5	92.5	92.5
32.5°	96.2	94.4	92.5	91.6	91.6	90.6	89.7	88.8	88.8	87.8	86.9
35°	86.0	85.0	85.0	84.1	83.2	82.2	81.3	81.3	81.3	80.4	80.4
37.5°	74.8	75.7	75.7	75.7	76.6	76.6	76.6	76.6	77.6	77.6	77.6
40°	70.1	70.1	70.1	71.0	72.0	72.0	72.9	72.9	73.8	73.8	73.8
42.5°	66.3	65.4	65.4	66.3	66.3	67.3	67.3	68.2	69.1	69.1	70.1
45°	64.5	63.5	63.5	63.5	63.5	62.6	62.6	63.5	64.5	65.4	66.3
47.5°	60.7	60.7	59.8	59.8	59.8	59.8	59.8	59.8	60.7	60.7	60.7
50°	58.9	58.9	57.9	57.9	57.9	57.9	57.9	57.9	57.9	57.9	57.9
52.5°	57.0	56.1	56.1	56.1	56.1	55.1	55.1	55.1	55.1	55.1	55.1
55°	54.2	53.3	53.3	53.3	53.3	53.3	53.3	53.3	54.2	54.2	54.2
57.5°	51.4	50.5	50.5	50.5	51.4	51.4	51.4	51.4	52.3	52.3	52.3
60°	48.6	48.6	48.6	48.6	48.6	48.6	48.6	49.5	49.5	50.5	50.5
62.5°	45.8	45.8	45.8	45.8	46.7	46.7	46.7	46.7	47.7	47.7	47.7
65°	43.0	43.0	43.0	43.0	43.9	43.9	43.9	43.9	43.9	43.9	43.9
67.5°	40.2	40.2	40.2	40.2	40.2	40.2	40.2	41.1	41.1	42.0	42.0
70°	36.4	35.5	35.5	36.4	36.4	37.4	37.4	38.3	38.3	39.2	39.2
72.5°	32.7	32.7	32.7	32.7	32.7	32.7	32.7	33.6	34.6	34.6	35.5
75°	29.0	29.0	29.0	29.0	29.9	29.9	29.9	30.8	30.8	31.8	31.8
77.5°	26.2	25.2	25.2	25.2	26.2	26.2	26.2	27.1	27.1	28.0	28.0
80°	21.5	21.5	21.5	21.5	22.4	22.4	22.4	22.4	23.4	23.4	23.4
82.5°	17.8	17.8	17.8	17.8	17.8	17.8	17.8	17.8	18.7	18.7	18.7
85°	13.1	13.1	13.1	13.1	14.0	14.0	14.0	14.0	14.0	14.0	14.0
87.5°	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4	9.3	9.3	9.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676020  
 CATALOG NUMBER: CCW-SA-1B-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P676020  
 CATALOG NUMBER: CCW-SA-1B-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8
2.5°	594.3	594.3	594.3	594.3	596.2	597.1	599.0	599.9	599.0	598.0	596.2
5°	499.9	500.9	500.9	501.8	501.8	501.8	501.8	501.8	503.7	505.5	507.4
7.5°	395.3	396.2	397.1	398.1	398.1	398.1	397.1	397.1	398.1	398.1	399.0
10°	302.8	306.5	309.3	312.1	310.2	307.4	305.6	302.8	302.8	302.8	301.8
12.5°	228.9	229.9	231.7	232.7	231.7	231.7	230.8	229.9	230.8	232.7	233.6
15°	181.3	181.3	182.2	182.2	183.1	184.1	184.1	185.0	186.9	187.8	189.7
17.5°	150.4	151.4	151.4	152.3	152.3	153.2	153.2	153.2	155.1	157.0	159.8
20°	135.5	135.5	135.5	135.5	135.5	134.6	134.6	133.6	134.6	136.4	137.4
22.5°	121.5	122.4	122.4	122.4	121.5	120.5	118.7	117.7	117.7	118.7	118.7
25°	106.5	105.6	105.6	104.7	104.7	105.6	105.6	105.6	106.5	106.5	107.5
27.5°	98.1	97.2	97.2	96.2	96.2	97.2	97.2	97.2	97.2	97.2	97.2
30°	91.6	91.6	90.6	89.7	90.6	90.6	91.6	91.6	92.5	92.5	93.4
32.5°	86.9	86.0	86.0	85.0	86.0	86.0	86.9	86.9	87.8	88.8	88.8
35°	80.4	80.4	80.4	80.4	80.4	80.4	79.4	79.4	79.4	79.4	79.4
37.5°	76.6	76.6	75.7	74.8	74.8	74.8	74.8	74.8	73.8	72.9	72.0
40°	73.8	72.9	72.9	72.0	71.0	71.0	70.1	69.1	69.1	68.2	68.2
42.5°	70.1	69.1	69.1	68.2	67.3	67.3	66.3	65.4	65.4	65.4	64.5
45°	65.4	65.4	64.5	63.5	63.5	63.5	62.6	62.6	62.6	62.6	61.7
47.5°	60.7	60.7	59.8	59.8	59.8	59.8	58.9	58.9	58.9	58.9	58.9
50°	57.9	57.9	57.9	57.9	57.9	57.9	57.0	57.0	57.0	57.0	57.0
52.5°	55.1	55.1	55.1	55.1	55.1	55.1	55.1	55.1	55.1	55.1	55.1
55°	54.2	54.2	54.2	54.2	54.2	54.2	53.3	53.3	53.3	54.2	54.2
57.5°	52.3	52.3	51.4	51.4	51.4	51.4	51.4	51.4	51.4	51.4	51.4
60°	50.5	50.5	50.5	50.5	50.5	50.5	50.5	50.5	50.5	50.5	50.5
62.5°	47.7	47.7	47.7	47.7	47.7	48.6	48.6	48.6	48.6	48.6	47.7
65°	43.9	44.9	44.9	44.9	44.9	44.9	44.9	44.9	44.9	44.9	44.9
67.5°	42.0	42.0	42.0	42.0	42.0	42.0	42.0	42.0	42.0	42.0	42.0
70°	39.2	39.2	38.3	38.3	38.3	39.2	39.2	39.2	39.2	39.2	39.2
72.5°	35.5	35.5	35.5	35.5	35.5	35.5	35.5	35.5	35.5	36.4	36.4
75°	31.8	31.8	31.8	31.8	31.8	31.8	31.8	31.8	31.8	31.8	31.8
77.5°	28.0	28.0	27.1	27.1	27.1	28.0	28.0	28.0	28.0	29.0	29.0
80°	23.4	23.4	23.4	23.4	23.4	23.4	23.4	23.4	23.4	24.3	24.3
82.5°	18.7	18.7	18.7	18.7	18.7	18.7	18.7	18.7	18.7	19.6	19.6
85°	14.0	15.0	15.0	15.0	15.0	15.0	15.0	15.0	15.0	15.9	15.9
87.5°	9.3	9.3	9.3	9.3	9.3	9.3	8.4	8.4	8.4	8.4	7.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676020  
 CATALOG NUMBER: CCW-SA-1B-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676020  
 CATALOG NUMBER: CCW-SA-1B-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8
2.5°	595.2	596.2	597.1	597.1	598.0	599.0	599.0	602.7	606.4	608.3	610.2
5°	509.3	508.3	508.3	507.4	506.5	509.3	512.1	517.7	523.3	524.2	526.1
7.5°	399.0	399.9	400.9	400.9	401.8	399.0	395.3	396.2	397.1	401.8	405.5
10°	301.8	302.8	303.7	303.7	304.6	303.7	301.8	304.6	307.4	311.2	315.8
12.5°	234.5	237.3	240.1	242.0	244.8	246.7	247.6	251.4	254.2	258.8	263.5
15°	191.6	193.4	195.3	197.2	199.0	200.9	202.8	206.5	210.2	215.9	221.5
17.5°	161.7	161.7	162.6	162.6	162.6	164.5	166.3	168.2	169.1	174.7	180.3
20°	138.3	137.4	136.4	135.5	134.6	136.4	137.4	138.3	139.2	143.0	145.8
22.5°	118.7	118.7	119.6	119.6	119.6	118.7	116.8	117.7	117.7	119.6	122.4
25°	107.5	107.5	107.5	106.5	106.5	107.5	108.4	108.4	107.5	108.4	109.3
27.5°	97.2	98.1	98.1	99.0	99.0	100.0	100.0	100.0	100.0	100.9	101.9
30°	93.4	93.4	94.4	94.4	94.4	95.3	96.2	96.2	96.2	97.2	99.0
32.5°	89.7	90.6	91.6	92.5	93.4	94.4	94.4	95.3	95.3	96.2	97.2
35°	79.4	78.5	78.5	77.6	76.6	76.6	76.6	76.6	75.7	76.6	76.6
37.5°	71.0	71.0	71.0	70.1	70.1	71.0	71.0	71.0	71.0	72.0	72.0
40°	67.3	67.3	67.3	67.3	67.3	67.3	67.3	68.2	68.2	69.1	70.1
42.5°	64.5	64.5	64.5	64.5	64.5	65.4	65.4	65.4	65.4	66.3	66.3
45°	61.7	61.7	61.7	61.7	61.7	61.7	61.7	62.6	62.6	63.5	64.5
47.5°	58.9	58.9	58.9	58.9	58.9	59.8	60.7	60.7	60.7	61.7	61.7
50°	57.0	57.0	57.0	57.0	57.0	57.9	57.9	58.9	58.9	59.8	60.7
52.5°	55.1	55.1	55.1	55.1	55.1	56.1	56.1	57.0	57.0	57.9	58.9
55°	54.2	54.2	54.2	53.3	53.3	54.2	54.2	55.1	55.1	56.1	56.1
57.5°	51.4	51.4	51.4	51.4	51.4	51.4	51.4	52.3	52.3	53.3	54.2
60°	50.5	50.5	49.5	49.5	48.6	49.5	49.5	50.5	50.5	51.4	51.4
62.5°	47.7	47.7	47.7	46.7	46.7	47.7	47.7	47.7	47.7	48.6	49.5
65°	44.9	44.9	44.9	43.9	43.9	44.9	44.9	44.9	44.9	45.8	46.7
67.5°	42.0	42.0	42.0	41.1	41.1	41.1	41.1	42.0	42.0	43.0	43.9
70°	39.2	39.2	39.2	38.3	38.3	38.3	37.4	38.3	39.2	40.2	40.2
72.5°	36.4	36.4	36.4	35.5	35.5	35.5	34.6	35.5	35.5	36.4	36.4
75°	31.8	31.8	31.8	31.8	31.8	31.8	30.8	30.8	30.8	31.8	31.8
77.5°	29.0	29.0	29.0	28.0	28.0	28.0	27.1	27.1	27.1	28.0	28.0
80°	24.3	24.3	24.3	23.4	23.4	23.4	22.4	22.4	22.4	23.4	23.4
82.5°	19.6	19.6	19.6	18.7	18.7	18.7	17.8	17.8	17.8	18.7	18.7
85°	15.9	15.9	15.9	15.9	15.9	15.9	15.0	15.0	15.0	15.9	16.8
87.5°	7.5	7.5	8.4	8.4	8.4	8.4	7.5	7.5	6.5	6.5	7.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676020  
 CATALOG NUMBER: CCW-SA-1B-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676020  
 CATALOG NUMBER: CCW-SA-1B-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8
2.5°	612.1	613.9	618.6	622.3	627.0	630.7	633.5	637.3	640.1	642.9	644.8
5°	527.0	528.0	532.6	537.3	541.0	545.7	552.3	558.8	565.3	571.9	576.5
7.5°	410.2	414.0	419.6	426.1	431.7	437.3	443.9	451.3	457.9	464.4	471.0
10°	319.6	323.3	328.9	334.5	339.2	344.8	352.3	359.8	367.2	374.7	382.2
12.5°	268.2	272.9	279.4	285.9	291.5	298.1	307.4	315.8	325.2	333.6	342.9
15°	226.1	231.7	240.1	249.5	257.9	266.3	275.7	285.0	293.4	302.8	312.1
17.5°	186.0	191.6	199.0	207.4	214.9	222.4	233.6	243.9	255.1	265.4	275.7
20°	149.5	152.3	159.8	167.3	174.7	182.2	190.6	199.0	207.4	215.9	228.9
22.5°	124.3	126.1	129.9	132.7	136.4	139.2	147.6	156.1	163.5	171.9	184.1
25°	109.3	110.3	113.1	114.9	117.7	119.6	125.2	129.9	135.5	140.2	151.4
27.5°	101.9	102.8	103.7	104.7	105.6	106.5	110.3	114.0	116.8	120.5	130.8
30°	100.0	100.9	103.7	105.6	108.4	110.3	112.1	114.0	115.9	117.7	124.3
32.5°	98.1	99.0	99.0	98.1	98.1	97.2	99.0	100.0	101.9	102.8	108.4
35°	77.6	77.6	78.5	79.4	80.4	81.3	84.1	86.0	88.8	90.6	95.3
37.5°	72.9	72.9	73.8	75.7	76.6	77.6	79.4	81.3	83.2	85.0	89.7
40°	70.1	71.0	72.0	72.9	73.8	74.8	76.6	77.6	79.4	80.4	84.1
42.5°	67.3	67.3	68.2	70.1	71.0	72.0	73.8	74.8	76.6	77.6	81.3
45°	65.4	66.3	67.3	68.2	68.2	69.1	71.0	72.9	73.8	75.7	79.4
47.5°	62.6	62.6	64.5	65.4	67.3	68.2	70.1	71.0	72.9	73.8	77.6
50°	60.7	61.7	63.5	64.5	66.3	67.3	70.1	72.0	74.8	76.6	78.5
52.5°	58.9	59.8	61.7	62.6	64.5	65.4	69.1	72.9	75.7	79.4	79.4
55°	57.0	57.0	58.9	61.7	63.5	65.4	67.3	70.1	72.0	73.8	73.8
57.5°	54.2	55.1	57.0	59.8	61.7	63.5	65.4	67.3	68.2	70.1	69.1
60°	52.3	52.3	55.1	57.9	60.7	63.5	63.5	63.5	62.6	62.6	62.6
62.5°	49.5	50.5	54.2	58.9	62.6	66.3	63.5	60.7	57.9	55.1	56.1
65°	47.7	48.6	50.5	53.3	55.1	57.0	55.1	54.2	52.3	50.5	51.4
67.5°	43.9	44.9	45.8	45.8	46.7	46.7	46.7	46.7	46.7	46.7	47.7
70°	41.1	41.1	41.1	42.0	42.0	42.0	42.0	42.0	42.0	42.0	43.0
72.5°	37.4	37.4	37.4	37.4	37.4	37.4	37.4	37.4	37.4	37.4	38.3
75°	32.7	32.7	32.7	32.7	32.7	32.7	32.7	32.7	32.7	32.7	33.6
77.5°	29.0	29.0	29.0	29.0	29.0	29.0	29.0	29.0	28.0	28.0	29.0
80°	24.3	24.3	24.3	24.3	23.4	23.4	23.4	23.4	23.4	23.4	24.3
82.5°	19.6	19.6	19.6	19.6	18.7	18.7	18.7	18.7	17.8	17.8	18.7
85°	17.8	18.7	18.7	19.6	19.6	19.6	18.7	17.8	16.8	15.9	15.9
87.5°	7.5	7.5	7.5	7.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676020  
 CATALOG NUMBER: CCW-SA-1B-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676020  
 CATALOG NUMBER: CCW-SA-1B-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8
2.5°	647.6	649.4	651.3	654.1	657.8	660.6	663.4	669.1	675.6	681.2	686.8
5°	581.2	585.9	590.6	596.2	601.8	606.4	612.1	623.3	634.5	644.8	656.0
7.5°	476.6	483.1	488.7	498.1	506.5	515.8	524.2	538.2	551.3	565.3	578.4
10°	389.7	397.1	404.6	416.8	429.8	442.0	454.1	465.3	477.5	488.7	499.9
12.5°	352.3	360.7	370.0	377.5	385.9	393.4	400.9	414.0	427.0	440.1	453.2
15°	321.4	330.8	340.1	349.5	357.9	367.2	375.6	386.9	399.0	410.2	421.4
17.5°	285.9	295.3	305.6	315.8	326.1	336.4	346.7	362.6	378.4	393.4	409.3
20°	241.1	254.2	266.3	280.3	294.3	308.4	322.4	339.2	356.0	371.9	388.7
22.5°	196.2	208.4	220.5	237.3	254.2	270.1	286.9	309.3	330.8	353.2	374.7
25°	163.5	174.7	186.0	204.6	222.4	241.1	258.8	285.9	312.1	339.2	365.4
27.5°	141.1	151.4	161.7	181.3	200.9	219.6	239.2	269.1	298.1	328.0	357.0
30°	130.8	137.4	143.9	162.6	181.3	199.0	217.7	246.7	275.7	304.6	333.6
32.5°	114.0	119.6	125.2	142.0	158.9	174.7	191.6	221.5	250.4	280.3	309.3
35°	100.9	105.6	110.3	126.1	141.1	157.0	171.9	201.8	231.7	261.6	291.5
37.5°	93.4	98.1	101.9	115.9	130.8	144.8	158.9	188.8	217.7	247.6	276.6
40°	87.8	90.6	94.4	108.4	121.5	135.5	148.6	175.7	203.7	230.8	257.9
42.5°	84.1	87.8	90.6	102.8	115.9	128.0	140.2	166.3	192.5	217.7	243.9
45°	83.2	86.9	90.6	100.9	111.2	120.5	130.8	156.1	181.3	206.5	231.7
47.5°	81.3	84.1	87.8	96.2	103.7	112.1	119.6	144.8	170.1	194.4	219.6
50°	80.4	81.3	83.2	90.6	98.1	105.6	113.1	138.3	163.5	188.8	214.0
52.5°	79.4	79.4	79.4	86.0	92.5	98.1	104.7	129.9	156.1	181.3	206.5
55°	73.8	72.9	72.9	79.4	85.0	91.6	97.2	122.4	147.6	171.9	197.2
57.5°	68.2	67.3	66.3	72.0	77.6	83.2	88.8	114.0	140.2	165.4	190.6
60°	62.6	61.7	61.7	67.3	72.0	77.6	82.2	108.4	133.6	159.8	185.0
62.5°	56.1	57.0	57.0	61.7	67.3	72.0	76.6	102.8	129.9	156.1	182.2
65°	51.4	52.3	52.3	57.9	63.5	69.1	74.8	100.0	126.1	151.4	176.6
67.5°	47.7	48.6	48.6	55.1	60.7	67.3	72.9	95.3	118.7	141.1	163.5
70°	43.9	43.9	44.9	51.4	57.9	64.5	71.0	90.6	110.3	129.0	148.6
72.5°	39.2	40.2	41.1	47.7	53.3	59.8	65.4	83.2	100.9	118.7	136.4
75°	34.6	35.5	36.4	42.0	47.7	53.3	58.9	75.7	91.6	108.4	124.3
77.5°	30.8	31.8	32.7	37.4	42.0	46.7	51.4	63.5	76.6	88.8	100.9
80°	25.2	25.2	26.2	29.9	33.6	36.4	40.2	48.6	57.0	64.5	72.9
82.5°	18.7	19.6	19.6	22.4	24.3	27.1	29.0	33.6	37.4	42.0	45.8
85°	15.9	15.0	15.0	16.8	17.8	19.6	20.6	23.4	25.2	28.0	29.9
87.5°	6.5	5.6	5.6	6.5	8.4	9.3	10.3	10.3	11.2	11.2	11.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676020  
 CATALOG NUMBER: CCW-SA-1B-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P676020

CATALOG NUMBER: CCW-SA-1B-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8
2.5°	689.6	691.5	694.3	696.2	700.8	704.6	709.2	713.0	715.8	720.4	718.6
5°	664.4	672.8	681.2	689.6	696.2	702.7	708.3	714.8	722.3	736.3	740.1
7.5°	589.6	600.8	611.1	622.3	635.4	648.5	661.6	674.7	686.8	704.6	715.8
10°	515.8	531.7	546.6	562.5	574.7	586.8	598.0	610.2	627.0	644.8	665.3
12.5°	469.1	485.0	500.9	516.7	534.5	551.3	569.1	585.9	601.8	615.8	639.2
15°	438.2	456.0	472.8	489.6	511.1	531.7	553.2	573.7	597.1	615.8	631.7
17.5°	430.8	452.3	472.8	494.3	516.7	539.2	561.6	584.0	607.4	635.4	656.0
20°	417.7	446.7	475.6	504.6	533.6	561.6	590.6	618.6	649.4	683.1	692.4
22.5°	410.2	444.8	480.3	514.9	554.1	594.3	633.5	672.8	705.5	730.7	758.8
25°	409.3	452.3	496.2	539.2	588.7	637.3	686.8	735.4	777.4	802.7	825.1
27.5°	408.3	460.7	512.1	563.5	624.2	684.0	744.7	804.5	843.8	880.2	898.9
30°	397.1	459.7	523.3	585.9	654.1	722.3	790.5	858.7	898.9	924.2	933.5
32.5°	383.1	456.9	530.8	604.6	682.1	759.7	836.3	913.9	945.6	967.1	959.7
35°	371.9	453.2	533.6	613.9	696.2	779.3	861.5	943.8	989.6	1019.5	1007.3
37.5°	361.6	446.7	531.7	616.7	713.0	809.2	905.5	1001.7	1045.6	1077.4	1063.4
40°	349.5	440.1	531.7	622.3	732.6	841.9	952.2	1061.5	1118.5	1145.6	1124.1
42.5°	339.2	433.6	528.9	623.3	741.0	858.7	976.5	1094.2	1157.8	1196.1	1169.0
45°	326.1	420.5	513.9	608.3	738.2	868.1	997.0	1126.9	1200.7	1230.6	1193.3
47.5°	312.1	405.5	498.1	590.6	728.9	867.2	1005.5	1143.7	1212.0	1247.5	1212.9
50°	307.4	400.9	493.4	586.8	736.3	886.8	1036.3	1185.8	1235.3	1264.3	1218.5
52.5°	306.5	405.5	505.5	604.6	755.0	904.5	1055.0	1204.5	1244.7	1275.5	1234.4
55°	303.7	411.2	517.7	624.2	781.2	939.1	1096.1	1253.1	1293.3	1315.7	1284.8
57.5°	306.5	422.4	537.3	653.2	814.8	976.5	1138.1	1299.8	1348.4	1364.3	1357.7
60°	308.4	431.7	554.1	677.5	835.4	993.3	1151.2	1309.1	1359.6	1398.8	1406.3
62.5°	303.7	425.2	545.7	667.2	810.2	953.1	1096.1	1239.1	1322.2	1380.2	1413.8
65°	289.7	401.8	514.9	627.0	758.8	891.4	1023.2	1155.0	1242.8	1328.8	1355.9
67.5°	258.8	354.2	449.5	544.8	659.7	774.6	888.6	1003.6	1113.8	1197.0	1234.4
70°	224.3	299.0	374.7	449.5	554.1	658.8	763.4	868.1	965.3	1056.8	1092.4
72.5°	195.3	253.2	312.1	370.0	444.8	518.6	593.4	667.2	782.1	873.7	908.3
75°	166.3	208.4	249.5	291.5	342.9	394.3	444.8	496.2	577.5	659.7	694.3
77.5°	128.0	156.1	183.1	210.2	245.8	280.3	315.8	350.4	407.4	469.1	486.8
80°	88.8	104.7	119.6	135.5	163.5	191.6	219.6	247.6	285.0	319.6	346.7
82.5°	55.1	65.4	74.8	84.1	106.5	129.0	150.4	172.9	187.8	189.7	216.8
85°	35.5	42.0	47.7	53.3	66.3	80.4	93.4	106.5	95.3	88.8	105.6
87.5°	14.0	17.8	20.6	23.4	22.4	21.5	20.6	19.6	16.8	15.0	18.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676020  
 CATALOG NUMBER: CCW-SA-1B-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676020  
 CATALOG NUMBER: CCW-SA-1B-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8
2.5°	720.4	723.3	726.1	727.9	730.7	731.7	732.6	732.6	733.5	734.5	736.3
5°	755.0	760.6	766.2	770.9	776.5	781.2	784.9	789.6	793.3	793.3	792.4
7.5°	726.1	740.1	754.1	768.1	782.1	792.4	801.7	812.0	821.4	823.2	825.1
10°	687.7	702.7	716.7	731.7	745.7	761.6	776.5	791.5	807.4	810.2	813.9
12.5°	652.2	670.0	687.7	704.6	722.3	733.5	744.7	755.0	766.2	773.7	781.2
15°	651.3	666.3	681.2	695.2	710.2	716.7	723.3	728.9	735.4	735.4	736.3
17.5°	672.8	682.1	691.5	699.9	709.2	710.2	712.0	713.0	713.9	711.1	708.3
20°	714.8	718.6	722.3	726.1	729.8	723.3	717.6	711.1	704.6	697.1	690.5
22.5°	776.5	768.1	759.7	751.3	742.9	731.7	719.5	708.3	696.2	686.8	677.5
25°	834.4	824.2	813.9	803.6	793.3	769.0	744.7	719.5	695.2	684.9	674.7
27.5°	912.0	896.1	880.2	864.4	848.5	815.8	783.1	750.4	717.6	699.9	683.1
30°	930.7	912.9	895.2	876.5	858.7	827.0	796.1	764.4	732.6	712.0	692.4
32.5°	957.8	937.2	916.7	896.1	875.6	844.7	813.9	782.1	751.3	732.6	713.0
35°	1002.6	979.3	955.9	931.6	908.3	876.5	845.7	813.9	782.1	760.6	740.1
37.5°	1041.0	1013.9	986.8	959.7	932.6	904.5	875.6	847.5	818.6	797.1	776.5
40°	1083.9	1054.0	1024.1	995.2	965.3	939.1	912.9	885.8	859.7	842.9	826.0
42.5°	1121.3	1084.9	1049.4	1013.9	977.4	959.7	942.8	925.1	907.3	898.9	889.6
45°	1147.5	1113.8	1079.3	1045.6	1012.0	998.9	985.8	972.7	959.7	968.1	976.5
47.5°	1158.7	1131.6	1105.4	1079.3	1052.2	1056.8	1061.5	1065.3	1069.9	1081.1	1093.3
50°	1169.0	1154.0	1138.1	1123.2	1107.3	1125.1	1141.9	1159.6	1177.4	1200.7	1224.1
52.5°	1189.5	1181.1	1173.6	1165.2	1156.8	1187.7	1218.5	1249.3	1280.2	1306.3	1332.5
55°	1251.2	1244.7	1238.1	1230.6	1224.1	1268.0	1311.0	1354.9	1398.8	1425.9	1453.0
57.5°	1336.2	1332.5	1327.8	1324.1	1319.4	1362.4	1404.5	1446.5	1489.5	1515.7	1542.7
60°	1400.7	1401.7	1401.7	1402.6	1402.6	1435.3	1468.0	1501.6	1534.3	1556.8	1580.1
62.5°	1435.3	1433.4	1431.6	1429.7	1427.8	1454.9	1482.0	1509.1	1536.2	1553.0	1569.8
65°	1397.9	1408.2	1418.5	1428.7	1439.0	1442.8	1445.6	1449.3	1452.1	1462.4	1472.7
67.5°	1272.7	1293.3	1312.9	1333.4	1353.1	1339.0	1326.0	1311.9	1297.9	1300.7	1302.6
70°	1133.5	1156.8	1181.1	1204.5	1227.8	1195.1	1162.4	1128.8	1096.1	1084.9	1073.7
72.5°	955.9	976.5	998.0	1018.5	1039.1	998.9	959.7	919.5	879.3	859.7	840.1
75°	730.7	755.0	780.3	804.5	828.8	784.0	738.2	693.3	647.6	634.5	622.3
77.5°	532.6	561.6	590.6	619.5	648.5	608.3	568.1	527.0	486.8	479.4	471.9
80°	387.8	410.2	431.7	454.1	475.6	452.3	428.9	405.5	382.2	381.2	380.3
82.5°	261.6	281.3	300.0	319.6	338.3	328.9	320.5	311.2	301.8	311.2	321.4
85°	134.6	161.7	189.7	216.8	243.9	241.1	239.2	236.4	233.6	245.8	257.0
87.5°	27.1	50.5	73.8	96.2	119.6	114.0	108.4	101.9	96.2	100.0	102.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676020  
 CATALOG NUMBER: CCW-SA-1B-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676020

CATALOG NUMBER: CCW-SA-1B-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8
2.5°	737.3	738.2	738.2	738.2	738.2	738.2	736.3	735.4	733.5	731.7	728.9
5°	792.4	791.5	787.7	784.0	779.3	775.6	772.8	769.0	766.2	762.5	756.9
7.5°	827.0	828.8	822.3	816.7	810.2	803.6	797.1	790.5	784.0	777.4	764.4
10°	816.7	819.5	815.8	812.0	807.4	803.6	796.1	787.7	780.3	771.8	756.0
12.5°	787.7	795.2	793.3	791.5	789.6	787.7	783.1	777.4	772.8	767.2	749.4
15°	736.3	736.3	737.3	738.2	738.2	739.1	740.1	741.0	741.9	742.9	732.6
17.5°	705.5	702.7	702.7	702.7	702.7	702.7	706.4	711.1	714.8	718.6	715.8
20°	683.1	676.5	675.6	675.6	674.7	673.7	680.3	687.7	694.3	700.8	704.6
22.5°	668.1	658.8	657.8	656.9	656.0	655.0	663.4	671.9	680.3	688.7	701.8
25°	664.4	654.1	655.0	656.0	656.0	656.9	663.4	670.0	676.5	683.1	705.5
27.5°	665.3	648.5	649.4	650.4	650.4	651.3	661.6	670.9	681.2	690.5	718.6
30°	671.9	652.2	650.4	648.5	646.6	644.8	658.8	672.8	686.8	700.8	722.3
32.5°	694.3	675.6	670.9	666.3	661.6	656.9	673.7	689.6	706.4	722.3	740.1
35°	718.6	698.0	696.2	694.3	691.5	689.6	704.6	720.4	735.4	750.4	766.2
37.5°	755.0	734.5	732.6	729.8	727.9	725.1	741.9	757.8	774.6	790.5	804.5
40°	809.2	792.4	791.5	791.5	790.5	789.6	802.7	816.7	829.8	842.9	852.2
42.5°	881.2	872.8	875.6	879.3	882.1	884.9	895.2	906.4	916.7	927.0	924.2
45°	984.9	993.3	994.2	995.2	996.1	997.0	999.8	1003.6	1006.4	1009.2	998.0
47.5°	1104.5	1115.7	1121.3	1126.9	1131.6	1137.2	1133.5	1128.8	1125.1	1120.4	1092.4
50°	1246.5	1269.9	1269.0	1268.0	1266.2	1265.2	1257.7	1250.3	1241.9	1234.4	1193.3
52.5°	1358.7	1384.8	1389.5	1394.2	1398.8	1403.5	1389.5	1375.5	1360.5	1346.5	1295.1
55°	1479.2	1506.3	1507.2	1508.2	1508.2	1509.1	1489.5	1469.9	1449.3	1429.7	1376.4
57.5°	1568.9	1595.1	1592.3	1590.4	1587.6	1584.8	1561.4	1538.1	1514.7	1491.4	1438.1
60°	1602.6	1625.0	1619.4	1613.8	1607.2	1601.6	1583.9	1566.1	1547.4	1529.7	1478.3
62.5°	1586.7	1603.5	1595.1	1587.6	1579.2	1570.8	1548.4	1525.0	1502.6	1479.2	1441.8
65°	1482.0	1492.3	1481.1	1470.8	1460.5	1449.3	1430.6	1411.9	1392.3	1373.6	1348.4
67.5°	1305.4	1307.3	1306.3	1305.4	1304.5	1303.5	1276.4	1249.3	1221.3	1194.2	1192.3
70°	1063.4	1052.2	1054.0	1056.8	1058.7	1060.6	1040.0	1020.4	999.8	979.3	988.6
72.5°	820.4	800.8	805.5	811.1	815.8	820.4	803.6	787.7	770.9	754.1	767.2
75°	609.3	597.1	601.8	607.4	612.1	616.7	610.2	603.6	596.2	589.6	601.8
77.5°	464.4	456.9	457.9	457.9	458.8	458.8	459.7	461.6	462.5	463.5	476.6
80°	378.4	377.5	376.6	375.6	373.8	372.8	382.2	391.5	400.9	410.2	416.8
82.5°	330.8	340.1	334.5	329.9	324.2	318.6	327.1	335.5	343.9	352.3	349.5
85°	269.1	280.3	270.1	259.8	248.6	238.3	245.8	252.3	259.8	266.3	262.6
87.5°	106.5	109.3	92.5	76.6	59.8	43.0	68.2	92.5	117.7	142.0	145.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676020  
 CATALOG NUMBER: CCW-SA-1B-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676020

CATALOG NUMBER: CCW-SA-1B-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8
2.5°	726.1	722.3	719.5	718.6	716.7	715.8	713.9	712.0	709.2	707.4	704.6
5°	750.4	744.7	738.2	728.9	720.4	711.1	701.8	693.3	684.9	675.6	667.2
7.5°	751.3	738.2	725.1	713.0	699.9	687.7	674.7	663.4	651.3	639.2	627.9
10°	741.0	725.1	709.2	693.3	678.4	662.5	646.6	633.5	619.5	605.5	592.4
12.5°	732.6	714.8	697.1	678.4	660.6	642.0	623.3	610.2	597.1	584.0	570.9
15°	722.3	711.1	700.8	684.0	667.2	650.4	633.5	615.8	599.0	581.2	563.5
17.5°	713.9	711.1	708.3	697.1	685.9	673.7	662.5	644.8	627.0	608.3	590.6
20°	709.2	713.0	716.7	711.1	705.5	699.0	693.3	680.3	667.2	653.2	640.1
22.5°	714.8	728.9	741.9	742.9	744.7	745.7	746.6	734.5	722.3	709.2	697.1
25°	727.9	750.4	772.8	784.9	797.1	810.2	822.3	814.8	807.4	799.9	792.4
27.5°	745.7	773.7	801.7	819.5	836.3	854.1	871.8	870.9	870.0	868.1	867.2
30°	742.9	764.4	785.9	807.4	828.8	850.3	871.8	883.0	893.3	904.5	915.7
32.5°	758.8	776.5	795.2	817.6	840.1	863.4	885.8	909.2	931.6	955.0	978.4
35°	783.1	798.9	815.8	840.1	865.3	889.6	914.8	942.8	971.8	1000.8	1028.8
37.5°	819.5	833.5	848.5	869.0	890.5	911.1	932.6	973.7	1014.8	1056.8	1098.0
40°	861.5	870.9	880.2	899.9	919.5	939.1	958.7	1010.1	1061.5	1112.9	1164.3
42.5°	922.3	919.5	916.7	932.6	949.4	965.3	982.1	1028.8	1075.5	1122.3	1169.0
45°	986.8	975.5	964.3	971.8	980.2	987.7	996.1	1043.8	1091.4	1140.0	1187.7
47.5°	1064.3	1036.3	1008.3	1001.7	995.2	987.7	981.2	1032.5	1083.9	1136.3	1187.7
50°	1152.2	1110.1	1069.0	1052.2	1034.4	1017.6	999.8	1041.9	1084.9	1127.9	1169.9
52.5°	1243.7	1191.4	1140.0	1113.8	1087.7	1060.6	1034.4	1069.9	1106.4	1142.8	1178.3
55°	1322.2	1269.0	1214.8	1183.9	1153.1	1122.3	1091.4	1126.9	1162.4	1197.9	1233.5
57.5°	1384.8	1331.6	1278.3	1249.3	1219.4	1190.5	1160.6	1194.2	1228.8	1263.4	1297.0
60°	1427.8	1376.4	1325.0	1297.0	1269.0	1240.9	1212.9	1253.1	1293.3	1334.4	1374.6
62.5°	1405.4	1368.0	1330.6	1318.5	1306.3	1293.3	1281.1	1319.4	1356.8	1395.1	1433.4
65°	1323.2	1297.9	1272.7	1284.8	1297.9	1310.1	1323.2	1348.4	1373.6	1399.8	1425.0
67.5°	1189.5	1187.7	1184.9	1212.0	1239.1	1267.1	1294.2	1311.0	1326.9	1343.7	1360.5
70°	998.0	1008.3	1017.6	1064.3	1111.0	1157.8	1204.5	1211.0	1217.6	1224.1	1230.6
72.5°	781.2	794.3	808.3	870.0	930.7	992.4	1054.0	1050.3	1046.6	1041.9	1038.2
75°	614.9	627.0	640.1	697.1	754.1	811.1	868.1	852.2	837.3	821.4	805.5
77.5°	490.6	503.7	517.7	570.9	624.2	678.4	731.7	693.3	655.0	616.7	578.4
80°	422.4	428.9	434.5	471.0	506.5	542.9	579.3	540.1	499.9	459.7	420.5
82.5°	346.7	342.9	340.1	361.6	383.1	404.6	426.1	388.7	351.3	313.0	275.7
85°	258.8	255.1	251.4	262.6	273.8	285.9	297.1	254.2	211.2	167.3	124.3
87.5°	150.4	154.2	157.9	170.1	182.2	195.3	207.4	163.5	119.6	74.8	30.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676020  
 CATALOG NUMBER: CCW-SA-1B-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P676020  
 CATALOG NUMBER: CCW-SA-1B-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
0°	672.8	672.8
2.5°	699.0	694.3
5°	660.6	654.1
7.5°	618.6	610.2
10°	580.3	569.1
12.5°	556.0	542.0
15°	546.6	529.8
17.5°	574.7	558.8
20°	617.7	596.2
22.5°	670.0	643.8
25°	760.6	728.9
27.5°	834.4	801.7
30°	880.2	844.7
32.5°	930.7	884.0
35°	983.0	938.2
37.5°	1046.6	996.1
40°	1112.0	1059.6
42.5°	1134.4	1100.8
45°	1155.9	1124.1
47.5°	1160.6	1134.4
50°	1165.2	1161.5
52.5°	1178.3	1177.4
55°	1234.4	1235.3
57.5°	1303.5	1309.1
60°	1367.1	1360.5
62.5°	1399.8	1366.1
65°	1377.4	1330.6
67.5°	1310.1	1259.6
70°	1162.4	1094.2
72.5°	978.4	918.5
75°	754.1	703.6
77.5°	536.4	494.3
80°	377.5	335.5
82.5°	242.0	208.4
85°	109.3	95.3
87.5°	30.8	29.9
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P676020  
CATALOG NUMBER: CCW-SA-1B-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)