

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P676047

Luminaire Tested: **CCW-SA-2A-835-U-SLR**

Issue Date: 04/25/2023



Test Information

Test Method: LM-79-08
Report Number: P676047
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-2A-835-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @350mA w/
SLR distribution lens
Light Source: (32) 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3741.6 lumens
Efficiency: N/A
Efficacy: 103.4 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2

Input Watts (W): 36.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P676047
 CATALOG NUMBER: CCW-SA-2A-835-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 5.3 fc
 Type IV - Short - N/A

REPORT NUMBER: P676047
CATALOG NUMBER: CCW-SA-2A-835-U-SLR

Luminous Intensity Polar Plot



— Vertical Plane Through 305-Deg Lateral - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P676047

CATALOG NUMBER: CCW-SA-2A-835-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	769.9	0.0	769.9
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	2971.7	0.0	2971.7
	% Fixture	79.4	0.0	79.4
Total	Lumens	3741.6	0.0	3741.6
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.8	2.5
10°-20°	196.0	5.2
20°-30°	286.8	7.7
30°-40°	404.0	10.8
40°-50°	555.2	14.8
50°-60°	756.7	20.2
60°-70°	828.3	22.1
70°-80°	478.3	12.8
80°-90°	143.4	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3741.6	100.0
0°-180°	3741.6	100.0




REPORT NUMBER: P676047
 CATALOG NUMBER: CCW-SA-2A-835-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	384.3	10.3			
FM (30°-60°)	1365.4	36.5			
FH (60°-80°)	1100.2	29.4			G1/1800
FVH (80°-90°)	121.8	3.3			G2/225
BL (0°-30°)	191.4	5.1	B1/500		
BM (30°-60°)	350.6	9.4	B1/1000		
BH (60°-80°)	206.3	5.5	B1/500		G1/500
BVH (80°-90°)	21.6	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P676047

CATALOG NUMBER: CCW-SA-2A-835-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8
2.5°	1233.0	1226.4	1221.4	1216.4	1209.8	1204.8	1198.1	1191.5	1183.2	1176.6	1168.3
5°	1161.6	1141.7	1121.8	1110.2	1096.9	1085.3	1072.0	1057.1	1042.2	1025.6	1010.6
7.5°	1083.6	1058.8	1033.9	1013.9	992.4	972.5	950.9	932.6	914.4	896.1	877.9
10°	1010.6	987.4	964.2	939.3	912.7	887.8	861.3	836.4	811.5	786.6	761.7
12.5°	962.5	934.3	907.7	879.5	853.0	824.8	796.6	773.3	750.1	725.2	702.0
15°	940.9	914.4	889.5	861.3	833.1	804.9	776.6	750.1	725.2	698.6	672.1
17.5°	992.4	954.2	916.0	879.5	843.0	806.5	770.0	736.8	703.6	670.4	637.2
20°	1058.8	1010.6	964.2	919.4	872.9	828.1	781.6	735.2	688.7	642.2	595.8
22.5°	1143.4	1088.6	1035.5	977.4	917.7	859.6	799.9	741.8	683.7	624.0	565.9
25°	1294.4	1229.7	1165.0	1082.0	997.4	914.4	829.7	753.4	678.7	602.4	526.1
27.5°	1423.8	1335.9	1249.6	1150.0	1050.5	950.9	851.3	763.4	677.1	589.1	501.2
30°	1500.2	1413.9	1327.6	1206.4	1087.0	965.8	844.7	746.8	650.5	552.6	454.7
32.5°	1569.9	1473.6	1377.4	1244.6	1110.2	977.4	843.0	735.2	628.9	521.1	413.2
35°	1666.1	1559.9	1455.4	1301.0	1146.7	992.4	838.0	726.9	614.0	502.8	390.0
37.5°	1769.0	1637.9	1508.5	1337.5	1166.6	995.7	824.8	715.2	605.7	496.2	386.7
40°	1881.9	1722.5	1564.9	1375.7	1188.2	999.0	809.8	700.3	590.8	479.6	370.1
42.5°	1954.9	1782.3	1609.7	1405.6	1203.1	999.0	794.9	687.0	579.2	469.6	361.8
45°	1996.4	1828.8	1662.8	1442.1	1221.4	1000.7	780.0	673.8	567.5	459.7	353.5
47.5°	2014.6	1858.6	1702.6	1470.3	1239.6	1007.3	775.0	667.1	557.6	449.7	340.2
50°	2062.7	1925.0	1787.3	1538.3	1291.1	1042.2	793.2	677.1	562.6	446.4	330.2
52.5°	2091.0	1973.1	1855.3	1599.7	1344.2	1088.6	833.1	703.6	574.2	444.7	315.3
55°	2193.8	2081.0	1968.2	1696.0	1422.2	1150.0	876.2	733.5	590.8	446.4	303.7
57.5°	2324.9	2205.5	2087.6	1793.9	1500.2	1206.4	912.7	760.0	605.7	453.0	298.7
60°	2416.2	2300.0	2185.5	1873.6	1559.9	1247.9	934.3	775.0	615.7	454.7	295.4
62.5°	2426.2	2276.8	2129.1	1825.4	1521.7	1216.4	912.7	758.4	604.1	448.1	293.7
65°	2363.1	2188.9	2014.6	1724.2	1433.8	1143.4	853.0	711.9	570.9	428.1	287.1
67.5°	2237.0	2032.9	1828.8	1563.2	1297.7	1032.2	766.7	645.5	526.1	404.9	283.8
70°	1943.3	1764.0	1586.5	1355.8	1126.8	896.1	665.5	565.9	468.0	368.4	268.8
72.5°	1631.3	1463.7	1297.7	1110.2	924.3	736.8	549.3	474.6	399.9	323.6	248.9
75°	1249.6	1123.5	999.0	859.6	720.2	579.2	439.8	385.0	330.2	275.5	220.7
77.5°	877.9	809.8	743.4	638.9	534.4	429.8	325.3	288.8	252.2	215.7	179.2
80°	595.8	557.6	521.1	446.4	371.7	295.4	220.7	197.5	172.6	149.4	124.5
82.5°	370.1	368.4	365.1	313.6	262.2	210.8	159.3	139.4	121.1	101.2	81.3
85°	169.3	197.5	224.0	195.8	167.6	139.4	111.2	97.9	84.6	69.7	56.4
87.5°	53.1	64.7	74.7	71.4	66.4	63.1	58.1	49.8	41.5	33.2	24.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676047
 CATALOG NUMBER: CCW-SA-2A-835-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676047
 CATALOG NUMBER: CCW-SA-2A-835-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8
2.5°	1161.6	1156.7	1150.0	1143.4	1135.1	1128.5	1120.2	1111.9	1110.2	1106.9	1105.2
5°	1000.7	990.7	979.1	969.1	959.2	947.6	937.6	926.0	917.7	907.7	899.4
7.5°	859.6	843.0	824.8	806.5	789.9	773.3	755.1	738.5	730.2	721.9	713.6
10°	746.8	730.2	715.2	698.6	687.0	677.1	665.5	653.8	643.9	633.9	624.0
12.5°	690.3	678.7	667.1	655.5	642.2	630.6	617.3	604.1	592.4	582.5	570.9
15°	655.5	638.9	620.6	604.1	585.8	569.2	550.9	532.7	519.4	507.8	494.5
17.5°	614.0	589.1	565.9	541.0	521.1	501.2	479.6	459.7	444.7	428.1	413.2
20°	567.5	539.3	509.5	481.3	458.0	436.4	413.2	390.0	373.4	355.1	338.5
22.5°	527.7	491.2	453.0	414.9	390.0	365.1	338.5	313.6	298.7	282.1	267.2
25°	484.6	444.7	403.3	361.8	336.9	310.3	285.4	258.9	247.3	237.3	225.7
27.5°	461.3	421.5	380.0	340.2	317.0	292.1	268.8	243.9	235.6	225.7	217.4
30°	414.9	376.7	336.9	297.0	280.5	265.5	248.9	232.3	229.0	227.3	224.0
32.5°	373.4	333.6	293.7	253.9	239.0	224.0	209.1	194.2	192.5	189.2	187.5
35°	351.8	313.6	273.8	235.6	222.4	207.4	194.2	179.2	175.9	170.9	167.6
37.5°	346.8	307.0	265.5	225.7	212.4	199.1	184.2	170.9	167.6	164.3	161.0
40°	333.6	295.4	258.9	220.7	207.4	194.2	179.2	165.9	162.6	159.3	156.0
42.5°	323.6	287.1	248.9	210.8	199.1	187.5	174.2	162.6	159.3	156.0	151.0
45°	315.3	277.1	237.3	199.1	190.8	182.5	172.6	164.3	161.0	156.0	152.7
47.5°	302.0	265.5	227.3	189.2	180.9	174.2	165.9	157.7	154.3	151.0	147.7
50°	292.1	253.9	215.7	177.6	170.9	164.3	157.7	151.0	151.0	152.7	152.7
52.5°	278.8	242.3	205.8	169.3	162.6	156.0	149.4	142.7	144.4	146.0	147.7
55°	267.2	232.3	195.8	159.3	152.7	146.0	137.7	131.1	132.8	134.4	136.1
57.5°	262.2	225.7	189.2	152.7	146.0	137.7	131.1	122.8	122.8	122.8	122.8
60°	258.9	220.7	184.2	146.0	137.7	131.1	122.8	114.5	112.8	112.8	111.2
62.5°	257.2	219.1	182.5	144.4	134.4	126.1	116.2	106.2	104.5	102.9	101.2
65°	250.6	215.7	179.2	142.7	131.1	121.1	109.5	97.9	96.3	96.3	94.6
67.5°	248.9	212.4	177.6	141.1	129.4	116.2	104.5	91.3	89.6	88.0	86.3
70°	235.6	204.1	170.9	137.7	124.5	112.8	99.6	86.3	84.6	81.3	79.7
72.5°	219.1	190.8	161.0	131.1	117.8	104.5	91.3	78.0	76.3	74.7	71.4
75°	194.2	167.6	141.1	114.5	102.9	92.9	81.3	69.7	68.0	66.4	63.1
77.5°	159.3	137.7	117.8	96.3	88.0	79.7	71.4	63.1	61.4	59.7	56.4
80°	112.8	99.6	88.0	74.7	69.7	63.1	58.1	51.4	51.4	49.8	49.8
82.5°	74.7	68.0	61.4	54.8	51.4	48.1	44.8	41.5	41.5	39.8	39.8
85°	53.1	49.8	44.8	41.5	39.8	36.5	34.8	31.5	31.5	31.5	31.5
87.5°	24.9	24.9	23.2	23.2	21.6	21.6	19.9	18.3	18.3	18.3	18.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676047
 CATALOG NUMBER: CCW-SA-2A-835-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676047

CATALOG NUMBER: CCW-SA-2A-835-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8
2.5°	1101.9	1096.9	1091.9	1085.3	1080.3	1073.7	1065.4	1058.8	1050.5	1050.5	1048.8
5°	889.5	884.5	879.5	872.9	867.9	861.3	856.3	849.7	843.0	843.0	841.4
7.5°	705.3	695.3	685.4	673.8	663.8	657.2	650.5	642.2	635.6	630.6	625.6
10°	614.0	604.1	592.4	582.5	570.9	562.6	554.3	544.3	536.0	529.4	522.7
12.5°	559.2	547.6	536.0	524.4	512.8	501.2	491.2	479.6	468.0	459.7	451.4
15°	481.3	469.6	458.0	446.4	434.8	421.5	408.2	393.3	380.0	373.4	368.4
17.5°	396.6	385.0	371.7	360.1	346.8	336.9	326.9	317.0	307.0	300.4	295.4
20°	320.3	307.0	293.7	280.5	267.2	260.5	253.9	247.3	240.6	235.6	232.3
22.5°	250.6	242.3	235.6	227.3	219.1	214.1	210.8	205.8	200.8	200.8	200.8
25°	214.1	209.1	205.8	200.8	195.8	194.2	192.5	189.2	187.5	185.9	185.9
27.5°	207.4	202.5	197.5	192.5	187.5	185.9	184.2	180.9	179.2	179.2	179.2
30°	220.7	219.1	217.4	215.7	214.1	210.8	205.8	202.5	197.5	194.2	190.8
32.5°	184.2	182.5	182.5	180.9	179.2	182.5	184.2	187.5	189.2	190.8	192.5
35°	162.6	159.3	156.0	152.7	149.4	147.7	146.0	144.4	142.7	142.7	141.1
37.5°	157.7	154.3	151.0	147.7	144.4	142.7	141.1	139.4	137.7	137.7	136.1
40°	152.7	149.4	147.7	144.4	141.1	139.4	137.7	134.4	132.8	131.1	131.1
42.5°	147.7	146.0	142.7	141.1	137.7	136.1	134.4	131.1	129.4	127.8	126.1
45°	147.7	144.4	141.1	137.7	134.4	132.8	129.4	127.8	124.5	124.5	122.8
47.5°	144.4	141.1	137.7	134.4	131.1	129.4	126.1	124.5	121.1	119.5	117.8
50°	152.7	147.7	141.1	136.1	129.4	127.8	124.5	122.8	119.5	117.8	116.2
52.5°	149.4	144.4	137.7	132.8	126.1	122.8	121.1	117.8	114.5	112.8	111.2
55°	137.7	132.8	129.4	124.5	119.5	116.2	112.8	109.5	106.2	104.5	104.5
57.5°	122.8	121.1	119.5	117.8	116.2	112.8	109.5	104.5	101.2	99.6	97.9
60°	109.5	111.2	112.8	114.5	116.2	111.2	106.2	101.2	96.3	94.6	92.9
62.5°	99.6	102.9	106.2	107.9	111.2	106.2	101.2	96.3	91.3	89.6	88.0
65°	92.9	94.6	94.6	96.3	96.3	92.9	91.3	88.0	84.6	83.0	83.0
67.5°	84.6	84.6	84.6	83.0	83.0	81.3	81.3	79.7	78.0	76.3	76.3
70°	76.3	76.3	76.3	74.7	74.7	73.0	73.0	71.4	69.7	69.7	68.0
72.5°	69.7	69.7	68.0	68.0	66.4	66.4	66.4	64.7	64.7	63.1	63.1
75°	61.4	61.4	59.7	59.7	58.1	58.1	58.1	56.4	56.4	56.4	54.8
77.5°	54.8	54.8	53.1	53.1	51.4	51.4	51.4	49.8	49.8	48.1	48.1
80°	48.1	48.1	46.5	46.5	44.8	44.8	43.1	43.1	41.5	41.5	39.8
82.5°	38.2	38.2	38.2	38.2	38.2	36.5	36.5	34.8	33.2	33.2	31.5
85°	31.5	31.5	31.5	29.9	29.9	29.9	28.2	28.2	26.6	24.9	24.9
87.5°	18.3	18.3	18.3	16.6	16.6	16.6	16.6	16.6	16.6	16.6	14.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676047
 CATALOG NUMBER: CCW-SA-2A-835-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676047

CATALOG NUMBER: CCW-SA-2A-835-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8
2.5°	1048.8	1047.1	1040.5	1033.9	1040.5	1047.1	1047.1	1047.1	1045.5	1045.5	1045.5
5°	841.4	839.7	836.4	833.1	833.1	831.4	834.7	838.0	841.4	844.7	848.0
7.5°	619.0	614.0	609.0	604.1	607.4	609.0	614.0	617.3	622.3	625.6	633.9
10°	516.1	509.5	504.5	499.5	496.2	492.9	489.5	487.9	484.6	481.3	484.6
12.5°	441.4	433.1	424.8	414.9	413.2	411.6	408.2	404.9	401.6	398.3	396.6
15°	361.8	355.1	351.8	346.8	340.2	333.6	330.2	328.6	325.3	321.9	320.3
17.5°	288.8	282.1	277.1	272.2	270.5	267.2	267.2	267.2	267.2	267.2	267.2
20°	227.3	222.4	222.4	220.7	220.7	219.1	220.7	222.4	222.4	224.0	225.7
22.5°	199.1	199.1	197.5	195.8	197.5	197.5	199.1	200.8	202.5	204.1	205.8
25°	184.2	182.5	184.2	185.9	185.9	185.9	187.5	187.5	189.2	189.2	189.2
27.5°	177.6	177.6	179.2	179.2	180.9	180.9	180.9	179.2	179.2	177.6	177.6
30°	187.5	184.2	184.2	184.2	182.5	180.9	179.2	179.2	177.6	175.9	174.2
32.5°	194.2	195.8	194.2	190.8	189.2	185.9	184.2	180.9	179.2	175.9	172.6
35°	141.1	139.4	142.7	144.4	146.0	147.7	149.4	151.0	151.0	152.7	152.7
37.5°	136.1	134.4	134.4	132.8	132.8	132.8	132.8	132.8	131.1	131.1	132.8
40°	129.4	127.8	127.8	126.1	126.1	124.5	124.5	124.5	124.5	124.5	124.5
42.5°	124.5	122.8	122.8	122.8	122.8	121.1	121.1	119.5	119.5	117.8	117.8
45°	122.8	121.1	119.5	117.8	117.8	116.2	116.2	116.2	114.5	114.5	114.5
47.5°	116.2	114.5	114.5	112.8	112.8	111.2	111.2	111.2	109.5	109.5	109.5
50°	112.8	111.2	111.2	109.5	109.5	107.9	107.9	107.9	106.2	106.2	106.2
52.5°	107.9	106.2	106.2	106.2	104.5	102.9	102.9	102.9	101.2	101.2	101.2
55°	102.9	101.2	101.2	101.2	99.6	97.9	97.9	97.9	96.3	96.3	96.3
57.5°	96.3	94.6	94.6	92.9	92.9	92.9	92.9	92.9	91.3	91.3	91.3
60°	91.3	89.6	89.6	88.0	88.0	86.3	86.3	86.3	86.3	86.3	86.3
62.5°	86.3	84.6	83.0	81.3	83.0	83.0	83.0	83.0	81.3	81.3	81.3
65°	81.3	79.7	78.0	76.3	76.3	76.3	76.3	76.3	76.3	76.3	76.3
67.5°	74.7	73.0	71.4	69.7	71.4	71.4	71.4	71.4	71.4	71.4	71.4
70°	68.0	66.4	66.4	64.7	64.7	63.1	63.1	64.7	64.7	64.7	64.7
72.5°	61.4	59.7	59.7	58.1	58.1	58.1	58.1	58.1	58.1	58.1	58.1
75°	54.8	53.1	53.1	51.4	51.4	51.4	51.4	51.4	51.4	51.4	51.4
77.5°	46.5	44.8	44.8	44.8	44.8	44.8	44.8	46.5	46.5	46.5	46.5
80°	39.8	38.2	38.2	38.2	38.2	38.2	38.2	38.2	38.2	38.2	38.2
82.5°	31.5	29.9	29.9	29.9	29.9	29.9	29.9	29.9	29.9	29.9	29.9
85°	23.2	21.6	21.6	21.6	23.2	23.2	23.2	23.2	23.2	23.2	23.2
87.5°	14.9	13.3	13.3	13.3	14.9	14.9	14.9	14.9	13.3	13.3	13.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676047
 CATALOG NUMBER: CCW-SA-2A-835-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676047
 CATALOG NUMBER: CCW-SA-2A-835-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8
2.5°	1045.5	1045.5	1045.5	1043.8	1042.2	1040.5	1038.8	1043.8	1047.1	1052.1	1055.4
5°	849.7	853.0	854.6	859.6	864.6	869.6	874.5	877.9	881.2	882.8	886.2
7.5°	640.6	648.9	655.5	662.1	668.8	673.8	680.4	685.4	690.3	695.3	700.3
10°	486.2	489.5	491.2	497.8	502.8	509.5	514.4	519.4	524.4	527.7	532.7
12.5°	395.0	391.6	390.0	390.0	390.0	390.0	390.0	393.3	396.6	399.9	403.3
15°	318.6	317.0	315.3	313.6	312.0	308.7	307.0	310.3	313.6	317.0	320.3
17.5°	267.2	267.2	267.2	265.5	263.9	262.2	260.5	262.2	263.9	263.9	265.5
20°	229.0	230.7	232.3	234.0	234.0	235.6	235.6	237.3	239.0	239.0	240.6
22.5°	205.8	207.4	207.4	207.4	209.1	209.1	209.1	210.8	212.4	214.1	215.7
25°	187.5	187.5	185.9	185.9	187.5	187.5	187.5	187.5	189.2	189.2	189.2
27.5°	177.6	175.9	175.9	175.9	175.9	174.2	174.2	174.2	174.2	174.2	174.2
30°	172.6	170.9	169.3	167.6	167.6	165.9	164.3	164.3	164.3	164.3	164.3
32.5°	170.9	167.6	164.3	162.6	162.6	161.0	159.3	157.7	157.7	156.0	154.3
35°	152.7	151.0	151.0	149.4	147.7	146.0	144.4	144.4	144.4	142.7	142.7
37.5°	132.8	134.4	134.4	134.4	136.1	136.1	136.1	136.1	137.7	137.7	137.7
40°	124.5	124.5	124.5	126.1	127.8	127.8	129.4	129.4	131.1	131.1	131.1
42.5°	117.8	116.2	116.2	117.8	117.8	119.5	119.5	121.1	122.8	122.8	124.5
45°	114.5	112.8	112.8	112.8	112.8	111.2	111.2	112.8	114.5	116.2	117.8
47.5°	107.9	107.9	106.2	106.2	106.2	106.2	106.2	106.2	107.9	107.9	107.9
50°	104.5	104.5	102.9	102.9	102.9	102.9	102.9	102.9	102.9	102.9	102.9
52.5°	101.2	99.6	99.6	99.6	99.6	97.9	97.9	97.9	97.9	97.9	97.9
55°	96.3	94.6	94.6	94.6	94.6	94.6	94.6	94.6	96.3	96.3	96.3
57.5°	91.3	89.6	89.6	89.6	91.3	91.3	91.3	91.3	92.9	92.9	92.9
60°	86.3	86.3	86.3	86.3	86.3	86.3	86.3	88.0	88.0	89.6	89.6
62.5°	81.3	81.3	81.3	81.3	83.0	83.0	83.0	83.0	84.6	84.6	84.6
65°	76.3	76.3	76.3	76.3	78.0	78.0	78.0	78.0	78.0	78.0	78.0
67.5°	71.4	71.4	71.4	71.4	71.4	71.4	71.4	73.0	73.0	74.7	74.7
70°	64.7	63.1	63.1	64.7	64.7	66.4	66.4	68.0	68.0	69.7	69.7
72.5°	58.1	58.1	58.1	58.1	58.1	58.1	58.1	59.7	61.4	61.4	63.1
75°	51.4	51.4	51.4	51.4	53.1	53.1	53.1	54.8	54.8	56.4	56.4
77.5°	46.5	44.8	44.8	44.8	46.5	46.5	46.5	48.1	48.1	49.8	49.8
80°	38.2	38.2	38.2	38.2	39.8	39.8	39.8	39.8	41.5	41.5	41.5
82.5°	31.5	31.5	31.5	31.5	31.5	31.5	31.5	31.5	33.2	33.2	33.2
85°	23.2	23.2	23.2	23.2	24.9	24.9	24.9	24.9	24.9	24.9	24.9
87.5°	14.9	14.9	14.9	14.9	14.9	14.9	14.9	14.9	16.6	16.6	16.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676047
 CATALOG NUMBER: CCW-SA-2A-835-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676047
 CATALOG NUMBER: CCW-SA-2A-835-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8
2.5°	1055.4	1055.4	1055.4	1055.4	1058.8	1060.4	1063.7	1065.4	1063.7	1062.1	1058.8
5°	887.8	889.5	889.5	891.1	891.1	891.1	891.1	891.1	894.5	897.8	901.1
7.5°	702.0	703.6	705.3	706.9	706.9	706.9	705.3	705.3	706.9	706.9	708.6
10°	537.7	544.3	549.3	554.3	550.9	546.0	542.7	537.7	537.7	537.7	536.0
12.5°	406.6	408.2	411.6	413.2	411.6	411.6	409.9	408.2	409.9	413.2	414.9
15°	321.9	321.9	323.6	323.6	325.3	326.9	326.9	328.6	331.9	333.6	336.9
17.5°	267.2	268.8	268.8	270.5	270.5	272.2	272.2	272.2	275.5	278.8	283.8
20°	240.6	240.6	240.6	240.6	240.6	239.0	239.0	237.3	239.0	242.3	243.9
22.5°	215.7	217.4	217.4	217.4	215.7	214.1	210.8	209.1	209.1	210.8	210.8
25°	189.2	187.5	187.5	185.9	185.9	187.5	187.5	187.5	189.2	189.2	190.8
27.5°	174.2	172.6	172.6	170.9	170.9	172.6	172.6	172.6	172.6	172.6	172.6
30°	162.6	162.6	161.0	159.3	161.0	161.0	162.6	162.6	164.3	164.3	165.9
32.5°	154.3	152.7	152.7	151.0	152.7	152.7	154.3	154.3	156.0	157.7	157.7
35°	142.7	142.7	142.7	142.7	142.7	142.7	141.1	141.1	141.1	141.1	141.1
37.5°	136.1	136.1	134.4	132.8	132.8	132.8	132.8	132.8	131.1	129.4	127.8
40°	131.1	129.4	129.4	127.8	126.1	126.1	124.5	122.8	122.8	121.1	121.1
42.5°	124.5	122.8	122.8	121.1	119.5	119.5	117.8	116.2	116.2	116.2	114.5
45°	116.2	116.2	114.5	112.8	112.8	112.8	111.2	111.2	111.2	111.2	109.5
47.5°	107.9	107.9	106.2	106.2	106.2	106.2	104.5	104.5	104.5	104.5	104.5
50°	102.9	102.9	102.9	102.9	102.9	102.9	101.2	101.2	101.2	101.2	101.2
52.5°	97.9	97.9	97.9	97.9	97.9	97.9	97.9	97.9	97.9	97.9	97.9
55°	96.3	96.3	96.3	96.3	96.3	96.3	94.6	94.6	94.6	96.3	96.3
57.5°	92.9	92.9	91.3	91.3	91.3	91.3	91.3	91.3	91.3	91.3	91.3
60°	89.6	89.6	89.6	89.6	89.6	89.6	89.6	89.6	89.6	89.6	89.6
62.5°	84.6	84.6	84.6	84.6	84.6	86.3	86.3	86.3	86.3	86.3	84.6
65°	78.0	79.7	79.7	79.7	79.7	79.7	79.7	79.7	79.7	79.7	79.7
67.5°	74.7	74.7	74.7	74.7	74.7	74.7	74.7	74.7	74.7	74.7	74.7
70°	69.7	69.7	68.0	68.0	68.0	69.7	69.7	69.7	69.7	69.7	69.7
72.5°	63.1	63.1	63.1	63.1	63.1	63.1	63.1	63.1	63.1	64.7	64.7
75°	56.4	56.4	56.4	56.4	56.4	56.4	56.4	56.4	56.4	56.4	56.4
77.5°	49.8	49.8	48.1	48.1	48.1	49.8	49.8	49.8	49.8	51.4	51.4
80°	41.5	41.5	41.5	41.5	41.5	41.5	41.5	41.5	41.5	43.1	43.1
82.5°	33.2	33.2	33.2	33.2	33.2	33.2	33.2	33.2	33.2	34.8	34.8
85°	24.9	26.6	26.6	26.6	26.6	26.6	26.6	26.6	26.6	28.2	28.2
87.5°	16.6	16.6	16.6	16.6	16.6	16.6	14.9	14.9	14.9	14.9	13.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676047
 CATALOG NUMBER: CCW-SA-2A-835-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676047
 CATALOG NUMBER: CCW-SA-2A-835-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8
2.5°	1057.1	1058.8	1060.4	1060.4	1062.1	1063.7	1063.7	1070.4	1077.0	1080.3	1083.6
5°	904.4	902.8	902.8	901.1	899.4	904.4	909.4	919.4	929.3	931.0	934.3
7.5°	708.6	710.3	711.9	711.9	713.6	708.6	702.0	703.6	705.3	713.6	720.2
10°	536.0	537.7	539.3	539.3	541.0	539.3	536.0	541.0	546.0	552.6	560.9
12.5°	416.5	421.5	426.5	429.8	434.8	438.1	439.8	446.4	451.4	459.7	468.0
15°	340.2	343.5	346.8	350.2	353.5	356.8	360.1	366.7	373.4	383.3	393.3
17.5°	287.1	287.1	288.8	288.8	288.8	292.1	295.4	298.7	300.4	310.3	320.3
20°	245.6	243.9	242.3	240.6	239.0	242.3	243.9	245.6	247.3	253.9	258.9
22.5°	210.8	210.8	212.4	212.4	212.4	210.8	207.4	209.1	209.1	212.4	217.4
25°	190.8	190.8	190.8	189.2	189.2	190.8	192.5	192.5	190.8	192.5	194.2
27.5°	172.6	174.2	174.2	175.9	175.9	177.6	177.6	177.6	177.6	179.2	180.9
30°	165.9	165.9	167.6	167.6	167.6	169.3	170.9	170.9	170.9	172.6	175.9
32.5°	159.3	161.0	162.6	164.3	165.9	167.6	167.6	169.3	169.3	170.9	172.6
35°	141.1	139.4	139.4	137.7	136.1	136.1	136.1	136.1	134.4	136.1	136.1
37.5°	126.1	126.1	126.1	124.5	124.5	126.1	126.1	126.1	126.1	127.8	127.8
40°	119.5	119.5	119.5	119.5	119.5	119.5	119.5	121.1	121.1	122.8	124.5
42.5°	114.5	114.5	114.5	114.5	114.5	116.2	116.2	116.2	116.2	117.8	117.8
45°	109.5	109.5	109.5	109.5	109.5	109.5	109.5	111.2	111.2	112.8	114.5
47.5°	104.5	104.5	104.5	104.5	104.5	106.2	107.9	107.9	107.9	109.5	109.5
50°	101.2	101.2	101.2	101.2	101.2	102.9	102.9	104.5	104.5	106.2	107.9
52.5°	97.9	97.9	97.9	97.9	97.9	99.6	99.6	101.2	101.2	102.9	104.5
55°	96.3	96.3	96.3	94.6	94.6	96.3	96.3	97.9	97.9	99.6	99.6
57.5°	91.3	91.3	91.3	91.3	91.3	91.3	91.3	92.9	92.9	94.6	96.3
60°	89.6	89.6	88.0	88.0	86.3	88.0	88.0	89.6	89.6	91.3	91.3
62.5°	84.6	84.6	84.6	83.0	83.0	84.6	84.6	84.6	84.6	86.3	88.0
65°	79.7	79.7	79.7	78.0	78.0	79.7	79.7	79.7	79.7	81.3	83.0
67.5°	74.7	74.7	74.7	73.0	73.0	73.0	73.0	74.7	74.7	76.3	78.0
70°	69.7	69.7	69.7	68.0	68.0	68.0	66.4	68.0	69.7	71.4	71.4
72.5°	64.7	64.7	64.7	63.1	63.1	63.1	61.4	63.1	63.1	64.7	64.7
75°	56.4	56.4	56.4	56.4	56.4	56.4	54.8	54.8	54.8	56.4	56.4
77.5°	51.4	51.4	51.4	49.8	49.8	49.8	48.1	48.1	48.1	49.8	49.8
80°	43.1	43.1	43.1	41.5	41.5	41.5	39.8	39.8	39.8	41.5	41.5
82.5°	34.8	34.8	34.8	33.2	33.2	33.2	31.5	31.5	31.5	33.2	33.2
85°	28.2	28.2	28.2	28.2	28.2	28.2	26.6	26.6	26.6	28.2	29.9
87.5°	13.3	13.3	14.9	14.9	14.9	14.9	13.3	13.3	11.6	11.6	13.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676047
 CATALOG NUMBER: CCW-SA-2A-835-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676047
 CATALOG NUMBER: CCW-SA-2A-835-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8
2.5°	1087.0	1090.3	1098.6	1105.2	1113.5	1120.2	1125.1	1131.8	1136.7	1141.7	1145.0
5°	935.9	937.6	945.9	954.2	960.8	969.1	980.8	992.4	1004.0	1015.6	1023.9
7.5°	728.5	735.2	745.1	756.7	766.7	776.6	788.3	801.5	813.1	824.8	836.4
10°	567.5	574.2	584.1	594.1	602.4	612.4	625.6	638.9	652.2	665.5	678.7
12.5°	476.3	484.6	496.2	507.8	517.8	529.4	546.0	560.9	577.5	592.4	609.0
15°	401.6	411.6	426.5	443.1	458.0	473.0	489.5	506.1	521.1	537.7	554.3
17.5°	330.2	340.2	353.5	368.4	381.7	395.0	414.9	433.1	453.0	471.3	489.5
20°	265.5	270.5	283.8	297.0	310.3	323.6	338.5	353.5	368.4	383.3	406.6
22.5°	220.7	224.0	230.7	235.6	242.3	247.3	262.2	277.1	290.4	305.3	326.9
25°	194.2	195.8	200.8	204.1	209.1	212.4	222.4	230.7	240.6	248.9	268.8
27.5°	180.9	182.5	184.2	185.9	187.5	189.2	195.8	202.5	207.4	214.1	232.3
30°	177.6	179.2	184.2	187.5	192.5	195.8	199.1	202.5	205.8	209.1	220.7
32.5°	174.2	175.9	175.9	174.2	174.2	172.6	175.9	177.6	180.9	182.5	192.5
35°	137.7	137.7	139.4	141.1	142.7	144.4	149.4	152.7	157.7	161.0	169.3
37.5°	129.4	129.4	131.1	134.4	136.1	137.7	141.1	144.4	147.7	151.0	159.3
40°	124.5	126.1	127.8	129.4	131.1	132.8	136.1	137.7	141.1	142.7	149.4
42.5°	119.5	119.5	121.1	124.5	126.1	127.8	131.1	132.8	136.1	137.7	144.4
45°	116.2	117.8	119.5	121.1	121.1	122.8	126.1	129.4	131.1	134.4	141.1
47.5°	111.2	111.2	114.5	116.2	119.5	121.1	124.5	126.1	129.4	131.1	137.7
50°	107.9	109.5	112.8	114.5	117.8	119.5	124.5	127.8	132.8	136.1	139.4
52.5°	104.5	106.2	109.5	111.2	114.5	116.2	122.8	129.4	134.4	141.1	141.1
55°	101.2	101.2	104.5	109.5	112.8	116.2	119.5	124.5	127.8	131.1	131.1
57.5°	96.3	97.9	101.2	106.2	109.5	112.8	116.2	119.5	121.1	124.5	122.8
60°	92.9	92.9	97.9	102.9	107.9	112.8	112.8	112.8	111.2	111.2	111.2
62.5°	88.0	89.6	96.3	104.5	111.2	117.8	112.8	107.9	102.9	97.9	99.6
65°	84.6	86.3	89.6	94.6	97.9	101.2	97.9	96.3	92.9	89.6	91.3
67.5°	78.0	79.7	81.3	81.3	83.0	83.0	83.0	83.0	83.0	83.0	84.6
70°	73.0	73.0	73.0	74.7	74.7	74.7	74.7	74.7	74.7	74.7	76.3
72.5°	66.4	66.4	66.4	66.4	66.4	66.4	66.4	66.4	66.4	66.4	68.0
75°	58.1	58.1	58.1	58.1	58.1	58.1	58.1	58.1	58.1	58.1	59.7
77.5°	51.4	51.4	51.4	51.4	51.4	51.4	51.4	51.4	49.8	49.8	51.4
80°	43.1	43.1	43.1	43.1	41.5	41.5	41.5	41.5	41.5	41.5	43.1
82.5°	34.8	34.8	34.8	34.8	33.2	33.2	33.2	33.2	31.5	31.5	33.2
85°	31.5	33.2	33.2	34.8	34.8	34.8	33.2	31.5	29.9	28.2	28.2
87.5°	13.3	13.3	13.3	13.3	11.6	11.6	11.6	11.6	11.6	11.6	11.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676047
 CATALOG NUMBER: CCW-SA-2A-835-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676047
 CATALOG NUMBER: CCW-SA-2A-835-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8
2.5°	1150.0	1153.3	1156.7	1161.6	1168.3	1173.3	1178.2	1188.2	1199.8	1209.8	1219.7
5°	1032.2	1040.5	1048.8	1058.8	1068.7	1077.0	1087.0	1106.9	1126.8	1145.0	1165.0
7.5°	846.3	858.0	867.9	884.5	899.4	916.0	931.0	955.9	979.1	1004.0	1027.2
10°	692.0	705.3	718.6	740.1	763.4	784.9	806.5	826.4	848.0	867.9	887.8
12.5°	625.6	640.6	657.2	670.4	685.4	698.6	711.9	735.2	758.4	781.6	804.9
15°	570.9	587.5	604.1	620.6	635.6	652.2	667.1	687.0	708.6	728.5	748.4
17.5°	507.8	524.4	542.7	560.9	579.2	597.4	615.7	643.9	672.1	698.6	726.9
20°	428.1	451.4	473.0	497.8	522.7	547.6	572.5	602.4	632.3	660.5	690.3
22.5°	348.5	370.1	391.6	421.5	451.4	479.6	509.5	549.3	587.5	627.3	665.5
25°	290.4	310.3	330.2	363.4	395.0	428.1	459.7	507.8	554.3	602.4	648.9
27.5°	250.6	268.8	287.1	321.9	356.8	390.0	424.8	477.9	529.4	582.5	633.9
30°	232.3	243.9	255.6	288.8	321.9	353.5	386.7	438.1	489.5	541.0	592.4
32.5°	202.5	212.4	222.4	252.2	282.1	310.3	340.2	393.3	444.7	497.8	549.3
35°	179.2	187.5	195.8	224.0	250.6	278.8	305.3	358.4	411.6	464.7	517.8
37.5°	165.9	174.2	180.9	205.8	232.3	257.2	282.1	335.2	386.7	439.8	491.2
40°	156.0	161.0	167.6	192.5	215.7	240.6	263.9	312.0	361.8	409.9	458.0
42.5°	149.4	156.0	161.0	182.5	205.8	227.3	248.9	295.4	341.9	386.7	433.1
45°	147.7	154.3	161.0	179.2	197.5	214.1	232.3	277.1	321.9	366.7	411.6
47.5°	144.4	149.4	156.0	170.9	184.2	199.1	212.4	257.2	302.0	345.2	390.0
50°	142.7	144.4	147.7	161.0	174.2	187.5	200.8	245.6	290.4	335.2	380.0
52.5°	141.1	141.1	141.1	152.7	164.3	174.2	185.9	230.7	277.1	321.9	366.7
55°	131.1	129.4	129.4	141.1	151.0	162.6	172.6	217.4	262.2	305.3	350.2
57.5°	121.1	119.5	117.8	127.8	137.7	147.7	157.7	202.5	248.9	293.7	338.5
60°	111.2	109.5	109.5	119.5	127.8	137.7	146.0	192.5	237.3	283.8	328.6
62.5°	99.6	101.2	101.2	109.5	119.5	127.8	136.1	182.5	230.7	277.1	323.6
65°	91.3	92.9	92.9	102.9	112.8	122.8	132.8	177.6	224.0	268.8	313.6
67.5°	84.6	86.3	86.3	97.9	107.9	119.5	129.4	169.3	210.8	250.6	290.4
70°	78.0	78.0	79.7	91.3	102.9	114.5	126.1	161.0	195.8	229.0	263.9
72.5°	69.7	71.4	73.0	84.6	94.6	106.2	116.2	147.7	179.2	210.8	242.3
75°	61.4	63.1	64.7	74.7	84.6	94.6	104.5	134.4	162.6	192.5	220.7
77.5°	54.8	56.4	58.1	66.4	74.7	83.0	91.3	112.8	136.1	157.7	179.2
80°	44.8	44.8	46.5	53.1	59.7	64.7	71.4	86.3	101.2	114.5	129.4
82.5°	33.2	34.8	34.8	39.8	43.1	48.1	51.4	59.7	66.4	74.7	81.3
85°	28.2	26.6	26.6	29.9	31.5	34.8	36.5	41.5	44.8	49.8	53.1
87.5°	11.6	10.0	10.0	11.6	14.9	16.6	18.3	18.3	19.9	19.9	19.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676047
 CATALOG NUMBER: CCW-SA-2A-835-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676047

CATALOG NUMBER: CCW-SA-2A-835-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8
2.5°	1224.7	1228.0	1233.0	1236.3	1244.6	1251.3	1259.5	1266.2	1271.2	1279.5	1276.1
5°	1179.9	1194.8	1209.8	1224.7	1236.3	1247.9	1257.9	1269.5	1282.8	1307.7	1314.3
7.5°	1047.1	1067.0	1085.3	1105.2	1128.5	1151.7	1174.9	1198.1	1219.7	1251.3	1271.2
10°	916.0	944.2	970.8	999.0	1020.6	1042.2	1062.1	1083.6	1113.5	1145.0	1181.6
12.5°	833.1	861.3	889.5	917.7	949.2	979.1	1010.6	1040.5	1068.7	1093.6	1135.1
15°	778.3	809.8	839.7	869.6	907.7	944.2	982.4	1018.9	1060.4	1093.6	1121.8
17.5°	765.0	803.2	839.7	877.9	917.7	957.5	997.4	1037.2	1078.7	1128.5	1165.0
20°	741.8	793.2	844.7	896.1	947.6	997.4	1048.8	1098.6	1153.3	1213.1	1229.7
22.5°	728.5	789.9	853.0	914.4	984.1	1055.4	1125.1	1194.8	1252.9	1297.7	1347.5
25°	726.9	803.2	881.2	957.5	1045.5	1131.8	1219.7	1306.0	1380.7	1425.5	1465.3
27.5°	725.2	818.1	909.4	1000.7	1108.5	1214.7	1322.6	1428.8	1498.5	1563.2	1596.4
30°	705.3	816.5	929.3	1040.5	1161.6	1282.8	1403.9	1525.1	1596.4	1641.2	1657.8
32.5°	680.4	811.5	942.6	1073.7	1211.4	1349.2	1485.2	1623.0	1679.4	1717.6	1704.3
35°	660.5	804.9	947.6	1090.3	1236.3	1384.0	1530.0	1676.1	1757.4	1810.5	1788.9
37.5°	642.2	793.2	944.2	1095.3	1266.2	1437.1	1608.0	1779.0	1857.0	1913.4	1888.5
40°	620.6	781.6	944.2	1105.2	1301.0	1495.2	1691.0	1885.2	1986.4	2034.5	1996.4
42.5°	602.4	770.0	939.3	1106.9	1316.0	1525.1	1734.2	1943.3	2056.1	2124.1	2076.0
45°	579.2	746.8	912.7	1080.3	1311.0	1541.7	1770.7	2001.3	2132.4	2185.5	2119.2
47.5°	554.3	720.2	884.5	1048.8	1294.4	1540.0	1785.6	2031.2	2152.4	2215.4	2154.0
50°	546.0	711.9	876.2	1042.2	1307.7	1574.9	1840.4	2105.9	2193.8	2245.3	2164.0
52.5°	544.3	720.2	897.8	1073.7	1340.9	1606.4	1873.6	2139.1	2210.4	2265.2	2192.2
55°	539.3	730.2	919.4	1108.5	1387.3	1667.8	1946.6	2225.4	2296.7	2336.6	2281.8
57.5°	544.3	750.1	954.2	1160.0	1447.1	1734.2	2021.3	2308.3	2394.6	2422.8	2411.2
60°	547.6	766.7	984.1	1203.1	1483.6	1764.0	2044.5	2324.9	2414.6	2484.3	2497.5
62.5°	539.3	755.1	969.1	1184.9	1438.8	1692.7	1946.6	2200.5	2348.2	2451.1	2510.8
65°	514.4	713.6	914.4	1113.5	1347.5	1583.1	1817.1	2051.1	2207.1	2359.8	2407.9
67.5°	459.7	628.9	798.2	967.5	1171.6	1375.7	1578.2	1782.3	1978.1	2125.8	2192.2
70°	398.3	531.0	665.5	798.2	984.1	1169.9	1355.8	1541.7	1714.2	1876.9	1939.9
72.5°	346.8	449.7	554.3	657.2	789.9	921.0	1053.8	1184.9	1389.0	1551.6	1613.0
75°	295.4	370.1	443.1	517.8	609.0	700.3	789.9	881.2	1025.6	1171.6	1233.0
77.5°	227.3	277.1	325.3	373.4	436.4	497.8	560.9	622.3	723.5	833.1	864.6
80°	157.7	185.9	212.4	240.6	290.4	340.2	390.0	439.8	506.1	567.5	615.7
82.5°	97.9	116.2	132.8	149.4	189.2	229.0	267.2	307.0	333.6	336.9	385.0
85°	63.1	74.7	84.6	94.6	117.8	142.7	165.9	189.2	169.3	157.7	187.5
87.5°	24.9	31.5	36.5	41.5	39.8	38.2	36.5	34.8	29.9	26.6	33.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676047
 CATALOG NUMBER: CCW-SA-2A-835-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676047

CATALOG NUMBER: CCW-SA-2A-835-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8
2.5°	1279.5	1284.4	1289.4	1292.7	1297.7	1299.4	1301.0	1301.0	1302.7	1304.4	1307.7
5°	1340.9	1350.8	1360.8	1369.1	1379.0	1387.3	1394.0	1402.3	1408.9	1408.9	1407.2
7.5°	1289.4	1314.3	1339.2	1364.1	1389.0	1407.2	1423.8	1442.1	1458.7	1462.0	1465.3
10°	1221.4	1247.9	1272.8	1299.4	1324.3	1352.5	1379.0	1405.6	1433.8	1438.8	1445.4
12.5°	1158.3	1189.9	1221.4	1251.3	1282.8	1302.7	1322.6	1340.9	1360.8	1374.1	1387.3
15°	1156.7	1183.2	1209.8	1234.7	1261.2	1272.8	1284.4	1294.4	1306.0	1306.0	1307.7
17.5°	1194.8	1211.4	1228.0	1243.0	1259.5	1261.2	1264.5	1266.2	1267.8	1262.9	1257.9
20°	1269.5	1276.1	1282.8	1289.4	1296.1	1284.4	1274.5	1262.9	1251.3	1238.0	1226.4
22.5°	1379.0	1364.1	1349.2	1334.2	1319.3	1299.4	1277.8	1257.9	1236.3	1219.7	1203.1
25°	1481.9	1463.7	1445.4	1427.2	1408.9	1365.8	1322.6	1277.8	1234.7	1216.4	1198.1
27.5°	1619.7	1591.4	1563.2	1535.0	1506.8	1448.7	1390.6	1332.6	1274.5	1243.0	1213.1
30°	1652.8	1621.3	1589.8	1556.6	1525.1	1468.6	1413.9	1357.5	1301.0	1264.5	1229.7
32.5°	1701.0	1664.5	1628.0	1591.4	1554.9	1500.2	1445.4	1389.0	1334.2	1301.0	1266.2
35°	1780.6	1739.1	1697.7	1654.5	1613.0	1556.6	1501.8	1445.4	1389.0	1350.8	1314.3
37.5°	1848.7	1800.5	1752.4	1704.3	1656.2	1606.4	1554.9	1505.2	1453.7	1415.5	1379.0
40°	1925.0	1871.9	1818.8	1767.4	1714.2	1667.8	1621.3	1573.2	1526.7	1496.9	1467.0
42.5°	1991.4	1926.7	1863.6	1800.5	1735.8	1704.3	1674.4	1642.9	1611.4	1596.4	1579.8
45°	2037.8	1978.1	1916.7	1857.0	1797.2	1774.0	1750.8	1727.5	1704.3	1719.2	1734.2
47.5°	2057.8	2009.6	1963.2	1916.7	1868.6	1876.9	1885.2	1891.8	1900.1	1920.0	1941.6
50°	2076.0	2049.5	2021.3	1994.7	1966.5	1998.0	2027.9	2059.4	2091.0	2132.4	2173.9
52.5°	2112.5	2097.6	2084.3	2069.4	2054.4	2109.2	2164.0	2218.7	2273.5	2320.0	2366.4
55°	2222.1	2210.4	2198.8	2185.5	2173.9	2251.9	2328.3	2406.3	2484.3	2532.4	2580.5
57.5°	2373.1	2366.4	2358.1	2351.5	2343.2	2419.5	2494.2	2568.9	2645.2	2691.7	2739.8
60°	2487.6	2489.2	2489.2	2490.9	2490.9	2549.0	2607.1	2666.8	2724.9	2764.7	2806.2
62.5°	2549.0	2545.7	2542.3	2539.0	2535.7	2583.8	2631.9	2680.1	2728.2	2758.1	2787.9
65°	2482.6	2500.8	2519.1	2537.4	2555.6	2562.2	2567.2	2573.9	2578.8	2597.1	2615.3
67.5°	2260.2	2296.7	2331.6	2368.1	2402.9	2378.0	2354.8	2329.9	2305.0	2310.0	2313.3
70°	2013.0	2054.4	2097.6	2139.1	2180.6	2122.5	2064.4	2004.7	1946.6	1926.7	1906.7
72.5°	1697.7	1734.2	1772.3	1808.8	1845.3	1774.0	1704.3	1632.9	1561.6	1526.7	1491.9
75°	1297.7	1340.9	1385.7	1428.8	1472.0	1392.3	1311.0	1231.3	1150.0	1126.8	1105.2
77.5°	945.9	997.4	1048.8	1100.2	1151.7	1080.3	1009.0	935.9	864.6	851.3	838.0
80°	688.7	728.5	766.7	806.5	844.7	803.2	761.7	720.2	678.7	677.1	675.4
82.5°	464.7	499.5	532.7	567.5	600.7	584.1	569.2	552.6	536.0	552.6	570.9
85°	239.0	287.1	336.9	385.0	433.1	428.1	424.8	419.8	414.9	436.4	456.4
87.5°	48.1	89.6	131.1	170.9	212.4	202.5	192.5	180.9	170.9	177.6	182.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676047
 CATALOG NUMBER: CCW-SA-2A-835-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676047

CATALOG NUMBER: CCW-SA-2A-835-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8
2.5°	1309.3	1311.0	1311.0	1311.0	1311.0	1311.0	1307.7	1306.0	1302.7	1299.4	1294.4
5°	1407.2	1405.6	1398.9	1392.3	1384.0	1377.4	1372.4	1365.8	1360.8	1354.1	1344.2
7.5°	1468.6	1472.0	1460.3	1450.4	1438.8	1427.2	1415.5	1403.9	1392.3	1380.7	1357.5
10°	1450.4	1455.4	1448.7	1442.1	1433.8	1427.2	1413.9	1398.9	1385.7	1370.7	1342.5
12.5°	1398.9	1412.2	1408.9	1405.6	1402.3	1398.9	1390.6	1380.7	1372.4	1362.4	1330.9
15°	1307.7	1307.7	1309.3	1311.0	1311.0	1312.7	1314.3	1316.0	1317.6	1319.3	1301.0
17.5°	1252.9	1247.9	1247.9	1247.9	1247.9	1247.9	1254.6	1262.9	1269.5	1276.1	1271.2
20°	1213.1	1201.5	1199.8	1199.8	1198.1	1196.5	1208.1	1221.4	1233.0	1244.6	1251.3
22.5°	1186.5	1169.9	1168.3	1166.6	1165.0	1163.3	1178.2	1193.2	1208.1	1223.0	1246.3
25°	1179.9	1161.6	1163.3	1165.0	1165.0	1166.6	1178.2	1189.9	1201.5	1213.1	1252.9
27.5°	1181.6	1151.7	1153.3	1155.0	1155.0	1156.7	1174.9	1191.5	1209.8	1226.4	1276.1
30°	1193.2	1158.3	1155.0	1151.7	1148.4	1145.0	1169.9	1194.8	1219.7	1244.6	1282.8
32.5°	1233.0	1199.8	1191.5	1183.2	1174.9	1166.6	1196.5	1224.7	1254.6	1282.8	1314.3
35°	1276.1	1239.6	1236.3	1233.0	1228.0	1224.7	1251.3	1279.5	1306.0	1332.6	1360.8
37.5°	1340.9	1304.4	1301.0	1296.1	1292.7	1287.8	1317.6	1345.8	1375.7	1403.9	1428.8
40°	1437.1	1407.2	1405.6	1405.6	1403.9	1402.3	1425.5	1450.4	1473.6	1496.9	1513.5
42.5°	1564.9	1550.0	1554.9	1561.6	1566.6	1571.5	1589.8	1609.7	1628.0	1646.2	1641.2
45°	1749.1	1764.0	1765.7	1767.4	1769.0	1770.7	1775.6	1782.3	1787.3	1792.2	1772.3
47.5°	1961.5	1981.4	1991.4	2001.3	2009.6	2019.6	2013.0	2004.7	1998.0	1989.7	1939.9
50°	2213.8	2255.2	2253.6	2251.9	2248.6	2246.9	2233.7	2220.4	2205.5	2192.2	2119.2
52.5°	2412.9	2459.4	2467.7	2476.0	2484.3	2492.5	2467.7	2442.8	2416.2	2391.3	2300.0
55°	2627.0	2675.1	2676.8	2678.4	2678.4	2680.1	2645.2	2610.4	2573.9	2539.0	2444.4
57.5°	2786.3	2832.7	2827.8	2824.4	2819.5	2814.5	2773.0	2731.5	2690.0	2648.5	2553.9
60°	2846.0	2885.8	2875.9	2865.9	2854.3	2844.4	2812.8	2781.3	2748.1	2716.6	2625.3
62.5°	2817.8	2847.7	2832.7	2819.5	2804.5	2789.6	2749.8	2708.3	2668.5	2627.0	2560.6
65°	2631.9	2650.2	2630.3	2612.0	2593.8	2573.9	2540.7	2507.5	2472.6	2439.4	2394.6
67.5°	2318.3	2321.6	2320.0	2318.3	2316.6	2315.0	2266.9	2218.7	2168.9	2120.8	2117.5
70°	1888.5	1868.6	1871.9	1876.9	1880.2	1883.5	1847.0	1812.2	1775.6	1739.1	1755.7
72.5°	1457.0	1422.2	1430.5	1440.4	1448.7	1457.0	1427.2	1398.9	1369.1	1339.2	1362.4
75°	1082.0	1060.4	1068.7	1078.7	1087.0	1095.3	1083.6	1072.0	1058.8	1047.1	1068.7
77.5°	824.8	811.5	813.1	813.1	814.8	814.8	816.5	819.8	821.4	823.1	846.3
80°	672.1	670.4	668.8	667.1	663.8	662.1	678.7	695.3	711.9	728.5	740.1
82.5°	587.5	604.1	594.1	585.8	575.8	565.9	580.8	595.8	610.7	625.6	620.6
85°	477.9	497.8	479.6	461.3	441.4	423.2	436.4	448.1	461.3	473.0	466.3
87.5°	189.2	194.2	164.3	136.1	106.2	76.3	121.1	164.3	209.1	252.2	258.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676047
 CATALOG NUMBER: CCW-SA-2A-835-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676047

CATALOG NUMBER: CCW-SA-2A-835-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8	1194.8
2.5°	1289.4	1282.8	1277.8	1276.1	1272.8	1271.2	1267.8	1264.5	1259.5	1256.2	1251.3
5°	1332.6	1322.6	1311.0	1294.4	1279.5	1262.9	1246.3	1231.3	1216.4	1199.8	1184.9
7.5°	1334.2	1311.0	1287.8	1266.2	1243.0	1221.4	1198.1	1178.2	1156.7	1135.1	1115.2
10°	1316.0	1287.8	1259.5	1231.3	1204.8	1176.6	1148.4	1125.1	1100.2	1075.3	1052.1
12.5°	1301.0	1269.5	1238.0	1204.8	1173.3	1140.1	1106.9	1083.6	1060.4	1037.2	1013.9
15°	1282.8	1262.9	1244.6	1214.7	1184.9	1155.0	1125.1	1093.6	1063.7	1032.2	1000.7
17.5°	1267.8	1262.9	1257.9	1238.0	1218.1	1196.5	1176.6	1145.0	1113.5	1080.3	1048.8
20°	1259.5	1266.2	1272.8	1262.9	1252.9	1241.3	1231.3	1208.1	1184.9	1160.0	1136.7
22.5°	1269.5	1294.4	1317.6	1319.3	1322.6	1324.3	1325.9	1304.4	1282.8	1259.5	1238.0
25°	1292.7	1332.6	1372.4	1394.0	1415.5	1438.8	1460.3	1447.1	1433.8	1420.5	1407.2
27.5°	1324.3	1374.1	1423.8	1455.4	1485.2	1516.8	1548.3	1546.6	1545.0	1541.7	1540.0
30°	1319.3	1357.5	1395.6	1433.8	1472.0	1510.1	1548.3	1568.2	1586.5	1606.4	1626.3
32.5°	1347.5	1379.0	1412.2	1452.1	1491.9	1533.4	1573.2	1614.7	1654.5	1696.0	1737.5
35°	1390.6	1418.9	1448.7	1491.9	1536.7	1579.8	1624.6	1674.4	1725.9	1777.3	1827.1
37.5°	1455.4	1480.3	1506.8	1543.3	1581.5	1618.0	1656.2	1729.2	1802.2	1876.9	1949.9
40°	1530.0	1546.6	1563.2	1598.1	1632.9	1667.8	1702.6	1793.9	1885.2	1976.4	2067.7
42.5°	1637.9	1632.9	1628.0	1656.2	1686.0	1714.2	1744.1	1827.1	1910.1	1993.0	2076.0
45°	1752.4	1732.5	1712.6	1725.9	1740.8	1754.1	1769.0	1853.6	1938.3	2024.6	2109.2
47.5°	1890.2	1840.4	1790.6	1779.0	1767.4	1754.1	1742.5	1833.7	1925.0	2017.9	2109.2
50°	2046.1	1971.5	1898.5	1868.6	1837.1	1807.2	1775.6	1850.3	1926.7	2003.0	2077.7
52.5°	2208.8	2115.8	2024.6	1978.1	1931.6	1883.5	1837.1	1900.1	1964.8	2029.6	2092.6
55°	2348.2	2253.6	2157.3	2102.6	2047.8	1993.0	1938.3	2001.3	2064.4	2127.5	2190.5
57.5°	2459.4	2364.8	2270.2	2218.7	2165.6	2114.2	2061.1	2120.8	2182.2	2243.6	2303.4
60°	2535.7	2444.4	2353.2	2303.4	2253.6	2203.8	2154.0	2225.4	2296.7	2369.7	2441.1
62.5°	2495.9	2429.5	2363.1	2341.5	2320.0	2296.7	2275.2	2343.2	2409.6	2477.6	2545.7
65°	2349.8	2305.0	2260.2	2281.8	2305.0	2326.6	2349.8	2394.6	2439.4	2485.9	2530.7
67.5°	2112.5	2109.2	2104.2	2152.4	2200.5	2250.3	2298.4	2328.3	2356.5	2386.3	2416.2
70°	1772.3	1790.6	1807.2	1890.2	1973.1	2056.1	2139.1	2150.7	2162.3	2173.9	2185.5
72.5°	1387.3	1410.6	1435.5	1545.0	1652.8	1762.4	1871.9	1865.3	1858.6	1850.3	1843.7
75°	1091.9	1113.5	1136.7	1238.0	1339.2	1440.4	1541.7	1513.5	1486.9	1458.7	1430.5
77.5°	871.2	894.5	919.4	1013.9	1108.5	1204.8	1299.4	1231.3	1163.3	1095.3	1027.2
80°	750.1	761.7	771.7	836.4	899.4	964.2	1028.9	959.2	887.8	816.5	746.8
82.5°	615.7	609.0	604.1	642.2	680.4	718.6	756.7	690.3	624.0	555.9	489.5
85°	459.7	453.0	446.4	466.3	486.2	507.8	527.7	451.4	375.0	297.0	220.7
87.5°	267.2	273.8	280.5	302.0	323.6	346.8	368.4	290.4	212.4	132.8	54.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676047
 CATALOG NUMBER: CCW-SA-2A-835-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676047
 CATALOG NUMBER: CCW-SA-2A-835-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1194.8	1194.8
2.5°	1241.3	1233.0
5°	1173.3	1161.6
7.5°	1098.6	1083.6
10°	1030.5	1010.6
12.5°	987.4	962.5
15°	970.8	940.9
17.5°	1020.6	992.4
20°	1096.9	1058.8
22.5°	1189.9	1143.4
25°	1350.8	1294.4
27.5°	1481.9	1423.8
30°	1563.2	1500.2
32.5°	1652.8	1569.9
35°	1745.8	1666.1
37.5°	1858.6	1769.0
40°	1974.8	1881.9
42.5°	2014.6	1954.9
45°	2052.8	1996.4
47.5°	2061.1	2014.6
50°	2069.4	2062.7
52.5°	2092.6	2091.0
55°	2192.2	2193.8
57.5°	2315.0	2324.9
60°	2427.8	2416.2
62.5°	2485.9	2426.2
65°	2446.1	2363.1
67.5°	2326.6	2237.0
70°	2064.4	1943.3
72.5°	1737.5	1631.3
75°	1339.2	1249.6
77.5°	952.5	877.9
80°	670.4	595.8
82.5°	429.8	370.1
85°	194.2	169.3
87.5°	54.8	53.1
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P676047
CATALOG NUMBER: CCW-SA-2A-835-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)