

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: Pxxxxxx

Luminaire Tested: **203-SS-8LED2710-12-BK**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: Pxxxxxx
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (Pxxxxxx)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED2710-12-BK
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 2700K CCT, 10 DEGREE SPOT OPTIC,
REGRESSED HOOD BLACK
Light Source: (1) SORAA 2700K 95 CRI 10°NSP LED
SM16-07-10D-927-03
Ballast/Driver: CHROMA POWER SUPPLY IN0004

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 272.5 lumens
Efficiency: N/A
Efficacy: 34.1 lumens/watt
Spacing Criteria (0/90/45): 0.21 / 0.21 / 0.19
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: Pxxxxxx

CATALOG NUMBER: 203-SS-8LED2710-12-BK

Luminous Intensity Polar Plot





TEST NUMBER: Pxxxxxx

CATALOG NUMBER: 203-SS-8LED2710-12-BK

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10							
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10				
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	111	106	106	106	106	102	102	102	102	100	100	100	100
1	116	114	113	111	114	112	111	109	108	107	106	106	105	104	103	103	101	101	100	100	98	98	98	98
2	113	110	108	106	111	109	106	105	106	104	102	102	103	101	100	100	100	99	98	98	97	97	97	97
3	111	107	104	102	109	106	103	101	103	101	99	99	101	99	98	98	99	98	97	97	95	95	95	95
4	108	104	101	99	107	103	100	98	101	99	97	97	100	98	96	96	98	96	95	95	94	94	94	94
5	106	102	99	96	105	101	98	96	100	97	95	95	98	96	95	95	97	95	94	94	93	93	93	93
6	105	100	97	95	104	99	96	94	98	96	94	94	97	95	93	93	96	94	93	93	92	92	92	92
7	103	98	95	93	102	98	95	93	97	94	92	92	96	94	92	92	95	93	92	92	91	91	91	91
8	101	97	94	92	101	96	94	92	96	93	91	91	95	93	91	91	94	92	91	91	90	90	90	90
9	100	95	93	91	99	95	92	90	94	92	90	90	94	92	90	90	93	91	90	90	89	89	89	89
10	99	94	91	90	98	94	91	90	93	91	89	89	93	91	89	89	92	90	89	89	88	88	88	88

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2495662
5°	1694546
10°	194835
15°	57821
20°	25885
25°	13392
30°	9343
35°	7710
40°	6441
45°	4466
50°	3531
55°	2322
60°	888
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: Pxxxxxx

CATALOG NUMBER: 203-SS-8LED2710-12-BK

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	206.5	75.8
10°-20°	38.1	14.0
20°-30°	12.3	4.5
30°-40°	7.9	2.9
40°-50°	5.2	1.9
50°-60°	2.2	0.8
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	256.8	94.2
0°-40°	264.7	97.1
0°-60°	272.2	99.9
0°-90°	272.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	272.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5058	
5°	3422	206
15°	113	38
25°	25	12
35°	13	8
45°	6	5
55°	3	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: Pxxxxxx

CATALOG NUMBER: 203-SS-8LED2710-12-BK

CANDELA DISTRIBUTION (FULL):

0°	
0°	5058.3
1°	4986.2
2°	4825.5
3°	4531.6
4°	4051.4
5°	3421.5
6°	2651.9
7°	1835.8
8°	1111.9
9°	636.3
10°	388.9
12.5°	184.4
15°	113.2
17.5°	79.4
20°	49.3
22.5°	32.0
25°	24.6
27.5°	20.1
30°	16.4
32.5°	13.7
35°	12.8
37.5°	11.0
40°	10.0
42.5°	8.2
45°	6.4
47.5°	5.5
50°	4.6
52.5°	2.7
55°	2.7
57.5°	1.8
60°	0.9
62.5°	0.9
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)