

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P247011

Luminaire Tested: **203-SS-8LED2710-12-BK-OSL**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P247011
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-27)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED2710-12-BK-OSL
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 2700K CCT, 10 DEGREE SPOT OPTIC, REGRESSED HOOD BLACK, OVERALL SPREAD LENS
Light Source: (1) SORAA 2700K 95 CRI 10°NSP LED SM16-07-10D-927-03
Ballast/Driver: CHROMA POWER SUPPLY IN0004

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 260.8 lumens
Efficiency: N/A
Efficacy: 32.6 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P247011
CATALOG NUMBER: 203-SS-8LED2710-12-BK-OSL

Luminous Intensity Polar Plot





TEST NUMBER: P247011

CATALOG NUMBER: 203-SS-8LED2710-12-BK-OSL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97
2	112	109	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	95
3	109	104	101	98	107	103	100	98	101	98	96	98	96	95	96	95	93	92
4	106	101	97	94	104	100	96	94	98	95	93	96	94	92	94	92	91	90
5	103	98	94	91	102	97	93	91	95	92	90	94	91	89	92	90	89	88
6	101	95	91	88	99	94	91	88	93	90	88	92	89	87	91	88	87	86
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	86	85	84
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	86	83	81	80
10	92	86	83	80	91	86	82	80	85	82	80	85	82	80	84	82	80	79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	765676
5°	764094
10°	487965
15°	156657
20°	39326
25°	17910
30°	11451
35°	8794
40°	6441
45°	5094
50°	3531
55°	2322
60°	888
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P247011

CATALOG NUMBER: 203-SS-8LED2710-12-BK-OSL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.8	49.0
10°-20°	98.9	37.9
20°-30°	17.0	6.5
30°-40°	9.0	3.4
40°-50°	5.6	2.1
50°-60°	2.4	0.9
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	243.7	93.4
0°-40°	252.7	96.9
0°-60°	260.7	100.0
0°-90°	260.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	260.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1552	
5°	1543	128
15°	307	99
25°	33	17
35°	15	9
45°	7	6
55°	3	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P247011

CATALOG NUMBER: 203-SS-8LED2710-12-BK-OSL

CANDELA DISTRIBUTION (FULL):

0°	
0°	1551.9
1°	1559.2
2°	1577.5
3°	1591.2
4°	1582.9
5°	1542.8
6°	1469.7
7°	1368.4
8°	1244.3
9°	1112.8
10°	974.0
12.5°	618.9
15°	306.7
17.5°	135.1
20°	74.9
22.5°	47.5
25°	32.9
27.5°	24.6
30°	20.1
32.5°	16.4
35°	14.6
37.5°	11.9
40°	10.0
42.5°	8.2
45°	7.3
47.5°	6.4
50°	4.6
52.5°	3.7
55°	2.7
57.5°	1.8
60°	0.9
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)