

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331260-927

Luminaire Tested: **S122DIP-S290D725U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331260-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S290D725U927-4F0-1E-UDD-A4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3276.7 lumens  
Efficiency: N/A  
Efficacy: 105.0 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 31.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331260-927

CATALOG NUMBER: S122DIP-S290D725U927-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331260-927

CATALOG NUMBER: S122DIP-S290D725U927-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	32
1	94	90	86	83	84	81	78	75	64	62	60	49	48	47	35	34	34	27
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	30	29	23
3	78	69	63	57	70	63	57	52	50	46	43	39	36	34	28	26	25	20
4	72	62	54	48	64	56	49	44	45	40	37	35	32	29	25	23	22	17
5	66	55	47	41	59	50	43	38	40	35	32	31	28	25	23	21	19	15
6	61	49	42	36	55	45	38	33	36	31	28	28	25	22	21	19	17	14
7	56	44	37	32	50	40	34	29	33	28	24	26	22	20	19	17	15	12
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	15	14	11
9	48	37	30	25	44	34	27	23	27	23	19	22	18	16	16	14	12	10
10	45	34	27	22	41	31	25	21	25	21	17	20	17	14	15	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7561	7561	7561	7561
5°	8475	7609	6744	7609
10°	9712	7547	5835	7547
15°	10745	7408	5157	7408
20°	10581	7261	4699	7261
25°	9540	7062	4411	7062
30°	7884	6747	4200	6747
35°	5746	6416	4050	6416
40°	4591	6028	3967	6028
45°	4010	5576	3854	5576
50°	3770	5139	3778	5139
55°	3474	4695	3676	4695
60°	3184	4224	3523	4224
65°	2904	3801	3370	3801
70°	2634	3389	3144	3389
75°	2339	2932	2782	2932
80°	2008	2427	2241	2427
85°	1797	1797	1334	1797



TEST NUMBER: P331260-927

CATALOG NUMBER: S122DIP-S290D725U927-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.6	1.4
10°-20°	129.6	4.0
20°-30°	188.1	5.7
30°-40°	198.5	6.1
40°-50°	175.8	5.4
50°-60°	140.3	4.3
60°-70°	95.4	2.9
70°-80°	48.9	1.5
80°-90°	14.7	0.4
90°-100°	128.7	3.9
100°-110°	436.9	13.3
110°-120°	464.2	14.2
120°-130°	382.1	11.7
130°-140°	306.8	9.4
140°-150°	231.9	7.1
150°-160°	163.0	5.0
160°-170°	95.9	2.9
170°-180°	31.2	1.0
0°-30°	362.4	11.1
0°-40°	560.9	17.1
0°-60°	877.0	26.8
0°-90°	1035.9	31.6
90°-120°	1029.8	31.4
90°-150°	1950.7	59.5
90°-180°	2241.0	68.4
0°-180°	3276.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	468	468	468	468	468	
5°	523	470	416	470	523	52
15°	643	443	308	443	643	177
25°	536	396	248	396	536	242
35°	292	326	206	326	292	190
45°	176	244	169	244	176	138
55°	123	167	131	167	123	111
65°	76	100	88	100	76	76
75°	38	47	45	47	38	40
85°	10	10	7	10	10	11
90°	20	1	20	1	20	11
95°	71	22	71	22	71	92
105°	698	76	698	76	698	675
115°	918	133	918	133	918	899
125°	745	186	745	186	745	673
135°	617	218	617	218	617	480
145°	493	249	493	249	493	313
155°	414	283	414	283	414	193
165°	364	308	364	308	364	104
175°	328	321	328	321	328	32
180°	322	322	322	322	322	



TEST NUMBER: P331260-927

CATALOG NUMBER: S122DIP-S290D725U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	489.8	490.0	490.3	488.0	487.7	487.7	485.7	483.9	481.9	479.2	479.5
5°	522.9	524.9	525.6	523.5	520.2	519.9	516.8	511.8	507.1	503.4	500.7
7.5°	562.4	563.2	561.5	558.6	556.3	551.9	546.2	540.7	532.8	525.7	520.4
10°	592.4	593.5	590.4	586.3	582.9	577.8	569.6	561.1	550.9	541.0	533.1
12.5°	615.1	617.8	613.9	613.4	607.5	600.6	590.7	586.5	572.0	558.3	549.7
15°	642.8	642.6	643.0	639.5	635.3	634.1	623.8	612.4	592.1	583.9	569.9
17.5°	634.8	637.5	638.8	638.7	638.7	637.9	634.6	627.5	617.3	604.1	588.0
20°	615.8	619.4	620.0	624.1	626.5	629.5	630.7	628.8	622.5	611.5	597.5
22.5°	586.5	587.5	589.1	595.6	600.6	608.3	612.3	619.0	616.6	611.2	599.4
25°	535.5	533.8	540.0	543.3	555.0	567.2	576.1	585.7	594.4	599.6	596.2
27.5°	474.4	471.7	481.2	489.8	499.2	512.5	526.2	542.5	556.0	572.9	578.7
30°	422.9	424.5	433.5	442.7	457.1	475.8	491.3	509.1	528.4	547.2	560.4
32.5°	367.3	373.5	379.2	393.3	406.0	426.8	449.6	471.8	495.8	517.3	537.7
35°	291.5	298.7	306.7	316.9	334.7	355.4	377.6	407.6	440.4	469.7	493.8
37.5°	245.4	244.2	248.7	256.2	270.6	287.3	312.8	342.5	381.0	415.5	449.6
40°	217.8	217.1	220.2	227.1	238.1	250.3	272.7	298.7	334.5	376.7	417.2
42.5°	198.8	199.2	201.0	205.8	213.3	223.4	240.1	262.3	295.1	334.8	378.3
45°	175.6	176.9	178.9	181.3	185.5	193.8	203.2	219.0	244.9	278.1	320.8
47.5°	159.0	159.1	161.1	163.1	165.6	170.3	178.0	187.9	206.2	233.1	270.0
50°	150.1	148.9	150.3	151.9	154.6	157.8	162.9	172.2	184.4	206.2	237.0
52.5°	139.1	139.2	140.5	141.1	143.5	146.7	151.3	157.8	168.9	185.9	211.2
55°	123.4	124.4	125.1	126.1	128.3	130.6	134.3	138.6	147.2	159.9	178.7
57.5°	108.7	109.0	109.7	111.8	113.1	115.3	118.7	122.6	128.3	137.7	151.8
60°	98.6	98.6	100.1	100.9	102.7	104.9	107.6	111.4	116.5	124.1	135.5
62.5°	89.4	89.3	89.8	91.3	92.7	94.7	97.4	100.6	105.4	112.3	121.5
65°	76.0	75.6	76.7	77.0	78.4	80.4	82.6	86.0	89.8	94.8	103.1
67.5°	63.0	63.5	64.0	64.6	65.4	67.6	69.0	71.4	74.6	78.8	84.4
70°	55.8	55.8	55.8	56.3	57.4	58.5	59.9	61.9	65.0	68.5	73.6
72.5°	47.7	48.3	48.9	48.6	49.9	50.5	52.3	53.4	56.3	58.6	63.1
75°	37.5	37.5	37.5	38.3	38.9	39.4	40.5	41.6	43.0	45.9	48.2
77.5°	28.0	27.9	28.0	28.3	28.8	29.5	29.8	30.7	32.1	33.4	35.4
80°	21.6	21.9	22.1	22.5	22.5	22.8	23.1	24.3	25.2	26.1	27.3
82.5°	16.7	16.8	16.8	16.9	17.0	17.3	17.7	18.1	18.5	19.2	20.1
85°	9.7	9.5	9.5	9.9	9.7	9.7	10.1	10.5	10.5	10.6	11.2
87.5°	7.8	7.8	8.0	7.8	7.8	7.8	7.6	7.7	8.0	8.2	8.2
90°	20.4	20.4	20.4	20.4	20.4	19.8	18.6	19.8	20.4	21.1	20.4
92.5°	34.3	35.3	34.8	36.8	37.3	41.1	46.3	54.0	68.0	80.5	79.4
95°	70.6	69.9	71.9	76.8	84.8	98.5	124.5	162.2	212.4	242.7	214.9
97.5°	138.9	144.2	153.2	168.4	198.0	242.7	309.7	378.6	434.7	414.4	312.1
100°	221.7	232.8	250.8	277.4	328.8	403.8	488.6	565.4	578.4	489.2	336.8
102.5°	390.1	405.2	427.6	473.1	528.9	608.3	670.4	687.8	631.8	491.7	327.5
105°	697.9	706.5	733.2	771.6	810.0	830.4	822.4	752.4	623.6	458.8	309.0
107.5°	891.4	903.0	908.3	910.5	905.6	875.6	811.2	705.8	569.2	423.7	299.8
110°	949.9	950.5	945.0	933.2	906.6	855.8	776.6	665.7	535.0	406.9	297.9



TEST NUMBER: P331260-927

CATALOG NUMBER: S122DIP-S290D725U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	949.0	945.6	935.1	915.4	878.4	820.1	735.4	629.1	511.3	395.9	298.3
115°	918.4	912.8	896.7	868.2	824.2	760.4	679.3	583.9	481.8	384.0	301.0
117.5°	863.7	859.0	842.1	812.0	767.1	707.3	633.7	550.0	463.2	378.1	305.4
120°	828.5	822.4	804.4	775.3	732.0	675.6	610.0	533.1	453.3	374.6	308.4
122.5°	791.9	786.7	770.7	742.1	703.2	652.3	590.2	519.8	444.9	372.6	311.9
125°	745.0	740.0	724.5	701.0	665.0	618.6	564.1	500.3	432.8	369.1	317.0
127.5°	703.9	699.9	686.5	664.5	633.1	590.3	538.8	481.2	421.7	366.9	322.4
130°	680.6	675.6	663.2	642.1	611.8	570.9	522.0	468.7	414.3	366.0	326.4
132.5°	656.2	651.8	640.4	619.4	589.5	551.1	506.2	456.9	408.4	365.5	330.3
135°	617.4	614.9	603.8	583.4	556.7	522.0	481.2	440.3	400.1	364.7	335.0
137.5°	579.2	575.5	565.8	548.2	523.9	493.7	461.2	427.1	394.2	364.6	339.2
140°	553.0	549.3	540.0	523.9	504.1	476.8	448.4	418.6	390.8	364.1	341.2
142.5°	526.7	526.0	517.7	503.1	484.3	461.4	437.0	411.7	387.3	364.1	342.7
145°	492.9	491.1	484.9	474.4	459.5	441.6	422.3	401.9	382.7	362.9	344.3
147.5°	464.5	463.4	459.2	450.8	438.6	425.4	410.4	394.3	378.0	360.7	344.8
150°	447.7	447.1	443.4	435.9	426.7	415.5	402.5	388.9	374.0	359.2	344.3
152.5°	433.3	433.2	430.5	424.1	416.8	407.1	396.1	383.4	370.6	356.7	343.3
155°	414.3	415.5	413.0	408.7	401.9	395.1	385.8	375.9	364.1	352.4	341.8
157.5°	398.1	398.1	397.0	393.3	388.5	383.2	375.4	367.1	358.1	347.9	339.0
160°	387.6	387.6	387.1	384.0	379.6	375.3	368.4	361.6	353.6	344.9	337.5
162.5°	377.7	378.3	377.6	375.5	371.2	367.8	362.0	356.2	349.6	342.5	336.0
165°	363.5	364.1	364.1	361.6	359.2	356.7	352.4	348.0	343.1	337.5	333.2
167.5°	350.4	351.1	351.3	349.9	348.8	346.5	343.6	340.2	336.6	333.2	330.3
170°	342.5	343.6	344.3	342.5	341.8	340.6	338.1	336.3	333.2	330.7	328.8
172.5°	336.0	336.8	337.4	336.5	335.9	335.2	333.2	331.8	329.7	327.7	326.9
175°	327.6	328.8	329.5	328.8	328.8	328.2	327.6	326.9	325.1	324.5	323.8
177.5°	322.5	323.5	324.0	324.0	324.0	324.0	323.5	323.5	322.5	322.0	322.5
180°	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0



TEST NUMBER: P331260-927

CATALOG NUMBER: S122DIP-S290D725U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	480.5	479.3	478.6	476.0	473.7	471.4	470.7	471.0	467.8	464.8	463.5
5°	499.2	495.6	492.2	487.4	481.6	475.2	472.1	469.5	463.2	456.4	452.4
7.5°	515.9	510.8	504.2	495.1	486.7	476.8	470.5	464.9	455.7	446.1	440.1
10°	526.2	519.2	510.7	499.6	489.3	477.2	468.8	460.3	449.6	438.0	430.8
12.5°	535.0	525.5	517.2	502.9	490.8	475.6	465.6	453.7	442.4	428.6	421.6
15°	555.9	538.4	522.6	506.4	491.5	470.4	459.2	443.2	428.3	411.4	403.3
17.5°	572.0	552.4	527.5	506.9	489.5	466.1	449.8	430.6	413.0	393.6	382.6
20°	581.2	558.7	532.0	507.5	486.6	459.9	442.1	422.6	401.9	380.1	368.2
22.5°	586.7	563.1	536.5	505.3	480.9	455.0	432.5	411.0	390.1	366.5	354.1
25°	588.4	566.9	538.8	503.5	473.6	444.3	417.3	396.4	371.1	349.1	331.0
27.5°	579.9	564.4	537.4	500.1	465.3	431.0	400.9	377.3	350.5	326.7	308.4
30°	569.3	560.4	534.1	496.7	458.7	421.8	388.7	361.9	335.3	311.2	292.4
32.5°	553.1	551.2	528.1	491.8	451.6	410.2	375.9	348.8	319.2	295.6	277.7
35°	521.2	529.8	515.2	480.9	438.4	393.6	356.5	325.5	294.9	272.3	255.6
37.5°	478.3	499.8	496.0	464.9	420.4	375.5	334.5	302.2	273.1	250.2	233.8
40°	448.8	476.2	480.1	452.6	407.8	361.6	318.1	286.0	257.5	236.6	220.1
42.5°	417.2	449.1	459.9	437.9	394.0	346.8	303.5	270.1	241.9	221.7	207.0
45°	364.1	406.3	426.0	413.4	370.9	322.7	278.1	244.2	218.6	199.6	188.2
47.5°	314.4	360.6	387.0	382.5	345.2	297.5	253.3	220.9	196.0	180.8	170.6
50°	279.3	326.8	358.6	360.1	326.8	279.5	235.2	204.6	181.7	167.5	159.2
52.5°	248.7	294.1	328.8	336.5	306.2	260.8	219.0	188.5	168.3	155.3	147.9
55°	208.9	247.2	285.7	299.8	275.5	232.3	193.6	166.8	147.9	138.9	132.5
57.5°	173.7	205.7	241.2	256.7	241.8	204.8	168.5	145.2	129.9	122.0	117.0
60°	155.1	180.3	212.0	230.5	217.5	184.7	153.0	130.8	118.2	111.2	106.5
62.5°	137.8	160.2	187.0	203.9	196.9	165.8	137.4	117.9	107.0	100.4	97.0
65°	113.8	131.3	152.1	167.7	163.0	139.5	116.2	99.5	90.9	85.6	82.9
67.5°	93.6	106.4	120.7	134.4	130.7	114.0	95.4	82.3	75.9	71.4	69.7
70°	81.0	90.7	103.5	114.5	111.4	97.8	82.9	71.8	66.2	62.4	60.8
72.5°	68.9	76.8	86.7	95.6	93.6	82.1	69.9	61.5	57.1	53.6	52.4
75°	52.0	58.1	64.1	70.0	69.5	60.7	53.5	47.0	43.6	40.9	40.3
77.5°	38.4	41.8	45.9	49.4	48.4	43.3	37.7	34.0	31.5	29.7	29.4
80°	29.3	31.3	34.2	36.7	35.5	33.3	28.8	26.1	24.3	22.5	21.8
82.5°	21.3	23.2	25.0	26.4	25.3	23.4	20.6	18.8	17.7	16.5	16.2
85°	11.2	12.2	13.0	13.3	13.0	11.7	10.5	9.7	8.8	8.2	8.1
87.5°	7.7	6.8	6.2	6.1	5.4	5.1	4.1	3.3	3.5	3.9	3.8
90°	16.7	12.4	9.3	7.4	6.2	5.0	2.5	0.6	2.5	5.0	6.2
92.5°	61.8	42.1	28.1	22.3	18.1	15.4	10.9	7.5	10.9	15.4	18.1
95°	143.1	89.2	60.7	45.8	35.9	30.3	24.2	21.7	24.2	30.3	35.9
97.5°	192.7	117.6	81.8	65.0	53.6	45.2	38.7	35.3	38.7	45.2	53.6
100°	203.1	127.5	94.7	77.4	65.0	55.1	49.5	47.7	49.5	55.1	65.0
102.5°	203.6	136.5	106.2	88.8	75.9	66.0	60.4	59.1	60.4	66.0	75.9
105°	206.8	151.7	122.6	105.3	91.7	82.4	78.0	75.6	78.0	82.4	91.7
107.5°	215.4	167.3	139.1	121.6	108.1	99.6	95.4	93.4	95.4	99.6	108.1
110°	222.3	177.7	150.5	132.5	119.5	111.5	107.7	105.3	107.7	111.5	119.5





TEST NUMBER: P331260-927

CATALOG NUMBER: S122DIP-S290D725U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	229.7	187.7	161.4	142.9	130.4	122.9	118.7	116.1	118.7	122.9	130.4
115°	240.9	203.1	176.5	159.8	147.3	140.0	136.3	133.2	136.3	140.0	147.3
117.5°	252.8	217.4	192.7	175.4	163.5	156.9	153.2	150.8	153.2	156.9	163.5
120°	260.7	227.3	203.1	185.8	173.4	167.8	164.1	161.6	164.1	167.8	173.4
122.5°	267.7	236.7	214.0	196.1	183.8	177.7	174.0	172.1	174.0	177.7	183.8
125°	278.7	250.8	228.5	211.2	198.8	191.3	187.7	185.8	187.7	191.3	198.8
127.5°	288.9	264.0	242.2	224.4	212.5	204.4	199.2	196.7	199.2	204.4	212.5
130°	295.4	271.9	250.2	232.8	220.5	211.8	205.6	203.1	205.6	211.8	220.5
132.5°	301.8	278.8	258.1	240.7	227.9	218.7	212.1	209.1	212.1	218.7	227.9
135°	310.2	288.6	268.8	251.4	237.2	227.9	220.5	218.0	220.5	227.9	237.2
137.5°	316.7	296.5	276.9	260.9	246.7	236.8	229.3	226.4	229.3	236.8	246.7
140°	320.1	301.0	282.4	266.3	252.6	242.7	235.3	232.8	235.3	242.7	252.6
142.5°	323.1	304.4	286.4	271.2	258.1	248.2	241.3	239.2	241.3	248.2	258.1
145°	326.9	309.7	292.9	279.2	266.9	257.6	251.4	248.9	251.4	257.6	266.9
147.5°	329.1	313.9	298.1	286.0	275.7	267.1	261.2	259.4	261.2	267.1	275.7
150°	330.0	315.8	301.6	290.4	281.1	273.1	268.2	266.3	268.2	273.1	281.1
152.5°	330.6	317.8	305.1	294.9	286.1	279.0	274.1	273.2	274.1	279.0	286.1
155°	331.3	320.8	310.2	301.0	294.1	287.3	283.6	283.0	283.6	287.3	294.1
157.5°	331.3	322.9	313.9	306.2	300.7	294.8	291.8	291.2	291.8	294.8	300.7
160°	331.3	323.8	316.4	309.7	304.7	299.7	297.2	296.6	297.2	299.7	304.7
162.5°	330.8	324.4	317.9	312.6	308.2	304.2	301.7	302.1	301.7	304.2	308.2
165°	329.5	325.1	319.6	315.8	312.8	309.0	307.8	308.4	307.8	309.0	312.8
167.5°	328.6	325.0	320.9	318.5	316.3	313.9	312.8	313.6	312.8	313.9	316.3
170°	327.6	324.5	321.4	319.6	318.3	316.4	315.8	317.0	315.8	316.4	318.3
172.5°	326.1	324.0	321.9	320.5	319.8	317.9	318.3	319.0	318.3	317.9	319.8
175°	324.5	323.2	322.0	321.4	321.4	320.1	320.8	321.4	320.8	320.1	321.4
177.5°	323.5	322.5	322.0	322.0	322.0	321.0	321.5	322.5	321.5	321.0	322.0
180°	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0



TEST NUMBER: P331260-927

CATALOG NUMBER: S122DIP-S290D725U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	462.1	461.2	458.2	456.6	454.0	451.5	450.0	450.7	451.2	451.0	450.5
5°	448.8	445.4	440.1	435.7	432.5	426.5	424.0	422.7	421.6	420.4	419.1
7.5°	433.0	427.6	420.2	413.8	407.7	400.3	396.1	393.6	391.0	388.2	385.6
10°	421.8	414.2	406.3	397.4	390.1	383.5	377.6	373.6	369.9	366.5	364.1
12.5°	410.0	401.3	391.5	379.2	371.3	361.7	360.8	353.9	348.2	346.1	343.2
15°	391.3	379.0	366.5	352.0	345.7	337.1	331.7	326.2	321.4	318.0	317.1
17.5°	369.9	354.0	341.7	331.2	320.9	312.0	307.0	302.8	298.7	294.2	293.6
20°	353.6	339.9	326.5	317.3	306.7	297.6	291.5	287.2	283.8	281.1	278.8
22.5°	338.2	323.2	310.9	300.9	290.4	283.1	278.3	274.1	271.2	268.3	266.1
25°	313.5	301.8	288.3	276.9	268.3	263.6	259.7	256.1	254.3	252.3	249.8
27.5°	291.8	278.8	266.3	257.5	249.9	245.7	242.9	240.4	238.8	237.6	236.1
30°	276.6	263.5	253.6	244.9	238.6	234.5	232.7	231.2	229.3	228.5	227.8
32.5°	261.9	250.1	241.6	234.1	228.1	225.4	223.8	222.4	220.9	220.2	218.7
35°	241.1	231.2	223.0	218.8	214.0	211.6	210.4	208.6	207.2	206.4	206.2
37.5°	221.6	213.0	207.6	202.2	200.2	198.8	197.0	195.8	195.4	195.3	195.0
40°	208.9	201.9	197.0	192.7	191.9	189.6	188.2	187.2	187.2	187.4	187.2
42.5°	197.4	191.1	186.8	183.1	182.0	180.8	179.3	179.3	179.5	180.1	179.5
45°	180.0	175.5	172.4	170.6	168.7	167.4	167.2	167.7	167.9	168.1	168.7
47.5°	163.9	160.9	158.1	156.1	155.3	155.1	154.9	155.8	156.7	157.0	157.8
50°	154.4	151.0	148.6	147.3	146.6	146.3	146.6	147.7	148.5	149.3	149.9
52.5°	143.8	141.3	139.7	138.7	138.5	138.7	138.7	140.0	141.1	141.5	141.7
55°	129.0	127.2	126.9	125.2	126.0	125.8	126.7	127.4	128.5	129.6	129.8
57.5°	114.3	112.9	111.9	112.1	112.3	113.1	113.8	115.1	116.2	117.4	117.5
60°	104.6	103.9	103.3	103.3	103.6	104.7	105.6	106.9	107.6	108.4	108.8
62.5°	95.6	94.9	94.3	94.7	95.6	96.3	97.3	98.0	98.7	99.4	99.7
65°	81.5	81.2	81.7	82.1	82.2	83.1	84.4	84.9	85.6	86.0	87.3
67.5°	68.5	68.6	68.5	69.0	70.1	70.3	71.5	72.7	72.9	73.6	74.4
70°	59.7	60.1	60.4	60.8	61.7	62.1	63.0	63.5	64.2	64.8	65.4
72.5°	51.7	51.7	52.1	52.0	52.8	53.6	54.3	54.9	55.6	56.3	56.8
75°	39.8	39.8	40.2	40.3	41.2	42.1	41.9	42.3	43.0	43.7	44.1
77.5°	29.1	28.7	29.1	29.2	29.5	30.3	30.4	30.9	31.8	31.5	31.9
80°	22.1	21.6	22.1	22.3	22.3	23.2	23.2	23.6	24.1	23.6	24.1
82.5°	15.8	15.5	15.9	16.0	16.2	16.3	16.6	16.6	17.2	17.0	17.2
85°	7.9	7.8	7.9	7.8	7.9	8.1	8.1	7.9	7.9	8.2	7.8
87.5°	4.0	4.2	4.7	5.5	6.1	6.1	5.8	5.7	5.5	5.4	5.5
90°	7.4	9.3	12.4	16.7	20.4	21.1	20.4	19.8	18.6	19.8	20.4
92.5°	22.3	28.1	42.1	61.8	79.4	80.5	68.0	54.0	46.3	41.1	37.3
95°	45.8	60.7	89.2	143.1	214.9	242.7	212.4	162.2	124.5	98.5	84.8
97.5°	65.0	81.8	117.6	192.7	312.1	414.4	434.7	378.6	309.7	242.7	198.0
100°	77.4	94.7	127.5	203.1	336.8	489.2	578.4	565.4	488.6	403.8	328.8
102.5°	88.8	106.2	136.5	203.6	327.5	491.7	631.8	687.8	670.4	608.3	528.9
105°	105.3	122.6	151.7	206.8	309.0	458.8	623.6	752.4	822.4	830.4	810.0
107.5°	121.6	139.1	167.3	215.4	299.8	423.7	569.2	705.8	811.2	875.6	905.6
110°	132.5	150.5	177.7	222.3	297.9	406.9	535.0	665.7	776.6	855.8	906.6



TEST NUMBER: P331260-927

CATALOG NUMBER: S122DIP-S290D725U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	142.9	161.4	187.7	229.7	298.3	395.9	511.3	629.1	735.4	820.1	878.4
115°	159.8	176.5	203.1	240.9	301.0	384.0	481.8	583.9	679.3	760.4	824.2
117.5°	175.4	192.7	217.4	252.8	305.4	378.1	463.2	550.0	633.7	707.3	767.1
120°	185.8	203.1	227.3	260.7	308.4	374.6	453.3	533.1	610.0	675.6	732.0
122.5°	196.1	214.0	236.7	267.7	311.9	372.6	444.9	519.8	590.2	652.3	703.2
125°	211.2	228.5	250.8	278.7	317.0	369.1	432.8	500.3	564.1	618.6	665.0
127.5°	224.4	242.2	264.0	288.9	322.4	366.9	421.7	481.2	538.8	590.3	633.1
130°	232.8	250.2	271.9	295.4	326.4	366.0	414.3	468.7	522.0	570.9	611.8
132.5°	240.7	258.1	278.8	301.8	330.3	365.5	408.4	456.9	506.2	551.1	589.5
135°	251.4	268.8	288.6	310.2	335.0	364.7	400.1	440.3	481.2	522.0	556.7
137.5°	260.9	276.9	296.5	316.7	339.2	364.6	394.2	427.1	461.2	493.7	523.9
140°	266.3	282.4	301.0	320.1	341.2	364.1	390.8	418.6	448.4	476.8	504.1
142.5°	271.2	286.4	304.4	323.1	342.7	364.1	387.3	411.7	437.0	461.4	484.3
145°	279.2	292.9	309.7	326.9	344.3	362.9	382.7	401.9	422.3	441.6	459.5
147.5°	286.0	298.1	313.9	329.1	344.8	360.7	378.0	394.3	410.4	425.4	438.6
150°	290.4	301.6	315.8	330.0	344.3	359.2	374.0	388.9	402.5	415.5	426.7
152.5°	294.9	305.1	317.8	330.6	343.3	356.7	370.6	383.4	396.1	407.1	416.8
155°	301.0	310.2	320.8	331.3	341.8	352.4	364.1	375.9	385.8	395.1	401.9
157.5°	306.2	313.9	322.9	331.3	339.0	347.9	358.1	367.1	375.4	383.2	388.5
160°	309.7	316.4	323.8	331.3	337.5	344.9	353.6	361.6	368.4	375.3	379.6
162.5°	312.6	317.9	324.4	330.8	336.0	342.5	349.6	356.2	362.0	367.8	371.2
165°	315.8	319.6	325.1	329.5	333.2	337.5	343.1	348.0	352.4	356.7	359.2
167.5°	318.5	320.9	325.0	328.6	330.3	333.2	336.6	340.2	343.6	346.5	348.8
170°	319.6	321.4	324.5	327.6	328.8	330.7	333.2	336.3	338.1	340.6	341.8
172.5°	320.5	321.9	324.0	326.1	326.9	327.7	329.7	331.8	333.2	335.2	335.9
175°	321.4	322.0	323.2	324.5	323.8	324.5	325.1	326.9	327.6	328.2	328.8
177.5°	322.0	322.0	322.5	323.5	322.5	322.0	322.5	323.5	323.5	324.0	324.0
180°	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0



TEST NUMBER: P331260-927

CATALOG NUMBER: S122DIP-S290D725U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	449.1	448.8	448.8	447.5	448.8	448.8	449.1	450.5	451.0	451.2	450.7
5°	416.6	416.1	415.2	416.1	415.2	416.1	416.6	419.1	420.4	421.6	422.7
7.5°	384.4	382.3	382.0	379.9	382.0	382.3	384.4	385.6	388.2	391.0	393.6
10°	361.0	359.6	359.3	355.9	359.3	359.6	361.0	364.1	366.5	369.9	373.6
12.5°	343.2	339.7	340.4	338.4	340.4	339.7	343.2	343.2	346.1	348.2	353.9
15°	312.2	312.2	311.5	308.5	311.5	312.2	312.2	317.1	318.0	321.4	326.2
17.5°	290.0	289.6	288.0	288.8	288.0	289.6	290.0	293.6	294.2	298.7	302.8
20°	276.8	275.7	273.5	273.5	273.5	275.7	276.8	278.8	281.1	283.8	287.2
22.5°	264.3	264.2	261.9	262.6	261.9	264.2	264.3	266.1	268.3	271.2	274.1
25°	249.6	248.2	247.1	247.6	247.1	248.2	249.6	249.8	252.3	254.3	256.1
27.5°	235.7	234.9	234.8	233.4	234.8	234.9	235.7	236.1	237.6	238.8	240.4
30°	227.7	225.9	226.2	225.3	226.2	225.9	227.7	227.8	228.5	229.3	231.2
32.5°	218.4	217.8	217.5	216.7	217.5	217.8	218.4	218.7	220.2	220.9	222.4
35°	205.9	206.0	205.2	205.5	205.2	206.0	205.9	206.2	206.4	207.2	208.6
37.5°	194.9	195.4	195.0	195.1	195.0	195.4	194.9	195.0	195.3	195.4	195.8
40°	187.7	187.7	187.7	188.2	187.7	187.7	187.7	187.2	187.4	187.2	187.2
42.5°	180.8	180.5	180.2	180.1	180.2	180.5	180.8	179.5	180.1	179.5	179.3
45°	169.0	169.5	169.7	168.8	169.7	169.5	169.0	168.7	168.1	167.9	167.7
47.5°	158.3	158.4	158.3	159.1	158.3	158.4	158.3	157.8	157.0	156.7	155.8
50°	150.8	150.4	150.8	150.4	150.8	150.4	150.8	149.9	149.3	148.5	147.7
52.5°	142.9	143.0	142.8	142.7	142.8	143.0	142.9	141.7	141.5	141.1	140.0
55°	130.5	130.8	130.6	130.6	130.6	130.8	130.5	129.8	129.6	128.5	127.4
57.5°	117.6	118.0	118.2	117.4	118.2	118.0	117.6	117.5	117.4	116.2	115.1
60°	108.7	109.6	109.4	109.1	109.4	109.6	108.7	108.8	108.4	107.6	106.9
62.5°	100.4	100.8	100.8	100.7	100.8	100.8	100.4	99.7	99.4	98.7	98.0
65°	87.9	88.2	87.6	88.2	87.6	88.2	87.9	87.3	86.0	85.6	84.9
67.5°	74.1	74.3	74.7	74.9	74.7	74.3	74.1	74.4	73.6	72.9	72.7
70°	65.7	65.5	66.1	66.6	66.1	65.5	65.7	65.4	64.8	64.2	63.5
72.5°	56.7	57.1	57.0	57.4	57.0	57.1	56.7	56.8	56.3	55.6	54.9
75°	43.7	44.3	44.1	44.6	44.1	44.3	43.7	44.1	43.7	43.0	42.3
77.5°	31.6	31.7	31.6	31.9	31.6	31.7	31.6	31.9	31.5	31.8	30.9
80°	24.1	23.8	23.4	24.1	23.4	23.8	24.1	24.1	23.6	24.1	23.6
82.5°	16.8	17.0	16.6	16.6	16.6	17.0	16.8	17.2	17.0	17.2	16.6
85°	7.8	7.5	7.2	7.2	7.2	7.5	7.8	7.8	8.2	7.9	7.9
87.5°	5.5	5.4	5.4	5.2	5.4	5.4	5.5	5.5	5.4	5.5	5.7
90°	20.4	20.4	20.4	20.4	20.4	20.4	20.4	20.4	19.8	18.6	19.8
92.5°	36.8	34.8	35.3	34.3	35.3	34.8	36.8	37.3	41.1	46.3	54.0
95°	76.8	71.9	69.9	70.6	69.9	71.9	76.8	84.8	98.5	124.5	162.2
97.5°	168.4	153.2	144.2	138.9	144.2	153.2	168.4	198.0	242.7	309.7	378.6
100°	277.4	250.8	232.8	221.7	232.8	250.8	277.4	328.8	403.8	488.6	565.4
102.5°	473.1	427.6	405.2	390.1	405.2	427.6	473.1	528.9	608.3	670.4	687.8
105°	771.6	733.2	706.5	697.9	706.5	733.2	771.6	810.0	830.4	822.4	752.4
107.5°	910.5	908.3	903.0	891.4	903.0	908.3	910.5	905.6	875.6	811.2	705.8
110°	933.2	945.0	950.5	949.9	950.5	945.0	933.2	906.6	855.8	776.6	665.7



TEST NUMBER: P331260-927

CATALOG NUMBER: S122DIP-S290D725U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	915.4	935.1	945.6	949.0	945.6	935.1	915.4	878.4	820.1	735.4	629.1
115°	868.2	896.7	912.8	918.4	912.8	896.7	868.2	824.2	760.4	679.3	583.9
117.5°	812.0	842.1	859.0	863.7	859.0	842.1	812.0	767.1	707.3	633.7	550.0
120°	775.3	804.4	822.4	828.5	822.4	804.4	775.3	732.0	675.6	610.0	533.1
122.5°	742.1	770.7	786.7	791.9	786.7	770.7	742.1	703.2	652.3	590.2	519.8
125°	701.0	724.5	740.0	745.0	740.0	724.5	701.0	665.0	618.6	564.1	500.3
127.5°	664.5	686.5	699.9	703.9	699.9	686.5	664.5	633.1	590.3	538.8	481.2
130°	642.1	663.2	675.6	680.6	675.6	663.2	642.1	611.8	570.9	522.0	468.7
132.5°	619.4	640.4	651.8	656.2	651.8	640.4	619.4	589.5	551.1	506.2	456.9
135°	583.4	603.8	614.9	617.4	614.9	603.8	583.4	556.7	522.0	481.2	440.3
137.5°	548.2	565.8	575.5	579.2	575.5	565.8	548.2	523.9	493.7	461.2	427.1
140°	523.9	540.0	549.3	553.0	549.3	540.0	523.9	504.1	476.8	448.4	418.6
142.5°	503.1	517.7	526.0	526.7	526.0	517.7	503.1	484.3	461.4	437.0	411.7
145°	474.4	484.9	491.1	492.9	491.1	484.9	474.4	459.5	441.6	422.3	401.9
147.5°	450.8	459.2	463.4	464.5	463.4	459.2	450.8	438.6	425.4	410.4	394.3
150°	435.9	443.4	447.1	447.7	447.1	443.4	435.9	426.7	415.5	402.5	388.9
152.5°	424.1	430.5	433.2	433.3	433.2	430.5	424.1	416.8	407.1	396.1	383.4
155°	408.7	413.0	415.5	414.3	415.5	413.0	408.7	401.9	395.1	385.8	375.9
157.5°	393.3	397.0	398.1	398.1	398.1	397.0	393.3	388.5	383.2	375.4	367.1
160°	384.0	387.1	387.6	387.6	387.6	387.1	384.0	379.6	375.3	368.4	361.6
162.5°	375.5	377.6	378.3	377.7	378.3	377.6	375.5	371.2	367.8	362.0	356.2
165°	361.6	364.1	364.1	363.5	364.1	364.1	361.6	359.2	356.7	352.4	348.0
167.5°	349.9	351.3	351.1	350.4	351.1	351.3	349.9	348.8	346.5	343.6	340.2
170°	342.5	344.3	343.6	342.5	343.6	344.3	342.5	341.8	340.6	338.1	336.3
172.5°	336.5	337.4	336.8	336.0	336.8	337.4	336.5	335.9	335.2	333.2	331.8
175°	328.8	329.5	328.8	327.6	328.8	329.5	328.8	328.8	328.2	327.6	326.9
177.5°	324.0	324.0	323.5	322.5	323.5	324.0	324.0	324.0	324.0	323.5	323.5
180°	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0



TEST NUMBER: P331260-927

CATALOG NUMBER: S122DIP-S290D725U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	450.0	451.5	454.0	456.6	458.2	461.2	462.1	463.5	464.8	467.8	471.0
5°	424.0	426.5	432.5	435.7	440.1	445.4	448.8	452.4	456.4	463.2	469.5
7.5°	396.1	400.3	407.7	413.8	420.2	427.6	433.0	440.1	446.1	455.7	464.9
10°	377.6	383.5	390.1	397.4	406.3	414.2	421.8	430.8	438.0	449.6	460.3
12.5°	360.8	361.7	371.3	379.2	391.5	401.3	410.0	421.6	428.6	442.4	453.7
15°	331.7	337.1	345.7	352.0	366.5	379.0	391.3	403.3	411.4	428.3	443.2
17.5°	307.0	312.0	320.9	331.2	341.7	354.0	369.9	382.6	393.6	413.0	430.6
20°	291.5	297.6	306.7	317.3	326.5	339.9	353.6	368.2	380.1	401.9	422.6
22.5°	278.3	283.1	290.4	300.9	310.9	323.2	338.2	354.1	366.5	390.1	411.0
25°	259.7	263.6	268.3	276.9	288.3	301.8	313.5	331.0	349.1	371.1	396.4
27.5°	242.9	245.7	249.9	257.5	266.3	278.8	291.8	308.4	326.7	350.5	377.3
30°	232.7	234.5	238.6	244.9	253.6	263.5	276.6	292.4	311.2	335.3	361.9
32.5°	223.8	225.4	228.1	234.1	241.6	250.1	261.9	277.7	295.6	319.2	348.8
35°	210.4	211.6	214.0	218.8	223.0	231.2	241.1	255.6	272.3	294.9	325.5
37.5°	197.0	198.8	200.2	202.2	207.6	213.0	221.6	233.8	250.2	273.1	302.2
40°	188.2	189.6	191.9	192.7	197.0	201.9	208.9	220.1	236.6	257.5	286.0
42.5°	179.3	180.8	182.0	183.1	186.8	191.1	197.4	207.0	221.7	241.9	270.1
45°	167.2	167.4	168.7	170.6	172.4	175.5	180.0	188.2	199.6	218.6	244.2
47.5°	154.9	155.1	155.3	156.1	158.1	160.9	163.9	170.6	180.8	196.0	220.9
50°	146.6	146.3	146.6	147.3	148.6	151.0	154.4	159.2	167.5	181.7	204.6
52.5°	138.7	138.7	138.5	138.7	139.7	141.3	143.8	147.9	155.3	168.3	188.5
55°	126.7	125.8	126.0	125.2	126.9	127.2	129.0	132.5	138.9	147.9	166.8
57.5°	113.8	113.1	112.3	112.1	111.9	112.9	114.3	117.0	122.0	129.9	145.2
60°	105.6	104.7	103.6	103.3	103.3	103.9	104.6	106.5	111.2	118.2	130.8
62.5°	97.3	96.3	95.6	94.7	94.3	94.9	95.6	97.0	100.4	107.0	117.9
65°	84.4	83.1	82.2	82.1	81.7	81.2	81.5	82.9	85.6	90.9	99.5
67.5°	71.5	70.3	70.1	69.0	68.5	68.6	68.5	69.7	71.4	75.9	82.3
70°	63.0	62.1	61.7	60.8	60.4	60.1	59.7	60.8	62.4	66.2	71.8
72.5°	54.3	53.6	52.8	52.0	52.1	51.7	51.7	52.4	53.6	57.1	61.5
75°	41.9	42.1	41.2	40.3	40.2	39.8	39.8	40.3	40.9	43.6	47.0
77.5°	30.4	30.3	29.5	29.2	29.1	28.7	29.1	29.4	29.7	31.5	34.0
80°	23.2	23.2	22.3	22.3	22.1	21.6	22.1	21.8	22.5	24.3	26.1
82.5°	16.6	16.3	16.2	16.0	15.9	15.5	15.8	16.2	16.5	17.7	18.8
85°	8.1	8.1	7.9	7.8	7.9	7.8	7.9	8.1	8.2	8.8	9.7
87.5°	5.8	6.1	6.1	5.5	4.7	4.2	4.0	3.8	3.9	3.5	3.3
90°	20.4	21.1	20.4	16.7	12.4	9.3	7.4	6.2	5.0	2.5	0.6
92.5°	68.0	80.5	79.4	61.8	42.1	28.1	22.3	18.1	15.4	10.9	7.5
95°	212.4	242.7	214.9	143.1	89.2	60.7	45.8	35.9	30.3	24.2	21.7
97.5°	434.7	414.4	312.1	192.7	117.6	81.8	65.0	53.6	45.2	38.7	35.3
100°	578.4	489.2	336.8	203.1	127.5	94.7	77.4	65.0	55.1	49.5	47.7
102.5°	631.8	491.7	327.5	203.6	136.5	106.2	88.8	75.9	66.0	60.4	59.1
105°	623.6	458.8	309.0	206.8	151.7	122.6	105.3	91.7	82.4	78.0	75.6
107.5°	569.2	423.7	299.8	215.4	167.3	139.1	121.6	108.1	99.6	95.4	93.4
110°	535.0	406.9	297.9	222.3	177.7	150.5	132.5	119.5	111.5	107.7	105.3



TEST NUMBER: P331260-927

CATALOG NUMBER: S122DIP-S290D725U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	511.3	395.9	298.3	229.7	187.7	161.4	142.9	130.4	122.9	118.7	116.1
115°	481.8	384.0	301.0	240.9	203.1	176.5	159.8	147.3	140.0	136.3	133.2
117.5°	463.2	378.1	305.4	252.8	217.4	192.7	175.4	163.5	156.9	153.2	150.8
120°	453.3	374.6	308.4	260.7	227.3	203.1	185.8	173.4	167.8	164.1	161.6
122.5°	444.9	372.6	311.9	267.7	236.7	214.0	196.1	183.8	177.7	174.0	172.1
125°	432.8	369.1	317.0	278.7	250.8	228.5	211.2	198.8	191.3	187.7	185.8
127.5°	421.7	366.9	322.4	288.9	264.0	242.2	224.4	212.5	204.4	199.2	196.7
130°	414.3	366.0	326.4	295.4	271.9	250.2	232.8	220.5	211.8	205.6	203.1
132.5°	408.4	365.5	330.3	301.8	278.8	258.1	240.7	227.9	218.7	212.1	209.1
135°	400.1	364.7	335.0	310.2	288.6	268.8	251.4	237.2	227.9	220.5	218.0
137.5°	394.2	364.6	339.2	316.7	296.5	276.9	260.9	246.7	236.8	229.3	226.4
140°	390.8	364.1	341.2	320.1	301.0	282.4	266.3	252.6	242.7	235.3	232.8
142.5°	387.3	364.1	342.7	323.1	304.4	286.4	271.2	258.1	248.2	241.3	239.2
145°	382.7	362.9	344.3	326.9	309.7	292.9	279.2	266.9	257.6	251.4	248.9
147.5°	378.0	360.7	344.8	329.1	313.9	298.1	286.0	275.7	267.1	261.2	259.4
150°	374.0	359.2	344.3	330.0	315.8	301.6	290.4	281.1	273.1	268.2	266.3
152.5°	370.6	356.7	343.3	330.6	317.8	305.1	294.9	286.1	279.0	274.1	273.2
155°	364.1	352.4	341.8	331.3	320.8	310.2	301.0	294.1	287.3	283.6	283.0
157.5°	358.1	347.9	339.0	331.3	322.9	313.9	306.2	300.7	294.8	291.8	291.2
160°	353.6	344.9	337.5	331.3	323.8	316.4	309.7	304.7	299.7	297.2	296.6
162.5°	349.6	342.5	336.0	330.8	324.4	317.9	312.6	308.2	304.2	301.7	302.1
165°	343.1	337.5	333.2	329.5	325.1	319.6	315.8	312.8	309.0	307.8	308.4
167.5°	336.6	333.2	330.3	328.6	325.0	320.9	318.5	316.3	313.9	312.8	313.6
170°	333.2	330.7	328.8	327.6	324.5	321.4	319.6	318.3	316.4	315.8	317.0
172.5°	329.7	327.7	326.9	326.1	324.0	321.9	320.5	319.8	317.9	318.3	319.0
175°	325.1	324.5	323.8	324.5	323.2	322.0	321.4	321.4	320.1	320.8	321.4
177.5°	322.5	322.0	322.5	323.5	322.5	322.0	322.0	322.0	321.0	321.5	322.5
180°	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0



TEST NUMBER: P331260-927

CATALOG NUMBER: S122DIP-S290D725U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	470.7	471.4	473.7	476.0	478.6	479.3	480.5	479.5	479.2	481.9	483.9
5°	472.1	475.2	481.6	487.4	492.2	495.6	499.2	500.7	503.4	507.1	511.8
7.5°	470.5	476.8	486.7	495.1	504.2	510.8	515.9	520.4	525.7	532.8	540.7
10°	468.8	477.2	489.3	499.6	510.7	519.2	526.2	533.1	541.0	550.9	561.1
12.5°	465.6	475.6	490.8	502.9	517.2	525.5	535.0	549.7	558.3	572.0	586.5
15°	459.2	470.4	491.5	506.4	522.6	538.4	555.9	569.9	583.9	592.1	612.4
17.5°	449.8	466.1	489.5	506.9	527.5	552.4	572.0	588.0	604.1	617.3	627.5
20°	442.1	459.9	486.6	507.5	532.0	558.7	581.2	597.5	611.5	622.5	628.8
22.5°	432.5	455.0	480.9	505.3	536.5	563.1	586.7	599.4	611.2	616.6	619.0
25°	417.3	444.3	473.6	503.5	538.8	566.9	588.4	596.2	599.6	594.4	585.7
27.5°	400.9	431.0	465.3	500.1	537.4	564.4	579.9	578.7	572.9	556.0	542.5
30°	388.7	421.8	458.7	496.7	534.1	560.4	569.3	560.4	547.2	528.4	509.1
32.5°	375.9	410.2	451.6	491.8	528.1	551.2	553.1	537.7	517.3	495.8	471.8
35°	356.5	393.6	438.4	480.9	515.2	529.8	521.2	493.8	469.7	440.4	407.6
37.5°	334.5	375.5	420.4	464.9	496.0	499.8	478.3	449.6	415.5	381.0	342.5
40°	318.1	361.6	407.8	452.6	480.1	476.2	448.8	417.2	376.7	334.5	298.7
42.5°	303.5	346.8	394.0	437.9	459.9	449.1	417.2	378.3	334.8	295.1	262.3
45°	278.1	322.7	370.9	413.4	426.0	406.3	364.1	320.8	278.1	244.9	219.0
47.5°	253.3	297.5	345.2	382.5	387.0	360.6	314.4	270.0	233.1	206.2	187.9
50°	235.2	279.5	326.8	360.1	358.6	326.8	279.3	237.0	206.2	184.4	172.2
52.5°	219.0	260.8	306.2	336.5	328.8	294.1	248.7	211.2	185.9	168.9	157.8
55°	193.6	232.3	275.5	299.8	285.7	247.2	208.9	178.7	159.9	147.2	138.6
57.5°	168.5	204.8	241.8	256.7	241.2	205.7	173.7	151.8	137.7	128.3	122.6
60°	153.0	184.7	217.5	230.5	212.0	180.3	155.1	135.5	124.1	116.5	111.4
62.5°	137.4	165.8	196.9	203.9	187.0	160.2	137.8	121.5	112.3	105.4	100.6
65°	116.2	139.5	163.0	167.7	152.1	131.3	113.8	103.1	94.8	89.8	86.0
67.5°	95.4	114.0	130.7	134.4	120.7	106.4	93.6	84.4	78.8	74.6	71.4
70°	82.9	97.8	111.4	114.5	103.5	90.7	81.0	73.6	68.5	65.0	61.9
72.5°	69.9	82.1	93.6	95.6	86.7	76.8	68.9	63.1	58.6	56.3	53.4
75°	53.5	60.7	69.5	70.0	64.1	58.1	52.0	48.2	45.9	43.0	41.6
77.5°	37.7	43.3	48.4	49.4	45.9	41.8	38.4	35.4	33.4	32.1	30.7
80°	28.8	33.3	35.5	36.7	34.2	31.3	29.3	27.3	26.1	25.2	24.3
82.5°	20.6	23.4	25.3	26.4	25.0	23.2	21.3	20.1	19.2	18.5	18.1
85°	10.5	11.7	13.0	13.3	13.0	12.2	11.2	11.2	10.6	10.5	10.5
87.5°	4.1	5.1	5.4	6.1	6.2	6.8	7.7	8.2	8.2	8.0	7.7
90°	2.5	5.0	6.2	7.4	9.3	12.4	16.7	20.4	21.1	20.4	19.8
92.5°	10.9	15.4	18.1	22.3	28.1	42.1	61.8	79.4	80.5	68.0	54.0
95°	24.2	30.3	35.9	45.8	60.7	89.2	143.1	214.9	242.7	212.4	162.2
97.5°	38.7	45.2	53.6	65.0	81.8	117.6	192.7	312.1	414.4	434.7	378.6
100°	49.5	55.1	65.0	77.4	94.7	127.5	203.1	336.8	489.2	578.4	565.4
102.5°	60.4	66.0	75.9	88.8	106.2	136.5	203.6	327.5	491.7	631.8	687.8
105°	78.0	82.4	91.7	105.3	122.6	151.7	206.8	309.0	458.8	623.6	752.4
107.5°	95.4	99.6	108.1	121.6	139.1	167.3	215.4	299.8	423.7	569.2	705.8
110°	107.7	111.5	119.5	132.5	150.5	177.7	222.3	297.9	406.9	535.0	665.7





TEST NUMBER: P331260-927

CATALOG NUMBER: S122DIP-S290D725U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	118.7	122.9	130.4	142.9	161.4	187.7	229.7	298.3	395.9	511.3	629.1
115°	136.3	140.0	147.3	159.8	176.5	203.1	240.9	301.0	384.0	481.8	583.9
117.5°	153.2	156.9	163.5	175.4	192.7	217.4	252.8	305.4	378.1	463.2	550.0
120°	164.1	167.8	173.4	185.8	203.1	227.3	260.7	308.4	374.6	453.3	533.1
122.5°	174.0	177.7	183.8	196.1	214.0	236.7	267.7	311.9	372.6	444.9	519.8
125°	187.7	191.3	198.8	211.2	228.5	250.8	278.7	317.0	369.1	432.8	500.3
127.5°	199.2	204.4	212.5	224.4	242.2	264.0	288.9	322.4	366.9	421.7	481.2
130°	205.6	211.8	220.5	232.8	250.2	271.9	295.4	326.4	366.0	414.3	468.7
132.5°	212.1	218.7	227.9	240.7	258.1	278.8	301.8	330.3	365.5	408.4	456.9
135°	220.5	227.9	237.2	251.4	268.8	288.6	310.2	335.0	364.7	400.1	440.3
137.5°	229.3	236.8	246.7	260.9	276.9	296.5	316.7	339.2	364.6	394.2	427.1
140°	235.3	242.7	252.6	266.3	282.4	301.0	320.1	341.2	364.1	390.8	418.6
142.5°	241.3	248.2	258.1	271.2	286.4	304.4	323.1	342.7	364.1	387.3	411.7
145°	251.4	257.6	266.9	279.2	292.9	309.7	326.9	344.3	362.9	382.7	401.9
147.5°	261.2	267.1	275.7	286.0	298.1	313.9	329.1	344.8	360.7	378.0	394.3
150°	268.2	273.1	281.1	290.4	301.6	315.8	330.0	344.3	359.2	374.0	388.9
152.5°	274.1	279.0	286.1	294.9	305.1	317.8	330.6	343.3	356.7	370.6	383.4
155°	283.6	287.3	294.1	301.0	310.2	320.8	331.3	341.8	352.4	364.1	375.9
157.5°	291.8	294.8	300.7	306.2	313.9	322.9	331.3	339.0	347.9	358.1	367.1
160°	297.2	299.7	304.7	309.7	316.4	323.8	331.3	337.5	344.9	353.6	361.6
162.5°	301.7	304.2	308.2	312.6	317.9	324.4	330.8	336.0	342.5	349.6	356.2
165°	307.8	309.0	312.8	315.8	319.6	325.1	329.5	333.2	337.5	343.1	348.0
167.5°	312.8	313.9	316.3	318.5	320.9	325.0	328.6	330.3	333.2	336.6	340.2
170°	315.8	316.4	318.3	319.6	321.4	324.5	327.6	328.8	330.7	333.2	336.3
172.5°	318.3	317.9	319.8	320.5	321.9	324.0	326.1	326.9	327.7	329.7	331.8
175°	320.8	320.1	321.4	321.4	322.0	323.2	324.5	323.8	324.5	325.1	326.9
177.5°	321.5	321.0	322.0	322.0	322.0	322.5	323.5	322.5	322.0	322.5	323.5
180°	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0



TEST NUMBER: P331260-927

CATALOG NUMBER: S122DIP-S290D725U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	485.7	487.7	487.7	488.0	490.3	490.0	489.8
5°	516.8	519.9	520.2	523.5	525.6	524.9	522.9
7.5°	546.2	551.9	556.3	558.6	561.5	563.2	562.4
10°	569.6	577.8	582.9	586.3	590.4	593.5	592.4
12.5°	590.7	600.6	607.5	613.4	613.9	617.8	615.1
15°	623.8	634.1	635.3	639.5	643.0	642.6	642.8
17.5°	634.6	637.9	638.7	638.7	638.8	637.5	634.8
20°	630.7	629.5	626.5	624.1	620.0	619.4	615.8
22.5°	612.3	608.3	600.6	595.6	589.1	587.5	586.5
25°	576.1	567.2	555.0	543.3	540.0	533.8	535.5
27.5°	526.2	512.5	499.2	489.8	481.2	471.7	474.4
30°	491.3	475.8	457.1	442.7	433.5	424.5	422.9
32.5°	449.6	426.8	406.0	393.3	379.2	373.5	367.3
35°	377.6	355.4	334.7	316.9	306.7	298.7	291.5
37.5°	312.8	287.3	270.6	256.2	248.7	244.2	245.4
40°	272.7	250.3	238.1	227.1	220.2	217.1	217.8
42.5°	240.1	223.4	213.3	205.8	201.0	199.2	198.8
45°	203.2	193.8	185.5	181.3	178.9	176.9	175.6
47.5°	178.0	170.3	165.6	163.1	161.1	159.1	159.0
50°	162.9	157.8	154.6	151.9	150.3	148.9	150.1
52.5°	151.3	146.7	143.5	141.1	140.5	139.2	139.1
55°	134.3	130.6	128.3	126.1	125.1	124.4	123.4
57.5°	118.7	115.3	113.1	111.8	109.7	109.0	108.7
60°	107.6	104.9	102.7	100.9	100.1	98.6	98.6
62.5°	97.4	94.7	92.7	91.3	89.8	89.3	89.4
65°	82.6	80.4	78.4	77.0	76.7	75.6	76.0
67.5°	69.0	67.6	65.4	64.6	64.0	63.5	63.0
70°	59.9	58.5	57.4	56.3	55.8	55.8	55.8
72.5°	52.3	50.5	49.9	48.6	48.9	48.3	47.7
75°	40.5	39.4	38.9	38.3	37.5	37.5	37.5
77.5°	29.8	29.5	28.8	28.3	28.0	27.9	28.0
80°	23.1	22.8	22.5	22.5	22.1	21.9	21.6
82.5°	17.7	17.3	17.0	16.9	16.8	16.8	16.7
85°	10.1	9.7	9.7	9.9	9.5	9.5	9.7
87.5°	7.6	7.8	7.8	7.8	8.0	7.8	7.8
90°	18.6	19.8	20.4	20.4	20.4	20.4	20.4
92.5°	46.3	41.1	37.3	36.8	34.8	35.3	34.3
95°	124.5	98.5	84.8	76.8	71.9	69.9	70.6
97.5°	309.7	242.7	198.0	168.4	153.2	144.2	138.9
100°	488.6	403.8	328.8	277.4	250.8	232.8	221.7
102.5°	670.4	608.3	528.9	473.1	427.6	405.2	390.1
105°	822.4	830.4	810.0	771.6	733.2	706.5	697.9
107.5°	811.2	875.6	905.6	910.5	908.3	903.0	891.4
110°	776.6	855.8	906.6	933.2	945.0	950.5	949.9



TEST NUMBER: P331260-927

CATALOG NUMBER: S122DIP-S290D725U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	735.4	820.1	878.4	915.4	935.1	945.6	949.0
115°	679.3	760.4	824.2	868.2	896.7	912.8	918.4
117.5°	633.7	707.3	767.1	812.0	842.1	859.0	863.7
120°	610.0	675.6	732.0	775.3	804.4	822.4	828.5
122.5°	590.2	652.3	703.2	742.1	770.7	786.7	791.9
125°	564.1	618.6	665.0	701.0	724.5	740.0	745.0
127.5°	538.8	590.3	633.1	664.5	686.5	699.9	703.9
130°	522.0	570.9	611.8	642.1	663.2	675.6	680.6
132.5°	506.2	551.1	589.5	619.4	640.4	651.8	656.2
135°	481.2	522.0	556.7	583.4	603.8	614.9	617.4
137.5°	461.2	493.7	523.9	548.2	565.8	575.5	579.2
140°	448.4	476.8	504.1	523.9	540.0	549.3	553.0
142.5°	437.0	461.4	484.3	503.1	517.7	526.0	526.7
145°	422.3	441.6	459.5	474.4	484.9	491.1	492.9
147.5°	410.4	425.4	438.6	450.8	459.2	463.4	464.5
150°	402.5	415.5	426.7	435.9	443.4	447.1	447.7
152.5°	396.1	407.1	416.8	424.1	430.5	433.2	433.3
155°	385.8	395.1	401.9	408.7	413.0	415.5	414.3
157.5°	375.4	383.2	388.5	393.3	397.0	398.1	398.1
160°	368.4	375.3	379.6	384.0	387.1	387.6	387.6
162.5°	362.0	367.8	371.2	375.5	377.6	378.3	377.7
165°	352.4	356.7	359.2	361.6	364.1	364.1	363.5
167.5°	343.6	346.5	348.8	349.9	351.3	351.1	350.4
170°	338.1	340.6	341.8	342.5	344.3	343.6	342.5
172.5°	333.2	335.2	335.9	336.5	337.4	336.8	336.0
175°	327.6	328.2	328.8	328.8	329.5	328.8	327.6
177.5°	323.5	324.0	324.0	324.0	324.0	323.5	322.5
180°	322.0	322.0	322.0	322.0	322.0	322.0	322.0

(END OF REPORT)