

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331332-927

Luminaire Tested: **S122DIP-S675D330U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331332-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S675D330U927-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3335.6 lumens
Efficiency: N/A
Efficacy: 95.3 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 35
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331332-927

CATALOG NUMBER: S122DIP-S675D330U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331332-927

CATALOG NUMBER: S122DIP-S675D330U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	70
1	103	99	95	91	97	93	90	87	84	81	79	75	73	71	67	65	64	60
2	94	87	81	76	89	83	77	73	74	70	66	67	63	61	59	57	55	51
3	86	77	70	64	82	73	67	62	66	61	57	59	55	52	53	50	48	44
4	79	69	61	55	75	65	58	53	59	54	49	53	49	45	48	45	42	39
5	73	62	54	48	69	59	52	46	53	47	43	48	44	40	44	40	37	34
6	68	56	48	42	64	53	46	41	49	42	38	44	39	35	40	36	33	30
7	63	51	43	37	60	49	41	36	44	38	34	40	35	32	37	33	29	27
8	59	46	39	33	56	44	37	32	41	35	30	37	32	28	34	30	27	24
9	55	43	35	30	52	41	34	29	37	32	27	34	29	26	31	27	24	22
10	51	39	32	27	49	38	31	26	35	29	25	32	27	24	29	25	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16990	16990	16990	16990
5°	19047	17099	15152	17099
10°	21827	16959	13114	16959
15°	24145	16649	11587	16649
20°	23778	16314	10562	16314
25°	21440	15871	9912	15871
30°	17717	15163	9439	15163
35°	12912	14420	9102	14420
40°	10313	13544	8916	13544
45°	9012	12529	8661	12529
50°	8470	11549	8493	11549
55°	7809	10553	8265	10553
60°	7156	9494	7915	9494
65°	6518	8542	7568	8542
70°	5915	7619	7062	7619
75°	5246	6581	6257	6581
80°	4519	5449	5040	5449
85°	4057	4057	3001	4057



TEST NUMBER: P331332-927

CATALOG NUMBER: S122DIP-S675D330U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.2	3.0
10°-20°	291.3	8.7
20°-30°	422.8	12.7
30°-40°	446.2	13.4
40°-50°	395.0	11.8
50°-60°	315.3	9.5
60°-70°	214.3	6.4
70°-80°	109.9	3.3
80°-90°	27.8	0.8
90°-100°	58.2	1.7
100°-110°	197.5	5.9
110°-120°	209.8	6.3
120°-130°	172.7	5.2
130°-140°	138.7	4.2
140°-150°	104.8	3.1
150°-160°	73.7	2.2
160°-170°	43.4	1.3
170°-180°	14.1	0.4
0°-30°	814.3	24.4
0°-40°	1260.5	37.8
0°-60°	1970.8	59.1
0°-90°	2322.8	69.6
90°-120°	465.5	14.0
90°-150°	881.7	26.4
90°-180°	1013.0	30.4
0°-180°	3335.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1052	1052	1052	1052	1052	
5°	1175	1055	935	1055	1175	117
15°	1444	996	693	996	1444	399
25°	1204	891	556	891	1204	544
35°	655	732	462	732	655	426
45°	395	549	379	549	395	310
55°	277	375	294	375	277	249
65°	171	224	198	224	171	170
75°	84	106	100	106	84	90
85°	22	22	16	22	22	24
90°	9	0	9	0	9	6
95°	32	10	32	10	32	41
105°	315	34	315	34	315	305
115°	415	60	415	60	415	406
125°	337	84	337	84	337	304
135°	279	98	279	98	279	217
145°	223	112	223	112	223	142
155°	187	128	187	128	187	87
165°	164	139	164	139	164	47
175°	148	145	148	145	148	14
180°	146	146	146	146	146	



TEST NUMBER: P331332-927

CATALOG NUMBER: S122DIP-S675D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1100.7	1101.1	1101.8	1096.5	1095.9	1095.9	1091.4	1087.5	1083.0	1076.8	1077.4
5°	1175.2	1179.6	1181.2	1176.4	1169.1	1168.3	1161.4	1150.1	1139.6	1131.1	1125.1
7.5°	1264.0	1265.7	1261.8	1255.4	1250.0	1240.3	1227.5	1215.0	1197.4	1181.3	1169.3
10°	1331.3	1333.7	1326.8	1317.6	1309.9	1298.5	1279.9	1260.9	1237.9	1215.6	1197.8
12.5°	1382.4	1388.4	1379.6	1378.3	1365.2	1349.6	1327.5	1317.9	1285.4	1254.4	1235.3
15°	1444.5	1444.1	1444.9	1437.3	1427.5	1425.1	1401.6	1376.2	1330.5	1312.2	1280.7
17.5°	1426.6	1432.7	1435.5	1435.4	1435.2	1433.7	1426.2	1410.1	1387.2	1357.6	1321.2
20°	1383.9	1391.9	1393.1	1402.5	1407.7	1414.6	1417.4	1412.9	1398.8	1374.1	1342.6
22.5°	1317.9	1320.1	1323.9	1338.4	1349.8	1367.0	1376.0	1391.0	1385.5	1373.5	1347.1
25°	1203.5	1199.4	1213.6	1220.8	1247.1	1274.6	1294.5	1316.3	1335.7	1347.4	1339.7
27.5°	1066.1	1060.1	1081.2	1100.6	1122.0	1151.8	1182.6	1219.1	1249.4	1287.4	1300.4
30°	950.3	953.9	974.2	994.8	1027.1	1069.2	1104.0	1144.1	1187.3	1229.8	1259.3
32.5°	825.5	839.5	852.2	883.8	912.3	959.3	1010.2	1060.3	1114.2	1162.4	1208.2
35°	655.1	671.3	689.1	712.2	752.2	798.7	848.4	915.9	989.6	1055.5	1109.7
37.5°	551.4	548.8	559.0	575.7	608.2	645.6	702.9	769.7	856.3	933.7	1010.2
40°	489.3	487.7	495.0	510.3	535.0	562.5	612.7	671.3	751.8	846.4	937.4
42.5°	446.6	447.6	451.6	462.5	479.3	502.0	539.6	589.5	663.1	752.3	850.0
45°	394.7	397.5	402.0	407.3	416.9	435.5	456.5	492.2	550.4	624.8	721.0
47.5°	357.4	357.4	361.9	366.5	372.3	382.8	400.0	422.2	463.3	523.9	606.7
50°	337.2	334.5	337.7	341.3	347.4	354.7	366.0	387.0	414.5	463.4	532.6
52.5°	312.7	312.8	315.7	317.0	322.5	329.7	340.1	354.7	379.5	417.8	474.7
55°	277.4	279.4	281.1	283.4	288.4	293.6	301.7	311.4	330.8	359.5	401.6
57.5°	244.2	244.9	246.5	251.1	254.2	259.0	266.7	275.5	288.2	309.4	341.0
60°	221.6	221.6	224.8	226.9	230.9	235.8	241.9	250.3	261.7	279.0	304.5
62.5°	200.9	200.6	201.8	205.2	208.3	212.8	218.9	226.1	236.7	252.2	273.1
65°	170.6	169.8	172.3	173.1	176.3	180.8	185.6	193.3	201.8	213.1	231.7
67.5°	141.6	142.5	143.8	145.4	147.1	151.8	155.0	160.5	167.6	177.1	189.6
70°	125.3	125.3	125.3	126.6	129.0	131.4	134.7	139.1	146.0	154.1	165.4
72.5°	107.3	108.5	109.8	109.1	112.2	113.6	117.5	120.0	126.6	131.7	141.8
75°	84.1	84.1	84.1	86.1	87.4	88.6	91.0	93.4	96.6	103.1	108.4
77.5°	62.7	62.6	63.0	63.5	64.8	66.2	66.9	69.2	72.2	75.1	79.6
80°	48.6	49.4	49.7	50.5	50.5	51.3	51.7	54.6	56.6	58.6	61.5
82.5°	37.5	37.7	37.8	37.9	38.3	38.7	39.8	40.7	41.4	43.1	45.3
85°	21.9	21.5	21.5	22.3	21.9	21.9	22.7	23.4	23.4	23.8	25.0
87.5°	10.3	10.3	10.6	10.3	10.3	10.5	10.4	10.2	10.6	10.9	11.2
90°	9.3	9.3	9.3	9.3	9.3	9.0	8.4	9.0	9.3	9.5	9.3
92.5°	15.5	15.9	15.8	16.6	16.9	18.6	20.9	24.4	30.7	36.4	35.9
95°	31.9	31.6	32.5	34.7	38.3	44.5	56.2	73.4	96.0	109.7	97.1
97.5°	62.8	65.2	69.2	76.1	89.5	109.7	140.0	171.1	196.5	187.3	141.1
100°	100.2	105.3	113.4	125.4	148.6	182.5	220.9	255.6	261.4	221.1	152.3
102.5°	176.3	183.2	193.3	213.8	239.1	275.0	303.0	310.9	285.6	222.2	148.0
105°	315.4	319.3	331.4	348.7	366.1	375.3	371.7	340.1	281.9	207.4	139.7
107.5°	403.0	408.1	410.6	411.5	409.3	395.8	366.7	319.0	257.3	191.5	135.5
110°	429.4	429.7	427.1	421.8	409.8	386.8	351.0	300.9	241.9	183.9	134.7



TEST NUMBER: P331332-927

CATALOG NUMBER: S122DIP-S675D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	428.9	427.4	422.6	413.8	397.0	370.7	332.4	284.3	231.1	179.0	134.8
115°	415.1	412.6	405.3	392.4	372.6	343.7	307.0	264.0	217.8	173.6	136.0
117.5°	390.4	388.2	380.6	367.0	346.7	319.7	286.5	248.6	209.4	170.9	138.1
120°	374.5	371.7	363.6	350.5	330.8	305.4	275.7	241.0	204.9	169.4	139.4
122.5°	357.9	355.6	348.4	335.4	317.8	294.9	266.7	235.0	201.1	168.4	140.9
125°	336.8	334.5	327.5	316.9	300.6	279.6	255.0	226.2	195.7	166.8	143.3
127.5°	318.1	316.3	310.3	300.3	286.1	266.8	243.6	217.5	190.6	165.9	145.7
130°	307.6	305.4	299.8	290.3	276.6	258.1	236.0	211.9	187.3	165.4	147.5
132.5°	296.7	294.6	289.5	280.0	266.5	249.1	228.8	206.5	184.6	165.2	149.3
135°	279.1	278.0	272.9	263.6	251.6	236.0	217.5	199.0	180.8	164.9	151.5
137.5°	261.8	260.2	255.7	247.8	236.8	223.2	208.5	193.1	178.2	164.8	153.4
140°	249.9	248.3	244.1	236.8	227.8	215.6	202.6	189.2	176.6	164.6	154.2
142.5°	238.1	237.7	234.0	227.4	218.9	208.6	197.5	186.1	175.1	164.6	154.9
145°	222.8	222.0	219.2	214.4	207.7	199.6	190.9	181.6	173.0	164.0	155.6
147.5°	210.0	209.5	207.6	203.7	198.2	192.3	185.5	178.2	170.9	163.0	155.8
150°	202.4	202.1	200.4	197.0	192.8	187.8	182.0	175.8	169.1	162.3	155.6
152.5°	195.9	195.8	194.6	191.7	188.4	184.0	179.0	173.3	167.5	161.2	155.2
155°	187.3	187.8	186.7	184.7	181.6	178.6	174.4	169.9	164.6	159.2	154.5
157.5°	179.9	179.9	179.4	177.8	175.6	173.2	169.7	166.0	161.8	157.2	153.2
160°	175.2	175.2	174.9	173.6	171.6	169.6	166.5	163.4	159.8	155.9	152.6
162.5°	170.7	171.0	170.7	169.8	167.8	166.3	163.7	161.0	158.0	154.8	151.9
165°	164.3	164.6	164.6	163.4	162.3	161.2	159.2	157.3	155.0	152.6	150.6
167.5°	158.4	158.7	158.8	158.1	157.6	156.6	155.3	153.8	152.2	150.6	149.3
170°	154.8	155.3	155.6	154.8	154.5	153.9	152.8	152.0	150.6	149.5	148.6
172.5°	151.9	152.2	152.5	152.1	151.8	151.5	150.6	150.0	149.0	148.1	147.7
175°	148.1	148.6	148.9	148.6	148.6	148.4	148.1	147.8	146.9	146.6	146.4
177.5°	145.8	146.2	146.5	146.5	146.5	146.5	146.2	146.2	145.8	145.5	145.8
180°	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5



TEST NUMBER: P331332-927

CATALOG NUMBER: S122DIP-S675D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1079.7	1077.1	1075.5	1069.7	1064.5	1059.4	1057.7	1058.4	1051.3	1044.5	1041.6
5°	1121.8	1113.7	1106.0	1095.1	1082.2	1068.0	1060.7	1055.0	1040.9	1025.6	1016.7
7.5°	1159.5	1148.0	1133.1	1112.5	1093.8	1071.5	1057.3	1044.8	1024.1	1002.4	989.1
10°	1182.5	1166.6	1147.6	1122.6	1099.5	1072.5	1053.4	1034.4	1010.2	984.3	968.1
12.5°	1202.2	1180.9	1162.2	1130.0	1102.8	1068.9	1046.3	1019.5	994.0	963.3	947.5
15°	1249.2	1210.0	1174.3	1138.0	1104.4	1057.1	1032.1	996.0	962.4	924.5	906.3
17.5°	1285.5	1241.4	1185.3	1139.1	1099.9	1047.6	1010.7	967.7	928.0	884.5	859.8
20°	1306.2	1255.6	1195.4	1140.4	1093.4	1033.6	993.6	949.5	903.0	854.1	827.4
22.5°	1318.5	1265.4	1205.8	1135.5	1080.5	1022.3	971.9	923.6	876.5	823.7	795.7
25°	1322.4	1273.8	1210.8	1131.5	1064.4	998.5	937.8	890.9	833.9	784.5	743.7
27.5°	1303.1	1268.4	1207.7	1123.9	1045.7	968.6	901.0	847.9	787.7	734.1	693.1
30°	1279.5	1259.3	1200.2	1116.1	1030.8	947.9	873.5	813.3	753.4	699.2	657.1
32.5°	1242.9	1238.6	1186.7	1105.1	1014.9	921.7	844.7	783.8	717.5	664.2	624.2
35°	1171.2	1190.6	1157.8	1080.5	985.1	884.4	801.1	731.6	662.8	611.9	574.3
37.5°	1074.9	1123.1	1114.5	1044.6	944.8	843.8	751.9	679.1	613.6	562.2	525.3
40°	1008.5	1070.0	1079.0	1017.1	916.4	812.5	714.9	642.6	578.7	531.8	494.6
42.5°	937.4	1009.2	1033.6	984.0	885.3	779.4	682.0	607.0	543.8	498.1	465.2
45°	818.1	913.1	957.2	928.9	833.5	725.1	624.8	548.7	491.3	448.5	423.0
47.5°	706.5	810.4	869.7	859.7	775.8	668.4	569.3	496.4	440.5	406.2	383.4
50°	627.6	734.4	806.0	809.2	734.4	628.0	528.5	459.8	408.4	376.5	357.9
52.5°	559.0	660.9	739.0	756.1	688.1	586.0	492.0	423.6	378.3	349.0	332.3
55°	469.5	555.6	642.1	673.8	619.1	522.0	435.1	374.9	332.4	312.2	297.6
57.5°	390.3	462.2	542.1	576.9	543.3	460.2	378.7	326.4	291.9	274.2	263.0
60°	348.6	405.2	476.3	518.0	488.9	414.9	343.7	294.0	265.7	249.9	239.4
62.5°	309.7	359.9	420.1	458.2	442.4	372.6	308.8	264.9	240.4	225.6	218.1
65°	255.6	295.2	341.7	376.9	366.4	313.4	261.3	223.6	204.2	192.5	186.4
67.5°	210.5	239.1	271.3	302.1	293.7	256.1	214.3	185.0	170.5	160.4	156.8
70°	182.0	203.8	232.5	257.2	250.3	219.6	186.4	161.4	148.9	140.3	136.7
72.5°	154.8	172.8	194.6	214.8	210.2	184.7	157.0	138.1	128.4	120.6	117.6
75°	116.8	130.6	143.9	157.3	156.1	136.3	120.1	105.5	97.8	91.8	90.5
77.5°	86.3	94.0	103.1	111.0	108.8	97.4	84.8	76.4	70.7	66.7	66.1
80°	65.9	70.3	76.8	82.5	79.7	74.8	64.7	58.6	54.6	50.5	49.0
82.5°	47.8	52.3	56.2	59.2	57.0	52.5	46.3	42.1	39.7	37.0	36.3
85°	25.0	27.5	29.2	29.9	29.2	26.3	23.4	21.9	19.8	18.6	18.2
87.5°	11.2	10.9	10.5	11.0	9.9	9.8	8.3	7.2	7.1	6.9	6.4
90°	7.5	5.6	4.2	3.3	2.8	2.2	1.1	0.3	1.1	2.2	2.8
92.5°	28.0	19.0	12.7	10.1	8.2	7.0	4.9	3.4	4.9	7.0	8.2
95°	64.6	40.3	27.4	20.7	16.2	13.7	10.9	9.8	10.9	13.7	16.2
97.5°	87.1	53.2	37.0	29.4	24.2	20.4	17.4	15.9	17.4	20.4	24.2
100°	91.8	57.7	42.9	35.0	29.4	24.9	22.4	21.5	22.4	24.9	29.4
102.5°	92.1	61.7	48.0	40.2	34.3	29.9	27.3	26.7	27.3	29.9	34.3
105°	93.5	68.6	55.5	47.6	41.4	37.2	35.3	34.1	35.3	37.2	41.4
107.5°	97.4	75.7	62.9	55.0	48.9	45.0	43.1	42.2	43.1	45.0	48.9
110°	100.4	80.3	68.0	59.9	54.0	50.4	48.7	47.6	48.7	50.4	54.0



TEST NUMBER: P331332-927

CATALOG NUMBER: S122DIP-S675D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	103.9	84.8	73.0	64.6	58.9	55.5	53.6	52.5	53.6	55.5	58.9
115°	108.8	91.8	79.8	72.2	66.6	63.3	61.6	60.2	61.6	63.3	66.6
117.5°	114.2	98.2	87.1	79.3	73.9	70.9	69.2	68.1	69.2	70.9	73.9
120°	117.9	102.7	91.8	84.0	78.3	75.9	74.1	73.0	74.1	75.9	78.3
122.5°	121.0	106.9	96.7	88.6	83.1	80.3	78.7	77.8	78.7	80.3	83.1
125°	126.0	113.4	103.3	95.5	89.8	86.5	84.8	84.0	84.8	86.5	89.8
127.5°	130.6	119.3	109.5	101.4	96.1	92.4	90.0	88.9	90.0	92.4	96.1
130°	133.5	122.9	113.0	105.3	99.7	95.7	92.9	91.8	92.9	95.7	99.7
132.5°	136.4	126.0	116.7	108.8	103.0	98.9	95.9	94.5	95.9	98.9	103.0
135°	140.2	130.5	121.4	113.7	107.2	103.0	99.7	98.5	99.7	103.0	107.2
137.5°	143.1	134.0	125.2	117.9	111.5	107.0	103.7	102.3	103.7	107.0	111.5
140°	144.7	136.0	127.6	120.3	114.2	109.7	106.4	105.3	106.4	109.7	114.2
142.5°	146.1	137.6	129.4	122.6	116.7	112.2	109.1	108.1	109.1	112.2	116.7
145°	147.8	140.0	132.4	126.3	120.6	116.5	113.7	112.5	113.7	116.5	120.6
147.5°	148.8	141.9	134.8	129.3	124.6	120.7	118.0	117.2	118.0	120.7	124.6
150°	149.2	142.8	136.3	131.3	127.1	123.4	121.2	120.3	121.2	123.4	127.1
152.5°	149.4	143.6	137.8	133.3	129.3	126.1	123.9	123.5	123.9	126.1	129.3
155°	149.7	145.0	140.2	136.0	132.9	129.8	128.2	127.9	128.2	129.8	132.9
157.5°	149.7	145.9	141.9	138.4	135.9	133.2	131.9	131.6	131.9	133.2	135.9
160°	149.7	146.4	143.1	140.0	137.7	135.5	134.4	134.0	134.4	135.5	137.7
162.5°	149.5	146.6	143.7	141.3	139.3	137.5	136.3	136.6	136.3	137.5	139.3
165°	148.9	146.9	144.4	142.8	141.3	139.7	139.1	139.4	139.1	139.7	141.3
167.5°	148.5	146.9	145.0	144.0	143.0	141.9	141.4	141.7	141.4	141.9	143.0
170°	148.1	146.6	145.3	144.4	143.9	143.1	142.8	143.3	142.8	143.1	143.9
172.5°	147.4	146.5	145.5	144.9	144.6	143.7	143.9	144.2	143.9	143.7	144.6
175°	146.6	146.1	145.5	145.3	145.3	144.7	145.0	145.3	145.0	144.7	145.3
177.5°	146.2	145.8	145.5	145.5	145.5	145.1	145.3	145.8	145.3	145.1	145.5
180°	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5



TEST NUMBER: P331332-927

CATALOG NUMBER: S122DIP-S675D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1038.3	1036.4	1029.6	1026.0	1020.2	1014.7	1011.1	1012.8	1014.1	1013.4	1012.4
5°	1008.5	1000.8	989.1	979.1	971.8	958.4	952.8	949.9	947.5	944.7	941.8
7.5°	973.1	961.0	944.2	929.8	916.2	899.6	890.2	884.5	878.7	872.3	866.6
10°	947.9	930.9	913.1	892.9	876.7	861.7	848.4	839.6	831.5	823.8	818.1
12.5°	921.4	901.8	879.8	852.2	834.3	812.9	810.9	795.2	782.6	777.8	771.2
15°	879.2	851.7	823.8	791.0	776.8	757.4	745.3	733.2	722.2	714.5	712.6
17.5°	831.2	795.6	767.9	744.3	721.1	701.2	690.1	680.3	671.4	661.1	659.7
20°	794.6	763.9	733.6	713.0	689.1	668.8	655.1	645.4	637.7	631.7	626.4
22.5°	760.0	726.4	698.6	676.0	652.5	636.2	625.3	616.0	609.6	602.9	597.9
25°	704.5	678.2	647.8	622.3	602.9	592.5	583.5	575.4	571.4	567.0	561.3
27.5°	655.8	626.6	598.3	578.5	561.5	552.2	545.8	540.3	536.5	533.9	530.8
30°	621.5	592.0	569.8	550.4	536.2	527.0	522.9	519.7	515.2	513.6	512.0
32.5°	588.6	562.0	543.0	526.1	512.6	506.5	502.8	499.9	496.5	494.8	491.5
35°	541.9	519.7	501.1	491.7	480.9	475.5	472.8	468.7	465.5	463.8	463.4
37.5°	498.0	478.6	466.4	454.5	449.9	446.6	442.8	440.0	439.0	438.8	438.4
40°	469.5	453.8	442.8	433.1	431.1	426.2	423.0	420.6	420.6	421.0	420.6
42.5°	443.6	429.4	419.9	411.5	409.1	406.2	402.9	402.7	403.5	404.8	403.5
45°	404.4	394.3	387.4	383.3	378.9	376.0	375.7	376.9	377.3	377.7	378.9
47.5°	368.3	361.6	355.4	350.9	349.0	348.5	348.0	350.1	352.0	352.8	354.7
50°	347.0	339.3	334.1	331.2	329.5	328.8	329.5	332.0	333.6	335.6	336.8
52.5°	323.1	317.6	313.9	311.8	311.2	311.6	311.8	314.6	317.1	317.8	318.5
55°	289.9	285.9	285.1	281.5	283.0	282.7	284.7	286.3	288.8	291.1	291.6
57.5°	257.0	253.7	251.5	251.8	252.3	254.1	255.8	258.6	261.3	263.8	264.0
60°	235.0	233.3	232.1	232.1	232.9	235.4	237.4	240.2	241.9	243.4	244.6
62.5°	214.9	213.3	212.1	212.7	214.8	216.3	218.6	220.1	221.7	223.4	223.9
65°	183.2	182.4	183.6	184.4	184.8	186.8	189.6	190.8	192.5	193.3	196.1
67.5°	154.0	154.2	154.0	155.1	157.5	158.0	160.7	163.4	163.7	165.3	167.2
70°	134.3	135.1	135.9	136.7	138.7	139.5	141.6	142.8	144.3	145.6	146.8
72.5°	116.1	116.3	117.1	116.9	118.7	120.4	122.2	123.3	124.9	126.5	127.7
75°	89.4	89.4	90.2	90.5	92.6	94.7	94.2	95.1	96.6	98.2	99.1
77.5°	65.3	64.4	65.3	65.7	66.3	68.0	68.4	69.5	71.3	70.7	71.7
80°	49.7	48.6	49.7	50.1	50.1	52.2	52.2	53.0	54.2	53.0	54.2
82.5°	35.5	34.9	35.8	35.9	36.5	36.6	37.3	37.5	38.7	38.1	38.7
85°	17.8	17.4	17.8	17.4	17.8	18.2	18.2	17.8	17.8	18.6	17.4
87.5°	6.2	6.0	5.9	6.3	6.3	6.1	5.7	5.7	5.5	5.0	5.1
90°	3.3	4.2	5.6	7.5	9.3	9.5	9.3	9.0	8.4	9.0	9.3
92.5°	10.1	12.7	19.0	28.0	35.9	36.4	30.7	24.4	20.9	18.6	16.9
95°	20.7	27.4	40.3	64.6	97.1	109.7	96.0	73.4	56.2	44.5	38.3
97.5°	29.4	37.0	53.2	87.1	141.1	187.3	196.5	171.1	140.0	109.7	89.5
100°	35.0	42.9	57.7	91.8	152.3	221.1	261.4	255.6	220.9	182.5	148.6
102.5°	40.2	48.0	61.7	92.1	148.0	222.2	285.6	310.9	303.0	275.0	239.1
105°	47.6	55.5	68.6	93.5	139.7	207.4	281.9	340.1	371.7	375.3	366.1
107.5°	55.0	62.9	75.7	97.4	135.5	191.5	257.3	319.0	366.7	395.8	409.3
110°	59.9	68.0	80.3	100.4	134.7	183.9	241.9	300.9	351.0	386.8	409.8



TEST NUMBER: P331332-927

CATALOG NUMBER: S122DIP-S675D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	64.6	73.0	84.8	103.9	134.8	179.0	231.1	284.3	332.4	370.7	397.0
115°	72.2	79.8	91.8	108.8	136.0	173.6	217.8	264.0	307.0	343.7	372.6
117.5°	79.3	87.1	98.2	114.2	138.1	170.9	209.4	248.6	286.5	319.7	346.7
120°	84.0	91.8	102.7	117.9	139.4	169.4	204.9	241.0	275.7	305.4	330.8
122.5°	88.6	96.7	106.9	121.0	140.9	168.4	201.1	235.0	266.7	294.9	317.8
125°	95.5	103.3	113.4	126.0	143.3	166.8	195.7	226.2	255.0	279.6	300.6
127.5°	101.4	109.5	119.3	130.6	145.7	165.9	190.6	217.5	243.6	266.8	286.1
130°	105.3	113.0	122.9	133.5	147.5	165.4	187.3	211.9	236.0	258.1	276.6
132.5°	108.8	116.7	126.0	136.4	149.3	165.2	184.6	206.5	228.8	249.1	266.5
135°	113.7	121.4	130.5	140.2	151.5	164.9	180.8	199.0	217.5	236.0	251.6
137.5°	117.9	125.2	134.0	143.1	153.4	164.8	178.2	193.1	208.5	223.2	236.8
140°	120.3	127.6	136.0	144.7	154.2	164.6	176.6	189.2	202.6	215.6	227.8
142.5°	122.6	129.4	137.6	146.1	154.9	164.6	175.1	186.1	197.5	208.6	218.9
145°	126.3	132.4	140.0	147.8	155.6	164.0	173.0	181.6	190.9	199.6	207.7
147.5°	129.3	134.8	141.9	148.8	155.8	163.0	170.9	178.2	185.5	192.3	198.2
150°	131.3	136.3	142.8	149.2	155.6	162.3	169.1	175.8	182.0	187.8	192.8
152.5°	133.3	137.8	143.6	149.4	155.2	161.2	167.5	173.3	179.0	184.0	188.4
155°	136.0	140.2	145.0	149.7	154.5	159.2	164.6	169.9	174.4	178.6	181.6
157.5°	138.4	141.9	145.9	149.7	153.2	157.2	161.8	166.0	169.7	173.2	175.6
160°	140.0	143.1	146.4	149.7	152.6	155.9	159.8	163.4	166.5	169.6	171.6
162.5°	141.3	143.7	146.6	149.5	151.9	154.8	158.0	161.0	163.7	166.3	167.8
165°	142.8	144.4	146.9	148.9	150.6	152.6	155.0	157.3	159.2	161.2	162.3
167.5°	144.0	145.0	146.9	148.5	149.3	150.6	152.2	153.8	155.3	156.6	157.6
170°	144.4	145.3	146.6	148.1	148.6	149.5	150.6	152.0	152.8	153.9	154.5
172.5°	144.9	145.5	146.5	147.4	147.7	148.1	149.0	150.0	150.6	151.5	151.8
175°	145.3	145.5	146.1	146.6	146.4	146.6	146.9	147.8	148.1	148.4	148.6
177.5°	145.5	145.5	145.8	146.2	145.8	145.5	145.8	146.2	146.2	146.5	146.5
180°	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5



TEST NUMBER: P331332-927

CATALOG NUMBER: S122DIP-S675D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1009.2	1008.5	1008.5	1005.7	1008.5	1008.5	1009.2	1012.4	1013.4	1014.1	1012.8
5°	936.2	934.9	933.0	934.9	933.0	934.9	936.2	941.8	944.7	947.5	949.9
7.5°	864.0	859.1	858.4	853.6	858.4	859.1	864.0	866.6	872.3	878.7	884.5
10°	811.2	807.9	807.6	799.9	807.6	807.9	811.2	818.1	823.8	831.5	839.6
12.5°	771.1	763.3	764.9	760.4	764.9	763.3	771.1	771.2	777.8	782.6	795.2
15°	701.6	701.6	700.0	693.2	700.0	701.6	701.6	712.6	714.5	722.2	733.2
17.5°	651.7	650.9	647.1	649.0	647.1	650.9	651.7	659.7	661.1	671.4	680.3
20°	621.9	619.6	614.7	614.7	614.7	619.6	621.9	626.4	631.7	637.7	645.4
22.5°	593.8	593.7	588.5	590.1	588.5	593.7	593.8	597.9	602.9	609.6	616.0
25°	560.9	557.7	555.2	556.4	555.2	557.7	560.9	561.3	567.0	571.4	575.4
27.5°	529.7	527.9	527.8	524.4	527.8	527.9	529.7	530.8	533.9	536.5	540.3
30°	511.6	507.6	508.3	506.3	508.3	507.6	511.6	512.0	513.6	515.2	519.7
32.5°	490.8	489.4	488.6	486.9	488.6	489.4	490.8	491.5	494.8	496.5	499.9
35°	462.6	463.0	461.1	461.8	461.1	463.0	462.6	463.4	463.8	465.5	468.7
37.5°	438.0	439.3	438.3	438.6	438.3	439.3	438.0	438.4	438.8	439.0	440.0
40°	421.8	421.8	421.8	423.0	421.8	421.8	421.8	420.6	421.0	420.6	420.6
42.5°	406.2	405.6	405.0	404.9	405.0	405.6	406.2	403.5	404.8	403.5	402.7
45°	379.7	381.0	381.4	379.3	381.4	381.0	379.7	378.9	377.7	377.3	376.9
47.5°	355.7	355.8	355.7	357.5	355.7	355.8	355.7	354.7	352.8	352.0	350.1
50°	338.9	338.1	338.9	338.1	338.9	338.1	338.9	336.8	335.6	333.6	332.0
52.5°	321.1	321.2	320.8	320.6	320.8	321.2	321.1	318.5	317.8	317.1	314.6
55°	293.2	294.0	293.6	293.6	293.6	294.0	293.2	291.6	291.1	288.8	286.3
57.5°	264.4	265.1	265.6	263.8	265.6	265.1	264.4	264.0	263.8	261.3	258.6
60°	244.2	246.3	245.9	245.1	245.9	246.3	244.2	244.6	243.4	241.9	240.2
62.5°	225.9	226.6	226.5	226.3	226.5	226.6	225.9	223.9	223.4	221.7	220.1
65°	197.3	198.1	196.9	198.1	196.9	198.1	197.3	196.1	193.3	192.5	190.8
67.5°	166.7	166.9	167.9	168.4	167.9	166.9	166.7	167.2	165.3	163.7	163.4
70°	147.6	147.2	148.4	149.6	148.4	147.2	147.6	146.8	145.6	144.3	142.8
72.5°	127.5	128.4	128.0	128.9	128.0	128.4	127.5	127.7	126.5	124.9	123.3
75°	98.2	99.5	99.1	100.3	99.1	99.5	98.2	99.1	98.2	96.6	95.1
77.5°	71.0	71.1	71.0	71.7	71.0	71.1	71.0	71.7	70.7	71.3	69.5
80°	54.2	53.4	52.6	54.2	52.6	53.4	54.2	54.2	53.0	54.2	53.0
82.5°	37.7	38.2	37.4	37.4	37.4	38.2	37.7	38.7	38.1	38.7	37.5
85°	17.4	17.0	16.2	16.2	16.2	17.0	17.4	17.4	18.6	17.8	17.8
87.5°	5.1	4.8	4.8	4.4	4.8	4.8	5.1	5.1	5.0	5.5	5.7
90°	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.0	8.4	9.0
92.5°	16.6	15.8	15.9	15.5	15.9	15.8	16.6	16.9	18.6	20.9	24.4
95°	34.7	32.5	31.6	31.9	31.6	32.5	34.7	38.3	44.5	56.2	73.4
97.5°	76.1	69.2	65.2	62.8	65.2	69.2	76.1	89.5	109.7	140.0	171.1
100°	125.4	113.4	105.3	100.2	105.3	113.4	125.4	148.6	182.5	220.9	255.6
102.5°	213.8	193.3	183.2	176.3	183.2	193.3	213.8	239.1	275.0	303.0	310.9
105°	348.7	331.4	319.3	315.4	319.3	331.4	348.7	366.1	375.3	371.7	340.1
107.5°	411.5	410.6	408.1	403.0	408.1	410.6	411.5	409.3	395.8	366.7	319.0
110°	421.8	427.1	429.7	429.4	429.7	427.1	421.8	409.8	386.8	351.0	300.9



TEST NUMBER: P331332-927

CATALOG NUMBER: S122DIP-S675D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	413.8	422.6	427.4	428.9	427.4	422.6	413.8	397.0	370.7	332.4	284.3
115°	392.4	405.3	412.6	415.1	412.6	405.3	392.4	372.6	343.7	307.0	264.0
117.5°	367.0	380.6	388.2	390.4	388.2	380.6	367.0	346.7	319.7	286.5	248.6
120°	350.5	363.6	371.7	374.5	371.7	363.6	350.5	330.8	305.4	275.7	241.0
122.5°	335.4	348.4	355.6	357.9	355.6	348.4	335.4	317.8	294.9	266.7	235.0
125°	316.9	327.5	334.5	336.8	334.5	327.5	316.9	300.6	279.6	255.0	226.2
127.5°	300.3	310.3	316.3	318.1	316.3	310.3	300.3	286.1	266.8	243.6	217.5
130°	290.3	299.8	305.4	307.6	305.4	299.8	290.3	276.6	258.1	236.0	211.9
132.5°	280.0	289.5	294.6	296.7	294.6	289.5	280.0	266.5	249.1	228.8	206.5
135°	263.6	272.9	278.0	279.1	278.0	272.9	263.6	251.6	236.0	217.5	199.0
137.5°	247.8	255.7	260.2	261.8	260.2	255.7	247.8	236.8	223.2	208.5	193.1
140°	236.8	244.1	248.3	249.9	248.3	244.1	236.8	227.8	215.6	202.6	189.2
142.5°	227.4	234.0	237.7	238.1	237.7	234.0	227.4	218.9	208.6	197.5	186.1
145°	214.4	219.2	222.0	222.8	222.0	219.2	214.4	207.7	199.6	190.9	181.6
147.5°	203.7	207.6	209.5	210.0	209.5	207.6	203.7	198.2	192.3	185.5	178.2
150°	197.0	200.4	202.1	202.4	202.1	200.4	197.0	192.8	187.8	182.0	175.8
152.5°	191.7	194.6	195.8	195.9	195.8	194.6	191.7	188.4	184.0	179.0	173.3
155°	184.7	186.7	187.8	187.3	187.8	186.7	184.7	181.6	178.6	174.4	169.9
157.5°	177.8	179.4	179.9	179.9	179.9	179.4	177.8	175.6	173.2	169.7	166.0
160°	173.6	174.9	175.2	175.2	175.2	174.9	173.6	171.6	169.6	166.5	163.4
162.5°	169.8	170.7	171.0	170.7	171.0	170.7	169.8	167.8	166.3	163.7	161.0
165°	163.4	164.6	164.6	164.3	164.6	164.6	163.4	162.3	161.2	159.2	157.3
167.5°	158.1	158.8	158.7	158.4	158.7	158.8	158.1	157.6	156.6	155.3	153.8
170°	154.8	155.6	155.3	154.8	155.3	155.6	154.8	154.5	153.9	152.8	152.0
172.5°	152.1	152.5	152.2	151.9	152.2	152.5	152.1	151.8	151.5	150.6	150.0
175°	148.6	148.9	148.6	148.1	148.6	148.9	148.6	148.6	148.4	148.1	147.8
177.5°	146.5	146.5	146.2	145.8	146.2	146.5	146.5	146.5	146.5	146.2	146.2
180°	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5



TEST NUMBER: P331332-927

CATALOG NUMBER: S122DIP-S675D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1011.1	1014.7	1020.2	1026.0	1029.6	1036.4	1038.3	1041.6	1044.5	1051.3	1058.4
5°	952.8	958.4	971.8	979.1	989.1	1000.8	1008.5	1016.7	1025.6	1040.9	1055.0
7.5°	890.2	899.6	916.2	929.8	944.2	961.0	973.1	989.1	1002.4	1024.1	1044.8
10°	848.4	861.7	876.7	892.9	913.1	930.9	947.9	968.1	984.3	1010.2	1034.4
12.5°	810.9	812.9	834.3	852.2	879.8	901.8	921.4	947.5	963.3	994.0	1019.5
15°	745.3	757.4	776.8	791.0	823.8	851.7	879.2	906.3	924.5	962.4	996.0
17.5°	690.1	701.2	721.1	744.3	767.9	795.6	831.2	859.8	884.5	928.0	967.7
20°	655.1	668.8	689.1	713.0	733.6	763.9	794.6	827.4	854.1	903.0	949.5
22.5°	625.3	636.2	652.5	676.0	698.6	726.4	760.0	795.7	823.7	876.5	923.6
25°	583.5	592.5	602.9	622.3	647.8	678.2	704.5	743.7	784.5	833.9	890.9
27.5°	545.8	552.2	561.5	578.5	598.3	626.6	655.8	693.1	734.1	787.7	847.9
30°	522.9	527.0	536.2	550.4	569.8	592.0	621.5	657.1	699.2	753.4	813.3
32.5°	502.8	506.5	512.6	526.1	543.0	562.0	588.6	624.2	664.2	717.5	783.8
35°	472.8	475.5	480.9	491.7	501.1	519.7	541.9	574.3	611.9	662.8	731.6
37.5°	442.8	446.6	449.9	454.5	466.4	478.6	498.0	525.3	562.2	613.6	679.1
40°	423.0	426.2	431.1	433.1	442.8	453.8	469.5	494.6	531.8	578.7	642.6
42.5°	402.9	406.2	409.1	411.5	419.9	429.4	443.6	465.2	498.1	543.8	607.0
45°	375.7	376.0	378.9	383.3	387.4	394.3	404.4	423.0	448.5	491.3	548.7
47.5°	348.0	348.5	349.0	350.9	355.4	361.6	368.3	383.4	406.2	440.5	496.4
50°	329.5	328.8	329.5	331.2	334.1	339.3	347.0	357.9	376.5	408.4	459.8
52.5°	311.8	311.6	311.2	311.8	313.9	317.6	323.1	332.3	349.0	378.3	423.6
55°	284.7	282.7	283.0	281.5	285.1	285.9	289.9	297.6	312.2	332.4	374.9
57.5°	255.8	254.1	252.3	251.8	251.5	253.7	257.0	263.0	274.2	291.9	326.4
60°	237.4	235.4	232.9	232.1	232.1	233.3	235.0	239.4	249.9	265.7	294.0
62.5°	218.6	216.3	214.8	212.7	212.1	213.3	214.9	218.1	225.6	240.4	264.9
65°	189.6	186.8	184.8	184.4	183.6	182.4	183.2	186.4	192.5	204.2	223.6
67.5°	160.7	158.0	157.5	155.1	154.0	154.2	154.0	156.8	160.4	170.5	185.0
70°	141.6	139.5	138.7	136.7	135.9	135.1	134.3	136.7	140.3	148.9	161.4
72.5°	122.2	120.4	118.7	116.9	117.1	116.3	116.1	117.6	120.6	128.4	138.1
75°	94.2	94.7	92.6	90.5	90.2	89.4	89.4	90.5	91.8	97.8	105.5
77.5°	68.4	68.0	66.3	65.7	65.3	64.4	65.3	66.1	66.7	70.7	76.4
80°	52.2	52.2	50.1	50.1	49.7	48.6	49.7	49.0	50.5	54.6	58.6
82.5°	37.3	36.6	36.5	35.9	35.8	34.9	35.5	36.3	37.0	39.7	42.1
85°	18.2	18.2	17.8	17.4	17.8	17.4	17.8	18.2	18.6	19.8	21.9
87.5°	5.7	6.1	6.3	6.3	5.9	6.0	6.2	6.4	6.9	7.1	7.2
90°	9.3	9.5	9.3	7.5	5.6	4.2	3.3	2.8	2.2	1.1	0.3
92.5°	30.7	36.4	35.9	28.0	19.0	12.7	10.1	8.2	7.0	4.9	3.4
95°	96.0	109.7	97.1	64.6	40.3	27.4	20.7	16.2	13.7	10.9	9.8
97.5°	196.5	187.3	141.1	87.1	53.2	37.0	29.4	24.2	20.4	17.4	15.9
100°	261.4	221.1	152.3	91.8	57.7	42.9	35.0	29.4	24.9	22.4	21.5
102.5°	285.6	222.2	148.0	92.1	61.7	48.0	40.2	34.3	29.9	27.3	26.7
105°	281.9	207.4	139.7	93.5	68.6	55.5	47.6	41.4	37.2	35.3	34.1
107.5°	257.3	191.5	135.5	97.4	75.7	62.9	55.0	48.9	45.0	43.1	42.2
110°	241.9	183.9	134.7	100.4	80.3	68.0	59.9	54.0	50.4	48.7	47.6



TEST NUMBER: P331332-927

CATALOG NUMBER: S122DIP-S675D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	231.1	179.0	134.8	103.9	84.8	73.0	64.6	58.9	55.5	53.6	52.5
115°	217.8	173.6	136.0	108.8	91.8	79.8	72.2	66.6	63.3	61.6	60.2
117.5°	209.4	170.9	138.1	114.2	98.2	87.1	79.3	73.9	70.9	69.2	68.1
120°	204.9	169.4	139.4	117.9	102.7	91.8	84.0	78.3	75.9	74.1	73.0
122.5°	201.1	168.4	140.9	121.0	106.9	96.7	88.6	83.1	80.3	78.7	77.8
125°	195.7	166.8	143.3	126.0	113.4	103.3	95.5	89.8	86.5	84.8	84.0
127.5°	190.6	165.9	145.7	130.6	119.3	109.5	101.4	96.1	92.4	90.0	88.9
130°	187.3	165.4	147.5	133.5	122.9	113.0	105.3	99.7	95.7	92.9	91.8
132.5°	184.6	165.2	149.3	136.4	126.0	116.7	108.8	103.0	98.9	95.9	94.5
135°	180.8	164.9	151.5	140.2	130.5	121.4	113.7	107.2	103.0	99.7	98.5
137.5°	178.2	164.8	153.4	143.1	134.0	125.2	117.9	111.5	107.0	103.7	102.3
140°	176.6	164.6	154.2	144.7	136.0	127.6	120.3	114.2	109.7	106.4	105.3
142.5°	175.1	164.6	154.9	146.1	137.6	129.4	122.6	116.7	112.2	109.1	108.1
145°	173.0	164.0	155.6	147.8	140.0	132.4	126.3	120.6	116.5	113.7	112.5
147.5°	170.9	163.0	155.8	148.8	141.9	134.8	129.3	124.6	120.7	118.0	117.2
150°	169.1	162.3	155.6	149.2	142.8	136.3	131.3	127.1	123.4	121.2	120.3
152.5°	167.5	161.2	155.2	149.4	143.6	137.8	133.3	129.3	126.1	123.9	123.5
155°	164.6	159.2	154.5	149.7	145.0	140.2	136.0	132.9	129.8	128.2	127.9
157.5°	161.8	157.2	153.2	149.7	145.9	141.9	138.4	135.9	133.2	131.9	131.6
160°	159.8	155.9	152.6	149.7	146.4	143.1	140.0	137.7	135.5	134.4	134.0
162.5°	158.0	154.8	151.9	149.5	146.6	143.7	141.3	139.3	137.5	136.3	136.6
165°	155.0	152.6	150.6	148.9	146.9	144.4	142.8	141.3	139.7	139.1	139.4
167.5°	152.2	150.6	149.3	148.5	146.9	145.0	144.0	143.0	141.9	141.4	141.7
170°	150.6	149.5	148.6	148.1	146.6	145.3	144.4	143.9	143.1	142.8	143.3
172.5°	149.0	148.1	147.7	147.4	146.5	145.5	144.9	144.6	143.7	143.9	144.2
175°	146.9	146.6	146.4	146.6	146.1	145.5	145.3	145.3	144.7	145.0	145.3
177.5°	145.8	145.5	145.8	146.2	145.8	145.5	145.5	145.5	145.1	145.3	145.8
180°	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5



TEST NUMBER: P331332-927

CATALOG NUMBER: S122DIP-S675D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1057.7	1059.4	1064.5	1069.7	1075.5	1077.1	1079.7	1077.4	1076.8	1083.0	1087.5
5°	1060.7	1068.0	1082.2	1095.1	1106.0	1113.7	1121.8	1125.1	1131.1	1139.6	1150.1
7.5°	1057.3	1071.5	1093.8	1112.5	1133.1	1148.0	1159.5	1169.3	1181.3	1197.4	1215.0
10°	1053.4	1072.5	1099.5	1122.6	1147.6	1166.6	1182.5	1197.8	1215.6	1237.9	1260.9
12.5°	1046.3	1068.9	1102.8	1130.0	1162.2	1180.9	1202.2	1235.3	1254.4	1285.4	1317.9
15°	1032.1	1057.1	1104.4	1138.0	1174.3	1210.0	1249.2	1280.7	1312.2	1330.5	1376.2
17.5°	1010.7	1047.6	1099.9	1139.1	1185.3	1241.4	1285.5	1321.2	1357.6	1387.2	1410.1
20°	993.6	1033.6	1093.4	1140.4	1195.4	1255.6	1306.2	1342.6	1374.1	1398.8	1412.9
22.5°	971.9	1022.3	1080.5	1135.5	1205.8	1265.4	1318.5	1347.1	1373.5	1385.5	1391.0
25°	937.8	998.5	1064.4	1131.5	1210.8	1273.8	1322.4	1339.7	1347.4	1335.7	1316.3
27.5°	901.0	968.6	1045.7	1123.9	1207.7	1268.4	1303.1	1300.4	1287.4	1249.4	1219.1
30°	873.5	947.9	1030.8	1116.1	1200.2	1259.3	1279.5	1259.3	1229.8	1187.3	1144.1
32.5°	844.7	921.7	1014.9	1105.1	1186.7	1238.6	1242.9	1208.2	1162.4	1114.2	1060.3
35°	801.1	884.4	985.1	1080.5	1157.8	1190.6	1171.2	1109.7	1055.5	989.6	915.9
37.5°	751.9	843.8	944.8	1044.6	1114.5	1123.1	1074.9	1010.2	933.7	856.3	769.7
40°	714.9	812.5	916.4	1017.1	1079.0	1070.0	1008.5	937.4	846.4	751.8	671.3
42.5°	682.0	779.4	885.3	984.0	1033.6	1009.2	937.4	850.0	752.3	663.1	589.5
45°	624.8	725.1	833.5	928.9	957.2	913.1	818.1	721.0	624.8	550.4	492.2
47.5°	569.3	668.4	775.8	859.7	869.7	810.4	706.5	606.7	523.9	463.3	422.2
50°	528.5	628.0	734.4	809.2	806.0	734.4	627.6	532.6	463.4	414.5	387.0
52.5°	492.0	586.0	688.1	756.1	739.0	660.9	559.0	474.7	417.8	379.5	354.7
55°	435.1	522.0	619.1	673.8	642.1	555.6	469.5	401.6	359.5	330.8	311.4
57.5°	378.7	460.2	543.3	576.9	542.1	462.2	390.3	341.0	309.4	288.2	275.5
60°	343.7	414.9	488.9	518.0	476.3	405.2	348.6	304.5	279.0	261.7	250.3
62.5°	308.8	372.6	442.4	458.2	420.1	359.9	309.7	273.1	252.2	236.7	226.1
65°	261.3	313.4	366.4	376.9	341.7	295.2	255.6	231.7	213.1	201.8	193.3
67.5°	214.3	256.1	293.7	302.1	271.3	239.1	210.5	189.6	177.1	167.6	160.5
70°	186.4	219.6	250.3	257.2	232.5	203.8	182.0	165.4	154.1	146.0	139.1
72.5°	157.0	184.7	210.2	214.8	194.6	172.8	154.8	141.8	131.7	126.6	120.0
75°	120.1	136.3	156.1	157.3	143.9	130.6	116.8	108.4	103.1	96.6	93.4
77.5°	84.8	97.4	108.8	111.0	103.1	94.0	86.3	79.6	75.1	72.2	69.2
80°	64.7	74.8	79.7	82.5	76.8	70.3	65.9	61.5	58.6	56.6	54.6
82.5°	46.3	52.5	57.0	59.2	56.2	52.3	47.8	45.3	43.1	41.4	40.7
85°	23.4	26.3	29.2	29.9	29.2	27.5	25.0	25.0	23.8	23.4	23.4
87.5°	8.3	9.8	9.9	11.0	10.5	10.9	11.2	11.2	10.9	10.6	10.2
90°	1.1	2.2	2.8	3.3	4.2	5.6	7.5	9.3	9.5	9.3	9.0
92.5°	4.9	7.0	8.2	10.1	12.7	19.0	28.0	35.9	36.4	30.7	24.4
95°	10.9	13.7	16.2	20.7	27.4	40.3	64.6	97.1	109.7	96.0	73.4
97.5°	17.4	20.4	24.2	29.4	37.0	53.2	87.1	141.1	187.3	196.5	171.1
100°	22.4	24.9	29.4	35.0	42.9	57.7	91.8	152.3	221.1	261.4	255.6
102.5°	27.3	29.9	34.3	40.2	48.0	61.7	92.1	148.0	222.2	285.6	310.9
105°	35.3	37.2	41.4	47.6	55.5	68.6	93.5	139.7	207.4	281.9	340.1
107.5°	43.1	45.0	48.9	55.0	62.9	75.7	97.4	135.5	191.5	257.3	319.0
110°	48.7	50.4	54.0	59.9	68.0	80.3	100.4	134.7	183.9	241.9	300.9



TEST NUMBER: P331332-927

CATALOG NUMBER: S122DIP-S675D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	53.6	55.5	58.9	64.6	73.0	84.8	103.9	134.8	179.0	231.1	284.3
115°	61.6	63.3	66.6	72.2	79.8	91.8	108.8	136.0	173.6	217.8	264.0
117.5°	69.2	70.9	73.9	79.3	87.1	98.2	114.2	138.1	170.9	209.4	248.6
120°	74.1	75.9	78.3	84.0	91.8	102.7	117.9	139.4	169.4	204.9	241.0
122.5°	78.7	80.3	83.1	88.6	96.7	106.9	121.0	140.9	168.4	201.1	235.0
125°	84.8	86.5	89.8	95.5	103.3	113.4	126.0	143.3	166.8	195.7	226.2
127.5°	90.0	92.4	96.1	101.4	109.5	119.3	130.6	145.7	165.9	190.6	217.5
130°	92.9	95.7	99.7	105.3	113.0	122.9	133.5	147.5	165.4	187.3	211.9
132.5°	95.9	98.9	103.0	108.8	116.7	126.0	136.4	149.3	165.2	184.6	206.5
135°	99.7	103.0	107.2	113.7	121.4	130.5	140.2	151.5	164.9	180.8	199.0
137.5°	103.7	107.0	111.5	117.9	125.2	134.0	143.1	153.4	164.8	178.2	193.1
140°	106.4	109.7	114.2	120.3	127.6	136.0	144.7	154.2	164.6	176.6	189.2
142.5°	109.1	112.2	116.7	122.6	129.4	137.6	146.1	154.9	164.6	175.1	186.1
145°	113.7	116.5	120.6	126.3	132.4	140.0	147.8	155.6	164.0	173.0	181.6
147.5°	118.0	120.7	124.6	129.3	134.8	141.9	148.8	155.8	163.0	170.9	178.2
150°	121.2	123.4	127.1	131.3	136.3	142.8	149.2	155.6	162.3	169.1	175.8
152.5°	123.9	126.1	129.3	133.3	137.8	143.6	149.4	155.2	161.2	167.5	173.3
155°	128.2	129.8	132.9	136.0	140.2	145.0	149.7	154.5	159.2	164.6	169.9
157.5°	131.9	133.2	135.9	138.4	141.9	145.9	149.7	153.2	157.2	161.8	166.0
160°	134.4	135.5	137.7	140.0	143.1	146.4	149.7	152.6	155.9	159.8	163.4
162.5°	136.3	137.5	139.3	141.3	143.7	146.6	149.5	151.9	154.8	158.0	161.0
165°	139.1	139.7	141.3	142.8	144.4	146.9	148.9	150.6	152.6	155.0	157.3
167.5°	141.4	141.9	143.0	144.0	145.0	146.9	148.5	149.3	150.6	152.2	153.8
170°	142.8	143.1	143.9	144.4	145.3	146.6	148.1	148.6	149.5	150.6	152.0
172.5°	143.9	143.7	144.6	144.9	145.5	146.5	147.4	147.7	148.1	149.0	150.0
175°	145.0	144.7	145.3	145.3	145.5	146.1	146.6	146.4	146.6	146.9	147.8
177.5°	145.3	145.1	145.5	145.5	145.5	145.8	146.2	145.8	145.5	145.8	146.2
180°	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5



TEST NUMBER: P331332-927

CATALOG NUMBER: S122DIP-S675D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1091.4	1095.9	1095.9	1096.5	1101.8	1101.1	1100.7
5°	1161.4	1168.3	1169.1	1176.4	1181.2	1179.6	1175.2
7.5°	1227.5	1240.3	1250.0	1255.4	1261.8	1265.7	1264.0
10°	1279.9	1298.5	1309.9	1317.6	1326.8	1333.7	1331.3
12.5°	1327.5	1349.6	1365.2	1378.3	1379.6	1388.4	1382.4
15°	1401.6	1425.1	1427.5	1437.3	1444.9	1444.1	1444.5
17.5°	1426.2	1433.7	1435.2	1435.4	1435.5	1432.7	1426.6
20°	1417.4	1414.6	1407.7	1402.5	1393.1	1391.9	1383.9
22.5°	1376.0	1367.0	1349.8	1338.4	1323.9	1320.1	1317.9
25°	1294.5	1274.6	1247.1	1220.8	1213.6	1199.4	1203.5
27.5°	1182.6	1151.8	1122.0	1100.6	1081.2	1060.1	1066.1
30°	1104.0	1069.2	1027.1	994.8	974.2	953.9	950.3
32.5°	1010.2	959.3	912.3	883.8	852.2	839.5	825.5
35°	848.4	798.7	752.2	712.2	689.1	671.3	655.1
37.5°	702.9	645.6	608.2	575.7	559.0	548.8	551.4
40°	612.7	562.5	535.0	510.3	495.0	487.7	489.3
42.5°	539.6	502.0	479.3	462.5	451.6	447.6	446.6
45°	456.5	435.5	416.9	407.3	402.0	397.5	394.7
47.5°	400.0	382.8	372.3	366.5	361.9	357.4	357.4
50°	366.0	354.7	347.4	341.3	337.7	334.5	337.2
52.5°	340.1	329.7	322.5	317.0	315.7	312.8	312.7
55°	301.7	293.6	288.4	283.4	281.1	279.4	277.4
57.5°	266.7	259.0	254.2	251.1	246.5	244.9	244.2
60°	241.9	235.8	230.9	226.9	224.8	221.6	221.6
62.5°	218.9	212.8	208.3	205.2	201.8	200.6	200.9
65°	185.6	180.8	176.3	173.1	172.3	169.8	170.6
67.5°	155.0	151.8	147.1	145.4	143.8	142.5	141.6
70°	134.7	131.4	129.0	126.6	125.3	125.3	125.3
72.5°	117.5	113.6	112.2	109.1	109.8	108.5	107.3
75°	91.0	88.6	87.4	86.1	84.1	84.1	84.1
77.5°	66.9	66.2	64.8	63.5	63.0	62.6	62.7
80°	51.7	51.3	50.5	50.5	49.7	49.4	48.6
82.5°	39.8	38.7	38.3	37.9	37.8	37.7	37.5
85°	22.7	21.9	21.9	22.3	21.5	21.5	21.9
87.5°	10.4	10.5	10.3	10.3	10.6	10.3	10.3
90°	8.4	9.0	9.3	9.3	9.3	9.3	9.3
92.5°	20.9	18.6	16.9	16.6	15.8	15.9	15.5
95°	56.2	44.5	38.3	34.7	32.5	31.6	31.9
97.5°	140.0	109.7	89.5	76.1	69.2	65.2	62.8
100°	220.9	182.5	148.6	125.4	113.4	105.3	100.2
102.5°	303.0	275.0	239.1	213.8	193.3	183.2	176.3
105°	371.7	375.3	366.1	348.7	331.4	319.3	315.4
107.5°	366.7	395.8	409.3	411.5	410.6	408.1	403.0
110°	351.0	386.8	409.8	421.8	427.1	429.7	429.4



TEST NUMBER: P331332-927

CATALOG NUMBER: S122DIP-S675D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	332.4	370.7	397.0	413.8	422.6	427.4	428.9
115°	307.0	343.7	372.6	392.4	405.3	412.6	415.1
117.5°	286.5	319.7	346.7	367.0	380.6	388.2	390.4
120°	275.7	305.4	330.8	350.5	363.6	371.7	374.5
122.5°	266.7	294.9	317.8	335.4	348.4	355.6	357.9
125°	255.0	279.6	300.6	316.9	327.5	334.5	336.8
127.5°	243.6	266.8	286.1	300.3	310.3	316.3	318.1
130°	236.0	258.1	276.6	290.3	299.8	305.4	307.6
132.5°	228.8	249.1	266.5	280.0	289.5	294.6	296.7
135°	217.5	236.0	251.6	263.6	272.9	278.0	279.1
137.5°	208.5	223.2	236.8	247.8	255.7	260.2	261.8
140°	202.6	215.6	227.8	236.8	244.1	248.3	249.9
142.5°	197.5	208.6	218.9	227.4	234.0	237.7	238.1
145°	190.9	199.6	207.7	214.4	219.2	222.0	222.8
147.5°	185.5	192.3	198.2	203.7	207.6	209.5	210.0
150°	182.0	187.8	192.8	197.0	200.4	202.1	202.4
152.5°	179.0	184.0	188.4	191.7	194.6	195.8	195.9
155°	174.4	178.6	181.6	184.7	186.7	187.8	187.3
157.5°	169.7	173.2	175.6	177.8	179.4	179.9	179.9
160°	166.5	169.6	171.6	173.6	174.9	175.2	175.2
162.5°	163.7	166.3	167.8	169.8	170.7	171.0	170.7
165°	159.2	161.2	162.3	163.4	164.6	164.6	164.3
167.5°	155.3	156.6	157.6	158.1	158.8	158.7	158.4
170°	152.8	153.9	154.5	154.8	155.6	155.3	154.8
172.5°	150.6	151.5	151.8	152.1	152.5	152.2	151.9
175°	148.1	148.4	148.6	148.6	148.9	148.6	148.1
177.5°	146.2	146.5	146.5	146.5	146.5	146.2	145.8
180°	145.5	145.5	145.5	145.5	145.5	145.5	145.5

(END OF REPORT)