

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331629-927

Luminaire Tested: **S122RDIP-S290D725U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331629-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S290D725U927-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3138.7 lumens
Efficiency: N/A
Efficacy: 100.6 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331629-927

CATALOG NUMBER: S122RDIP-S290D725U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot



— 0°-180° - - - 45°-225° - - - 90°-270° - - - 135°-315°



TEST NUMBER: P331629-927

CATALOG NUMBER: S122RDIP-S290D725U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	29
1	93	89	86	83	84	80	77	75	63	61	59	47	46	45	33	32	32	25
2	85	79	73	68	76	71	66	62	56	53	50	42	40	38	29	28	27	22
3	78	69	63	57	70	63	57	52	50	46	42	38	35	33	27	25	24	19
4	72	62	54	49	64	56	49	45	44	40	36	34	31	29	24	22	21	17
5	66	55	48	42	59	50	43	38	40	35	32	31	27	25	22	20	19	15
6	61	49	42	36	54	45	38	34	36	31	28	28	25	22	20	18	17	13
7	56	45	37	32	50	41	34	30	33	28	25	25	22	20	18	16	15	12
8	52	41	33	28	47	37	31	26	30	25	22	23	20	18	17	15	14	11
9	49	37	30	25	44	34	28	23	27	23	20	21	18	16	16	14	12	10
10	45	34	27	23	41	31	25	21	25	21	18	20	17	15	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8360	8360	8360	8360
5°	9339	8413	7460	8413
10°	10362	8355	6466	8355
15°	10870	8232	5095	8232
20°	9424	8052	4409	8052
25°	6180	7803	3935	7803
30°	4161	7500	3563	7500
35°	3370	7121	3213	7121
40°	2995	6709	2974	6709
45°	2710	6224	2653	6224
50°	2467	5745	2459	5745
55°	2320	5210	2291	5210
60°	1941	4724	1918	4724
65°	1639	4290	1857	4290
70°	1511	3829	1751	3829
75°	1416	3337	1616	3337
80°	1302	2743	1432	2743
85°	1204	2167	1260	2167



TEST NUMBER: P331629-927

CATALOG NUMBER: S122RDIP-S290D725U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.1	1.6
10°-20°	136.8	4.4
20°-30°	176.3	5.6
30°-40°	167.5	5.3
40°-50°	143.5	4.6
50°-60°	109.3	3.5
60°-70°	69.1	2.2
70°-80°	34.5	1.1
80°-90°	11.9	0.4
90°-100°	128.7	4.1
100°-110°	436.9	13.9
110°-120°	464.2	14.8
120°-130°	382.1	12.2
130°-140°	306.8	9.8
140°-150°	231.9	7.4
150°-160°	163.0	5.2
160°-170°	95.9	3.1
170°-180°	31.2	1.0
0°-30°	362.2	11.5
0°-40°	529.7	16.9
0°-60°	782.5	24.9
0°-90°	897.9	28.6
90°-120°	1029.8	32.8
90°-150°	1950.7	62.1
90°-180°	2241.0	71.4
0°-180°	3138.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	518	518	518	518	518	
5°	576	519	460	519	576	57
15°	650	492	305	492	650	175
25°	347	438	221	438	347	165
35°	171	361	163	361	171	109
45°	119	273	116	273	119	92
55°	82	185	81	185	82	72
65°	43	112	49	112	43	44
75°	23	54	26	54	23	24
85°	6	12	7	12	6	8
90°	20	1	20	1	20	11
95°	71	22	71	22	71	92
105°	698	76	698	76	698	675
115°	918	133	918	133	918	899
125°	745	186	745	186	745	673
135°	617	218	617	218	617	480
145°	493	249	493	249	493	313
155°	414	283	414	283	414	193
165°	364	308	364	308	364	104
175°	328	321	328	321	328	32
180°	322	322	322	322	322	



TEST NUMBER: P331629-927

CATALOG NUMBER: S122RDIP-S290D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8
2.5°	538.9	539.3	539.8	538.8	538.8	537.9	536.0	534.6	530.5	530.0	530.0
5°	576.2	575.8	576.6	574.2	571.0	570.2	566.8	562.3	557.6	552.5	551.4
7.5°	613.2	612.7	611.2	610.9	608.4	602.9	597.5	591.6	583.8	576.2	572.4
10°	632.0	637.9	634.3	628.0	629.2	620.8	616.3	608.6	602.1	590.7	588.3
12.5°	650.4	652.8	651.6	648.0	646.4	640.6	634.5	627.7	615.8	605.6	596.8
15°	650.3	653.7	654.7	653.6	654.4	654.1	650.9	645.3	634.9	623.7	613.9
17.5°	602.3	604.7	610.6	614.6	619.6	630.3	635.6	637.5	636.0	629.6	622.8
20°	548.5	544.5	561.1	569.5	576.7	594.7	610.2	616.2	625.7	625.5	623.7
22.5°	472.1	473.1	488.8	498.8	519.8	537.9	555.5	577.8	596.3	608.5	615.6
25°	346.9	353.8	369.4	383.1	406.5	440.0	470.4	505.6	538.9	565.2	590.3
27.5°	260.5	261.1	273.5	286.1	300.0	327.4	365.8	407.8	455.3	494.5	539.5
30°	223.2	222.0	227.3	235.0	246.9	268.2	296.9	338.3	385.6	444.7	497.2
32.5°	196.6	196.7	200.7	206.4	216.2	230.5	250.3	283.9	328.6	386.7	448.2
35°	171.0	170.8	173.6	177.8	181.9	191.1	204.6	222.2	253.0	307.1	370.1
37.5°	152.5	153.3	154.7	157.3	161.8	167.0	175.1	187.0	208.8	240.9	293.8
40°	142.1	142.5	144.5	146.6	149.3	153.3	159.9	169.5	185.5	211.0	249.8
42.5°	132.7	133.0	134.4	136.4	138.6	142.5	148.1	156.3	169.3	189.2	221.1
45°	118.7	118.7	120.0	120.9	123.3	126.8	131.3	138.2	147.2	161.9	183.2
47.5°	105.8	105.8	106.6	108.1	109.6	112.4	116.8	122.5	129.0	140.4	158.5
50°	98.2	98.5	98.9	100.2	101.2	103.6	107.1	111.9	118.7	127.6	142.7
52.5°	92.2	92.1	92.8	93.3	94.0	95.7	98.3	102.6	108.7	116.4	128.9
55°	82.4	81.7	82.8	83.7	84.2	84.9	86.3	89.0	94.3	100.8	110.1
57.5°	70.2	69.9	70.7	71.5	73.2	75.1	76.4	78.0	80.7	85.4	94.7
60°	60.1	60.1	61.7	62.3	64.2	66.8	69.3	70.7	73.4	76.4	83.3
62.5°	51.2	51.3	52.0	52.6	53.7	56.8	60.4	63.5	66.1	69.0	73.5
65°	42.9	43.2	43.2	43.6	44.3	45.0	46.4	49.0	53.5	57.6	61.0
67.5°	36.4	36.4	36.6	36.9	37.1	37.9	38.5	39.6	40.6	44.5	48.8
70°	32.0	32.6	32.4	32.7	33.0	33.3	34.0	34.5	36.2	37.1	39.6
72.5°	28.0	28.4	28.4	28.6	29.1	29.2	29.7	30.3	31.3	32.0	33.4
75°	22.7	22.5	22.7	23.1	23.2	23.4	23.4	24.1	24.6	25.3	26.3
77.5°	17.5	17.7	17.7	17.7	17.7	18.1	18.0	18.3	18.9	19.3	19.6
80°	14.0	14.2	14.0	14.2	14.4	14.6	14.4	14.6	15.1	15.4	15.4
82.5°	10.9	10.9	11.0	11.0	11.1	11.1	11.4	11.4	11.8	11.7	11.9
85°	6.5	6.3	6.3	6.3	6.5	6.7	6.5	6.5	6.7	6.7	6.7
87.5°	6.4	6.5	6.5	6.5	6.5	6.4	6.2	6.6	6.5	6.8	6.5
90°	20.4	20.4	20.4	20.4	20.4	19.8	18.6	19.8	20.4	21.1	20.4
92.5°	34.3	35.3	34.8	36.8	37.3	41.1	46.3	54.0	68.0	80.5	79.4
95°	70.6	69.9	71.9	76.8	84.8	98.5	124.5	162.2	212.4	242.7	214.9
97.5°	138.9	144.2	153.2	168.4	198.0	242.7	309.7	378.6	434.7	414.4	312.1
100°	221.7	232.8	250.8	277.4	328.8	403.8	488.6	565.4	578.4	489.2	336.8
102.5°	390.1	405.2	427.6	473.1	528.9	608.3	670.4	687.8	631.8	491.7	327.5
105°	697.9	706.5	733.2	771.6	810.0	830.4	822.4	752.4	623.6	458.8	309.0
107.5°	891.4	903.0	908.3	910.5	905.6	875.6	811.2	705.8	569.2	423.7	299.8
110°	949.9	950.5	945.0	933.2	906.6	855.8	776.6	665.7	535.0	406.9	297.9



TEST NUMBER: P331629-927

CATALOG NUMBER: S122RDIP-S290D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	949.0	945.6	935.1	915.4	878.4	820.1	735.4	629.1	511.3	395.9	298.3
115°	918.4	912.8	896.7	868.2	824.2	760.4	679.3	583.9	481.8	384.0	301.0
117.5°	863.7	859.0	842.1	812.0	767.1	707.3	633.7	550.0	463.2	378.1	305.4
120°	828.5	822.4	804.4	775.3	732.0	675.6	610.0	533.1	453.3	374.6	308.4
122.5°	791.9	786.7	770.7	742.1	703.2	652.3	590.2	519.8	444.9	372.6	311.9
125°	745.0	740.0	724.5	701.0	665.0	618.6	564.1	500.3	432.8	369.1	317.0
127.5°	703.9	699.9	686.5	664.5	633.1	590.3	538.8	481.2	421.7	366.9	322.4
130°	680.6	675.6	663.2	642.1	611.8	570.9	522.0	468.7	414.3	366.0	326.4
132.5°	656.2	651.8	640.4	619.4	589.5	551.1	506.2	456.9	408.4	365.5	330.3
135°	617.4	614.9	603.8	583.4	556.7	522.0	481.2	440.3	400.1	364.7	335.0
137.5°	579.2	575.5	565.8	548.2	523.9	493.7	461.2	427.1	394.2	364.6	339.2
140°	553.0	549.3	540.0	523.9	504.1	476.8	448.4	418.6	390.8	364.1	341.2
142.5°	526.7	526.0	517.7	503.1	484.3	461.4	437.0	411.7	387.3	364.1	342.7
145°	492.9	491.1	484.9	474.4	459.5	441.6	422.3	401.9	382.7	362.9	344.3
147.5°	464.5	463.4	459.2	450.8	438.6	425.4	410.4	394.3	378.0	360.7	344.8
150°	447.7	447.1	443.4	435.9	426.7	415.5	402.5	388.9	374.0	359.2	344.3
152.5°	433.3	433.2	430.5	424.1	416.8	407.1	396.1	383.4	370.6	356.7	343.3
155°	414.3	415.5	413.0	408.7	401.9	395.1	385.8	375.9	364.1	352.4	341.8
157.5°	398.1	398.1	397.0	393.3	388.5	383.2	375.4	367.1	358.1	347.9	339.0
160°	387.6	387.6	387.1	384.0	379.6	375.3	368.4	361.6	353.6	344.9	337.5
162.5°	377.7	378.3	377.6	375.5	371.2	367.8	362.0	356.2	349.6	342.5	336.0
165°	363.5	364.1	364.1	361.6	359.2	356.7	352.4	348.0	343.1	337.5	333.2
167.5°	350.4	351.1	351.3	349.9	348.8	346.5	343.6	340.2	336.6	333.2	330.3
170°	342.5	343.6	344.3	342.5	341.8	340.6	338.1	336.3	333.2	330.7	328.8
172.5°	336.0	336.8	337.4	336.5	335.9	335.2	333.2	331.8	329.7	327.7	326.9
175°	327.6	328.8	329.5	328.8	328.8	328.2	327.6	326.9	325.1	324.5	323.8
177.5°	322.5	323.5	324.0	324.0	324.0	324.0	323.5	323.5	322.5	322.0	322.5
180°	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0



TEST NUMBER: P331629-927

CATALOG NUMBER: S122RDIP-S290D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8
2.5°	530.3	529.1	528.1	525.5	524.2	521.3	520.9	520.8	517.1	513.4	512.4
5°	548.5	545.6	541.3	536.2	531.0	525.6	522.0	519.1	511.9	505.1	501.1
7.5°	566.8	560.6	553.2	543.7	535.7	526.8	520.1	514.2	504.0	494.2	487.6
10°	580.5	570.5	560.5	547.4	537.1	527.0	517.7	509.6	498.1	485.1	475.9
12.5°	589.0	577.9	564.3	551.4	538.1	525.3	512.8	502.4	488.9	475.5	464.6
15°	600.5	588.6	572.0	553.7	536.6	519.8	505.5	492.5	474.9	458.8	445.5
17.5°	609.9	593.5	575.8	554.5	534.7	513.5	495.0	478.4	458.8	439.4	423.7
20°	612.9	596.7	576.2	554.9	531.6	506.5	486.6	468.6	447.5	426.4	408.4
22.5°	611.0	598.4	575.6	550.2	526.2	500.1	477.5	456.6	433.2	411.8	390.9
25°	598.3	594.0	572.4	544.7	517.4	487.0	460.8	438.0	411.4	388.3	365.7
27.5°	568.7	578.1	564.7	535.1	504.7	472.1	442.8	416.8	389.1	363.2	340.6
30°	540.2	561.6	555.9	528.5	494.5	462.5	429.5	402.3	372.9	346.2	323.9
32.5°	501.2	536.5	542.2	519.3	484.1	448.9	414.4	387.4	356.6	328.5	306.7
35°	439.0	491.9	516.3	501.7	466.4	428.4	392.8	361.3	330.3	302.7	281.1
37.5°	365.0	437.0	477.5	478.6	446.2	406.7	367.9	336.6	304.9	277.7	254.4
40°	316.9	395.0	447.7	459.4	432.1	389.4	350.1	318.3	287.4	260.7	233.9
42.5°	273.7	351.5	416.3	436.7	414.9	372.6	333.2	299.9	269.8	244.6	217.2
45°	221.3	289.4	360.8	397.1	385.1	345.9	304.3	272.6	244.4	222.6	196.3
47.5°	186.7	234.6	303.8	352.9	352.8	317.0	276.0	245.7	219.5	199.1	177.8
50°	167.0	208.7	267.2	323.0	327.6	297.6	258.7	228.7	204.2	182.8	165.7
52.5°	149.2	183.7	236.2	289.8	303.1	277.0	239.3	211.6	187.8	168.1	153.5
55°	126.1	152.8	192.7	242.7	262.9	244.5	211.0	185.1	165.9	149.3	136.7
57.5°	106.7	126.7	158.8	199.0	222.4	211.0	183.3	162.2	145.8	130.8	120.9
60°	94.5	110.8	138.0	171.7	197.6	189.5	165.9	146.3	132.3	119.3	110.0
62.5°	82.9	97.0	120.3	147.7	171.3	168.0	148.8	132.3	120.0	108.2	100.3
65°	66.8	77.0	95.2	116.6	135.7	137.3	123.4	112.3	101.3	92.0	84.9
67.5°	53.2	59.9	72.6	90.7	105.0	110.1	101.6	93.1	84.4	77.2	71.1
70°	44.8	50.2	59.6	74.1	87.3	92.7	87.8	81.1	73.6	67.7	62.4
72.5°	36.3	41.6	48.5	59.2	70.4	76.3	74.5	69.8	63.7	58.7	53.8
75°	27.3	29.0	33.7	40.9	49.7	54.7	55.9	53.5	48.6	44.8	41.9
77.5°	20.2	21.2	23.4	27.2	33.0	37.5	39.3	39.0	35.6	33.5	30.7
80°	16.2	16.7	17.8	19.4	23.8	28.3	29.5	29.5	27.2	26.3	23.6
82.5°	12.3	12.7	13.4	14.3	16.2	20.2	21.6	21.9	20.4	19.3	17.1
85°	7.1	6.8	7.2	7.8	8.1	9.2	11.3	11.7	11.3	9.9	9.3
87.5°	5.8	5.1	4.4	4.0	3.8	3.7	4.0	4.3	4.1	4.1	4.1
90°	16.7	12.4	9.3	7.4	6.2	5.0	2.5	0.6	2.5	5.0	6.2
92.5°	61.8	42.1	28.1	22.3	18.1	15.4	10.9	7.5	10.9	15.4	18.1
95°	143.1	89.2	60.7	45.8	35.9	30.3	24.2	21.7	24.2	30.3	35.9
97.5°	192.7	117.6	81.8	65.0	53.6	45.2	38.7	35.3	38.7	45.2	53.6
100°	203.1	127.5	94.7	77.4	65.0	55.1	49.5	47.7	49.5	55.1	65.0
102.5°	203.6	136.5	106.2	88.8	75.9	66.0	60.4	59.1	60.4	66.0	75.9
105°	206.8	151.7	122.6	105.3	91.7	82.4	78.0	75.6	78.0	82.4	91.7
107.5°	215.4	167.3	139.1	121.6	108.1	99.6	95.4	93.4	95.4	99.6	108.1
110°	222.3	177.7	150.5	132.5	119.5	111.5	107.7	105.3	107.7	111.5	119.5



TEST NUMBER: P331629-927

CATALOG NUMBER: S122RDIP-S290D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	229.7	187.7	161.4	142.9	130.4	122.9	118.7	116.1	118.7	122.9	130.4
115°	240.9	203.1	176.5	159.8	147.3	140.0	136.3	133.2	136.3	140.0	147.3
117.5°	252.8	217.4	192.7	175.4	163.5	156.9	153.2	150.8	153.2	156.9	163.5
120°	260.7	227.3	203.1	185.8	173.4	167.8	164.1	161.6	164.1	167.8	173.4
122.5°	267.7	236.7	214.0	196.1	183.8	177.7	174.0	172.1	174.0	177.7	183.8
125°	278.7	250.8	228.5	211.2	198.8	191.3	187.7	185.8	187.7	191.3	198.8
127.5°	288.9	264.0	242.2	224.4	212.5	204.4	199.2	196.7	199.2	204.4	212.5
130°	295.4	271.9	250.2	232.8	220.5	211.8	205.6	203.1	205.6	211.8	220.5
132.5°	301.8	278.8	258.1	240.7	227.9	218.7	212.1	209.1	212.1	218.7	227.9
135°	310.2	288.6	268.8	251.4	237.2	227.9	220.5	218.0	220.5	227.9	237.2
137.5°	316.7	296.5	276.9	260.9	246.7	236.8	229.3	226.4	229.3	236.8	246.7
140°	320.1	301.0	282.4	266.3	252.6	242.7	235.3	232.8	235.3	242.7	252.6
142.5°	323.1	304.4	286.4	271.2	258.1	248.2	241.3	239.2	241.3	248.2	258.1
145°	326.9	309.7	292.9	279.2	266.9	257.6	251.4	248.9	251.4	257.6	266.9
147.5°	329.1	313.9	298.1	286.0	275.7	267.1	261.2	259.4	261.2	267.1	275.7
150°	330.0	315.8	301.6	290.4	281.1	273.1	268.2	266.3	268.2	273.1	281.1
152.5°	330.6	317.8	305.1	294.9	286.1	279.0	274.1	273.2	274.1	279.0	286.1
155°	331.3	320.8	310.2	301.0	294.1	287.3	283.6	283.0	283.6	287.3	294.1
157.5°	331.3	322.9	313.9	306.2	300.7	294.8	291.8	291.2	291.8	294.8	300.7
160°	331.3	323.8	316.4	309.7	304.7	299.7	297.2	296.6	297.2	299.7	304.7
162.5°	330.8	324.4	317.9	312.6	308.2	304.2	301.7	302.1	301.7	304.2	308.2
165°	329.5	325.1	319.6	315.8	312.8	309.0	307.8	308.4	307.8	309.0	312.8
167.5°	328.6	325.0	320.9	318.5	316.3	313.9	312.8	313.6	312.8	313.9	316.3
170°	327.6	324.5	321.4	319.6	318.3	316.4	315.8	317.0	315.8	316.4	318.3
172.5°	326.1	324.0	321.9	320.5	319.8	317.9	318.3	319.0	318.3	317.9	319.8
175°	324.5	323.2	322.0	321.4	321.4	320.1	320.8	321.4	320.8	320.1	321.4
177.5°	323.5	322.5	322.0	322.0	322.0	321.0	321.5	322.5	321.5	321.0	322.0
180°	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0



TEST NUMBER: P331629-927

CATALOG NUMBER: S122RDIP-S290D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8
2.5°	510.6	509.5	507.6	504.8	503.0	500.0	498.0	499.2	499.5	499.2	498.9
5°	496.9	493.1	487.8	482.8	478.1	473.1	470.2	469.0	466.4	465.0	464.2
7.5°	480.2	473.7	466.4	457.6	450.1	442.3	438.3	436.3	431.2	428.4	426.0
10°	467.9	457.6	450.2	438.7	431.7	421.4	414.4	414.6	407.6	403.6	400.8
12.5°	454.2	442.9	430.6	420.3	410.5	402.3	393.8	390.4	382.9	379.1	371.4
15°	431.5	418.4	405.4	391.4	381.5	368.7	356.5	341.5	329.5	319.0	316.2
17.5°	406.8	390.5	377.5	361.0	344.0	322.6	308.4	299.7	292.5	286.9	282.8
20°	389.8	373.2	359.3	334.5	311.6	297.1	286.7	280.0	272.4	266.5	263.2
22.5°	371.9	354.7	335.7	308.0	290.2	278.5	269.3	261.6	256.4	251.8	248.8
25°	346.6	327.6	296.5	277.5	263.1	250.8	244.4	239.7	234.3	228.0	225.1
27.5°	319.8	289.8	267.4	253.2	239.5	231.6	225.7	218.7	213.9	211.0	208.0
30°	299.8	269.7	252.3	236.8	227.1	218.2	211.4	207.5	202.8	198.0	196.0
32.5°	277.5	253.5	236.7	223.9	214.0	206.4	201.1	194.6	191.3	188.3	184.2
35°	249.8	231.6	216.3	205.9	196.5	190.4	184.1	180.3	174.2	171.7	170.1
37.5°	226.3	210.6	199.2	188.1	180.7	174.0	170.1	164.1	161.4	157.9	154.5
40°	213.0	197.6	186.6	177.6	169.3	164.3	159.5	154.6	150.6	149.0	144.9
42.5°	199.6	187.0	175.9	166.1	160.6	155.2	149.1	145.5	141.4	138.8	136.3
45°	180.9	169.7	160.3	152.3	146.1	140.5	136.6	130.6	128.3	123.1	120.9
47.5°	164.5	154.1	145.1	137.4	131.5	127.9	122.1	117.4	113.7	110.4	107.7
50°	152.8	144.1	135.5	128.7	123.3	118.0	112.1	109.8	104.0	102.3	100.8
52.5°	142.1	133.9	126.0	119.3	113.9	108.8	103.6	100.5	96.6	95.1	93.9
55°	127.2	119.3	111.8	105.8	100.4	95.2	92.0	88.2	86.3	85.1	83.7
57.5°	112.3	105.1	99.3	93.3	87.9	83.7	80.0	77.7	75.9	74.2	72.5
60°	102.7	95.9	90.7	85.1	79.5	76.1	73.3	70.5	68.4	65.8	65.1
62.5°	92.7	86.7	81.9	76.4	71.6	68.5	65.8	63.2	60.6	57.0	55.9
65°	78.8	74.1	69.1	64.6	60.3	57.2	53.2	50.4	49.3	49.0	48.8
67.5°	66.3	61.9	57.5	52.9	49.0	46.2	44.1	43.7	42.9	42.8	42.2
70°	57.9	53.8	49.5	45.2	41.4	40.9	40.2	39.4	38.5	38.2	37.8
72.5°	50.5	46.2	41.8	38.4	36.8	36.1	35.4	34.6	34.1	33.7	33.5
75°	38.7	34.7	31.8	30.6	29.7	29.2	28.0	27.6	27.2	26.6	26.5
77.5°	27.9	25.6	24.3	23.5	22.6	22.0	21.4	20.8	20.4	20.4	20.0
80°	21.2	20.1	19.3	18.1	17.8	17.1	17.0	16.4	16.6	16.0	16.0
82.5°	16.5	15.1	14.3	13.9	13.5	12.9	12.8	12.5	12.5	12.1	12.1
85°	8.5	8.1	7.8	7.4	7.4	6.8	7.1	6.8	6.8	6.5	6.3
87.5°	4.2	4.4	4.8	5.6	6.4	6.3	6.3	5.9	5.7	5.9	5.9
90°	7.4	9.3	12.4	16.7	20.4	21.1	20.4	19.8	18.6	19.8	20.4
92.5°	22.3	28.1	42.1	61.8	79.4	80.5	68.0	54.0	46.3	41.1	37.3
95°	45.8	60.7	89.2	143.1	214.9	242.7	212.4	162.2	124.5	98.5	84.8
97.5°	65.0	81.8	117.6	192.7	312.1	414.4	434.7	378.6	309.7	242.7	198.0
100°	77.4	94.7	127.5	203.1	336.8	489.2	578.4	565.4	488.6	403.8	328.8
102.5°	88.8	106.2	136.5	203.6	327.5	491.7	631.8	687.8	670.4	608.3	528.9
105°	105.3	122.6	151.7	206.8	309.0	458.8	623.6	752.4	822.4	830.4	810.0
107.5°	121.6	139.1	167.3	215.4	299.8	423.7	569.2	705.8	811.2	875.6	905.6
110°	132.5	150.5	177.7	222.3	297.9	406.9	535.0	665.7	776.6	855.8	906.6



TEST NUMBER: P331629-927

CATALOG NUMBER: S122RDIP-S290D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	142.9	161.4	187.7	229.7	298.3	395.9	511.3	629.1	735.4	820.1	878.4
115°	159.8	176.5	203.1	240.9	301.0	384.0	481.8	583.9	679.3	760.4	824.2
117.5°	175.4	192.7	217.4	252.8	305.4	378.1	463.2	550.0	633.7	707.3	767.1
120°	185.8	203.1	227.3	260.7	308.4	374.6	453.3	533.1	610.0	675.6	732.0
122.5°	196.1	214.0	236.7	267.7	311.9	372.6	444.9	519.8	590.2	652.3	703.2
125°	211.2	228.5	250.8	278.7	317.0	369.1	432.8	500.3	564.1	618.6	665.0
127.5°	224.4	242.2	264.0	288.9	322.4	366.9	421.7	481.2	538.8	590.3	633.1
130°	232.8	250.2	271.9	295.4	326.4	366.0	414.3	468.7	522.0	570.9	611.8
132.5°	240.7	258.1	278.8	301.8	330.3	365.5	408.4	456.9	506.2	551.1	589.5
135°	251.4	268.8	288.6	310.2	335.0	364.7	400.1	440.3	481.2	522.0	556.7
137.5°	260.9	276.9	296.5	316.7	339.2	364.6	394.2	427.1	461.2	493.7	523.9
140°	266.3	282.4	301.0	320.1	341.2	364.1	390.8	418.6	448.4	476.8	504.1
142.5°	271.2	286.4	304.4	323.1	342.7	364.1	387.3	411.7	437.0	461.4	484.3
145°	279.2	292.9	309.7	326.9	344.3	362.9	382.7	401.9	422.3	441.6	459.5
147.5°	286.0	298.1	313.9	329.1	344.8	360.7	378.0	394.3	410.4	425.4	438.6
150°	290.4	301.6	315.8	330.0	344.3	359.2	374.0	388.9	402.5	415.5	426.7
152.5°	294.9	305.1	317.8	330.6	343.3	356.7	370.6	383.4	396.1	407.1	416.8
155°	301.0	310.2	320.8	331.3	341.8	352.4	364.1	375.9	385.8	395.1	401.9
157.5°	306.2	313.9	322.9	331.3	339.0	347.9	358.1	367.1	375.4	383.2	388.5
160°	309.7	316.4	323.8	331.3	337.5	344.9	353.6	361.6	368.4	375.3	379.6
162.5°	312.6	317.9	324.4	330.8	336.0	342.5	349.6	356.2	362.0	367.8	371.2
165°	315.8	319.6	325.1	329.5	333.2	337.5	343.1	348.0	352.4	356.7	359.2
167.5°	318.5	320.9	325.0	328.6	330.3	333.2	336.6	340.2	343.6	346.5	348.8
170°	319.6	321.4	324.5	327.6	328.8	330.7	333.2	336.3	338.1	340.6	341.8
172.5°	320.5	321.9	324.0	326.1	326.9	327.7	329.7	331.8	333.2	335.2	335.9
175°	321.4	322.0	323.2	324.5	323.8	324.5	325.1	326.9	327.6	328.2	328.8
177.5°	322.0	322.0	322.5	323.5	322.5	322.0	322.5	323.5	323.5	324.0	324.0
180°	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0



TEST NUMBER: P331629-927

CATALOG NUMBER: S122RDIP-S290D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8
2.5°	497.3	497.6	497.2	497.4	497.2	497.6	497.3	498.9	499.2	499.5	499.2
5°	463.3	461.2	460.8	460.3	460.8	461.2	463.3	464.2	465.0	466.4	469.0
7.5°	422.9	422.6	421.6	420.3	421.6	422.6	422.9	426.0	428.4	431.2	436.3
10°	396.8	395.9	395.7	394.4	395.7	395.9	396.8	400.8	403.6	407.6	414.6
12.5°	366.2	360.4	359.9	356.7	359.9	360.4	366.2	371.4	379.1	382.9	390.4
15°	311.9	310.8	307.1	304.8	307.1	310.8	311.9	316.2	319.0	329.5	341.5
17.5°	280.7	277.2	276.1	275.6	276.1	277.2	280.7	282.8	286.9	292.5	299.7
20°	260.7	257.5	257.0	256.6	257.0	257.5	260.7	263.2	266.5	272.4	280.0
22.5°	246.9	243.5	242.2	241.1	242.2	243.5	246.9	248.8	251.8	256.4	261.6
25°	223.3	222.0	221.3	220.9	221.3	222.0	223.3	225.1	228.0	234.3	239.7
27.5°	204.9	202.1	201.5	200.6	201.5	202.1	204.9	208.0	211.0	213.9	218.7
30°	194.3	193.5	192.2	191.1	192.2	193.5	194.3	196.0	198.0	202.8	207.5
32.5°	182.0	181.2	180.1	179.6	180.1	181.2	182.0	184.2	188.3	191.3	194.6
35°	168.3	165.7	164.6	163.0	164.6	165.7	168.3	170.1	171.7	174.2	180.3
37.5°	153.8	152.4	150.9	151.5	150.9	152.4	153.8	154.5	157.9	161.4	164.1
40°	142.5	141.6	141.2	141.1	141.2	141.6	142.5	144.9	149.0	150.6	154.6
42.5°	133.6	131.1	130.2	130.2	130.2	131.1	133.6	136.3	138.8	141.4	145.5
45°	120.0	117.7	116.1	116.2	116.1	117.7	120.0	120.9	123.1	128.3	130.6
47.5°	106.2	106.1	105.0	105.4	105.0	106.1	106.2	107.7	110.4	113.7	117.4
50°	99.5	98.5	97.7	97.9	97.7	98.5	99.5	100.8	102.3	104.0	109.8
52.5°	93.2	92.2	91.7	92.4	91.7	92.2	93.2	93.9	95.1	96.6	100.5
55°	82.8	81.7	81.5	81.4	81.5	81.7	82.8	83.7	85.1	86.3	88.2
57.5°	71.1	70.4	69.3	68.9	69.3	70.4	71.1	72.5	74.2	75.9	77.7
60°	62.8	61.4	59.6	59.4	59.6	61.4	62.8	65.1	65.8	68.4	70.5
62.5°	55.1	54.9	54.5	54.5	54.5	54.9	55.1	55.9	57.0	60.6	63.2
65°	48.4	48.2	48.4	48.6	48.4	48.2	48.4	48.8	49.0	49.3	50.4
67.5°	42.1	41.8	41.5	41.7	41.5	41.8	42.1	42.2	42.8	42.9	43.7
70°	37.4	37.2	37.1	37.1	37.1	37.2	37.4	37.8	38.2	38.5	39.4
72.5°	32.8	32.8	32.6	32.5	32.6	32.8	32.8	33.5	33.7	34.1	34.6
75°	26.3	25.9	25.9	25.9	25.9	25.9	26.3	26.5	26.6	27.2	27.6
77.5°	20.0	19.8	19.6	19.5	19.6	19.8	20.0	20.0	20.4	20.4	20.8
80°	15.8	15.7	15.4	15.4	15.4	15.7	15.8	16.0	16.0	16.6	16.4
82.5°	12.1	11.9	11.9	11.7	11.9	11.9	12.1	12.1	12.1	12.5	12.5
85°	6.5	6.7	6.5	6.8	6.5	6.7	6.5	6.3	6.5	6.8	6.8
87.5°	5.9	5.8	5.9	5.8	5.9	5.8	5.9	5.9	5.9	5.7	5.9
90°	20.4	20.4	20.4	20.4	20.4	20.4	20.4	20.4	19.8	18.6	19.8
92.5°	36.8	34.8	35.3	34.3	35.3	34.8	36.8	37.3	41.1	46.3	54.0
95°	76.8	71.9	69.9	70.6	69.9	71.9	76.8	84.8	98.5	124.5	162.2
97.5°	168.4	153.2	144.2	138.9	144.2	153.2	168.4	198.0	242.7	309.7	378.6
100°	277.4	250.8	232.8	221.7	232.8	250.8	277.4	328.8	403.8	488.6	565.4
102.5°	473.1	427.6	405.2	390.1	405.2	427.6	473.1	528.9	608.3	670.4	687.8
105°	771.6	733.2	706.5	697.9	706.5	733.2	771.6	810.0	830.4	822.4	752.4
107.5°	910.5	908.3	903.0	891.4	903.0	908.3	910.5	905.6	875.6	811.2	705.8
110°	933.2	945.0	950.5	949.9	950.5	945.0	933.2	906.6	855.8	776.6	665.7



TEST NUMBER: P331629-927

CATALOG NUMBER: S122RDIP-S290D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	915.4	935.1	945.6	949.0	945.6	935.1	915.4	878.4	820.1	735.4	629.1
115°	868.2	896.7	912.8	918.4	912.8	896.7	868.2	824.2	760.4	679.3	583.9
117.5°	812.0	842.1	859.0	863.7	859.0	842.1	812.0	767.1	707.3	633.7	550.0
120°	775.3	804.4	822.4	828.5	822.4	804.4	775.3	732.0	675.6	610.0	533.1
122.5°	742.1	770.7	786.7	791.9	786.7	770.7	742.1	703.2	652.3	590.2	519.8
125°	701.0	724.5	740.0	745.0	740.0	724.5	701.0	665.0	618.6	564.1	500.3
127.5°	664.5	686.5	699.9	703.9	699.9	686.5	664.5	633.1	590.3	538.8	481.2
130°	642.1	663.2	675.6	680.6	675.6	663.2	642.1	611.8	570.9	522.0	468.7
132.5°	619.4	640.4	651.8	656.2	651.8	640.4	619.4	589.5	551.1	506.2	456.9
135°	583.4	603.8	614.9	617.4	614.9	603.8	583.4	556.7	522.0	481.2	440.3
137.5°	548.2	565.8	575.5	579.2	575.5	565.8	548.2	523.9	493.7	461.2	427.1
140°	523.9	540.0	549.3	553.0	549.3	540.0	523.9	504.1	476.8	448.4	418.6
142.5°	503.1	517.7	526.0	526.7	526.0	517.7	503.1	484.3	461.4	437.0	411.7
145°	474.4	484.9	491.1	492.9	491.1	484.9	474.4	459.5	441.6	422.3	401.9
147.5°	450.8	459.2	463.4	464.5	463.4	459.2	450.8	438.6	425.4	410.4	394.3
150°	435.9	443.4	447.1	447.7	447.1	443.4	435.9	426.7	415.5	402.5	388.9
152.5°	424.1	430.5	433.2	433.3	433.2	430.5	424.1	416.8	407.1	396.1	383.4
155°	408.7	413.0	415.5	414.3	415.5	413.0	408.7	401.9	395.1	385.8	375.9
157.5°	393.3	397.0	398.1	398.1	398.1	397.0	393.3	388.5	383.2	375.4	367.1
160°	384.0	387.1	387.6	387.6	387.6	387.1	384.0	379.6	375.3	368.4	361.6
162.5°	375.5	377.6	378.3	377.7	378.3	377.6	375.5	371.2	367.8	362.0	356.2
165°	361.6	364.1	364.1	363.5	364.1	364.1	361.6	359.2	356.7	352.4	348.0
167.5°	349.9	351.3	351.1	350.4	351.1	351.3	349.9	348.8	346.5	343.6	340.2
170°	342.5	344.3	343.6	342.5	343.6	344.3	342.5	341.8	340.6	338.1	336.3
172.5°	336.5	337.4	336.8	336.0	336.8	337.4	336.5	335.9	335.2	333.2	331.8
175°	328.8	329.5	328.8	327.6	328.8	329.5	328.8	328.8	328.2	327.6	326.9
177.5°	324.0	324.0	323.5	322.5	323.5	324.0	324.0	324.0	324.0	323.5	323.5
180°	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0



TEST NUMBER: P331629-927

CATALOG NUMBER: S122RDIP-S290D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8
2.5°	498.0	500.0	503.0	504.8	507.6	509.5	510.6	512.4	513.4	517.1	520.8
5°	470.2	473.1	478.1	482.8	487.8	493.1	496.9	501.1	505.1	511.9	519.1
7.5°	438.3	442.3	450.1	457.6	466.4	473.7	480.2	487.6	494.2	504.0	514.2
10°	414.4	421.4	431.7	438.7	450.2	457.6	467.9	475.9	485.1	498.1	509.6
12.5°	393.8	402.3	410.5	420.3	430.6	442.9	454.2	464.6	475.5	488.9	502.4
15°	356.5	368.7	381.5	391.4	405.4	418.4	431.5	445.5	458.8	474.9	492.5
17.5°	308.4	322.6	344.0	361.0	377.5	390.5	406.8	423.7	439.4	458.8	478.4
20°	286.7	297.1	311.6	334.5	359.3	373.2	389.8	408.4	426.4	447.5	468.6
22.5°	269.3	278.5	290.2	308.0	335.7	354.7	371.9	390.9	411.8	433.2	456.6
25°	244.4	250.8	263.1	277.5	296.5	327.6	346.6	365.7	388.3	411.4	438.0
27.5°	225.7	231.6	239.5	253.2	267.4	289.8	319.8	340.6	363.2	389.1	416.8
30°	211.4	218.2	227.1	236.8	252.3	269.7	299.8	323.9	346.2	372.9	402.3
32.5°	201.1	206.4	214.0	223.9	236.7	253.5	277.5	306.7	328.5	356.6	387.4
35°	184.1	190.4	196.5	205.9	216.3	231.6	249.8	281.1	302.7	330.3	361.3
37.5°	170.1	174.0	180.7	188.1	199.2	210.6	226.3	254.4	277.7	304.9	336.6
40°	159.5	164.3	169.3	177.6	186.6	197.6	213.0	233.9	260.7	287.4	318.3
42.5°	149.1	155.2	160.6	166.1	175.9	187.0	199.6	217.2	244.6	269.8	299.9
45°	136.6	140.5	146.1	152.3	160.3	169.7	180.9	196.3	222.6	244.4	272.6
47.5°	122.1	127.9	131.5	137.4	145.1	154.1	164.5	177.8	199.1	219.5	245.7
50°	112.1	118.0	123.3	128.7	135.5	144.1	152.8	165.7	182.8	204.2	228.7
52.5°	103.6	108.8	113.9	119.3	126.0	133.9	142.1	153.5	168.1	187.8	211.6
55°	92.0	95.2	100.4	105.8	111.8	119.3	127.2	136.7	149.3	165.9	185.1
57.5°	80.0	83.7	87.9	93.3	99.3	105.1	112.3	120.9	130.8	145.8	162.2
60°	73.3	76.1	79.5	85.1	90.7	95.9	102.7	110.0	119.3	132.3	146.3
62.5°	65.8	68.5	71.6	76.4	81.9	86.7	92.7	100.3	108.2	120.0	132.3
65°	53.2	57.2	60.3	64.6	69.1	74.1	78.8	84.9	92.0	101.3	112.3
67.5°	44.1	46.2	49.0	52.9	57.5	61.9	66.3	71.1	77.2	84.4	93.1
70°	40.2	40.9	41.4	45.2	49.5	53.8	57.9	62.4	67.7	73.6	81.1
72.5°	35.4	36.1	36.8	38.4	41.8	46.2	50.5	53.8	58.7	63.7	69.8
75°	28.0	29.2	29.7	30.6	31.8	34.7	38.7	41.9	44.8	48.6	53.5
77.5°	21.4	22.0	22.6	23.5	24.3	25.6	27.9	30.7	33.5	35.6	39.0
80°	17.0	17.1	17.8	18.1	19.3	20.1	21.2	23.6	26.3	27.2	29.5
82.5°	12.8	12.9	13.5	13.9	14.3	15.1	16.5	17.1	19.3	20.4	21.9
85°	7.1	6.8	7.4	7.4	7.8	8.1	8.5	9.3	9.9	11.3	11.7
87.5°	6.3	6.3	6.4	5.6	4.8	4.4	4.2	4.1	4.1	4.1	4.3
90°	20.4	21.1	20.4	16.7	12.4	9.3	7.4	6.2	5.0	2.5	0.6
92.5°	68.0	80.5	79.4	61.8	42.1	28.1	22.3	18.1	15.4	10.9	7.5
95°	212.4	242.7	214.9	143.1	89.2	60.7	45.8	35.9	30.3	24.2	21.7
97.5°	434.7	414.4	312.1	192.7	117.6	81.8	65.0	53.6	45.2	38.7	35.3
100°	578.4	489.2	336.8	203.1	127.5	94.7	77.4	65.0	55.1	49.5	47.7
102.5°	631.8	491.7	327.5	203.6	136.5	106.2	88.8	75.9	66.0	60.4	59.1
105°	623.6	458.8	309.0	206.8	151.7	122.6	105.3	91.7	82.4	78.0	75.6
107.5°	569.2	423.7	299.8	215.4	167.3	139.1	121.6	108.1	99.6	95.4	93.4
110°	535.0	406.9	297.9	222.3	177.7	150.5	132.5	119.5	111.5	107.7	105.3



TEST NUMBER: P331629-927

CATALOG NUMBER: S122RDIP-S290D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	511.3	395.9	298.3	229.7	187.7	161.4	142.9	130.4	122.9	118.7	116.1
115°	481.8	384.0	301.0	240.9	203.1	176.5	159.8	147.3	140.0	136.3	133.2
117.5°	463.2	378.1	305.4	252.8	217.4	192.7	175.4	163.5	156.9	153.2	150.8
120°	453.3	374.6	308.4	260.7	227.3	203.1	185.8	173.4	167.8	164.1	161.6
122.5°	444.9	372.6	311.9	267.7	236.7	214.0	196.1	183.8	177.7	174.0	172.1
125°	432.8	369.1	317.0	278.7	250.8	228.5	211.2	198.8	191.3	187.7	185.8
127.5°	421.7	366.9	322.4	288.9	264.0	242.2	224.4	212.5	204.4	199.2	196.7
130°	414.3	366.0	326.4	295.4	271.9	250.2	232.8	220.5	211.8	205.6	203.1
132.5°	408.4	365.5	330.3	301.8	278.8	258.1	240.7	227.9	218.7	212.1	209.1
135°	400.1	364.7	335.0	310.2	288.6	268.8	251.4	237.2	227.9	220.5	218.0
137.5°	394.2	364.6	339.2	316.7	296.5	276.9	260.9	246.7	236.8	229.3	226.4
140°	390.8	364.1	341.2	320.1	301.0	282.4	266.3	252.6	242.7	235.3	232.8
142.5°	387.3	364.1	342.7	323.1	304.4	286.4	271.2	258.1	248.2	241.3	239.2
145°	382.7	362.9	344.3	326.9	309.7	292.9	279.2	266.9	257.6	251.4	248.9
147.5°	378.0	360.7	344.8	329.1	313.9	298.1	286.0	275.7	267.1	261.2	259.4
150°	374.0	359.2	344.3	330.0	315.8	301.6	290.4	281.1	273.1	268.2	266.3
152.5°	370.6	356.7	343.3	330.6	317.8	305.1	294.9	286.1	279.0	274.1	273.2
155°	364.1	352.4	341.8	331.3	320.8	310.2	301.0	294.1	287.3	283.6	283.0
157.5°	358.1	347.9	339.0	331.3	322.9	313.9	306.2	300.7	294.8	291.8	291.2
160°	353.6	344.9	337.5	331.3	323.8	316.4	309.7	304.7	299.7	297.2	296.6
162.5°	349.6	342.5	336.0	330.8	324.4	317.9	312.6	308.2	304.2	301.7	302.1
165°	343.1	337.5	333.2	329.5	325.1	319.6	315.8	312.8	309.0	307.8	308.4
167.5°	336.6	333.2	330.3	328.6	325.0	320.9	318.5	316.3	313.9	312.8	313.6
170°	333.2	330.7	328.8	327.6	324.5	321.4	319.6	318.3	316.4	315.8	317.0
172.5°	329.7	327.7	326.9	326.1	324.0	321.9	320.5	319.8	317.9	318.3	319.0
175°	325.1	324.5	323.8	324.5	323.2	322.0	321.4	321.4	320.1	320.8	321.4
177.5°	322.5	322.0	322.5	323.5	322.5	322.0	322.0	322.0	321.0	321.5	322.5
180°	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0



TEST NUMBER: P331629-927

CATALOG NUMBER: S122RDIP-S290D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8
2.5°	520.9	521.3	524.2	525.5	528.1	529.1	530.3	530.0	530.0	530.5	534.6
5°	522.0	525.6	531.0	536.2	541.3	545.6	548.5	551.4	552.5	557.6	562.3
7.5°	520.1	526.8	535.7	543.7	553.2	560.6	566.8	572.4	576.2	583.8	591.6
10°	517.7	527.0	537.1	547.4	560.5	570.5	580.5	588.3	590.7	602.1	608.6
12.5°	512.8	525.3	538.1	551.4	564.3	577.9	589.0	596.8	605.6	615.8	627.7
15°	505.5	519.8	536.6	553.7	572.0	588.6	600.5	613.9	623.7	634.9	645.3
17.5°	495.0	513.5	534.7	554.5	575.8	593.5	609.9	622.8	629.6	636.0	637.5
20°	486.6	506.5	531.6	554.9	576.2	596.7	612.9	623.7	625.5	625.7	616.2
22.5°	477.5	500.1	526.2	550.2	575.6	598.4	611.0	615.6	608.5	596.3	577.8
25°	460.8	487.0	517.4	544.7	572.4	594.0	598.3	590.3	565.2	538.9	505.6
27.5°	442.8	472.1	504.7	535.1	564.7	578.1	568.7	539.5	494.5	455.3	407.8
30°	429.5	462.5	494.5	528.5	555.9	561.6	540.2	497.2	444.7	385.6	338.3
32.5°	414.4	448.9	484.1	519.3	542.2	536.5	501.2	448.2	386.7	328.6	283.9
35°	392.8	428.4	466.4	501.7	516.3	491.9	439.0	370.1	307.1	253.0	222.2
37.5°	367.9	406.7	446.2	478.6	477.5	437.0	365.0	293.8	240.9	208.8	187.0
40°	350.1	389.4	432.1	459.4	447.7	395.0	316.9	249.8	211.0	185.5	169.5
42.5°	333.2	372.6	414.9	436.7	416.3	351.5	273.7	221.1	189.2	169.3	156.3
45°	304.3	345.9	385.1	397.1	360.8	289.4	221.3	183.2	161.9	147.2	138.2
47.5°	276.0	317.0	352.8	352.9	303.8	234.6	186.7	158.5	140.4	129.0	122.5
50°	258.7	297.6	327.6	323.0	267.2	208.7	167.0	142.7	127.6	118.7	111.9
52.5°	239.3	277.0	303.1	289.8	236.2	183.7	149.2	128.9	116.4	108.7	102.6
55°	211.0	244.5	262.9	242.7	192.7	152.8	126.1	110.1	100.8	94.3	89.0
57.5°	183.3	211.0	222.4	199.0	158.8	126.7	106.7	94.7	85.4	80.7	78.0
60°	165.9	189.5	197.6	171.7	138.0	110.8	94.5	83.3	76.4	73.4	70.7
62.5°	148.8	168.0	171.3	147.7	120.3	97.0	82.9	73.5	69.0	66.1	63.5
65°	123.4	137.3	135.7	116.6	95.2	77.0	66.8	61.0	57.6	53.5	49.0
67.5°	101.6	110.1	105.0	90.7	72.6	59.9	53.2	48.8	44.5	40.6	39.6
70°	87.8	92.7	87.3	74.1	59.6	50.2	44.8	39.6	37.1	36.2	34.5
72.5°	74.5	76.3	70.4	59.2	48.5	41.6	36.3	33.4	32.0	31.3	30.3
75°	55.9	54.7	49.7	40.9	33.7	29.0	27.3	26.3	25.3	24.6	24.1
77.5°	39.3	37.5	33.0	27.2	23.4	21.2	20.2	19.6	19.3	18.9	18.3
80°	29.5	28.3	23.8	19.4	17.8	16.7	16.2	15.4	15.4	15.1	14.6
82.5°	21.6	20.2	16.2	14.3	13.4	12.7	12.3	11.9	11.7	11.8	11.4
85°	11.3	9.2	8.1	7.8	7.2	6.8	7.1	6.7	6.7	6.7	6.5
87.5°	4.0	3.7	3.8	4.0	4.4	5.1	5.8	6.5	6.8	6.5	6.6
90°	2.5	5.0	6.2	7.4	9.3	12.4	16.7	20.4	21.1	20.4	19.8
92.5°	10.9	15.4	18.1	22.3	28.1	42.1	61.8	79.4	80.5	68.0	54.0
95°	24.2	30.3	35.9	45.8	60.7	89.2	143.1	214.9	242.7	212.4	162.2
97.5°	38.7	45.2	53.6	65.0	81.8	117.6	192.7	312.1	414.4	434.7	378.6
100°	49.5	55.1	65.0	77.4	94.7	127.5	203.1	336.8	489.2	578.4	565.4
102.5°	60.4	66.0	75.9	88.8	106.2	136.5	203.6	327.5	491.7	631.8	687.8
105°	78.0	82.4	91.7	105.3	122.6	151.7	206.8	309.0	458.8	623.6	752.4
107.5°	95.4	99.6	108.1	121.6	139.1	167.3	215.4	299.8	423.7	569.2	705.8
110°	107.7	111.5	119.5	132.5	150.5	177.7	222.3	297.9	406.9	535.0	665.7



TEST NUMBER: P331629-927

CATALOG NUMBER: S122RDIP-S290D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	118.7	122.9	130.4	142.9	161.4	187.7	229.7	298.3	395.9	511.3	629.1
115°	136.3	140.0	147.3	159.8	176.5	203.1	240.9	301.0	384.0	481.8	583.9
117.5°	153.2	156.9	163.5	175.4	192.7	217.4	252.8	305.4	378.1	463.2	550.0
120°	164.1	167.8	173.4	185.8	203.1	227.3	260.7	308.4	374.6	453.3	533.1
122.5°	174.0	177.7	183.8	196.1	214.0	236.7	267.7	311.9	372.6	444.9	519.8
125°	187.7	191.3	198.8	211.2	228.5	250.8	278.7	317.0	369.1	432.8	500.3
127.5°	199.2	204.4	212.5	224.4	242.2	264.0	288.9	322.4	366.9	421.7	481.2
130°	205.6	211.8	220.5	232.8	250.2	271.9	295.4	326.4	366.0	414.3	468.7
132.5°	212.1	218.7	227.9	240.7	258.1	278.8	301.8	330.3	365.5	408.4	456.9
135°	220.5	227.9	237.2	251.4	268.8	288.6	310.2	335.0	364.7	400.1	440.3
137.5°	229.3	236.8	246.7	260.9	276.9	296.5	316.7	339.2	364.6	394.2	427.1
140°	235.3	242.7	252.6	266.3	282.4	301.0	320.1	341.2	364.1	390.8	418.6
142.5°	241.3	248.2	258.1	271.2	286.4	304.4	323.1	342.7	364.1	387.3	411.7
145°	251.4	257.6	266.9	279.2	292.9	309.7	326.9	344.3	362.9	382.7	401.9
147.5°	261.2	267.1	275.7	286.0	298.1	313.9	329.1	344.8	360.7	378.0	394.3
150°	268.2	273.1	281.1	290.4	301.6	315.8	330.0	344.3	359.2	374.0	388.9
152.5°	274.1	279.0	286.1	294.9	305.1	317.8	330.6	343.3	356.7	370.6	383.4
155°	283.6	287.3	294.1	301.0	310.2	320.8	331.3	341.8	352.4	364.1	375.9
157.5°	291.8	294.8	300.7	306.2	313.9	322.9	331.3	339.0	347.9	358.1	367.1
160°	297.2	299.7	304.7	309.7	316.4	323.8	331.3	337.5	344.9	353.6	361.6
162.5°	301.7	304.2	308.2	312.6	317.9	324.4	330.8	336.0	342.5	349.6	356.2
165°	307.8	309.0	312.8	315.8	319.6	325.1	329.5	333.2	337.5	343.1	348.0
167.5°	312.8	313.9	316.3	318.5	320.9	325.0	328.6	330.3	333.2	336.6	340.2
170°	315.8	316.4	318.3	319.6	321.4	324.5	327.6	328.8	330.7	333.2	336.3
172.5°	318.3	317.9	319.8	320.5	321.9	324.0	326.1	326.9	327.7	329.7	331.8
175°	320.8	320.1	321.4	321.4	322.0	323.2	324.5	323.8	324.5	325.1	326.9
177.5°	321.5	321.0	322.0	322.0	322.0	322.5	323.5	322.5	322.0	322.5	323.5
180°	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0



TEST NUMBER: P331629-927

CATALOG NUMBER: S122RDIP-S290D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	517.8	517.8	517.8	517.8	517.8	517.8	517.8
2.5°	536.0	537.9	538.8	538.8	539.8	539.3	538.9
5°	566.8	570.2	571.0	574.2	576.6	575.8	576.2
7.5°	597.5	602.9	608.4	610.9	611.2	612.7	613.2
10°	616.3	620.8	629.2	628.0	634.3	637.9	632.0
12.5°	634.5	640.6	646.4	648.0	651.6	652.8	650.4
15°	650.9	654.1	654.4	653.6	654.7	653.7	650.3
17.5°	635.6	630.3	619.6	614.6	610.6	604.7	602.3
20°	610.2	594.7	576.7	569.5	561.1	544.5	548.5
22.5°	555.5	537.9	519.8	498.8	488.8	473.1	472.1
25°	470.4	440.0	406.5	383.1	369.4	353.8	346.9
27.5°	365.8	327.4	300.0	286.1	273.5	261.1	260.5
30°	296.9	268.2	246.9	235.0	227.3	222.0	223.2
32.5°	250.3	230.5	216.2	206.4	200.7	196.7	196.6
35°	204.6	191.1	181.9	177.8	173.6	170.8	171.0
37.5°	175.1	167.0	161.8	157.3	154.7	153.3	152.5
40°	159.9	153.3	149.3	146.6	144.5	142.5	142.1
42.5°	148.1	142.5	138.6	136.4	134.4	133.0	132.7
45°	131.3	126.8	123.3	120.9	120.0	118.7	118.7
47.5°	116.8	112.4	109.6	108.1	106.6	105.8	105.8
50°	107.1	103.6	101.2	100.2	98.9	98.5	98.2
52.5°	98.3	95.7	94.0	93.3	92.8	92.1	92.2
55°	86.3	84.9	84.2	83.7	82.8	81.7	82.4
57.5°	76.4	75.1	73.2	71.5	70.7	69.9	70.2
60°	69.3	66.8	64.2	62.3	61.7	60.1	60.1
62.5°	60.4	56.8	53.7	52.6	52.0	51.3	51.2
65°	46.4	45.0	44.3	43.6	43.2	43.2	42.9
67.5°	38.5	37.9	37.1	36.9	36.6	36.4	36.4
70°	34.0	33.3	33.0	32.7	32.4	32.6	32.0
72.5°	29.7	29.2	29.1	28.6	28.4	28.4	28.0
75°	23.4	23.4	23.2	23.1	22.7	22.5	22.7
77.5°	18.0	18.1	17.7	17.7	17.7	17.7	17.5
80°	14.4	14.6	14.4	14.2	14.0	14.2	14.0
82.5°	11.4	11.1	11.1	11.0	11.0	10.9	10.9
85°	6.5	6.7	6.5	6.3	6.3	6.3	6.5
87.5°	6.2	6.4	6.5	6.5	6.5	6.5	6.4
90°	18.6	19.8	20.4	20.4	20.4	20.4	20.4
92.5°	46.3	41.1	37.3	36.8	34.8	35.3	34.3
95°	124.5	98.5	84.8	76.8	71.9	69.9	70.6
97.5°	309.7	242.7	198.0	168.4	153.2	144.2	138.9
100°	488.6	403.8	328.8	277.4	250.8	232.8	221.7
102.5°	670.4	608.3	528.9	473.1	427.6	405.2	390.1
105°	822.4	830.4	810.0	771.6	733.2	706.5	697.9
107.5°	811.2	875.6	905.6	910.5	908.3	903.0	891.4
110°	776.6	855.8	906.6	933.2	945.0	950.5	949.9



TEST NUMBER: P331629-927

CATALOG NUMBER: S122RDIP-S290D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	735.4	820.1	878.4	915.4	935.1	945.6	949.0
115°	679.3	760.4	824.2	868.2	896.7	912.8	918.4
117.5°	633.7	707.3	767.1	812.0	842.1	859.0	863.7
120°	610.0	675.6	732.0	775.3	804.4	822.4	828.5
122.5°	590.2	652.3	703.2	742.1	770.7	786.7	791.9
125°	564.1	618.6	665.0	701.0	724.5	740.0	745.0
127.5°	538.8	590.3	633.1	664.5	686.5	699.9	703.9
130°	522.0	570.9	611.8	642.1	663.2	675.6	680.6
132.5°	506.2	551.1	589.5	619.4	640.4	651.8	656.2
135°	481.2	522.0	556.7	583.4	603.8	614.9	617.4
137.5°	461.2	493.7	523.9	548.2	565.8	575.5	579.2
140°	448.4	476.8	504.1	523.9	540.0	549.3	553.0
142.5°	437.0	461.4	484.3	503.1	517.7	526.0	526.7
145°	422.3	441.6	459.5	474.4	484.9	491.1	492.9
147.5°	410.4	425.4	438.6	450.8	459.2	463.4	464.5
150°	402.5	415.5	426.7	435.9	443.4	447.1	447.7
152.5°	396.1	407.1	416.8	424.1	430.5	433.2	433.3
155°	385.8	395.1	401.9	408.7	413.0	415.5	414.3
157.5°	375.4	383.2	388.5	393.3	397.0	398.1	398.1
160°	368.4	375.3	379.6	384.0	387.1	387.6	387.6
162.5°	362.0	367.8	371.2	375.5	377.6	378.3	377.7
165°	352.4	356.7	359.2	361.6	364.1	364.1	363.5
167.5°	343.6	346.5	348.8	349.9	351.3	351.1	350.4
170°	338.1	340.6	341.8	342.5	344.3	343.6	342.5
172.5°	333.2	335.2	335.9	336.5	337.4	336.8	336.0
175°	327.6	328.2	328.8	328.8	329.5	328.8	327.6
177.5°	323.5	324.0	324.0	324.0	324.0	323.5	322.5
180°	322.0	322.0	322.0	322.0	322.0	322.0	322.0

(END OF REPORT)