

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331634-927

Luminaire Tested: **S122RDIP-S290D925U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331634-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S290D925U927-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3518.3 lumens
Efficiency: N/A
Efficacy: 94.3 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331634-927

CATALOG NUMBER: S122RDIP-S290D925U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270° - - - 135°-315°



TEST NUMBER: P331634-927

CATALOG NUMBER: S122RDIP-S290D925U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26				
1	93	89	85	82	82	79	76	74	61	60	58	45	44	43	30	30	29	22				
2	85	78	72	67	75	70	65	61	54	51	48	40	38	36	27	26	25	19				
3	77	69	62	57	69	62	56	51	48	44	41	36	33	31	24	23	22	17				
4	71	61	54	48	63	55	49	44	43	39	35	32	29	27	22	21	19	15				
5	65	54	47	41	58	49	43	38	39	34	31	29	26	24	20	18	17	13				
6	60	49	41	36	54	44	38	33	35	30	27	26	23	21	18	17	15	12				
7	56	44	37	31	50	40	33	29	32	27	24	24	21	19	17	15	14	11				
8	52	40	33	28	46	36	30	26	29	24	21	22	19	17	16	14	12	10				
9	48	37	30	25	43	33	27	23	27	22	19	20	17	15	15	13	11	9				
10	45	33	27	22	40	30	24	20	24	20	17	19	16	14	14	12	10	8				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8360	8360	8360	8360
5°	9339	8413	7460	8413
10°	10362	8355	6466	8355
15°	10870	8232	5095	8232
20°	9424	8052	4409	8052
25°	6180	7803	3935	7803
30°	4161	7500	3563	7500
35°	3370	7121	3213	7121
40°	2995	6709	2974	6709
45°	2710	6224	2653	6224
50°	2467	5745	2459	5745
55°	2320	5210	2291	5210
60°	1941	4724	1918	4724
65°	1639	4290	1857	4290
70°	1511	3829	1751	3829
75°	1416	3337	1616	3337
80°	1302	2743	1432	2743
85°	1204	2167	1260	2167



TEST NUMBER: P331634-927

CATALOG NUMBER: S122RDIP-S290D925U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.1	1.4
10°-20°	136.8	3.9
20°-30°	176.3	5.0
30°-40°	167.5	4.8
40°-50°	143.5	4.1
50°-60°	109.3	3.1
60°-70°	69.1	2.0
70°-80°	34.5	1.0
80°-90°	12.7	0.4
90°-100°	59.4	1.7
100°-110°	184.4	5.2
110°-120°	315.1	9.0
120°-130°	414.4	11.8
130°-140°	465.2	13.2
140°-150°	456.1	13.0
150°-160°	382.5	10.9
160°-170°	253.7	7.2
170°-180°	88.7	2.5
0°-30°	362.2	10.3
0°-40°	529.7	15.1
0°-60°	782.5	22.2
0°-90°	898.8	25.5
90°-120°	558.9	15.9
90°-150°	1894.5	53.8
90°-180°	2620.0	74.5
0°-180°	3518.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	518	518	518	518	518	
5°	576	519	460	519	576	57
15°	650	492	305	492	650	175
25°	347	438	221	438	347	165
35°	171	361	163	361	171	109
45°	119	273	116	273	119	92
55°	82	185	81	185	82	72
65°	43	112	49	112	43	44
75°	23	54	26	54	23	24
85°	6	12	7	12	6	8
90°	27	1	27	1	27	12
95°	49	41	49	41	49	55
105°	176	170	176	170	176	185
115°	316	316	316	316	316	312
125°	462	460	462	460	462	412
135°	602	595	602	595	602	464
145°	730	722	730	722	730	456
155°	832	826	832	826	832	383
165°	900	899	900	899	900	254
175°	932	935	932	935	932	89
180°	937	937	937	937	937	



TEST NUMBER: P331634-927

CATALOG NUMBER: S122RDIP-S290D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8
2.5°	538.9	539.3	539.8	538.8	538.8	537.9	536.0	534.6	530.5	530.0	530.0
5°	576.2	575.8	576.6	574.2	571.0	570.2	566.8	562.3	557.6	552.5	551.4
7.5°	613.2	612.7	611.2	610.9	608.4	602.9	597.5	591.6	583.8	576.2	572.4
10°	632.0	637.9	634.3	628.0	629.2	620.8	616.3	608.6	602.1	590.7	588.3
12.5°	650.4	652.8	651.6	648.0	646.4	640.6	634.5	627.7	615.8	605.6	596.8
15°	650.3	653.7	654.7	653.6	654.4	654.1	650.9	645.3	634.9	623.7	613.9
17.5°	602.3	604.7	610.6	614.6	619.6	630.3	635.6	637.5	636.0	629.6	622.8
20°	548.5	544.5	561.1	569.5	576.7	594.7	610.2	616.2	625.7	625.5	623.7
22.5°	472.1	473.1	488.8	498.8	519.8	537.9	555.5	577.8	596.3	608.5	615.6
25°	346.9	353.8	369.4	383.1	406.5	440.0	470.4	505.6	538.9	565.2	590.3
27.5°	260.5	261.1	273.5	286.1	300.0	327.4	365.8	407.8	455.3	494.5	539.5
30°	223.2	222.0	227.3	235.0	246.9	268.2	296.9	338.3	385.6	444.7	497.2
32.5°	196.6	196.7	200.7	206.4	216.2	230.5	250.3	283.9	328.6	386.7	448.2
35°	171.0	170.8	173.6	177.8	181.9	191.1	204.6	222.2	253.0	307.1	370.1
37.5°	152.5	153.3	154.7	157.3	161.8	167.0	175.1	187.0	208.8	240.9	293.8
40°	142.1	142.5	144.5	146.6	149.3	153.3	159.9	169.5	185.5	211.0	249.8
42.5°	132.7	133.0	134.4	136.4	138.6	142.5	148.1	156.3	169.3	189.2	221.1
45°	118.7	118.7	120.0	120.9	123.3	126.8	131.3	138.2	147.2	161.9	183.2
47.5°	105.8	105.8	106.6	108.1	109.6	112.4	116.8	122.5	129.0	140.4	158.5
50°	98.2	98.5	98.9	100.2	101.2	103.6	107.1	111.9	118.7	127.6	142.7
52.5°	92.2	92.1	92.8	93.3	94.0	95.7	98.3	102.6	108.7	116.4	128.9
55°	82.4	81.7	82.8	83.7	84.2	84.9	86.3	89.0	94.3	100.8	110.1
57.5°	70.2	69.9	70.7	71.5	73.2	75.1	76.4	78.0	80.7	85.4	94.7
60°	60.1	60.1	61.7	62.3	64.2	66.8	69.3	70.7	73.4	76.4	83.3
62.5°	51.2	51.3	52.0	52.6	53.7	56.8	60.4	63.5	66.1	69.0	73.5
65°	42.9	43.2	43.2	43.6	44.3	45.0	46.4	49.0	53.5	57.6	61.0
67.5°	36.4	36.4	36.6	36.9	37.1	37.9	38.5	39.6	40.6	44.5	48.8
70°	32.0	32.6	32.4	32.7	33.0	33.3	34.0	34.5	36.2	37.1	39.6
72.5°	28.0	28.4	28.4	28.6	29.1	29.2	29.7	30.3	31.3	32.0	33.4
75°	22.7	22.5	22.7	23.1	23.2	23.4	23.4	24.1	24.6	25.3	26.3
77.5°	17.5	17.7	17.7	17.7	17.7	18.1	18.0	18.3	18.9	19.3	19.6
80°	14.0	14.2	14.0	14.2	14.4	14.6	14.4	14.6	15.1	15.4	15.4
82.5°	10.9	10.9	11.0	11.0	11.1	11.1	11.4	11.4	11.8	11.7	11.9
85°	6.5	6.3	6.3	6.3	6.5	6.7	6.5	6.5	6.7	6.7	6.7
87.5°	7.7	7.8	7.8	7.7	7.7	7.7	7.8	8.0	7.9	8.2	7.2
90°	26.9	26.7	26.5	26.4	26.1	26.3	26.6	26.9	27.3	27.6	23.8
92.5°	25.6	25.6	25.5	25.5	25.5	25.4	25.3	25.3	25.2	25.1	24.2
95°	49.0	49.4	49.7	50.1	50.4	50.6	50.6	50.6	50.6	50.6	50.2
97.5°	84.9	84.9	85.0	85.0	85.1	85.1	85.1	85.1	85.1	85.1	84.4
100°	108.3	108.4	108.7	108.8	109.0	109.1	109.1	109.1	109.1	109.1	108.6
102.5°	134.9	135.1	135.2	135.4	135.5	135.6	135.5	135.3	135.1	135.1	134.4
105°	175.5	175.5	175.5	175.5	175.5	175.3	175.0	174.6	174.3	173.9	173.6
107.5°	213.7	214.6	215.4	216.2	217.0	217.3	217.2	217.1	216.9	216.7	216.7
110°	243.5	244.0	244.5	245.1	245.6	245.9	245.9	245.9	245.9	245.9	245.9



TEST NUMBER: P331634-927

CATALOG NUMBER: S122RDIP-S290D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	272.0	272.4	272.7	273.1	273.5	273.9	274.3	274.7	275.2	275.6	275.8
115°	316.2	316.7	317.3	317.8	318.3	318.7	318.9	319.0	319.2	319.4	319.7
117.5°	358.5	358.9	359.5	360.0	360.5	361.0	361.5	361.9	362.3	362.7	363.7
120°	388.2	388.7	389.2	389.8	390.3	390.5	390.5	390.5	390.5	390.5	392.0
122.5°	417.2	417.6	418.0	418.4	418.8	419.2	419.6	420.0	420.5	420.9	421.9
125°	461.7	461.8	462.0	462.2	462.4	462.7	463.3	463.8	464.3	464.9	465.4
127.5°	502.2	502.7	503.3	503.8	504.4	505.0	505.6	506.3	506.9	507.6	508.2
130°	531.2	532.0	532.7	533.4	534.1	534.6	535.0	535.3	535.7	536.0	536.4
132.5°	559.1	559.7	560.2	560.8	561.3	562.0	562.8	563.6	564.4	565.1	565.0
135°	602.4	602.9	603.5	604.0	604.5	604.8	605.1	605.2	605.4	605.5	605.2
137.5°	641.6	642.3	643.0	643.7	644.4	644.8	645.0	645.2	645.3	645.4	645.0
140°	668.8	669.6	670.2	670.9	671.6	672.0	672.0	672.0	672.0	672.0	671.1
142.5°	693.5	694.2	694.9	695.6	696.3	696.6	696.4	696.3	696.2	696.0	695.4
145°	730.5	731.2	731.9	732.6	733.3	733.6	733.4	733.2	733.0	732.8	731.8
147.5°	763.5	764.2	764.9	765.6	766.2	766.4	766.0	765.6	765.2	764.8	764.1
150°	785.1	785.5	786.1	786.6	787.1	787.1	786.6	786.1	785.5	785.1	784.3
152.5°	805.3	806.0	806.6	807.2	807.9	807.9	807.2	806.6	806.0	805.3	804.4
155°	832.4	833.0	833.5	834.0	834.6	834.4	833.5	832.7	831.8	830.8	830.4
157.5°	855.9	856.7	857.5	858.4	859.2	859.0	857.9	856.7	855.5	854.3	854.0
160°	870.4	871.1	871.8	872.5	873.2	873.1	872.0	870.9	869.9	868.8	868.6
162.5°	883.0	883.9	884.7	885.6	886.5	886.2	885.0	883.8	882.6	881.5	881.3
165°	899.7	900.6	901.4	902.3	903.2	903.0	901.7	900.6	899.3	898.1	898.1
167.5°	913.2	914.2	915.0	916.0	916.9	916.7	915.5	914.3	913.1	911.8	911.9
170°	920.2	921.2	922.3	923.4	924.4	924.3	923.1	921.9	920.7	919.4	919.6
172.5°	925.9	926.9	928.0	929.1	930.1	930.0	928.8	927.6	926.4	925.1	925.3
175°	932.1	933.1	934.1	935.3	936.3	936.2	934.9	933.7	932.5	931.3	931.6
177.5°	934.9	935.7	936.6	937.5	938.3	938.3	937.5	936.6	935.7	934.9	935.2
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8



TEST NUMBER: P331634-927

CATALOG NUMBER: S122RDIP-S290D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8
2.5°	530.3	529.1	528.1	525.5	524.2	521.3	520.9	520.8	517.1	513.4	512.4
5°	548.5	545.6	541.3	536.2	531.0	525.6	522.0	519.1	511.9	505.1	501.1
7.5°	566.8	560.6	553.2	543.7	535.7	526.8	520.1	514.2	504.0	494.2	487.6
10°	580.5	570.5	560.5	547.4	537.1	527.0	517.7	509.6	498.1	485.1	475.9
12.5°	589.0	577.9	564.3	551.4	538.1	525.3	512.8	502.4	488.9	475.5	464.6
15°	600.5	588.6	572.0	553.7	536.6	519.8	505.5	492.5	474.9	458.8	445.5
17.5°	609.9	593.5	575.8	554.5	534.7	513.5	495.0	478.4	458.8	439.4	423.7
20°	612.9	596.7	576.2	554.9	531.6	506.5	486.6	468.6	447.5	426.4	408.4
22.5°	611.0	598.4	575.6	550.2	526.2	500.1	477.5	456.6	433.2	411.8	390.9
25°	598.3	594.0	572.4	544.7	517.4	487.0	460.8	438.0	411.4	388.3	365.7
27.5°	568.7	578.1	564.7	535.1	504.7	472.1	442.8	416.8	389.1	363.2	340.6
30°	540.2	561.6	555.9	528.5	494.5	462.5	429.5	402.3	372.9	346.2	323.9
32.5°	501.2	536.5	542.2	519.3	484.1	448.9	414.4	387.4	356.6	328.5	306.7
35°	439.0	491.9	516.3	501.7	466.4	428.4	392.8	361.3	330.3	302.7	281.1
37.5°	365.0	437.0	477.5	478.6	446.2	406.7	367.9	336.6	304.9	277.7	254.4
40°	316.9	395.0	447.7	459.4	432.1	389.4	350.1	318.3	287.4	260.7	233.9
42.5°	273.7	351.5	416.3	436.7	414.9	372.6	333.2	299.9	269.8	244.6	217.2
45°	221.3	289.4	360.8	397.1	385.1	345.9	304.3	272.6	244.4	222.6	196.3
47.5°	186.7	234.6	303.8	352.9	352.8	317.0	276.0	245.7	219.5	199.1	177.8
50°	167.0	208.7	267.2	323.0	327.6	297.6	258.7	228.7	204.2	182.8	165.7
52.5°	149.2	183.7	236.2	289.8	303.1	277.0	239.3	211.6	187.8	168.1	153.5
55°	126.1	152.8	192.7	242.7	262.9	244.5	211.0	185.1	165.9	149.3	136.7
57.5°	106.7	126.7	158.8	199.0	222.4	211.0	183.3	162.2	145.8	130.8	120.9
60°	94.5	110.8	138.0	171.7	197.6	189.5	165.9	146.3	132.3	119.3	110.0
62.5°	82.9	97.0	120.3	147.7	171.3	168.0	148.8	132.3	120.0	108.2	100.3
65°	66.8	77.0	95.2	116.6	135.7	137.3	123.4	112.3	101.3	92.0	84.9
67.5°	53.2	59.9	72.6	90.7	105.0	110.1	101.6	93.1	84.4	77.2	71.1
70°	44.8	50.2	59.6	74.1	87.3	92.7	87.8	81.1	73.6	67.7	62.4
72.5°	36.3	41.6	48.5	59.2	70.4	76.3	74.5	69.8	63.7	58.7	53.8
75°	27.3	29.0	33.7	40.9	49.7	54.7	55.9	53.5	48.6	44.8	41.9
77.5°	20.2	21.2	23.4	27.2	33.0	37.5	39.3	39.0	35.6	33.5	30.7
80°	16.2	16.7	17.8	19.4	23.8	28.3	29.5	29.5	27.2	26.3	23.6
82.5°	12.3	12.7	13.4	14.3	16.2	20.2	21.6	21.9	20.4	19.3	17.1
85°	7.1	6.8	7.2	7.8	8.1	9.2	11.3	11.7	11.3	9.9	9.3
87.5°	6.4	5.8	5.1	4.3	4.0	3.7	4.0	4.4	4.2	4.2	4.3
90°	20.0	16.1	12.2	9.2	7.1	5.0	2.9	0.8	2.9	5.0	7.1
92.5°	23.3	22.4	21.5	20.3	18.7	17.2	15.6	14.1	15.6	17.2	18.7
95°	49.9	49.5	49.2	48.2	46.3	44.6	42.9	41.1	42.9	44.6	46.3
97.5°	83.7	83.1	82.4	81.3	79.8	78.2	76.7	75.1	76.7	78.2	79.8
100°	108.1	107.5	107.0	106.0	104.6	103.2	101.8	100.4	101.8	103.2	104.6
102.5°	133.7	133.0	132.4	131.4	130.3	129.2	128.1	127.0	128.1	129.2	130.3
105°	173.3	172.9	172.5	172.1	171.6	171.0	170.5	170.0	170.5	171.0	171.6
107.5°	216.7	216.7	216.7	216.4	215.6	214.8	214.0	213.3	214.0	214.8	215.6
110°	245.9	245.9	245.9	245.3	244.3	243.2	242.2	241.1	242.2	243.2	244.3



TEST NUMBER: P331634-927

CATALOG NUMBER: S122RDIP-S290D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	275.8	276.0	276.2	275.7	274.6	273.6	272.5	271.5	272.5	273.6	274.6
115°	320.1	320.4	320.8	320.4	319.4	318.3	317.3	316.2	317.3	318.3	319.4
117.5°	364.6	365.7	366.6	366.5	365.0	363.6	362.2	360.8	362.2	363.6	365.0
120°	393.3	394.7	396.2	396.2	394.7	393.3	392.0	390.5	392.0	393.3	394.7
122.5°	422.9	423.8	424.8	424.5	422.8	421.1	419.4	417.7	419.4	421.1	422.8
125°	465.9	466.4	467.0	466.4	464.9	463.3	461.7	460.1	461.7	463.3	464.9
127.5°	508.8	509.5	510.1	509.4	507.4	505.4	503.4	501.4	503.4	505.4	507.4
130°	536.7	537.0	537.4	536.5	534.2	531.9	529.6	527.3	529.6	531.9	534.2
132.5°	565.0	564.9	564.8	563.9	562.0	560.2	558.3	556.4	558.3	560.2	562.0
135°	604.8	604.5	604.2	603.0	601.1	599.1	597.2	595.3	597.2	599.1	601.1
137.5°	644.5	644.0	643.6	642.5	641.0	639.4	637.8	636.3	637.8	639.4	641.0
140°	670.2	669.3	668.4	667.3	665.7	664.1	662.5	660.9	662.5	664.1	665.7
142.5°	694.8	694.2	693.6	692.5	690.9	689.4	687.8	686.2	687.8	689.4	690.9
145°	730.7	729.7	728.6	727.5	726.3	725.0	723.8	722.5	723.8	725.0	726.3
147.5°	763.3	762.7	762.0	760.9	759.4	758.0	756.5	754.9	756.5	758.0	759.4
150°	783.6	782.9	782.2	781.3	780.3	779.2	778.2	777.1	778.2	779.2	780.3
152.5°	803.6	802.7	801.9	801.0	799.9	798.8	797.8	796.7	797.8	798.8	799.9
155°	829.8	829.3	828.8	828.2	827.8	827.2	826.6	826.2	826.6	827.2	827.8
157.5°	853.7	853.3	853.0	852.7	852.3	852.0	851.6	851.3	851.6	852.0	852.3
160°	868.5	868.3	868.2	867.8	867.5	867.1	866.8	866.5	866.8	867.1	867.5
162.5°	881.1	881.0	880.7	880.7	880.6	880.5	880.4	880.4	880.4	880.5	880.6
165°	898.1	898.1	898.1	898.2	898.3	898.5	898.7	898.9	898.7	898.5	898.3
167.5°	911.9	912.0	912.0	912.3	912.8	913.3	913.9	914.3	913.9	913.3	912.8
170°	919.8	920.0	920.1	920.4	921.0	921.5	922.0	922.6	922.0	921.5	921.0
172.5°	925.4	925.7	925.8	926.1	926.7	927.2	927.7	928.3	927.7	927.2	926.7
175°	932.0	932.3	932.7	933.1	933.7	934.1	934.7	935.3	934.7	934.1	933.7
177.5°	935.5	935.7	936.0	936.4	936.8	937.2	937.6	938.1	937.6	937.2	936.8
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8



TEST NUMBER: P331634-927

CATALOG NUMBER: S122RDIP-S290D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8
2.5°	510.6	509.5	507.6	504.8	503.0	500.0	498.0	499.2	499.5	499.2	498.9
5°	496.9	493.1	487.8	482.8	478.1	473.1	470.2	469.0	466.4	465.0	464.2
7.5°	480.2	473.7	466.4	457.6	450.1	442.3	438.3	436.3	431.2	428.4	426.0
10°	467.9	457.6	450.2	438.7	431.7	421.4	414.4	414.6	407.6	403.6	400.8
12.5°	454.2	442.9	430.6	420.3	410.5	402.3	393.8	390.4	382.9	379.1	371.4
15°	431.5	418.4	405.4	391.4	381.5	368.7	356.5	341.5	329.5	319.0	316.2
17.5°	406.8	390.5	377.5	361.0	344.0	322.6	308.4	299.7	292.5	286.9	282.8
20°	389.8	373.2	359.3	334.5	311.6	297.1	286.7	280.0	272.4	266.5	263.2
22.5°	371.9	354.7	335.7	308.0	290.2	278.5	269.3	261.6	256.4	251.8	248.8
25°	346.6	327.6	296.5	277.5	263.1	250.8	244.4	239.7	234.3	228.0	225.1
27.5°	319.8	289.8	267.4	253.2	239.5	231.6	225.7	218.7	213.9	211.0	208.0
30°	299.8	269.7	252.3	236.8	227.1	218.2	211.4	207.5	202.8	198.0	196.0
32.5°	277.5	253.5	236.7	223.9	214.0	206.4	201.1	194.6	191.3	188.3	184.2
35°	249.8	231.6	216.3	205.9	196.5	190.4	184.1	180.3	174.2	171.7	170.1
37.5°	226.3	210.6	199.2	188.1	180.7	174.0	170.1	164.1	161.4	157.9	154.5
40°	213.0	197.6	186.6	177.6	169.3	164.3	159.5	154.6	150.6	149.0	144.9
42.5°	199.6	187.0	175.9	166.1	160.6	155.2	149.1	145.5	141.4	138.8	136.3
45°	180.9	169.7	160.3	152.3	146.1	140.5	136.6	130.6	128.3	123.1	120.9
47.5°	164.5	154.1	145.1	137.4	131.5	127.9	122.1	117.4	113.7	110.4	107.7
50°	152.8	144.1	135.5	128.7	123.3	118.0	112.1	109.8	104.0	102.3	100.8
52.5°	142.1	133.9	126.0	119.3	113.9	108.8	103.6	100.5	96.6	95.1	93.9
55°	127.2	119.3	111.8	105.8	100.4	95.2	92.0	88.2	86.3	85.1	83.7
57.5°	112.3	105.1	99.3	93.3	87.9	83.7	80.0	77.7	75.9	74.2	72.5
60°	102.7	95.9	90.7	85.1	79.5	76.1	73.3	70.5	68.4	65.8	65.1
62.5°	92.7	86.7	81.9	76.4	71.6	68.5	65.8	63.2	60.6	57.0	55.9
65°	78.8	74.1	69.1	64.6	60.3	57.2	53.2	50.4	49.3	49.0	48.8
67.5°	66.3	61.9	57.5	52.9	49.0	46.2	44.1	43.7	42.9	42.8	42.2
70°	57.9	53.8	49.5	45.2	41.4	40.9	40.2	39.4	38.5	38.2	37.8
72.5°	50.5	46.2	41.8	38.4	36.8	36.1	35.4	34.6	34.1	33.7	33.5
75°	38.7	34.7	31.8	30.6	29.7	29.2	28.0	27.6	27.2	26.6	26.5
77.5°	27.9	25.6	24.3	23.5	22.6	22.0	21.4	20.8	20.4	20.4	20.0
80°	21.2	20.1	19.3	18.1	17.8	17.1	17.0	16.4	16.6	16.0	16.0
82.5°	16.5	15.1	14.3	13.9	13.5	12.9	12.8	12.5	12.5	12.1	12.1
85°	8.5	8.1	7.8	7.4	7.4	6.8	7.1	6.8	6.8	6.5	6.3
87.5°	4.6	5.1	5.5	6.3	7.1	7.7	7.6	7.4	7.4	7.3	7.1
90°	9.2	12.2	16.1	20.0	23.8	27.6	27.3	26.9	26.6	26.3	26.1
92.5°	20.3	21.5	22.4	23.3	24.2	25.1	25.2	25.3	25.3	25.4	25.5
95°	48.2	49.2	49.5	49.9	50.2	50.6	50.6	50.6	50.6	50.6	50.4
97.5°	81.3	82.4	83.1	83.7	84.4	85.1	85.1	85.1	85.1	85.1	85.1
100°	106.0	107.0	107.5	108.1	108.6	109.1	109.1	109.1	109.1	109.1	109.0
102.5°	131.4	132.4	133.0	133.7	134.4	135.1	135.1	135.3	135.5	135.6	135.5
105°	172.1	172.5	172.9	173.3	173.6	173.9	174.3	174.6	175.0	175.3	175.5
107.5°	216.4	216.7	216.7	216.7	216.7	216.7	216.9	217.1	217.2	217.3	217.0
110°	245.3	245.9	245.9	245.9	245.9	245.9	245.9	245.9	245.9	245.9	245.6



TEST NUMBER: P331634-927

CATALOG NUMBER: S122RDIP-S290D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	275.7	276.2	276.0	275.8	275.8	275.6	275.2	274.7	274.3	273.9	273.5
115°	320.4	320.8	320.4	320.1	319.7	319.4	319.2	319.0	318.9	318.7	318.3
117.5°	366.5	366.6	365.7	364.6	363.7	362.7	362.3	361.9	361.5	361.0	360.5
120°	396.2	396.2	394.7	393.3	392.0	390.5	390.5	390.5	390.5	390.5	390.3
122.5°	424.5	424.8	423.8	422.9	421.9	420.9	420.5	420.0	419.6	419.2	418.8
125°	466.4	467.0	466.4	465.9	465.4	464.9	464.3	463.8	463.3	462.7	462.4
127.5°	509.4	510.1	509.5	508.8	508.2	507.6	506.9	506.3	505.6	505.0	504.4
130°	536.5	537.4	537.0	536.7	536.4	536.0	535.7	535.3	535.0	534.6	534.1
132.5°	563.9	564.8	564.9	565.0	565.0	565.1	564.4	563.6	562.8	562.0	561.3
135°	603.0	604.2	604.5	604.8	605.2	605.5	605.4	605.2	605.1	604.8	604.5
137.5°	642.5	643.6	644.0	644.5	645.0	645.4	645.3	645.2	645.0	644.8	644.4
140°	667.3	668.4	669.3	670.2	671.1	672.0	672.0	672.0	672.0	672.0	671.6
142.5°	692.5	693.6	694.2	694.8	695.4	696.0	696.2	696.3	696.4	696.6	696.3
145°	727.5	728.6	729.7	730.7	731.8	732.8	733.0	733.2	733.4	733.6	733.3
147.5°	760.9	762.0	762.7	763.3	764.1	764.8	765.2	765.6	766.0	766.4	766.2
150°	781.3	782.2	782.9	783.6	784.3	785.1	785.5	786.1	786.6	787.1	787.1
152.5°	801.0	801.9	802.7	803.6	804.4	805.3	806.0	806.6	807.2	807.9	807.9
155°	828.2	828.8	829.3	829.8	830.4	830.8	831.8	832.7	833.5	834.4	834.6
157.5°	852.7	853.0	853.3	853.7	854.0	854.3	855.5	856.7	857.9	859.0	859.2
160°	867.8	868.2	868.3	868.5	868.6	868.8	869.9	870.9	872.0	873.1	873.2
162.5°	880.7	880.7	881.0	881.1	881.3	881.5	882.6	883.8	885.0	886.2	886.5
165°	898.2	898.1	898.1	898.1	898.1	898.1	899.3	900.6	901.7	903.0	903.2
167.5°	912.3	912.0	912.0	911.9	911.9	911.8	913.1	914.3	915.5	916.7	916.9
170°	920.4	920.1	920.0	919.8	919.6	919.4	920.7	921.9	923.1	924.3	924.4
172.5°	926.1	925.8	925.7	925.4	925.3	925.1	926.4	927.6	928.8	930.0	930.1
175°	933.1	932.7	932.3	932.0	931.6	931.3	932.5	933.7	934.9	936.2	936.3
177.5°	936.4	936.0	935.7	935.5	935.2	934.9	935.7	936.6	937.5	938.3	938.3
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8



TEST NUMBER: P331634-927

CATALOG NUMBER: S122RDIP-S290D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8
2.5°	497.3	497.6	497.2	497.4	497.2	497.6	497.3	498.9	499.2	499.5	499.2
5°	463.3	461.2	460.8	460.3	460.8	461.2	463.3	464.2	465.0	466.4	469.0
7.5°	422.9	422.6	421.6	420.3	421.6	422.6	422.9	426.0	428.4	431.2	436.3
10°	396.8	395.9	395.7	394.4	395.7	395.9	396.8	400.8	403.6	407.6	414.6
12.5°	366.2	360.4	359.9	356.7	359.9	360.4	366.2	371.4	379.1	382.9	390.4
15°	311.9	310.8	307.1	304.8	307.1	310.8	311.9	316.2	319.0	329.5	341.5
17.5°	280.7	277.2	276.1	275.6	276.1	277.2	280.7	282.8	286.9	292.5	299.7
20°	260.7	257.5	257.0	256.6	257.0	257.5	260.7	263.2	266.5	272.4	280.0
22.5°	246.9	243.5	242.2	241.1	242.2	243.5	246.9	248.8	251.8	256.4	261.6
25°	223.3	222.0	221.3	220.9	221.3	222.0	223.3	225.1	228.0	234.3	239.7
27.5°	204.9	202.1	201.5	200.6	201.5	202.1	204.9	208.0	211.0	213.9	218.7
30°	194.3	193.5	192.2	191.1	192.2	193.5	194.3	196.0	198.0	202.8	207.5
32.5°	182.0	181.2	180.1	179.6	180.1	181.2	182.0	184.2	188.3	191.3	194.6
35°	168.3	165.7	164.6	163.0	164.6	165.7	168.3	170.1	171.7	174.2	180.3
37.5°	153.8	152.4	150.9	151.5	150.9	152.4	153.8	154.5	157.9	161.4	164.1
40°	142.5	141.6	141.2	141.1	141.2	141.6	142.5	144.9	149.0	150.6	154.6
42.5°	133.6	131.1	130.2	130.2	130.2	131.1	133.6	136.3	138.8	141.4	145.5
45°	120.0	117.7	116.1	116.2	116.1	117.7	120.0	120.9	123.1	128.3	130.6
47.5°	106.2	106.1	105.0	105.4	105.0	106.1	106.2	107.7	110.4	113.7	117.4
50°	99.5	98.5	97.7	97.9	97.7	98.5	99.5	100.8	102.3	104.0	109.8
52.5°	93.2	92.2	91.7	92.4	91.7	92.2	93.2	93.9	95.1	96.6	100.5
55°	82.8	81.7	81.5	81.4	81.5	81.7	82.8	83.7	85.1	86.3	88.2
57.5°	71.1	70.4	69.3	68.9	69.3	70.4	71.1	72.5	74.2	75.9	77.7
60°	62.8	61.4	59.6	59.4	59.6	61.4	62.8	65.1	65.8	68.4	70.5
62.5°	55.1	54.9	54.5	54.5	54.5	54.9	55.1	55.9	57.0	60.6	63.2
65°	48.4	48.2	48.4	48.6	48.4	48.2	48.4	48.8	49.0	49.3	50.4
67.5°	42.1	41.8	41.5	41.7	41.5	41.8	42.1	42.2	42.8	42.9	43.7
70°	37.4	37.2	37.1	37.1	37.1	37.2	37.4	37.8	38.2	38.5	39.4
72.5°	32.8	32.8	32.6	32.5	32.6	32.8	32.8	33.5	33.7	34.1	34.6
75°	26.3	25.9	25.9	25.9	25.9	25.9	26.3	26.5	26.6	27.2	27.6
77.5°	20.0	19.8	19.6	19.5	19.6	19.8	20.0	20.0	20.4	20.4	20.8
80°	15.8	15.7	15.4	15.4	15.4	15.7	15.8	16.0	16.0	16.6	16.4
82.5°	12.1	11.9	11.9	11.7	11.9	11.9	12.1	12.1	12.1	12.5	12.5
85°	6.5	6.7	6.5	6.8	6.5	6.7	6.5	6.3	6.5	6.8	6.8
87.5°	7.1	7.1	7.2	7.1	7.2	7.1	7.1	7.1	7.3	7.4	7.4
90°	26.4	26.5	26.7	26.9	26.7	26.5	26.4	26.1	26.3	26.6	26.9
92.5°	25.5	25.5	25.6	25.6	25.6	25.5	25.5	25.5	25.4	25.3	25.3
95°	50.1	49.7	49.4	49.0	49.4	49.7	50.1	50.4	50.6	50.6	50.6
97.5°	85.0	85.0	84.9	84.9	84.9	85.0	85.0	85.1	85.1	85.1	85.1
100°	108.8	108.7	108.4	108.3	108.4	108.7	108.8	109.0	109.1	109.1	109.1
102.5°	135.4	135.2	135.1	134.9	135.1	135.2	135.4	135.5	135.6	135.5	135.3
105°	175.5	175.5	175.5	175.5	175.5	175.5	175.5	175.5	175.3	175.0	174.6
107.5°	216.2	215.4	214.6	213.7	214.6	215.4	216.2	217.0	217.3	217.2	217.1
110°	245.1	244.5	244.0	243.5	244.0	244.5	245.1	245.6	245.9	245.9	245.9



TEST NUMBER: P331634-927

CATALOG NUMBER: S122RDIP-S290D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	273.1	272.7	272.4	272.0	272.4	272.7	273.1	273.5	273.9	274.3	274.7
115°	317.8	317.3	316.7	316.2	316.7	317.3	317.8	318.3	318.7	318.9	319.0
117.5°	360.0	359.5	358.9	358.5	358.9	359.5	360.0	360.5	361.0	361.5	361.9
120°	389.8	389.2	388.7	388.2	388.7	389.2	389.8	390.3	390.5	390.5	390.5
122.5°	418.4	418.0	417.6	417.2	417.6	418.0	418.4	418.8	419.2	419.6	420.0
125°	462.2	462.0	461.8	461.7	461.8	462.0	462.2	462.4	462.7	463.3	463.8
127.5°	503.8	503.3	502.7	502.2	502.7	503.3	503.8	504.4	505.0	505.6	506.3
130°	533.4	532.7	532.0	531.2	532.0	532.7	533.4	534.1	534.6	535.0	535.3
132.5°	560.8	560.2	559.7	559.1	559.7	560.2	560.8	561.3	562.0	562.8	563.6
135°	604.0	603.5	602.9	602.4	602.9	603.5	604.0	604.5	604.8	605.1	605.2
137.5°	643.7	643.0	642.3	641.6	642.3	643.0	643.7	644.4	644.8	645.0	645.2
140°	670.9	670.2	669.6	668.8	669.6	670.2	670.9	671.6	672.0	672.0	672.0
142.5°	695.6	694.9	694.2	693.5	694.2	694.9	695.6	696.3	696.6	696.4	696.3
145°	732.6	731.9	731.2	730.5	731.2	731.9	732.6	733.3	733.6	733.4	733.2
147.5°	765.6	764.9	764.2	763.5	764.2	764.9	765.6	766.2	766.4	766.0	765.6
150°	786.6	786.1	785.5	785.1	785.5	786.1	786.6	787.1	787.1	786.6	786.1
152.5°	807.2	806.6	806.0	805.3	806.0	806.6	807.2	807.9	807.9	807.2	806.6
155°	834.0	833.5	833.0	832.4	833.0	833.5	834.0	834.6	834.4	833.5	832.7
157.5°	858.4	857.5	856.7	855.9	856.7	857.5	858.4	859.2	859.0	857.9	856.7
160°	872.5	871.8	871.1	870.4	871.1	871.8	872.5	873.2	873.1	872.0	870.9
162.5°	885.6	884.7	883.9	883.0	883.9	884.7	885.6	886.5	886.2	885.0	883.8
165°	902.3	901.4	900.6	899.7	900.6	901.4	902.3	903.2	903.0	901.7	900.6
167.5°	916.0	915.0	914.2	913.2	914.2	915.0	916.0	916.9	916.7	915.5	914.3
170°	923.4	922.3	921.2	920.2	921.2	922.3	923.4	924.4	924.3	923.1	921.9
172.5°	929.1	928.0	926.9	925.9	926.9	928.0	929.1	930.1	930.0	928.8	927.6
175°	935.3	934.1	933.1	932.1	933.1	934.1	935.3	936.3	936.2	934.9	933.7
177.5°	937.5	936.6	935.7	934.9	935.7	936.6	937.5	938.3	938.3	937.5	936.6
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8



TEST NUMBER: P331634-927

CATALOG NUMBER: S122RDIP-S290D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8
2.5°	498.0	500.0	503.0	504.8	507.6	509.5	510.6	512.4	513.4	517.1	520.8
5°	470.2	473.1	478.1	482.8	487.8	493.1	496.9	501.1	505.1	511.9	519.1
7.5°	438.3	442.3	450.1	457.6	466.4	473.7	480.2	487.6	494.2	504.0	514.2
10°	414.4	421.4	431.7	438.7	450.2	457.6	467.9	475.9	485.1	498.1	509.6
12.5°	393.8	402.3	410.5	420.3	430.6	442.9	454.2	464.6	475.5	488.9	502.4
15°	356.5	368.7	381.5	391.4	405.4	418.4	431.5	445.5	458.8	474.9	492.5
17.5°	308.4	322.6	344.0	361.0	377.5	390.5	406.8	423.7	439.4	458.8	478.4
20°	286.7	297.1	311.6	334.5	359.3	373.2	389.8	408.4	426.4	447.5	468.6
22.5°	269.3	278.5	290.2	308.0	335.7	354.7	371.9	390.9	411.8	433.2	456.6
25°	244.4	250.8	263.1	277.5	296.5	327.6	346.6	365.7	388.3	411.4	438.0
27.5°	225.7	231.6	239.5	253.2	267.4	289.8	319.8	340.6	363.2	389.1	416.8
30°	211.4	218.2	227.1	236.8	252.3	269.7	299.8	323.9	346.2	372.9	402.3
32.5°	201.1	206.4	214.0	223.9	236.7	253.5	277.5	306.7	328.5	356.6	387.4
35°	184.1	190.4	196.5	205.9	216.3	231.6	249.8	281.1	302.7	330.3	361.3
37.5°	170.1	174.0	180.7	188.1	199.2	210.6	226.3	254.4	277.7	304.9	336.6
40°	159.5	164.3	169.3	177.6	186.6	197.6	213.0	233.9	260.7	287.4	318.3
42.5°	149.1	155.2	160.6	166.1	175.9	187.0	199.6	217.2	244.6	269.8	299.9
45°	136.6	140.5	146.1	152.3	160.3	169.7	180.9	196.3	222.6	244.4	272.6
47.5°	122.1	127.9	131.5	137.4	145.1	154.1	164.5	177.8	199.1	219.5	245.7
50°	112.1	118.0	123.3	128.7	135.5	144.1	152.8	165.7	182.8	204.2	228.7
52.5°	103.6	108.8	113.9	119.3	126.0	133.9	142.1	153.5	168.1	187.8	211.6
55°	92.0	95.2	100.4	105.8	111.8	119.3	127.2	136.7	149.3	165.9	185.1
57.5°	80.0	83.7	87.9	93.3	99.3	105.1	112.3	120.9	130.8	145.8	162.2
60°	73.3	76.1	79.5	85.1	90.7	95.9	102.7	110.0	119.3	132.3	146.3
62.5°	65.8	68.5	71.6	76.4	81.9	86.7	92.7	100.3	108.2	120.0	132.3
65°	53.2	57.2	60.3	64.6	69.1	74.1	78.8	84.9	92.0	101.3	112.3
67.5°	44.1	46.2	49.0	52.9	57.5	61.9	66.3	71.1	77.2	84.4	93.1
70°	40.2	40.9	41.4	45.2	49.5	53.8	57.9	62.4	67.7	73.6	81.1
72.5°	35.4	36.1	36.8	38.4	41.8	46.2	50.5	53.8	58.7	63.7	69.8
75°	28.0	29.2	29.7	30.6	31.8	34.7	38.7	41.9	44.8	48.6	53.5
77.5°	21.4	22.0	22.6	23.5	24.3	25.6	27.9	30.7	33.5	35.6	39.0
80°	17.0	17.1	17.8	18.1	19.3	20.1	21.2	23.6	26.3	27.2	29.5
82.5°	12.8	12.9	13.5	13.9	14.3	15.1	16.5	17.1	19.3	20.4	21.9
85°	7.1	6.8	7.4	7.4	7.8	8.1	8.5	9.3	9.9	11.3	11.7
87.5°	7.6	7.7	7.1	6.3	5.5	5.1	4.6	4.3	4.2	4.2	4.4
90°	27.3	27.6	23.8	20.0	16.1	12.2	9.2	7.1	5.0	2.9	0.8
92.5°	25.2	25.1	24.2	23.3	22.4	21.5	20.3	18.7	17.2	15.6	14.1
95°	50.6	50.6	50.2	49.9	49.5	49.2	48.2	46.3	44.6	42.9	41.1
97.5°	85.1	85.1	84.4	83.7	83.1	82.4	81.3	79.8	78.2	76.7	75.1
100°	109.1	109.1	108.6	108.1	107.5	107.0	106.0	104.6	103.2	101.8	100.4
102.5°	135.1	135.1	134.4	133.7	133.0	132.4	131.4	130.3	129.2	128.1	127.0
105°	174.3	173.9	173.6	173.3	172.9	172.5	172.1	171.6	171.0	170.5	170.0
107.5°	216.9	216.7	216.7	216.7	216.7	216.7	216.4	215.6	214.8	214.0	213.3
110°	245.9	245.9	245.9	245.9	245.9	245.9	245.3	244.3	243.2	242.2	241.1



TEST NUMBER: P331634-927

CATALOG NUMBER: S122RDIP-S290D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	275.2	275.6	275.8	275.8	276.0	276.2	275.7	274.6	273.6	272.5	271.5
115°	319.2	319.4	319.7	320.1	320.4	320.8	320.4	319.4	318.3	317.3	316.2
117.5°	362.3	362.7	363.7	364.6	365.7	366.6	366.5	365.0	363.6	362.2	360.8
120°	390.5	390.5	392.0	393.3	394.7	396.2	396.2	394.7	393.3	392.0	390.5
122.5°	420.5	420.9	421.9	422.9	423.8	424.8	424.5	422.8	421.1	419.4	417.7
125°	464.3	464.9	465.4	465.9	466.4	467.0	466.4	464.9	463.3	461.7	460.1
127.5°	506.9	507.6	508.2	508.8	509.5	510.1	509.4	507.4	505.4	503.4	501.4
130°	535.7	536.0	536.4	536.7	537.0	537.4	536.5	534.2	531.9	529.6	527.3
132.5°	564.4	565.1	565.0	565.0	564.9	564.8	563.9	562.0	560.2	558.3	556.4
135°	605.4	605.5	605.2	604.8	604.5	604.2	603.0	601.1	599.1	597.2	595.3
137.5°	645.3	645.4	645.0	644.5	644.0	643.6	642.5	641.0	639.4	637.8	636.3
140°	672.0	672.0	671.1	670.2	669.3	668.4	667.3	665.7	664.1	662.5	660.9
142.5°	696.2	696.0	695.4	694.8	694.2	693.6	692.5	690.9	689.4	687.8	686.2
145°	733.0	732.8	731.8	730.7	729.7	728.6	727.5	726.3	725.0	723.8	722.5
147.5°	765.2	764.8	764.1	763.3	762.7	762.0	760.9	759.4	758.0	756.5	754.9
150°	785.5	785.1	784.3	783.6	782.9	782.2	781.3	780.3	779.2	778.2	777.1
152.5°	806.0	805.3	804.4	803.6	802.7	801.9	801.0	799.9	798.8	797.8	796.7
155°	831.8	830.8	830.4	829.8	829.3	828.8	828.2	827.8	827.2	826.6	826.2
157.5°	855.5	854.3	854.0	853.7	853.3	853.0	852.7	852.3	852.0	851.6	851.3
160°	869.9	868.8	868.6	868.5	868.3	868.2	867.8	867.5	867.1	866.8	866.5
162.5°	882.6	881.5	881.3	881.1	881.0	880.7	880.7	880.6	880.5	880.4	880.4
165°	899.3	898.1	898.1	898.1	898.1	898.1	898.2	898.3	898.5	898.7	898.9
167.5°	913.1	911.8	911.9	911.9	912.0	912.0	912.3	912.8	913.3	913.9	914.3
170°	920.7	919.4	919.6	919.8	920.0	920.1	920.4	921.0	921.5	922.0	922.6
172.5°	926.4	925.1	925.3	925.4	925.7	925.8	926.1	926.7	927.2	927.7	928.3
175°	932.5	931.3	931.6	932.0	932.3	932.7	933.1	933.7	934.1	934.7	935.3
177.5°	935.7	934.9	935.2	935.5	935.7	936.0	936.4	936.8	937.2	937.6	938.1
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8



TEST NUMBER: P331634-927

CATALOG NUMBER: S122RDIP-S290D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8
2.5°	520.9	521.3	524.2	525.5	528.1	529.1	530.3	530.0	530.0	530.5	534.6
5°	522.0	525.6	531.0	536.2	541.3	545.6	548.5	551.4	552.5	557.6	562.3
7.5°	520.1	526.8	535.7	543.7	553.2	560.6	566.8	572.4	576.2	583.8	591.6
10°	517.7	527.0	537.1	547.4	560.5	570.5	580.5	588.3	590.7	602.1	608.6
12.5°	512.8	525.3	538.1	551.4	564.3	577.9	589.0	596.8	605.6	615.8	627.7
15°	505.5	519.8	536.6	553.7	572.0	588.6	600.5	613.9	623.7	634.9	645.3
17.5°	495.0	513.5	534.7	554.5	575.8	593.5	609.9	622.8	629.6	636.0	637.5
20°	486.6	506.5	531.6	554.9	576.2	596.7	612.9	623.7	625.5	625.7	616.2
22.5°	477.5	500.1	526.2	550.2	575.6	598.4	611.0	615.6	608.5	596.3	577.8
25°	460.8	487.0	517.4	544.7	572.4	594.0	598.3	590.3	565.2	538.9	505.6
27.5°	442.8	472.1	504.7	535.1	564.7	578.1	568.7	539.5	494.5	455.3	407.8
30°	429.5	462.5	494.5	528.5	555.9	561.6	540.2	497.2	444.7	385.6	338.3
32.5°	414.4	448.9	484.1	519.3	542.2	536.5	501.2	448.2	386.7	328.6	283.9
35°	392.8	428.4	466.4	501.7	516.3	491.9	439.0	370.1	307.1	253.0	222.2
37.5°	367.9	406.7	446.2	478.6	477.5	437.0	365.0	293.8	240.9	208.8	187.0
40°	350.1	389.4	432.1	459.4	447.7	395.0	316.9	249.8	211.0	185.5	169.5
42.5°	333.2	372.6	414.9	436.7	416.3	351.5	273.7	221.1	189.2	169.3	156.3
45°	304.3	345.9	385.1	397.1	360.8	289.4	221.3	183.2	161.9	147.2	138.2
47.5°	276.0	317.0	352.8	352.9	303.8	234.6	186.7	158.5	140.4	129.0	122.5
50°	258.7	297.6	327.6	323.0	267.2	208.7	167.0	142.7	127.6	118.7	111.9
52.5°	239.3	277.0	303.1	289.8	236.2	183.7	149.2	128.9	116.4	108.7	102.6
55°	211.0	244.5	262.9	242.7	192.7	152.8	126.1	110.1	100.8	94.3	89.0
57.5°	183.3	211.0	222.4	199.0	158.8	126.7	106.7	94.7	85.4	80.7	78.0
60°	165.9	189.5	197.6	171.7	138.0	110.8	94.5	83.3	76.4	73.4	70.7
62.5°	148.8	168.0	171.3	147.7	120.3	97.0	82.9	73.5	69.0	66.1	63.5
65°	123.4	137.3	135.7	116.6	95.2	77.0	66.8	61.0	57.6	53.5	49.0
67.5°	101.6	110.1	105.0	90.7	72.6	59.9	53.2	48.8	44.5	40.6	39.6
70°	87.8	92.7	87.3	74.1	59.6	50.2	44.8	39.6	37.1	36.2	34.5
72.5°	74.5	76.3	70.4	59.2	48.5	41.6	36.3	33.4	32.0	31.3	30.3
75°	55.9	54.7	49.7	40.9	33.7	29.0	27.3	26.3	25.3	24.6	24.1
77.5°	39.3	37.5	33.0	27.2	23.4	21.2	20.2	19.6	19.3	18.9	18.3
80°	29.5	28.3	23.8	19.4	17.8	16.7	16.2	15.4	15.4	15.1	14.6
82.5°	21.6	20.2	16.2	14.3	13.4	12.7	12.3	11.9	11.7	11.8	11.4
85°	11.3	9.2	8.1	7.8	7.2	6.8	7.1	6.7	6.7	6.7	6.5
87.5°	4.0	3.7	4.0	4.3	5.1	5.8	6.4	7.2	8.2	7.9	8.0
90°	2.9	5.0	7.1	9.2	12.2	16.1	20.0	23.8	27.6	27.3	26.9
92.5°	15.6	17.2	18.7	20.3	21.5	22.4	23.3	24.2	25.1	25.2	25.3
95°	42.9	44.6	46.3	48.2	49.2	49.5	49.9	50.2	50.6	50.6	50.6
97.5°	76.7	78.2	79.8	81.3	82.4	83.1	83.7	84.4	85.1	85.1	85.1
100°	101.8	103.2	104.6	106.0	107.0	107.5	108.1	108.6	109.1	109.1	109.1
102.5°	128.1	129.2	130.3	131.4	132.4	133.0	133.7	134.4	135.1	135.1	135.3
105°	170.5	171.0	171.6	172.1	172.5	172.9	173.3	173.6	173.9	174.3	174.6
107.5°	214.0	214.8	215.6	216.4	216.7	216.7	216.7	216.7	216.7	216.9	217.1
110°	242.2	243.2	244.3	245.3	245.9	245.9	245.9	245.9	245.9	245.9	245.9



TEST NUMBER: P331634-927

CATALOG NUMBER: S122RDIP-S290D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	272.5	273.6	274.6	275.7	276.2	276.0	275.8	275.8	275.6	275.2	274.7
115°	317.3	318.3	319.4	320.4	320.8	320.4	320.1	319.7	319.4	319.2	319.0
117.5°	362.2	363.6	365.0	366.5	366.6	365.7	364.6	363.7	362.7	362.3	361.9
120°	392.0	393.3	394.7	396.2	396.2	394.7	393.3	392.0	390.5	390.5	390.5
122.5°	419.4	421.1	422.8	424.5	424.8	423.8	422.9	421.9	420.9	420.5	420.0
125°	461.7	463.3	464.9	466.4	467.0	466.4	465.9	465.4	464.9	464.3	463.8
127.5°	503.4	505.4	507.4	509.4	510.1	509.5	508.8	508.2	507.6	506.9	506.3
130°	529.6	531.9	534.2	536.5	537.4	537.0	536.7	536.4	536.0	535.7	535.3
132.5°	558.3	560.2	562.0	563.9	564.8	564.9	565.0	565.0	565.1	564.4	563.6
135°	597.2	599.1	601.1	603.0	604.2	604.5	604.8	605.2	605.5	605.4	605.2
137.5°	637.8	639.4	641.0	642.5	643.6	644.0	644.5	645.0	645.4	645.3	645.2
140°	662.5	664.1	665.7	667.3	668.4	669.3	670.2	671.1	672.0	672.0	672.0
142.5°	687.8	689.4	690.9	692.5	693.6	694.2	694.8	695.4	696.0	696.2	696.3
145°	723.8	725.0	726.3	727.5	728.6	729.7	730.7	731.8	732.8	733.0	733.2
147.5°	756.5	758.0	759.4	760.9	762.0	762.7	763.3	764.1	764.8	765.2	765.6
150°	778.2	779.2	780.3	781.3	782.2	782.9	783.6	784.3	785.1	785.5	786.1
152.5°	797.8	798.8	799.9	801.0	801.9	802.7	803.6	804.4	805.3	806.0	806.6
155°	826.6	827.2	827.8	828.2	828.8	829.3	829.8	830.4	830.8	831.8	832.7
157.5°	851.6	852.0	852.3	852.7	853.0	853.3	853.7	854.0	854.3	855.5	856.7
160°	866.8	867.1	867.5	867.8	868.2	868.3	868.5	868.6	868.8	869.9	870.9
162.5°	880.4	880.5	880.6	880.7	880.7	881.0	881.1	881.3	881.5	882.6	883.8
165°	898.7	898.5	898.3	898.2	898.1	898.1	898.1	898.1	898.1	899.3	900.6
167.5°	913.9	913.3	912.8	912.3	912.0	912.0	911.9	911.9	911.8	913.1	914.3
170°	922.0	921.5	921.0	920.4	920.1	920.0	919.8	919.6	919.4	920.7	921.9
172.5°	927.7	927.2	926.7	926.1	925.8	925.7	925.4	925.3	925.1	926.4	927.6
175°	934.7	934.1	933.7	933.1	932.7	932.3	932.0	931.6	931.3	932.5	933.7
177.5°	937.6	937.2	936.8	936.4	936.0	935.7	935.5	935.2	934.9	935.7	936.6
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8



TEST NUMBER: P331634-927

CATALOG NUMBER: S122RDIP-S290D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	517.8	517.8	517.8	517.8	517.8	517.8	517.8
2.5°	536.0	537.9	538.8	538.8	539.8	539.3	538.9
5°	566.8	570.2	571.0	574.2	576.6	575.8	576.2
7.5°	597.5	602.9	608.4	610.9	611.2	612.7	613.2
10°	616.3	620.8	629.2	628.0	634.3	637.9	632.0
12.5°	634.5	640.6	646.4	648.0	651.6	652.8	650.4
15°	650.9	654.1	654.4	653.6	654.7	653.7	650.3
17.5°	635.6	630.3	619.6	614.6	610.6	604.7	602.3
20°	610.2	594.7	576.7	569.5	561.1	544.5	548.5
22.5°	555.5	537.9	519.8	498.8	488.8	473.1	472.1
25°	470.4	440.0	406.5	383.1	369.4	353.8	346.9
27.5°	365.8	327.4	300.0	286.1	273.5	261.1	260.5
30°	296.9	268.2	246.9	235.0	227.3	222.0	223.2
32.5°	250.3	230.5	216.2	206.4	200.7	196.7	196.6
35°	204.6	191.1	181.9	177.8	173.6	170.8	171.0
37.5°	175.1	167.0	161.8	157.3	154.7	153.3	152.5
40°	159.9	153.3	149.3	146.6	144.5	142.5	142.1
42.5°	148.1	142.5	138.6	136.4	134.4	133.0	132.7
45°	131.3	126.8	123.3	120.9	120.0	118.7	118.7
47.5°	116.8	112.4	109.6	108.1	106.6	105.8	105.8
50°	107.1	103.6	101.2	100.2	98.9	98.5	98.2
52.5°	98.3	95.7	94.0	93.3	92.8	92.1	92.2
55°	86.3	84.9	84.2	83.7	82.8	81.7	82.4
57.5°	76.4	75.1	73.2	71.5	70.7	69.9	70.2
60°	69.3	66.8	64.2	62.3	61.7	60.1	60.1
62.5°	60.4	56.8	53.7	52.6	52.0	51.3	51.2
65°	46.4	45.0	44.3	43.6	43.2	43.2	42.9
67.5°	38.5	37.9	37.1	36.9	36.6	36.4	36.4
70°	34.0	33.3	33.0	32.7	32.4	32.6	32.0
72.5°	29.7	29.2	29.1	28.6	28.4	28.4	28.0
75°	23.4	23.4	23.2	23.1	22.7	22.5	22.7
77.5°	18.0	18.1	17.7	17.7	17.7	17.7	17.5
80°	14.4	14.6	14.4	14.2	14.0	14.2	14.0
82.5°	11.4	11.1	11.1	11.0	11.0	10.9	10.9
85°	6.5	6.7	6.5	6.3	6.3	6.3	6.5
87.5°	7.8	7.7	7.7	7.7	7.8	7.8	7.7
90°	26.6	26.3	26.1	26.4	26.5	26.7	26.9
92.5°	25.3	25.4	25.5	25.5	25.5	25.6	25.6
95°	50.6	50.6	50.4	50.1	49.7	49.4	49.0
97.5°	85.1	85.1	85.1	85.0	85.0	84.9	84.9
100°	109.1	109.1	109.0	108.8	108.7	108.4	108.3
102.5°	135.5	135.6	135.5	135.4	135.2	135.1	134.9
105°	175.0	175.3	175.5	175.5	175.5	175.5	175.5
107.5°	217.2	217.3	217.0	216.2	215.4	214.6	213.7
110°	245.9	245.9	245.6	245.1	244.5	244.0	243.5



TEST NUMBER: P331634-927

CATALOG NUMBER: S122RDIP-S290D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	274.3	273.9	273.5	273.1	272.7	272.4	272.0
115°	318.9	318.7	318.3	317.8	317.3	316.7	316.2
117.5°	361.5	361.0	360.5	360.0	359.5	358.9	358.5
120°	390.5	390.5	390.3	389.8	389.2	388.7	388.2
122.5°	419.6	419.2	418.8	418.4	418.0	417.6	417.2
125°	463.3	462.7	462.4	462.2	462.0	461.8	461.7
127.5°	505.6	505.0	504.4	503.8	503.3	502.7	502.2
130°	535.0	534.6	534.1	533.4	532.7	532.0	531.2
132.5°	562.8	562.0	561.3	560.8	560.2	559.7	559.1
135°	605.1	604.8	604.5	604.0	603.5	602.9	602.4
137.5°	645.0	644.8	644.4	643.7	643.0	642.3	641.6
140°	672.0	672.0	671.6	670.9	670.2	669.6	668.8
142.5°	696.4	696.6	696.3	695.6	694.9	694.2	693.5
145°	733.4	733.6	733.3	732.6	731.9	731.2	730.5
147.5°	766.0	766.4	766.2	765.6	764.9	764.2	763.5
150°	786.6	787.1	787.1	786.6	786.1	785.5	785.1
152.5°	807.2	807.9	807.9	807.2	806.6	806.0	805.3
155°	833.5	834.4	834.6	834.0	833.5	833.0	832.4
157.5°	857.9	859.0	859.2	858.4	857.5	856.7	855.9
160°	872.0	873.1	873.2	872.5	871.8	871.1	870.4
162.5°	885.0	886.2	886.5	885.6	884.7	883.9	883.0
165°	901.7	903.0	903.2	902.3	901.4	900.6	899.7
167.5°	915.5	916.7	916.9	916.0	915.0	914.2	913.2
170°	923.1	924.3	924.4	923.4	922.3	921.2	920.2
172.5°	928.8	930.0	930.1	929.1	928.0	926.9	925.9
175°	934.9	936.2	936.3	935.3	934.1	933.1	932.1
177.5°	937.5	938.3	938.3	937.5	936.6	935.7	934.9
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8

(END OF REPORT)