

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331647-927

Luminaire Tested: **S122RDIP-S485D330U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331647-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S485D330U927-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2485.6 lumens
Efficiency: N/A
Efficacy: 90.4 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331647-927

CATALOG NUMBER: S122RDIP-S485D330U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331647-927

CATALOG NUMBER: S122RDIP-S485D330U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65	59					59			
1	101	97	93	90	94	91	87	85	79	77	75	68	67	65	59	57	56	52					52			
2	93	86	80	75	86	80	75	71	70	67	63	61	58	56	53	51	49	45					45			
3	85	76	69	64	79	72	66	61	63	58	54	55	52	49	48	45	43	39					39			
4	78	68	61	55	73	64	58	52	57	52	47	50	46	43	43	40	38	35					35			
5	72	61	54	48	68	58	51	46	51	46	42	45	41	38	40	36	34	31					31			
6	67	56	48	42	63	53	46	41	47	41	37	41	37	34	36	33	30	28					28			
7	62	51	43	38	58	48	41	36	43	37	33	38	34	30	34	30	27	25					25			
8	58	46	39	34	55	44	37	33	39	34	30	35	31	27	31	28	25	23					23			
9	55	43	35	31	51	41	34	29	36	31	27	33	28	25	29	25	23	21					21			
10	51	39	32	28	48	38	31	27	34	29	25	30	26	23	27	24	21	19					19			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13747	13747	13747	13747
5°	15352	13833	12266	13833
10°	17033	13736	10632	13736
15°	17870	13534	8376	13534
20°	15493	13235	7247	13235
25°	10162	12827	6472	12827
30°	6840	12333	5858	12333
35°	5541	11710	5282	11710
40°	4926	11030	4890	11030
45°	4459	10234	4364	10234
50°	4057	9445	4042	9445
55°	3814	8569	3764	8569
60°	3190	7766	3152	7766
65°	2690	7053	3053	7053
70°	2488	6297	2875	6297
75°	2327	5483	2658	5483
80°	2148	4510	2362	4510
85°	1964	3575	2075	3575



TEST NUMBER: P331647-927

CATALOG NUMBER: S122RDIP-S485D330U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.7	3.2
10°-20°	224.9	9.0
20°-30°	289.8	11.7
30°-40°	275.4	11.1
40°-50°	235.9	9.5
50°-60°	179.7	7.2
60°-70°	113.6	4.6
70°-80°	56.7	2.3
80°-90°	16.1	0.6
90°-100°	58.2	2.3
100°-110°	197.5	7.9
110°-120°	209.8	8.4
120°-130°	172.7	6.9
130°-140°	138.7	5.6
140°-150°	104.8	4.2
150°-160°	73.7	3.0
160°-170°	43.4	1.7
170°-180°	14.1	0.6
0°-30°	595.4	24.0
0°-40°	870.8	35.0
0°-60°	1286.4	51.8
0°-90°	1472.7	59.3
90°-120°	465.5	18.7
90°-150°	881.7	35.5
90°-180°	1013.0	40.8
0°-180°	2485.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	851	851	851	851	851	
5°	947	854	757	854	947	93
15°	1069	810	501	810	1069	288
25°	570	720	363	720	570	271
35°	281	594	268	594	281	180
45°	195	448	191	448	195	151
55°	136	304	134	304	136	119
65°	70	185	80	185	70	72
75°	37	88	43	88	37	40
85°	11	19	11	19	11	12
90°	9	0	9	0	9	5
95°	32	10	32	10	32	41
105°	315	34	315	34	315	305
115°	415	60	415	60	415	406
125°	337	84	337	84	337	304
135°	279	98	279	98	279	217
145°	223	112	223	112	223	142
155°	187	128	187	128	187	87
165°	164	139	164	139	164	47
175°	148	145	148	145	148	14
180°	146	146	146	146	146	



TEST NUMBER: P331647-927

CATALOG NUMBER: S122RDIP-S485D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	886.0	886.7	887.4	885.7	885.7	884.3	881.2	878.8	872.2	871.2	871.2
5°	947.2	946.7	947.8	944.0	938.7	937.5	931.8	924.5	916.8	908.2	906.4
7.5°	1008.2	1007.3	1005.0	1004.2	1000.2	991.3	982.2	972.6	959.8	947.3	941.0
10°	1038.9	1048.7	1042.8	1032.5	1034.5	1020.6	1013.2	1000.5	989.8	971.2	967.1
12.5°	1069.2	1073.1	1071.2	1065.3	1062.7	1053.0	1043.1	1032.0	1012.3	995.6	981.0
15°	1069.1	1074.8	1076.3	1074.4	1075.9	1075.3	1070.0	1060.8	1043.7	1025.3	1009.4
17.5°	990.2	994.1	1003.8	1010.3	1018.7	1036.2	1044.8	1048.2	1045.6	1035.1	1023.9
20°	901.7	895.2	922.4	936.3	948.2	977.7	1003.1	1012.9	1028.6	1028.3	1025.3
22.5°	776.3	777.8	803.6	820.1	854.7	884.2	913.2	950.0	980.3	1000.4	1012.1
25°	570.4	581.6	607.4	629.8	668.3	723.3	773.3	831.3	886.0	929.2	970.3
27.5°	428.3	429.2	449.6	470.4	493.2	538.3	601.3	670.5	748.5	812.9	886.9
30°	366.9	365.0	373.7	386.3	405.9	440.8	488.1	556.2	634.0	731.0	817.4
32.5°	323.3	323.4	329.9	339.3	355.5	379.0	411.5	466.7	540.3	635.6	736.9
35°	281.1	280.7	285.5	292.3	299.0	314.2	336.4	365.4	416.0	505.0	608.6
37.5°	250.7	252.1	254.4	258.6	266.1	274.5	287.9	307.3	343.3	396.0	483.0
40°	233.7	234.3	237.6	241.1	245.6	252.1	263.0	278.7	305.0	347.0	410.6
42.5°	218.1	218.6	221.0	224.3	227.8	234.3	243.4	256.9	278.3	311.0	363.5
45°	195.3	195.3	197.3	198.8	202.6	208.6	215.9	227.2	242.0	266.3	301.2
47.5°	173.8	173.9	175.2	177.8	180.2	184.8	192.1	201.3	212.1	230.8	260.6
50°	161.5	161.8	162.7	164.8	166.3	170.4	176.0	184.0	195.3	209.8	234.6
52.5°	151.5	151.4	152.5	153.4	154.4	157.4	161.6	168.7	178.7	191.3	211.9
55°	135.5	134.3	136.1	137.5	138.5	139.7	142.0	146.5	155.0	165.6	181.0
57.5°	115.3	114.9	116.1	117.5	120.3	123.5	125.5	128.3	132.8	140.4	155.7
60°	98.8	98.8	101.5	102.3	105.6	109.7	113.9	116.3	120.7	125.7	137.0
62.5°	84.1	84.4	85.6	86.5	88.3	93.4	99.3	104.4	108.6	113.4	120.9
65°	70.4	71.0	71.0	71.6	72.8	74.0	76.3	80.5	87.9	94.7	100.3
67.5°	59.7	60.0	60.1	60.7	61.0	62.3	63.2	65.1	66.8	73.3	80.2
70°	52.7	53.6	53.2	53.9	54.1	54.7	55.9	56.8	59.5	60.9	65.1
72.5°	46.0	46.7	46.7	47.0	47.8	47.8	48.8	49.7	51.4	52.7	54.9
75°	37.3	37.0	37.3	37.9	38.2	38.4	38.4	39.6	40.6	41.7	43.2
77.5°	28.8	29.1	29.0	29.1	29.1	29.6	29.5	30.1	31.0	31.6	32.3
80°	23.1	23.4	23.1	23.4	23.7	23.9	23.7	23.9	24.9	25.4	25.4
82.5°	17.9	17.9	18.1	18.1	18.2	18.3	18.7	18.8	19.4	19.3	19.5
85°	10.6	10.4	10.4	10.4	10.6	10.9	10.6	10.6	10.9	10.9	10.9
87.5°	5.6	5.9	5.9	5.9	5.9	5.8	5.7	6.0	5.9	6.2	5.9
90°	9.3	9.3	9.3	9.3	9.3	9.0	8.4	9.0	9.3	9.5	9.3
92.5°	15.5	15.9	15.8	16.6	16.9	18.6	20.9	24.4	30.7	36.4	35.9
95°	31.9	31.6	32.5	34.7	38.3	44.5	56.2	73.4	96.0	109.7	97.1
97.5°	62.8	65.2	69.2	76.1	89.5	109.7	140.0	171.1	196.5	187.3	141.1
100°	100.2	105.3	113.4	125.4	148.6	182.5	220.9	255.6	261.4	221.1	152.3
102.5°	176.3	183.2	193.3	213.8	239.1	275.0	303.0	310.9	285.6	222.2	148.0
105°	315.4	319.3	331.4	348.7	366.1	375.3	371.7	340.1	281.9	207.4	139.7
107.5°	403.0	408.1	410.6	411.5	409.3	395.8	366.7	319.0	257.3	191.5	135.5
110°	429.4	429.7	427.1	421.8	409.8	386.8	351.0	300.9	241.9	183.9	134.7



TEST NUMBER: P331647-927

CATALOG NUMBER: S122RDIP-S485D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	428.9	427.4	422.6	413.8	397.0	370.7	332.4	284.3	231.1	179.0	134.8
115°	415.1	412.6	405.3	392.4	372.6	343.7	307.0	264.0	217.8	173.6	136.0
117.5°	390.4	388.2	380.6	367.0	346.7	319.7	286.5	248.6	209.4	170.9	138.1
120°	374.5	371.7	363.6	350.5	330.8	305.4	275.7	241.0	204.9	169.4	139.4
122.5°	357.9	355.6	348.4	335.4	317.8	294.9	266.7	235.0	201.1	168.4	140.9
125°	336.8	334.5	327.5	316.9	300.6	279.6	255.0	226.2	195.7	166.8	143.3
127.5°	318.1	316.3	310.3	300.3	286.1	266.8	243.6	217.5	190.6	165.9	145.7
130°	307.6	305.4	299.8	290.3	276.6	258.1	236.0	211.9	187.3	165.4	147.5
132.5°	296.7	294.6	289.5	280.0	266.5	249.1	228.8	206.5	184.6	165.2	149.3
135°	279.1	278.0	272.9	263.6	251.6	236.0	217.5	199.0	180.8	164.9	151.5
137.5°	261.8	260.2	255.7	247.8	236.8	223.2	208.5	193.1	178.2	164.8	153.4
140°	249.9	248.3	244.1	236.8	227.8	215.6	202.6	189.2	176.6	164.6	154.2
142.5°	238.1	237.7	234.0	227.4	218.9	208.6	197.5	186.1	175.1	164.6	154.9
145°	222.8	222.0	219.2	214.4	207.7	199.6	190.9	181.6	173.0	164.0	155.6
147.5°	210.0	209.5	207.6	203.7	198.2	192.3	185.5	178.2	170.9	163.0	155.8
150°	202.4	202.1	200.4	197.0	192.8	187.8	182.0	175.8	169.1	162.3	155.6
152.5°	195.9	195.8	194.6	191.7	188.4	184.0	179.0	173.3	167.5	161.2	155.2
155°	187.3	187.8	186.7	184.7	181.6	178.6	174.4	169.9	164.6	159.2	154.5
157.5°	179.9	179.9	179.4	177.8	175.6	173.2	169.7	166.0	161.8	157.2	153.2
160°	175.2	175.2	174.9	173.6	171.6	169.6	166.5	163.4	159.8	155.9	152.6
162.5°	170.7	171.0	170.7	169.8	167.8	166.3	163.7	161.0	158.0	154.8	151.9
165°	164.3	164.6	164.6	163.4	162.3	161.2	159.2	157.3	155.0	152.6	150.6
167.5°	158.4	158.7	158.8	158.1	157.6	156.6	155.3	153.8	152.2	150.6	149.3
170°	154.8	155.3	155.6	154.8	154.5	153.9	152.8	152.0	150.6	149.5	148.6
172.5°	151.9	152.2	152.5	152.1	151.8	151.5	150.6	150.0	149.0	148.1	147.7
175°	148.1	148.6	148.9	148.6	148.6	148.4	148.1	147.8	146.9	146.6	146.4
177.5°	145.8	146.2	146.5	146.5	146.5	146.5	146.2	146.2	145.8	145.5	145.8
180°	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5



TEST NUMBER: P331647-927

CATALOG NUMBER: S122RDIP-S485D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	871.7	869.9	868.2	864.0	861.8	857.1	856.3	856.1	850.0	844.1	842.4
5°	901.7	897.0	889.9	881.5	873.0	864.1	858.2	853.5	841.6	830.4	823.9
7.5°	931.8	921.7	909.4	893.7	880.7	866.0	855.2	845.3	828.5	812.5	801.6
10°	954.3	937.8	921.5	899.9	883.0	866.5	851.1	837.8	818.9	797.6	782.4
12.5°	968.3	950.1	927.6	906.6	884.7	863.6	843.0	825.9	803.7	781.7	763.7
15°	987.2	967.7	940.5	910.3	882.2	854.7	831.0	809.7	780.7	754.4	732.5
17.5°	1002.7	975.7	946.5	911.6	879.1	844.1	813.7	786.4	754.2	722.4	696.6
20°	1007.6	981.0	947.2	912.4	873.9	832.7	799.9	770.3	735.7	701.1	671.5
22.5°	1004.5	983.8	946.3	904.5	865.1	822.1	785.1	750.7	712.3	677.0	642.7
25°	983.7	976.5	941.0	895.5	850.5	800.5	757.6	720.0	676.3	638.4	601.1
27.5°	934.9	950.3	928.3	879.7	829.7	776.1	727.9	685.2	639.7	597.1	559.9
30°	888.1	923.3	913.8	868.9	812.9	760.3	706.2	661.5	613.0	569.2	532.5
32.5°	823.9	882.1	891.4	853.7	795.9	738.0	681.3	636.8	586.2	540.0	504.3
35°	721.8	808.8	848.7	824.7	766.8	704.4	645.8	594.1	543.1	497.6	462.1
37.5°	600.0	718.4	785.1	786.7	733.5	668.6	604.8	553.4	501.3	456.6	418.2
40°	520.9	649.4	736.0	755.3	710.3	640.2	575.7	523.3	472.5	428.6	384.6
42.5°	450.0	577.9	684.4	717.9	682.1	612.5	547.8	493.1	443.5	402.1	357.1
45°	363.8	475.7	593.1	652.9	633.1	568.5	500.3	448.2	401.7	365.9	322.7
47.5°	307.0	385.8	499.4	580.3	579.9	521.0	453.8	403.9	360.8	327.3	292.3
50°	274.5	343.2	439.3	531.0	538.7	489.3	425.4	376.0	335.8	300.6	272.4
52.5°	245.4	302.0	388.4	476.3	498.2	455.4	393.5	347.8	308.8	276.4	252.3
55°	207.4	251.1	316.9	399.1	432.2	402.0	347.0	304.4	272.7	245.6	224.8
57.5°	175.4	208.3	260.9	327.2	365.8	346.7	301.4	266.8	239.7	215.1	198.8
60°	155.3	182.2	226.9	282.3	324.8	311.5	272.7	240.5	217.5	196.1	180.8
62.5°	136.4	159.5	197.8	242.7	281.8	276.2	244.6	217.5	197.3	177.9	164.9
65°	109.7	126.6	156.5	191.7	223.1	225.7	203.0	184.6	166.5	151.1	139.7
67.5°	87.4	98.4	119.5	149.1	172.6	181.0	167.1	153.0	138.7	126.8	116.8
70°	73.7	82.5	97.9	121.9	143.5	152.3	144.3	133.4	121.0	111.2	102.7
72.5°	59.7	68.4	79.7	97.3	115.8	125.4	122.6	114.7	104.6	96.6	88.5
75°	45.0	47.6	55.3	67.2	81.7	89.9	92.0	87.9	79.9	73.7	68.9
77.5°	33.3	34.9	38.5	44.8	54.2	61.6	64.6	64.2	58.6	55.1	50.6
80°	26.6	27.5	29.3	31.9	39.1	46.4	48.5	48.5	44.7	43.2	38.7
82.5°	20.2	20.9	21.9	23.4	26.8	33.2	35.5	36.0	33.5	31.6	28.1
85°	11.6	11.2	11.8	12.8	13.3	15.1	18.6	19.3	18.6	16.2	15.4
87.5°	5.5	5.4	5.1	4.7	4.8	4.9	5.9	6.9	6.2	5.6	5.3
90°	7.5	5.6	4.2	3.3	2.8	2.2	1.1	0.3	1.1	2.2	2.8
92.5°	28.0	19.0	12.7	10.1	8.2	7.0	4.9	3.4	4.9	7.0	8.2
95°	64.6	40.3	27.4	20.7	16.2	13.7	10.9	9.8	10.9	13.7	16.2
97.5°	87.1	53.2	37.0	29.4	24.2	20.4	17.4	15.9	17.4	20.4	24.2
100°	91.8	57.7	42.9	35.0	29.4	24.9	22.4	21.5	22.4	24.9	29.4
102.5°	92.1	61.7	48.0	40.2	34.3	29.9	27.3	26.7	27.3	29.9	34.3
105°	93.5	68.6	55.5	47.6	41.4	37.2	35.3	34.1	35.3	37.2	41.4
107.5°	97.4	75.7	62.9	55.0	48.9	45.0	43.1	42.2	43.1	45.0	48.9
110°	100.4	80.3	68.0	59.9	54.0	50.4	48.7	47.6	48.7	50.4	54.0



TEST NUMBER: P331647-927

CATALOG NUMBER: S122RDIP-S485D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	103.9	84.8	73.0	64.6	58.9	55.5	53.6	52.5	53.6	55.5	58.9
115°	108.8	91.8	79.8	72.2	66.6	63.3	61.6	60.2	61.6	63.3	66.6
117.5°	114.2	98.2	87.1	79.3	73.9	70.9	69.2	68.1	69.2	70.9	73.9
120°	117.9	102.7	91.8	84.0	78.3	75.9	74.1	73.0	74.1	75.9	78.3
122.5°	121.0	106.9	96.7	88.6	83.1	80.3	78.7	77.8	78.7	80.3	83.1
125°	126.0	113.4	103.3	95.5	89.8	86.5	84.8	84.0	84.8	86.5	89.8
127.5°	130.6	119.3	109.5	101.4	96.1	92.4	90.0	88.9	90.0	92.4	96.1
130°	133.5	122.9	113.0	105.3	99.7	95.7	92.9	91.8	92.9	95.7	99.7
132.5°	136.4	126.0	116.7	108.8	103.0	98.9	95.9	94.5	95.9	98.9	103.0
135°	140.2	130.5	121.4	113.7	107.2	103.0	99.7	98.5	99.7	103.0	107.2
137.5°	143.1	134.0	125.2	117.9	111.5	107.0	103.7	102.3	103.7	107.0	111.5
140°	144.7	136.0	127.6	120.3	114.2	109.7	106.4	105.3	106.4	109.7	114.2
142.5°	146.1	137.6	129.4	122.6	116.7	112.2	109.1	108.1	109.1	112.2	116.7
145°	147.8	140.0	132.4	126.3	120.6	116.5	113.7	112.5	113.7	116.5	120.6
147.5°	148.8	141.9	134.8	129.3	124.6	120.7	118.0	117.2	118.0	120.7	124.6
150°	149.2	142.8	136.3	131.3	127.1	123.4	121.2	120.3	121.2	123.4	127.1
152.5°	149.4	143.6	137.8	133.3	129.3	126.1	123.9	123.5	123.9	126.1	129.3
155°	149.7	145.0	140.2	136.0	132.9	129.8	128.2	127.9	128.2	129.8	132.9
157.5°	149.7	145.9	141.9	138.4	135.9	133.2	131.9	131.6	131.9	133.2	135.9
160°	149.7	146.4	143.1	140.0	137.7	135.5	134.4	134.0	134.4	135.5	137.7
162.5°	149.5	146.6	143.7	141.3	139.3	137.5	136.3	136.6	136.3	137.5	139.3
165°	148.9	146.9	144.4	142.8	141.3	139.7	139.1	139.4	139.1	139.7	141.3
167.5°	148.5	146.9	145.0	144.0	143.0	141.9	141.4	141.7	141.4	141.9	143.0
170°	148.1	146.6	145.3	144.4	143.9	143.1	142.8	143.3	142.8	143.1	143.9
172.5°	147.4	146.5	145.5	144.9	144.6	143.7	143.9	144.2	143.9	143.7	144.6
175°	146.6	146.1	145.5	145.3	145.3	144.7	145.0	145.3	145.0	144.7	145.3
177.5°	146.2	145.8	145.5	145.5	145.5	145.1	145.3	145.8	145.3	145.1	145.5
180°	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5



TEST NUMBER: P331647-927

CATALOG NUMBER: S122RDIP-S485D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	839.3	837.7	834.6	829.9	827.0	822.0	818.7	820.6	821.1	820.6	820.1
5°	816.8	810.6	802.0	793.7	786.0	777.8	773.0	771.0	766.8	764.5	763.3
7.5°	789.5	778.8	766.7	752.3	740.0	727.1	720.6	717.3	708.8	704.3	700.2
10°	769.1	752.3	740.1	721.2	709.7	692.8	681.3	681.6	670.0	663.5	658.8
12.5°	746.7	728.2	708.0	690.9	674.9	661.4	647.5	641.8	629.5	623.3	610.5
15°	709.4	687.8	666.5	643.4	627.2	606.2	586.1	561.5	541.7	524.5	519.8
17.5°	668.7	642.0	620.6	593.5	565.6	530.3	507.0	492.7	480.8	471.7	465.0
20°	640.8	613.5	590.8	549.9	512.4	488.4	471.3	460.3	447.9	438.2	432.8
22.5°	611.4	583.0	552.0	506.4	477.1	457.9	442.6	430.0	421.6	414.0	409.2
25°	569.7	538.7	487.5	456.1	432.5	412.4	401.7	394.0	385.2	374.8	370.1
27.5°	525.8	476.3	439.6	416.3	393.7	380.6	371.1	359.6	351.6	347.0	342.1
30°	492.8	443.5	414.8	389.3	373.4	358.9	347.6	341.1	333.4	325.4	322.2
32.5°	456.1	416.7	389.2	368.0	351.8	339.5	330.6	320.0	314.5	309.6	302.8
35°	410.6	380.7	355.6	338.4	323.1	313.0	302.6	296.4	286.4	282.3	279.6
37.5°	372.0	346.1	327.3	309.3	297.1	286.0	279.6	269.7	265.4	259.6	254.0
40°	350.2	324.8	306.8	292.0	278.4	270.1	262.1	254.1	247.6	244.9	238.1
42.5°	328.0	307.3	289.2	273.1	264.0	255.2	245.1	239.2	232.4	228.1	223.9
45°	297.3	279.0	263.6	250.3	240.2	231.1	224.5	214.8	211.0	202.3	198.8
47.5°	270.3	253.3	238.6	225.9	216.1	210.2	200.7	193.0	186.9	181.6	177.1
50°	251.1	236.9	222.8	211.5	202.6	194.1	184.3	180.5	171.0	168.3	165.6
52.5°	233.6	220.1	207.2	196.1	187.3	179.0	170.3	165.3	158.9	156.2	154.3
55°	209.1	196.1	183.7	174.0	165.1	156.5	151.1	145.0	142.0	139.9	137.5
57.5°	184.5	172.9	163.3	153.4	144.5	137.7	131.5	127.8	124.7	122.0	119.1
60°	168.9	157.6	149.1	139.9	130.8	125.2	120.4	116.0	112.4	108.3	107.1
62.5°	152.3	142.5	134.7	125.7	117.7	112.6	108.1	103.9	99.7	93.6	92.0
65°	129.6	121.9	113.6	106.2	99.1	94.1	87.5	82.9	81.0	80.5	80.2
67.5°	109.0	101.7	94.6	87.1	80.6	75.9	72.6	71.9	70.7	70.3	69.5
70°	95.2	88.5	81.4	74.2	68.0	67.2	66.0	64.8	63.3	62.7	62.1
72.5°	82.9	75.9	68.8	63.1	60.4	59.3	58.1	57.0	56.0	55.4	55.1
75°	63.6	57.1	52.4	50.3	48.8	47.9	46.2	45.2	44.7	43.8	43.5
77.5°	45.8	42.1	39.9	38.7	37.1	36.1	35.2	34.2	33.6	33.4	33.0
80°	34.9	33.1	31.7	29.9	29.3	28.1	27.8	26.9	27.3	26.3	26.3
82.5°	27.1	24.9	23.6	22.8	22.2	21.2	20.9	20.5	20.6	20.0	20.0
85°	13.9	13.3	12.8	12.1	12.1	11.2	11.6	11.2	11.2	10.6	10.4
87.5°	5.1	5.1	4.9	5.3	5.6	5.5	5.4	5.1	5.0	5.1	4.9
90°	3.3	4.2	5.6	7.5	9.3	9.5	9.3	9.0	8.4	9.0	9.3
92.5°	10.1	12.7	19.0	28.0	35.9	36.4	30.7	24.4	20.9	18.6	16.9
95°	20.7	27.4	40.3	64.6	97.1	109.7	96.0	73.4	56.2	44.5	38.3
97.5°	29.4	37.0	53.2	87.1	141.1	187.3	196.5	171.1	140.0	109.7	89.5
100°	35.0	42.9	57.7	91.8	152.3	221.1	261.4	255.6	220.9	182.5	148.6
102.5°	40.2	48.0	61.7	92.1	148.0	222.2	285.6	310.9	303.0	275.0	239.1
105°	47.6	55.5	68.6	93.5	139.7	207.4	281.9	340.1	371.7	375.3	366.1
107.5°	55.0	62.9	75.7	97.4	135.5	191.5	257.3	319.0	366.7	395.8	409.3
110°	59.9	68.0	80.3	100.4	134.7	183.9	241.9	300.9	351.0	386.8	409.8



TEST NUMBER: P331647-927

CATALOG NUMBER: S122RDIP-S485D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	64.6	73.0	84.8	103.9	134.8	179.0	231.1	284.3	332.4	370.7	397.0
115°	72.2	79.8	91.8	108.8	136.0	173.6	217.8	264.0	307.0	343.7	372.6
117.5°	79.3	87.1	98.2	114.2	138.1	170.9	209.4	248.6	286.5	319.7	346.7
120°	84.0	91.8	102.7	117.9	139.4	169.4	204.9	241.0	275.7	305.4	330.8
122.5°	88.6	96.7	106.9	121.0	140.9	168.4	201.1	235.0	266.7	294.9	317.8
125°	95.5	103.3	113.4	126.0	143.3	166.8	195.7	226.2	255.0	279.6	300.6
127.5°	101.4	109.5	119.3	130.6	145.7	165.9	190.6	217.5	243.6	266.8	286.1
130°	105.3	113.0	122.9	133.5	147.5	165.4	187.3	211.9	236.0	258.1	276.6
132.5°	108.8	116.7	126.0	136.4	149.3	165.2	184.6	206.5	228.8	249.1	266.5
135°	113.7	121.4	130.5	140.2	151.5	164.9	180.8	199.0	217.5	236.0	251.6
137.5°	117.9	125.2	134.0	143.1	153.4	164.8	178.2	193.1	208.5	223.2	236.8
140°	120.3	127.6	136.0	144.7	154.2	164.6	176.6	189.2	202.6	215.6	227.8
142.5°	122.6	129.4	137.6	146.1	154.9	164.6	175.1	186.1	197.5	208.6	218.9
145°	126.3	132.4	140.0	147.8	155.6	164.0	173.0	181.6	190.9	199.6	207.7
147.5°	129.3	134.8	141.9	148.8	155.8	163.0	170.9	178.2	185.5	192.3	198.2
150°	131.3	136.3	142.8	149.2	155.6	162.3	169.1	175.8	182.0	187.8	192.8
152.5°	133.3	137.8	143.6	149.4	155.2	161.2	167.5	173.3	179.0	184.0	188.4
155°	136.0	140.2	145.0	149.7	154.5	159.2	164.6	169.9	174.4	178.6	181.6
157.5°	138.4	141.9	145.9	149.7	153.2	157.2	161.8	166.0	169.7	173.2	175.6
160°	140.0	143.1	146.4	149.7	152.6	155.9	159.8	163.4	166.5	169.6	171.6
162.5°	141.3	143.7	146.6	149.5	151.9	154.8	158.0	161.0	163.7	166.3	167.8
165°	142.8	144.4	146.9	148.9	150.6	152.6	155.0	157.3	159.2	161.2	162.3
167.5°	144.0	145.0	146.9	148.5	149.3	150.6	152.2	153.8	155.3	156.6	157.6
170°	144.4	145.3	146.6	148.1	148.6	149.5	150.6	152.0	152.8	153.9	154.5
172.5°	144.9	145.5	146.5	147.4	147.7	148.1	149.0	150.0	150.6	151.5	151.8
175°	145.3	145.5	146.1	146.6	146.4	146.6	146.9	147.8	148.1	148.4	148.6
177.5°	145.5	145.5	145.8	146.2	145.8	145.5	145.8	146.2	146.2	146.5	146.5
180°	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5



TEST NUMBER: P331647-927

CATALOG NUMBER: S122RDIP-S485D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	817.5	818.0	817.3	817.8	817.3	818.0	817.5	820.1	820.6	821.1	820.6
5°	761.8	758.2	757.6	756.8	757.6	758.2	761.8	763.3	764.5	766.8	771.0
7.5°	695.1	694.6	693.2	691.0	693.2	694.6	695.1	700.2	704.3	708.8	717.3
10°	652.3	650.9	650.5	648.5	650.5	650.9	652.3	658.8	663.5	670.0	681.6
12.5°	602.1	592.6	591.6	586.5	591.6	592.6	602.1	610.5	623.3	629.5	641.8
15°	512.7	510.9	505.0	501.1	505.0	510.9	512.7	519.8	524.5	541.7	561.5
17.5°	461.5	455.7	453.9	453.1	453.9	455.7	461.5	465.0	471.7	480.8	492.7
20°	428.6	423.3	422.5	421.8	422.5	423.3	428.6	432.8	438.2	447.9	460.3
22.5°	405.9	400.4	398.1	396.3	398.1	400.4	405.9	409.2	414.0	421.6	430.0
25°	367.1	365.0	363.8	363.3	363.8	365.0	367.1	370.1	374.8	385.2	394.0
27.5°	336.8	332.2	331.3	329.8	331.3	332.2	336.8	342.1	347.0	351.6	359.6
30°	319.5	318.0	315.9	314.2	315.9	318.0	319.5	322.2	325.4	333.4	341.1
32.5°	299.1	297.9	296.0	295.2	296.0	297.9	299.1	302.8	309.6	314.5	320.0
35°	276.6	272.4	270.7	268.0	270.7	272.4	276.6	279.6	282.3	286.4	296.4
37.5°	252.8	250.6	248.1	249.0	248.1	250.6	252.8	254.0	259.6	265.4	269.7
40°	234.3	232.8	232.2	232.0	232.2	232.8	234.3	238.1	244.9	247.6	254.1
42.5°	219.6	215.6	214.0	214.0	214.0	215.6	219.6	223.9	228.1	232.4	239.2
45°	197.3	193.5	190.8	191.1	190.8	193.5	197.3	198.8	202.3	211.0	214.8
47.5°	174.5	174.4	172.7	173.3	172.7	174.4	174.5	177.1	181.6	186.9	193.0
50°	163.6	161.8	160.7	160.9	160.7	161.8	163.6	165.6	168.3	171.0	180.5
52.5°	153.2	151.6	150.7	151.9	150.7	151.6	153.2	154.3	156.2	158.9	165.3
55°	136.1	134.3	134.0	133.7	134.0	134.3	136.1	137.5	139.9	142.0	145.0
57.5°	117.0	115.8	114.0	113.3	114.0	115.8	117.0	119.1	122.0	124.7	127.8
60°	103.2	100.8	97.9	97.6	97.9	100.8	103.2	107.1	108.3	112.4	116.0
62.5°	90.7	90.2	89.7	89.6	89.7	90.2	90.7	92.0	93.6	99.7	103.9
65°	79.6	79.3	79.6	79.9	79.6	79.3	79.6	80.2	80.5	81.0	82.9
67.5°	69.3	68.8	68.3	68.5	68.3	68.8	69.3	69.5	70.3	70.7	71.9
70°	61.6	61.2	60.9	60.9	60.9	61.2	61.6	62.1	62.7	63.3	64.8
72.5°	53.9	53.9	53.6	53.4	53.6	53.9	53.9	55.1	55.4	56.0	57.0
75°	43.2	42.6	42.6	42.6	42.6	42.6	43.2	43.5	43.8	44.7	45.2
77.5°	32.9	32.6	32.3	32.1	32.3	32.6	32.9	33.0	33.4	33.6	34.2
80°	26.1	25.7	25.4	25.4	25.4	25.7	26.1	26.3	26.3	27.3	26.9
82.5°	19.9	19.6	19.5	19.3	19.5	19.6	19.9	20.0	20.0	20.6	20.5
85°	10.6	10.9	10.6	11.2	10.6	10.9	10.6	10.4	10.6	11.2	11.2
87.5°	4.9	4.7	4.9	4.7	4.9	4.7	4.9	4.9	5.1	5.0	5.1
90°	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.0	8.4	9.0
92.5°	16.6	15.8	15.9	15.5	15.9	15.8	16.6	16.9	18.6	20.9	24.4
95°	34.7	32.5	31.6	31.9	31.6	32.5	34.7	38.3	44.5	56.2	73.4
97.5°	76.1	69.2	65.2	62.8	65.2	69.2	76.1	89.5	109.7	140.0	171.1
100°	125.4	113.4	105.3	100.2	105.3	113.4	125.4	148.6	182.5	220.9	255.6
102.5°	213.8	193.3	183.2	176.3	183.2	193.3	213.8	239.1	275.0	303.0	310.9
105°	348.7	331.4	319.3	315.4	319.3	331.4	348.7	366.1	375.3	371.7	340.1
107.5°	411.5	410.6	408.1	403.0	408.1	410.6	411.5	409.3	395.8	366.7	319.0
110°	421.8	427.1	429.7	429.4	429.7	427.1	421.8	409.8	386.8	351.0	300.9



TEST NUMBER: P331647-927

CATALOG NUMBER: S122RDIP-S485D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	413.8	422.6	427.4	428.9	427.4	422.6	413.8	397.0	370.7	332.4	284.3
115°	392.4	405.3	412.6	415.1	412.6	405.3	392.4	372.6	343.7	307.0	264.0
117.5°	367.0	380.6	388.2	390.4	388.2	380.6	367.0	346.7	319.7	286.5	248.6
120°	350.5	363.6	371.7	374.5	371.7	363.6	350.5	330.8	305.4	275.7	241.0
122.5°	335.4	348.4	355.6	357.9	355.6	348.4	335.4	317.8	294.9	266.7	235.0
125°	316.9	327.5	334.5	336.8	334.5	327.5	316.9	300.6	279.6	255.0	226.2
127.5°	300.3	310.3	316.3	318.1	316.3	310.3	300.3	286.1	266.8	243.6	217.5
130°	290.3	299.8	305.4	307.6	305.4	299.8	290.3	276.6	258.1	236.0	211.9
132.5°	280.0	289.5	294.6	296.7	294.6	289.5	280.0	266.5	249.1	228.8	206.5
135°	263.6	272.9	278.0	279.1	278.0	272.9	263.6	251.6	236.0	217.5	199.0
137.5°	247.8	255.7	260.2	261.8	260.2	255.7	247.8	236.8	223.2	208.5	193.1
140°	236.8	244.1	248.3	249.9	248.3	244.1	236.8	227.8	215.6	202.6	189.2
142.5°	227.4	234.0	237.7	238.1	237.7	234.0	227.4	218.9	208.6	197.5	186.1
145°	214.4	219.2	222.0	222.8	222.0	219.2	214.4	207.7	199.6	190.9	181.6
147.5°	203.7	207.6	209.5	210.0	209.5	207.6	203.7	198.2	192.3	185.5	178.2
150°	197.0	200.4	202.1	202.4	202.1	200.4	197.0	192.8	187.8	182.0	175.8
152.5°	191.7	194.6	195.8	195.9	195.8	194.6	191.7	188.4	184.0	179.0	173.3
155°	184.7	186.7	187.8	187.3	187.8	186.7	184.7	181.6	178.6	174.4	169.9
157.5°	177.8	179.4	179.9	179.9	179.9	179.4	177.8	175.6	173.2	169.7	166.0
160°	173.6	174.9	175.2	175.2	175.2	174.9	173.6	171.6	169.6	166.5	163.4
162.5°	169.8	170.7	171.0	170.7	171.0	170.7	169.8	167.8	166.3	163.7	161.0
165°	163.4	164.6	164.6	164.3	164.6	164.6	163.4	162.3	161.2	159.2	157.3
167.5°	158.1	158.8	158.7	158.4	158.7	158.8	158.1	157.6	156.6	155.3	153.8
170°	154.8	155.6	155.3	154.8	155.3	155.6	154.8	154.5	153.9	152.8	152.0
172.5°	152.1	152.5	152.2	151.9	152.2	152.5	152.1	151.8	151.5	150.6	150.0
175°	148.6	148.9	148.6	148.1	148.6	148.9	148.6	148.6	148.4	148.1	147.8
177.5°	146.5	146.5	146.2	145.8	146.2	146.5	146.5	146.5	146.5	146.2	146.2
180°	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5



TEST NUMBER: P331647-927

CATALOG NUMBER: S122RDIP-S485D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	818.7	822.0	827.0	829.9	834.6	837.7	839.3	842.4	844.1	850.0	856.1
5°	773.0	777.8	786.0	793.7	802.0	810.6	816.8	823.9	830.4	841.6	853.5
7.5°	720.6	727.1	740.0	752.3	766.7	778.8	789.5	801.6	812.5	828.5	845.3
10°	681.3	692.8	709.7	721.2	740.1	752.3	769.1	782.4	797.6	818.9	837.8
12.5°	647.5	661.4	674.9	690.9	708.0	728.2	746.7	763.7	781.7	803.7	825.9
15°	586.1	606.2	627.2	643.4	666.5	687.8	709.4	732.5	754.4	780.7	809.7
17.5°	507.0	530.3	565.6	593.5	620.6	642.0	668.7	696.6	722.4	754.2	786.4
20°	471.3	488.4	512.4	549.9	590.8	613.5	640.8	671.5	701.1	735.7	770.3
22.5°	442.6	457.9	477.1	506.4	552.0	583.0	611.4	642.7	677.0	712.3	750.7
25°	401.7	412.4	432.5	456.1	487.5	538.7	569.7	601.1	638.4	676.3	720.0
27.5°	371.1	380.6	393.7	416.3	439.6	476.3	525.8	559.9	597.1	639.7	685.2
30°	347.6	358.9	373.4	389.3	414.8	443.5	492.8	532.5	569.2	613.0	661.5
32.5°	330.6	339.5	351.8	368.0	389.2	416.7	456.1	504.3	540.0	586.2	636.8
35°	302.6	313.0	323.1	338.4	355.6	380.7	410.6	462.1	497.6	543.1	594.1
37.5°	279.6	286.0	297.1	309.3	327.3	346.1	372.0	418.2	456.6	501.3	553.4
40°	262.1	270.1	278.4	292.0	306.8	324.8	350.2	384.6	428.6	472.5	523.3
42.5°	245.1	255.2	264.0	273.1	289.2	307.3	328.0	357.1	402.1	443.5	493.1
45°	224.5	231.1	240.2	250.3	263.6	279.0	297.3	322.7	365.9	401.7	448.2
47.5°	200.7	210.2	216.1	225.9	238.6	253.3	270.3	292.3	327.3	360.8	403.9
50°	184.3	194.1	202.6	211.5	222.8	236.9	251.1	272.4	300.6	335.8	376.0
52.5°	170.3	179.0	187.3	196.1	207.2	220.1	233.6	252.3	276.4	308.8	347.8
55°	151.1	156.5	165.1	174.0	183.7	196.1	209.1	224.8	245.6	272.7	304.4
57.5°	131.5	137.7	144.5	153.4	163.3	172.9	184.5	198.8	215.1	239.7	266.8
60°	120.4	125.2	130.8	139.9	149.1	157.6	168.9	180.8	196.1	217.5	240.5
62.5°	108.1	112.6	117.7	125.7	134.7	142.5	152.3	164.9	177.9	197.3	217.5
65°	87.5	94.1	99.1	106.2	113.6	121.9	129.6	139.7	151.1	166.5	184.6
67.5°	72.6	75.9	80.6	87.1	94.6	101.7	109.0	116.8	126.8	138.7	153.0
70°	66.0	67.2	68.0	74.2	81.4	88.5	95.2	102.7	111.2	121.0	133.4
72.5°	58.1	59.3	60.4	63.1	68.8	75.9	82.9	88.5	96.6	104.6	114.7
75°	46.2	47.9	48.8	50.3	52.4	57.1	63.6	68.9	73.7	79.9	87.9
77.5°	35.2	36.1	37.1	38.7	39.9	42.1	45.8	50.6	55.1	58.6	64.2
80°	27.8	28.1	29.3	29.9	31.7	33.1	34.9	38.7	43.2	44.7	48.5
82.5°	20.9	21.2	22.2	22.8	23.6	24.9	27.1	28.1	31.6	33.5	36.0
85°	11.6	11.2	12.1	12.1	12.8	13.3	13.9	15.4	16.2	18.6	19.3
87.5°	5.4	5.5	5.6	5.3	4.9	5.1	5.1	5.3	5.6	6.2	6.9
90°	9.3	9.5	9.3	7.5	5.6	4.2	3.3	2.8	2.2	1.1	0.3
92.5°	30.7	36.4	35.9	28.0	19.0	12.7	10.1	8.2	7.0	4.9	3.4
95°	96.0	109.7	97.1	64.6	40.3	27.4	20.7	16.2	13.7	10.9	9.8
97.5°	196.5	187.3	141.1	87.1	53.2	37.0	29.4	24.2	20.4	17.4	15.9
100°	261.4	221.1	152.3	91.8	57.7	42.9	35.0	29.4	24.9	22.4	21.5
102.5°	285.6	222.2	148.0	92.1	61.7	48.0	40.2	34.3	29.9	27.3	26.7
105°	281.9	207.4	139.7	93.5	68.6	55.5	47.6	41.4	37.2	35.3	34.1
107.5°	257.3	191.5	135.5	97.4	75.7	62.9	55.0	48.9	45.0	43.1	42.2
110°	241.9	183.9	134.7	100.4	80.3	68.0	59.9	54.0	50.4	48.7	47.6



TEST NUMBER: P331647-927

CATALOG NUMBER: S122RDIP-S485D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	231.1	179.0	134.8	103.9	84.8	73.0	64.6	58.9	55.5	53.6	52.5
115°	217.8	173.6	136.0	108.8	91.8	79.8	72.2	66.6	63.3	61.6	60.2
117.5°	209.4	170.9	138.1	114.2	98.2	87.1	79.3	73.9	70.9	69.2	68.1
120°	204.9	169.4	139.4	117.9	102.7	91.8	84.0	78.3	75.9	74.1	73.0
122.5°	201.1	168.4	140.9	121.0	106.9	96.7	88.6	83.1	80.3	78.7	77.8
125°	195.7	166.8	143.3	126.0	113.4	103.3	95.5	89.8	86.5	84.8	84.0
127.5°	190.6	165.9	145.7	130.6	119.3	109.5	101.4	96.1	92.4	90.0	88.9
130°	187.3	165.4	147.5	133.5	122.9	113.0	105.3	99.7	95.7	92.9	91.8
132.5°	184.6	165.2	149.3	136.4	126.0	116.7	108.8	103.0	98.9	95.9	94.5
135°	180.8	164.9	151.5	140.2	130.5	121.4	113.7	107.2	103.0	99.7	98.5
137.5°	178.2	164.8	153.4	143.1	134.0	125.2	117.9	111.5	107.0	103.7	102.3
140°	176.6	164.6	154.2	144.7	136.0	127.6	120.3	114.2	109.7	106.4	105.3
142.5°	175.1	164.6	154.9	146.1	137.6	129.4	122.6	116.7	112.2	109.1	108.1
145°	173.0	164.0	155.6	147.8	140.0	132.4	126.3	120.6	116.5	113.7	112.5
147.5°	170.9	163.0	155.8	148.8	141.9	134.8	129.3	124.6	120.7	118.0	117.2
150°	169.1	162.3	155.6	149.2	142.8	136.3	131.3	127.1	123.4	121.2	120.3
152.5°	167.5	161.2	155.2	149.4	143.6	137.8	133.3	129.3	126.1	123.9	123.5
155°	164.6	159.2	154.5	149.7	145.0	140.2	136.0	132.9	129.8	128.2	127.9
157.5°	161.8	157.2	153.2	149.7	145.9	141.9	138.4	135.9	133.2	131.9	131.6
160°	159.8	155.9	152.6	149.7	146.4	143.1	140.0	137.7	135.5	134.4	134.0
162.5°	158.0	154.8	151.9	149.5	146.6	143.7	141.3	139.3	137.5	136.3	136.6
165°	155.0	152.6	150.6	148.9	146.9	144.4	142.8	141.3	139.7	139.1	139.4
167.5°	152.2	150.6	149.3	148.5	146.9	145.0	144.0	143.0	141.9	141.4	141.7
170°	150.6	149.5	148.6	148.1	146.6	145.3	144.4	143.9	143.1	142.8	143.3
172.5°	149.0	148.1	147.7	147.4	146.5	145.5	144.9	144.6	143.7	143.9	144.2
175°	146.9	146.6	146.4	146.6	146.1	145.5	145.3	145.3	144.7	145.0	145.3
177.5°	145.8	145.5	145.8	146.2	145.8	145.5	145.5	145.5	145.1	145.3	145.8
180°	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5



TEST NUMBER: P331647-927

CATALOG NUMBER: S122RDIP-S485D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	856.3	857.1	861.8	864.0	868.2	869.9	871.7	871.2	871.2	872.2	878.8
5°	858.2	864.1	873.0	881.5	889.9	897.0	901.7	906.4	908.2	916.8	924.5
7.5°	855.2	866.0	880.7	893.7	909.4	921.7	931.8	941.0	947.3	959.8	972.6
10°	851.1	866.5	883.0	899.9	921.5	937.8	954.3	967.1	971.2	989.8	1000.5
12.5°	843.0	863.6	884.7	906.6	927.6	950.1	968.3	981.0	995.6	1012.3	1032.0
15°	831.0	854.7	882.2	910.3	940.5	967.7	987.2	1009.4	1025.3	1043.7	1060.8
17.5°	813.7	844.1	879.1	911.6	946.5	975.7	1002.7	1023.9	1035.1	1045.6	1048.2
20°	799.9	832.7	873.9	912.4	947.2	981.0	1007.6	1025.3	1028.3	1028.6	1012.9
22.5°	785.1	822.1	865.1	904.5	946.3	983.8	1004.5	1012.1	1000.4	980.3	950.0
25°	757.6	800.5	850.5	895.5	941.0	976.5	983.7	970.3	929.2	886.0	831.3
27.5°	727.9	776.1	829.7	879.7	928.3	950.3	934.9	886.9	812.9	748.5	670.5
30°	706.2	760.3	812.9	868.9	913.8	923.3	888.1	817.4	731.0	634.0	556.2
32.5°	681.3	738.0	795.9	853.7	891.4	882.1	823.9	736.9	635.6	540.3	466.7
35°	645.8	704.4	766.8	824.7	848.7	808.8	721.8	608.6	505.0	416.0	365.4
37.5°	604.8	668.6	733.5	786.7	785.1	718.4	600.0	483.0	396.0	343.3	307.3
40°	575.7	640.2	710.3	755.3	736.0	649.4	520.9	410.6	347.0	305.0	278.7
42.5°	547.8	612.5	682.1	717.9	684.4	577.9	450.0	363.5	311.0	278.3	256.9
45°	500.3	568.5	633.1	652.9	593.1	475.7	363.8	301.2	266.3	242.0	227.2
47.5°	453.8	521.0	579.9	580.3	499.4	385.8	307.0	260.6	230.8	212.1	201.3
50°	425.4	489.3	538.7	531.0	439.3	343.2	274.5	234.6	209.8	195.3	184.0
52.5°	393.5	455.4	498.2	476.3	388.4	302.0	245.4	211.9	191.3	178.7	168.7
55°	347.0	402.0	432.2	399.1	316.9	251.1	207.4	181.0	165.6	155.0	146.5
57.5°	301.4	346.7	365.8	327.2	260.9	208.3	175.4	155.7	140.4	132.8	128.3
60°	272.7	311.5	324.8	282.3	226.9	182.2	155.3	137.0	125.7	120.7	116.3
62.5°	244.6	276.2	281.8	242.7	197.8	159.5	136.4	120.9	113.4	108.6	104.4
65°	203.0	225.7	223.1	191.7	156.5	126.6	109.7	100.3	94.7	87.9	80.5
67.5°	167.1	181.0	172.6	149.1	119.5	98.4	87.4	80.2	73.3	66.8	65.1
70°	144.3	152.3	143.5	121.9	97.9	82.5	73.7	65.1	60.9	59.5	56.8
72.5°	122.6	125.4	115.8	97.3	79.7	68.4	59.7	54.9	52.7	51.4	49.7
75°	92.0	89.9	81.7	67.2	55.3	47.6	45.0	43.2	41.7	40.6	39.6
77.5°	64.6	61.6	54.2	44.8	38.5	34.9	33.3	32.3	31.6	31.0	30.1
80°	48.5	46.4	39.1	31.9	29.3	27.5	26.6	25.4	25.4	24.9	23.9
82.5°	35.5	33.2	26.8	23.4	21.9	20.9	20.2	19.5	19.3	19.4	18.8
85°	18.6	15.1	13.3	12.8	11.8	11.2	11.6	10.9	10.9	10.9	10.6
87.5°	5.9	4.9	4.8	4.7	5.1	5.4	5.5	5.9	6.2	5.9	6.0
90°	1.1	2.2	2.8	3.3	4.2	5.6	7.5	9.3	9.5	9.3	9.0
92.5°	4.9	7.0	8.2	10.1	12.7	19.0	28.0	35.9	36.4	30.7	24.4
95°	10.9	13.7	16.2	20.7	27.4	40.3	64.6	97.1	109.7	96.0	73.4
97.5°	17.4	20.4	24.2	29.4	37.0	53.2	87.1	141.1	187.3	196.5	171.1
100°	22.4	24.9	29.4	35.0	42.9	57.7	91.8	152.3	221.1	261.4	255.6
102.5°	27.3	29.9	34.3	40.2	48.0	61.7	92.1	148.0	222.2	285.6	310.9
105°	35.3	37.2	41.4	47.6	55.5	68.6	93.5	139.7	207.4	281.9	340.1
107.5°	43.1	45.0	48.9	55.0	62.9	75.7	97.4	135.5	191.5	257.3	319.0
110°	48.7	50.4	54.0	59.9	68.0	80.3	100.4	134.7	183.9	241.9	300.9



TEST NUMBER: P331647-927

CATALOG NUMBER: S122RDIP-S485D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	53.6	55.5	58.9	64.6	73.0	84.8	103.9	134.8	179.0	231.1	284.3
115°	61.6	63.3	66.6	72.2	79.8	91.8	108.8	136.0	173.6	217.8	264.0
117.5°	69.2	70.9	73.9	79.3	87.1	98.2	114.2	138.1	170.9	209.4	248.6
120°	74.1	75.9	78.3	84.0	91.8	102.7	117.9	139.4	169.4	204.9	241.0
122.5°	78.7	80.3	83.1	88.6	96.7	106.9	121.0	140.9	168.4	201.1	235.0
125°	84.8	86.5	89.8	95.5	103.3	113.4	126.0	143.3	166.8	195.7	226.2
127.5°	90.0	92.4	96.1	101.4	109.5	119.3	130.6	145.7	165.9	190.6	217.5
130°	92.9	95.7	99.7	105.3	113.0	122.9	133.5	147.5	165.4	187.3	211.9
132.5°	95.9	98.9	103.0	108.8	116.7	126.0	136.4	149.3	165.2	184.6	206.5
135°	99.7	103.0	107.2	113.7	121.4	130.5	140.2	151.5	164.9	180.8	199.0
137.5°	103.7	107.0	111.5	117.9	125.2	134.0	143.1	153.4	164.8	178.2	193.1
140°	106.4	109.7	114.2	120.3	127.6	136.0	144.7	154.2	164.6	176.6	189.2
142.5°	109.1	112.2	116.7	122.6	129.4	137.6	146.1	154.9	164.6	175.1	186.1
145°	113.7	116.5	120.6	126.3	132.4	140.0	147.8	155.6	164.0	173.0	181.6
147.5°	118.0	120.7	124.6	129.3	134.8	141.9	148.8	155.8	163.0	170.9	178.2
150°	121.2	123.4	127.1	131.3	136.3	142.8	149.2	155.6	162.3	169.1	175.8
152.5°	123.9	126.1	129.3	133.3	137.8	143.6	149.4	155.2	161.2	167.5	173.3
155°	128.2	129.8	132.9	136.0	140.2	145.0	149.7	154.5	159.2	164.6	169.9
157.5°	131.9	133.2	135.9	138.4	141.9	145.9	149.7	153.2	157.2	161.8	166.0
160°	134.4	135.5	137.7	140.0	143.1	146.4	149.7	152.6	155.9	159.8	163.4
162.5°	136.3	137.5	139.3	141.3	143.7	146.6	149.5	151.9	154.8	158.0	161.0
165°	139.1	139.7	141.3	142.8	144.4	146.9	148.9	150.6	152.6	155.0	157.3
167.5°	141.4	141.9	143.0	144.0	145.0	146.9	148.5	149.3	150.6	152.2	153.8
170°	142.8	143.1	143.9	144.4	145.3	146.6	148.1	148.6	149.5	150.6	152.0
172.5°	143.9	143.7	144.6	144.9	145.5	146.5	147.4	147.7	148.1	149.0	150.0
175°	145.0	144.7	145.3	145.3	145.5	146.1	146.6	146.4	146.6	146.9	147.8
177.5°	145.3	145.1	145.5	145.5	145.5	145.8	146.2	145.8	145.5	145.8	146.2
180°	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5



TEST NUMBER: P331647-927

CATALOG NUMBER: S122RDIP-S485D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	881.2	884.3	885.7	885.7	887.4	886.7	886.0
5°	931.8	937.5	938.7	944.0	947.8	946.7	947.2
7.5°	982.2	991.3	1000.2	1004.2	1005.0	1007.3	1008.2
10°	1013.2	1020.6	1034.5	1032.5	1042.8	1048.7	1038.9
12.5°	1043.1	1053.0	1062.7	1065.3	1071.2	1073.1	1069.2
15°	1070.0	1075.3	1075.9	1074.4	1076.3	1074.8	1069.1
17.5°	1044.8	1036.2	1018.7	1010.3	1003.8	994.1	990.2
20°	1003.1	977.7	948.2	936.3	922.4	895.2	901.7
22.5°	913.2	884.2	854.7	820.1	803.6	777.8	776.3
25°	773.3	723.3	668.3	629.8	607.4	581.6	570.4
27.5°	601.3	538.3	493.2	470.4	449.6	429.2	428.3
30°	488.1	440.8	405.9	386.3	373.7	365.0	366.9
32.5°	411.5	379.0	355.5	339.3	329.9	323.4	323.3
35°	336.4	314.2	299.0	292.3	285.5	280.7	281.1
37.5°	287.9	274.5	266.1	258.6	254.4	252.1	250.7
40°	263.0	252.1	245.6	241.1	237.6	234.3	233.7
42.5°	243.4	234.3	227.8	224.3	221.0	218.6	218.1
45°	215.9	208.6	202.6	198.8	197.3	195.3	195.3
47.5°	192.1	184.8	180.2	177.8	175.2	173.9	173.8
50°	176.0	170.4	166.3	164.8	162.7	161.8	161.5
52.5°	161.6	157.4	154.4	153.4	152.5	151.4	151.5
55°	142.0	139.7	138.5	137.5	136.1	134.3	135.5
57.5°	125.5	123.5	120.3	117.5	116.1	114.9	115.3
60°	113.9	109.7	105.6	102.3	101.5	98.8	98.8
62.5°	99.3	93.4	88.3	86.5	85.6	84.4	84.1
65°	76.3	74.0	72.8	71.6	71.0	71.0	70.4
67.5°	63.2	62.3	61.0	60.7	60.1	60.0	59.7
70°	55.9	54.7	54.1	53.9	53.2	53.6	52.7
72.5°	48.8	47.8	47.8	47.0	46.7	46.7	46.0
75°	38.4	38.4	38.2	37.9	37.3	37.0	37.3
77.5°	29.5	29.6	29.1	29.1	29.0	29.1	28.8
80°	23.7	23.9	23.7	23.4	23.1	23.4	23.1
82.5°	18.7	18.3	18.2	18.1	18.1	17.9	17.9
85°	10.6	10.9	10.6	10.4	10.4	10.4	10.6
87.5°	5.7	5.8	5.9	5.9	5.9	5.9	5.6
90°	8.4	9.0	9.3	9.3	9.3	9.3	9.3
92.5°	20.9	18.6	16.9	16.6	15.8	15.9	15.5
95°	56.2	44.5	38.3	34.7	32.5	31.6	31.9
97.5°	140.0	109.7	89.5	76.1	69.2	65.2	62.8
100°	220.9	182.5	148.6	125.4	113.4	105.3	100.2
102.5°	303.0	275.0	239.1	213.8	193.3	183.2	176.3
105°	371.7	375.3	366.1	348.7	331.4	319.3	315.4
107.5°	366.7	395.8	409.3	411.5	410.6	408.1	403.0
110°	351.0	386.8	409.8	421.8	427.1	429.7	429.4



TEST NUMBER: P331647-927

CATALOG NUMBER: S122RDIP-S485D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	332.4	370.7	397.0	413.8	422.6	427.4	428.9
115°	307.0	343.7	372.6	392.4	405.3	412.6	415.1
117.5°	286.5	319.7	346.7	367.0	380.6	388.2	390.4
120°	275.7	305.4	330.8	350.5	363.6	371.7	374.5
122.5°	266.7	294.9	317.8	335.4	348.4	355.6	357.9
125°	255.0	279.6	300.6	316.9	327.5	334.5	336.8
127.5°	243.6	266.8	286.1	300.3	310.3	316.3	318.1
130°	236.0	258.1	276.6	290.3	299.8	305.4	307.6
132.5°	228.8	249.1	266.5	280.0	289.5	294.6	296.7
135°	217.5	236.0	251.6	263.6	272.9	278.0	279.1
137.5°	208.5	223.2	236.8	247.8	255.7	260.2	261.8
140°	202.6	215.6	227.8	236.8	244.1	248.3	249.9
142.5°	197.5	208.6	218.9	227.4	234.0	237.7	238.1
145°	190.9	199.6	207.7	214.4	219.2	222.0	222.8
147.5°	185.5	192.3	198.2	203.7	207.6	209.5	210.0
150°	182.0	187.8	192.8	197.0	200.4	202.1	202.4
152.5°	179.0	184.0	188.4	191.7	194.6	195.8	195.9
155°	174.4	178.6	181.6	184.7	186.7	187.8	187.3
157.5°	169.7	173.2	175.6	177.8	179.4	179.9	179.9
160°	166.5	169.6	171.6	173.6	174.9	175.2	175.2
162.5°	163.7	166.3	167.8	169.8	170.7	171.0	170.7
165°	159.2	161.2	162.3	163.4	164.6	164.6	164.3
167.5°	155.3	156.6	157.6	158.1	158.8	158.7	158.4
170°	152.8	153.9	154.5	154.8	155.6	155.3	154.8
172.5°	150.6	151.5	151.8	152.1	152.5	152.2	151.9
175°	148.1	148.4	148.6	148.6	148.9	148.6	148.1
177.5°	146.2	146.5	146.5	146.5	146.5	146.2	145.8
180°	145.5	145.5	145.5	145.5	145.5	145.5	145.5

(END OF REPORT)