

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331689-927

Luminaire Tested: **S122RDIP-S675D725U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331689-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S675D725U927-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4254.9 lumens
Efficiency: N/A
Efficacy: 92.7 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331689-927

CATALOG NUMBER: S122RDIP-S675D725U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331689-927

CATALOG NUMBER: S122RDIP-S675D725U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47
1	98	94	90	87	90	87	83	81	73	71	69	60	59	57	49	48	47	41
2	90	83	77	72	82	77	72	67	65	61	58	54	51	49	44	42	41	36
3	82	74	67	61	76	68	62	57	58	53	50	48	45	42	39	37	35	31
4	76	66	58	53	70	61	54	49	52	47	43	44	40	37	36	33	31	28
5	70	59	51	46	64	55	48	43	47	42	38	40	36	33	33	30	28	25
6	65	53	46	40	60	50	43	38	43	37	33	36	32	29	30	27	25	22
7	60	48	41	35	55	45	38	34	39	34	30	33	29	26	28	25	23	20
8	56	44	37	32	52	41	35	30	36	31	27	31	27	24	26	23	21	18
9	52	41	33	29	48	38	31	27	33	28	24	28	24	22	24	21	19	17
10	49	37	30	26	45	35	29	25	31	26	22	26	22	20	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	18791	18791	18791	18791
5°	20985	18908	16765	18908
10°	23282	18775	14532	18775
15°	24428	18501	11450	18501
20°	21179	18093	9907	18093
25°	13890	17533	8845	17533
30°	9350	16858	8006	16858
35°	7571	16005	7222	16005
40°	6734	15076	6681	15076
45°	6094	13988	5966	13988
50°	5546	12911	5526	12911
55°	5213	11713	5146	11713
60°	4363	10618	4308	10618
65°	3679	9639	4172	9639
70°	3399	8611	3932	8611
75°	3175	7492	3631	7492
80°	2929	6165	3236	6165
85°	2705	4872	2853	4872



TEST NUMBER: P331689-927

CATALOG NUMBER: S122RDIP-S675D725U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.3	2.6
10°-20°	307.4	7.2
20°-30°	396.1	9.3
30°-40°	376.4	8.8
40°-50°	322.5	7.6
50°-60°	245.6	5.8
60°-70°	155.2	3.6
70°-80°	77.5	1.8
80°-90°	23.1	0.5
90°-100°	128.7	3.0
100°-110°	436.9	10.3
110°-120°	464.2	10.9
120°-130°	382.1	9.0
130°-140°	306.8	7.2
140°-150°	231.9	5.4
150°-160°	163.0	3.8
160°-170°	95.9	2.3
170°-180°	31.2	0.7
0°-30°	813.8	19.1
0°-40°	1190.3	28.0
0°-60°	1758.3	41.3
0°-90°	2014.2	47.3
90°-120°	1029.8	24.2
90°-150°	1950.7	45.8
90°-180°	2241.0	52.7
0°-180°	4254.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1164	1164	1164	1164	1164	
5°	1295	1167	1034	1167	1295	128
15°	1461	1107	685	1107	1461	394
25°	780	984	496	984	780	370
35°	384	812	366	812	384	246
45°	267	613	261	613	267	207
55°	185	416	183	416	185	163
65°	96	252	109	252	96	98
75°	51	120	58	120	51	54
85°	15	26	15	26	15	16
90°	20	1	20	1	20	12
95°	71	22	71	22	71	92
105°	698	76	698	76	698	675
115°	918	133	918	133	918	899
125°	745	186	745	186	745	673
135°	617	218	617	218	617	480
145°	493	249	493	249	493	313
155°	414	283	414	283	414	193
165°	364	308	364	308	364	104
175°	328	321	328	321	328	32
180°	322	322	322	322	322	



TEST NUMBER: P331689-927

CATALOG NUMBER: S122RDIP-S675D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1211.0	1212.0	1213.0	1210.7	1210.7	1208.7	1204.5	1201.3	1192.2	1191.0	1191.0
5°	1294.8	1294.0	1295.6	1290.4	1283.1	1281.4	1273.7	1263.7	1253.2	1241.4	1239.0
7.5°	1378.1	1376.9	1373.6	1372.8	1367.1	1354.9	1342.6	1329.4	1311.9	1294.9	1286.3
10°	1420.1	1433.5	1425.4	1411.3	1414.1	1395.1	1385.0	1367.6	1353.0	1327.5	1321.9
12.5°	1461.6	1466.8	1464.3	1456.2	1452.5	1439.4	1425.8	1410.6	1383.8	1360.9	1341.0
15°	1461.4	1469.1	1471.1	1468.7	1470.7	1469.9	1462.6	1450.1	1426.6	1401.5	1379.7
17.5°	1353.5	1358.8	1372.1	1381.1	1392.4	1416.3	1428.1	1432.7	1429.3	1415.0	1399.6
20°	1232.6	1223.6	1260.8	1279.8	1296.0	1336.4	1371.2	1384.6	1406.0	1405.6	1401.5
22.5°	1061.0	1063.2	1098.4	1121.0	1168.2	1208.6	1248.3	1298.5	1340.0	1367.4	1383.5
25°	779.7	795.0	830.2	860.9	913.5	988.7	1057.0	1136.3	1211.1	1270.1	1326.4
27.5°	585.5	586.7	614.6	642.9	674.1	735.8	821.8	916.5	1023.1	1111.1	1212.4
30°	501.5	499.0	510.7	528.1	554.8	602.5	667.2	760.3	866.6	999.2	1117.3
32.5°	441.9	442.0	450.9	463.7	485.9	518.1	562.4	637.9	738.5	868.9	1007.3
35°	384.1	383.7	390.2	399.5	408.8	429.4	459.8	499.4	568.5	690.2	831.8
37.5°	342.8	344.5	347.7	353.5	363.8	375.3	393.5	420.1	469.3	541.3	660.3
40°	319.5	320.3	324.7	329.5	335.6	344.5	359.5	380.9	416.9	474.4	561.3
42.5°	298.1	298.9	302.1	306.6	311.3	320.3	332.6	351.2	380.3	425.2	496.9
45°	266.9	266.9	269.7	271.7	277.0	285.1	295.2	310.5	330.8	363.9	411.6
47.5°	237.6	237.7	239.6	243.0	246.4	252.6	262.6	275.1	289.9	315.5	356.2
50°	220.8	221.2	222.4	225.2	227.3	232.9	240.6	251.5	266.9	286.7	320.7
52.5°	207.2	206.9	208.5	209.7	211.1	215.2	220.9	230.5	244.2	261.5	289.6
55°	185.2	183.5	186.0	188.1	189.3	190.8	194.1	200.2	211.9	226.5	247.5
57.5°	157.7	157.1	158.8	160.7	164.5	168.8	171.5	175.4	181.5	191.9	212.8
60°	135.1	135.1	138.7	139.9	144.3	150.0	155.7	158.9	165.0	171.8	187.2
62.5°	115.0	115.3	117.0	118.3	120.7	127.7	135.6	142.8	148.5	155.0	165.2
65°	96.3	97.0	97.0	97.8	99.5	101.1	104.3	110.0	120.1	129.4	137.0
67.5°	81.7	81.9	82.1	82.9	83.4	85.2	86.4	89.0	91.3	100.1	109.6
70°	72.0	73.2	72.8	73.6	74.0	74.8	76.4	77.6	81.3	83.3	89.0
72.5°	62.9	63.8	63.7	64.2	65.3	65.4	66.7	68.0	70.3	72.0	75.0
75°	50.9	50.5	50.9	51.7	52.1	52.6	52.6	54.2	55.4	57.0	59.0
77.5°	39.3	39.7	39.6	39.7	39.8	40.5	40.4	41.2	42.4	43.2	44.1
80°	31.5	31.9	31.5	31.9	32.3	32.7	32.3	32.7	34.0	34.8	34.8
82.5°	24.4	24.5	24.7	24.8	24.9	25.0	25.6	25.7	26.5	26.4	26.7
85°	14.6	14.2	14.2	14.2	14.6	15.0	14.6	14.6	15.0	15.0	15.0
87.5°	9.3	9.6	9.6	9.6	9.6	9.4	9.2	9.8	9.6	10.1	9.6
90°	20.4	20.4	20.4	20.4	20.4	19.8	18.6	19.8	20.4	21.1	20.4
92.5°	34.3	35.3	34.8	36.8	37.3	41.1	46.3	54.0	68.0	80.5	79.4
95°	70.6	69.9	71.9	76.8	84.8	98.5	124.5	162.2	212.4	242.7	214.9
97.5°	138.9	144.2	153.2	168.4	198.0	242.7	309.7	378.6	434.7	414.4	312.1
100°	221.7	232.8	250.8	277.4	328.8	403.8	488.6	565.4	578.4	489.2	336.8
102.5°	390.1	405.2	427.6	473.1	528.9	608.3	670.4	687.8	631.8	491.7	327.5
105°	697.9	706.5	733.2	771.6	810.0	830.4	822.4	752.4	623.6	458.8	309.0
107.5°	891.4	903.0	908.3	910.5	905.6	875.6	811.2	705.8	569.2	423.7	299.8
110°	949.9	950.5	945.0	933.2	906.6	855.8	776.6	665.7	535.0	406.9	297.9



TEST NUMBER: P331689-927

CATALOG NUMBER: S122RDIP-S675D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	949.0	945.6	935.1	915.4	878.4	820.1	735.4	629.1	511.3	395.9	298.3
115°	918.4	912.8	896.7	868.2	824.2	760.4	679.3	583.9	481.8	384.0	301.0
117.5°	863.7	859.0	842.1	812.0	767.1	707.3	633.7	550.0	463.2	378.1	305.4
120°	828.5	822.4	804.4	775.3	732.0	675.6	610.0	533.1	453.3	374.6	308.4
122.5°	791.9	786.7	770.7	742.1	703.2	652.3	590.2	519.8	444.9	372.6	311.9
125°	745.0	740.0	724.5	701.0	665.0	618.6	564.1	500.3	432.8	369.1	317.0
127.5°	703.9	699.9	686.5	664.5	633.1	590.3	538.8	481.2	421.7	366.9	322.4
130°	680.6	675.6	663.2	642.1	611.8	570.9	522.0	468.7	414.3	366.0	326.4
132.5°	656.2	651.8	640.4	619.4	589.5	551.1	506.2	456.9	408.4	365.5	330.3
135°	617.4	614.9	603.8	583.4	556.7	522.0	481.2	440.3	400.1	364.7	335.0
137.5°	579.2	575.5	565.8	548.2	523.9	493.7	461.2	427.1	394.2	364.6	339.2
140°	553.0	549.3	540.0	523.9	504.1	476.8	448.4	418.6	390.8	364.1	341.2
142.5°	526.7	526.0	517.7	503.1	484.3	461.4	437.0	411.7	387.3	364.1	342.7
145°	492.9	491.1	484.9	474.4	459.5	441.6	422.3	401.9	382.7	362.9	344.3
147.5°	464.5	463.4	459.2	450.8	438.6	425.4	410.4	394.3	378.0	360.7	344.8
150°	447.7	447.1	443.4	435.9	426.7	415.5	402.5	388.9	374.0	359.2	344.3
152.5°	433.3	433.2	430.5	424.1	416.8	407.1	396.1	383.4	370.6	356.7	343.3
155°	414.3	415.5	413.0	408.7	401.9	395.1	385.8	375.9	364.1	352.4	341.8
157.5°	398.1	398.1	397.0	393.3	388.5	383.2	375.4	367.1	358.1	347.9	339.0
160°	387.6	387.6	387.1	384.0	379.6	375.3	368.4	361.6	353.6	344.9	337.5
162.5°	377.7	378.3	377.6	375.5	371.2	367.8	362.0	356.2	349.6	342.5	336.0
165°	363.5	364.1	364.1	361.6	359.2	356.7	352.4	348.0	343.1	337.5	333.2
167.5°	350.4	351.1	351.3	349.9	348.8	346.5	343.6	340.2	336.6	333.2	330.3
170°	342.5	343.6	344.3	342.5	341.8	340.6	338.1	336.3	333.2	330.7	328.8
172.5°	336.0	336.8	337.4	336.5	335.9	335.2	333.2	331.8	329.7	327.7	326.9
175°	327.6	328.8	329.5	328.8	328.8	328.2	327.6	326.9	325.1	324.5	323.8
177.5°	322.5	323.5	324.0	324.0	324.0	324.0	323.5	323.5	322.5	322.0	322.5
180°	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0



TEST NUMBER: P331689-927

CATALOG NUMBER: S122RDIP-S675D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1191.6	1189.0	1186.8	1180.9	1178.1	1171.6	1170.6	1170.3	1161.8	1153.7	1151.5
5°	1232.6	1226.1	1216.3	1205.0	1193.3	1181.1	1173.1	1166.6	1150.4	1135.0	1126.2
7.5°	1273.7	1259.9	1243.1	1221.7	1203.8	1183.8	1168.9	1155.6	1132.6	1110.6	1095.7
10°	1304.5	1281.8	1259.6	1230.1	1207.0	1184.4	1163.4	1145.2	1119.3	1090.2	1069.5
12.5°	1323.6	1298.7	1268.0	1239.1	1209.3	1180.5	1152.4	1129.0	1098.6	1068.5	1044.0
15°	1349.4	1322.7	1285.5	1244.3	1205.9	1168.2	1135.9	1106.8	1067.1	1031.2	1001.2
17.5°	1370.5	1333.8	1293.8	1246.1	1201.7	1153.8	1112.1	1075.0	1030.9	987.5	952.2
20°	1377.3	1340.9	1294.8	1247.1	1194.5	1138.3	1093.4	1053.0	1005.7	958.4	917.9
22.5°	1373.1	1344.8	1293.5	1236.4	1182.6	1123.7	1073.0	1026.1	973.7	925.3	878.5
25°	1344.6	1334.8	1286.3	1224.0	1162.6	1094.2	1035.6	984.2	924.4	872.7	821.7
27.5°	1277.9	1298.9	1268.8	1202.5	1134.2	1060.9	995.0	936.5	874.4	816.2	765.4
30°	1213.9	1262.0	1249.1	1187.6	1111.2	1039.3	965.3	904.2	837.9	778.0	727.9
32.5°	1126.2	1205.8	1218.4	1167.0	1087.9	1008.8	931.3	870.5	801.3	738.2	689.4
35°	986.7	1105.6	1160.2	1127.4	1048.1	962.8	882.7	812.0	742.4	680.2	631.6
37.5°	820.1	982.1	1073.0	1075.4	1002.6	913.9	826.7	756.5	685.2	624.1	571.6
40°	712.1	887.6	1006.1	1032.4	970.9	875.0	786.9	715.3	645.8	585.9	525.7
42.5°	615.1	789.9	935.6	981.3	932.4	837.2	748.8	673.9	606.3	549.7	488.1
45°	497.4	650.2	810.8	892.5	865.4	777.2	683.8	612.6	549.1	500.2	441.2
47.5°	419.5	527.3	682.6	793.1	792.7	712.2	620.3	552.2	493.3	447.4	399.6
50°	375.3	469.1	600.5	725.9	736.3	668.8	581.5	514.0	459.0	410.8	372.4
52.5°	335.5	412.8	530.9	651.1	681.0	622.6	537.8	475.5	422.1	377.9	344.9
55°	283.4	343.3	433.1	545.5	590.8	549.5	474.4	416.1	372.8	335.6	307.3
57.5°	239.8	284.7	356.7	447.3	499.9	474.0	411.9	364.6	327.6	294.0	271.6
60°	212.3	249.1	310.1	385.8	444.0	425.8	372.8	328.8	297.2	268.1	247.1
62.5°	186.4	218.0	270.4	331.8	385.2	377.6	334.3	297.4	269.7	243.2	225.4
65°	150.0	173.1	213.9	262.1	304.9	308.6	277.4	252.3	227.7	206.6	190.8
67.5°	119.5	134.5	163.3	203.8	235.9	247.4	228.4	209.2	189.6	173.4	159.7
70°	100.7	112.8	133.9	166.6	196.1	208.3	197.3	182.4	165.4	152.0	140.3
72.5°	81.6	93.4	108.9	132.9	158.3	171.3	167.5	156.9	143.1	132.0	120.9
75°	61.5	65.1	75.7	91.8	111.6	122.9	125.8	120.1	109.2	100.7	94.2
77.5°	45.5	47.6	52.7	61.2	74.1	84.2	88.3	87.7	80.2	75.2	69.2
80°	36.4	37.6	40.0	43.6	53.4	63.5	66.3	66.3	61.1	59.0	53.0
82.5°	27.6	28.5	30.0	32.0	36.5	45.4	48.6	49.2	45.9	43.2	38.4
85°	15.8	15.4	16.2	17.3	18.2	20.6	25.5	26.3	25.5	22.3	21.0
87.5°	8.9	8.3	7.7	7.0	7.1	7.1	8.2	9.5	8.6	8.1	7.7
90°	16.7	12.4	9.3	7.4	6.2	5.0	2.5	0.6	2.5	5.0	6.2
92.5°	61.8	42.1	28.1	22.3	18.1	15.4	10.9	7.5	10.9	15.4	18.1
95°	143.1	89.2	60.7	45.8	35.9	30.3	24.2	21.7	24.2	30.3	35.9
97.5°	192.7	117.6	81.8	65.0	53.6	45.2	38.7	35.3	38.7	45.2	53.6
100°	203.1	127.5	94.7	77.4	65.0	55.1	49.5	47.7	49.5	55.1	65.0
102.5°	203.6	136.5	106.2	88.8	75.9	66.0	60.4	59.1	60.4	66.0	75.9
105°	206.8	151.7	122.6	105.3	91.7	82.4	78.0	75.6	78.0	82.4	91.7
107.5°	215.4	167.3	139.1	121.6	108.1	99.6	95.4	93.4	95.4	99.6	108.1
110°	222.3	177.7	150.5	132.5	119.5	111.5	107.7	105.3	107.7	111.5	119.5



TEST NUMBER: P331689-927

CATALOG NUMBER: S122RDIP-S675D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	229.7	187.7	161.4	142.9	130.4	122.9	118.7	116.1	118.7	122.9	130.4
115°	240.9	203.1	176.5	159.8	147.3	140.0	136.3	133.2	136.3	140.0	147.3
117.5°	252.8	217.4	192.7	175.4	163.5	156.9	153.2	150.8	153.2	156.9	163.5
120°	260.7	227.3	203.1	185.8	173.4	167.8	164.1	161.6	164.1	167.8	173.4
122.5°	267.7	236.7	214.0	196.1	183.8	177.7	174.0	172.1	174.0	177.7	183.8
125°	278.7	250.8	228.5	211.2	198.8	191.3	187.7	185.8	187.7	191.3	198.8
127.5°	288.9	264.0	242.2	224.4	212.5	204.4	199.2	196.7	199.2	204.4	212.5
130°	295.4	271.9	250.2	232.8	220.5	211.8	205.6	203.1	205.6	211.8	220.5
132.5°	301.8	278.8	258.1	240.7	227.9	218.7	212.1	209.1	212.1	218.7	227.9
135°	310.2	288.6	268.8	251.4	237.2	227.9	220.5	218.0	220.5	227.9	237.2
137.5°	316.7	296.5	276.9	260.9	246.7	236.8	229.3	226.4	229.3	236.8	246.7
140°	320.1	301.0	282.4	266.3	252.6	242.7	235.3	232.8	235.3	242.7	252.6
142.5°	323.1	304.4	286.4	271.2	258.1	248.2	241.3	239.2	241.3	248.2	258.1
145°	326.9	309.7	292.9	279.2	266.9	257.6	251.4	248.9	251.4	257.6	266.9
147.5°	329.1	313.9	298.1	286.0	275.7	267.1	261.2	259.4	261.2	267.1	275.7
150°	330.0	315.8	301.6	290.4	281.1	273.1	268.2	266.3	268.2	273.1	281.1
152.5°	330.6	317.8	305.1	294.9	286.1	279.0	274.1	273.2	274.1	279.0	286.1
155°	331.3	320.8	310.2	301.0	294.1	287.3	283.6	283.0	283.6	287.3	294.1
157.5°	331.3	322.9	313.9	306.2	300.7	294.8	291.8	291.2	291.8	294.8	300.7
160°	331.3	323.8	316.4	309.7	304.7	299.7	297.2	296.6	297.2	299.7	304.7
162.5°	330.8	324.4	317.9	312.6	308.2	304.2	301.7	302.1	301.7	304.2	308.2
165°	329.5	325.1	319.6	315.8	312.8	309.0	307.8	308.4	307.8	309.0	312.8
167.5°	328.6	325.0	320.9	318.5	316.3	313.9	312.8	313.6	312.8	313.9	316.3
170°	327.6	324.5	321.4	319.6	318.3	316.4	315.8	317.0	315.8	316.4	318.3
172.5°	326.1	324.0	321.9	320.5	319.8	317.9	318.3	319.0	318.3	317.9	319.8
175°	324.5	323.2	322.0	321.4	321.4	320.1	320.8	321.4	320.8	320.1	321.4
177.5°	323.5	322.5	322.0	322.0	322.0	321.0	321.5	322.5	321.5	321.0	322.0
180°	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0



TEST NUMBER: P331689-927

CATALOG NUMBER: S122RDIP-S675D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1147.3	1145.0	1140.8	1134.3	1130.4	1123.6	1119.1	1121.7	1122.4	1121.7	1121.1
5°	1116.5	1107.9	1096.2	1084.9	1074.4	1063.1	1056.6	1053.8	1048.1	1044.9	1043.3
7.5°	1079.2	1064.5	1048.0	1028.3	1011.5	994.0	985.0	980.5	968.9	962.7	957.1
10°	1051.4	1028.3	1011.8	985.9	970.1	947.1	931.3	931.7	915.9	907.0	900.6
12.5°	1020.6	995.3	967.7	944.4	922.5	904.0	885.0	877.3	860.5	852.0	834.6
15°	969.7	940.2	911.1	879.5	857.3	828.5	801.1	767.5	740.4	716.9	710.5
17.5°	914.0	877.5	848.3	811.3	773.2	724.8	693.0	673.5	657.2	644.8	635.6
20°	875.8	838.7	807.6	751.7	700.4	667.7	644.2	629.2	612.2	598.9	591.6
22.5°	835.8	796.9	754.5	692.2	652.2	625.9	605.0	587.8	576.3	565.9	559.3
25°	778.8	736.3	666.4	623.5	591.2	563.7	549.1	538.6	526.5	512.3	505.9
27.5°	718.7	651.1	600.9	569.0	538.1	520.2	507.2	491.5	480.6	474.3	467.5
30°	673.7	606.2	567.0	532.2	510.3	490.5	475.2	466.3	455.7	444.8	440.4
32.5°	623.5	569.6	532.0	503.0	480.9	464.0	451.9	437.4	429.8	423.1	413.8
35°	561.3	520.5	486.1	462.6	441.6	427.9	413.7	405.2	391.4	385.8	382.1
37.5°	508.5	473.1	447.5	422.7	406.1	390.9	382.2	368.7	362.7	354.9	347.2
40°	478.8	444.0	419.3	399.1	380.5	369.2	358.3	347.4	338.4	334.9	325.5
42.5°	448.4	420.1	395.4	373.2	360.8	348.8	335.0	327.0	317.7	311.9	306.1
45°	406.4	381.4	360.3	342.1	328.4	315.8	306.9	293.6	288.4	276.6	271.7
47.5°	369.6	346.2	326.1	308.9	295.4	287.2	274.3	263.8	255.4	248.2	242.0
50°	343.3	323.9	304.5	289.1	277.0	265.3	251.9	246.7	233.7	230.0	226.5
52.5°	319.4	301.0	283.1	268.1	256.0	244.5	232.8	225.9	217.2	213.6	211.0
55°	285.9	268.1	251.1	237.7	225.6	213.9	206.6	198.1	194.1	191.2	188.1
57.5°	252.2	236.2	223.2	209.7	197.5	188.2	179.7	174.7	170.5	166.8	162.9
60°	230.9	215.6	203.8	191.2	178.7	171.0	164.6	158.5	153.7	148.0	146.4
62.5°	208.3	194.8	184.1	171.8	161.0	153.9	147.7	142.0	136.2	127.9	125.6
65°	177.1	166.6	155.3	145.2	135.5	128.6	119.7	113.2	110.8	110.0	109.6
67.5°	149.0	139.0	129.3	119.0	110.1	103.8	99.3	98.2	96.6	96.1	95.0
70°	130.2	120.9	111.2	101.5	93.0	91.8	90.2	88.6	86.5	85.7	84.9
72.5°	113.4	103.8	94.0	86.3	82.6	81.1	79.5	77.9	76.5	75.7	75.2
75°	86.9	78.0	71.6	68.8	66.7	65.5	63.1	61.9	61.1	59.8	59.4
77.5°	62.6	57.6	54.6	52.8	50.7	49.4	48.0	46.8	45.9	45.7	45.1
80°	47.7	45.3	43.3	40.9	40.0	38.4	38.0	36.8	37.2	36.0	36.0
82.5°	37.1	34.0	32.2	31.1	30.3	29.1	28.6	28.0	28.1	27.3	27.3
85°	19.0	18.2	17.3	16.6	16.6	15.4	15.8	15.4	15.4	14.6	14.2
87.5°	7.6	7.7	7.7	8.6	9.3	9.0	9.0	8.5	8.2	8.5	8.3
90°	7.4	9.3	12.4	16.7	20.4	21.1	20.4	19.8	18.6	19.8	20.4
92.5°	22.3	28.1	42.1	61.8	79.4	80.5	68.0	54.0	46.3	41.1	37.3
95°	45.8	60.7	89.2	143.1	214.9	242.7	212.4	162.2	124.5	98.5	84.8
97.5°	65.0	81.8	117.6	192.7	312.1	414.4	434.7	378.6	309.7	242.7	198.0
100°	77.4	94.7	127.5	203.1	336.8	489.2	578.4	565.4	488.6	403.8	328.8
102.5°	88.8	106.2	136.5	203.6	327.5	491.7	631.8	687.8	670.4	608.3	528.9
105°	105.3	122.6	151.7	206.8	309.0	458.8	623.6	752.4	822.4	830.4	810.0
107.5°	121.6	139.1	167.3	215.4	299.8	423.7	569.2	705.8	811.2	875.6	905.6
110°	132.5	150.5	177.7	222.3	297.9	406.9	535.0	665.7	776.6	855.8	906.6



TEST NUMBER: P331689-927

CATALOG NUMBER: S122RDIP-S675D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	142.9	161.4	187.7	229.7	298.3	395.9	511.3	629.1	735.4	820.1	878.4
115°	159.8	176.5	203.1	240.9	301.0	384.0	481.8	583.9	679.3	760.4	824.2
117.5°	175.4	192.7	217.4	252.8	305.4	378.1	463.2	550.0	633.7	707.3	767.1
120°	185.8	203.1	227.3	260.7	308.4	374.6	453.3	533.1	610.0	675.6	732.0
122.5°	196.1	214.0	236.7	267.7	311.9	372.6	444.9	519.8	590.2	652.3	703.2
125°	211.2	228.5	250.8	278.7	317.0	369.1	432.8	500.3	564.1	618.6	665.0
127.5°	224.4	242.2	264.0	288.9	322.4	366.9	421.7	481.2	538.8	590.3	633.1
130°	232.8	250.2	271.9	295.4	326.4	366.0	414.3	468.7	522.0	570.9	611.8
132.5°	240.7	258.1	278.8	301.8	330.3	365.5	408.4	456.9	506.2	551.1	589.5
135°	251.4	268.8	288.6	310.2	335.0	364.7	400.1	440.3	481.2	522.0	556.7
137.5°	260.9	276.9	296.5	316.7	339.2	364.6	394.2	427.1	461.2	493.7	523.9
140°	266.3	282.4	301.0	320.1	341.2	364.1	390.8	418.6	448.4	476.8	504.1
142.5°	271.2	286.4	304.4	323.1	342.7	364.1	387.3	411.7	437.0	461.4	484.3
145°	279.2	292.9	309.7	326.9	344.3	362.9	382.7	401.9	422.3	441.6	459.5
147.5°	286.0	298.1	313.9	329.1	344.8	360.7	378.0	394.3	410.4	425.4	438.6
150°	290.4	301.6	315.8	330.0	344.3	359.2	374.0	388.9	402.5	415.5	426.7
152.5°	294.9	305.1	317.8	330.6	343.3	356.7	370.6	383.4	396.1	407.1	416.8
155°	301.0	310.2	320.8	331.3	341.8	352.4	364.1	375.9	385.8	395.1	401.9
157.5°	306.2	313.9	322.9	331.3	339.0	347.9	358.1	367.1	375.4	383.2	388.5
160°	309.7	316.4	323.8	331.3	337.5	344.9	353.6	361.6	368.4	375.3	379.6
162.5°	312.6	317.9	324.4	330.8	336.0	342.5	349.6	356.2	362.0	367.8	371.2
165°	315.8	319.6	325.1	329.5	333.2	337.5	343.1	348.0	352.4	356.7	359.2
167.5°	318.5	320.9	325.0	328.6	330.3	333.2	336.6	340.2	343.6	346.5	348.8
170°	319.6	321.4	324.5	327.6	328.8	330.7	333.2	336.3	338.1	340.6	341.8
172.5°	320.5	321.9	324.0	326.1	326.9	327.7	329.7	331.8	333.2	335.2	335.9
175°	321.4	322.0	323.2	324.5	323.8	324.5	325.1	326.9	327.6	328.2	328.8
177.5°	322.0	322.0	322.5	323.5	322.5	322.0	322.5	323.5	323.5	324.0	324.0
180°	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0



TEST NUMBER: P331689-927

CATALOG NUMBER: S122RDIP-S675D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1117.5	1118.2	1117.2	1117.8	1117.2	1118.2	1117.5	1121.1	1121.7	1122.4	1121.7
5°	1041.2	1036.4	1035.6	1034.4	1035.6	1036.4	1041.2	1043.3	1044.9	1048.1	1053.8
7.5°	950.2	949.4	947.5	944.6	947.5	949.4	950.2	957.1	962.7	968.9	980.5
10°	891.6	889.6	889.2	886.4	889.2	889.6	891.6	900.6	907.0	915.9	931.7
12.5°	823.1	810.0	808.7	801.6	808.7	810.0	823.1	834.6	852.0	860.5	877.3
15°	700.8	698.4	690.2	685.0	690.2	698.4	700.8	710.5	716.9	740.4	767.5
17.5°	630.9	623.0	620.4	619.3	620.4	623.0	630.9	635.6	644.8	657.2	673.5
20°	585.9	578.7	577.4	576.6	577.4	578.7	585.9	591.6	598.9	612.2	629.2
22.5°	554.8	547.2	544.2	541.7	544.2	547.2	554.8	559.3	565.9	576.3	587.8
25°	501.8	499.0	497.4	496.5	497.4	499.0	501.8	505.9	512.3	526.5	538.6
27.5°	460.3	454.1	452.9	450.8	452.9	454.1	460.3	467.5	474.3	480.6	491.5
30°	436.7	434.7	431.9	429.4	431.9	434.7	436.7	440.4	444.8	455.7	466.3
32.5°	408.9	407.2	404.7	403.5	404.7	407.2	408.9	413.8	423.1	429.8	437.4
35°	378.1	372.4	370.0	366.4	370.0	372.4	378.1	382.1	385.8	391.4	405.2
37.5°	345.5	342.5	339.1	340.3	339.1	342.5	345.5	347.2	354.9	362.7	368.7
40°	320.3	318.2	317.4	317.0	317.4	318.2	320.3	325.5	334.9	338.4	347.4
42.5°	300.2	294.6	292.6	292.5	292.6	294.6	300.2	306.1	311.9	317.7	327.0
45°	269.7	264.4	260.8	261.3	260.8	264.4	269.7	271.7	276.6	288.4	293.6
47.5°	238.5	238.4	236.1	236.8	236.1	238.4	238.5	242.0	248.2	255.4	263.8
50°	223.6	221.2	219.6	220.0	219.6	221.2	223.6	226.5	230.0	233.7	246.7
52.5°	209.4	207.3	206.0	207.7	206.0	207.3	209.4	211.0	213.6	217.2	225.9
55°	186.0	183.5	183.2	182.8	183.2	183.5	186.0	188.1	191.2	194.1	198.1
57.5°	159.9	158.3	155.8	154.8	155.8	158.3	159.9	162.9	166.8	170.5	174.7
60°	141.1	137.9	133.9	133.4	133.9	137.9	141.1	146.4	148.0	153.7	158.5
62.5°	124.0	123.3	122.6	122.5	122.6	123.3	124.0	125.6	127.9	136.2	142.0
65°	108.8	108.4	108.8	109.2	108.8	108.4	108.8	109.6	110.0	110.8	113.2
67.5°	94.8	94.0	93.3	93.6	93.3	94.0	94.8	95.0	96.1	96.6	98.2
70°	84.1	83.7	83.3	83.3	83.3	83.7	84.1	84.9	85.7	86.5	88.6
72.5°	73.8	73.7	73.3	73.0	73.3	73.7	73.8	75.2	75.7	76.5	77.9
75°	59.0	58.2	58.2	58.2	58.2	58.2	59.0	59.4	59.8	61.1	61.9
77.5°	45.0	44.6	44.1	43.8	44.1	44.6	45.0	45.1	45.7	45.9	46.8
80°	35.6	35.2	34.8	34.8	34.8	35.2	35.6	36.0	36.0	37.2	36.8
82.5°	27.2	26.8	26.7	26.4	26.7	26.8	27.2	27.3	27.3	28.1	28.0
85°	14.6	15.0	14.6	15.4	14.6	15.0	14.6	14.2	14.6	15.4	15.4
87.5°	8.3	8.0	8.3	8.0	8.3	8.0	8.3	8.3	8.5	8.2	8.5
90°	20.4	20.4	20.4	20.4	20.4	20.4	20.4	20.4	19.8	18.6	19.8
92.5°	36.8	34.8	35.3	34.3	35.3	34.8	36.8	37.3	41.1	46.3	54.0
95°	76.8	71.9	69.9	70.6	69.9	71.9	76.8	84.8	98.5	124.5	162.2
97.5°	168.4	153.2	144.2	138.9	144.2	153.2	168.4	198.0	242.7	309.7	378.6
100°	277.4	250.8	232.8	221.7	232.8	250.8	277.4	328.8	403.8	488.6	565.4
102.5°	473.1	427.6	405.2	390.1	405.2	427.6	473.1	528.9	608.3	670.4	687.8
105°	771.6	733.2	706.5	697.9	706.5	733.2	771.6	810.0	830.4	822.4	752.4
107.5°	910.5	908.3	903.0	891.4	903.0	908.3	910.5	905.6	875.6	811.2	705.8
110°	933.2	945.0	950.5	949.9	950.5	945.0	933.2	906.6	855.8	776.6	665.7



TEST NUMBER: P331689-927

CATALOG NUMBER: S122RDIP-S675D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	915.4	935.1	945.6	949.0	945.6	935.1	915.4	878.4	820.1	735.4	629.1
115°	868.2	896.7	912.8	918.4	912.8	896.7	868.2	824.2	760.4	679.3	583.9
117.5°	812.0	842.1	859.0	863.7	859.0	842.1	812.0	767.1	707.3	633.7	550.0
120°	775.3	804.4	822.4	828.5	822.4	804.4	775.3	732.0	675.6	610.0	533.1
122.5°	742.1	770.7	786.7	791.9	786.7	770.7	742.1	703.2	652.3	590.2	519.8
125°	701.0	724.5	740.0	745.0	740.0	724.5	701.0	665.0	618.6	564.1	500.3
127.5°	664.5	686.5	699.9	703.9	699.9	686.5	664.5	633.1	590.3	538.8	481.2
130°	642.1	663.2	675.6	680.6	675.6	663.2	642.1	611.8	570.9	522.0	468.7
132.5°	619.4	640.4	651.8	656.2	651.8	640.4	619.4	589.5	551.1	506.2	456.9
135°	583.4	603.8	614.9	617.4	614.9	603.8	583.4	556.7	522.0	481.2	440.3
137.5°	548.2	565.8	575.5	579.2	575.5	565.8	548.2	523.9	493.7	461.2	427.1
140°	523.9	540.0	549.3	553.0	549.3	540.0	523.9	504.1	476.8	448.4	418.6
142.5°	503.1	517.7	526.0	526.7	526.0	517.7	503.1	484.3	461.4	437.0	411.7
145°	474.4	484.9	491.1	492.9	491.1	484.9	474.4	459.5	441.6	422.3	401.9
147.5°	450.8	459.2	463.4	464.5	463.4	459.2	450.8	438.6	425.4	410.4	394.3
150°	435.9	443.4	447.1	447.7	447.1	443.4	435.9	426.7	415.5	402.5	388.9
152.5°	424.1	430.5	433.2	433.3	433.2	430.5	424.1	416.8	407.1	396.1	383.4
155°	408.7	413.0	415.5	414.3	415.5	413.0	408.7	401.9	395.1	385.8	375.9
157.5°	393.3	397.0	398.1	398.1	398.1	397.0	393.3	388.5	383.2	375.4	367.1
160°	384.0	387.1	387.6	387.6	387.6	387.1	384.0	379.6	375.3	368.4	361.6
162.5°	375.5	377.6	378.3	377.7	378.3	377.6	375.5	371.2	367.8	362.0	356.2
165°	361.6	364.1	364.1	363.5	364.1	364.1	361.6	359.2	356.7	352.4	348.0
167.5°	349.9	351.3	351.1	350.4	351.1	351.3	349.9	348.8	346.5	343.6	340.2
170°	342.5	344.3	343.6	342.5	343.6	344.3	342.5	341.8	340.6	338.1	336.3
172.5°	336.5	337.4	336.8	336.0	336.8	337.4	336.5	335.9	335.2	333.2	331.8
175°	328.8	329.5	328.8	327.6	328.8	329.5	328.8	328.8	328.2	327.6	326.9
177.5°	324.0	324.0	323.5	322.5	323.5	324.0	324.0	324.0	324.0	323.5	323.5
180°	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0



TEST NUMBER: P331689-927

CATALOG NUMBER: S122RDIP-S675D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1119.1	1123.6	1130.4	1134.3	1140.8	1145.0	1147.3	1151.5	1153.7	1161.8	1170.3
5°	1056.6	1063.1	1074.4	1084.9	1096.2	1107.9	1116.5	1126.2	1135.0	1150.4	1166.6
7.5°	985.0	994.0	1011.5	1028.3	1048.0	1064.5	1079.2	1095.7	1110.6	1132.6	1155.6
10°	931.3	947.1	970.1	985.9	1011.8	1028.3	1051.4	1069.5	1090.2	1119.3	1145.2
12.5°	885.0	904.0	922.5	944.4	967.7	995.3	1020.6	1044.0	1068.5	1098.6	1129.0
15°	801.1	828.5	857.3	879.5	911.1	940.2	969.7	1001.2	1031.2	1067.1	1106.8
17.5°	693.0	724.8	773.2	811.3	848.3	877.5	914.0	952.2	987.5	1030.9	1075.0
20°	644.2	667.7	700.4	751.7	807.6	838.7	875.8	917.9	958.4	1005.7	1053.0
22.5°	605.0	625.9	652.2	692.2	754.5	796.9	835.8	878.5	925.3	973.7	1026.1
25°	549.1	563.7	591.2	623.5	666.4	736.3	778.8	821.7	872.7	924.4	984.2
27.5°	507.2	520.2	538.1	569.0	600.9	651.1	718.7	765.4	816.2	874.4	936.5
30°	475.2	490.5	510.3	532.2	567.0	606.2	673.7	727.9	778.0	837.9	904.2
32.5°	451.9	464.0	480.9	503.0	532.0	569.6	623.5	689.4	738.2	801.3	870.5
35°	413.7	427.9	441.6	462.6	486.1	520.5	561.3	631.6	680.2	742.4	812.0
37.5°	382.2	390.9	406.1	422.7	447.5	473.1	508.5	571.6	624.1	685.2	756.5
40°	358.3	369.2	380.5	399.1	419.3	444.0	478.8	525.7	585.9	645.8	715.3
42.5°	335.0	348.8	360.8	373.2	395.4	420.1	448.4	488.1	549.7	606.3	673.9
45°	306.9	315.8	328.4	342.1	360.3	381.4	406.4	441.2	500.2	549.1	612.6
47.5°	274.3	287.2	295.4	308.9	326.1	346.2	369.6	399.6	447.4	493.3	552.2
50°	251.9	265.3	277.0	289.1	304.5	323.9	343.3	372.4	410.8	459.0	514.0
52.5°	232.8	244.5	256.0	268.1	283.1	301.0	319.4	344.9	377.9	422.1	475.5
55°	206.6	213.9	225.6	237.7	251.1	268.1	285.9	307.3	335.6	372.8	416.1
57.5°	179.7	188.2	197.5	209.7	223.2	236.2	252.2	271.6	294.0	327.6	364.6
60°	164.6	171.0	178.7	191.2	203.8	215.6	230.9	247.1	268.1	297.2	328.8
62.5°	147.7	153.9	161.0	171.8	184.1	194.8	208.3	225.4	243.2	269.7	297.4
65°	119.7	128.6	135.5	145.2	155.3	166.6	177.1	190.8	206.6	227.7	252.3
67.5°	99.3	103.8	110.1	119.0	129.3	139.0	149.0	159.7	173.4	189.6	209.2
70°	90.2	91.8	93.0	101.5	111.2	120.9	130.2	140.3	152.0	165.4	182.4
72.5°	79.5	81.1	82.6	86.3	94.0	103.8	113.4	120.9	132.0	143.1	156.9
75°	63.1	65.5	66.7	68.8	71.6	78.0	86.9	94.2	100.7	109.2	120.1
77.5°	48.0	49.4	50.7	52.8	54.6	57.6	62.6	69.2	75.2	80.2	87.7
80°	38.0	38.4	40.0	40.9	43.3	45.3	47.7	53.0	59.0	61.1	66.3
82.5°	28.6	29.1	30.3	31.1	32.2	34.0	37.1	38.4	43.2	45.9	49.2
85°	15.8	15.4	16.6	16.6	17.3	18.2	19.0	21.0	22.3	25.5	26.3
87.5°	9.0	9.0	9.3	8.6	7.7	7.7	7.6	7.7	8.1	8.6	9.5
90°	20.4	21.1	20.4	16.7	12.4	9.3	7.4	6.2	5.0	2.5	0.6
92.5°	68.0	80.5	79.4	61.8	42.1	28.1	22.3	18.1	15.4	10.9	7.5
95°	212.4	242.7	214.9	143.1	89.2	60.7	45.8	35.9	30.3	24.2	21.7
97.5°	434.7	414.4	312.1	192.7	117.6	81.8	65.0	53.6	45.2	38.7	35.3
100°	578.4	489.2	336.8	203.1	127.5	94.7	77.4	65.0	55.1	49.5	47.7
102.5°	631.8	491.7	327.5	203.6	136.5	106.2	88.8	75.9	66.0	60.4	59.1
105°	623.6	458.8	309.0	206.8	151.7	122.6	105.3	91.7	82.4	78.0	75.6
107.5°	569.2	423.7	299.8	215.4	167.3	139.1	121.6	108.1	99.6	95.4	93.4
110°	535.0	406.9	297.9	222.3	177.7	150.5	132.5	119.5	111.5	107.7	105.3



TEST NUMBER: P331689-927

CATALOG NUMBER: S122RDIP-S675D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	511.3	395.9	298.3	229.7	187.7	161.4	142.9	130.4	122.9	118.7	116.1
115°	481.8	384.0	301.0	240.9	203.1	176.5	159.8	147.3	140.0	136.3	133.2
117.5°	463.2	378.1	305.4	252.8	217.4	192.7	175.4	163.5	156.9	153.2	150.8
120°	453.3	374.6	308.4	260.7	227.3	203.1	185.8	173.4	167.8	164.1	161.6
122.5°	444.9	372.6	311.9	267.7	236.7	214.0	196.1	183.8	177.7	174.0	172.1
125°	432.8	369.1	317.0	278.7	250.8	228.5	211.2	198.8	191.3	187.7	185.8
127.5°	421.7	366.9	322.4	288.9	264.0	242.2	224.4	212.5	204.4	199.2	196.7
130°	414.3	366.0	326.4	295.4	271.9	250.2	232.8	220.5	211.8	205.6	203.1
132.5°	408.4	365.5	330.3	301.8	278.8	258.1	240.7	227.9	218.7	212.1	209.1
135°	400.1	364.7	335.0	310.2	288.6	268.8	251.4	237.2	227.9	220.5	218.0
137.5°	394.2	364.6	339.2	316.7	296.5	276.9	260.9	246.7	236.8	229.3	226.4
140°	390.8	364.1	341.2	320.1	301.0	282.4	266.3	252.6	242.7	235.3	232.8
142.5°	387.3	364.1	342.7	323.1	304.4	286.4	271.2	258.1	248.2	241.3	239.2
145°	382.7	362.9	344.3	326.9	309.7	292.9	279.2	266.9	257.6	251.4	248.9
147.5°	378.0	360.7	344.8	329.1	313.9	298.1	286.0	275.7	267.1	261.2	259.4
150°	374.0	359.2	344.3	330.0	315.8	301.6	290.4	281.1	273.1	268.2	266.3
152.5°	370.6	356.7	343.3	330.6	317.8	305.1	294.9	286.1	279.0	274.1	273.2
155°	364.1	352.4	341.8	331.3	320.8	310.2	301.0	294.1	287.3	283.6	283.0
157.5°	358.1	347.9	339.0	331.3	322.9	313.9	306.2	300.7	294.8	291.8	291.2
160°	353.6	344.9	337.5	331.3	323.8	316.4	309.7	304.7	299.7	297.2	296.6
162.5°	349.6	342.5	336.0	330.8	324.4	317.9	312.6	308.2	304.2	301.7	302.1
165°	343.1	337.5	333.2	329.5	325.1	319.6	315.8	312.8	309.0	307.8	308.4
167.5°	336.6	333.2	330.3	328.6	325.0	320.9	318.5	316.3	313.9	312.8	313.6
170°	333.2	330.7	328.8	327.6	324.5	321.4	319.6	318.3	316.4	315.8	317.0
172.5°	329.7	327.7	326.9	326.1	324.0	321.9	320.5	319.8	317.9	318.3	319.0
175°	325.1	324.5	323.8	324.5	323.2	322.0	321.4	321.4	320.1	320.8	321.4
177.5°	322.5	322.0	322.5	323.5	322.5	322.0	322.0	322.0	321.0	321.5	322.5
180°	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0



TEST NUMBER: P331689-927

CATALOG NUMBER: S122RDIP-S675D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1170.6	1171.6	1178.1	1180.9	1186.8	1189.0	1191.6	1191.0	1191.0	1192.2	1201.3
5°	1173.1	1181.1	1193.3	1205.0	1216.3	1226.1	1232.6	1239.0	1241.4	1253.2	1263.7
7.5°	1168.9	1183.8	1203.8	1221.7	1243.1	1259.9	1273.7	1286.3	1294.9	1311.9	1329.4
10°	1163.4	1184.4	1207.0	1230.1	1259.6	1281.8	1304.5	1321.9	1327.5	1353.0	1367.6
12.5°	1152.4	1180.5	1209.3	1239.1	1268.0	1298.7	1323.6	1341.0	1360.9	1383.8	1410.6
15°	1135.9	1168.2	1205.9	1244.3	1285.5	1322.7	1349.4	1379.7	1401.5	1426.6	1450.1
17.5°	1112.1	1153.8	1201.7	1246.1	1293.8	1333.8	1370.5	1399.6	1415.0	1429.3	1432.7
20°	1093.4	1138.3	1194.5	1247.1	1294.8	1340.9	1377.3	1401.5	1405.6	1406.0	1384.6
22.5°	1073.0	1123.7	1182.6	1236.4	1293.5	1344.8	1373.1	1383.5	1367.4	1340.0	1298.5
25°	1035.6	1094.2	1162.6	1224.0	1286.3	1334.8	1344.6	1326.4	1270.1	1211.1	1136.3
27.5°	995.0	1060.9	1134.2	1202.5	1268.8	1298.9	1277.9	1212.4	1111.1	1023.1	916.5
30°	965.3	1039.3	1111.2	1187.6	1249.1	1262.0	1213.9	1117.3	999.2	866.6	760.3
32.5°	931.3	1008.8	1087.9	1167.0	1218.4	1205.8	1126.2	1007.3	868.9	738.5	637.9
35°	882.7	962.8	1048.1	1127.4	1160.2	1105.6	986.7	831.8	690.2	568.5	499.4
37.5°	826.7	913.9	1002.6	1075.4	1073.0	982.1	820.1	660.3	541.3	469.3	420.1
40°	786.9	875.0	970.9	1032.4	1006.1	887.6	712.1	561.3	474.4	416.9	380.9
42.5°	748.8	837.2	932.4	981.3	935.6	789.9	615.1	496.9	425.2	380.3	351.2
45°	683.8	777.2	865.4	892.5	810.8	650.2	497.4	411.6	363.9	330.8	310.5
47.5°	620.3	712.2	792.7	793.1	682.6	527.3	419.5	356.2	315.5	289.9	275.1
50°	581.5	668.8	736.3	725.9	600.5	469.1	375.3	320.7	286.7	266.9	251.5
52.5°	537.8	622.6	681.0	651.1	530.9	412.8	335.5	289.6	261.5	244.2	230.5
55°	474.4	549.5	590.8	545.5	433.1	343.3	283.4	247.5	226.5	211.9	200.2
57.5°	411.9	474.0	499.9	447.3	356.7	284.7	239.8	212.8	191.9	181.5	175.4
60°	372.8	425.8	444.0	385.8	310.1	249.1	212.3	187.2	171.8	165.0	158.9
62.5°	334.3	377.6	385.2	331.8	270.4	218.0	186.4	165.2	155.0	148.5	142.8
65°	277.4	308.6	304.9	262.1	213.9	173.1	150.0	137.0	129.4	120.1	110.0
67.5°	228.4	247.4	235.9	203.8	163.3	134.5	119.5	109.6	100.1	91.3	89.0
70°	197.3	208.3	196.1	166.6	133.9	112.8	100.7	89.0	83.3	81.3	77.6
72.5°	167.5	171.3	158.3	132.9	108.9	93.4	81.6	75.0	72.0	70.3	68.0
75°	125.8	122.9	111.6	91.8	75.7	65.1	61.5	59.0	57.0	55.4	54.2
77.5°	88.3	84.2	74.1	61.2	52.7	47.6	45.5	44.1	43.2	42.4	41.2
80°	66.3	63.5	53.4	43.6	40.0	37.6	36.4	34.8	34.8	34.0	32.7
82.5°	48.6	45.4	36.5	32.0	30.0	28.5	27.6	26.7	26.4	26.5	25.7
85°	25.5	20.6	18.2	17.3	16.2	15.4	15.8	15.0	15.0	15.0	14.6
87.5°	8.2	7.1	7.1	7.0	7.7	8.3	8.9	9.6	10.1	9.6	9.8
90°	2.5	5.0	6.2	7.4	9.3	12.4	16.7	20.4	21.1	20.4	19.8
92.5°	10.9	15.4	18.1	22.3	28.1	42.1	61.8	79.4	80.5	68.0	54.0
95°	24.2	30.3	35.9	45.8	60.7	89.2	143.1	214.9	242.7	212.4	162.2
97.5°	38.7	45.2	53.6	65.0	81.8	117.6	192.7	312.1	414.4	434.7	378.6
100°	49.5	55.1	65.0	77.4	94.7	127.5	203.1	336.8	489.2	578.4	565.4
102.5°	60.4	66.0	75.9	88.8	106.2	136.5	203.6	327.5	491.7	631.8	687.8
105°	78.0	82.4	91.7	105.3	122.6	151.7	206.8	309.0	458.8	623.6	752.4
107.5°	95.4	99.6	108.1	121.6	139.1	167.3	215.4	299.8	423.7	569.2	705.8
110°	107.7	111.5	119.5	132.5	150.5	177.7	222.3	297.9	406.9	535.0	665.7



TEST NUMBER: P331689-927

CATALOG NUMBER: S122RDIP-S675D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	118.7	122.9	130.4	142.9	161.4	187.7	229.7	298.3	395.9	511.3	629.1
115°	136.3	140.0	147.3	159.8	176.5	203.1	240.9	301.0	384.0	481.8	583.9
117.5°	153.2	156.9	163.5	175.4	192.7	217.4	252.8	305.4	378.1	463.2	550.0
120°	164.1	167.8	173.4	185.8	203.1	227.3	260.7	308.4	374.6	453.3	533.1
122.5°	174.0	177.7	183.8	196.1	214.0	236.7	267.7	311.9	372.6	444.9	519.8
125°	187.7	191.3	198.8	211.2	228.5	250.8	278.7	317.0	369.1	432.8	500.3
127.5°	199.2	204.4	212.5	224.4	242.2	264.0	288.9	322.4	366.9	421.7	481.2
130°	205.6	211.8	220.5	232.8	250.2	271.9	295.4	326.4	366.0	414.3	468.7
132.5°	212.1	218.7	227.9	240.7	258.1	278.8	301.8	330.3	365.5	408.4	456.9
135°	220.5	227.9	237.2	251.4	268.8	288.6	310.2	335.0	364.7	400.1	440.3
137.5°	229.3	236.8	246.7	260.9	276.9	296.5	316.7	339.2	364.6	394.2	427.1
140°	235.3	242.7	252.6	266.3	282.4	301.0	320.1	341.2	364.1	390.8	418.6
142.5°	241.3	248.2	258.1	271.2	286.4	304.4	323.1	342.7	364.1	387.3	411.7
145°	251.4	257.6	266.9	279.2	292.9	309.7	326.9	344.3	362.9	382.7	401.9
147.5°	261.2	267.1	275.7	286.0	298.1	313.9	329.1	344.8	360.7	378.0	394.3
150°	268.2	273.1	281.1	290.4	301.6	315.8	330.0	344.3	359.2	374.0	388.9
152.5°	274.1	279.0	286.1	294.9	305.1	317.8	330.6	343.3	356.7	370.6	383.4
155°	283.6	287.3	294.1	301.0	310.2	320.8	331.3	341.8	352.4	364.1	375.9
157.5°	291.8	294.8	300.7	306.2	313.9	322.9	331.3	339.0	347.9	358.1	367.1
160°	297.2	299.7	304.7	309.7	316.4	323.8	331.3	337.5	344.9	353.6	361.6
162.5°	301.7	304.2	308.2	312.6	317.9	324.4	330.8	336.0	342.5	349.6	356.2
165°	307.8	309.0	312.8	315.8	319.6	325.1	329.5	333.2	337.5	343.1	348.0
167.5°	312.8	313.9	316.3	318.5	320.9	325.0	328.6	330.3	333.2	336.6	340.2
170°	315.8	316.4	318.3	319.6	321.4	324.5	327.6	328.8	330.7	333.2	336.3
172.5°	318.3	317.9	319.8	320.5	321.9	324.0	326.1	326.9	327.7	329.7	331.8
175°	320.8	320.1	321.4	321.4	322.0	323.2	324.5	323.8	324.5	325.1	326.9
177.5°	321.5	321.0	322.0	322.0	322.0	322.5	323.5	322.5	322.0	322.5	323.5
180°	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0



TEST NUMBER: P331689-927

CATALOG NUMBER: S122RDIP-S675D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1204.5	1208.7	1210.7	1210.7	1213.0	1212.0	1211.0
5°	1273.7	1281.4	1283.1	1290.4	1295.6	1294.0	1294.8
7.5°	1342.6	1354.9	1367.1	1372.8	1373.6	1376.9	1378.1
10°	1385.0	1395.1	1414.1	1411.3	1425.4	1433.5	1420.1
12.5°	1425.8	1439.4	1452.5	1456.2	1464.3	1466.8	1461.6
15°	1462.6	1469.9	1470.7	1468.7	1471.1	1469.1	1461.4
17.5°	1428.1	1416.3	1392.4	1381.1	1372.1	1358.8	1353.5
20°	1371.2	1336.4	1296.0	1279.8	1260.8	1223.6	1232.6
22.5°	1248.3	1208.6	1168.2	1121.0	1098.4	1063.2	1061.0
25°	1057.0	988.7	913.5	860.9	830.2	795.0	779.7
27.5°	821.8	735.8	674.1	642.9	614.6	586.7	585.5
30°	667.2	602.5	554.8	528.1	510.7	499.0	501.5
32.5°	562.4	518.1	485.9	463.7	450.9	442.0	441.9
35°	459.8	429.4	408.8	399.5	390.2	383.7	384.1
37.5°	393.5	375.3	363.8	353.5	347.7	344.5	342.8
40°	359.5	344.5	335.6	329.5	324.7	320.3	319.5
42.5°	332.6	320.3	311.3	306.6	302.1	298.9	298.1
45°	295.2	285.1	277.0	271.7	269.7	266.9	266.9
47.5°	262.6	252.6	246.4	243.0	239.6	237.7	237.6
50°	240.6	232.9	227.3	225.2	222.4	221.2	220.8
52.5°	220.9	215.2	211.1	209.7	208.5	206.9	207.2
55°	194.1	190.8	189.3	188.1	186.0	183.5	185.2
57.5°	171.5	168.8	164.5	160.7	158.8	157.1	157.7
60°	155.7	150.0	144.3	139.9	138.7	135.1	135.1
62.5°	135.6	127.7	120.7	118.3	117.0	115.3	115.0
65°	104.3	101.1	99.5	97.8	97.0	97.0	96.3
67.5°	86.4	85.2	83.4	82.9	82.1	81.9	81.7
70°	76.4	74.8	74.0	73.6	72.8	73.2	72.0
72.5°	66.7	65.4	65.3	64.2	63.7	63.8	62.9
75°	52.6	52.6	52.1	51.7	50.9	50.5	50.9
77.5°	40.4	40.5	39.8	39.7	39.6	39.7	39.3
80°	32.3	32.7	32.3	31.9	31.5	31.9	31.5
82.5°	25.6	25.0	24.9	24.8	24.7	24.5	24.4
85°	14.6	15.0	14.6	14.2	14.2	14.2	14.6
87.5°	9.2	9.4	9.6	9.6	9.6	9.6	9.3
90°	18.6	19.8	20.4	20.4	20.4	20.4	20.4
92.5°	46.3	41.1	37.3	36.8	34.8	35.3	34.3
95°	124.5	98.5	84.8	76.8	71.9	69.9	70.6
97.5°	309.7	242.7	198.0	168.4	153.2	144.2	138.9
100°	488.6	403.8	328.8	277.4	250.8	232.8	221.7
102.5°	670.4	608.3	528.9	473.1	427.6	405.2	390.1
105°	822.4	830.4	810.0	771.6	733.2	706.5	697.9
107.5°	811.2	875.6	905.6	910.5	908.3	903.0	891.4
110°	776.6	855.8	906.6	933.2	945.0	950.5	949.9



TEST NUMBER: P331689-927

CATALOG NUMBER: S122RDIP-S675D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	735.4	820.1	878.4	915.4	935.1	945.6	949.0
115°	679.3	760.4	824.2	868.2	896.7	912.8	918.4
117.5°	633.7	707.3	767.1	812.0	842.1	859.0	863.7
120°	610.0	675.6	732.0	775.3	804.4	822.4	828.5
122.5°	590.2	652.3	703.2	742.1	770.7	786.7	791.9
125°	564.1	618.6	665.0	701.0	724.5	740.0	745.0
127.5°	538.8	590.3	633.1	664.5	686.5	699.9	703.9
130°	522.0	570.9	611.8	642.1	663.2	675.6	680.6
132.5°	506.2	551.1	589.5	619.4	640.4	651.8	656.2
135°	481.2	522.0	556.7	583.4	603.8	614.9	617.4
137.5°	461.2	493.7	523.9	548.2	565.8	575.5	579.2
140°	448.4	476.8	504.1	523.9	540.0	549.3	553.0
142.5°	437.0	461.4	484.3	503.1	517.7	526.0	526.7
145°	422.3	441.6	459.5	474.4	484.9	491.1	492.9
147.5°	410.4	425.4	438.6	450.8	459.2	463.4	464.5
150°	402.5	415.5	426.7	435.9	443.4	447.1	447.7
152.5°	396.1	407.1	416.8	424.1	430.5	433.2	433.3
155°	385.8	395.1	401.9	408.7	413.0	415.5	414.3
157.5°	375.4	383.2	388.5	393.3	397.0	398.1	398.1
160°	368.4	375.3	379.6	384.0	387.1	387.6	387.6
162.5°	362.0	367.8	371.2	375.5	377.6	378.3	377.7
165°	352.4	356.7	359.2	361.6	364.1	364.1	363.5
167.5°	343.6	346.5	348.8	349.9	351.3	351.1	350.4
170°	338.1	340.6	341.8	342.5	344.3	343.6	342.5
172.5°	333.2	335.2	335.9	336.5	337.4	336.8	336.0
175°	327.6	328.2	328.8	328.8	329.5	328.8	327.6
177.5°	323.5	324.0	324.0	324.0	324.0	323.5	322.5
180°	322.0	322.0	322.0	322.0	322.0	322.0	322.0

(END OF REPORT)