

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331731-927

Luminaire Tested: **S122RDIP-S865D1080U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331731-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S865D1080U927-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5948.6 lumens
Efficiency: N/A
Efficacy: 91.0 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331731-927

CATALOG NUMBER: S122RDIP-S865D1080U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331731-927

CATALOG NUMBER: S122RDIP-S865D1080U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	97	93	89	86	89	85	82	80	71	69	67	58	56	55	46	45	44	38
2	89	82	76	72	81	75	71	66	63	60	57	52	49	47	41	40	38	33
3	82	73	66	61	75	67	61	56	56	52	48	46	43	41	37	35	33	29
4	75	65	58	52	69	60	54	49	51	46	42	42	38	36	34	31	29	26
5	69	58	51	45	63	54	47	42	46	41	37	38	34	31	31	28	26	23
6	64	53	45	39	59	49	42	37	41	36	32	35	31	28	28	26	23	21
7	59	48	40	35	54	44	38	33	38	33	29	32	28	25	26	23	21	19
8	55	44	36	31	51	40	34	29	35	30	26	29	25	23	24	21	19	17
9	52	40	33	28	47	37	31	26	32	27	23	27	23	21	22	20	18	16
10	48	37	30	25	44	34	28	24	30	25	21	25	21	19	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	24425	24425	24425	24425
5°	27279	24577	21793	24577
10°	30263	24405	18889	24405
15°	31753	24047	14883	24047
20°	27527	23517	12880	23517
25°	18054	22792	11500	22792
30°	12152	21912	10407	21912
35°	9841	20802	9386	20802
40°	8753	19597	8686	19597
45°	7921	18182	7752	18182
50°	7209	16779	7181	16779
55°	6776	15226	6688	15226
60°	5667	13798	5603	13798
65°	4779	12531	5421	12531
70°	4419	11188	5113	11188
75°	4130	9738	4722	9738
80°	3812	8015	4203	8015
85°	3501	6317	3705	6317



TEST NUMBER: P331731-927

CATALOG NUMBER: S122RDIP-S865D1080U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.4	2.4
10°-20°	399.6	6.7
20°-30°	514.9	8.7
30°-40°	489.3	8.2
40°-50°	419.2	7.0
50°-60°	319.2	5.4
60°-70°	201.8	3.4
70°-80°	100.8	1.7
80°-90°	30.5	0.5
90°-100°	191.3	3.2
100°-110°	649.3	10.9
110°-120°	689.8	11.6
120°-130°	567.8	9.5
130°-140°	456.0	7.7
140°-150°	344.6	5.8
150°-160°	242.2	4.1
160°-170°	142.6	2.4
170°-180°	46.4	0.8
0°-30°	1057.9	17.8
0°-40°	1547.2	26.0
0°-60°	2285.6	38.4
0°-90°	2618.6	44.0
90°-120°	1530.4	25.7
90°-150°	2898.8	48.7
90°-180°	3330.0	56.0
0°-180°	5948.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1513	1513	1513	1513	1513	
5°	1683	1516	1345	1516	1683	166
15°	1900	1439	890	1439	1900	512
25°	1013	1279	646	1279	1013	481
35°	499	1055	476	1055	499	319
45°	347	796	340	796	347	269
55°	241	541	238	541	241	211
65°	125	328	142	328	125	127
75°	66	156	76	156	66	70
85°	19	34	20	34	19	21
90°	30	1	30	1	30	17
95°	105	32	105	32	105	136
105°	1037	112	1037	112	1037	1003
115°	1365	198	1365	198	1365	1336
125°	1107	276	1107	276	1107	1000
135°	918	324	918	324	918	713
145°	732	370	732	370	732	465
155°	616	421	616	421	616	287
165°	540	458	540	458	540	154
175°	487	478	487	478	487	47
180°	479	479	479	479	479	



TEST NUMBER: P331731-927

CATALOG NUMBER: S122RDIP-S865D1080U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8
2.5°	1574.1	1575.4	1576.7	1573.7	1573.7	1571.2	1565.7	1561.5	1549.7	1548.1	1548.1
5°	1683.1	1682.0	1684.1	1677.3	1667.8	1665.7	1655.7	1642.6	1628.9	1613.7	1610.5
7.5°	1791.3	1789.7	1785.5	1784.4	1777.1	1761.3	1745.2	1728.1	1705.3	1683.1	1672.0
10°	1845.9	1863.3	1852.8	1834.4	1838.1	1813.4	1800.2	1777.7	1758.7	1725.6	1718.2
12.5°	1899.8	1906.6	1903.3	1892.8	1888.2	1871.0	1853.2	1833.6	1798.6	1768.9	1743.0
15°	1899.6	1909.6	1912.2	1909.1	1911.7	1910.7	1901.2	1884.8	1854.4	1821.8	1793.4
17.5°	1759.4	1766.3	1783.5	1795.2	1809.9	1841.0	1856.4	1862.3	1857.8	1839.2	1819.2
20°	1602.1	1590.5	1638.9	1663.6	1684.6	1737.2	1782.4	1799.8	1827.6	1827.1	1821.8
22.5°	1379.2	1382.0	1427.8	1457.1	1518.5	1571.1	1622.6	1687.9	1741.8	1777.4	1798.3
25°	1013.4	1033.4	1079.1	1119.0	1187.4	1285.2	1374.0	1477.0	1574.2	1651.0	1724.0
27.5°	761.1	762.6	798.8	835.8	876.3	956.4	1068.3	1191.3	1329.9	1444.3	1575.9
30°	651.8	648.6	663.8	686.4	721.1	783.2	867.3	988.2	1126.4	1298.8	1452.3
32.5°	574.4	574.6	586.1	602.8	631.6	673.4	731.0	829.3	959.9	1129.3	1309.3
35°	499.3	498.8	507.2	519.3	531.4	558.2	597.6	649.1	739.0	897.2	1081.2
37.5°	445.5	447.8	451.9	459.5	472.9	487.7	511.4	546.1	610.1	703.6	858.3
40°	415.3	416.3	422.1	428.4	436.3	447.8	467.3	495.1	541.9	616.6	729.5
42.5°	387.5	388.6	392.6	398.5	404.7	416.3	432.4	456.5	494.4	552.6	645.9
45°	346.9	346.9	350.6	353.2	360.0	370.6	383.7	403.7	429.9	473.1	535.1
47.5°	308.9	309.0	311.4	315.9	320.2	328.4	341.4	357.7	376.8	410.1	463.1
50°	287.0	287.5	289.1	292.8	295.4	302.8	312.8	326.9	346.9	372.6	416.8
52.5°	269.3	269.0	271.0	272.6	274.4	279.6	287.1	299.6	317.5	339.8	376.4
55°	240.7	238.6	241.8	244.4	246.0	248.1	252.3	260.2	275.4	294.4	321.7
57.5°	205.0	204.1	206.4	208.7	213.7	219.4	223.0	228.0	235.9	249.5	276.6
60°	175.5	175.5	180.3	181.9	187.7	195.0	202.4	206.6	214.4	223.4	243.4
62.5°	149.5	149.9	152.1	153.7	156.9	166.0	176.3	185.5	193.0	201.5	214.8
65°	125.1	126.1	126.1	127.2	129.3	131.4	135.6	143.0	156.1	168.2	178.2
67.5°	106.2	106.5	106.8	107.9	108.4	110.7	112.4	115.7	118.7	130.2	142.5
70°	93.6	95.1	94.6	95.7	96.2	97.2	99.3	100.9	105.7	108.3	115.7
72.5°	81.8	82.9	82.9	83.5	84.8	85.1	86.7	88.3	91.3	93.6	97.5
75°	66.2	65.7	66.2	67.3	67.8	68.4	68.4	70.4	72.0	74.1	76.8
77.5°	51.1	51.7	51.5	51.7	51.7	52.7	52.6	53.5	55.1	56.2	57.4
80°	41.0	41.5	41.0	41.5	42.1	42.5	42.1	42.5	44.1	45.2	45.2
82.5°	31.8	31.8	32.2	32.2	32.4	32.5	33.2	33.4	34.5	34.3	34.7
85°	18.9	18.4	18.4	18.4	18.9	19.4	18.9	18.9	19.4	19.4	19.4
87.5°	12.8	13.2	13.2	13.2	13.2	13.1	12.7	13.5	13.2	13.9	13.2
90°	30.3	30.3	30.3	30.3	30.3	29.5	27.6	29.5	30.3	31.3	30.3
92.5°	51.0	52.4	51.7	54.7	55.4	61.1	68.8	80.2	101.1	119.6	118.0
95°	104.9	104.0	106.8	114.1	126.0	146.3	185.0	241.1	315.7	360.8	319.3
97.5°	206.5	214.2	227.7	250.3	294.3	360.8	460.3	562.6	646.0	615.8	463.8
100°	329.5	346.0	372.7	412.3	488.6	600.0	726.1	840.2	859.5	727.0	500.6
102.5°	579.8	602.2	635.6	703.1	786.1	904.0	996.2	1022.1	939.1	730.7	486.6
105°	1037.1	1050.0	1089.6	1146.6	1203.7	1234.1	1222.1	1118.1	926.7	681.9	459.2
107.5°	1324.8	1341.9	1349.8	1353.0	1345.8	1301.2	1205.5	1048.9	845.9	629.6	445.6
110°	1411.7	1412.6	1404.3	1386.8	1347.3	1271.8	1154.0	989.3	795.1	604.6	442.7



TEST NUMBER: P331731-927

CATALOG NUMBER: S122RDIP-S865D1080U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1410.2	1405.3	1389.6	1360.3	1305.3	1218.8	1092.9	934.8	759.8	588.4	443.4
115°	1364.8	1356.5	1332.5	1290.2	1224.9	1130.0	1009.6	867.8	716.0	570.5	447.3
117.5°	1283.6	1276.6	1251.3	1206.7	1140.0	1051.1	941.8	817.4	688.3	561.9	453.8
120°	1231.3	1222.1	1195.4	1152.1	1087.7	1004.0	906.4	792.3	673.6	556.7	458.3
122.5°	1176.8	1169.1	1145.3	1102.8	1045.0	969.4	877.0	772.5	661.1	553.8	463.4
125°	1107.1	1099.7	1076.7	1041.7	988.3	919.3	838.4	743.5	643.3	548.5	471.2
127.5°	1046.0	1040.1	1020.2	987.5	940.9	877.2	800.8	715.0	626.7	545.3	479.1
130°	1011.4	1004.0	985.6	954.3	909.2	848.5	775.8	696.6	615.7	543.8	485.0
132.5°	975.3	968.7	951.7	920.4	876.1	819.0	752.3	679.0	606.8	543.1	490.8
135°	917.5	913.8	897.2	866.9	827.3	775.8	715.0	654.3	594.5	542.0	497.9
137.5°	860.8	855.3	840.7	814.6	778.6	733.6	685.4	634.6	585.8	541.9	504.1
140°	821.8	816.3	802.5	778.6	749.1	708.6	666.3	622.1	580.7	541.1	507.1
142.5°	782.8	781.6	769.4	747.6	719.6	685.8	649.4	611.8	575.5	541.1	509.3
145°	732.5	729.8	720.6	704.9	682.9	656.2	627.6	597.2	568.7	539.2	511.7
147.5°	690.4	688.7	682.5	669.9	651.7	632.2	610.0	586.1	561.7	536.0	512.4
150°	665.4	664.4	658.9	647.8	634.1	617.5	598.2	577.9	555.8	533.8	511.7
152.5°	644.0	643.8	639.8	630.2	619.3	605.0	588.6	569.8	550.6	530.0	510.2
155°	615.7	617.5	613.8	607.4	597.2	587.1	573.3	558.6	541.1	523.6	507.9
157.5°	591.5	591.5	589.9	584.6	577.3	569.4	557.9	545.5	532.1	517.0	503.7
160°	576.1	576.1	575.1	570.5	564.1	557.7	547.6	537.4	525.5	512.6	501.5
162.5°	561.3	562.1	561.2	558.0	551.6	546.6	538.0	529.3	519.6	508.9	499.3
165°	540.2	541.1	541.1	537.4	533.8	530.0	523.6	517.2	509.8	501.5	495.1
167.5°	520.7	521.8	522.0	519.9	518.3	515.0	510.6	505.6	500.3	495.1	490.8
170°	508.9	510.7	511.7	508.9	507.9	506.1	502.5	499.7	495.1	491.4	488.6
172.5°	499.3	500.4	501.4	500.1	499.2	498.0	495.1	493.1	490.0	487.0	485.7
175°	486.8	488.6	489.6	488.6	488.6	487.7	486.8	485.9	483.2	482.2	481.3
177.5°	479.3	480.8	481.5	481.5	481.5	481.5	480.8	480.8	479.3	478.6	479.3
180°	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6



TEST NUMBER: P331731-927

CATALOG NUMBER: S122RDIP-S865D1080U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8
2.5°	1548.9	1545.5	1542.6	1535.0	1531.2	1522.8	1521.5	1521.1	1510.2	1499.7	1496.7
5°	1602.1	1593.7	1581.0	1566.4	1551.1	1535.3	1524.8	1516.4	1495.4	1475.4	1463.9
7.5°	1655.7	1637.6	1615.9	1588.0	1564.8	1538.7	1519.3	1502.0	1472.2	1443.6	1424.3
10°	1695.7	1666.2	1637.3	1598.9	1569.0	1539.5	1512.2	1488.6	1454.9	1417.1	1390.3
12.5°	1720.5	1688.1	1648.2	1610.7	1571.9	1534.5	1497.9	1467.5	1428.0	1388.9	1357.0
15°	1754.0	1719.3	1671.0	1617.3	1567.4	1518.5	1476.5	1438.6	1387.1	1340.3	1301.4
17.5°	1781.5	1733.7	1681.8	1619.8	1561.9	1499.8	1445.7	1397.3	1340.0	1283.6	1237.7
20°	1790.3	1743.0	1683.1	1621.0	1552.7	1479.6	1421.3	1368.7	1307.2	1245.7	1193.2
22.5°	1784.8	1748.0	1681.3	1607.1	1537.2	1460.7	1394.8	1333.8	1265.6	1202.8	1141.9
25°	1747.7	1735.0	1672.0	1591.0	1511.2	1422.4	1346.1	1279.4	1201.6	1134.3	1068.0
27.5°	1661.2	1688.4	1649.3	1563.1	1474.3	1379.0	1293.3	1217.3	1136.6	1060.9	994.9
30°	1577.9	1640.5	1623.7	1543.7	1444.4	1350.8	1254.7	1175.3	1089.1	1011.3	946.1
32.5°	1464.0	1567.3	1583.7	1516.9	1414.1	1311.3	1210.5	1131.6	1041.6	959.6	896.0
35°	1282.5	1437.0	1508.0	1465.5	1362.4	1251.5	1147.4	1055.4	965.0	884.1	821.0
37.5°	1066.0	1276.5	1394.8	1397.8	1303.2	1187.9	1074.6	983.3	890.7	811.3	743.0
40°	925.6	1153.7	1307.7	1341.9	1262.0	1137.4	1022.9	929.8	839.4	761.6	683.3
42.5°	799.5	1026.7	1216.1	1275.5	1212.0	1088.2	973.3	876.0	788.1	714.5	634.5
45°	646.5	845.2	1053.8	1160.1	1124.8	1010.3	888.8	796.3	713.8	650.2	573.5
47.5°	545.4	685.4	887.3	1030.9	1030.3	925.7	806.3	717.7	641.1	581.5	519.4
50°	487.7	609.7	780.5	943.5	957.1	869.3	755.8	668.0	596.6	534.0	484.1
52.5°	436.0	536.5	690.1	846.4	885.3	809.2	699.1	618.1	548.7	491.2	448.4
55°	368.4	446.2	562.9	709.1	767.9	714.3	616.6	540.9	484.7	436.3	399.5
57.5°	311.7	370.0	463.7	581.3	649.9	616.2	535.5	474.0	425.9	382.1	353.1
60°	275.9	323.8	403.1	501.5	577.1	553.5	484.7	427.3	386.3	348.5	321.2
62.5°	242.3	283.4	351.4	431.2	500.6	490.8	434.6	386.5	350.6	316.1	292.9
65°	195.0	225.0	278.1	340.6	396.3	401.1	360.6	328.0	296.0	268.6	248.1
67.5°	155.3	174.8	212.2	264.9	306.7	321.5	296.8	272.0	246.5	225.4	207.6
70°	130.9	146.6	174.0	216.6	254.9	270.7	256.5	237.0	215.0	197.6	182.4
72.5°	106.1	121.4	141.6	172.9	205.7	222.8	217.9	203.8	185.9	171.6	157.2
75°	79.9	84.6	98.3	119.3	145.0	159.8	163.5	156.1	141.9	130.9	122.5
77.5°	59.1	61.9	68.4	79.5	96.3	109.4	114.8	113.9	104.2	97.8	89.9
80°	47.3	48.9	52.0	56.8	69.4	82.5	86.2	86.2	79.4	76.8	68.8
82.5°	36.0	37.1	39.0	41.6	47.5	58.9	63.1	63.9	59.6	56.2	49.9
85°	20.5	20.0	21.0	22.6	23.7	26.8	33.1	34.1	33.1	28.9	27.3
87.5°	12.1	11.2	10.3	9.3	9.4	9.4	10.9	12.4	11.2	10.7	10.2
90°	24.9	18.4	13.8	11.0	9.2	7.4	3.6	1.0	3.6	7.4	9.2
92.5°	91.8	62.6	41.7	33.1	26.9	22.8	16.2	11.2	16.2	22.8	26.9
95°	212.5	132.5	90.2	68.1	53.4	45.1	35.9	32.2	35.9	45.1	53.4
97.5°	286.4	174.8	121.7	96.6	79.7	67.2	57.4	52.4	57.4	67.2	79.7
100°	301.8	189.6	140.8	115.0	96.6	81.9	73.6	70.8	73.6	81.9	96.6
102.5°	302.6	202.8	157.7	132.0	112.8	98.1	89.8	87.8	89.8	98.1	112.8
105°	307.4	225.5	182.2	156.5	136.2	122.4	116.0	112.3	116.0	122.4	136.2
107.5°	320.0	248.7	206.7	180.8	160.7	148.0	141.7	138.8	141.7	148.0	160.7
110°	330.3	264.1	223.6	196.9	177.6	165.6	160.1	156.5	160.1	165.6	177.6



TEST NUMBER: P331731-927

CATALOG NUMBER: S122RDIP-S865D1080U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	341.4	278.8	239.8	212.4	193.8	182.6	176.3	172.6	176.3	182.6	193.8
115°	358.0	301.8	262.3	237.4	219.0	207.9	202.5	197.9	202.5	207.9	219.0
117.5°	375.7	323.0	286.4	260.6	243.0	233.2	227.7	224.0	227.7	233.2	243.0
120°	387.5	337.7	301.8	276.1	257.7	249.4	243.8	240.2	243.8	249.4	257.7
122.5°	397.8	351.7	318.1	291.5	273.1	264.1	258.6	255.6	258.6	264.1	273.1
125°	414.2	372.7	339.6	313.8	295.4	284.4	278.8	276.1	278.8	284.4	295.4
127.5°	429.4	392.2	360.0	333.5	315.8	303.7	296.0	292.2	296.0	303.7	315.8
130°	438.9	404.0	371.8	346.0	327.6	314.7	305.5	301.8	305.5	314.7	327.6
132.5°	448.5	414.3	383.6	357.8	338.7	325.0	315.1	310.7	315.1	325.0	338.7
135°	461.1	428.8	399.4	373.6	352.4	338.7	327.6	323.9	327.6	338.7	352.4
137.5°	470.6	440.6	411.5	387.6	366.6	351.9	340.9	336.4	340.9	351.9	366.6
140°	475.8	447.3	419.6	395.7	375.5	360.8	349.7	346.0	349.7	360.8	375.5
142.5°	480.2	452.4	425.6	403.1	383.6	368.8	358.5	355.6	358.5	368.8	383.6
145°	485.9	460.1	435.3	415.0	396.6	382.9	373.6	369.9	373.6	382.9	396.6
147.5°	489.0	466.4	443.0	425.0	409.7	397.0	388.2	385.4	388.2	397.0	409.7
150°	490.5	469.4	448.1	431.6	417.8	405.8	398.5	395.7	398.5	405.8	417.8
152.5°	491.2	472.3	453.3	438.2	425.2	414.6	407.3	406.0	407.3	414.6	425.2
155°	492.3	476.7	461.1	447.3	437.1	427.0	421.4	420.6	421.4	427.0	437.1
157.5°	492.3	479.8	466.6	455.0	446.9	438.1	433.6	432.7	433.6	438.1	446.9
160°	492.3	481.3	470.2	460.1	452.7	445.4	441.7	440.8	441.7	445.4	452.7
162.5°	491.6	482.0	472.5	464.5	457.9	452.0	448.4	448.9	448.4	452.0	457.9
165°	489.6	483.2	474.8	469.4	464.7	459.2	457.4	458.3	457.4	459.2	464.7
167.5°	488.3	482.9	476.9	473.4	470.1	466.6	464.9	466.0	464.9	466.6	470.1
170°	486.8	482.2	477.6	474.8	473.0	470.2	469.4	471.2	469.4	470.2	473.0
172.5°	484.6	481.5	478.3	476.3	475.2	472.5	473.0	474.1	473.0	472.5	475.2
175°	482.2	480.4	478.6	477.6	477.6	475.8	476.7	477.6	476.7	475.8	477.6
177.5°	480.8	479.3	478.6	478.6	478.6	477.1	477.8	479.3	477.8	477.1	478.6
180°	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6



TEST NUMBER: P331731-927

CATALOG NUMBER: S122RDIP-S865D1080U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8
2.5°	1491.3	1488.4	1482.9	1474.5	1469.4	1460.6	1454.7	1458.1	1458.9	1458.1	1457.2
5°	1451.2	1440.2	1425.0	1410.2	1396.5	1381.9	1373.4	1369.8	1362.4	1358.2	1356.1
7.5°	1402.8	1383.8	1362.2	1336.6	1314.8	1292.0	1280.3	1274.5	1259.5	1251.3	1244.1
10°	1366.6	1336.6	1315.1	1281.4	1261.0	1231.0	1210.5	1211.0	1190.5	1178.9	1170.5
12.5°	1326.7	1293.8	1257.9	1227.6	1199.1	1175.0	1150.4	1140.3	1118.6	1107.5	1084.7
15°	1260.4	1222.1	1184.2	1143.2	1114.3	1077.0	1041.2	997.6	962.4	931.9	923.5
17.5°	1188.1	1140.6	1102.6	1054.5	1005.0	942.2	900.8	875.4	854.2	838.1	826.2
20°	1138.5	1090.1	1049.6	977.2	910.4	867.8	837.3	817.8	795.8	778.5	769.0
22.5°	1086.3	1035.9	980.7	899.8	847.7	813.6	786.4	764.1	749.1	735.5	726.9
25°	1012.3	957.1	866.3	810.5	768.4	732.7	713.8	700.1	684.4	666.0	657.5
27.5°	934.1	846.4	781.1	739.7	699.5	676.3	659.3	638.8	624.7	616.5	607.7
30°	875.7	787.9	736.9	691.7	663.3	637.5	617.6	606.0	592.4	578.2	572.4
32.5°	810.5	740.4	691.5	653.9	625.0	603.1	587.3	568.6	558.7	550.0	537.9
35°	729.5	676.4	631.8	601.3	574.0	556.1	537.7	526.6	508.8	501.5	496.7
37.5°	661.0	615.0	581.6	549.5	527.8	508.0	496.8	479.3	471.5	461.3	451.3
40°	622.3	577.1	545.1	518.8	494.6	479.9	465.7	451.5	440.0	435.2	423.1
42.5°	582.8	546.1	514.0	485.1	469.0	453.4	435.5	425.0	413.0	405.4	397.9
45°	528.2	495.7	468.3	444.7	426.8	410.5	398.9	381.6	374.8	359.5	353.2
47.5°	480.3	450.0	424.0	401.5	384.0	373.4	356.5	342.9	332.0	322.7	314.5
50°	446.2	421.0	395.8	375.8	360.0	344.8	327.5	320.6	303.8	299.0	294.4
52.5°	415.1	391.2	368.0	348.5	332.7	317.9	302.6	293.7	282.3	277.7	274.2
55°	371.6	348.5	326.4	309.0	293.3	278.1	268.6	257.5	252.3	248.6	244.4
57.5°	327.9	307.0	290.2	272.6	256.7	244.6	233.7	227.0	221.6	216.7	211.8
60°	300.2	280.1	264.9	248.6	232.3	222.4	213.9	206.0	199.7	192.3	190.3
62.5°	270.7	253.3	239.2	223.4	209.2	200.0	192.0	184.6	177.1	166.3	163.3
65°	230.2	216.6	201.8	188.7	176.1	167.2	155.6	147.2	144.0	143.0	142.4
67.5°	193.6	180.7	168.1	154.6	143.1	134.9	129.0	127.7	125.5	124.8	123.4
70°	169.2	157.2	144.6	131.9	120.9	119.3	117.2	115.1	112.5	111.5	110.4
72.5°	147.3	134.9	122.2	112.2	107.4	105.4	103.3	101.2	99.4	98.4	97.8
75°	113.0	101.5	93.0	89.4	86.7	85.2	82.0	80.4	79.4	77.8	77.2
77.5°	81.4	74.9	71.0	68.7	65.9	64.2	62.4	60.8	59.7	59.4	58.5
80°	62.0	58.9	56.2	53.1	52.0	49.9	49.4	47.8	48.3	46.8	46.8
82.5°	48.2	44.1	41.9	40.5	39.5	37.7	37.2	36.4	36.6	35.4	35.4
85°	24.7	23.7	22.6	21.5	21.5	20.0	20.5	20.0	20.0	18.9	18.4
87.5°	10.2	10.3	10.4	11.7	12.8	12.6	12.4	11.8	11.4	11.8	11.6
90°	11.0	13.8	18.4	24.9	30.3	31.3	30.3	29.5	27.6	29.5	30.3
92.5°	33.1	41.7	62.6	91.8	118.0	119.6	101.1	80.2	68.8	61.1	55.4
95°	68.1	90.2	132.5	212.5	319.3	360.8	315.7	241.1	185.0	146.3	126.0
97.5°	96.6	121.7	174.8	286.4	463.8	615.8	646.0	562.6	460.3	360.8	294.3
100°	115.0	140.8	189.6	301.8	500.6	727.0	859.5	840.2	726.1	600.0	488.6
102.5°	132.0	157.7	202.8	302.6	486.6	730.7	939.1	1022.1	996.2	904.0	786.1
105°	156.5	182.2	225.5	307.4	459.2	681.9	926.7	1118.1	1222.1	1234.1	1203.7
107.5°	180.8	206.7	248.7	320.0	445.6	629.6	845.9	1048.9	1205.5	1301.2	1345.8
110°	196.9	223.6	264.1	330.3	442.7	604.6	795.1	989.3	1154.0	1271.8	1347.3



TEST NUMBER: P331731-927

CATALOG NUMBER: S122RDIP-S865D1080U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	212.4	239.8	278.8	341.4	443.4	588.4	759.8	934.8	1092.9	1218.8	1305.3
115°	237.4	262.3	301.8	358.0	447.3	570.5	716.0	867.8	1009.6	1130.0	1224.9
117.5°	260.6	286.4	323.0	375.7	453.8	561.9	688.3	817.4	941.8	1051.1	1140.0
120°	276.1	301.8	337.7	387.5	458.3	556.7	673.6	792.3	906.4	1004.0	1087.7
122.5°	291.5	318.1	351.7	397.8	463.4	553.8	661.1	772.5	877.0	969.4	1045.0
125°	313.8	339.6	372.7	414.2	471.2	548.5	643.3	743.5	838.4	919.3	988.3
127.5°	333.5	360.0	392.2	429.4	479.1	545.3	626.7	715.0	800.8	877.2	940.9
130°	346.0	371.8	404.0	438.9	485.0	543.8	615.7	696.6	775.8	848.5	909.2
132.5°	357.8	383.6	414.3	448.5	490.8	543.1	606.8	679.0	752.3	819.0	876.1
135°	373.6	399.4	428.8	461.1	497.9	542.0	594.5	654.3	715.0	775.8	827.3
137.5°	387.6	411.5	440.6	470.6	504.1	541.9	585.8	634.6	685.4	733.6	778.6
140°	395.7	419.6	447.3	475.8	507.1	541.1	580.7	622.1	666.3	708.6	749.1
142.5°	403.1	425.6	452.4	480.2	509.3	541.1	575.5	611.8	649.4	685.8	719.6
145°	415.0	435.3	460.1	485.9	511.7	539.2	568.7	597.2	627.6	656.2	682.9
147.5°	425.0	443.0	466.4	489.0	512.4	536.0	561.7	586.1	610.0	632.2	651.7
150°	431.6	448.1	469.4	490.5	511.7	533.8	555.8	577.9	598.2	617.5	634.1
152.5°	438.2	453.3	472.3	491.2	510.2	530.0	550.6	569.8	588.6	605.0	619.3
155°	447.3	461.1	476.7	492.3	507.9	523.6	541.1	558.6	573.3	587.1	597.2
157.5°	455.0	466.6	479.8	492.3	503.7	517.0	532.1	545.5	557.9	569.4	577.3
160°	460.1	470.2	481.3	492.3	501.5	512.6	525.5	537.4	547.6	557.7	564.1
162.5°	464.5	472.5	482.0	491.6	499.3	508.9	519.6	529.3	538.0	546.6	551.6
165°	469.4	474.8	483.2	489.6	495.1	501.5	509.8	517.2	523.6	530.0	533.8
167.5°	473.4	476.9	482.9	488.3	490.8	495.1	500.3	505.6	510.6	515.0	518.3
170°	474.8	477.6	482.2	486.8	488.6	491.4	495.1	499.7	502.5	506.1	507.9
172.5°	476.3	478.3	481.5	484.6	485.7	487.0	490.0	493.1	495.1	498.0	499.2
175°	477.6	478.6	480.4	482.2	481.3	482.2	483.2	485.9	486.8	487.7	488.6
177.5°	478.6	478.6	479.3	480.8	479.3	478.6	479.3	480.8	480.8	481.5	481.5
180°	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6



TEST NUMBER: P331731-927

CATALOG NUMBER: S122RDIP-S865D1080U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8
2.5°	1452.6	1453.4	1452.1	1453.0	1452.1	1453.4	1452.6	1457.2	1458.1	1458.9	1458.1
5°	1353.4	1347.2	1346.1	1344.6	1346.1	1347.2	1353.4	1356.1	1358.2	1362.4	1369.8
7.5°	1235.1	1234.1	1231.5	1227.9	1231.5	1234.1	1235.1	1244.1	1251.3	1259.5	1274.5
10°	1159.0	1156.3	1155.9	1152.1	1155.9	1156.3	1159.0	1170.5	1178.9	1190.5	1211.0
12.5°	1069.8	1052.9	1051.1	1042.0	1051.1	1052.9	1069.8	1084.7	1107.5	1118.6	1140.3
15°	910.9	907.8	897.2	890.4	897.2	907.8	910.9	923.5	931.9	962.4	997.6
17.5°	820.1	809.8	806.5	805.0	806.5	809.8	820.1	826.2	838.1	854.2	875.4
20°	761.6	752.2	750.6	749.6	750.6	752.2	761.6	769.0	778.5	795.8	817.8
22.5°	721.3	711.4	707.3	704.1	707.3	711.4	721.3	726.9	735.5	749.1	764.1
25°	652.3	648.6	646.5	645.5	646.5	648.6	652.3	657.5	666.0	684.4	700.1
27.5°	598.3	590.3	588.7	586.0	588.7	590.3	598.3	607.7	616.5	624.7	638.8
30°	567.7	565.1	561.3	558.2	561.3	565.1	567.7	572.4	578.2	592.4	606.0
32.5°	531.5	529.3	526.0	524.6	526.0	529.3	531.5	537.9	550.0	558.7	568.6
35°	491.5	484.1	480.9	476.2	480.9	484.1	491.5	496.7	501.5	508.8	526.6
37.5°	449.1	445.2	440.8	442.4	440.8	445.2	449.1	451.3	461.3	471.5	479.3
40°	416.3	413.7	412.6	412.1	412.6	413.7	416.3	423.1	435.2	440.0	451.5
42.5°	390.2	382.9	380.2	380.1	380.2	382.9	390.2	397.9	405.4	413.0	425.0
45°	350.6	343.7	339.1	339.5	339.1	343.7	350.6	353.2	359.5	374.8	381.6
47.5°	310.0	309.8	306.9	307.8	306.9	309.8	310.0	314.5	322.7	332.0	342.9
50°	290.7	287.5	285.4	285.9	285.4	287.5	290.7	294.4	299.0	303.8	320.6
52.5°	272.2	269.4	267.8	270.0	267.8	269.4	272.2	274.2	277.7	282.3	293.7
55°	241.8	238.6	238.1	237.6	238.1	238.6	241.8	244.4	248.6	252.3	257.5
57.5°	207.9	205.7	202.6	201.2	202.6	205.7	207.9	211.8	216.7	221.6	227.0
60°	183.5	179.3	174.0	173.5	174.0	179.3	183.5	190.3	192.3	199.7	206.0
62.5°	161.1	160.3	159.2	159.1	159.2	160.3	161.1	163.3	166.3	177.1	184.6
65°	141.4	140.9	141.4	141.9	141.4	140.9	141.4	142.4	143.0	144.0	147.2
67.5°	123.2	122.2	121.3	121.8	121.3	122.2	123.2	123.4	124.8	125.5	127.7
70°	109.3	108.8	108.3	108.3	108.3	108.8	109.3	110.4	111.5	112.5	115.1
72.5°	95.9	95.8	95.2	94.8	95.2	95.8	95.9	97.8	98.4	99.4	101.2
75°	76.8	75.7	75.7	75.7	75.7	75.7	76.8	77.2	77.8	79.4	80.4
77.5°	58.5	57.9	57.4	57.0	57.4	57.9	58.5	58.5	59.4	59.7	60.8
80°	46.3	45.7	45.2	45.2	45.2	45.7	46.3	46.8	46.8	48.3	47.8
82.5°	35.3	34.8	34.7	34.3	34.7	34.8	35.3	35.4	35.4	36.6	36.4
85°	18.9	19.4	18.9	20.0	18.9	19.4	18.9	18.4	18.9	20.0	20.0
87.5°	11.6	11.1	11.6	11.1	11.6	11.1	11.6	11.6	11.8	11.4	11.8
90°	30.3	30.3	30.3	30.3	30.3	30.3	30.3	30.3	29.5	27.6	29.5
92.5°	54.7	51.7	52.4	51.0	52.4	51.7	54.7	55.4	61.1	68.8	80.2
95°	114.1	106.8	104.0	104.9	104.0	106.8	114.1	126.0	146.3	185.0	241.1
97.5°	250.3	227.7	214.2	206.5	214.2	227.7	250.3	294.3	360.8	460.3	562.6
100°	412.3	372.7	346.0	329.5	346.0	372.7	412.3	488.6	600.0	726.1	840.2
102.5°	703.1	635.6	602.2	579.8	602.2	635.6	703.1	786.1	904.0	996.2	1022.1
105°	1146.6	1089.6	1050.0	1037.1	1050.0	1089.6	1146.6	1203.7	1234.1	1222.1	1118.1
107.5°	1353.0	1349.8	1341.9	1324.8	1341.9	1349.8	1353.0	1345.8	1301.2	1205.5	1048.9
110°	1386.8	1404.3	1412.6	1411.7	1412.6	1404.3	1386.8	1347.3	1271.8	1154.0	989.3



TEST NUMBER: P331731-927

CATALOG NUMBER: S122RDIP-S865D1080U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1360.3	1389.6	1405.3	1410.2	1405.3	1389.6	1360.3	1305.3	1218.8	1092.9	934.8
115°	1290.2	1332.5	1356.5	1364.8	1356.5	1332.5	1290.2	1224.9	1130.0	1009.6	867.8
117.5°	1206.7	1251.3	1276.6	1283.6	1276.6	1251.3	1206.7	1140.0	1051.1	941.8	817.4
120°	1152.1	1195.4	1222.1	1231.3	1222.1	1195.4	1152.1	1087.7	1004.0	906.4	792.3
122.5°	1102.8	1145.3	1169.1	1176.8	1169.1	1145.3	1102.8	1045.0	969.4	877.0	772.5
125°	1041.7	1076.7	1099.7	1107.1	1099.7	1076.7	1041.7	988.3	919.3	838.4	743.5
127.5°	987.5	1020.2	1040.1	1046.0	1040.1	1020.2	987.5	940.9	877.2	800.8	715.0
130°	954.3	985.6	1004.0	1011.4	1004.0	985.6	954.3	909.2	848.5	775.8	696.6
132.5°	920.4	951.7	968.7	975.3	968.7	951.7	920.4	876.1	819.0	752.3	679.0
135°	866.9	897.2	913.8	917.5	913.8	897.2	866.9	827.3	775.8	715.0	654.3
137.5°	814.6	840.7	855.3	860.8	855.3	840.7	814.6	778.6	733.6	685.4	634.6
140°	778.6	802.5	816.3	821.8	816.3	802.5	778.6	749.1	708.6	666.3	622.1
142.5°	747.6	769.4	781.6	782.8	781.6	769.4	747.6	719.6	685.8	649.4	611.8
145°	704.9	720.6	729.8	732.5	729.8	720.6	704.9	682.9	656.2	627.6	597.2
147.5°	669.9	682.5	688.7	690.4	688.7	682.5	669.9	651.7	632.2	610.0	586.1
150°	647.8	658.9	664.4	665.4	664.4	658.9	647.8	634.1	617.5	598.2	577.9
152.5°	630.2	639.8	643.8	644.0	643.8	639.8	630.2	619.3	605.0	588.6	569.8
155°	607.4	613.8	617.5	615.7	617.5	613.8	607.4	597.2	587.1	573.3	558.6
157.5°	584.6	589.9	591.5	591.5	591.5	589.9	584.6	577.3	569.4	557.9	545.5
160°	570.5	575.1	576.1	576.1	576.1	575.1	570.5	564.1	557.7	547.6	537.4
162.5°	558.0	561.2	562.1	561.3	562.1	561.2	558.0	551.6	546.6	538.0	529.3
165°	537.4	541.1	541.1	540.2	541.1	541.1	537.4	533.8	530.0	523.6	517.2
167.5°	519.9	522.0	521.8	520.7	521.8	522.0	519.9	518.3	515.0	510.6	505.6
170°	508.9	511.7	510.7	508.9	510.7	511.7	508.9	507.9	506.1	502.5	499.7
172.5°	500.1	501.4	500.4	499.3	500.4	501.4	500.1	499.2	498.0	495.1	493.1
175°	488.6	489.6	488.6	486.8	488.6	489.6	488.6	488.6	487.7	486.8	485.9
177.5°	481.5	481.5	480.8	479.3	480.8	481.5	481.5	481.5	481.5	480.8	480.8
180°	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6



TEST NUMBER: P331731-927

CATALOG NUMBER: S122RDIP-S865D1080U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8
2.5°	1454.7	1460.6	1469.4	1474.5	1482.9	1488.4	1491.3	1496.7	1499.7	1510.2	1521.1
5°	1373.4	1381.9	1396.5	1410.2	1425.0	1440.2	1451.2	1463.9	1475.4	1495.4	1516.4
7.5°	1280.3	1292.0	1314.8	1336.6	1362.2	1383.8	1402.8	1424.3	1443.6	1472.2	1502.0
10°	1210.5	1231.0	1261.0	1281.4	1315.1	1336.6	1366.6	1390.3	1417.1	1454.9	1488.6
12.5°	1150.4	1175.0	1199.1	1227.6	1257.9	1293.8	1326.7	1357.0	1388.9	1428.0	1467.5
15°	1041.2	1077.0	1114.3	1143.2	1184.2	1222.1	1260.4	1301.4	1340.3	1387.1	1438.6
17.5°	900.8	942.2	1005.0	1054.5	1102.6	1140.6	1188.1	1237.7	1283.6	1340.0	1397.3
20°	837.3	867.8	910.4	977.2	1049.6	1090.1	1138.5	1193.2	1245.7	1307.2	1368.7
22.5°	786.4	813.6	847.7	899.8	980.7	1035.9	1086.3	1141.9	1202.8	1265.6	1333.8
25°	713.8	732.7	768.4	810.5	866.3	957.1	1012.3	1068.0	1134.3	1201.6	1279.4
27.5°	659.3	676.3	699.5	739.7	781.1	846.4	934.1	994.9	1060.9	1136.6	1217.3
30°	617.6	637.5	663.3	691.7	736.9	787.9	875.7	946.1	1011.3	1089.1	1175.3
32.5°	587.3	603.1	625.0	653.9	691.5	740.4	810.5	896.0	959.6	1041.6	1131.6
35°	537.7	556.1	574.0	601.3	631.8	676.4	729.5	821.0	884.1	965.0	1055.4
37.5°	496.8	508.0	527.8	549.5	581.6	615.0	661.0	743.0	811.3	890.7	983.3
40°	465.7	479.9	494.6	518.8	545.1	577.1	622.3	683.3	761.6	839.4	929.8
42.5°	435.5	453.4	469.0	485.1	514.0	546.1	582.8	634.5	714.5	788.1	876.0
45°	398.9	410.5	426.8	444.7	468.3	495.7	528.2	573.5	650.2	713.8	796.3
47.5°	356.5	373.4	384.0	401.5	424.0	450.0	480.3	519.4	581.5	641.1	717.7
50°	327.5	344.8	360.0	375.8	395.8	421.0	446.2	484.1	534.0	596.6	668.0
52.5°	302.6	317.9	332.7	348.5	368.0	391.2	415.1	448.4	491.2	548.7	618.1
55°	268.6	278.1	293.3	309.0	326.4	348.5	371.6	399.5	436.3	484.7	540.9
57.5°	233.7	244.6	256.7	272.6	290.2	307.0	327.9	353.1	382.1	425.9	474.0
60°	213.9	222.4	232.3	248.6	264.9	280.1	300.2	321.2	348.5	386.3	427.3
62.5°	192.0	200.0	209.2	223.4	239.2	253.3	270.7	292.9	316.1	350.6	386.5
65°	155.6	167.2	176.1	188.7	201.8	216.6	230.2	248.1	268.6	296.0	328.0
67.5°	129.0	134.9	143.1	154.6	168.1	180.7	193.6	207.6	225.4	246.5	272.0
70°	117.2	119.3	120.9	131.9	144.6	157.2	169.2	182.4	197.6	215.0	237.0
72.5°	103.3	105.4	107.4	112.2	122.2	134.9	147.3	157.2	171.6	185.9	203.8
75°	82.0	85.2	86.7	89.4	93.0	101.5	113.0	122.5	130.9	141.9	156.1
77.5°	62.4	64.2	65.9	68.7	71.0	74.9	81.4	89.9	97.8	104.2	113.9
80°	49.4	49.9	52.0	53.1	56.2	58.9	62.0	68.8	76.8	79.4	86.2
82.5°	37.2	37.7	39.5	40.5	41.9	44.1	48.2	49.9	56.2	59.6	63.9
85°	20.5	20.0	21.5	21.5	22.6	23.7	24.7	27.3	28.9	33.1	34.1
87.5°	12.4	12.6	12.8	11.7	10.4	10.3	10.2	10.2	10.7	11.2	12.4
90°	30.3	31.3	30.3	24.9	18.4	13.8	11.0	9.2	7.4	3.6	1.0
92.5°	101.1	119.6	118.0	91.8	62.6	41.7	33.1	26.9	22.8	16.2	11.2
95°	315.7	360.8	319.3	212.5	132.5	90.2	68.1	53.4	45.1	35.9	32.2
97.5°	646.0	615.8	463.8	286.4	174.8	121.7	96.6	79.7	67.2	57.4	52.4
100°	859.5	727.0	500.6	301.8	189.6	140.8	115.0	96.6	81.9	73.6	70.8
102.5°	939.1	730.7	486.6	302.6	202.8	157.7	132.0	112.8	98.1	89.8	87.8
105°	926.7	681.9	459.2	307.4	225.5	182.2	156.5	136.2	122.4	116.0	112.3
107.5°	845.9	629.6	445.6	320.0	248.7	206.7	180.8	160.7	148.0	141.7	138.8
110°	795.1	604.6	442.7	330.3	264.1	223.6	196.9	177.6	165.6	160.1	156.5



TEST NUMBER: P331731-927

CATALOG NUMBER: S122RDIP-S865D1080U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	759.8	588.4	443.4	341.4	278.8	239.8	212.4	193.8	182.6	176.3	172.6
115°	716.0	570.5	447.3	358.0	301.8	262.3	237.4	219.0	207.9	202.5	197.9
117.5°	688.3	561.9	453.8	375.7	323.0	286.4	260.6	243.0	233.2	227.7	224.0
120°	673.6	556.7	458.3	387.5	337.7	301.8	276.1	257.7	249.4	243.8	240.2
122.5°	661.1	553.8	463.4	397.8	351.7	318.1	291.5	273.1	264.1	258.6	255.6
125°	643.3	548.5	471.2	414.2	372.7	339.6	313.8	295.4	284.4	278.8	276.1
127.5°	626.7	545.3	479.1	429.4	392.2	360.0	333.5	315.8	303.7	296.0	292.2
130°	615.7	543.8	485.0	438.9	404.0	371.8	346.0	327.6	314.7	305.5	301.8
132.5°	606.8	543.1	490.8	448.5	414.3	383.6	357.8	338.7	325.0	315.1	310.7
135°	594.5	542.0	497.9	461.1	428.8	399.4	373.6	352.4	338.7	327.6	323.9
137.5°	585.8	541.9	504.1	470.6	440.6	411.5	387.6	366.6	351.9	340.9	336.4
140°	580.7	541.1	507.1	475.8	447.3	419.6	395.7	375.5	360.8	349.7	346.0
142.5°	575.5	541.1	509.3	480.2	452.4	425.6	403.1	383.6	368.8	358.5	355.6
145°	568.7	539.2	511.7	485.9	460.1	435.3	415.0	396.6	382.9	373.6	369.9
147.5°	561.7	536.0	512.4	489.0	466.4	443.0	425.0	409.7	397.0	388.2	385.4
150°	555.8	533.8	511.7	490.5	469.4	448.1	431.6	417.8	405.8	398.5	395.7
152.5°	550.6	530.0	510.2	491.2	472.3	453.3	438.2	425.2	414.6	407.3	406.0
155°	541.1	523.6	507.9	492.3	476.7	461.1	447.3	437.1	427.0	421.4	420.6
157.5°	532.1	517.0	503.7	492.3	479.8	466.6	455.0	446.9	438.1	433.6	432.7
160°	525.5	512.6	501.5	492.3	481.3	470.2	460.1	452.7	445.4	441.7	440.8
162.5°	519.6	508.9	499.3	491.6	482.0	472.5	464.5	457.9	452.0	448.4	448.9
165°	509.8	501.5	495.1	489.6	483.2	474.8	469.4	464.7	459.2	457.4	458.3
167.5°	500.3	495.1	490.8	488.3	482.9	476.9	473.4	470.1	466.6	464.9	466.0
170°	495.1	491.4	488.6	486.8	482.2	477.6	474.8	473.0	470.2	469.4	471.2
172.5°	490.0	487.0	485.7	484.6	481.5	478.3	476.3	475.2	472.5	473.0	474.1
175°	483.2	482.2	481.3	482.2	480.4	478.6	477.6	477.6	475.8	476.7	477.6
177.5°	479.3	478.6	479.3	480.8	479.3	478.6	478.6	478.6	477.1	477.8	479.3
180°	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6



TEST NUMBER: P331731-927

CATALOG NUMBER: S122RDIP-S865D1080U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8
2.5°	1521.5	1522.8	1531.2	1535.0	1542.6	1545.5	1548.9	1548.1	1548.1	1549.7	1561.5
5°	1524.8	1535.3	1551.1	1566.4	1581.0	1593.7	1602.1	1610.5	1613.7	1628.9	1642.6
7.5°	1519.3	1538.7	1564.8	1588.0	1615.9	1637.6	1655.7	1672.0	1683.1	1705.3	1728.1
10°	1512.2	1539.5	1569.0	1598.9	1637.3	1666.2	1695.7	1718.2	1725.6	1758.7	1777.7
12.5°	1497.9	1534.5	1571.9	1610.7	1648.2	1688.1	1720.5	1743.0	1768.9	1798.6	1833.6
15°	1476.5	1518.5	1567.4	1617.3	1671.0	1719.3	1754.0	1793.4	1821.8	1854.4	1884.8
17.5°	1445.7	1499.8	1561.9	1619.8	1681.8	1733.7	1781.5	1819.2	1839.2	1857.8	1862.3
20°	1421.3	1479.6	1552.7	1621.0	1683.1	1743.0	1790.3	1821.8	1827.1	1827.6	1799.8
22.5°	1394.8	1460.7	1537.2	1607.1	1681.3	1748.0	1784.8	1798.3	1777.4	1741.8	1687.9
25°	1346.1	1422.4	1511.2	1591.0	1672.0	1735.0	1747.7	1724.0	1651.0	1574.2	1477.0
27.5°	1293.3	1379.0	1474.3	1563.1	1649.3	1688.4	1661.2	1575.9	1444.3	1329.9	1191.3
30°	1254.7	1350.8	1444.4	1543.7	1623.7	1640.5	1577.9	1452.3	1298.8	1126.4	988.2
32.5°	1210.5	1311.3	1414.1	1516.9	1583.7	1567.3	1464.0	1309.3	1129.3	959.9	829.3
35°	1147.4	1251.5	1362.4	1465.5	1508.0	1437.0	1282.5	1081.2	897.2	739.0	649.1
37.5°	1074.6	1187.9	1303.2	1397.8	1394.8	1276.5	1066.0	858.3	703.6	610.1	546.1
40°	1022.9	1137.4	1262.0	1341.9	1307.7	1153.7	925.6	729.5	616.6	541.9	495.1
42.5°	973.3	1088.2	1212.0	1275.5	1216.1	1026.7	799.5	645.9	552.6	494.4	456.5
45°	888.8	1010.3	1124.8	1160.1	1053.8	845.2	646.5	535.1	473.1	429.9	403.7
47.5°	806.3	925.7	1030.3	1030.9	887.3	685.4	545.4	463.1	410.1	376.8	357.7
50°	755.8	869.3	957.1	943.5	780.5	609.7	487.7	416.8	372.6	346.9	326.9
52.5°	699.1	809.2	885.3	846.4	690.1	536.5	436.0	376.4	339.8	317.5	299.6
55°	616.6	714.3	767.9	709.1	562.9	446.2	368.4	321.7	294.4	275.4	260.2
57.5°	535.5	616.2	649.9	581.3	463.7	370.0	311.7	276.6	249.5	235.9	228.0
60°	484.7	553.5	577.1	501.5	403.1	323.8	275.9	243.4	223.4	214.4	206.6
62.5°	434.6	490.8	500.6	431.2	351.4	283.4	242.3	214.8	201.5	193.0	185.5
65°	360.6	401.1	396.3	340.6	278.1	225.0	195.0	178.2	168.2	156.1	143.0
67.5°	296.8	321.5	306.7	264.9	212.2	174.8	155.3	142.5	130.2	118.7	115.7
70°	256.5	270.7	254.9	216.6	174.0	146.6	130.9	115.7	108.3	105.7	100.9
72.5°	217.9	222.8	205.7	172.9	141.6	121.4	106.1	97.5	93.6	91.3	88.3
75°	163.5	159.8	145.0	119.3	98.3	84.6	79.9	76.8	74.1	72.0	70.4
77.5°	114.8	109.4	96.3	79.5	68.4	61.9	59.1	57.4	56.2	55.1	53.5
80°	86.2	82.5	69.4	56.8	52.0	48.9	47.3	45.2	45.2	44.1	42.5
82.5°	63.1	58.9	47.5	41.6	39.0	37.1	36.0	34.7	34.3	34.5	33.4
85°	33.1	26.8	23.7	22.6	21.0	20.0	20.5	19.4	19.4	19.4	18.9
87.5°	10.9	9.4	9.4	9.3	10.3	11.2	12.1	13.2	13.9	13.2	13.5
90°	3.6	7.4	9.2	11.0	13.8	18.4	24.9	30.3	31.3	30.3	29.5
92.5°	16.2	22.8	26.9	33.1	41.7	62.6	91.8	118.0	119.6	101.1	80.2
95°	35.9	45.1	53.4	68.1	90.2	132.5	212.5	319.3	360.8	315.7	241.1
97.5°	57.4	67.2	79.7	96.6	121.7	174.8	286.4	463.8	615.8	646.0	562.6
100°	73.6	81.9	96.6	115.0	140.8	189.6	301.8	500.6	727.0	859.5	840.2
102.5°	89.8	98.1	112.8	132.0	157.7	202.8	302.6	486.6	730.7	939.1	1022.1
105°	116.0	122.4	136.2	156.5	182.2	225.5	307.4	459.2	681.9	926.7	1118.1
107.5°	141.7	148.0	160.7	180.8	206.7	248.7	320.0	445.6	629.6	845.9	1048.9
110°	160.1	165.6	177.6	196.9	223.6	264.1	330.3	442.7	604.6	795.1	989.3



TEST NUMBER: P331731-927

CATALOG NUMBER: S122RDIP-S865D1080U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	176.3	182.6	193.8	212.4	239.8	278.8	341.4	443.4	588.4	759.8	934.8
115°	202.5	207.9	219.0	237.4	262.3	301.8	358.0	447.3	570.5	716.0	867.8
117.5°	227.7	233.2	243.0	260.6	286.4	323.0	375.7	453.8	561.9	688.3	817.4
120°	243.8	249.4	257.7	276.1	301.8	337.7	387.5	458.3	556.7	673.6	792.3
122.5°	258.6	264.1	273.1	291.5	318.1	351.7	397.8	463.4	553.8	661.1	772.5
125°	278.8	284.4	295.4	313.8	339.6	372.7	414.2	471.2	548.5	643.3	743.5
127.5°	296.0	303.7	315.8	333.5	360.0	392.2	429.4	479.1	545.3	626.7	715.0
130°	305.5	314.7	327.6	346.0	371.8	404.0	438.9	485.0	543.8	615.7	696.6
132.5°	315.1	325.0	338.7	357.8	383.6	414.3	448.5	490.8	543.1	606.8	679.0
135°	327.6	338.7	352.4	373.6	399.4	428.8	461.1	497.9	542.0	594.5	654.3
137.5°	340.9	351.9	366.6	387.6	411.5	440.6	470.6	504.1	541.9	585.8	634.6
140°	349.7	360.8	375.5	395.7	419.6	447.3	475.8	507.1	541.1	580.7	622.1
142.5°	358.5	368.8	383.6	403.1	425.6	452.4	480.2	509.3	541.1	575.5	611.8
145°	373.6	382.9	396.6	415.0	435.3	460.1	485.9	511.7	539.2	568.7	597.2
147.5°	388.2	397.0	409.7	425.0	443.0	466.4	489.0	512.4	536.0	561.7	586.1
150°	398.5	405.8	417.8	431.6	448.1	469.4	490.5	511.7	533.8	555.8	577.9
152.5°	407.3	414.6	425.2	438.2	453.3	472.3	491.2	510.2	530.0	550.6	569.8
155°	421.4	427.0	437.1	447.3	461.1	476.7	492.3	507.9	523.6	541.1	558.6
157.5°	433.6	438.1	446.9	455.0	466.6	479.8	492.3	503.7	517.0	532.1	545.5
160°	441.7	445.4	452.7	460.1	470.2	481.3	492.3	501.5	512.6	525.5	537.4
162.5°	448.4	452.0	457.9	464.5	472.5	482.0	491.6	499.3	508.9	519.6	529.3
165°	457.4	459.2	464.7	469.4	474.8	483.2	489.6	495.1	501.5	509.8	517.2
167.5°	464.9	466.6	470.1	473.4	476.9	482.9	488.3	490.8	495.1	500.3	505.6
170°	469.4	470.2	473.0	474.8	477.6	482.2	486.8	488.6	491.4	495.1	499.7
172.5°	473.0	472.5	475.2	476.3	478.3	481.5	484.6	485.7	487.0	490.0	493.1
175°	476.7	475.8	477.6	477.6	478.6	480.4	482.2	481.3	482.2	483.2	485.9
177.5°	477.8	477.1	478.6	478.6	478.6	479.3	480.8	479.3	478.6	479.3	480.8
180°	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6	478.6



TEST NUMBER: P331731-927

CATALOG NUMBER: S122RDIP-S865D1080U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8
2.5°	1565.7	1571.2	1573.7	1573.7	1576.7	1575.4	1574.1
5°	1655.7	1665.7	1667.8	1677.3	1684.1	1682.0	1683.1
7.5°	1745.2	1761.3	1777.1	1784.4	1785.5	1789.7	1791.3
10°	1800.2	1813.4	1838.1	1834.4	1852.8	1863.3	1845.9
12.5°	1853.2	1871.0	1888.2	1892.8	1903.3	1906.6	1899.8
15°	1901.2	1910.7	1911.7	1909.1	1912.2	1909.6	1899.6
17.5°	1856.4	1841.0	1809.9	1795.2	1783.5	1766.3	1759.4
20°	1782.4	1737.2	1684.6	1663.6	1638.9	1590.5	1602.1
22.5°	1622.6	1571.1	1518.5	1457.1	1427.8	1382.0	1379.2
25°	1374.0	1285.2	1187.4	1119.0	1079.1	1033.4	1013.4
27.5°	1068.3	956.4	876.3	835.8	798.8	762.6	761.1
30°	867.3	783.2	721.1	686.4	663.8	648.6	651.8
32.5°	731.0	673.4	631.6	602.8	586.1	574.6	574.4
35°	597.6	558.2	531.4	519.3	507.2	498.8	499.3
37.5°	511.4	487.7	472.9	459.5	451.9	447.8	445.5
40°	467.3	447.8	436.3	428.4	422.1	416.3	415.3
42.5°	432.4	416.3	404.7	398.5	392.6	388.6	387.5
45°	383.7	370.6	360.0	353.2	350.6	346.9	346.9
47.5°	341.4	328.4	320.2	315.9	311.4	309.0	308.9
50°	312.8	302.8	295.4	292.8	289.1	287.5	287.0
52.5°	287.1	279.6	274.4	272.6	271.0	269.0	269.3
55°	252.3	248.1	246.0	244.4	241.8	238.6	240.7
57.5°	223.0	219.4	213.7	208.7	206.4	204.1	205.0
60°	202.4	195.0	187.7	181.9	180.3	175.5	175.5
62.5°	176.3	166.0	156.9	153.7	152.1	149.9	149.5
65°	135.6	131.4	129.3	127.2	126.1	126.1	125.1
67.5°	112.4	110.7	108.4	107.9	106.8	106.5	106.2
70°	99.3	97.2	96.2	95.7	94.6	95.1	93.6
72.5°	86.7	85.1	84.8	83.5	82.9	82.9	81.8
75°	68.4	68.4	67.8	67.3	66.2	65.7	66.2
77.5°	52.6	52.7	51.7	51.7	51.5	51.7	51.1
80°	42.1	42.5	42.1	41.5	41.0	41.5	41.0
82.5°	33.2	32.5	32.4	32.2	32.2	31.8	31.8
85°	18.9	19.4	18.9	18.4	18.4	18.4	18.9
87.5°	12.7	13.1	13.2	13.2	13.2	13.2	12.8
90°	27.6	29.5	30.3	30.3	30.3	30.3	30.3
92.5°	68.8	61.1	55.4	54.7	51.7	52.4	51.0
95°	185.0	146.3	126.0	114.1	106.8	104.0	104.9
97.5°	460.3	360.8	294.3	250.3	227.7	214.2	206.5
100°	726.1	600.0	488.6	412.3	372.7	346.0	329.5
102.5°	996.2	904.0	786.1	703.1	635.6	602.2	579.8
105°	1222.1	1234.1	1203.7	1146.6	1089.6	1050.0	1037.1
107.5°	1205.5	1301.2	1345.8	1353.0	1349.8	1341.9	1324.8
110°	1154.0	1271.8	1347.3	1386.8	1404.3	1412.6	1411.7



TEST NUMBER: P331731-927

CATALOG NUMBER: S122RDIP-S865D1080U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1092.9	1218.8	1305.3	1360.3	1389.6	1405.3	1410.2
115°	1009.6	1130.0	1224.9	1290.2	1332.5	1356.5	1364.8
117.5°	941.8	1051.1	1140.0	1206.7	1251.3	1276.6	1283.6
120°	906.4	1004.0	1087.7	1152.1	1195.4	1222.1	1231.3
122.5°	877.0	969.4	1045.0	1102.8	1145.3	1169.1	1176.8
125°	838.4	919.3	988.3	1041.7	1076.7	1099.7	1107.1
127.5°	800.8	877.2	940.9	987.5	1020.2	1040.1	1046.0
130°	775.8	848.5	909.2	954.3	985.6	1004.0	1011.4
132.5°	752.3	819.0	876.1	920.4	951.7	968.7	975.3
135°	715.0	775.8	827.3	866.9	897.2	913.8	917.5
137.5°	685.4	733.6	778.6	814.6	840.7	855.3	860.8
140°	666.3	708.6	749.1	778.6	802.5	816.3	821.8
142.5°	649.4	685.8	719.6	747.6	769.4	781.6	782.8
145°	627.6	656.2	682.9	704.9	720.6	729.8	732.5
147.5°	610.0	632.2	651.7	669.9	682.5	688.7	690.4
150°	598.2	617.5	634.1	647.8	658.9	664.4	665.4
152.5°	588.6	605.0	619.3	630.2	639.8	643.8	644.0
155°	573.3	587.1	597.2	607.4	613.8	617.5	615.7
157.5°	557.9	569.4	577.3	584.6	589.9	591.5	591.5
160°	547.6	557.7	564.1	570.5	575.1	576.1	576.1
162.5°	538.0	546.6	551.6	558.0	561.2	562.1	561.3
165°	523.6	530.0	533.8	537.4	541.1	541.1	540.2
167.5°	510.6	515.0	518.3	519.9	522.0	521.8	520.7
170°	502.5	506.1	507.9	508.9	511.7	510.7	508.9
172.5°	495.1	498.0	499.2	500.1	501.4	500.4	499.3
175°	486.8	487.7	488.6	488.6	489.6	488.6	486.8
177.5°	480.8	481.5	481.5	481.5	481.5	480.8	479.3
180°	478.6	478.6	478.6	478.6	478.6	478.6	478.6

(END OF REPORT)