

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331707-927

Luminaire Tested: **S122RDIP-S865D330U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331707-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S865D330U927-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3628.5 lumens
Efficiency: N/A
Efficacy: 83.4 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331707-927

CATALOG NUMBER: S122RDIP-S865D330U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331707-927

CATALOG NUMBER: S122RDIP-S865D330U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	76	76	76	72
1	104	100	96	93	98	95	92	89	86	83	81	77	75	74	69	68	67	63
2	96	89	83	78	90	84	79	75	76	72	69	69	66	63	62	60	58	55
3	88	79	72	66	83	75	69	64	69	64	60	62	58	55	56	53	51	48
4	81	71	63	58	77	68	61	56	62	56	52	56	52	48	51	48	45	42
5	75	64	56	50	71	61	54	49	56	50	46	51	47	43	47	43	40	38
6	70	58	50	45	66	56	49	43	51	45	41	47	42	38	43	39	36	34
7	65	53	45	40	62	51	44	39	47	41	37	43	38	35	40	36	33	30
8	61	49	41	36	58	47	40	35	43	38	33	40	35	32	37	33	30	28
9	57	45	38	33	54	43	37	32	40	34	30	37	32	29	35	30	27	25
10	54	42	35	30	51	40	34	29	37	32	28	35	30	27	32	28	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	24425	24425	24425	24425
5°	27279	24577	21793	24577
10°	30263	24405	18889	24405
15°	31753	24047	14883	24047
20°	27527	23517	12880	23517
25°	18054	22792	11500	22792
30°	12152	21912	10407	21912
35°	9841	20802	9386	20802
40°	8753	19597	8686	19597
45°	7921	18182	7752	18182
50°	7209	16779	7181	16779
55°	6776	15226	6688	15226
60°	5667	13798	5603	13798
65°	4779	12531	5421	12531
70°	4419	11188	5113	11188
75°	4130	9738	4722	9738
80°	3812	8015	4203	8015
85°	3501	6317	3705	6317



TEST NUMBER: P331707-927

CATALOG NUMBER: S122RDIP-S865D330U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.4	4.0
10°-20°	399.6	11.0
20°-30°	514.9	14.2
30°-40°	489.3	13.5
40°-50°	419.2	11.6
50°-60°	319.2	8.8
60°-70°	201.8	5.6
70°-80°	100.8	2.8
80°-90°	27.5	0.8
90°-100°	58.2	1.6
100°-110°	197.5	5.4
110°-120°	209.8	5.8
120°-130°	172.7	4.8
130°-140°	138.7	3.8
140°-150°	104.8	2.9
150°-160°	73.7	2.0
160°-170°	43.4	1.2
170°-180°	14.1	0.4
0°-30°	1057.9	29.2
0°-40°	1547.2	42.6
0°-60°	2285.6	63.0
0°-90°	2615.6	72.1
90°-120°	465.5	12.8
90°-150°	881.7	24.3
90°-180°	1013.0	27.9
0°-180°	3628.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1513	1513	1513	1513	1513	
5°	1683	1516	1345	1516	1683	166
15°	1900	1439	890	1439	1900	512
25°	1013	1279	646	1279	1013	481
35°	499	1055	476	1055	499	319
45°	347	796	340	796	347	269
55°	241	541	238	541	241	211
65°	125	328	142	328	125	127
75°	66	156	76	156	66	70
85°	19	34	20	34	19	21
90°	9	0	9	0	9	6
95°	32	10	32	10	32	41
105°	315	34	315	34	315	305
115°	415	60	415	60	415	406
125°	337	84	337	84	337	304
135°	279	98	279	98	279	217
145°	223	112	223	112	223	142
155°	187	128	187	128	187	87
165°	164	139	164	139	164	47
175°	148	145	148	145	148	14
180°	146	146	146	146	146	



TEST NUMBER: P331707-927

CATALOG NUMBER: S122RDIP-S865D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8
2.5°	1574.1	1575.4	1576.7	1573.7	1573.7	1571.2	1565.7	1561.5	1549.7	1548.1	1548.1
5°	1683.1	1682.0	1684.1	1677.3	1667.8	1665.7	1655.7	1642.6	1628.9	1613.7	1610.5
7.5°	1791.3	1789.7	1785.5	1784.4	1777.1	1761.3	1745.2	1728.1	1705.3	1683.1	1672.0
10°	1845.9	1863.3	1852.8	1834.4	1838.1	1813.4	1800.2	1777.7	1758.7	1725.6	1718.2
12.5°	1899.8	1906.6	1903.3	1892.8	1888.2	1871.0	1853.2	1833.6	1798.6	1768.9	1743.0
15°	1899.6	1909.6	1912.2	1909.1	1911.7	1910.7	1901.2	1884.8	1854.4	1821.8	1793.4
17.5°	1759.4	1766.3	1783.5	1795.2	1809.9	1841.0	1856.4	1862.3	1857.8	1839.2	1819.2
20°	1602.1	1590.5	1638.9	1663.6	1684.6	1737.2	1782.4	1799.8	1827.6	1827.1	1821.8
22.5°	1379.2	1382.0	1427.8	1457.1	1518.5	1571.1	1622.6	1687.9	1741.8	1777.4	1798.3
25°	1013.4	1033.4	1079.1	1119.0	1187.4	1285.2	1374.0	1477.0	1574.2	1651.0	1724.0
27.5°	761.1	762.6	798.8	835.8	876.3	956.4	1068.3	1191.3	1329.9	1444.3	1575.9
30°	651.8	648.6	663.8	686.4	721.1	783.2	867.3	988.2	1126.4	1298.8	1452.3
32.5°	574.4	574.6	586.1	602.8	631.6	673.4	731.0	829.3	959.9	1129.3	1309.3
35°	499.3	498.8	507.2	519.3	531.4	558.2	597.6	649.1	739.0	897.2	1081.2
37.5°	445.5	447.8	451.9	459.5	472.9	487.7	511.4	546.1	610.1	703.6	858.3
40°	415.3	416.3	422.1	428.4	436.3	447.8	467.3	495.1	541.9	616.6	729.5
42.5°	387.5	388.6	392.6	398.5	404.7	416.3	432.4	456.5	494.4	552.6	645.9
45°	346.9	346.9	350.6	353.2	360.0	370.6	383.7	403.7	429.9	473.1	535.1
47.5°	308.9	309.0	311.4	315.9	320.2	328.4	341.4	357.7	376.8	410.1	463.1
50°	287.0	287.5	289.1	292.8	295.4	302.8	312.8	326.9	346.9	372.6	416.8
52.5°	269.3	269.0	271.0	272.6	274.4	279.6	287.1	299.6	317.5	339.8	376.4
55°	240.7	238.6	241.8	244.4	246.0	248.1	252.3	260.2	275.4	294.4	321.7
57.5°	205.0	204.1	206.4	208.7	213.7	219.4	223.0	228.0	235.9	249.5	276.6
60°	175.5	175.5	180.3	181.9	187.7	195.0	202.4	206.6	214.4	223.4	243.4
62.5°	149.5	149.9	152.1	153.7	156.9	166.0	176.3	185.5	193.0	201.5	214.8
65°	125.1	126.1	126.1	127.2	129.3	131.4	135.6	143.0	156.1	168.2	178.2
67.5°	106.2	106.5	106.8	107.9	108.4	110.7	112.4	115.7	118.7	130.2	142.5
70°	93.6	95.1	94.6	95.7	96.2	97.2	99.3	100.9	105.7	108.3	115.7
72.5°	81.8	82.9	82.9	83.5	84.8	85.1	86.7	88.3	91.3	93.6	97.5
75°	66.2	65.7	66.2	67.3	67.8	68.4	68.4	70.4	72.0	74.1	76.8
77.5°	51.1	51.7	51.5	51.7	51.7	52.7	52.6	53.5	55.1	56.2	57.4
80°	41.0	41.5	41.0	41.5	42.1	42.5	42.1	42.5	44.1	45.2	45.2
82.5°	31.8	31.8	32.2	32.2	32.4	32.5	33.2	33.4	34.5	34.3	34.7
85°	18.9	18.4	18.4	18.4	18.9	19.4	18.9	18.9	19.4	19.4	19.4
87.5°	8.6	9.0	9.0	9.0	9.0	9.0	8.8	9.3	9.0	9.5	9.0
90°	9.3	9.3	9.3	9.3	9.3	9.0	8.4	9.0	9.3	9.5	9.3
92.5°	15.5	15.9	15.8	16.6	16.9	18.6	20.9	24.4	30.7	36.4	35.9
95°	31.9	31.6	32.5	34.7	38.3	44.5	56.2	73.4	96.0	109.7	97.1
97.5°	62.8	65.2	69.2	76.1	89.5	109.7	140.0	171.1	196.5	187.3	141.1
100°	100.2	105.3	113.4	125.4	148.6	182.5	220.9	255.6	261.4	221.1	152.3
102.5°	176.3	183.2	193.3	213.8	239.1	275.0	303.0	310.9	285.6	222.2	148.0
105°	315.4	319.3	331.4	348.7	366.1	375.3	371.7	340.1	281.9	207.4	139.7
107.5°	403.0	408.1	410.6	411.5	409.3	395.8	366.7	319.0	257.3	191.5	135.5
110°	429.4	429.7	427.1	421.8	409.8	386.8	351.0	300.9	241.9	183.9	134.7



TEST NUMBER: P331707-927

CATALOG NUMBER: S122RDIP-S865D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	428.9	427.4	422.6	413.8	397.0	370.7	332.4	284.3	231.1	179.0	134.8
115°	415.1	412.6	405.3	392.4	372.6	343.7	307.0	264.0	217.8	173.6	136.0
117.5°	390.4	388.2	380.6	367.0	346.7	319.7	286.5	248.6	209.4	170.9	138.1
120°	374.5	371.7	363.6	350.5	330.8	305.4	275.7	241.0	204.9	169.4	139.4
122.5°	357.9	355.6	348.4	335.4	317.8	294.9	266.7	235.0	201.1	168.4	140.9
125°	336.8	334.5	327.5	316.9	300.6	279.6	255.0	226.2	195.7	166.8	143.3
127.5°	318.1	316.3	310.3	300.3	286.1	266.8	243.6	217.5	190.6	165.9	145.7
130°	307.6	305.4	299.8	290.3	276.6	258.1	236.0	211.9	187.3	165.4	147.5
132.5°	296.7	294.6	289.5	280.0	266.5	249.1	228.8	206.5	184.6	165.2	149.3
135°	279.1	278.0	272.9	263.6	251.6	236.0	217.5	199.0	180.8	164.9	151.5
137.5°	261.8	260.2	255.7	247.8	236.8	223.2	208.5	193.1	178.2	164.8	153.4
140°	249.9	248.3	244.1	236.8	227.8	215.6	202.6	189.2	176.6	164.6	154.2
142.5°	238.1	237.7	234.0	227.4	218.9	208.6	197.5	186.1	175.1	164.6	154.9
145°	222.8	222.0	219.2	214.4	207.7	199.6	190.9	181.6	173.0	164.0	155.6
147.5°	210.0	209.5	207.6	203.7	198.2	192.3	185.5	178.2	170.9	163.0	155.8
150°	202.4	202.1	200.4	197.0	192.8	187.8	182.0	175.8	169.1	162.3	155.6
152.5°	195.9	195.8	194.6	191.7	188.4	184.0	179.0	173.3	167.5	161.2	155.2
155°	187.3	187.8	186.7	184.7	181.6	178.6	174.4	169.9	164.6	159.2	154.5
157.5°	179.9	179.9	179.4	177.8	175.6	173.2	169.7	166.0	161.8	157.2	153.2
160°	175.2	175.2	174.9	173.6	171.6	169.6	166.5	163.4	159.8	155.9	152.6
162.5°	170.7	171.0	170.7	169.8	167.8	166.3	163.7	161.0	158.0	154.8	151.9
165°	164.3	164.6	164.6	163.4	162.3	161.2	159.2	157.3	155.0	152.6	150.6
167.5°	158.4	158.7	158.8	158.1	157.6	156.6	155.3	153.8	152.2	150.6	149.3
170°	154.8	155.3	155.6	154.8	154.5	153.9	152.8	152.0	150.6	149.5	148.6
172.5°	151.9	152.2	152.5	152.1	151.8	151.5	150.6	150.0	149.0	148.1	147.7
175°	148.1	148.6	148.9	148.6	148.6	148.4	148.1	147.8	146.9	146.6	146.4
177.5°	145.8	146.2	146.5	146.5	146.5	146.5	146.2	146.2	145.8	145.5	145.8
180°	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5



TEST NUMBER: P331707-927

CATALOG NUMBER: S122RDIP-S865D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8
2.5°	1548.9	1545.5	1542.6	1535.0	1531.2	1522.8	1521.5	1521.1	1510.2	1499.7	1496.7
5°	1602.1	1593.7	1581.0	1566.4	1551.1	1535.3	1524.8	1516.4	1495.4	1475.4	1463.9
7.5°	1655.7	1637.6	1615.9	1588.0	1564.8	1538.7	1519.3	1502.0	1472.2	1443.6	1424.3
10°	1695.7	1666.2	1637.3	1598.9	1569.0	1539.5	1512.2	1488.6	1454.9	1417.1	1390.3
12.5°	1720.5	1688.1	1648.2	1610.7	1571.9	1534.5	1497.9	1467.5	1428.0	1388.9	1357.0
15°	1754.0	1719.3	1671.0	1617.3	1567.4	1518.5	1476.5	1438.6	1387.1	1340.3	1301.4
17.5°	1781.5	1733.7	1681.8	1619.8	1561.9	1499.8	1445.7	1397.3	1340.0	1283.6	1237.7
20°	1790.3	1743.0	1683.1	1621.0	1552.7	1479.6	1421.3	1368.7	1307.2	1245.7	1193.2
22.5°	1784.8	1748.0	1681.3	1607.1	1537.2	1460.7	1394.8	1333.8	1265.6	1202.8	1141.9
25°	1747.7	1735.0	1672.0	1591.0	1511.2	1422.4	1346.1	1279.4	1201.6	1134.3	1068.0
27.5°	1661.2	1688.4	1649.3	1563.1	1474.3	1379.0	1293.3	1217.3	1136.6	1060.9	994.9
30°	1577.9	1640.5	1623.7	1543.7	1444.4	1350.8	1254.7	1175.3	1089.1	1011.3	946.1
32.5°	1464.0	1567.3	1583.7	1516.9	1414.1	1311.3	1210.5	1131.6	1041.6	959.6	896.0
35°	1282.5	1437.0	1508.0	1465.5	1362.4	1251.5	1147.4	1055.4	965.0	884.1	821.0
37.5°	1066.0	1276.5	1394.8	1397.8	1303.2	1187.9	1074.6	983.3	890.7	811.3	743.0
40°	925.6	1153.7	1307.7	1341.9	1262.0	1137.4	1022.9	929.8	839.4	761.6	683.3
42.5°	799.5	1026.7	1216.1	1275.5	1212.0	1088.2	973.3	876.0	788.1	714.5	634.5
45°	646.5	845.2	1053.8	1160.1	1124.8	1010.3	888.8	796.3	713.8	650.2	573.5
47.5°	545.4	685.4	887.3	1030.9	1030.3	925.7	806.3	717.7	641.1	581.5	519.4
50°	487.7	609.7	780.5	943.5	957.1	869.3	755.8	668.0	596.6	534.0	484.1
52.5°	436.0	536.5	690.1	846.4	885.3	809.2	699.1	618.1	548.7	491.2	448.4
55°	368.4	446.2	562.9	709.1	767.9	714.3	616.6	540.9	484.7	436.3	399.5
57.5°	311.7	370.0	463.7	581.3	649.9	616.2	535.5	474.0	425.9	382.1	353.1
60°	275.9	323.8	403.1	501.5	577.1	553.5	484.7	427.3	386.3	348.5	321.2
62.5°	242.3	283.4	351.4	431.2	500.6	490.8	434.6	386.5	350.6	316.1	292.9
65°	195.0	225.0	278.1	340.6	396.3	401.1	360.6	328.0	296.0	268.6	248.1
67.5°	155.3	174.8	212.2	264.9	306.7	321.5	296.8	272.0	246.5	225.4	207.6
70°	130.9	146.6	174.0	216.6	254.9	270.7	256.5	237.0	215.0	197.6	182.4
72.5°	106.1	121.4	141.6	172.9	205.7	222.8	217.9	203.8	185.9	171.6	157.2
75°	79.9	84.6	98.3	119.3	145.0	159.8	163.5	156.1	141.9	130.9	122.5
77.5°	59.1	61.9	68.4	79.5	96.3	109.4	114.8	113.9	104.2	97.8	89.9
80°	47.3	48.9	52.0	56.8	69.4	82.5	86.2	86.2	79.4	76.8	68.8
82.5°	36.0	37.1	39.0	41.6	47.5	58.9	63.1	63.9	59.6	56.2	49.9
85°	20.5	20.0	21.0	22.6	23.7	26.8	33.1	34.1	33.1	28.9	27.3
87.5°	8.6	8.7	8.4	7.8	8.2	8.5	10.3	12.3	10.8	9.7	9.0
90°	7.5	5.6	4.2	3.3	2.8	2.2	1.1	0.3	1.1	2.2	2.8
92.5°	28.0	19.0	12.7	10.1	8.2	7.0	4.9	3.4	4.9	7.0	8.2
95°	64.6	40.3	27.4	20.7	16.2	13.7	10.9	9.8	10.9	13.7	16.2
97.5°	87.1	53.2	37.0	29.4	24.2	20.4	17.4	15.9	17.4	20.4	24.2
100°	91.8	57.7	42.9	35.0	29.4	24.9	22.4	21.5	22.4	24.9	29.4
102.5°	92.1	61.7	48.0	40.2	34.3	29.9	27.3	26.7	27.3	29.9	34.3
105°	93.5	68.6	55.5	47.6	41.4	37.2	35.3	34.1	35.3	37.2	41.4
107.5°	97.4	75.7	62.9	55.0	48.9	45.0	43.1	42.2	43.1	45.0	48.9
110°	100.4	80.3	68.0	59.9	54.0	50.4	48.7	47.6	48.7	50.4	54.0



TEST NUMBER: P331707-927

CATALOG NUMBER: S122RDIP-S865D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	103.9	84.8	73.0	64.6	58.9	55.5	53.6	52.5	53.6	55.5	58.9
115°	108.8	91.8	79.8	72.2	66.6	63.3	61.6	60.2	61.6	63.3	66.6
117.5°	114.2	98.2	87.1	79.3	73.9	70.9	69.2	68.1	69.2	70.9	73.9
120°	117.9	102.7	91.8	84.0	78.3	75.9	74.1	73.0	74.1	75.9	78.3
122.5°	121.0	106.9	96.7	88.6	83.1	80.3	78.7	77.8	78.7	80.3	83.1
125°	126.0	113.4	103.3	95.5	89.8	86.5	84.8	84.0	84.8	86.5	89.8
127.5°	130.6	119.3	109.5	101.4	96.1	92.4	90.0	88.9	90.0	92.4	96.1
130°	133.5	122.9	113.0	105.3	99.7	95.7	92.9	91.8	92.9	95.7	99.7
132.5°	136.4	126.0	116.7	108.8	103.0	98.9	95.9	94.5	95.9	98.9	103.0
135°	140.2	130.5	121.4	113.7	107.2	103.0	99.7	98.5	99.7	103.0	107.2
137.5°	143.1	134.0	125.2	117.9	111.5	107.0	103.7	102.3	103.7	107.0	111.5
140°	144.7	136.0	127.6	120.3	114.2	109.7	106.4	105.3	106.4	109.7	114.2
142.5°	146.1	137.6	129.4	122.6	116.7	112.2	109.1	108.1	109.1	112.2	116.7
145°	147.8	140.0	132.4	126.3	120.6	116.5	113.7	112.5	113.7	116.5	120.6
147.5°	148.8	141.9	134.8	129.3	124.6	120.7	118.0	117.2	118.0	120.7	124.6
150°	149.2	142.8	136.3	131.3	127.1	123.4	121.2	120.3	121.2	123.4	127.1
152.5°	149.4	143.6	137.8	133.3	129.3	126.1	123.9	123.5	123.9	126.1	129.3
155°	149.7	145.0	140.2	136.0	132.9	129.8	128.2	127.9	128.2	129.8	132.9
157.5°	149.7	145.9	141.9	138.4	135.9	133.2	131.9	131.6	131.9	133.2	135.9
160°	149.7	146.4	143.1	140.0	137.7	135.5	134.4	134.0	134.4	135.5	137.7
162.5°	149.5	146.6	143.7	141.3	139.3	137.5	136.3	136.6	136.3	137.5	139.3
165°	148.9	146.9	144.4	142.8	141.3	139.7	139.1	139.4	139.1	139.7	141.3
167.5°	148.5	146.9	145.0	144.0	143.0	141.9	141.4	141.7	141.4	141.9	143.0
170°	148.1	146.6	145.3	144.4	143.9	143.1	142.8	143.3	142.8	143.1	143.9
172.5°	147.4	146.5	145.5	144.9	144.6	143.7	143.9	144.2	143.9	143.7	144.6
175°	146.6	146.1	145.5	145.3	145.3	144.7	145.0	145.3	145.0	144.7	145.3
177.5°	146.2	145.8	145.5	145.5	145.5	145.1	145.3	145.8	145.3	145.1	145.5
180°	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5



TEST NUMBER: P331707-927

CATALOG NUMBER: S122RDIP-S865D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8
2.5°	1491.3	1488.4	1482.9	1474.5	1469.4	1460.6	1454.7	1458.1	1458.9	1458.1	1457.2
5°	1451.2	1440.2	1425.0	1410.2	1396.5	1381.9	1373.4	1369.8	1362.4	1358.2	1356.1
7.5°	1402.8	1383.8	1362.2	1336.6	1314.8	1292.0	1280.3	1274.5	1259.5	1251.3	1244.1
10°	1366.6	1336.6	1315.1	1281.4	1261.0	1231.0	1210.5	1211.0	1190.5	1178.9	1170.5
12.5°	1326.7	1293.8	1257.9	1227.6	1199.1	1175.0	1150.4	1140.3	1118.6	1107.5	1084.7
15°	1260.4	1222.1	1184.2	1143.2	1114.3	1077.0	1041.2	997.6	962.4	931.9	923.5
17.5°	1188.1	1140.6	1102.6	1054.5	1005.0	942.2	900.8	875.4	854.2	838.1	826.2
20°	1138.5	1090.1	1049.6	977.2	910.4	867.8	837.3	817.8	795.8	778.5	769.0
22.5°	1086.3	1035.9	980.7	899.8	847.7	813.6	786.4	764.1	749.1	735.5	726.9
25°	1012.3	957.1	866.3	810.5	768.4	732.7	713.8	700.1	684.4	666.0	657.5
27.5°	934.1	846.4	781.1	739.7	699.5	676.3	659.3	638.8	624.7	616.5	607.7
30°	875.7	787.9	736.9	691.7	663.3	637.5	617.6	606.0	592.4	578.2	572.4
32.5°	810.5	740.4	691.5	653.9	625.0	603.1	587.3	568.6	558.7	550.0	537.9
35°	729.5	676.4	631.8	601.3	574.0	556.1	537.7	526.6	508.8	501.5	496.7
37.5°	661.0	615.0	581.6	549.5	527.8	508.0	496.8	479.3	471.5	461.3	451.3
40°	622.3	577.1	545.1	518.8	494.6	479.9	465.7	451.5	440.0	435.2	423.1
42.5°	582.8	546.1	514.0	485.1	469.0	453.4	435.5	425.0	413.0	405.4	397.9
45°	528.2	495.7	468.3	444.7	426.8	410.5	398.9	381.6	374.8	359.5	353.2
47.5°	480.3	450.0	424.0	401.5	384.0	373.4	356.5	342.9	332.0	322.7	314.5
50°	446.2	421.0	395.8	375.8	360.0	344.8	327.5	320.6	303.8	299.0	294.4
52.5°	415.1	391.2	368.0	348.5	332.7	317.9	302.6	293.7	282.3	277.7	274.2
55°	371.6	348.5	326.4	309.0	293.3	278.1	268.6	257.5	252.3	248.6	244.4
57.5°	327.9	307.0	290.2	272.6	256.7	244.6	233.7	227.0	221.6	216.7	211.8
60°	300.2	280.1	264.9	248.6	232.3	222.4	213.9	206.0	199.7	192.3	190.3
62.5°	270.7	253.3	239.2	223.4	209.2	200.0	192.0	184.6	177.1	166.3	163.3
65°	230.2	216.6	201.8	188.7	176.1	167.2	155.6	147.2	144.0	143.0	142.4
67.5°	193.6	180.7	168.1	154.6	143.1	134.9	129.0	127.7	125.5	124.8	123.4
70°	169.2	157.2	144.6	131.9	120.9	119.3	117.2	115.1	112.5	111.5	110.4
72.5°	147.3	134.9	122.2	112.2	107.4	105.4	103.3	101.2	99.4	98.4	97.8
75°	113.0	101.5	93.0	89.4	86.7	85.2	82.0	80.4	79.4	77.8	77.2
77.5°	81.4	74.9	71.0	68.7	65.9	64.2	62.4	60.8	59.7	59.4	58.5
80°	62.0	58.9	56.2	53.1	52.0	49.9	49.4	47.8	48.3	46.8	46.8
82.5°	48.2	44.1	41.9	40.5	39.5	37.7	37.2	36.4	36.6	35.4	35.4
85°	24.7	23.7	22.6	21.5	21.5	20.0	20.5	20.0	20.0	18.9	18.4
87.5°	8.6	8.4	7.8	8.2	8.6	8.2	8.2	7.7	7.6	7.7	7.3
90°	3.3	4.2	5.6	7.5	9.3	9.5	9.3	9.0	8.4	9.0	9.3
92.5°	10.1	12.7	19.0	28.0	35.9	36.4	30.7	24.4	20.9	18.6	16.9
95°	20.7	27.4	40.3	64.6	97.1	109.7	96.0	73.4	56.2	44.5	38.3
97.5°	29.4	37.0	53.2	87.1	141.1	187.3	196.5	171.1	140.0	109.7	89.5
100°	35.0	42.9	57.7	91.8	152.3	221.1	261.4	255.6	220.9	182.5	148.6
102.5°	40.2	48.0	61.7	92.1	148.0	222.2	285.6	310.9	303.0	275.0	239.1
105°	47.6	55.5	68.6	93.5	139.7	207.4	281.9	340.1	371.7	375.3	366.1
107.5°	55.0	62.9	75.7	97.4	135.5	191.5	257.3	319.0	366.7	395.8	409.3
110°	59.9	68.0	80.3	100.4	134.7	183.9	241.9	300.9	351.0	386.8	409.8



TEST NUMBER: P331707-927

CATALOG NUMBER: S122RDIP-S865D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	64.6	73.0	84.8	103.9	134.8	179.0	231.1	284.3	332.4	370.7	397.0
115°	72.2	79.8	91.8	108.8	136.0	173.6	217.8	264.0	307.0	343.7	372.6
117.5°	79.3	87.1	98.2	114.2	138.1	170.9	209.4	248.6	286.5	319.7	346.7
120°	84.0	91.8	102.7	117.9	139.4	169.4	204.9	241.0	275.7	305.4	330.8
122.5°	88.6	96.7	106.9	121.0	140.9	168.4	201.1	235.0	266.7	294.9	317.8
125°	95.5	103.3	113.4	126.0	143.3	166.8	195.7	226.2	255.0	279.6	300.6
127.5°	101.4	109.5	119.3	130.6	145.7	165.9	190.6	217.5	243.6	266.8	286.1
130°	105.3	113.0	122.9	133.5	147.5	165.4	187.3	211.9	236.0	258.1	276.6
132.5°	108.8	116.7	126.0	136.4	149.3	165.2	184.6	206.5	228.8	249.1	266.5
135°	113.7	121.4	130.5	140.2	151.5	164.9	180.8	199.0	217.5	236.0	251.6
137.5°	117.9	125.2	134.0	143.1	153.4	164.8	178.2	193.1	208.5	223.2	236.8
140°	120.3	127.6	136.0	144.7	154.2	164.6	176.6	189.2	202.6	215.6	227.8
142.5°	122.6	129.4	137.6	146.1	154.9	164.6	175.1	186.1	197.5	208.6	218.9
145°	126.3	132.4	140.0	147.8	155.6	164.0	173.0	181.6	190.9	199.6	207.7
147.5°	129.3	134.8	141.9	148.8	155.8	163.0	170.9	178.2	185.5	192.3	198.2
150°	131.3	136.3	142.8	149.2	155.6	162.3	169.1	175.8	182.0	187.8	192.8
152.5°	133.3	137.8	143.6	149.4	155.2	161.2	167.5	173.3	179.0	184.0	188.4
155°	136.0	140.2	145.0	149.7	154.5	159.2	164.6	169.9	174.4	178.6	181.6
157.5°	138.4	141.9	145.9	149.7	153.2	157.2	161.8	166.0	169.7	173.2	175.6
160°	140.0	143.1	146.4	149.7	152.6	155.9	159.8	163.4	166.5	169.6	171.6
162.5°	141.3	143.7	146.6	149.5	151.9	154.8	158.0	161.0	163.7	166.3	167.8
165°	142.8	144.4	146.9	148.9	150.6	152.6	155.0	157.3	159.2	161.2	162.3
167.5°	144.0	145.0	146.9	148.5	149.3	150.6	152.2	153.8	155.3	156.6	157.6
170°	144.4	145.3	146.6	148.1	148.6	149.5	150.6	152.0	152.8	153.9	154.5
172.5°	144.9	145.5	146.5	147.4	147.7	148.1	149.0	150.0	150.6	151.5	151.8
175°	145.3	145.5	146.1	146.6	146.4	146.6	146.9	147.8	148.1	148.4	148.6
177.5°	145.5	145.5	145.8	146.2	145.8	145.5	145.8	146.2	146.2	146.5	146.5
180°	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5



TEST NUMBER: P331707-927

CATALOG NUMBER: S122RDIP-S865D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8
2.5°	1452.6	1453.4	1452.1	1453.0	1452.1	1453.4	1452.6	1457.2	1458.1	1458.9	1458.1
5°	1353.4	1347.2	1346.1	1344.6	1346.1	1347.2	1353.4	1356.1	1358.2	1362.4	1369.8
7.5°	1235.1	1234.1	1231.5	1227.9	1231.5	1234.1	1235.1	1244.1	1251.3	1259.5	1274.5
10°	1159.0	1156.3	1155.9	1152.1	1155.9	1156.3	1159.0	1170.5	1178.9	1190.5	1211.0
12.5°	1069.8	1052.9	1051.1	1042.0	1051.1	1052.9	1069.8	1084.7	1107.5	1118.6	1140.3
15°	910.9	907.8	897.2	890.4	897.2	907.8	910.9	923.5	931.9	962.4	997.6
17.5°	820.1	809.8	806.5	805.0	806.5	809.8	820.1	826.2	838.1	854.2	875.4
20°	761.6	752.2	750.6	749.6	750.6	752.2	761.6	769.0	778.5	795.8	817.8
22.5°	721.3	711.4	707.3	704.1	707.3	711.4	721.3	726.9	735.5	749.1	764.1
25°	652.3	648.6	646.5	645.5	646.5	648.6	652.3	657.5	666.0	684.4	700.1
27.5°	598.3	590.3	588.7	586.0	588.7	590.3	598.3	607.7	616.5	624.7	638.8
30°	567.7	565.1	561.3	558.2	561.3	565.1	567.7	572.4	578.2	592.4	606.0
32.5°	531.5	529.3	526.0	524.6	526.0	529.3	531.5	537.9	550.0	558.7	568.6
35°	491.5	484.1	480.9	476.2	480.9	484.1	491.5	496.7	501.5	508.8	526.6
37.5°	449.1	445.2	440.8	442.4	440.8	445.2	449.1	451.3	461.3	471.5	479.3
40°	416.3	413.7	412.6	412.1	412.6	413.7	416.3	423.1	435.2	440.0	451.5
42.5°	390.2	382.9	380.2	380.1	380.2	382.9	390.2	397.9	405.4	413.0	425.0
45°	350.6	343.7	339.1	339.5	339.1	343.7	350.6	353.2	359.5	374.8	381.6
47.5°	310.0	309.8	306.9	307.8	306.9	309.8	310.0	314.5	322.7	332.0	342.9
50°	290.7	287.5	285.4	285.9	285.4	287.5	290.7	294.4	299.0	303.8	320.6
52.5°	272.2	269.4	267.8	270.0	267.8	269.4	272.2	274.2	277.7	282.3	293.7
55°	241.8	238.6	238.1	237.6	238.1	238.6	241.8	244.4	248.6	252.3	257.5
57.5°	207.9	205.7	202.6	201.2	202.6	205.7	207.9	211.8	216.7	221.6	227.0
60°	183.5	179.3	174.0	173.5	174.0	179.3	183.5	190.3	192.3	199.7	206.0
62.5°	161.1	160.3	159.2	159.1	159.2	160.3	161.1	163.3	166.3	177.1	184.6
65°	141.4	140.9	141.4	141.9	141.4	140.9	141.4	142.4	143.0	144.0	147.2
67.5°	123.2	122.2	121.3	121.8	121.3	122.2	123.2	123.4	124.8	125.5	127.7
70°	109.3	108.8	108.3	108.3	108.3	108.8	109.3	110.4	111.5	112.5	115.1
72.5°	95.9	95.8	95.2	94.8	95.2	95.8	95.9	97.8	98.4	99.4	101.2
75°	76.8	75.7	75.7	75.7	75.7	75.7	76.8	77.2	77.8	79.4	80.4
77.5°	58.5	57.9	57.4	57.0	57.4	57.9	58.5	58.5	59.4	59.7	60.8
80°	46.3	45.7	45.2	45.2	45.2	45.7	46.3	46.8	46.8	48.3	47.8
82.5°	35.3	34.8	34.7	34.3	34.7	34.8	35.3	35.4	35.4	36.6	36.4
85°	18.9	19.4	18.9	20.0	18.9	19.4	18.9	18.4	18.9	20.0	20.0
87.5°	7.3	6.9	7.3	6.9	7.3	6.9	7.3	7.3	7.7	7.6	7.7
90°	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.0	8.4	9.0
92.5°	16.6	15.8	15.9	15.5	15.9	15.8	16.6	16.9	18.6	20.9	24.4
95°	34.7	32.5	31.6	31.9	31.6	32.5	34.7	38.3	44.5	56.2	73.4
97.5°	76.1	69.2	65.2	62.8	65.2	69.2	76.1	89.5	109.7	140.0	171.1
100°	125.4	113.4	105.3	100.2	105.3	113.4	125.4	148.6	182.5	220.9	255.6
102.5°	213.8	193.3	183.2	176.3	183.2	193.3	213.8	239.1	275.0	303.0	310.9
105°	348.7	331.4	319.3	315.4	319.3	331.4	348.7	366.1	375.3	371.7	340.1
107.5°	411.5	410.6	408.1	403.0	408.1	410.6	411.5	409.3	395.8	366.7	319.0
110°	421.8	427.1	429.7	429.4	429.7	427.1	421.8	409.8	386.8	351.0	300.9



TEST NUMBER: P331707-927

CATALOG NUMBER: S122RDIP-S865D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	413.8	422.6	427.4	428.9	427.4	422.6	413.8	397.0	370.7	332.4	284.3
115°	392.4	405.3	412.6	415.1	412.6	405.3	392.4	372.6	343.7	307.0	264.0
117.5°	367.0	380.6	388.2	390.4	388.2	380.6	367.0	346.7	319.7	286.5	248.6
120°	350.5	363.6	371.7	374.5	371.7	363.6	350.5	330.8	305.4	275.7	241.0
122.5°	335.4	348.4	355.6	357.9	355.6	348.4	335.4	317.8	294.9	266.7	235.0
125°	316.9	327.5	334.5	336.8	334.5	327.5	316.9	300.6	279.6	255.0	226.2
127.5°	300.3	310.3	316.3	318.1	316.3	310.3	300.3	286.1	266.8	243.6	217.5
130°	290.3	299.8	305.4	307.6	305.4	299.8	290.3	276.6	258.1	236.0	211.9
132.5°	280.0	289.5	294.6	296.7	294.6	289.5	280.0	266.5	249.1	228.8	206.5
135°	263.6	272.9	278.0	279.1	278.0	272.9	263.6	251.6	236.0	217.5	199.0
137.5°	247.8	255.7	260.2	261.8	260.2	255.7	247.8	236.8	223.2	208.5	193.1
140°	236.8	244.1	248.3	249.9	248.3	244.1	236.8	227.8	215.6	202.6	189.2
142.5°	227.4	234.0	237.7	238.1	237.7	234.0	227.4	218.9	208.6	197.5	186.1
145°	214.4	219.2	222.0	222.8	222.0	219.2	214.4	207.7	199.6	190.9	181.6
147.5°	203.7	207.6	209.5	210.0	209.5	207.6	203.7	198.2	192.3	185.5	178.2
150°	197.0	200.4	202.1	202.4	202.1	200.4	197.0	192.8	187.8	182.0	175.8
152.5°	191.7	194.6	195.8	195.9	195.8	194.6	191.7	188.4	184.0	179.0	173.3
155°	184.7	186.7	187.8	187.3	187.8	186.7	184.7	181.6	178.6	174.4	169.9
157.5°	177.8	179.4	179.9	179.9	179.9	179.4	177.8	175.6	173.2	169.7	166.0
160°	173.6	174.9	175.2	175.2	175.2	174.9	173.6	171.6	169.6	166.5	163.4
162.5°	169.8	170.7	171.0	170.7	171.0	170.7	169.8	167.8	166.3	163.7	161.0
165°	163.4	164.6	164.6	164.3	164.6	164.6	163.4	162.3	161.2	159.2	157.3
167.5°	158.1	158.8	158.7	158.4	158.7	158.8	158.1	157.6	156.6	155.3	153.8
170°	154.8	155.6	155.3	154.8	155.3	155.6	154.8	154.5	153.9	152.8	152.0
172.5°	152.1	152.5	152.2	151.9	152.2	152.5	152.1	151.8	151.5	150.6	150.0
175°	148.6	148.9	148.6	148.1	148.6	148.9	148.6	148.6	148.4	148.1	147.8
177.5°	146.5	146.5	146.2	145.8	146.2	146.5	146.5	146.5	146.5	146.2	146.2
180°	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5



TEST NUMBER: P331707-927

CATALOG NUMBER: S122RDIP-S865D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8
2.5°	1454.7	1460.6	1469.4	1474.5	1482.9	1488.4	1491.3	1496.7	1499.7	1510.2	1521.1
5°	1373.4	1381.9	1396.5	1410.2	1425.0	1440.2	1451.2	1463.9	1475.4	1495.4	1516.4
7.5°	1280.3	1292.0	1314.8	1336.6	1362.2	1383.8	1402.8	1424.3	1443.6	1472.2	1502.0
10°	1210.5	1231.0	1261.0	1281.4	1315.1	1336.6	1366.6	1390.3	1417.1	1454.9	1488.6
12.5°	1150.4	1175.0	1199.1	1227.6	1257.9	1293.8	1326.7	1357.0	1388.9	1428.0	1467.5
15°	1041.2	1077.0	1114.3	1143.2	1184.2	1222.1	1260.4	1301.4	1340.3	1387.1	1438.6
17.5°	900.8	942.2	1005.0	1054.5	1102.6	1140.6	1188.1	1237.7	1283.6	1340.0	1397.3
20°	837.3	867.8	910.4	977.2	1049.6	1090.1	1138.5	1193.2	1245.7	1307.2	1368.7
22.5°	786.4	813.6	847.7	899.8	980.7	1035.9	1086.3	1141.9	1202.8	1265.6	1333.8
25°	713.8	732.7	768.4	810.5	866.3	957.1	1012.3	1068.0	1134.3	1201.6	1279.4
27.5°	659.3	676.3	699.5	739.7	781.1	846.4	934.1	994.9	1060.9	1136.6	1217.3
30°	617.6	637.5	663.3	691.7	736.9	787.9	875.7	946.1	1011.3	1089.1	1175.3
32.5°	587.3	603.1	625.0	653.9	691.5	740.4	810.5	896.0	959.6	1041.6	1131.6
35°	537.7	556.1	574.0	601.3	631.8	676.4	729.5	821.0	884.1	965.0	1055.4
37.5°	496.8	508.0	527.8	549.5	581.6	615.0	661.0	743.0	811.3	890.7	983.3
40°	465.7	479.9	494.6	518.8	545.1	577.1	622.3	683.3	761.6	839.4	929.8
42.5°	435.5	453.4	469.0	485.1	514.0	546.1	582.8	634.5	714.5	788.1	876.0
45°	398.9	410.5	426.8	444.7	468.3	495.7	528.2	573.5	650.2	713.8	796.3
47.5°	356.5	373.4	384.0	401.5	424.0	450.0	480.3	519.4	581.5	641.1	717.7
50°	327.5	344.8	360.0	375.8	395.8	421.0	446.2	484.1	534.0	596.6	668.0
52.5°	302.6	317.9	332.7	348.5	368.0	391.2	415.1	448.4	491.2	548.7	618.1
55°	268.6	278.1	293.3	309.0	326.4	348.5	371.6	399.5	436.3	484.7	540.9
57.5°	233.7	244.6	256.7	272.6	290.2	307.0	327.9	353.1	382.1	425.9	474.0
60°	213.9	222.4	232.3	248.6	264.9	280.1	300.2	321.2	348.5	386.3	427.3
62.5°	192.0	200.0	209.2	223.4	239.2	253.3	270.7	292.9	316.1	350.6	386.5
65°	155.6	167.2	176.1	188.7	201.8	216.6	230.2	248.1	268.6	296.0	328.0
67.5°	129.0	134.9	143.1	154.6	168.1	180.7	193.6	207.6	225.4	246.5	272.0
70°	117.2	119.3	120.9	131.9	144.6	157.2	169.2	182.4	197.6	215.0	237.0
72.5°	103.3	105.4	107.4	112.2	122.2	134.9	147.3	157.2	171.6	185.9	203.8
75°	82.0	85.2	86.7	89.4	93.0	101.5	113.0	122.5	130.9	141.9	156.1
77.5°	62.4	64.2	65.9	68.7	71.0	74.9	81.4	89.9	97.8	104.2	113.9
80°	49.4	49.9	52.0	53.1	56.2	58.9	62.0	68.8	76.8	79.4	86.2
82.5°	37.2	37.7	39.5	40.5	41.9	44.1	48.2	49.9	56.2	59.6	63.9
85°	20.5	20.0	21.5	21.5	22.6	23.7	24.7	27.3	28.9	33.1	34.1
87.5°	8.2	8.2	8.6	8.2	7.8	8.4	8.6	9.0	9.7	10.8	12.3
90°	9.3	9.5	9.3	7.5	5.6	4.2	3.3	2.8	2.2	1.1	0.3
92.5°	30.7	36.4	35.9	28.0	19.0	12.7	10.1	8.2	7.0	4.9	3.4
95°	96.0	109.7	97.1	64.6	40.3	27.4	20.7	16.2	13.7	10.9	9.8
97.5°	196.5	187.3	141.1	87.1	53.2	37.0	29.4	24.2	20.4	17.4	15.9
100°	261.4	221.1	152.3	91.8	57.7	42.9	35.0	29.4	24.9	22.4	21.5
102.5°	285.6	222.2	148.0	92.1	61.7	48.0	40.2	34.3	29.9	27.3	26.7
105°	281.9	207.4	139.7	93.5	68.6	55.5	47.6	41.4	37.2	35.3	34.1
107.5°	257.3	191.5	135.5	97.4	75.7	62.9	55.0	48.9	45.0	43.1	42.2
110°	241.9	183.9	134.7	100.4	80.3	68.0	59.9	54.0	50.4	48.7	47.6



TEST NUMBER: P331707-927

CATALOG NUMBER: S122RDIP-S865D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	231.1	179.0	134.8	103.9	84.8	73.0	64.6	58.9	55.5	53.6	52.5
115°	217.8	173.6	136.0	108.8	91.8	79.8	72.2	66.6	63.3	61.6	60.2
117.5°	209.4	170.9	138.1	114.2	98.2	87.1	79.3	73.9	70.9	69.2	68.1
120°	204.9	169.4	139.4	117.9	102.7	91.8	84.0	78.3	75.9	74.1	73.0
122.5°	201.1	168.4	140.9	121.0	106.9	96.7	88.6	83.1	80.3	78.7	77.8
125°	195.7	166.8	143.3	126.0	113.4	103.3	95.5	89.8	86.5	84.8	84.0
127.5°	190.6	165.9	145.7	130.6	119.3	109.5	101.4	96.1	92.4	90.0	88.9
130°	187.3	165.4	147.5	133.5	122.9	113.0	105.3	99.7	95.7	92.9	91.8
132.5°	184.6	165.2	149.3	136.4	126.0	116.7	108.8	103.0	98.9	95.9	94.5
135°	180.8	164.9	151.5	140.2	130.5	121.4	113.7	107.2	103.0	99.7	98.5
137.5°	178.2	164.8	153.4	143.1	134.0	125.2	117.9	111.5	107.0	103.7	102.3
140°	176.6	164.6	154.2	144.7	136.0	127.6	120.3	114.2	109.7	106.4	105.3
142.5°	175.1	164.6	154.9	146.1	137.6	129.4	122.6	116.7	112.2	109.1	108.1
145°	173.0	164.0	155.6	147.8	140.0	132.4	126.3	120.6	116.5	113.7	112.5
147.5°	170.9	163.0	155.8	148.8	141.9	134.8	129.3	124.6	120.7	118.0	117.2
150°	169.1	162.3	155.6	149.2	142.8	136.3	131.3	127.1	123.4	121.2	120.3
152.5°	167.5	161.2	155.2	149.4	143.6	137.8	133.3	129.3	126.1	123.9	123.5
155°	164.6	159.2	154.5	149.7	145.0	140.2	136.0	132.9	129.8	128.2	127.9
157.5°	161.8	157.2	153.2	149.7	145.9	141.9	138.4	135.9	133.2	131.9	131.6
160°	159.8	155.9	152.6	149.7	146.4	143.1	140.0	137.7	135.5	134.4	134.0
162.5°	158.0	154.8	151.9	149.5	146.6	143.7	141.3	139.3	137.5	136.3	136.6
165°	155.0	152.6	150.6	148.9	146.9	144.4	142.8	141.3	139.7	139.1	139.4
167.5°	152.2	150.6	149.3	148.5	146.9	145.0	144.0	143.0	141.9	141.4	141.7
170°	150.6	149.5	148.6	148.1	146.6	145.3	144.4	143.9	143.1	142.8	143.3
172.5°	149.0	148.1	147.7	147.4	146.5	145.5	144.9	144.6	143.7	143.9	144.2
175°	146.9	146.6	146.4	146.6	146.1	145.5	145.3	145.3	144.7	145.0	145.3
177.5°	145.8	145.5	145.8	146.2	145.8	145.5	145.5	145.5	145.1	145.3	145.8
180°	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5



TEST NUMBER: P331707-927

CATALOG NUMBER: S122RDIP-S865D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8
2.5°	1521.5	1522.8	1531.2	1535.0	1542.6	1545.5	1548.9	1548.1	1548.1	1549.7	1561.5
5°	1524.8	1535.3	1551.1	1566.4	1581.0	1593.7	1602.1	1610.5	1613.7	1628.9	1642.6
7.5°	1519.3	1538.7	1564.8	1588.0	1615.9	1637.6	1655.7	1672.0	1683.1	1705.3	1728.1
10°	1512.2	1539.5	1569.0	1598.9	1637.3	1666.2	1695.7	1718.2	1725.6	1758.7	1777.7
12.5°	1497.9	1534.5	1571.9	1610.7	1648.2	1688.1	1720.5	1743.0	1768.9	1798.6	1833.6
15°	1476.5	1518.5	1567.4	1617.3	1671.0	1719.3	1754.0	1793.4	1821.8	1854.4	1884.8
17.5°	1445.7	1499.8	1561.9	1619.8	1681.8	1733.7	1781.5	1819.2	1839.2	1857.8	1862.3
20°	1421.3	1479.6	1552.7	1621.0	1683.1	1743.0	1790.3	1821.8	1827.1	1827.6	1799.8
22.5°	1394.8	1460.7	1537.2	1607.1	1681.3	1748.0	1784.8	1798.3	1777.4	1741.8	1687.9
25°	1346.1	1422.4	1511.2	1591.0	1672.0	1735.0	1747.7	1724.0	1651.0	1574.2	1477.0
27.5°	1293.3	1379.0	1474.3	1563.1	1649.3	1688.4	1661.2	1575.9	1444.3	1329.9	1191.3
30°	1254.7	1350.8	1444.4	1543.7	1623.7	1640.5	1577.9	1452.3	1298.8	1126.4	988.2
32.5°	1210.5	1311.3	1414.1	1516.9	1583.7	1567.3	1464.0	1309.3	1129.3	959.9	829.3
35°	1147.4	1251.5	1362.4	1465.5	1508.0	1437.0	1282.5	1081.2	897.2	739.0	649.1
37.5°	1074.6	1187.9	1303.2	1397.8	1394.8	1276.5	1066.0	858.3	703.6	610.1	546.1
40°	1022.9	1137.4	1262.0	1341.9	1307.7	1153.7	925.6	729.5	616.6	541.9	495.1
42.5°	973.3	1088.2	1212.0	1275.5	1216.1	1026.7	799.5	645.9	552.6	494.4	456.5
45°	888.8	1010.3	1124.8	1160.1	1053.8	845.2	646.5	535.1	473.1	429.9	403.7
47.5°	806.3	925.7	1030.3	1030.9	887.3	685.4	545.4	463.1	410.1	376.8	357.7
50°	755.8	869.3	957.1	943.5	780.5	609.7	487.7	416.8	372.6	346.9	326.9
52.5°	699.1	809.2	885.3	846.4	690.1	536.5	436.0	376.4	339.8	317.5	299.6
55°	616.6	714.3	767.9	709.1	562.9	446.2	368.4	321.7	294.4	275.4	260.2
57.5°	535.5	616.2	649.9	581.3	463.7	370.0	311.7	276.6	249.5	235.9	228.0
60°	484.7	553.5	577.1	501.5	403.1	323.8	275.9	243.4	223.4	214.4	206.6
62.5°	434.6	490.8	500.6	431.2	351.4	283.4	242.3	214.8	201.5	193.0	185.5
65°	360.6	401.1	396.3	340.6	278.1	225.0	195.0	178.2	168.2	156.1	143.0
67.5°	296.8	321.5	306.7	264.9	212.2	174.8	155.3	142.5	130.2	118.7	115.7
70°	256.5	270.7	254.9	216.6	174.0	146.6	130.9	115.7	108.3	105.7	100.9
72.5°	217.9	222.8	205.7	172.9	141.6	121.4	106.1	97.5	93.6	91.3	88.3
75°	163.5	159.8	145.0	119.3	98.3	84.6	79.9	76.8	74.1	72.0	70.4
77.5°	114.8	109.4	96.3	79.5	68.4	61.9	59.1	57.4	56.2	55.1	53.5
80°	86.2	82.5	69.4	56.8	52.0	48.9	47.3	45.2	45.2	44.1	42.5
82.5°	63.1	58.9	47.5	41.6	39.0	37.1	36.0	34.7	34.3	34.5	33.4
85°	33.1	26.8	23.7	22.6	21.0	20.0	20.5	19.4	19.4	19.4	18.9
87.5°	10.3	8.5	8.2	7.8	8.4	8.7	8.6	9.0	9.5	9.0	9.3
90°	1.1	2.2	2.8	3.3	4.2	5.6	7.5	9.3	9.5	9.3	9.0
92.5°	4.9	7.0	8.2	10.1	12.7	19.0	28.0	35.9	36.4	30.7	24.4
95°	10.9	13.7	16.2	20.7	27.4	40.3	64.6	97.1	109.7	96.0	73.4
97.5°	17.4	20.4	24.2	29.4	37.0	53.2	87.1	141.1	187.3	196.5	171.1
100°	22.4	24.9	29.4	35.0	42.9	57.7	91.8	152.3	221.1	261.4	255.6
102.5°	27.3	29.9	34.3	40.2	48.0	61.7	92.1	148.0	222.2	285.6	310.9
105°	35.3	37.2	41.4	47.6	55.5	68.6	93.5	139.7	207.4	281.9	340.1
107.5°	43.1	45.0	48.9	55.0	62.9	75.7	97.4	135.5	191.5	257.3	319.0
110°	48.7	50.4	54.0	59.9	68.0	80.3	100.4	134.7	183.9	241.9	300.9



TEST NUMBER: P331707-927

CATALOG NUMBER: S122RDIP-S865D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	53.6	55.5	58.9	64.6	73.0	84.8	103.9	134.8	179.0	231.1	284.3
115°	61.6	63.3	66.6	72.2	79.8	91.8	108.8	136.0	173.6	217.8	264.0
117.5°	69.2	70.9	73.9	79.3	87.1	98.2	114.2	138.1	170.9	209.4	248.6
120°	74.1	75.9	78.3	84.0	91.8	102.7	117.9	139.4	169.4	204.9	241.0
122.5°	78.7	80.3	83.1	88.6	96.7	106.9	121.0	140.9	168.4	201.1	235.0
125°	84.8	86.5	89.8	95.5	103.3	113.4	126.0	143.3	166.8	195.7	226.2
127.5°	90.0	92.4	96.1	101.4	109.5	119.3	130.6	145.7	165.9	190.6	217.5
130°	92.9	95.7	99.7	105.3	113.0	122.9	133.5	147.5	165.4	187.3	211.9
132.5°	95.9	98.9	103.0	108.8	116.7	126.0	136.4	149.3	165.2	184.6	206.5
135°	99.7	103.0	107.2	113.7	121.4	130.5	140.2	151.5	164.9	180.8	199.0
137.5°	103.7	107.0	111.5	117.9	125.2	134.0	143.1	153.4	164.8	178.2	193.1
140°	106.4	109.7	114.2	120.3	127.6	136.0	144.7	154.2	164.6	176.6	189.2
142.5°	109.1	112.2	116.7	122.6	129.4	137.6	146.1	154.9	164.6	175.1	186.1
145°	113.7	116.5	120.6	126.3	132.4	140.0	147.8	155.6	164.0	173.0	181.6
147.5°	118.0	120.7	124.6	129.3	134.8	141.9	148.8	155.8	163.0	170.9	178.2
150°	121.2	123.4	127.1	131.3	136.3	142.8	149.2	155.6	162.3	169.1	175.8
152.5°	123.9	126.1	129.3	133.3	137.8	143.6	149.4	155.2	161.2	167.5	173.3
155°	128.2	129.8	132.9	136.0	140.2	145.0	149.7	154.5	159.2	164.6	169.9
157.5°	131.9	133.2	135.9	138.4	141.9	145.9	149.7	153.2	157.2	161.8	166.0
160°	134.4	135.5	137.7	140.0	143.1	146.4	149.7	152.6	155.9	159.8	163.4
162.5°	136.3	137.5	139.3	141.3	143.7	146.6	149.5	151.9	154.8	158.0	161.0
165°	139.1	139.7	141.3	142.8	144.4	146.9	148.9	150.6	152.6	155.0	157.3
167.5°	141.4	141.9	143.0	144.0	145.0	146.9	148.5	149.3	150.6	152.2	153.8
170°	142.8	143.1	143.9	144.4	145.3	146.6	148.1	148.6	149.5	150.6	152.0
172.5°	143.9	143.7	144.6	144.9	145.5	146.5	147.4	147.7	148.1	149.0	150.0
175°	145.0	144.7	145.3	145.3	145.5	146.1	146.6	146.4	146.6	146.9	147.8
177.5°	145.3	145.1	145.5	145.5	145.5	145.8	146.2	145.8	145.5	145.8	146.2
180°	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5



TEST NUMBER: P331707-927

CATALOG NUMBER: S122RDIP-S865D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8
2.5°	1565.7	1571.2	1573.7	1573.7	1576.7	1575.4	1574.1
5°	1655.7	1665.7	1667.8	1677.3	1684.1	1682.0	1683.1
7.5°	1745.2	1761.3	1777.1	1784.4	1785.5	1789.7	1791.3
10°	1800.2	1813.4	1838.1	1834.4	1852.8	1863.3	1845.9
12.5°	1853.2	1871.0	1888.2	1892.8	1903.3	1906.6	1899.8
15°	1901.2	1910.7	1911.7	1909.1	1912.2	1909.6	1899.6
17.5°	1856.4	1841.0	1809.9	1795.2	1783.5	1766.3	1759.4
20°	1782.4	1737.2	1684.6	1663.6	1638.9	1590.5	1602.1
22.5°	1622.6	1571.1	1518.5	1457.1	1427.8	1382.0	1379.2
25°	1374.0	1285.2	1187.4	1119.0	1079.1	1033.4	1013.4
27.5°	1068.3	956.4	876.3	835.8	798.8	762.6	761.1
30°	867.3	783.2	721.1	686.4	663.8	648.6	651.8
32.5°	731.0	673.4	631.6	602.8	586.1	574.6	574.4
35°	597.6	558.2	531.4	519.3	507.2	498.8	499.3
37.5°	511.4	487.7	472.9	459.5	451.9	447.8	445.5
40°	467.3	447.8	436.3	428.4	422.1	416.3	415.3
42.5°	432.4	416.3	404.7	398.5	392.6	388.6	387.5
45°	383.7	370.6	360.0	353.2	350.6	346.9	346.9
47.5°	341.4	328.4	320.2	315.9	311.4	309.0	308.9
50°	312.8	302.8	295.4	292.8	289.1	287.5	287.0
52.5°	287.1	279.6	274.4	272.6	271.0	269.0	269.3
55°	252.3	248.1	246.0	244.4	241.8	238.6	240.7
57.5°	223.0	219.4	213.7	208.7	206.4	204.1	205.0
60°	202.4	195.0	187.7	181.9	180.3	175.5	175.5
62.5°	176.3	166.0	156.9	153.7	152.1	149.9	149.5
65°	135.6	131.4	129.3	127.2	126.1	126.1	125.1
67.5°	112.4	110.7	108.4	107.9	106.8	106.5	106.2
70°	99.3	97.2	96.2	95.7	94.6	95.1	93.6
72.5°	86.7	85.1	84.8	83.5	82.9	82.9	81.8
75°	68.4	68.4	67.8	67.3	66.2	65.7	66.2
77.5°	52.6	52.7	51.7	51.7	51.5	51.7	51.1
80°	42.1	42.5	42.1	41.5	41.0	41.5	41.0
82.5°	33.2	32.5	32.4	32.2	32.2	31.8	31.8
85°	18.9	19.4	18.9	18.4	18.4	18.4	18.9
87.5°	8.8	9.0	9.0	9.0	9.0	9.0	8.6
90°	8.4	9.0	9.3	9.3	9.3	9.3	9.3
92.5°	20.9	18.6	16.9	16.6	15.8	15.9	15.5
95°	56.2	44.5	38.3	34.7	32.5	31.6	31.9
97.5°	140.0	109.7	89.5	76.1	69.2	65.2	62.8
100°	220.9	182.5	148.6	125.4	113.4	105.3	100.2
102.5°	303.0	275.0	239.1	213.8	193.3	183.2	176.3
105°	371.7	375.3	366.1	348.7	331.4	319.3	315.4
107.5°	366.7	395.8	409.3	411.5	410.6	408.1	403.0
110°	351.0	386.8	409.8	421.8	427.1	429.7	429.4



TEST NUMBER: P331707-927

CATALOG NUMBER: S122RDIP-S865D330U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	332.4	370.7	397.0	413.8	422.6	427.4	428.9
115°	307.0	343.7	372.6	392.4	405.3	412.6	415.1
117.5°	286.5	319.7	346.7	367.0	380.6	388.2	390.4
120°	275.7	305.4	330.8	350.5	363.6	371.7	374.5
122.5°	266.7	294.9	317.8	335.4	348.4	355.6	357.9
125°	255.0	279.6	300.6	316.9	327.5	334.5	336.8
127.5°	243.6	266.8	286.1	300.3	310.3	316.3	318.1
130°	236.0	258.1	276.6	290.3	299.8	305.4	307.6
132.5°	228.8	249.1	266.5	280.0	289.5	294.6	296.7
135°	217.5	236.0	251.6	263.6	272.9	278.0	279.1
137.5°	208.5	223.2	236.8	247.8	255.7	260.2	261.8
140°	202.6	215.6	227.8	236.8	244.1	248.3	249.9
142.5°	197.5	208.6	218.9	227.4	234.0	237.7	238.1
145°	190.9	199.6	207.7	214.4	219.2	222.0	222.8
147.5°	185.5	192.3	198.2	203.7	207.6	209.5	210.0
150°	182.0	187.8	192.8	197.0	200.4	202.1	202.4
152.5°	179.0	184.0	188.4	191.7	194.6	195.8	195.9
155°	174.4	178.6	181.6	184.7	186.7	187.8	187.3
157.5°	169.7	173.2	175.6	177.8	179.4	179.9	179.9
160°	166.5	169.6	171.6	173.6	174.9	175.2	175.2
162.5°	163.7	166.3	167.8	169.8	170.7	171.0	170.7
165°	159.2	161.2	162.3	163.4	164.6	164.6	164.3
167.5°	155.3	156.6	157.6	158.1	158.8	158.7	158.4
170°	152.8	153.9	154.5	154.8	155.6	155.3	154.8
172.5°	150.6	151.5	151.8	152.1	152.5	152.2	151.9
175°	148.1	148.4	148.6	148.6	148.9	148.6	148.1
177.5°	146.2	146.5	146.5	146.5	146.5	146.2	145.8
180°	145.5	145.5	145.5	145.5	145.5	145.5	145.5

(END OF REPORT)