

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331713-927

Luminaire Tested: **S122RDIP-S865D530U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331713-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S865D530U927-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4251.2 lumens
Efficiency: N/A
Efficacy: 87.1 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331713-927

CATALOG NUMBER: S122RDIP-S865D530U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331713-927

CATALOG NUMBER: S122RDIP-S865D530U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	97	94	90	95	91	88	85	80	78	76	70	68	67	60	59	58	54
2	93	86	80	76	87	81	76	72	71	68	64	63	60	57	54	52	51	47
3	86	77	70	64	80	72	66	61	64	59	55	56	53	50	49	47	44	41
4	79	69	61	55	74	65	58	53	58	52	48	51	47	44	45	42	39	36
5	73	62	54	48	68	59	52	46	52	47	42	46	42	39	41	38	35	32
6	68	56	48	43	63	53	46	41	48	42	38	42	38	35	38	34	31	29
7	63	51	43	38	59	49	42	37	44	38	34	39	34	31	35	31	28	26
8	59	47	39	34	55	45	38	33	40	35	31	36	32	28	32	29	26	24
9	55	43	36	31	52	41	34	30	37	32	28	33	29	26	30	26	24	22
10	52	40	33	28	49	38	32	27	34	29	25	31	27	24	28	24	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	24425	24425	24425	24425
5°	27279	24577	21793	24577
10°	30263	24405	18889	24405
15°	31753	24047	14883	24047
20°	27527	23517	12880	23517
25°	18054	22792	11500	22792
30°	12152	21912	10407	21912
35°	9841	20802	9386	20802
40°	8753	19597	8686	19597
45°	7921	18182	7752	18182
50°	7209	16779	7181	16779
55°	6776	15226	6688	15226
60°	5667	13798	5603	13798
65°	4779	12531	5421	12531
70°	4419	11188	5113	11188
75°	4130	9738	4722	9738
80°	3812	8015	4203	8015
85°	3501	6317	3705	6317



TEST NUMBER: P331713-927

CATALOG NUMBER: S122RDIP-S865D530U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.4	3.4
10°-20°	399.6	9.4
20°-30°	514.9	12.1
30°-40°	489.3	11.5
40°-50°	419.2	9.9
50°-60°	319.2	7.5
60°-70°	201.8	4.7
70°-80°	100.8	2.4
80°-90°	28.3	0.7
90°-100°	93.9	2.2
100°-110°	318.8	7.5
110°-120°	338.6	8.0
120°-130°	278.8	6.6
130°-140°	223.9	5.3
140°-150°	169.2	4.0
150°-160°	118.9	2.8
160°-170°	70.0	1.6
170°-180°	22.8	0.5
0°-30°	1057.9	24.9
0°-40°	1547.2	36.4
0°-60°	2285.6	53.8
0°-90°	2616.4	61.5
90°-120°	751.3	17.7
90°-150°	1423.1	33.5
90°-180°	1635.0	38.5
0°-180°	4251.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1513	1513	1513	1513	1513	
5°	1683	1516	1345	1516	1683	166
15°	1900	1439	890	1439	1900	512
25°	1013	1279	646	1279	1013	481
35°	499	1055	476	1055	499	319
45°	347	796	340	796	347	269
55°	241	541	238	541	241	211
65°	125	328	142	328	125	127
75°	66	156	76	156	66	70
85°	19	34	20	34	19	21
90°	15	0	15	0	15	9
95°	52	16	52	16	52	67
105°	509	55	509	55	509	493
115°	670	97	670	97	670	656
125°	544	136	544	136	544	491
135°	450	159	450	159	450	350
145°	360	182	360	182	360	228
155°	302	206	302	206	302	141
165°	265	225	265	225	265	76
175°	239	234	239	234	239	23
180°	235	235	235	235	235	



TEST NUMBER: P331713-927

CATALOG NUMBER: S122RDIP-S865D530U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8
2.5°	1574.1	1575.4	1576.7	1573.7	1573.7	1571.2	1565.7	1561.5	1549.7	1548.1	1548.1
5°	1683.1	1682.0	1684.1	1677.3	1667.8	1665.7	1655.7	1642.6	1628.9	1613.7	1610.5
7.5°	1791.3	1789.7	1785.5	1784.4	1777.1	1761.3	1745.2	1728.1	1705.3	1683.1	1672.0
10°	1845.9	1863.3	1852.8	1834.4	1838.1	1813.4	1800.2	1777.7	1758.7	1725.6	1718.2
12.5°	1899.8	1906.6	1903.3	1892.8	1888.2	1871.0	1853.2	1833.6	1798.6	1768.9	1743.0
15°	1899.6	1909.6	1912.2	1909.1	1911.7	1910.7	1901.2	1884.8	1854.4	1821.8	1793.4
17.5°	1759.4	1766.3	1783.5	1795.2	1809.9	1841.0	1856.4	1862.3	1857.8	1839.2	1819.2
20°	1602.1	1590.5	1638.9	1663.6	1684.6	1737.2	1782.4	1799.8	1827.6	1827.1	1821.8
22.5°	1379.2	1382.0	1427.8	1457.1	1518.5	1571.1	1622.6	1687.9	1741.8	1777.4	1798.3
25°	1013.4	1033.4	1079.1	1119.0	1187.4	1285.2	1374.0	1477.0	1574.2	1651.0	1724.0
27.5°	761.1	762.6	798.8	835.8	876.3	956.4	1068.3	1191.3	1329.9	1444.3	1575.9
30°	651.8	648.6	663.8	686.4	721.1	783.2	867.3	988.2	1126.4	1298.8	1452.3
32.5°	574.4	574.6	586.1	602.8	631.6	673.4	731.0	829.3	959.9	1129.3	1309.3
35°	499.3	498.8	507.2	519.3	531.4	558.2	597.6	649.1	739.0	897.2	1081.2
37.5°	445.5	447.8	451.9	459.5	472.9	487.7	511.4	546.1	610.1	703.6	858.3
40°	415.3	416.3	422.1	428.4	436.3	447.8	467.3	495.1	541.9	616.6	729.5
42.5°	387.5	388.6	392.6	398.5	404.7	416.3	432.4	456.5	494.4	552.6	645.9
45°	346.9	346.9	350.6	353.2	360.0	370.6	383.7	403.7	429.9	473.1	535.1
47.5°	308.9	309.0	311.4	315.9	320.2	328.4	341.4	357.7	376.8	410.1	463.1
50°	287.0	287.5	289.1	292.8	295.4	302.8	312.8	326.9	346.9	372.6	416.8
52.5°	269.3	269.0	271.0	272.6	274.4	279.6	287.1	299.6	317.5	339.8	376.4
55°	240.7	238.6	241.8	244.4	246.0	248.1	252.3	260.2	275.4	294.4	321.7
57.5°	205.0	204.1	206.4	208.7	213.7	219.4	223.0	228.0	235.9	249.5	276.6
60°	175.5	175.5	180.3	181.9	187.7	195.0	202.4	206.6	214.4	223.4	243.4
62.5°	149.5	149.9	152.1	153.7	156.9	166.0	176.3	185.5	193.0	201.5	214.8
65°	125.1	126.1	126.1	127.2	129.3	131.4	135.6	143.0	156.1	168.2	178.2
67.5°	106.2	106.5	106.8	107.9	108.4	110.7	112.4	115.7	118.7	130.2	142.5
70°	93.6	95.1	94.6	95.7	96.2	97.2	99.3	100.9	105.7	108.3	115.7
72.5°	81.8	82.9	82.9	83.5	84.8	85.1	86.7	88.3	91.3	93.6	97.5
75°	66.2	65.7	66.2	67.3	67.8	68.4	68.4	70.4	72.0	74.1	76.8
77.5°	51.1	51.7	51.5	51.7	51.7	52.7	52.6	53.5	55.1	56.2	57.4
80°	41.0	41.5	41.0	41.5	42.1	42.5	42.1	42.5	44.1	45.2	45.2
82.5°	31.8	31.8	32.2	32.2	32.4	32.5	33.2	33.4	34.5	34.3	34.7
85°	18.9	18.4	18.4	18.4	18.9	19.4	18.9	18.9	19.4	19.4	19.4
87.5°	9.7	10.1	10.1	10.1	10.1	10.1	9.8	10.5	10.1	10.6	10.1
90°	14.9	14.9	14.9	14.9	14.9	14.4	13.5	14.4	14.9	15.4	14.9
92.5°	25.0	25.7	25.4	26.9	27.2	30.0	33.8	39.4	49.6	58.7	57.9
95°	51.5	51.0	52.4	56.0	61.9	71.9	90.8	118.4	155.0	177.1	156.8
97.5°	101.4	105.2	111.8	122.9	144.5	177.1	226.0	276.2	317.1	302.3	227.7
100°	161.8	169.8	183.0	202.4	239.9	294.5	356.5	412.5	421.9	356.9	245.7
102.5°	284.6	295.6	312.0	345.2	385.9	443.9	489.1	501.8	461.0	358.7	238.9
105°	509.1	515.5	534.9	562.9	590.9	605.9	599.9	548.9	455.0	334.8	225.5
107.5°	650.4	658.8	662.7	664.2	660.7	638.8	591.8	514.9	415.3	309.1	218.7
110°	693.0	693.5	689.4	680.8	661.4	624.3	566.5	485.7	390.3	296.8	217.3



TEST NUMBER: P331713-927

CATALOG NUMBER: S122RDIP-S865D530U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	692.3	689.8	682.1	667.8	640.8	598.3	536.5	458.9	373.0	288.8	217.7
115°	669.9	665.9	654.2	633.3	601.3	554.8	495.6	426.0	351.5	280.1	219.6
117.5°	630.1	626.7	614.3	592.4	559.7	516.0	462.3	401.2	337.9	275.8	222.8
120°	604.4	599.9	586.8	565.6	534.0	492.9	445.0	389.0	330.7	273.3	225.0
122.5°	577.7	573.9	562.3	541.4	513.0	475.9	430.6	379.2	324.6	271.9	227.5
125°	543.5	539.9	528.5	511.4	485.2	451.3	411.5	365.0	315.8	269.3	231.3
127.5°	513.5	510.6	500.8	484.7	461.9	430.6	393.2	351.0	307.7	267.8	235.2
130°	496.5	492.9	483.9	468.5	446.3	416.5	380.9	342.0	302.2	267.0	238.1
132.5°	478.8	475.5	467.2	451.9	430.1	402.1	369.3	333.4	297.9	266.6	241.0
135°	450.4	448.6	440.5	425.6	406.2	380.9	351.0	321.2	291.8	266.1	244.4
137.5°	422.6	419.9	412.7	399.9	382.2	360.1	336.5	311.6	287.6	266.0	247.5
140°	403.5	400.7	394.0	382.2	367.7	347.8	327.1	305.4	285.1	265.6	248.9
142.5°	384.3	383.7	377.7	367.0	353.3	336.7	318.8	300.3	282.6	265.6	250.0
145°	359.6	358.2	353.7	346.0	335.3	322.1	308.1	293.2	279.2	264.7	251.2
147.5°	338.9	338.1	335.0	328.9	320.0	310.4	299.4	287.7	275.8	263.1	251.5
150°	326.6	326.1	323.4	318.1	311.2	303.2	293.7	283.7	272.9	262.1	251.2
152.5°	316.2	316.1	314.1	309.3	304.0	297.0	289.0	279.7	270.4	260.2	250.5
155°	302.2	303.2	301.3	298.2	293.2	288.2	281.5	274.3	265.6	257.1	249.4
157.5°	290.4	290.4	289.6	286.9	283.4	279.6	273.9	267.8	261.2	253.8	247.3
160°	282.8	282.8	282.3	280.1	276.9	273.8	268.8	263.8	257.9	251.7	246.2
162.5°	275.6	275.9	275.5	273.9	270.8	268.4	264.1	259.8	255.1	249.9	245.1
165°	265.2	265.6	265.6	263.8	262.1	260.2	257.1	253.9	250.3	246.2	243.0
167.5°	255.6	256.2	256.3	255.2	254.4	252.8	250.6	248.2	245.6	243.0	241.0
170°	249.9	250.7	251.2	249.9	249.4	248.5	246.7	245.3	243.0	241.2	239.9
172.5°	245.1	245.7	246.1	245.5	245.0	244.5	243.0	242.1	240.5	239.1	238.4
175°	239.0	239.9	240.3	239.9	239.9	239.5	239.0	238.5	237.2	236.7	236.3
177.5°	235.3	236.0	236.4	236.4	236.4	236.4	236.0	236.0	235.3	234.9	235.3
180°	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9



TEST NUMBER: P331713-927

CATALOG NUMBER: S122RDIP-S865D530U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8
2.5°	1548.9	1545.5	1542.6	1535.0	1531.2	1522.8	1521.5	1521.1	1510.2	1499.7	1496.7
5°	1602.1	1593.7	1581.0	1566.4	1551.1	1535.3	1524.8	1516.4	1495.4	1475.4	1463.9
7.5°	1655.7	1637.6	1615.9	1588.0	1564.8	1538.7	1519.3	1502.0	1472.2	1443.6	1424.3
10°	1695.7	1666.2	1637.3	1598.9	1569.0	1539.5	1512.2	1488.6	1454.9	1417.1	1390.3
12.5°	1720.5	1688.1	1648.2	1610.7	1571.9	1534.5	1497.9	1467.5	1428.0	1388.9	1357.0
15°	1754.0	1719.3	1671.0	1617.3	1567.4	1518.5	1476.5	1438.6	1387.1	1340.3	1301.4
17.5°	1781.5	1733.7	1681.8	1619.8	1561.9	1499.8	1445.7	1397.3	1340.0	1283.6	1237.7
20°	1790.3	1743.0	1683.1	1621.0	1552.7	1479.6	1421.3	1368.7	1307.2	1245.7	1193.2
22.5°	1784.8	1748.0	1681.3	1607.1	1537.2	1460.7	1394.8	1333.8	1265.6	1202.8	1141.9
25°	1747.7	1735.0	1672.0	1591.0	1511.2	1422.4	1346.1	1279.4	1201.6	1134.3	1068.0
27.5°	1661.2	1688.4	1649.3	1563.1	1474.3	1379.0	1293.3	1217.3	1136.6	1060.9	994.9
30°	1577.9	1640.5	1623.7	1543.7	1444.4	1350.8	1254.7	1175.3	1089.1	1011.3	946.1
32.5°	1464.0	1567.3	1583.7	1516.9	1414.1	1311.3	1210.5	1131.6	1041.6	959.6	896.0
35°	1282.5	1437.0	1508.0	1465.5	1362.4	1251.5	1147.4	1055.4	965.0	884.1	821.0
37.5°	1066.0	1276.5	1394.8	1397.8	1303.2	1187.9	1074.6	983.3	890.7	811.3	743.0
40°	925.6	1153.7	1307.7	1341.9	1262.0	1137.4	1022.9	929.8	839.4	761.6	683.3
42.5°	799.5	1026.7	1216.1	1275.5	1212.0	1088.2	973.3	876.0	788.1	714.5	634.5
45°	646.5	845.2	1053.8	1160.1	1124.8	1010.3	888.8	796.3	713.8	650.2	573.5
47.5°	545.4	685.4	887.3	1030.9	1030.3	925.7	806.3	717.7	641.1	581.5	519.4
50°	487.7	609.7	780.5	943.5	957.1	869.3	755.8	668.0	596.6	534.0	484.1
52.5°	436.0	536.5	690.1	846.4	885.3	809.2	699.1	618.1	548.7	491.2	448.4
55°	368.4	446.2	562.9	709.1	767.9	714.3	616.6	540.9	484.7	436.3	399.5
57.5°	311.7	370.0	463.7	581.3	649.9	616.2	535.5	474.0	425.9	382.1	353.1
60°	275.9	323.8	403.1	501.5	577.1	553.5	484.7	427.3	386.3	348.5	321.2
62.5°	242.3	283.4	351.4	431.2	500.6	490.8	434.6	386.5	350.6	316.1	292.9
65°	195.0	225.0	278.1	340.6	396.3	401.1	360.6	328.0	296.0	268.6	248.1
67.5°	155.3	174.8	212.2	264.9	306.7	321.5	296.8	272.0	246.5	225.4	207.6
70°	130.9	146.6	174.0	216.6	254.9	270.7	256.5	237.0	215.0	197.6	182.4
72.5°	106.1	121.4	141.6	172.9	205.7	222.8	217.9	203.8	185.9	171.6	157.2
75°	79.9	84.6	98.3	119.3	145.0	159.8	163.5	156.1	141.9	130.9	122.5
77.5°	59.1	61.9	68.4	79.5	96.3	109.4	114.8	113.9	104.2	97.8	89.9
80°	47.3	48.9	52.0	56.8	69.4	82.5	86.2	86.2	79.4	76.8	68.8
82.5°	36.0	37.1	39.0	41.6	47.5	58.9	63.1	63.9	59.6	56.2	49.9
85°	20.5	20.0	21.0	22.6	23.7	26.8	33.1	34.1	33.1	28.9	27.3
87.5°	9.6	9.3	9.0	8.2	8.5	8.7	10.5	12.3	10.9	10.0	9.3
90°	12.2	9.0	6.8	5.4	4.5	3.6	1.8	0.5	1.8	3.6	4.5
92.5°	45.1	30.7	20.5	16.2	13.2	11.2	7.9	5.5	7.9	11.2	13.2
95°	104.3	65.0	44.3	33.4	26.2	22.1	17.6	15.8	17.6	22.1	26.2
97.5°	140.6	85.9	59.7	47.5	39.1	33.0	28.2	25.7	28.2	33.0	39.1
100°	148.2	93.1	69.2	56.5	47.5	40.2	36.1	34.8	36.1	40.2	47.5
102.5°	148.5	99.6	77.4	64.8	55.4	48.2	44.1	43.1	44.1	48.2	55.4
105°	150.9	110.7	89.4	76.8	66.9	60.0	57.0	55.1	57.0	60.0	66.9
107.5°	157.1	122.1	101.5	88.7	78.9	72.6	69.6	68.1	69.6	72.6	78.9
110°	162.2	129.7	109.8	96.6	87.2	81.4	78.6	76.8	78.6	81.4	87.2



TEST NUMBER: P331713-927

CATALOG NUMBER: S122RDIP-S865D530U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	167.6	136.9	117.7	104.3	95.1	89.6	86.6	84.8	86.6	89.6	95.1
115°	175.7	148.2	128.7	116.5	107.5	102.1	99.4	97.1	99.4	102.1	107.5
117.5°	184.4	158.6	140.6	127.9	119.3	114.5	111.8	110.0	111.8	114.5	119.3
120°	190.2	165.8	148.2	135.5	126.5	122.4	119.7	117.9	119.7	122.4	126.5
122.5°	195.3	172.7	156.1	143.1	134.1	129.7	127.0	125.5	127.0	129.7	134.1
125°	203.3	183.0	166.7	154.1	145.0	139.6	136.9	135.5	136.9	139.6	145.0
127.5°	210.8	192.6	176.7	163.7	155.0	149.1	145.3	143.5	145.3	149.1	155.0
130°	215.5	198.4	182.5	169.8	160.8	154.5	150.0	148.2	150.0	154.5	160.8
132.5°	220.2	203.4	188.3	175.6	166.3	159.5	154.7	152.5	154.7	159.5	166.3
135°	226.3	210.6	196.1	183.4	173.0	166.3	160.8	159.0	160.8	166.3	173.0
137.5°	231.0	216.3	202.0	190.3	180.0	172.8	167.3	165.2	167.3	172.8	180.0
140°	233.5	219.6	206.0	194.2	184.3	177.1	171.7	169.8	171.7	177.1	184.3
142.5°	235.8	222.1	208.9	197.9	188.3	181.1	176.0	174.6	176.0	181.1	188.3
145°	238.5	225.9	213.7	203.7	194.7	187.9	183.4	181.6	183.4	187.9	194.7
147.5°	240.1	228.9	217.5	208.7	201.1	194.9	190.5	189.2	190.5	194.9	201.1
150°	240.8	230.4	220.0	211.9	205.1	199.2	195.6	194.2	195.6	199.2	205.1
152.5°	241.1	231.9	222.5	215.2	208.7	203.6	199.9	199.3	199.9	203.6	208.7
155°	241.7	234.0	226.3	219.6	214.6	209.6	206.9	206.4	206.9	209.6	214.6
157.5°	241.7	235.5	229.0	223.4	219.4	215.1	212.9	212.4	212.9	215.1	219.4
160°	241.7	236.3	230.8	225.9	222.3	218.6	216.8	216.4	216.8	218.6	222.3
162.5°	241.3	236.6	232.0	228.1	224.8	221.9	220.1	220.4	220.1	221.9	224.8
165°	240.3	237.2	233.1	230.4	228.1	225.5	224.5	225.0	224.5	225.5	228.1
167.5°	239.7	237.1	234.1	232.4	230.8	229.0	228.2	228.8	228.2	229.0	230.8
170°	239.0	236.7	234.5	233.1	232.2	230.8	230.4	231.3	230.4	230.8	232.2
172.5°	237.9	236.4	234.8	233.9	233.3	232.0	232.2	232.7	232.2	232.0	233.3
175°	236.7	235.8	234.9	234.5	234.5	233.5	234.0	234.5	234.0	233.5	234.5
177.5°	236.0	235.3	234.9	234.9	234.9	234.2	234.6	235.3	234.6	234.2	234.9
180°	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9



TEST NUMBER: P331713-927

CATALOG NUMBER: S122RDIP-S865D530U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8
2.5°	1491.3	1488.4	1482.9	1474.5	1469.4	1460.6	1454.7	1458.1	1458.9	1458.1	1457.2
5°	1451.2	1440.2	1425.0	1410.2	1396.5	1381.9	1373.4	1369.8	1362.4	1358.2	1356.1
7.5°	1402.8	1383.8	1362.2	1336.6	1314.8	1292.0	1280.3	1274.5	1259.5	1251.3	1244.1
10°	1366.6	1336.6	1315.1	1281.4	1261.0	1231.0	1210.5	1211.0	1190.5	1178.9	1170.5
12.5°	1326.7	1293.8	1257.9	1227.6	1199.1	1175.0	1150.4	1140.3	1118.6	1107.5	1084.7
15°	1260.4	1222.1	1184.2	1143.2	1114.3	1077.0	1041.2	997.6	962.4	931.9	923.5
17.5°	1188.1	1140.6	1102.6	1054.5	1005.0	942.2	900.8	875.4	854.2	838.1	826.2
20°	1138.5	1090.1	1049.6	977.2	910.4	867.8	837.3	817.8	795.8	778.5	769.0
22.5°	1086.3	1035.9	980.7	899.8	847.7	813.6	786.4	764.1	749.1	735.5	726.9
25°	1012.3	957.1	866.3	810.5	768.4	732.7	713.8	700.1	684.4	666.0	657.5
27.5°	934.1	846.4	781.1	739.7	699.5	676.3	659.3	638.8	624.7	616.5	607.7
30°	875.7	787.9	736.9	691.7	663.3	637.5	617.6	606.0	592.4	578.2	572.4
32.5°	810.5	740.4	691.5	653.9	625.0	603.1	587.3	568.6	558.7	550.0	537.9
35°	729.5	676.4	631.8	601.3	574.0	556.1	537.7	526.6	508.8	501.5	496.7
37.5°	661.0	615.0	581.6	549.5	527.8	508.0	496.8	479.3	471.5	461.3	451.3
40°	622.3	577.1	545.1	518.8	494.6	479.9	465.7	451.5	440.0	435.2	423.1
42.5°	582.8	546.1	514.0	485.1	469.0	453.4	435.5	425.0	413.0	405.4	397.9
45°	528.2	495.7	468.3	444.7	426.8	410.5	398.9	381.6	374.8	359.5	353.2
47.5°	480.3	450.0	424.0	401.5	384.0	373.4	356.5	342.9	332.0	322.7	314.5
50°	446.2	421.0	395.8	375.8	360.0	344.8	327.5	320.6	303.8	299.0	294.4
52.5°	415.1	391.2	368.0	348.5	332.7	317.9	302.6	293.7	282.3	277.7	274.2
55°	371.6	348.5	326.4	309.0	293.3	278.1	268.6	257.5	252.3	248.6	244.4
57.5°	327.9	307.0	290.2	272.6	256.7	244.6	233.7	227.0	221.6	216.7	211.8
60°	300.2	280.1	264.9	248.6	232.3	222.4	213.9	206.0	199.7	192.3	190.3
62.5°	270.7	253.3	239.2	223.4	209.2	200.0	192.0	184.6	177.1	166.3	163.3
65°	230.2	216.6	201.8	188.7	176.1	167.2	155.6	147.2	144.0	143.0	142.4
67.5°	193.6	180.7	168.1	154.6	143.1	134.9	129.0	127.7	125.5	124.8	123.4
70°	169.2	157.2	144.6	131.9	120.9	119.3	117.2	115.1	112.5	111.5	110.4
72.5°	147.3	134.9	122.2	112.2	107.4	105.4	103.3	101.2	99.4	98.4	97.8
75°	113.0	101.5	93.0	89.4	86.7	85.2	82.0	80.4	79.4	77.8	77.2
77.5°	81.4	74.9	71.0	68.7	65.9	64.2	62.4	60.8	59.7	59.4	58.5
80°	62.0	58.9	56.2	53.1	52.0	49.9	49.4	47.8	48.3	46.8	46.8
82.5°	48.2	44.1	41.9	40.5	39.5	37.7	37.2	36.4	36.6	35.4	35.4
85°	24.7	23.7	22.6	21.5	21.5	20.0	20.5	20.0	20.0	18.9	18.4
87.5°	9.1	9.0	8.6	9.2	9.7	9.3	9.3	8.8	8.6	8.8	8.5
90°	5.4	6.8	9.0	12.2	14.9	15.4	14.9	14.4	13.5	14.4	14.9
92.5°	16.2	20.5	30.7	45.1	57.9	58.7	49.6	39.4	33.8	30.0	27.2
95°	33.4	44.3	65.0	104.3	156.8	177.1	155.0	118.4	90.8	71.9	61.9
97.5°	47.5	59.7	85.9	140.6	227.7	302.3	317.1	276.2	226.0	177.1	144.5
100°	56.5	69.2	93.1	148.2	245.7	356.9	421.9	412.5	356.5	294.5	239.9
102.5°	64.8	77.4	99.6	148.5	238.9	358.7	461.0	501.8	489.1	443.9	385.9
105°	76.8	89.4	110.7	150.9	225.5	334.8	455.0	548.9	599.9	605.9	590.9
107.5°	88.7	101.5	122.1	157.1	218.7	309.1	415.3	514.9	591.8	638.8	660.7
110°	96.6	109.8	129.7	162.2	217.3	296.8	390.3	485.7	566.5	624.3	661.4



TEST NUMBER: P331713-927

CATALOG NUMBER: S122RDIP-S865D530U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	104.3	117.7	136.9	167.6	217.7	288.8	373.0	458.9	536.5	598.3	640.8
115°	116.5	128.7	148.2	175.7	219.6	280.1	351.5	426.0	495.6	554.8	601.3
117.5°	127.9	140.6	158.6	184.4	222.8	275.8	337.9	401.2	462.3	516.0	559.7
120°	135.5	148.2	165.8	190.2	225.0	273.3	330.7	389.0	445.0	492.9	534.0
122.5°	143.1	156.1	172.7	195.3	227.5	271.9	324.6	379.2	430.6	475.9	513.0
125°	154.1	166.7	183.0	203.3	231.3	269.3	315.8	365.0	411.5	451.3	485.2
127.5°	163.7	176.7	192.6	210.8	235.2	267.8	307.7	351.0	393.2	430.6	461.9
130°	169.8	182.5	198.4	215.5	238.1	267.0	302.2	342.0	380.9	416.5	446.3
132.5°	175.6	188.3	203.4	220.2	241.0	266.6	297.9	333.4	369.3	402.1	430.1
135°	183.4	196.1	210.6	226.3	244.4	266.1	291.8	321.2	351.0	380.9	406.2
137.5°	190.3	202.0	216.3	231.0	247.5	266.0	287.6	311.6	336.5	360.1	382.2
140°	194.2	206.0	219.6	233.5	248.9	265.6	285.1	305.4	327.1	347.8	367.7
142.5°	197.9	208.9	222.1	235.8	250.0	265.6	282.6	300.3	318.8	336.7	353.3
145°	203.7	213.7	225.9	238.5	251.2	264.7	279.2	293.2	308.1	322.1	335.3
147.5°	208.7	217.5	228.9	240.1	251.5	263.1	275.8	287.7	299.4	310.4	320.0
150°	211.9	220.0	230.4	240.8	251.2	262.1	272.9	283.7	293.7	303.2	311.2
152.5°	215.2	222.5	231.9	241.1	250.5	260.2	270.4	279.7	289.0	297.0	304.0
155°	219.6	226.3	234.0	241.7	249.4	257.1	265.6	274.3	281.5	288.2	293.2
157.5°	223.4	229.0	235.5	241.7	247.3	253.8	261.2	267.8	273.9	279.6	283.4
160°	225.9	230.8	236.3	241.7	246.2	251.7	257.9	263.8	268.8	273.8	276.9
162.5°	228.1	232.0	236.6	241.3	245.1	249.9	255.1	259.8	264.1	268.4	270.8
165°	230.4	233.1	237.2	240.3	243.0	246.2	250.3	253.9	257.1	260.2	262.1
167.5°	232.4	234.1	237.1	239.7	241.0	243.0	245.6	248.2	250.6	252.8	254.4
170°	233.1	234.5	236.7	239.0	239.9	241.2	243.0	245.3	246.7	248.5	249.4
172.5°	233.9	234.8	236.4	237.9	238.4	239.1	240.5	242.1	243.0	244.5	245.0
175°	234.5	234.9	235.8	236.7	236.3	236.7	237.2	238.5	239.0	239.5	239.9
177.5°	234.9	234.9	235.3	236.0	235.3	234.9	235.3	236.0	236.0	236.4	236.4
180°	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9



TEST NUMBER: P331713-927

CATALOG NUMBER: S122RDIP-S865D530U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8
2.5°	1452.6	1453.4	1452.1	1453.0	1452.1	1453.4	1452.6	1457.2	1458.1	1458.9	1458.1
5°	1353.4	1347.2	1346.1	1344.6	1346.1	1347.2	1353.4	1356.1	1358.2	1362.4	1369.8
7.5°	1235.1	1234.1	1231.5	1227.9	1231.5	1234.1	1235.1	1244.1	1251.3	1259.5	1274.5
10°	1159.0	1156.3	1155.9	1152.1	1155.9	1156.3	1159.0	1170.5	1178.9	1190.5	1211.0
12.5°	1069.8	1052.9	1051.1	1042.0	1051.1	1052.9	1069.8	1084.7	1107.5	1118.6	1140.3
15°	910.9	907.8	897.2	890.4	897.2	907.8	910.9	923.5	931.9	962.4	997.6
17.5°	820.1	809.8	806.5	805.0	806.5	809.8	820.1	826.2	838.1	854.2	875.4
20°	761.6	752.2	750.6	749.6	750.6	752.2	761.6	769.0	778.5	795.8	817.8
22.5°	721.3	711.4	707.3	704.1	707.3	711.4	721.3	726.9	735.5	749.1	764.1
25°	652.3	648.6	646.5	645.5	646.5	648.6	652.3	657.5	666.0	684.4	700.1
27.5°	598.3	590.3	588.7	586.0	588.7	590.3	598.3	607.7	616.5	624.7	638.8
30°	567.7	565.1	561.3	558.2	561.3	565.1	567.7	572.4	578.2	592.4	606.0
32.5°	531.5	529.3	526.0	524.6	526.0	529.3	531.5	537.9	550.0	558.7	568.6
35°	491.5	484.1	480.9	476.2	480.9	484.1	491.5	496.7	501.5	508.8	526.6
37.5°	449.1	445.2	440.8	442.4	440.8	445.2	449.1	451.3	461.3	471.5	479.3
40°	416.3	413.7	412.6	412.1	412.6	413.7	416.3	423.1	435.2	440.0	451.5
42.5°	390.2	382.9	380.2	380.1	380.2	382.9	390.2	397.9	405.4	413.0	425.0
45°	350.6	343.7	339.1	339.5	339.1	343.7	350.6	353.2	359.5	374.8	381.6
47.5°	310.0	309.8	306.9	307.8	306.9	309.8	310.0	314.5	322.7	332.0	342.9
50°	290.7	287.5	285.4	285.9	285.4	287.5	290.7	294.4	299.0	303.8	320.6
52.5°	272.2	269.4	267.8	270.0	267.8	269.4	272.2	274.2	277.7	282.3	293.7
55°	241.8	238.6	238.1	237.6	238.1	238.6	241.8	244.4	248.6	252.3	257.5
57.5°	207.9	205.7	202.6	201.2	202.6	205.7	207.9	211.8	216.7	221.6	227.0
60°	183.5	179.3	174.0	173.5	174.0	179.3	183.5	190.3	192.3	199.7	206.0
62.5°	161.1	160.3	159.2	159.1	159.2	160.3	161.1	163.3	166.3	177.1	184.6
65°	141.4	140.9	141.4	141.9	141.4	140.9	141.4	142.4	143.0	144.0	147.2
67.5°	123.2	122.2	121.3	121.8	121.3	122.2	123.2	123.4	124.8	125.5	127.7
70°	109.3	108.8	108.3	108.3	108.3	108.8	109.3	110.4	111.5	112.5	115.1
72.5°	95.9	95.8	95.2	94.8	95.2	95.8	95.9	97.8	98.4	99.4	101.2
75°	76.8	75.7	75.7	75.7	75.7	75.7	76.8	77.2	77.8	79.4	80.4
77.5°	58.5	57.9	57.4	57.0	57.4	57.9	58.5	58.5	59.4	59.7	60.8
80°	46.3	45.7	45.2	45.2	45.2	45.7	46.3	46.8	46.8	48.3	47.8
82.5°	35.3	34.8	34.7	34.3	34.7	34.8	35.3	35.4	35.4	36.6	36.4
85°	18.9	19.4	18.9	20.0	18.9	19.4	18.9	18.4	18.9	20.0	20.0
87.5°	8.5	8.0	8.5	8.0	8.5	8.0	8.5	8.5	8.8	8.6	8.8
90°	14.9	14.9	14.9	14.9	14.9	14.9	14.9	14.9	14.4	13.5	14.4
92.5°	26.9	25.4	25.7	25.0	25.7	25.4	26.9	27.2	30.0	33.8	39.4
95°	56.0	52.4	51.0	51.5	51.0	52.4	56.0	61.9	71.9	90.8	118.4
97.5°	122.9	111.8	105.2	101.4	105.2	111.8	122.9	144.5	177.1	226.0	276.2
100°	202.4	183.0	169.8	161.8	169.8	183.0	202.4	239.9	294.5	356.5	412.5
102.5°	345.2	312.0	295.6	284.6	295.6	312.0	345.2	385.9	443.9	489.1	501.8
105°	562.9	534.9	515.5	509.1	515.5	534.9	562.9	590.9	605.9	599.9	548.9
107.5°	664.2	662.7	658.8	650.4	658.8	662.7	664.2	660.7	638.8	591.8	514.9
110°	680.8	689.4	693.5	693.0	693.5	689.4	680.8	661.4	624.3	566.5	485.7



TEST NUMBER: P331713-927

CATALOG NUMBER: S122RDIP-S865D530U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	667.8	682.1	689.8	692.3	689.8	682.1	667.8	640.8	598.3	536.5	458.9
115°	633.3	654.2	665.9	669.9	665.9	654.2	633.3	601.3	554.8	495.6	426.0
117.5°	592.4	614.3	626.7	630.1	626.7	614.3	592.4	559.7	516.0	462.3	401.2
120°	565.6	586.8	599.9	604.4	599.9	586.8	565.6	534.0	492.9	445.0	389.0
122.5°	541.4	562.3	573.9	577.7	573.9	562.3	541.4	513.0	475.9	430.6	379.2
125°	511.4	528.5	539.9	543.5	539.9	528.5	511.4	485.2	451.3	411.5	365.0
127.5°	484.7	500.8	510.6	513.5	510.6	500.8	484.7	461.9	430.6	393.2	351.0
130°	468.5	483.9	492.9	496.5	492.9	483.9	468.5	446.3	416.5	380.9	342.0
132.5°	451.9	467.2	475.5	478.8	475.5	467.2	451.9	430.1	402.1	369.3	333.4
135°	425.6	440.5	448.6	450.4	448.6	440.5	425.6	406.2	380.9	351.0	321.2
137.5°	399.9	412.7	419.9	422.6	419.9	412.7	399.9	382.2	360.1	336.5	311.6
140°	382.2	394.0	400.7	403.5	400.7	394.0	382.2	367.7	347.8	327.1	305.4
142.5°	367.0	377.7	383.7	384.3	383.7	377.7	367.0	353.3	336.7	318.8	300.3
145°	346.0	353.7	358.2	359.6	358.2	353.7	346.0	335.3	322.1	308.1	293.2
147.5°	328.9	335.0	338.1	338.9	338.1	335.0	328.9	320.0	310.4	299.4	287.7
150°	318.1	323.4	326.1	326.6	326.1	323.4	318.1	311.2	303.2	293.7	283.7
152.5°	309.3	314.1	316.1	316.2	316.1	314.1	309.3	304.0	297.0	289.0	279.7
155°	298.2	301.3	303.2	302.2	303.2	301.3	298.2	293.2	288.2	281.5	274.3
157.5°	286.9	289.6	290.4	290.4	290.4	289.6	286.9	283.4	279.6	273.9	267.8
160°	280.1	282.3	282.8	282.8	282.8	282.3	280.1	276.9	273.8	268.8	263.8
162.5°	273.9	275.5	275.9	275.6	275.9	275.5	273.9	270.8	268.4	264.1	259.8
165°	263.8	265.6	265.6	265.2	265.6	265.6	263.8	262.1	260.2	257.1	253.9
167.5°	255.2	256.3	256.2	255.6	256.2	256.3	255.2	254.4	252.8	250.6	248.2
170°	249.9	251.2	250.7	249.9	250.7	251.2	249.9	249.4	248.5	246.7	245.3
172.5°	245.5	246.1	245.7	245.1	245.7	246.1	245.5	245.0	244.5	243.0	242.1
175°	239.9	240.3	239.9	239.0	239.9	240.3	239.9	239.9	239.5	239.0	238.5
177.5°	236.4	236.4	236.0	235.3	236.0	236.4	236.4	236.4	236.4	236.0	236.0
180°	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9



TEST NUMBER: P331713-927

CATALOG NUMBER: S122RDIP-S865D530U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8
2.5°	1454.7	1460.6	1469.4	1474.5	1482.9	1488.4	1491.3	1496.7	1499.7	1510.2	1521.1
5°	1373.4	1381.9	1396.5	1410.2	1425.0	1440.2	1451.2	1463.9	1475.4	1495.4	1516.4
7.5°	1280.3	1292.0	1314.8	1336.6	1362.2	1383.8	1402.8	1424.3	1443.6	1472.2	1502.0
10°	1210.5	1231.0	1261.0	1281.4	1315.1	1336.6	1366.6	1390.3	1417.1	1454.9	1488.6
12.5°	1150.4	1175.0	1199.1	1227.6	1257.9	1293.8	1326.7	1357.0	1388.9	1428.0	1467.5
15°	1041.2	1077.0	1114.3	1143.2	1184.2	1222.1	1260.4	1301.4	1340.3	1387.1	1438.6
17.5°	900.8	942.2	1005.0	1054.5	1102.6	1140.6	1188.1	1237.7	1283.6	1340.0	1397.3
20°	837.3	867.8	910.4	977.2	1049.6	1090.1	1138.5	1193.2	1245.7	1307.2	1368.7
22.5°	786.4	813.6	847.7	899.8	980.7	1035.9	1086.3	1141.9	1202.8	1265.6	1333.8
25°	713.8	732.7	768.4	810.5	866.3	957.1	1012.3	1068.0	1134.3	1201.6	1279.4
27.5°	659.3	676.3	699.5	739.7	781.1	846.4	934.1	994.9	1060.9	1136.6	1217.3
30°	617.6	637.5	663.3	691.7	736.9	787.9	875.7	946.1	1011.3	1089.1	1175.3
32.5°	587.3	603.1	625.0	653.9	691.5	740.4	810.5	896.0	959.6	1041.6	1131.6
35°	537.7	556.1	574.0	601.3	631.8	676.4	729.5	821.0	884.1	965.0	1055.4
37.5°	496.8	508.0	527.8	549.5	581.6	615.0	661.0	743.0	811.3	890.7	983.3
40°	465.7	479.9	494.6	518.8	545.1	577.1	622.3	683.3	761.6	839.4	929.8
42.5°	435.5	453.4	469.0	485.1	514.0	546.1	582.8	634.5	714.5	788.1	876.0
45°	398.9	410.5	426.8	444.7	468.3	495.7	528.2	573.5	650.2	713.8	796.3
47.5°	356.5	373.4	384.0	401.5	424.0	450.0	480.3	519.4	581.5	641.1	717.7
50°	327.5	344.8	360.0	375.8	395.8	421.0	446.2	484.1	534.0	596.6	668.0
52.5°	302.6	317.9	332.7	348.5	368.0	391.2	415.1	448.4	491.2	548.7	618.1
55°	268.6	278.1	293.3	309.0	326.4	348.5	371.6	399.5	436.3	484.7	540.9
57.5°	233.7	244.6	256.7	272.6	290.2	307.0	327.9	353.1	382.1	425.9	474.0
60°	213.9	222.4	232.3	248.6	264.9	280.1	300.2	321.2	348.5	386.3	427.3
62.5°	192.0	200.0	209.2	223.4	239.2	253.3	270.7	292.9	316.1	350.6	386.5
65°	155.6	167.2	176.1	188.7	201.8	216.6	230.2	248.1	268.6	296.0	328.0
67.5°	129.0	134.9	143.1	154.6	168.1	180.7	193.6	207.6	225.4	246.5	272.0
70°	117.2	119.3	120.9	131.9	144.6	157.2	169.2	182.4	197.6	215.0	237.0
72.5°	103.3	105.4	107.4	112.2	122.2	134.9	147.3	157.2	171.6	185.9	203.8
75°	82.0	85.2	86.7	89.4	93.0	101.5	113.0	122.5	130.9	141.9	156.1
77.5°	62.4	64.2	65.9	68.7	71.0	74.9	81.4	89.9	97.8	104.2	113.9
80°	49.4	49.9	52.0	53.1	56.2	58.9	62.0	68.8	76.8	79.4	86.2
82.5°	37.2	37.7	39.5	40.5	41.9	44.1	48.2	49.9	56.2	59.6	63.9
85°	20.5	20.0	21.5	21.5	22.6	23.7	24.7	27.3	28.9	33.1	34.1
87.5°	9.3	9.3	9.7	9.2	8.6	9.0	9.1	9.3	10.0	10.9	12.3
90°	14.9	15.4	14.9	12.2	9.0	6.8	5.4	4.5	3.6	1.8	0.5
92.5°	49.6	58.7	57.9	45.1	30.7	20.5	16.2	13.2	11.2	7.9	5.5
95°	155.0	177.1	156.8	104.3	65.0	44.3	33.4	26.2	22.1	17.6	15.8
97.5°	317.1	302.3	227.7	140.6	85.9	59.7	47.5	39.1	33.0	28.2	25.7
100°	421.9	356.9	245.7	148.2	93.1	69.2	56.5	47.5	40.2	36.1	34.8
102.5°	461.0	358.7	238.9	148.5	99.6	77.4	64.8	55.4	48.2	44.1	43.1
105°	455.0	334.8	225.5	150.9	110.7	89.4	76.8	66.9	60.0	57.0	55.1
107.5°	415.3	309.1	218.7	157.1	122.1	101.5	88.7	78.9	72.6	69.6	68.1
110°	390.3	296.8	217.3	162.2	129.7	109.8	96.6	87.2	81.4	78.6	76.8



TEST NUMBER: P331713-927

CATALOG NUMBER: S122RDIP-S865D530U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	373.0	288.8	217.7	167.6	136.9	117.7	104.3	95.1	89.6	86.6	84.8
115°	351.5	280.1	219.6	175.7	148.2	128.7	116.5	107.5	102.1	99.4	97.1
117.5°	337.9	275.8	222.8	184.4	158.6	140.6	127.9	119.3	114.5	111.8	110.0
120°	330.7	273.3	225.0	190.2	165.8	148.2	135.5	126.5	122.4	119.7	117.9
122.5°	324.6	271.9	227.5	195.3	172.7	156.1	143.1	134.1	129.7	127.0	125.5
125°	315.8	269.3	231.3	203.3	183.0	166.7	154.1	145.0	139.6	136.9	135.5
127.5°	307.7	267.8	235.2	210.8	192.6	176.7	163.7	155.0	149.1	145.3	143.5
130°	302.2	267.0	238.1	215.5	198.4	182.5	169.8	160.8	154.5	150.0	148.2
132.5°	297.9	266.6	241.0	220.2	203.4	188.3	175.6	166.3	159.5	154.7	152.5
135°	291.8	266.1	244.4	226.3	210.6	196.1	183.4	173.0	166.3	160.8	159.0
137.5°	287.6	266.0	247.5	231.0	216.3	202.0	190.3	180.0	172.8	167.3	165.2
140°	285.1	265.6	248.9	233.5	219.6	206.0	194.2	184.3	177.1	171.7	169.8
142.5°	282.6	265.6	250.0	235.8	222.1	208.9	197.9	188.3	181.1	176.0	174.6
145°	279.2	264.7	251.2	238.5	225.9	213.7	203.7	194.7	187.9	183.4	181.6
147.5°	275.8	263.1	251.5	240.1	228.9	217.5	208.7	201.1	194.9	190.5	189.2
150°	272.9	262.1	251.2	240.8	230.4	220.0	211.9	205.1	199.2	195.6	194.2
152.5°	270.4	260.2	250.5	241.1	231.9	222.5	215.2	208.7	203.6	199.9	199.3
155°	265.6	257.1	249.4	241.7	234.0	226.3	219.6	214.6	209.6	206.9	206.4
157.5°	261.2	253.8	247.3	241.7	235.5	229.0	223.4	219.4	215.1	212.9	212.4
160°	257.9	251.7	246.2	241.7	236.3	230.8	225.9	222.3	218.6	216.8	216.4
162.5°	255.1	249.9	245.1	241.3	236.6	232.0	228.1	224.8	221.9	220.1	220.4
165°	250.3	246.2	243.0	240.3	237.2	233.1	230.4	228.1	225.5	224.5	225.0
167.5°	245.6	243.0	241.0	239.7	237.1	234.1	232.4	230.8	229.0	228.2	228.8
170°	243.0	241.2	239.9	239.0	236.7	234.5	233.1	232.2	230.8	230.4	231.3
172.5°	240.5	239.1	238.4	237.9	236.4	234.8	233.9	233.3	232.0	232.2	232.7
175°	237.2	236.7	236.3	236.7	235.8	234.9	234.5	234.5	233.5	234.0	234.5
177.5°	235.3	234.9	235.3	236.0	235.3	234.9	234.9	234.9	234.2	234.6	235.3
180°	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9



TEST NUMBER: P331713-927

CATALOG NUMBER: S122RDIP-S865D530U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8
2.5°	1521.5	1522.8	1531.2	1535.0	1542.6	1545.5	1548.9	1548.1	1548.1	1549.7	1561.5
5°	1524.8	1535.3	1551.1	1566.4	1581.0	1593.7	1602.1	1610.5	1613.7	1628.9	1642.6
7.5°	1519.3	1538.7	1564.8	1588.0	1615.9	1637.6	1655.7	1672.0	1683.1	1705.3	1728.1
10°	1512.2	1539.5	1569.0	1598.9	1637.3	1666.2	1695.7	1718.2	1725.6	1758.7	1777.7
12.5°	1497.9	1534.5	1571.9	1610.7	1648.2	1688.1	1720.5	1743.0	1768.9	1798.6	1833.6
15°	1476.5	1518.5	1567.4	1617.3	1671.0	1719.3	1754.0	1793.4	1821.8	1854.4	1884.8
17.5°	1445.7	1499.8	1561.9	1619.8	1681.8	1733.7	1781.5	1819.2	1839.2	1857.8	1862.3
20°	1421.3	1479.6	1552.7	1621.0	1683.1	1743.0	1790.3	1821.8	1827.1	1827.6	1799.8
22.5°	1394.8	1460.7	1537.2	1607.1	1681.3	1748.0	1784.8	1798.3	1777.4	1741.8	1687.9
25°	1346.1	1422.4	1511.2	1591.0	1672.0	1735.0	1747.7	1724.0	1651.0	1574.2	1477.0
27.5°	1293.3	1379.0	1474.3	1563.1	1649.3	1688.4	1661.2	1575.9	1444.3	1329.9	1191.3
30°	1254.7	1350.8	1444.4	1543.7	1623.7	1640.5	1577.9	1452.3	1298.8	1126.4	988.2
32.5°	1210.5	1311.3	1414.1	1516.9	1583.7	1567.3	1464.0	1309.3	1129.3	959.9	829.3
35°	1147.4	1251.5	1362.4	1465.5	1508.0	1437.0	1282.5	1081.2	897.2	739.0	649.1
37.5°	1074.6	1187.9	1303.2	1397.8	1394.8	1276.5	1066.0	858.3	703.6	610.1	546.1
40°	1022.9	1137.4	1262.0	1341.9	1307.7	1153.7	925.6	729.5	616.6	541.9	495.1
42.5°	973.3	1088.2	1212.0	1275.5	1216.1	1026.7	799.5	645.9	552.6	494.4	456.5
45°	888.8	1010.3	1124.8	1160.1	1053.8	845.2	646.5	535.1	473.1	429.9	403.7
47.5°	806.3	925.7	1030.3	1030.9	887.3	685.4	545.4	463.1	410.1	376.8	357.7
50°	755.8	869.3	957.1	943.5	780.5	609.7	487.7	416.8	372.6	346.9	326.9
52.5°	699.1	809.2	885.3	846.4	690.1	536.5	436.0	376.4	339.8	317.5	299.6
55°	616.6	714.3	767.9	709.1	562.9	446.2	368.4	321.7	294.4	275.4	260.2
57.5°	535.5	616.2	649.9	581.3	463.7	370.0	311.7	276.6	249.5	235.9	228.0
60°	484.7	553.5	577.1	501.5	403.1	323.8	275.9	243.4	223.4	214.4	206.6
62.5°	434.6	490.8	500.6	431.2	351.4	283.4	242.3	214.8	201.5	193.0	185.5
65°	360.6	401.1	396.3	340.6	278.1	225.0	195.0	178.2	168.2	156.1	143.0
67.5°	296.8	321.5	306.7	264.9	212.2	174.8	155.3	142.5	130.2	118.7	115.7
70°	256.5	270.7	254.9	216.6	174.0	146.6	130.9	115.7	108.3	105.7	100.9
72.5°	217.9	222.8	205.7	172.9	141.6	121.4	106.1	97.5	93.6	91.3	88.3
75°	163.5	159.8	145.0	119.3	98.3	84.6	79.9	76.8	74.1	72.0	70.4
77.5°	114.8	109.4	96.3	79.5	68.4	61.9	59.1	57.4	56.2	55.1	53.5
80°	86.2	82.5	69.4	56.8	52.0	48.9	47.3	45.2	45.2	44.1	42.5
82.5°	63.1	58.9	47.5	41.6	39.0	37.1	36.0	34.7	34.3	34.5	33.4
85°	33.1	26.8	23.7	22.6	21.0	20.0	20.5	19.4	19.4	19.4	18.9
87.5°	10.5	8.7	8.5	8.2	9.0	9.3	9.6	10.1	10.6	10.1	10.5
90°	1.8	3.6	4.5	5.4	6.8	9.0	12.2	14.9	15.4	14.9	14.4
92.5°	7.9	11.2	13.2	16.2	20.5	30.7	45.1	57.9	58.7	49.6	39.4
95°	17.6	22.1	26.2	33.4	44.3	65.0	104.3	156.8	177.1	155.0	118.4
97.5°	28.2	33.0	39.1	47.5	59.7	85.9	140.6	227.7	302.3	317.1	276.2
100°	36.1	40.2	47.5	56.5	69.2	93.1	148.2	245.7	356.9	421.9	412.5
102.5°	44.1	48.2	55.4	64.8	77.4	99.6	148.5	238.9	358.7	461.0	501.8
105°	57.0	60.0	66.9	76.8	89.4	110.7	150.9	225.5	334.8	455.0	548.9
107.5°	69.6	72.6	78.9	88.7	101.5	122.1	157.1	218.7	309.1	415.3	514.9
110°	78.6	81.4	87.2	96.6	109.8	129.7	162.2	217.3	296.8	390.3	485.7



TEST NUMBER: P331713-927

CATALOG NUMBER: S122RDIP-S865D530U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	86.6	89.6	95.1	104.3	117.7	136.9	167.6	217.7	288.8	373.0	458.9
115°	99.4	102.1	107.5	116.5	128.7	148.2	175.7	219.6	280.1	351.5	426.0
117.5°	111.8	114.5	119.3	127.9	140.6	158.6	184.4	222.8	275.8	337.9	401.2
120°	119.7	122.4	126.5	135.5	148.2	165.8	190.2	225.0	273.3	330.7	389.0
122.5°	127.0	129.7	134.1	143.1	156.1	172.7	195.3	227.5	271.9	324.6	379.2
125°	136.9	139.6	145.0	154.1	166.7	183.0	203.3	231.3	269.3	315.8	365.0
127.5°	145.3	149.1	155.0	163.7	176.7	192.6	210.8	235.2	267.8	307.7	351.0
130°	150.0	154.5	160.8	169.8	182.5	198.4	215.5	238.1	267.0	302.2	342.0
132.5°	154.7	159.5	166.3	175.6	188.3	203.4	220.2	241.0	266.6	297.9	333.4
135°	160.8	166.3	173.0	183.4	196.1	210.6	226.3	244.4	266.1	291.8	321.2
137.5°	167.3	172.8	180.0	190.3	202.0	216.3	231.0	247.5	266.0	287.6	311.6
140°	171.7	177.1	184.3	194.2	206.0	219.6	233.5	248.9	265.6	285.1	305.4
142.5°	176.0	181.1	188.3	197.9	208.9	222.1	235.8	250.0	265.6	282.6	300.3
145°	183.4	187.9	194.7	203.7	213.7	225.9	238.5	251.2	264.7	279.2	293.2
147.5°	190.5	194.9	201.1	208.7	217.5	228.9	240.1	251.5	263.1	275.8	287.7
150°	195.6	199.2	205.1	211.9	220.0	230.4	240.8	251.2	262.1	272.9	283.7
152.5°	199.9	203.6	208.7	215.2	222.5	231.9	241.1	250.5	260.2	270.4	279.7
155°	206.9	209.6	214.6	219.6	226.3	234.0	241.7	249.4	257.1	265.6	274.3
157.5°	212.9	215.1	219.4	223.4	229.0	235.5	241.7	247.3	253.8	261.2	267.8
160°	216.8	218.6	222.3	225.9	230.8	236.3	241.7	246.2	251.7	257.9	263.8
162.5°	220.1	221.9	224.8	228.1	232.0	236.6	241.3	245.1	249.9	255.1	259.8
165°	224.5	225.5	228.1	230.4	233.1	237.2	240.3	243.0	246.2	250.3	253.9
167.5°	228.2	229.0	230.8	232.4	234.1	237.1	239.7	241.0	243.0	245.6	248.2
170°	230.4	230.8	232.2	233.1	234.5	236.7	239.0	239.9	241.2	243.0	245.3
172.5°	232.2	232.0	233.3	233.9	234.8	236.4	237.9	238.4	239.1	240.5	242.1
175°	234.0	233.5	234.5	234.5	234.9	235.8	236.7	236.3	236.7	237.2	238.5
177.5°	234.6	234.2	234.9	234.9	234.9	235.3	236.0	235.3	234.9	235.3	236.0
180°	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9



TEST NUMBER: P331713-927

CATALOG NUMBER: S122RDIP-S865D530U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8
2.5°	1565.7	1571.2	1573.7	1573.7	1576.7	1575.4	1574.1
5°	1655.7	1665.7	1667.8	1677.3	1684.1	1682.0	1683.1
7.5°	1745.2	1761.3	1777.1	1784.4	1785.5	1789.7	1791.3
10°	1800.2	1813.4	1838.1	1834.4	1852.8	1863.3	1845.9
12.5°	1853.2	1871.0	1888.2	1892.8	1903.3	1906.6	1899.8
15°	1901.2	1910.7	1911.7	1909.1	1912.2	1909.6	1899.6
17.5°	1856.4	1841.0	1809.9	1795.2	1783.5	1766.3	1759.4
20°	1782.4	1737.2	1684.6	1663.6	1638.9	1590.5	1602.1
22.5°	1622.6	1571.1	1518.5	1457.1	1427.8	1382.0	1379.2
25°	1374.0	1285.2	1187.4	1119.0	1079.1	1033.4	1013.4
27.5°	1068.3	956.4	876.3	835.8	798.8	762.6	761.1
30°	867.3	783.2	721.1	686.4	663.8	648.6	651.8
32.5°	731.0	673.4	631.6	602.8	586.1	574.6	574.4
35°	597.6	558.2	531.4	519.3	507.2	498.8	499.3
37.5°	511.4	487.7	472.9	459.5	451.9	447.8	445.5
40°	467.3	447.8	436.3	428.4	422.1	416.3	415.3
42.5°	432.4	416.3	404.7	398.5	392.6	388.6	387.5
45°	383.7	370.6	360.0	353.2	350.6	346.9	346.9
47.5°	341.4	328.4	320.2	315.9	311.4	309.0	308.9
50°	312.8	302.8	295.4	292.8	289.1	287.5	287.0
52.5°	287.1	279.6	274.4	272.6	271.0	269.0	269.3
55°	252.3	248.1	246.0	244.4	241.8	238.6	240.7
57.5°	223.0	219.4	213.7	208.7	206.4	204.1	205.0
60°	202.4	195.0	187.7	181.9	180.3	175.5	175.5
62.5°	176.3	166.0	156.9	153.7	152.1	149.9	149.5
65°	135.6	131.4	129.3	127.2	126.1	126.1	125.1
67.5°	112.4	110.7	108.4	107.9	106.8	106.5	106.2
70°	99.3	97.2	96.2	95.7	94.6	95.1	93.6
72.5°	86.7	85.1	84.8	83.5	82.9	82.9	81.8
75°	68.4	68.4	67.8	67.3	66.2	65.7	66.2
77.5°	52.6	52.7	51.7	51.7	51.5	51.7	51.1
80°	42.1	42.5	42.1	41.5	41.0	41.5	41.0
82.5°	33.2	32.5	32.4	32.2	32.2	31.8	31.8
85°	18.9	19.4	18.9	18.4	18.4	18.4	18.9
87.5°	9.8	10.1	10.1	10.1	10.1	10.1	9.7
90°	13.5	14.4	14.9	14.9	14.9	14.9	14.9
92.5°	33.8	30.0	27.2	26.9	25.4	25.7	25.0
95°	90.8	71.9	61.9	56.0	52.4	51.0	51.5
97.5°	226.0	177.1	144.5	122.9	111.8	105.2	101.4
100°	356.5	294.5	239.9	202.4	183.0	169.8	161.8
102.5°	489.1	443.9	385.9	345.2	312.0	295.6	284.6
105°	599.9	605.9	590.9	562.9	534.9	515.5	509.1
107.5°	591.8	638.8	660.7	664.2	662.7	658.8	650.4
110°	566.5	624.3	661.4	680.8	689.4	693.5	693.0



TEST NUMBER: P331713-927

CATALOG NUMBER: S122RDIP-S865D530U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	536.5	598.3	640.8	667.8	682.1	689.8	692.3
115°	495.6	554.8	601.3	633.3	654.2	665.9	669.9
117.5°	462.3	516.0	559.7	592.4	614.3	626.7	630.1
120°	445.0	492.9	534.0	565.6	586.8	599.9	604.4
122.5°	430.6	475.9	513.0	541.4	562.3	573.9	577.7
125°	411.5	451.3	485.2	511.4	528.5	539.9	543.5
127.5°	393.2	430.6	461.9	484.7	500.8	510.6	513.5
130°	380.9	416.5	446.3	468.5	483.9	492.9	496.5
132.5°	369.3	402.1	430.1	451.9	467.2	475.5	478.8
135°	351.0	380.9	406.2	425.6	440.5	448.6	450.4
137.5°	336.5	360.1	382.2	399.9	412.7	419.9	422.6
140°	327.1	347.8	367.7	382.2	394.0	400.7	403.5
142.5°	318.8	336.7	353.3	367.0	377.7	383.7	384.3
145°	308.1	322.1	335.3	346.0	353.7	358.2	359.6
147.5°	299.4	310.4	320.0	328.9	335.0	338.1	338.9
150°	293.7	303.2	311.2	318.1	323.4	326.1	326.6
152.5°	289.0	297.0	304.0	309.3	314.1	316.1	316.2
155°	281.5	288.2	293.2	298.2	301.3	303.2	302.2
157.5°	273.9	279.6	283.4	286.9	289.6	290.4	290.4
160°	268.8	273.8	276.9	280.1	282.3	282.8	282.8
162.5°	264.1	268.4	270.8	273.9	275.5	275.9	275.6
165°	257.1	260.2	262.1	263.8	265.6	265.6	265.2
167.5°	250.6	252.8	254.4	255.2	256.3	256.2	255.6
170°	246.7	248.5	249.4	249.9	251.2	250.7	249.9
172.5°	243.0	244.5	245.0	245.5	246.1	245.7	245.1
175°	239.0	239.5	239.9	239.9	240.3	239.9	239.0
177.5°	236.0	236.4	236.4	236.4	236.4	236.0	235.3
180°	234.9	234.9	234.9	234.9	234.9	234.9	234.9

(END OF REPORT)