

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331727-927

Luminaire Tested: **S122RDIP-S865D925U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331727-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S865D925U927-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5012.3 lumens  
Efficiency: N/A  
Efficacy: 82.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 60.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331727-927

CATALOG NUMBER: S122RDIP-S865D925U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331727-927

CATALOG NUMBER: S122RDIP-S865D925U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48
1	98	94	90	87	90	86	83	80	73	70	68	60	58	57	48	47	46	41
2	89	82	76	71	82	76	71	67	64	60	57	53	51	48	43	41	40	35
3	82	73	66	60	75	67	61	56	57	52	49	47	44	41	39	36	34	30
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	35	32	30	26
5	69	58	50	44	63	54	47	42	46	40	36	38	34	31	32	29	26	23
6	64	52	44	38	59	48	41	36	41	36	32	35	31	28	29	26	24	21
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	17
9	51	39	32	27	47	37	30	26	32	26	23	27	23	20	23	20	17	15
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	18755	18755	18755
5°	18827	18519	18621
10°	18682	18216	18061
15°	18467	17677	17167
20°	18170	16905	16057
25°	17865	16030	14982
30°	17443	15129	13601
35°	17030	14152	12390
40°	16617	13139	10989
45°	16130	12001	9720
50°	15631	10854	8475
55°	15122	9619	7279
60°	14528	8315	6042
65°	13857	6988	5501
70°	13053	5755	5061
75°	12071	5246	4722
80°	10646	4695	4305
85°	8373	3705	3705



TEST NUMBER: P331727-927

CATALOG NUMBER: S122RDIP-S865D925U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	108.7	2.2
10°-20°	298.5	6.0
20°-30°	419.2	8.4
30°-40°	457.1	9.1
40°-50°	420.3	8.4
50°-60°	330.1	6.6
60°-70°	215.2	4.3
70°-80°	111.0	2.2
80°-90°	32.5	0.6
90°-100°	59.4	1.2
100°-110°	184.4	3.7
110°-120°	315.1	6.3
120°-130°	414.4	8.3
130°-140°	465.2	9.3
140°-150°	456.1	9.1
150°-160°	382.5	7.6
160°-170°	253.7	5.1
170°-180°	88.7	1.8
0°-30°	826.5	16.5
0°-40°	1283.6	25.6
0°-60°	2034.0	40.6
0°-90°	2392.8	47.7
90°-120°	558.9	11.2
90°-150°	1894.5	37.8
90°-180°	2620.0	52.3
0°-180°	5012.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1162	1162	1162	1162	1162	
5°	1162	1156	1143	1151	1149	110
15°	1105	1092	1058	1038	1027	311
25°	1003	967	900	858	841	461
35°	864	808	718	654	629	541
45°	706	634	526	454	426	545
55°	537	453	342	281	259	480
65°	363	277	183	149	144	359
75°	194	122	84	77	76	205
85°	45	24	20	20	20	53
90°	1	11	28	26	27	4
95°	41	49	51	50	49	47
105°	170	172	174	175	176	180
115°	316	321	319	318	316	313
125°	460	467	465	463	462	411
135°	595	604	606	605	602	460
145°	722	728	733	733	730	451
155°	826	828	831	834	832	380
165°	899	898	898	903	900	253
175°	935	933	931	936	932	89
180°	937	937	937	937	937	



TEST NUMBER: P331727-927

CATALOG NUMBER: S122RDIP-S865D925U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6
2.5°	1165.8	1164.8	1163.9	1162.9	1162.1	1160.5	1158.5	1156.4	1154.4	1152.3	1154.2
5°	1161.6	1160.4	1159.2	1158.0	1156.9	1154.8	1151.8	1148.7	1145.7	1142.6	1144.7
7.5°	1149.5	1148.1	1146.7	1145.3	1143.8	1141.3	1137.7	1134.2	1130.6	1127.0	1127.7
10°	1139.5	1137.8	1136.2	1134.6	1132.9	1129.8	1125.1	1120.5	1115.8	1111.1	1110.4
12.5°	1126.9	1124.8	1122.8	1120.9	1118.8	1114.8	1108.8	1102.9	1096.9	1090.9	1089.6
15°	1104.8	1102.2	1099.6	1097.1	1094.5	1089.3	1081.3	1073.4	1065.4	1057.5	1053.0
17.5°	1077.7	1073.7	1069.8	1065.9	1062.0	1054.9	1044.7	1034.5	1024.4	1014.2	1008.9
20°	1057.5	1052.8	1048.1	1043.5	1038.8	1030.6	1018.9	1007.3	995.6	983.9	978.0
22.5°	1035.6	1030.4	1025.2	1019.9	1014.7	1005.5	992.3	979.1	966.0	952.8	945.2
25°	1002.8	995.4	987.9	980.4	973.0	961.5	946.0	930.7	915.2	899.8	890.3
27.5°	963.3	955.1	947.1	938.9	930.8	918.1	900.6	883.3	865.9	848.5	837.3
30°	935.6	926.7	917.8	908.9	900.1	886.3	867.6	848.9	830.2	811.5	799.6
32.5°	908.6	898.3	887.9	877.5	867.1	852.5	833.4	814.3	795.3	776.2	762.6
35°	864.0	852.2	840.3	828.3	816.4	800.2	779.6	759.1	738.6	718.0	703.2
37.5°	819.5	806.4	793.4	780.2	767.1	749.6	727.8	705.8	684.0	662.0	645.8
40°	788.4	774.4	760.3	746.3	732.3	714.0	691.3	668.7	646.0	623.4	606.7
42.5°	756.5	741.6	726.9	712.2	697.4	678.3	654.9	631.4	608.1	584.6	567.5
45°	706.4	690.7	675.1	659.4	643.8	623.7	599.2	574.6	550.1	525.6	509.0
47.5°	657.6	641.0	624.5	607.8	591.3	570.3	545.0	519.7	494.3	469.1	452.6
50°	622.3	605.7	589.1	572.5	556.0	534.8	509.1	483.4	457.7	432.1	415.9
52.5°	587.8	570.5	553.2	535.8	518.5	497.3	472.1	446.9	421.8	396.7	381.1
55°	537.2	519.0	500.7	482.5	464.3	442.5	417.3	392.1	366.9	341.7	327.6
57.5°	485.2	466.5	447.8	429.1	410.5	389.0	364.7	340.5	316.2	292.0	279.2
60°	449.9	431.2	412.6	393.9	375.2	353.8	329.7	305.6	281.6	257.5	245.7
62.5°	415.4	396.7	378.0	359.3	340.6	319.9	296.9	274.0	251.0	228.1	216.7
65°	362.7	343.7	324.8	305.9	287.0	267.0	246.0	225.0	203.9	182.9	175.0
67.5°	311.8	293.0	274.3	255.4	236.6	217.8	198.9	180.0	161.1	142.1	138.5
70°	276.5	258.3	240.0	221.8	203.6	186.4	170.3	154.2	138.1	121.9	119.6
72.5°	242.8	225.4	207.9	190.4	172.9	157.7	144.8	131.8	118.9	106.0	104.0
75°	193.5	177.1	160.7	144.3	128.0	115.9	107.9	100.0	92.1	84.1	82.5
77.5°	144.9	130.5	116.1	101.8	87.5	78.4	74.5	70.7	66.9	63.1	62.1
80°	114.5	102.7	90.8	78.8	66.9	59.8	57.4	55.1	52.8	50.5	49.5
82.5°	86.8	77.6	68.2	58.9	49.7	44.2	42.6	41.0	39.5	37.9	37.3
85°	45.2	40.3	35.4	30.5	25.6	22.8	22.1	21.4	20.7	20.0	20.0
87.5°	13.6	12.5	11.5	10.4	9.3	9.2	10.0	10.7	11.5	12.3	12.0
90°	0.8	2.9	5.0	7.1	9.2	12.2	16.1	20.0	23.8	27.6	27.3
92.5°	14.1	15.6	17.2	18.7	20.3	21.5	22.4	23.3	24.2	25.1	25.2
95°	41.1	42.9	44.6	46.3	48.2	49.2	49.5	49.9	50.2	50.6	50.6
97.5°	75.1	76.7	78.2	79.8	81.3	82.4	83.1	83.7	84.4	85.1	85.1
100°	100.4	101.8	103.2	104.6	106.0	107.0	107.5	108.1	108.6	109.1	109.1
102.5°	127.0	128.1	129.2	130.3	131.4	132.4	133.0	133.7	134.4	135.1	135.1
105°	170.0	170.5	171.0	171.6	172.1	172.5	172.9	173.3	173.6	173.9	174.3
107.5°	213.3	214.0	214.8	215.6	216.4	216.7	216.7	216.7	216.7	216.7	216.9
110°	241.1	242.2	243.2	244.3	245.3	245.9	245.9	245.9	245.9	245.9	245.9



TEST NUMBER: P331727-927

CATALOG NUMBER: S122RDIP-S865D925U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	271.5	272.5	273.6	274.6	275.7	276.2	276.0	275.8	275.8	275.6	275.2
115°	316.2	317.3	318.3	319.4	320.4	320.8	320.4	320.1	319.7	319.4	319.2
117.5°	360.8	362.2	363.6	365.0	366.5	366.6	365.7	364.6	363.7	362.7	362.3
120°	390.5	392.0	393.3	394.7	396.2	396.2	394.7	393.3	392.0	390.5	390.5
122.5°	417.7	419.4	421.1	422.8	424.5	424.8	423.8	422.9	421.9	420.9	420.5
125°	460.1	461.7	463.3	464.9	466.4	467.0	466.4	465.9	465.4	464.9	464.3
127.5°	501.4	503.4	505.4	507.4	509.4	510.1	509.5	508.8	508.2	507.6	506.9
130°	527.3	529.6	531.9	534.2	536.5	537.4	537.0	536.7	536.4	536.0	535.7
132.5°	556.4	558.3	560.2	562.0	563.9	564.8	564.9	565.0	565.0	565.1	564.4
135°	595.3	597.2	599.1	601.1	603.0	604.2	604.5	604.8	605.2	605.5	605.4
137.5°	636.3	637.8	639.4	641.0	642.5	643.6	644.0	644.5	645.0	645.4	645.3
140°	660.9	662.5	664.1	665.7	667.3	668.4	669.3	670.2	671.1	672.0	672.0
142.5°	686.2	687.8	689.4	690.9	692.5	693.6	694.2	694.8	695.4	696.0	696.2
145°	722.5	723.8	725.0	726.3	727.5	728.6	729.7	730.7	731.8	732.8	733.0
147.5°	754.9	756.5	758.0	759.4	760.9	762.0	762.7	763.3	764.1	764.8	765.2
150°	777.1	778.2	779.2	780.3	781.3	782.2	782.9	783.6	784.3	785.1	785.5
152.5°	796.7	797.8	798.8	799.9	801.0	801.9	802.7	803.6	804.4	805.3	806.0
155°	826.2	826.6	827.2	827.8	828.2	828.8	829.3	829.8	830.4	830.8	831.8
157.5°	851.3	851.6	852.0	852.3	852.7	853.0	853.3	853.7	854.0	854.3	855.5
160°	866.5	866.8	867.1	867.5	867.8	868.2	868.3	868.5	868.6	868.8	869.9
162.5°	880.4	880.4	880.5	880.6	880.7	880.7	881.0	881.1	881.3	881.5	882.6
165°	898.9	898.7	898.5	898.3	898.2	898.1	898.1	898.1	898.1	898.1	899.3
167.5°	914.3	913.9	913.3	912.8	912.3	912.0	912.0	911.9	911.9	911.8	913.1
170°	922.6	922.0	921.5	921.0	920.4	920.1	920.0	919.8	919.6	919.4	920.7
172.5°	928.3	927.7	927.2	926.7	926.1	925.8	925.7	925.4	925.3	925.1	926.4
175°	935.3	934.7	934.1	933.7	933.1	932.7	932.3	932.0	931.6	931.3	932.5
177.5°	938.1	937.6	937.2	936.8	936.4	936.0	935.7	935.5	935.2	934.9	935.7
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8



TEST NUMBER: P331727-927

CATALOG NUMBER: S122RDIP-S865D925U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6
2.5°	1156.0	1157.9	1159.8	1160.5	1160.2	1159.8	1159.4	1159.0
5°	1146.8	1148.9	1151.0	1151.8	1151.0	1150.3	1149.6	1148.9
7.5°	1128.3	1128.9	1129.5	1129.2	1128.0	1126.8	1125.5	1124.3
10°	1109.7	1109.0	1108.3	1107.2	1105.8	1104.5	1103.0	1101.6
12.5°	1088.4	1087.1	1085.8	1084.1	1081.7	1079.4	1077.1	1074.8
15°	1048.6	1044.2	1039.7	1036.3	1034.0	1031.7	1029.4	1027.0
17.5°	1003.6	998.3	993.1	988.4	984.4	980.4	976.4	972.3
20°	972.2	966.4	960.5	955.1	949.9	944.8	939.6	934.5
22.5°	937.8	930.3	922.7	917.0	913.2	909.3	905.5	901.7
25°	880.7	871.1	861.5	854.9	851.4	848.0	844.5	841.0
27.5°	826.2	815.0	803.8	795.5	790.0	784.3	778.8	773.2
30°	787.7	775.8	763.8	754.7	748.5	742.1	735.9	729.5
32.5°	749.0	735.4	721.8	712.0	706.2	700.2	694.3	688.3
35°	688.5	673.8	659.1	649.2	644.0	638.9	633.7	628.6
37.5°	629.6	613.4	597.2	586.1	580.3	574.3	568.5	562.6
40°	590.2	573.6	557.0	545.7	539.6	533.5	527.4	521.4
42.5°	550.4	533.2	516.1	504.5	498.7	492.8	486.9	481.0
45°	492.4	475.9	459.2	448.1	442.5	437.0	431.3	425.7
47.5°	436.0	419.5	403.1	392.3	387.2	382.1	377.0	371.9
50°	399.8	383.7	367.6	357.0	352.1	347.2	342.3	337.4
52.5°	365.6	350.1	334.5	324.5	319.9	315.4	310.9	306.3
55°	313.6	299.6	285.6	276.3	271.9	267.4	263.0	258.6
57.5°	266.3	253.5	240.7	232.3	228.6	224.8	221.1	217.4
60°	233.7	221.8	209.8	202.1	198.3	194.6	190.8	187.1
62.5°	205.4	194.1	182.7	175.9	173.6	171.4	169.1	166.9
65°	167.0	159.1	151.1	146.8	146.1	145.4	144.7	144.0
67.5°	134.8	131.2	127.5	125.3	124.6	123.8	123.1	122.4
70°	117.2	114.9	112.6	111.0	110.0	109.1	108.1	107.2
72.5°	102.0	100.1	98.1	96.9	96.3	95.7	95.1	94.6
75°	80.8	79.2	77.6	76.6	76.4	76.1	75.9	75.7
77.5°	61.2	60.3	59.3	58.7	58.3	57.9	57.6	57.2
80°	48.6	47.7	46.7	46.3	46.3	46.3	46.3	46.3
82.5°	36.8	36.1	35.6	35.3	35.3	35.3	35.3	35.3
85°	20.0	20.0	20.0	20.0	20.0	20.0	20.0	20.0
87.5°	11.7	11.5	11.2	11.1	11.2	11.2	11.2	11.2
90°	26.9	26.6	26.3	26.1	26.4	26.5	26.7	26.9
92.5°	25.3	25.3	25.4	25.5	25.5	25.5	25.6	25.6
95°	50.6	50.6	50.6	50.4	50.1	49.7	49.4	49.0
97.5°	85.1	85.1	85.1	85.1	85.0	85.0	84.9	84.9
100°	109.1	109.1	109.1	109.0	108.8	108.7	108.4	108.3
102.5°	135.3	135.5	135.6	135.5	135.4	135.2	135.1	134.9
105°	174.6	175.0	175.3	175.5	175.5	175.5	175.5	175.5
107.5°	217.1	217.2	217.3	217.0	216.2	215.4	214.6	213.7
110°	245.9	245.9	245.9	245.6	245.1	244.5	244.0	243.5





TEST NUMBER: P331727-927

CATALOG NUMBER: S122RDIP-S865D925U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	274.7	274.3	273.9	273.5	273.1	272.7	272.4	272.0
115°	319.0	318.9	318.7	318.3	317.8	317.3	316.7	316.2
117.5°	361.9	361.5	361.0	360.5	360.0	359.5	358.9	358.5
120°	390.5	390.5	390.5	390.3	389.8	389.2	388.7	388.2
122.5°	420.0	419.6	419.2	418.8	418.4	418.0	417.6	417.2
125°	463.8	463.3	462.7	462.4	462.2	462.0	461.8	461.7
127.5°	506.3	505.6	505.0	504.4	503.8	503.3	502.7	502.2
130°	535.3	535.0	534.6	534.1	533.4	532.7	532.0	531.2
132.5°	563.6	562.8	562.0	561.3	560.8	560.2	559.7	559.1
135°	605.2	605.1	604.8	604.5	604.0	603.5	602.9	602.4
137.5°	645.2	645.0	644.8	644.4	643.7	643.0	642.3	641.6
140°	672.0	672.0	672.0	671.6	670.9	670.2	669.6	668.8
142.5°	696.3	696.4	696.6	696.3	695.6	694.9	694.2	693.5
145°	733.2	733.4	733.6	733.3	732.6	731.9	731.2	730.5
147.5°	765.6	766.0	766.4	766.2	765.6	764.9	764.2	763.5
150°	786.1	786.6	787.1	787.1	786.6	786.1	785.5	785.1
152.5°	806.6	807.2	807.9	807.9	807.2	806.6	806.0	805.3
155°	832.7	833.5	834.4	834.6	834.0	833.5	833.0	832.4
157.5°	856.7	857.9	859.0	859.2	858.4	857.5	856.7	855.9
160°	870.9	872.0	873.1	873.2	872.5	871.8	871.1	870.4
162.5°	883.8	885.0	886.2	886.5	885.6	884.7	883.9	883.0
165°	900.6	901.7	903.0	903.2	902.3	901.4	900.6	899.7
167.5°	914.3	915.5	916.7	916.9	916.0	915.0	914.2	913.2
170°	921.9	923.1	924.3	924.4	923.4	922.3	921.2	920.2
172.5°	927.6	928.8	930.0	930.1	929.1	928.0	926.9	925.9
175°	933.7	934.9	936.2	936.3	935.3	934.1	933.1	932.1
177.5°	936.6	937.5	938.3	938.3	937.5	936.6	935.7	934.9
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8

(END OF REPORT)