

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331436-830

Luminaire Tested: **S122DIP-S1005D530U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331436-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S1005D530U830-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5605.4 lumens
Efficiency: N/A
Efficacy: 101.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331436-830

CATALOG NUMBER: S122DIP-S1005D530U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331436-830

CATALOG NUMBER: S122DIP-S1005D530U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	83	83	83	73	73	73	68
1	102	97	93	90	96	92	89	85	82	79	77	73	71	69	64	63	62	57
2	93	85	79	73	87	81	75	70	72	68	64	64	61	58	57	54	52	48
3	85	75	67	61	80	71	64	59	64	58	54	57	52	49	50	47	44	41
4	78	66	58	52	73	63	56	50	57	51	46	51	46	42	45	41	38	35
5	71	59	51	45	67	56	49	43	51	44	40	45	40	36	41	36	33	30
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	33	29	27
7	61	48	40	34	57	46	38	33	42	35	31	37	32	28	34	29	26	24
8	57	44	36	30	53	42	35	29	38	32	27	34	29	25	31	27	23	21
9	53	40	32	27	50	38	31	26	35	29	25	32	27	23	29	24	21	19
10	49	37	30	25	47	35	28	24	32	26	22	29	24	21	27	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	24254	24254	24254
5°	24347	23995	24136
10°	24202	23753	23871
15°	23903	23445	23422
20°	23479	22983	22957
25°	23058	22413	22413
30°	22514	21893	21705
35°	22007	21268	20954
40°	21372	20643	20244
45°	20747	20021	19527
50°	20065	19376	18686
55°	19356	18624	17931
60°	18564	17725	17073
65°	17712	16829	16061
70°	16636	15753	15002
75°	15140	14504	14148
80°	13436	13036	12357
85°	10967	10448	9355



TEST NUMBER: P331436-830

CATALOG NUMBER: S122DIP-S1005D530U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.3	2.5
10°-20°	397.5	7.1
20°-30°	584.2	10.4
30°-40°	678.6	12.1
40°-50°	677.9	12.1
50°-60°	591.2	10.5
60°-70°	437.1	7.8
70°-80°	247.6	4.4
80°-90°	69.1	1.2
90°-100°	40.4	0.7
100°-110°	125.3	2.2
110°-120°	214.3	3.8
120°-130°	281.8	5.0
130°-140°	316.2	5.6
140°-150°	310.1	5.5
150°-160°	260.1	4.6
160°-170°	172.5	3.1
170°-180°	60.3	1.1
0°-30°	1123.0	20.0
0°-40°	1801.6	32.1
0°-60°	3070.7	54.8
0°-90°	3824.5	68.2
90°-120°	380.0	6.8
90°-150°	1288.0	23.0
90°-180°	1781.0	31.8
0°-180°	5605.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1502	1502	1502	1502	1502	
5°	1502	1496	1480	1491	1489	142
15°	1430	1421	1403	1408	1401	402
25°	1294	1282	1258	1261	1258	595
35°	1116	1102	1079	1070	1063	697
45°	909	898	877	862	855	701
55°	688	678	662	645	637	615
65°	464	455	440	428	420	458
75°	243	240	232	225	227	259
85°	59	58	56	52	50	68
90°	1	7	19	18	18	4
95°	28	33	34	34	33	32
105°	116	117	118	119	119	122
115°	215	218	217	217	215	213
125°	313	317	316	314	314	279
135°	405	410	412	411	410	312
145°	491	495	498	499	497	307
155°	562	563	565	567	566	258
165°	611	611	611	614	612	172
175°	636	634	633	637	634	60
180°	637	637	637	637	637	



TEST NUMBER: P331436-830

CATALOG NUMBER: S122DIP-S1005D530U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2
2.5°	1509.2	1507.9	1506.7	1505.3	1504.0	1502.0	1499.2	1496.4	1493.6	1490.7	1493.3
5°	1502.2	1501.0	1499.7	1498.4	1497.1	1494.7	1491.2	1487.6	1484.1	1480.5	1483.2
7.5°	1488.9	1487.0	1485.0	1483.0	1481.0	1478.2	1474.6	1471.0	1467.4	1463.9	1466.4
10°	1476.2	1474.0	1471.8	1469.5	1467.3	1464.2	1460.4	1456.5	1452.6	1448.8	1451.4
12.5°	1459.0	1456.9	1454.9	1452.9	1451.0	1448.0	1444.2	1440.3	1436.5	1432.7	1434.5
15°	1430.0	1428.1	1426.2	1424.3	1422.3	1419.3	1415.1	1410.9	1406.7	1402.6	1403.9
17.5°	1393.1	1391.1	1389.2	1387.2	1385.3	1382.2	1378.0	1373.8	1369.5	1365.4	1366.8
20°	1366.5	1364.5	1362.6	1360.7	1358.8	1355.6	1351.0	1346.6	1342.1	1337.6	1338.5
22.5°	1339.9	1337.2	1334.5	1331.8	1329.1	1325.7	1321.4	1317.2	1313.0	1308.7	1308.9
25°	1294.3	1291.7	1289.1	1286.6	1284.0	1280.0	1274.5	1269.0	1263.6	1258.1	1258.8
27.5°	1242.3	1239.9	1237.7	1235.3	1233.0	1229.7	1225.4	1221.1	1216.8	1212.5	1211.5
30°	1207.6	1205.0	1202.4	1199.9	1197.3	1193.6	1188.8	1184.0	1179.2	1174.3	1173.4
32.5°	1170.6	1168.6	1166.5	1164.4	1162.3	1158.9	1153.8	1148.7	1143.6	1138.5	1136.8
35°	1116.5	1113.3	1110.1	1106.9	1103.7	1099.6	1094.4	1089.3	1084.2	1079.0	1077.1
37.5°	1055.6	1052.8	1050.0	1047.2	1044.3	1040.4	1035.2	1030.1	1024.9	1019.8	1017.4
40°	1014.0	1011.4	1008.9	1006.4	1003.7	999.9	994.8	989.7	984.5	979.4	976.5
42.5°	973.6	971.0	968.5	965.9	963.3	959.4	954.3	949.1	944.1	938.9	935.8
45°	908.6	906.3	904.1	901.8	899.6	896.1	891.3	886.5	881.7	876.8	873.3
47.5°	843.9	841.8	839.6	837.5	835.4	831.8	826.8	821.8	816.8	811.8	808.0
50°	798.8	797.2	795.6	794.0	792.4	789.3	784.9	780.3	775.8	771.4	766.9
52.5°	754.9	752.8	750.6	748.6	746.4	743.2	739.0	734.7	730.6	726.3	722.6
55°	687.6	685.6	683.7	681.8	679.9	676.9	673.2	669.3	665.4	661.6	657.7
57.5°	620.0	618.4	616.9	615.4	613.8	611.0	606.7	602.5	598.2	594.0	590.2
60°	574.9	573.6	572.3	571.1	569.8	566.8	562.4	557.9	553.4	548.9	545.4
62.5°	531.0	529.0	526.9	524.8	522.7	520.0	516.5	513.1	509.6	506.1	502.8
65°	463.6	461.8	459.9	457.9	456.0	453.4	450.2	447.0	443.7	440.5	437.7
67.5°	395.2	393.7	392.1	390.6	389.1	386.8	383.9	381.1	378.1	375.3	373.1
70°	352.4	351.2	349.9	348.6	347.3	345.3	342.3	339.4	336.6	333.7	331.4
72.5°	308.5	307.3	305.9	304.7	303.4	301.8	300.0	298.1	296.2	294.4	292.1
75°	242.7	242.0	241.4	240.7	240.1	238.9	237.3	235.7	234.1	232.5	230.6
77.5°	183.7	182.7	181.5	180.5	179.4	178.5	177.9	177.2	176.5	176.0	174.9
80°	144.5	144.1	143.8	143.5	143.2	142.7	142.0	141.4	140.7	140.2	139.1
82.5°	107.4	107.4	107.4	107.3	107.2	107.0	106.6	106.2	105.8	105.5	104.2
85°	59.2	58.9	58.6	58.2	58.0	57.6	57.3	56.9	56.6	56.4	55.3
87.5°	20.9	20.6	20.5	20.3	20.0	19.9	19.9	19.9	19.9	20.0	19.1
90°	0.6	2.0	3.4	4.8	6.3	8.3	10.9	13.6	16.2	18.9	18.6
92.5°	9.6	10.7	11.7	12.7	13.8	14.6	15.3	15.8	16.5	17.1	17.2
95°	28.0	29.1	30.3	31.6	32.7	33.5	33.6	33.9	34.1	34.4	34.4
97.5°	51.1	52.1	53.2	54.2	55.2	56.0	56.5	56.9	57.4	57.9	57.9
100°	68.2	69.2	70.1	71.2	72.1	72.8	73.1	73.4	73.8	74.2	74.2
102.5°	86.3	87.1	87.8	88.6	89.4	90.0	90.5	90.9	91.3	91.8	91.9
105°	115.6	115.9	116.3	116.6	117.0	117.3	117.5	117.7	118.0	118.3	118.5
107.5°	145.1	145.5	146.1	146.6	147.1	147.4	147.4	147.4	147.4	147.4	147.5
110°	163.9	164.7	165.3	166.1	166.8	167.1	167.1	167.1	167.1	167.1	167.1



TEST NUMBER: P331436-830

CATALOG NUMBER: S122DIP-S1005D530U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	184.5	185.3	186.0	186.7	187.5	187.8	187.7	187.6	187.5	187.4	187.1
115°	215.0	215.7	216.4	217.2	217.8	218.1	217.8	217.6	217.4	217.2	217.1
117.5°	245.3	246.3	247.2	248.2	249.1	249.3	248.6	247.9	247.2	246.6	246.3
120°	265.5	266.5	267.4	268.3	269.4	269.4	268.3	267.4	266.5	265.5	265.5
122.5°	284.0	285.1	286.3	287.5	288.6	288.8	288.1	287.5	286.8	286.2	285.9
125°	312.8	313.9	315.0	316.0	317.1	317.4	317.1	316.8	316.4	316.0	315.7
127.5°	340.8	342.2	343.6	345.0	346.3	346.8	346.4	345.9	345.5	345.1	344.6
130°	358.5	360.1	361.6	363.2	364.7	365.3	365.1	364.9	364.7	364.4	364.2
132.5°	378.2	379.6	380.8	382.1	383.3	384.0	384.1	384.1	384.2	384.2	383.7
135°	404.7	406.0	407.4	408.7	410.0	410.8	410.9	411.2	411.5	411.7	411.6
137.5°	432.5	433.7	434.7	435.8	436.9	437.5	437.9	438.2	438.5	438.8	438.7
140°	449.3	450.4	451.5	452.5	453.6	454.5	455.1	455.6	456.3	456.9	456.9
142.5°	466.6	467.6	468.7	469.8	470.8	471.6	472.0	472.4	472.8	473.2	473.3
145°	491.3	492.1	492.9	493.8	494.6	495.4	496.1	496.8	497.6	498.2	498.3
147.5°	513.3	514.3	515.3	516.3	517.3	518.0	518.5	519.0	519.4	520.0	520.2
150°	528.4	529.0	529.8	530.5	531.2	531.8	532.3	532.7	533.2	533.8	534.0
152.5°	541.7	542.4	543.1	543.8	544.5	545.2	545.7	546.3	546.9	547.5	547.9
155°	561.7	562.0	562.4	562.7	563.1	563.5	563.8	564.2	564.5	564.9	565.5
157.5°	578.7	579.0	579.2	579.5	579.8	579.9	580.1	580.4	580.6	580.8	581.6
160°	589.1	589.3	589.6	589.7	590.0	590.2	590.3	590.4	590.6	590.7	591.4
162.5°	598.5	598.6	598.6	598.7	598.7	598.8	598.9	599.1	599.2	599.3	600.1
165°	611.1	611.0	610.9	610.8	610.7	610.6	610.6	610.6	610.6	610.6	611.4
167.5°	621.6	621.3	620.9	620.6	620.2	620.0	620.0	620.0	619.9	619.9	620.8
170°	627.3	626.9	626.5	626.1	625.8	625.6	625.5	625.3	625.2	625.1	625.9
172.5°	631.1	630.7	630.4	630.0	629.7	629.4	629.3	629.2	629.1	629.0	629.8
175°	635.8	635.5	635.1	634.8	634.4	634.1	633.9	633.7	633.4	633.1	634.0
177.5°	637.8	637.4	637.2	636.9	636.6	636.4	636.2	636.0	635.8	635.7	636.2
180°	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9



TEST NUMBER: P331436-830

CATALOG NUMBER: S122DIP-S1005D530U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2
2.5°	1495.8	1498.4	1501.0	1502.0	1501.5	1501.0	1500.4	1500.0
5°	1485.7	1488.3	1490.8	1491.9	1491.2	1490.5	1489.9	1489.2
7.5°	1469.0	1471.5	1474.1	1475.1	1474.3	1473.7	1472.9	1472.3
10°	1454.0	1456.5	1459.1	1459.9	1459.0	1457.9	1457.0	1456.0
12.5°	1436.2	1438.0	1439.8	1440.4	1439.6	1439.0	1438.2	1437.6
15°	1405.1	1406.5	1407.7	1407.6	1406.0	1404.4	1402.8	1401.2
17.5°	1368.3	1369.8	1371.2	1371.2	1369.6	1368.1	1366.6	1365.0
20°	1339.5	1340.5	1341.4	1341.2	1340.0	1338.7	1337.5	1336.1
22.5°	1309.1	1309.3	1309.5	1309.2	1308.4	1307.7	1306.8	1306.1
25°	1259.4	1260.1	1260.7	1260.7	1260.1	1259.4	1258.8	1258.1
27.5°	1210.6	1209.6	1208.6	1207.4	1205.9	1204.3	1202.8	1201.3
30°	1172.4	1171.5	1170.5	1169.4	1168.1	1166.8	1165.5	1164.2
32.5°	1135.1	1133.3	1131.6	1130.1	1128.8	1127.6	1126.2	1124.9
35°	1075.2	1073.3	1071.3	1069.6	1068.0	1066.4	1064.7	1063.1
37.5°	1015.0	1012.7	1010.3	1008.3	1006.8	1005.2	1003.7	1002.2
40°	973.6	970.7	967.8	965.7	964.4	963.2	961.9	960.5
42.5°	932.6	929.4	926.3	923.9	922.1	920.3	918.5	916.6
45°	869.8	866.2	862.7	860.3	858.9	857.7	856.4	855.2
47.5°	804.4	800.6	796.9	794.1	792.2	790.4	788.5	786.6
50°	762.3	757.9	753.4	750.4	748.8	747.2	745.6	743.9
52.5°	718.9	715.1	711.4	708.5	706.3	704.3	702.1	700.0
55°	653.8	650.0	646.2	643.5	641.9	640.3	638.7	637.0
57.5°	586.4	582.6	578.8	576.3	575.1	573.9	572.7	571.5
60°	541.9	538.3	534.8	532.5	531.6	530.7	529.6	528.7
62.5°	499.6	496.3	493.0	490.8	489.6	488.3	487.1	485.9
65°	434.8	431.9	429.0	426.8	425.2	423.6	422.0	420.4
67.5°	370.8	368.5	366.3	364.5	363.3	361.9	360.7	359.4
70°	329.1	327.0	324.7	322.9	321.6	320.4	319.1	317.8
72.5°	289.9	287.7	285.4	283.8	282.8	281.7	280.7	279.7
75°	228.8	226.8	224.9	224.2	224.9	225.5	226.1	226.8
77.5°	174.0	173.1	172.1	171.2	170.2	169.4	168.4	167.6
80°	138.2	137.2	136.3	135.4	134.8	134.2	133.6	132.9
82.5°	103.0	101.8	100.6	99.9	99.7	99.6	99.5	99.3
85°	54.4	53.4	52.5	51.8	51.6	51.2	50.9	50.5
87.5°	18.3	17.5	16.7	16.1	15.9	15.6	15.5	15.2
90°	18.4	18.1	17.8	17.8	17.9	18.0	18.2	18.3
92.5°	17.2	17.2	17.2	17.3	17.3	17.3	17.4	17.4
95°	34.4	34.4	34.4	34.3	34.0	33.8	33.6	33.4
97.5°	57.9	57.9	57.9	57.8	57.8	57.8	57.8	57.7
100°	74.2	74.2	74.2	74.1	74.0	73.9	73.8	73.6
102.5°	92.0	92.1	92.2	92.2	92.1	91.9	91.8	91.7
105°	118.8	118.9	119.2	119.3	119.3	119.3	119.3	119.3
107.5°	147.6	147.7	147.8	147.5	146.9	146.5	145.9	145.3
110°	167.1	167.1	167.1	167.0	166.6	166.3	165.9	165.5



TEST NUMBER: P331436-830

CATALOG NUMBER: S122DIP-S1005D530U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	186.8	186.5	186.2	186.0	185.7	185.4	185.1	184.9
115°	216.9	216.8	216.7	216.4	216.0	215.7	215.4	215.0
117.5°	246.0	245.7	245.4	245.2	244.8	244.4	244.0	243.6
120°	265.5	265.5	265.5	265.3	264.9	264.7	264.3	263.9
122.5°	285.6	285.3	285.0	284.7	284.5	284.2	284.0	283.7
125°	315.3	315.0	314.6	314.3	314.2	314.1	314.0	313.9
127.5°	344.2	343.7	343.4	342.9	342.5	342.1	341.8	341.4
130°	363.9	363.7	363.4	363.1	362.6	362.1	361.7	361.2
132.5°	383.1	382.6	382.1	381.6	381.3	380.9	380.5	380.1
135°	411.5	411.3	411.2	410.9	410.7	410.3	409.9	409.5
137.5°	438.6	438.5	438.4	438.1	437.6	437.2	436.7	436.2
140°	456.9	456.9	456.9	456.7	456.1	455.6	455.2	454.7
142.5°	473.3	473.4	473.5	473.3	472.9	472.4	471.9	471.5
145°	498.5	498.6	498.7	498.5	498.0	497.6	497.1	496.6
147.5°	520.5	520.8	521.0	520.9	520.5	520.0	519.5	519.1
150°	534.4	534.8	535.2	535.2	534.8	534.4	534.0	533.8
152.5°	548.4	548.8	549.3	549.3	548.8	548.4	547.9	547.5
155°	566.1	566.7	567.3	567.4	567.0	566.7	566.3	566.0
157.5°	582.4	583.2	584.1	584.2	583.6	583.1	582.5	581.8
160°	592.1	592.9	593.5	593.7	593.2	592.8	592.2	591.7
162.5°	600.9	601.7	602.6	602.7	602.1	601.5	601.0	600.4
165°	612.3	613.1	613.9	614.1	613.4	612.8	612.3	611.6
167.5°	621.6	622.5	623.3	623.4	622.7	622.2	621.5	620.9
170°	626.8	627.6	628.4	628.5	627.7	627.1	626.3	625.7
172.5°	630.7	631.5	632.3	632.4	631.7	630.9	630.2	629.5
175°	634.8	635.7	636.5	636.6	635.8	635.1	634.4	633.7
177.5°	636.8	637.3	637.9	637.9	637.3	636.8	636.2	635.7
180°	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9

(END OF REPORT)